

AN1000: WT32i RANGE TESTS

APPLICATION NOTE

Thursday, 27 March 2014

Version 1.1



VERSION HISTORY

Version	Comment
1.0	Release
1.1	DKWT32i vs iPhone and Samsung S4 phones added

Contents

VERSION HISTORY	3
TABLE OF CONTENTS.....	Error! Bookmark not defined.
1 Introduction	5
3.3 Analysis.....	9
3.4 Conclusions.....	10

1 Introduction

2.4 GHz RF signal is strongly impacted by any obstacles within the RF path. Thus defining a range for a Bluetooth device is more or less question of how to determine the range. For example a radio located in a headset has much shorter range than a radio that is “floating” in free space because human head has an impact on the RF field. A person usually doesn’t keep his head so that the antenna is pointing directly towards the transmitter so occasionally the head is within the RF path and will attenuate the received RF signal.

To determine the range for WT32i, it was tested in an airfield using an A2DP connection between two DKWT32i boards. The result does not guarantee practical range for real application. The result should be considered as maximum theoretical range. In a practical application the range can be much shorter because the orientation and height of the antenna can’t be controlled and also typically there are obstacles within the RF path which will attenuate the signal significantly.

In practical application the range is impacted by:

- Persons / obstacles moving close to the antenna. This is because of multipath propagation and will have an impact even if the person is not in line of sight between the two radios.
- Any obstacles within the RF path
- PCB layout around the antenna
- The shape of the PCB
- The mechanical design of the end product

Because the range is impacted by many factors which are difficult to control, the practical range must be tested with the end product and the application should not be design based on the maximum theoretical range because the practical range will always be shorter.




Figure 1: Range test setup for WT32i

3




Figure 5: Range right to right direction

3.2

DKWT:
placing




Figure 7: DKWT32i vs Samsung S4

3.3 Analysis




Figure 8: Radiation pattern of WT32i

By taking into account the antenna attenuation the RF link budget becomes:

- Front: $6 \text{ dBm (TXP)} + 89 \text{ dBm (RX sensitivity)} - 6 \text{ dB (antenna attenuation for both TX and RX)} = 89 \text{ dB}$
- Sides @ -5 dB antenna attenuation: $6 \text{ dBm} + 89 \text{ dBm} - 10 \text{ dB} = 85 \text{ dB}$
- Sides @ 10 dB antenna attenuation: $6 \text{ dBm} + 89 \text{ dBm} - 20 \text{ dB} = 75 \text{ dB}$

The theoretical RF path loss in an open field is shown in the Figure 9. Reading from the figure the maximum theoretical range for WT32i when the antennas are 1.1 meters above ground is:

- Front: 200m
- Side @ -5 dB antenna attenuation: 150m
- Side @ -10 dB antenna attenuation: 80m

Thus the tested range is well in line with the theoretical range estimated based on the measured antenna radiation pattern.





Figure 9: RF path loss in an open field with antennas 1.2 meters above ground

3.4 Conclusions

The range of DKWT32i vs DKWT32i was tested in a controlled environment in an open field with antennas located 1.1 meters above ground. The results were compared to theoretical range based on the measured TX power, RX sensitivity and the antenna radiation pattern.

The measured range was well in line with the theoretical range and thus the range of DKWT32i can be estimated accurately based on the given TX power, RX sensitivity and the antenna radiation pattern. Looking at the radiation pattern shown in the Figure 8 and the other radiation pattern shown in the datasheet of WT32i, one can see that the attenuation is less than 10 dB to almost any direction. Thus, in line of sight, 80 meter range can be considered to be reliable to any direction.



Simplicity Studio

One-click access to MCU and wireless tools, documentation, software, source code libraries & more. Available for Windows, Mac and Linux!



IoT Portfolio
www.silabs.com/iot



SW/HW
www.silabs.com/simplicity



Quality
www.silabs.com/quality



Support and Community
community.silabs.com

Disclaimer

Silicon Laboratories intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Laboratories products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Laboratories reserves the right to make changes without further notice and limitation to product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Silicon Laboratories shall have no liability for the consequences of use of the information supplied herein. This document does not imply or express copyright licenses granted hereunder to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any Life Support System without the specific written consent of Silicon Laboratories. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Laboratories products are not designed or authorized for military applications. Silicon Laboratories products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons.

Trademark Information

Silicon Laboratories Inc.®, Silicon Laboratories®, Silicon Labs®, SiLabs® and the Silicon Labs logo®, Bluegiga®, Bluegiga Logo®, Clockbuilder®, CMEMS®, DSPLL®, EFM®, EFM32®, EFR®, Ember®, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Ember®, EZLink®, EZRadio®, EZRadioPRO®, Gecko®, ISOModem®, Precision32®, ProSLIC®, Simplicity Studio®, SIPHY®, Telegesis, the Telegesis Logo®, USBXpress® and others are trademarks or registered trademarks of Silicon Laboratories Inc. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. All other products or brand names mentioned herein are trademarks of their respective holders.



SILICON LABS

Silicon Laboratories Inc.
400 West Cesar Chavez
Austin, TX 78701
USA

<http://www.silabs.com>