

**Electromagnetic compatibility
and Radio Spectrum Matters ERM
ERM TEST REPORT
300271-1-4**

Test Report

*Electromagnetic compatibility
and Radio spectrum Matters (ERM)*



Equipment Under Test: Bluetooth Low Energy module
Model: BGM113
Trade Mark: Silicon Labs
Manufacturer/Customer: Silicon Laboratories Finland Oy
Bertel Jungin aukio 3
FI-02600 Espoo
Finland

Tests have been performed according to the following standard(s)

Title of the standard	Reference standard	Version
Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz band; Harmonised Standard for access to radio spectrum	EN 300 328	V2.2.2

- *partial testing, see test suite for details*

Date: 18 December 2020

Issued by:

A handwritten signature in blue ink, appearing to read 'Henri Mäki'.

Henri Mäki
Testing Engineer

Date:

18 December 2020

Checked by:

A handwritten signature in blue ink, appearing to read 'Mikko Halonen'.

Mikko Halonen
Development Engineer

GENERAL REMARKS

Disclaimer

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Document.aspx>

Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

TABLE OF CONTENTS

GENERAL REMARKS	3
Disclaimer	3
TABLE OF CONTENTS	4
RELEASE HISTORY	5
PRODUCT DESCRIPTION	6
Equipment Under Test	6
General Description.....	6
Samples and Modifications	6
Specifications	6
Ports and Cables	6
SUMMARY OF TESTING	7
Test conditions	7
Measurement Uncertainty	8
Test suite	9
TEST RESULTS	10
Receiver Blocking.....	10
TEST EQUIPMENT	11

RELEASE HISTORY

Version	Changes	Issued
1.0	Initial release	1 October 2020
1.1	General description updated. Typos corrected	18 December 2020

PRODUCT DESCRIPTION

Equipment Under Test

Type:	Bluetooth Low Energy module
Model:	BGM113
Trade Mark:	Silicon Labs
Serial no:	-
Software version:	-
Hardware version:	-

General Description

The BGM113 is a Bluetooth low energy module compliant to the specifications 4.2 and above.

The measurement results according to the standard versions V1.9.1 and V2.1.1 are presented in SGS Test Reports 283004-1-1 and 288405-2-1, respectively.

Samples and Modifications

No.	Name	Description
1	Conducted	BGM113, temporary antenna connector was soldered to replace the original antenna.

Specifications

Type of Modulation:	<input type="checkbox"/> FHSS <input checked="" type="checkbox"/> Other
Operating Frequency Range:	2402 – 2480 MHz
Conducted Power:	0 dBm
Channels:	40
Channel Bandwidth:	1.05 MHz (measured)
Channel Separation:	2 MHz
Adaptivity:	<input type="checkbox"/> Adaptive <input checked="" type="checkbox"/> Non-adaptive
	<input type="checkbox"/> LBT based (if adaptive) <input type="checkbox"/> Load based (if adaptive)
Antenna Type:	Integrated chip antenna
Antenna Gain:	1 dBi
Antenna Count:	1
Geo-location Capability:	<input checked="" type="checkbox"/> No <input type="checkbox"/> Yes
Beam Forming Capability:	<input checked="" type="checkbox"/> No <input type="checkbox"/> Yes
EUT Dimensions:	smaller than 40 x 40 x 40 mm
Power Requirements:	2.0 – 3.8 V (tested with 3.3 V regulated by the development board)
Operating Temperature Range:	-

Ports and Cables

Cable / Port	Description
USB Port	Device configuration, powering the EUT

SUMMARY OF TESTING

Test conditions

The EUT's radio was configured and monitored with software provided by the manufacturer. Normal modulation and maximum transmit power was used during the tests.

All tests were performed with BGM113 module.

Table 1: Normal and extreme test conditions

Test conditions:		Temperature [°C]:	Voltage [V]:
Normal		+20 - 25	3.3
Extreme	Minimum	-	
	Maximum	-	

Table 2: The test frequencies used in testing

Channel	Frequency [MHz]
Low	2402
Mid	-
High	2480

Measurement Uncertainty

Parameter	Uncertainty	Limit
Occupied Channel Bandwidth	$\pm 0.0005 \%$	$\pm 5 \%$
RF output power, conducted	$\pm 0.349 \text{ dB}$	$\pm 1,5 \text{ dB}$
Power Spectral Density, conducted	$\pm 0.372 \text{ dB}$	$\pm 3 \text{ dB}$
Unwanted Emissions, conducted	$\pm 2.90 \text{ dB}$	$\pm 3 \text{ dB}$
All emissions, radiated	$\pm 5.29 \text{ dB}$	$\pm 6 \text{ dB}$
Temperature	$\pm 3 \text{ }^{\circ}\text{C}$	$\pm 3 \text{ }^{\circ}\text{C}$
Supply voltages	$\pm 3 \%$	$\pm 3 \%$
Time	$\pm 0.1 \%$	$\pm 5 \%$
Level of confidence 95.45 % ($k = 2$)		

Test suite

Measurement/Test	Test Specification	Result								
RF Output Power	EN 300 328 V2.2.2 (2019-07)	N/T								
Power Spectral Density	EN 300 328 V2.2.2 (2019-07)	N/T								
Duty cycle, Tx-sequence, Tx-gap	EN 300 328 V2.2.2 (2019-07)	N/A ⁽¹⁾								
Accumulated Transmit Time, Frequency Occupation and Hopping Sequence	EN 300 328 V2.2.2 (2019-07)	N/A ⁽²⁾								
Hopping Frequency Separation	EN 300 328 V2.2.2 (2019-07)	N/A ⁽²⁾								
Medium Utilization	EN 300 328 V2.2.2 (2019-07)	N/T								
Adaptivity	EN 300 328 V2.2.2 (2019-07)	N/A ⁽⁴⁾								
Occupied Channel Bandwidth	EN 300 328 V2.2.2 (2019-07)	N/T								
Transmitter unwanted spurious emissions in the out-of-band domain	EN 300 328 V2.2.2 (2019-07)	N/T								
Transmitter unwanted spurious emissions in the spurious domain	EN 300 328 V2.2.2 (2019-07)	N/T								
Receiver spurious emissions	EN 300 328 V2.2.2 (2019-07)	N/T								
Receiver blocking	EN 300 328 V2.2.2 (2019-07)	PASS								
Geo-location capability	EN 300 328 V2.2.2 (2019-07)	N/A ⁽⁵⁾								
<p>Possible test case verdicts:</p> <table><tr><td>Test case does not apply to the EUT:</td><td>N/A</td></tr><tr><td>EUT does meet the requirement:</td><td>PASS</td></tr><tr><td>EUT does not meet the requirement:</td><td>FAIL</td></tr><tr><td>Test was not performed:</td><td>N/T</td></tr></table> <p><i>The decision rule applied for the tests results stated in this test report is according to the requirements of section 5.2 of ETSI EN 300 328 V2.2.2.</i></p> <p>1) This requirement applies only to non-adaptive equipment or to adaptive equipment operating in a non-adaptive mode. This requirement does not apply for equipment with a maximum declared RF Output power of less than 10 dBm E.I.R.P.</p> <p>2) This requirement applies only to all types of FHSS equipment.</p> <p>3) This requirement does not apply to adaptive equipment unless operating in a non-adaptive mode. Also this requirement does not apply for equipment with a maximum declared RF Output power of less than 10 dBm E.I.R.P.</p> <p>4) This requirement applies only to adaptive equipment.</p> <p>5) Applicable only for equipment with geo-location capability.</p>			Test case does not apply to the EUT:	N/A	EUT does meet the requirement:	PASS	EUT does not meet the requirement:	FAIL	Test was not performed:	N/T
Test case does not apply to the EUT:	N/A									
EUT does meet the requirement:	PASS									
EUT does not meet the requirement:	FAIL									
Test was not performed:	N/T									

Testing location / address:

SGS Fimko Ltd
Karakaarenkuja 4
FI-02610, ESPOO
FINLAND

TEST RESULTS

Receiver Blocking

Standard: EN 300 328 V2.2.2
Tested by: HEM
Date: 15 September 2020
Temperature: 23 ± 3 °C
Humidity: 20 - 75 % RH

Test result: **PASS**

Test plan

Measurements are performed according to ETSI EN 300 328 V2.2.2 clause 5.4.11.2.1

Receiver blocking is a measure of the ability of the equipment to receive a wanted signal on its operating channel without exceeding a given degradation in the presence of an unwanted signal (blocking signal) on frequencies other than those of the operating band.

The tests were performed while the EUT was set to low and high channels.

Antenna gain of the EUT was added to the wanted signal and blocking signal level.

Wanted signal level was calculated according to table 15 in clause 4.3.2.11.4. Measured Occupied Channel Bandwidths are used in the calculations.

Receiver category: 2

Minimum performance criteria:

Packet error rate (PER) shall be less than or equal to 10%.

Test results

Table 3: Results of receiver blocking, receiver category 2

Wanted signal level (dBm)	Blocking signal frequency (MHz)	Blocking signal level (dBm)	Type of blocking signal	PER (%)	Result
-67.8	2380	-33.0	CW	0.0	PASS
	2504			0.0	PASS
	2300			0.0	PASS
	2584			0.0	PASS

TEST EQUIPMENT

EQUIPMENT	MANUFACTURER	TYPE	INV OR SERIAL	PREV CALIB	NEXT CALIB
ATTENUATOR	ZYSEN	ZSJ70/1-06-2A2	inv:10332	NCR	NCR
OSP BASE UNIT	ROHDE & SCHWARZ	OSP120	inv:10882	2019-02-28	2021-02-28
OSP-B157W 8 PORT	ROHDE & SCHWARZ	OSP-B157W8	inv:10883	2019-02-06	2021-02-06
OSP-B157WX	ROHDE & SCHWARZ	OSP-B157WX	inv:10884	2019-02-13	2021-02-13
RF SIGNAL GENERATOR	ROHDE & SCHWARZ	SMB100A	inv:9288	2020-06-08	2023-06-07
SPECTRUM ANALYZER	ROHDE & SCHWARZ	FSV40	inv:10881	2019-02-07	2021-02-07

NCR = No calibration required

END OF REPORT