

## **BGM240P32N & MGM240P32N**

### **ATEX**

Document Revision History Table

<b>Rev.</b>	<b>Date</b>	<b>Initiator</b>	<b>Description of Changes</b>
<b>1.0</b>	7-Sep-22	Tuomas Hänninen	Initial version

## Total amount of capacitors, inductors, and resistors in BGM240P32N & MGM240P32N

Type	Package	Value	Tol	Qty	Max. value inc. tol.
Inductor	0201	2.2 nH	±0.1 nH	1	2.3 nH
Inductor	0603	2.2 uH	±20 %	1	2.64 uH
Inductor	0201	1.4 nH	±0.1 nH	1	1.5 nH
<b>TOTAL INDUCTANCE</b>		<b>2.2 uH</b>			
Ferrite Bead	0201	0.4 ohm	N/A	2	0.4 ohm
Inductor	0603	0.470 ohm	N/A	1	0.470 ohm
<b>TOTAL RESISTANCE</b>		<b>1.27 ohm</b>			
Ceramic Capacitor	0201	2.6 pF	±0.1 pF	2	2.7 pF
Ceramic Capacitor	0201	10 nF	±10 %	1	11 nF
Ceramic Capacitor	0402	4.7 uF	±20 %	1	5.64 uF
Ceramic Capacitor	0402	10 uF	±20 %	1	12 uF
Ceramic Capacitor	0201	100 nF	±10 %	3	110 nF
Ceramic Capacitor	0201	18 pF	±5 %	3	18.9 pF
Ceramic Capacitor	0201	1 uF	±20 %	2	1.2 uF
Ceramic Capacitor	0402	2.2 uF	±20 %	2	2.64 uF
<b>TOTAL CAPACITANCE</b>		<b>21.41 uF</b>			

- The maximum RF TX power is +20 dBm (2.2 Vrms)
- The maximum current is less than 200 mA.
- The module does not contain any voltage enhancing parts such as boost converters.
- The module contains a 1.8 V DC-DC buck regulator.
- The maximum output voltage of any external pin cannot exceed the maximum supply voltage, neither under normal condition, nor under fault condition.