

RF Exposure Report

(Portable mode)

Report No.: SCCDBM-WTW-P22060902

IC: 5123A-GM240S

Test Model: MGM240S22A

Series Model: BGM240S22A

Evaluation Date: Aug. 23, 2022

Issued Date: Oct. 12, 2022

Applicant: Silicon Laboratories Finland Oy

Address: Alberga Business Park - Bldg D/Floor 5, Bertel Jungin aukio 3, 02600
ESPOO, FINLAND

Issued By: Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch
Lin Kou Laboratories

Lab Address: No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

Test Location: No. 19, Hwa Ya 2nd Rd., Wen Hwa Vil., Kwei Shan Dist., Taoyuan City
33383, TAIWAN

ISED# / CAB Identifier: 7450F / TW2021



This report is governed by, and incorporates by reference, the Conditions of Testing as posted at the date of issuance of this report at <http://www.bureauveritas.com/home/about-us/our-business/cps/about-us/terms-conditions/> and is intended for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. Measurement uncertainty is only provided upon request for accredited tests. Statements of conformity are based on simple acceptance criteria without taking measurement uncertainty into account, unless otherwise requested in writing. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence or if you require measurement uncertainty; provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents.

Table of Contents

Release Control Record	3
1 Certificate of Conformity	4
2 Limits for Maximum Permissible Exposure	5
3 SAR Test Exclusion Thresholds	6

Release Control Record

Issue No.	Description	Date Issued
SCCDBM-WTW-P22060902	Original Release	Oct. 12, 2022

1 Certificate of Conformity

Product: Bluetooth Low Energy and 802.15.4 wireless radio module

Brand: SILICON LABS

Test Model: MGM240S22A

Series Model: BGM240S22A

Sample Status: Engineering samples fully representing production modules

Applicant: Silicon Laboratories Finland Oy

Evaluation Date: Aug. 23, 2022

Standards: RSS-102 Issue 5 (March 19, 2015), Amendment 1 (February 2, 2021)

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards. The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's RF characteristics under the conditions specified in this report.

Prepared by : Lena Wang, **Date:** Oct. 12, 2022
Lena Wang / Specialist

Approved by : Jeremy Lin, **Date:** Oct. 12, 2022
Jeremy Lin / Project Engineer

2 Limits for Maximum Permissible Exposure

Per draft RSS-102 issue 5, section 2.5.1 and 2.5.2 as reproduced below:

2.5.1 Exemption from Routine Evaluation Limits – SAR Evaluation

SAR evaluation is required if the separation distance between the user and/or bystander and the antenna and/or radiating element of the device is less than or equal to 20 cm, except when the device operates at or below the applicable output power level (adjusted for tune-up tolerance) for the specified separation distance defined in below table:

Frequency (MHz)	Exemption Limits (mW)				
	At separation distance of ≤ 5 mm	At separation distance of 10 mm	At separation distance of 15 mm	At separation distance of 20 mm	At separation distance of 25 mm
300	71 mW	101 mW	132 mW	162 mW	193 mW
450	52 mW	70 mW	88 mW	106 mW	123 mW
835	17 mW	30 mW	42 mW	55 mW	67 mW
1900	7 mW	10 mW	18 mW	34 mW	60 mW
2450	4 mW	7 mW	15 mW	30 mW	52 mW
3500	2 mW	6 mW	16 mW	32 mW	55 mW
5800	1 mW	6 mW	15 mW	27 mW	41 mW

Frequency (MHz)	Exemption Limits (mW)				
	At separation distance of 30 mm	At separation distance of 35 mm	At separation distance of 40 mm	At separation distance of 45 mm	At separation distance of ≥ 50 mm
300	223 mW	254 mW	284 mW	315 mW	345 mW
450	141 mW	159 mW	177 mW	195 mW	213 mW
835	80 mW	92 mW	105 mW	117 mW	130 mW
1900	99 mW	153 mW	225 mW	316 mW	431 mW
2450	83 mW	123 mW	173 mW	235 mW	309 mW
3500	86 mW	124 mW	170 mW	225 mW	290 mW
5800	56 mW	71 mW	85 mW	97 mW	106 mW

Output power level shall be the higher of the maximum conducted or equivalent isotropically radiated power (e.i.r.p.) source-based, time-averaged output power. For controlled use devices where the 8 W/kg for 1 g of tissue applies, the exemption limits for routine evaluation in Table 1 are multiplied by a factor of 5. For limb-worn devices where the 10 gram applies, the exemption limits for routine evaluation in Table 1 are multiplied by a factor of 2.5. If the operating frequency of the device is between two frequencies located in Table 1, linear interpolation shall be applied for the applicable separation distance. For test separation distance less than 5 mm, the exemption limits for a separation distance of 5 mm can be applied to determine if a routine evaluation is required. For medical implant devices, the exemption limit for routine evaluation is set at 1 mW. The output power of a medical implant device is defined as the higher of the conducted or e.i.r.p to determine if the device is exempt from the SAR evaluation.

3 SAR Test Exclusion Thresholds

RF Source	Operating Frequency (GHz)	Antenna Gain (dBi)	Tune-up Power (dBm)	Higher of tune-up power or EIRP (dBm)	Higher of tune-up power or EIRP (mW)	Minimum distance of SAR exemption applied. (mm)
Bluetooth	2.4	2.80	10.5	13.3	21.38	18
	2.4	1.48	10.5	11.98	15.78	16
SRD (802.15.4)	2.4	2.8	10.5	13.3	21.38	18
	2.4	1.48	10.5	11.98	15.78	16

Note:

1. The table above demonstrated the minimum separation distance that SAR exemption applied for each configuration.
2. The evaluations were specified by clients in this report.
3. The manufacturer reserves the right to further limit the max RF TX power in the firmware of production modules.

---END---