



# AN1498: EFR32xG27/29 WLCSP – Support for +6 dBm 125 °C Operation

---

This application note presents pre-compliance radiated TX tests of the EFR32xG27/29 WLCSP Wireless MCU that allow extending the output power range from +4 dBm to +6 dBm without facing any issues regarding the radiated harmonic limits of FCC 15.247. This document can also be used as a reference for using the SoC up to 125 °C temperature.

## KEY FEATURES

- Pre-compliance radiated harmonic tests
- 125 °C support

**Note:** The RF validation of the WLCSP package was performed up to +4 dBm output power of the high power PA. However, +6 dBm capability has been thoroughly tested and deemed applicable up to 125 °C and will be referred to as the highest power level in this application note.

# Table of Contents

- 1. Elevating the Output Power and Temperature Range Restrictions . . . . . 3
- 2. FCC Pre-Compliance Radiated Harmonic Tests . . . . . 4
- 3. 125 °C Support. . . . . 5
- 4. Revision History . . . . . 6

## 1. Elevating the Output Power and Temperature Range Restrictions

The original restrictions of +4 dBm and 85 °C for the CSP package were determined considering the technological differences compared to the QFN package (e.g., detuning of the RF matching network at higher power) and to avoid the increased temperature dependent TX current draw that could potentially exceed the capabilities of the DC-DC boost converter.

As a result of recent investigations, Silicon Labs has elevated these limitations and allows the use of the xG27/29 WLCSP package at +6 dBm up to 125 °C temperature.

The recommended hardware reference designs to follow continue to be:

- BRD4110B and BRD4111B for xG27
- BRD4414 and BRD4420A for xG29

## 2. FCC Pre-Compliance Radiated Harmonic Tests

While Silicon Labs recommends using an RF shield to avoid harmonics of the fundamental power to exceed the -41 dBm FCC limit (or E field strength of 54 dBuV/m at 3m from DUT), the xG27/29 WLCSP package has been tested up to the 5<sup>th</sup> harmonic and found to be compliant to the limits with great margins, even without an RF shield. The table below summarizes the measurements.

**Table 2.1. Radiated TX Harmonic Emissions with a CW TX Signal at the Center and Edge Channels (BRD4111B)**

Radiated Emissions		Measured Maximums in EIRP [dBm]	FCC_15.247 Limit in EIRP [dBm]	Margin [dB]
2402 MHz	Fund.	8.9	30	21.1
	H2	-56.9	-41.2	15.7
	H3	-56.1	-11.1	45
	H4	-60.2	-11.1	49.1
	H5	-53.1	-41.2	11.8
2450 MHz	Fund.	9.1	30	20.9
	H2	-58	-41.2	16.8
	H3	-55.8	-11.1	14.6
	H4	-59.4	-11.1	48.5
	H5	-53.9	-41.2	12.7
2480 MHz	Fund.	8.5	30	21.5
	H2	-56.9	-41.2	15.6
	H3	-55.3	-11.1	14.1
	H4	-59.2	-11.1	47.7
	H5	-55.2	-41.2	13.9

A raw power setting of 74 was used which was determined on a Spectrum Analyzer in a conducted measurement setting to output +6 dBm power. The onboard Inverted-F (IFA) of BRD4111B was used, which has a peak gain of 3.1 dBi, which explains the 9.1 dBm output power reading in the maximum direction.

The device was measured in all three XYZ planes. The values in the table represent the orientations where the harmonic level were found to be the worst. The measurements confirm FCC compliant +6 dBm operation.

See [AN930.2](#) for conducted TX harmonic emissions and TX current consumption measurements.

### Note:

1. Silicon Labs SoCs – as opposed to Modules – are not officially certified for any RF standard (FCC 15.247, ETSI, etc.). The presented results only showcase that the device is capable of excellent RF performance if the RF design guidelines of [AN930.2](#) and [AN928.2](#) are followed. Consequently, the customer must do the full RF certification on their end-product with an accredited test house.

### 3. 125 °C Support

The verification tests were performed on multiple corner parts<sup>1</sup> of multiple die revisions. The devices were tested in a temperature chamber for 30 minutes at 6 dBm output power in CW transmit mode, and no anomalies were observed.

**Note:**

1. Specifically selected parts that perform below average across multiple RF metrics.

## 4. Revision History

### Revision 0.2

July, 2025

- Added EFR32xG29 support

### Revision 0.1

October, 2024

Initial version.

# Simplicity Studio

One-click access to MCU and wireless tools, documentation, software, source code libraries & more. Available for Windows, Mac and Linux!



**IoT Portfolio**  
[www.silabs.com/iot](http://www.silabs.com/iot)



**SW/HW**  
[www.silabs.com/simplicity](http://www.silabs.com/simplicity)



**Quality**  
[www.silabs.com/quality](http://www.silabs.com/quality)



**Support & Community**  
[www.silabs.com/community](http://www.silabs.com/community)

## Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs may update product firmware during the manufacturing process for security or reliability reasons. Such changes will not alter the specifications or the performance of the product. Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for military applications. Silicon Labs products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons. Silicon Labs disclaims all express and implied warranties and shall not be responsible or liable for any injuries or damages related to use of a Silicon Labs product in such unauthorized applications.

## Trademark Information

Silicon Laboratories Inc.<sup>®</sup>, Silicon Laboratories<sup>®</sup>, Silicon Labs<sup>®</sup>, SiLabs<sup>®</sup> and the Silicon Labs logo<sup>®</sup>, Bluegiga<sup>®</sup>, Bluegiga Logo<sup>®</sup>, EFM<sup>®</sup>, EFM32<sup>®</sup>, EFR, Ember<sup>®</sup>, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Redpine Signals<sup>®</sup>, WiSeConnect, n-Link, EZLink<sup>®</sup>, EZRadio<sup>®</sup>, EZRadioPRO<sup>®</sup>, Gecko<sup>®</sup>, Gecko OS, Gecko OS Studio, Precision32<sup>®</sup>, Simplicity Studio<sup>®</sup>, Telegesis, the Telegesis Logo<sup>®</sup>, USBXpress<sup>®</sup>, Zentri, the Zentri logo and Zentri DMS, Z-Wave<sup>®</sup>, and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



**Silicon Laboratories Inc.**  
400 West Cesar Chavez  
Austin, TX 78701  
USA

[www.silabs.com](http://www.silabs.com)