

## EN 300 328 RF Test Report

### (Bluetooth Low Energy)

**Report No.:** RECDBM-WTW-P22060902

**Test Model:** MGM240S22A

**Series Model:** BGM240S22A (refer to item 3.1 for more details)

**Received Date:** Jul. 06, 2022

**Test Date:** Jul. 13, 2022 ~ Aug. 01, 2022

**Issued Date:** Oct. 04, 2022

**Applicant:** Silicon Laboratories Finland Oy

**Address:** Alberga Business Park - Bldg D/Floor 5, Bertel Jungin aukio 3, 02600  
ESPOO, FINLAND

**Issued By:** Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch  
Lin Kou Laboratories

**Lab Address:** No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

**Test Location:** No.19, Hwa Ya 2nd Rd., Wen Hwa Vil., Kwei Shan Dist., Taoyuan City  
33383, Taiwan



This report is governed by, and incorporates by reference, the Conditions of Testing as posted at the date of issuance of this report at <http://www.bureauveritas.com/home/about-us/our-business/cps/about-us/terms-conditions/> and is intended for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. Measurement uncertainty is only provided upon request for accredited tests. Statements of conformity are based on simple acceptance criteria without taking measurement uncertainty into account, unless otherwise requested in writing. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence or if you require measurement uncertainty; provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents.

## Table of Contents

<b>Release Control Record .....</b>	<b>4</b>
<b>1 Certificate of Conformity .....</b>	<b>5</b>
<b>2 Summary of Test Results .....</b>	<b>6</b>
2.1 Test Instruments .....	7
2.2 Measurement Uncertainty .....	9
2.3 Modification Record .....	9
<b>3 General Information .....</b>	<b>10</b>
3.1 General Description of EUT .....	10
3.2 Description of Test Modes .....	13
3.2.1 Test Mode Applicability and Tested Channel Detail .....	14
3.3 Description of Support Units .....	17
3.3.1 Configuration of System under Test .....	17
3.4 General Description of Applied Standards .....	17
<b>4 Test Procedure and Results .....</b>	<b>18</b>
4.1 RF Output Power .....	18
4.1.1 Limits of RF Output Power .....	18
4.1.2 Test Procedures .....	18
4.1.3 Deviation from Test Standard .....	18
4.1.4 Test Setup .....	18
4.1.5 Test Results .....	19
4.2 Adaptivity (Adaptive Frequency Hopping) .....	21
4.2.1 Limit of Adaptive .....	21
4.2.2 Test Procedure .....	22
4.2.3 Deviation from Test Standard .....	22
4.2.4 Test Setup Configuration .....	23
4.2.5 List of Measurements .....	24
4.2.6 Interference Threshold Level .....	25
4.2.7 Test Result .....	26
4.2.7.1 Adaptive Result .....	26
4.2.7.2 The Channel Occupancy Time Result .....	29
4.2.7.3 Unwanted Signal Interference .....	30
4.2.7.4 Short Control Signalling Transmissions Result .....	31
4.3 Power Spectral Density .....	33
4.3.1 Limit of Power Spectral Density .....	33
4.3.2 Test Procedures .....	33
4.3.3 Deviation of Test Standard .....	33
4.3.4 Test Setup .....	33
4.3.5 Test Results .....	34
4.4 Occupied Channel Bandwidth .....	36
4.4.1 Limit of Occupied Channel Bandwidth .....	36
4.4.2 Test Procedure .....	36
4.4.3 Deviation from Test Standard .....	36
4.4.4 Test Setup .....	36
4.4.5 Test Results .....	37
4.5 Transmitter Unwanted Emissions in the Out-of-band Domain .....	39
4.5.1 Limits of Transmitter Unwanted Emissions in the Out-of-band Domain .....	39
4.5.2 Test Procedure .....	39
4.5.3 Deviation from Test Standard .....	39
4.5.4 Test Setup .....	39
4.5.5 Test Results .....	40
4.6 Transmitter Spurious Emissions in the spurious domain .....	42
4.6.1 Limits of Transmitter Spurious Emissions .....	42
4.6.2 Test Procedure .....	42

4.6.3	Deviation from Test Standard .....	42
4.6.4	Test Setup.....	42
4.6.5	Test Results .....	43
4.7	Receiver Spurious Emissions .....	47
4.7.1	Limit of Receiver Spurious Emissions .....	47
4.7.2	Test Procedure .....	47
4.7.3	Deviation from Test Standard .....	47
4.7.4	Test Setup.....	47
4.7.5	Test Results .....	48
4.8	Receiver Blocking.....	52
4.8.1	Limit of Receiver Blocking .....	52
4.8.2	Test Procedure .....	53
4.8.3	Deviation from Test Standard .....	53
4.8.4	Test Setup Configuration .....	54
4.8.5	Test Results .....	55
<b>5</b>	<b>Photographs of the Test Configuration .....</b>	<b>56</b>
	<b>Appendix – Information of the Testing Laboratories .....</b>	<b>58</b>

### Release Control Record

Issue No.	Description	Date Issued
RECDBM-WTW-P22060902	Original Release	Oct. 04, 2022

## 1 Certificate of Conformity

**Product:** Bluetooth Low Energy and 802.15.4 wireless radio module  
**Brand:** SILICON LABS  
**Test Model:** MGM240S22A  
**Series Model:** BGM240S22A (refer to item 3.1 for more details)  
**Sample Status:** Engineering sample fully representing the production models  
**Applicant:** Silicon Laboratories Finland Oy  
**Test Date:** Jul. 13, 2022 ~ Aug. 01, 2022  
**Standards:** EN 300 328 V2.2.2 (2019-07)

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards. The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's RF characteristics under the conditions specified in this report.

**Prepared by :** Lena Wang , **Date:** Oct. 04, 2022  
Lena Wang / Specialist

**Approved by :** Jeremy Lin , **Date:** Oct. 04, 2022  
Jeremy Lin / Project Engineer

## 2 Summary of Test Results

The EUT has been tested according to the following specifications:

EN 300 328 V2.2.2		
Clause	Test Parameter	Results
4.3.2.2	RF Output Power	Pass
4.3.2.3	Power Spectral Density (Modulations other than FHSS equipment)	Pass
4.3.2.4	Duty cycle, Tx-sequence, Tx-gap (Non-adaptive equipment)	Not Applicable
4.3.2.5	Medium Utilization (Non-Adaptive Equipment)	Not Applicable
4.3.2.6	Adaptivity (Adaptive Equipment)	Pass
4.3.2.7	Occupied Channel Bandwidth	Pass
4.3.2.8	Transmitter Unwanted Emissions in the OOB Domain	Pass
4.3.2.9	Transmitter Unwanted Emissions in the Spurious Domain	Pass
4.3.2.10	Receiver Spurious Emissions	Pass
4.3.2.11	Receiver Blocking	Pass
4.3.2.12	Geo-location capability	Not Applicable

Note: Determining compliance based on the results of the compliance measurement, not taking into account measurement instrumentation uncertainty.

## 2.1 Test Instruments

For all tests except adaptive & receiver blocking:

Description & Manufacturer	Model No.	Serial No.	Calibrated Date	Calibrated Until
Spectrum Analyzer Agilent	N9030B	MY57140488	Feb. 24, 2022	Feb. 23, 2023
Spectrum Analyzer Rohde & Schwarz	FSV40	100980	Apr. 20, 2022	Apr. 19, 2023
USB Wideband Power Sensor KEYSIGHT	U2021XA	MY55050005/MY55190004/MY55190007/MY55210005	Jul. 13, 2022	Jul. 12, 2023
BILOG Antenna SCHWARZBECK	VULB 9168	9168-161	Oct. 28, 2021	Oct. 27, 2022
HORN Antenna ETS	3117	00034130	Nov. 14, 2021	Nov. 13, 2022
HORN Antenna SCHWARZBECK	BBHA 9170	BBHA9170243	Nov. 14, 2021	Nov. 13, 2022
Loop Antenna TESEQ	HLA 6121	45745	Jul. 21, 2021 Jul. 27, 2022	Jul. 20, 2022 Jul. 26, 2023
Preamplifier Agilent	8449B	3008A01976	Jul. 09, 2022	Jul. 08, 2023
Preamplifier Agilent	8447D	2944A10634	Jul. 09, 2022	Jul. 08, 2023
RF signal cable HUBER+SUHNER	SUCOFLEX 104	Cable-RF2-03 (246272/4)	Jul. 09, 2022	Jul. 08, 2023
RF signal cable WOKEN	8D-FB	Cable-RF2-01	Jul. 09, 2022	Jul. 08, 2023
RF signal cable INFINET	CA3501-3501-G.90 (3m) & CA3501-3501-F.90 (2m)	INF090 (3m)*2 & TCF427S (2m)*1	Jul. 09, 2022	Jul. 08, 2023
Software ADT	ADT_Radiated_V7.6.15.9.5	NA	NA	NA
Antenna Tower Max-Full	MFA-440H	1308111	NA	NA
Turn Table ADT	NA	SN30303	NA	NA
Controller Max-Full	MF7802	MF780208363	NA	NA
Temperature & Humidity chamber TERCHY	MHU-225AU	920842	Jun. 21, 2022	Jun. 20, 2023

- Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
 2. The test was performed in HwaYa RF Chamber 2.  
 3. The horn antenna and preamplifier (model: 8449B) are used only for the measurement of emission frequency above 1GHz if tested.  
 4. Tested date: Jul. 25 ~ Aug. 01, 2022

**For Adaptive:**

Description & Manufacturer	Model No.	Serial No.	Calibrated Date	Calibrated Until
MXG Vector signal generator KEYSIGHT	N5182B	MY53052282	Dec. 21, 2021	Dec. 20, 2022
Vector signal generator Agilent	E4438C	MY47271120	Nov. 09, 2021	Nov. 08, 2022
PXA Signal Analyzer KEYSIGHT	N9030B	MY57140938	Mar. 15, 2022	Mar. 14, 2023

- Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. Tested date: Aug. 01, 2022

**For receiver blocking**

Description & Manufacturer	Model No.	Serial No.	Calibrated Date	Calibrated Until
Spectrum Analyzer Rohde & Schwarz	FSV40	100980	Apr. 20, 2022	Apr. 19, 2023
Vector signal generator Agilent	E4438C	MY47271120	Nov. 09, 2021	Nov. 08, 2022
Radio Communication Analyzer Anritsu	CBT	100946	Aug. 06, 2020	Aug. 05, 2022

- Note: 1. The calibration interval of the above test instruments is 12/24 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. Tested date: Jul. 13, 2022



## 2.2 Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT:

This uncertainty represents an expanded uncertainty expressed at approximately the 95% confidence level using a coverage factor of  $k=2$ .

Parameter	Uncertainty
Occupied Channel Bandwidth	$\pm 1.132 \times 10^{-4} \%$
RF output power, conducted	$\pm 1.371 \text{ dB}$
Power Spectral Density, conducted	$\pm 1.371 \text{ dB}$
Unwanted Emissions, conducted	$\pm 1.371 \text{ dB}$
All emissions, radiated	$\pm 3.294 \text{ dB}$
Temperature	$\pm 0.23 \text{ }^{\circ}\text{C}$
Supply voltages	$\pm 0.3 \%$
Time	$\pm 2.53 \%$

## 2.3 Modification Record

There were no modifications required for compliance.

### 3 General Information

#### 3.1 General Description of EUT

Product	Bluetooth Low Energy and 802.15.4 wireless radio module
Brand	SILICON LABS
Test Model	MGM240S22A
Series Model	BGM240S22A
Model Difference	Refer to note
Status of EUT	Engineering sample fully representing the production module
Power Supply Rating	1.8Vdc to 3.8Vdc (from host equipment)
Typical Nominal Supply Voltage	3.0Vdc
Normal Testing Voltage	3.3Vdc
Temperature Operating Range	-40~105°C
Modulation Type	GFSK
Modulation Technology	DTS
Transfer Rate	1MBaud with 1Mbps transfer rate 1MBaud with coded 125Kbps transfer rate 1MBaud with coded 500Kbps transfer rate 2MBaud with 2Mbps transfer rate
Operating Frequency	2402 ~ 2480MHz
Number of Channel	1MBaud: 40 2MBaud: 37
Adaptive/Non-Adaptive	<input checked="" type="checkbox"/> non-adaptive Equipment <input checked="" type="checkbox"/> adaptive Equipment without the possibility to switch to a non-adaptive mode <input type="checkbox"/> adaptive Equipment which can also operate in a non-adaptive mode
EIRP Power (Measured Max. Average)	Mode A : 11.03dBm Mode B : 11.04dBm
Antenna Type	Refer to note
Antenna Connector	Refer to note
Accessory Device	NA
Data Cable Supplied	NA

Note:

1. All models are listed as below. Model MGM240S22A is the representative for final test.

Note: All models are listed as below. Model MGM240S22A is the representative for final test.				
Product Spec.	Model			
	Main Model: MGM240S22A		Series Model: BGM240S22A	
	Power rating: Low-Power Wireless protocols: BLE and 802.15.4		Power rating: Low-Power Wireless protocols: BLE	
Test mode	To be tested as DTS for both 802.15.4 and BLE In the case of BLE, three PHYs to test: 2Mbps , 1Mbps and 125Kbps		Testing of the Main Model will cover this Series Model / In fact, the hardware and software are exactly the same, except for one single software-related difference: the 802.15.4 protocol is disabled in the factory for marketing differentiation	
RF nominal max TX output power	10dBm			
Antenna type	Integral antenna	RF pin	Integral antenna	RF pin
Hardware	<p>Hardware-wise, the main model and the first series model are identical. Supply voltage range: 1V8 to 3V8 (nominal 3V0) / Fully internally regulated, including the RF PA. Temperature range: -40C to +105C.</p> <p>The BLE wireless protocol is identical in all the models. The 802.15.4 wireless protocol is made available only for the main model.</p> <p>The module's RF OUT pin exposes the 50Ω-matched RF port of the embedded radio chipset. Conducted measurements are taken at the module's RF OUT pin.</p> <p>The RF OUT pin can be further connected either to the adjacent RF ANT IN pin (using a 0Ω resistor), so that the integral antenna can be used, or directly to an external antenna. All radiated tests are taken both with a sample using the integral antenna, and with a sample where the RF signal from the RF OUT pin is routed instead to an external reference dipole antenna.</p>			

2. The antenna information is listed as below.

No.	Type	Connector	Gain (dBi)	Remark
1	Integral antenna	NA	1.48	For model: MGM240S22A, BGM240S22A
2	External reference dipole antenna**	RP-SMA	2.80	For model: MGM240S22A, BGM240S22A

\* The above Antenna information is declared by manufacturer and for more detailed features description, please refer to the manufacturer's specifications, the laboratory shall not be held responsible.

\*\* The dipole antenna is not sold with the EUT, but is used during testing as a reference antenna for radiated measurements of the parts making use of the RF pin.

3. For 1MBaud, after the pretesting three transfer rates (1Mbps, 125Kbps and 500Kbps), 1MBaud with 1Mbps and 125Kbps transfer rate were the worst case test and chosen for final test.

4. The power setting is list as below.

**1MBaud**

Test Mode	MGM240S22A / Integral ant.	Test Mode	MGM240S22A / Dipole ant.
CH 0	77	CH 0	66
CH 1	77	CH 1	66
CH 19	78	CH 19	66
CH 38	81	CH 38	68
CH 39	81	CH 39	68

**2MBaud**

Test Mode	MGM240S22A / Integral ant.	Test Mode	MGM240S22A / Dipole ant.
CH 1	86	CH 1	70
CH 19	86	CH 19	71
CH 38	92	CH 38	73

**125Kbps**

Test Mode	MGM240S22A / Integral ant.	Test Mode	MGM240S22A / Dipole ant.
CH 0	77	CH 0	66
CH 1	77	CH 1	66
CH 19	78	CH 19	66
CH 38	81	CH 38	68
CH 39	81	CH 39	68

### 3.2 Description of Test Modes

1MBaud:

40 channels are provided to this EUT:

Channel	Freq. (MHz)	Channel	Freq. (MHz)	Channel	Freq. (MHz)	Channel	Freq. (MHz)
0	2402	10	2422	20	2442	30	2462
1	2404	11	2424	21	2444	31	2464
2	2406	12	2426	22	2446	32	2466
3	2408	13	2428	23	2448	33	2468
4	2410	14	2430	24	2450	34	2470
5	2412	15	2432	25	2452	35	2472
6	2414	16	2434	26	2454	36	2474
7	2416	17	2436	27	2456	37	2476
8	2418	18	2438	28	2458	38	2478
9	2420	19	2440	29	2460	39	2480

Note: Physical Channels 0, 12 and 39 are special low-duty-cycle channels used only for BLE advertising mode.

2MBaud:

37 channels are provided to this EUT:

Channel	Freq. (MHz)	Channel	Freq. (MHz)	Channel	Freq. (MHz)	Channel	Freq. (MHz)
1	2404	11	2424	22	2446	32	2466
2	2406	13	2428	23	2448	33	2468
3	2408	14	2430	24	2450	34	2470
4	2410	15	2432	25	2452	35	2472
5	2412	16	2434	26	2454	36	2474
6	2414	17	2436	27	2456	37	2476
7	2416	18	2438	28	2458	38	2478
8	2418	19	2440	29	2460		
9	2420	20	2442	30	2462		
10	2422	21	2444	31	2464		

### 3.2.1 Test Mode Applicability and Tested Channel Detail

EUT Configure Mode	Applicable to										Description
	ROP	PSD	DC/TS/TG	MU	AD	OCB	EOB	SE< 1G	SE≥ 1G	RB	Condition
A	√	√	-	-	√	√	√	√	√	-	Integral ant.
B	√	√	-	-	-	√	√	√	√	√	Dipole ant.

Where ROP: RF Output Power PSD: Power Spectral Density  
DC/TS/TG: Duty Cycle/ Tx-Sequence / Tx-gap MU: Medium Utilization  
AD: Adaptivity (Channel Access Mechanism) OCB: Occupied Channel Bandwidth  
EOB: Transmitter unwanted emissions in the out-of-band domain SE<1G: Unwanted Emissions in the Spurious Domain below 1 GHz  
SE≥1G: Unwanted Emissions in the Spurious Domain above 1 GHz RB: Receiver Blocking

Note:

- The EUT had been pre-tested on the positioned of each 3 axis. The worst case was found when positioned on **Y-plane for Mode A and Z-plane for Mode B.**
- "-": Means no effect.

#### RF Output Power Test:

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 1, 19, 38, 39	GFSK	1 Mbps
	1 to 38	1, 19, 38	GFSK	2 Mbps
	0 to 39	0, 1, 19, 38, 39	GFSK	125Kbps
B	0 to 39	0, 1, 19, 38, 39	GFSK	1 Mbps
	1 to 38	1, 19, 38	GFSK	2 Mbps
	0 to 39	0, 1, 19, 38, 39	GFSK	125Kbps

#### Power Spectral Density Test:

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 1, 19, 38, 39	GFSK	1 Mbps
	1 to 38	1, 19, 38	GFSK	2 Mbps
	0 to 39	0, 1, 19, 38, 39	GFSK	125Kbps
B	0 to 39	0, 1, 19, 38, 39	GFSK	1 Mbps
	1 to 38	1, 19, 38	GFSK	2 Mbps
	0 to 39	0, 1, 19, 38, 39	GFSK	125Kbps

#### **Adaptivity:**

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps

#### **Occupied Channel Bandwidth Test:**

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps
	0 to 39	0, 39	GFSK	125Kbps
B	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps
	0 to 39	0, 39	GFSK	125Kbps

#### **Transmitter Unwanted Emissions in the Out-of-band Domain Test:**

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps
	0 to 39	0, 39	GFSK	125Kbps
B	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps
	0 to 39	0, 39	GFSK	125Kbps

#### **Unwanted Emissions in the Spurious Domain Test (Below 1 GHz):**

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).
- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	39	GFSK	1 Mbps
	1 to 38	38	GFSK	2 Mbps
B	0 to 39	39	GFSK	1 Mbps
	1 to 38	38	GFSK	2 Mbps

### Unwanted Emissions in the Spurious Domain Test (Above 1 GHz):

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).

- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
A	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps
B	0 to 39	0, 39	GFSK	1 Mbps
	1 to 38	1, 38	GFSK	2 Mbps

### Receiver Blocking test:

- ☒ Pre-Scan has been conducted to determine the worst-case mode from all possible combinations between available modulations, data rates and antenna ports (if EUT with antenna diversity architecture).

- ☒ Following channel(s) was (were) selected for the final test as listed below.

EUT Configure Mode	Available Channel	Tested Channel	Modulation Type	Data Rate
B	0 to 39	0, 39	GFSK	125Kbps

### Test Condition:

Applicable To	Environmental Conditions	Input Power	Tested by
ROP	25 deg. C, 60% RH	3.3Vdc	Chun Wu
PSD	25 deg. C, 60% RH	3.3Vdc	Chun Wu
AD	25 deg. C, 65% RH	3.3Vdc	Matthew Yang
OCB	25 deg. C, 60% RH	3.3Vdc	Chun Wu
EOB	25 deg. C, 60% RH	3.3Vdc	Chun Wu
SE<1G	25 deg. C, 64% RH, 21 deg. C, 66% RH	230Vac, 50Hz (System)	Jay Chang
SE≥1G	25 deg. C, 64% RH, 21 deg. C, 66% RH	230Vac, 50Hz (System)	Jay Chang
RB	25 deg. C, 65% RH	3.3Vdc	Oakley Chen



### 3.3 Description of Support Units

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.


ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Host board specifically designed for worst-case certification testing of the EUT	Silicon Labs.	N/A	N/A	N/A	Provided by client
B.	Notebook	DELL	E5520	8Y4DMQ1	N/A	-

Note:

1. All power cords of the above support units are non-shielded (1.8m).
2. Item B acted as a communication partner to transfer data.

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	USB cable	1	1.5	Y	0	Provided by client

#### 3.3.1 Configuration of System under Test



### 3.4 General Description of Applied Standards

The EUT is a RF Product. According to the specifications of the manufacturer, it must comply with the requirements of the following standards:

#### EN 300 328 V2.2.2 (2019-07)

All test items have been performed and recorded as per the above standards.

## 4 Test Procedure and Results

### 4.1 RF Output Power

#### 4.1.1 Limits of RF Output Power

Condition	Frequency Band	Limit (e.i.r.p)
Under all test conditions	2400 ~ 2483.5 MHz	AV: 20dBm

#### 4.1.2 Test Procedures

Refer to chapter 5.4.2 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement

For extreme test condition refer to chapter Annex B.4 and procedure follow Annex B.4.3.

#### 4.1.3 Deviation from Test Standard

No deviation.

#### 4.1.4 Test Setup

The measurements for RF output power was performed at both normal environmental conditions and at the extremes of the operating temperature. Controlling software (provided by manufacturer) has been activated to set the EUT on specific channel and power level.





## 4.2 Adaptivity (Adaptive Frequency Hopping)

This requirement does not apply to non-adaptive equipment or adaptive equipment operating in a non-adaptive mode providing the equipment complies with the requirements and/or restrictions applicable to non-adaptive equipment.

In addition, this requirement does not apply for equipment with a maximum declared RF Output power level of less than 10 dBm e.i.r.p. or for equipment when operating in a mode where the RF Output power is less than 10 dBm e.i.r.p.

### 4.2.1 Limit of Adaptive

#### Applicability of adaptive requirements and limit for frequency hopping equipment

Requirement	Operational Mode	
	Using LBT based DAA (CCA using 'energy detect')	using other forms of DAA (non-LBT based)
Minimum Clear Channel Assessment (CCA) Time	18 us (see note 1)	NA
Maximum Channel Occupancy (COT) Time	60 ms (see note 6)	40ms (see note2)
Minimum Idle Period	100us (see note 7)	100us (see note 2)
Extended CCA check	See note 4	NA
Minimum time for unavailable	NA	(see note 3)
Short Control Signalling Transmissions	Maximum duty cycle of 10 % within an observation period of 50 ms (see note 5)	
Note 1: The CCA observation time shall be not less than 0,2 % of the Channel Occupancy Time with a minimum of 18 μs		
Note 2: For equipment using a dwell time > 40 ms that want to have other transmissions during the same hop (dwell time) an Idle Period (no transmissions) of minimum 5 % of the Channel Occupancy Period with a minimum of 100 μs shall be implemented.		
Note 3: The frequency shall remain unavailable for a minimum time equal to 1 second or 5 times the actual number of hopping frequencies multiplied with the Channel Occupancy Time whichever is the longest.		
Note 4: Observed for a random duration between the value defined for the CCA observation time and 5 % of the Channel Occupancy Time.		
Note 5: Adaptive equipment may or may not have Short Control Signaling Transmissions.		
Note 6: For LBT based frequency hopping equipment with a dwell time < 60 ms, the maximum Channel Occupancy Time is limited by the dwell time.		
Note 7: Minimum 5 % of the Channel Occupancy Time with a minimum of 100 μs.		

#### Interference threshold level

Maximum transmit power ( $P_H$ ) EIRP dBm	Threshold level (TL) (see notes 1 and 2)
20	-70 dBm / MHz
Note 1: For a 20 dBm e.i.r.p. transmitter the detection threshold level (TL) shall be equal or less than -70 dBm/MHz at the input to the receiver (assuming a 0 dBi receive antenna) Note 2: For power levels below 20 dBm e.i.r.p., the detection threshold level may be relaxed to $TL = -70 \text{ dBm/MHz} + 10 \times \log_{10} (100 \text{ mW} / P_{out})$ ( $P_{out}$ in mW e.i.r.p.)	

Unwanted signal parameters for Adaptive frequency hopping using LBT based DAA		
Wanted signal mean power from companion device (dBm)	Unwanted signal frequency (MHz)	Unwanted CW signal power (dBm)
sufficient to maintain the link (see note 2)	2 395 or 2 488.5 (see note 1)	-35 (see note 3)
<p>Note 1: The highest frequency shall be used for testing operating channels within the range 2 400 MHz to 2 442 MHz, while the lowest frequency shall be used for testing operating channels within the range 2 442 MHz to 2 483.5 MHz.</p> <p>Note 2: A typical value which can be used in most cases is -50 dBm/MHz.</p> <p>Note 3: The level specified is the level in front of the UUT antenna. In case of conducted measurements, this level has to be corrected by the actual antenna assembly gain.</p>		

Unwanted signal parameters for Adaptive frequency hopping using other forms of DAA (non-LBT based)		
Wanted signal mean power from companion device (dBm)	Unwanted signal frequency (MHz)	Unwanted CW signal power (dBm)
-30	2 395 or 2 488.5 (see note 1)	-35 (see note 2)
<p>Note 1: The highest frequency shall be used for testing operating channels within the range 2 400 MHz to 2 442 MHz, while the lowest frequency shall be used for testing operating channels within the range 2 442 MHz to 2 483,5 MHz.</p> <p>Note 2: The level specified is the level in front of the UUT antenna. In case of conducted measurements, this level has to be corrected by the actual antenna assembly gain.</p>		

#### 4.2.2 Test Procedure


Refer to chapter 5.4.6 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement

#### 4.2.3 Deviation from Test Standard

No deviation.

#### 4.2.4 Test Setup Configuration



#### UUT Software and Firmware Version

Product	Model No.	Software/Firmware Version
Bluetooth Low Energy wireless radio module	MGM240S22A	2.1.7

#### Companion Device Information

Product	Model No.	Software/Firmware Version
Bluetooth Low Energy wireless radio module	MGM240S22A	2.1.7

#### 4.2.5 List of Measurements

UUT Operational Mode	Applicable	Limit	
		The Maximum Channel Occupancy Time	The Minimum idle Period
Frame Based Equipment		meet in 1 ms ~ 10 ms	> 5 % x channel occupancy time
Load Based Equipment (CCA using 'energy detect')		Follow IEEE 802.11 Less than ____ms	Follow IEEE 802.11 More than ____ms
	v	13 ms	18 us
Load Based Equipment (CCA not using any of the mechanisms referenced)		13 ms	18 us

Clause	Test Parameter	Remarks	Pass/Fail
4.3.2.6.3.2.2	Adaptive (Frame Based Equipment)	Not Applicable	NA
4.3.2.6.3.2.3	Adaptive (Load Based Equipment)	Applicable	Pass
4.3.2.6.4	Short Control Signalling Transmissions	Applicable	Pass
4.3.2.6.2	Unwanted Signal Parameters	Not Applicable	NA



## 4.2.6 Interference Threshold Level



### 1MBaud

#### Detection Threshold Level

The maximum EIRP power is 10.17dBm and antenna gain is 1.48dBi.

Detection Threshold Level =  $-70\text{dBm/MHz} + 10 \cdot \log_{10} (100\text{mW} / P_{\text{out}} (10.4\text{mW})) + G (1.48\text{dBi}) = -58.69\text{dBm/MHz}$ .

The interference signal level to the UUT is -58.69dBm/MHz





### 2MBaud

#### Detection Threshold Level

The maximum EIRP power is 11.05dBm and antenna gain is 1.48dBi.

Detection Threshold Level =  $-70\text{dBm/MHz} + 10 \cdot \log_{10} (100\text{mW} / P_{\text{out}} (12.74\text{mW})) + G (1.48\text{dBi}) = -59.57\text{dBm/MHz}$ .

The interference signal level to the UUT is -59.57dBm/MHz



#### 4.2.7 Test Result


- |  |
|--|
| <input type="checkbox"/> Not applicable to non-adaptive equipment or adaptive equipment operating in a non-adaptive mode |
| <input type="checkbox"/> Not applicable to equipment with RF output power is less than 10 dBm e.i.r.p.                   |
| <input checked="" type="checkbox"/> Refer to below test result   |

##### 4.2.7.1 Adaptive Result

###### Operating Frequency Bands and Mode of EUT


Operational Mode	Operating Frequency (Low power Channel, MHz)	Operating Frequency (High power Channel, MHz)	Test Result
BT LE 1M	2402	2480	Pass
BT LE 2M	2404	2478	Pass

## 1MBaud 2402MHz




Date: 1.AUG.2022 21:04:51

## 2480MHz




Date: 1.AUG.2022 21:08:14

2MBaud  
2404MHz



Date: 1.AUG.2022 21:27:56

2478MHz




Date: 1.AUG.2022 21:32:54

## 4.2.7.2 The Channel Occupancy Time Result

### Operating Frequency Bands and Mode of EUT


Operational Mode	Operating Frequency Low power Channel (MHz)	The Channel Occupancy Time (ms)	Minimum Idle Period (us)	Test Result
BT LE 1M	2402	0.3375	49321.5	Pass
BT LE 2M	2404	0.08437	99993.75	Pass

### 1Mbaud



Date: 1.AUG.2022 19:44:51

### 2Mbaud



Date: 1.AUG.2022 21:17:29

#### 4.2.7.3 Unwanted Signal Interference

##### 1MBaud

Channel	Channel Frequency (MHz)	Wanted Signal Mean Power from Companion Device (dBm/MHz)	Blocking Signal Frequency (MHz)	Blocking Signal Power (dBm)	Pass/Fail
0	2402	-50	2488.5	-32.2	Pass
39	2480	-50	2395.0	-32.2	Pass

##### 2MBaud

Channel	Channel Frequency (MHz)	Wanted Signal Mean Power from Companion Device (dBm/MHz)	Blocking Signal Frequency (MHz)	Blocking Signal Power (dBm)	Pass/Fail
1	2404	-50	2488.5	-32.2	Pass
38	2478	-50	2395.0	-32.2	Pass


#### 4.2.7.4 Short Control Signalling Transmissions Result

1MBaud

2402MHz

Short Control Signalling Transmission Result		
SCST total on time (ms)	SCST Limit (ms)	Test Result
0.154688	5	Pass


#### Duty Cycle



2480MHz

Short Control Signalling Transmission Result		
SCST total on time (ms)	SCST Limit (ms)	Test Result
0.173438	5	Pass

#### Duty Cycle




2MBaud

2404MHz

Short Control Signalling Transmission Result		
SCST total on time (ms)	SCST Limit (ms)	Test Result
0.154688	5	Pass


#### Duty Cycle



2478MHz

Short Control Signalling Transmission Result		
SCST total on time (ms)	SCST Limit (ms)	Test Result
0.240625	5	Pass

#### Duty Cycle





### 4.3 Power Spectral Density

#### 4.3.1 Limit of Power Spectral Density

Condition	Frequency Band	Limit (e.i.r.p.)
Under normal conditions	2400 ~ 2483.5 MHz	10dBm / 1MHz

#### 4.3.2 Test Procedures

Refer to chapter 5.4.3 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement
<input checked="" type="checkbox"/> Option 1: For equipment with continuous and non-continuous transmissions	
<input type="checkbox"/> Option 2: For equipment with continuous transmission capability or for equipment operating (or with the capability to operate) with a constant duty cycle (e.g. Frame Based equipment)	

#### 4.3.3 Deviation of Test Standard

No deviation.

#### 4.3.4 Test Setup

The test setup has been constructed as the normal test condition. (In case of conducted measurements the transmitter shall be connected to the measuring equipment via a suitable attenuator.) The power spectral density as defined in EN 300 328 clause 4.3.2.3 shall be measured and recorded. Controlling software (provided by manufacturer) has been activated to set the EUT on specific status.

#### 4.3.5 Test Results

##### Mode A 1MBaud

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
0	2402	9.95	10	Pass
1	2404	9.94	10	Pass
19	2440	9.95	10	Pass
38	2478	9.93	10	Pass
39	2480	9.91	10	Pass

##### 2MBaud

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
1	2404	9.56	10	Pass
19	2440	9.49	10	Pass
38	2478	9.93	10	Pass

##### 125Kbps

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
0	2402	9.93	10	Pass
1	2404	9.92	10	Pass
19	2440	9.92	10	Pass
38	2478	9.92	10	Pass
39	2480	9.90	10	Pass

**Mode B**  
**1MBaud**

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
0	2402	9.92	10	Pass
1	2404	9.92	10	Pass
19	2440	9.89	10	Pass
38	2478	9.91	10	Pass
39	2480	9.87	10	Pass

**2MBaud**

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
1	2404	9.88	10	Pass
19	2440	9.86	10	Pass
38	2478	9.89	10	Pass

**125Kbps**

Channel	Frequency (MHz)	EIRP PSD (dBm/MHz)	PSD Limit (dBm)	Test Result
0	2402	9.93	10	Pass
1	2404	9.94	10	Pass
19	2440	9.91	10	Pass
38	2478	9.92	10	Pass
39	2480	9.89	10	Pass

#### 4.4 Occupied Channel Bandwidth

##### 4.4.1 Limit of Occupied Channel Bandwidth

Condition		Limit
All types of equipment		Shall fall completely within the band 2400 to 2483.5 MHz.
Additional requirement	For non-adaptive using wide band modulations other than FHSS system and e.i.r.p >10dBm.	Less than 20MHz
	For non-adaptive Frequency Hopping system and e.i.r.p >10dBm.	Less than 5MHz

##### 4.4.2 Test Procedure

Refer to chapter 5.4.7 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement

##### 4.4.3 Deviation from Test Standard

No deviation.

##### 4.4.4 Test Setup

These measurements only were performed at normal test conditions. The measurement shall be performed only on the lowest and the highest frequency within the stated frequency range. In case of conducted measurements the transmitter shall be connected to the measuring equipment via a suitable attenuator. Controlling software (provided by manufacturer) has been activated to set the EUT on specific status.

#### 4.4.5 Test Results

##### Mode A 1MBaud

Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Measured Frequencies		Limit	Pass/Fail
			F <sub>L</sub> (MHz)	F <sub>H</sub> (MHz)		
0	2402	1.03	2401.48	2402.51	F <sub>L</sub> > 2400 MHz and F <sub>H</sub> < 2483.5 MHz	Pass
39	2480	1.03	2479.48	2480.51		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

##### 2MBaud

Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Measured Frequencies		Limit	Pass/Fail
			F <sub>L</sub> (MHz)	F <sub>H</sub> (MHz)		
1	2404	2.05	2402.97	2405.02	F <sub>L</sub> > 2400 MHz and F <sub>H</sub> < 2483.5 MHz	Pass
38	2478	2.06	2476.97	2479.03		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

##### 125Kbps

Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Measured Frequencies		Limit	Pass/Fail
			F <sub>L</sub> (MHz)	F <sub>H</sub> (MHz)		
0	2402	1.03	2401.48	2402.51	F <sub>L</sub> > 2400 MHz and F <sub>H</sub> < 2483.5 MHz	Pass
39	2480	1.03	2479.48	2480.51		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

### Mode B 1MBaud

Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Additional requirement	Measured Frequencies		Limit	Test Result
				FL (MHz)	FH (MHz)		
0	2402	1.03	Less than 20 MHz	2401.49	2402.52	FL > 2400 MHz and FH < 2483.5 MHz	Pass
39	2480	1.03		2479.49	2480.52		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

### 2MBaud

Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Additional requirement	Measured Frequencies		Limit	Test Result
				FL (MHz)	FH (MHz)		
1	2404	2.06	Less than 20 MHz	2402.97	2405.03	FL > 2400 MHz and FH < 2483.5 MHz	Pass
38	2478	2.06		2476.97	2479.03		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

### 125Kbps


Channel	Channel Frequency (MHz)	Occupied Bandwidth (MHz)	Additional requirement	Measured Frequencies		Limit	Test Result
				FL (MHz)	FH (MHz)		
0	2402	1.03	Less than 20 MHz	2401.48	2402.51	FL > 2400 MHz and FH < 2483.5 MHz	Pass
39	2480	1.03		2479.48	2480.51		Pass

Note: FL is the lowest frequency of the 99% occupied bandwidth of power envelope.  
FH is the highest frequency of the 99% occupied bandwidth of power envelope.

## 4.5 Transmitter Unwanted Emissions in the Out-of-band Domain

### 4.5.1 Limits of Transmitter Unwanted Emissions in the Out-of-band Domain

Condition	Limit
Under all test conditions	The transmitter unwanted emissions in the out-of-band domain but outside the allocated band, shall not exceed the values provided by the mask in below figure.



### 4.5.2 Test Procedure

Refer to chapter 5.4.8 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement

### 4.5.3 Deviation from Test Standard

No deviation

### 4.5.4 Test Setup

The measurements were performed at normal environmental conditions. The measurement was performed at the lowest and the highest channel on which the equipment can operate. The equipment was configured to operate under its worst case situation with respect to output power. In case of conducted measurements the transmitter shall be connected to the measuring equipment via a suitable attenuator. The frequency has to be recorded for the right and left end above threshold of highest and lowest channel respectively.

#### 4.5.5 Test Results

##### Mode A 1MBaud

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
0	2402	2397.94 ~ 2398.97	2398.47	-38.72	-20	Pass
		2398.97 ~ 2400	2399.50	-21.78	-10	Pass
39	2480	2483.5 ~ 2484.53	2484.00	-39.76	-10	Pass
		2484.53 ~ 2485.56	2485.03	-49.58	-20	Pass

##### 2MBaud

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
1	2404	2395.9 ~ 2397.95	2397.45	-52.52	-20	Pass
		2397.95 ~ 2400	2399.50	-45.06	-10	Pass
38	2478	2483.5 ~ 2485.56	2484.00	-49.96	-10	Pass
		2485.56 ~ 2487.62	2487.06	-52.83	-20	Pass

##### 125Kbps

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
0	2402	2397.94 ~ 2398.97	2398.47	-38.67	-20	Pass
		2398.97 ~ 2400	2399.50	-21.95	-10	Pass
39	2480	2483.5 ~ 2484.53	2484.00	-39.74	-10	Pass
		2484.53 ~ 2485.56	2485.03	-49.59	-20	Pass



### Mode B 1MBaud

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
0	2402	2397.94 ~ 2398.97	2398.47	-38.48	-20	Pass
		2398.97 ~ 2400	2399.50	-21.89	-10	Pass
39	2480	2483.5 ~ 2484.53	2484.00	-40.14	-10	Pass
		2484.53 ~ 2485.56	2485.03	-49.71	-20	Pass

### 2MBaud

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
1	2404	2395.88 ~ 2397.94	2397.44	-51.90	-20	Pass
		2397.94 ~ 2400	2399.50	-44.71	-10	Pass
38	2478	2483.5 ~ 2485.56	2484.00	-49.26	-10	Pass
		2485.56 ~ 2487.62	2487.06	-51.73	-20	Pass

### 125Kbps

Channel	Frequency (MHz)	Out-Of-Band Domain			Limit (dBm/MHz)	Test Result
		Frequency Range (MHz)	Worst Frequency (MHz)	Emission Level (dBm/MHz)		
0	2402	2397.94 ~ 2398.97	2398.47	-38.48	-20	Pass
		2398.97 ~ 2400	2399.50	-22.18	-10	Pass
39	2480	2483.5 ~ 2484.53	2484.00	-40.14	-10	Pass
		2484.53 ~ 2485.56	2485.03	-49.63	-20	Pass

## 4.6 Transmitter Spurious Emissions in the spurious domain

### 4.6.1 Limits of Transmitter Spurious Emissions

Frequency Range	Maximum Power Limit	Bandwidth
30 MHz to 47 MHz	-36dBm	100kHz
47 MHz to 74 MHz	-54dBm	100kHz
74 MHz to 87,5 MHz	-36dBm	100kHz
87,5 MHz to 118 MHz	-54dBm	100kHz
118 MHz to 174 MHz	-36dBm	100kHz
174 MHz to 230 MHz	-54dBm	100kHz
230 MHz to 470 MHz	-36dBm	100kHz
470 MHz to 694 MHz	-54dBm	100kHz
694 MHz to 1 GHz	-36dBm	100kHz
1GHz ~ 12.75GHz	-30dBm	1MHz

Note: These limits are e.r.p. for emissions up to 1 GHz and as e.i.r.p. for emissions above 1 GHz.

### 4.6.2 Test Procedure

Refer to chapter 5.4.9 of EN 300 328 V2.2.2.

Measurement Method	
<input type="checkbox"/> Conducted measurement	<input checked="" type="checkbox"/> Radiated measurement
<p><u>For Conducted measurement:</u>            The level of unwanted emissions shall be measured as their power in a specified load (conducted spurious emissions) and their effective radiated power when radiated by the cabinet or structure of the equipment with the antenna connector(s) terminated by a specified load (cabinet radiation).</p>	
<p><u>Conducted measurement (For equipment with multiple transmit chains):</u>  <input type="checkbox"/> Option 1: The results for each of the transmit chains for the corresponding 1MHz segments shall be added and compared with the limits.  <input type="checkbox"/> Option 2: The results for each of the transmit chains shall be individually compared with the limits after these limits have been reduced by <math>10 \times \log(N)</math> (number of active transmit chains)</p>	

### 4.6.3 Deviation from Test Standard

No deviation.

### 4.6.4 Test Setup

1. For the actual test configuration, please refer to the related Item in this test report (Photographs of the Test Configuration).
2. The equipment was configured to operate under its worst case situation with respect to output power.
3. The test setup has been constructed as the normal use condition. Controlling software (provided by manufacturer) has been activated to set the EUT on specific status.

#### 4.6.5 Test Results

##### Below 1 GHz Worst-case Data

##### Mode A

##### 1MBaud

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	39
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
48.05	V	-69.69	-54.00	-15.69
68.60	H	-72.19	-54.00	-18.19
99.60	V	-69.54	-54.00	-15.54
140.06	H	-77.69	-36.00	-41.69
233.21	V	-71.49	-36.00	-35.49
233.26	H	-74.49	-36.00	-38.49
445.82	V	-68.47	-36.00	-32.47
479.97	H	-65.13	-54.00	-11.13
612.78	H	-68.64	-54.00	-14.64
613.43	V	-70.74	-54.00	-16.74
860.94	H	-67.10	-36.00	-31.10
871.69	V	-66.30	-36.00	-30.30

##### 2MBaud

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	38
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
63.40	H	-63.57	-54.00	-9.57
99.95	V	-70.84	-54.00	-16.84
100.75	H	-63.93	-54.00	-9.93
202.51	H	-70.22	-54.00	-16.22
226.21	V	-72.13	-54.00	-18.13
342.02	H	-66.44	-36.00	-30.44
346.82	V	-66.62	-36.00	-30.62
445.37	V	-65.56	-36.00	-29.56
599.88	H	-68.97	-54.00	-14.97
609.68	V	-69.97	-54.00	-15.97
862.64	H	-65.86	-36.00	-29.86
878.39	V	-66.72	-36.00	-30.72

**Mode B**  
**1MBaud**

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	39
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
47.85	V	-70.17	-54.00	-16.17
92.45	H	-63.39	-54.00	-9.39
110.25	V	-70.41	-54.00	-16.41
180.01	H	-65.63	-54.00	-11.63
180.01	V	-64.02	-54.00	-10.02
232.36	H	-64.92	-36.00	-28.92
348.62	H	-65.25	-36.00	-29.25
445.67	V	-68.47	-36.00	-32.47
540.03	H	-65.97	-54.00	-11.97
607.43	V	-71.53	-54.00	-17.53
866.69	V	-67.43	-36.00	-31.43
888.24	H	-66.18	-36.00	-30.18

**2MBaud**

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	38
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
46.35	V	-66.23	-36.00	-30.23
59.85	H	-77.97	-54.00	-23.97
180.01	H	-69.57	-54.00	-15.57
180.01	V	-61.83	-54.00	-7.83
232.36	H	-66.59	-36.00	-30.59
342.62	V	-66.08	-36.00	-30.08
452.62	V	-64.77	-36.00	-28.77
452.72	H	-70.96	-36.00	-34.96
590.48	H	-70.02	-54.00	-16.02
592.83	V	-69.60	-54.00	-15.60
805.14	H	-68.13	-36.00	-32.13
822.24	V	-66.70	-36.00	-30.70

# Above 1 GHz Worst-case Data

## Mode A

### 1MBaud

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	0, 39
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
0	4804.40	H	-56.77	-30.00	-26.77
	4806.36	V	-56.91	-30.00	-26.91
	7206.31	H	-54.57	-30.00	-24.57
	7208.35	V	-54.50	-30.00	-24.50
39	4960.01	H	-57.10	-30.00	-27.10
	4960.21	V	-57.28	-30.00	-27.28

### 2MBaud

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	1, 38
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
1	4808.14	V	-56.49	-30.00	-26.49
	4808.19	H	-56.73	-30.00	-26.73
38	4956.17	V	-56.50	-30.00	-26.50
	4956.62	H	-57.32	-30.00	-27.32

**Mode B**  
**1MBaud**

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	0, 39
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
0	4804.42	H	-57.21	-30.00	-27.21
	4804.69	V	-54.23	-30.00	-24.23
	7206.04	V	-54.31	-30.00	-24.31
	7206.13	H	-53.80	-30.00	-23.80
39	4960.43	H	-57.19	-30.00	-27.19
	4960.63	V	-55.35	-30.00	-25.35

**2MBaud**

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	1, 38
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
1	4808.68	H	-57.20	-30.00	-27.20
	4808.86	V	-54.52	-30.00	-24.52
38	4956.10	V	-55.99	-30.00	-25.99
	4956.29	H	-56.81	-30.00	-26.81

## 4.7 Receiver Spurious Emissions

### 4.7.1 Limit of Receiver Spurious Emissions

Frequency Range	Maximum Power Limit	Bandwidth
30 MHz ~ 1 GHz	-57dBm	100 kHz
1 GHz ~ 12.75 GHz	-47dBm	1 MHz

Note: These limits are e.r.p. for emissions up to 1 GHz and as e.i.r.p. for emissions above 1 GHz.

### 4.7.2 Test Procedure

Refer to chapter 5.4.10 of EN 300 328 V2.2.2.

Measurement Method	
<input type="checkbox"/> Conducted measurement	<input checked="" type="checkbox"/> Radiated measurement
<p><u>For Conducted measurement:</u>            The level of unwanted emissions shall be measured as their power in a specified load (conducted spurious emissions) and their effective radiated power when radiated by the cabinet or structure of the equipment with the antenna connector(s) terminated by a specified load (cabinet radiation).</p>	
<p><u>Conducted measurement (For equipment with multiple transmit chains):</u>  <input type="checkbox"/> Option 1: The results for each of the transmit chains for the corresponding 1MHz segments shall be added and compared with the limits.  <input type="checkbox"/> Option 2: The results for each of the transmit chains shall be individually compared with the limits after these limits have been reduced by <math>10 \times \log(N)</math> (number of active transmit chains)</p>	

### 4.7.3 Deviation from Test Standard

No deviation.

### 4.7.4 Test Setup

1. For the actual test configuration, please refer to the related Item in this test report (Photographs of the Test Configuration).
2. Testing was performed when the equipment was in a receive-only mode.
3. The test setup has been constructed as the normal use condition. Controlling software (provided by manufacturer) has been activated to set the EUT on specific status.

#### 4.7.5 Test Results

##### Below 1 GHz Worst-case Data

##### Mode A

##### 1MBaud

Spurious Emission Frequency Range	30MHz ~ 1GHz	Operating Channel	39
-----------------------------------	--------------	-------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
99.70	V	-69.95	-57.00	-12.95
99.90	H	-71.84	-57.00	-14.84
201.61	H	-71.54	-57.00	-14.54
232.36	V	-73.86	-57.00	-16.86
338.82	H	-69.50	-57.00	-12.50
338.92	V	-66.02	-57.00	-9.02
451.12	V	-69.36	-57.00	-12.36
480.02	H	-68.93	-57.00	-11.93
604.58	V	-70.91	-57.00	-13.91
611.63	H	-69.98	-57.00	-12.98
820.69	V	-67.95	-57.00	-10.95
871.14	H	-66.89	-57.00	-9.89

##### 2MBaud

Spurious Emission Frequency Range	30MHz ~ 1GHz	Operating Channel	38
-----------------------------------	--------------	-------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
53.15	V	-61.51	-57.00	-4.51
99.60	H	-72.56	-57.00	-15.56
225.26	V	-73.04	-57.00	-16.04
226.26	H	-68.63	-57.00	-11.63
342.62	H	-67.06	-57.00	-10.06
344.87	V	-66.48	-57.00	-9.48
445.82	V	-66.01	-57.00	-9.01
479.97	H	-63.90	-57.00	-6.90
594.13	H	-69.63	-57.00	-12.63
616.63	V	-69.39	-57.00	-12.39
851.14	H	-66.94	-57.00	-9.94
883.94	V	-67.20	-57.00	-10.20



**Mode B**  
**1MBaud**

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	39
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
47.75	V	-70.29	-57.00	-13.29
109.60	H	-75.90	-57.00	-18.90
180.01	V	-63.47	-57.00	-6.47
196.31	H	-68.58	-57.00	-11.58
300.01	V	-63.91	-57.00	-6.91
331.17	H	-67.65	-57.00	-10.65
351.27	V	-69.57	-57.00	-12.57
479.97	H	-70.87	-57.00	-13.87
540.03	V	-67.09	-57.00	-10.09
606.43	H	-70.30	-57.00	-13.30
849.99	H	-66.49	-57.00	-9.49
854.14	V	-67.21	-57.00	-10.21

**2MBaud**

<b>Spurious Emission Frequency Range</b>	30MHz ~ 1GHz	<b>Operating Channel</b>	38
--	--------------	--------------------------	----

Spurious Emission Level				
Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
74.40	H	-69.72	-57.00	-12.72
75.25	V	-70.22	-57.00	-13.22
180.01	V	-62.28	-57.00	-5.28
232.31	H	-65.08	-57.00	-8.08
348.02	V	-68.24	-57.00	-11.24
352.47	H	-66.87	-57.00	-9.87
445.77	H	-69.25	-57.00	-12.25
445.92	V	-63.94	-57.00	-6.94
591.08	H	-69.67	-57.00	-12.67
598.93	V	-69.08	-57.00	-12.08
839.89	V	-67.25	-57.00	-10.25
863.04	H	-66.06	-57.00	-9.06

# Above 1 GHz Worst-case Data

## Mode A

### 1MBaud

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	0, 39
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
0	4804.05	H	-57.19	-47.00	-10.19
	4804.30	V	-56.94	-47.00	-9.94
39	4960.25	V	-57.51	-47.00	-10.51
	4960.60	H	-57.22	-47.00	-10.22

### 2MBaud

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	1, 38
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
1	4808.43	H	-56.49	-47.00	-9.49
	4808.68	V	-57.29	-47.00	-10.29
38	4956.17	H	-57.33	-47.00	-10.33
	4956.57	V	-56.84	-47.00	-9.84

**Mode B**  
**1MBaud**

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	0, 39
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
0	4804.08	V	-56.87	-47.00	-9.87
	4804.96	H	-57.98	-47.00	-10.98
39	4960.60	V	-57.67	-47.00	-10.67
	4960.86	H	-57.15	-47.00	-10.15

**2MBaud**

<b>Spurious Emission Frequency Range</b>	1GHz ~ 12.75GHz	<b>Operating Channel</b>	1, 38
--	-----------------	--------------------------	-------

Spurious Emission Level					
Channel	Frequency (MHz)	Antenna Polarization	Level (dBm)	Limit (dBm)	Margin (dB)
1	4808.49	V	-57.54	-47.00	-10.54
	4808.76	H	-57.26	-47.00	-10.26
38	4956.28	V	-57.25	-47.00	-10.25
	4956.31	H	-57.09	-47.00	-10.09

## 4.8 Receiver Blocking

### 4.8.1 Limit of Receiver Blocking

This requirement applies to all receiver categories.

Receiver Category 1 Equipment			
Wanted signal mean power from companion device (dBm) (see notes 1 to 4)	Blocking Signal Frequency (MHz)	Blocking Signal Power (dBm) (see note 4)	Type of blocking signal
(-133 dBm + 10 × log <sub>10</sub> (OCBW)) or -68 dBm whichever is less (see note 2)	2 380 2 504	-34	CW
(-139 dBm + 10 × log <sub>10</sub> (OCBW)) or -74 dBm whichever is less (see note 3)	2 300 2 330 2 360 2 524 2 584 2 674		
<p>NOTE 1: OCBW is in Hz.</p> <p>NOTE 2: In case of radiated measurements using a companion device and the level of the wanted signal from the companion device cannot be determined, a relative test may be performed using a wanted signal up to Pmin + 26 dB where Pmin is the minimum level of wanted signal required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.</p> <p>NOTE 3: In case of radiated measurements using a companion device and the level of the wanted signal from the companion device cannot be determined, a relative test may be performed using a wanted signal up to Pmin + 20 dB where Pmin is the minimum level of wanted signal required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.</p> <p>NOTE 4: The level specified is the level at the UUT receiver input assuming a 0 dBi antenna assembly gain. In case of conducted measurements, this level has to be corrected for the (in-band) antenna assembly gain (G). In case of radiated measurements, this level is equivalent to a power flux density (PFD) in front of the UUT antenna with the UUT being configured / positioned as recorded in clause 5.4.3.2.2.</p>			

Receiver Category 2 Equipment			
Wanted signal mean power from companion device (dBm) (see notes 1 to 3)	Blocking Signal Frequency (MHz)	Blocking Signal Power (dBm) (see note 3)	Type of blocking signal
$(-139 \text{ dBm} + 10 \times \log_{10}(\text{OCBW}) + 10)$ or $(-74 \text{ dBm} + 10)$ whichever is less (see note 2)	2 380 2 504 2 300 2 584	-34	CW

NOTE 1: OCBW is in Hz.

NOTE 2: In case of radiated measurements using a companion device and the level of the wanted signal from the companion device cannot be determined, a relative test may be performed using a wanted signal up to  $P_{\text{min}} + 26 \text{ dB}$  where  $P_{\text{min}}$  is the minimum level of wanted signal required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.

NOTE 3: The level specified is the level at the UUT receiver input assuming a 0 dBi antenna assembly gain. In case of conducted measurements, this level has to be corrected for the (in-band) antenna assembly gain (G). In case of radiated measurements, this level is equivalent to a power flux density (PFD) in front of the UUT antenna with the UUT being configured / positioned as recorded in clause 5.4.3.2.2.

Receiver Category 3 Equipment			
Wanted signal mean power from companion device (dBm) (see notes 1 to 3)	Blocking Signal Frequency (MHz)	Blocking Signal Power (dBm) (See note 3)	Type of blocking signal
$(-139 \text{ dBm} + 10 \times \log_{10}(\text{OCBW}) + 20)$ or $(-74 \text{ dBm} + 20)$ whichever is less (see note 2)	2 380 2 504 2 300 2 584	-34	CW

NOTE 1: OCBW is in Hz.

NOTE 2: In case of radiated measurements using a companion device and the level of the wanted signal from the companion device cannot be determined, a relative test may be performed using a wanted signal up to  $P_{\text{min}} + 26 \text{ dB}$  where  $P_{\text{min}}$  is the minimum level of wanted signal required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.

NOTE 3: The level specified is the level at the UUT receiver input assuming a 0 dBi antenna assembly gain. In case of conducted measurements, this level has to be corrected for the (in-band) antenna assembly gain (G). In case of radiated measurements, this level is equivalent to a power flux density (PFD) in front of the UUT antenna with the UUT being configured / positioned as recorded in clause 5.4.3.2.2.

#### 4.8.2 Test Procedure


Refer to chapter 5.4.11 of EN 300 328 V2.2.2.

Measurement Method	
<input checked="" type="checkbox"/> Conducted measurement	<input type="checkbox"/> Radiated measurement

#### 4.8.3 Deviation from Test Standard

No deviation.

#### 4.8.4 Test Setup Configuration



#### 4.8.5 Test Results



Receiver Category 1 Equipment							
Minimum Performance Criterion:			PER or FER ≤10%				
Receiver Blocking Measure Of The Capability							
Operation Mode	Operating Frequency (MHz)	Wanted Signal Mean Power From Companion Device (dBm) (Note 1 & 2)	Blocking Signal Frequency (MHz)	Blocking Signal Frequency Shift (MHz) (Note 3)	Blocking Signal Power (dBm) (Note 2)	PER (%)	Test Result
BT LE-1M with 125KHz	2402	-70.07	2380	-	-31.2	0.7	Pass
		-76.07	2300	-	-31.2	1.5	Pass
			2330	-	-31.2	1.9	Pass
			2360	-	-31.2	2.6	Pass
	2480	-70.07	2504	-	-31.2	1.2	Pass
		-76.07	2524	-	-31.2	0.8	Pass
			2584	-	-31.2	1.1	Pass
			2674	-	-31.2	1.3	Pass

Notes:

1. Wanted signal level was calculated based on the formula, which corresponds to OCBW. OCBW is 1.03 MHz.
2. In conducted measurements, the blocking signal power level has to be corrected for the (in-band) antenna assembly gain (G) at the antenna connector. The antenna gain is 2.8 dBi.
3. If the performance criteria is not met, those frequencies of the blocking signal has been increased/decreased with a value equal to the Occupied Channel Bandwidth except the blocking frequencies 2380, 2504MHz shall be increased/decreased with a value equal to 10MHz also if the frequency offset is more than 7MHz, the level of the wanted signal shall be increased by 3dB.



## 5 Photographs of the Test Configuration

TX / RX Spurious Emission Test  
Mode A





Mode B



## Appendix – Information of the Testing Laboratories

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are FCC recognized accredited test firms and accredited and approved according to ISO/IEC 17025.

If you have any comments, please feel free to contact us at the following:

### **Lin Kou EMC/RF Lab**

Tel: 886-2-26052180

Fax: 886-2-26051924

### **Hsin Chu EMC/RF/Telecom Lab**

Tel: 886-3-6668565

Fax: 886-3-6668323

### **Hwa Ya EMC/RF/Safety Lab**

Tel: 886-3-3183232

Fax: 886-3-3270892

**Email:** [service.adt@tw.bureauveritas.com](mailto:service.adt@tw.bureauveritas.com)

**Web Site:** [www.bureauveritas-adt.com](http://www.bureauveritas-adt.com)

The address and road map of all our labs can be found in our web site also.

--- END ---