

EFR32xG14 Wireless Gecko Reference Manual



The Wireless Gecko portfolio of SoCs (EFR32) includes Mighty Gecko (EFR32MG14), Blue Gecko (EFR32BG14), and Flex Gecko (EFR32FG14) families. With support for Zigbee[®], Thread, Bluetooth Low Energy (BLE) and proprietary protocols, the Wireless Gecko portfolio is ideal for enabling energy-friendly wireless networking for IoT devices.

The single-die solution provides industry-leading energy efficiency, ultra-fast wakeup times, a scalable high-power amplifier, an integrated balun and no-compromise MCU features.

KEY FEATURES

- 32-bit ARM® Cortex-M4 core with 40 MHz maximum operating frequency
- Scalable Memory and Radio configuration options available in several footprint compatible QFN packages
- 12-channel Peripheral Reflex System enabling autonomous interaction of MCU peripherals
- · Autonomous Hardware Crypto Accelerator
- Integrated balun for 2.4 GHz and integrated PA with up to 19 dBm transmit power for 2.4 GHz and 20 dBm transmit power for Sub-GHz radios
- · Integrated DC-DC with RF noise mitigation




Table of Contents

1.	. About This Document		 							26
	1.1 Introduction		 	 						.26
	1.2 Conventions		 	 						.26
	1.3 Related Documentation		 	 	-					.27
2.	. System Overview		 							28
	2.1 Introduction		 	 						.28
	2.2 Block Diagrams		 	 						.29
	2.3 MCU Features Overview		 	 						.30
	2.4 Oscillators and Clocks		 	 						.32
	2.5 RF Frequency Synthesizer		 	 						.32
	2.6 Modulation Modes		 	 						.32
	2.7 Transmit Mode		 	 						.33
	2.8 Receive Mode		 	 						.33
	2.9 Data Buffering		 	 						.33
	2.10 Unbuffered Data Transfer		 	 						.33
	2.11 Frame Format Support		 	 						.33
	2.12 Hardware CRC Support		 	 						.34
	2.13 Convolutional Encoding / Decoding		 	 						.34
	2.14 Binary Block Encoding / Decoding		 	 						.34
	2.15 Data Encryption and Authentication		 	 						.35
	2.16 Timers		 	 						.36
	2.17 RF Test Modes		 	 						.36
3.	. System Processor		 	 						. 37
	3.1 Introduction		 	 						.37
	3.2 Features		 	 						.38
	3.3 Functional Description		 	 						.38
	3.3.1 Interrupt Operation									
	3.3.2 Interrupt Request Lines (IRQ)		 	 	-	•	•	•	•	.40
4.	. Memory and Bus System		 	 •		•	•	•	•	41
	4.1 Introduction									
	4.2 Functional Description									
	4.2.1 Peripheral Non-Word Access Behavior 4.2.2 Bit-banding									
	4.2.3 Peripheral Bit Set and Clear									
	4.2.4 Peripherals									
	4.2.5 Bus Matrix									
	4.3 Access to Low Energy Peripherals (Asynchronous Rec	gisters)	 	 						.50

4.3.1 Writing							
4.3.2 Reading							
4.3.3 FREEZE Register							.53
4.4 Flash			•				.53
4.5 SRAM							.54
4.6 DI Page Entry Map							.55
4.7 DI Page Entry Description							.57
4.7.1 CAL - CRC of DI-page and calibration temperature							
4.7.2 MODULEINFO - Module trace information							
4.7.3 EXTINFO - External Component description							.58
4.7.4 EUI48L - EUI48 OUI and Unique identifier							.59
4.7.5 EUI48H - OUI							
4.7.6 CUSTOMINFO - Custom information							.59
4.7.7 MEMINFO - Flash page size and misc. chip information							.60
4.7.8 UNIQUEL - Low 32 bits of device unique number							
4.7.9 UNIQUEH - High 32 bits of device unique number							
4.7.10 MSIZE - Flash and SRAM Memory size in kB							
4.7.11 PART - Part description							
4.7.12 DEVINFOREV - Device information page revision							
4.7.13 EMUTEMP - EMU Temperature Calibration Information							
4.7.14 ADC0CAL0 - ADC0 calibration register 0							
4.7.15 ADC0CAL1 - ADC0 calibration register 1							
4.7.16 ADC0CAL1 - ADC0 calibration register 2							
4.7.17 ADC0CAL2 - ADC0 calibration register 3							
G							
4.7.18 HFRCOCALO - HFRCO Calibration Register (4 MHz)							
4.7.19 HFRCOCAL3 - HFRCO Calibration Register (7 MHz)							
4.7.20 HFRCOCAL6 - HFRCO Calibration Register (13 MHz)							
4.7.21 HFRCOCAL7 - HFRCO Calibration Register (16 MHz)							
4.7.22 HFRCOCAL8 - HFRCO Calibration Register (19 MHz)							
4.7.23 HFRCOCAL10 - HFRCO Calibration Register (26 MHz)							.73
4.7.24 HFRCOCAL11 - HFRCO Calibration Register (32 MHz)							
4.7.25 HFRCOCAL12 - HFRCO Calibration Register (38 MHz)							
4.7.26 AUXHFRCOCAL0 - AUXHFRCO Calibration Register (4 MHz)							
• • • • • • • • • • • • • • • • • • • •							
4.7.28 AUXHFRCOCAL6 - AUXHFRCO Calibration Register (13 MHz)							
4.7.29 AUXHFRCOCAL7 - AUXHFRCO Calibration Register (16 MHz)							.79
4.7.30 AUXHFRCOCAL8 - AUXHFRCO Calibration Register (19 MHz)							.80
4.7.31 AUXHFRCOCAL10 - AUXHFRCO Calibration Register (26 MHz)							.81
4.7.32 AUXHFRCOCAL11 - AUXHFRCO Calibration Register (32 MHz)							.82
4.7.33 AUXHFRCOCAL12 - AUXHFRCO Calibration Register (38 MHz)							.83
4.7.34 VMONCAL0 - VMON Calibration Register 0							.84
4.7.35 VMONCAL1 - VMON Calibration Register 1							.85
4.7.36 VMONCAL2 - VMON Calibration Register 2							
4.7.37 IDAC0CAL0 - IDAC0 Calibration Register 0							
4.7.38 IDAC0CAL1 - IDAC0 Calibration Register 1							
4.7.39 DCDCLNVCTRL0 - DCDC Low-noise VREF Trim Register 0 .							
4.7.40 DCDCLPVCTRL0 - DCDC Low-power VREF Trim Register 0 .							
= = = = = = = =	-	•	-	•	-	-	

	4.7.41	DCDCLPVCTRL1 - DCDC Low-power VREF Trim Register 1		-	•		.00
	4.7.42	DCDCLPVCTRL2 - DCDC Low-power VREF Trim Register 2					.91
	4.7.43	DCDCLPVCTRL3 - DCDC Low-power VREF Trim Register 3					.92
	4.7.44	DCDCLPCMPHYSSEL0 - DCDC LPCMPHYSSEL Trim Register 0					.92
	4.7.45	DCDCLPCMPHYSSEL1 - DCDC LPCMPHYSSEL Trim Register 1					
	4.7.46	VDAC0MAINCAL - VDAC0 Cals for Main Path					
	4.7.47						
	4.7.48	VDAC0CH1CAL - VDAC0 CH1 Error Cal					
	4.7.49						
	4.7.50						.98
	4.7.51	•					
	4.7.52	OPA0CAL3 - OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=1			Ċ		100
	4.7.53	OPA1CAL0 - OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=1					101
	4.7.54	OPA1CAL1 - OPA1 Calibration Register for DRIVESTRENGTH 1, INCBW=1					102
	4.7.55	OPA1CAL2 - OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=1					103
	4.7.56	OPA1CAL3 - OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=1					104
	4.7.57	OPA0CAL4 - OPA0 Calibration Register for DRIVESTRENGTH 0, INCBW=0					105
	4.7.58	OPA0CAL5 - OPA0 Calibration Register for DRIVESTRENGTH 1, INCBW=0					106
	4.7.59						107
		OPACCAL 7 OPAC Calibration Register for DRIVESTRENGTH 2, INCRIN-0			•		
	4.7.60	OPA0CAL7 - OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=0					108
	4.7.61	OPA1CAL4 - OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=0					109
	4.7.62	· · · · · · · · · · · · · · · · · · ·					110
	4.7.63	OPA1CAL6 - OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=0					111
	4.7.64	OPA1CAL7 - OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=0	•	٠		-	112
E	Padia Ti	ansceiver					112
ວ.	Naulo II	ansceiver	•		•	•	113
Э.	5.1 Introd						
	5.1 Introd	luction					. 114
	5.1 Introd	ebug Interface					. 114 115
	5.1 Introd	ebug Interface					. 114 115
	5.1 Introd	luction					. 114 115 . 115
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu	luction					. 114 115 . 115 . 115
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func	duction					. 114 115 . 115 . 115
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E	duction					. 114 115 . 115 . 115 . 116
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E	duction ebug Interface duction ires tional Description Debug Pins			• •		. 114 115 . 115 . 115 . 115 . 116 . 116
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.3 A	duction					. 114 115 . 115 . 115 . 116 . 116 . 116
	5.1 Introd DBG - D 6.1 Introd 6.2 Feature 6.3 Functions 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E	duction ebug Interface duction ires tional Description Debug Pins Debug and EM2 Deep Sleep/EM3 Stop Authentication Access Point					. 114 115 . 115 . 115 . 116 . 116 . 116
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E 6.3.5 A	duction ebug Interface duction ures tional Description Debug Pins Debug and EM2 Deep Sleep/EM3 Stop authentication Access Point Debug Lock					. 114 115 . 115 . 115 . 116 . 116 . 116 . 117 . 117
	5.1 Introd DBG - D 6.1 Introd 6.2 Feature 6.3 Functions 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E 6.3.5 A 6.3.6 E	duction duc					. 114 115 . 115 . 115 . 116 . 116 . 116 . 117 . 117
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E	luction ebug Interface fluction f					. 114 115 . 115 . 115 . 116 . 116 . 116 . 117 . 117 . 118 . 118
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E 6.4 Regis	duction duction duction duction debug Interface duction description debug Pins debug Pins debug and EM2 Deep Sleep/EM3 Stop duthentication Access Point debug Lock dAP Lock debugger Reads of Actionable Registers debug Recovery deter Map					114 115 115 115 116 116 116 117 117 118 118
	5.1 Introd DBG - D 6.1 Introd 6.2 Feature 6.3 Func 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis	duction ductio					. 114 115 . 115 . 115 . 116 . 116 . 117 . 117 . 118 . 118 . 119
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis 6.5.1 A	duction duc					. 114 115 . 115 . 115 . 116 . 116 . 117 . 117 . 118 . 118 . 119 . 119
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis 6.5.1 A 6.5.2	duction duc					. 114 115 . 115 . 115 . 116 . 116 . 117 . 117 . 118 . 118 . 119 . 119 . 119
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.3 A 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis 6.5.1 A 6.5.2 A 6.5.3 A	duction duc					. 114 115 . 115 . 115 . 116 . 116 . 117 . 117 . 118 . 118 . 119 . 119 . 120
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E 6.4 Regis 6.5.1 A 6.5.2 A 6.5.3 A 6.5.4 A	duction ebug Interface duction ducti					114 115 115 115 116 116 117 118 118 118 119 119 120 120
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis 6.5.1 E 6.5.2 E 6.5.3 E 6.5.4 E 6.5.5 E	duction debug Interface duction duct					114 115 115 115 116 116 117 118 118 118 119 119 120 120 121
	5.1 Introd DBG - D 6.1 Introd 6.2 Featu 6.3 Func 6.3.1 E 6.3.2 E 6.3.4 E 6.3.5 A 6.3.6 E 6.3.7 E 6.4 Regis 6.5 Regis 6.5.1 A 6.5.2 A 6.5.3 A 6.5.4 A 6.5.5 A 6.5.5 A	duction ebug Interface duction ducti					114 115 115 115 116 116 117 118 118 118 119 119 120 120 121

	6.5.8 AAP_CRCRESULT - CRC Result Register	
7.	MSC - Memory System Controller	124
	7.1 Introduction	. 124
	7.2 Features	
	7.3 Functional Description	
	7.3.1 User Data (UD) Page Description	
	7.3.2 Lock Bits (LB) Page Description	
	7.3.3 Device Information (DI) Page	
	7.3.4 Bootloader	
	7.3.5 Post-reset Behavior	
	7.3.6 Flash Startup	
	7.3.7 Wait-states	. 128
	7.3.8 Suppressed Conditional Branch Target Prefetch (SCBTP)	129
	7.3.9 Cortex-M4 If-Then Block Folding	
	7.3.10 Instruction Cache	
	7.3.11 Low Voltage Flash Read	
	7.3.12 Erase and Write Operations	131
	7.4 Register Map	132
	7.5 Register Description	. 133
	7.5.1 MSC_CTRL - Memory System Control Register	. 133
	7.5.2 MSC_READCTRL - Read Control Register	134
	7.5.3 MSC_WRITECTRL - Write Control Register	
	7.5.4 MSC_WRITECMD - Write Command Register	
	7.5.5 MSC_ADDRB - Page Erase/Write Address Buffer	
	7.5.6 MSC_WDATA - Write Data Register	
	7.5.7 MSC_STATUS - Status Register	
	7.5.8 MSC_IF - Interrupt Flag Register	
	7.5.9 MSC_IFS - Interrupt Flag Set Register	
	7.5.10 MSC_IFC - Interrupt Flag Clear Register	
	7.5.11 MSC_IEN - Interrupt Enable Register	
	7.5.12 MSC_LOCK - Configuration Lock Register	
	7.5.13 MSC_CACHECMD - Flash Cache Command Register	
	7.5.14 MSC_CACHEMISSES - Cache Misses Performance Counter	
	7.5.16 MSC MASSLOCK - Mass Erase Lock Register	
	7.5.17 MSC_STARTUP - Startup Control	
	7.5.18 MSC CMD - Command Register	
	7.5.19 MSC BOOTLOADERCTRL - Bootloader Read and Write Enable, Write Once Register	
	7.5.20 MSC_AAPUNLOCKCMD - Software Unlock AAP Command Register	
	7.5.21 MSC_CACHECONFIG0 - Cache Configuration Register 0	
8.	 LDMA - Linked DMA Controller	151
	8.1 Introduction	
	8.1.1 Features	
	8.2 Block Diagram	
	0.4 DIUUN DIQUI (III)	. เบง

8.3 Functional Description	154
8.3.1 Channel Descriptor	154
8.3.2 Channel Configuration	159
8.3.3 Channel Select Configuration	159
8.3.4 Starting a Transfer	159
8.3.5 Managing Transfer Errors	160
8.3.6 Arbitration	
8.3.7 Channel Descriptor Data Structure	
8.3.8 Interaction With the EMU	
8.3.9 Interrupts	
8.3.10 Debugging	166
8.4 Examples	166
8.4.1 Single Direct Register DMA Transfer	167
8.4.2 Descriptor Linked List	168
8.4.3 Single Descriptor Looped Transfer	170
8.4.4 Descriptor List With Looping	171
8.4.5 Simple Inter-Channel Synchronization	172
8.4.6 2D Copy	174
8.4.7 Ping-Pong	176
8.4.8 Scatter-Gather	177
8.5 Register Map	178
8.6 Register Description	179
8.6.1 LDMA_CTRL - DMA Control Register	
8.6.2 LDMA_STATUS - DMA Status Register	180
8.6.3 LDMA_SYNC - DMA Synchronization Trigger Register (Single-Cycle RMW)	181
8.6.4 LDMA_CHEN - DMA Channel Enable Register (Single-Cycle RMW)	
8.6.5 LDMA_CHBUSY - DMA Channel Busy Register	182
8.6.6 LDMA_CHDONE - DMA Channel Linking Done Register (Single-Cycle RMW)	182
8.6.7 LDMA_DBGHALT - DMA Channel Debug Halt Register	183
8.6.8 LDMA_SWREQ - DMA Channel Software Transfer Request Register	183
8.6.9 LDMA_REQDIS - DMA Channel Request Disable Register	
8.6.10 LDMA_REQPEND - DMA Channel Requests Pending Register	
8.6.11 LDMA_LINKLOAD - DMA Channel Link Load Register	
8.6.12 LDMA_REQCLEAR - DMA Channel Request Clear Register	
8.6.13 LDMA_IF - Interrupt Flag Register	
8.6.14 LDMA_IFS - Interrupt Flag Set Register	
8.6.15 LDMA_IFC - Interrupt Flag Clear Register	
8.6.16 LDMA_IEN - Interrupt Enable Register	
8.6.17 LDMA_CHx_REQSEL - Channel Peripheral Request Select Register	
8.6.18 LDMA_CHx_CFG - Channel Configuration Register	
8.6.19 LDMA_CHx_LOOP - Channel Loop Counter Register	
8.6.20 LDMA_CHx_CTRL - Channel Descriptor Control Word Register	
8.6.21 LDMA_CHx_SRC - Channel Descriptor Source Data Address Register	
8.6.22 LDMA_CHx_DST - Channel Descriptor Destination Data Address Register	
8.6.23 LDMA_CHx_LINK - Channel Descriptor Link Structure Address Register	197
9. RMU - Reset Management Unit	198
9.1 Introduction	198

9.2 Features	98
9.3 Functional Description 19 9.3.1 Reset Levels 20 9.3.2 RMU_RSTCAUSE Register 20 9.3.3 Power-On Reset (POR) 20 9.3.4 Brown-Out Detector (BOD) 20 9.3.5 RESETn Pin Reset 20 9.3.6 Watchdog Reset 20 9.3.7 Lockup Reset 20 9.3.8 System Reset Request 20 9.3.9 Reset State 20	00 01 02 02 03 03 03 03
9.3.10 Register Reset Signals	
9.4 Register Map	
9.5 Register Description .20 9.5.1 RMU_CTRL - Control Register .20 9.5.2 RMU_RSTCAUSE - Reset Cause Register .20 9.5.3 RMU_CMD - Command Register .20 9.5.4 RMU_RST - Reset Control Register .20 9.5.5 RMU_LOCK - Configuration Lock Register .20	06 08 09 09
10. EMU - Energy Management Unit......................21	11
10.1 Introduction	11
10.2 Features	12
10.3 Functional Description 2' 10.3.1 Energy Modes 2' 10.3.2 Entering Low Energy Modes 2' 10.3.3 Exiting a Low Energy Mode 2' 10.3.4 Power Configurations 2' 10.3.5 DC-to-DC Interface 2' 10.3.6 Analog Peripheral Power Selection 2' 10.3.7 Digital LDO Power Selection 2' 10.3.8 IOVDD Connection. 2' 10.3.9 Voltage Scaling 2' 10.3.10 EM2/EM3 Peripheral Retention Disable 2' 10.3.11 Brown Out Detector (BOD) 2' 10.3.12 Voltage Monitor (VMON) 2' 10.3.13 Powering Off SRAM Blocks 2' 10.3.14 Temperature Sensor 2' 10.3.15 Registers latched in EM4 2' 10.3.16 Register Resets 2'	14 18 20 21 25 27 28 29 31 32 33 33 34 34
10.4 Register Map	
10.5 Register Description . 23 10.5.1 EMU_CTRL - Control Register . 23 10.5.2 EMU_STATUS - Status Register . 23 10.5.3 EMU_LOCK - Configuration Lock Register . 24 10.5.4 EMU_RAMOCTRL - Memory Control Register . 24	37 39

10.5.5 EMU_CMD - Command Register	. 242
10.5.6 EMU_EM4CTRL - EM4 Control Register	. 243
10.5.7 EMU_TEMPLIMITS - Temperature Limits for Interrupt Generation	. 244
10.5.8 EMU_TEMP - Value of Last Temperature Measurement	. 244
10.5.9 EMU_IF - Interrupt Flag Register	. 245
10.5.10 EMU_IFS - Interrupt Flag Set Register	247
10.5.11 EMU_IFC - Interrupt Flag Clear Register	. 249
10.5.12 EMU_IEN - Interrupt Enable Register	. 251
10.5.13 EMU_PWRLOCK - Regulator and Supply Lock Register	253
10.5.14 EMU_PWRCTRL - Power Control Register	. 254
10.5.15 EMU_DCDCCTRL - DCDC Control	255
10.5.16 EMU_DCDCMISCCTRL - DCDC Miscellaneous Control Register	256
10.5.17 EMU_DCDCZDETCTRL - DCDC Power Train NFET Zero Current Detector Control	
Register	. 258
10.5.18 EMU_DCDCCLIMCTRL - DCDC Power Train PFET Current Limiter Control Register	. 259
10.5.19 EMU_DCDCLNCOMPCTRL - DCDC Low Noise Compensator Control Register	260
10.5.20 EMU_DCDCLNVCTRL - DCDC Low Noise Voltage Register	
10.5.21 EMU_DCDCLPVCTRL - DCDC Low Power Voltage Register	. 262
10.5.22 EMU_DCDCLPCTRL - DCDC Low Power Control Register	263
10.5.23 EMU_DCDCLNFREQCTRL - DCDC Low Noise Controller Frequency Control	. 264
10.5.24 EMU_DCDCSYNC - DCDC Read Status Register	264
10.5.25 EMU_VMONAVDDCTRL - VMON AVDD Channel Control	. 265
10.5.26 EMU_VMONALTAVDDCTRL - Alternate VMON AVDD Channel Control	. 266
10.5.27 EMU_VMONDVDDCTRL - VMON DVDD Channel Control	. 267
10.5.28 EMU_VMONIO0CTRL - VMON IOVDD0 Channel Control	. 268
10.5.29 EMU_RAM1CTRL - Memory Control Register	. 269
10.5.30 EMU_RAM2CTRL - Memory Control Register	. 270
10.5.31 EMU_DCDCLPEM01CFG - Configuration Bits for Low Power Mode to Be Applied During EM01, This Field is Only Relevant If LP Mode is Used in EM01	
10.5.32 EMU_EM23PERNORETAINCMD - Clears Corresponding Bits in	
EM23PERNORETAINSTATUS Unlocking Access to Peripheral	. 272
10.5.33 EMU_EM23PERNORETAINSTATUS - Status Indicating If Peripherals Were Powered	
Down in EM23, Subsequently Locking Access to It	274
10.5.34 EMU_EM23PERNORETAINCTRL - When Set Corresponding Peripherals May Get	
Powered Down in EM23	276
11. CMU - Clock Management Unit	. 278
11.1 Introduction	. 278
11.2 Features	
11.3 Functional Description	
11.3.1 System Clocks	
11.3.2 Oscillators	
11.3.3 Configuration for Operating Frequencies	
11.3.4 Energy Modes	
11.3.5 Clock Output on a Pin	
11.3.6 Clock Input From a Pin	
11.3.7 Clock Output on PRS	
11.3.8 Frror Handling	303

		Interrupts	
	11.3.10	Wake-up	304
	11.3.11	Protection	.304
11	.4 Reg	ister Map	. 305
11	.5 Reg	ister Description	307
	11.5.1	CMU_CTRL - CMU Control Register	.307
	11.5.2	CMU_HFRCOCTRL - HFRCO Control Register	309
		CMU_AUXHFRCOCTRL - AUXHFRCO Control Register	
		CMU_LFRCOCTRL - LFRCO Control Register	
		CMU_HFXOCTRL - HFXO Control Register	
		CMU_HFXOSTARTUPCTRL - HFXO Startup Control	
	11.5.7	CMU_HFXOSTEADYSTATECTRL - HFXO Steady State Control	317
		CMU_HFXOTIMEOUTCTRL - HFXO Timeout Control	
	11.5.9	CMU_LFXOCTRL - LFXO Control Register	. 321
		CMU_CALCTRL - Calibration Control Register	
	11.5.11	-	
	11.5.12	CMU_OSCENCMD - Oscillator Enable/Disable Command Register	
		CMU CMD - Command Register	
		CMU_DBGCLKSEL - Debug Trace Clock Select	
		CMU_HFCLKSEL - High Frequency Clock Select Command Register	
		CMU_LFACLKSEL - Low Frequency A Clock Select Register	
		CMU_LFBCLKSEL - Low Frequency B Clock Select Register	
		CMU_LFECLKSEL - Low Frequency E Clock Select Register	
	11.5.19		
	11.5.20	-	
	11.5.21		
		CMU IF - Interrupt Flag Register	
		CMU_IFS - Interrupt Flag Set Register	
		CMU IFC - Interrupt Flag Clear Register	
		CMU_IEN - Interrupt Enable Register	
		CMU_HFBUSCLKEN0 - High Frequency Bus Clock Enable Register 0	.343
	11.5.27	_	.344
		CMU_HFRADIOALTCLKEN0 - High Frequency Alternate Radio Peripheral Clock Enable	. 577
		Register 0	. 345
		•	. 345
	11.5.30		. 346
	11.5.31		. 346
	11.5.32		347
	11.5.32		348
		CMU_HFPERPRESC - High Frequency Peripheral Clock Prescaler Register	.348
	11.5.35		.349
		CMU_HFEXPPRESC - High Frequency Export Clock Prescaler Register	349
	11.5.36		.350
		_ ` ` ` ` ` ` ` ` ` ` ` ` ` ` ` ` ` ` `	
	11.5.38		.351
	11.5.39		.352
	11.5.40		352
		legister	353
	11.3.4 l	OIVIO OTINODUOT - OYIIGIIIGIIIZALIUH DUSY NEGISLEL	ააა

11.5.42 CMU_FREEZE - Freeze Register	. 356
11.5.43 CMU_PCNTCTRL - PCNT Control Register	. 357
11.5.44 CMU_ADCCTRL - ADC Control Register	. 358
11.5.45 CMU_ROUTEPEN - I/O Routing Pin Enable Register	
11.5.46 CMU_ROUTELOC0 - I/O Routing Location Register	. 360
11.5.47 CMU ROUTELOC1 - I/O Routing Location Register	. 361
11.5.48 CMU LOCK - Configuration Lock Register	. 362
_	
12. SMU - Security Management Unit	
12.1 Introduction	
12.2 Features	
12.3 Functional Description	. 364
12.3.1 PPU - Peripheral Protection Unit	. 364
12.3.2 Programming Model	.365
12.4 Register Map	. 366
12.5 Register Description	
12.5.1 SMU_IF - Interrupt Flag Register	
12.5.2 SMU_IFS - Interrupt Flag Set Register	
12.5.3 SMU IFC - Interrupt Flag Clear Register	
12.5.4 SMU_IEN - Interrupt Enable Register	
12.5.5 SMU_PPUCTRL - PPU Control Register	
12.5.6 SMU_PPUPATD0 - PPU Privilege Access Type Descriptor 0	
12.5.7 SMU_PPUPATD1 - PPU Privilege Access Type Descriptor 1	
12.5.8 SMU PPUFS - PPU Fault Status	
_	
13. RTCC - Real Time Counter and Calendar	. 375
13.1 Introduction	. 375
13.2 Features	. 375
13.3 Functional Description	. 376
13.3.1 Counter	
13.3.2 Capture/Compare Channels	
13.3.3 Interrupts and PRS Output	
13.3.4 Energy Mode Availability	
13.3.5 Register Lock	
13.3.6 Oscillator Failure Detection	
13.3.7 Retention Registers	
13.3.8 Debug Session	
•	
13.4 Register Map	
13.5 Register Description	
13.5.1 RTCC_CTRL - Control Register (Async Reg)	
13.5.2 RTCC_PRECNT - Pre-Counter Value Register (Async Reg)	
13.5.3 RTCC_CNT - Counter Value Register (Async Reg)	
13.5.4 RTCC_COMBCNT - Combined Pre-Counter and Counter Value Register	
13.5.5 RTCC_TIME - Time of Day Register (Async Reg)	
13.5.6 RTCC_DATE - Date Register (Async Reg)	
13.5.7 RTCC IF - RTCC Interrupt Flags	. 392

13.5.8 RTCC_IFS - Interrupt Flag Set Register	.393
13.5.9 RTCC_IFC - Interrupt Flag Clear Register	394
13.5.10 RTCC_IEN - Interrupt Enable Register	.395
13.5.11 RTCC_STATUS - Status Register	. 396
13.5.12 RTCC_CMD - Command Register (Async Reg)	.396
13.5.13 RTCC_SYNCBUSY - Synchronization Busy Register	.397
13.5.14 RTCC_POWERDOWN - Retention RAM Power-down Register (Async Reg)	.397
13.5.15 RTCC_LOCK - Configuration Lock Register (Async Reg)	. 398
13.5.16 RTCC_EM4WUEN - Wake Up Enable	.398
13.5.17 RTCC_CCx_CTRL - CC Channel Control Register (Async Reg)	
13.5.18 RTCC_CCx_CCV - Capture/Compare Value Register (Async Reg)	
13.5.19 RTCC_CCx_TIME - Capture/Compare Time Register (Async Reg)	
13.5.20 RTCC_CCx_DATE - Capture/Compare Date Register (Async Reg)	
13.5.21 RTCC_RETx_REG - Retention Register	. 403
14. WDOG - Watchdog Timer	404
14.1 Introduction	. 404
14.2 Features	. 404
14.3 Functional Description	. 404
14.3.1 Clock Source	
14.3.2 Debug Functionality	
14.3.3 Energy Mode Handling	
14.3.4 Register Access	
14.3.5 Warning Interrupt	
14.3.6 Window Interrupt	
14.3.7 PRS as Watchdog Clear	
14.3.8 PRS Rising Edge Monitoring	407
14.4 Register Map	. 408
14.5 Register Description	. 409
14.5.1 WDOG_CTRL - Control Register (Async Reg)	. 409
14.5.2 WDOG_CMD - Command Register (Async Reg)	
14.5.3 WDOG_SYNCBUSY - Synchronization Busy Register	413
14.5.4 WDOGn_PCHx_PRSCTRL - PRS Control Register (Async Reg)	. 414
14.5.5 WDOG_IF - Watchdog Interrupt Flags	. 415
14.5.6 WDOG_IFS - Interrupt Flag Set Register	. 416
14.5.7 WDOG_IFC - Interrupt Flag Clear Register	.417
14.5.8 WDOG_IEN - Interrupt Enable Register	.418
15. PRS - Peripheral Reflex System	. 419
15.1 Introduction	. 419
15.2 Features	. 419
15.3 Functional Description	. 420
15.3.1 Channel Functions	
15.3.2 Producers	
15.3.3 Consumers	
15.3.4 Event on PRS	
15.3.5 DMA Request on PRS	

15.3.6 Example	.424
15.4 Register Map	. 424
15.5 Register Description	425
15.5.1 PRS SWPULSE - Software Pulse Register	
15.5.2 PRS_SWLEVEL - Software Level Register	
15.5.3 PRS_ROUTEPEN - I/O Routing Pin Enable Register	
15.5.4 PRS_ROUTELOC0 - I/O Routing Location Register	
15.5.5 PRS ROUTELOC1 - I/O Routing Location Register	
15.5.6 PRS_ROUTELOC2 - I/O Routing Location Register	
15.5.7 PRS_CTRL - Control Register	
15.5.8 PRS_DMAREQ0 - DMA Request 0 Register	
15.5.9 PRS_DMAREQ1 - DMA Request 1 Register	
15.5.10 PRS_PEEK - PRS Channel Values	
15.5.11 PRS_CHx_CTRL - Channel Control Register	
16. PCNT - Pulse Counter	445
16.1 Introduction	445
16.2 Features	445
16.3 Functional Description	
16.3.1 Pulse Counter Modes	
16.3.2 Hysteresis	
16.3.3 Auxiliary Counter	
16.3.4 Triggered Compare and Clear	
16.3.5 Register Access.	
16.3.6 Clock Sources	
16.3.7 Input Filter	
16.3.8 Edge Polarity	
16.3.9 PRS and PCNTn_S0IN,PCNTn_S1IN Inputs	
16.3.10 Interrupts	
16.3.11 Cascading Pulse Counters	
16.4 Register Map	
16.5 Register Description	
16.5.1 PCNTn_CTRL - Control Register (Async Reg)	
16.5.2 PCNTn_CMD - Command Register (Async Reg)	
16.5.3 PCNTn_STATUS - Status Register	
16.5.4 PCNTn_CNT - Counter Value Register	
16.5.5 PCNTn_TOP - Top Value Register	
16.5.6 PCNTn_TOPB - Top Value Buffer Register (Async Reg)	
16.5.7 PCNTn_IF - Interrupt Flag Register	
16.5.8 PCNTn_IFS - Interrupt Flag Set Register	
16.5.9 PCNTn_IFC - Interrupt Flag Clear Register	
16.5.10 PCNTn_IEN - Interrupt Enable Register	
16.5.11 PCNTn_ROUTELOC0 - I/O Routing Location Register	
16.5.12 PCNTn_FREEZE - Freeze Register	
16.5.13 PCNTn_SYNCBUSY - Synchronization Busy Register	
16.5.14 PCNTn_AUXCNT - Auxiliary Counter Value Register	
16.5.15 PCNTn_INPUT - PCNT Input Register	.475

16.5.16 PCNTn_OVSCFG - Oversampling Config Register (Async Reg)	476
17. I2C - Inter-Integrated Circuit Interface	. 477
17.1 Introduction	. 477
17.2 Features	. 477
17.3 Functional Description	. 478
17.3.1 I2C-Bus Overview	
17.3.2 Enable and Reset	. 483
17.3.3 Safely Disabling and Changing Slave Configuration	. 483
17.3.4 Clock Generation	
17.3.5 Arbitration	
17.3.6 Buffers	
17.3.7 Master Operation	
17.3.8 Bus States	
17.3.9 Slave Operation	
17.3.10 Transfer Automation	
17.3.11 Osing 10-bit Addresses	
17.3.13 DMA Support	
17.3.14 Interrupts	
17.3.15 Wake-up	
17.4 Register Map	
17.5 Register Description	
17.5.1 I2Cn_CTRL - Control Register	
17.5.2 I2Cn_CMD - Command Register	
17.5.3 I2Cn_STATE - State Register	
17.5.4 I2Cn_STATUS - Status Register	
17.5.5 I2Cn_CLKDIV - Clock Division Register	.509
17.5.6 I2Cn_SADDR - Slave Address Register	.509
17.5.7 I2Cn_SADDRMASK - Slave Address Mask Register	. 510
17.5.8 I2Cn_RXDATA - Receive Buffer Data Register (Actionable Reads)	
17.5.9 I2Cn_RXDOUBLE - Receive Buffer Double Data Register (Actionable Reads)	
17.5.10 I2Cn_RXDATAP - Receive Buffer Data Peek Register	
17.5.11 I2Cn_RXDOUBLEP - Receive Buffer Double Data Peek Register	
17.5.12 I2Cn_TXDATA - Transmit Buffer Data Register	
17.5.13 I2Cn_TXDOUBLE - Transmit Buffer Double Data Register	
17.5.14 I2Cn_IF - Interrupt Flag Register	
17.5.15 I2Cn_IFS - Interrupt Flag Set Register	
17.5.10 I2CII_II C - Interrupt Flag Clear Register	
17.5.17 I2CII_IEIV - Interrupt Enable Register	
17.5.19 I2Cn_ROUTELOC0 - I/O Routing Location Register	
18. USART - Universal Synchronous Asynchronous Receiver/Transmitter	
18.1 Introduction	
18.2 Features	
18.3 Functional Description	. 527

18.3.1 Modes of Operation	
18.3.2 Asynchronous Operation	
18.3.3 Synchronous Operation	
18.3.4 Hardware Flow Control	
18.3.5 Debug Halt	
18.3.6 PRS-triggered Transmissions	
18.3.7 PRS RX Input	
18.3.8 PRS CLK Input	
18.3.9 DMA Support	
18.3.10 Timer	
18.3.11 Interrupts	
18.3.12 IrDA Modulator/ Demodulator	559
18.4 Register Map	560
18.5 Register Description	561
18.5.1 USARTn_CTRL - Control Register	
18.5.2 USARTn_FRAME - USART Frame Format Register	
18.5.3 USARTn_TRIGCTRL - USART Trigger Control Register	
18.5.4 USARTn_CMD - Command Register	
18.5.5 USARTn_STATUS - USART Status Register	
18.5.6 USARTn_CLKDIV - Clock Control Register	
18.5.7 USARTn_RXDATAX - RX Buffer Data Extended Register (Actionable Reads)	
18.5.8 USARTn_RXDATA - RX Buffer Data Register (Actionable Reads)	
18.5.9 USARTn_RXDOUBLEX - RX Buffer Double Data Extended Register (Actionable Reads	-
18.5.10 USARTn_RXDOUBLE - RX FIFO Double Data Register (Actionable Reads)	
18.5.11 USARTn_RXDATAXP - RX Buffer Data Extended Peek Register	
18.5.12 USARTn_RXDOUBLEXP - RX Buffer Double Data Extended Peek Register	
18.5.13 USARTn_TXDATAX - TX Buffer Data Extended Register	
18.5.14 USARTn_TXDATA - TX Buffer Data Register	
18.5.15 USARTn_TXDOUBLEX - TX Buffer Double Data Extended Register	
18.5.16 USARTn_TXDOUBLE - TX Buffer Double Data Register	
18.5.17 USARTn_IF - Interrupt Flag Register	
18.5.18 USARTn_IFS - Interrupt Flag Set Register	
18.5.19 USARTn_IFC - Interrupt Flag Clear Register	
18.5.20 USARTn_IEN - Interrupt Enable Register	
18.5.21 USARTn_IRCTRL - IrDA Control Register	
18.5.22 USARTn_INPUT - USART Input Register	
18.5.24 USARTn_TIMING - Timing Register	
18.5.25 USARTn_CTRLX - Control Register Extended	
18.5.26 USARTn_TIMECMP0 - Used to Generate Interrupts and Various Delays	
-	600
-	602
18.5.29 USARTh ROUTEPEN - I/O Routing Pin Enable Register	
18.5.30 USARTn_ROUTELOC0 - I/O Routing Fire Enable Register	
18.5.31 USARTn_ROUTELOCG - I/O Routing Location Register	
19. LEUART - Low Energy Universal Asynchronous Receiver/Transmitter	
19.1 Introduction	614

19.2 Features	615
19.3 Functional Description	616
19.3.1 Frame Format	617
19.3.2 Clock Source	617
19.3.3 Clock Generation	618
19.3.4 Data Transmission	618
19.3.5 Data Reception	620
19.3.6 Loopback	
19.3.7 Half Duplex Communication	
19.3.8 Transmission Delay	
19.3.9 PRS RX Input	
19.3.10 DMA Support	
19.3.11 Pulse Generator/ Pulse Extender	
19.3.12 Register Access	626
19.4 Register Map	626
19.5 Register Description	627
19.5.1 LEUARTn_CTRL - Control Register (Async Reg)	
19.5.2 LEUARTn_CMD - Command Register (Async Reg)	
19.5.3 LEUARTn_STATUS - Status Register	631
19.5.4 LEUARTn_CLKDIV - Clock Control Register (Async Reg)	632
19.5.5 LEUARTn_STARTFRAME - Start Frame Register (Async Reg)	632
19.5.6 LEUARTn_SIGFRAME - Signal Frame Register (Async Reg)	633
19.5.7 LEUARTn_RXDATAX - Receive Buffer Data Extended Register (Actionable Reads)	633
19.5.8 LEUARTn_RXDATA - Receive Buffer Data Register (Actionable Reads)	
19.5.9 LEUARTn_RXDATAXP - Receive Buffer Data Extended Peek Register	
19.5.10 LEUARTn_TXDATAX - Transmit Buffer Data Extended Register (Async Reg)	
19.5.11 LEUARTn_TXDATA - Transmit Buffer Data Register (Async Reg)	
19.5.12 LEUARTn_IF - Interrupt Flag Register	
19.5.13 LEUARTn_IFS - Interrupt Flag Set Register	
19.5.14 LEUARTn_IFC - Interrupt Flag Clear Register	
19.5.15 LEUARTn_IEN - Interrupt Enable Register	
19.5.16 LEUARTn_PULSECTRL - Pulse Control Register (Async Reg)	
19.5.17 LEUARTn_FREEZE - Freeze Register	
19.5.18 LEUARTn_SYNCBUSY - Synchronization Busy Register	
19.5.19 LEUARTn_ROUTEPEN - I/O Routing Pin Enable Register	
19.5.20 LEUARTII_ROUTELOCU - I/O Routing Location Register	
19.5.21 LEOAKTII_INFOT - LEOAKT IIIput Kegistei	040
20. TIMER/WTIMER - Timer/Counter	649
20.1 Introduction	649
20.2 Features	650
20.3 Functional Description	
20.3.1 Counter Modes	
20.3.2 Compare/Capture Channels	
20.3.3 Dead-Time Insertion Unit	
20.3.4 Debug Mode	
20.3.5 Interrupts, DMA and PRS Output	

20.3.6 GPIO Input/Output	672
20.4 Register Map	. 673
20.5 Register Description	674
20.5.1 TIMERn_CTRL - Control Register	
20.5.2 TIMERn_CMD - Command Register	
20.5.3 TIMERn_STATUS - Status Register	
20.5.4 TIMERn_IF - Interrupt Flag Register	
20.5.5 TIMERn_IFS - Interrupt Flag Set Register	
20.5.6 TIMERn_IFC - Interrupt Flag Clear Register	
20.5.7 TIMERn_IEN - Interrupt Enable Register	. 685
20.5.8 TIMERn_TOP - Counter Top Value Register	686
20.5.9 TIMERn_TOPB - Counter Top Value Buffer Register	686
20.5.10 TIMERn_CNT - Counter Value Register	687
20.5.11 TIMERn_LOCK - TIMER Configuration Lock Register	. 687
20.5.12 TIMERn_ROUTEPEN - I/O Routing Pin Enable Register	. 688
20.5.13 TIMERn_ROUTELOC0 - I/O Routing Location Register	689
20.5.14 TIMERn_ROUTELOC2 - I/O Routing Location Register	694
20.5.15 TIMERn_CCx_CTRL - CC Channel Control Register	698
20.5.16 TIMERn_CCx_CCV - CC Channel Value Register (Actionable Reads)	701
20.5.17 TIMERn_CCx_CCVP - CC Channel Value Peek Register	701
20.5.18 TIMERn_CCx_CCVB - CC Channel Buffer Register	702
20.5.19 TIMERn_DTCTRL - DTI Control Register	.703
20.5.20 TIMERn_DTTIME - DTI Time Control Register	
20.5.21 TIMERn_DTFC - DTI Fault Configuration Register	
20.5.22 TIMERn_DTOGEN - DTI Output Generation Enable Register	
20.5.23 TIMERn_DTFAULT - DTI Fault Register	
20.5.24 TIMERn_DTFAULTC - DTI Fault Clear Register	
20.5.25 TIMERn_DTLOCK - DTI Configuration Lock Register	.712
1. LETIMER - Low Energy Timer....................................	713
21.1 Introduction	713
21.2 Features	
21.3 Functional Description	
21.3.1 Timer	
21.3.2 Compare Registers	
21.3.3 Top Value	
21.3.4 Underflow Output Action	
21.3.6 Examples	
21.3.7 Register Access	
21.4 Register Map	
21.5 Register Description	
21.5.1 LETIMERn_CTRL - Control Register (Async Reg)	
21.5.2 LETIMERn_CMD - Command Register (Async Reg)	
21.5.3 LETIMERn_STATUS - Status Register	
21.5.4 LETIMERn_CNT - Counter Value Register	
21.5.5 LETIMERn_COMP0 - Compare Value Register 0 (Async Reg)	731

21.5.6 LETIMERn_COMP1 - Compare Value Register 1 (Async Reg)	732
21.5.7 LETIMERn_REP0 - Repeat Counter Register 0 (Async Reg)	.732
21.5.8 LETIMERn_REP1 - Repeat Counter Register 1 (Async Reg)	.733
21.5.9 LETIMERn_IF - Interrupt Flag Register	733
21.5.10 LETIMERn_IFS - Interrupt Flag Set Register	.734
21.5.11 LETIMERn_IFC - Interrupt Flag Clear Register	735
21.5.12 LETIMERn_IEN - Interrupt Enable Register	736
21.5.13 LETIMERn_SYNCBUSY - Synchronization Busy Register	. 7.36
21.5.14 LETIMERn_ROUTEPEN - I/O Routing Pin Enable Register	.737
21.5.15 LETIMERn_ROUTELOC0 - I/O Routing Location Register	738
21.5.16 LETIMERn_PRSSEL - PRS Input Select Register	741
22. CRYOTIMER - Ultra Low Energy Timer/Counter	. 744
22.1 Introduction	. 744
22.2 Features	. 7.44
22.3 Functional Description	. 744
22.3.1 Block Diagram	
22.3.2 Operation	
22.3.3 Debug Mode	
22.3.4 Energy Mode Availability	
22.4 Register Map	
22.5 Register Description	748
22.5.1 CRYOTIMER_CTRL - Control Register	
22.5.2 CRYOTIMER_PERIODSEL - Interrupt Duration	
22.5.3 CRYOTIMER CNT - Counter Value	
22.5.4 CRYOTIMER EM4WUEN - Wake Up Enable	
22.5.5 CRYOTIMER IF - Interrupt Flag Register	
22.5.6 CRYOTIMER_IFS - Interrupt Flag Set Register	
22.5.7 CRYOTIMER IFC - Interrupt Flag Clear Register	
22.5.8 CRYOTIMER_IEN - Interrupt Enable Register	
23. VDAC - Digital to Analog Converter	
23.1 Introduction	
23.3 Functional Description	
23.3.1 Power Supply	
23.3.2 I/O Pin Considerations	
23.3.3 Enabling and Disabling a Channel	
23.3.4 Conversions	
23.3.5 Reference Selection	
23.3.6 Warmup Time and Initial Conversion	
23.3.7 Analog Output	
23.3.8 Output Mode	
·	
23.3.9 Async Mode	
23.3.10 Refresh Timer	
23.3.11 Clock Prescaling	. 758 . 758
7.0.0 TZ 1.00H.00550	. 130

23.3.13 Sine	e Generation Mode	′59
23.3.14 Inte	rrupt Flags	'59
23.3.15 PRS	S Outputs	'60
23.3.16 DM/	A Request	'60
23.3.17 LES	SENSE Trigger Mode	'60
23.3.18 Opa	ımps	'60
23.3.19 Cali	bration	'60
23.3.20 War	mup Mode	'61
23.4 Register I	Мар	'62
23.5 Register I	Description	'63
23.5.1 VDA	Cn_CTRL - Control Register	63
23.5.2 VDA	Cn_STATUS - Status Register	'66
23.5.3 VDA	Cn_CH0CTRL - Channel 0 Control Register	'68
23.5.4 VDA	Cn_CH1CTRL - Channel 1 Control Register	70
23.5.5 VDA	Cn_CMD - Command Register	'72
23.5.6 VDA	Cn_IF - Interrupt Flag Register	73
23.5.7 VDA	Cn_IFS - Interrupt Flag Set Register	75
23.5.8 VDA	Cn_IFC - Interrupt Flag Clear Register	77
23.5.9 VDA	Cn_IEN - Interrupt Enable Register	'79
23.5.10 VD	ACn_CH0DATA - Channel 0 Data Register	'80
23.5.11 VD	ACn_CH1DATA - Channel 1 Data Register	'81
23.5.12 VD	ACn_COMBDATA - Combined Data Register	'81
23.5.13 VD	ACn_CAL - Calibration Register	'82
23.5.14 VD	ACn_OPAx_APORTREQ - Operational Amplifier APORT Request Status Register 7	'83
23.5.15 VD	ACn_OPAx_APORTCONFLICT - Operational Amplifier APORT Conflict Status Register 7	′84
23.5.16 VD	ACn_OPAx_CTRL - Operational Amplifier Control Register	'85
23.5.17 VD	ACn_OPAx_TIMER - Operational Amplifier Timer Control Register	'88
23.5.18 VD	ACn_OPAx_MUX - Operational Amplifier Mux Configuration Register	89
23.5.19 VD	ACn_OPAx_OUT - Operational Amplifier Output Configuration Register 7	92
23.5.20 VD	ACn_OPAx_CAL - Operational Amplifier Calibration Register	'94
24. OPAMP - Op	perational Amplifier	96
24.1 Introducti	on	'96
24.2 Features		'96
	al Description	
24.3.1 Opai	mp Configuration	'98
24.3.2 Interr	upts and PRS Output	02
	RT Request and Conflict Status	
	np Modes	
24.3.5 Opan	np VDAC Combination..........................8	09
24.4 Register I	Мар	10
24.5 Register I	Description...............................8	10
25 ACMP - Ana		
23. ACIVII - AIIG	log Comparator	
		11

25.3 Functional Description	. 813
25.3.1 Power Supply	813
25.3.2 Warm-up Time	814
25.3.3 Response Time	814
25.3.4 Hysteresis	815
25.3.5 Input Pin Considerations	816
25.3.6 Input Selection	. 816
25.3.7 Capacitive Sense Mode	817
25.3.8 Interrupts and PRS Output	819
25.3.9 Output to GPIO	819
25.3.10 APORT Conflicts	819
25.3.11 Supply Voltage Monitoring	.819
25.3.12 External Override Interface	. 820
25.4 Register Map	. 820
25.5 Register Description	821
25.5.1 ACMPn_CTRL - Control Register	821
25.5.2 ACMPn_INPUTSEL - Input Selection Register	
25.5.3 ACMPn_STATUS - Status Register	
25.5.4 ACMPn_IF - Interrupt Flag Register	830
25.5.5 ACMPn_IFS - Interrupt Flag Set Register	830
25.5.6 ACMPn_IFC - Interrupt Flag Clear Register	
25.5.7 ACMPn_IEN - Interrupt Enable Register	
25.5.8 ACMPn_APORTREQ - APORT Request Status Register	833
25.5.9 ACMPn_APORTCONFLICT - APORT Conflict Status Register	
25.5.10 ACMPn_HYSTERESIS0 - Hysteresis 0 Register	. 836
25.5.11 ACMPn_HYSTERESIS1 - Hysteresis 1 Register	
25.5.12 ACMPn_ROUTEPEN - I/O Routing Pine Enable Register	. 838
25.5.13 ACMPn_ROUTELOC0 - I/O Routing Location Register	839
25.5.14 ACMPn_EXTIFCTRL - External Override Interface Control	841
26. ADC - Analog to Digital Converter	.843
26.1 Introduction	
26.2 Features	844
26.3 Functional Description	. 845
26.3.1 Clock Selection	
26.3.2 Conversions	. 846
26.3.3 ADC Modes	. 847
26.3.4 Warm-up Time	. 848
26.3.5 Power Supply	849
26.3.6 Input Pin Considerations	849
26.3.7 Input Selection	. 850
26.3.8 Reference Selection and Input Range Definition	
26.3.9 Programming of Bias Current	
26.3.10 Feature Set	858
26.3.11 Interrupts, PRS Output	
26.3.12 DMA Request	. 865
26.3.13 Calibration	065

26.3.14 EM2 Deep Sleep or EM3 Stop Operation	. 866
26.3.15 ASYNC ADC_CLK Usage Restrictions and Benefits	. 867
26.3.16 Window Compare Function	
26.3.17 ADC Programming Model	. 868
26.4 Register Map	. 869
26.5 Register Description	. 870
26.5.1 ADCn_CTRL - Control Register	. 870
26.5.2 ADCn_CMD - Command Register	.873
26.5.3 ADCn_STATUS - Status Register	.874
26.5.4 ADCn_SINGLECTRL - Single Channel Control Register	. 876
26.5.5 ADCn_SINGLECTRLX - Single Channel Control Register Continued	881
26.5.6 ADCn_SCANCTRL - Scan Control Register	. 884
26.5.7 ADCn_SCANCTRLX - Scan Control Register Continued	. 887
26.5.8 ADCn_SCANMASK - Scan Sequence Input Mask Register	. 890
26.5.9 ADCn_SCANINPUTSEL - Input Selection Register for Scan Mode	.892
26.5.10 ADCn_SCANNEGSEL - Negative Input Select Register for Scan	.895
26.5.11 ADCn_CMPTHR - Compare Threshold Register	. 897
26.5.12 ADCn_BIASPROG - Bias Programming Register for Various Analog Blocks Used in ADC	
Operation	. 898
26.5.13 ADCn_CAL - Calibration Register	. 899
26.5.14 ADCn_IF - Interrupt Flag Register	. 901
26.5.15 ADCn_IFS - Interrupt Flag Set Register	. 903
26.5.16 ADCn_IFC - Interrupt Flag Clear Register	.905
26.5.17 ADCn_IEN - Interrupt Enable Register	.907
26.5.18 ADCn_SINGLEDATA - Single Conversion Result Data (Actionable Reads)	. 908
26.5.19 ADCn_SCANDATA - Scan Conversion Result Data (Actionable Reads)	. 908
26.5.20 ADCn_SINGLEDATAP - Single Conversion Result Data Peek Register	. 909
26.5.21 ADCn_SCANDATAP - Scan Sequence Result Data Peek Register	. 909
26.5.22 ADCn_SCANDATAX - Scan Sequence Result Data + Data Source Register (Actionable	
Reads)	
26.5.23 ADCn_SCANDATAXP - Scan Sequence Result Data + Data Source Peek Register	. 910
26.5.24 ADCn_APORTREQ - APORT Request Status Register	
26.5.25 ADCn_APORTCONFLICT - APORT Conflict Status Register	
26.5.26 ADCn_SINGLEFIFOCOUNT - Single FIFO Count Register	
26.5.27 ADCn_SCANFIFOCOUNT - Scan FIFO Count Register	
26.5.28 ADCn_SINGLEFIFOCLEAR - Single FIFO Clear Register	
26.5.29 ADCn_SCANFIFOCLEAR - Scan FIFO Clear Register	
26.5.30 ADCn_APORTMASTERDIS - APORT Bus Master Disable Register	.915
27. IDAC - Current Digital to Analog Converter	. 918
27.1 Introduction	. 918
27.2 Features	. 918
27.3 Functional Description	. 919
27.3.1 Current Programming	
27.3.2 IDAC Enable and Warm-up	
27.3.3 Output Control	
27.3.4 APORT Configuration	
27.3.5 Interrupts	

27.3.6 Minimizing Output Transition	. 920
27.3.7 Duty Cycle Configuration	. 920
27.3.8 Calibration	. 920
27.3.9 PRS Triggered Charge Injection	. 921
27.4 Register Map	. 921
27.5 Register Description	. 922
27.5.1 IDAC_CTRL - Control Register	
27.5.2 IDAC_CURPROG - Current Programming Register	
27.5.3 IDAC_DUTYCONFIG - Duty Cycle Configuration Register	
27.5.4 IDAC_STATUS - Status Register	
27.5.5 IDAC IF - Interrupt Flag Register	
27.5.6 IDAC_IFS - Interrupt Flag Set Register	
27.5.7 IDAC_IFC - Interrupt Flag Clear Register	
27.5.8 IDAC_IEN - Interrupt Enable Register	
27.5.9 IDAC_APORTREQ - APORT Request Status Register	
27.5.10 IDAC_APORTCONFLICT - APORT Request Status Register	
28. LESENSE - Low Energy Sensor Interface	
28.1 Introduction	
28.2 Features	
28.3 Functional Description	
28.3.1 Channel Configuration	
28.3.2 Scan Sequence	
28.3.3 Sensor Timing	
28.3.4 Sensor Interaction	
28.3.5 Sensor Sampling	
28.3.6 Sensor Evaluation	
28.3.7 Decoder	
28.3.8 Measurement Results	
28.3.9 VDAC Interface	
28.3.10 ACMP Interface	
28.3.11 ACMP and VDAC Duty Cycling	
28.3.12 ADC Interface	
28.3.13 DMA Requests	. 944
28.3.14 PRS Output	. 944
28.3.15 RAM	. 944
28.3.16 Application Examples	. 944
28.4 Register Map	. 950
28.5 Register Description	. 952
28.5.1 LESENSE_CTRL - Control Register (Async Reg)	. 952
28.5.2 LESENSE_TIMCTRL - Timing Control Register (Async Reg)	
28.5.3 LESENSE_PERCTRL - Peripheral Control Register (Async Reg)	
28.5.4 LESENSE_DECCTRL - Decoder Control Register (Async Reg)	
28.5.5 LESENSE_BIASCTRL - Bias Control Register (Async Reg)	
28.5.6 LESENSE_EVALCTRL - LESENSE Evaluation Control (Async Reg)	
28.5.7 LESENSE_PRSCTRL - PRS Control Register (Async Reg)	
28.5.8 LESENSE_CMD - Command Register (Async Reg)	

28.5.9 LESENSE_CHEN - Channel Enable Register (Async Reg)	. 965
28.5.10 LESENSE_SCANRES - Scan Result Register (Async Reg)	. 966
28.5.11 LESENSE_STATUS - Status Register (Async Reg)	. 967
28.5.12 LESENSE_PTR - Result Buffer Pointers (Async Reg)	. 968
28.5.13 LESENSE_BUFDATA - Result Buffer Data Register (Async Reg) (Actionable Reads)	968
28.5.14 LESENSE_CURCH - Current Channel Index (Async Reg)	. 969
28.5.15 LESENSE_DECSTATE - Current Decoder State (Async Reg)	969
28.5.16 LESENSE_SENSORSTATE - Decoder Input Register (Async Reg)	. 970
28.5.17 LESENSE_IDLECONF - GPIO Idle Phase Configuration (Async Reg)	. 971
28.5.18 LESENSE_ALTEXCONF - Alternative Excite Pin Configuration (Async Reg)	. 975
28.5.19 LESENSE_IF - Interrupt Flag Register	978
28.5.20 LESENSE_IFS - Interrupt Flag Set Register	. 980
28.5.21 LESENSE_IFC - Interrupt Flag Clear Register	. 982
28.5.22 LESENSE_IEN - Interrupt Enable Register	. 984
28.5.23 LESENSE_SYNCBUSY - Synchronization Busy Register	. 985
28.5.24 LESENSE_ROUTEPEN - I/O Routing Register (Async Reg)	
28.5.25 LESENSE_STx_TCONFA - State Transition Configuration a (Async Reg)	988
28.5.26 LESENSE_STx_TCONFB - State Transition Configuration B (Async Reg)	
28.5.27 LESENSE_BUFx_DATA - Scan Results (Async Reg)	
28.5.28 LESENSE_CHx_TIMING - Scan Configuration (Async Reg)	
28.5.29 LESENSE_CHx_INTERACT - Scan Configuration (Async Reg)	
28.5.30 LESENSE_CHx_EVAL - Scan Configuration (Async Reg)	. 995
29. GPCRC - General Purpose Cyclic Redundancy Check	. 997
29.1 Introduction	. 997
29.2 Features	
29.3 Functional Description	
29.3.1 Polynomial Specification	
29.3.2 Input and Output Specification	
29.3.4 DMA Usage	
29.3.5 Byte-Level Bit Reversal and Byte Reordering	
29.4 Register Map	
29.5 Register Description	
29.5.1 GPCRC_CTRL - Control Register	
29.5.2 GPCRC_CMD - Command Register	
29.5.3 GPCRC_INIT - CRC Init Value	
29.5.4 GPCRC_POLY - CRC Polynomial Value	
29.5.5 GPCRC_INPUTDATA - Input 32-bit Data Register	
29.5.6 GPCRC_INPUTDATAHWORD - Input 16-bit Data Register	
29.5.7 GPCRC_INPUTDATABYTE - Input 8-bit Data Register	
29.5.8 GPCRC_DATA - CRC Data Register	
29.5.9 GPCRC_DATAREV - CRC Data Reverse Register	
29.5.10 GPCRC_DATABYTEREV - CRC Data Byte Reverse Register	. 1008
30. CRYPTO - Crypto Accelerator	.1009
30.1 Introduction	1000

30.2 Features	. 1010
30.3 Usage and Programming Interface	.1010
30.4 Functional Description	. 1011
30.4.1 Data and Key Registers	. 1012
30.4.2 Instructions and Execution	. 1014
30.4.3 Repeated Sequence	. 1019
30.4.4 AES	
30.4.5 SHA	. 1022
30.4.6 ECC	. 1022
30.4.7 GCM and GMAC	
30.4.8 DMA	. 1023
30.4.9 BUFC Data Transfer	
30.4.10 Debugging	
30.4.11 Example: Cipher Block Chaining (CBC)	
30.5 Register Map	
30.6 Register Description	
30.6.1 CRYPTO_CTRL - Control Register	.1031
30.6.2 CRYPTO_WAC - Wide Arithmetic Configuration	
30.6.3 CRYPTO_CMD - Command Register	
30.6.4 CRYPTO_STATUS - Status Register	
30.6.5 CRYPTO_DSTATUS - Data Status Register	
30.6.6 CRYPTO_CSTATUS - Control Status Register	
30.6.7 CRYPTO_KEY - KEY Register Access (No Bit Access) (Actionable Reads)	
30.6.8 CRYPTO KEYBUF - KEY Buffer Register Access (No Bit Access) (Actionable Reads)	
30.6.9 CRYPTO SEQCTRL - Sequence Control	
30.6.10 CRYPTO_SEQCTRLB - Sequence Control B	
30.6.11 CRYPTO_IF - AES Interrupt Flags	
30.6.12 CRYPTO_IFS - Interrupt Flag Set Register	
30.6.13 CRYPTO_IFC - Interrupt Flag Clear Register	
30.6.14 CRYPTO IEN - Interrupt Enable Register	
30.6.15 CRYPTO SEQ0 - Sequence Register 0	
30.6.16 CRYPTO SEQ1 - Sequence Register 1	
30.6.17 CRYPTO SEQ2 - Sequence Register 2	
30.6.18 CRYPTO SEQ3 - Sequence Register 3	
30.6.19 CRYPTO SEQ4 - Sequence Register 4	
30.6.20 CRYPTO_DATA0 - DATA0 Register Access (No Bit Access) (Actionable Reads)	
30.6.21 CRYPTO_DATA1 - DATA1 Register Access (No Bit Access) (Actionable Reads)	
30.6.22 CRYPTO_DATA2 - DATA2 Register Access (No Bit Access) (Actionable Reads)	
30.6.23 CRYPTO DATA3 - DATA3 Register Access (No Bit Access) (Actionable Reads)	
30.6.24 CRYPTO_DATA0XOR - DATA0XOR Register Access (No Bit Access) (Actionable Reads	
30.6.25 CRYPTO_DATA0BYTE - DATA0 Register Byte Access (No Bit Access) (Actionable Read	•
	. 1056
30.6.26 CRYPTO_DATA1BYTE - DATA1 Register Byte Access (No Bit Access) (Actionable Reac	
	-
30.6.27 CRYPTO_DATA0XORBYTE - DATA0 Register Byte XOR Access (No Bit Access)	
(Actionable Reads)	
30.6.28 CRYPTO DATA0BYTE12 - DATA0 Register Byte 12 Access (No Bit Access)	1058

30.6.30 CRYPTO_DATA0BYTE14 - DATA0 Register Byte 14 Access (No Bit Access)	59
30.6.32 CRYPTO_DDATA0 - DDATA0 Register Access (No Bit Access) (Actionable Reads) 106 30.6.33 CRYPTO_DDATA1 - DDATA1 Register Access (No Bit Access) (Actionable Reads) 106 30.6.34 CRYPTO_DDATA2 - DDATA2 Register Access (No Bit Access) (Actionable Reads) 106	
30.6.33 CRYPTO_DDATA1 - DDATA1 Register Access (No Bit Access) (Actionable Reads) 106 30.6.34 CRYPTO_DDATA2 - DDATA2 Register Access (No Bit Access) (Actionable Reads)	59
30.6.34 CRYPTO_DDATA2 - DDATA2 Register Access (No Bit Access) (Actionable Reads)106	60
	60
20.6.25 CDVDTO DDATA2 DDATA2 Dogistor Assess (No Dit Assess) (Actionable Doods)	61
30.6.35 CRYPTO DDATA3 - DDATA3 Register Access (No Bit Access) (Actionable Reads) 106	61
30.6.36 CRYPTO DDATA4 - DDATA4 Register Access (No Bit Access) (Actionable Reads) 106	62
30.6.37 CRYPTO_DDATA0BIG - DDATA0 Register Big Endian Access (No Bit Access) (Actionable	
Reads)	62
30.6.38 CRYPTO_DDATA0BYTE - DDATA0 Register Byte Access (No Bit Access) (Actionable	
Reads)	63
30.6.39 CRYPTO_DDATA1BYTE - DDATA1 Register Byte Access (No Bit Access) (Actionable	
Reads)	63
30.6.40 CRYPTO_DDATA0BYTE32 - DDATA0 Register Byte 32 Access (No Bit Access)106	64
30.6.41 CRYPTO_QDATA0 - QDATA0 Register Access (No Bit Access) (Actionable Reads) . 106	64
30.6.42 CRYPTO_QDATA1 - QDATA1 Register Access (No Bit Access) (Actionable Reads) . 106	65
30.6.43 CRYPTO_QDATA1BIG - QDATA1 Register Big Endian Access (No Bit Access) (Actionable	
Reads)	65
30.6.44 CRYPTO_QDATA0BYTE - QDATA0 Register Byte Access (No Bit Access) (Actionable	
Reads)	66
30.6.45 CRYPTO_QDATA1BYTE - QDATA1 Register Byte Access (No Bit Access) (Actionable	
Reads)	66
31. GPIO - General Purpose Input/Output.......................	67
31.1 Introduction	67
31.2 Features	68
	~~
31.3 Functional Description 106	hu
31.3 Functional Description	
31.3.1 Pin Configuration	70
31.3.1 Pin Configuration	70 73
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 1.07	70 73 73
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107	70 73 73 74
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07	70 73 73 74 74
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 107	70 73 73 74 74 76
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 1.07 31.3.4 Alternate Functions 1.07 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 1.07	70 73 73 74 74 76 76
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 107	70 73 73 74 74 76 76
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 1.07 31.3.4 Alternate Functions 1.07 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 1.07	70 73 73 74 74 76 76 77
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 1.07 31.3.4 Alternate Functions 1.07 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 1.07 31.4 Register Map 1.07	70 73 73 74 74 76 76 77
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107	70 73 73 74 74 76 76 77 79
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107	70 73 73 74 76 76 77 79 81
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108	70 73 74 74 76 76 77 79 81 86
31.3.1 Pin Configuration 1.07 31.3.2 EM4 Wake-up 1.07 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 1.07 31.3.6 Output to PRS 1.07 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register 108	70 73 73 74 74 76 76 77 79 81 86 91
31.3.1 Pin Configuration 107 31.3.2 EM4 Wake-up 107 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register 108 31.5.4 GPIO_Px_DOUT - Port Data Out Register 108 31.5.4 GPIO_Px_DOUT - Port Data Out Register 108	70 73 74 74 76 76 77 79 81 86 91
31.3.1 Pin Configuration 107 31.3.2 EM4 Wake-up 107 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register 108 31.5.4 GPIO_Px_DOUT - Port Data Out Register 108 31.5.5 GPIO_Px_DOUTGL - Port Data Out Register 108 31.5.5 GPIO_Px_DOUTGL - Port Data Out Register 108 31.5.5 GPIO_Px_DOUTGL - Port Data Out Toggle Register 108	70 73 74 74 76 76 77 79 81 86 91 91
31.3.1 Pin Configuration 107 31.3.2 EM4 Wake-up 107 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register 108 31.5.4 GPIO_Px_DOUT - Port Data Out Register 108 31.5.5 GPIO_Px_DOUT - Port Data Out Register 108 31.5.6 GPIO_Px_DIN - Port Data in Register 108 31.5.6 GPIO_Px_DIN - Port Data in Register 108	70 73 74 74 76 76 77 79 81 86 91 91 92
31.3.1 Pin Configuration 107 31.3.2 EM4 Wake-up 107 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_PX_CTRL - Port Control Register 107 31.5.2 GPIO_PX_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_PX_MODEH - Port Pin Mode High Register 108 31.5.4 GPIO_PX_DOUT - Port Data Out Register 108 31.5.5 GPIO_PX_DOUT - Port Data Out Register 108 31.5.6 GPIO_PX_DIN - Port Data in Register 108 31.5.7 GPIO_PX_PINLOCKN - Port Unlocked Pins Register 108	70 73 74 74 76 76 77 79 81 86 91 92 92 93
31.3.1 Pin Configuration 107 31.3.2 EM4 Wake-up 107 31.3.3 EM4 Retention 107 31.3.4 Alternate Functions 107 31.3.5 Interrupt Generation 107 31.3.6 Output to PRS 107 31.3.7 Synchronization 107 31.4 Register Map 107 31.5 Register Description 107 31.5.1 GPIO_Px_CTRL - Port Control Register 107 31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register 108 31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register 108 31.5.4 GPIO_Px_DOUT - Port Data Out Register 108 31.5.5 GPIO_Px_DOUTTGL - Port Data Out Register 108 31.5.6 GPIO_Px_DIN - Port Data in Register 108 31.5.7 GPIO_Px_DIN - Port Data in Register 108 31.5.8 GPIO_Px_DINDOCKN - Port Unlocked Pins Register 108 31.5.8 GPIO_Px_OVTDIS - Over Voltage Disable for All Modes 108	70 73 74 74 76 76 77 79 81 86 91 92 92 93 94

31.5.12 GPIO_EXTIPINSELH - External Interrupt Pin Select High Register
31.5.17 GPIO_IFS - Interrupt Flag Set Register
31.5.19 GPIO_IEN - Interrupt Enable Register
31.5.20 GPIO_EM4WUEN - EM4 Wake Up Enable Register
31.5.21 GPIO_ROUTEPEN - I/O Routing Pin Enable Register
31.5.22 GPIO_ROUTELOC0 - I/O Routing Location Register
31.5.23 GPIO_INSENSE - Input Sense Register
31.5.24 GPIO_LOCK - Configuration Lock Register
32. APORT - Analog Port
32.1 Introduction
32.2 Features
32.3 Functional Description
33. FPUEH - Floating Point Unit Exception Handler
33.1 Functional Description
33.2 Register Map
33.3 Register Description
34. Revision History
Appendix 1. Abbreviations

1. About This Document

1.1 Introduction

This document contains reference material for the EFR32 devices. All modules and peripherals in the EFR32 devices are described in general terms. Not all modules are present in all devices and the feature set for each device might vary. Such differences, including pinout, are covered in the device data sheets and applicable errata documents.

1.2 Conventions

Register Names

Register names are given with a module name prefix followed by the short register name:

TIMERn_CTRL - Control Register

The "n" denotes the module number for modules which can exist in more than one instance.

Some registers are grouped which leads to a group name following the module prefix:

GPIO Px DOUT - Port Data Out Register

The "x" denotes the different ports.

Bit Fields

Registers contain one or more bit fields which can be 1 to 32 bits wide. Bit fields wider than 1 bit are given with start (x) and stop (y) bit [y:x].

Bit fields containing more than one bit are unsigned integers unless otherwise is specified.

Unspecified bit field settings must not be used, as this may lead to unpredictable behaviour.

Address

The address for each register can be found by adding the base address of the module found in the Memory Map (see Figure 4.2 System Address Space With Core and Code Space Listing on page 43), and the offset address for the register (found in module Register Map).

Access Type

The register access types used in the register descriptions are explained in Table 1.1 Register Access Types on page 26.

Table 1.1. Register Access Types

Access Type	Description	
R	Read only. Writes are ignored	
RW	Readable and writable	
RW1	Readable and writable. Only writes to 1 have effect	
(R)W1	Sometimes readable. Only writes to 1 have effect. Currently only used for IFC registers (see 3.3.1.2 IFC Read-clear Operation)	
W1	Read value undefined. Only writes to 1 have effect	
W	Write only. Read value undefined.	
RWH	Readable, writable, and updated by hardware	
RW(nB), RWH(nB), etc.	"(nB)" suffix indicates that register explicitly does not support peripheral bit set or clear (see 4.2.3 Peripheral Bit Set and Clear)	

Access Type	Description
	"(a)" suffix indicates that register has actionable reads (see 6.3.6 Debugger Reads of Actionable Registers)

Number format

0x prefix is used for hexadecimal numbers

0b prefix is used for binary numbers

Numbers without prefix are in decimal representation.

Reserved

Registers and bit fields marked with **reserved** are reserved for future use. These should be written to 0 unless otherwise stated in the Register Description. Reserved bits might be read as 1 in future devices.

Reset Value

The reset value denotes the value after reset.

Registers denoted with X have unknown value out of reset and need to be initialized before use. Note that read-modify-write operations on these registers before they are initialized results in undefined register values.

Pin Connections

Pin connections are given with a module prefix followed by a short pin name:

CMU CLKOUT1 (Clock management unit, clock output pin number 1)

The location for the pin names given in the module documentation can be found in the device-specific data sheet.

1.3 Related Documentation

Further documentation on the EFR32 devices and the ARM Cortex-M4 can be found at the Silicon Labs and ARM web pages:

www.silabs.com

www.arm.com

2. System Overview





Quick Facts

What?

The EFR32 Wireless Gecko is a highly integrated, configurable and low power wireless System-on-Chip (SoC) with a robust set of MCU and radio peripherals.

Why?

The radio enables support for zigbee, Thread, Bluetooth Low Energy (BLE) and proprietary protocols in 2.4 GHz and sub-GHz frequency bands while the MCU system allows customized protocols and applications to run efficiently.

How?

Dynamic or fixed packet lengths, optional address recognition, and flexible CRC and crypto schemes makes the EFR32 ideal for many low power wireless IoT applications. High performance analog and digital peripherals allows complete applications to run on the EFR32 SoC.

2.1 Introduction

The high level features of EFR32 include:

- · High performance radio transceiver
 - · Dual-band operation
 - · Low power consumption in transmit, receive, and standby modes
 - · Excellent receiver performance, including sensitivity, selectivity and blocking
 - Excellent transmitter performance, including programmable output power, low phase noise and PA ramping
- · Configurable protocol support, including standards and customer developed protocols
 - · Preamble and frame synchronization insertion in transmit and recovery in receive
 - Flexible CRC support, including configurable polynomial and multiple CRCs for single data frames
 - · Basic address filtering performed in hardware
- · High performance, low power MCU system
 - · High Performance 32-bit ARM Cortex-M4 CPU
 - · Flexible and efficient energy management
 - · Complete set of digital peripherals
 - Peripheral Reflex System (PRS)
 - · Precision analog interfaces
- · Low external component count
 - · Fully integrated 2.4 GHz BALUN
 - · Integrated tunable crystal loading capacitors

A further introduction to the MCU and radio system is included in the following sections.

Note:

Detailed performance numbers, current consumption, pinout etc. is available in the device data sheet.

2.2 Block Diagrams

The block diagram for the EFR32 System-On-Chip series is shown in (Figure 2.1 EFR32 System-On-Chip Block Diagram on page 29).




Figure 2.1. EFR32 System-On-Chip Block Diagram

2.3 MCU Features Overview

ARMCortex-M4 CPU platform

- · High Performance 32-bit processor @ up to 40 MHz
- · Memory Protection Unit
- · Wake-up Interrupt Controller

Flexible Energy Management System

- 5 Energy Modes from EM0 to EM4 provide flexibility between higher performance and low power
- · Power routing configurations including DCDC control
- · Voltage Monitoring and Brown Out Detection
- · State Retention
- · Up to 256 KB Flash
- Up to 32 KB RAM

Up to 31 General Purpose I/O pins

- · Configurable push-pull, open-drain, pull-up/down, input filter, drive strength
- · Configurable peripheral I/O locations
- · 16 asynchronous external interrupts
- · Output state retention and wake-up from Shutoff Mode

8 Channel DMA Controller

· Alternate/primary descriptors with scatter-gather/ping-pong operation

• 12 Channel Peripheral Reflex System

· Autonomous inter-peripheral signaling enables smart operation in low energy modes

CRYPTO Advanced Encryption Standard Accelerator

- AES encryption / decryption, with 128 or 256 bit keys
- Multiple AES modes of operation, including Counter (CTR), Galois/Counter Mode (GCM), Cipher Block Chaining (CBC), Cipher Feedback (CFB) and Output Feedback (OFB).
- Accelerated SHA-1 and SHA-2 (SHA-224 / SHA-256)
- · Accelerated Elliptic Curve Cryptography (ECC), with binary or prime fields
- · Flexible 256-bit ALU and sequencer

General Purpose Cyclic Redundancy Check

- · Programmable 16-bit polynomial, fixed 32-bit polynomial
- · The General Purpose Cyclic Redundancy Check (GPCRC) module comes in addition to the radio CRC

· Communication Interfaces

- · 2 Universal Synchronous/Asynchronous Receiver/Transmitter
 - UART/SPI/SmartCard (ISO 7816)/IrDA/I2S
 - · Triple buffered full/half-duplex operation
 - · Hardware flow control
 - 4-16 data bits
- 1 Low Energy UART
 - · Autonomous operation with DMA in Deep Sleep Mode
- 1 I²C Interface with SMBus support
 - · Address recognition in Stop Mode

· Timers/Counters

- · 2 16-bit Timer/Counter
 - 3 or 4 Compare/Capture/PWM channels
 - Dead-Time Insertion on TIMER0
- 1 32-bit Timer/Counter
 - 3 or 4 Compare/Capture/PWM channels
 - Dead-Time Insertion on WTIMER0
- · 16-bit Low Energy Timer
- · 32-bit Ultra Low Energy Timer/Counter (CRYOTIMER) for periodic wake-up from any Energy Mode
- · 32-bit Real-Time Counter and Calendar
- · 16+16+32 bit Protocol Timer
- · 16-bit Pulse Counter
 - · Asynchronous pulse counting/quadrature decoding
- · 2 Watchdog Timers with dedicated RC oscillator

Ultra Low Power Precision Analog Peripherals

- · 12-bit 1 Msamples/s Analog to Digital Converter
 - · All APORT input channels available
 - · On-chip temperature sensor
 - · Single ended or differential operation
 - · Conversion tailgating for predictable latency
- · 12-bit 500 ksps Digital to Analog Converter
 - · 2 single ended channels/1 differential channel
- · Up to 2 Operational Amplifiers
 - · Supports rail-to-rail inputs and outputs
 - · Programmable gain
- · Current Digital to Analog Converter
 - · Source or sink a configurable constant current
- 2 Analog Comparator
 - · Programmable speed/current
- · Analog Port

· Low-Energy Sensor Interface

- · Autonomous sensor monitoring in deep sleep mode
- · Wide range of supported sensors, including LC sensors and capacitive touch switches
- · Ultra Efficient Power-on Reset and Brown-Out Detector
- Debug Interface
 - · 4-pin Joint Test Action Group (JTAG) interface
 - · 2-pin serial-wire debug (SWD) interface

2.4 Oscillators and Clocks

EFR32 has six different oscillators integrated, as shown in Table 2.1 EFR32 Oscillators on page 32.

Table 2.1. EFR32 Oscillators

Oscillator	Frequency	Optional?	External components	Description
HFXO	38 MHz - 40 MHz	No	Crystal	High accuracy, low jitter high frequency crystal oscillator. Tunable crystal loading capacitors are fully integrated. The HFXO is required for all types of RF communication to be active.
HFRCO	1 MHz - 38 MHz	No	-	Medium accuracy RC oscillator, typically used for timing during startup of the HFXO and as a clock source as long as no RF communication is active.
AUXHFRCO	1 MHz - 38 MHz	No	-	Medium accuracy RC oscillator, typically used as alternative clock source for Analog to Digital Converter or Debug Trace.
LFRCO	32768 Hz	No	-	Medium accuracy frequency reference typically used for medium accuracy RTCC timing.
LFXO	32768 Hz	Yes	Crystal	High accuracy frequency reference typically used for high accuracy RTCC timing. Tunable crystal loading capacitors are fully integrated.
ULFRCO	1000 Hz	No	-	Ultra low frequency oscillator typically used for the watchdog timer.

The RC oscillators can be calibrated against either of the crystal oscillators in order to compensate for temperature and voltage supply variations. Hardware support is included to measure the frequency of various oscillators against each other.

Oscillator and clock management is available through the Clock Management Unit (CMU), see section 11. CMU - Clock Management Unit for details.

2.5 RF Frequency Synthesizer

The Fractional-N RF Frequency Synthesizer (SYNTH) provides a low phase noise LO signal to be used in both receive and transmit modes.

The capabilities of the SYNTH include:

- · High performance, low phase noise
- · Fast frequency settling
- · Fast and fully automated calibration
- · Sub 100 Hz frequency resolution across the supported frequency bands

2.6 Modulation Modes

EFR32 supports a wide range of modulation modes in transmit and receive:

- 2-FSK, 2-GFSK, 4-FSK, 4-GFSK, MSK, GMSK, O-QPSK with half-sine shaping, ASK / OOK, DBPSK TX
- · NRZ or Manchester support
- · UART mode over air for legacy protocols
- · Data rates ranging from 600 bps up to 2 Mbps
- · Configurable frequency deviation
- · Configurable Direct Sequence Spread Spectrum (DSSS), with spread sequences up to 32 chips encoding up to 4 information bits
- · Configurable 4-FSK symbol encoding

2.7 Transmit Mode

In transmit mode EFR32 performs the following functionality:

- · Automatic PA power ramping during the start and end of a frame transmit
- · Programmable output power
- · Optional preamble and synchronization word insertion
- Accurate transmit frame timing to support time synchronized radio protocols
- · Optional Carrier Sense Multiple Access Collision Avoidance (CSMA-CA) or Listen Before Talk (LBT) hardware support
- Integrated transmit test modes, as described in 2.17 RF Test Modes

2.8 Receive Mode

In receive mode EFR32 performs the following functionality:

- A single-ended (2.4 GHz) or differential (Sub-GHz) LNA amplifies the input RF signal. The amplified signal is then mixed to a low-IF signal through the quadrature down-coversion mixer. Further signal filtering is performed before conversion to a digital signal through the I/Q ADC.
- Digitally configurable receiver bandwidth from 100 Hz to 2.5 MHz
- · Timing recovery on received data, including simultaneous support for two different frame synchronization words
- Automatic frequency offset compensation, to compensate for carrier frequency offset between the transmitter and receiver
- · Support for a wide range of modulation formats as described in section 2.6 Modulation Modes

2.9 Data Buffering

EFR32 supports buffered transmit and receive modes through its buffer controller (BUFC), with four individually configurable buffers. The BUFC uses the system RAM as storage, and each buffer can be individually configured with parameters such as:

- · Buffer size
- · Buffer interrupt thresholds
- · Buffer RAM location
- · Overflow and underflow detection

In receive mode, data following frame synchronization is moved directly from the demodulator to the buffer storage.

In transmit mode, data following the inserted preamble and synchronization word is moved directly from the buffer storage to the modulator.

2.10 Unbuffered Data Transfer

For most system designs it is recommended to use the data buffering within EFR32 to provide a convenient user interface.

In cases where data buffering within EFR32 is not desired, it is possible to set up direct unbuffered data transfers using a single-pin or two-pin interface on EFR32. A bit clock output is provided on the Serial Clock (SC) output pin, and a serial bitstream is provided to EFR32 in a transmit mode and from EFR32 in a receive mode.

In unbuffered data transfer modes the hardware support provided by EFR32 to perform preamble and frame synchronization insertion in transmit mode and detection in receive mode can still optionally be used.

2.11 Frame Format Support

EFR32 has an extensive support for frame handling in transmit and receive modes, which allows effective handling of even advanced protocols. The support includes:

- · Preamble and frame synchronization inserted into transmitted frames
- · Full frame synchronization of received frames
- Simple address matching of received frames in hardware, further configurable address and frame filtering supported through sequencer
- · Support for variable length frames
- · Automated CRC calculation and verification
- · Configurable bit ordering, with the most or least significant bit transmitted and received first

The frame format support is controlled by the Frame Controller (FRC).

2.12 Hardware CRC Support

EFR32 supports a configurable CRC generation in transmit and verification in receive mode:

- 8, 16, 24 or 32 bit CRC value
- · Configurable polynomial and initialization value
- · Optional inversion of CRC value over air
- Configurable CRC byte ordering
- · Support for multiple CRC values calculated and verified per transmitted or received frame
- The CRC module is typically controlled by the Frame Controller (FRC) for in-line operations in transmit and receive modes. Alternatively, the CRC module may be accessed directly from software to calculate and verify CRC data.

2.13 Convolutional Encoding / Decoding

EFR32 includes hardware support for convolutional encoding and decoding, for forward error correction (FEC). This feature is performed by the Frame Controller (FRC) module:

- · Constraint length configurable up to 7, for the highest robustness
- · Configurable puncturing, to achieve rates between 1/2 rate and full rate
- · Configurable soft decision or hard decision decoding
- · Convolutional coding may be used together with the symbol interleaver to improve robustness against burst errors

2.14 Binary Block Encoding / Decoding

EFR32 includes hardware support for binary block encoding and decoding, both performed real-time in the transmit and receive path. This is performed in the Frame Controller (FRC) module:

The block coding works on blocks of up to 16 bits of data and adds parity bits to be capable of single or multiple bit corrections by the receiver.

- · One or more parity bits can be added and verified
- · Bit error correction
- · Lookup-codes can be used to implement virtually any block coding scheme

2.15 Data Encryption and Authentication

EFR32 has hardware support for AES encryption, decryption and authentication modes. These security operations can be performed on data in RAM or any data buffer, without further CPU intervention. The key size is 128 bits.

AES modes of operations directly supported by the EFR32 hardware are listed in Table 2.2 AES Modes of Operation With Hardware Support on page 35. In addition to these modes, other modes can also be implemented by using combinations of modes. For example, the CCM mode can be implemented using the CTR and CBC-MAC modes in combination.

Table 2.2. AES Modes of Operation With Hardware Support

AES Mode	Encryption / Decryption	Authentication	Comment
ECB	Yes	-	Electronic Code Book
CTR	Yes	-	Counter mode
ССМ	Yes	Yes	Counter with CBC-MAC
CCM*	Yes	Yes	CCM with encryption-only and integrity-only capabilities
GCM	Yes	Yes	Galois Counter Mode
CBC	Yes	-	Cipher Block Chaining
CBC-MAC	-	Yes	Cipher Block Chaining, Message Authentication Code
CMAC	-	Yes	Cipher-based MAC
CFB	Yes	-	Cipher Feedback
OFB	Yes	-	Output Feedback

The CRYPTO module can operate directly on data buffers provided by the BUFC module. It is also possible to provide data directly from the embedded Cortex-M4 or via DMA.

2.16 Timers

EFR32 includes multiple timers, as can be seen from Table 2.3 EFR32 Timers Overview on page 36.

Table 2.3. EFR32 Timers Overview

Timer	Number of instances	Typical clock source	Overview
RTCC	1 (2)	Low frequency (LFXO or LFRCO)	32 bit Real Time Counter and Calendar, typically used to enable wakeup on compare match. A second RTC module is used by the radio software drivers for accurately timing inactive periods in the radio communication protocol.
PROTIMER	1	High frequency (HFXO or HFRCO)	16+16+32 bit Protocol Timer, typically used to accurately con- trol detailed RF protocol timing in transmit and receive modes.
TIMER	2	High frequency (HFXO or HFRCO)	16 bit general purpose timer.
WTIMER	2	High frequency (HFXO or HFRCO)	32 bit general purpose timer.
SysTick timer	1	High frequency (HFXO or HFRCO) or low frequency (LFXO, LFRCO or ULFRCO)	24-bit SysTick timer integrated in the Cortex-M4. Typically used as an Operating System timer.
WDOG	1	Low frequency (LFXO, LFRCO or ULFRCO)	Watch dog timer. Once enabled, this module must be periodically accessed. If not, this is considered an error and the EFR32 is reset in order to recover the system.
LETIMER	1	Low frequency (LFXO, LFRCO or ULFRCO)	Low energy general purpose timer.

Advanced interconnect features allows synchronization between timers. This includes:

- · Start / stop any high frequency timer synchronized with the RTCC
- Trigger RSM state transitions based on compare timer compare match, for instance to provide clock cycle accuracy on frame transmit timing


2.17 RF Test Modes

EFR32 supports a wide range of RF test modes typically used for characterization and regulation compliance testing, including:

- · Unmodulated carrier transmit
- · Modulated carrier transmit, with internal configurable pseudo random data generator
- · Continuous data reception for Bit Error Rate (BER) measurements
- Storing of raw receiver data to RAM
- · Transmit of raw frequency data from RAM

3. System Processor





Quick Facts

What?

The industry leading Cortex-M4 processor from ARM is the CPU in the EFR32 devices.

Why?

The ARM Cortex-M4 is designed for exceptionally short response time, high code density, and high 32-bit throughput while maintaining a strict cost and power consumption budget.

How?

Combined with the ultra low energy peripherals available in EFR32 devices, the Cortex-M4 process-or's Harvard architecture, 3 stage pipeline, single cycle instructions, Thumb-2 instruction set support, and fast interrupt handling make it perfect for 8-bit, 16-bit, and 32-bit applications.

3.1 Introduction

The ARM Cortex-M4 32-bit RISC processor provides outstanding computational performance and exceptional system response to interrupts while meeting low cost requirements and low power consumption.

The ARM Cortex-M4 implemented is revision r0p1.

3.2 Features

- · Harvard architecture
 - · Separate data and program memory buses (No memory bottleneck as in a single bus system)
- · 3-stage pipeline
- · Thumb-2 instruction set
 - Enhanced levels of performance, energy efficiency, and code density
- · Single cycle multiply and hardware divide instructions
 - · 32-bit multiplication in a single cycle
 - · Signed and unsigned divide operations between 2 and 12 cycles
- · Atomic bit manipulation with bit banding
 - · Direct access to single bits of data
 - · Two 1MB bit banding regions for memory and peripherals mapping to 32MB alias regions
 - · Atomic operation, cannot be interrupted by other bus activities
- 1.25 DMIPS/MHz
- · Memory Protection Unit
 - · Up to 8 protected memory regions
- 24 bits System Tick Timer for Real Time OS
- · Excellent 32-bit migration choice for 8/16 bit architecture based designs
 - Simplified stack-based programmer's model is compatible with traditional ARM architecture and retains the programming simplicity of legacy 8-bit and 16-bit architectures
- · Alligned or unaligned data storage and access
 - · Contiguous storage of data requiring different byte lengths
 - · Data access in a single core access cycle
- · Integrated power modes
 - · Sleep Now mode for immediate transfer to low power state
 - · Sleep on Exit mode for entry into low power state after the servicing of an interrupt
 - · Ability to extend power savings to other system components
- · Optimized for low latency, nested interrupts

3.3 Functional Description

For a full functional description of the ARM Cortex-M4 implementation in the EFR32 family, the reader is referred to the ARM Cortex-M4 documentation provided by ARM.

3.3.1 Interrupt Operation




Figure 3.1. Interrupt Operation

The interrupt request (IRQ) lines are connected to the Cortex-M4. Each of these lines (shown in Table 3.1 Interrupt Request Lines (IRQ) on page 40) is connected to one or more interrupt flags in one or more modules. The interrupt flags are set by hardware on an interrupt condition. It is also possible to set/clear the interrupt flags through the IFS/IFC registers. Each interrupt flag is then qualified with its own interrupt enable bit (IEN register), before being OR'ed with the other interrupt flags to generate the IRQ. A high IRQ line will set the corresponding pending bit (can also be set/cleared with the SETPEND/CLRPEND bits in ISPR0/ICPR0) in the Cortex-M4 NVIC. The pending bit is then qualified with an enable bit (set/cleared with SETENA/CLRENA bits in ISER0/ICER0) before generating an interrupt request to the core. Figure 3.1 Interrupt Operation on page 39 illustrates the interrupt system. For more information on how the interrupts are handled inside the Cortex-M4, the reader is referred to the **ARM Cortex-M4 Technical Reference Manual**.

3.3.1.1 Avoiding Extraneous Interrupts

There can be latencies in the system such that clearing an interrupt flag could take longer than leaving an Interrupt Service Routine (ISR). This can lead to the ISR being re-entered as the interrupt flag has yet to clear immediately after leaving the ISR. To avoid this, when clearing an interrupt flag at the end of an ISR, the user should execute ARM's Data Synchronization Barrier (DSB) instruction. Another approach is to clear the interrupt flag immediately after identifying the interrupt source and then service the interrupt as shown in the pseudo-code below. The ISR typically is sufficiently long to more than cover the few cycles it may take to clear the interrupt status, and also allows the status to be checked for further interrupts before exiting the ISR.

```
irqXServiceRoutine() {
   do {
     clearIrqXStatus();
     serviceIrqX();
   } while(irqXStatusIsActive());
}
```

3.3.1.2 IFC Read-clear Operation

In addition to the normal interrupt setting and clearing operations via the IFS/IFC registers, there is an additional atomic Read-clear operation that can be enabled by setting IFCREADCLEAR=1 in the MSC_CTRL register. When enabled, reads of peripheral IFC registers will return the interrupt vector (mirroring the IF register), while at the same time clearing whichever interrupt flags are set. This operation is functionally equivalent to reading the IF register and then writing the result immediately back to the IFC register.


3.3.2 Interrupt Request Lines (IRQ)

Table 3.1. Interrupt Request Lines (IRQ)

IRQ#	Source(s)
0	ЕМИ
2	WDOG0
3	WDOG1
9	LDMA
10	GPIO_EVEN
11	TIMER0
12	USART0_RX
13	USART0_TX
14	ACMP0
	ACMP1
15	ADC0
16	IDAC0
17	I2C0
18	GPIO_ODD
19	TIMER1
20	USART1_RX
21	USART1_TX
22	LEUART0
23	PCNT0
24	СМИ
25	MSC
26	CRYPTO0
27	LETIMER0
31	RTCC
33	CRYOTIMER
35	FPUEH
36	SMU
37	WTIMER0
38	VDAC0
39	LESENSE

4. Memory and Bus System





Quick Facts

What?

A low latency memory system including low energy Flash and RAM with data retention which makes the energy modes attractive.

Why?

RAM retention reduces the need for storing data in Flash and enables frequent use of the ultra low energy modes EM2 Deep Sleep and EM3 Stop.

How?

Low energy and non-volatile Flash memory stores program and application data in all energy modes and can easily be reprogrammed in system. Low leakage RAM with data retention in EM0 Active to EM3 Stop removes the data restore time penalty, and the DMA ensures fast autonomous transfers with predictable response time.

4.1 Introduction

The EFR32 contains an AMBA AHB Bus system to allow bus masters to access the memory mapped address space. A multilayer AHB bus matrix connects the 5 master bus interfaces to the AHB slaves (Figure 4.1 EFR32 Bus System on page 42). The bus matrix allows several AHB slaves to be accessed simultaneously. An AMBA APB interface is used for the peripherals, which are accessed through an AHB-to-APB bridge connected to the AHB bus matrix. The 5 AHB bus masters are:

- Cortex-M4 ICode: Used for instruction fetches from Code memory (valid address range: 0x00000000 0x1FFFFFFF)
- Cortex-M4 DCode: Used for debug and data access to Code memory (valid address range: 0x00000000 0x1FFFFFFF)
- Cortex-M4 System: Used for data and debug access to system space. It can access entire memory space except Code memory (valid address range: 0x20000000 0xFFFFFFFF)
- · DMA: Can access the entire memory space except the internal core memory region and the DMEM code region
- **Sequencer Code:** Used for instruction fetches and data accesses. Instruction fetches still come from data memory. (valid address range: 0x00000000 0x0FFFFFFF, 0x20000000 0x3FFFFFFF)
- Sequencer System: Can access entire memory space except internal core memory region and RAM code space (valid address range: 0x00000000 - 0x0FFFFFFF, 0x20000000 - 0xDFFFFFFF)
- BUFC: Can access general purpose SRAM (valid address range: 0x20000000 0x20FFFFFF)
- FRC: Can access general purpose SRAM (valid address range: 0x20000000 0x20FFFFFF)




Figure 4.1. EFR32 Bus System

4.2 Functional Description

The memory segments are mapped together with the internal segments of the Cortex-M4 into the system memory map shown by Figure 4.2 System Address Space With Core and Code Space Listing on page 43.




Figure 4.2. System Address Space With Core and Code Space Listing

Additionally, the peripheral address map is detailed by Figure 4.3 System Address Space With Peripheral Listing on page 44.




Figure 4.3. System Address Space With Peripheral Listing

The embedded SRAM is located at address 0x20000000 in the memory map of the EFR32. When running code located in SRAM starting at this address, the Cortex-M4 uses the System bus interface to fetch instructions. This results in reduced performance as the Cortex-M4 accesses stack, other data in SRAM and peripherals using the System bus interface. To be able to run code from SRAM efficiently, the SRAM is also mapped in the code space at address 0x10000000.

When running code from this space, the Cortex-M4 fetches instructions through the I/D-Code bus interface, leaving the System bus interface for data access.

The SRAM mapped into the code space can however only be accessed by the CPU and not any other bus masters, e.g. DMA. See 4.5 SRAM for more detailed info on the system SRAM.

The Sequencer RAM is used by the Sequencer for both instructions and data. This RAM is also available for general use by most AHB masters.

4.2.1 Peripheral Non-Word Access Behavior

When writing to peripheral registers, all accesses are treated as 32-bit accesses. This means that writes to a register need to be large enough to cover all bits of register, otherwise, any uncovered bits may become corrupted from the partial-word transfer. Thus, the safest practice is to always do 32-bit writes to peripheral registers.

When reading, there is generally no issue with partial word accesses, however, note that any read action (e.g. FIFO popping) will be triggered regardless of whether the actual FIFO bit-field was included in the transfer size.

Note: The implementation of bit-banding in the core is such that bit-band accesses forward the transfer size info into the actual bus transfer size, so the same restrictions apply to bit-band accesses as apply to normal read/write accesses.

4.2.2 Bit-banding

The SRAM bit-band alias and peripheral bit-band alias regions are located at 0x22000000 and 0x42000000 respectively. Read and write operations to these regions are converted into masked single-bit reads and atomic single-bit writes to the embedded SRAM and peripherals of the EFR32.

Note: Bit-banding is only available through the CPU. No other AHB masters (e.g. DMA) can perform Bit-banding operations.

Using a standard approach to modify a single register or SRAM bit in the aliased regions, would require software to read the value of the byte, half-word or word containing the bit, modify the bit, and then write the byte, half-word or word back to the register or SRAM address. Using bit-banding, this can be done in a single operation, consuming only two bus cycles. As read-writeback, bit-masking and bit-shift operations are not necessary in software, code size is reduced and execution speed improved.

The bit-band regions allow each bit in the SRAM and Peripheral areas of the memory map to be addressed. To set or clear a bit in the embedded SRAM, write a 1 or a 0 to the following address:

bit_address = 0x22000000 + (address - 0x20000000) · 32 + bit · 4

where address is the address of the 32-bit word containing the bit to modify, and bit is the index of the bit in the 32-bit word.

To modify a bit in the Peripheral area, use the following address:

bit address = $0x42000000 + (address - 0x40000000) \cdot 32 + bit \cdot 4$

4.2.3 Peripheral Bit Set and Clear

The EFR32 supports bit set and bit clear access to all peripherals except those listed in Table 4.1 Peripherals that Do Not Support Bit Set and Bit Clear on page 46. The bit set and bit clear functionality (also called Bit Access) enables modification of bit fields (single bit or multiple bit wide) without the need to perform a read-modify-write (though it is functionally equivalent). Also, the operation is contained within a single bus access (for HF peripherals), unlike the Bit-banding operation described in section 4.2.2 Bit-banding which consumes two bus accesses per operation. All AHB masters can utilize this feature.

The bit clear aliasing region starts at 0x44000000 and the bit set aliasing region starts at 0x46000000. Thus, to apply a bit set or clear operation, write the bit set or clear mask to the following addresses:

```
bit_clear_address = address + 0x04000000
bit_set_address = address + 0x06000000
```

For bit set operations, bit locations that are 1 in the bit mask will be set in the destination register:

```
register = (register OR mask)
```

For bit clear operations, bit locations that are 1 in the bit mask will be cleared in the destination register:

```
register = (register AND (NOT mask))
```

Note: It is possible to combine bit clear and bit set operations in order to arbitrarily modify multi-bit register fields, without affecting other fields in the same register. In this case, care should be taken to ensure that the field does not have intermediate values that can lead to erroneous behavior. For example, if bit clear and bit set operations are used to change an analog tuning register field from 25 to 26, the field would initially take on a value of zero. If the analog module is active at the time, this could lead to undesired behavior.

The peripherals listed in Table 4.1 Peripherals that Do Not Support Bit Set and Bit Clear on page 46 do not support Bit Access for any registers. All other peripherals do support Bit Access, however, there may be cases of certain registers that do not support it. Such registers have a note regarding this lack of support.

Table 4.1. Peripherals that Do Not Support Bit Set and Bit Clear

Module	
EMU	
RMU	
CRYOTIMER	

4.2.4 Peripherals

The peripherals are mapped into the peripheral memory segment, each with a fixed size address range according to Table 4.2 Peripherals on page 47, Table 4.3 Low Energy Peripherals on page 47 and Table 4.4 Core Peripherals on page 47.

Table 4.2. Peripherals

Address Range	Module Name
0x400E6000 - 0x400E6400	PRS
0x40022000 - 0x40022400	SMU
0x4001E000 - 0x4001E400	CRYOTIMER
0x4001C000 - 0x4001C400	GPCRC
0x4001A000 - 0x4001A400	WTIMER0
0x40018400 - 0x40018800	TIMER1
0x40018000 - 0x40018400	TIMER0
0x40010400 - 0x40010800	USART1
0x40010000 - 0x40010400	USART0
0x4000C000 - 0x4000C400	I2C0
0x4000A000 - 0x4000B000	GPIO
0x40008000 - 0x40008400	VDAC0
0x40006000 - 0x40006400	IDAC0
0x40002000 - 0x40002400	ADC0
0x40000400 - 0x40000800	ACMP1
0x40000000 - 0x40000400	ACMP0

Table 4.3. Low Energy Peripherals

Address Range	Module Name
0x40055000 - 0x40055400	LESENSE
0x40052400 - 0x40052800	WDOG1
0x40052000 - 0x40052400	WDOG0
0x4004E000 - 0x4004E400	PCNT0
0x4004A000 - 0x4004A400	LEUART0
0x40046000 - 0x40046400	LETIMER0
0x40042000 - 0x40042400	RTCC

Table 4.4. Core Peripherals

Address Range	Module Name
0xE0000000 - 0xE0040000	CM4
0x400F0000 - 0x400F0400	CRYPTO0
0x400E2000 - 0x400E3000	LDMA

Address Range	Module Name						
0x400E1000 - 0x400E1400	FPUEH						
0x400E0000 - 0x400E0800	MSC						

4.2.5 Bus Matrix

The Bus Matrix connects the memory segments to the bus masters as detailed in 4.1 Introduction.

4.2.5.1 Arbitration

The Bus Matrix uses a round-robin arbitration algorithm which enables high throughput and low latency, while starvation of simultaneous accesses to the same bus slave are eliminated. Round-robin does not assign a fixed priority to each bus master. The arbiter does not insert any bus wait-states during peak interaction. However, one wait state is inserted for master accesses occurring after a prolonged inactive time. This wait state allows for increased power efficiency during master idle time.

4.2.5.2 Peripheral Access Performance

The Bus Matrix is a multi-layer energy optimized AMBA AHB compliant bus with an internal bandwidth of 5x a single AHB interface.

The Cortex-M4, DMA Controller, and peripherals (not peripherals in the low frequency clock domain) run on clocks which can be prescaled separately. Clocks and prescaling are described in more detail in 11. CMU - Clock Management Unit . This section describes the expected bus wait states for a peripheral based on its frequency relative to the HFCLK frequency. For this discussion, PERCLK refers to a selected peripheral's clock frequency, which is some integer division of the HFCLK frequency.

4.2.5.2.1 WS0 Mode

In general, when accessing a peripheral, the latency in number of HFCLK cycles, not including master arbitration, is given by:

```
N_{bus\ cycles} = N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK}, \ best-case\ write\ accesses N_{bus\ cycles} = N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK} + 1, \ best-case\ read\ accesses N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK} - 1, \ worst-case\ write\ accesses N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK}, \ worst-case\ read\ accesses
```

where N_{slave cycles} is the throughput of the slave's bus interface in number of PERCLK cycles per transfer, including any wait cycles introduced by the slave.

Figure 4.4. Bus Access Latency (General Case)

Note that a latency of 1 cycle corresponds to 0 wait states.

Additionally, for back-to-back accesses to the same peripheral, the throughput in number of cycles per transfer is given by:

```
N_{bus\ cycles} = N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK}, write accesses N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK}, read accesses
```

Figure 4.5. Bus Access Throughput (Back-to-Back Transfers)

Lastly, in the highest performing case, where PERCLK equals HFCLK and the slave does not introduce any additional wait states, the access latency in number of cycles is given by:

```
N_{\text{bus cycles}} = 1, write accesses N_{\text{bus cycles}} = 2, read accesses
```

Figure 4.6. Bus Access Latency (Max Performance)

4.2.5.2.2 WS1 Mode

In general, when accessing a peripheral, the latency in number of HFCLK cycles, not including master arbitration, is given by:

 $N_{bus\ cycles} = N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK} + 2, \ best-case\ write\ accesses$ $N_{bus\ cycles} = N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK} + 1, \ best-case\ read\ accesses$ $N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK} + 1, \ worst-case\ write\ accesses$ $N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK}, \ worst-case\ read\ accesses$

where N_{slave cycles} is the throughput of the slave's bus interface in number of PERCLK cycles per transfer, including any wait cycles introduced by the slave.

Figure 4.7. Bus Access Latency (General Case)

Note that a latency of ${\bf 1}$ cycle corresponds to ${\bf 0}$ wait states.

Additionally, for back-to-back accesses to the same peripheral, the throughput in number of cycles per transfer is given by:

$$N_{bus\ cycles} = max\{f_{HFCLK}/f_{PERCLK}, 2\} + N_{slave\ cycles} \cdot f_{HFCLK}/f_{PERCLK}, write\ accesses$$

$$N_{bus\ cycles} = (N_{slave\ cycles} + 1) \cdot f_{HFCLK}/f_{PERCLK}, read\ accesses$$

Figure 4.8. Bus Access Throughput (Back-to-Back Transfers)

Lastly, in the highest performing case, where PERCLK equals HFCLK and the slave does not introduce any additional wait states, the access latency in number of cycles is given by:

 $N_{bus\ cycles}$ = 3, write accesses $N_{bus\ cycles}$ = 2, read accesses

Figure 4.9. Bus Access Latency (Max Performance)

4.2.5.2.3 Core Access Latency

Note that the cycle counts in the equations above is in terms of the HFCLK. When the core is prescaled from the bus clock, the core will see a reduced number of latency cycles given by:

 $N_{core\ cycles}$ = ceiling($N_{bus\ cycles} \cdot f_{HFCORECLK}/f_{HFCLK}$) where master arbitration is not included.

Figure 4.10. Core Access Latency

4.2.5.3 Bus Faults

System accesses from the core can receive a bus fault in the following condition(s):

- The core attempts to access an address that is not assigned to any peripheral or other system device. These faults can be enabled or disabled by setting the ADDRFAULTEN bit appropriately in MSC_CTRL.
- The core attempts to access a peripheral or system device that has its clock disabled. These faults can be enabled or disabled by setting the CLKDISFAULTEN bit appropriately in MSC_CTRL.
- The bus times out during an access. For example, this could happen while trying to synchronize volatile read data during an LE
 peripheral access. See 11.3.1.1 HFCLK High Frequency Clock. These faults can be enabled or disabled by setting the TIMEOUTFAULTEN bit appropriately in MSC CTRL.

In addition to any condition-specific bus fault control bits, the bus fault interrupt itself can be enabled or disabled in the same way as all other internal core interrupts.

Note: The icache flush is not triggered at the event of a bus fault. As a result, when an instruction fetch results in a bus fault, invalid data may be cached. This means that the next time the instruction that caused the bus fault is fetched, the processor core will get the invalid cached data without any bus fault. In order to avoid invalid cached data propagation to the processor core, software should manually invalidate cache by writing 1 to MSC_CMD_INVCACHE bitfield at the event of a bus fault.

4.3 Access to Low Energy Peripherals (Asynchronous Registers)

The Low Energy Peripherals are capable of running when the high frequency oscillator and core system is powered off, i.e. in energy mode EM2 Deep Sleep and in some cases also EM3 Stop. This enables the peripherals to perform tasks while the system energy consumption is minimal.

The Low Energy Peripherals are listed in Table 4.3 Low Energy Peripherals on page 47.

All Low Energy Peripherals are memory mapped, with automatic data synchronization. Because the Low Energy Peripherals are running on clocks asynchronous to the high frequency system clock, there are some constraints on how register accesses are performed, as described in the following sections.

4.3.1 Writing

Every Low Energy Peripheral has one or more registers with data that needs to be synchronized into the Low Energy clock domain to maintain data consistency and predictable operation. There are two different synchronization mechanisms on the EFR32, immediate synchronization, and delayed synchronization. Immediate synchronization is available for the RTCC, LESENSE and LETIMER, and results in an immediate update of the target registers. Delayed synchronization is used for the remaining Low Energy Peripherals, and for these peripherals, a write operation requires 3 positive edges of the clock on the Low Energy Peripheral being accessed. Registers requiring synchronization are marked "Async Reg" in their description header.

Note: On the Gecko series of devices, all LE peripherals are subject to delayed synchronization.




Figure 4.11. Write Operation to Low Energy Peripherals

4.3.1.1 Delayed Synchronization

After writing data to a register which value is to be synchronized into the Low Energy Peripheral using delayed synchronization, a corresponding busy flag in the <module_name>_SYNCBUSY register (e.g. LETIMER_SYNCBUSY) is set. This flag is set as long as synchronization is in progress and is cleared upon completion.

Note: Subsequent writes to the same register before the corresponding busy flag is cleared is not supported. Write before the busy flag is cleared may result in undefined behavior. In general the SYNCBUSY register only needs to be observed if there is a risk of multiple write access to a register (which must be prevented). It is not required to wait until the relevant flag in the SYNCBUSY register is cleared after writing a register. E.g., EM2 Deep Sleep can be entered directly after writing a register.

See Figure 4.12 Write Operation to Low Energy Peripherals on page 52 for an overview of the writing mechanism operation.




Figure 4.12. Write Operation to Low Energy Peripherals

4.3.1.2 Immediate Synchronization

In contrast to the peripherals with delayed synchronization, peripherals with immediate synchronization do not experience a register write delay for most registers. Registers are updated immediately on the peripheral write access. If such a write is done close to an edge on the clock of the peripheral, the write can be delayed until after that clock edge. This will introduce wait-states on the peripheral access.

One exception is made for commands (writing to the CMD register) in peripherals with immediate synchronization. Peripherals with immediate synchronization each have a SYNCBUSY register with a bit for the CMD register status. Commands written to a peripheral with immediate synchronization are not executed before the first peripheral clock after the write. In this period, the SYNCBUSY flag for the command register is set, indicating that the command has not yet been performed.

To maintain compatibility with earlier Gecko series, the SYNCBUSY register reserves placeholders where other register synchronization bits resided. These bits always read 0, indicating that register writes are always safe.

Note: If compatibility with earlier Gecko series is a requirement for a given application, the rules that apply to delayed synchronization with respect to SYNCBUSY should also be followed for the peripherals that support immediate synchronization.

4.3.2 Reading

When reading from a Low Energy Peripheral, the data read is synchronized regardless if it originates in the Low Energy clock domain or High Frequency clock domain. See Figure 4.13 Read Operation From Low Energy Peripherals on page 53 for an overview of the reading operation.

Note: Writing a register and then immediately reading the new value of the register may give the impression that the write operation is complete. This may not be the case. Refer to the SYNCBUSY register for correct status of the write operation to the Low Energy Peripheral.




Figure 4.13. Read Operation From Low Energy Peripherals

4.3.3 FREEZE Register

In all Low Energy Peripheral with delayed synchronization there is a <module_name>_FREEZE register (e.g. RTCC_FREEZE). The register contains a bit named REGFREEZE. If precise control of the synchronization process is required, this bit may be utilized. When REGFREEZE is set, the synchronization process is halted allowing the software to write multiple Low Energy registers before starting the synchronization process, thus providing precise control of the module update process. The synchronization process is started by clearing the REGFREEZE bit.

Note: The FREEZE register is also present on peripherals with immediate synchronization, but there it has no effect

4.4 Flash

The Flash retains data in any state and typically stores the application code, special user data and security information. The Flash memory is typically programmed through the debug interface, but can also be erased and written to from software.

- · Up to 256 KB of memory
- · Page size of 2 KB (minimum erase unit)
- · Minimum 10K erase cycles endurance
- Greater than 10 years data retention at 85 °C
- · Lock-bits for memory protection
- · Data retention in any state

4.5 SRAM

The primary task of the SRAM memory is to store application data. Additionally, it is possible to execute instructions from SRAM, and the DMA may be set up to transfer data between the SRAM, flash and peripherals.

- · Up to 32 KB of memory
- · Bit-band access support
- · Set of RAM blocks may be powered down when not in use
- Data retention of the entire memory in EM0 Active to EM3 Stop

Note: The individual RAM sections may be smaller on some parts, however, the RAM AHB slaves maintain a contiguous address map. For example, if RAM0 is half-size on a part, then RAM1 is relocated to begin immediately after RAM0's last address. Using the provided software header files and linker scripts allows handling of this remapping in an autonomous manner.

4.6 DI Page Entry Map

The DI page contains production calibration data as well as device identification information. See the peripheral chapters for how each calibration value is to be used with the associated peripheral.

The offset address is relative to the start address of the DI page (see 7.3 Functional Description).

Offset	Name	Туре	Description
0x000	CAL	RO	CRC of DI-page and calibration temperature
0x004	MODULEINFO	RO	Module trace information
0x020	EXTINFO	RO	External Component description
0x028	EUI48L	RO	EUI48 OUI and Unique identifier
0x02C	EUI48H	RO	OUI
0x030	CUSTOMINFO	RO	Custom information
0x034	MEMINFO	RO	Flash page size and misc. chip information
0x040	UNIQUEL	RO	Low 32 bits of device unique number
0x044	UNIQUEH	RO	High 32 bits of device unique number
0x048	MSIZE	RO	Flash and SRAM Memory size in kB
0x04C	PART	RO	Part description
0x050	DEVINFOREV	RO	Device information page revision
0x054	EMUTEMP	RO	EMU Temperature Calibration Information
0x060	ADC0CAL0	RO	ADC0 calibration register 0
0x064	ADC0CAL1	RO	ADC0 calibration register 1
0x068	ADC0CAL2	RO	ADC0 calibration register 2
0x06C	ADC0CAL3	RO	ADC0 calibration register 3
0x080	HFRCOCAL0	RO	HFRCO Calibration Register (4 MHz)
0x08C	HFRCOCAL3	RO	HFRCO Calibration Register (7 MHz)
0x098	HFRCOCAL6	RO	HFRCO Calibration Register (13 MHz)
0x09C	HFRCOCAL7	RO	HFRCO Calibration Register (16 MHz)
0x0A0	HFRCOCAL8	RO	HFRCO Calibration Register (19 MHz)
0x0A8	HFRCOCAL10	RO	HFRCO Calibration Register (26 MHz)
0x0AC	HFRCOCAL11	RO	HFRCO Calibration Register (32 MHz)
0x0B0	HFRCOCAL12	RO	HFRCO Calibration Register (38 MHz)
0x0E0	AUXHFRCOCAL0	RO	AUXHFRCO Calibration Register (4 MHz)
0x0EC	AUXHFRCOCAL3	RO	AUXHFRCO Calibration Register (7 MHz)
0x0F8	AUXHFRCOCAL6	RO	AUXHFRCO Calibration Register (13 MHz)
0x0FC	AUXHFRCOCAL7	RO	AUXHFRCO Calibration Register (16 MHz)
0x100	AUXHFRCOCAL8	RO	AUXHFRCO Calibration Register (19 MHz)
0x108	AUXHFRCOCAL10	RO	AUXHFRCO Calibration Register (26 MHz)
0x10C	AUXHFRCOCAL11	RO	AUXHFRCO Calibration Register (32 MHz)
0x110	AUXHFRCOCAL12	RO	AUXHFRCO Calibration Register (38 MHz)

Offset	Name	Туре	Description
0x140	VMONCAL0	RO	VMON Calibration Register 0
0x144	VMONCAL1	RO	VMON Calibration Register 1
0x148	VMONCAL2	RO	VMON Calibration Register 2
0x158	IDAC0CAL0	RO	IDAC0 Calibration Register 0
0x15C	IDAC0CAL1	RO	IDAC0 Calibration Register 1
0x168	DCDCLNVCTRL0	RO	DCDC Low-noise VREF Trim Register 0
0x16C	DCDCLPVCTRL0	RO	DCDC Low-power VREF Trim Register 0
0x170	DCDCLPVCTRL1	RO	DCDC Low-power VREF Trim Register 1
0x174	DCDCLPVCTRL2	RO	DCDC Low-power VREF Trim Register 2
0x178	DCDCLPVCTRL3	RO	DCDC Low-power VREF Trim Register 3
0x17C	DCDCLPCMPHYSSEL0	RO	DCDC LPCMPHYSSEL Trim Register 0
0x180	DCDCLPCMPHYSSEL1	RO	DCDC LPCMPHYSSEL Trim Register 1
0x184	VDAC0MAINCAL	RO	VDAC0 Cals for Main Path
0x188	VDAC0ALTCAL	RO	VDAC0 Cals for Alternate Path
0x18C	VDAC0CH1CAL	RO	VDAC0 CH1 Error Cal
0x190	OPA0CAL0	RO	OPA0 Calibration Register for DRIVESTRENGTH 0, INCBW=1
0x194	OPA0CAL1	RO	OPA0 Calibration Register for DRIVESTRENGTH 1, INCBW=1
0x198	OPA0CAL2	RO	OPA0 Calibration Register for DRIVESTRENGTH 2, INCBW=1
0x19C	OPA0CAL3	RO	OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=1
0x1A0	OPA1CAL0	RO	OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=1
0x1A4	OPA1CAL1	RO	OPA1 Calibration Register for DRIVESTRENGTH 1, INCBW=1
0x1A8	OPA1CAL2	RO	OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=1
0x1AC	OPA1CAL3	RO	OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=1
0x1D0	OPA0CAL4	RO	OPA0 Calibration Register for DRIVESTRENGTH 0, INCBW=0
0x1D4	OPA0CAL5	RO	OPA0 Calibration Register for DRIVESTRENGTH 1, INCBW=0
0x1D8	OPA0CAL6	RO	OPA0 Calibration Register for DRIVESTRENGTH 2, INCBW=0
0x1DC	OPA0CAL7	RO	OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=0
0x1E0	OPA1CAL4	RO	OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=0
0x1E4	OPA1CAL5	RO	OPA1 Calibration Register for DRIVESTRENGTH 1, INCBW=0
0x1E8	OPA1CAL6	RO	OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=0
0x1EC	OPA1CAL7	RO	OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=0

4.7 DI Page Entry Description

4.7.1 CAL - CRC of DI-page and calibration temperature

Offset		Bit Position																									
0x000	33 30 30 30 30 30 30 30 30 30 30 30 30 3										16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Access	8											S O															
Name			TEMP								CA.C																

Bit	Name	Access	Description
31:24	Reserved	Reserved for futu	ire use
23:16	TEMP	RO	Calibration temperature as an usigned int in DegC (25 = 25DegC)
15:0	CRC	RO	CRC of DI-page (CRC-16-CCITT)

4.7.2 MODULEINFO - Module trace information

Offset		Bit Position																														
0x004	31	0 - 1 - 2 - 3 - 3 - 4 - 5 - 6 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1													0																	
Access		<u>&</u>																														
Name		RESERVE																														
																٥	<u> </u>															

Bit	Name	Access	Description
31:0	RESERVED1	RO	Reserved for future use

4.7.3 EXTINFO - External Component description

Offset															Bi	t Po	sitio	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	တ	∞	7	9	5	4	3	2	_	0
Access						•						2	2								2							2	2			
Name														ECTION																		
		REV																					TYPF] -								

Bit	Name	Access	Description
31:24	Reserved	Reserved for fut	ure use
23:16	REV	RO	MCM Revision
	Value	Mode	Description
	1	REV1	Revision 1
	255	NONE	No external component present
15:8	CONNECTION	RO	Connection protocal to external interface
	Value	Mode	Description
	1	SPI	SPI control interface
	255	NONE	None
7:0	TYPE	RO	
	External Component		
	Value	Mode	Description
	1	IS25LQ040B	IS25LQ040B-JWLE1 512kB Serial Flash
	2	AT25S041	AT25S041-DWFHT 512kB Serial Flash
	255	NONE	None

4.7.4 EUI48L - EUI48 OUI and Unique identifier

Offset		Bit Position
0x028	31 30 30 29 27 27 27 27 27 27 27 27 28 29 29 29 29 29 29 29 29 29 29 29 29 29	0 - 1 - 2 - 3 - 4 - 5 - 6 - 4 - 8 - 8 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1
Access	RO	RO
Name	OUI48L	UNIQUEID

Bit	Name	Access	Description
31:24	OUI48L	RO	Lower Octet of EUI48 Organizationally Unique Identifier
23:0	UNIQUEID	RO	Unique identifier

4.7.5 EUI48H - OUI

Offset	Bit Pos	sition
0x02C	1 1 <t< th=""><th>2 4 8 7 1 0</th></t<>	2 4 8 7 1 0
Access		8
Name		OUI48H

Bit	Name	Access	Description
31:16	Reserved	Reserved for futu	ire use
15:0	OUI48H	RO	Upper two Octets of EUI48 Organizationally Unique Identifier

4.7.6 CUSTOMINFO - Custom information

Offset		Bit												t Po	ositi	on																
0x030	31	33 30 30 30 30 30 30 30 30 30 30 30 30 3										15	4	13	12	11	10	6	8	7	9	5	4	က	7	-	0					
Access		'	•				•		2					•		'		'		'								•		1	'	
Name		PARTINO R																														

Bit	Name	Access	Description
31:16	PARTNO	RO	Custom part identifier as unsigned integer (e.g. 903) 65535 for standard product
15:0	Reserved	Reserved for futu	ire use

4.7.7 MEMINFO - Flash page size and misc. chip information

Offset															Bi	t Po	sitio	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	2 4 6 2 1 0 0							7	9	5	4	က	2	_	0
Access			•	0	2	•	•			NO NO									RO								•		S S			
Name				בו אכות באכוב מוצב								TNICONIA								7071	77G - 77E								TEMPGRADE			

Bit	Name	Access	Description
31:24	FLASH_PAGE_SIZE	RO	Flash page size in bytes coded as 2 ^ ((MEM_IN-FO_PAGE_SIZE + 10) & 0xFF). le. the value 0xFF = 512 bytes.
23:16	PINCOUNT	RO	Device pin count as unsigned integer (eg. 48)
15:8	PKGTYPE	RO	Package Identifier as character
	Value	Mode	Description
	74	WLCSP	WLCSP package
	76	BGA	BGA package
	77	QFN	QFN package
	81	QFP	QFP package
7:0	TEMPGRADE	RO	Temperature Grade of product as unsigned integer enumeration
	Value	Mode	Description
	0	N40TO85	-40 to 85degC
	1	N40TO125	-40 to 125degC
	2	N40TO105	-40 to 105degC
	3	N0TO70	0 to 70degC

4.7.8 UNIQUEL - Low 32 bits of device unique number

Offset	Bit Position
0x040	33 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3
Access	S O
Name	UNIQUEL

Bit	Name	Access	Description
31:0	UNIQUEL	RO	Low 32 bits of device unique number

4.7.9 UNIQUEH - High 32 bits of device unique number

Offset	Bit Position
0x044	33 34 4 5 6 6 6 7 7 8 8 10
Access	8
Name	UNIQUEH

Bit	Name	Access	Description
31:0	UNIQUEH	RO	High 32 bits of device unique number

4.7.10 MSIZE - Flash and SRAM Memory size in kB

Offset	Bit P	osition								
0x048	33 30 30 30 30 30 30 30 30 30 30 30 30 3	15 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1								
Access	8	OS OS								
Name	SRAM	FLASH								

Bit	Name	Access	Description
31:16	SRAM	RO	Ram size, kbyte count as unsigned integer (eg. 16)
15:0	FLASH	RO	Flash size, kbyte count as unsigned integer (eg. 128)

4.7.11 PART - Part description

Offset		Bit Po	osition							
0x04C	31 30 29 27 27 26 26 27 27 27 27 27 28 29 29 20 20 20 20 20 20 20 20 20 20 20 20 20	23 22 21 20 20 19 17 17	1 1							
Access	S O	RO	8							
Name	PROD_REV	DEVICE_FAMILY	DEVICE_NUMBER							

	PRG	DEV	DE)
Bit	Name	Access	Description
31:24	PROD_REV	RO	Production revision as unsigned integer
23:16	DEVICE_FAMILY	RO	Device Family
	Value	Mode	Description
	16	EFR32MG1P	EFR32 Mighty Gecko Family Series 1 Device Config 1
	17	EFR32MG1B	EFR32 Mighty Gecko Family Series 1 Device Config 1
	18	EFR32MG1V	EFR32 Mighty Gecko Family Series 1 Device Config 1
	19	EFR32BG1P	EFR32 Blue Gecko Family Series 1 Device Config 1
	20	EFR32BG1B	EFR32 Blue Gecko Family Series 1 Device Config 1
	21	EFR32BG1V	EFR32 Blue Gecko Family Series 1 Device Config 1
	25	EFR32FG1P	EFR32 Flex Gecko Family Series 1 Device Config 1
	26	EFR32FG1B	EFR32 Flex Gecko Family Series 1 Device Config 1
	27	EFR32FG1V	EFR32 Flex Gecko Family Series 1 Device Config 1
	28	EFR32MG12P	EFR32 Mighty Gecko Family Series 1 Device Config 2
	29	EFR32MG12B	EFR32 Mighty Gecko Family Series 1 Device Config 2
	30	EFR32MG12V	EFR32 Mighty Gecko Family Series 1 Device Config 2
	31	EFR32BG12P	EFR32 Blue Gecko Family Series 1 Device Config 2
	32	EFR32BG12B	EFR32 Blue Gecko Family Series 1 Device Config 2
	33	EFR32BG12V	EFR32 Blue Gecko Family Series 1 Device Config 2
	37	EFR32FG12P	EFR32 Flex Gecko Family Series 1 Device Config 2
	38	EFR32FG12B	EFR32 Flex Gecko Family Series 1 Device Config 2
	39	EFR32FG12V	EFR32 Flex Gecko Family Series 1 Device Config 2
	40	EFR32MG13P	EFR32 Mighty Gecko Family Series 1 Device Config 3
	41	EFR32MG13B	EFR32 Mighty Gecko Family Series 1 Device Config 3
	42	EFR32MG13V	EFR32 Mighty Gecko Family Series 1 Device Config 3
	43	EFR32BG13P	EFR32 Blue Gecko Family Series 1 Device Config 3
	44	EFR32BG13B	EFR32 Blue Gecko Family Series 1 Device Config 3

Bit	Name	Access	Description
	45	EFR32BG13V	EFR32 Blue Gecko Family Series 1 Device Config 3
	46	EFR32ZG13P	EFR32 Zen Gecko Family Series 1 Device Config 3
	49	EFR32FG13P	EFR32 Flex Gecko Family Series 1 Device Config 3
	50	EFR32FG13B	EFR32 Flex Gecko Family Series 1 Device Config 3
	51	EFR32FG13V	EFR32 Flex Gecko Family Series 1 Device Config 3
	52	EFR32MG14P	EFR32 Mighty Gecko Family Series 1 Device Config 4
	53	EFR32MG14B	EFR32 Mighty Gecko Family Series 1 Device Config 4
	54	EFR32MG14V	EFR32 Mighty Gecko Family Series 1 Device Config 4
	55	EFR32BG14P	EFR32 Blue Gecko Family Series 1 Device Config 4
	56	EFR32BG14B	EFR32 Blue Gecko Family Series 1 Device Config 4
	57	EFR32BG14V	EFR32 Blue Gecko Family Series 1 Device Config 4
	58	EFR32ZG14P	EFR32 Zen Gecko Family Series 1 Device Config 4
	61	EFR32FG14P	EFR32 Flex Gecko Family Series 1 Device Config 4
	62	EFR32FG14B	EFR32 Flex Gecko Family Series 1 Device Config 4
	63	EFR32FG14V	EFR32 Flex Gecko Family Series 1 Device Config 4
	71	EFM32G	EFM32 Gecko Device Family
	71	G	EFM32 Gecko Device Family
	72	EFM32GG	EFM32 Giant Gecko Device Family
	72	GG	EFM32 Giant Gecko Device Family
	73	TG	EFM32 Tiny Gecko Device Family
	73	EFM32TG	EFM32 Tiny Gecko Device Family
	74	EFM32LG	EFM32 Leopard Gecko Device Family
	74	LG	EFM32 Leopard Gecko Device Family
	75	EFM32WG	EFM32 Wonder Gecko Device Family
	75	WG	EFM32 Wonder Gecko Device Family
	76	ZG	EFM32 Zero Gecko Device Family
	76	EFM32ZG	EFM32 Zero Gecko Device Family
	77	HG	EFM32 Happy Gecko Device Family
	77	EFM32HG	EFM32 Happy Gecko Device Family
	81	EFM32PG1B	EFM32 Pearl Gecko Family Series 1 Device Config 1
	83	EFM32JG1B	EFM32 Jade Gecko Family Series 1 Device Config 1
	85	EFM32PG12B	EFM32 Pearl Gecko Family Series 1 Device Config 2
	87	EFM32JG12B	EFM32 Jade Gecko Family Series 1 Device Config 2
	100	EFM32GG11B	EFM32 Giant Gecko Family Series 1 Device Config 1
	103	EFM32TG11B	EFM32 Tiny Gecko Family Series 1 Device Config 1
	106	EFM32GG12B	EFM32 Giant Gecko Family Series 1 Device Config 2
	120	EZR32LG	EZR32 Leopard Gecko Device Family

Bit	Name	Access	Description
	121	EZR32WG	EZR32 Wonder Gecko Device Family
	122	EZR32HG	EZR32 Happy Gecko Device Family
15:0	DEVICE_NUMBER	RO	Part number as unsigned integer (e.g. 233 for EFR32BG1P 233 F256GM48-B0)

4.7.12 DEVINFOREV - Device information page revision

Offset															Bi	t Pc	siti	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Access																													2			
																												0077) 			
Name																																
																												ב נו	>			

Bit	Name	Access	Description						
31:8	Reserved	Reserved for futu	ure use						
7:0	DEVINFOREV	RO DEVINFO layout revision as unsigned integer (initially 1							

4.7.13 EMUTEMP - EMU Temperature Calibration Information

														Bi	t Po	siti	on													
31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	6	∞	7	9	2	4	က	7 7	- 0
						•						•			•				•						•		S)		
																											MOC	: :)		
																											-MPR			
																											⊢			
	31	30	30 30 29	30 31 32 32 38 39 31	31 30 29 28 27	31 30 29 27 27 26	31 30 29 27 27 26 26 25	31 22 23 24 25 24 24	31 30 30 27 28 27 28 27 28 27 28 29 20 20 20 20 20 20 20 20 20 20 20 20 20	31 22 23 24 25 25 27 28 27 28 27 28 27 28 28 29 20 20 21 22 23 24 25 26 27 27 28 28 28 28 28 28 28 28 28 28 28 28 28	31 30 28 28 27 28 27 28 28 27 28 29 20 21 22 23 23 24 25 27 27 28 28 29 29 20 20 20 20 20 20 20 20 20 20 20 20 20	25 22 22 23 20 20 20 20 20 20 20 20 20 20 20 20 20	31 30 28 28 27 28 27 28 27 28 20 21 20 21 29	30 30 28 27 28 24 24 22 21 20 19 19				Bit Position 31 24 25 27 28 30 41 41 41 41 41 41 41 41 41 4										MONOM		TEMPROOM RO 4 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1

Bit	Name	Access	Description
31:8	Reserved	Reserved for futu	ire use
7:0	EMUTEMPROOM	RO	EMU_TEMP temperature reading at room

4.7.14 ADC0CAL0 - ADC0 calibration register 0

Offset															Bi	t Po	siti	on														
0x060	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access			O _A								2			0	2				•		80	•				(2	1		2	2	
Name					GAIN2V5					ALC CEDEFORM	71135127			3/61-19-14-0	7						GAIN1V25					, ; ; ; ; ; ; ; ; ; ; ; ; ; ; ; ; ; ; ;	NEGSEOFFSEI 1V25			OFFSET11/25	-	

Bit	Name	Access	Description
31	Reserved	Reserved for	future use
30:24	GAIN2V5	RO	Gain for 2.5V reference
23:20	NEGSEOFFSET2V5	RO	Negative single ended offset for 2.5V reference
19:16	OFFSET2V5	RO	Offset for 2.5V reference
15	Reserved	Reserved for	future use
14:8	GAIN1V25	RO	Gain for 1.25V reference
7:4	NEGSEOFFSET1V25	RO	Negative single ended offset for 1.25V reference
3:0	OFFSET1V25	RO	Offset for 1.25V reference

4.7.15 ADC0CAL1 - ADC0 calibration register 1

Offset															Bi	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access			S O						2				2	•					RO					(2				2			
Name					GAIN5VDIFF									OFFORTEVOICE	- I						GAINVDD						NEGSEOFFSELVDD			OEESETVOD) - -	

Bit	Name	Access	Description
31	Reserved	Reserved for	future use
30:24	GAIN5VDIFF	RO	Gain for for 5V differential reference
23:20	NEGSEOFFSET5VDIFF	RO	Negative single ended offset with for 5V differential reference
19:16	OFFSET5VDIFF	RO	Offset for 5V differential reference
15	Reserved	Reserved for	future use
14:8	GAINVDD	RO	Gain for VDD reference
7:4	NEGSEOFFSETVDD	RO	Negative single ended offset for VDD reference
3:0	OFFSETVDD	RO	Offset for VDD reference

4.7.16 ADC0CAL2 - ADC0 calibration register 2

Offset															Ві	t Po	siti	on														
0x068	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Access			•	•			•							•	•					•						0	2	•			2	
Name																											1 2 A V D			OFFSETOXYOR	01127400	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:24	Reserved	Reserved for futu	ire use
23:20	Reserved	Reserved for futu	ire use
19:16	Reserved	Reserved for futu	ire use
15:8	Reserved	Reserved for futu	ire use
7:4	NEGSEOFFSET2XVDD	RO	Negative single ended offset for 2XVDD reference
3:0	OFFSET2XVDD	RO	Offset for 2XVDD reference

4.7.17 ADC0CAL3 - ADC0 calibration register 3

Offset															Bi	t Po	siti	on														
0x06C	33	30	59	78	27	56	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	∞	7	9	5	4	က	7	_	0
Access																						(2									
																						ŗ										
Nama																							AD1									
Name																						ָ נ	I EMPRE									
																						Ĺ	≥ - -									

Bit	Name	Access	Description
31:16	Reserved	Reserved for futu	ire use
15:4	TEMPREAD1V25	RO	Temperature reading at 1V25 reference
3:0	Reserved	Reserved for futu	ire use

4.7.18 HFRCOCAL0 - HFRCO Calibration Register (4 MHz)

Offset															Bi	t Po	siti	on														
0x080	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Access			2		RO	0	2	RO		RO				RO							C	2							RO		'	
Name		VBEETC	_ _		FINETUNINGEN	2	CLAUIV	LDOHP		CMPBIAS				FREQRANGE							Ē								TUNING			

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for	future use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for	future use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.19 HFRCOCAL3 - HFRCO Calibration Register (7 MHz)

Offset			Bit Position		
0x08C	30 30 29 28	27 28 24 27 27 27 27 27 27 27 27 27 27 27 27 27	02 01 11 11 12 14 14 14 14 14 14 14 14 14 14 14 14 14	11 12 13 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 16 16 16 16 16 16 16 16 16 16 16 16 16	0 ω 4 m 0 t 0
Access	RO	8 8 8 8 8 8 9 8 9 8 9 8 9 8 9 9 9 9 9 9	RO	RO	RO
Name	VREFTC	CLKDIV LDOHP CMPBIAS	FREQRANGE	FINETUNING	TUNING

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for	future use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for	future use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.20 HFRCOCAL6 - HFRCO Calibration Register (13 MHz)

Offset	Bit Position									
0x098	30 30 28 28	27 26 25 25 23 23 23 27 27	20 20 118 129 141 141 141 141 141 141 141 141 141 14	11 11 12 13 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 15 16 16 16 16 16 16 16 16 16 16 16 16 16	0 0 4 6 7 - 0					
Access	RO	80 80 80 RO	RO	RO	RO					
Name	VREFTC	CLKDIV LDOHP CMPBIAS	FREQRANGE	FINETUNING	TUNING					

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for	future use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for	future use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.21 HFRCOCAL7 - HFRCO Calibration Register (16 MHz)

Offset		Bit Position																														
0x09C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access			2		8	0	2	RO		8		S S					RO								RO							
Name		VBEETC.	_		FINETUNINGEN	2 2	CLKUIV	LDOHP		CMPBIAS		FREQRANGE								Ē								TUNING				

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for	future use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for	future use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.22 HFRCOCAL8 - HFRCO Calibration Register (19 MHz)

Offset	Bit Position									
0x0A0	330 30 29 28	25 24 25 25 27 27 27 27 27 27 27 27 27 27 27 27 27	20 19 17 17 17 17 17 17 17 17 17 17 17 17 17	11 11 12 13 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 15 16 16 16 16 16 16 16 16 16 16 16 16 16	0 0 4 6 7 - 0					
Access	0 G	0	RO	RO	RO					
Name	VREFTC	CLKDIV LDOHP CMPBIAS	FREQRANGE	FINETUNING	TUNING					

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for futu	ıre use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ure use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.23 HFRCOCAL10 - HFRCO Calibration Register (26 MHz)

Offset															Ві	t Po	siti	on														
0x0A8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Access			2	•	RO	0	2	RO		RO				80		•						2							RO			
Name		VBEETC.	_		FINETUNINGEN	210	CLKUIV	LDOHP		CMPBIAS				FREQRANGE							Ē								TUNING			

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for futu	ıre use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ıre use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.24 HFRCOCAL11 - HFRCO Calibration Register (32 MHz)

Offset															Ві	t Po	siti	on														
0x0AC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Access			2	•	RO	0	2	RO		RO				80		•						2							RO			
Name		VBEETC.	_		FINETUNINGEN	210	CLKUIV	LDOHP		CMPBIAS				FREQRANGE							F								TUNING			

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.25 HFRCOCAL12 - HFRCO Calibration Register (38 MHz)

Offset															Ві	t Po	siti	on														
0x0B0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Access			2	•	RO	0	2	RO		RO				8	•	•						2							RO			
Name		VBEETC	_		FINETUNINGEN	210	CLKUIV	LDOHP		CMPBIAS				FREQRANGE							Ē								TUNING			

Bit	Name	Access	Description
31:28	VREFTC	RO	HFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	HFRCO enable reference for fine tuning
26:25	CLKDIV	RO	HFRCO Clock Output Divide
24	LDOHP	RO	HFRCO LDO High Power Mode
23:21	CMPBIAS	RO	HFRCO Comparator Bias Current
20:16	FREQRANGE	RO	HFRCO Frequency Range
15:14	Reserved	Reserved for futu	ıre use
13:8	FINETUNING	RO	HFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ıre use
6:0	TUNING	RO	HFRCO Tuning Value

4.7.26 AUXHFRCOCAL0 - AUXHFRCO Calibration Register (4 MHz)

Offset															Ві	t Po	siti	on														
0x0E0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	1	10	6	ω	7	9	5	4	က	2	_	0
Access			2		RO		2	RO		RO				RO		•					C	2					•		RO			
Name		CETTO			FINETUNINGEN	2 2	CLKUIV	ГРОНР		CMPBIAS				FREGRANGE							C								TUNING			_

Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ıre use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.27 AUXHFRCOCAL3 - AUXHFRCO Calibration Register (7 MHz)

Offset															Bi	t Po	siti	on														
0x0EC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Access			2		RO	0	2	RO		RO				RO							C	2							RO			
Name		75557	_		FINETUNINGEN		CLKUIV	ГРОНР		CMPBIAS				FREQRANGE							C	5							TUNING			

·			
Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.28 AUXHFRCOCAL6 - AUXHFRCO Calibration Register (13 MHz)

Offset			Bit Position		
0x0F8	31 30 29 28 27	25 25 25 22 22 22 22 23 23 23 23 23 23 23 23 24 24 25 25 25 25 25 25 25 25 25 25 25 25 25	20 19 10 17 17 17 14 17	11 11 12 13 14 15 17 17 17 17 17 17 17 17 17 17 17 17 17	0 0 4 6 0 - 0
Access	RO RO	8 8 8 8 8 9 8 9 9 9 9 9 9 9 9 9 9 9 9 9	NO NO	NO NO	RO
Name	VREFTC	IV HP 3IAS	FREQRANGE	FINETUNING	TUNING

Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ıre use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.29 AUXHFRCOCAL7 - AUXHFRCO Calibration Register (16 MHz)

Offset			Bit Position											
0x0FC	30 30 29 28	27 28 24 27 22 23 23 23 23	20 19 19 17 17 14 17 17 17 17 17 17 17 17 17 17 17 17 17	11 12 13 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 14 15 15 16 16 16 16 16 16 16 16 16 16 16 16 16	0 ω 4 m 0 t 0									
Access	RO	8 8 8 8 8 9 8 9 9 9 9 9 9 9 9 9 9 9 9 9												
Name	VREFTC	CLKDIV LDOHP CMPBIAS	FREQRANGE	FINETUNING	TUNING									

Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.30 AUXHFRCOCAL8 - AUXHFRCO Calibration Register (19 MHz)

Offset			Bit Position											
0x100	31 30 29 28 27	22 23 24 25 25 27 27 27 27 27 27 27 27 27 27 27 27 27	20 19 17 17 17 17 17 17 17 17 17 17 17 17 17	11 11 12 13	0 0 4 6 7 - 0									
Access	RO RO	8 8 8 8 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9												
Name	VREFTC	CLKDIV	FREQRANGE	FINETUNING	TUNING									

Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for fu	uture use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for fu	uture use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.31 AUXHFRCOCAL10 - AUXHFRCO Calibration Register (26 MHz)

Offset															Ві	t Po	siti	on														
0x108	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Access			2		8		2	RO	8 8 8																							
Name		VECTO	_		FINETUNINGEN	2	CLADIV	LDOHP		CMPBIAS				FREQRANGE															TUNING			

Bit	Name	Access	Description
DIL	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.32 AUXHFRCOCAL11 - AUXHFRCO Calibration Register (32 MHz)

Offset															Ві	t Po	siti	on														
0x10C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Access			2		RO	C	2	RO	2 2 2																							
Name		CFIIII	-		FINETUNINGEN	2 2	CLKDIV	ГРОНР		CMPBIAS				FREGRANGE							F								TUNING			

Bit	Name	Access	Description
DIL	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.33 AUXHFRCOCAL12 - AUXHFRCO Calibration Register (38 MHz)

Offset															Ві	t Po	siti	on														
0x110	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Access			2	•	RO	0	2																									
Name		VBEETC.	_		FINETUNINGEN	210	CLKUIV	LDOHP		CMPBIAS				FREQRANGE							Ē								TUNING			

Bit	Name	Access	Description
31:28	VREFTC	RO	AUXHFRCO Temperature Coefficient Trim on Comparator Reference
27	FINETUNINGEN	RO	AUXHFRCO enable reference for fine tuning
26:25	CLKDIV	RO	AUXHFRCO Clock Output Divide
24	LDOHP	RO	AUXHFRCO LDO High Power Mode
23:21	CMPBIAS	RO	AUXHFRCO Comparator Bias Current
20:16	FREQRANGE	RO	AUXHFRCO Frequency Range
15:14	Reserved	Reserved for futu	ire use
13:8	FINETUNING	RO	AUXHFRCO Fine Tuning Value
7	Reserved	Reserved for futu	ire use
6:0	TUNING	RO	AUXHFRCO Tuning Value

4.7.34 VMONCAL0 - VMON Calibration Register 0

Offset															Bit	: Po	sitio	on														
0x140	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access			2			2	2		й О О													() Y			(2			0	2	
Name			ALIAY DDZV30111NESCOANSE			AI TAV/DD2V98THRESEINE				ALTAY/DD4//86THBESCOABSE	7			AI TAV/DD1V86THDESEINE				AVDD3V88THRESCOARSE	AV DD2V 9011 XEOODANGE				AVDDZV981 HRESFINE				AVDD1V861HRESCOARSE			AVOD4V86THDESEINE		

Bit	Name	Access	Description
31:28	ALTAVDD2V98THRESCOARSE	RO	ALTAVDD 2.98 V Coarse Threshold Adjust
27:24	ALTAVDD2V98THRESFINE	RO	ALTAVDD 2.98 V Fine Threshold Adjust
23:20	ALTAVDD1V86THRESCOARSE	RO	ALTAVDD 1.86 V Coarse Threshold Adjust
19:16	ALTAVDD1V86THRESFINE	RO	ALTAVDD 1.86 V Fine Threshold Adjust
15:12	AVDD2V98THRESCOARSE	RO	AVDD 2.98 V Coarse Threshold Adjust
11:8	AVDD2V98THRESFINE	RO	AVDD 2.98 V Fine Threshold Adjust
7:4	AVDD1V86THRESCOARSE	RO	AVDD 1.86 V Coarse Threshold Adjust
3:0	AVDD1V86THRESFINE	RO	AVDD 1.86 V Fine Threshold Adjust

4.7.35 VMONCAL1 - VMON Calibration Register 1

Offset	Bit Position																															
0x144	31	30	29	20 22 23 24 25 25 27 28 20 20 20 20 20 20 20 20 20 20 20 20 20					20	19	18	17	16	15	4	13	12	7	10	0	8	7	9	5	4	က	2	_	0			
Access		٥	2			٥	2			0	2				2			0	2				RO			(2	•		0	2	
Name			IOUZ V 30 I II NE SOCOANSE			ENISCHEDER FINE			IO01V86THRESCOARSE R					DO41/06TUBESEINE	IOU I VOO I II KESPIINE				DVDDZV881 HKESCOAKSE				DVDD2V98THRESFINE				DVDD1V861HKESCOAKSE			DVDD4V86THPESEINE		

Bit	Name	Access	Description
31:28	IO02V98THRESCOARSE	RO	IO0 2.98 V Coarse Threshold Adjust
27:24	IO02V98THRESFINE	RO	IO0 2.98 V Fine Threshold Adjust
23:20	IO01V86THRESCOARSE	RO	IO0 1.86 V Coarse Threshold Adjust
19:16	IO01V86THRESFINE	RO	IO0 1.86 V Fine Threshold Adjust
15:12	DVDD2V98THRESCOARSE	RO	DVDD 2.98 V Coarse Threshold Adjust
11:8	DVDD2V98THRESFINE	RO	DVDD 2.98 V Fine Threshold Adjust
7:4	DVDD1V86THRESCOARSE	RO	DVDD 1.86 V Coarse Threshold Adjust
3:0	DVDD1V86THRESFINE	RO	DVDD 1.86 V Fine Threshold Adjust

4.7.36 VMONCAL2 - VMON Calibration Register 2

Offset			Bit P	osition			
0x148	31 30 29 28 27	22 23 24 25 26 27 27 23 23 23 23 23 23 23 23 23 23 23 23 23	19 19 19 16 17 17 16	7 4 5 4 5 6 7 7	11 0 8	7 6 4	0 1 2 3
Access	RO	RO RO	RO	RO	RO	RO	RO
Name	FVDD2V98THRESCOARSE	FVDD2V98THRESFINE FVDD1V86THRESCOARSE	FVDD1V86THRESFINE	PAVDD2V98THRESCOARSE	PAVDD2V98THRESFINE	PAVDD1V86THRESCOARSE	PAVDD1V86THRESFINE

Bit	Name	Access	Description
31:28	FVDD2V98THRESCOARSE	RO	FVDD 2.98 V Coarse Threshold Adjust
27:24	FVDD2V98THRESFINE	RO	FVDD 2.98 V Fine Threshold Adjust
23:20	FVDD1V86THRESCOARSE	RO	FVDD 1.86 V Coarse Threshold Adjust
19:16	FVDD1V86THRESFINE	RO	FVDD 1.86 V Fine Threshold Adjust
15:12	PAVDD2V98THRESCOARSE	RO	PAVDD 2.98 V Coarse Threshold Adjust
11:8	PAVDD2V98THRESFINE	RO	PAVDD 2.98 V Fine Threshold Adjust
7:4	PAVDD1V86THRESCOARSE	RO	PAVDD 1.86 V Coarse Threshold Adjust
3:0	PAVDD1V86THRESFINE	RO	PAVDD 1.86 V Fine Threshold Adjust

4.7.37 IDAC0CAL0 - IDAC0 Calibration Register 0

Offset	Bit Position											
0x158	31 30 29 28 27 27 26 25 27	23 22 21 20 20 19 17 17	41 14 12 11 11 10 0 0 8	L 0								
Access	RO	RO	RO	S S								
Name	SOURCERANGE3TUNING	SOURCERANGE2TUNING	SOURCERANGE1TUNING	SOURCERANGE0TUNING								

Bit	Name	Access	Description
31:24	SOURCERANGE3TUNING	RO	Calibrated middle step (16) of current source mode range 3
23:16	SOURCERANGE2TUNING	RO	Calibrated middle step (16) of current source mode range 2
15:8	SOURCERANGE1TUNING	RO	Calibrated middle step (16) of current source mode range 1
7:0	SOURCERANGE0TUNING	RO	Calibrated middle step (16) of current source mode range 0

4.7.38 IDAC0CAL1 - IDAC0 Calibration Register 1

Offset	Bit Position											
0x15C	31 30 29 28 27 27 26 25 24	0 0 1 1 2 3 4 5 6 7 8 8 6 8 7 6 9 8 8 8 8 8 8 8 8 8 8 8 8 8 8 8 8 8 8	8									
Access	RO	8 8	RO									
Name	SINKRANGE3TUNING	SINKRANGE2TUNING SINKRANGE1TUNING	SINKRANGEOTUNING									

Bit	Name	Access	Description
31:24	SINKRANGE3TUNING	RO	Calibrated middle step (16) of current sink mode range 3
23:16	SINKRANGE2TUNING	RO	Calibrated middle step (16) of current sink mode range 2
15:8	SINKRANGE1TUNING	RO	Calibrated middle step (16) of current sink mode range 1
7:0	SINKRANGE0TUNING	RO	Calibrated middle step (16) of current sink mode range 0

4.7.39 DCDCLNVCTRL0 - DCDC Low-noise VREF Trim Register 0

Offset	Bit Position																															
0x168	31 30 30 29 29 27 27 26 26 26 27 27								23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	_∞	7	6	5	4	က	2	_	0
Access	8 0									RO							S O															
Name		3V0LNATT1 F										17/8 NIATT1								OTT VIV 10/11	O I I WAI I O A I							OTT VIN 10/11	01188110			

Bit	Name	Access	Description
31:24	3V0LNATT1	RO	DCDC LNVREF Trim for 3.0V output, LNATT=1
23:16	1V8LNATT1	RO	DCDC LNVREF Trim for 1.8V output, LNATT=1
15:8	1V8LNATT0	RO	DCDC LNVREF Trim for 1.8V output, LNATT=0
7:0	1V2LNATT0	RO	DCDC LNVREF Trim for 1.2V output, LNATT=0

4.7.40 DCDCLPVCTRL0 - DCDC Low-power VREF Trim Register 0

Offset	Bit Position											
0x16C	31 30 29 28 27 27 26 26 27 27	23 22 22 21 20 119 149 149 149 149 149 149 149 149 149	5 4 5 7 7 0 6 8	V 0 0 4 8 0 T 0								
Access	RO	RO	RO	RO								
Name	1V8LPATT0LPCMPBIAS1	1V2LPATT0LPCMPBIAS1	1V8LPATT0LPCMPBIAS0	1V2LPATT0LPCMPBIAS0								

Bit	Name	Access	Description
31:24	1V8LPATT0LPCMPBIAS1	RO	DCDC LPVREF Trim for 1.8V output, LPATT=0, LPCMPBIAS=1
23:16	1V2LPATT0LPCMPBIAS1	RO	DCDC LPVREF Trim for 1.2V output, LPATT=0, LPCMPBIAS=1
15:8	1V8LPATT0LPCMPBIAS0	RO	DCDC LPVREF Trim for 1.8V output, LPATT=0, LPCMPBIAS=0
7:0	1V2LPATT0LPCMPBIAS0	RO	DCDC LPVREF Trim for 1.2V output, LPATT=0, LPCMPBIAS=0

4.7.41 DCDCLPVCTRL1 - DCDC Low-power VREF Trim Register 1

Offset		Bit Po	sition	
0x170	31 30 29 28 27 27 26 25 27	23 22 22 21 20 119 149 149 149 149 149 149 149 149 149	6 9 9 8	L 0 0 4 8 0 L 0
Access	RO	RO	RO	RO
Name	1V8LPATT0LPCMPBIAS3	1V2LPATT0LPCMPBIAS3	1V8LPATT0LPCMPBIAS2	1V2LPATT0LPCMPBIAS2

Bit	Name	Access	Description
31:24	1V8LPATT0LPCMPBIAS3	RO	DCDC LPVREF Trim for 1.8V output, LPATT=0, LPCMPBIAS=3
23:16	1V2LPATT0LPCMPBIAS3	RO	DCDC LPVREF Trim for 1.2V output, LPATT=0, LPCMPBIAS=3
15:8	1V8LPATT0LPCMPBIAS2	RO	DCDC LPVREF Trim for 1.8V output, LPATT=0, LPCMPBIAS=2
7:0	1V2LPATT0LPCMPBIAS2	RO	DCDC LPVREF Trim for 1.2V output, LPATT=0, LPCMPBIAS=2

4.7.42 DCDCLPVCTRL2 - DCDC Low-power VREF Trim Register 2

Offset		Bit Po	sition	
0x174	31 30 29 28 27 27 26 26 27 27	23 22 22 21 20 119 119 119 119 119 119 119 119 119 11	4 5 6 6 6 7 8 <t< th=""><th>r 0 0 4 m 0 t 0</th></t<>	r 0 0 4 m 0 t 0
Access	RO	RO	RO	RO
Name	3V0LPATT1LPCMPBIAS1	1V8LPATT1LPCMPBIAS1	3V0LPATT1LPCMPBIAS0	1V8LPATT1LPCMPBIAS0

Bit	Name	Access	Description
31:24	3V0LPATT1LPCMPBIAS1	RO	DCDC LPVREF Trim for 3.0V output, LPATT=1, LPCMPBIAS=1
23:16	1V8LPATT1LPCMPBIAS1	RO	DCDC LPVREF Trim for 1.8V output, LPATT=1, LPCMPBIAS=1
15:8	3V0LPATT1LPCMPBIAS0	RO	DCDC LPVREF Trim for 3.0V output, LPATT=1, LPCMPBIAS=0
7:0	1V8LPATT1LPCMPBIAS0	RO	DCDC LPVREF Trim for 1.8V output, LPATT=1, LPCMPBIAS=0

4.7.43 DCDCLPVCTRL3 - DCDC Low-power VREF Trim Register 3

Offset															Bi	t Po	siti	on														
0x178	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	19	ဝ	∞	7	9	5	4	က	2	_	0
Access		0 0																														
Name				A1441	ũ							41/8 DATT4 DOMDBIAS3									3VULPATITLPCIMPBIASZ							1V8I PATT1I PCMPBIAS2				

Bit	Name	Access	Description
31:24	3V0LPATT1LPCMPBIAS3	RO	DCDC LPVREF Trim for 3.0V output, LPATT=1, LPCMPBIAS=3
23:16	1V8LPATT1LPCMPBIAS3	RO	DCDC LPVREF Trim for 1.8V output, LPATT=1, LPCMPBIAS=3
15:8	3V0LPATT1LPCMPBIAS2	RO	DCDC LPVREF Trim for 3.0V output, LPATT=1, LPCMPBIAS=3
7:0	1V8LPATT1LPCMPBIAS2	RO	DCDC LPVREF Trim for 1.8V output, LPATT=1, LPCMPBIAS=2

4.7.44 DCDCLPCMPHYSSEL0 - DCDC LPCMPHYSSEL Trim Register 0

Offset															Bi	t Po	siti	on														
0x17C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Access																					2							2	2			
Name																				T CONTIGUENCE TO SERVICE TO SERVI	LPOMPHIOSELLPAIII							OTT ACT LINGS VILLENDO	_			

Bit	Name	Access	Description
31:16	Reserved	Reserved for futu	ire use
15:8	LPCMPHYSSELLPATT1	RO	DCDC LPCMPHYSSEL Trim, LPATT=1
7:0	LPCMPHYSSELLPATT0	RO	DCDC LPCMPHYSSEL Trim, LPATT=0

4.7.45 DCDCLPCMPHYSSEL1 - DCDC LPCMPHYSSEL Trim Register 1

Offset		Bit Po	sition	
0x180	31 30 29 28 27 27 26 26 27 27	22 22 23 20 19 19 14 14 14 15 17 17 19 19 19 19 19 19 19 19 19 19 19 19 19	4 7 7 7 7 7 7 7 7 8	ν Θ ω 4 ω ν τ Ο
Access	RO	RO	RO	RO
Name	LPCMPHYSSELLPCMPBIAS3	LPCMPHYSSELLPCMPBIAS2	LPCMPHYSSELLPCMPBIAS1	LPCMPHYSSELLPCMPBIAS0

Bit	Name	Access	Description
31:24	LPCMPHYSSELLPCMPBIAS3	RO	DCDC LPCMPHYSSEL Trim, LPCMPBIAS=3
23:16	LPCMPHYSSELLPCMPBIAS2	RO	DCDC LPCMPHYSSEL Trim, LPCMPBIAS=2
15:8	LPCMPHYSSELLPCMPBIAS1	RO	DCDC LPCMPHYSSEL Trim, LPCMPBIAS=1
7:0	LPCMPHYSSELLPCMPBIAS0	RO	DCDC LPCMPHYSSEL Trim, LPCMPBIAS=0

4.7.46 VDAC0MAINCAL - VDAC0 Cals for Main Path

Offset															Bi	t Po	siti	on														
0x184	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Access				•		2						2					0	2					(2	•				(2		
Name					NIGT > I A I A GO A MAIGT GO INIA O	GAINERKI KINIVUDANAEXI PIIN					CAINEDBTDIMOVE						CAINEDBTDIM41/26							GAINERRIRIMZV5LN						GAINERKI KIMI VZSLN		

Bit	Name	Access	Description
31:30	Reserved	Reserved for futu	ire use
29:24	GAINERRTRIMVDDANAEXTPIN	RO	Gain Error Trim Value for DAC main output using references VDDANA and EXTPIN
23:18	GAINERRTRIM2V5	RO	Gain Error Trim Value for DAC main output using reference 2V5
17:12	GAINERRTRIM1V25	RO	Gain Error Trim Value for DAC main output using reference 1V25
11:6	GAINERRTRIM2V5LN	RO	Gain Error Trim Value for DAC main output using reference 2V5LN
5:0	GAINERRTRIM1V25LN	RO	Gain Error Trim Value for DAC main output using reference 1V25LN

4.7.47 VDAC0ALTCAL - VDAC0 Cals for Alternate Path

Offset															Bi	t Po	sitio	on														
0x188	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	- 9	5	_	۲	2	_	0
Access					٥	2					0	2					0	2					(2						RO		
Name					CAINEBBIBINATORANAEXTBINALT						+ ^ 1/ (2/) (1 + 1 + 1 + 1 + 1 + 1 + 1 + 1 + 1 + 1	GAINERRIRINGVOALI					GAINEBBTBIM1//25AI T							GAINERRIRIMZVSCNALI						GAINERRTRIM1V25LNALT		

Bit	Name	Access	Description
31:30	Reserved	Reserved for futu	ire use
29:24	GAINERRTRIMVDDANAEXTPI- NALT	RO	Gain Error Trim Value for DAC alternative output using references VDDANA and EXTPIN
23:18	GAINERRTRIM2V5ALT	RO	Gain Error Trim Value for DAC alternative output using reference 2V5
17:12	GAINERRTRIM1V25ALT	RO	Gain Error Trim Value for DAC alternative output using reference 1V25
11:6	GAINERRTRIM2V5LNALT	RO	Gain Error Trim Value for DAC alternative output using reference 2V5LN
5:0	GAINERRTRIM1V25LNALT	RO	Gain Error Trim Value for DAC alternative output using reference 1V25LN

4.7.48 VDAC0CH1CAL - VDAC0 CH1 Error Cal

Offset															Ві	it Po	siti	on														
0x18C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access				•	•		•							•	•	•						<u> </u>	2			(2				8	
Name																							GAINERRIRIMONIB			<u> </u>	GAINERRI KINICHTA				OFFSETTRIM	

							O
Bit	Name	Access	Description				
31:12	Reserved	Reserved for	future use				
11:8	GAINERRTRIMCH1B	RO	Gain Error Trim Va	alue for Channe	I 1 for reference	s 2V	5LN, 2V5
7:4	GAINERRTRIMCH1A	RO	Gain Error Trim Va 1V25, VDDANA, E		I 1 for reference	s 1V	'25LN,
3	Reserved	Reserved for	future use				
2:0	OFFSETTRIM	RO	Input Buffer Offset	Calibration Val	ue for all DAC re	efere	ences

4.7.49 OPA0CAL0 - OPA0 Calibration Register for DRIVESTRENGTH 0, INCBW=1

Offset															Bi	it Po	siti	on														
0x190	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				80	•					RO	•	•			2			RO			0	2			0	2					2	
Name				OFFSETN						OFFSETP				940	GIMIS			GM			CM3	2			CMO	<u> </u>					5	

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.50 OPA0CAL1 - OPA0 Calibration Register for DRIVESTRENGTH 1, INCBW=1

Offset															Bi	t Po	siti	on														
0x194	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access			•	80	•					RO	•			0	2			RO			0	2			0	2	•			0	2	
Name				OFFSETN						OFFSETP					SIMB			ВМ			CM3	2			CMO	O N					5	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.51 OPA0CAL2 - OPA0 Calibration Register for DRIVESTRENGTH 2, INCBW=1

Offset															Bi	t Po	siti	on														
0x198	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access			•	8	1				•	RO	•	1		2	2			RO	•			2			0	2	•			0	2	
Name				OFFSETN						OFFSETP				2	SINIS			ВМ			CM3	2			CMO	O N				72	5	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.52 OPA0CAL3 - OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=1

Offset															Bi	t Po	siti	on														
0x19C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				80	•					RO	•				2			RO			0	2			0	2	•			0	2	
Name				OFFSETN						OFFSETP				2	5 N			GM			CM3	2			CMO	O N					<u> </u>	

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.53 OPA1CAL0 - OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=1

Offset															Bi	t Po	siti	on														
0x1A0	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Access				RO						RO		•		0	2			RO			0	2			0	2				0	2	
Name				OFFSETN						OFFSETP				C A	SINIS			В			CM3	2			CMO	S S					- - - - -	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	re use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	re use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	re use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	re use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	re use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	re use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	re use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.54 OPA1CAL1 - OPA1 Calibration Register for DRIVESTRENGTH 1, INCBW=1

Offset															Bi	t Po	siti	on														
0x1A4	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	11	10	6	8	7	9	5	4	က	2	_	0
Access			0 2							RO				2	2			RO			0	2			0	2				S	2	
Name	DFFSETN RO								OFFSETP				CV4				GM			CM3	2			CM2	2				Z.	- - - - -		

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.55 OPA1CAL2 - OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=1

Offset															Bi	t Po	siti	on														
0x1A8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				8	•					RO	•			0	2			RO			0	2				2				0	2	
Name		OFFSETN RO								OFFSETP				940	5 N			GM			CM3	2			CMO	<u> </u>					5	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.56 OPA1CAL3 - OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=1

Offset															Bi	t Po	siti	on														
0x1AC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	6	8	7	9	2	4	3	2	_	0
Access			•	8	1				•	RO	1			6	2			RO	•		0	2			2	2				2	2	
Name				OFFSETN						OFFSETP				2	SING			ВМ			CM3	2			CM2	O N				ZM2	- - - - -	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.57 OPA0CAL4 - OPA0 Calibration Register for DRIVESTRENGTH 0, INCBW=0

Offset															Bi	t Po	siti	on														
0x1D0	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access			•	8	•					RO	•				2			RO			0	2			0	2	•			0	2	
Name		OFFSETN RO								OFFSETP				2	5 N			GM			CM3	2			CMO	O N					5	

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.58 OPA0CAL5 - OPA0 Calibration Register for DRIVESTRENGTH 1, INCBW=0

Offset															Bi	t Po	siti	on														
0x1D4	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				8	•					RO	•			5	2			RO			0	2				2	•			0	2	
Name		OFFSETN RO								OFFSETP				2	5 1 1			GM			CM3	2			CMO	CIVIZ					<u> </u>	

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.59 OPA0CAL6 - OPA0 Calibration Register for DRIVESTRENGTH 2, INCBW=0

Offset	Bit Position																															
0x1D8	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				8	•				S S					5		RO			RO					RO				RO				
Name	OFFSETN							OFFSETP				2	5 1 1			GM			CM3	2			CMO	OINT N					<u> </u>			

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.60 OPA0CAL7 - OPA0 Calibration Register for DRIVESTRENGTH 3, INCBW=0

Offset	Bit Position																															
0x1DC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Access			•	8	1				80				RO			RO			RO				RO				RO					
Name	OFFSETN						OFFSETP				2	SINIS			ВМ			CM3	2		CM2						ZM2	- - - - -				

	9 9													
Bit	Name	Access	Description											
31	Reserved	Reserved for fut	ure use											
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.											
25	Reserved	Reserved for futt	ure use											
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.											
19	Reserved	Reserved for futt	ure use											
18:17	GM3	RO	Gm3 Trim Value											
16	Reserved	Reserved for future use												
15:13	GM	RO	Gm Trim Value											
12	Reserved	Reserved for fut	ire use											
11:10	CM3	RO	Compensation cap Cm3 trim value											
9	Reserved	Reserved for fut	ure use											
8:5	CM2	RO	Compensation cap Cm2 trim value											
4	Reserved	Reserved for fut	re use											
3:0	CM1	RO	Compensation cap Cm1 trim value											

4.7.61 OPA1CAL4 - OPA1 Calibration Register for DRIVESTRENGTH 0, INCBW=0

Offset															Bi	t Po	siti	on														
0x1E0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	1	0
Access			•	RO	•					RO	•				2			RO			0	2			0	2	•			0	2	
Name				OFFSETN						OFFSETP				9	GINIS			GM			CM3	2			CMO	Z NZ				7	<u> </u>	

Bit	Name	Access	Description
31	Reserved	Reserved for fut	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for fut	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for fut	ure use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for fut	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for fut	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for fut	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for fut	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.62 OPA1CAL5 - OPA1 Calibration Register for DRIVESTRENGTH 1, INCBW=0

Offset															Bi	t Po	siti	on														
0x1E4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Access				80	•					RO	•			5	2			RO			0	2			0	2	•			0	2	
Name	Z F								OFFSETP					5 N			GM			CM3	2			CMO	O N					<u> </u>		

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.63 OPA1CAL6 - OPA1 Calibration Register for DRIVESTRENGTH 2, INCBW=0

Offset															Bi	t Po	siti	on														
0x1E8	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	41	13	12	11	10	ဝ	8	7	9	5	4	က	2	_	0
Access			•	80	•					RO	•				2			8			0	2			0	2				0	2	
Name	Z H								OFFSETP				2	5 N			GM			CM3	2			CMO	O N					5		

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ire use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	IVA LISA
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ıre use
18:17	GM3	RO	Gm3 Trim Value
16	Reserved	Reserved for futu	ire use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ire use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ire use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ire use
3:0	CM1	RO	Compensation cap Cm1 trim value

4.7.64 OPA1CAL7 - OPA1 Calibration Register for DRIVESTRENGTH 3, INCBW=0

Offset															Bi	t Po	siti	on														
0x1EC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	6	8	7	9	5	4	က	2	_	0
Access				RO	•					RO	•			5	2			RO			0	2			0	2				0	2	
Name				OFFSETN						OFFSETP				2	SINIS			ВМ			CM3	2			CMO	O N				72	5	

Bit	Name	Access	Description
31	Reserved	Reserved for futu	ure use
30:26	OFFSETN	RO	OPA Inverting Input Offset Configuration Value.
25	Reserved	Reserved for futu	ure use
24:20	OFFSETP	RO	OPA Non-Inverting Input Offset Configuration Value.
19	Reserved	Reserved for futu	ure use
18:17	GM3	RO	Gm3 Trim Value
-			
16	Reserved	Reserved for futu	ure use
15:13	GM	RO	Gm Trim Value
12	Reserved	Reserved for futu	ure use
11:10	CM3	RO	Compensation cap Cm3 trim value
9	Reserved	Reserved for futu	ure use
8:5	CM2	RO	Compensation cap Cm2 trim value
4	Reserved	Reserved for futu	ure use
3:0	CM1	RO	Compensation cap Cm1 trim value

5. Radio Transceiver





Quick Facts

What?

The Radio Transceiver provides access to transmit and receive data, radio settings and control interface.

Why?

The Radio Transceiver enables the user to communicate using a wide range of data rates, modulation and frame formats.

How?

Dynamic or fixed frame lengths, optional address recognition, flexible CRC and crypto schemes makes the EFR32 perfectly suit any application using low or medium data rate radio communication.

5.1 Introduction

The Radio Transceiver of the EFR32 enables the user to control a wide range of settings and options for tailoring radio operation precisely to the users need. It provides access to the transmit and receive data buffers and supports both dynamic and static frame lengths, as well as automatic address filtering and CRC insertion/verification.

As seen in the Radio Overview illustration (Figure 5.1 Radio Overview on page 114), the radio consists of several modules all responsible for specific tasks. Please refer to the abbreviations section (Appendix 1. Abbreviations) for a comprehensive description of acronyms.




Figure 5.1. Radio Overview


During transmission (TX), the Radio Controller enables the SYNTH, Modulator and PA. The Modulator requests data from the Frame Controller, which reads data from a buffer. Based upon modulation format and data to send, the Modulator manipulates the SYNTH to output the correct frequency and phase. When the whole frame has been transmitted, the radio can automatically switch to receive mode.

In receive mode (RX), the radio controller enables the LNA, SYNTH, Mixer, ADC and Demodulator. The Demodulator searches for valid frames according to modulation format and data rate. If a frame is detected, the demodulated data is handed to the Frame Controller, which stores the data in the Buffer. When the complete frame has been received (determined by the Frame Controller), it is possible to either go to TX or stay in RX to search for a new frame.

The Radio Transceiver interface is accessible through software drivers provided by Silicon Labs.

6. DBG - Debug Interface





Quick Facts

What?

The Debug Interface is used to program and debug EFR32 devices.

Why?

The Debug Interface makes it easy to re-program and update the system in the field, and allows debugging with minimal I/O pin usage.

How?

The Cortex-M4 supports advanced debugging features. EFR32 devices can use a minimum of two port pins for debugging or programming. The internal and external state of the system can be examined with debug extensions supporting instruction or data access break and watch points.

6.1 Introduction

The EFR32 devices include hardware debug support through a 2-pin serial-wire debug (SWD) interface or a 4-pin Joint Test Action Group (JTAG) interface.

For more technical information about the debug interface the reader is referred to:

- · ARM Cortex-M4 Technical Reference Manual
- · ARM CoreSight Components Technical Reference Manual
- ARM Debug Interface v5 Architecture Specification
- IEEE Standard for Test Access Port and Boundary-Scan Architecture, IEEE 1149.1-2013

6.2 Features

- · Debug Access Port Serial Wire JTAG (DAP SWJ-DP)
 - Implements the ADIv5 debug interface
- Authentication Access Point (AAP)
 - · Implements various user commands
- · Flash Patch and Breakpoint (FPB) unit
 - · Implement breakpoints and code patches
- · Data Watch point and Trace (DWT) unit
 - · Implement watch points, trigger resources and system profiling
- Instrumentation Trace Macrocell (ITM)
 - · Application-driven trace source that supports printf style debugging

6.3 Functional Description

Operation of the available debug interface is described in the following sections.

6.3.1 Debug Pins

The following pins are the debug connections for the device:

- Serial Wire Clock Input and Test Clock Input (SWCLKTCK): This pin is enabled after power-up and has a built-in pull down.
- Serial Wire Data Input/Output and Test Mode Select Input (SWDIOTMS): This pin is enabled after power-up and has a built-in pull-up.
- Test Data Output (TDO): This pin is assigned to JTAG functionality after power-up. However, it remains in high-Z state until the first valid JTAG command is received.
- Test Data Input (TDI): This pin is assigned to JTAG functionality after power-up. However, it remains in high-Z state until the first valid JTAG command is received. Once enabled, the pin has a built-in pull-up.

The debug pins have pull-down and pull-up enabled by default, so leaving them enabled may increase the current consumption if left connected to supply or ground. The debug pins can be enabled and disabled through GPIO_ROUTEPEN, see 31.3.4.2.3 Disabling Debug Connections. Remember that upon disabling the debug pins, debug contact with the device is lost once the DAP SWJ-DP power request bits are deasserted. By default after power cycle the part's debug pins are in JTAG mode. If during debugging session the pins are switched to SWD mode, a power cycle is required to bring restore the pins to JTAG mode.

6.3.2 Debug and EM2 Deep Sleep/EM3 Stop

Leaving the debugger connected when issuing a WFI or WFE to enter EM2 Deep Sleep or EM3 Stop will make the system enter a special EM2 Deep Sleep. This mode differs from regular EM2 Deep Sleep and EM3 Stop in that the high frequency clocks are still enabled, and certain core functionality is still powered in order to maintain debug-functionality. Because of this, the current consumption in this mode is closer to EM1 Sleep and it is therefore important to deassert the power requests in the DAP SWJ-DP and disconnect the debugger before doing current consumption measurements.

6.3.3 Authentication Access Point

The Authentication Acces Point (AAP) is a set of registers that provide a minimal amount of debugging and system level commands. The AAP registers contain commands to issue a FLASH erase, a system reset, a CRC of user code pages, and stalling the system bus. The user must program the APSEL bit field to 255 inside of the ARM DAP SWJ Debug Port SELECT register to access the AAP. The AAP is only accessible from a debugger and not from the core.

6.3.3.1 System Bus Stall

The system bus can be stalled at any time using the SYSBUSSTALL register bit. Once the SYSBUSSTALL is set, the system bus will remain stalled until SYSBUSSTALL is cleared. While the system bus is stalled, only the registers inside the Cortex-M4, AAP and the debugger can be accessed. The SYSBUSSTALL register is available at all times through the AAP.

6.3.3.2 Command Key

The AAP uses a command key to enable the DEVICEERASE and SYSRESETREQ AAP commands. The command key must be written with the correct key in order for the commands to execute.

6.3.3.3 Device Erase

The device can be erased by stalling the system bus, writing AAP_CMDKEY, and then writing the DEVICEERASE register bit. Upon writing the command bit, the ERASEBUSY bit is asserted. The ERASEBUSY bit will be de-asserted once the erase is complete. The SYSRESETREQ bit must then be set to resume a normal debugger session. The DEVICEERASE register is available at all times through the AAP once the CMDKEY is entered.

6.3.3.4 System Reset

The system can be reset by writing AAP_CMDKEY followed by writing the SYSRESTREQ register bit. This must be done after asserting DEVICEERASE or CRCREQ. Depending on the reset level setting for system reset, asserting SYSRESETREQ will either reset the entire AAP register space or just the SYSRESETREQ bit. See 9.3.1 Reset Levels for more details on reset levels. The SYSRESETREQ register is available at all times through the AAP once the CMDKEY is enetered.

6.3.3.5 User Flash Page CRC

The CRCREQ command initiates a CRC calculation on a given Flash Page. The CRC is only available on the Main, User Data, and Lock Bit pages. It is highly recommended that the system bus is stalled before any CRCREQ commands are issued. The CRC calculation uses the on chip CRC block configured in 32 bit CRC mode. The Flash Page address for the CRCREQ command is written to the CRCADDR register. After issuing the CRCREQ, the CRCBUSY flag is asserted. Once the CRCBUSY flag is de-asserted, the resulting page CRC can be found in the CRCRESULT register. Once issuing a CRC command, the CPU is stalled and remains stalled until a system reset occurs. Multiple CRC requests can occur before resetting the system. However, a CRC request that occurs while the CRCBUSY flag is asserted will be ignored. The CRC registers are available at all times through the AAP.

6.3.4 Debug Lock

The debug access to the Cortex-M4 is locked by clearing the Debug Lock Word (DLW) and resetting the device, see 7.3.2 Lock Bits (LB) Page Description.

When debug access is locked, the debugger can access the DAP SWJ-DP and AAP registers. However, the connection to the Cortex-M4 core and the whole bus-system is blocked. This mechanism is controlled by the Authentication Access Port (AAP) as illustrated by Figure 6.1 AAP - Authentication Access Port on page 117.




Figure 6.1. AAP - Authentication Access Port

If the DLW is cleared, the device is locked. If the device is locked and the the AAP Lock Word (ALW) has not been cleared, it can be unlocked by writing a valid key to the AAP_CMDKEY register and then setting the DEVICEERASE bit of the AAP_CMD register via the debug interface. This operation erases the main block of flash, clears all lock bits, and debug access to the Cortex-M4 and bus-system is enabled. The operation takes tens of mili seconds to complete. Note that the SRAM contents will also be deleted during a device erase, while the UD-page is not erased.

The debugger may read the status of the device erase from the AAP_STATUS register. When the ERASEBUSY bit is set low after DEVICEERASE of the AAP_CMD register is set, the debugger may set the SYSRESETREQ bit in the AAP_CMD register. After reset, the debugger may resume a normal debug session through the AHB-AP.

6.3.5 AAP Lock

Take extreme caution when using this feature. Once the AAP has been locked, the state of the FLASH can not be changed via the debugger.

6.3.6 Debugger Reads of Actionable Registers

Some peripheral registers cause particular actions when read, e.g FIFOs which pop and IFC registers which clear the IF flags when read. This can cause problems when debugging and the user wants to read the value without triggering the read action. For this reason, by default, the peripherals will not execute these triggered actions when an attached debugger is performing the read accesses through the AAP. To override this behavior, the debugger can configure the MASTERTYPE bitfield of the Cortex-M4 AHB Access Port CSW register in order to emulate a core access when performing system bus transfers.

Note:

Registers with actionable reads are noted in their register descriptions. Refer to Table 1.1 Register Access Types on page 26.

6.3.7 Debug Recovery

Debug recovery is the ability to stall the system bus before the Cortex-M4 executes code. For example, the first few instructions may disconnect the debugger pins. When this occurs it is difficult to connect the debugger and halt the Cortex-M4 before the Cortex-M4 starts to execute. By holding down pin reset, issuing the System Bus Stall AAP instruction, then releasing pin reset, the debugger can stall the system bus before the Cortex-M4 has a chance to execute. Because the system is under reset during this procedure the Debugger can not look for ACK's from the part. Once the system bus is stalled, the FLASH can be erased by issuing the AAP_CMDKEY and then the writting the DEVICEERASE in the AAP_CMD register.

6.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	AAP_CMD	W1	Command Register
0x004	AAP_CMDKEY	W1	Command Key Register
0x008	AAP_STATUS	R	Status Register
0x00C	AAP_CTRL	RW	Control Register
0x010	AAP_CRCCMD	W1	CRC Command Register
0x014	AAP_CRCSTATUS	R	CRC Status Register
0x018	AAP_CRCADDR	RW	CRC Address Register
0x01C	AAP_CRCRESULT	R	CRC Result Register
0x0FC	AAP_IDR	R	AAP Identification Register

6.5 Register Description

6.5.1 AAP_CMD - Command Register

Offset															Bi	it Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•		'	•		•				•		•	'	•	•													1	0	0
Access																															W K	W1
Name																															SYSRESETREQ	DEVICEERASE

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	SYSRESETREQ	0	W1	System Reset Request
	A system reset reques	st is generated v	vhen set to	1. This register is write enabled from the AAP_CMDKEY register.
0	DEVICEERASE	0	W1	Erase the Flash Main Block, SRAM and Lock Bits
	erased. This also inc	ludes the Debu	g Lock Wo	in block is erased, the SRAM is cleared and then the Lock Bit (LB) page is ord (DLW), causing debug access to be enabled after the next reset. The changed, but the User data page Lock Word (ULW) is erased. This register

6.5.2 AAP_CMDKEY - Command Key Register

is write enabled from the AAP_CMDKEY register.

Offset	Bit Position
0x004	33 34 37 38 39 30 30 31 32 33 34 35 36 37 38 40
Reset	00000000000000000000000000000000000000
Access	*
Name	WRITEKEY

Bit	Name	Reset	Access	Description
31:0	WRITEKEY	0x00000000	W1	CMD Key Register
	The key value mus	t be written to this	register to	write enable the AAP_CMD register.
	Value	Mode		Description
	0xCFACC118	WRITEEN		Enable write to AAP_CMD

6.5.3 AAP_STATUS - Status Register

Offset															Ві	t Po	siti	on														
0x008	31	30	59	78	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	7	_	0
Reset				•		•		•	•					•	•							•			•		•	•		•	0	0
Access																															œ	2
Name																															LOCKED	ERASEBUSY

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	LOCKED	0	R	AAP Locked
	Set when the AAP is I	ocked, .e.g the	AAP Lock	Word AAP lsb bits are not 0xF
0	ERASEBUSY	0	R	Device Erase Command Status
	This bit is set when a	device erase is	executing.	

6.5.4 AAP_CTRL - Control Register

Offset															Bi	it Po	ositi	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•		•		•					•					•						•		•		•	•	•			0
Access																																A M
Name																																SYSBUSSTALL

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	SYSBUSSTALL	0	RW	Stall the System Bus
	When this bit is set,	the system bus	is stalled. C	nly the Cortex registers are accessible

6.5.5 AAP_CRCCMD - CRC Command Register

Offset															Bi	t Pc	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	3	2	_	0
Reset						•								'														•				0
Access																																W1
Name																																CRCREQ

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	CRCREQ	0	W1	CRC Request
	A CRC request is ger	nerated when se	t to 1. This	command is not available if debug access or AAP is locked.

6.5.6 AAP_CRCSTATUS - CRC Status Register

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset																																0
Access																																~
Name																																CRCBUSY

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	CRCBUSY	0	R	CRC Calculation is Busy
	Set when the CRC ca	lculation is exec	cuting. Will	transition from 1 to 0 on valid data.

6.5.7 AAP_CRCADDR - CRC Address Register

Offset													Bi	t Po	sitio	on													
0x018	33	29	28	27	26	25	24	2 2	27 27	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	က	7	1 0
Reset														0x000000x0															
Access														S S	: : :														
Name														CRCADDR															
Bit	Name	!				Rese	et		A	cces	s	Des	crip	tion															
31:0	CRCA	DDR	2			0x00	0000	000	R'	W		Star	ting	Pag	je A	ddr	ress	for	CR	CE	xec	utio	n						

6.5.8 AAP_CRCRESULT - CRC Result Register

Set this to the address the CRC executes on.

Offset															Bit	Posi	ior	n													
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	15	7	4 6	2 2	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		00000000000000000000000000000000000000																													
Access																~															
Name																CRCRESULT															

Bit	Name	Reset	Access	Description
31:0	CRCRESULT	0x00000000	R	CRC Result of the CRCADDRESS
	Result of the CRC of	calculation using t	he CRCAD	DRESS.

6.5.9 AAP_IDR - AAP Identification Register

Offset	Bit Position										
0x0FC	0 1 2 3 4 5 6 7 8 8 6 10 11 12 13 14 15 16 17 18 18 18 18 18 18 18 18 18 18 18 18 18										
Reset	0x26E60011										
Access	<u>«</u>										
Name	Ω										

Bit	Name	Reset	Access	Description						
31:0	ID	0x26E60011	R	AAP Identification Register						
	Access port identification register in compliance with the ARM ADI v5 specification (JEDEC Manufacturer ID) .									

7. MSC - Memory System Controller



011001010110111001100101011110010

Quick Facts

What?

The user can perform flash memory read, read configuration and write operations through the Memory System Controller (MSC).

Why?

The MSC allows the application code, user data and flash lock bits to be stored in non-volatile flash memory. Certain memory system functions, such as program memory wait-states and bus faults are also configured from the MSC peripheral register interface, giving the developer the ability to dynamically customize the memory system performance, security level, energy consumption and error handling capabilities to the requirements at hand.

How?

The MSC integrates a low-energy flash IP with a charge pump, enabling minimum energy consumption while eliminating the need for external programming voltage to erase the memory. An easy to use write and erase interface is supported by an internal, fixed-frequency oscillator and autonomous flash timing and control reduces software complexity while not using other timer resources.

Application code may dynamically scale between high energy optimization and high code execution performance through advanced read modes.

A highly efficient low energy instruction cache reduces the number of flash reads significantly, thus saving energy. Performance is also improved when wait-states are used, since many of the wait-states are eliminated. Built-in performance counters can be used to measure the efficiency of the instruction cache.

7.1 Introduction

The Memory System Controller (MSC) is the program memory unit of the EFR32 microcontroller. The flash memory is readable and writable from both the Cortex-M4 and DMA. The flash memory is divided into two blocks; the main block and the information block. Program code is normally written to the main block. Additionally, the information block is available for special user data and flash lock bits. There is also a read-only page in the information block containing system and device calibration data. Read and write operations are supported in the energy modes EM0 Active and EM1 Sleep.

7.2 Features

- · AHB read interface
 - · Scalable access performance to optimize the Cortex-M4 code interface
 - Zero wait-state access up to 25 MHz
 - · Advanced energy optimization functionality
 - Conditional branch target prefetch suppression
 - · Cortex-M4 disfolding of if-then (IT) blocks
 - · Instruction Cache
 - · DMA read support in EM0 Active and EM1 Sleep
- · Command and status interface
 - · Flash write and erase
 - · Accessible from Cortex-M4 in EM0 Active
 - DMA write support in EM0 Active and EM1 Sleep
 - · Core clock independent flash timing
 - · Internal oscillator and internal timers for precise and autonomous flash timing
 - · General purpose timers are not occupied during flash erase and write operations
 - · Configurable interrupt erase abort
 - · Improved interrupt predictability
 - · Memory and bus fault control
- · Security features
 - · Lockable debug access
 - · Page lock bits
 - · SW mass erase lock bits
 - · Authentication Access Port (AAP) lock bits
- · End-of-write and end-of-erase interrupts

7.3 Functional Description

The size of the main block is device dependent. The largest size available is 256 KB (128 pages). The information block has 2 KB available for user data. The information block also contains chip configuration data located in a reserved area. The main block is mapped to address 0x000000000 and the information block is mapped to address 0x0FE00000. Table 7.1 MSC Flash Memory Mapping on page 126 outlines how the flash is mapped in the memory space. All flash memory is organized into 2 KB pages.

Table 7.1. MSC Flash Memory Mapping

Block	Page	Base address	Write/Erase by	Software Reada- ble?	Purpose/Name	Size
Main ¹	0	0x00000000	Software, debug	Yes	User code and data	16 KB - 256 KB
			Software, debug	Yes		
	127	0x0003F800	Software, debug	Yes		
Reserved	-	0x00040000	-	-	Reserved for flash expansion	~24 MB
Information	0	0x0FE00000	Software, debug	Yes	User Data (UD)	2 kB
	-	0x0FE00800	-	-	Reserved	-
	1	0x0FE04000	Write: Software, debug	Yes	Lock Bits (LB)	2 kB
			Erase: Debug only			
	-	0x0FE04800	-	-	Reserved	-
	2	0x0FE081B0	-	Yes	Device Information (DI)	1 kB
	-	0x0FE08400	-	-	Reserved	-
	2	0x0FE0C000	-	-		1 kB
	-	0x0FE0C400	-	-	Reserved	-
		0x0FE10000	Software, debug	Yes	Bootloader (BL)	18 kB
			-	-		
	11	0x0FE14000	-	-		
Reserved	-	0x0FE14800	-	Reserved for flash expansion	Rest of code space	-

Note:

7.3.1 User Data (UD) Page Description

This is the user data page in the information block. The page can be erased and written by software. The page is erased by the ERA-SEPAGE command of the MSC_WRITECMD register. Note that the page is not erased by a device erase operation. The device erase operation is described in 6.3.3 Authentication Access Point.

^{1.} Block/page erased by a device erase.

7.3.2 Lock Bits (LB) Page Description

This page contains the following information:

- · Main block Page Lock Words (PLWs)
- User data page Lock Word (ULWs)
- Debug Lock Word (DLW)
- Mass erase Lock Word (MLW)
- Authentication Access Port (AAP) lock word (ALW)
- Bootloader enable (CLW0)
- Pin reset soft (CLW0)

The words in this page are organized as shown in Table 7.2 Lock Bits Page Structure on page 127:

Table 7.2. Lock Bits Page Structure

127	DLW
126	ULW
125	MLW
124	ALW
122	CLW0
N	PLW[N]
1	PLW[1]
0	PLW[0]

There are 32 page lock bits per page lock word (PLW). Bit 0 refers to the first page and bit 31 refers to the last page within a PLW. Thus, PLW[0] contains lock bits for page 0-31 in the main block, PLW[1] contains lock bits for page 32-63 etc. A page is locked when the bit is 0. A locked page cannot be erased or written.

Word 127 is the debug lock word (DLW). The four LSBs of this word are the debug lock bits. If these bits are 0xF, then debug access is enabled. Debug access to the core is disabled from power-on reset until the DLW is evaluated immediately before the Cortex-M4 starts execution of the user application code. If the bits are not 0xF, then debug access to the core remains blocked.

Word 126 is the user page lock word (ULW). Bit 0 of this word is the User Data Page lock bit. Bit 1 in this word locks the Lock Bits Page. The lock bits can be reset by a device erase operation initiated from the Authentication Access Port (AAP) registers. The AAP is described in more detail in 6.3.3 Authentication Access Point. Note that the AAP is only accessible from the debug interface, and cannot be accessed from the Cortex-M4 core.

Word 125 is the mass erase lock word (MLW). Bit 0 locks the entire flash. The mass erase lock bits will not have any effect on device erases initiated from the Authenitication Access Port (AAP) registers. The AAP is described in more detail in 6.3.3 Authentication Access Point.

Word 124 is the Authentication Access Port (AAP) lock word (ALW) and the four LSBs of this word are the lock bits. If these bits are 0xF, then AAP access is enabled. If the bits are not 0xF, AAP is disabled and it is impossible to access the device through the AAP. Bit 31 of the ALW may be used to allow AAP access under controlled conditions. If bit 31 is set to 1, software running on the device can unlock AAP access using the MSC_AAPUNLOCKCMD register. If bit 31 is cleared to 0, software will not be able to use MSC_AAPUNLOCKCMD to unlock AAP access. NOTE - locking the AAP completely (including the LSBs and bit 31) is irreversible. Once the AAP is locked, it will be impossible to perform an external mass erase and the AAP lock cannot be reset. The only way to program the device when the AAP is locked is through a boot loader or by SW already loaded into the FLASH.

Word 122 is Configuration Lock Word 0 (CLW0). Bit 2 is the Pin Reset Soft bit. By default, a pin reset is handled as a soft reset (See 9.3.5 RESETn Pin Reset). Bit 1 is the bootloader enable bit. Because the state of erased flash bits is 1, the bootloader is enabled by default.

7.3.3 Device Information (DI) Page

This read-only page holds calibration data from the production test as well as a unique device ID. The page is further described in 4. Memory and Bus System.

7.3.4 Bootloader

The memory space includes an area for custom-programmed bootloaders. The available bootloader area is 18 kB for this device family. By default, the system is configured to boot directly into user software after system reset, and there is not a pre-programmed bootloader in the device. If a custom bootloader which follows Silicon Labs' bootloader recommendations outlined in *AN0003: UART Bootloader* (www.silabs.com/32bit-appnotes) is programmed into the bootloader area, or a Gecko Bootloader is programmed into the bootloader area, the system can be redirected to boot from this area by setting bit 1 in config lock word 0 (CLW0) at word 122 of the lockbit (LB) page. More information about Gecko Bootloader can be found in UG266: Silicon Labs Gecko Bootloader User's Guide for GSDK 3.2 and Lower and in UG489: Silicon Labs Gecko Bootloader User's Guide for GSDK 4.0 and Higher.

After any device reset, the bootloader area is accessible to both software reads and writes. Reading and writing of this area may be disabled with the MSC_BOOTLOADERCTRL register. Note that this register is write-once, so after writing the register, a reset of the system is required in order to change permissions again.

Note: Software should never erase "Reserved" pages when bootloader write/erase is enabled. Doing so may cause the device to become non-functional and irrevocably locked.

7.3.5 Post-reset Behavior

Calibration values are automatically written to registers by the MSC before application code startup. The values are also available to read from the DI page for later reference by software. Other information such as the device ID and production date is also stored in the DI page and is readable from software.

If the bootloader is not bypassed, the system will boot up from the bootloader at address 0x0FE10000.

7.3.6 Flash Startup

On transitions from EM2/3 to EM0, the flash must be powered up. The time this takes depends on the current operating conditions. To have a deterministic startup-time, set STDLY0 in MSC_STARTUP to 0x64 and clear STDLY1, ASTWAIT, STWSEN and STWS. This will result in a 10 us delay before the flash is ready. The system will wake up before this, but the Cortex will stall on the first access to the flash until it is ready. Execute code from RAM or cache to get a quicker startup.

To get the fastest possible startup when waking, i.e. a startup that depends on the current operating conditions, set STDLY0 to 0x28 and set ASTWAIT in MSC_STARTUP. When configured this way, the system will poll the flash to determine when it is ready, and then start execution.

For even quicker startup, run code in beginning with a set of wait-states. Set STDLY0 to 0x32, STDLY1 to 0x32, and set ASTWAIT and STWSEN. Then configure STWS in MSC_STARTUP to the number of waitstates to run with. With this setup, sampling will begin with the given number of waitstates after 5 us, and the system will run with this number of waitstates for the remaining 5 us before returning to normal operation

A recommended setting for MSC_STARTUP register is to leave STDLY0 at its reset value and set ASTWAIT to one for active sampling Set STWSEN to zero to bypass the second delay period.

Flash wakeup on demand is supported when wakeup from EM2/3 to EM0. Set bit PWRUPONDEMAND of register MSC_CTRL to one to enable the power up on demand. When enabled during powerup, flash will enter sleep mode and waiting for either pending flash read transaction or software command to MSC_CMD.PWRUP bit. If software command wakeup, and interrupt of MSC_IF.PWRUPF will be flaged if the MSC_IEN.PWRUPF is set

7.3.7 Wait-states

Table 7.3. Flash Wait-States

Wait-States	Frequency
WS0	no more than 25 MHz
WS1	above 25 MHz and no more than 40 MHz

7.3.7.1 One Wait-state Access

After reset, the HFCORECLK is normally 19 MHz from the HFRCO and the MODE field of the MSC_READCTRL register is set to WS1 (one wait-state). Software must not select a zero wait-state mode unless the clock is guaranteed to be 25 MHz or below, otherwise the resulting behavior is undefined. If a HFCORECLK frequency above 25 MHz is to be set by software, the MODE field of the MSC READCTRL register must be set to WS1 or WS1SCBTP before the core clock is switched to the higher frequency clock source.

When changing to a lower frequency, the MODE field of the MSC_READCTRL register must be set to WS0 or WS0SCBTP only after the frequency transition has completed. If the HFRCO is used, wait until the oscillator is stable on the new frequency. Otherwise, the behavior is unpredictable.

To run at a frequency higher than 40 MHz, WS2 or WS2SCBTP must be selected to insert two wait-states for every flash access.

7.3.7.2 Zero Wait-state Access

At 25 MHz and below, read operations from flash may be performed without any wait-states. Zero wait-state access greatly improves code execution performance at frequencies from 25 MHz and below. By default, the Cortex-M4 uses speculative prefetching and If-Then block folding to maximize code execution performance at the cost of additional flash accesses and energy consumption.

7.3.7.3 Operation Above

To run at frequencies higher than 25 MHz, MODE in MSC READCTRL must be set to WS1 or WS1SCBTP.

7.3.8 Suppressed Conditional Branch Target Prefetch (SCBTP)

MSC offers a special instruction fetch mode which optimizes energy consumption by cancelling Cortex-M4 conditional branch target prefetches. Normally, the Cortex-M4 core prefetches both the next sequential instruction and the instruction at the branch target address when a conditional branch instruction reaches the pipeline decode stage. This prefetch scheme improves performance while one extra instruction is fetched from memory at each conditional branch, regardless of whether the branch is taken or not. To optimize for low energy, the MSC can be configured to cancel these speculative branch target prefetches. With this configuration, energy consumption is more optimal, as the branch target instruction fetch is delayed until the branch condition is evaluated.

The performance penalty with this mode enabled is source code dependent, but is normally less than 1% for core frequencies from 25 MHz and below. To enable the mode at frequencies from 25 MHz and below write WS0SCBTP to the MODE field of the MSC_READCTRL register. For frequencies above 25 MHz, use the WS1SCBTP mode, and for frequencies above 40 MHz, use the WS2SCBTP mode. An increased performance penalty per clock cycle must be expected compared to WS0SCBTP mode. The performance penalty in WS1SCBTP/WS2SCBTP mode depends greatly on the density and organization of conditional branch instructions in the code.

7.3.9 Cortex-M4 If-Then Block Folding

The Cortex-M4 offers a mechanism known as if-then block folding. This is a form of speculative prefetching where small if-then blocks are collapsed in the prefetch buffer if the condition evaluates to false. The instructions in the block then appear to execute in zero cycles. With this scheme, performance is optimized at the cost of higher energy consumption as the processor fetches more instructions from memory than it actually executes. To disable the mode, write a 1 to the DISFOLD bit in the NVIC Auxiliary Control Register; see the Cortex-M4 Technical Reference Manual for details. Normally, it is expected that this feature is most efficient at core frequencies above 25 MHz. Folding is enabled by default.

7.3.10 Instruction Cache

The MSC includes an instruction cache. The instruction cache for the internal flash memory is enabled by default, but can be disabled by setting IFCDIS in MSC_READCTRL. When enabled, the instruction cache typically reduces the number of flash reads significantly, thus saving energy. In most cases a cache hit-rate of more than 70 % is achievable. When a 32-bit instruction fetch hits in the cache the data is returned to the processor in one clock cycle. Thus, performance is also improved when wait-states are used (i.e. running at frequencies above 25 MHz).

The instruction cache is connected directly to the ICODE bus on the ARM core and functions as a memory access filter between the processor and the memory system, as illustrated in Figure 7.1 Instruction Cache on page 130. The cache consists of an access filter, lookup logic, SRAM, and two performance counters. The access filter checks that the address for the access is to on-chip flash memory (instructions in RAM are not cached). If the address matches, the cache lookup logic and SRAM is enabled. Otherwise, the cache is bypassed and the access is forwarded to the memory system. The cache is then updated when the memory access completes. The access filter also disables cache updates for interrupt context accesses if caching in interrupt context is disabled. The performance counters, when enabled, keep track of the number of cache hits and misses. The cachelines are filled up continuously one word at a time as the individual words are requested by the processor. Thus, not all words of a cacheline might be valid at a given time.




Figure 7.1. Instruction Cache

By default, the instruction cache is automatically invalidated when the contents of the flash is changed (i.e. written or erased). In many cases, however, the application only makes changes to data in the flash, not code. In this case, the automatic invalidate feature can be disabled by setting AIDIS in MSC_READCTRL. The cache can (independent of the AIDIS setting) be manually invalidated by writing 1 to INVCACHE in MSC_CMD.

Note: The instruction cache flush is not triggered at the event of a bus fault. As a result, when an instruction fetch results in a bus fault, invalid data may be cached. This means that the next time the instruction that caused the bus fault is fetched, the processor core will get the invalid cached data without any bus fault. In order to avoid invalid cached data propagation to the processor core, software should manually invalidate the instruction cache by writing 1 to INVCACHE in MSC CMD at the event of a bus fault.

In general it is highly recommended to keep the cache enabled all the time. However, for some sections of code with very low cache hitrate more energy-efficient execution can be achieved by disabling the cache temporarily. To measure the hit-rate of a code-section, the built-in performance counters can be used. Before the section, start the performance counters by writing 1 to STARTPC in MSC_CMD. This starts the performance counters, counting from 0. At the end of the section, stop the performance counters by writing 1 to STOPPC in MSC_CMD. The number of cache hits and cache misses for that section can then be read from MSC_CACHEHITS and MSC_CACHEMISSES respectively. The total number of 32-bit instruction fetches will be MSC_CACHEHITS + MSC_CACHEMISSES. Thus, the cache hit-ratio can be calculated as MSC_CACHEHITS / (MSC_CACHEHITS + MSC_CACHEMISSES). When MSC_CACHEHITS overflows the CHOF interrupt flag is set. When MSC_CACHEMISSES overflows the CMOF interrupt flag is set. These flags must be cleared explicitly by software. The range of the performance counters can thus be extended by increasing a counter in the MSC interrupt routine. The performance counters only count when a cache lookup is performed. If the lookup fails, MSC_CACHEMISSES is increased. If the lookup is successful, MSC_CACHEHITS is increased. For example, a cache lookup is not performed if the cache is disabled or the code is executed from RAM.

Note: When caching of vector fetches and instructions in interrupt routines is disabled (ICCDIS in MSC_READCTRL is set), the performance counters do not count when these types of fetches occur (i.e. while in interrupt context).

By default, interrupt vector fetches and instructions in interrupt routines are also cached. Some applications may get better cache utilization by not caching instructions in interrupt context. This is done by setting ICCDIS in MSC_READCTRL. You should only set this bit based on the results from a cache hit ratio measurement. In general, it is recommended to keep the ICCDIS bit cleared. Note that look-ups in the cache are still performed, regardless of the ICCDIS setting - but instructions are not cached when cache misses occur inside

the interrupt routine. So, for example, if a cached function is called from the interrupt routine, the instructions for that function will be taken from the cache.

The cache content is not retained in EM2, EM3 and EM4. The cache is therefore invalidated regardless of the setting of AIDIS in MSC_READCTRL when entering these energy modes. Applications that switch frequently between EM0 and EM2/3 and executes the very same non-looping code almost every time will most likely benefit from putting this code in RAM. The interrupt vectors can also be put in RAM to reduce current consumption even further.

7.3.11 Low Voltage Flash Read

The devices support low voltage flash reads. Because it takes more time to read from flash with a lower voltage supply MSC_READCTRL.MODE should be programmed accordingly. It is recommended that software should follow certain sequences for supply voltage scaling up and down. See the EMU chapter for details.

Flash write/erase is not supported in low voltage mode. Any write/erase command will be ignored if flash is operated in a low voltage mode and the interrupt flag MSC IF.LVEWRITE will be set.

7.3.12 Erase and Write Operations

Both page erase and write operations require that the address is written into the MSC_ADDRB register. For erase operations, the address may be any within the page to be erased. Load the address by writing 1 to the LADDRIM bit in the MSC_WRITECMD register. The LADDRIM bit only has to be written once when loading the first address. After each word is written the internal address register ADDR will be incremented automatically by 4. The INVADDR bit of the MSC_STATUS register is set if the loaded address is outside the flash and the LOCKED bit of the MSC_STATUS register is set if the page addressed is locked. Any attempts to command erase of or write to the page are ignored if INVADDR or the LOCKED bits of the MSC_STATUS register are set. To abort an ongoing erase, set the ERASEABORT bit in the MSC_WRITECMD register.

When a word is written to the MSC_WDATA register, the WDATAREADY bit of the MSC_STATUS register is cleared. When this status bit is set, software or DMA may write the next word.

A single word write is commanded by setting the WRITEONCE bit of the MSC_WRITECMD register. The operation is complete when the BUSY bit of the MSC_STATUS register is cleared and control of the flash is handed back to the AHB interface, allowing application code to resume execution.

For a DMA write the software must write the first word to the MSC_WDATA register and then set the WRITETRIG bit of the MSC WRITECMD register. DMA triggers when the WDATAREADY bit of the MSC_STATUS register is set.

It is possible to write words twice between each erase by keeping at 1 the bits that are not to be changed. Let us take as an example writing two 16 bit values, 0xAAAA and 0x5555. To safely write them in the same flash word this method can be used:

- Write 0xFFFFAAAA (word in flash becomes 0xFFFFAAAA)
- Write 0x5555FFFF (word in flash becomes 0x5555AAAA)

Note:

- There is a maximum of two writes to the same word between each erase due to a physical limitation of the flash.
- Flash write/erase is not supported in low voltage mode. Any write/erase command will be ignored if flash is operated in a low voltage mode and the interrupt flag MSC IF.LVEWRITE will be set.
- During a write or erase, flash read accesses will be stalled, effectively halting code execution from flash. Code execution continues upon write/erase completion. Code residing in RAM may be executed during a write/erase operation.

7.3.12.1 Mass Erase

A mass erase can be initiated from software using ERASEMAIN0 MSC_WRITECMD. This command will start a mass erase of the entire flash. Prior to initiating a mass erase, MSC_MASSLOCK must be unlocked by writing 0x631A to it. After a mass erase has been started, this register can be locked again to prevent runaway code from accidentally triggering a mass erase.

The regular flash page lock bits will not prevent a mass erase. To prevent software from initiating mass erases, use the mass erase lock bits in the mass erase lock word (MLW).

7.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	MSC_CTRL	RWH	Memory System Control Register
0x004	MSC_READCTRL	RWH	Read Control Register
0x008	MSC_WRITECTRL	RW	Write Control Register
0x00C	MSC_WRITECMD	W1	Write Command Register
0x010	MSC_ADDRB	RW	Page Erase/Write Address Buffer
0x018	MSC_WDATA	RW	Write Data Register
0x01C	MSC_STATUS	R	Status Register
0x030	MSC_IF	R	Interrupt Flag Register
0x034	MSC_IFS	W1	Interrupt Flag Set Register
0x038	MSC_IFC	(R)W1	Interrupt Flag Clear Register
0x03C	MSC_IEN	RW	Interrupt Enable Register
0x040	MSC_LOCK	RWH	Configuration Lock Register
0x044	MSC_CACHECMD	W1	Flash Cache Command Register
0x048	MSC_CACHEHITS	R	Cache Hits Performance Counter
0x04C	MSC_CACHEMISSES	R	Cache Misses Performance Counter
0x054	MSC_MASSLOCK	RWH	Mass Erase Lock Register
0x05C	MSC_STARTUP	RW	Startup Control
0x074	MSC_CMD	W1	Command Register
0x090	MSC_BOOTLOADERCTRL	RW	Bootloader Read and Write Enable, Write Once Register
0x094	MSC_AAPUNLOCKCMD	W1	Software Unlock AAP Command Register
0x098	MSC_CACHECONFIG0	RW	Cache Configuration Register 0

7.5 Register Description

7.5.1 MSC_CTRL - Memory System Control Register

7.3.1 IVI	SC_CIRL	- 1414	511101	уЗ	ysı	CIII	00	·····	יו וכ	egi	3161																				
Offset														В	it P	ositi	ion														
0x000	30	87	28 7	i	8	22	24	23	22	2	20	10	5 6	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset		•	•	·		·	•		•		•	•	•	•	•	•	•										0	0	0	0	_
Access																											W.	₩ W	₩ M	S S S	₩
Name																											TIMEOUTFAULTEN	IFCREADCLEAR	PWRUPONDEMAND	CLKDISFAULTEN	ADDRFAULTEN
Bit	Name					Res	et			Ac	ces	ss	De	scri	otio	n															
31:5	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions																														
4	TIMEOU	TF	AULT	ΕN		0				RV	٧		Tin	neou	ıt B	us F	ault	Re	spo	nse	Ena	ble									
	When thi ter from a																		out	duri	ng a	n ac	ces	ss, e	.g.,	whe	n re	adin	ıg a	regi	S-
3	IFCREA	DCL	EAR		(0				RV	٧		IFC	Re	ad (Clea	rs IF														
	This bit c	ont	rols v	vha	ıt ha	арре	ens	whe	en a	an IF	-C r	egi	ster	in a	mo	dule	is re	ad.													
	Value												De	scrip	tion	1															_
	0												IFC	reg	iste	r rea	ds C). No	sid	e-ef	fect	whe	en re	eadir	ng.						_
	1													_		r rea re cl			ame	val	ue a	ıs IF	, an	nd th	e co	orres	pon	ding	g int	er-	
2	PWRUP	ONI	DEM	٩N[D (0				RV	٧		Ро	wer	Up	on D)em	and	Dui	ring	Wal	ke U	Jр								
	When se issue pov															MSC	to is	ssue	e po	wer	up re	eque	est t	to CI	MU.	If no	ot se	et, w	⁄ill a	lway	/S
1	CLKDISF	FAL	JLTEI	V		0				RV	٧		Clo	ock-	disa	blec	l Bu	s Fa	ault	Res	pon	se I	Ena	ble							
	When thi	When this bit is set, busfaults are generated on accesses to peripherals/system devices with clocks disabled																													
0	ADDRFA	NUL	TEN			1				R۷	٧		Inv	alid	Ad	dres	s Bı	us F	ault	Re	spoi	nse	Ena	able							

When this bit is set, busfaults are generated on accesses to unmapped parts of system and code address space

7.5.2 MSC_READCTRL - Read Control Register

Offset		Bit Position																														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Reset				0		•	3	Š				•											0	_		•	0	0	0			
Access				RW W			1/4/0	[} Y															RW	RW			RW	RW	X W			
Name				SCBTP				NO.															USEHPROT	PREFETCH			ICCDIS	AIDIS	IFCDIS			

Bit	Name	Reset	Access	Description
31:29	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
28	SCBTP	0	RW	Suppress Conditional Branch Target Perfetch

Enable suppressed Conditional Branch Target Prefetch (SCBTP) function. SCBTP saves energy by delaying Cortex-M conditional branch target prefetches until the conditional branch instruction is in the execute stage. When the instruction reaches this stage, the evaluation of the branch condition is completed and the core does not perform a speculative prefetch of both the branch target address and the next sequential address. With the SCBTP function enabled, one instruction fetch is saved for each branch not taken, with a negligible performance penalty.

27:26	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
25.24	MODE	0x1	RWH	Read Mode

After reset, the core clock is 19 MHz from the HFRCO and the MODE field of MSC_READCTRL register is set to WS1. The reset value is WS1 because the HFRCO may produce a frequency above 19 MHz before it is calibrated. A large wait states is associated with high frequency. When changing to a higher frequency, this register must be set to a large wait states first before the core clock is switched to the higher frequency. When changing to a lower frequency, this register should be set to lower wait states after the frequency transition has been completed. If the HFRCO is used as clock source, wait until the oscillator is stable on the new frequency to avoid unpredictable behavior. See Flash Wait-States table for the corresponding threshold for different wait-states.

	Value	Mode		Description
	0	WS0		Zero wait-states inserted in fetch or read transfers
	1	WS1		One wait-state inserted for each fetch or read transfer. See Flash Wait-States table for details
	2	WS2		Two wait-states inserted for eatch fetch or read transfer. See Flash Wait-States table for details
	3	WS3		Three wait-states inserted for eatch fetch or read transfer. See Flash Wait-States table for details
3:10	Reserved	To ensure tions	compatibility	y with future devices, always write bits to 0. More information in 1.2 Conven-
	USEHPROT	0	RW	AHB_HPROT Mode
	Use ahb_hrpot to	determine if the	instruction is	s cacheable or not
	PREFETCH	1	RW	Prefetch Mode
	Set to configure le	evel of prefetchir	ng.	
:6	Reserved	To ensure	compatibility	y with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description					
5	ICCDIS	0	RW	Interrupt Context Cache Disable					
		•	•	vector fetches and instruction fetches in interrupt context. Cache lookup will the performance counters will not count when these types of fetches occur.					
4	AIDIS	0	RW	Automatic Invalidate Disable					
	When this bit is set the	ne cache is not a	utomatical	y invalidated when a write or page erase is performed.					
3	IFCDIS	0	RW	Internal Flash Cache Disable					
	Disable instruction ca	ache for internal	flash mem	ory.					
2:0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions							

7.5.3 MSC_WRITECTRL - Write Control Register

Offset															Ві	it Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	7	_	0
Reset			•	•	•	•	•	•			•			•	•	•	•	•	•		•	•	•	•		•	•	•		•	0	0
Access																															₩	RW W
Name																															IRQERASEABORT	WREN

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	IRQERASEABORT	0	RW	Abort Page Erase on Interrupt
	When this bit is set to from Flash will halt the		1 interrupt	aborts any current page erase operation. Executing that interrupt vector
0	WREN	0	RW	Enable Write/Erase Controller
	When this bit is set, th	ne MSC write an	d erase fu	nctionality is enabled

7.5.4 MSC_WRITECMD - Write Command Register

Offset				В	it Posit	ion													
0x00C	33 33 25 28 28 28 28 28 28 28 29 26 26	25 24 23 23 22	20 20	7 2 2	16	4	13	7 7	- 6	6	ω	7	9	5	4	က	2	_	0
Reset								5	'		0			0	0	0	0	0	0
Access							25	W			W1			×	W M	W 1	M1	M1	M1
Name							i i	CLEAKWDAIA			ERASEMAINO			ERASEABORT	WRITETRIG	WRITEONCE	WRITEEND	ERASEPAGE	LADDRIM
Bit	Name	Reset	Access	Descrip	otion														
31:13	Reserved	EARWDATA 0 W1 Clear WDATA State Il set WDATAREADY and DMA request. Should only be used when no write is active. Served To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Clear wdata tions														Col	nver	7-	
12	CLEARWDATA	0	W1	Clear W	/DATA	State	9												
	Will set WDATAREAD	tet WDATAREADY and DMA request. Should only be used when no write is active. To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions																	
11:9	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions ARWDATA 0 W1 Clear WDATA State Set WDATAREADY and DMA request. Should only be used when no write is active. To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions SEMAINO 0 W1 Mass Erase Region 0 Internation 0. Before use MSC_MASSLOCK must be unlocked. To completely prevent access frow the mass erase lock-word (MLW) To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions														Col	nver	7-	
8	ERASEMAIN0	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 tions 0 W1 Clear WDATA State EADY and DMA request. Should only be used when no write is active. To ensure compatibility with future devices, always write bits to 0. More information in 1.2 tions 0 W1 Mass Erase Region 0 e of region 0. Before use MSC_MASSLOCK must be unlocked. To completely prevent access for the mass erase lock-word (MLW) To ensure compatibility with future devices, always write bits to 0. More information in 1.2 tions																	
					OCK mı	ust be	e unlo	ocke	d. To	com	plet	ely p	orev	ent	acce	ess f	from	sof	t-
7:6	Reserved		npatibility v	vith future	e device	s, alv	ways	write	bits i	o 0.	Мог	re in	forn	natio	on in	1.2	Col	nver	1-
5	ERASEABORT	0	W1	Abort E	rase Se	eque	nce												
	Writing to this bit will a	abort an ongoing	g erase sec	quence.															
4	WRITETRIG	0	W1	Word W	/rite Se	quer	nce T	rigg	er										
	Start write of the first v timeout. When ADDR two words are require	is incremented	past the p	age boun	ndary, A	DDR													
3	WRITEONCE	0	W1	Word W	/rite-Or	ice T	rigge	er											
	Write the word in MS completes. The WREI is written, but the inter	N bit in the MSC	_WRITEC	TRL regis	ster mus	st be	set in	ord	er to ι	ıse t	his o	com	mar	nd. (Only	a si	ngle	wo	rd
2	WRITEEND	0	W1	End Wr	ite Mod	le													
	Write 1 to end write m	ode when using	the WRIT	ETRIG co	ommano	d.													
1	ERASEPAGE	0	W1	Erase P	Page														
	Erase any user define be set in order to use		l by the MS	SC_ADDF	RB regis	ter. 1	Γhe W	/REI	N bit i	n the	e MS	SC_'	WRI	TEC	CTR	L re	giste	er m	ust
0	LADDRIM	0	W1	Load M	SC_AD	DRB	Into	ADI	OR										
	Load the internal write cremented automatica to the base of the pag	ally by 4 after ea																	

7.5.5 MSC_ADDRB - Page Erase/Write Address Buffer

Offset	Bit Position
0x010	33
Reset	00000000000000000000000000000000000000
Access	R ≪
Name	ADDRB
Bit	Name Reset Access Description

This register holds the page address for the erase or write operation. This register is loaded into the internal MSC_ADDR register when the LADDRIM field in MSC_WRITECMD is set.

Page Erase or Write Address Buffer

7.5.6 MSC_WDATA - Write Data Register

0x00000000

RW

ADDRB

31:0

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	0000000000															
Access																2	2															
Name																V T V U W	7															

В	it	Name	Reset	Access	Description
3	1:0	WDATA	0x00000000	RW	Write Data
		The data to be written	to the address	in MSC Al	DDR. This register must be written when the WDATAREADY bit of

The data to be written to the address in MSC_ADDR. This register must be written when the WDATAREADY bit of MSC_STATUS is set.

7.5.7 MSC_STATUS - Status Register

Offset						1		Bi	t Posit	ion									1					
0x01C	30 30 28 28	27 26	25 24	23	22	20	6 8	17	16	4	13	12	7	9	တ	∞	7	ဖ	2	4	က	7	_	0
Reset	0×0	9	S S															0	0	0	_	0	0	0
Access	<u>~</u>	٥	r															22	22	22	22	2	22	<u>~</u>
Name	PWRUPCKBDFAILCOUNT	7	WDAIAVALID															PCRUNNING	ERASEABORTED	WORDTIMEOUT	WDATAREADY	INVADDR	LOCKED	BUSY
Bit	Name		Reset		Ac	ces	s Des	scrip	tion															
31:28		FAIL-	0x0		R		Fla	sh P	ower U	lp C	hec	kerb	oar	d P	atte	rn C	hec	k Fa	ail C	our	nt			
	Name Reset Access Description PWRUPCKBDFAIL- 0x0 R Flash Power Up Checkerboard Pattern Check Fail Count COUNT This field tells how many times checkboard pattern check fail occured after a reset sequence.																							
27:24	WDATAVALID)	0x0		R		Wri	te Da	ata But	ffer \	Vali	id Fla	ag											
	This field tells I	how ma	ny valid	data	a in the	write	e buffer	, eac	h bit in	dicat	tes	one l	ouffe	er e	ntry									
23:7	Reserved		To ens	sure	compat	ibility	y with f	uture	device	es, al	lway	ys wi	ite k	oits	to 0	. Мо	re in	forn	natio	on in	1.2	? Co	nvei	n-
6	PCRUNNING		0		R		Per	form	ance (Cour	nter	rs Rı	ınni	ng										
	This bit is set we this bit is cleared		e perforr	mano	ce coun	ters	are run	ning.	When	one	pe	rform	anc	e c	ount	er re	each	es t	he n	naxi	mur	n va	lue,	
5	ERASEABOR	TED	0		R		The	Cur	rent F	ash	Era	ase (Ope	rati	on A	Abor	ted							
	When set, the	current	erase o	pera	tion wa	s ab	orted b	y inte	errupt.															
4	WORDTIMEO		0		R				rite W															
	When this bit is flash is returne in MSC_WRIT	ed to the	AHB in	terfa	ice. This																			
3	WDATAREAD	Υ	1		R		WD	ATA	Write	Rea	dy													
	When this bit is with the next 3																	regis	ster	may	be /	upd	ated	t
2	INVADDR		0		R		Inv	alid \	Nrite A	ddr	ess	or E	ras	e P	age									
	Set when softw	vare atte	empts to	load	d an inv	alid	(unma	oped)) addre	ss in	nto A	ADD	₹											
1	LOCKED		0		R		Acc	cess	Locke	d														
	When set, the	last era	se or wr	ite is		d du	e to era	ase/w	vrite ac	cess	s co	nstra	ints											
0	BUSY		0		R				/rite Bu	-														
	When set, an e	erase or	write of	perat	tion is ir	n pro	gress a	and n	iew cor	nma	nds	are	igno	orec	l									

7.5.8 MSC_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	О	8	7	9	2	4	က	2	_	0
Reset		•	'	•		•						•		•										0		0	0	0	0	0	0	0
Access																								2		22	22	22	22	2	2	<u>~</u>
Name																								LVEWRITE		WDATAOV	ICACHERR	PWRUPF	CMOF	CHOF	WRITE	ERASE

D:4	Name	Do not a	A	Description
Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8	LVEWRITE	0	R	Flash LVE Write Error Flag
	If one, flash contro	oller write comma	and received v	while in LVE mode
7	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
6	WDATAOV	0	R	Flash Controller Write Buffer Overflow
	If one, flash contro	oller write buffer o	overflow detec	cted
5	ICACHERR	0	R	ICache RAM Parity Error Flag
	If one, iCache RAI	M parity Error de	tected	
4	PWRUPF	0	R	Flash Power Up Sequence Complete Flag
	Set after MSC_CM	ID.PWRUP rece	ived, flash po	wered up complete and ready for read/write
3	CMOF	0	R	Cache Misses Overflow Interrupt Flag
	Set when MSC_C	ACHEMISSES o	verflows	
2	CHOF	0	R	Cache Hits Overflow Interrupt Flag
	Set when MSC_C	ACHEHITS over	flows	
1	WRITE	0	R	Write Done Interrupt Read Flag
	Set when a write is	s done		
0	ERASE	0	R	Erase Done Interrupt Read Flag
	Set when erase is	done		
-				

7.5.9 MSC_IFS - Interrupt Flag Set Register

Offset															Ві	it Po	siti	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	ω	7	9	2	4	က	2	_	0
Reset			'		'	•								•	'	'								0		0	0	0	0	0	0	0
Access																								W W		W W	W W	W W	W W	M1	W	W1
Name																								LVEWRITE		WDATAOV	ICACHERR	PWRUPF	CMOF	CHOF	WRITE	ERASE

Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8	LVEWRITE	0	W1	Set LVEWRITE Interrupt Flag
	Write 1 to set the	LVEWRITE interr	upt flag	
7	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6	WDATAOV	0	W1	Set WDATAOV Interrupt Flag
	Write 1 to set the	WDATAOV interr	upt flag	
5	ICACHERR	0	W1	Set ICACHERR Interrupt Flag
	Write 1 to set the	ICACHERR inter	rupt flag	
4	PWRUPF	0	W1	Set PWRUPF Interrupt Flag
	Write 1 to set the	PWRUPF interrup	ot flag	
3	CMOF	0	W1	Set CMOF Interrupt Flag
	Write 1 to set the	CMOF interrupt fl	ag	
2	CHOF	0	W1	Set CHOF Interrupt Flag
	Write 1 to set the	CHOF interrupt fl	ag	
1	WRITE	0	W1	Set WRITE Interrupt Flag
	Write 1 to set the	WRITE interrupt t	ag	
0	ERASE	0	W1	Set ERASE Interrupt Flag
	Write 1 to set the	ERASE interrupt	flag	

7.5.10 MSC_IFC - Interrupt Flag Clear Register

	_		-																										
Offset												Bi	t Po	siti	on				1				ı		T		1		
0x038	30 31	78	27	26	25	44 2	23	22	20	6	9	17	16	15	4	13	2 2	7	9	စ	∞	7	9	2	4	က	7	-	0
Reset																					0		0	0	0	0	0	0	0
Access																					(R)W1		(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name																					LVEWRITE		WDATAOV	ICACHERR	PWRUPF	CMOF	CHOF	WRITE	ERASE
Bit	Name				Rese	et		A	cces	s	Des	crip	tion																
31:9	Reserved	tions LVEWRITE 0 (R)W1 Clear LVEWRITE Interrupt Flag Write 1 to clear the LVEWRITE interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).														nvei	n-												
8	LVEWRIT	VEWRITE 0 (R)W1 Clear LVEWRITE Interrupt Flag Write 1 to clear the LVEWRITE interrupt flag. Reading returns the value of the IF and clears the corresponding interrulages (This feature must be enabled globally in MSC.).																											
		tions LVEWRITE 0 (R)W1 Clear LVEWRITE Interrupt Flag Write 1 to clear the LVEWRITE interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).														upt													
7	Reserved	tions LVEWRITE 0 (R)W1 Clear LVEWRITE Interrupt Flag Write 1 to clear the LVEWRITE interrupt flag. Reading returns the value of the IF and clears the corresponding interruflags (This feature must be enabled globally in MSC.). Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Con														nvei	n-												
6	WDATAO	V			0			(F)W1		Clea	ar W	DA1	AC	l V	nte	rrupt	Fla	g										
	Write 1 to flags (This												urns	the	valı	ue	of the	e IF	and	l cle	ars t	he c	orre	espo	ndir	ng in	iterri	upt	
5	ICACHER	iR			0			(R)W1		Clea	ar IC	ACI	ΙEF	RR I	nte	errup	t Fla	ag										
	Write 1 to flags (This												urns	the	val	ue	of the	e IF	and	d cle	ars	the o	corre	espo	ondi	ng ir	nterr	upt	
4	PWRUPF				0			(R)W1		Clea	ar P	WRL	JPF	Inte	err	upt F	lag											
	Write 1 to (This feat										ding r	etur	ns th	ie v	alue	e of	f the I	F aı	nd d	clear	s the	e co	rres	pon	ding	inte	errup	t fla	ıgs
3	CMOF				0			(R)W1		Clea	ar C	MOF	Int	terri	upt	t Flaç	j											
	Write 1 to (This feat										retu	rns t	the v	alu	e of	the	e IF a	ınd (clea	ırs th	ne co	orre	spor	ndin	g int	erru	pt fl	ags	
2	CHOF				0			(R)W1		Clea	ar C	HOF	Int	erru	upt	Flag												
	Write 1 to (This feat										retu	rns t	he v	alu	e of	the	e IF a	nd c	clea	rs th	ne co	rres	spon	nding	g int	erru	pt fla	ags	
1	WRITE				0			(R)W1		Clea	ar W	RITI	E In	terr	up	t Fla	g											
	Write 1 to (This feat										g reti	ırns	the	valu	ie o	f th	e IF	and	cle	ars t	he c	orre	spo	ndin	ıg in	terrı	upt f	lags	i
0	ERASE				0			(F)W1		Clea	ar El	RAS	E Ir	nter	rup	ot Fla	g											
	Write 1 to (This feat										g ret	urns	the	valı	ue o	of th	ne IF	and	cle	ars	the o	corre	espo	ndir	ng ir	nterr	upt 1	lags	6

7.5.11 MSC_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	7	_	0
Reset			•												•	•				•				0		0	0	0	0	0	0	0
Access																								Z.		W.	Z.	RW	Z.	₩.	₩ M	R W
Name																								LVEWRITE		WDATAOV	ICACHERR	PWRUPF	CMOF	CHOF	WRITE	ERASE

Di4	Nama	Paget -	A 00000	Description
Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8	LVEWRITE	0	RW	LVEWRITE Interrupt Enable
	Enable/disable the	e LVEWRITE inte	rrupt	
7	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
6	WDATAOV	0	RW	WDATAOV Interrupt Enable
	Enable/disable the	e WDATAOV inte	rrupt	
5	ICACHERR	0	RW	ICACHERR Interrupt Enable
	Enable/disable the	e ICACHERR inte	errupt	
4	PWRUPF	0	RW	PWRUPF Interrupt Enable
	Enable/disable the	e PWRUPF interr	upt	
3	CMOF	0	RW	CMOF Interrupt Enable
	Enable/disable the	e CMOF interrupt		
2	CHOF	0	RW	CHOF Interrupt Enable
	Enable/disable the	e CHOF interrupt		
1	WRITE	0	RW	WRITE Interrupt Enable
	Enable/disable the	e WRITE interrup	t	
0	ERASE	0	RW	ERASE Interrupt Enable
	Enable/disable the	e ERASE interrup	ot	
-				

7.5.12 MSC_LOCK - Configuration Lock Register

Offset															Bi	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset			•		1		1			·		1	1	•		1			'	•					nannan				•	1	1	
Access																									[} Y							
Name																								\L\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LOCANE							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock

Write any other value than the unlock code to lock access to MSC_CTRL, MSC_READCTRL, MSC_WRITECMD, MSC_STARTUP and MSC_AAPUNLOCKCMD. Write the unlock code to enable access. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	MSC registers are unlocked
LOCKED	1	MSC registers are locked
Write Operation		
LOCK	0	Lock MSC registers
UNLOCK	0x1B71	Unlock MSC registers

7.5.13 MSC_CACHECMD - Flash Cache Command Register

Offset															Bi	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	7	_	0
Reset				•									'		'					'									'	0	0	0
Access																														W W	W	W W
Name																														STOPPC	STARTPC	INVCACHE

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2	STOPPC	0	W1	Stop Performance Counters
	Use this commant	bit to stop the p	erformance c	ounters.
1	STARTPC	0	W1	Start Performance Counters
	Use this command	d bit to start the p	erformance o	counters. The performance counters always start counting from 0.
0	INVCACHE	0	W1	Invalidate Instruction Cache
	Use this register to	o invalidate the in	nstruction cac	che.

7.5.14 MSC_CACHEHITS - Cache Hits Performance Counter

Offset															Bi	t Po	siti	on														
0x048	31	30	29	28	27	26	25	24	23	22	21	20	19	28	17	16	15	4	13	12	7	19	6	ω	7	9	2	4	က	2	_	0
Reset																							00000x0		•	•						
Access																						1	Y									
Name																						!	CACHEHIIS									

Bit	Name	Reset	Access	Description							
31:20	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-							
19:0	CACHEHITS	0x00000	R	Cache Hits Since Last Performance Counter Start Command							
	Use to measure cache performance for a particular code section.										

7.5.15 MSC_CACHEMISSES - Cache Misses Performance Counter

Use to measure cache performance for a particular code section.

Offset															Bi	t Po	siti	on														
0x04C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	11	10	2 o	8	7	9	2	4	3	2	_	0
Reset																							0x00000									
Access																							<u>~</u>									
Name																							CACHEMISSES									
Bit	Na	ne					Re	set			Ac	ces	s l	Des	crip	tion																
31:20	Re	serve	d				To tion		ure	con	npati	bility	/ Wi	th fu	ture	dev	vices	s, alı	way	s wr	ite b	oits	s to 0.	Мо	re i	nforr	natio	on i	n 1.2	2 Co	nvei	n-
19:0	CA	CHEI	MIS	SES	S		0x0	0000	00		R			Cac	he N	liss	es S	Sinc	e L	ast	Perf	for	rman	ce C	ou	nter	Sta	rt C	om	man	d	

7.5.16 MSC_MASSLOCK - Mass Erase Lock Register

Offset															Bi	t Po	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	19	6	∞	7	9	5	4	က	2	_	0
Reset				,										•				•						000	100000	•					•	
Access																									[} Y							
Name																								\L\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LOCANE							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0001	RWH	Mass Erase Lock

Write any other value than the unlock code to lock access the the ERASEMAINn commands. Write the unlock code 631A to enable access. When reading the register, bit 0 is set when the lock is enabled. Locked by default.

Mode	Value	Description
Read Operation		
UNLOCKED	0	Mass erase unlocked
LOCKED	1	Mass erase locked
Write Operation		
LOCK	0	Lock mass erase
UNLOCK	0x631A	Unlock mass erase

7.5.17 MSC_STARTUP - Startup Control

Offset															Bi	it Po	siti	on														
0x05C	33	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			0x1			0	_	-				•	•		200	0000		•						•		•	2	UX04D	•			
Access			Z ≪			M	Z N	RW W							2	≥ Y											2	≩ Y				
Name			STWS			STWSAEN	STWSEN	ASTWAIT			STDLY1 RW STDLY0 RW																					

	STS	STV		STE		STIS
Bit	Name	Reset	Access	Description		
31	Reserved	To ensure co	mpatibility	with future devices, always wr	rite bits t	to 0. More information in 1.2 Conven-
30:28	STWS	0x1	RW	Startup Waitstates		
	Active wait for flash	startup startup at	fter SDLY0	•		
27	Reserved	To ensure co	mpatibility	with future devices, always wr	rite bits t	to 0. More information in 1.2 Conven-
26	STWSAEN	0	RW	Startup Waitstates Always	s Enable	e
	Use the number of	waitstates given b	y STWS d	uring startup always.		
25	STWSEN	1	RW	Startup Waitstates Enable)	
	Use the number of	waitstates given b	y STWS d	uring startup. During the optio	nal STD	DLY1 timeout.
24	ASTWAIT	1	RW	Active Startup Wait		
	Active wait for flash	startup startup at	fter SDLY0			
23:22	Reserved	To ensure co	mpatibility (with future devices, always wr	rite bits t	to 0. More information in 1.2 Conven-
21:12	STDLY1	0x001	RW	Startup Delay 0		
		tem. Note that the	reset valu	e of this field may differ from t		tartup sampling will be attempted be- e shown in this description. The reset
11:10	Reserved	To ensure co	mpatibility (with future devices, always wr	rite bits t	to 0. More information in 1.2 Conven-
9:0	STDLY0	0x04D	RW	Startup Delay 0		
				Note that the reset value of th device is the optimal value.	is field r	may differ from the value shown in this

7.5.18 MSC_CMD - Command Register

Offset															Bi	t Pc	siti	on														
0x074	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Reset																																0
Access																																W1
Name																																PWRUP

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	PWRUP	0	W1	Flash Power Up Command
	Write to this bit to pov	ver up the Flash	. IRQ PWF	RUPF will be fired when power up sequence completed.

7.5.19 MSC_BOOTLOADERCTRL - Bootloader Read and Write Enable, Write Once Register

Offset															Ві	t Po	siti	on														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																															0	0
Access																															₹	RW
Name																															BLWDIS	BLRDIS

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	BLWDIS	0	RW	Flash Bootloader Write/Erase Disable
	Controls write/erase a disabled.	ccess of the flas	sh bootload	der pages. When cleared, write/erase is enabled. When set, write/erase is
0	BLRDIS	0	RW	Flash Bootloader Read Disable
	Controls read access	of the flash boo	tloader paç	ges. When cleared, read is enabled. When set, read is disabled.

7.5.20 MSC_AAPUNLOCKCMD - Software Unlock AAP Command Register

Offset	Bit Position	
0x094	33 34 6 6 6 6 6 7 7 8 8 8 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9 10 10 10 10 10 10 10 10 10 10 10 10 10 <th>0</th>	0
Reset		0
Access		W
Name		UNLOCKAAP


Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	UNLOCKAAP	0	W1	Software Unlock AAP Command
				ible when bit 31 of the AAP Lock Word (ALW) in flash is set to 1. If bit 31 of nas no effect. Register is writable only when MSC_LOCK is unlocked

7.5.21 MSC_CACHECONFIG0 - Cache Configuration Register 0

Offset														Bi	t Po	sitio	on														
0x098	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	8	7	9	2	4	က	2	_	0
Reset		'			•			•	<u>'</u>												•		'	1			1	'	•		0x3
Access																														:	¥ §
Name																														į į	CACHELPLEVEL
Bit	Name	;				Re	set			Ac	ces	s I	Des	crip	tion																
31:2	Rese	ved				To tio		ure	con	npati	bilit	y wi	th fu	ture	dev	rices	s, alı	way.	s wr	ite k	its t	o 0.	Мо	re ir	nforr	natio	on in	1.2	? Co	nve	n-
1:0	CACH	IELPI	LEV	EL		0x3	3			RV	/		Inst	ruct	ion	Cac	he	Low	/-Po	wer	Lev	/el									
	Use th	nis to	set	the	low-	-pov	ver I	eve	l of t	he c	ach	e. Ir	n ge	nera	ıl, th	e de	faul	lt se	tting	j is l	est	for	mos	st ap	plic	atior	ns.				
	Value					Мс	ode						Des	cript	ion																_
	0					ВА	SE						Base	e ins	struc	tion	cac	he f	unc	tion	ality.										_
	1					AD	1AV	NCE	Ð															e us low						to	
	3					MII	NAC	VIT	ΊΤΥ			 	logio intro exits is sr duce state	thanductory sone mall, e the	at it e wa e of but e van	predait-si its lo use riabi wish	licts tate ow-a rs r lity to	has s infactive unni that low	s a to the ity s ing v the er the	low ne ir tate with cac ne c	prol stru s. T 0-w he r	bab letic he r ait-s nigh	ility on fe num state nt in ow-p	cach beir etch ber e me trod owe	ng u stre of w emo uce er le	sed. am ait-s ry ai with vel.	Thing whe state and ware and w	is men the single in the singl	node ne c trod ing t nal	e ca ach uce o re wai	n e d e- t-

8. LDMA - Linked DMA Controller





Quick Facts

What?

The LDMA controller can move data without CPU intervention, effectively reducing the energy consumption for a data transfer.

Why?

The LDMA can perform data transfers more energy efficiently than the CPU and allows autonomous operation in low energy modes. For example the LEUART can provide full UART communication in EM2 Deep Sleep, consuming only a few μA by using the LDMA to move data between the LEUART and RAM.

How?

The LDMA controller has multiple highly configurable, prioritized DMA channels. A linked list of flexible descriptors makes it possible to tailor the controller to the specific needs of an application.

8.1 Introduction

The Linked Direct Memory Access (LDMA) controller performs memory transfer operations independently of the CPU. This has the benefit of reducing the energy consumption and the workload of the CPU, and enables the system to stay in low energy modes while still routing data to memory and peripherals. For example, moving data from the LEUART to memory or memory to LEUART. Each of the DMA channels on the EFR32 can be connected to any of the EFR32 peripherals.

8.1.1 Features

- · Flexible Source and Destination transfers
 - · Memory-to-memory
 - · Memory-to-peripheral
 - · Peripheral-to-memory
 - · Peripheral-to-peripheral
- DMA transfers triggered by peripherals, software, or linked list
- · Single or multiple data transfers for each peripheral or software request
- · Inter-channel and hardware event synchronization via trigger and wait functions
- · Supports single or multiple descriptors
 - · Single descriptor
 - · Linked list of descriptors
 - · Circular and ping-pong buffers
 - · Scatter-Gather
 - Looping
 - · Pause and restart triggered by other channels
 - · Sophisticated flow control which can function without CPU interaction
- · Channel arbitration includes:
 - · Fixed priority
 - · Simple round robin
 - · Round robin with programmable multiple interleaved entries for higher priority requesters
- · Programmable data size and source and destination address strides
- · Programmable interrupt generation at the end of each DMA descriptor execution
- · Little-endian/big-endian conversion
- · DMA write-immediate function

8.2 Block Diagram

An overview of the LDMA and the modules it interacts with is shown in Figure 8.1 LDMA Block Diagram on page 153.




Figure 8.1. LDMA Block Diagram

The Linked DMA Controller consists of three main parts

- · A DMA core that executes transfers and communicates status to the core
- · A channel select block that routes peripheral DMA requests and acknowledge signals to the DMA
- · A set of internal channel configuration registers for tracking the progress of each DMA channel

The DMA has access to all system memory through the AHB bus and the AHB->APB bridge. It can load channel descriptors from memory with no CPU intervention.

8.3 Functional Description

The Linked DMA Controller is highly flexible. It is capable of transferring data between peripherals and memory without involvement from the processor core. This can be used to increase system performance by off-loading the processor from copying large amounts of data or avoiding frequent interrupts to service peripherals needing more data or having available data. It can also be used to reduce the system energy consumption by making the LDMA work autonomously with some EM2/3 peripherals for data transfer without having to wake up the processor core from sleep.

The Linked DMA Controller has 8 independent channels. Each of these channels can be connected to any of the available peripheral DMA transfer request input sources by writing to the channel configuration registers, see 8.3.2 Channel Configuration. In addition, each channel can also be triggered directly by software, which is useful for memory-to-memory transfers.

The channel descriptors determine what the Linked DMA Controller will do when it receives DMA transfer request. The initial descriptor is written directly to the LDMA's channel registers. If desired, the initial descriptor can link to additional linked descriptors stored in memory (RAM or Flash). Alternatively, software may also load the initial descriptor by writing the descriptor address to the LDMA_CHx_LINK register and then setting the corresponding bit the LDMA_LINKLOAD register.

Before enabling a channel, the software must take care to properly configure the channel registers including the link address and any linked descriptors. When a channel is triggered, the Linked DMA Controller will perform the memory transfers as specified by the descriptors. A descriptor contains the memory address to read from, the memory address to write to, link address of the next descriptor, the number of bytes to be transferred, etc. The channel descriptor is described in detail in 8.3.7 Channel Descriptor Data Structure.

The Linked DMA Controller supports both fixed priority and round robin arbitration. The number of fixed and round robin channels is programmable. For round robin channels, the number of arbitration slots requested for each channel is programmable. Using this scheme, it is possible to ensure that timing-critical transfers are serviced on time.

DMA transfers take place by reading a block of data at a time from the source, storing it in the LDMA's local FIFO, then writing the block out to the destination from the FIFO. Interrupts may optionally be signaled to the CPU's interrupt controller at the end of any DMA transfer or at the completion of a descriptor if the DONEIFSEN bit is set. An AHB error will always generate an interrupt.

8.3.1 Channel Descriptor

Each DMA channel has descriptor registers. A transfer can be initialized by software writing to the registers or by the DMA itself copying a descriptor from RAM to memory. When using a linked list of descriptors the first descriptor should be initialized by the CPU. The DMA itself will then copy linked descriptors to its descriptor registers as required. In addition to manually initializing the first transfer, software may also cause the LDMA to load the initial descriptor by writing the descriptor address to the LDMA_CHx_LINK register and then setting the corresponding bit the LDMA_LINKLOAD register.

The contents of the descriptor registers are dynamically updated during the DMA transfer. The contents of descriptors in memory are not edited by the controller.

Some descriptor field values are only used for linked descriptors. For example, the SRCMODE and DSTMODE bits of the LDMA_CHx_CTRL registers determine if a linked descriptor is using relative or absolute addressing. Software writes to the address registers will always use absolute addressing and never set these bits. Therefore, these bits are read only.

8.3.1.1 DMA Transfer Size

A DMA transfer is the smallest unit of data that can be transfered by the LDMA. The LDMA supports byte, half-word and word sized transfers. The SIZE field in the LDMA_CHx_CTRL register specifies the data width of one DMA transfer.

8.3.1.2 Source/Destination Increments

The SRCINC and DSTINC in the LDMA_CHx_CTRL register determines the increment between DMA transfers. The increment is in units of DMA transfers and using an increment size of 1 will transfer contiguous bytes, half-words, or words depending on the value of the SIZE field. Multiple unit increments are useful for transferring or packing/unpacking alligned data. For example using an increment of 4 with a size of BYTE will transfer word aligned bytes. An increment of 2 units with a size of HALFWORD is suitable for the transfer of word aligned half-word data. The LDMA can also pack or unpack data by using a different increment size for source and destination. For example - to convert from word aligned byte data (unpacked) to contiguous byte data (packed), set the SIZE to BYTE, SRCINC to 4, and DSTINC to 1.

SRCINC or DSTINC may also be set to NONE which will cause the LDMA to read or write the same location for every DMA transfer. This is useful for accessing peripheral FIFO or data registers.

8.3.1.3 Block Size

The block size defines the amount of data transferred in one arbitration. It consists of one or more DMA transfers. See 8.3.6.1 Arbitration Priority for more details.

8.3.1.4 Transfer Count

The descriptor transfer count defines how many DMA transfers to perform. The number of bytes transferred by the descripter will depend on both the transfer count XFERCNT and the SIZE field settings. TOTAL BYTES = XFERCNT * SIZE

8.3.1.5 Descriptor List

A descriptor list consists of one or more descriptors which are executed in serially. This list may be a simple sequence of descriptors, a loop of descriptors, or a combination of the two.

Each descriptor in the list can be one of several types.

- Single Transfer descriptor: Transfers TOTAL_BYTES of data and then stops.
- · Linked Transfer descriptor: Transfers TOTAL_BYTES of data and then loads the next linked descriptor.
- Loop Transfer descriptor: Transfers TOTAL BYTES of data and performs loop control (see 8.3.2.2 Loop Counter).
- Sync descriptor: Handle synchronization of the list with other entities (see 8.3.7.2 SYNC Descriptor Structure).
- WRI descriptor: Writes a value to a location in memory (see 8.3.7.3 WRI Descriptor Structure).

8.3.1.6 Addresses

Before initiating a transfer, software should write the source address, destination address, and if applicable the link address to the descriptor registers. Alternatively, software may load a descriptor from memory by writing the descriptor address to the LDMA_CHx_LINK register and setting the corresponding bit in the LDMA_LINKLOAD register.

During a DMA transfer, the DMA source and destination address registers are pointers to the next transfer address. The LDMA will update the SRC and DST addresses after each transfer. If software halts a DMA transfer by clearing the enable bit, the SRC and DST addresses will indicate the next transfer address.

When a desriptor is finished the DMA will either halt or load the next (linked) descriptor depending on the value of the LINK field in the LDMA_Chx_LINK register. After loading a linked descriptor, the descriptor registers will reflect the content of the loaded descriptor. Note that the linked descriptor must be word aligned in memory. The two least significant bits of the LDMA_CHx_LINK register are used by the LINK and LINKMODE bits. The two least significant bits of the link address are always zero.

8.3.1.7 Addressing Modes

The DMA descriptors support absolute addressing or relative addressing. When using relative addressing, the offset is relative to the current contents of the respective address registers. Regardless of the descriptor addressing modes, the address registers always indicate the absolute address. For example, when loading a descriptor using relative SRC addressing, the LDMA will add the descriptor source address (offset) to the contents of the SRCADDR register (base address). After loading, the SRCADDR register will indicate the absolute address of the loaded descriptor.

The initial descriptor must use absolute addressing. The LDMA will ignore the DSTMODE, SRCMODE, and LINKMODE bits for the initial descriptor and interpret the addresses as an absolute addresses.

Relative addressing is most useful for the link address. The initial descriptor will indicate the absolute address of the linked descriptors in memory. The linked descriptors might be an array of structures. In this case the offset between descriptors is constant and is always 4 words or 16 bytes (each descriptor has 4 words). The LINK address is not incremented or decremented after each transfer. Thus, a relative offset of 0x10 may be used for all linked descriptors.

The source and destination addresses also support relative addressing. When using relative addressing with the source or destination address registers, the LDMA adds the relative offset to the current contents of the respective address register. Since the source and destination addresses are normally incremented after each transfer, the final address will point to one unit past the last transfer. Thus, an offset of zero will give the next sequential data address.

See the example 8.4.6 2D Copy for an common use of relative addressing.

8.3.1.8 Byte Swap

Enabling byte swap reverses the endianness of the incoming source data read into the LDMA's FIFO. Byte swap is only valid for transfer sizes of word and half-word. Note that linked structure reads are not byte swapped.




Figure 8.2. Word and Half-Word Endian Byte Swap Examples

8.3.1.9 DMA Size and Source/Destination Increment Programming

The DMA channels' SIZE, SRCINC, and DSTINC bit-fields are programmed to best utilize memory resources. They provide a means for memory packing and unpacking, as well as for matching the size of data being transmitted to or received from an IO peripheral. The following figure shows how 32-bit words of data are read from a memory source into the DMA's internal transfer FIFO, and then written out to the memory destination. The memory organization in bytes is shown as well as the first read to and write from the DMA's FIFO.




Figure 8.3. Memory-to-Memory Transfer WORD Size Example

The next example shows four variations of half-word sized transfers, with all possible combinations of half- and full-word source and destination increments. Note that when the size and source/destination increments are all configured for half-word, the resulting DMA transfer organization is equivalent to the full-word sized transfer in the previous example. The difference is that the half-word configuration requires twice as many DMA transfers.




Figure 8.4. Memory-to-Memory Transfer HALF Size Examples

Fields SRCINCSIGN and DSTINCSIGN allow for address decrement. These can be used to mirror an image, for example, in the pixel copy application.

8.3.2 Channel Configuration

Each DMA channel has associated configuration and loop counter registers for controlling direction of address increment, arbitration slots, and descriptor looping.

8.3.2.1 Address Increment/Decrement

Normally DMA transfers increment the source and destination addresses after each DMA transfer. Each channel is also capable of decrementing the source and/or destination addresses after each DMA transfer. This may be useful for flipping an array or copying data from tail to head. For example, a data packet might be prepared as an array of data with increasing addresses and then transmitted from the highest address to the lowest address, from tail to head.

After reset the SRCINCSIGN and DSTINCSIGN bits in the LDMA_CHx_CFG register are cleared causing the source and destination addresses to increment after each transfer. If the SRCINCSIGN bit is set , the DMA will decrement the source address after each transfer. If the DSTINCSIGN bit in the LDMA_CHx_CFG register is set , the DMA will decrement the destination address after each transfer. Setting only one of these bits will flip the data. Setting both bits will copy from tail to head, but will not flip the data.

The SRCINCSIGN and DSTINCSIGN bits apply to all descriptors used by that channel. Software should take care to set the starting source and/or destination address to the highest data address when decrementing.

8.3.2.2 Loop Counter

Each channel has a LDMA_CHx_LOOP register that includes a loop counter field. To use looping, software should initialize the loop counter with the desired number of repetitions before enabling the transfer. A descriptor with the DECLOOPCNT bit set to TRUE will repeat the loop and decrement the loop counter until LOOPCNT = 0.

For a looping descriptor, with DECLOOPCNT=1, the LINK address in the LDMA_CHx_LINK register is used as the loop address. While LOOPCNT is greater than zero, the descriptor will execute and then the LDMA will load the next descriptor using the address specified in the LDMA_CHx_LINK register. This feature enables looping of multiple descriptors. To repeat a single descriptor, the LINK address of the descriptor should point to itself.

After LOOPCNT reaches zero, if the LINK bit in the descriptor LINK word is clear the transfer stops. If the LINK bit is set, the LDMA will load the next sequential descriptor located immediately following the looping descriptor. The behavior of the LINK bit is different for a looping descriptor. This is necessary because the LINK address is re-purposed as the loop address for a looping descriptor.

Note that LOOPCNT sets the number of repeats, not the number of iterations. The total number of loop iterations will be LOOPCNT plus 1. Normally, the LOOPCNT should be set to one or more repeats.

Also note that because there is only one LOOPCNT per channel, software intervention is required to update the LOOPCNT if a sequence of transfers contains multiple loops. It is also possible to use a write immediate DMA data transfer to update the LDMA CHx LOOP register.

8.3.3 Channel Select Configuration

The channel select block determines which peripheral request signal connects to each DMA channel.

This configuration is done by software through the SOURCESEL and SIGSEL fields of the LDMA_CHn_REQSEL register. SOURCE-SEL selects the peripheral and SIGSEL picks which DMA request signals to use from the selected peripheral.

8.3.4 Starting a Transfer

A transfer may be started by software, a peripheral request, or a descriptor load.

Software may initiate a transfer by setting the bit for the desired channel in the LDMA_SREQ register. In this case the channel should set SOURCESEL to NONE to prevent unintentional triggering of the channel by a peripheral.

A peripheral may trigger the channel by configuring the peripheral source and signal as described in 8.3.3 Channel Select Configuration

The LDMA may also be configured to begin a transfer immediately after a new descriptor is loaded by setting the STRUCTREQ field of the LDMA CHx CTRL register or descriptor word.

This configuration is done by software through the SOURCESEL and SIGSEL fields of the LDMA_CHn_REQSEL register. SOURCE-SEL selects the peripheral and SIGSEL picks which DMA request signals to use from the selected peripheral.

8.3.4.1 Peripheral Transfer Requests

By default peripherals issue a Single Request (SREQ) when any data is present. For peripherals with a data buffer or FIFO this occurs any time the FIFO is not empty. Upon receiving an SREQ the LDMA will perform one DMA transfer and stop till another request is made.

It is generally more efficient to wait for a peripheral to accumulate data and transfer in a burst. This both reduces overhead of the DMA engine and allows EM2 peripherals to save power by using the LDMA less often. To enable this set the IGNORESREQ bit in the LDMA_CHx_CTRL register (or descriptor) which will cause the LDMA to ignore SREQ's and wait for a full Request (REQ) signal. When the REQ is received the entire descriptor will be executed. For most peripherals with a FIFO the REQ signal is set when the FIFO is full, or a predetermined threshold has been reached. See the individual peripheral chapters for more information.

8.3.5 Managing Transfer Errors

LDMA transfer errors are normally managed using interrupts. Software should clear the ERROR flag in the bit in the LDMA_IF register and enable error interrupts by setting the ERROR bit in the LDMA_IEN register before initiating a DMA transfer.

The LDMA interrupt handler should check the ERROR flag bit in the LDMA_IF register. If the ERROR flag bit is set, it should then read the CHERROR field in the LDMA_STATUS register to determine the errant channel. The interrupt handler should reset the channel and clear the ERROR flag bit in the LDMA_IF register before returning.

8.3.6 Arbitration

While multiple channels are configured simultaneously the LDMA engine can only be actively copying data for one channel at a time. Arbitration determines which channel is being serviced at any point in time. The LDMA will choose a channel through arbitration, transfer BLOCK_SIZE elements of that channel and then arbitrate again choosing another channel to service. This allows high priority channels to be serviced while lower priority channels are in the middle of a transfer.

8.3.6.1 Arbitration Priority

There are two modes in determining priority when the controller arbitrates: fixed priority and round robin priority.

In fixed priority mode, channel 0 has the highest priority. As the channel number increases, the priority decreases. When the LDMA controller is idle or when a transfer completes, the highest priority channel with an active request is granted the transfer. This mode guarantees smallest latency for the highest priority requesters. It is best suited for systems where peak bandwidth is well below LDMA controller's maximum ability to serve. The drawback of this mode is the possibility of starvation for lowest priority requesters.

In the round robin priority mode, each active requesting channel is serviced in the order of priority. A late arriving request on a higher priority channel will not get serviced until the next round. This mode minimizes the risk of starving low-priority latency-tolerant requesters. The drawback of this mode is higher risk of starving low-latency requesters.

The NUMFIXED field in the LDMA_CTRL register determines which channels are fixed priority and which are round robin. Channels lower than NUMFIXED are fixed priority while those above it are round robin. A value of 0x0 implies all channels are round robin. A value of 0x4 implies channels 0 through 3 are fixed priority and 4 through 7 are round robin. A value of 7 implies that channels 0 through 6 are fixed and channel 7 is round robin. This is functionally equivalent to having 8 fixed priority channels.

Fixed priority channels always take priority over round robin. As long as NUMFIXED is greater than 0, there is a possibility that a higher priority channel can starve the remaining channels.

To address the drawbacks of using fixed priority or round robin priority the LDMA implements the concept of arbitration slots. This allows for channels to have high bandwidth and low latency while preventing starvation of latency tolerant low priority channels.

Each channel has a two bit ARBSLOT field in its LDM_CHx_CFG register. This field only applies to channels marked as round robin (determined by NUMFIXED). The channels in the same arbitration slot are treated equally with round robin scheduling. Channels marked with a higher arbitration slot will get serviced more frequently. By default all channels are placed in arbitration slot 1.

Every time the channels in slot 1 get serviced the channels in slot 2 get serviced twice, those in slot 4 get serviced 4 times, and those in slot 8 get serviced 7 times. The specific arbitration allocation can be seen by the following table. The highest arbitration slot is serviced every other arbitration cycle, allowing for low latency response. If there are no requests from channels in arbitration slot then that slot is immediately skipped.

Table 8.1. Arbitration Slot Order

Arbslot order	8	4	8	2	8	4	8	1	8	4	8	2	8	4
Arbslot1								1						
Arbslot2				1								1		
Arbslot4		1				1				1				1
Arbslot8	1		1		1		1		1		1		1	

The top row shows the order at which the arbitration slots are executed. The remaining part of the table shows a more visual interpretation of the arbitration order.

For example, if we have one low latency channel (CHNL0) and two latency tolerant channels (CHNL1 and CHNL2). We could use the following settings.

LDMA CTRL.NUMFIXED = 0; set round robin for all channels.

CHNL0_CFG.ARBSLOTS = TWO;

CHNL1 CFG.ARBSLOTS = ONE;

CHNL2_CFG.ARBSLOTS = ONE;

If all channels are constantly requesting transfers, then the arbitration order is: CHNL0, CHNL1, CHNL0, CHNL1, CHNL0, CHNL1, CHNL0, CHNL2, CHNL0, etc

Note, there are no channels assigned to arbitration slot four or eight in this example, so those slots are skipped and the final sequence is ARBSLOT2, ARBSLOT1, ARBSLOT2, ARBSLOT1, etc...

Channel 1 and Channel 2 are selected in round robin order when arbitration slot 1 is executed.

If we replace the ARBSLOTS value for channel 0 with EIGHT, then the sequence would look like the following:

CHNL0, CHNL0, CHNL0, CHNL1, CHNL1, CHNL0, CHNL0, CHNL2, CHNL0, CHNL0, CHNL0, CHNL0, CHNL1, etc.

8.3.6.2 DMA Transfer Arbitration

In addition to the inter channel arbitration, software can configure when the controller arbitrates during a DMA transfer. This provides reduced latency to higher priority channels when configuring low priority transfers with more arbitration cycles.

The LDMA provides four bits that configure how many DMA transfers occur before it re-arbitrates. These bits are known as the BLOCK-SIZE bits and they map to the arbitration rate as shown below. For example, if BLOCKSIZE = 4 then the arbitration rate is 6, that is, the controller arbitrates every 6 DMA transfers.

Table 8.2 AHB Bus Transfer Arbitration Interval on page 162 lists the arbitration rates.

Table 8.2. AHB Bus Transfer Arbitration Interval

BLOCKSIZE	Arbitrate After x DMA transfers
0	x = 1
1	x = 2
2	x = 3
3	x = 4
4	x = 6
5	x = 8
6	x = 12
7	x = 16
8	x = 24
9	x = 32
10	x = 64
11	x = 128
12	x = 256
13	x = 512
14	x = 1024
15	x = lock

Note: Software must take care not to assign a low-priority channel with a large BLOCKSIZE because this prevents the controller from servicing high-priority requests, until it re-arbitrates.

The number of DMA transfers that need to be done is specified by the user in XFERCNT. When XFERCNT > BLOCKSIZE and is not an integer multiple of BLOCKSIZE then the controller always performs sequences of BLOCKSIZE transfers until XFERCNT < BLOCKSIZE remain to be transferred. The controller performs the remaining XFERCNT transfers at the end of the DMA cycle.

Software must store the value of the BLOCKSIZE bits in the channel control data structure. See 8.3.7.1 XFER Descriptor Structure for more information about the location of the BLOCKSIZE bits in the data structure.

8.3.7 Channel Descriptor Data Structure

Each channel descriptor consists of four 32-bit words:

- · CTRL control word contains information like transfer count and block size.
- SRC source address points to where to copy data from
- · DST destination address points to where to copy data to
- · LINK link address points to where to load the next linked descriptor

These words map directly to the LDMA_CHx_CTRL, LDMA_CHx_SRC, LDMA_CHx_DST, and LDMA_CHx_LINK registers. The usage of the SRC and DST fields may differ depending on the structure type

There are three different types of descriptor data structures: XFER, SYNC, and WRI

8.3.7.1 XFER Descriptor Structure

This descriptor defines a typical data transfer which may be a Normal, Link, or Loop transfer.

Only this structure type can be written directly into LDMA's registers by the CPU. All descriptors may be linked to. Refer to the register descriptions for additional information.

For specifying XFER structure type, set STRUCTTYPE to 0. See the peripheral register descriptions for information on the fields in this structure.

Name															Bi	t Po	sitio	on														
	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	ω	7	9	2	4	ဗ	2	1	0
CTRL	DSTMODE	SRCMODE	CAL		SIZE	OIZE	0	SACING	IGNORESREQ	DECLOOPCNT	REQMODE	DONEIFSEN		3 DOVO 19	BLOCKSIZE		BYTESWAP						XFERCNT						STRUCTREQ		STELLCTTVDE	
SRC															S	RCA	ADD	R														
DST															D	STA	ADD	R														
LINK														L	INKA	ADD	R														LINK	LINKMODE

8.3.7.2 SYNC Descriptor Structure

This descriptor defines an intra-channel synchronizing structure. It allows the channel to wait for some external stimulus before continuing on to the next descriptor. This structure is also used to provide stimulus to another channel to indicate that it may continue.

For example channel 1 may be configured to transfer a header into a buffer while channel 2 is simultaneously transferring data into the same structure. When channel 1 has completed it can wait for a sync signal from channel 2 before transferring the now complete buffer to a peripheral.

Synch descriptors do nothing until a condition is met. The condition is formed by the SYNCTRIG field in the LDMA_SYNC register and the MATCHEN and MATCHVAL fields of the descriptor. When (SYNCTRIG & MATCHEN) == (MATCHVAL & MATCHEN) the next descriptor is loaded. In addition to waiting for the condition a Link descriptor can set or clear bits in SYNCTRIG to meet the conditions of another channel and cause it to continue. The CPU also has the ability to set and clear the SYNCTRIG bits from software.

This structure type can only be linked in from memory.

For specifying SYNC structure type, set STRUCTTYPE to 1.

Name															В	it Po	sitio	on														
	3	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	80	7	9	5	4	3	2	- 0	 >
CTRL												DONEIFSEN		1										'							STRUCTTYPE	
SRC																			S	SYNO	СС	LR					S	YN	CSE	Т		
DST																			Ν	ИΑТ	CH	EN					M	AT(CHV	ΑL		
LINK														L	_INK.	ADD	ıR														LINK	LINKMODE
Bit				Name Description																												
1:0			,	STF	RUCT	ГТҮР	Έ					D	esc	ript	or T	ype																
			-	This	field	d indi	cate	s wh	hich	type	of o	desc	ripto	r th	is is.	It m	ust t	oe 1	for a	a SY	/NC	C des	cript	or.								
20			I	וסכ	NEIF	SEN						D	one	if S	Set i	ndic	ator															
			ı	f se	et the	inte	rrup	t flaç	g wil	l be	set v	wher	de:	scri	ptor (com	olete	S.														
15:	8		(YE	ICCI	_R						S	ync	Tri	gger	Cle	ar															
			á	a gi are	ven b	oit, a ed w	one ith a	sho one	uld e. Th	be lo e sy	ade nc t	d to rigge	the er cle	cor ear	respo funct	ondir	ng bi can c	t. Se	t is be ι	give	n p	riori	y ov	er cl	ear i	f bo	th co	rre	spon	ding	Γο clea bits ernate-	
7:0			(1YS	NCSE	ΞΤ						S	ync	Tri	gger	Set																
			ţ	o th ger	ne co	rresp uncti	on c	ling an c	bit. S	Set is be u	s giv	en p	orior	ity c	over (clear	if bo	oth c	orre	espo	ndi	ng b	its ar	e lo	adec	d wit	h a c	ne.	The	syn	loade c trig- SYN-	
15:	8		ı	MA	TCHI	ΕN						S	ync	Tri	gger	Ma	tch E	Enak	ole													
					bit-f																						link	ed I	DMA	stru	cture	
7:0			ı	MA	TCH	VAL						S	ync	Tri	gger	Ma	tch \	/alu	е													_

Bit Name Description

This bit-field serves as the SYNCTRIG match value. A sync match triggers the load of the next linked DMA structure as specified by link_mode, when: (SYNCTRIG & MATCHEN) == (MATCHVAL & MATCHEN).

8.3.7.3 WRI Descriptor Structure

This descriptor defines a write-immediate structure. This allows a list of descriptors to write a value to a register or memory location. For example, if a channel wishes to perform two loops in a descriptor sequence a WRI may be used to program the loop count for the second loop.

This structure type can only be linked in from memory.

For specifying WRI structure type, set STRUCTTYPE to 2.

Name															В	it Po	siti	on														
	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	3	2	1	0
CTRL												DONEIFSEN																			STELLCTTVDE	-
SRC																IMM	IVAL	-														
DST															С	STA	ADD	R														
LINK														L	INK	ADD	R														LINK	LINKMODE

Bit	Name	Description
1:0	STRUCTTYPE	Descriptor Type
	This field indicates which type of	descriptor this is. It must be 2 for a WRI descriptor.
20	DONEIFSEN	Done if Set indicator
	If set the interrupt flag will be set	when descriptor completes.
31:0	IMMVAL	Immediate Value for Write
	This bit-field specifies the immedi write occurs for WRI structures.	ate data value that is to be written to the address pointed to by DSTADDR. Only one
31:0	DSTADDR	Address to write
	This bit-field specifies the address	s the immediate data should be written to.

8.3.8 Interaction With the EMU

The LDMA interacts with the Energy Management Unit (EMU) to allow transfers from a low energy peripheral while in EM2 Deep Sleep. For example, when using the LEUART in EM2 Deep Sleep the EMU can wake up the LDMA sufficiently long to allow data transfers to occur. See section "DMA Support" in the LEUART documentation.

Similarly, when using the ADC in EM2 Deep Sleep or EM3 Stop the EMU can wake up the LDMA as needed to allow data transfers to occur.

Table 8.3 List of Peripherals Capable of Waking Up LDMA in EM2 Deep Sleep or EM3 Stop on page 166 shows complete list of peripherals that are capable of waking up LDMA via EMU in EM2 Deep Sleep or EM3 Stop

Table 8.3. List of Peripherals Capable of Waking Up LDMA in EM2 Deep Sleep or EM3 Stop

Peripheral Peripheran Peripheran Peripheran Peripheran Peripheran Peripheran Peripheran Peripheran
ADC0
IDAC0
LESENSE
LEUART0

8.3.9 Interrupts

The LDMA_IF Interrupt flag register contains one DONE bit for each channel and one combined ERROR bit. When enabled, these interrupts are available as interrupts to the Cortex-M4 core. They are combined into one interrupt vector, DMA_INT. If the interrupt for the DMA is enabled in the ARM Cortex-M4 core, an interrupt will be made if one or more of the interrupt flags in LDMA_IF and their corresponding bits in LDMA_IEN are set.

When a descriptor finishes execution the interrupt flag for that channel will be set if the DONEIFSEN field of the LDMA_CHx_LOOP register is set. If LINK and DONEIFSEN are both set when the descriptor completes the interrupt and the linked descriptor will be immediatly loaded. When the final descriptor in a linked list (LINK = 0) is finished the interrupt flag is always set regardless of the state of DONEIFSEN.

8.3.10 Debugging

For a peripheral request DMA transfer, if software sets a bit for a channel in the LDMA_DBGHALT register then the DMA will halt durring a debug halt and the SRC and DST registers in the debug window will show the transfer in progress. Otherwise, during debug halt the DMA will continue to run and complete the entire transfer causing the descriptor registers to indicate the transfer has completed.

8.4 Examples

This section provides examples of common LDMA usage. All examples assume the LDMA is in the reset state with the channel being configured disabled and LDAM CHx CFG, LDMA CHx LOOP, and LDMA CHx LINK cleared.

8.4.1 Single Direct Register DMA Transfer

This simple example uses only the Channel Descriptor registers directly and does not use linking. Software writes directly to the LDMA channel registers. This example does not use a memory based descriptor list.

This example is suitable for most simple transfers that are limited to transferring one block of data. It supports anything that can be done using a single descriptor. This includes endian conversion and packing/unpacking data. Channel 0 is used for this example.

The LDMA will be used to copy 127 contiguous half words (254 bytes) from 0x0 to 0x1000. It will allow arbitration every 4 transfers and is triggered by a CPU write to the LDMA_SWREQ register. The CH0 interrupt flag will be set when the transfer completes since the descriptor does not link to another descriptor.

- Configure LDMA_CH0_CTRL
 - DSTMODE = 0 (absolute)
 - SRCMODE = 0 (absolute)
 - SIZE = HALFWORD (16 bits)
 - DSTINC = 0 (1 half-word)
 - SRCINC = 0 (1 half-word)
 - DECLOOPCNT=0 (unused)
 - REQMODE = 1 (one request transfers all data)
 - BLOCKSIZE = 3 (4 transfers)
 - BYTESWAP=0 (no byte swap)
 - XFERCNT=127 (transfer 127 half words)
 - STRUCTTPYE=0 (TRANSFER)
- · Write source address to LDMA CH0 SRC register
- Write destination address to LDMA CH0 DST register
- · Configure the LDMA_CH0REQSEL register for the desired peripheral or select none for a memory-to-memory transfer
- · Clear and enable interrupts.
 - Write a 1 to bit 0 of the LDMA IFC register to clear the CH0 DONE flag
 - Write a 1 to bit 0 of the LDMA IEN register to enable the CH0 interrupt
- · Write a 1 to bit 0 of the LDMA_CHEN register to enable CH0

The REQMODE field is normally cleared to zero for a peripheral request transfer and will transfer the specified block size for each peripheral request. The REQMODE may be set to 1 for a memory-to-memory transfer or any time it is desired for a single DMA request to initiate complete transfer.

8.4.2 Descriptor Linked List

This example shows how to use a Linked List of descriptors. Each descriptor has a link address which points to the next descriptor in the list. A descriptor may be removed from the Linked list by altering the Link address of the one before it to point to the one after it. Descriptor Linked lists are useful when handling an array of buffers for communication data. For example, a bad packet can be removed from a receiver queue by simply removing the descriptor from the linked list.

Software loads the first descriptor into the DMA by writing the descriptor address to LDMA_CHx_LINK and setting the bit for that channel in the LDMA_LINKLOAD register. This method is preferred when using a linked list in memory since it treats the first descriptor just like all the others. However, it is also allowed for software to write the first descriptor directly to the LDMA registers.

In this example 4 descriptors are executed in series, the interrupt flag is set after the 2nd and 4th (last) descriptors have completed.

- · Prepare a list of descriptors using the XFER structure type in RAM
- · Initialize the CTRL, SRC, and DST members as desired
 - · Setting STRUCTREQ in the CTRL word for descritpors 2-4 will cause them to begin transfering data as soon as they are loaded.
- Write 0x00000013 to the LINK member of all but the last descriptor
 - LINKMODE = 1 (relative addressing)
 - LINK = 1 (Link to the next descriptor)
 - LINKADDR = 0x00000010 (size of descriptor)
- · Set the DONEIFSEN bit in the CTRL member of the 2nd structure so that the interrupt flag will be set when it completes
- Write 0x00000000 to the LINK member of the last descriptor
 - LINK = 0 (Do not link to the next descriptor)
 - LINKMODE = 0 (don't care)
 - LINKADDR = 0x00000000 (don't care)

Each descriptor now points to the start of the next descriptor as shown on the left in Figure 8.5 Descriptor Linked List on page 168. To remove a descriptor from the linked list modify the LINK address of the descriptor of the one before to point to the one after. For example to remove the third descriptor, add 0x00000010 to the LINK register of the second descriptor. The second descriptor will now point to the forth descriptor and skip over the third descriptor as shown on the right in Figure 8.5 Descriptor Linked List on page 168.




Figure 8.5. Descriptor Linked List

To start execution of the linked list of descriptors:

- Write the absolute address of the first descriptor to the LINKADR field of the LDMA_CH0_LINK register
- · Set the LINK bit of LDMA CH0 LINK register.
- Configure the LDMA_CH0REQSEL register for the desired peripheral or select none for memory-to-memory
- · Clear and enable interrupts as desired
- · Set bit 0 in the LDMA LINKLOAD register to initiate loading and execution of the first descriptor

Alternativley, software can manually copy the first descriptor contents to the LDMA_CH0_CTRL, LDMA_CH0_SRC, LDMA_CH0_DST, and LDMA_CH0_LINK registers and then enable the channel in the LDMA_CHEN register.


8.4.3 Single Descriptor Looped Transfer

This example demonstrates how to use looping using a single descriptor. This method allows a single DMA transfer to be repeated a specified number of times. The looping descriptor is stored in memory and reloaded by hardware. After a specified number of iterations, the transfer stops.

CH0 is setup to copy 4 words from the ADC FIFO into a 15 word buffer at 0x1000. It repeats 4 times to fill the entire 16 word buffer. An interrupt will fire when the entire 16 words have been transferred.

Initialize the Linked descriptor in memory as follows:

- · Configure CTRL member
 - DSTMODE = 0 (absolute)
 - SRCMODE = 0 (absolute)
 - SIZE = WORD
 - DSTINC = 0 (1 WORD)
 - SRCINC = 3 (0 WORDS)
 - DECLOOPCNT=1 (decrement loop count)
 - REQMODE=1 (Use XFERCNT)
 - BLOCKSIZE = 4 (4 words)
 - BYTESWAP=0 (no swap)
 - XFERCNT= 4 (4 words)
 - STRUCTTPYE=0 (TRANSFER)
 - IGNORESREQ=1 (ignore single requests)
- Write the address ADC0_SINGLEDATA register to the SRC member
- · Write 0x1000 address to DST member
- · Configure the LINKLink member
 - LINK = 0 (stop after loop)
 - MODE = 1 (relative link address)
 - LINKADDR = 0 (point to ourself)
- · Configure the Channel
 - · Write the desired number of repeats to the LDMA CH0 LOOP register
 - SOURCESEL in LDMA CH0REQSEL = ADC0 (select the ADC)
 - SIG in LDMA_CH0REQSEL = ADC0SCAN (select the scan conversion request)
- · Clear and enable interrupts
- Load the descriptor using LINKLOAD as described in 8.4.2 Descriptor Linked List







Figure 8.6. Single Descriptor Looped Transfer

Note that the looping descriptor must be stored in memory, because it must load itself from the link address in memory on each iteration.

8.4.4 Descriptor List With Looping

This example uses a descriptor list in memory with looping over multiple descriptors. This example also uses the looping feature and continues on with the next sequential descriptor after looping completes.

The descriptor list in memory is shown in figure Figure 8.7 Descriptor List With Looping on page 171. Descriptor A links to descriptor B. Descriptor B has the DECLOOPCNT bit enabled and loops back to the start of descriptor A. The LINK address of descriptor B is used for the loop address. The LINK bit is set to indicate that execution will continue after completion of looping. Once the LOOPCNT reaches zero, the LDMA will load descriptor C. Descriptor C must be located immediately following descriptor B.






Figure 8.7. Descriptor List With Looping

Initialization is similar to the single looping descriptor with the following modifications.

- · Set the LINK bit in descriptors A and B
- · write the address of descriptor A into the LIKADDRESS of descriptor B
- · write the address of descriptor B into the LIKADDRESS of descriptor A
- · Descriptor C must be located immediately after descriptor B in memory

8.4.5 Simple Inter-Channel Synchronization

The LDMA controller features synchronization structures which allow differing channels and/or hardware events to pause a DMA sequence, and wait for a synchronizing event to restart it.

In this example DMA channel 0 and 1 are tasked with the transfer of different sets of data. Channel 0 has two transfer structures, and channel 1 just one, but channel 0 must wait until channel 1 has completed its transfer before it starts its second transfer structure.

Pausing channel 0 is accomplished by inserting a sync wait structure between the two transfer structures. This sync structure waits on SYNCTRIG[7] to be set by a sync set/clear structure which is controlled by channel 1. Sync structures do not transfer data, they can only set, clear, or wait to match the SYNCTRIG[7:0] bits. Note that sync structures cannot decrement loop counter.

```
LDMA SYNC
    SYNCTRIG=0x0 (at time 0)
LDMA_CH0
    Structure A @ 0x00
                                    Structure B @ 0x10
                                                                         Structure C @ 0x20
    CTRL
                                        CTRL
                                                                             CTRL
       STRUCTTYPE=XFER
                                            STRUCTTYPE=SYNC
                                                                                 STRUCTTYPE=XFER
    T.TNK
                                         T.TNK
                                                                             LINK
        LINKADDR[29:0]=0x00000004
                                            LINKADDR[29:0]=0x00000008
                                                                                 LINKADDR[29:0]=NA
        LINK=1
                                             LINK=1
                                                                                  LINK=0
                                         DST
                                            MATCHEN=0×80
                                             MATCHVAL=0x80 (waits for SYNCTRIG[7]=1)
LDMA_CH1
    Structure Y @ 0x30
                                    Structure Z @ 0x40
                                         CTRL
    CTRL
        STRUCTTYPE=XFER
                                             STRUCTTYPE=SYNC
    LINK
                                         LINK
        LINKADDR[29:0]=0x00000010
                                             LINKADDR=NA
                                             LINK=0
                                         SRC
                                             SRCCLR=0x0
                                             SRCSET=0x80 (sets SYNCTRIG[7])
```




Figure 8.8. Simple Intra-channel Synchronization Example

Both A and Y effectively start at the same time. A finishes earlier, then it links to B, which waits for the SYNCTRIG[7] bit to be set before loading C. Y finishes after B is loaded, and it links to sync structure Z, which sets the SYNCTRIG[7] bit. Channel 0 responds to the trigger set by loading C for the final data transfer.

8.4.6 2D Copy

The LDMA can easily perform a 2D copy using a descriptor list with looping. This set up is visualized in Figure 8.9 2D Copy on page 174

For an application working with graphics, this would mean the ability to copy a rectangle of a given width and height from one picture to another.




Figure 8.9. 2D Copy

The first descriptor will use absolute addressing mode and the source and destination addresses should point to the desired target addresses. The first descriptor will copy only the first row. The XFERCNT of the first descriptor is set to the desired width minus one.

- CTRL
 - XFERCNT = WIDTH 1
 - SRCMD = 0 (absolute)
 - DSTMD = 0 (absolute)
- SRCADDR = target source address
- DSTADDR = target destination address
- LINK = 0x00000013
 - LINK=1
 - LINKMD=1
 - LINKADDR=0x00000010 (point to next descriptor)

The second descriptor will use relative addressing and the source and destination addresses are set to the desired offset. After the completion of the first descriptor, the address registers will point to the last address transferred. Thus, the width must be subtracted from the stride to get the offset. The second descriptor uses looping and the link register has not offset.

- CTRL
 - XFERCNT = WIDTH 1
 - SRCMD = 1 (relative)
 - DSTMD = 1 (relative)
 - DECLOOPCNT = 1
- · SRCADDR = desired source offset (SRCSTRIDE-WIDTH)
- DSTADDR = desired destination offset (DSTSTRIDE-WIDTH)
- LINK = 0x00000001
 - LINK=0
 - LINKMD=1 (relative)
 - LINKADDR=0x000000000 (no offset)

Because the first descriptor already transferred one row, the number of looping repeats should be the desired height minus two. Therefore, LOOPCNT should be set to HEIGHT minus two before initiating the transfer.

This same method is easily extended to copy multiple rectangles by linking descriptors together. To initialize the LDMA_CHx_LOOP register, precede each descriptor pair described above with a write immediate descriptor which writes the desired value to the LOOPCNT field of the LDMA_CHx_LOOP register.

8.4.7 Ping-Pong

Communication peripherals often use ping-pong buffers. Ping-pong buffers allow the CPU to process data in one buffer while a peripheral transmits or receives data in the other buffer.

Both transmit and receive ping-pong buffers are easily implemented using the LDMA. In either case, this requires two descriptors as shown in Figure 8.10 Infinite Ping-Pong Example on page 176. The LINKADDR field of the LINK member should point to the other descriptor. Using two adjacent descriptors and relative link addressing ensures the descriptors are easily reloadable.




Figure 8.10. Infinite Ping-Pong Example

A **receiver** ping-pong buffer controller consists of two buffers and two descriptors stored in memory that point to the two buffers. Once initialized, as the peripheral receives data, it will fill the first buffer. Once the first buffer is full, it will link automatically to the second buffer and generate an interrupt. Software will then process the data in the first buffer while the LDMA is transferring data to the second buffer. For a receiver ping-pong buffer each descriptor should link to the other descriptor. The link bit should be set to provide infinite ping pong between the two buffers. The DONIFS bit in each descriptor should be set to generate an interrupt on the completion of each descriptor.

- · Descriptor A
 - CTRL
 - DONEIFS = 1
 - · other settings as desired
 - SRCADDR = peripheral source address
 - DSTADDR = memory destination address
 - LINK = 0x00000013
 - LINKADDR = 0x00000010 (next descriptor)
 - LINK = 1 (link to next descriptor)
 - LINKMD = 1 (relative addressing)
- Descriptor B
 - CTRL
 - DONEIFS = 1
 - · other settings as desired
 - SRCADDR = peripheral source address
 - DSTADDR = memory destination address
 - LINK = 0xFFFFFF3
 - LINKADDR = 0xFFFFFF0 (previous descriptor)
 - LINK = 1 (link to previous descriptor)
 - LINKMD = 1 (relative addressing)

For transmitter ping-pong buffer, software will fill the first buffer and then initiate the DMA transfer. The LDMA will transmit the first buffer data while software is filling the second buffer. In this case, the two descriptors should point to each other, but not automatically

continue to the second buffer. The LINK bit should be cleared to zero. Once software has loaded the first buffer, it will use the LINK-LOAD bit to load the first descriptor and transmit the data. The DONIFS need not be set in each descriptor. The DMA will stop and then generate an interrupt at the completion of each descriptor.

- · Descriptor A
 - CTRL
 - DONEIFS = 0
 - other settings as desired
 - SRCADDR = memory source address
 - DSTADDR = peripheral destination address
 - LINK = 0x00000013
 - LINKADDR = 0x00000010 (next descriptor)
 - LINK = 0 (link to next descriptor)
 - LINKMD = 1 (relative addressing)
- · Descriptor B
 - CTRL
 - DONEIFS = 0
 - · other settings as desired
 - · SRCADDR = memory source address
 - DSTADDR = peripheral destination address
 - LINK = 0xFFFFFF3
 - LINKADDR = 0xFFFFFF0 (previous descriptor)
 - LINK = 0 (link to previous descriptor)
 - LINKMD = 1 (relative addressing)

8.4.8 Scatter-Gather

Scatter-Gather in general refers to a process that copies data from multiple locations scattered in memory and gathers the data to a single location in memory, or vice versa. A simple descriptor list allows data gathering. For example, data from a discontiguous list of buffers might be copied to a contiguous sequential array of buffers. The inverse is also possible when a sequential array of buffers is scattered to a discontiguous list of available buffers. See section 8.4.2 Descriptor Linked List.

Some DMAs which only have two descriptors implement scatter-gather by using one descriptor to modify the other descriptor. While it is possible to implement this same behavior using the LDMA, it is much more straight-forward to just use a simple descriptor list.

8.5 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	LDMA_CTRL	RW	DMA Control Register
0x004	LDMA_STATUS	R	DMA Status Register
0x008	LDMA_SYNC	RWH	DMA Synchronization Trigger Register (Single-Cycle RMW)
0x020	LDMA_CHEN	RWH	DMA Channel Enable Register (Single-Cycle RMW)
0x024	LDMA_CHBUSY	R	DMA Channel Busy Register
0x028	LDMA_CHDONE	RWH	DMA Channel Linking Done Register (Single-Cycle RMW)
0x02C	LDMA_DBGHALT	RW	DMA Channel Debug Halt Register
0x030	LDMA_SWREQ	W1	DMA Channel Software Transfer Request Register
0x034	LDMA_REQDIS	RW	DMA Channel Request Disable Register
0x038	LDMA_REQPEND	R	DMA Channel Requests Pending Register
0x03C	LDMA_LINKLOAD	W1	DMA Channel Link Load Register
0x040	LDMA_REQCLEAR	W1	DMA Channel Request Clear Register
0x060	LDMA_IF	R	Interrupt Flag Register
0x064	LDMA_IFS	W1	Interrupt Flag Set Register
0x068	LDMA_IFC	(R)W1	Interrupt Flag Clear Register
0x06C	LDMA_IEN	RW	Interrupt Enable Register
0x080	LDMA_CH0_REQSEL	RW	Channel Peripheral Request Select Register
0x084	LDMA_CH0_CFG	RW	Channel Configuration Register
0x088	LDMA_CH0_LOOP	RWH	Channel Loop Counter Register
0x08C	LDMA_CH0_CTRL	RWH	Channel Descriptor Control Word Register
0x090	LDMA_CH0_SRC	RWH	Channel Descriptor Source Data Address Register
0x094	LDMA_CH0_DST	RWH	Channel Descriptor Destination Data Address Register
0x098	LDMA_CH0_LINK	RWH	Channel Descriptor Link Structure Address Register
	LDMA_CHx_REQSEL	RW	Channel Peripheral Request Select Register
	LDMA_CHx_CFG	RW	Channel Configuration Register
	LDMA_CHx_LOOP	RWH	Channel Loop Counter Register
	LDMA_CHx_CTRL	RWH	Channel Descriptor Control Word Register
	LDMA_CHx_SRC	RWH	Channel Descriptor Source Data Address Register
	LDMA_CHx_DST	RWH	Channel Descriptor Destination Data Address Register
	LDMA_CHx_LINK	RWH	Channel Descriptor Link Structure Address Register
0x1D0	LDMA_CH7_REQSEL	RW	Channel Peripheral Request Select Register
0x1D4	LDMA_CH7_CFG	RW	Channel Configuration Register
0x1D8	LDMA_CH7_LOOP	RWH	Channel Loop Counter Register
0x1DC	LDMA_CH7_CTRL	RWH	Channel Descriptor Control Word Register
0x1E0	LDMA_CH7_SRC	RWH	Channel Descriptor Source Data Address Register

Offset	Name	Туре	Description
0x1E4	LDMA_CH7_DST	RWH	Channel Descriptor Destination Data Address Register
0x1E8	LDMA_CH7_LINK	RWH	Channel Descriptor Link Structure Address Register

8.6 Register Description

8.6.1 LD	MA_CTRL - DMA Con	trol Register								
Offset		Bit Po	sition							
0x000	31 30 29 28 27 27	25 24 2 2 3 3 4 4 5 5 1 5 6 1 6 1 6 1 6 1 6 1 6 1 6 1 6 1	6 4 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	7 9 2 4 8 2 1 0						
Reset		7×0	00X0	00×00						
Access		XX .	RW	RW						
Name	NUMFIXED SYNCPRSCLREN SYNCPRSSETEN									
Bit	Name	Reset Access Description	ı							
31:27	Reserved	To ensure compatibility with future dev	rices, always write bits to 0. Mor	re information in 1.2 Conven-						
26:24	NUMFIXED	0x7 RW Number of	Fixed Priority Channels							
		number of Fixed Priority Arbitration chan re round robin, where n is the field value								

23:16	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	SYNCPRSCLREN	0x00	RW	Synchronization PRS Clear Enable
	Setting a bit in this fie	eld will enable	e the corresp	onding PRS input to clear the respective bit in the SYNCTRIG field of the

LDMA_SYNC register. Refer to the PRS section for a list of the PRS inputs.

7:0 **SYNCPRSSETEN** 0x00 RW Synchronization PRS Set Enable

Setting a bit in this field will enable the corresponding PRS input to set the respective bit in the SYNCTRIG field of the LDMA_SYNC register. Refer to the PRS section for a list of the PRS inputs.

8.6.2 LDMA_STATUS - DMA Status Register

Offset	Bit Position																															
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset						0x08				'				0x10				'		•	1		0x0	•				0x0	•		0	0
Access						<u>~</u>								<u>~</u>									~					<u>~</u>			œ	~
Name						CHNUM								FIFOLEVEL									CHERROR					CHGRANT			ANYREQ	ANYBUSY

Bit	Name	Reset	Access	Description	l				
31:29	Reserved	To ensure o	compatibility	with future de	vices, always write	bits to 0. Mo	ore infori	mation in 1.	2 Conven-
28:24	CHNUM	0x08	R	Number of	Channels				
	The value of CHN	NUM always reads	s the total nu	mber of chann	els present for this	s instance of	the DM/	A controller	module.
23:21	Reserved	To ensure o	compatibility	with future de	vices, always write	bits to 0. Mo	ore infori	mation in 1.	2 Conven-
20:16	FIFOLEVEL	0x10	R	FIFO Level					
	The value of FIF0 register will read				ently in the FIFO.	(Note when a	all chanr	iels are disa	abled, this
15:11	Reserved	To ensure o	compatibility	with future de	vices, always write	e bits to 0. Mo	ore infori	mation in 1.	2 Conven-
10:8	CHERROR	0x0	R	Errant Cha	nnel Number				
	When the ERROI transfer error.	R flag is set in the	LDMA_IF re	gister, the CH	ERROR field will i	ndicate the n	nost rece	ent channel	to have a
7:6	Reserved	To ensure o	compatibility	with future de	vices, always write	bits to 0. Mo	ore infori	mation in 1.	2 Conven-
5:3	CHGRANT	0x0	R	Granted Ch	annel Number				
	The value of this zero.	field indicates the	currently act	tive channel o	last active channe	el. Note that	the rese	t value for t	his field is
2	Reserved	To ensure o	compatibility	with future de	vices, always write	bits to 0. Mo	ore infori	mation in 1.	2 Conven-
1	ANYREQ	0	R	Any DMA C	hannel Request	Pending			
	The value of this	bit will be TRUE (1) if any requ	iests are pend	ing				
0	ANYBUSY	0	R	Any DMA C	hannel Busy				
	The value of this	bit will be TRUE (1) if one or m	nore DMA cha	nnels are actively	transferring o	lata		

8.6.3 LDMA_SYNC - DMA Synchronization Trigger Register (Single-Cycle RMW)

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	∞	7	9	5	4	က	2	_	0
Reset													•										•						00x0			
Access																													I M Y			
Name																												- 1	SYNCIRIG			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	SYNCTRIG	0x00	RWH	Synchronization Trigger

The SYNC trigger field allows a transfer to pause until a specified trigger bit is set or cleared. The SYNC trigger bits may be set and cleared by a SYNC descriptor, PRS signal, or software. Note: software requires to use single-cycle read-modify-write, detailed in 4.2.3 Peripheral Bit Set and Clear

8.6.4 LDMA_CHEN - DMA Channel Enable Register (Single-Cycle RMW)

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	2	_	0
Reset		'	•	•		•	'	•					'	•		•		'	•			'		'			•	2	200			
Access																													[}			
Name																																

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co tions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	CHEN	0x00	RWH	Channel Enables

Setting one of these bits will enable the respective DMA channel. If cleared while a transfer is in progress, the current transfer block will complete. The remaining blocks will pause until resumed later by setting this bit again. Note: software requires to use single-cycle read-modify-write, detailed in 4.2.3 Peripheral Bit Set and Clear

8.6.5 LDMA_CHBUSY - DMA Channel Busy Register

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	တ	8	7	9	5	4	3	7	_	0
Reset		•			1					ı		1		•				•			1							0	0000			
Access																												ſ	Y			
Name																													BUSY			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	BUSY	0x00	R	Channels Busy
	The bits of this field re	ead 1 when the	correspond	ling channel is busy.

8.6.6 LDMA_CHDONE - DMA Channel Linking Done Register (Single-Cycle RMW)

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset																													0000			
Access																												ם, אינם				
Name																													AND OFF			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	CHDONE	0x00	RWH	DMA Channel Linking or Done

Each DMA channel sets the corresponding bit in this register when the entire transfer is done. The interrupt service routine should clear these bits. Enabling a DMA channel will also clear the corresponding LINKDONE bit. Note: software requires to use single-cycle read-modify-write, detailed in 4.2.3 Peripheral Bit Set and Clear

8.6.7 LDMA_DBGHALT - DMA Channel Debug Halt Register

Offset															Bi	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset							•		•	•		ı				•						'		•			•	2	200			
Access																												<u> </u>	2			
Name																												TIVHUU	7			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DBGHALT	0x00	RW	DMA Debug Halt
	Catting one of th	ana hita will maak	the correcte	nding DMA shannelle peripheral request when debugging and the CDL is

Setting one of these bits will mask the corresponding DMA channel's peripheral request when debugging and the CPU is halted. This may be useful for debugging DMA software.

8.6.8 LDMA_SWREQ - DMA Channel Software Transfer Request Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset							•	•	•				•	•	•							•						Ç	noxn			
Access																												3	<u>-</u>			
Name																													SWK WKF W			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	SWREQ	0x00	W1	Software Transfer Requests
	Setting one of these	bits will trigger a	DMA trans	sfer for the corresponding channel. Writing zeros has no effect.

8.6.9 LDMA_REQDIS - DMA Channel Request Disable Register

Offset															Bi	t Po	siti	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	ω	7	9	2	4	က	2	_	0
Reset			1				•	•		•			•					•			•	•	ı	•			•	2	200			
Access																												<u> </u>	}			
Name																												SICCIO	2			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	REQDIS	0x00	RW	DMA Request Disables
	Setting one of these be eral requests will be s		eripheral r	equests for the corresponding channel. When cleared any pending periph-

8.6.10 LDMA_REQPEND - DMA Channel Requests Pending Register

Offset															Bi	t Po	sitio	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	3	2	_	0
Reset																		•									•	OXO				
Access																												Ω	:			
Name																												REOPEND	i i			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	REQPEND	0x00	R	DMA Requests Pending
	When a DMA channe	el has a pending	peripheral	request the corresponding REQPEND bit will read 1.

8.6.11 LDMA_LINKLOAD - DMA Channel Link Load Register

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset		•	•	r		•	•	•		•	•	r		•		•	•	•	•	•	•			•			•	2	200			
Access																												×	<u>-</u>			
Name																													LIINLOAD			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	LINKLOAD	0x00	W1	DMA Link Loads

Setting one of these bits will force the corresponding DMA channel to load the next DMA structure and enable the channel. This empowers software to step through a sequence of descriptors.

8.6.12 LDMA_REQCLEAR - DMA Channel Request Clear Register

Offset															Ві	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	စ	8	7	9	2	4	က	2	_	0
Reset			•					•	•			•				•		•	•					•				0	0000			
Access																												2	<u> </u>			
Name																												L	KECCLEAK			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	REQCLEAR	0x00	W1	DMA Request Clear
	Setting one of these	bits will clear	any internally	registered transfer requests for the corresponding channel.

8.6.13 LDMA_IF - Interrupt Flag Register

Offset														Bi	t Po	siti	on														
0x060	31	30	29	28	27	26	25 25	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	3	2	_	0
Reset	0																										2				
Access	2																										Δ	<u> </u>			
Name	ERROR																										HACC	7			

Bit	Name	Reset	Access	Description
31	ERROR	0	R	Transfer Error Interrupt Flag
	The ERRORIF fla the number of the	•		rror occurs. The CHERROR field in the LDMA_STATUS register reflects ror.
30:8	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DONE	0x00	R	DMA Structure Operation Done Interrupt Flag
	When a channel of	completes a trans	fer or sync or	peration, the corresponding DONE bit is set in the LDMA_IF register.

8.6.14 LDMA_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset	0		•		•	•	•			•	•		•					•	•	•	•	•	•			•	•	ć	0000			
Access	×																											3	X			
Name	ERROR																											L	DONE			

Bit	Name	Reset	Access	Description
31	ERROR	0	W1	Set ERROR Interrupt Flag
	Write 1 to set the	ERROR interrupt	flag	
30:8	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DONE	0x00	W1	Set DONE Interrupt Flag
	\\/:ita	DONE interrupt fl		

8.6.15 LDMA_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x068	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	0		•	•								•		•		•						•				•	•		00×0			
Access	(R)W1																												(R)W1			
Name	ERROR																												DONE			

Bit	Name	Reset	Access	Description
31	ERROR	0	(R)W1	Clear ERROR Interrupt Flag
	Write 1 to clear th (This feature mus			ing returns the value of the IF and clears the corresponding interrupt flags .
30:8	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DONE	0x00	(R)W1	Clear DONE Interrupt Flag
	Write 1 to clear th (This feature mus			g returns the value of the IF and clears the corresponding interrupt flags .

8.6.16 LDMA_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x06C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	စ	∞	7	9	2	4	က	7	_	0
Reset	0				•	•	•	•	•	•		•	•					•		•	•		•	•		•		0	200			
Access	₩ M																											<u> </u>	<u> </u>			
Name	ERROR																											HNOC	7			

Bit	Name	Reset	Access	Description
31	ERROR	0	RW	ERROR Interrupt Enable
	Enable/disable the Ef	RROR interrupt		
30:8	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DONE	0x00	RW	DONE Interrupt Enable
	Enable/disable the Do	ONE interrupt		

8.6.17 LDMA_CHx_REQSEL - Channel Peripheral Request Select Register

		<u> </u>	•
Offset			Bit Position
0x080	30 29 29 27 28 27	2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2	0 1 2 3 4 6 0 0 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Reset			0×00
Access			RW W
Name			O C E SI
			SOURCESEL
			σ σ
Bit	Name	Reset Acces	s Description
31:22	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	SOURCESEL	0x00 RW	Source Select
	Select input source t	o DMA channel.	
	Value	Mode	Description
	0b000000	NONE	No source selected
	0b000001	PRS	Peripheral Reflex System
	0b001000	ADC0	Analog to Digital Converter 0
	0b001010	VDAC0	Digital to Analog Converter 0
	0b001100	USART0	Universal Synchronous/Asynchronous Receiver/Transmitter 0
	0b001101	USART1	Universal Synchronous/Asynchronous Receiver/Transmitter 1
	0b010000	LEUART0	Low Energy UART 0
	0b010100	I2C0	I2C 0
	0b011000	TIMER0	Timer 0
	0b011001	TIMER1	Timer 1
	0b011010	WTIMER0	Wide Timer 0
	0b110000	MSC	Memory System Controller
	0b110001	CRYPTO0	Advanced Encryption Standard Accelerator 0
	0b110011	LESENSE	Low Energy Sensor Interface
15:4	Reserved	To ensure compatibilit	ty with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	SIGSEL	0x0 RW	Signal Select
	Select input signal to	DMA channel.	
	Value	Mode	Description
	SOURCESEL =	0b000000	(NONE)
	0bxxxx	OFF	Channel input selection is turned off
	SOURCESEL =	0b000001	(PRS)

Name	Reset Access	Description
0b0000	PRSREQ0	PRSREQ0
0b0001	PRSREQ1	PRSREQ1
SOURCESEL =	0b001000	(ADC0)
0b0000	ADC0SINGLE	ADC0SINGLE REQ/SREQ
0b0001	ADC0SCAN	ADC0SCAN REQ/SREQ
SOURCESEL =	0b001010	(VDAC0)
0b0000	VDAC0CH0	VDAC0CH0
0b0001	VDAC0CH1	VDAC0CH1
SOURCESEL =	0b001100	(USART0)
0b0000	USART0RXDATAV	USART0RXDATAV REQ/SREQ
0b0001	USART0TXBL	USART0TXBL REQ/SREQ
0b0010	USART0TXEMPTY	USART0TXEMPTY
SOURCESEL =	0b001101	(USART1)
0b0000	USART1RXDATAV	USART1RXDATAV REQ/SREQ
0b0001	USART1TXBL	USART1TXBL REQ/SREQ
0b0010	USART1TXEMPTY	USART1TXEMPTY
0b0011	USART1RXDATAV- RIGHT	USART1RXDATAVRIGHT REQ/SREQ
0b0100	USART1TXBLRIGHT	USART1TXBLRIGHT REQ/SREQ
SOURCESEL =	0b010000	(LEUARTO)
0b0000	LEUART0RXDATAV	LEUART0RXDATAV
0b0001	LEUART0TXBL	LEUART0TXBL
0b0010	LEUART0TXEMPTY	LEUART0TXEMPTY
SOURCESEL =	0b010100	(I2C0)
0b0000	I2C0RXDATAV	I2C0RXDATAV REQ/SREQ
0b0001	I2C0TXBL	I2C0TXBL REQ/SREQ
SOURCESEL =	0b011000	(TIMERO)
0b0000	TIMER0UFOF	TIMER0UFOF
0b0001	TIMER0CC0	TIMER0CC0
0b0010	TIMER0CC1	TIMER0CC1
0b0011	TIMER0CC2	TIMER0CC2
SOURCESEL =	0b011001	(TIMER1)
0b0000	TIMER1UFOF	TIMER1UFOF
0b0001	TIMER1CC0	TIMER1CC0
0b0010	TIMER1CC1	TIMER1CC1
0b0011	TIMER1CC2	TIMER1CC2
0b0100	TIMER1CC3	TIMER1CC3

Bit	Name	Reset Acce	ess Description
	SOURCESEL =	0b011010	(WTIMER0)
	0b0000	WTIMER0UFOF	WTIMER0UFOF
	0b0001	WTIMER0CC0	WTIMER0CC0
	0b0010	WTIMER0CC1	WTIMER0CC1
	0b0011	WTIMER0CC2	WTIMER0CC2
	SOURCESEL =	0b110000	(MSC)
	0b0000	MSCWDATA	MSCWDATA REQ/SREQ
	SOURCESEL =	0b110001	(CRYPTO0)
	0b0000	CRYPTO0DATA0WF	R CRYPTO0DATA0WR
	0b0001	CRYPTO0DATA0XV	VR CRYPTO0DATA0XWR
	0b0010	CRYPTO0DATA0RD	CRYPTO0DATA0RD
	0b0011	CRYPTO0DATA1WF	R CRYPTO0DATA1WR
	0b0100	CRYPTO0DATA1RD	CRYPTO0DATA1RD
	SOURCESEL =	0b110011	(LESENSE)
	0b0000	LESENSEBUFDATA	V LESENSEBUFDATAV REQ/SREQ

8.6.18 LDMA_CHx_CFG - Channel Configuration Register

Offset										Bi	it Po	sitic	on													
0x084	30 29 28	27	26	25	23	22	21	20	19	17	16	15	14	13	12	11	10	6	∞	7	9	5	4	3	2	- c
Reset							0	0		2	OXO															
Access							Z ≷	RW		Ž	<u>}</u>															
Name							-	SRCINCSIGN		O I S G G	AKBOLOLO															
Bit	Name			Reset		,	Acc	ess	s Des	crip	tion															
31:22	Reserved			To ens	sure	сотр	atib	oility	with fo	ıture	dev	ices	, alı	vay	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on in	1.2	Cor	iven-
21	DSTINCSIGN		(0		1	RW		Des	tina	tion	Add	dres	ss Ir	ncre	mei	nt S	ign								
	Value			Mode					Des	cript	tion															
	0		F	POSIT	IVE				Incr	eme	nt de	estin	atio	n a	ddre	ss										
	1		1	NEGA	TIVE				Dec	rem	ent d	esti	nati	on a	addr	ess										
20	SRCINCSIGN		(0			RW		Sou	ırce	Add	ress	s In	crei	men	t Si	gn									
	Value		1	Mode					Des	cript	ion															
	0		F	POSIT	IVE				Incr	eme	nt sc	urce	e ac	dre	ss											
	1		١	NEGA	TIVE	.			Dec	rem	ent s	our	ce a	ddr	ess											
19:18	Reserved			To ens	sure	сотр	patib	oility	with fo	ıture	dev	ices	, alı	vay:	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on in	1.2	Cor	iven-
17:16	ARBSLOTS		(0x0			RW		Arb	itrat	ion (Slot	Nu	mbe	er S	elec	:t									
	For channels i	using	roun	nd robi	in arl	bitrati	on,	this	bit-fiel	d is	used	to s	sele	ct th	ne ni	umb	er o	fslo	ots in	n the	e roi	und	robir	n qu	eue.	
	Value		ı	Mode					Des	cript	ion															
	0		(ONE					One	arb	itrati	on s	lot	sele	cted											
	1		-	TWO					Two	arb	itrati	on s	lots	sel	ecte	d										
	2		F	FOUR					Fou	r arb	oitrati	on s	slots	sel	lecte	ed										
	3		-	EIGHT	Γ				Eigl	nt arl	bitrat	ion :	slot	s se	lect	ed										
15:0	Reserved			To ens	sure	comp	patib	oility	with fo	ıture	dev	ices	, alı	vay:	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on in	1.2	Cor	iven-

8.6.19 LDMA_CHx_LOOP - Channel Loop Counter Register

Offset															Bi	t Po	siti	on														
0x088	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	1	0
Reset																												OVO				
Access																												Z Z Z				
Name																												LOOPCNT	5			
Bit	Na	me					Re	set			Ac	cess	s I	Des	crip	tion																

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	LOOPCNT	0x00	RWH	Linked Structure Sequence Loop Counter
	This bit-field specif		of iterations w	when using looping descriptors. Software should write to LOOPCNT before

using a looping descriptor.

8.6.20 LDMA_CHx_CTRL - Channel Descriptor Control Word Register

Offset															Bi	t Po	siti	on															
0x08C	31	30	29	27	7 00	97	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	5	2 .	၈	ω	7	9	L	ر د	1	ν (7	- 0
Reset	0	0	0x0		0x0		2	OXO	0	0	0	0		2	OXO		0							000x0							0		0×0
Access	2	œ	RWH		RWH			[}	RWH	RWH	RWH	RWH			[} Y		RWH						i	Z Z Z							M		<u>~</u>
Name	DSTMODE	SRCMODE	DSTINC		SIZE		CNICO		IGNORESREQ	DECLOOPCNT	REQMODE	DONEIFSEN			BLUCKSIZE		BYTESWAP						!	XFERCNT							SIRUCIRED		STRUCTTYPE

Bit	Name	Reset	Access	Description
31	DSTMODE	0	R	Destination Addressing Mode

This field specifies the destination addressing mode of linked descriptors. After loading a linked descriptor, reading this field will indicate the destination addressing mode of the linked descriptor. Note that the first descriptor always uses absolute addressing mode.

Value	Mode		Description
0	ABSOLUTE		The DSTADDR field of LDMA_CHx_DST contains the absolute address of the destination data.
1	RELATIVE		The DSTADDR field of LDMA_CHx_DST contains the relative offset of the destination data.
SRCMODE	0	R	Source Addressing Mode

This field specifies the source addressing mode of linked descriptors. After loading a linked descriptor, reading this field will indicate the source addressing mode of the linked descriptor. Note that the first descriptor always uses absolute addressing mode.

DSTINC	0x0	RWH	Destination Address Increment Size
1	RELATIVE		The SRCADDR field of LDMA_CHx_SRC contains the relative offset of the source data.
0	ABSOLUTE		The SRCADDR field of LDMA_CHx_SRC contains the absolute address of the source data.
Value	Mode		Description

This bit-field specifies the stride or number of unit data addresses to increment the destination address after each unit of data is transferred. The unit data width is controlled by the SIZE bit-field and can be a byte, half-word or word.

Value	Mode	Description
0	ONE	Increment destination address by one unit data size after each write
1	TWO	Increment destination address by two unit data sizes after each write
2	FOUR	Increment destination address by four unit data sizes after each write
3	NONE	Do not increment the destination address. Writes are made to a fixed destination address, for example writing to a FIFO.

30

29:28

Bit	Name	Reset	Access	Description
27:26	SIZE	0x0	RWH	Unit Data Transfer Size
	This field specifies	the size of data t	transferred.	
	Value	Mode		Description
	0	BYTE		Each unit transfer is a byte
	1	HALFWORE)	Each unit transfer is a half-word
	2	WORD		Each unit transfer is a word
25:24	SRCINC	0x0	RWH	Source Address Increment Size
				nit data addresses to increment the source address after each unit of data is the SIZE bit-field and can be a byte, half-word or word.
	Value	Mode		Description
	0	ONE		Increment source address by one unit data size after each read
	1	TWO		Increment source address by two unit data sizes after each read
	2	FOUR		Increment source address by four unit data sizes after each read
	3	NONE		Do not increment the source address. In this mode reads are made from a fixed source address, for example reading FIFO.
23	IGNORESREQ	0	RWH	Ignore Sreq
23				Ignore Sreq SREQ) and only respond to multiple requests (REQ) when this bit is set.
23				
	The channel arbiter	will ignore singl	e requests (SREQ) and only respond to multiple requests (REQ) when this bit is set.
	The channel arbiter DECLOOPCNT When using looping	will ignore singl	e requests (SREQ) and only respond to multiple requests (REQ) when this bit is set. Decrement Loop Count
22	The channel arbiter DECLOOPCNT When using looping scriptor execution.	will ignore singl 0 g, setting this bit	e requests (RWH will decreme	SREQ) and only respond to multiple requests (REQ) when this bit is set. Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de-
22	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE	will ignore singl 0 g, setting this bit 0	e requests (RWH will decreme	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select
22	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value	0 g, setting this bit 0 Mode	e requests (RWH will decreme	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description
22	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0	o g, setting this bit Mode BLOCK	e requests (RWH will decreme	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT
22	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN	o will ignore single o o o o o o o o o o o o o o o o o o o	e requests (SRWH) will decreme RWH RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field.
22	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will seems to see the seems to see t	o will ignore single o o o o o o o o o o o o o o o o o o o	e requests (SRWH) will decreme RWH RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will s synchronized in the BLOCKSIZE	o g, setting this bit Mode BLOCK ALL o set the interrupt for case of a SYNC 0x0	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will s synchronized in the BLOCKSIZE	o g, setting this bit Mode BLOCK ALL o set the interrupt for case of a SYNC 0x0	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will s synchronized in the BLOCKSIZE This bit-field control	o will ignore single o o o o o o o o o o o o o o o o o o o	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or Block Transfer Size ensfers per arbitration cycle
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will s synchronized in the BLOCKSIZE This bit-field control Value	o g, setting this bit O Mode BLOCK ALL O set the interrupt for case of a SYNC 0x0 Is the number of	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or Block Transfer Size ensfers per arbitration cycle Description
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will s synchronized in the BLOCKSIZE This bit-field control Value 0	o g, setting this bit O Mode BLOCK ALL O set the interrupt for case of a SYNC 0x0 Is the number of Mode UNIT1	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or Block Transfer Size ensfers per arbitration cycle Description One unit transfer per arbitration
22 21 20	The channel arbiter DECLOOPCNT When using looping scriptor execution. REQMODE Value 0 1 DONEIFSEN Setting this bit will synchronized in the BLOCKSIZE This bit-field control Value 0 1	o g, setting this bit O Mode BLOCK ALL O set the interrupt for case of a SYNC 0x0 Is the number of Mode UNIT1 UNIT2	e requests (S RWH will decreme RWH	Decrement Loop Count ent the LOOPCNT field in the LDMA_CHx_LOOP register after each de- DMA Request Transfer Mode Select Description The LDMA transfers one BLOCKSIZE per transfer request. One transfer request transfers all units as defined by the XFRCNT field. DMA Operation Done Interrupt Flag Set Enable et transfer is done, or linked in the case where the LINK bit is set, or Block Transfer Size ensfers per arbitration cycle Description One unit transfer per arbitration Two unit transfers per arbitration

Bit	Name	Reset	Access	Description
	5	UNIT8		Eight unit transfers per arbitration
	7	UNIT16		Sixteen unit transfers per arbitration
	9	UNIT32		32 unit transfers per arbitration
	10	UNIT64		64 unit transfers per arbitration
	11	UNIT128		128 unit transfers per arbitration
	12	UNIT256		256 unit transfers per arbitration
	13	UNIT512		512 unit transfers per arbitration
	14	UNIT1024		1024 unit transfers per arbitration
	15	ALL		Transfer all units as specified by the XFRCNT field
15	BYTESWAP	0	RWH	Endian Byte Swap
	For word and half-v	vord transfers, set	ting this bit	will swap all bytes of each word or half-word.
14:4	XFERCNT	0x000	RWH	DMA Unit Data Transfer Count
	Specifies number o should be one less			s, or bytes) to transfer, as determined by the SIZE field. The value written unt.
3				
3	should be one less STRUCTREQ	than the desired to	w1	unt.
3	should be one less STRUCTREQ	than the desired to 0 criptor is loaded wi	w1 W1 ith this bit s	Structure DMA Transfer Request
	should be one less STRUCTREQ When a linked desc	than the desired to 0 criptor is loaded wi To ensure con	w1 W1 ith this bit s	Structure DMA Transfer Request set, it will immediately trigger a transfer.
2	should be one less STRUCTREQ When a linked desc Reserved	than the desired to 0 criptor is loaded wi To ensure contions	w1 w1 ith this bit s	Structure DMA Transfer Request set, it will immediately trigger a transfer. with future devices, always write bits to 0. More information in 1.2 Conven-
2	should be one less STRUCTREQ When a linked desc Reserved	than the desired to 0 criptor is loaded wi To ensure contions	w1 w1 ith this bit s	Structure DMA Transfer Request set, it will immediately trigger a transfer. with future devices, always write bits to 0. More information in 1.2 Conven-
2	should be one less STRUCTREQ When a linked desc Reserved STRUCTTYPE	than the desired to 0 criptor is loaded wi To ensure contions 0x0	w1 w1 ith this bit s	Structure DMA Transfer Request set, it will immediately trigger a transfer. with future devices, always write bits to 0. More information in 1.2 Conven- DMA Structure Type
2	should be one less STRUCTREQ When a linked desc Reserved STRUCTTYPE Value	than the desired to 0 criptor is loaded with the desired to the criptor is loaded with the contions 0x0 Mode	ransfer cou W1 ith this bit s mpatibility v	Structure DMA Transfer Request set, it will immediately trigger a transfer. with future devices, always write bits to 0. More information in 1.2 Conven- DMA Structure Type Description

8.6.21 LDMA_CHx_SRC - Channel Descriptor Source Data Address Register

Offset		Bit Position																														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		0000000X0																														
Access																RWH																
Name		SRCADDR																														
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
31:0	SR	CAE	DDR				0x0	0000	0000	0	RW	/H		Sou	rce	Data	Ac	ddre	SS													

Writing to this register sets the source address. Reading from this register during a DMA transfer will indicate the next source read address. The value of this register is incremented or decremented with each source read.

8.6.22 LDMA_CHx_DST - Channel Descriptor Destination Data Address Register

Offset															Bit	Po	siti	on														
0x094	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset																00000000x0																
Access																RWH																
Name																DSTADDR																

Bit	Name	Reset	Access	Description
31:0	DSTADDR	0x00000000	RWH	Destination Data Address


Writing to this register sets the destination address. Reading from this register during a DMA transfer will indicate the next destination write address. This value of this register is incremented or decremented with each destination write.

8.6.23 LDMA_CHx_LINK - Channel Descriptor Link Structure Address Register

Offset															В	it Po	ositi	on														
0x098	31	30	29	78	27	26	25	24	23	22	21	20	9	18	17	16	15	4	13	12	7	9	о	ω	7	9	2	4	3	2	1	0
Reset													•			nnnnnnnn				•											0	0
Access															2	I M Y															RWH	œ
Name																LINKADDK															LINK	LINKMODE
Bit	Nan	1e					Re	set			Ac	ces	s	Des	scrip	tion	1															
31:2	LIN	(A[DDF	₹			0x	0000	0000	00	RV	/H		Lin	k Stı	ruct	ure	Add	Ires	s												
	To ι also														l des ister															ed, i	t ma	y
1	LIN	(0				RV	/H		Lin	k Ne	xt S	truc	tur	е													
	Afte also																	ad t	he r	next	link	ed c	lesc	ripto	or. If	the	nex	t link	ked	des	cript	or
0	LIN	ΚM	ODE				0				R			Lin	k Stı	ruct	ure	Add	Ires	sing	ј Мс	ode										
	This field specifies the addressing mode of linked descriptors. After loading a linked descriptor, reading this field will in cate the addressing mode of the loaded linked descriptor. Note that the first descriptor always uses absolute addressi mode.																															
	Valu	ie					Mc	de						Des	scrip	tion																_
	0	O ABSOLUTE The LINKADDR field of LDMA_CHx_LINK contains the absolute address of the linked descriptor.											-																			
	1													et																		

9. RMU - Reset Management Unit





9.1 Introduction

The RMU is responsible for handling the reset functionality of the EFR32.

9.2 Features

- · Reset sources
 - Power-on Reset (POR)
 - Brown-out Detection (BOD) on the following power domains:
 - · Analog Unregulated Power Domain AVDD
 - · Digital Unregulated Power Domain DVDD
 - · Regulated Digital Domain DECOUPLE (DEC)
 - · RESETn pin reset
 - · Watchdog reset
 - Software triggered reset (SYSRESETREQ)
 - · Core LOCKUP condition
- EM4 Hibernate/Shutoff Detection
- EM4 Hibernate/Shutoff wakeup reset from GPIO pin
- · Configurable reset levels
- · A software readable register indicates the cause of the last reset

Quick Facts

What?

The RMU ensures correct reset operation. It is responsible for connecting the different reset sources to the reset lines of the EFR32.

Why?

A correct reset sequence is needed to ensure safe and synchronous startup of the EFR32. In the case of error situations such as power supply glitches or software crash, the RMU provides proper reset and startup of the EFR32.

How?

The Power-on Reset and Brown-out Detector of the EFR32 provides power line monitoring with exceptionally low power consumption. The cause of the reset may be read from a register, thus providing software with information about the cause of the reset.

9.3 Functional Description

The RMU monitors each of the reset sources of the EFR32. If one or more reset sources go active, the RMU applies reset to the EFR32. When the reset sources go inactive the EFR32 starts up. At startup the EFR32 loads the stack pointer and program entry point from memory, and starts execution. Figure 9.1 RMU Reset Input Sources and Connections on page 199 shows an overview of the reset system on EFR32.




Figure 9.1. RMU Reset Input Sources and Connections

9.3.1 Reset Levels

The reset sources on EFR32 can be divided in two main groups; Hard resets and Soft resets.

The soft resets can be configured to be either DISABLED, LIMITED, EXTENDED or FULL. The reset level for soft reset sources is configured in the xxxRMODE bitfields in RMU_CTRL.

Table 9.1. Reset Levels

RMU_CTRL_xxxRMODE	Parts of System Reset
DISABLED	Nothing is reset, request will not be registered in RMU_RSTCAUSE
LIMITED	Everything reset, with exception of CRYOTIMER, DEBUGGER, RTCC, VMON and parts of CMU, RMU and EMU.
EXTENDED	Everything reset, with exception of CRYOTIMER, DEBUGGER, and parts of CMU, RMU and EMU.
FULL	Everything reset, with exception of some registers in RMU and EMU.

The reset sources resulting in a soft reset are:

- · Watchdog reset
- · Lockup reset
- · System reset request
- Pin reset (Pin reset can be configured to be either a soft or a hard reset, see 9.3.5 RESETn Pin Reset for details.)

Note: LIMITED and EXTENDED resets are synchronized to HFSRCCLK. If HFSRCCLK is slow, there will be latency on reset assertion. If HFSRCCLK is not running, reset will be asserted after a timeout.

Hard resets will reset the entire chip, the reset sources resulting in a hard reset are:

- Power-on reset
- · Brown-out reset
- Pin reset (Pin reset can be configured to be either a soft or a hard reset, see 9.3.5 RESETn Pin Reset for details.)

9.3.2 RMU_RSTCAUSE Register

Whenever a reset source is active, the corresponding bit in the RMU_RSTCAUSE register is set. At startup the program code may investigate this register in order to determine the cause of the reset. The register is cleared upon POR and software write to RMU_CMD_RCCLR. The register should be cleared after the value has been read at startup, otherwise the register may indicate multiple causes for the reset at next startup.

RMU_RSTCAUSE should be interpreted according to Table 9.2 RMU Reset Cause Register Interpretation on page 201. In Table 9.2 RMU Reset Cause Register Interpretation on page 201, the reset causes are ordered by severity from right to left. A reset cause bit is invalidated (i.e. can not be trusted) if one of the bits to the right of it does not match the table. X bits are don't care.

Note: It is possible to have multiple reset causes. For example, an external reset and a watchdog reset may happen simultaneously.

Table 9.2. RMU Reset Cause Register Interpretation

RMU_R	STCAUS	E							Reset cause
EM4RST	WDOGRST	SYSREQRST	LOCKUPRST	EXTRST	DECBOD	DVDDBOD	AVDDBOD	PORST	
Х	Х	Х	Х	Х	Х	Х	Х	1	Power on reset
Х	Х	Х	Х	X	Х	Х	1	0	Brown-out on AVDD power
Х	Х	Х	Х	Х	Х	1	Х	0	Brown-out on DVDD power
Х	Х	Х	Х	Х	1	Х	Х	0	Brown-out on DEC power
Х	Х	Х	Х	1	Х	Х	Х	0	Pin reset
Х	Х	Х	1	0/X ¹	0	0	0	0	Lockup reset
Х	Х	1	Х	0/X ¹	0	0	0	0	System reset request
Х	1	Х	Х	0/X ¹	0	0	0	0	Watchdog reset
1	Х	Х	Х	0/X ¹	0	0	0	0	System has been in EM4
1. Pin	reset cor	nfigured a	s hard/so	oft	1	1	1	1	1

9.3.3 Power-On Reset (POR)

The POR ensures that the EFR32 does not start up before the AVDD supply voltage has reached the threshold voltage VPORthr (roughly 1.2V). Before the POR threshold voltage is reached, the EFR32 is kept in reset state. The operation of the POR is illustrated in Figure 9.2 RMU Power-on Reset Operation on page 202, with the active low POWERONn reset signal. The reason for the "unknown" region is that the corresponding supply voltage is too low for any reliable operation.




Figure 9.2. RMU Power-on Reset Operation

9.3.4 Brown-Out Detector (BOD)

The EFR32 has 3 brownout detectors, one for the unregulated power (DVDD), one for the regulated internal power (DECOUPLE), and one for the Analog Power Domain (AVDD). The BODs are constantly monitoring these supply voltages. Whenever the unregulated or regulated power drops below the VBODthr value (see the Electrical Characteristics section of the data sheet for details), or if AVDD drops below the voltage at the DECOUPLE pin, the corresponding active low BROWNOUTn line is held low. The BODs also include hysteresis, which prevents instability in the corresponding BROWNOUTn line when the supply is crossing the VBODthr limit or the AVDD supply drops below the DECOUPLE pin. The operation of the BOD is illustrated in Figure 9.3 RMU Brown-out Detector Operation on page 202. The "unknown" regions are handled by the POR module.




Figure 9.3. RMU Brown-out Detector Operation

9.3.5 RESETn Pin Reset

The pin reset on EFR32 can be configured to be either hard or soft. By default, pin reset is configured as a soft reset source. To configure it as a hard reset, clear the PINRESETSOFT bit in CLW0 in the Lock bit page, see 7.3.2 Lock Bits (LB) Page Description for details. Forcing the RESETn pin low generates a reset of the EFR32. The RESETn pin includes an on-chip pull-up resistor, and can therefore be left unconnected if no external reset source is needed. Also connected to the RESETn line is a filter which prevents glitches from resetting the EFR32.

9.3.6 Watchdog Reset

The Watchdog circuit is a timer which (when enabled) must be cleared by software regularly. If software does not clear it, a Watchdog reset is activated. This functionality provides recovery from a software stalemate. Refer to the Watchdog section for specifications and description. The Watchdog reset can be configured to cause different levels of reset as determined by WDOGRMODE in the RMU CTRL register.

9.3.7 Lockup Reset

A Cortex-M4 lockup is the result of the core being locked up because of an unrecoverable exception following the activation of the processor's built-in system state protection hardware.

A Cortex-M4 lockup gives immediate indication of seriously errant kernel software. This is the result of the core being locked up due to an unrecoverable exception following the activation of the processor's built in system state protection hardware. For more information about the Cortex-M4 lockup conditions see the ARMv7-M Architecture Reference Manual. The Lockup reset does not reset the Debug Interface, unless configured as a FULL reset. The Lockup reset can be configured to cause different levels of reset as determined by the LOCKUPRMODE bits in the RMU_CTRL register. This includes disabling the reset.

9.3.8 System Reset Request

Software may initiate a reset (e.g. if it finds itself in a non-recoverable state). By asserting the SYSRESETREQ in the Application Interrupt and Reset Control Register, a reset is issued. The SYSRESETREQ does not reset the Debug Interface, unless configured as a FULL reset. The SYSRESTREQ reset can be configured to cause different levels of reset as determined by SYSRESETRMODE bits in the RMU_CTRL register. This includes disabling the reset.

9.3.9 Reset State

The RESETSTATE bitfield in RMU_CTRL is a read-write register intended for software use only, and can be used to keep track of state throughout a reset. This bitfield is only reset by POR and hard pin reset.

9.3.10 Register Reset Signals

Figure 9.1 RMU Reset Input Sources and Connections on page 199 shows an overview of how the different parts of the design are affected by the different levels of reset. For RMU, EMU and CMU there are some exceptions. These are given in the following tables.

9.3.10.1 Registers With Alternate Reset

Table 9.3. Alternate Reset for Registers in RMU

RMU Reset Levels	
POR and hard pin reset	RMU_CTRL_WDOGRMODE
	RMU_CTRL_LOCKUPRMODE
	RMU_CTRL_SYSRMODE
	RMU_CTRL_PINRMODE
	RMU_CTRL_RESETSTATE
FULL reset	RMU_LOCK_LOCKKEY

Table 9.4. Alternate Reset for Registers in CMU

CMU Reset Levels	
FULL reset	CMU_LFRCOCTRL
	CMU_LFXOCTRL
EXTENDED reset	CMU_LFECLKSEL
	CMU_LFECLKEN0
	CMU_LFEPRESC0

Table 9.5. Alternate Reset for Registers in EMU

EMU Reset Levels	
POR, BOD, and hard pin reset	EMU_BIASCONF_LSBIAS_SEL
POR, BOD, and hard pin reset	EMU_DCDCLNVCTRL
POR and hard pin reset	EMU_CTRL_EM2BODDIS
POR, BOD, and hard pin reset	EMU_PWRCTRL
	EMU_DCDCCTRL
	EMU_DCDCMISCCTRL
	EMU_DCDCZDETCTRL
	EMU_DCDCCLIMCTRL
	EMU_DCDCLNCOMPCTRL
	EMU_DCDCLPVCTRL
	EMU_DCDCLPCTRL
	EMU_DCDCLNFREQCTRL
	EMU_DCDCLPEM01CFG

EMU Reset Levels	
EXTENDED reset	EMU_VMONAVDDCTRL
	EMU_VMONALTAVDDCTRL
	EMU_VMONDVDDCTRL
	EMU_VMONIO0CTRL
FULL reset	EMU_EM4CTRL

9.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	RMU_CTRL	RW	Control Register
0x004	RMU_RSTCAUSE	R	Reset Cause Register
0x008	RMU_CMD	W1	Command Register
0x00C	RMU_RST	RW	Reset Control Register
0x010	RMU_LOCK	RWH	Configuration Lock Register

9.5 Register Description

9.5.1 RMU_CTRL - Control Register

Offset											Bit	Posi	tion														
0x000	30 29 29	28	26	25	23	22	27	20	19	8	17	9 7	4	13	7	7	10	တ	∞	7	9	5	4	က	2	_	c
Reset				0×0								l		0×4				0x2	ı			0×0				0x4	
Access				§ S S										N N				Z N				₩					_
Name				RESETSTATE										PINRMODE				SYSRMODE				_OCKUPRMODE F				WDOGRMODE	
Bit	Name			Reset			Acce	ess	D	esc	ript	ion															
31:26	Reserved			To ens	ure	comp	atibi	ility	with	ı futi	ure	devic	es, al	ways	wr	ite k	its t	0.	Мо	re in	forn	natio	on i	in 1	2 C	onver	7-
25:24	RESETST	ATE		0x0		-	₹W		S	yste	em :	Softw	are F	Rese	t St	ate											
	Bit-field for	r softwa	ire us	se only.	This	field	has	no	effe	ect o	n th	e RM	U an	d is r	ese	t by	pow	er-c	on re	eset	and	l hai	rd p	oin re	eset	only	
23:15	Reserved			To ens																							
14:12	PINRMOD	E		0x4																							
	Controls the page is se		leve	l for Pin	or Pin reset request. These settings only apply when PINRESETSOFT in CLW0 in the Lock bit																						
	Value			Mode					D	esci	ripti	on															_
	0			DISAB	LEC)			R	lese	t red	quest	is blo	ckec	l.												
	1			LIMITE	D				Т	he C	CRY	OTIM	IER,	DEB	JG	GEF	R, R	CC	, ar	e no	t re	set.					
	2			EXTEN	NDE	D			Т	he C	CRY	OTIM	IER,	DEB	JG	GEF	R are	no	t res	et.	RTC	C is	s re	set.			
	4			FULL					Т	he e	entir	e dev	ice is	rese	t ex	сер	t so	ne	ЕΜΙ	J ar	ıd R	MU	reç	giste	rs.		
11	Reserved			To ens	ure	comp	atibi	ility	with	ı futi	ure	devic	es, al	ways	wr	ite k	its t	0.	Мо	re in	forn	natio	on i	in 1.:	2 C	onver	7-
10:8	SYSRMO	DE		0x2 RW Core Sysreset Reset Mode																							
	Controls th	ne reset	leve	l for Co	re S	YSRI	ST	res	et re	eque	est.																
	Value			Mode					D	Description																	
	0			DISAB	LEC)			R	lese	t red	quest	is blo	ckec													_
	1			LIMITE	Đ				Т	he C	CRY	OTIM	IER,	DEB	JG	GEF	R, R	CC	, ar	e no	t re	set.					
	2			EXTEN	NDE	D			The CRYOTIMER, DEBUGGER, RTCC, are not reset. The CRYOTIMER, DEBUGGER are not reset. RTCC is reset.																		
	4			FULL					Т	he e	entir	e dev	ice is	rese	t ex	сер	t so	ne	EMU	J ar	ıd R	MU	reç	giste	rs.		_
7	Reserved			To ens	o ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-																						

tions

Bit	Name	Reset	Access	Description
6:4	LOCKUPRMODE	0x0	RW	Core LOCKUP Reset Mode
	Controls the reset le	vel for Core LOC	KUP reset	request.
	Value	Mode		Description
	0	DISABLED		Reset request is blocked.
	1	LIMITED		The CRYOTIMER, DEBUGGER, RTCC, are not reset.
	2	EXTENDED		The CRYOTIMER, DEBUGGER are not reset. RTCC is reset.
	4	FULL		The entire device is reset except some EMU and RMU registers.
3	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	WDOGRMODE	0x4	RW	WDOG Reset Mode
	Controls the reset le	vel for WDOG res	set request	i.
	Value	Mode		Description
	0	DISABLED		Reset request is blocked. This disable bit is redundant with enable/ disable bit in WDOG
	1	LIMITED		The CRYOTIMER, DEBUGGER, RTCC, are not reset.
	2	EXTENDED		The CRYOTIMER, DEBUGGER are not reset. RTCC is reset.
	4	FULL		The entire device is reset except some EMU and RMU registers.

9.5.2 RMU_RSTCAUSE - Reset Cause Register

Offset				В	it Po	sition											
0x004	33 33 25 28 28 27 27 27	23 24 22 23 23 23 23	20	18 17	16	5 4	13	7	9	6	8	~	2	4	က	7	- 0
Reset				'	0			0	0	0	0			0	0	0	0
Access					~			œ	22	2	œ			2	22	œ	2
Name					EM4RST			WDOGRST	SYSREQRST	LOCKUPRST	EXTRST			DECBOD	DVDDBOD	AVDDBOD	PORST
Bit	Name	Reset	Access	Descrip	tion												
31:17	Reserved	To ensure contions	mpatibility	with future	e devi	ices, al	lways w	rite t	oits t	o 0.	Mor	e info	rmati	on ir	า 1.2	Cor	iven-
16	EM4RST	0	R	EM4 Re	set												
	Set if the system has to interpret this bit.	been in EM4. M	lust be clea	ared by so	ftwar	e. See	9.3.2 R	RMU_	_RS	TCA	USE	E Reg	ister '	for d	etail	s on	how
15:12	Reserved	To ensure contions	mpatibility	with future	e devi	ices, al	lways w	rite t	oits t	o 0.	Mor	e info	rmati	on ir	1.2	Cor	iven-
11	WDOGRST	0	R	Watchd	log R	eset											
	Set if a watchdog reset has been performed. Must be cleared by software. See 9.3.2 RMU_RSTCAUSE Register for details on how to interpret this bit.																
10	SYSREQRST	0	R	System	Req	uest R	leset										
	Set if a system reque details on how to inte		n performe	ed. Must b	e cle	ared by	y softwa	are. S	See	9.3.2	2 RN	/IU_R	STCA	AUSI	E Re	egist	er for
9	LOCKUPRST	0	R	LOCKU	P Re	set											
	Set if a LOCKUP res on how to interpret the		uested. Mu	st be clea	red b	y softw	/are. Se	e 9.:	3.2 F	RMU	J_RS	STCA	JSE	Regi	ister	for c	letails
8	EXTRST	0	R	Externa	ıl Pin	Reset	t										
	Set if an external pin details on how to inte		performed	. Must be	cleare	ed by s	oftware	. Se	e 9.3	3.2 F	RMU	_RST	CAU	SE F	Regi	ster	for
7:5	Reserved	To ensure contions	mpatibility	with future	e devi	ices, al	lways w	rite t	oits t	o 0.	Mor	e info	rmati	on ir	1.2	Cor	iven-
4	DECBOD	0	R	Brown	Out [Detect	or Deco	uple	e Do	mai	n R	eset					
	Set if a regulated domain brown out detector reset has been performed. Must be cleared by software. See 9.3.2 RMU_RSTCAUSE Register for details on how to interpret this bit.																
3	DVDDBOD	0	R	Brown	Out [Detect	or DVD	D Re	set								
	Set if a unregulated domain brown out detector reset has been performed. Must be cleared by software. See 9.3.2 RMU_RSTCAUSE Register for details on how to interpret this bit.																
2	AVDDBOD	0	R	Brown	Out [Detect	or AVD	D Re	set								
	Set if a unregulated of 9.3.2 RMU_RSTCAL							ust t	oe cl	eare	ed by	/ soft\	vare.	See	;		
1	Reserved	To ensure contions	mpatibility	with future	devi	ices, al	lways w	rite t	oits t	o 0.	Mor	e info	rmati	on ir	1.2	Cor	nven-

Bit	Name	Reset	Access	Description								
0	PORST	0	R	Power on Reset								
	•	set if a power on reset has been performed. Must be cleared by software. See 9.3.2 RMU_RSTCAUSE Register for detail n how to interpret this bit.										

9.5.3 RMU_CMD - Command Register

Offset															Bi	t Po	sitio	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	æ	7	9	2	4	က	2	_	0
Reset			'				•																	'			'					0
Access																																W1
Name																																RCCLR
Dit	No						Po	oot			٨٥	0000	, ,	Doo	orin	tion																

Bit	Name	Reset	Access	Description						
31:1	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-						
0	RCCLR	0	W1	Reset Cause Clear						
	Set this bit to clear the RSTCAUSE register.									

9.5.4 RMU_RST - Reset Control Register

Offset															Bi	t Po	ositi	on														
0x00C	31	30	53	78	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	11	10	6	8	7	9	5	4	က	2	_	_ o
Reset			•	•	•												•						•									
Access																																
Name																																

Bit	Name	Reset Access D	Description
31:0	Reserved	To ensure compatibility with tions	h future devices, always write bits to 0. More information in 1.2 Conven-

9.5.5 RMU_LOCK - Configuration Lock Register


Offset															Bi	t Pc	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Reset																									0000x0							
Access																									ZW H							
Name																									LOCKKEY							
Bit	Na	me					Re	set			Ac	ces	s l	Des	crip	tion																
21.16							T-					:1:4.		46 f.	4	da	<i>.</i> :				rita l	ita	to 0	111		nfor		- i	- 1 -	20-	n (0	

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock Key

Write any other value than the unlock code to lock RMU_CTRL and RMU_RST from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	RMU registers are unlocked
LOCKED	1	RMU registers are locked
Write Operation		
LOCK	0	Lock RMU registers
UNLOCK	0xE084	Unlock RMU registers

10. EMU - Energy Management Unit



Quick Facts

What?

The EMU (Energy Management Unit) handles the different low energy modes in EFR32

Why?

The need for performance and peripheral functions varies over time in most applications. By efficiently scaling the available resources in real time to match the demands of the application, the energy consumption can be kept at a minimum.

How?

With a broad selection of energy modes, a high number of low-energy peripherals available even in EM2 Deep Sleep, and short wake-up time (3 µs from EM2 Deep Sleep and EM3 Stop), applications can dynamically minimize energy consumption during program execution.

10.1 Introduction

The Energy Management Unit (EMU) manages all the low energy modes (EM) in EFR32. Each energy mode manages whether the CPU and the various peripherals are available. The energy modes range from EM0 Active to EM4 Shutoff. EM0 Active mode provides the highest amount of features, enabling the CPU, Radio, and peripherals with the highest clock frequency. EM4 Shutoff Mode provides the lowest power state, allowing the part to return to EM0 Active on a wake-up condition. The EMU also controls the various power routing configurations, internal regulators settings, and voltage monitoring needed for optimal power configuration and protection.


10.2 Features

The primary features of the EMU are listed below:

- · Energy Modes control
 - · Entry into EM4 Hibernate or EM4 Shutoff
 - · Configuration of regulators and clocks for each Energy Mode
 - · Configuration of various EM4 Hibernate/Shutoff wake-up conditions
 - · Configuration of RAM power and retention settings
 - · Configuration of GPIO retention settings
- · Power routing configurations
 - DCDC control
 - · Internal power switches allowing for extensible system power architecture
- · Temperature measurement control and status
- · Brown Out Detection
- · Voltage Monitoring
 - · Four dedicated continuous monitor channels
 - · Optional monitor features include interrupt generation and low power mode wake-up
- · State Retention
- · Voltage Scaling
 - EM0/EM1 voltage scaling
 - EM2/EM3 voltage scaling
 - · EM4H voltage scaling

10.3 Functional Description

The EMU is responsible for managing the wide range of energy modes available in EFR32. The block works in harmony with the entire platform to easily transition between energy modes in the most efficient manner possible. The following diagram Figure 10.1 EMU Overview on page 213, shows the relative connectivity to the various blocks in the system.



The combined state of these modules defines the required energy mode

Figure 10.1. EMU Overview

The EMU is available on the peripheral bus. The energy management state machine controls the internal voltage regulators, oscillators, memories, and interrupt system. Events, interrupts, and resets can trigger the energy management state machine to return to the active state. This is further described in the following sections.

The power architecture is highly configurable to meet system power performance needs. Several external power configurations are supported. The EMU allows flexible control of internal DCDC, Digital LDO Regulator, and internal power switching.

10.3.1 Energy Modes

EFR32 features six main energy modes, referred to as Energy Mode 0 (EM0 Active) through Energy Mode 4 (EM4 Shutoff). The Cortex-M4 is only available for program execution in EM0 Active. In EM0 Active/EM1 Sleep any peripheral function can be enabled. EM2 Deep Sleep through EM4 Shutoff, also referred to as low energy modes, provide a significantly reduced energy consumption while still allowing a rich set of peripheral functionality. The following Table 10.1 table on page 214 shows the possible transitions between different energy modes.

Table 10.1. Energy Mode Transitions

Current Mode	EM Transition	EM Transition Action										
	Enter EM0 Active	Enter EM1 Sleep	Enter EM2 Deep Sleep	EnterEM3 Stop	EnterEM4 Hi- bernate	Enter EM4 Shutoff						
EM0 Active		Sleep (WFI, WFE)	Deep Sleep (WFI, WFE)	Deep Sleep (WFI, WFE)	EM4 Entry	EM4 Entry						
EM1 Sleep	IRQ		Peripheral wake up done ¹	Peripheral wake up done ¹								
EM2 Deep Sleep	IRQ	Peripheral wake up req ¹										
EM3 Stop	IRQ	Peripheral wake up req ¹										
EM4 Hibernate	Wake Up											
EM4 Shutoff	Wake Up											
N		1	1	1	1	1						

Note:

The LESENSE, ADC, RAC, and LEUART have the ability to temporarily wake up the part from either EM2 Deep Sleep or EM3 Stop to EM1 Sleep in order to transfer data. Once completed, the part is automatically placed back into the EM2 Deep Sleep or EM3 Stop mode.

The Core can always request to go to EM1 Sleep with the WFI or WFE command during EM0 Active. The core will be prevented from entering EM2 Deep Sleep or EM3 Stop if the RAC is transferring data or if Flash is programming or erasing.

An overview of supported energy modes and available functionality is shown in Table 10.2 EMU Energy Mode Overview on page 214. For each energy mode, the system will typically default to its lowest power configuration, with non-essential clocks and peripherals disabled. Functionality may be then selectively enabled by software.

Table 10.2. EMU Energy Mode Overview

	EM0 Active/EM1 Sleep	EM2 Deep Sleep	EM3 Stop	EM4 Hiber- nate	EM4 Shutoff
Wake-up time to EM0 Active/EM1 Sleep	_	3 µs ¹	3 µs ¹	90 μs ¹	90 μs ¹
Core Active	Yes, in EM0 only	_	_	_	_
Debug	Available	See Note ²	See Note ²	_	_
Digital logic and system RAM retained	Yes	Yes	Yes	_	_
Flash Memory Access	Available	_	_	_	_
LDMA (Linked DMA Controller)	Available	Available ³	Available ³	_	_
RAC (Radio Controller)	Available	Available ⁴	_	_	_

^{1.} Peripheral wake-up from EM2/3 to EM1 and then automatically back to EM2/3 when done.

	EM0 Active/EM1 Sleep	EM2 Deep Sleep	EM3 Stop	EM4 Hiber- nate	EM4 Shutoff
High Frequency Oscillators (HFRCO, HFXO) and Clocks (HFSRCLK, HFCLK, HFCORECLK, HFBUSCLK, HFPERCLK, HFRADIOCLK, HFCLKLE)	Available	_	_	_	_
Auxiliary High Frequency Oscillator (AUXHFR-CO) and Clock (AUXCLK)	Available	Available ⁵	Available ⁵	_	_
Low Frequency Oscillators (LFRCO, LFXO)	Available	Available	_	Available	Available
Low Energy Clocks A and B (LFACLK, LFBCLK)	Available	Available	Available ⁷	_	_
Low Energy Clock E (LFECLK)	Available	Available	Available ⁷	Available	_
ULFRCO (Ultra Low Frequency Oscillator)	On	On	On	On	Available
CRYPTO (Crypto Accelerator)	Available	_	_	_	_
GPCRC (Cyclic Redundancy Check)	Available	_	_	_	_
RTCC (Real Time Counter and Calendar)	Available	Available	Available ⁷	Available	_
RTCC Memory Retained	Yes	Yes	Yes	Yes	_
USART (USART/SPI)	Available	_	_	_	_
LEUART (Low Energy UART)	Available	Available ³	_	_	_
I ² C	Available	Available ⁶	Available ⁶	_	_
TIMER (Timer/Counter)	Available	_	_	_	_
LETIMER (Low Energy Timer)	Available	Available	Available ⁷	_	_
CRYOTIMER (Ultra Low Energy Timer/Counter)	Available	Available	Available ⁷	Available	Available
WDOG (Watchdog)	Available	Available	Available ⁷	_	_
PCNT (Pulse Counter)	Available	Available	Available	_	_
ACMP (Analog Comparator)	Available	Available ⁸	Available ⁸	_	_
ADC (Analog to Digital Converter)	Available	Available ^{3, 5}	Available ^{3, 5}	_	_
IDAC (Current Digital to Analog Converter)	Available	Available	Available	_	_
VDAC (Voltage Digital to Analog Converter)	Available	Available	Available	_	_
OPAMP (Operational Amplifier)	Available	Available	Available	_	_
LESENSE (Low Energy Sensor)	Available	Available ³	_	_	_
EMU Temperature Sensor	Available	Available	Available	Available	_
DC-DC Converter	Available	Available	Available	Available	_
VMON Wake-up or Reset	Available	Available	Available	Available	_
Brown-Out Detect/Power-on Reset	Available	Available	Available	Available	Available
Pin Reset	Available	Available	Available	Available	Available
GPIO Pin Interrupts	Available	Available	Available	Available ⁹	Available ⁹
GPIO Pin State Retention	Yes	Yes	Yes	Available ¹⁰	Available ¹⁰

Sleep	A	Active/EM1	EM2 Deep Sleep	EM3 Stop	EM4 Hiber- nate	EM4 Shutoff
-------	---	------------	-------------------	----------	--------------------	-------------

Note:

- 1. Approximate time. Refer to the data sheet
- 2. Leaving the debugger connected when in EM2 or EM3 will cause the system to enter a higher power EM2 mode in which the high frequency clocks are still enabled and certain core functionality is still powered-up in order to maintain debug-functionality.
- 3. The LDMA can be used with some low power peripherals (e.g., ADC, LEUART, LESENSE) in EM2/3. Features required by the LDMA which are not supported in EM2/3 (e.g., HFCLK), will be automatically enabled prior to the LDMA transfer and then automatically disabled afterwards.
- 4. The RAC can be woken via a PRS interrupt to EM1 to transfer data. Once complete, the system will return to EM2.
- 5. While in EM2/3, an asynchronous event can be routed through PRS (e.g. GPIO IRQ or ACMP output) to wake up the ADC. Features required by the ADC which are not supported in EM2/3 (e.g., AUXHFRCO) will be automatically enabled to allow the ADC to convert a sample, and then automatically disabled afterwards.
- 6. I2C functionality limited to receive address recognition
- 7. Must be using ULFRCO
- 8. ACMP functionality in EM2/3 limited to edge interrupt
- 9. Pin wake-up in EM4 supported only on GPIO_EM4WUx pins. Consult data sheet for complete list of pins.
- 10. If enabled in EMU->EM4CTRL.EM4IORETMODE.

The different energy modes are summarized in the following sections.

10.3.1.1 EM0 Active

EM0 Active provides all system features.

- · Cortex-M4 is executing code
- · Radio functionality is available
- · High and low frequency clock trees are active
- · All oscillators are available
- · All peripheral functionality is available

10.3.1.2 EM1 Sleep

EM1 Sleep disables the core but leaves the remaining system fully available.

- · Cortex-M4 is in sleep mode. Clocks to the core are off
- · Radio functionality is available
- · High and low frequency clock trees are active
- · All oscillators are available
- · All peripheral functionality is available

10.3.1.3 EM2 Deep Sleep

This is the first level into the low power energy modes. Most of the high frequency peripherals are disabled or have reduced functionality. Memory and registers retain their values.

- · Cortex-M4 is in sleep mode. Clocks to the core are off.
- · High frequency clock tree is inactive
- · Low frequency clock tree is active
- · The following oscillators are available
 - LFRCO, LFXO, ULFRCO, AUXHFRCO (on demand, if used by the ADC)
- · The following low frequency peripherals are available
 - RTCC, WDOG, LEUART, LETIMER, LESENSE, PCNT, CRYOTIMER
- The following analog peripherals are available (with potential limitations on functionality)
 - · ADC, IDAC, VDAC, OPAMP
- · Wake-up to EM0 Active through
 - Peripheral interrupt, reset pin, power on reset, asynchronous pin interrupt, I2C address recognition, or ACMP edge interrupt
- · Wake-up to EM1 Sleep through
 - RAC data transfer request
 - · Part returns to EM2 Deep Sleep when transfers are complete
- · RAM and register values are preserved
 - RAM blocks may be optionally powered down for lower power
- · GPIO pin state is retained
- · RTCC memory is retained
- The DC-DC converter can be configured to remain on in Low Power mode.

10.3.1.4 EM3 Stop

In this low energy mode, all low frequency oscillators (LFXO, LFRCO) and all low frequency clocks derived from them, are stopped, as well as all high frequency clocks. Most peripherals are disabled or have reduced functionality. Memory and registers retain their values.

- · Cortex-M4 is in sleep mode. Clocks to the core are off.
- · High frequency clock tree is inactive
- All low frequency clock trees derived from the low frequency oscillators (LFXO, LFRCO) are inactive
- · The following oscillators are available
 - ULFRCO, AUXHFRCO (on demand, if used by the ADC)
- The following low frequency peripherals are available if clocked by the ULFRCO
 - RTCC, WDOG, CRYOTIMER
- · The following analog peripherals are available (with potential limitations on functionality)
 - ADC, IDAC, VDAC, OPAMP
- · Wake-up to EM0 Active through
 - Peripheral interrupt, reset pin, power on reset, asynchronous pin interrupt, I2C address recognition, or ACMP edge interrupt
- · Wake-up to EM1 Sleep through
 - · RAC data transfer request
 - · Part returns to EM3 Stop when transfers are complete
- RAM and register values are preserved
 - · RAM blocks may be optionally powered down for lower power
- · GPIO pin state is retained
- · RTCC memory is retained
- The DC-DC converter can be configured to remain on in Low Power mode.

10.3.1.5 EM4 Hibernate

The majority of peripherals are shutoff to reduce leakage power. A few selected peripherals are available. System memory and registers do not retain values. GPIO PAD state and RTCC RAM are retained. Wake-up from EM4 Hibernate requires a reset to the system, returning it back to EM0 Active

- · Cortex-M4 is off
- · High frequency clock tree is off
- · Some low frequency clock trees may be active
- · The following oscillators are available
 - · LFRCO, LFXO, ULFRCO
- · The following low frequency peripherals are available
 - · RTCC, CRYOTIMER
- Wake-up to EM0 Active through
 - VMON, EMU temperature sensor, RTCC, CRYOTIMER, reset pin, power on reset, and asynchronous pin interrupt (on GPIO_EM4WUx pins only)
- GPIO pin state may be retained (depending on EMU->EM4CTRL.EM4IORETMODE configuration)
- RTCC memory is retained
- The DC-DC converter can be configured to remain on in Low Power mode.

10.3.1.6 EM4 Shutoff

EM4 Shutoff is the lowest energy mode of the part. There is no retention except for GPIO PAD state. Wake-up from EM4 Shutoff requires a reset to the system, returning it back to EM0 Active

- · Cortex-M4 is off
- · High frequency clock tree is off
- · Low frequency clock tree may be active
- · The following oscillators are available
 - LFRCO, LFXO, ULFRCO
- · The following low frequency peripherals are available
 - CRYOTIMER
- · Wake-up to EM0 Active through
 - CRYOTIMER, reset pin, power on reset, and asynchronous pin interrupt (on GPIO_EM4WUx pins only)
- GPIO pin state may be retained (depending on EMU->EM4CTRL.EM4IORETMODE configuration)
- The DC-DC converter configuration is reset to its default Unconfigured configuration (DC-DC converter disabled and bypass switch is off)

10.3.2 Entering Low Energy Modes

The following sections describe the requirements for entering the various energy modes.

Note: If Voltage scaling is being used to save system energy, it is important to ensure the proper conditions for entry and exit of EM2 Deep Sleep, EM3 Stop or EM4 Hibernate be met. See 10.3.9.2.1 EM2/EM3 Voltage Scaling Guidelines and 10.3.9.3.1 EM4H Voltage Scaling Guidelines for details.

10.3.2.1 Entry Into EM1 Sleep

Energy mode EM1 Sleep is entered when the Cortex-M4 executes the Wait For Interrupt (WFI) or Wait For Event (WFE) instruction while the SLEEPDEEP bit the Cortex-M4 System Control Register is cleared. The MCU can re-enter sleep automatically out of an Interrupt Service Routine (ISR) if the SLEEPONEXIT bit in the Cortex-M4 System Control Register is set. Refer to ARM documentation on entering Sleep modes.

Alternately, EM1 Sleep can be entered from either EM2 Deep Sleep or EM3 Stop from a Peripheral Wake-up Request allowing transfers between the Peripheral and System RAM or Flash. On EFR32, ADC, IDAC, LESENSE, and LEUART peripherals can request this wake-up event. Refer to their respective register specification to enable this option. The system will return back to EM2 DeepSleep or EM3 Stop once the ADC, IDAC, LESENSE, or LEUART have completed its transfers and processing.

During Peripheral Wake-Up Request, additional system resources such as FLASH and other Peripherals can be enabled for access.

10.3.2.2 Entry Into EM2 Deep Sleep or EM3 Stop

Energy mode EM2 Deep Sleep or EM3 Stop may be entered when all of the following conditions are true:

- · Radio RAC state machine is in OFF state
- · IDAC is currently not updating output.
- Cortex-M4 (if present) is in DEEPSLEEP state
- · Flash Program/Erase Inactive
- · DMA done with all current requests
- · A debugger is not currently connected.

Entry into EM2 Deep Sleep and EM3 Stop can be blocked by setting the EMU CTRL->EM2BLOCK bit.

Note: When EM2 Deep Sleep or EM3 Stop entry is blocked, the part is not able to enter a lower energy state. The core will be in a sleep state, similar to EM1, where it is waiting for a proper interrupt of other valid wake-up event. Once the blocking conditions are removed, then the part will automatically enter a lower energy state.

Energy mode EM2 Deep Sleep is entered from EM0 Active when the Cortex-M4 executes the Wait For Interrupt (WFI) or Wait For Event (WFE) instruction while the SLEEPDEEP bit in the Cortex-M4 System Control Register is set. The MCU can re-enter DeepSleep automatically out of an Interrupt Service Routine (ISR) if the SLEEPONEXIT bit in the Cortex-M4 System Control Register is set. Refer to ARM documentation on entering Sleep modes.

Alternately, EM2 Deep Sleep or EM3 Stop is entered from EM1 Sleep upon the completion of a Peripheral Wake-Up Request from the RAC if no EM0 Active wake-up happens in the meantime.

10.3.2.3 Entry Into EM4 Hibernate or EM4 Shutoff

Energy mode EM4 Hibernate and EM4 Shutoff is entered through register access.

Software must ensure no modules are active, such as RAC, when entering EM4 Hibernate/Shutoff. EM4CTRL->EM4STATE field must be configured to select either Hibernate (EM4H) or Shutoff (EM4S) mode prior to entering EM4.

Software may enter EM4 Hibernate/Shutoff from EM0 Active by writing the sequence 2,3,2,3,2,3,2,3,2 to EM4CTRL->EM4ENTRY bit field. If the EM4BLOCK bit in WDOGn_CTRL is set, the CPU will be prevented from entering EM4 Hibernate/Shutoff by software request.

An active debugger connection will prevent entry into EM4 Hibernate/Shutoff.

Note that upon entry into EM4 Shutoff, the DC-DC converter configuration is reset to its default (i.e. Unconfigured) configuration. In the Unconfigured configuration, the DC-DC converter will be disabled and the bypass switch will be turned off.

10.3.3 Exiting a Low Energy Mode

A system in EM2 Deep Sleep and EM3 Stop can be woken up to EM0 Active through regular interrupt requests from active peripherals. Since state and RAM retention is available, the EFR32 is fully restored and can continue to operate as before it went into the Low Energy Mode.

Wake-Up from EM4 Hibernate or EM4 Shutoff is performed through reset. Wake-Up from a specific module must be enabled in that module's EM4WUEN register.

Enabled interrupts that can cause wake-up from a low energy mode are shown in Table 10.3 EMU Wake-Up Triggers from Low Energy Modes on page 220. The wake-up triggers always return the EFR32 to EMO Active/EM1 Sleep. Additionally, any reset source will return to EMO Active. VMON-based EM4 Hibernate wake-ups also set the corresponding rise or fall interrupt flag. These flags serve as the wake-up source for EM4 Hibernate and must be cleared by software on EM4 Hibernate exit. Not doing so will result in an immediate wake-up after next EM4 Hibernate entry.

Table 10.3. EMU Wake-Up Triggers from Low Energy Modes

Peripheral	Wake-Up Trigger	EM2 Deep Sleep	EM3 Stop	EM4 Hiber- nate	EM4 Shut- off
LEUART (Low Energy UART)	Receive / transmit	Yes	_	_	_
LETIMER	Any enabled interrupt	Yes	_	_	_
WDOG	Any enabled interrupt	Yes	Yes	_	_
LESENSE	Any enabled interrupt	Yes	_	_	_
LFXO	Ready Interrupt	Yes	_	_	_
LFRCO	Ready Interrupt	Yes	_	_	_
I ² C	Receive address recognition	Yes	Yes	_	_
ACMP	Any enabled edge interrupt	Yes	Yes	_	_
ADC	SINGLE / SCAN FIFO events, window comparator, and VREF overvoltage	Yes	Yes	_	_
VDAC	Any enabled interrupt except EM23ERRIF	Yes	Yes	_	_
PCNT	Any enabled interrupt	Yes	Yes ¹	_	_
RTCC	Any enabled interrupt	Yes	Yes	Yes ²	
VMON	Rising or falling edge on any monitored power	Yes	Yes	Yes ²	_
EMU Temperature Sensor	Measured temperature outside the defined limits	Yes	Yes	Yes ²	_
CRYOTIMER	Timeout	Yes	Yes	Yes ²	Yes ²
Pin Interrupts	Transition	Yes	Yes	Yes ^{2, 3}	Yes ^{2, 3}
Reset Pin	Assertion	Yes	Yes	Yes	Yes
Power	Cycle Off/On	Yes	Yes	Yes	Yes

Note:

- 1. When using an external clock
- 2. Corresponding bit in the module's EM4WUEN must be set.
- 3. Only available on a subset of the pins. Refer to the data sheet for details.

10.3.4 Power Configurations

The EFR32 allows several power configurations with additional options giving flexible power architecture selection.

In order to provide the lowest power consuming radio solutions, the EFR32 comes with a DC-DC module to power internal circuits. The DC-DC requires an external inductor and capacitor (refer to the data sheet for recommended values).

The EFR32 has multiple internal power domains: IO Supply (IOVDD), Analog & Flash (AVDD), RF Analog Supply (RFVDD), RF Power Amplifier Supply (PAVDD), Input to Digital LDO (DVDD), and Low Voltage Digital Supply (DECOUPLE). Additional detail for each configuration and option is given in the following sections.

When assigning supply sources, the following requirement must be adhered to:

- VREGVDD = AVDD (Must be the highest voltage in the system)
- VREGVDD >= DVDD
- VREGVDD >= PAVDD
- VREGVDD >= RFVDD
- VREGVDD >= IOVDD

10.3.4.1 Power Configuration 0: Unconfigured

Upon power-on reset (POR) or entry into EM4 Shutoff, the system is configured in a safe state that supports all of the available Power Configurations. The Unconfigured Configuration is shown in the simplified diagram below.

In the Unconfigured Configuration:

- The DC-DC converter's Bypass switch is OFF.
- The internal digital LDO is powered from the AVDD pin (i.e. REGPWRSEL=0 in EMU_PWRCTRL). Note the maximum allowable current into the LDO when REGPWRSEL=0 is 20 mA. For this reason, immediately after startup firmware should configure RE-GPWRSEL=1 to power the digital LDO from DVDD.
- The analog blocks are powered from the AVDD supply pin (i.e., ANASW=0 in EMU_PWRCTRL).

After power on, firmware can configure the device to based on the external hardware configuration. Note that the PWRCFG register can only be written once to a valid value and is then locked. This should be done immediately out of boot to select the proper power configuration. The DC-DC and PWRCTRL registers will be locked until the PWRCFG register is configured.




Figure 10.2. Unconfigured Power Configuration

10.3.4.2 Power Configuration 1: No DC-DC

In Power Configuration 1, the DC-DC converter is programmed in Off mode and the Bypass switch is Off. The DVDD pin must be powered externally - typically, DVDD is connected to the main supply. DVDD powers the internal Digital LDO (i.e., REGPWRSEL=1) which powers the digital circuits. IOVDD and AVDD are powered from the main supply as well. RFVDD and PAVDD, which power the radio, are shorted to the main supply as well.

VREGSW must be left disconnected in this configuration.




Figure 10.3. DC-DC Off Power Configuration

10.3.4.3 Power Configuration 2: DC-DC

For the lowest power applications, the DC-DC converter can be used to power the DVDD supply, as well as RFVDD and PAVDD.

In Power Configuration 2, the DC-DC Output (V_{DCDC}) is connected to DVDD. DVDD powers the internal Digital LDO (i.e., RE-GPWRSEL=1) which powers the digital circuits. AVDD is connected to the main supply voltage. The internal analog blocks may be powered from AVDD or DVDD, depending on the ANASW configuration. RFVDD and PAVDD are powered from V_{DCDC} as well.

IOVDD could be connected to either the main supply (as shown below) or to V_{DCDC} , depending on the system IO requirements. Because V_{DCDC} will be unpowered (i.e., floating) at startup, if IOVDD is powered from the DC-DC converter then any circuit attached to IOVDD will not be powered until the DC-DC is configured (or the bypass switch is enabled). Refer to 10.3.8 IOVDD Connection section for further details and issues that may result when connecting IOVDD to V_{DCDC} .




Figure 10.4. DC-DC Standard Power Configuration

As the Main Supply voltage approaches the DC-DC output voltage, it eventually reaches a point where becomes inefficient (or impossible) for the DC-DC module to regulate V_{DCDC} . At this point, firmware can enable bypass mode, which effectively disables the DC-DC and shorts the Main Supply voltage directly to the DC-DC output. If and when sufficient voltage margin on the Main Supply returns, the system can be switched back into DC-DC regulation mode.

An alternate "High RF Power" DC-DC configuration has the external Main Supply connected directly to the PAVDD. This configuration supports a higher transmit power (e.g., >13 dBm) required for some radio protocol specifications. No additional software setting is required for this mode. The following diagram shows an example of connecting PAVDD to the Main Supply while DVDD and RFVDD are connected to the filtered V_{DCDC} .




Figure 10.5. DC-DC High RF Power Configuration

10.3.5 DC-to-DC Interface

The EFR32 devices feature a DC-DC buck converter which requires a single external inductor and a single external capacitor. The converter takes the VREGVDD input voltage and converts it down to an output voltage between VREGVDD and 1.8 V with a peak efficiency of approximately 90% in Low Noise (LN) mode and 85% in Low Power (LP) mode. Refer to the data sheet for full DC-DC specifications.

The DC-DC converter operates in either Low Noise (LN) or Low Power (LP) mode. LN mode is intended for higher current operation (e.g., >= 10 mA), whereas LP mode is intended for very low current operation (e.g., < 10 mA).

In addition, the DC-DC converter supports an unregulated Bypass mode, in which the input voltage is directly shorted to the DC-DC output.

10.3.5.1 Bypass Mode

In Bypass mode, the VREGVDD input voltage is directly shorted to the DC-DC converter output through an internal switch. Consult the data sheet for the Bypass switch impedance specification.

The Bypass Current Limit limits the maximum current drawn from the input supply in Bypass mode. This current limit is enabled by setting the BYPLIMEN bit in the EMU_DCDCCLIMCTRL register, and the limit value may be adjusted between 20 mA and 320 mA using the BYPLIMSEL bitfield in the EMU_DCDCMISCCTRL register. When the difference between the DC-DC output voltage (V_{DCDC}) and the DC-DC input voltage (VREGVDD) is large, applications should enable the Bypass Current Limit before enabling Bypass mode. For example, if Bypass mode is enabled with VREGVDD=3.8 V and V_{DCDC} =1.8 V with a 4.7 μ F capacitor, the peak current draw may be quite large as it is limited only by the bypass switch on-resistance, which could result in drooping on the input supply voltage. For smaller input / output voltage differences (e.g., VREGVDD=2.4 V and V_{DCDC} =1.8 V), it may not be necessary to enable the Bypass Current Limit at all.

Note that the device will see an additional ~10 μ A of current draw when both the Bypass Current Limiter and Bypass Mode are enabled. Applications should therefore disable the Bypass Current Limiter (i.e., set BYPLIMEN = 0) after the DVDD voltage has reached the main supply voltage in Bypass Mode.

10.3.5.2 Low Power (LP) Mode

The Low Power (LP) controller operates in a hysteretic mode to keep the output voltage within a defined voltage band. Once the DC-DC output voltage drops below a programmable internal reference, the LP controller generates a pulse train to control the powertrain PFET switch, which charges up the DC-DC output capacitor. When the output voltage is at the programmed upper level, the powertrain PFET is turned off. The output ripple voltage may be quite large (>100 mV) in LP mode.

The LP controller supports load currents up to approximately 10 mA, making it suitable for light loads in EM0 and EM1, as well as EM2, EM3, or EM4 low energy modes.

10.3.5.3 Low Noise (LN) Mode

The Low Noise (LN) controller continuously switches the powertrain NFET and PFET switches to maintain a constant programmed voltage at the DVDD pin. The LN controller supports load current from sub-mA up to 200 mA.

The LN controller switching frequency is programmable using the RCOBAND bitfield in the EMU_DCDCLNFREQCTRL register. See below for recommended RCOBAND settings for each mode.

The DC-DC Low Noise controller operates in one of two modes:

- 1. Continuous Conduction Mode (CCM)
- 2. Discontinuous Conduction Mode (DCM)

10.3.5.3.1 Low Noise (LN) Continuous Conduction Mode (CCM)

CCM operation is configured by setting the LNFORCECCM bit in the EMU_DCDCMISCCTRL register. CCM can be used to improve the DC-DC converter's output transient response time to quick load current changes, which minimizes voltage transients on the DC-DC output.

Note that all references to CCM in the documentation actually refer to Forced Continuous Conduction Mode (FCCM) - that is, if the LNFORCECCM bit is set and the output load current is very low, the DC-DC will be forced to operated in CCM. In this case, the current through the inductor may be negative and current may flow back into the battery.

CCM is required for radio or Wireless Gecko systems because, unlike DCM, it allows use of the radio's interference minimization features. In CCM, the recommended DC-DC converter switching frequency is 6.4 MHz (RCOBAND = 4). Note that when the radio's interference minimization features are enabled, RCOBAND = 4 corresponds to a DC-DC converter switching frequency of 7 MHz.

10.3.5.3.2 Low Noise (LN) Discontinuous Conduction Mode (DCM)

To enable DCM, the LNFORCECCM bit in EMU_DCDCMISCCTRL must be cleared before entering LN. Typically, this configuration would occur while the part was in Bypass mode. Once DCM is enabled, the DC-DC should operate in DCM at light load currents. However, as the load current increases, the DC-DC will automatically transition into CCM without software intervention.

The advantage of DCM is improved efficiency for light load currents. However, in DCM the DC-DC has poorer dynamic response to changes in load current, leading to potentially larger changes in the regulated output voltage. In addition, DCM increases the potential RF switching interference, because in DCM the DC-DC switching events are load dependent and can no longer be synchronized with radio operation. For these reasons, DCM is not recommended for radio applications or for non-radio applications that expect large instantaneous load current steps. For example, if the DC-DC is in DCM, firmware may need to increment the core clock frequency in small steps to prevent a large sudden load increase.

In DCM, the recommended DC-DC converter switching frequency is 3 MHz (RCOBAND = 0).

10.3.5.4 DC-to-DC Programming Guidelines

Note: Refer to Application Note *AN0948: EFM32 and EFR32 Series 1 Power Configurations and DC-DC* detailed information on programming the DC-DC. Application Notes can be found on the Silicon Labs website (www.silabs.com/32bit-appnotes) or using the [**Application Notes**] tile in Simplicity Studio.

10.3.6 Analog Peripheral Power Selection

The analog peripherals (e.g., ULFRCO, LFRCO, LFXO, HFRCO, AUXHFRCO, VMON, IDAC, ADC) are powered from an internal analog supply domain, VDDX_ANA. VDDX_ANA may be supplied from either the AVDD or DVDD supply pins, depending on the configuration of the ANASW bit in the EMU_PWRCTRL register. Changes to the ANASW setting should be made immediately out of reset (i.e., in the Unconfigured Configuration), before all clocks (with the exception of HFRCO and ULFRCO) are enabled. If the DCDC converter is used and ANASW is set to 1, the switch will not take effect until after the DCDC output voltage has reached its target level. To prevent supply transients, firmware should configure and enable the DCDC, configure ANASW, and then enable clocks. If the DCDC converter is not used, IMMEDIATEPWRSWITCH should be set prior to setting ANASW so hardware can immediately apply the switch without waiting for the DCDC to settle.

Once ANASW is configured it should not be changed. Note that the flash is always powered from the AVDD pin, regardless of the state of the ANASW bit.

Table 10.4. Analog Peripheral Power Configuration

ANASW	Analog Peripheral Power Supply Source (VDDX_ANA)	Comments
0 (default)	AVDD pin	This configuration may provide a quieter supply to the analog modules, but is less efficient as AVDD is typically at a higher voltage than DVDD.
1	DVDD pin	This configuration may provide a noisier supply to the analog modules, but is more efficient. However, because the maximum allowable input voltage to many of the analog modules using APORT is limited to MIN(VDDX_ANA,IOVDD), this setting could artificially limit your analog input range.

10.3.7 Digital LDO Power Selection

The digital LDO may be powered from one of two supply pins, depending on the configuration of the REGPWRSEL bit in the EMU_PWRCTRL register. At startup, the digital is powered from the AVDD pin. When powered from AVDD, the LDO current is limited to 20 mA. Out of startup, firmware should configure and enable the DCDC (if desired) and then set REGPWRSEL=1 before increasing the core clock frequency.

Table 10.5. Digital LDO Power Configuration

REGPWRSEL	Digital LDO Power Source	Comments
0 (default)	AVDD pin	Maximum LDO current in this configuration is 20 mA. Firmware should configure REGPWRSEL to 1 after startup.
1	DVDD pin	This configuration supports all core frequencies, and should be used after startup.

10.3.8 IOVDD Connection

The IOVDD supply(s) must be less than or equal to AVDD. IOVDD will typically be connected to either the DC-DC Output (V_{DCDC}) or the main supply.

Because V_{DCDC} will be unpowered (i.e., floating) at startup, if IOVDD is powered from the DC-DC converter then any circuit attached to IOVDD will not be powered until the DC-DC is configured (or the bypass switch is enabled).

Note: This constraint can have serious and unintended side-effects. For example, if IOVDD=V_{DCDC}:

- 1. It isn't directly possible to program an unprogrammed device on a PCB through the serial wire interface. Programming the device requires IOVDD to be present (i.e., for SWCLK, SWDIO, etc), and IOVDD won't be present until after the part is programmed (i.e., the DC-DC is enabled in firmware to power up V_{DCDC}). It is possible to work around this issue, however, by providing an external supply for V_{DCDC} during programming.
- 2. Some unprogrammed devices are preloaded with a bootloader. The bootloader is expecting to read a logic high on the SWCLK pin to determine if the bootloader should execute. With no valid IOVDD voltage present, the code may incorrectly decide to execute the bootloader, which will cause the system to wait in the bootloader until a reset occurs.

Additionally, upon entry into EM4 Shutoff, the DC-DC converter configuration is reset to its default (Unconfigured) configuration. If $IOVDD = V_{DCDC}$, then any circuits attached to IOVDD will remain unpowered until the system is reset to exit EM4 Shutoff, and the DC-DC is configured (or the bypass switch is enabled).

Any application with powering external loads from the DC-DC converter must take into consideration the maximum allowable DC-DC load current. Refer to the data sheet for DC-DC load current specification.

10.3.9 Voltage Scaling

The voltage scaling feature allows for a tradeoff between power and performance. Voltage scaling applies an adjustment to the supply voltage for the on-chip digital logic and memories. For EM0 and EM1 operation, full device performance is supported when the Voltage Scale Level is set to its highest value. The Voltage Scale Level may be set lower when operating the system at slower clock speeds to save power. Voltage scaling does not affect the input or output range for analog peripherals or digital I/O logic levels. For more information about max system frequency supported for different voltage scaling levels. Refer to the CMU chapter and the data sheet specification tables.

Note: Some device sub-systems and operations are only supported at Voltage Scale Level 2.

- Flash write/erase is only supported at Voltage Scale Level 2.
- HFXO supports only 38-40 MHz crystals and is only supported at Voltage Scale Level 2.
- Radio operation and radio module register access is only supported at Voltage Scale Level 2. When using any other Voltage Scale
 Level access to all radio peripherals is locked out. Thus, firmware may only use Voltage Scale Level 0 during periods when radio
 operations or radio register accesses are not required.

Separate voltage scaling controls are available for the different energy modes. These are as follows:

- EM0/EM1 Voltage Scaling
- EM2/EM3 Voltage Scaling
- EM4H Voltage Scaling

10.3.9.1 EM0/EM1 Voltage Scaling

In energy modes EM0 and EM1, the user can dynamically scale voltages between Voltage Scale Level 2 and Voltage Scale Level 0 using the EM01VSCALE2 and EM01VSCALE0 bitfields in EMU_CMD register. A lower Voltage Scale Level can be used in conjunction with lower processor frequency to reduce power consumption. Once these commands are issued, hardware begins the process of voltage scaling and when done, the VSCALEDONE interrupt is triggered. Users can also poll VSCALEBUSY in EMU_STATUS which indicates that hardware is busy changing the voltage scale setting when set. VSCALE in EMU_STATUS shows the current voltage the system is in at any time.

Note:

- If more than one voltage scaling command is issued in EMU_CMD simultaneously, the lower voltage scaling level has higher priority.
 e.g. priority order: EM01VSCALE0 > EM01VSCALE2.
- The reset value of VSCALE for EM0 and EM1 operation is Voltage Scale Level 2.

When voltage scaling up or down, the user should follow the following sequences in order to ensure proper scaling.

- · Voltage Scale Down
 - 1. Decrease system clock frequency to the target frequency
 - 2. Update the wait states of Flash for the target frequency
 - 3. Issue voltage scaling command by setting EM01VSCALE2 or EM01VSCALE0 in EMU CMD
 - 4. Once Hardware completes voltage scaling up, VSCALEDONE interrupt is set.
- · Voltage Scale Up
 - 1. Issue voltage scaling command by setting EM01VSCALE2 or EM01VSCALE0 in EMU_CMD
 - 2. Wait for hardware to complete voltage scaling. When done, VSCALEDONE interrupt is set.
 - 3. Update the wait states of Flash for the target frequency
 - 4. Increase system clock frequency to the target frequency

Multiple voltage scaling commands are allowed to be issued even when the current voltage scaling is not yet completed. In such a case, the current scaling will be aborted and the last command will be executed. VSCALEDONE interrupt will be issued for every voltage scaling command.

Note: When a hard reset occurs, VSCALE will be set to the reset value (Voltage Scale Level 2). In most cases, a soft reset will not affect the current VSCALE level. However, when a soft reset is issued in the middle of the voltage scaling process, the minimum voltage scale level indicated by VSCALE or the EMU_CMD which triggered the voltage scale operation will be applied and reflected in VSCALE.

10.3.9.2 EM2/EM3 Voltage Scaling

The EM23VSCALE bitfield in EMU_CTRL allows user to independently setup the voltage scaling value for EM2/EM3 energy mode. The EM23VSCALE in EMU_CTRL should be programmed to a level which is less than or equal to VSCALE in EMU_STATUS. This means that EM2/EM3 voltage scaling is always a voltage scaling down process. If EM23VSCALE level in EMU_CTRL is greater than VSCALE level in EMU_STATUS, the VSCALE level will be implemented in EM2/EM3 instead of EM23VSCALE. Upon EM2/EM3 entry, the system will scale down the voltage to a smaller level between VSCALE or EM23VSCALE.

Note: The reset value of EM23VSCALE is Voltage Scale Level 2. Therefore, if user scales EM0/EM1 voltage to Voltage Scale Level 0 (reflected in VSCALE in EMU_STATUS) and enters EM2/EM3, this VSCALE voltage of Voltage Scale Level 0 is maintained in EM2/EM3 as well since this is smaller level between VSCALE and EM23VSCALE.

10.3.9.2.1 EM2/EM3 Voltage Scaling Guidelines

Note that when using EM23VSCALE in EMU_CTRL to scale down EM2/EM3, the scaled down voltage in EM2/EM3 is maintained after waking from EM2/EM3 to EM0/EM1. For example, if VSCALE was at Voltage Scale Level 2 prior to EM2/EM3 entry, and EM23VSCALE was set to Voltage Scale Level 0, the system will scale down to Voltage Scale Level 0 on EM2/EM3 entry. When waking up to EM0/EM1, the system maintains its voltage at Voltage Scale Level 0. Therefore, user must ensure the system clock frequency and Flash wait states are programmed to correct values to support waking up to EM0/EM1 at the lower voltages prior to EM2/EM3 entry.

EM23VSCALEAUTOWSEN bitfield in EMU_CTRL enables hardware to automatically configure the system clock frequency and Flash wait states to support low voltage operation when waking up to EM0/EM1 from EM2/EM3. Therefore, this obviates the need for user to setup the clock frequency and Flash wait states prior to EM2/EM3 entry with EM23VSCALE. When waking up to EM0/EM1, while using EM23VSCALEAUTOWSEN set to 1, the HFRCO will default to its production calibrated 19 MHz frequency.

10.3.9.3 EM4H Voltage Scaling

EM4HVSCALE bitfield in EMU_CTRL allows user to independently setup the voltage scaling levels for EM4H energy mode. The EM4HVSCALE in EMU_CTRL should be programmed to a level which is smaller than or equal to VSCALE level in EMU_STATUS or EM23VSCALE in EMU_CTRL. This means that EM4H voltage scaling is always a voltage scaling down process. If EM4HVSCALE level in EMU_CTRL is greater than level of VSCALE in EMU_STATUS or level of EM23VSCALE in EMU_CTRL, the smaller of VSCALE, EM23VSCALE or EM4HVSCALE levels will be implemented in EM4H.

Note: The reset level of EM4HVSCALE is Voltage Scale Level 2. Therefore, if user scales EM0/EM1 voltage to Voltage Scale Level 0 (reflected in VSCALE in EMU_STATUS) and enters EM4H, this VSCALE voltage of Voltage Scale Level 0 is maintained in EM2/EM3 as well since this is minimum of VSCALE and EM23VSCALE.

10.3.9.3.1 EM4H Voltage Scaling Guidelines

Note that when using EM4HVSCALE in EMU_CTRL to scale down voltage in EM4H, the scaled down voltage in EM4H is maintained after waking from EM4H to EM0/EM1. For example prior to EM4H entry, if VSCALE was at Voltage Scale Level 2 and EM4HVSCALE was set to Voltage Scale Level 0, the system will scale down to Voltage Scale Level 0 on EM4H entry. When waking up to EM0/EM1, the system maintains its voltage at Voltage Scale Level 0.

10.3.9.4 Voltage Scaling Recommended Use

Refer to the data sheet for the maximum supported system frequencies for different Voltage Scaling Levels. Use of the lowest voltage scaling level is recommended for maximum power savings. For any voltage scaling level, it is recommend to use the highest frequency for performance benefits.

Voltage can then be scaled to higher voltage scale levels only when higher system clock frequency is required by the application for a period of time after which user can dynamically scale the voltage back to lower voltage scale levels to continue saving power.

10.3.10 EM2/EM3 Peripheral Retention Disable

Peripherals that are available in EM2 Deep Sleep or EM3 Stop can optionally be powered down during EM2 Deep Sleep or EM3 Stop. This allows lower energy consumption in these energy modes. However, when powering down, these peripherals are independently reset so the registers lose their configuration values. Therefore, they will have to be reconfigured upon wake-up to EM0 Active if they were previously configured to non reset values.

EMU_EM23PERNORETAINCTRL register can be used to setup unused peripherals for powering down prior to EM2/EM3 entry. Once setup, upon EM2/EM3 entry, all peripherals in the power-down domain will get powered down if all of them are setup to be disabled.

Note: User must ensure that the peripherals being powered down should have their clocks disabled in CMU prior to EM2/EM3 entry.

On waking up from EM2/EM3, EMU_EM23PERNORETAINSTATUS register indicates if the peripherals were powered down by the system and subsequently locked out from register access. Locking out peripherals prevents users from accidentally using peripherals with configurations at their reset state. EMU_EM23PERNORETAINCMD allows user to unlock these peripherals and hence grant access to their registers for updating their configurations.

10.3.11 Brown Out Detector (BOD)

The EFR32 contains multiple supply brown out detectors (BODs).

10.3.11.1 AVDD BOD

The EFR32 has a fast response BOD on AVDD that is always active. This BOD ensures the minimal supply is provided to the AVDD supply (typically also connected to VREGVDD). Once triggered, the BOD will cause the system to reset.

Note: In EM4 Hibernate/Shutoff a low power version of the AVDD BOD, called EM4BOD, is available to trigger a reset at level lower than in other energy modes. All other BODs are disabled during EM4 Hibernate/Shutoff

10.3.11.2 DVDD and DECOUPLE BOD

Additional BODs will monitor DVDD and DECOUPLE during EM0 Active through EM3 Stop. This can cause a reset to the internal logic, but will not cause a power-on reset or reset the EMU or RTCC.

10.3.12 Voltage Monitor (VMON)

The EFR32 features an extremely low energy Voltage Monitor (VMON) capable of running down to EM4 Hibernate. Trigger points are preloaded but may be reconfigured.

- AVDD X 2
- DVDD
- IOVDD0

Table 10.6. VMON Events

Feature	Condition	AVDD	DVDD	IOVDD
Hysteresis (separate rise and fall triggers)	_	Yes	_	_
Interrupt	Fall or Rise	Yes	Yes	Yes
Wake-Up from EM4 Hibernate	Fall or Rise	Yes	Yes	Yes

The status of the VMON is reflected in the EMU STATUS register.

The status of the sticky interrupt can be found at EMU_IF. These interrupt flags also serve as the wake-up source of EM4H when the associated RISEWU and FALLWU bits are set. This means that if these flags are set, EM4H entry will result in an immediate wake-up. To prevent this, these must be cleared by software before EM4H entry.

Note that the VMON has offset high hysteresis, specified in the device Data Sheet. For rising edge detection the threshold will be the threshold setting (as described below) + V_{VMON HST}, and for falling edge detection the threshold will simply be the threshold setting.

VMON channels are calibrated at two voltages: 1.86 V and 2.98 V. The calibration results (coarse thresholds and fine thresholds for 1.86 V and 2.98 V) are placed in the VMONCAL registers in the DI page. Using these thresholds it is possible to calculate thresholds for the entire supported VMON VDD range, i.e., 1.62 V to 3.4 V. Using the values given in VMONCAL registers, one can calculate $T_{1.86}$, $T_{2.98}$, V_a and V_b .

$$\begin{split} T_{1.86} = & (10 \text{ x VMONCALX_XVDD1V86THRESCOARSE}) + \text{VMONCALX_XVDD1V86THRESFINE}, \\ T_{2.98} = & (10 \text{ x VMONCALX_XVDD2V98THRESCOARSE}) + \text{VMONCALX_XVDD2V98THRESFINE}, \\ V_a = & (1.12) / (T_{2.98} - T_{1.86}), \\ V_b = & 1.86 - (V_a \text{ x T}_{1.86}), \end{split}$$

Figure 10.6. VMON Calibration Equations

Now if it is required to find the coarse and fine thresholds for a certain voltage Y, following equation can be used:

Thres_Y =
$$(Y - V_b) / V_a$$
,
 Y_{calib} = $(Thres_Y \times V_a) + V_b$,

Figure 10.7. VMON Threshold Equations

Thres $_{Y}$ should be rounded to the nearest integer. The least significant digit of the rounded Thres $_{Y}$ gives the fine threshold and remaining digits give the coarse threshold for Y. These can now be programmed in the relevant EMU_VMONXVDDCTRL register as the coarse and fine thresholds. It may not be possible to set threshold exactly for Y. In that case the closest possible voltage is used. Y_{calib} gives the value of this closest possible voltage.

Consider the example where it is required to set the AVDD rise threshold to 2.2 V (so Y=2.2 V). This means that the EMU_VMO-NAVDDCTRL_RISETHRESCOARSE and EMU_VMONAVDDCTRL_RISETHRESFINE need to be programmed. Here are the steps that should be followed:

- Check VMONCAL0 register. It has the VMON AVDD channel calibrated thresholds for 1.86 V and 2.98 V. Lets assume that the following values are present in the associated bitfields:
 - AVDD1V86THRESCOARSE = 3
 - AVDD1V86THRESFINE = 5
 - AVDD2V98THRESCOARSE = 8
 - AVDD2V98THRESFINE = 7

- $T_{1.86} = 35$
- $T_{2.98} = 87$
- $V_a = 21.53 \text{ mV}$
- $V_b = 1.106 V$
- Using the VMON threshold equations (with Y=2.2 V), Thres_Y = 51 (rounded from 50.8) and Y_{calib} = 2.204 V

EMU_VMONAVDDCTRL_RISETHRESCOARSE should be programmed to 5 and EMU_VMONAVDDCTRL_RISETHRESFINE should be programmed to 1 (since Thres $_{\rm Y}$ = 51). With these programmed values, VMON AVDD rise threshold is set for Y_{calib} = 2.204 V, which is the closest programmable threshold.

10.3.13 Powering Off SRAM Blocks

SRAM blocks may be powered off using the EMU_RAMxCTRL RAMPOWERDOWN fields. Selected blocks are powered down in order from the highest to lowest address in each bank. The lowest SRAM block in RAM0 cannot be powered off and will always remain powered on for proper system functionality. The stack must be located in retained memory. Refer to the EMU_RAMxCTRL register descriptions for power configuration options and the associated address ranges.

10.3.14 Temperature Sensor

EMU provides low energy periodic temperature measurement. A temperature measurement is taken every 250 ms, with the 8-bit result stored in EMU->TEMP register.

Note: The EMU temperature sensor is always running (except in EM4 Shutoff) and is independent from the ADC temperature sensor.

The EMU provides the following features around temperature changes

- · Wake-Up from EM4 Hibernate on Temperature Change
- · Interrupt from High Level Trip
- · Interrupt from Low Level Trip

During production test, the EMU temperature sensor for each device is calibrated at room temperature, with the corresponding calibration temperature and reading stored off in the DI page as follows:

- DEVINFO->CAL.TEMP: This bitfield contains the temperature in degrees C at calibration
- DEVINFO->EMUTEMP: This register contains the EMU->TEMP reading at the calibration temperature stored in DEVINFO->CAL.TEMP

The current calibrated EMU temperature sensor result from EMU->TEMP may be converted to degrees C using the following equation:

Figure 10.8. Temperature Calculation

TEMPCO_{EMxx} is a temperature coefficient that varies based on the energy mode at the time of the EMU temperature sensor reading:

- TEMPCO_{EM01} = 0.278 + (DEVINFO->EMUTEMP) / 100
- TEMPCO_{EM234} = 0.268 + (DEVINFO->EMUTEMP) / 100

For maximum accuracy when using the high/low level temperature interrupts, firmware should ensure that TEMPCO_{EM234} is used to set the temperature thresholds in EMU->TEMPLIMITS before entering EM2/3/4. Similarly, when exiting EM2/3/4, the temperature thresholds should be updated using TEMPCO_{EM01}.

Note that an increasing reading in EMU->TEMP corresponds to a decreasing temperature, and vice-versa. If enabled, the TEMPHIGH High Level Limit in EMU-> TEMPLIMITS causes an interrupt flag on a increasing EMU->TEMP reading (i.e., decreasing temperature). Similarly, the TEMPLOW Low Level Limit causes a interrupt flag on a decreasing EMU->TEMP reading (i.e., increasing temperature).

The EMU temperature sensor accuracy is approximately ±10°C over most of the useable temperature range, but may be +15°C at higher temperatures. Accordingly, any use of the EMU temperature sensor should include margin to account for that accuracy.

10.3.15 Registers latched in EM4

The following registers will be latched when entering EM4. After wake-up from EM4, these registers will be reset and require reprogramming prior to writing the EMU_CMD_EM4UNLATCH command.

- CMU LFRCOCTRL
- CMU_LFXOCTRL
- CMU_LFECLKSEL
- CMU_LFECLKEN0
- CMU_LFEPRESC0

10.3.16 Register Resets

Each EMU register requires retaining state in various energy modes and power transitions and will consequently need to be reset with a different condition. The following reset conditions will apply to the appropriate set of registers as marked in the Register Description table.

- · Reset with POR or Hard Pin Reset
- · Reset with POR, Hard Pin Reset, or any BOD reset
- Reset with SYSEXTENDEDRESETn
- · Reset with FULLRESETn (default)

If a register field is not marked with a specific reset condition then it is assumed to be reset with FULLRESETn.

10.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	EMU_CTRL	RW	Control Register
0x004	EMU_STATUS	R	Status Register
0x008	EMU_LOCK	RWH	Configuration Lock Register
0x00C	EMU_RAM0CTRL	RW	Memory Control Register
0x010	EMU_CMD	W1	Command Register
0x018	EMU_EM4CTRL	RW	EM4 Control Register
0x01C	EMU_TEMPLIMITS	RW	Temperature Limits for Interrupt Generation
0x020	EMU_TEMP	R	Value of Last Temperature Measurement
0x024	EMU_IF	R	Interrupt Flag Register
0x028	EMU_IFS	W1	Interrupt Flag Set Register
0x02C	EMU_IFC	(R)W1	Interrupt Flag Clear Register
0x030	EMU_IEN	RW	Interrupt Enable Register
0x034	EMU_PWRLOCK	RW	Regulator and Supply Lock Register
0x03C	EMU_PWRCTRL	RW	Power Control Register
0x040	EMU_DCDCCTRL	RW	DCDC Control
0x04C	EMU_DCDCMISCCTRL	RW	DCDC Miscellaneous Control Register
0x050	EMU_DCDCZDETCTRL	RW	DCDC Power Train NFET Zero Current Detector Control Register
0x054	EMU_DCDCCLIMCTRL	RW	DCDC Power Train PFET Current Limiter Control Register
0x058	EMU_DCDCLNCOMPCTRL	RW	DCDC Low Noise Compensator Control Register
0x05C	EMU_DCDCLNVCTRL	RWH	DCDC Low Noise Voltage Register
0x064	EMU_DCDCLPVCTRL	RW	DCDC Low Power Voltage Register
0x06C	EMU_DCDCLPCTRL	RW	DCDC Low Power Control Register
0x070	EMU_DCDCLNFREQCTRL	RW	DCDC Low Noise Controller Frequency Control
0x078	EMU_DCDCSYNC	R	DCDC Read Status Register
0x090	EMU_VMONAVDDCTRL	RW	VMON AVDD Channel Control
0x094	EMU_VMONALTAVDDCTRL	RW	Alternate VMON AVDD Channel Control
0x098	EMU_VMONDVDDCTRL	RW	VMON DVDD Channel Control
0x09C	EMU_VMONIO0CTRL	RW	VMON IOVDD0 Channel Control
0x0B4	EMU_RAM1CTRL	RW	Memory Control Register
0x0B8	EMU_RAM2CTRL	RW	Memory Control Register
0x0EC	EMU_DCDCLPEM01CFG	RW	Configuration Bits for Low Power Mode to Be Applied During EM01, This Field is Only Relevant If LP Mode is Used in EM01
0x100	EMU_EM23PERNORETAINCMD	W1	Clears Corresponding Bits in EM23PERNORETAINSTATUS Unlocking Access to Peripheral
0x104	EMU_EM23PERNORETAINSTATUS	R	Status Indicating If Peripherals Were Powered Down in EM23, Subsequently Locking Access to It

Offset	Name	Туре	Description
0x108	EMU EM23PERNORETAINCTRI	RW	When Set Corresponding Peripherals May Get Powered Down in FM23

10.5 Register Description

Offset					Bit F	Positi	on												
0x000	30 39 29 27 27	25 25 24 23	2 2 2 2	8 8	17	5 5	4	<u>5</u> 5	7	9	6	_∞	7	9	2	4	3	7	_
Reset					0x0			,			OXO	2				0	0	0	0
Access					Z S						8					RW	RW	₩ N	Z.
Name					EM4HVSCALE						EM23VSCALE					EM23VSCALEAUTOWSEN	EM01LD	EM2BODDIS	EM2BLOCK
Bit	Name	Reset	Access	Des	criptic	on													
31:18	Reserved	To ensure c	ompatibility (with fu	ture de	evices	s, alw	ays w	rite l	bits t	to 0.	Mor	e inf	orm	atio	n in	1.2	Cor	ıveı
17:16	EM4HVSCALE	0x0	RW	EM4	H Vol	tage \$	Scale)											
	Set EM4H voltage. than that of VSCAL		vill trigger vo	ltage s	scaling	to th	is vol	tage i	f volt	tage	scal	e le	vel ir	n EN	Л4⊢	IVS	CAL	E is	les
	Value	Mode		Desc	cription	า													
	0	VSCALE2		Volta	age So	cale Le	evel 2	2											
	2	VSCALE0		Volta	age So	ale L	evel ()											
	3	RESV		RES	SV.														
15:10	Reserved	To ensure c	ompatibility v	with fu	ture de	evices	s, alw	ays w	rite l	bits t	to 0.	Mor	e inf	orm	atio	n in	1.2	Cor	ıveı
			RW		3 Volt														

Value	Mode	Description
0	VSCALE2	Voltage Scale Level 2
2	VSCALE0	Voltage Scale Level 0
3	RESV	RESV
<u> </u>		<u> </u>

7:5 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions

4 EM23VSCALEAU- 0 RW Automatically Configures Flash and Frequency to Wakeup From

With voltage scaling on EM2/3 entry, wakeup to EM0/1 will be at the same voltage as EM2. When this bit is set the Flash wait states and CMU clock frequency are automatically configured to safe value without needing software to configure it prior to EM2/3 entry.

EM2 or EM3 at Low Voltage

TOWSEN

Bit	Name	Reset	Access	Description
3	EM01LD	0	RW	Reserved for internal use. Do not change.
	Reserved for intern	al use. Do not c	hange.	
2	EM2BODDIS	0	RW	Disable BOD in EM2
	This bit is used to d	lisable BODs to	minimize cur	rent in EM2. Reset with POR or Hard Pin Reset
1	EM2BLOCK	0	RW	Energy Mode 2 Block
	This bit is used to p	revent the MCU	from enterin	g Energy Mode 2 or 3.
0	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

10.5.2 EMU_STATUS - Status Register

10.3.2					.cgi	J.61																									
Offset													Bi	it Po	ositi	on															
0x004	30	59	28	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	∞	7	9	2	4	က	2	_	0	
Reset				0	0					0		0	2	2								0				0	0	0	0	0	
Access				2	22					~		~	٥	צ								22				22	~	~	22	22	
Name				TEMPACTIVE	RACACTIVE					EM4IORET		VSCALEBUSY	H - V - O - O - O - O - O - O - O - O - O	VSCALE								VMONFVDD				VMONIO0	VMONDVDD	VMONALTAVDD	VMONAVDD	VMONRDY	
Bit	Name				Re	set			Ac	ces	s I	Des	crip	tion	1																
31:27	Reserv	/ed			To tion		ure	con	npati	bilit <u>.</u>	y wi	th fu	ture	de	vices	s, al	wa)	/S W	rite l	bits	to 0.	Мо	re ii	nfor	mati	on ir	1.2	? Co	nvei	n-	
26	TEMP	ACTI	VE		0				R			Tem	per	atuı	re M	leas	ure	eme	nt A	ctiv	е										
	This si	gnal	is set o	durin	g El	MU ⁻	Tem	pera	ature	e me	eası	urem	ent																		
25	RACA	CTIV	E		0				R			Rad	io C	ont	roll	er A	ctiv	ve													
	This bit indicates the status of the RAC state machine. System can not enter EM2 or lower if set. Value Description																														
	·																														
	0) RAC															RAC is in OFF state														
	0 RAC is in OFF state 1 RAC is not in OFF state															_															
24:21	Reserv	/ed			To tion		ure	con	npati	bilit _.	y wi	th fu	ture	e de i	vices	s, al	wa)	/S W	rite l	bits	to 0.	Мо	re ii	nfor	mati	on ir	1.2	? Co	nvei	n-	
20	EM4IC	RET			0				R			IO R	ete	ntio	n St	tatu	s														
	The sta																			E ir	ı EM	1U_I	EM4	ICT	RL.	Clea	red	by s	ettir	ng	
	Value				Мо	de						Des	cript	tion																_	
	0				DIS	SAB	LEC)				IO re	eten	tion	is d	isat	oled													_	
	1				EN	ABL	.ED					IO re	eten	tion	is e	nble	ed.														
19	Reserv	/ed			To tion		ure	con	npati	bilit _.	y wi	th fu	ture	de	vices	s, al	wa)	/S W	rite l	bits	to 0.	Мо	re ii	nfor	mati	on ir	1.2	? Co	nvei	n-	
18	VSCAI	EBL	JSY		0				R		,	Sys	tem	is E	Busy	y Sc	aliı	ng V	'olta	ge											
	Indicat ter whi																					/101\	VSC	AL	E2 ir	i EM	IU_C	CME	reg	jis-	
17:16	VSCAL	_E			0x0)			R			Cur	rent	: Vo	ltag	e So	cale	Va	lue												
	This shexit	าดพร	the cu	rren	t sys	stem	vol	tage	e val	ue.	This	s get	s up	odat	ed a	fter	VS	CAL	ED(ONE	inte	errup	ot or	on	EM	23 e	xit o	r EN	/4H		
	Value				Мо	de						Des	cript	tion																_	
	0				VS	CAL	E2				,	Volt	age	Sca	ıle L	eve	12													_	
	2				VS	CAL	E0				,	Volt	age	Sca	le L	eve	Ι 0														

Bit	Name	Reset	Access	Description
	3	RESV		RESV
15:9	Reserved	To ensure comp	atibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8	VMONFVDD	0 F	R	VMON VDDFLASH Channel
	Indicates the status	of the VDDFLASH of	channel o	of the VMON.
7:5	Reserved	To ensure comp tions	atibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	VMONIO0	0 F	R	VMON IOVDD0 Channel
	Indicates the status	of the IOVDD0 char	nnel of th	ne VMON.
3	VMONDVDD	0 F	R	VMON DVDD Channel
	Indicates the status	of the DVDD chann	el of the	VMON.
2	VMONALTAVDD	0 F	R	Alternate VMON AVDD Channel
	Indicates the status	of the Alternate AVI	DD chan	nel of the VMON.
1	VMONAVDD	0 F	R	VMON AVDD Channel
	Indicates the status	of the AVDD channe	el of the	VMON.
0	VMONRDY	0 F	R	VMON Ready
	VMON status. Wher of the enabled chan	•	ites that	all the enabled channels are ready. When low, it indicates that one or more

10.5.3 EMU_LOCK - Configuration Lock Register

Offset	Bit Positio															Position																
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	2	_	0
Reset			1		1		1	ı	1	1	•	1		•		1		1	ı		'		'		nnnnxn	,		ı			1	
Access																									I A Y							
Name																								\L\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LOCKNEY							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock Kev

Write any other value than the unlock code to lock all EMU registers, except the interrupt registers and regulator control registers, from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	EMU registers are unlocked
LOCKED	1	EMU registers are locked
Write Operation		
LOCK	0	Lock EMU registers
UNLOCK	0xADE8	Unlock EMU registers

10.5.4 EMU_RAM0CTRL - Memory Control Register

Offset															Bi	t Po	ositi	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	ဝ	∞	7	9	2	4	က	2	_	0
Reset				•						•				•			•		•			•				•		•				
Access																																
Name																																

Bit	Name	Reset Access Description
31:0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions

10.5.5 EMU_CMD - Command Register

Offset															Bi	t Po	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset			•		'							•		•	'	'	•						•			0		0				0
Access																										×		W W				M
Name																										EM01VSCALE2		EM01VSCALE0				EM4UNLATCH

Bit	Name	Reset	Access	Description
31:7	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
6	EM01VSCALE2	0	W1	EM01 Voltage Scale Command to Scale to Voltage Scale Level 2
	Start EM01 voltage s 2 followed by an VS			vel 2. Write to this register will trigger voltage scaling to Voltage Scale Level
5	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
4	EM01VSCALE0	0	W1	EM01 Voltage Scale Command to Scale to Voltage Scale Level 0
	Start EM01 voltage s 0 followed by an VS			vel 0. Write to this register will trigger voltage scaling to Voltage Scale Level
3:1	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EM4UNLATCH	0	W1	EM4 Unlatch
	wakeup, these regist tion from EM4 to EM	ers will be reset 10, the unlatch o	and can hacommand s	latched in order to maintain constant functionality throughout EM4. Upon ave contradictory values to the latched values. To ensure a seamless transihould be given after properly reconfiguring these latched registers. The uncondition but is only needed after EM4 wakeup.

10.5.6 EMU_EM4CTRL - EM4 Control Register

Name Reset Access Description	RW 0
Reset	RW 0
Name Name Reset Access Description Reset Access Description	RW S
Name EM4 OPE PROPERTY PRO	
Bit Name Reset Access Description	EM4STATE
*	
31:18 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convitions	∍n-
17:16 EM4ENTRY 0x0 W1 Energy Mode 4 Entry	
This register is used to enter the Energy Mode 4 sequence. Writing the sequence 2,3,2,3,2,3,2,3,2 will enter the part in Energy Mode 4.	0
15:6 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convitions	∍n-
5:4 EM4IORETMODE 0x0 RW EM4 IO Retention Disable	
Determine when IO retention will be applied and removed.	
Value Mode Description	
0 DISABLE No Retention: Pads enter reset state when entering EM4	
1 EM4EXIT Retention through EM4: Pads enter reset state when exiting EM4	
2 SWUNLATCH Retention through EM4 and Wakeup: software writes UNLATCH register to remove retention	i -
3 RETAINULFRCO 0 RW ULFRCO Retain During EM4S	
Retain the ULFRCO upon EM4S entry. If set to 1, an already running ULFRCO will be retained in its running state in El ULFRCO will always be retained if EM4STATE is in EM4H.	<i>1</i> 4.
2 RETAINLFXO 0 RW LFXO Retain During EM4	
Retain the LFXO upon EM4(SH/H) entry. If set to 1, an already running LFXO will be retained in its running state in EM	1.
1 RETAINLFRCO 0 RW LFRCO Retain During EM4	
Retain the LFRCO upon EM4(S/H) entry. If set to 1, an already running LFRCO will be retained in its running state in E	VI4.
0 EM4STATE 0 RW Energy Mode 4 State	
When set, the system will enter Hibernate state (EM4H) when entering EM4. In EM4H, the regulator will be on in redu mode allowing for RTCC. Otherwise, when entering in EM4, the regulator will be disabled allowing for lowest power mc Shutoff state (EM4S). Only reset with POR or Hard Pin Reset	
Value Mode Description	
0 EM4S EM4S Shutoff state	

10.5.7 EMU_TEMPLIMITS - Temperature Limits for Interrupt Generation

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Reset	0 X0																															
Access																																
Name																EM4WUEN												Č				

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
16	EM4WUEN	0	RW	Enable EM4 Wakeup Due to Low/high Temperature
	Enable EM4 wakeu	p from low or hig	ıh temperatı	ure from EM4H
15:8	TEMPHIGH	0xFF	RW	Temperature High Limit
		d during a tempe	•	riodic temperature measurement is equal to or higher than this value. If the surement (TEMPACTIVE=1), the limit update will be delayed until the end of
7:0	TEMPLOW	0x00	RW	Temperature Low Limit

The TEMPLOW interrupt flag is set when a periodic temperature measurement is equal to or lower than this value. If the low limit is changed during a temperature measurement (TEMPACTIVE=1), the limit update will be delayed until the end of the temperature measurement.

10.5.8 EMU_TEMP - Value of Last Temperature Measurement

Offset															Bi	t Pc	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																						>>>	\									
Access																												Δ	۷			
Name																												TEMD	L 2 1			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TEMP	0xXX	R	Temperature Measurement

Value of last periodic temperature measurement. Value is asynchronously updated. Value is stable for 250 ms after a temperature-based interrupt (TEMPHIGH, TEMPLOW, or TEMP) and can be read with a single read operation. If register is read not in response to a temperature-based interrupt, multiple readings should be taken until two consecutive values are the same.

10.5.9 EMU_IF - Interrupt Flag Register

Offset															Bi	t Po	sitio	on														
0x024	31	30	59	7 28	7 2	7 7	52	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	- ω	_	9	2	4	က	2	_	0
Reset	0	0	0				5	0				0	0	0	0	0	0	0							0	0	0	0	0	0	0	0
Access	2	22	~				r	22				22	22	22	22	22	~	2							2	22	~	22	22	~	~	~
Name	TEMPHIGH	TEMPLOW	TEMP				VSCALEDONE	EM23WAKEUP				DCDCINBYPASS	DCDCLNRUNNING	DCDCLPRUNNING	NFETOVERCURRENTLIMIT	PFETOVERCURRENTLIMIT	VMONFVDDRISE	VMONFVDDFALL							VMONIOORISE	VMONIO0FALL	VMONDVDDRISE	VMONDVDDFALL	VMONALTAVDDRISE	VMONALTAVDDFALL	VMONAVDDRISE	VMONAVDDFALL
Bit	Na	me				F	Res	et			Ac	ces	s I	Des	crip	tion																
31	TE	MP	HIGH	4		C)				R		•	Tem	per	atuı	e H	igh	Lim	it R	Reac	hec	l									
	Se	t wh	en t	he val	ue o	f a	per	riod	ic te	mpe	eratı	ure i	mea	sure	eme	nt is	higl	her	or e	qua	ıl tha	an T	EM	PHI	GH ir	ı EN	/IU_	TEM	1PLI	MIT	S	
30	TE	MPL	_OW	1		C)				R			Tem	per	atuı	e Lo	ow I	Limi	it R	eac	hed										
		Set when the value of a periodic temperature measurement is lower or equal than TEMPHIGH in EMU_TEMPLIMITS TEMP 0 R New Temperature Measurement Valid															3															
29																																
20.06				a new	perio													1				h:4-	4- 0		!	. 	4:	:	. 1 0			_
28:26	Re	serv	'ea				ion		ure (com	ıpatı	DIIIT	y Wii	ın tu	ture	aeı	vices	s, an	way.	S W	rite	DITS	το υ	. IVIC	re in	itorn	natio	on in	17.2	Col	nver	7-
25	VS	CAL	.ED	ONE		C)				R		•	Volt	age	Sca	ale S	Step	s D	one	e IR	Q										
	clo	ck fr	equ	wher ency g of E	after	this	s in	terr	upt.	For	vol	tage	do	wng	rade	e, th	is wi	ill in	dica	te t	hat	hard	lwa	re ha	as fir	ishe	ed a	ll the				
24	EM	123V	VAK	EUP		C)				R		1	Wak	eup	IR	Q Fr	om	EM	2 aı	nd E	МЗ										
				when the s													nis ir	nterr	upt	car	be	use	d to	run	initia	aliza	tion	cod	le ne	ed t	to	
23:21	Re	serv	red				To e		ure (com	pati	bilit	y wi	th fu	ture	dev	vices	s, alı	way.	S W	rite	bits	to C). Мс	re in	forn	natio	on in	1.2	Col	nver	7-
20	DC	DCI	NΒ	YPAS	S	C)				R		I	DCE)C is	s in	Вур	ass	•													
				bypa																												
19				UNNI							R						Rui		•													
40				set o				DC	reg	ulat		as s																				
18				UNNI set o		C ha		יחי	rec	ulat	R or h	20.0					Rur		•													
17	NF		VE	RCUF		C			reg	uiai	R	as 3					ent L			t												
	Re	serv	ed f	or inte	ernal	use	e.																									

Bit	Name	Reset	Access	Description
16	PFETOVERCUR- RENTLIMIT	0	R	PFET Current Limit Hit
	Reserved for internal	use.		
15	VMONFVDDRISE	0	R	VMON VDDFLASH Channel Rise
	A rising edge on VM	ON VDDFLASH	channel ha	as been detected.
14	VMONFVDDFALL	0	R	VMON VDDFLASH Channel Fall
	A falling edge on VM	ON VDDFLASH	channel ha	as been detected.
13:8	Reserved	To ensure cor	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7	VMONIO0RISE	0	R	VMON IOVDD0 Channel Rise
	A rising edge on VM	ON IOVDD0 cha	nnel has be	een detected.
6	VMONIO0FALL	0	R	VMON IOVDD0 Channel Fall
	A falling edge on VM	ON IOVDD0 cha	nnel has b	een detected.
5	VMONDVDDRISE	0	R	VMON DVDD Channel Rise
	A rising edge on VM	ON DVDD chann	el has bee	en detected.
4	VMONDVDDFALL	0	R	VMON DVDD Channel Fall
	A falling edge on VM	ON DVDD chanr	nel has bee	en detected.
3	VMONALTAVDD- RISE	0	R	Alternate VMON AVDD Channel Rise
	A rising edge on Alte	rnate VMON AV	DD channe	el has been detected.
2	VMONALTAVDD- FALL	0	R	Alternate VMON AVDD Channel Fall
	A falling edge on Alte	ernate VMON AV	DD chann	el has been detected.
1	VMONAVDDRISE	0	R	VMON AVDD Channel Rise
	A rising edge on VM	ON AVDD chann	el has bee	n detected.
0	VMONAVDDFALL	0	R	VMON AVDD Channel Fall
	A falling edge on VM	ON AVDD chanr	nel has bee	en detected.

10.5.10 EMU_IFS - Interrupt Flag Set Register

Offset															Βi	t De	siti	on.															
						(0	10	_		0.1						I	T			0.1	1_			T		Ŧ							
0x028	3	30	29	28	27	56	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	2 0	ກ o	7 0	. (٥	2	4	က	7	_	0
Reset	0	0	0				0	0				0	0	0	0	0	0	0							c	+	>	0	0	0	0	0	0
Access	×	Ž	×				×	×				×	×	×	W	×	N N	ž							>		<u> </u>	×	×	×	W	Ž	<u>></u>
Name	TEMPHIGH	TEMPLOW	TEMP				VSCALEDONE	EM23WAKEUP				DCDCINBYPASS	DCDCLNRUNNING	DCDCLPRUNNING	NFETOVERCURRENTLIMIT	PFETOVERCURRENTLIMIT	VMONFVDDRISE	VMONFVDDFALL							AMONIOORISE		VIMONIOUFALL	VMONDVDDRISE	VMONDVDDFALL	VMONALTAVDDRISE	VMONALTAVDDFALL	VMONAVDDRISE	VMONAVDDFALL
Bit	Na	me					Re	set			Ac	ces	s	Des	crip	tion																	
31	TE	MPI	HIGI	Н			0				W1			Set	TEN	ſРН	IGH	Inte	erru	upt	Flag												
	Wr	ite 1	to s	set	the '	TEM	PHI	GH	inte	rup	t flaç	g																					
30	TE	MPL	_OV	V			0				W1		,	Set	TEN	/IPL	ow	Inte	erru	ıpt l	Flag												
	Wr	ite 1	to s	set	the '	TEM	PLC)W i	nter	rupt	flag	J																					
29	TEMP 0 W1 Set TEMP Interrupt Flag Write 1 to set the TEMP interrupt flag																																
	Wr	ite 1	tos	set	the '	TEM	P in	terrı	upt f	lag																							
28:26	Re	serv	red				To tion		ure	com	pati	ibilit _.	y wi	th fu	ture	dev	/ices	s, alı	way	/s w	rite i	bits	to	0. M	lore	info	orm	natio	on in	1.2	? Co	nvei	7-
25	VS	CAL	.ED	ON	Ε		0				W1		;	Set	vsc	AL	EDC	NE	Int	terrı	ıpt F	Flaç	3										
	Wr	ite 1	to	set	the '	VSC	ALE	DO	NE i	nter	rupt	flag)																				
24	ΕM	123V	VAK	ŒU	IP		0				W1		;	Set	EM2	23W	AKI	EUP	Int	terr	upt l	Fla	g										
	Wr	ite 1	tos	set	the	EM2	3WA	١KE	UP	inter	rupt	t flaç	9																				
23:21	Re	serv	red				To tion		ure	com	pati	ibilit _.	y wi	th fu	ture	dev	/ices	s, alı	way	/S W	rite i	bits	to	0. M	lore	info	orm	natio	on in	1.2	? Co	nvei	1-
20	DC	DCI	INB'	ΥP	ASS		0				W1		,	Set	DC	OCIN	NBY	PAS	SS I	Inte	rrup	t F	lag										
	Wr	ite 1	to	set	the	DCD	CIN	BYF	PAS	S in	terru	ıpt f	lag																				
19	DC	DCI	LNR	NUS	ININ	IG	0				W1		;	Set	DC	OCL	NRU	JNN	IINC	G In	terrı	upt	Fla	ag									
	Wr	ite 1	to s	set	the	DCD	CLN	IRU	NNI	NG	inte	rrup	t fla	g																			
18					ININ		0				W1				DC	OCL	PRU	JNN	INC	3 In	terrı	ıpt	Fla	ıg									
	Wr	ite 1	to s	set	the	DCD	CLF	PRU	NNI	NG	inte	rrup	t fla	g																			
17			JMI.		UR-		0				W1			Set	NFE	TO'	VER	CU	RR	ENT	ΓLIM	IIT I	Inte	erru	ot F	ag							
	Wr	ite 1	tos	set	the	NFE	TOV	/ER	CUF	RE	NTL	IMI.	T int	erru	pt fl	ag																	
16			JMI.		UR-		0				W1		;	Set	PFE	OT:	VER	CUI	RRI	ENT	LIM	IT I	Inte	erru	ot Fl	ag							
	Write 1 to set the PFETOVERCURRENTLIMIT interrupt flag																																

Bit	Name	Reset	Access	Description
15	VMONFVDDRISE	0	W1	Set VMONFVDDRISE Interrupt Flag
	Write 1 to set the VM	ONFVDDRISE i	nterrupt fla	g
14	VMONFVDDFALL	0	W1	Set VMONFVDDFALL Interrupt Flag
	Write 1 to set the VM	ONFVDDFALL i	interrupt fla	g
13:8	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7	VMONIO0RISE	0	W1	Set VMONIO0RISE Interrupt Flag
	Write 1 to set the VM	ONIO0RISE inte	errupt flag	
6	VMONIO0FALL	0	W1	Set VMONIO0FALL Interrupt Flag
	Write 1 to set the VM	ONIO0FALL inte	errupt flag	
5	VMONDVDDRISE	0	W1	Set VMONDVDDRISE Interrupt Flag
	Write 1 to set the VM	ONDVDDRISE	interrupt fla	ng
4	VMONDVDDFALL	0	W1	Set VMONDVDDFALL Interrupt Flag
	Write 1 to set the VM	ONDVDDFALL	interrupt fla	ag
3	VMONALTAVDD- RISE	0	W1	Set VMONALTAVDDRISE Interrupt Flag
	Write 1 to set the VM	ONALTAVDDRI	SE interrup	ot flag
2	VMONALTAVDD- FALL	0	W1	Set VMONALTAVDDFALL Interrupt Flag
	Write 1 to set the VM	ONALTAVDDFA	ALL interrup	pt flag
1	VMONAVDDRISE	0	W1	Set VMONAVDDRISE Interrupt Flag
	Write 1 to set the VM	ONAVDDRISE i	interrupt fla	g
0	VMONAVDDFALL	0	W1	Set VMONAVDDFALL Interrupt Flag
	Write 1 to set the VM	ONAVDDFALL	interrupt fla	ng

10.5.11 EMU_IFC - Interrupt Flag Clear Register

Offset													Bi	t Po	siti	on													
0x02C	31	30	29	28	26	25	24	23	22	20	19	18	17	16	15	4	13	7 7	-	9 0	n @	7	9	5	4	က	2	_	0
Reset	0	0	0	'	<u> </u>	0	0		'	0	0	0	0	0	0	0				<u>'</u>		0	0	0	0	0	0	0	0
Access	(R)W1	(R)W1	(R)W1			(R)W1	(R)W1			(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1						(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name	TEMPHIGH	TEMPLOW	TEMP			VSCALEDONE	EM23WAKEUP			DCDCINBYPASS	DCDCLNRUNNING	DCDCLPRUNNING	NFETOVERCURRENTLIMIT	PFETOVERCURRENTLIMIT	VMONFVDDRISE	VMONFVDDFALL						VMONIOORISE	VMONIO0FALL	VMONDVDDRISE	VMONDVDDFALL	VMONALTAVDDRISE	VMONALTAVDDFALL	VMONAVDDRISE	VMONAVDDFALL
Bit	Na	me				Re	set		1	Acces	s	Des	crip	tion															
31	TE	MPI	HIGH	+		0			(R)W1		Clea	ar Ti	EMP	PHIG	H I	nterr	upt F	la	9									
				clear the										urns	s the	val	ue of	the I	Fa	and c	lears	the	corr	espo	ondi	ng ir	nterr	upt	
30	TEMPLOW 0									R)W1		Clea	ar Ti	EMP	LO	W Ir	nterru	ıpt F	laç	J									
	Write 1 to clear the TEMPLOW interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).																												
29	TE	MP				0			(R)W1		Clea	ar Ti	EMP	Int	erru	ıpt F	ag											
				clear the								retu	rns t	he v	/alue	e of	the II	and	l cl	ears	the c	orres	spor	ding	g inte	erru	pt fla	ags	
28:26	Re	serv	/ed			To tio		ure	comp	atibili	y wi	th fu	ıture	dev	/ices	s, al	ways	write	e bi	ts to	0. M	ore ii	nforr	natio	on ir	1.2	? Co	nver	7-
25	VS	CAL	ED	ONE		0			(R)W1		Clea	ar V	SCA	LE	001	IE In	terru	pt	Flag									
	-	-		clear the feature									_	retu	urns	the	valu	e of t	he	IF ar	nd cle	ears	the o	corre	espo	ndir	ng in	terrı	Jpt
24	EM	123V	VAK	EUP		0			(R)W1		Clea	ar El	M23	WA	ΚEι	JP In	terru	pt	Flag									
				clear the										ret	urns	the	valu	e of t	he	IF a	nd cle	ears	the	corr	espo	ndir	ng ir	iterr	upt
23:21	Re	serv	⁄ed			To tio		ure	comp	atibili	y wi	th fu	iture	dev	/ices	s, al	ways	write	e bi	ts to	0. M	ore ii	nforr	natio	on ir	1.2	? Co	nver	7-
20	DC	DCI	INB	YPASS		0			(R)W1		Clea	ar D	CDC	CINE	3YP	ASS	Inter	ru	pt Fla	ag								
				clear the This fea											etur	ns t	he va	lue c	of t	ne IF	and	clea	s th	e cc	rres	pon	ding	inte	er-
19	DC	DCI	LNR	UNNIN	G	0		_	(R)W1		Clea	ar D	CDC	CLN	RUN	NIN	G Int	eri	upt	Flag								
				clear the igs (Thi												urns	s the	value	e o	f the	IF an	d cle	ears	the	corr	espo	ondi	ng	
18	DC	DCI	LPR	UNNIN	G	0			(R)W1		Clea	ar D	CDC	CLP	RUN	ININ	G Int	erı	upt l	Flag								_
	Write 1 to clear the DCDCLPRUNNING interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).																												

				Eine Energy Management ont
Bit	Name	Reset	Access	Description
17	NFETOVERCUR- RENTLIMIT	0	(R)W1	Clear NFETOVERCURRENTLIMIT Interrupt Flag
				T interrupt flag. Reading returns the value of the IF and clears the correnabled globally in MSC.).
16	PFETOVERCUR- RENTLIMIT	0	(R)W1	Clear PFETOVERCURRENTLIMIT Interrupt Flag
				T interrupt flag. Reading returns the value of the IF and clears the correnabled globally in MSC.).
15	VMONFVDDRISE	0	(R)W1	Clear VMONFVDDRISE Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding intery in MSC.).
14	VMONFVDDFALL	0	(R)W1	Clear VMONFVDDFALL Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding intery in MSC.).
13:8	Reserved	To ensure co tions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7	VMONIO0RISE	0	(R)W1	Clear VMONIO0RISE Interrupt Flag
	Write 1 to clear the V flags (This feature m			g. Reading returns the value of the IF and clears the corresponding interrupt MSC.).
6	VMONIO0FALL	0	(R)W1	Clear VMONIO0FALL Interrupt Flag
	Write 1 to clear the V flags (This feature m			g. Reading returns the value of the IF and clears the corresponding interrupt MSC.).
5	VMONDVDDRISE	0	(R)W1	Clear VMONDVDDRISE Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding intery in MSC.).
4	VMONDVDDFALL	0	(R)W1	Clear VMONDVDDFALL Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding intery in MSC.).
3	VMONALTAVDD- RISE	0	(R)W1	Clear VMONALTAVDDRISE Interrupt Flag
	Write 1 to clear the Vinterrupt flags (This f			rupt flag. Reading returns the value of the IF and clears the corresponding obally in MSC.).
2	VMONALTAVDD- FALL	0	(R)W1	Clear VMONALTAVDDFALL Interrupt Flag
	Write 1 to clear the Vinterrupt flags (This f			rupt flag. Reading returns the value of the IF and clears the corresponding obally in MSC.).
1	VMONAVDDRISE	0	(R)W1	Clear VMONAVDDRISE Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding intery in MSC.).
0	VMONAVDDFALL	0	(R)W1	Clear VMONAVDDFALL Interrupt Flag
	Write 1 to clear the Vrupt flags (This featu			flag. Reading returns the value of the IF and clears the corresponding inter-y in MSC.).

10.5.12 EMU_IEN - Interrupt Enable Register

Offset															Bi	it Po	ositi	on															
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	: =		2	6	8	7	9	2	4	က	2	_	0
Reset	0	0	0				0	0				0	0	0	0	0	0	0								0	0	0	0	0	0	0	0
Access	₽	₩	₩				₹	% N				₩ M	R ₩	₩	R W	S.	R W	₩								₽	R W	₹	R M M	Z S	R W	₩	RW
Name	TEMPHIGH	TEMPLOW	TEMP				VSCALEDONE	EM23WAKEUP				DCDCINBYPASS	DCDCLNRUNNING	DCDCLPRUNNING	NFETOVERCURRENTLIMIT	PFETOVERCURRENTLIMIT	VMONFVDDRISE	VMONFVDDFALL								VMONIOORISE	VMONIO0FALL	VMONDVDDRISE	VMONDVDDFALL	VMONALTAVDDRISE	VMONALTAVDDFALL	VMONAVDDRISE	VMONAVDDFALL
Bit	Na	me					Re	set			Α	cces	s	Des	crip	tion	n																
31	TE	MPH	HIGH	Н			0				R'	N		TEN	IРН	IGH	Inte	erru	pt E	Ena	ble												
	En	able	/disa	abl	e th	e TE	MPI	HIG	iH ir	nterr	upt																						
30	TE	MPL	_OV	/			0				R'	N		TEN	1PL	ow	Inte	rru	pt E	na	ble												
	Enable/disable the TEMPLOW inte								terru	ıpt																							
29	TEMP 0									R	N		TEN	1P Ir	nter	rupt	En	able	Э														
	En	able	/disa	abl	e th	e TE	MP	inte	erru	pt																							
28:26	Re	serv	red				To tio		sur	e coi	пра	tibilit	y wi	th fu	ture	de	/ices	s, al	way	′Ѕ И	vrite	bit	s to	0.	Мо	re in	forn	natio	on ir	1.2	? Co	nvei	1-
25	VS	CAL	.ED	O١	ΙE		0				R	N		vsc	ALI	EDC	NE	Inte	erru	pt	Ena	ble	•										
	En	able	/disa	abl	e th	e VS	CAI	EC	100	IE in	terrı	ıpt																					
24	ΕM	123V	VAK	Œι	JP		0				R'	N		EM2	23W	AKE	EUP	Inte	erru	ıpt	Ena	ble	•										
	En	able	/disa	abl	e th	e EN	/123\	۷AI	KEL	JP in	terr	upt																					
23:21	Re	serv	red					en ns	sur	e coi	пра	tibilit	y wi	th fu	ture	de	/ices	s, al	way	′Ѕ И	vrite	bit	s to	0.	Мо	re in	forn	natio	on ir	า 1.2	? Co	nvei	7-
20	DC	DCI	NΒ	YP.	ASS	3	0				R	N		DC	CIN	IBY	PAS	SS In	nter	rup	ot E	nal	ole										
	En	able	/disa	abl	e th	e DO	DC	INB	YP.	ASS	inte	rrup	t																				
19	DC	DCI	_NR	NU!	IINI	٧G	0				R'	N		DC	CL	NRI	JNN	ING	Int	err	upt	En	ab	le									
	En	able	/disa	abl	e th	e DO	DC	LNF	RUN	ININ	IG ir	terru	ıpt																				
18		DCI					0				R'			DC	CL	PRU	JNN	ING	Int	err	upt	En	ab	le									
						e DO		LPF	RUN	ININ																							
17		ETC NTL			UR		0				R'	N		NFE	TO	VER	CUI	RRE	ENT	LIN	/IIT I	nte	erri	upt	En	able							
	En	able	/disa	abl	e th	e NF	ETO	OVE	RC	URI	REN	TLIN	/IIT i	nter	rupt																		
16		ETC NTL			UR	-	0				R'	N		PFE	TOV	/ER	CUI	RRE	NTI	LIN	IT I	nte	erru	ıpt	Ena	able							

Enable/disable the PFETOVERCURRENTLIMIT interrupt

Bit	Name	Reset	Access	Description
15	VMONFVDDRISE	0	RW	VMONFVDDRISE Interrupt Enable
	Enable/disable the V	MONFVDDRISE	interrupt	
14	VMONFVDDFALL	0	RW	VMONFVDDFALL Interrupt Enable
	Enable/disable the Vi	MONFVDDFALL	interrupt	
13:8	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7	VMONIO0RISE	0	RW	VMONIO0RISE Interrupt Enable
	Enable/disable the V	MONIO0RISE in	terrupt	
6	VMONIO0FALL	0	RW	VMONIO0FALL Interrupt Enable
	Enable/disable the Vi	MONIO0FALL in	terrupt	
5	VMONDVDDRISE	0	RW	VMONDVDDRISE Interrupt Enable
	Enable/disable the Vi	MONDVDDRISE	interrupt	
4	VMONDVDDFALL	0	RW	VMONDVDDFALL Interrupt Enable
	Enable/disable the V	MONDVDDFALI	_ interrupt	
3	VMONALTAVDD- RISE	0	RW	VMONALTAVDDRISE Interrupt Enable
	Enable/disable the V	MONALTAVDDF	RISE interro	upt
2	VMONALTAVDD- FALL	0	RW	VMONALTAVDDFALL Interrupt Enable
	Enable/disable the V	MONALTAVDDF	ALL interr	upt
1	VMONAVDDRISE	0	RW	VMONAVDDRISE Interrupt Enable
	Enable/disable the Vi	MONAVDDRISE	interrupt	
0	VMONAVDDFALL	0	RW	VMONAVDDFALL Interrupt Enable
	Enable/disable the V	MONAVDDFALL	interrupt	

10.5.13 EMU_PWRLOCK - Regulator and Supply Lock Register

Offset	Bit Positi	tion
0x034	33 34 35 36 37 38 39 31 31 32 33 34 35 36 37 38 39 31 40 <th>4 6 7 7 7 7 7 8 8 7 9 9 7 7 7 7 7 7 7 7 7 7</th>	4 6 7 7 7 7 7 8 8 7 9 9 7 7 7 7 7 7 7 7 7 7
Reset		000000
Access		RW
Name		LOCKKEY

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RW	Regulator and Supply Configuration Lock Key

Write any other value than the unlock code to lock all regulator control registers, from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled. Registers that are locked: PWRCFG, PWRCTRL and DCDC* registers.

Mode	Value	Description
Read Operation		
UNLOCKED	0	EMU Regulator registers are unlocked
LOCKED	1	EMU Regulator registers are locked
Write Operation		
LOCK	0	Lock EMU Regulator registers
UNLOCK	0xADE8	Unlock EMU Regulator registers

10.5.14 EMU_PWRCTRL - Power Control Register

Offset			Bit Position													
0x03C	30 28 28 27 27 26	22 23 24 25 27 27 20 27 20 27 20 27 27 27 27 27 27 27 27 27 27 27 27 27	0 - 1 - 2 - 3 - 4 - 5 - 6 - 7 - 7 - 7 - 7 - 7 - 7 - 7 - 7 - 7													
Reset			0 0 0													
Access			A A													
Name			IMMEDIATEPWRSWITCH REGPWRSEL ANASW													
Bit	Name	Reset Access	Description													
31:14	Reserved	To ensure compatibility t	with future devices, always write bits to 0. More information in 1.2 Conven-													
13	IMMEDIATEPWRS- WITCH	0 RW	Allows Immediate Switching of ANASW and REGPWRSEL Bit-fields													
12:11	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convertions														
10	REGPWRSEL	0 RW	This Field Selects the Input Supply Pin for the Digital LDO													
	DCDC is not configure	ed to drive DVDD, IMMED	e Digital LDO. Firmware should select DVDD as the input after startup. If IATEPWRSWITCH needs to be set to prior to setting this bit to immediately DVDD, hardware will make the switch to DVDD only when DCDC is stable													
	Value	Mode	Description													
	0	AVDD	The AVDD pin is the supply for the digital LDO. LDO current is limited to 20 mA in this configuration.													
	1	DVDD	The DVDD pin is the supply for the digital LDO. Firmware should set REGPWRSEL=1 after startup, before increasing the core clock frequency.													
9:6	Reserved	To ensure compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-													
5	ANASW	0 RW	Analog Switch Selection													
	LFRCO, LFXO, HFRO is not configured to di	CO, AUXHFRCO, VMON, I rive DVDD, IMMEDIATEP\	alog supply (VDDX_ANA) used by the analog peripherals (e.g., ULFRCO, IDAC, and ADC). Reset with POR, Hard Pin Reset, or BOD Reset. If DCDC WRSWITCH needs to be set to prior to setting this bit to immediately make D, hardware will make the switch to DVDD only when DCDC is stable													
	Value	Mode	Description													
	0	AVDD	Select AVDD as the analog power supply													
	1	DVDD	Select DVDD as the analog power supply													
4:0	Reserved	To ensure compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-													

10.5.15 EMU_DCDCCTRL - DCDC Control

Offset			Bit Position	
0x040	30 30 27 28 27 27 26	23 23 24 27 27 27 27 27 27 27 27 27 27 27 27 27	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	- 0
Reset			~ ~	0x3
Access			R R	RW
Name			DCDCMODEEM4 DCDCMODEEM23	DCDCMODE
Bit	Name	Reset Ac	ess Description	
31:6	Reserved	To ensure compat	lity with future devices, always write bits to 0. More information in 1.2 Cor	nven-
5	DCDCMODEEM4	1 RV	DCDC Mode EM4H	
	Determines the DCD0 BOD Reset.	C mode in EM4H. Th	bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin Reset,	or
	Value	Mode	Description	
	0	EM4SW	DCDC mode is according to DCDCMODE field.	
	1	EM4LOWPOWER	DCDC mode is low power.	
4	DCDCMODEEM23	1 RV	DCDC Mode EM23	
4			DCDC Mode EM23 13. This bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin	ı Re-
4	Determines the DCD0			ı Re-
4	Determines the DCD0 set, or BOD Reset.	C mode in EM2 and I	13. This bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin	ı Re-
4	Determines the DCD0 set, or BOD Reset. Value	C mode in EM2 and I	M3. This bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin	ı Re-
3:2	Determines the DCD0 set, or BOD Reset. Value 0	Mode EM23SW EM23LOWPOWEI	M3. This bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin Description DCDC mode is according to DCDCMODE field.	
	Determines the DCD0 set, or BOD Reset. Value 0 1	Mode EM23SW EM23LOWPOWEI	M3. This bit is ignored if DCDCMODE=Bypass. Reset with POR, Hard Pin Description DCDC mode is according to DCDCMODE field. DCDC mode is low power.	
3:2	Determines the DCD0 set, or BOD Reset. Value 0 1 Reserved DCDCMODE	Mode EM23SW EM23LOWPOWER To ensure compatitions 0x3 RV	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power. DCDC mode is low power. DCDC mode is low power.	
3:2	Determines the DCD0 set, or BOD Reset. Value 0 1 Reserved DCDCMODE	Mode EM23SW EM23LOWPOWER To ensure compatitions 0x3 RV	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power.	
3:2	Determines the DCDC set, or BOD Reset. Value 0 1 Reserved DCDCMODE Determines the operations and the properties of	Mode EM23SW EM23LOWPOWEI To ensure compatitions 0x3 RV atting mode of the DC	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power.	nven-
3:2	Determines the DCD0 set, or BOD Reset. Value 0 1 Reserved DCDCMODE Determines the operators and the operators are also as a set of the content of the	Mode EM23SW EM23LOWPOWED To ensure compatitions 0x3 RV atting mode of the DC Mode	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power. DCDC regulator is operating in bypass mode. Prior to configuring DCDCMODE=BYPASS, software must set EMU_DCDCCLIMCTRL.BYPLIMEN=1 to prevent excessive current	nven-
3:2	Determines the DCD0 set, or BOD Reset. Value 0 1 Reserved DCDCMODE Determines the operative of the property of the prope	Mode EM23SW EM23LOWPOWED To ensure compatitions 0x3 RV atting mode of the DC Mode BYPASS	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power. DCDC regulator in power information in 1.2 Cord mode is low power. DCDC regulator is operating in bypass mode. Prior to configuring DCDCMODE=BYPASS, software must set must set mode. DCDC mode is low power.	nven-
3:2	Determines the DCD0 set, or BOD Reset. Value 0 1 Reserved DCDCMODE Determines the operative of the properation of the pro	Mode EM23SW EM23LOWPOWED To ensure compatitions 0x3 RV atting mode of the DC Mode BYPASS	Description DCDC mode is according to DCDCMODE field. DCDC mode is low power. DCDC regulator is operating in bypass mode. Prior to configuring DCDCMODE=BYPASS, software must set EMU_DCDCCLIMCTRL.BYPLIMEN=1 to prevent excessive current between VREGVDD and DVDD supplies. DCDC regulator is operating in low noise mode.	nven-

10.5.16 EMU_DCDCMISCCTRL - DCDC Miscellaneous Control Register

Offset										В	it Po	siti	on												
0x04C	30	29 28 28	27	26	25 24	23	22	2 8	19	18 7	16	15	<u>4</u> ε	2 2	1	9 0	n	7	9	5	4	က	2	_	0
Reset		0×0			0x3		2	5		0x0			0x7			0x7	'			0		'	_	_	0
Access		SX SX			₩ M		<u> </u>	<u> </u>		RW			R W			S S				RW			₩ M	Z.	₩ M
Name		LPCMPBIASEM234H			LNCLIMILIMSEL		I I I I I I I I I I I I I I I I I I I			BYPLIMSEL			NFETCNT			PFETCNT				LNFORCECCMIMM			LPCMPHYSHI	LPCMPHYSDIS	LNFORCECCM
Bit	Name				Reset		A	cces	s C	escri	otion														
31:30	Reserv	red			To ens	ure	compa	atibilit	y witl	h future	e dev	/ices	s, alwa	ys wr	rite b	its to	0. Mo	re in	forn	natic	n in	1.2	Co.	nver	7-
29:28	LPCMF	PBIASE	M23	84H	0x0		F	RW	L	.P Mod	de Co	omp	parator	Bias	s Se	ectio	n for	EM2	23 o	r EN	14H				
	LP mod	de comp	oara	tor b	ias sele	ctio	n. Res	et wi	th PC	R, Ha	rd Pi	n Re	eset, o	r BOI) Re	set.									
	Value																	_							
	0	**** *** * **** * *** * **** * ***** * **** * **** * **** * **** * ***** * ***** * ***** * ****** * ****** * ********															_								
	1				BIAS1				N	/laximu	ım lo	ad c	current	less	than	500u	A.								
	2				BIAS2				N	/laximu	ım lo	ad c	current	less	than	2.5m	A.								
	3				BIAS3					/laximu	ım lo	ad c	current	less	than	10m/	۹.								_
27	Reserv	red .			To ens	ure	compa	atibilit	y witl	h future	e dev	/ices	s, alwa	ys wr	rite b	its to	0. Mo	re in	forn	natic	n in	1.2	? Coi	nver	7-
26:24	LNCLI	MILIMSI	EL		0x3		R	RW	C	urren	t Lin	nit L	evel S	elect	tion	for C	urren	t Lin	nite	r in	LN	Mod	le		
23	MILIMS and 40 tions. F	ide curre SEL=(I_ mA represent strong For strong her than	MAX rese ng (i	<+40 nts t .e., l	mA)*1. the curre low inte	5/(5) ent r rnal d rel	mA*(Pripple volume impediately)	PFET(with s dance r issu	ONT+ ome) batt es. R	·1))-1, margir tery, it eset w	whern, and is rewith P	e I_ d the com OR,	MAX is e factor nmende , Hard	s the r of 1 ed to Pin R	max .5 ad have leset	imum coun e I_M , or B	averats for AX=2	age of dete 00m. eset.	cting A. I	ent a g err _MA	allow or a X s	ved and o houl	to tho	ie lo r va ever	ria- be
20	7.00077				tions	arc	compe	ationit,	y vvici	Tratar		,,,,,,	s, anva	yo w	ne s	113 10	0. 1010	10 111	10111	Tatio	,,,,,,	1 1.2	. 001	1001	
22:20		MILIMSE			0x1			RW					evel S												
	setting	gh-side LPCLIN ds wher	/ILIN	MSE	L=1, co	rres	pondii	ng to	a ma	ximum	curr	ent	of 80 r	nA fo	r op	timal	efficie								
19:16	BYPLI	MSEL			0x0		R	RW	C	urren	t Lin	nit ir	п Вура	ass M	lode										
		rent lim DR, Har							MEN	equals	s one	e. Th	ne limit	is fro	m 20)mA t	o 320	mA,	with	า 20เ	mA/	step	. Re	eset	
15:12	NFETO	CNT			0x7		F	RW	N	IFET S	Switc	h N	umbei	r Sele	ectio	n									
		oise moo														ches a	are Ni	ETC	CNT	+1.	This	s ma	ву са	use	: a

Bit	Name	Reset	Access	Description
11:8	PFETCNT	0x7	RW	PFET Switch Number Selection
	Low Noise mode PFE Hard Pin Reset, or B0	•	count num	ber. The selected number of switches are PFETCNT+1. Reset with POR,
7:6	Reserved	To ensure com	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	LNFORCECCMIMM	0	RW	Force DCDC Into CCM Mode Immediately, Based on LNFOR-CECCM
				FORCECCM bit and have the change take effect while DCDC is running. ed prior to enabling the DCDC.
4:3	Reserved	To ensure com	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	LPCMPHYSHI	1	RW	Comparator Threshold on the High Side
	Reserved for internal	use. Should alwa	ays be set	to 1.
1	LPCMPHYSDIS	1	RW	Disable LP Mode Hysteresis in the State Machine Control
	Reserved for internal	use. Should alwa	ays be set	to 1.
0	LNFORCECCM	0	RW	Force DCDC Into CCM Mode in Low Noise Operation
	in forced CCM mode. zero detector is config	The threshold s gured as reverse In low power n	et by ZDE -current lir	zero detector is configured as zero-crossing detector and the DCDC will be TILIMSEL will be ignored. When this bit is set to 1 in low noise mode, the miter and the DCDC will be in DCM mode. The reverse current limit level is zero detector is always configured as zero-crossing detector. Reset with

10.5.17 EMU_DCDCZDETCTRL - DCDC Power Train NFET Zero Current Detector Control Register

	_																					_	,								
Offset														Bi	it Po	ositi	on														
0x050	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset																						3	Š			0x5					
Access																						Š	≩ Y			Z.					
Name																						\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	ZDEIBLANKULY			ZDETILIMSEL					
Bit	Name	;				Re	set			Ac	ces	s	Des	crip	tior	1															
31:10	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convetions														nven	-															
9:8	ZDET	BLA	NKE	DLY		0x′	1			RV	V		Res	erve	ed f	or ir	nteri	nal	use.	Do	not	cha	ange	е.							
	Rese	ved	for i	nterr	nal u	ıse.	Do	not o	chai	nge.																					
7	Rese	ved				To tio		ure	con	npati	ibilit	y wi	ith fu	ıture	de	vices	s, al	way	'S WI	rite t	oits t	o 0.	Мо	re in	forr	natio	on in	1.2	? Coi	nven	-
6:4	ZDET	ILIM	ISEL			0x	5			RV	V		Rev	erse	e Cı	ırreı	nt L	imit	Lev	el S	Sele	ctio	n fo	r Ze	ro l	Dete	cto	r			
	Zero of this reserved the thick the	egist A)*1 s for I_RI EL=(LNI	er is .5/(2 detendant MAX: D, the	cald 2.5m ectin =160 e DC CEC	culat A*(N ig ei OmA CDC CCM	ted by the state of the state o	oy the TCN and maximal ending the tender of	ne al IT+1 otho imiza ior v zero	llow l)), v er v e Zl will o de	ed a when ariat DET be v	avera re 40 tions ILIM rery or w	age 0m/ s. W ISE sim ill o	revolution	erse orese the 7 wi to wi detec	cur ents bat ith N	rent the tery NFE	I_R curi can TCN FOR	MA rent tole IT=	X th ripp erate 15. N	roug le w e lar lote 1=0	gh the vith some of the some o	ne e som reve t wh at is	quate makerse when the makers with the makers with the makers with the makers where the mak	tion: argir curr _NF • DC	ZD n, ar ent, OR(DC	ETII nd th it is CEC will	_IMS ne fa rec CM: be i	SEL actor comr =1 b	=(I_I r of 1 mend out Z CM I	RMA 1.5 add ded t DET mode	X c- to I- e.

3:0 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions

10.5.18 EMU_DCDCCLIMCTRL - DCDC Power Train PFET Current Limiter Control Register

Offset															Bi	t Po	ositi	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•				•													0				3	Š			•	•				
Access																			W.				Ž	<u>}</u>								
Name																			BYPLIMEN				\	CLIMBLAINFULT								
Bit	Na	ame					Re	set			Ac	ces	s I	Des	crip	tior	1															
31:14	Re	eser	ved				To tio		ure	con	pati	bility	/ wi	th fu	ture	de	/ices	s, al	way.	s wi	rite k	oits t	o 0.	Мо	re ir	forr	natio	on in	1.2	Col	nven	1-
13	В	/PLI	MEN	1			0				RW	/		Вур	ass	Cu	rren	t Li	mit l	Ena	ble											
	P.A en	SS able	s cur mod ed. To volta	e. N o pr	lote eve	that nt th	the	de\ xce	/ice ss c	will urre	see nt, a	an a appli	addi icati	tion: ons	al ~′ sho	10 μ ould	A of disa	cur ble	rent the	dra Byp	w w ass	hen Cur	BY ren	PLIN t Lin	ЛÉN nit (I	i=1 a BYP	and LIM	Byp: EN=	ass :0) c	Mod nce	le is the	
12:10	Re	eser	ved				To tio		ure	con	pati	bility	/ wi	th fu	ture	de	/ices	s, al	way.	s wi	rite k	oits t	o 0.	Мо	re ir	forr	natio	on in	1.2	Col	nven	1-
9:8	CI	IME	BLAN	IKD	LY		0x′	1			RW	/		Res	erve	ed f	or ir	teri	nal ເ	use.	Do	not	cha	ang	е.							
	Re	eser	ved f	or ir	nterr	nal u	ıse.	Do	not o	char	ige.																					

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

7:0

Reserved

tions

10.5.19 EMU_DCDCLNCOMPCTRL - DCDC Low Noise Compensator Control Register

Offset															Bi	t Po	siti	on														
0x058	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		ζ,	CYO				0x7	•			ç	Z		•		•		2	5 5	•						0x07	•				0x7	
Access		2	<u>}</u>				Z ≪				2	<u>}</u>						2	<u>}</u>							₩					₩ M	
Name		COMBENICS	COMPENS				COMPENC2											COMPENDS								COMPENR2					COMPENR1	

Bit	Name	Reset	Access	Description
31:28	COMPENC3	0x5	RW	Low Noise Mode Compensator C3 Trim Value
	LN mode compensato	or C3 trim, 0.5pF	-8pF in 0.	5pF steps. Reset with POR, Hard Pin Reset, or BOD Reset.
27	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
26:24	COMPENC2	0x7	RW	Low Noise Mode Compensator C2 Trim Value
	LN mode compensato	or C2 trim, 1pF-8	3pF in 1pF	steps. Reset with POR, Hard Pin Reset, or BOD Reset.
23:22	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
21:20	COMPENC1	0x2	RW	Low Noise Mode Compensator C1 Trim Value
	LN mode compensato	or C1 trim, 0.15p	F-0.60pF i	n 0.15pF step. Reset with POR, Hard Pin Reset, or BOD Reset.
19:16	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:12	COMPENR3	0x4	RW	Low Noise Mode Compensator R3 Trim Value
	LN mode compensato	or r3 trim, 5-80K	Ohm in 5K	hom steps. Reset with POR, Hard Pin Reset, or BOD Reset.
11:9	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:4	COMPENR2	0x07	RW	Low Noise Mode Compensator R2 Trim Value
	LN mode compensato	or r2 trim, 50-160	00KOhm, i	n 50KOhm steps. Reset with POR, Hard Pin Reset, or BOD Reset.
3	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	COMPENR1	0x7	RW	Low Noise Mode Compensator R1 Trim Value
	LN mode compensato	or r1 trim, 500-12	200kOhm,	in 100KOhm steps. Reset with POR, Hard Pin Reset, or BOD Reset.

10.5.20 EMU_DCDCLNVCTRL - DCDC Low Noise Voltage Register

Offset															Bi	t Po	siti	on														
0x05C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset												•	•								0x71	•				•					0	
Access																					RWH										W.	
Name																					LNVREF										LNATT	

Bit	Name	Reset	Access	Description
31:15	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
14:8	LNVREF	0x71	RWH	Low Noise Mode VREF Trim
				F set the output of the DCDC to 3*(1+LNATT)*(235.48+3.226*LNVREF). configuring this field. Reset with POR, Hard Pin Reset, or BOD Reset.
7:2	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
1	LNATT	0	RW	Low Noise Mode Feedback Attenuation
	Low noise mode Hard Pin Reset,		tion. Custome	ners should use the emlib functions for configuring this field. Reset with POR
	Value	Mode		Description
	0	DIV3		Feedback Ratio is 1/3
	1	DIV6		Feedback Ratio is 1/6
0	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

10.5.21 EMU_DCDCLPVCTRL - DCDC Low Power Voltage Register

DIV4

DIV8

Offset															Bi	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	1	10	6	∞	7	9	2	4	က	2	_	0
Reset																											Ç	UXD 4				0
Access																											Ž	≥ Y				RW
Name																											L Q	7 7 7 1				LPATT
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
31:9	Re	serv	red				To tior		ure	com	pati	bility	y wit	th fu	ture	dev	ices	s, al	way	's WI	rite t	oits t	o 0.	Мо	re ir	nforr	natio	on i	n 1.2	? Co	nvei	7-
8:1	LP	VRE	F				0xE	34			RW	/	ı	LP N	/lod	e Re	efer	enc	e S	elec	tion	for	EM	23 a	and	EM	4H					
	4*(1+L	PAT	T)*(30+	LPV		=)*2	.2m																				he [set w			
0	LP	ATT					0				RW	/	I	Low	Po	wer	Fee	dba	ack	Atte	enua	atio	1									
		•					tten or B				t. Cı	usto	mer	rs sh	oul	d use	e the	e en	nlib	fund	ction	is fo	r co	nfigu	urin	g thi	s fie	ld.	Rese	et wi	th	
	Va	lue					Мо	de					ı	Des	cript	ion																_

Feedback Ratio is 1/4

Feedback Ratio is 1/8

0

1

10.5.22 EMU_DCDCLPCTRL - DCDC Low Power Control Register

Offset															Bi	t Po	siti	on														
0x06C	31	30	29	78	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	19	6	ω	7	9	5	4	က	2	_	0
Reset						3	Š	_							•			2	e X					•	•						·	
Access						2	<u>}</u>	RW										\ 0	<u>}</u>													
Name						7124	LFBLAINA	LPVREFDUTYEN											LPCIVIPH 1 SSELEIVIZS4H													
Bit	Na	me					Re	set			Ac	cess	s [Des	crip	tion																

Bit	Name	Reset	Access	Description
31:27	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
26:25	LPBLANK	0x1	RW	Reserved for internal use. Do not change.
	Reserved for interna	l use. Do not cha	nge.	
24	LPVREFDUTYEN	1	RW	LP Mode Duty Cycling Enable
	Allow duty cycling of	the bias. This is	to minimiz	e DC bias. Reset with POR, Hard Pin Reset, or BOD Reset.
23:16	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:12	LPCMPHYSSE- LEM234H	0x0	RW	LP Mode Hysteresis Selection for EM23 and EM4H
		PHYSSEL*3.13n	nv. Custom	e low power comparator. Hysteresis voltage at the output is ners should use the emlib functions for configuring this field. Reset with
11:0	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-

10.5.23 EMU_DCDCLNFREQCTRL - DCDC Low Noise Controller Frequency Control

Offset															Ві	t Po	siti	on														
0x070	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•	0X0													0x0															
Access						₩ M																									Z N	
Name						RCOTRIM																									RCOBAND	

Bit	Name	Reset	Access	Description
31:29	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
28:24	RCOTRIM	0x10	RW	Reserved for internal use. Do not change.
	Reserved for interna	ıl use. Do not c	hange.	
23:3	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	RCOBAND	0x0	RW	LN Mode RCO Frequency Band Selection
				7: 3~8.95MHz, approximately 0.85MHz/step when the radio is disabled.

10.5.24 EMU_DCDCSYNC - DCDC Read Status Register

Reset, or BOD Reset.

Offset															Bi	t Po	siti	on														
0x078	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	1	10	6	ω	7	9	5	4	3	2	_	0
Reset																										•						0
Access																																22
Name																																DCDCCTRLBUSY

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	DCDCCTRLBUSY	0	R	DCDC CTRL Register Transfer Busy
	Indicates the status o register until this sign		RL transfer	to the EMU OSC clock domain. Software cannot re-write the DCDCCTRL

10.5.25 EMU_VMONAVDDCTRL - VMON AVDD Channel Control

Offset															Bi	t Po	sitic	on														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	1	2 0	, ω	7	9	5	4	က	7	_	0
Reset			•	•	•	•	•			>	3			2	2			>	OX O				0×0			•	•	•	0	0		0
Access										<u> </u>	2			2	<u>}</u>			<u> </u>	<u>}</u>				₽						\ N	RW		RW
Name										PISETHDESCOADSE	ζ				אוואם חדורם חדורם הוא			TAPESCOAPSE	LALLINESCOARSE				FALLTHRESFINE						FALLWU	RISEWU		N H

Bit	Name	Reset	Access	Description
31:24	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
23:20	RISETHRES- COARSE	0x0	RW	Rising Threshold Coarse Adjust
	Check VMON section	n for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
19:16	RISETHRESFINE	0x0	RW	Rising Threshold Fine Adjust
	Check VMON section	n for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
15:12	FALLTHRES- COARSE	0x0	RW	Falling Threshold Coarse Adjust
	Check VMON section	n for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
11:8	FALLTHRESFINE	0x0	RW	Falling Threshold Fine Adjust
	Check VMON section	n for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
7:4	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
3	FALLWU	0	RW	Fall Wakeup
	When set, a wakeup	from EM4H will t	take place	upon a falling edge. Reset with SYSEXTENDEDRESETn.
2	RISEWU	0	RW	Rise Wakeup
	When set, a wakeup	from EM4H will t	take place	upon a rising edge. Reset with SYSEXTENDEDRESETn.
1	Reserved	To ensure cor tions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EN	0	RW	Enable
	Set this bit to enable	the AVDD VMO	N. Reset w	vith SYSEXTENDEDRESETn.

10.5.26 EMU_VMONALTAVDDCTRL - Alternate VMON AVDD Channel Control

Offset															Bi	it Po	siti	on														
0x094	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10		- ∞	7	9	5	4	က	2	_	0
Reset			•	•	•		•		•	•			•	•		•		2) X				000	•			•	•	0	0		0
Access																		Š	} Y				Z.						\ N	₩ M		W.
Name																		T 000	IHKESCOAKSE				THRESFINE						FALLWU	RISEWU		EN

Name	Reset	Access	Description
Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
THRESCOARSE	0x0	RW	Threshold Coarse Adjust
Check VMON section	for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
THRESFINE	0x0	RW	Threshold Fine Adjust
Check VMON section	for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.
Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
FALLWU	0	RW	Fall Wakeup
When set, a wakeup t	from EM4H will t	ake place	upon a falling edge. Reset with SYSEXTENDEDRESETn.
RISEWU	0	RW	Rise Wakeup
When set, a wakeup t	from EM4H will t	ake place	upon a rising edge. Reset with SYSEXTENDEDRESETn.
Reserved	To ensure cor	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
EN	0	RW	Enable
Set this bit to enable t	the ALTAVDD V	MON. Res	et with SYSEXTENDEDRESETn.
	Reserved THRESCOARSE Check VMON section THRESFINE Check VMON section Reserved FALLWU When set, a wakeup to the s	Reserved To ensure contions THRESCOARSE 0x0 Check VMON section for programmin THRESFINE 0x0 Check VMON section for programmin Reserved To ensure contions FALLWU 0 When set, a wakeup from EM4H will the RISEWU 0 When set, a wakeup from EM4H will the Reserved To ensure contions EN 0	Reserved To ensure compatibility to tions THRESCOARSE 0x0 RW Check VMON section for programming the three THRESFINE 0x0 RW Check VMON section for programming the three Reserved To ensure compatibility to tions FALLWU 0 RW When set, a wakeup from EM4H will take place RISEWU 0 RW When set, a wakeup from EM4H will take place Reserved To ensure compatibility to tions

10.5.27 EMU_VMONDVDDCTRL - VMON DVDD Channel Control

Offset	Bit Po	sition
0x098	33 30 30 29 29 29 27 27 27 27 27 27 27 27 27 27 27 27 27	10 4 11 12 14 17 17 17 17 17 17 17 17 17 17 17 17 17
Reset		000 00 0
Access		R R F W
Name		THRESCOARSE THRESFINE FALLWU RISEWU EN

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:12	THRESCOARSE	0x0	RW	Threshold Coarse Adjust
	Check VMON section	n for programmir	ng the thres	shold value. Reset with SYSEXTENDEDRESETn.
11:8	THRESFINE	0x0	RW	Threshold Fine Adjust
	Check VMON section	n for programmir	ng the thres	shold value. Reset with SYSEXTENDEDRESETn.
7:4	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3	FALLWU	0	RW	Fall Wakeup
	When set, a wakeup	from EM4H will	take place	upon a falling edge. Reset with SYSEXTENDEDRESETn.
2	RISEWU	0	RW	Rise Wakeup
	When set, a wakeup	from EM4H will	take place	upon a rising edge. Reset with SYSEXTENDEDRESETn.
1	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EN	0	RW	Enable
	Set this bit to enable	the DVDD VMO	N. Reset w	vith SYSEXTENDEDRESETn.

10.5.28 EMU_VMONIO0CTRL - VMON IOVDD0 Channel Control

Offset	Bit Po	sition
0x09C	33 30 29 28 28 27 27 27 27 27 27 27 19 19 19	17
Reset		000000000000000000000000000000000000000
Access		R R R R R
Name		THRESCOARSE THRESFINE FALLWU RISEWU EN

Bit	Name	Reset	Access	Description											
31:16	Reserved	To ensure cor tions	npatibility ı	with future devices, always write bits to 0. More information in 1.2 Conven-											
15:12	THRESCOARSE	0x0	RW	Threshold Coarse Adjust											
	Check VMON section	for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.											
11:8	THRESFINE	0x0	RW	Threshold Fine Adjust											
	Check VMON section	for programmin	g the thres	shold value. Reset with SYSEXTENDEDRESETn.											
7:5	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-											
4	RETDIS														
	When set, the IO0 ReDEDRESETn.	etention will be d	isabled wh	nen this IO0 voltage drops below the threshold set. Reset with SYSEXTEN-											
3	FALLWU	0	RW	Fall Wakeup											
	When set, a wakeup	from EM4H will t	ake place	upon a falling edge. Reset with SYSEXTENDEDRESETn.											
2	RISEWU	0	RW	Rise Wakeup											
	When set, a wakeup	from EM4H will t	ake place	upon a rising edge. Reset with SYSEXTENDEDRESETn.											
1	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-											
0	EN	0	RW	Enable											
	Set this bit to enable	the IO0 VMON.	Reset with	SYSEXTENDEDRESETn.											

10.5.29 EMU_RAM1CTRL - Memory Control Register

Offset														Bit	t Po	sitio	on														
0x0B4	31	30	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	က	2	_	0
Reset		·	•	•												•	·														0×0
Access																															X ≷
Name																															RAMPOWERDOWN
Bit	Nan	ne				Re	set			Ac	ces	s I	Des	crip	tion																
31:1	Res	served				To tior		ure	con	npati	ibility	y wit	th fu	ture	dev	ices	, alv	vays	s wr	ite b	its t	o 0.	Мог	re in	forn	natic	n in	1.2	Cor	iven)-

31:1	Reserved	To ensure com tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0:0	RAMPOWERDOWN	0x0	RW	RAM1 Blockset Power-down
	RAM blockset power-	down in EM23 w	ith full acc	ess in EM01.
	Value	Mode		Description
	0	NONE		None of the RAM blocks powered down
	1	BLK		Power down RAM block (address range 0x20004000-0x20007FFC)

10.5.30 EMU_RAM2CTRL - Memory Control Register

Offset															Ві	it Po	siti	on														
0x0B8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset		•	•		•	•	•				•		•	•	•	•		•					•		•	•	•	•	•			0x0
Access																																R W
Name																																RAMPOWERDOWN

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0:0	RAMPOWERDOWN	0x0	RW	RAM2 Blockset Power-down
	RAM blockset power-	down in EM23 v	vith full acc	cess in EM01.
	Mode	Value		Description
	NONE	0x00		None of the RAM blocks powered down
	BLK	0x1		Power down RAM blocks 0-3 (address range 0x20040000-0x200407FF)
				·

10.5.31 EMU_DCDCLPEM01CFG - Configuration Bits for Low Power Mode to Be Applied During EM01, This Field is Only Relevant If LP Mode is Used in EM01

Offset															Bi	t Po	sitio	on														
0x0EC	31	30	29	28	27	26	25	24	23	22	21	50	9	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset												•						2	2				6	CX3								
Access																		<u> </u>	2				í	≩								
Name																		- DOMBHYSSEI EM04	LT CIVIT II SSELEIVIO					LPCMPBIASEMU1								
Bit	Na	me					Re	set			Acc	cess	D	es	crip	tion																

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:12	LPCMPHYSSE- LEM01	0x0	RW	LP Mode Hysteresis Selection for EM01
	LP mode hysteresis functions for configur		e output is 4	4*(1+LPATT)*LPCMPHYSSEL*3.13mV. Customers should use the emlib
11:10	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
9:8	LPCMPBIASEM01	0x3	RW	LP Mode Comparator Bias Selection for EM01
	Reserved for internal	use. Do not ch	ange.	
	Value	Mode		Description
	0	BIAS0		Maximum load current less than 75uA.
	1	BIAS1		Maximum load current less than 500uA.
	2	BIAS2		Maximum load current less than 2.5mA.
	3	BIAS3		Maximum load current less than 10mA.
7:0	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

10.5.32 EMU_EM23PERNORETAINCMD - Clears Corresponding Bits in EM23PERNORETAINSTATUS Unlocking Access to Peripheral

Offset															Ві	t Po	siti	on														
0x100	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	7	_	0
Reset																	0		0	0	0	0	0	0	0		0		•	0	0	0
Access																	M		W1	W1	W1	W1	M1	W1	W1		W1			W1	W1	M1
Name																	LEUART0UNLOCK		LESENSE0UNLOCK	WDOG1UNLOCK	WDOGOUNLOCK	LETIMEROUNLOCK	ADC0UNLOCK	IDAC0UNLOCK	DACOUNLOCK		I2C0UNLOCK			PCNT0UNLOCK	ACMP1UNLOCK	ACMPOUNLOCK

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15	LEUART0UNLOCK	0	W1	Clears Status Bit of LEUART0 and Unlocks Access to It
	clears status bit of LE	UART0 and unl	ocks acces	es to it
14	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13	LESENSE0UNLOCK	0	W1	Clears Status Bit of LESENSE0 and Unlocks Access to It
	clears status bit of LE	SENSE0 and ur	nlocks acce	ess to it
12	WDOG1UNLOCK	0	W1	Clears Status Bit of WDOG1 and Unlocks Access to It
	clears status bit of WI	OOG1 and unloa	cks access	to it
11	WDOG0UNLOCK	0	W1	Clears Status Bit of WDOG0 and Unlocks Access to It
	clears status bit of WI	OOG0 and unloc	cks access	to it
10	LETIMEROUNLOCK	0	W1	Clears Status Bit of LETIMER0 and Unlocks Access to It
	clears status bit of LE	TIMER0 and un	locks acce	ess to it
9	ADC0UNLOCK	0	W1	Clears Status Bit of ADC0 and Unlocks Access to It
	clears status bit of AD	C0 and unlocks	access to	it
8	IDAC0UNLOCK	0	W1	Clears Status Bit of IDAC0 and Unlocks Access to It
	clears status bit of IDA	AC0 and unlock	s access to	o it
7	DAC0UNLOCK	0	W1	Clears Status Bit of DAC0 and Unlocks Access to It
	clears status bit of DA	C0 and unlocks	access to	it
6	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	I2C0UNLOCK	0	W1	Clears Status Bit of I2C0 and Unlocks Access to It
	clears status bit of I20	00 and unlocks	access to it	t
4:3	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	PCNT0UNLOCK	0	W1	Clears Status Bit of PCNT0 and Unlocks Access to It
	clears status bit of PC	NT0 and unlock	s access t	o it

Bit	Name	Reset	Access	Description									
1	ACMP1UNLOCK	0	W1	Clears Status Bit of ACMP1 and Unlocks Access to It									
	clears status bit of ACMP1 and unlocks access to it												
0	ACMP0UNLOCK	0	W1	Clears Status Bit of ACMP0 and Unlocks Access to It									
	clears status bit of AC	clears status bit of ACMP0 and unlocks access to it											

10.5.33 EMU_EM23PERNORETAINSTATUS - Status Indicating If Peripherals Were Powered Down in EM23, Subsequently Locking Access to It

Offset	Bit Position																															
0x104	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset								•							•		0		0	0	0	0	0	0	0		0		•	0	0	0
Access																	22		2	2	Ж	22	2	2	2		2			22	22	2
Name																	LEUARTOLOCKED		LESENSE0LOCKED	WDOG1LOCKED	WDOG0LOCKED	LETIMEROLOCKED	ADC0LOCKED	IDACOLOCKED	DACOLOCKED		12C0LOCKED			PCNT0LOCKED	ACMP1LOCKED	ACMP0LOCKED

				LEUA WDOO WDOO WDOO IDACO IDACO IZCOL IZCOL
Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15	LEUART0LOCKED	0	R	Indicates If LEUART0 Powered Down During EM23
	Indicates if LEUARTO NORETAINCMD	powered down	during EM	123. Access to this peripheral locked until this bit cleared using EM23PER-
14	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
13	LESENSE0LOCKED	0	R	Indicates If LESENSE0 Powered Down During EM23
	Indicates if LESENSE NORETAINCMD	0 powered dow	n during E	M23. Access to this peripheral locked until this bit cleared using EM23PER-
12	WDOG1LOCKED	0	R	Indicates If WDOG1 Powered Down During EM23
	Indicates if WDOG1 p	oowered down d	luring EM2	3. Access to this peripheral locked until this bit cleared using EM23PER-
11	WDOG0LOCKED	0	R	Indicates If WDOG0 Powered Down During EM23
	Indicates if WDOG0 p	oowered down d	luring EM2	3. Access to this peripheral locked until this bit cleared using EM23PER-
10	LETIMER0LOCKED	0	R	Indicates If LETIMER0 Powered Down During EM23
	Indicates if LETIMER NORETAINCMD	0 powered dow	n during EN	M23. Access to this peripheral locked until this bit cleared using EM23PER-
9	ADC0LOCKED	0	R	Indicates If ADC0 Powered Down During EM23
	Indicates if ADC0 pov ETAINCMD	vered down duri	ing EM23.	Access to this peripheral locked until this bit cleared using EM23PERNOR-
8	IDAC0LOCKED	0	R	Indicates If IDAC0 Powered Down During EM23
	Indicates if IDAC0 po ETAINCMD	wered down dui	ring EM23.	Access to this peripheral locked until this bit cleared using EM23PERNOR-
7	DAC0LOCKED	0	R	Indicates If DAC0 Powered Down During EM23
	Indicates if DAC0 pov ETAINCMD	vered down duri	ing EM23.	Access to this peripheral locked until this bit cleared using EM23PERNOR-
6	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
5	I2C0LOCKED	0	R	Indicates If I2C0 Powered Down During EM23
	Indicates if I2C0 power TAINCMD	ered down durin	g EM23. A	ccess to this peripheral locked until this bit cleared using EM23PERNORE-
4:3	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	PCNT0LOCKED	0	R	Indicates If PCNT0 Powered Down During EM23
	Indicates if PCNT0 po NORETAINCMD	owered down du	ring EM23.	Access to this peripheral locked until this bit cleared using EM23PER-
1	ACMP1LOCKED	0	R	Indicates If ACMP1 Powered Down During EM23
	Indicates if ACMP1 po	owered down du	ıring EM23	. Access to this peripheral locked until this bit cleared using EM23PER-
0	ACMP0LOCKED	0	R	Indicates If ACMP0 Powered Down During EM23
	Indicates if ACMP0 po NORETAINCMD	owered down du	ıring EM23	. Access to this peripheral locked until this bit cleared using EM23PER-

10.5.34 EMU_EM23PERNORETAINCTRL - When Set Corresponding Peripherals May Get Powered Down in EM23


Offset	Bit Position																															
0x108	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	æ	7	9	2	4	က	2	_	0
Reset			'	•								•		'			0		0	0	0	0	0	0	0		0			0	0	0
Access																	₩ M		₹ Š	Σ	₽	₽	₽	₽	Z M		₽			₽	₽	RW W
Name																	LEUARTODIS		LESENSE0DIS	WDOG1DIS	WDOG0DIS	LETIMERODIS	ADCODIS	IDACODIS	VDAC0DIS		ISCODIS			PCNT0DIS	ACMP1DIS	ACMPODIS

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15	LEUART0DIS	0	RW	Allow Power Down of LEUART0 During EM23
	Allow power down of	of LEUART0 during	g EM23	
14	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13	LESENSE0DIS	0	RW	Allow Power Down of LESENSE0 During EM23
	Allow power down of	of LESENSE0 durin	ng EM23	
12	WDOG1DIS	0	RW	Allow Power Down of WDOG1 During EM23
	Allow power down o	of WDOG1 during I	EM23	
11	WDOG0DIS	0	RW	Allow Power Down of WDOG0 During EM23
	Allow power down o	of WDOG0 during I	EM23	
10	LETIMER0DIS	0	RW	Allow Power Down of LETIMER0 During EM23
	Allow power down of	of LETIMER0 durin	g EM23	
9	ADC0DIS	0	RW	Allow Power Down of ADC0 During EM23
	Allow power down of	of ADC0 during EM	123	
8	IDAC0DIS	0	RW	Allow Power Down of IDAC0 During EM23
	Allow power down o	of IDAC0 during EN	И23	
7	VDAC0DIS	0	RW	Allow Power Down of DAC0 During EM23
	Allow power down of	of DAC0 during EM	123	
6	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	I2C0DIS	0	RW	Allow Power Down of I2C0 During EM23
	Allow power down o	of I2C0 during EM2	23	
4:3	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	PCNT0DIS	0	RW	Allow Power Down of PCNT0 During EM23
	Allow power down of	of PCNT0 during E	M23	

Bit	Name	Reset	Access	Description
1	ACMP1DIS	0	RW	Allow Power Down of ACMP1 During EM23
	Allow power down	n of ACMP1 durir	ng EM23	
)	ACMP0DIS	0	RW	Allow Power Down of ACMP0 During EM23
	Allow power down	n of ACMP0 durir	ng EM23	

11. CMU - Clock Management Unit





Quick Facts

What?

The CMU controls oscillators and clocks. EFR32 supports 6 different oscillators with minimized power consumption and short start-up time. The CMU has HW support for calibration of RC oscillators.

Why?

Oscillators and clocks contribute significantly to the power consumption of an MCU. Low power oscillators combined with a flexible clock control scheme make it possible to minimize the energy consumption in any given application.

How?

The CMU can configure different clock sources, enable/disable clocks to peripherals on an individual basis and set the prescaler for the different clocks. The short oscillator start-up times makes duty-cycling between active mode and the different low energy modes (EM2 Deep Sleep, EM3 Stop, and EM4 Hibernate/Shutoff) very efficient. The calibration feature ensures high accuracy RC oscillators. Several interrupts are available to avoid CPU polling of flags.

11.1 Introduction

The Clock Management Unit (CMU) is responsible for controlling the oscillators and clocks in the EFR32. The CMU provides the capability to turn on and off the clock on an individual basis to all peripheral modules in addition to enable/disable and configure the available oscillators. The high degree of flexibility enables software to minimize energy consumption in any specific application by not wasting power on peripherals and oscillators that do not need to be active.

11.2 Features

- · Multiple clock sources available:
 - 38 MHz 40 MHz High Frequency Crystal Oscillator (HFXO)
 - 1 MHz 38 MHz High Frequency RC Oscillator (HFRCO)
 - 1 MHz 38 MHz Auxiliary High Frequency RC Oscillator (AUXHFRCO)
 - 32768 Hz Low Frequency Crystal Oscillator (LFXO)
 - 32768 Hz Low Frequency RC Oscillator (LFRCO)
 - 1000 Hz Ultra Low Frequency RC Oscillator (ULFRCO)
- · All oscillator sources are low power.
- · Fast start-up times.
- Separate prescalers for High Frequency Core Clocks (HFCORECLK), Radio Clocks (HFRADIOCLK), and Peripheral Clocks (HFPERCLK).
- Individual clock prescaler selection for each Low Energy Peripheral.
- · Clock gating on an individual basis to core modules and all peripherals.
- · Selectable clock output to external pins and/or PRS.
- Wakeup interrupt for LFRCO or LFXO ready allows entry into EM2 Deep Sleep while waiting for low-frequency oscillator startup.
 This avoids the need for software polling and saves power during oscillator startup.
- Auxiliary 1 MHz 38 MHz RC oscillator (AUXHFRCO), which is asynchronous to the HFSRCCLK system clock, can be selected for ADC operation, LESENSE timing and debug trace.

11.3 Functional Description

An overview of the high frequency portion of the CMU is shown in Figure 11.1 CMU Overview - High Frequency Portion on page 279. An overview of the low frequency portion is shown in Figure 11.2 CMU Overview - Low Frequency Portion on page 280. These figures show the CMU for the largest device in the EFR32 family. Refer to the Configuration Summary in the device data sheet to see which core, radio, and peripheral modules, and therefore clock connections, are present in a specific device.




Figure 11.1. CMU Overview - High Frequency Portion




Figure 11.2. CMU Overview - Low Frequency Portion

11.3.1 System Clocks

Available system clock sources are detailed in the following sections.

11.3.1.1 HFCLK - High Frequency Clock

HFSRCCLK is the selected High Frequency Source Clock. HFCLK is an optionally prescaled version of HFSRCCLK. The HFSRCCLK, and therefore HFCLK, can be driven by a high-frequency oscillator, such as HFRCO or HFXO, or one of the low-frequency oscillators (LFRCO or LFXO). Additionally, HFSRCCLK can also be driven from a pin (CLKINO) described in 11.3.6 Clock Input From a Pin. By default the HFRCO is selected. In most applications, one of the high frequency oscillators will be the preferred choice. To change the selected clock source, write to the HF bitfield in CMU_HFCLKSEL. The high frequency clock source can also be changed automatically by hardware as explained in 11.3.2.4.1 Automatic HFXO Start. The currently selected source for HFSRCCLK and HFCLK can be read from CMU_HFCLKSTATUS. The HFSRCCLK is running in EM0 Active and EM1 Sleep and is automatically stopped in EM2 Deep Sleep. During Voltage Scaling (see 10.3.9 Voltage Scaling), if a fixed frequency oscillator source (i.e. HFXO or CLKINO) exceeds the maximum system frequency supported, it must be disabled or not selected. Likewise, an adjustable oscillator source (i.e. HFRCO or AUXHFRCO) must be configured to not exceed the maximum system frequency supported before voltage scaling is applied.

Note: If a low frequency clock (i.e. LFRCO or LFXO) is selected as source clock for HFSRCCLK via the HF bitfield in CMU_HFCLKSEL, then no register reads should be performed from Low Energy Peripherals for registers which can change value every clock cycle (e.g., a counter register). In addition to the peripherals on LFACLK, LFBCLK and LFECLK, this restriction applies in general to any low frequency peripheral, which is not directly or indirectly clocked from HFSRCCLK (e.g., WDOGn).

HFCLK can optionally be prescaled by setting PRESC in CMU_HFPRESC to a non-zero value. This prescales HFCLK to all high frequency components and is typically used to save energy in applications where the system is not required to run at the highest frequency. The prescaler setting can be changed dynamically and the new setting takes effect immediately. HFCLK is used by the CMU and drives the prescalers that generate HFCORECLK, HFRADIOCLK and HFPERCLK allowing for flexible clock prescaling. The HFBUSCLK, used in for example the bus and memory system, is equal to HFCLK.

The HFXO clock is fed directly to the Radio Transceiver. The clock received by the Radio Transceiver is therefore not affected by the selected clock source for HFSRCCLK nor by any clock prescaler.

11.3.1.2 HFCORECLK - High Frequency Core Clock

HFCORECLK is a prescaled version of HFCLK. This clock drives the Core Modules, which consists of the CPU and modules that are tightly coupled to the CPU (e.g., the cache). The prescale factor for prescaling HFCLK into HFCORECLK is set using the CMU_HFCOREPRESC register. The setting can be changed dynamically and the new setting takes effect immediately.

Note: If HFPERCLK or HFRADIOCLK runs faster than HFCORECLK, the number of clock cycles for each bus-access to (radio) peripheral modules will increase with the ratio between the clocks. Refer to 4.2.5 Bus Matrix for more details.

11.3.1.3 HFBUSCLK - High Frequency Bus Clock

HFBUSCLK is equal to HFCLK. This clock drives the Bus and Memory System. HFBUSCLK is also used to drive the bus interface to the Low Energy Peripherals as described further in 11.3.1.7 LFACLK - Low Frequency a Clock, 11.3.1.8 LFBCLK - Low Frequency B Clock and 11.3.1.9 LFECLK - Low Frequency E Clock. Some of the modules that are driven by this clock can be clock gated completely when not in use. This is done by clearing the clock enable bit for the specific module in CMU_HFBUSCLKEN0. The frequency of HFBUSCLK is equal to the frequency of HFCLK and can therefore only be prescaled by using the PRESC bitfield in CMU_HFPRESC.

11.3.1.4 HFPERCLK - High Frequency Peripheral Clock

Like HFCORECLK, HFPERCLK is a prescaled version of HFCLK. This clock drives the High-Frequency Peripherals. All the peripherals that are driven by this clock can be clock gated individually when not in use. This is done by clearing the clock enable bit for the specific peripheral in CMU_HFPERCLKEN0. All high frequency peripheral clocks can be universally and simultaneously gated by clearing the HFPERCLKEN bit in the CMU_CTRL register. The prescale factor for prescaling HFCLK into HFPERCLK is set using the CMU_HFPERPRESC register. The setting can be changed dynamically and the new setting takes effect immediately.

Note: If HFPERCLK runs faster than HFCORECLK, the number of clock cycles for each bus-access to peripheral modules will increase with the ratio between the clocks. For example, if a bus-access normally takes three cycles, it will take 9 cycles of HFCORECLK if HFPERCLK runs three times as fast as HFCORECLK.

11.3.1.5 HFRADIOCLK - High Frequency Radio Clock

HFRADIOCLK is a prescaled version of HFCLK which drives the High-Frequency Radio Peripherals. All the radio peripherals that are driven by this clock can be clock gated completely when not in use. This is done by clearing the clock enable bit for the specific peripheral in CMU_HFRADIOCLKENO. The radio peripherals can also be gated simultaneously by clearing the HFRADIOCLKEN bit in the CMU_CTRL register. The prescale factor for prescaling HFCLK into HFRADIOCLK is set using the CMU_HFRADIOPRESC register. The setting can be changed dynamically and the new setting takes effect immediately.

Note: If HFRADIOCLK runs faster than HFCORECLK, the number of clock cycles for each bus-access to radio peripheral modules will increase with the ratio between the clocks. E.g. if a bus-access normally takes three cycles, it will take 9 cycles if HFRADIOCLK runs three times as fast as the HFCORECLK.

11.3.1.6 ADCnCLK - ADC Core Clock

ADCnCLK is a selectable core clock for ADCn. There are three selectable sources for ADCnCLK: HFSRCCLK, HFXO and AUXHFR-CO. In addition, the ADCnCLK can be disabled, which is the default setting. The selection is configured using the ADCnCLKSEL field in CMU_ADCCTRL. The ADCnCLKINV bit in CMU_ADCCTRL can be used to invert ADCnCLK. The ADCnCLKDIV bitfield in CMU_ADCCTRL can be used to prescale ADCnCLK. The bus interface of ADCn is clocked with HFBUSCLK.

11.3.1.7 LFACLK - Low Frequency a Clock

LFACLK is the selected clock for the Low Energy A Peripherals. There are several selectable sources for LFACLK: LFRCO, LFXO and ULFRCO. In addition, the LFACLK can be disabled, which is the default setting. The selection is configured using the LFA field in CMU LFACLKSEL.

The bus interface to the Low Energy A Peripherals is clocked by HFBUSCLK_{LE} and this clock therefore needs to be enabled when programming a Low Energy (LE) peripheral.

Each Low Energy Peripheral that is clocked by LFACLK has its own prescaler setting and enable bit. The prescaler settings are configured using CMU LFAPRESC0 and the clock enable bits can be found in CMU LFACLKEN0.

When operating in oversampling mode, the pulse counters are clocked by LFACLK. This is configured for each pulse counter (n) individually by setting PCNTnCLKSEL in CMU PCNTCTRL.

11.3.1.8 LFBCLK - Low Frequency B Clock

LFBCLK is the selected clock for the Low Energy B Peripherals. There are several selectable sources for LFBCLK: LFRCO, LFXO, HFCLKLE and ULFRCO. In addition, the LFBCLK can be disabled, which is the default setting. The selection is configured using the LFB field in CMU_LFBCLKSEL. The HFCLKLE setting allows the Low Energy B Peripherals to be used as high-frequency peripherals.

The bus interface to the Low Energy B Peripherals is clocked by HFBUSCLK_{LE} and this clock therefore needs to be enabled when programming a LE peripheral.

Note: If HFCLKLE is selected as LFBCLK, the clock will stop in EM2 Deep Sleep and EM3 Stop.

Each Low Energy Peripheral that is clocked by LFBCLK has its own prescaler setting and enable bit. The prescaler settings are configured using CMU_LFBPRESC0 and the clock enable bits can be found in CMU_LFBCLKEN0.

11.3.1.9 LFECLK - Low Frequency E Clock

LFECLK is the selected clock for the Low Energy E Peripherals. There are several selectable sources for LFECLK: LFRCO, LFXO and ULFRCO. In addition, the LFECLK can be disabled, which is the default setting. The selection is configured using the LFE field in CMU_LFECLKSEL.

The bus interface to the Low Energy E Peripherals is clocked by HFBUSCLK_{LE} and this clock therefore needs to be enabled when programming a LE peripheral.

Note: LFECLK is in a different power domain than LFACLK and LFBCLK, which makes it available all the way down to EM4 Hibernate.

Each Low Energy Peripheral that is clocked by LFECLK has its own prescaler setting and enable bit. The prescaler settings are configured using CMU LFEPRESC0 and the clock enable bits can be found in CMU LFECLKEN0.

11.3.1.10 PCNTnCLK - Pulse Counter N Clock

Each available pulse counter is driven by its own clock, PCNTnCLK where n is the pulse counter instance number. Each pulse counter can be configured to use an external pin (PCNTn_S0) or LFACLK as PCNTnCLK.

11.3.1.11 WDOGnCLK - Watchdog Timer Clock

The Watchdog Timer (WDOGn) can be configured to use one of many different clock sources. Refer to CLKSEL field in WDOGn_CTRL for a complete list.

11.3.1.12 CRYOCLK - CRYOTIMER Clock

The CRYOTIMER clock can be configured to use one of many different clock sources. Refer to OSCSEL field in CRYOTIMER_CTRL for a complete list. The CRYOTIMER can also run in EM4 Hibernate/Shutoff provided that its selected clock is kept enabled as configured in EMU_EM4CTRL.

11.3.1.13 AUXCLK - Auxiliary Clock

AUXCLK is a 1 MHz - 38 MHz clock driven by a separate RC oscillator, the AUXHFRCO. This clock can be used for ADC operation LESENSE operation. When the AUXHFRCO is selected as the ADCn clock via the ADCnCLKSEL bitfield in the CMU_ADCCTRL register, or if needed by LESENSE, this clock will become active automatically when needed. Even if the AUXHFRCO has not been enabled explicitly by software, the ADC or LESENSE can automatically start and stop it. The AUXHFRCO is explicitly enabled by writing a 1 to AUXHFRCOEN in CMU_OSCENCMD. This explicit enabling is required when selecting the AUXCLK for SWO operation.

11.3.1.14 Debug Trace Clock

The CMU selects the clock used for debug trace via the DBGCLKSEL register. The user can useAUXHFRCO or the HFCLK. The selected debug trace clock will be used to run the Cortex-M4 trace logic.

Note: When using AUXHFRCO as the debug trace clock, it must be stopped before entering EM2 or EM3.

11.3.2 Oscillators

Control of the various oscillators available in the device is detailed in the following sections.

11.3.2.1 Enabling and Disabling

The different oscillators can typically be enabled and disabled via both hardware and software mechanisms. Enabling via software is done by setting the corresponding enable bit in the CMU_OSCENCMD register. Disabling via software is done by setting the corresponding disable bit in CMU_OSCENCMD. Enabling via hardware can be performed by various peripherals and varies per oscillator. Disabling via hardware is typically performed on entry of low energy modes. The enable and disable mechanisms for each of the oscillators are summarized in Table 11.1 Software Based and Hardware Based Enabling and Disabling of Oscillators on page 284 and described in more detail below.

Table 11.1. Software Based and Hardware Based Enabling and Disabling of Oscillators

Oscillator	SW Enable	SW Disable	HW Enable	HW Disable
ULFRCO	-	-	Enabled when in EM0/EM1/EM2/EM3/ EM4H.	EM4S entry depending on configuration in EMU_EM4CTRL.
LFRCO	Via LFRCOEN in CMU_OSCENCMD.	Via LFRCODIS in CMU_OSCENCMD.	Via WDOGn if it is configured to use LFRCO as its clock source via the CLKSEL bitfield in WDOGn_CTRL while SWOSCBLOCK is set.	EM3 entry. EM4 entry depending on configuration in EMU_EM4CTRL.
LFXO	Via LFXOEN in CMU_OSCENCMD.	Via LFXODIS in CMU_OSCENCMD.	Via WDOGn if it is configured to use LFXO as its clock source via the CLKSEL bitfield in WDOGn_CTRL while SWOSCBLOCK is set.	EM3 entry. EM4 entry depending on configuration in EMU_EM4CTRL.
HFRCO	Via HFRCOEN in CMU_OSCENCMD.	Via HFRCODIS in CMU_OSCENCMD.	Reset exit. EM2/EM3 exit. Automatic control by LEUART RX/TX DMA wake-up as configured in LEUARTn_CTRL.	EM2/EM3/EM4 entry. Automatic control by LEUART RX/TX DMA wake-up as configured in LEUARTn_CTRL. Automatic start and selection of HFXO causes HFRCO disable.
AUXHFRCO	Via AUXHFRCOEN in CMU_OSCENCMD.	Via AUXHFRCODIS in CMU_OSCENCMD.	Automatic control by ADC and LESENSE.	EM2/EM3/EM4 entry. Automatic control by ADC and LESENSE even in EM2/EM3.
HFXO	Via HFXOEN in CMU_OSCENCMD.	Via HFXODIS in CMU_OSCENCMD.	Automatic start by Radio Controller (RAC) or EM0/EM1 entry as con- figured in CMU_HFXOCTRL.	EM2/EM3/EM4 entry.

11.3.2.1.1 LFRCO and LFXO

The LFXO and LFRCO can be enabled and disabled by software via the CMU_OSCENCMD register. WDOGn can be configured to force the LFXO or LFRCO to become (and remain) enabled when such an oscillator is selected as its clock source via the CLKSEL bitfield in the WDOGn_CTRL register while SWOSCBLOCK is set. In that case LFXODIS and LFRCODIS commands are blocked. They are automatically disabled when entering EM3. Upon EM4 entry they are default turned off, but they can optionally be retained depending on the EMU_EM4CTRL configuration. Retaining of the LFXO or LFRCO in EM4 is needed if such an oscillator is required by a specific peripheral in EM4. Retaining can also be used to guarantee guick oscillator availability after EM4 exit.

The oscillators should never be retained in case they are off before entering EM4. The following are the valid ways of using the LFXO/LFRCO retention mechanism:

- Turn on LFXO/LFRCO always (even in EM4):
 - 1. POR
 - 2. Enable LFXO/LFRCO
 - 3. Enable RETAINLFXO/RETAINLFRCO
 - 4. EM4 entry
 - 5. LFXO/LFRCO are retained and remain running in EM4
 - 6. EM4 wakeup
 - 7. Enable LFXO/LFRCO
 - 8. Set EM4UNLATCH in EMU CMD
- Turn off LFXO/LFRCO in EM4:
 - 1. POR
 - 2. Disable RETAINLFXO/RETAINLFRCO (default)
 - 3. Enable LFXO/LFRCO
 - 4. EM4 entry
 - 5. LFXO/LFRCO are off in EM4
 - 6. EM4 wakeup
 - 7. Enable LFXO/LFRCO
 - 8. Set EM4UNLATCH in EMU CMD
- · Turn on LFXO/LFRCO after EM4 exit:
 - 1. POR
 - 2. Disable RETAINLFXO/RETAINLFRCO (default)
 - 3. Enable LFXO/LFRCO
 - 4. EM4 entry
 - 5. LFXO/LFRCO are off in EM4
 - 6. EM4 wakeup
 - 7. Enable LFXO/LFRCO
 - 8. Set EM4UNLATCH in EMU_CMD
 - 9. Enable RETAINLFXO/RETAINLFRCO

In summary RETAINLFXO/RETAINLFRCO should either be changed once after POR and kept static, or they can be changed on-the-fly only after asserting EM4UNLATCH.

Note:

- In order to support usage of LFRCO and LFXO in EM4, their settings are automatically latched upon EM4 entry. These settings
 remain latched upon wake-up from EM4 to EM0 although the related registers (CMU_LFRCOCTRL, CMU_LFXOCTRL,
 CMU_LFECLKSEL, CMU_LFECLKEN0 and CMU_LEEPRESC0) will have been reset. The registers can be rewritten by software,
 but they will only affect the LFRCO and LFXO after unlatching their settings by setting EM4UNLATCH in the EMU_CMD register.
- Turning off the LFRCO and LFXO upon EM4 Hibernate/Shutoff entry is most easily done by using the RETAINLFRCO and RETAINLFXO bitfields from the EMU_EM4CTRL register, which are default such that the LFRCO and LFXO are turned off automatically upon EM4 Hibernate/Shutoff entry. Alternatively the LFRCO and LFXO can be disabled via the CMU_OSCENCMD register, in which case software should wait for the oscillators to be properly disabled before executing the EM4 Hibernate/Shutoff entry routine.

After enabling the LFRCO (or LFXO), it should not be disabled before it has been signaled to be ready. Similarly, after disabling the LFRCO (or LFXO), it should not be re-enabled before it has been signaled to be non-ready. Before entering EM4, software should check that the LFRCO (or LFXO) is signaled to be ready before allowing or initiating the EM4 entry if that oscillator is required in EM4. Also, to guarantee latching the latest settings, no control write should be ongoing upon EM4 entry as can be checked via the CMU SYNCBUSY register. Typical enable and disable sequences are as follows:

```
CMU->OSCENCMD = CMU_OSCENCMD_LFRCOEN;
while ((CMU->STATUS & CMU_STATUS_LFRCORDY) != CMU_STATUS_LFRCORDY);

CMU->OSCENCMD = CMU_OSCENCMD_LFRCODIS;
while ((CMU->STATUS & CMU_STATUS_LFRCORDY) == CMU_STATUS_LFRCORDY);
```

When the LFXO is disabled, the interface to the LFXTAL_N and LFXTAL_P pins are set in a high-Z state. The XTAL oscillations will not stop immediately when LFXO is disabled, but typically die out gradually over some 100 ms. If the LFXO is enabled before XTAL oscillations have had time to reach zero amplitude, startup time can be significantly shorter.

Note: The LFRCORDY and LFXORDY interrupts can be used to wake up the system from EM2 Deep Sleep. In this way busy waiting for the LFRCO or LFXO to become ready can be avoided by going into EM2 after enabling these oscillators and sleeping until the interrupt causes a wakeup.

11.3.2.1.2 ULFRCO

The ULFRCO is automatically enabled in EM0, EM1, EM2, EM3, and EM4H and cannot be controlled via CMU_OSCENCMD. It is automatically disabled upon entering EM4S unless prevented by the configuration in EMU_EM4CTRL.

11.3.2.1.3 HFRCO

The HFRCO can be enabled and disabled by software via the CMU_OSCENCMD register. The HFRCO is disabled automatically when entering EM2, EM3, or EM4. Further hardware based enabling and disabling can be performed by the LEUART when using automatic RX/TX DMA wakeup as controlled by the RXDMAWU and TXDMAWU bits in the LEUARTn_CTRL register. An automatic start and selection of the HFXO will lead to an automatic HFRCO disabling.

The supported HFRCO frequency range is from 1 MHz to 38 MHz. The default HFRCO frequency is 19 MHz

11.3.2.1.4 HFXO

The HFXO can be enabled and disabled by software via the CMU_OSCENCMD register. The HFXO is disabled automatically when entering EM2, EM3, or EM4. Hardware based HFXO enabling can be initiated by various peripherals as configured via the AUTOSTARTRDYSELRAC, AUTOSTARTEM0EM1, and AUTOSTARTSELEM0EM1 bits in the CMU_HFXOCTRL register. The interaction between hardware based and software based control of the HFXO is further explained in 11.3.2.4.1 Automatic HFXO Start.

The supported HFXO frequency range is from 38 MHz to 40 MHz.

After enabling the HFXO, it should not be disabled before it has been signaled to be enabled. Similarly, after disabling the HFXO it should not be re-enabled before it has been signaled to be non-enabled. Typical enable and disable sequences are as follows:

```
CMU->OSCENCMD = CMU_OSCENCMD_HFXOEN;
while ((CMU->STATUS & CMU_STATUS_HFXOENS) != CMU_STATUS_HFXOENS);

CMU->OSCENCMD = CMU_OSCENCMD_HFXODIS;
while ((CMU->STATUS & CMU_STATUS_HFXOENS) == CMU_STATUS_HFXOENS);
```

11.3.2.1.5 AUXHFRCO

The AUXHFRCO can be enabled and disabled by software via the CMU_OSCENCMD register. The AUXHFRCO is disabled automatically when entering EM2, EM3, or EM4. Hardware based AUXHFRCO enabling and disabling is however performed by the ADC module when AUXCLK is selected for its operation and by the LESENSE module making it available even when being in EM2/EM3.

The supported AUXHFRCO frequency range is from 1 MHz to 38 MHz. The default AUXHFRCO frequency is 19 MHz

After enabling the AUXHFRCO, it should not be disabled before it has been signaled to be enabled. Similarly, after disabling the AUXHFRCO, it should not be re-enabled before it has been signaled to be non-enabled. Typical enable and disable sequences are as follows:

```
CMU->OSCENCMD = CMU_OSCENCMD_AUXHFRCOEN;
while ((CMU->STATUS & CMU_STATUS_AUXHFRCOENS) != CMU_STATUS_AUXHFRCOENS);

CMU->OSCENCMD = CMU_OSCENCMD_AUXHFRCODIS;
while ((CMU->STATUS & CMU_STATUS_AUXHFRCOENS) == CMU_STATUS_AUXHFRCOENS);
```

Note: When using AUXHFRCO as the debug trace clock (as selected in CMU_DBGCLKSEL), it must be stopped before entering EM2 or EM3.

11.3.2.2 Oscillator Start-up Time and Time-out

The start-up time differs per oscillator and the usage of an oscillator clock can further be delayed by a time-out. The LFRCO, LFXO and the HFXO have a configurable time-out which is set by software in the (various) TIMEOUT bitfields of the CMU_LFRCOCTRL, CMU_LFXOCTRL and CMU_HFXOTIMEOUTCTRL registers respectively. The time-out delays the assertion of the READY signal for LFRCO, LFXO and HFXO and should allow for enough time for the oscillator to stabilize. The time-out can be optimized for the chosen crystal (for LFXO and HFXO) used in the application. In case LFRCO and/or LFXO has been retained throughout EM4 Hibernate/Shutoff, such retained oscillators can be quickly restarted for use as LFACLK, LFBCLK or LFECLK by using the minimum TIMEOUT settings for them. For the other RC oscillators (HFRCO, AUXHFRCO, and ULFRCO), the start-up time is known and a fixed time-out is used.

There are individual bits in the CMU STATUS register for each oscillator indicating the status of the oscillator:

- · ENABLED Indicates that the oscillator is enabled
- · READY Start-up time including time-out is exceeded

These status bits are located in the CMU STATUS register.

Additionaly, the HFXO has a second time-out counter which can be used to achieve deterministic start-up time based on timing from the LFXO, ULFRCO, or LFRCO. This second counter runs off LFECLK and can be programmed via the LFTIMEOUT bitfield in the CMU_HFXOCTRL register. It can be used when waking up from EM2 when either ULFRCO, LFRCO or LFXO is already running and stable. In this case the HFXO ready assertion can be delayed with the number of LFECLK cycles as programmed in LFTIMEOUT. The HFXO ready signal is asserted when both the TIMEOUT counter (configured via the CMU_HFXOTIMEOUTCTRL register) and the LFTIMEOUT counter (configured via CMU_HFXOCTRL register) have timed out as shown in Figure 11.3 CMU Deterministic HFXO startup using LFTIMEOUT on page 288. The TIMEOUT should cover the actual crystal startup time. Typically the time base used for the TIMEOUT counter is not as accurate as the time base accuracy that can be achieved for the LFTIMEOUT counter, specifically if that one is based on the LFXO timing. If LFTIMEOUT is triggered before TIMEOUT is triggered, then the LFTIMEOUTERR bitfield in CMU_IF will be set to 1. Note that use of LFTIMEOUT requires that the peripheral causing the wake-up is on the LFECLK domain. The intended use scenario is for example to wake up from EM2 by the RTCC triggering RAC wake-up via the PRS, which in turn can wake up the entire system. The RAC wake-up causes an automatic start of the HFXO in case the AUTOSTARTRDYSELRAC bit in CMU_HFXOCTRL is set to 1. Assertion of the HFXO ready signal, and therefore the radio start timing, can then be made deterministic by using LFTIMEOUT.




Figure 11.3. CMU Deterministic HFXO startup using LFTIMEOUT

The startup behavior of the HFXO also depends on how and how long the HFXO is disabled. This can be controlled by configuring the XTI2GND, and XTO2GND bitfields in the CMU_HFXOCTRL register.

11.3.2.3 Switching Clock Source

The HFRCO oscillator is a low energy oscillator with extremely short start-up time. Therefore, this oscillator is always chosen by hardware as the clock source for HFCLK when the device starts up (e.g., after reset and after waking up from EM2 Deep Sleep and EM3 Stop). After reset, the HFRCO frequency is 19 MHz.

Software can switch between the different clock sources at run-time. For example, when the HFRCO is the clock source, software can switch to HFXO by writing the field HF in the CMU_HFCLKSEL command register. See Figure 11.4 CMU Switching from HFRCO to HFXO before HFXO is ready on page 289 for a description of the sequence of events for this specific operation.

Note: Before switching the HFCLKSRC to HFXO via the HF bitfield in CMU_HFCLKSEL it is important to first enable the HFXO. Switching to a disabled oscillator will effectively stop HFSRCCLK and only a reset can recover the system.

When selecting an oscillator which has been enabled, but which is not ready yet, the HFSRCCLK will stop for the duration of the oscillator start-up time since the oscillator driving it is not ready. This effectively stalls the Core Modules and the High-Frequency Peripherals. It is possible to avoid this by first enabling the target oscillator (e.g., HFXO) and then waiting for that oscillator to become ready before switching the clock source. This way, the system continues to run on the HFRCO until the target oscillator (e.g., HFXO) has timed out and provides a reliable clock. This sequence of events is shown in Figure 11.5 CMU Switching from HFRCO to HFXO after HFXO is ready on page 290.

A separate flag is set when the oscillator is ready. This flag can also be configured to generate an interrupt.




Figure 11.4. CMU Switching from HFRCO to HFXO before HFXO is ready




Figure 11.5. CMU Switching from HFRCO to HFXO after HFXO is ready

Switching clock source for LFACLK, LFBCLK, and LFECLK is done by setting the LFA, LFB and LFE bitfields in CMU_LFACLKSEL, CMU_LFBCLKSEL and CMU_LFECLKSEL respectively. To ensure no stalls in the Low Energy Peripherals, the clock source should be ready before switching to it.

Note: To save energy, remember to turn off all oscillators not in use.

11.3.2.4 HFXO Configuration

The High Frequency Crystal Oscillator needs to be configured to ensure safe startup for the given crystal. Refer to the device data sheet and application notes for guidelines in selecting correct components and crystals as well as for configuration trade-offs.

The HFXO crystal is connected to the HFXTAL N/HFXTAL P pins as shown in Figure 11.6 HFXO Pin Connection on page 291




Figure 11.6. HFXO Pin Connection

By default the HFXO is started in crystal mode, but it is possible to connect an active external sine wave or square wave clock source to the HFXTAL_N pin of the HFXO. By configuring the MODE field in CMU_HFXOCTRL to EXTCLK, the HFXO can be bypassed and the source clock can be provided through the HFXTAL_N pin.

Upon enabling the HFXO, a hardware state machine sequentially applies the configurable startup state and steady state control settings from the CMU_HFXOSTARTUPCTRL and CMU_HFXOSTEADYSTATECTRL registers. Configuration is required for both the startup state and the steady state of the HFXO. After reaching the steady operation state of the HFXO, further optimization can optionally be performed to optimize the HFXO for noise and current consumption. Optimization for noise can be performed by an automatic Peak Detection Algorithm (PDA). Optimization for current can be performed by an automatic Shunt Current Optimization algorithm (SCO). HFXO operation is possible without PDA and SCO at the cost of higher noise and current consumption than required. Note that the HFXO circuit supports only crystals in the frequency range from 38-40 MHz, and is therefore only supported at voltage scale level 2. See 10.3.9 Voltage Scaling for more details.

Upon fully disabling the HFXO, the HFXTAL_N and HFXTAL_P pins can optionally be automatically pulled to ground as configured via the XTI2GND and XTO2GND bits respectively from the CMU_HFXOCTRL register. Do not set XTI2GND to 1 when the HFXO is in EXTCLK mode and an external wave is connected.




Figure 11.7. CMU HFXO Control State Machine

Refer to the device data sheet to find the configuration values for a given crystal. The startup state configuration needs to be written into the IBTRIMXOCORE and CTUNE bitfields of the CMU_HFXOSTARTUPCTRL register. The duration of the startup phase is configured in the STARTUPTIMEOUT bitfield of the CMU_HFXOTIMEOUTCTRL register. Similarly, the device data sheet provides the steady

state configuration depending on the crystal's CL, RESR and oscillation frequency. This configuration is programmed into the IBTRIM-XOCORE, REGISH and CTUNE bitfields of the CMU_HFXOSTEADYSTATECTRL register. The minimum duration of the steady phase is configured in the STEADYTIMEOUT bitfield of the CMU_HFXOTIMEOUTCTRL register.

All HFXO configuration needs to be performed prior to enabling the HFXO via HFXOEN in CMU_OSCENCMD unless noted otherwise. The HFXOENS flag in CMU_STATUS indicates if the HFXO has been successfully enabled. Once the HFXO startup time (STARTUP-TIMEOUT plus STEADYTIMEOUT) has exceeded and oscillations begin, the HFXO is ready for use as indicated by the HFXORDY flag in CMU_STATUS. If PDA and SCO are enabled, the HFXOPEAKDETRDY and HFXOSHUNTOPTRDY flags in the CMU_STATUS register indicate when these algorithms are ready and it is advised to also wait for these flags before using the HFXO.

The HFXO crystal bias current may be optimized and set to a value which decreases output phase noise without sacrificing PSR. This is done by programming the recommended IBTRIMXOCORE value into the CMU_HFXOSTEADYSTATECTRL register. The built-in Peak Detector Algorithm (PDA) performs further optimization to accommodate for process variations. Once PDA is ready as indicated by the HFXOPEAKDETRDY flag, the found optimal bias current setting is available in the IBTRIMXOCORE bitfield of the CMU_HFXOTRIMSTATUS register. This IBTRIMXOCORE setting should be saved and can be applied directly during a future HFXO startup as a low noise setting by programming it into the corresponding bitfield in CMU_HFXOSTEADYSTATECTRL while the HFXO is off.

If low noise is not required, the same PDA algorithm can be configured to optimize the HFXO for low current consumption by enabling LOWPOWER in the CMU_HFXOCTRL register before starting up the HFXO. The found IBTRIMXOCORE setting can be saved as a future low current setting.

Default PDA is started automatically once the HFXO has become ready. Repeated PDA can be triggered by writing HFXOPEAKDET-START to 1 in the CMU_CMD register. PDA can also be triggered only by the command register by configuring PEAKDETSHUNTOPT-MODE to CMD in the CMU_HFXOCTRL register before starting the HFXO. For PDA to work correctly, the REGISHUPPER bitfield of CMU_HFXOSTEADYSTATECTRL should be programmed to the value of the steady state REGISH + 3. The PEAKDETTIMEOUT bitfield in the CMU_HFXOTIMEOUTCTRL register is used to time the PDA steps and needs to be configured according to the device data sheet for the given crystal. The PEAKDETEN bitfield of the CMU_HFXOSTEADYSTATECTRL register is only used during manual (i.e. fully software controlled) peak detection and is ignored during automatic or command based triggering of the PDA. Note that the manual PDA mode is not recommended for general usage and therefore it is not further described. PDA should not be used when using an external wave as clock source.

Current consumption can be (further) reduced by running Shunt Current Optimization (SCO) after PDA. Once SCO is ready as indicated by the HFXOSHUNTOPTRDY flag, the found optimal regulator output current setting is available in the REGISH bitfield of the CMU_HFXOTRIMSTATUS register. This REGISH setting should be saved and can be applied directly during a future HFXO startup as a low current setting by programming it into the corresponding bitfield in CMU_HFXOSTEADYSTATECTRL while the HFXO is off. Normally SCO is run only for initial HFXO start up. The amplitude of the oscillator is not strongly dependent on temperature, but further optimization may be done each time that the temperature changes significantly. In that case, run SCO again by writing HFXOSHUNTOPTSTART to 1 in the CMU_CMD register. SCO depends on the LOWPOWER setting in the CMU_HFXOCTRL and needs to be rerun if that value has been changed. SCO should not be run when the HFXO is in use by the Radio Transceiver.

Default SCO is started automatically once the HFXO has become ready and PDA has finished. Repeated SCO can be triggered by writing HFXOSHUNTOPTSTART to 1 in the CMU_CMD register. SCO can also be triggered only by the command register by configuring PEAKDETSHUNTOPTMODE to CMD in the CMU_HFXOCTRL register before starting the HFXO. For SCO to work correctly, the REGISHUPPER bitfield of CMU_HFXOSTEADYSTATECTRL should be programmed to the value of the steady state REGISH + 3. The SHUNTOPTTIMEOUT bitfield in the CMU_HFXOTIMEOUTCTRL register is used to time the SCO steps and needs to be configured according to the device data sheet for the given crystal. The REGSELILOW bitfield of the CMU_HFXOSTEADYSTATECTRL register is only used during manual (i.e. fully software controlled) shunt current optimization and is ignored during automatic or command based triggering of the SCO. Note that the manual SCO mode is not recommended for general usage and therefore it is not further described.

11.3.2.4.1 Automatic HFXO Start

The enabling of the HFXO and its selection as HFSRCCLK source can be performed automatically by hardware. Automatic HFXO enable and select can for example be used upon wake-up of the Radio Controller (RAC). Automatic control of the HFXO is controlled via the AUTOSTARTRDYSELRAC, AUTOSTARTSELEM0EM1 and AUTOSTARTEM0EM1 bits in the CMU_HFXOCTRL register. It further depends on the energy mode of the EFR32 and on the status of the RAC.

The HFXO autostart functionality is typically used when the RAC is used. The RAC module always requires the HFXO for its operation. The hardware requirement from RAC for an HFXO based HFSRCCLK is indicated in the HFXOREQ bitfield of the CMU_STATUS register. This requirement in itself does not lead to an automatic enable or select of the HFXO.

An automatic HFXO enable is performed only if any of the following conditions are met:

- EFR32 is in EM0/EM1 and AUTOSTARTEM0EM1 or AUTOSTARTSELEM0EM1 are set to 1.
- RAC is awake and AUTOSTARTRDYSELRAC is set to 1.

An automatic HFXO select is performed only if any of the following conditions is met:

- EFR32 is in EM0/EM1 and AUTOSTARTSELEM0EM1 is set to 1.
- · RAC is awake, HFXO is ready, and AUTOSTARTRDYSELRAC is set to 1.

Whenever any of the conditions for automatic HFXO enable is met, software is not allowed to disable the HFXO. An attempt to do so (e.g., by writing 1 to the HFXODIS bit) is ignored and causes the HFXODISERR bit in the CMU_IF register to be set to 1. Similarly, whenever any of the conditions for automatic HFXO selection is met, software is not allowed to deselect the HFXO as clock source for HFSRCCLK. An attempt to do so (e.g., by selecting another clock source via CMU_HFCLKSEL) is ignored and causes the HFXODISERR bit in the CMU_IF register to be set to 1. Note that CMUERR is not implied by HFXODISERR. CMUERR will not get set to 1 for the above scenarios in which HFXODISERR gets set.

Software can only disable or deselect the HFXO after removing all of the HFXO automatic enable or select reasons. Note that if the autostart functionality is not used, software can always disable or deselect the HFXO even if hardware requires the HFXO as indicated via HFXOREQ bitfield in CMU_STATUS. The HFXODISERR flag will not get set in that case. The HFXO is only disabled by hardware upon EM2, EM3 or EM4 entry.

In case that AUTOSTARTSELEM0EM1 is set to 1 in EM0/EM1 (irrespective of the other autostart bits), the HFXO select will occur immediately, even if HFXO is not ready yet. Upon wake-up into EM0/EM1 this can therefore lead to a relatively long startup time as the system will not start operating from the HFRCO as it would otherwise do. In case of an automatic select triggered by the RAC (while AUTOSTARTSELEM0EM1 is set to 0), such a select will only occur upon the HFXO becoming ready and software can select and use another clock source in the mean time.

A typical use scenario of the AUTOSTARTRDYSELRAC bit is as follows. Set the AUTOSTARTRDYSELRAC bit in the CMU_HFXOCTRL register to 1 and set up the RTCC to periodically generate a compare match. Setup a PRS channel which uses this RTCC compare match as its source and allow the PRS channel to cause a wake-up into EM1. Setup the RAC to use the PRS channel as its source for TXEN or RXEN. Now, when the EFR32 is in EM2 and the RTCC generates a compare match, a wake-up into EM1 will occur and the HFXO will automatically start and become selected after which the RAC can perform its work and trigger a transition back into EM2 when done. The system started, used, and stopped the HFXO without ever being in EM0.

Note that the user should take care that the settings in the MSC_READCTRL and CMU_CTRL registers, as described in 11.3.3 Configuration for Operating Frequencies, are compatible with 40 MHz HFXO operation before enabling the HFXO automatic startup feature. A basic automatic HFXO start scenario is shown in Figure 11.8 CMU Automatic Startup and Selection of HFXO on page 295.




Figure 11.8. CMU Automatic Startup and Selection of HFXO

If an automatic selection of HFXO is performed, which switches the clock source used for HFSRCCLK, then the HFXOAUTOSW bit in CMU_IF is set to 1. After automatic enable and selection of the HFXO, the HFRCO is automatically disabled in case it is running. The disabling of a running HFRCO is signalled via the HFRCODIS bit in CMU_IF. This only applies to the HFRCO. If for example the LFXO was used as HFSRCCLK at the time of automatic selection of the HFXO, the LFXO remains unaffected.

The interaction between automatic HFXO startup and selection with startup and selection of HFRCO is shown in Figure 11.9 CMU HFRCO Startup/Selection While Awaiting Automatic HFXO Startup/Selection on page 295 and Figure 11.10 CMU Automatic HFXO startup/selection while HFRCO started/selected on page 296.




Figure 11.9. CMU HFRCO Startup/Selection While Awaiting Automatic HFXO Startup/Selection




Figure 11.10. CMU Automatic HFXO startup/selection while HFRCO started/selected

11.3.2.5 LFXO Configuration

The Low Frequency Crystal Oscillator (LFXO) is default configured to ensure safe startup for all crystals. In order to optimize startup time and power consumption for a given crystal, it is possible to adjust the startup gain in the oscillator by programming the GAIN field in CMU LFXOCTRL. Recommendations for the GAIN setting are as follows:

- 1. C0 must be < 2 pF
- 2. For 12.5 pF < CL < 18 pF, GAIN = 3
- 3. For 8 pF < CL < 12.5 pF, GAIN = 2
- 4. For 6 pF < CL < 8 pF, GAIN = 1
- 5. For CL = 6 pF, GAIN = 0

Refer to the device data sheet and application notes for guidelines in selecting correct components and crystals as well as for configuration trade-offs.

The LFXO can be retained on in EM4 Hibernate/Shutoff. In that case its required configuration is latched/retained throughout EM4 even though the CMU_LFXOCTRL register itself will be reset. Upon EM4 exit, the CMU_LFXOCTRL register therefore needs to be reconfigured to its original settings and the LFXO needs to be restarted via CMU_OSCENCMD, before optionally unlatching the retained LFXO configuration by writing 1 to EM4UNLATCH in the EMU_CMD register. The LFXO startup time is configured via the TIMEOUT bitfield of the CMU_LFXOCTRL register. If the LFXO has been retained throughout EM4 Hibernate/Shutoff, it can be quickly restarted for use as LFACLK, LFBCLK or LFECLK by using its minimum TIMEOUT setting. While retained, the LFXO can be used down to EM4 Hibernate as the source for LFECLK and down to EM4 Shutoff as the source for the CRYOCLK.

The LFXO crystal is connected to the LFXTAL_N/LFXTAL_P pins as shown in Figure 11.11 LFXO Pin Connection on page 297.




Figure 11.11. LFXO Pin Connection

By configuring the MODE field in CMU_LFXOCTRL, the LFXO can be bypassed, and an external clock source can be connected to the LFXTAL_N pin of the LFXO oscillator. If MODE is set to BUFEXTCLK, an external active sine source can be used as clock source. If MODE is set to DIGEXTCLK, an external active CMOS source can be used as clock source.

The LFXO includes on-chip tunable capacitance, which can replace external load capacitors. The TUNING bitfield of the CMU_LFXOCTRL register is used to tune the internal load capacitance connected between LFXTAL_P and ground and LFXTAL_N and ground symmetrically. The capacitance range and step size information is available in the device data sheets. Use the formula below to calculate the TUNING bitfield:

TUNING = ((desiredTotalLoadCap * 2 - Min(C_{LFXO T})) / C_{LFXO TS})

Figure 11.12. CMU LFXO Tuning Capacitance Equation

These tunable capacitors can also be used to compensate for temperature drift of the XTAL in software. Crystals normally have a temperature dependency which is given by a parabolic function. The crystal has highest frequency at its turnover temperature, normally 25C. The frequency is reduced following a parabola for higher and lower temperatures. The LFXO offers a mechanism to internally add capacitance on the LFXTAL_N and LFXTAL_P pins (in parallel to an optional external load capacitance). The variation in frequency as a function of temperature can therefore be compensated by adjusting the load capacitance. When the temperature compensation scheme is used, the maximum internal capacitance should be used to obtain good frequency matching at the turnover temperature. For higher and lower temperatures software then has the maximum range available to adjust the tuning. The external load capacitance

must then of course be reduced accordingly. Note that the ADC0 (26. ADC - Analog to Digital Converter) includes an embedded temperature sensor and that the EMU (10. EMU - Energy Management Unit) offers a temperature management interface, both of which can be used in combination with this LFXO temperature compensation scheme.

The XTAL oscillation amplitude can be controlled via the HIGHAMPL bitfield in CMU_LFXOCTRL. Setting HIGHAMPL to 1 will result in higher amplitude, which in turn provides safer operation, somewhat improved duty cycle, and lower sensitivity to noise at the cost of increased current consumption.

The AGC bit of the CMU_LFXOCTRL register is used to turn on or off the Automatic Gain Control module that adjusts the amplitude of the XTAL. When disabled, the LFXO will run at the startup current and the XTAL will oscillate rail to rail, again providing safer operation, improved duty cycle, and lower sensitivity to noise at the cost of increased current consumption.

11.3.2.6 HFRCO and AUXHFRCO Configuration

It is possible to calibrate the HFRCO and AUXHFRCO to achieve higher accuracy (see the device data sheets for details on accuracy). The frequency is adjusted by changing the TUNING and FINETUNING bitfields in CMU_HFRCOCTRL and CMU_AUXHFRCOCTRL. Changing to a higher value will result in a lower frequency. Refer to the data sheet for stepsize details.

The HFRCO can be set to one of several different frequency bands from 1 MHz to 38 MHz by setting the FREQRANGE field in CMU_HFRCOCTRL. Similarly the AUXHFRCO can be set to one of several different frequency bands from 1 MHz to 38 MHz by setting the FREQRANGE field in CMU_AUXHFRCOCTRL. The HFRCO and AUXHFRCO frequency bands are calibrated during production test, and the production tested calibration values can be read from the Device Information (DI) page. The DI page contains separate tuning values for various frequency bands. During reset, HFRCO and AUXHFRCO tuning values are set to the production calibrated values for the 19 MHz band, which is the default frequency band. When changing to a different HFRCO or AUXHFRCO band, make sure to also update the TUNING value and other bitfields in the CMU_HFRCOCTRL and CMU_AUXHFRCOCTRL registers. Typically the entire register is written with a value obtained from the Device Information (DI) page. Refer to 4.6 DI Page Entry Map for information on which frequency band settings are stored in the DI page.

The frequency can be tuned more accurately via the FINETUNING bitfield if fine tuning has been enabled via the FINETUNINGEN bit. Note that there will be a slight increase in the oscillator current consumption when fine tuning is enabled. Note also that changing the value of FINETUNINGEN will result in a frequency shift, regardless of the FINETUNING field value. If the oscillator is to be used at different times with fine tuning enabled and disabled, it should be tuned separately for both settings. The HFRCO and AUXHFRCO contain a local prescaler, which can be used in combination with any FREQRANGE setting. These prescalers allow the output clocks to be divided by 1, 2, or 4 as configured in the CLKDIV bitfield.

When using 11.3.2.8 RC Oscillator Calibration to tune HFRCO and AUXHFRCO to the desired frequency, linear search must be used to avoid over clocking the calibration counters. Before changing the FREQRANGE field in CMU_HFRCOCTRL, TUNING and FINE-TUNING fields should initially be set to the highest value (slowest frequency). After changing the FREQRANGE, linearly step TUNING value until desired frequency is reached. Likewise, before changing the TUNING field, FINETUNING field should initially be set to the highest value (lowest frequency). After changing the TUNING field, linearly step FINETUNING until accuracy is reached.

11.3.2.7 LFRCO Configuration

It is possible to calibrate the LFRCO to achieve higher accuracy (see the device data sheets for details on accuracy). The frequency is adjusted by changing the TUNING bitfield in CMU_LFRCOCTRL. Changing to a higher value will result in a lower frequency. Refer to the data sheet for stepsize details.

The LFRCO can be retained on in EM4 Hibernate/Shutoff. In that case its required configuration is latched/retained throughout EM4 even though the CMU_LFRCOCTRL register itself will be reset. Upon EM4 exit the CMU_LFRCOCTRL register therefore needs to be reconfigured to its original settings and the LFRCO needs to be restarted via CMU_OSCENCMD, before optionally unlatching the retained LFRCO configuration by writing 1 to EM4UNLATCH in the EMU_CMD register. The LFRCO startup time is configured via the TIMEOUT bitfield of the CMU_LFRCOCTRL register. Default its 16 cycle startup should be used. However, in case the LFRCO has been retained throughout EM4 Hibernate/Shutoff, it can be quickly restarted for use as LFACLK or LFBCLK by using its minimum TIMEOUT setting. While retained, the LFRCO can be used down to EM4 Hibernate as the source for LFECLK and down to EM4 Shutoff as the source for the CRYOCLK.

The LFRCO is also calibrated in production and its TUNING values are set to the correct value during reset.

The LFRCO can be put in duty cycle mode by setting the ENVREF bit in CMU_LFRCOCTRL to 1 before starting the LFRCO. This will reduce current consumption, but will result in slightly worse accuracy especially at high temperatures. Setting the ENCHOP and/or ENDEM bitfields to 1 in the CMU_LFRCOCTRL register will improve the average LFRCO frequency accuracy at the cost of a worse cycle-to-cycle accuracy.

11.3.2.8 RC Oscillator Calibration

The CMU has built-in HW support to efficiently calibrate the RC oscillators (LFRCO, HFRCO, AUXHFRCO, etc) at run-time. For a complete list of supported oscillators, refer to DOWNSEL and UPSEL fields in CMU_CALCTRL. See Figure 11.13 HW-support for RC Oscillator Calibration on page 299 for an illustration of this circuit. The concept is to select a reference and compare the RC frequency with the reference frequency. When the calibration circuit is started, one down-counter running on a selectable clock (DOWNSEL in CMU_CALCTRL) and one up-counter running on a selectable clock (UPSEL in CMU_CALCTRL) are started simultaneously. The top value for the down-counter must be written to CMU_CALCNT before calibration is started. The down-counter counts for CMU_CALCNT +1 cycles. When the down-counter has reached 0, the up-counter is sampled and the CALRDY interrupt flag is set. If CONT in CMU_CALCTRL is cleared, the counters are stopped after finishing the ongoing calibration. If continuous mode is selected by setting CONT in CMU_CALCTRL the down-counter reloads the top value and continues counting and the up-counter restarts from 0. Software can then read out the sampled up-counter value from CMU_CALCNT. The up-counter has counted (the sampled value)+1 cycles. The ratio between the reference and the oscillator subject to the calibration can easily be found using top+1 and sample+1. Overflows of the up-counter will not occur. If the up-counter reaches its top value before the down-counter reaches 0, the up-counter stays at its top value. Calibration can be stopped by writing CALSTOP in CMU_CMD. With this HW support, it is simple to write efficient calibration algorithms in software.




Figure 11.13. HW-support for RC Oscillator Calibration

The counter operation for single and continuous mode are shown in Figure 11.14 Single Calibration (CONT=0) on page 300 and Figure 11.15 Continuous Calibration (CONT=1) on page 300 respectively.




Figure 11.14. Single Calibration (CONT=0)




Figure 11.15. Continuous Calibration (CONT=1)

11.3.3 Configuration for Operating Frequencies

The HFXO is capable of frequencies up to 40 MHz, which allows the EFR32 to run at up to this frequency. However the Memory System Controller (MSC) and the Low Energy Peripheral Interface need to be configured correctly to allow operation at higher frequencies as explained below.

The MODE bitfield in MSC_READCTRL makes sure the flash is able to operate at the given HFCLK frequency by inserting wait states for flash accesses. The required settings for controlling flash wait states are shown in Table 11.2 MSC Configuration for Operating Frequencies, at VSCALE2: Flash Wait States on page 301. The WSHFLE bitfield in CMU_CTRL is used to ensure that the Low Energy Peripheral Interface is able to operate at the given HFBUSCLK_{LE} frequency by inserting wait states when using this interface. The required settings are shown in Table 11.4 LE Configuration for Operating Frequencies: Low Energy Peripheral Interface on page 301.

Before going to a high frequency, make sure the registers in the table have the correct values. When going down in frequency, make sure to keep the registers at the values required by the higher frequency until after the switch has been done.

Table 11.2. MSC Configuration for Operating Frequencies, at VSCALE2: Flash Wait States

Condition	MODE in MSC_READCTRL
HFCLK <= 25 MHz	WS0 or above
25 MHz < HFCLK <= 40 MHz	WS1 or above

Table 11.3. MSC Configuration for Operating Frequencies, at VSCALE0: Flash Wait States

Condition	MODE in MSC_READCTRL
HFCLK <= 7 MHz	WS0 or above
7 MHz < HFCLK <= 14 MHz	WS1 or above
14 MHz < HFCLK <= 20 MHz	WS2

Table 11.4. LE Configuration for Operating Frequencies: Low Energy Peripheral Interface

Condition	WSHFLE in CMU_CTRL
HFBUSCLK _{LE} <= 32 MHz	0 / 1
HFBUSCLK _{LE} > 32 MHz	1

11.3.4 Energy Modes

The availability of oscillators and system clocks depends on the chosen energy mode. Default the high frequency oscillators (HFRCO, AUXHFRCO, and HFXO) and high frequency clocks (HFSRCLK, HFCLK, HFCDRECLK, HFBUSCLK, HFPERCLK, HFRADIOCLK, HFCLKLE) are available downto EM1 Sleep. From EM2 Deep Sleep onwards these oscillators and clocks are normally off, although special cases exist as summarized in Table 11.5 Oscillator and Clock Availability in Energy Modes on page 302 and Table 10.2 EMU Energy Mode Overview on page 214. The CMU overview figure in Figure 11.1 CMU Overview - High Frequency Portion on page 279 and Figure 11.2 CMU Overview - Low Frequency Portion on page 280 also indicate which oscillators and clocks can be used in what energy modes.

The low frequency oscillators (LFRCO and LFXO) are available in all energy modes except in EM3 Stop when they are off by definition. Default these oscillators are also off in EM4 Hibernate and EM4 Shutoff, but they can be retained on in these states as well if needed. The ultra low frequency oscillator (ULFRCO) is default on in all energy modes, except for EM4 Shutoff, but it can be retained on in that mode as well if needed. The low frequency clocks (LFACLK, LFBCLK, LFECLK, WDOGnCLK, and CRYOCLK) are in various power domains and therefore their availability not only depends on the chosen clock source, but also on the chosen energy mode as indicated in Table 11.5 Oscillator and Clock Availability in Energy Modes on page 302.

Table 11.5. Oscillator and Clock Availability in Energy Modes

	EM0 Active/EM1 Sleep	EM2 Deep Sleep	EM3 Stop	EM4 Hibernate	EM4 Shutoff
HFRCO	On ¹	Off	Off	Off	Off
HFXO	On ¹	Off	Off	Off	Off
AUXHFRCO	On ¹	On ²	On ²	Off	Off
LFRCO, LFXO	On ¹	On ¹	Off	Retained on ³	Retained on ³
ULFRCO	On	On	On	On	Retained on ³
HFSRCLK, HFCLK, HFCORECLK, HFBUSCLK, HFPERCLK, HFRA- DIOCLK, HFCLKLE	On ¹	Off	Off	Off	Off
AUXCLK	On ¹	On ²	On ²	Off	Off
ADCnCLK	On ¹	On ⁴	On ⁴	Off	Off
LFACLK, LFBCLK	On ¹	On ¹	On ⁵	Off	Off
LFECLK	On ¹	On ¹	On ⁵	Retained on ³	Off
WDOGnCLK	On ¹	On ¹	On ⁵	Off	Off
CRYOCLK	On ¹	On ¹	On ⁵	Retained on ³	Retained on ³

Note:

- 1. Under software control.
- 2. Default off, but kept active if used by the ADC.
- 3. Default off, but can be retained on.
- 4. Will be kept on if AUXHFRCO is selected as clock source.
- 5. On only if ULFRCO is used as clock source.

11.3.5 Clock Output on a Pin

It is possible to configure the CMU to output clocks on the CMU_CLK0 and CMU_CLK1 pins. This clock selection is done using the CLKOUTSEL0 and CLKOUTSEL1 fields, respectively, in CMU_CTRL. The required output pins must be enabled in the CMU_ROUTEPEN register and the pin locations can be configured in the CMU_ROUTELOC0 register. The following clocks can be output on a pin:

- HFSRCCLK and HFEXPCLK. The HFSRCCLK is the high frequency clock before any prescaling has been applied. The HFEXPCLK
 is a prescaled version of HFCLK as controlled by the HFEXPPRESC bitfield in the CMU_HFPRESC register.
- The unqualified clock output from any of the oscillators (ULFRCO, LFXO, HFXO). Note that these unqualified clocks can
 exhibit glitches or skewed duty-cycle during startup and therefore these clock outputs are normally not used before observing the
 related ready flag being set to 1 in CMU_STATUS.
- The qualified clock from any of the oscillators (ULFRCO, LFRCO, LFXO, HFXO, HFRCO, AUXHFRCO). A qualified clock will not
 have any glitches or skewed duty-cycle during startup. For LFRCO, LFXO and HFXO correct configuration of the TIMEOUT bitfield(s) in CMU_LFRCOCTRL, CMU_LFXOCTRL and CMU_HFXOTIMEOUTCTRL respectively is required to guarantee a properly
 qualified clock.

HFCLK will not have a 50-50 duty cycle when any other division factor than 1 is used in CMU_HFPRESC (i.e. if PRESC is not equal to 0). In such a case, the exported HFEXPCLK will therefore also not be 50-50 when its division factor is not set to an even number in CMU HFEXPPRESC.

11.3.6 Clock Input From a Pin

It is possible to configure the CMU to input a low-frequency (< 1 MHz) clock from the CMU_CLKI0. This clock can be selected to drive HFSRCCLK reference using CMU_HFCLKSEL. The required input pin must be enabled in the CMU_ROUTEPEN register and the pin location can be configured in the CMU_ROUTELOC1 register.

11.3.7 Clock Output on PRS

The CMU can be used as a PRS producer. It can output clocks onto PRS which can be selected by a consumer as CMUCLKOUT0 and CMUCLKOUT1. The clocks which can be produced via CMUCLKOUT0 and CMUCLKOUT1 are selected via the CLKOUTSEL0 and CLKOUTSEL1 fields, respectively, in CMU_CTRL.

Note that the CLKOUTSEL0 and CLKOUTSEL1 fields are also used for selecting which clock is output onto a pin as described in 11.3.5 Clock Output on a Pin. In contrast with clock output on a pin however, output of a clock onto PRS does not depend on any configuration of the CMU ROUTEPEN and CMU ROUTELOC0 registers.

11.3.8 Error Handling

Certain restrictions apply to how and when the CMU registers can be configured as is described for the respective registers. Not adhering to these restrictions can lead to unpredictable and non-defined behaviour. Some of these software restrictions are checked in hardware and not adhering to them will cause the CMUERR interrupt flag in CMU_IF to be set to 1. The restrictions impacting CMUERR are as follows:

- CMU_HFRCOCTRL should not be written while HFRCOBSY in the CMU_SYNCBUSY register is set to 1.
- · CMU AUXHFRCOCTRL should not be written while AUXHFRCOBSY in the CMU SYNCBUSY register is set to 1.
- CMU_HFXOSTARTUPCTRL, CMU_HFXOSTEADYSTATECTRL and CMU_HFXOTIMEOUTCTRL should not be written while HFXOBSY in the CMU_SYNCBUSY register is set to 1. Note that writes to CMU_HFXOCTRL do not impact CMUERR. Although most of its bitfields need to be configured before enabling the HFXO, it it allowed to change the AUTOSTART bits (i.e. AUTOSTARTDYSELRAC, AUTOSTARTSELEM0EM1 and AUTOSTARTEM0EM1) at any time.
- HFXO should not be enabled before it has been properly disabled (so only enable HFXO when HFXOENS=0 or HFXOBSY=0). Likewise, HFXO should not be disabled before it has been properly enabled (so only disable HFXO when HFXOENS=1 or HFXOBSY=0).
- CMU_LFRCOCTRL should not be written while LFRCOBSY in the CMU_SYNCBUSY register is set to 1. The GMCCURTUNE bit-field should not be written with a differing value while the LFRCOVREFBSY flag is set to 1.
- CMU LFXOCTRL should not be written while LFXOBSY in the CMU SYNCBUSY register is set to 1.

11.3.9 Interrupts

The interrupts generated by the CMU module are combined into one interrupt vector. If CMU interrupts are enabled, an interrupt will be made if one or more of the interrupt flags in CMU IF and their corresponding bits in CMU IEN are set.

11.3.10 Wake-up

The CMU can be (partially) active all the way down to EM4 Shutoff. It can wake up the CPU from EM2 upon LFRCO or LFXO becoming ready as LFRCORDY and LFXORDY can be used as wake-up interrupt.

11.3.11 Protection

It is possible to lock the control- and command registers to prevent unintended software writes to critical clock settings. This is control-led by the CMU_LOCK register.

11.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	CMU_CTRL	RW	CMU Control Register
0x010	CMU_HFRCOCTRL	RWH	HFRCO Control Register
0x018	CMU_AUXHFRCOCTRL	RW	AUXHFRCO Control Register
0x020	CMU_LFRCOCTRL	RW	LFRCO Control Register
0x024	CMU_HFXOCTRL	RW	HFXO Control Register
0x02C	CMU_HFXOSTARTUPCTRL	RW	HFXO Startup Control
0x030	CMU_HFXOSTEADYSTATECTRL	RW	HFXO Steady State Control
0x034	CMU_HFXOTIMEOUTCTRL	RW	HFXO Timeout Control
0x038	CMU_LFXOCTRL	RW	LFXO Control Register
0x050	CMU_CALCTRL	RW	Calibration Control Register
0x054	CMU_CALCNT	RWH	Calibration Counter Register
0x060	CMU_OSCENCMD	W1	Oscillator Enable/Disable Command Register
0x064	CMU_CMD	W1	Command Register
0x070	CMU_DBGCLKSEL	RW	Debug Trace Clock Select
0x074	CMU_HFCLKSEL	W1	High Frequency Clock Select Command Register
0x080	CMU_LFACLKSEL	RW	Low Frequency A Clock Select Register
0x084	CMU_LFBCLKSEL	RW	Low Frequency B Clock Select Register
0x088	CMU_LFECLKSEL	RW	Low Frequency E Clock Select Register
0x090	CMU_STATUS	R	Status Register
0x094	CMU_HFCLKSTATUS	R	HFCLK Status Register
0x09C	CMU_HFXOTRIMSTATUS	R	HFXO Trim Status
0x0A0	CMU_IF	R	Interrupt Flag Register
0x0A4	CMU_IFS	W1	Interrupt Flag Set Register
0x0A8	CMU_IFC	(R)W1	Interrupt Flag Clear Register
0x0AC	CMU_IEN	RW	Interrupt Enable Register
0x0B0	CMU_HFBUSCLKEN0	RW	High Frequency Bus Clock Enable Register 0
0x0C0	CMU_HFPERCLKEN0	RW	High Frequency Peripheral Clock Enable Register 0
0x0CC	CMU_HFRADIOALTCLKEN0	RW	High Frequency Alternate Radio Peripheral Clock Enable Register 0
0x0E0	CMU_LFACLKEN0	RW	Low Frequency a Clock Enable Register 0 (Async Reg)
0x0E8	CMU_LFBCLKEN0	RW	Low Frequency B Clock Enable Register 0 (Async Reg)
0x0F0	CMU_LFECLKEN0	RW	Low Frequency E Clock Enable Register 0 (Async Reg)
0x100	CMU_HFPRESC	RW	High Frequency Clock Prescaler Register
0x108	CMU_HFCOREPRESC	RW	High Frequency Core Clock Prescaler Register
0x10C	CMU_HFPERPRESC	RW	High Frequency Peripheral Clock Prescaler Register
0x110	CMU_HFRADIOPRESC	RW	High Frequency Radio Peripheral Clock Prescaler Register

Offset	Name	Туре	Description
0x114	CMU_HFEXPPRESC	RW	High Frequency Export Clock Prescaler Register
0x120	CMU_LFAPRESC0	RW	Low Frequency a Prescaler Register 0 (Async Reg)
0x128	CMU_LFBPRESC0	RW	Low Frequency B Prescaler Register 0 (Async Reg)
0x130	CMU_LFEPRESC0	RW	Low Frequency E Prescaler Register 0 (Async Reg)
0x138	CMU_HFRADIOALTPRESC	RW	High Frequency Alternate Radio Peripheral Clock Prescaler Register
0x140	CMU_SYNCBUSY	R	Synchronization Busy Register
0x144	CMU_FREEZE	RW	Freeze Register
0x150	CMU_PCNTCTRL	RWH	PCNT Control Register
0x15C	CMU_ADCCTRL	RWH	ADC Control Register
0x170	CMU_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x174	CMU_ROUTELOC0	RW	I/O Routing Location Register
0x178	CMU_ROUTELOC1	RW	I/O Routing Location Register
0x180	CMU_LOCK	RWH	Configuration Lock Register

11.5 Register Description

11.5.1 CMU_CTRL - CMU Control Register

Offset						Bit I	Pos	sition															
0x000	30 29 29 27 27	23 24 25 23 23 23 23 24 25 25 25 25 25 25 25 25 25 25 25 25 25	2	70	19 19	17	16	5 4	13	12	7	9	6	∞	^	u	2 2	4		ν (.7	-	0
Reset			_	_			5								00X0					0	0 0 0 0 0		
Access			₹ §	ZW W		Ž	≥ Y														 } }		
			-				_											+					
Name			HFRADIOCLKEN	HFPERCLKEN		<u> </u>	WSHFLE								CLKOUTSEL1					<u> </u>	CLKOUISELO		
			生	岦		Š	≶								겁					ō	<u>ゴ</u>		
Bit	Name	Reset	Ac	ces	s Desc	riptio	on																
31:22	Reserved	To ensure con tions	npati	ibilit _.	y with fut	ure d	levi	ces, a	lway	/s w	rite l	bits t	o 0	Мс	re ii	nfoi	rmat	ion i	in 1	1.2 (Cor	ven-	•
21	HFRADIOCLKEN	1	RV	V	HFRA	ADIO	CL	K Ena	able														
	Set to enable the HF	RADIOCLK.																					
20	HFPERCLKEN	1	RV	V	HFPE	RCL	LK	Enabl	е														
	Set to enable the HF	PERCLK.														_							
19:17	Reserved	To ensure con tions	npati	ibilit _.	y with fut	ure d	levi	ces, a	lway	/S W	rite l	bits t	o 0	Мс	re ii	nfoi	rmat	ion i	in 1	1.2 (Cor	ven-	
16	WSHFLE	0	RV	V	Wait	State	e fo	r Hig	h-Fr	equ	ienc	y LE	In	erfa	ace								
	Set to allow access to	LE peripherals	whe	n ru	nning HF	BUS	CL	K _{LE} at	frec	quei	ncies	hig	her	thar	า 32	Mł	Ηz						
15:10	Reserved	To ensure con tions	npati	ibilit <u>.</u>	y with fut	ure d	levi	ces, a	lway	/s w	rite l	bits t	o 0	Мс	re ii	nfoi	rmat	ion i	in 1	1.2 (Cor	ven-	•
9:5	CLKOUTSEL1	0x00	RV	V	Clock	k Ou	tpu	t Sele	ct 1														
	Controls the clock ou	tput 1 multiplexe	r. To	act	ually outp	out o	n th	ne pin,	set	CLI	KOU	T1P	ΕN	in C	MU	_R	TUO	E.					
	Value	Mode			Desc	riptio	n																
	0	DISABLED			Disab	led																	
	1	ULFRCO			ULFF	CO	(dir	ectly f	rom	osc	illato	or)											
	2	LFRCO			LFRC	O (d	dire	ctly fro	m o	scil	lator)											
	3	LFXO			LFXC	(dire	ectl	y from	oso	cilla	tor)												
	6	HFXO			HFXC) (dir	rect	ly fron	n os	cilla	tor)												
	7	HFEXPCLK			HFE	(PCL	_K																
	9	ULFRCOQ						alified)														
	10	LFRCOQ			LFRC			-															
	11	LFXOQ			LFXC			-															
	12	HFRCOQ			HFR		-	-															
	13	AUXHFRCOQ			AUXI	HFRO	CO	(quali	fied))													

		_								
Bit	Name	Reset	Access	Description						
	14	HFXOQ		HFXO (qualified)						
	15	HFSRCCLK		HFSRCCLK						
4:0	CLKOUTSEL0	0x00	RW	Clock Output Select 0						
	Controls the clock output multiplexer. To actually output on the pin, set CLKOUT0PEN in CMU_ROUTE.									
	Value	Mode		Description						
	0	DISABLED		Disabled						
	1	ULFRCO		ULFRCO (directly from oscillator)						
	2	LFRCO		LFRCO (directly from oscillator)						
	3	LFXO		LFXO (directly from oscillator)						
	6	HFXO		HFXO (directly from oscillator)						
	7	HFEXPCLK		HFEXPCLK						
	9	ULFRCOQ		ULFRCO (qualified)						
	10	LFRCOQ		LFRCO (qualified)						
	11	LFXOQ		LFXO (qualified)						
	12	HFRCOQ		HFRCO (qualified)						
	13	AUXHFRCOQ		AUXHFRCO (qualified)						
	14	HFXOQ		HFXO (qualified)						
	15	HFSRCCLK		HFSRCCLK						

11.5.2 CMU_HFRCOCTRL - HFRCO Control Register

Write this register to set the frequency band in which the HFRCO is to operate. Always update all fields in this register at once by writing the value for the desired band, which has been obtained from the Device Information page entry for that band. The TUNING, FINE-TUNING, FINE-TUNING, FINE-TUNINGEN and CLKDIV bitfields can be used to tune a specific band (FREQRANGE) of the oscillator to a non-preconfigured frequency. When changing this setting there will be no glitches on the HFRCO output, hence it is safe to change this setting

even while the system is running on the HFRCO. Only write CMU_HFRCOCTRL when it is ready for an update as indicated by HFRCOBSY=0 in CMU_SYNCBUSY.

Offset			Bit Positio	on				
0x010	31 30 29 28 27	26 27 23 23 23 21 21	20 19 17 16 15	4 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	0 2 4 6 7 - 0			
Reset	0 0 0 0	000 1 000	0×08	0×1F	0x7F			
Access	RWH	RWH RWH	RWH	RWH	RWH			
Name	VREFTC	CLKDIV LDOHP CMPBIAS	FREQRANGE	FINETUNING	TUNING			

) > L	L 0		0		Щ		Щ	<u> </u>			
Bit	Name	Re	eset	Ac	cess	Description	า					
31:28	VREFTC	0x	έΒ	RV	VH	HFRCO Te	mperatu	re Coefficient Trim or	n Comparator Reference			
	Writing this field	adjusts th	ne tem	perature o	coeffici	ent trim on co	omparato	or reference.				
27	FINETUNINGEN	1 0		RV	VH	Enable Ref	erence	or Fine Tuning				
	Settings this bit	enables F	IFRCC) fine tunir	ng.							
26:25	CLKDIV	0x	:0	RV	VH	Locally Div	ide HFF	CO Clock Output				
	Writing this field	Writing this field configures the HFRCO clock output divider.										
	Value	M	ode			Description						
	0	DI	V1			Divide by 1.						
	1	DI	V2			Divide by 2.						
	2	DI	V4			Divide by 4.						
24	LDOHP	1		RV	VH	HFRCO LD	O High	Power Mode				
	Settings this bit	outs the F	HFRCC	DLDO in h	nigh po	ower mode.						
23:21	CMPBIAS	0x	2	RV	VH	HFRCO Co	mparato	or Bias Current				
	Writing this field	adjusts th	ne HFF	RCO comp	parator	bias current						
20:16	FREQRANGE	0x	:08	RV	VH	HFRCO Fre	equency	Range				
	Writing this field	adjusts th	ne HFF	RCO frequ	ency r	ange.						
15:14	Reserved		ensui ens	re compat	ibility v	vith future de	vices, al	ways write bits to 0. Mo	re information in 1.2 Conven-			
13:8	FINETUNING	0x	1F	RV	VH	HFRCO Fir	e Tunin	g Value				
	Writing this field when FINETUNI	-		RCO fine t	uning	value. Higher	value m	eans lower frequency.	Fine tuning is only enabled			
7	Reserved		ensui ens	re compat	ibility v	vith future de	vices, al	ways write bits to 0. Mo	re information in 1.2 Conven-			
6:0	TUNING	0x	7F	RV	VH	HFRCO Tu	ning Va	ue				
	Writing this field	adjusts th	ne HFF	RCO tunin	g value	e. Higher valı	ue mean	s lower frequency.				

11.5.3 CMU_AUXHFRCOCTRL - AUXHFRCO Control Register

Write this register with the production calibrated values from the Device Info pages. The TUNING, FINETUNINGEN and CLKDIV bitfields can be used to tune a specific band (FREQRANGE) of the oscillator to a non-preconfigured frequency. Only write CMU_AUXHFRCOCTRL when it is ready for an update as indicated by AUXHFRCOBSY=0 in CMU_SYNCBUSY.

Offset			Bit Position					
0x018	31 30 29 28	27 26 25 25 24 23 23 22 21	20 19 17 17 17 17 17	13 13 13 13 14 17 17 17 17 17 17 17 17 17 17 17 17 17	0 0 4 6 0 -0			
Reset	0xB	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	0×08	0×1F	0x7F			
Access	RW	RW RW W	RW	RW	RW W			
Name	VREFTC	CMPBIAS	FREQRANGE	FINETUNING	TUNING			

	\ R	Z Z	C.	LDC	CM		H. H.		Ξ		בֿר בֿר	
Bit	Name		Re	eset	Ac	cess	Description					
31:28	VREFTC		0x	В	RV	/	AUXHFRCO ence	Tempe	erature Coefficient Tri	m on	Comparator Refer-	
	Writing this field	d ad	justs th	ne ter	mperature c	oeffici	ent trim on com	parato	or reference.			
27	FINETUNINGE	:N	0		RW	/	Enable Refer	ence 1	for Fine Tuning			
	Settings this bit	t ena	ables A	UXH	FRCO fine	tuning						
26:25	CLKDIV		0x	0	RW	/	Locally Divid	e AUX	(HFRCO Clock Output	t		
	Writing this field	Writing this field configures the AUXHFRCO clock output divider.										
	Value		М	ode			Description					
	0		DI	V1			Divide by 1.					
	1		DI	V2			Divide by 2.					
	2		DI	V4			Divide by 4.					
24	LDOHP		1		RV	/	AUXHFRCO I	DO H	ligh Power Mode			
	Settings this bit	Settings this bit puts the AUXHFRCO LDO in high power mode.										
23:21	CMPBIAS		0x	2	RV	1	AUXHFRCO (Comp	arator Bias Current			
	Writing this field	d ad	justs th	ne Al	JXHFRCO (compa	rator bias curre	nt.				
20:16	FREQRANGE		0x	08	RV	/	AUXHFRCO I	requ	ency Range			
	Writing this field	d ad	justs th	ne Al	JXHFRCO f	requer	ncy range.					
15:14	Reserved			ens ns	ure compati	bility v	vith future devic	es, alı	ways write bits to 0. Mo	re inf	ormation in 1.2 Conven-	
13:8	FINETUNING		0x	1F	RW	/	AUXHFRCO I	ine T	uning Value			
	Writing this field bled when FINI	d ad ETU	justs th NINGE	ne Al EN is	JXHFRCO f set.	ine tur	ning value. High	er val	ue means lower freque	ncy. I	Fine tuning is only ena-	
7	Reserved			ens ns	ure compati	bility v	vith future devic	es, alı	ways write bits to 0. Mo	re inf	ormation in 1.2 Conven-	
6:0	TUNING		0x	7F	RW	1	AUXHFRCO	Tuning	g Value			
	Writing this field	d ad	justs th	ne Al	JXHFRCO t	uning	value. Higher v	alue n	neans lower frequency.			

11.5.4 CMU_LFRCOCTRL - LFRCO Control Register

Offset								Bi	t Po	sitio	on											
0x020	30 29 28	27	25	23	20	19	8	17	16	15	4	13	12	7	10	6	8 /	0 4	4	က	2	- 0
Reset	0x8		0x1		0x1		-	_	0				•		•	•			0x100	•		·
Access	RW W		¥ ≷		₩ X		S.	W.	¥ N										ΑŠ			
Name	GMCCURTUNE		TIMEOUT		VREFUPDATE		ENDEM	ENCHOP	ENVREF										TUNING			
Bit	Name		Reset		Acces	s I	Des	crip	tion													
31:28	GMCCURTUN	E	0x8		RW	-	Tun	ing	of G	mc	Cur	ren	t									
	Set to tune GMC current. This field is updated with the production calibrated value during reset, and the reset value mitherefore vary between devices.								night													
27:26	Reserved		To ens	ure con	npatibilit	y wit	th fu	ture	dev	vices	, alv	vay	s w	rite	bits	to 0.	More in	format	ion i	n 1.2	? Con	ven-
25:24	TIMEOUT		0x1		RW	ı	LFR	СО	Tim	eou	t											
	Configures the start-up delay for LFRCO. Do not change while LFRCO is enabled. When starting up the LFRCO after it has been completely turned off, use TIMEOUT=16cycles. If the LFRCO has been retained on in EM4, then the TIMEOUT=2cycles configuration is also allowed when re-enabling the LFRCO after EM4 exit (as it is still running).																					
	Value		Mode			[Des	cript	ion													
	0		2CYCL	.ES		-	Time	eout	per	iod c	of 2 (cyc	les									
	1		16CYC	LES		Timeout period of 16 cycles																
	2		32CYC	LES		-	Timeout period of 32 cycles															
23:22	Reserved		To ens	ure con	npatibilit	y wit	th fu	ture	dev	vices	, alv	vay	s W	rite	bits	to 0.	More in	format	ion i	n 1.2	? Con	ven-
21:20	VREFUPDATE		0x1		RW	(Con	trol	Vre	f Up	date	e R	ate									
	Specify Vref up therefore differ		te. This	field ca	n be upo	dated	d wit	th th	e pr	odu	ction	n te:	st va	alue	dur	ing ı	eset, an	nd the i	eset	: valu	e mi	ght
	Value		Mode			[Des	cript	ion													
	0		32CYC	LES		;	32 c	lock	S.													
	1		64CYC	LES		(64 c	lock	S.													
	2		128CY	CLES		•	128	cloc	ks.													
	3		256CY	CLES		2	256	cloc	ks.													
19	Reserved		To ens	ure con	npatibilit	y wit	th fu	ture	dev	vices	, alv	vay	S W	rite	bits	to 0.	More in	nformat	ion i	n 1.2	? Con	ven-
18	ENDEM		1		RW	ı	Ena	ble l	Dyn	ami	c El	em	ent	Mat	tchi	ng						
	Set to enable of	lynamic	elemen	t match	ing. This	s imp	prov	es a	vera	age 1	frequ	uen	су а	iccl	ıracı	/ at	he cost	of incr	ease	ed jitte	er.	

Bit	Name	Reset	Access	Description
17	ENCHOP	1	RW	Enable Comparator Chopping
	Set to enable compa	rator chopping.	This improv	ves average frequency accuracy at the cost of increased jitter.
16	ENVREF	0	RW	Enable Duty Cycling of Vref
	Set to enable duty cy	cling of vref. Cle	ear during c	calibration of LFRCO. Only change when LFRCO is off.
15:9	Reserved	To ensure co tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	TUNING	0x100	RW	LFRCO Tuning Value
	•			the higher the value, the lower the frequency). This field is updated with the e reset value might therefore vary between devices.

11.5.5 C	MU_	_HF	(OC	TRI	F	łFX(O C	ontr	ol F	Regi	ster	•																				
Offset															Ві	it Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset		0	0	0			0X0															0	0	0			2	2				0
Access		₩ M	RW	RW			ΑŠ															RW	RW	RW			2	≷				A W
Name		AUTOSTARTRDYSELRAC	AUTOSTARTSELEM0EM1	AUTOSTARTEM0EM1			LFTIMEOUT															XTO2GND	XTI2GND	LOWPOWER				PEAKUE I SHUNI OP I MODE				MODE
Bit	Na	me					Re	set			Ac	cess	s l	Des	crip	tion	1															
31	Re	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions																														

Bit	Name	Reset	Access	Description
31	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
30	AUTOSTARTRDY- SELRAC	0	RW	Automatically Start HFXO on RAC Wake-up and Select It Upon HFXO Ready
	This bit enables auto time.	matic HFXO st	art-up and H	IFXO selection when ready on RAC wake-up. Allowed to change at any
29	AUTOSTARTSE- LEM0EM1	0	RW	Automatically Start and Select of HFXO Upon EM0/EM1 Entry From EM2/EM3
				tte selection of the HFXO when in EM0/EM1 (also after entry from EM2/SRCCLK until HFXO becomes ready. Allowed to change at any time.
28	AUTOSTAR- TEM0EM1	0	RW	Automatically Start of HFXO Upon EM0/EM1 Entry From EM2/EM3
	This bit enables auto			when in EM0/EM1 (also after entry from EM2/EM3) without causing an t any time.
27	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
26:24	LFTIMEOUT	0x0	RW	HFXO Low Frequency Timeout
	Configures the start-	up delay for HF	XO measure	ed in LFECLK cycles. Only change when both HFXO and LFECLK are off.
	Value	Mode		Description

Value	Mode	Description
0	0CYCLES	Timeout period of 0 cycles (disabled)
1	2CYCLES	Timeout period of 2 cycles
2	4CYCLES	Timeout period of 4 cycles
3	16CYCLES	Timeout period of 16 cycles
4	32CYCLES	Timeout period of 32 cycles
5	64CYCLES	Timeout period of 64 cycles
6	1KCYCLES	Timeout period of 1024 cycles
7	4KCYCLES	Timeout period of 4096 cycles

Bit	Name	Reset	Access	Description
23:11	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
10	XTO2GND	0	RW	Clamp HFXTAL_P Pin to Ground When HFXO Oscillator is Off
	Set to enable ground	ding of HFXTAL_	P pin wher	n HFXO oscillator is off
9	XTI2GND	0	RW	Clamp HFXTAL_N Pin to Ground When HFXO Oscillator is Off
	Set to enable ground source is supplied.	ding of HFXTAL_	_N pin wher	n HFXO oscillator is off. Do not enable if MODE=EXTCLK and an external
8	LOWPOWER	0	RW	Low Power Mode Control
	Set LOWPOWER=0 tion).) for RF performa	ince. Set L0	DWPOWER=1 for non RF performance (not compatible with Radio opera-
7:6	Reserved	To ensure co tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	PEAKDETSHUN- TOPTMODE	0x0	RW	HFXO Automatic Peak Detection and Shunt Current Optimization Mode
				k detection and shunt current optimization (MANUAL mode provides direct TEN, REGSELILOW).
	Value	Mode		Description
	Value 0	Mode AUTOCMD		Description Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used.
				Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-
	0	AUTOCMD		Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequen-
3:1	1	AUTOCMD CMD MANUAL	mpatibility v	Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequences. CMU_HFXOSTEADYSTATECTRL IBTRIMXOCORE, REGISH, REGSELILOW, and PEAKDETEN are under full software control and are
<i>3:1</i> 0	1 2	AUTOCMD CMD MANUAL To ensure co	mpatibility v	Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequences. CMU_HFXOSTEADYSTATECTRL IBTRIMXOCORE, REGISH, REGSELILOW, and PEAKDETEN are under full software control and are allowed to be changed once HFXO is ready.
	0 1 2 Reserved MODE	AUTOCMD CMD MANUAL To ensure cotions 0 the external sou	RW	Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequences. CMU_HFXOSTEADYSTATECTRL IBTRIMXOCORE, REGISH, REGSELILOW, and PEAKDETEN are under full software control and are allowed to be changed once HFXO is ready. with future devices, always write bits to 0. More information in 1.2 Conven-
	0 1 2 Reserved MODE Set this to configure	AUTOCMD CMD MANUAL To ensure cotions 0 the external sou	RW	Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequences. CMU_HFXOSTEADYSTATECTRL IBTRIMXOCORE, REGISH, REGSELILOW, and PEAKDETEN are under full software control and are allowed to be changed once HFXO is ready. with future devices, always write bits to 0. More information in 1.2 Conventional and the sequences.
	0 1 2 Reserved MODE Set this to configure CMU_OSCENCMD.	AUTOCMD CMD MANUAL To ensure cotions 0 the external sou	RW	Automatic control of HFXO peak detection and shunt optimization sequences. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPT-START can also be used. CMU_CMD HFXOPEAKDETSTART and HFXOSHUNTOPTSTART can be used to trigger peak detection and shunt optimization sequences. CMU_HFXOSTEADYSTATECTRL IBTRIMXOCORE, REGISH, REGSELILOW, and PEAKDETEN are under full software control and are allowed to be changed once HFXO is ready. with future devices, always write bits to 0. More information in 1.2 Conventional and the sequence of the seq

11.5.6 CMU_HFXOSTARTUPCTRL - HFXO Startup Control

Offset		Bit Position		
0x02C	31 30 30 29 29 24 25 25 27 27 28 29 29 29 20 20 20 20 20 20 20 20 20 20 20 20 20	6 8 7 9 5 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7	0 0 0 7	0 0 4 0 7 - 0
Reset		0x0A0		0x20
Access		RW		RW
Name		CTUNE		IBTRIMXOCORE

Bit	Name	Reset	Access	Description
31:20	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
19:11	CTUNE	0x0A0	RW	Sets Oscillator Tuning Capacitance
				phase of the HFXO. Capacitance on HFXTAL_N and HFXTAL_P (pF) = ne 25pF (CLmax ~12.5pF). CL(DNLmax)=50fF ~ 0.6ppm (12.5ppm/pF).
10:7	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
6:0	IBTRIMXOCORE	0x20	RW	Sets the Startup Oscillator Core Bias Current
	This IBTRIMXOCOF Bits 6 and 5 may on	• • •	•	ne startup phase of the HFXO. Current (uA) = IBTRIMXOCORE X 40uA. cillator startup phase.

11.5.7 CMU_HFXOSTEADYSTATECTRL - HFXO Steady State Control

Offset			Bit Position		
0x030	30 30 29 28 29 28	26 26 27 23 23 23 20 20	01 10 10 10 11 12 13 14 15 17 17 17 18 19 10 10 10 10 10 11 12 12 12 12 12 12 12 12 12 12 13 14 15 16 17 18 18 19 10 10 10 10 11 12 12 12 12 12 12 12 12 12 13 14 15 16 17 18 18 19 10 10 11 12 12 12 <th>0 0 0 7</th> <th>0 0 4 8 7 - 0</th>	0 0 0 7	0 0 4 8 7 - 0
Reset	0xA	0 0x3	0x168	0xA	0x07
Access	XX X	RW RW	RW	RW W	RW
Name	REGISHUPPER	PEAKDETEN REGSELILOW	CTUNE	REGISH	IBTRIMXOCORE
Bit	Name	Reset Access	S Description		
04.00	DEGIGLILIBBED	0.4 514/	0.45		

Bit	Name	Reset	Access	Description
31:28	REGISHUPPER	0xA	RW	Set Regulator Output Current Level (shunt Regulator). lsh = 120uA + REGISHUPPER X 120uA
	Set to steady state v	alue of REGISH	+ 3.	
27	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
26	PEAKDETEN	0	RW	Enables Oscillator Peak Detectors
	Direct control allowe	d when PEAKDE	TSHUNTO	PTMODE=MANUAL and HFXO is ready.
25:24	REGSELILOW	0x3	RW	Controls Regulator Minimum Shunt Current Detection Relative to Nominal
	Steady state used d ready.	uring HFXO FSM	. Direct co	ntrol allowed when PEAKDETSHUNTOPTMODE=MANUAL and HFXO is
23:20	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
19:11	CTUNE	0x168	RW	Sets Oscillator Tuning Capacitance
	current optimization	algorithms). Capa	acitance or	state phase of the HFXO (as well as during the peak detection and shunt in HFXTAL_N and HFXTAL_P (pF) = Ctune = Cpar + CTUNE<8:0> X 40fF. x)=50fF ~ 0.6ppm (12.5ppm/pF).
10:7	REGISH	0xA	RW	Sets the Steady State Regulator Output Current Level (shunt Regulator)
				state phase of the HFXO. Direct control allowed when PEAKDETSHUN= 120uA + REGISH X 120uA.
6:0	IBTRIMXOCORE	0x07	RW	Sets the Steady State Oscillator Core Bias Current.
	the peak detection	algorithm. Direct	control all	ne steady state phase of the HFXO. It is also used as the initial value during owed when PEAKDETSHUNTOPTMODE=MANUAL and HFXO is ready. and 5 may only be high in the crystal oscillator startup phase

11.5.8 CMU_HFXOTIMEOUTCTRL - HFXO Timeout Control

Offset		Bit Po	sition	
0x034	15	19 19 16	6 4 5 7 7 1 9 8	r 0 r 4 m 7 r 0
Reset		0x2	0xA	0x6 7x0
Access		RW	RW	X X
Name		SHUNTOPTTIMEOUT	PEAKDETTIMEOUT	STEADYTIMEOUT

Bit	Name	Reset	Access	Description
31:20	Reserved	To ensure c	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
19:16	SHUNTOPTTIME- OUT	0x2	RW	Wait Duration in HFXO Shunt Current Optimization Wait State

Wait duration depends on the chosen XTAL (expected value is around 1 us). Program the desired duration measured in cycles of (at least) 83 ns.

Value	Mode	Description
0	2CYCLES	Timeout period of 2 cycles
1	4CYCLES	Timeout period of 4 cycles
2	16CYCLES	Timeout period of 16 cycles
3	32CYCLES	Timeout period of 32 cycles
4	256CYCLES	Timeout period of 256 cycles
5	1KCYCLES	Timeout period of 1024 cycles
6	2KCYCLES	Timeout period of 2048 cycles
7	4KCYCLES	Timeout period of 4096 cycles
8	8KCYCLES	Timeout period of 8192 cycles
9	16KCYCLES	Timeout period of 16384 cycles
10	32KCYCLES	Timeout period of 32768 cycles
-		

15:12 PEAKDETTIMEOUT 0xA RW Wait Duration in HFXO Peak Detection Wait State

Wait duration depends on the chosen XTAL (expected value is between 25 us and 200 us). Program the desired duration measured in cycles of (at least) 83 ns.

Value	Mode	Description
0	2CYCLES	Timeout period of 2 cycles
1	4CYCLES	Timeout period of 4 cycles
2	16CYCLES	Timeout period of 16 cycles
3	32CYCLES	Timeout period of 32 cycles

Bit	Name	Reset	Access	Description
	4	256CYCLES		Timeout period of 256 cycles
	5	1KCYCLES		Timeout period of 1024 cycles
	6	2KCYCLES		Timeout period of 2048 cycles
	7	4KCYCLES		Timeout period of 4096 cycles
	8	8KCYCLES		Timeout period of 8192 cycles
	9	16KCYCLES		Timeout period of 16384 cycles
	10	32KCYCLES		Timeout period of 32768 cycles
11:8	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:4	STEADYTIMEOUT	0x6	RW	Wait Duration in HFXO Startup Steady Wait State

Wait duration depends on the chosen XTAL (expected value is around 100 us). Program the desired duration measured in cycles of (at least) 83 ns.

Value	Mode		Description
0	2CYCLES		Timeout period of 2 cycles
1	4CYCLES		Timeout period of 4 cycles
2	16CYCLES		Timeout period of 16 cycles
3	32CYCLES		Timeout period of 32 cycles
4	256CYCLES		Timeout period of 256 cycles
5	1KCYCLES		Timeout period of 1024 cycles
6	2KCYCLES		Timeout period of 2048 cycles
7	4KCYCLES		Timeout period of 4096 cycles
8	8KCYCLES		Timeout period of 8192 cycles
9	16KCYCLES		Timeout period of 16384 cycles
10	32KCYCLES		Timeout period of 32768 cycles
STARTUPTIMEOUT	0x7	RW	Wait Duration in HFXO Startup Enable Wait State

Wait duration depends on the chosen XTAL (expected value is between 100 us and 1600 us). Program the desired duration measured in cycles of (at least) 83 ns.

Value	Mode	Description
0	2CYCLES	Timeout period of 2 cycles
1	4CYCLES	Timeout period of 4 cycles
2	16CYCLES	Timeout period of 16 cycles
3	32CYCLES	Timeout period of 32 cycles
4	256CYCLES	Timeout period of 256 cycles
5	1KCYCLES	Timeout period of 1024 cycles
6	2KCYCLES	Timeout period of 2048 cycles
7	4KCYCLES	Timeout period of 4096 cycles
8	8KCYCLES	Timeout period of 8192 cycles

3:0

Bit	Name	Reset	Access	Description					
	9	16KCYCLES		Timeout period of 16384 cycles					
	10	32KCYCLES		Timeout period of 32768 cycles					

11.5.9 CMU_LFXOCTRL - LFXO Control Register

Offset		Bit Position																														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•	•			0x7					0		•	5	S	-	0		Ş	Z		Š) N					00×0		•	
Access							X M					₩.			ک ا	Ž	S. N	₩ M		2	Š		2	<u>}</u>					Z.			
Name							TIMEOUT					BUFCUR			0	۲	AGC	HIGHAMPL		4				NO N					TUNING			

Bit	Name	Reset	Access	Description
31:27	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
26:24	TIMEOUT	0x7	RW	LFXO Timeout

Configures the start-up delay for LFXO. Do not change while LFXO is enabled. When starting up the LFXO after it has been completely turned off, use the TIMEOUT setting required by the XTAL. If the LFXO has been retained on in EM4, then the TIMEOUT=2cycles configuration is also allowed when re-enabling the LFXO after EM4 exit (as it is still running).

	Value	Mode		Description
	0	2CYCLES		Timeout period of 2 cycles
	1	256CYCLES		Timeout period of 256 cycles
	2	1KCYCLES		Timeout period of 1024 cycles
	3	2KCYCLES		Timeout period of 2048 cycles
	4	4KCYCLES		Timeout period of 4096 cycles
	5	8KCYCLES		Timeout period of 8192 cycles
	6	16KCYCLES		Timeout period of 16384 cycles
	7	32KCYCLES		Timeout period of 32768 cycles
23:21	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
20	BUFCUR	0	RW	LFXO Buffer Bias Current
	The default value enabled.	is intended to cove	r all use o	cases and reprogramming is not recommended. Do not change while LFXO is
19:18	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	CUR	0x0	RW	LFXO Current Trim
	The default value enabled.	is intended to cove	r all use o	cases and reprogramming is not recommended. Do not change while LFXO is
15	AGC	1	RW	LFXO AGC Enable
	Set this bit to enal	ole automatic gain	control wh	nich limits XTAL oscillation amplitude. Do not change while LFXO is enabled.
14	HIGHAMPL	0	RW	LFXO High XTAL Oscillation Amplitude Enable
	Set this bit to enal	ole high XTAL oscil	lation am	plitude. Do not change while LFXO is enabled.
13	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

tions

Bit	Name	Reset	Access	Description							
12:11	GAIN	0x2	RW	LFXO Startup Gain							
	The optimal values Studio for more		artup margin o	depends on the chosen XTAL. Refer to the device data sheet or Simplicity							
10	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-							
9:8	MODE	0x0	RW	LFXO Mode							
	Set this to config effect when 1 is LFXODIS in CM	written to LFXOE	ource for the N in CMU_O	LFXO. Do not change while LFXO is enabled. The oscillator setting takes SCENCMD. The oscillator setting is reset to default when 1 is written to							
	Value	Mode		Description							
	0	XTAL		32768 Hz crystal oscillator							
	1	BUFEXTCL	_K	An AC coupled buffer is coupled in series with LFXTAL_N pin, suitable for external sinus wave (32768 Hz).							
	2	DIGEXTCL	K	Digital external clock on LFXTAL_N pin. Oscillator is effectively bypassed.							
7	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-							
6:0	TUNING	0x00	RW	LFXO Internal Capacitor Array Tuning Value							
	Writing this field adjusts the internal load capacitance connected between LFXTAL_P and ground and LFXTAL_N and ground symmetrically (the higher the value, the higher the capacitance, the lower the frequency). Only increment or decrement by 1 LSB at a time.										

11.5.10 CMU_CALCTRL - Calibration Control Register

Offset				Bit Po	osition									
0x050	30 29 28	27 26 25 24	22 23	1	5 4 6 6 4 5 6 6	7 1 2	တ ထ	> 0 4	8 7 - 0					
Reset		0×0		0×0			0	0×0	0×0					
Access		RW		RW			RW	XX	W.W.					
				_				_	_					
Name		PRSDOWNSEL		PRSUPSEL			CONT	DOWNSEL	UPSEL					
Bit	Name	Reset	: Acce	ss Description	า									
31:28	Reserved	To ens	sure compatibil	ity with future de		write bits to	0. Mo	re information ir	1.2 Conven-					
27:24	PRSDOWNS	EL 0x0	RW	PRS Select	for PRS Inpu	ut When Se	elected	d in DOWNSEL						
	Select PRS in	put for PRS bas	sed calibration.	Only change wh	en calibration	circuit is off	f.							
	Value	Mode		Description										
	0	PRSC	CH0	PRS Chann	PRS Channel 0 selected as input									
	1	PRSC	PRS Chann	PRS Channel 1 selected as input										
	2	PRSC	PRS Chann	PRS Channel 2 selected as input										
	3	PRSC	CH3	PRS Chann	PRS Channel 3 selected as input									
	4	PRSC	CH4	PRS Chann	PRS Channel 4 selected as input									
	5	PRSC	CH5	PRS Chann	PRS Channel 5 selected as input									
	6	PRSC	CH6	PRS Chann	PRS Channel 6 selected as input									
	7	PRSC	CH7	PRS Chann	PRS Channel 7 selected as input									
	8	PRSC	CH8	PRS Chann	PRS Channel 8 selected as input									
	9	PRSC	CH9	PRS Chann	PRS Channel 9 selected as input									
	10	PRSC	H10	PRS Chann	PRS Channel 10 selected as input									
	11	PRSC	CH11	PRS Chann	iel 11 selected	l as input								
23:20	Reserved	To ens	sure compatibil	ity with future de	vices, always i	write bits to	0. Mo	re information ir	1.2 Conven-					
19:16	PRSUPSEL	0x0	RW	PRS Select	for PRS Inpu	ut When Se	elected	d in UPSEL						
	Select PRS in	put for PRS bas	sed calibration.	Only change who	en calibration	circuit is off	f.							
	Value	Mode		Description	Description									
	0	PRSC	CH0	PRS Chann	PRS Channel 0 selected as input									
	1	PRSC	H1	PRS Chann	PRS Channel 1 selected as input									
	2	PRSC	CH2	PRS Chann	PRS Channel 2 selected as input									
	3	PRSC	CH3	PRS Chann	PRS Channel 3 selected as input									
	4	PRSC	CH4	PRS Chann	el 4 selected a	as input								

Bit	Name	Reset	Access	Description								
	5	PRSCH5		PRS Channel 5 selected as input								
	6	PRSCH6		PRS Channel 6 selected as input								
	7	PRSCH7		PRS Channel 7 selected as input								
	8	PRSCH8		PRS Channel 8 selected as input								
	9	PRSCH9		PRS Channel 9 selected as input								
	10	10 PRSCH10		PRS Channel 10 selected as input								
	11	PRSCH11		PRS Channel 11 selected as input								
15:9	Reserved	To ensure comp	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-								
8	CONT	0	RW	Continuous Calibration								
	Set this bit to ena	ble continuous calibra	ation									
7:4	DOWNSEL	0x0	RW	Calibration Down-counter Select								
	Selects clock source for the calibration down-counter. Only change when calibration circuit is off.											
	Value	Mode		Description								
	0	HFCLK		Select HFCLK for down-counter								
	1	HFXO		Select HFXO for down-counter								
	2	LFXO		Select LFXO for down-counter								
	3	HFRCO		Select HFRCO for down-counter								
	4	LFRCO		Select LFRCO for down-counter								
	5	AUXHFRCO		Select AUXHFRCO for down-counter								
	6	PRS		Select PRS input selected by PRSDOWNSEL as down-counter								
3:0	UPSEL	0x0	RW	Calibration Up-counter Select								
	Selects clock sou	rce for the calibration	up-count	er. Only change when calibration circuit is off.								
	Value	Mode		Description								
	0	HFXO		Select HFXO as up-counter								
	1	LFXO		Select LFXO as up-counter								
	2	HFRCO		Select HFRCO as up-counter								
	3	LFRCO		Select LFRCO as up-counter								
	4	AUXHFRCO		Select AUXHFRCO as up-counter								
	5	PRS		Select PRS input selected by PRSUPSEL as up-counter								

11.5.11 CMU_CALCNT - Calibration Counter Register

Offset															Bi	t Po	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	∞	7	9	5	4	က	2	_	0
Reset																							00000x0									
Access																							RWH									
Name																							CALCNT									
Bit	Na	me					Re	set			Ac	ces	s l	Des	crip	tior																
31:20	Re	serv	red				To tion		ure	con	pati	bility	/ wi	th fu	ture	de	/ices	s, al	way	's wr	ite b	its	to 0.	Мо	re i	nforn	natio	on I	in 1.2	2 Co	nvei	n-
19:0	CA	LCN	١T				0x0	0000	00		RW	/H		Cali	brat	ion	Cou	unte	r													
	Wr	ite to	op v	alue	be	fore	cali	orati	on.	Rea	id ca	alibra	atio	n res	sult 1	from	this	s reg	giste	er wł	nen	Cal	librat	ion l	Rea	ady f	lag l	าลร	bee	n se	t.	

11.5.12 CMU_OSCENCMD - Oscillator Enable/Disable Command Register

	CMO_OSCENCIO	- Coomator End																		
Offset				Ві	it Positio	n														
0x060	31 30 29 29 27	26 24 23	2 2 8	19 19 17	15 16	4	13	12	7	10	6	∞	7	9	ည	4	က	7	_	0
Reset											0	0	0	0	0	0	0	0	0	0
Access											W1	W1	W1	W W	W W	W1	W W	W1	W W	W
Name											LFXODIS	LFXOEN	LFRCODIS	LFRCOEN	AUXHFRCODIS	AUXHFRCOEN	HFXODIS	HFXOEN	HFRCODIS	HFRCOEN
Bit	Name	Reset	Access	s Descrip	tion															
31:10	Reserved	To ensure o	ompatibility	/ with future	devices,	al	ways	s wr	ite b	oits t	o 0.	Мо	re in	forn	natio	on in	1.2	Co	nvei	7-
9	LFXODIS	0	W1	LFXO D	isable															
	Disables the LFXC lator is selected at this to take effect																			
8	LFXOEN	0	W1	LFXO E	nable															
	Enables the LFXC	. When waking u	p from EM4	4 make sure	e EM4UN	LA	TCH	l in I	ΞΜι	J_C	MD	is s	et fo	r thi	s to	take	e eff	ect		
7	LFRCODIS	0	W1	LFRCO	Disable															
	Disables the LFRO oscillator is selected for this to take effects	ed as the source																		
6	LFRCOEN	0	W1	LFRCO	Enable															
	Enables the LFRC	O. When waking	up from EN	M4 make su	ıre EM4U	NL	.ATC	H ir	ı EN	ИU_	СМІ	D is	set	for t	his t	to ta	ke e	effec	t	
5	AUXHFRCODIS	0	W1	AUXHF	RCO Dis	ab	le													
	Disables the AUXI	HFRCO. AUXHF	RCOEN has	s higher pri	ority if wr	itte	n sin	nulta	ane	ousl	y.									
4	AUXHFRCOEN	0	W1	AUXHF	RCO Ena	able	е													
	Enables the AUXI	IFRCO.																		
3	HFXODIS	0	W1	HFXO D	Disable															
	Disables the HFX0 cillator is selected			ity if written	simultar	eo	usly.	WA	ARN	IING	: Do	o no	t dis	able	the	HF	XO	if thi	is os	S-
2	HFXOEN	0	W1	HFXO E	nable															
	Enables the HFXC).																		

HFRCO Disable

HFRCO Enable

Disables the HFRCO. HFRCOEN has higher priority if written simultaneously. WARNING: Do not disable the HFRCO if this

Enables the HFRCO.

HFRCODIS

HFRCOEN

0

oscillator is selected as the source for HFCLK.

0

W1

1

0

11.5.13 CMU_CMD - Command Register

Offset	Bit Position
0x064	0 1 2 3 4 5 2 6 0 8 8 0 10 11 12 13 14 15 14 15 15 15 15 15 15 15 15 15 15 15 15 15
Reset	0000
Access	M M M M M M M M M M M M M M M M M M M
Name	HEXOSHUNTOPTSTART HEXOPEAKDETSTART CALSTOP CALSTOP

Bit	Name	Reset	Access	Description										
31:6	Reserved	To ensure comp tions	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-										
5	HFXOSHUNTOPT- START	0	W1	HFXO Shunt Current Optimization Start										
	Starts the HFXO Shu	Starts the HFXO Shunt Current Optimization and runs it one time.												
4	HFXOPEAKDET- START	0	W1	HFXO Peak Detection Start										
	Starts the HFXO pea	k detection and ru	ins it one	time.										
	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions													
3:2	Reserved		patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-										
3:2	Reserved CALSTOP	tions	patibility v W1	vith future devices, always write bits to 0. More information in 1.2 Conven- Calibration Stop										
3:2		tions 0												
3:2 1 0	CALSTOP	0 counters.												

11.5.14 CMU_DBGCLKSEL - Debug Trace Clock Select

Offset	Bit Position											
0x070	4 2 2 3 <th>e 2 -</th> <th>0</th>	e 2 -	0									
Reset			0x0									
Access			RW									
Name			DBG									

Bit	Name	Reset	Access	Description								
31:1	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
0:0	DBG	0x0	RW	Debug Trace Clock								
	Select clock used	Select clock used for debug trace.										
	Value	Mode		Description								
	0	AUXHFRCO		AUXHFRCO is the debug trace clock								
	1	HFCLK		HFCLK is the debug trace clock								

11.5.15 CMU_HFCLKSEL - High Frequency Clock Select Command Register

Offset	Bit Position											
0x074	31 30 30 30 30 30 30 30 30 30 30 4 4 4 4 4	0 7 7 8										
Reset		0×0										
Access		W N										
Name		生										

Bit	Name	Reset	Access	Description							
31:3	Reserved	To ensure c	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 tions								
2:0	HF	0x0	W1	HFCLK Select							

Selects the clock source for HFCLK. Note that selecting an oscillator that is disabled will cause the system clock to stop. Check the status register and confirm that oscillator is ready before switching. If the system can deal with a temporarily stopped system clock, then it is okay to switch to an oscillator as soon as the status register indicates that the oscillator has been enabled successfully.

Value	Mode	Description
1	HFRCO	Select HFRCO as HFCLK
2	HFXO	Select HFXO as HFCLK
3	LFRCO	Select LFRCO as HFCLK
4	LFXO	Select LFXO as HFCLK
5	HFRCODIV2	Select HFRCO divided by 2 as HFCLK
7	CLKIN0	Select CLKIN0 as HFCLK

11.5.16 CMU_LFACLKSEL - Low Frequency A Clock Select Register

Offset	Bit Position										
0x080	31 31 32 33 33 33 34 35 35 35 35 35 35 35 35 35 35 35 35 35	0 1 2									
Reset		0×0									
Access		S S									
Name		LFA									

		Reset	Access	Description									
31:3	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-									
2:0	LFA	0x0	RW	Clock Select for LFA									
	Selects the clock source for LFACLK.												
	Value	Mode		Description									
	0	DISABLED		LFACLK is disabled									
	1	LFRCO		LFRCO selected as LFACLK									
	2	LFXO		LFXO selected as LFACLK									
	4	ULFRCO		ULFRCO selected as LFACLK									

11.5.17 CMU_LFBCLKSEL - Low Frequency B Clock Select Register

Offset	Bit Position										
0x084	3 3 3 5 7 7 8 8 7 7 9 8 7 7 9 8 8 7 7 9 8 8 7 7 9 8 8 7 7 9 8 8 8 8	0 1 2									
Reset		0×0									
Access		S S									
Name		LFB									

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	LFB	0x0	RW	Clock Select for LFB
	Selects the clock	k source for LFBCLh	ζ.	
	Value	Mode		Description
	0	DISABLED		LFBCLK is disabled
	1	LFRCO		LFRCO selected as LFBCLK
	2	LFXO		LFXO selected as LFBCLK
	3	HFCLKLE		HFCLK divided by two/four is selected as LFBCLK
	4	ULFRCO		ULFRCO selected as LFBCLK

11.5.18 CMU_LFECLKSEL - Low Frequency E Clock Select Register

Offset	Bit Position	
0x088	31 30 29 29 29 27 27 27 27 27 27 27 27 27 27 27 27 27	0 7 5
Reset		0×0
Access		S S
Name		E

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	LFE	0x0	RW	Clock Select for LFE
	Selects the clock take effect	source for LFECLK	K. When wal	king up from EM4 make sure EM4UNLATCH in EMU_CMD is set for this to
	Value	Mode		Description
	0	DISABLED		LFECLK is disabled
	1	LFRCO		LFRCO selected as LFECLK
	2	LFXO		LFXO selected as LFECLK
	4	ULFRCO		ULFRCO selected as LFECLK

11.5.19 CMU_STATUS - Status Register

Offset															В	it Po	ositi	on														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset			0	0	0	0	0	0	0	0	0			•	•	-		•		•		•	0	0	0	0	0	0	0	0	_	_
Access			22	22	22	22	22	2	22	2	22					2							2	22	2	22	2	22	22	2	22	<u>~</u>
Name			ULFRCOPHASE	LFRCOPHASE	LFXOPHASE	HFXOREGILOW	HFXOAMPLOW	HFXOAMPHIGH	HFXOSHUNTOPTRDY	HFXOPEAKDETRDY	HFXOREQ					CALRDY							LFXORDY	LFXOENS	LFRCORDY	LFRCOENS	AUXHFRCORDY	AUXHFRCOENS	HFXORDY	HFXOENS	HFRCORDY	HFRCOENS

Bit	Name	Reset	Access	Description
31:30	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
29	ULFRCOPHASE	0	R	ULFRCO Clock Phase
	Used to determine if	ULFRCO is in hi	igh or low p	phase.
28	LFRCOPHASE	0	R	LFRCO Clock Phase
	Used to determine if	LFRCO is in hig	h or low ph	ase.
27	LFXOPHASE	0	R	LFXO Clock Phase
	Used to determine if	LFXO is in high	or low phas	se.
26	HFXOREGILOW	0	R	HFXO Regulator Shunt Current Too Low
	HFXO regulator shun CMU_HFXOSTEAD\			ing PEAKDETSHUNTOPTMODE=MANUAL, the REGISH value in need up by 1 LSB.
25	HFXOAMPLOW	0	R	HFXO Amplitude Tuning Value Too Low
	HFXO oscillation amp			ing PEAKDETSHUNTOPTMODE=MANUAL, the IBTRIMXOCORE value in need up by 1 LSB.
24	HFXOAMPHIGH	0	R	HFXO Oscillation Amplitude is Too High
	HFXO oscillation amp			sing PEAKDETSHUNTOPTMODE=MANUAL, the IBTRIMXOCORE value in need down by 1 LSB.
23	HFXOSHUNTOPTR- DY	0	R	HFXO Shunt Current Optimization Ready
	HFXO shunt current	optimization is re	eady.	
22	HFXOPEAKDETRDY	′ 0	R	HFXO Peak Detection Ready
	HFXO peak detection	n is ready.		
21	HFXOREQ	0	R	HFXO is Required By Hardware
		HFXO can be pe	erformed a	d HFXO should typically not be disabled or deselected. Whether disabling nd whether this leads to setting of HFXODISERR depends on whether the
20:17	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
16	CALRDY	1	R	Calibration Ready
	Calibration is Ready	(0 when calibrate	tion is ongo	ing).
15:10	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
9	LFXORDY	0	R	LFXO Ready
	LFXO is enabled and	d start-up time h	as exceede	d.
8	LFXOENS	0	R	LFXO Enable Status
	LFXO is enabled (sh	ows disabled sta	atus if EM4	repaint is required).
7	LFRCORDY	0	R	LFRCO Ready
	LFRCO is enabled a	nd start-up time	has exceed	ded.
6	LFRCOENS	0	R	LFRCO Enable Status
	LFRCO is enabled (s	shows disabled	status if EM	4 repaint is required).
5	AUXHFRCORDY	0	R	AUXHFRCO Ready
	AUXHFRCO is enab	led and start-up	time has ex	xceeded.
4	AUXHFRCOENS	0	R	AUXHFRCO Enable Status
	AUXHFRCO is enab	led.		
3	HFXORDY	0	R	HFXO Ready
	HFXO is enabled and	d start-up time h	as exceede	ed.
2	HFXOENS	0	R	HFXO Enable Status
	HFXO is enabled.			
1	HFRCORDY	1	R	HFRCO Ready
	HFRCO is enabled a	nd start-up time	has excee	ded.
0	HFRCOENS	1	R	HFRCO Enable Status
	HFRCO is enabled.			

11.5.20 CMU_HFCLKSTATUS - HFCLK Status Register

Officet															D:	4 D.	-:4:	0.10														
Offset														T	ВІ	t Po	SITIO	on		T					T	ı				I		
0x094	31	30	53	78	27	26	25	24	23	22	7	20	19	18	17	16	15	4	13	12	7	9	6	ω	^	9	2	4	3	7	_	0
Reset																															0 X	
Access																															<u>~</u>	
Name																															SELECTED	
Bit	Na	me					Re	set			Ac	cess	s I	Des	crip	tion																
31:3	Re	serv	red				To tion		ure	com	pati	bility	/ Wit	th fu	ture	dev	ices	s, alı	way	s wi	ite k	its t	o 0.	Мо	re in	forn	natio	n in	1.2	Col	nver	7-
2:0	SE	LEC	TED)			0x1	1			R			HFC	LK	Sele	cte	d														
	Clo	ock s	selec	ted	as I	HFC	LK	cloc	k so	urce	Э.																					
	Va	lue					Мо	de						Des	cript	ion																_
	1						HF	RC)					HFR	CO	is se	elec	ted	as ŀ	HFC	LK	clock	so	urce	;							_
	2						HF	хо					l	HFX	O is	sele	ecte	d as	s HF	CLI	< clo	ock s	our	се								
	3						LFI	RCC)				ı	LFR	СО	is se	elect	ted a	as F	IFC	_K c	lock	sou	ırce								
							LF)	VO						LFX	O is	sele	ecte	d as	HF	CL	Clo	ck s	our	ce								
	4						LL	۸٥																								
	4 5) DDI\	/2				HFR	CO	divid	ded	by 2	2 is	sele	ctec	l as	HF	CLK	cloc	ck so	ourc	е				

11.5.21 CMU_HFXOTRIMSTATUS - HFXO Trim Status

Offset															В	it Po	siti	on														
0x09C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•		•	•							•		•	•			•		•				K X O				•	00×0			
Access																							ſ	Y					~			
Name																							- - - - - -	KEGISH					IBTRIMXOCORE			

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
10:7	REGISH	0xA	R	Value of REGISH Found By Automatic HFXO Shunt Current Optimization Algorithm
	Can be used as initiagagain.	al value for RE0	GISH value i	n the CMU_HFXOSTEADYSTATECTRL register if HFXO is to be started
6:0	IBTRIMXOCORE	0x00	R	Value of IBTRIMXOCORE Found By Automatic HFXO Peak Detection Algorithm
	Can be used as initiagagain.	al value for IBT	RIMXOCOR	E in the CMU_HFXOSTEADYSTATECTRL register if HFXO is to be started

11.5.22 CMU_IF - Interrupt Flag Register

Offset															В	it Po	siti	on														
0x0A0	31	30	29	28	27	26	25	24	23	22	12	20	19	18	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	_	0
Reset	0		0	0	0													0	0	0	0	0	0	0		0	0	0	0	0	0	_
Access	2		œ	22	œ													2	2	22	2	œ	~	22		22	2	22	2	2	œ	~
Name	CMUERR		ULFRCOEDGE	LFRCOEDGE	LFXOEDGE													LFTIMEOUTERR	HFRCODIS	HFXOSHUNTOPTRDY	HFXOPEAKDETRDY	HFXOPEAKDETERR	HFXOAUTOSW	HFXODISERR		CALOF	CALRDY	AUXHFRCORDY	LFXORDY	LFRCORDY	HFXORDY	HFRCORDY
Bit	Na	me					Re	set			Ac	ces	s	Des	crip	tior																
31	CN	1UE	RR				0				R			СМ	U Er	ror	Inte	rrup	ot Fl	ag												
	Se	t upo	on il	lega	II CN	۸U۱	write	atte	emp	ot (e	e.g. v	/ritin	g C	CMU	_LFF	RCC	СТ	RL v	vhile	LFI	RCC)BS	Y is	set)).							
30	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions ULFRCOEDGE 0 R ULFRCO Clock Edge Detected Interrupt Flag															nvei	7-															
29	ULFRCOEDGE 0 R ULFRCO Clock Edge Detected Interrupt Flag																															
	ULFRCOEDGE 0 R ULFRCO Clock Edge Detected Interrupt Flag Sets when ULFRCO clock switches phases.																															
28	LFI	RCC	DED	GE			0				R			LFF	CO	Clo	ck l	Edg	e De	etec	ted	Inte	rrup	ot FI	ag							
	Se	ts w	hen	LFF	RCO	clo	ck s	witc	hes	ph	ases	i.																				
27	LF	XOE	DG	E			0				R			LF	(O C	loc	ς Eα	dge	Dete	ecte	d In	terr	upt	Flag	g							
	Se	ts w	hen	LF>	(O c	lock	< sw	itch	es p	has	ses.																					
26:15	Re	serv	/ed				To tion		ure	CO	mpat	ibilit	y w	ith f	ıture	de	/ice	s, al	way	s wr	ite k	its t	o 0.	Мо	re in	forn	natio	on in	1.2	? Co	nvei	า-
14	LF	TIMI	EOL	JTEI	RR		0				R			Lov	v Fre	eque	enc	y Tiı	meo	ut E	rro	r Int	errı	ıpt F	-lag							
											OCT ster t				befo	re t	ne c	omb	oined	TS b	'AR'	TUP	TIM	IEO	UT p	olus	STE	EAD	YTII	MEC	DUT	of
13	HF	RC	ODIS	S			0				R			HF	RCO	Dis	abl	e Int	terru	ıpt l	Flag	ı										
	Se	t wh	en a	a rur	nin	g HF	FRC	O is	dis	abl	ed b	ecau	ıse	of a	uton	natio	HF	XO	start	and	d se	lecti	on.									
12	HF DY		SHU	NT	OPT	R-	0				R			HF	(O A	luto	ma	tic S	hun	it C	urre	nt C	pti	miza	atio	n Re	eady	/ Int	erru	ıpt F	Flag	
	Se	t wh	en a	auto	mati	ic H	FXC	sh	unt d	cur	rent (optir	niza	ation	is re	eady	'															
11	HF	XOI	PEA	KDE	TR	DY	0				R			HFX	(O A	uto	ma	tic P	eak	De	tect	ion	Rea	dy I	nte	rrup	t Fl	ag				
	Se	t wh	en a	auto	mati	ic H	FXC) pe	ak d	lete	ection	ı is r	ead	dy.																		
10	HF	XOF	PEA	KDE	ETEI	RR	0				R			HF	(O A	uto	ma	tic P	eak	De	tect	ion	Erro	or In	terr	upt	Fla	g				

HFXOAUTOSW

9

Set when automatic HFXO peak detection failed.

0

R

Set when automatic selection of HFXO causes a switch of the source clock used for HFCLKSRC.

HFXO Automatic Switch Interrupt Flag

Bit	Name	Reset	Access	Description
8	HFXODISERR	0	R	HFXO Disable Error Interrupt Flag
	Set when software to not disabled/deseled		eselect the I	HFXO in case the automatic enable/select reason is met. The HFXO was
7	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
6	CALOF	0	R	Calibration Overflow Interrupt Flag
	Set when calibration	overflow has oc	curred (i.e.	if a new calibration completes before CMU_CALCNT has been read).
5	CALRDY	0	R	Calibration Ready Interrupt Flag
	Set when calibration	is completed.		
4	AUXHFRCORDY	0	R	AUXHFRCO Ready Interrupt Flag
	Set when AUXHFRO	CO is ready (star	t-up time ex	cceeded).
3	LFXORDY	0	R	LFXO Ready Interrupt Flag
	Set when LFXO is re	eady (start-up tin	ne exceede	d). LFXORDY can be used as wake-up interrupt.
2	LFRCORDY	0	R	LFRCO Ready Interrupt Flag
	Set when LFRCO is	ready (start-up t	ime exceed	led). LFRCORDY can be used as wake-up interrupt.
1	HFXORDY	0	R	HFXO Ready Interrupt Flag
	Set when HFXO is re	eady (start-up tir	ne exceede	d).
0	HFRCORDY	1	R	HFRCO Ready Interrupt Flag
	Set when HFRCO is	ready (start-up	time exceed	ded).

11.5.23 CMU_IFS - Interrupt Flag Set Register

Offset															Ві	it Po	siti	on														
0x0A4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	0		0	0	0			•							•	•		0	0	0	0	0	0	0		0	0	0	0	0	0	0
Access	W1		×	W1	W1													×	W	W	W1	W	W1	W 1		W	×	W	W1	W1	W	W1
Name	CMUERR		ULFRCOEDGE	LFRCOEDGE	LFXOEDGE													LFTIMEOUTERR	HFRCODIS	HFXOSHUNTOPTRDY	HFXOPEAKDETRDY	HFXOPEAKDETERR	HFXOAUTOSW	HFXODISERR		CALOF	CALRDY	AUXHFRCORDY	LFXORDY	LFRCORDY	HFXORDY	HFRCORDY

Bit Name Reset Access Description 31 CMUERR 0 W1 Set CMUERR Interrupt Flag	
31 CMUERR 0 W1 Set CMUERR Interrupt Flag	
Write 1 to set the CMUERR interrupt flag	
30 Reserved To ensure compatibility with future devices, always write bits to 0. More infortions	rmation in 1.2 Conven-
29 ULFRCOEDGE 0 W1 Set ULFRCOEDGE Interrupt Flag	
Write 1 to set the ULFRCOEDGE interrupt flag	
28 LFRCOEDGE 0 W1 Set LFRCOEDGE Interrupt Flag	
Write 1 to set the LFRCOEDGE interrupt flag	
27 LFXOEDGE 0 W1 Set LFXOEDGE Interrupt Flag	
Write 1 to set the LFXOEDGE interrupt flag	
26:15 Reserved To ensure compatibility with future devices, always write bits to 0. More infortions	rmation in 1.2 Conven-
14 LFTIMEOUTERR 0 W1 Set LFTIMEOUTERR Interrupt Flag	
Write 1 to set the LFTIMEOUTERR interrupt flag	
13 HFRCODIS 0 W1 Set HFRCODIS Interrupt Flag	
Write 1 to set the HFRCODIS interrupt flag	
12 HFXOSHUNTOPTR- 0 W1 Set HFXOSHUNTOPTRDY Interrupt Flag DY	
Write 1 to set the HFXOSHUNTOPTRDY interrupt flag	
11 HFXOPEAKDETRDY 0 W1 Set HFXOPEAKDETRDY Interrupt Flag	
Write 1 to set the HFXOPEAKDETRDY interrupt flag	
10 HFXOPEAKDETERR 0 W1 Set HFXOPEAKDETERR Interrupt Flag	
Write 1 to set the HFXOPEAKDETERR interrupt flag	
9 HFXOAUTOSW 0 W1 Set HFXOAUTOSW Interrupt Flag	
Write 1 to set the HFXOAUTOSW interrupt flag	
8 HFXODISERR 0 W1 Set HFXODISERR Interrupt Flag	
Write 1 to set the HFXODISERR interrupt flag	

Bit	Name	Reset	Access	Description
7	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
6	CALOF	0	W1	Set CALOF Interrupt Flag
	Write 1 to set the CA	LOF interrupt fla	ag	
5	CALRDY	0	W1	Set CALRDY Interrupt Flag
	Write 1 to set the CA	LRDY interrupt	flag	
4	AUXHFRCORDY	0	W1	Set AUXHFRCORDY Interrupt Flag
	Write 1 to set the AL	IXHFRCORDY i	nterrupt flag	3
3	LFXORDY	0	W1	Set LFXORDY Interrupt Flag
	Write 1 to set the LF	XORDY interrup	ot flag	
2	LFRCORDY	0	W1	Set LFRCORDY Interrupt Flag
	Write 1 to set the LF	RCORDY interre	upt flag	
1	HFXORDY	0	W1	Set HFXORDY Interrupt Flag
	Write 1 to set the HF	XORDY interrup	ot flag	
0	HFRCORDY	0	W1	Set HFRCORDY Interrupt Flag
	Write 1 to set the HF	RCORDY interr	upt flag	

11.5.24 CMU_IFC - Interrupt Flag Clear Register

Offset															Ві	it Po	siti	on														
0x0A8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset	0		0	0	0											•		0	0	0	0	0	0	0		0	0	0	0	0	0	0
Access	(R)W1		(R)W1	(R)W1	(R)W1													(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1		(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name	CMUERR		ULFRCOEDGE	LFRCOEDGE	LFXOEDGE													LFTIMEOUTERR	HFRCODIS	HFXOSHUNTOPTRDY	HFXOPEAKDETRDY	HFXOPEAKDETERR	HFXOAUTOSW	HFXODISERR		CALOF	CALRDY	AUXHFRCORDY	LFXORDY	LFRCORDY	HFXORDY	HFRCORDY

	CMUER ULFRCO LFRCO			LFTIME HFXCO HFXCO HFXCO HFXCO HFXCO CALCO CALCO CALCO CALCO CALCO CALCO HFXCO HFXCO HFXCO
Bit	Name	Reset	Access	Description
31	CMUERR	0	(R)W1	Clear CMUERR Interrupt Flag
	Write 1 to clear the 0 (This feature must be			iding returns the value of the IF and clears the corresponding interrupt flags .
30	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
29	ULFRCOEDGE	0	(R)W1	Clear ULFRCOEDGE Interrupt Flag
	Write 1 to clear the L flags (This feature m			g. Reading returns the value of the IF and clears the corresponding interrupt MSC.).
28	LFRCOEDGE	0	(R)W1	Clear LFRCOEDGE Interrupt Flag
	Write 1 to clear the L flags (This feature m			Reading returns the value of the IF and clears the corresponding interrupt // ISC.).
27	LFXOEDGE	0	(R)W1	Clear LFXOEDGE Interrupt Flag
	Write 1 to clear the L flags (This feature m			leading returns the value of the IF and clears the corresponding interrupt MSC.).
26:15	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
14	LFTIMEOUTERR	0	(R)W1	Clear LFTIMEOUTERR Interrupt Flag
	Write 1 to clear the L rupt flags (This featu			ag. Reading returns the value of the IF and clears the corresponding inter-
13	HFRCODIS	0	(R)W1	Clear HFRCODIS Interrupt Flag
	Write 1 to clear the H			eading returns the value of the IF and clears the corresponding interrupt //ISC.).
12	HFXOSHUNTOPTR DY	- 0	(R)W1	Clear HFXOSHUNTOPTRDY Interrupt Flag
	Write 1 to clear the Hinterrupt flags (This f			rupt flag. Reading returns the value of the IF and clears the corresponding bally in MSC.).
11	HFXOPEAKDETRD	Y 0	(R)W1	Clear HFXOPEAKDETRDY Interrupt Flag
	Write 1 to clear the Finterrupt flags (This f			upt flag. Reading returns the value of the IF and clears the corresponding bally in MSC.).

Bit	Name	Reset	Access	Description
10	HFXOPEAKDETER	₹ 0	(R)W1	Clear HFXOPEAKDETERR Interrupt Flag
	Write 1 to clear the Finterrupt flags (This f			upt flag. Reading returns the value of the IF and clears the corresponding obally in MSC.).
9	HFXOAUTOSW	0	(R)W1	Clear HFXOAUTOSW Interrupt Flag
	Write 1 to clear the Frupt flags (This featu			g. Reading returns the value of the IF and clears the corresponding inter-y in MSC.).
8	HFXODISERR	0	(R)W1	Clear HFXODISERR Interrupt Flag
	Write 1 to clear the F flags (This feature m			. Reading returns the value of the IF and clears the corresponding interrupt MSC.).
7	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6	CALOF	0	(R)W1	Clear CALOF Interrupt Flag
	Write 1 to clear the 0 (This feature must be			ng returns the value of the IF and clears the corresponding interrupt flags
5	CALRDY	0	(R)W1	Clear CALRDY Interrupt Flag
	Write 1 to clear the 0 (This feature must be			ding returns the value of the IF and clears the corresponding interrupt flags i.
4	AUXHFRCORDY	0	(R)W1	Clear AUXHFRCORDY Interrupt Flag
	Write 1 to clear the A rupt flags (This featu			ag. Reading returns the value of the IF and clears the corresponding inter-y in MSC.).
3	LFXORDY	0	(R)W1	Clear LFXORDY Interrupt Flag
	Write 1 to clear the L flags (This feature m			ading returns the value of the IF and clears the corresponding interrupt MSC.).
2	LFRCORDY	0	(R)W1	Clear LFRCORDY Interrupt Flag
	Write 1 to clear the L flags (This feature m			Reading returns the value of the IF and clears the corresponding interrupt MSC.).
1	HFXORDY	0	(R)W1	Clear HFXORDY Interrupt Flag
	Write 1 to clear the F flags (This feature m			eading returns the value of the IF and clears the corresponding interrupt MSC.).
0	HFRCORDY	0	(R)W1	Clear HFRCORDY Interrupt Flag
	Write 1 to clear the F flags (This feature m			Reading returns the value of the IF and clears the corresponding interrupt MSC.).

11.5.25 CMU_IEN - Interrupt Enable Register

Offset															Ві	t Po	siti	on														
0x0AC	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset	0		0	0	0							•				'		0	0	0	0	0	0	0		0	0	0	0	0	0	0
Access	RW		W.	RW	₽													₽	RW	₽	RW	₽	RW	₽		₽	₽	R≷	W.	R	₽	RW
Name	CMUERR		ULFRCOEDGE	LFRCOEDGE	LFXOEDGE													LFTIMEOUTERR	HFRCODIS	HFXOSHUNTOPTRDY	HFXOPEAKDETRDY	HFXOPEAKDETERR	HFXOAUTOSW	HFXODISERR		CALOF	CALRDY	AUXHFRCORDY	LFXORDY	LFRCORDY	HFXORDY	HFRCORDY

	RS JULY F			
Bit	Name	Reset	Access	Description
31	CMUERR	0	RW	CMUERR Interrupt Enable
	Enable/disable the CN	MUERR interrup	t	
30	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
29	ULFRCOEDGE	0	RW	ULFRCOEDGE Interrupt Enable
	Enable/disable the UL	FRCOEDGE in	terrupt	
28	LFRCOEDGE	0	RW	LFRCOEDGE Interrupt Enable
	Enable/disable the LF	RCOEDGE inte	rrupt	
27	LFXOEDGE	0	RW	LFXOEDGE Interrupt Enable
	Enable/disable the LF	XOEDGE interr	upt	
26:15	Reserved	To ensure cor	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
14	LFTIMEOUTERR	0	RW	LFTIMEOUTERR Interrupt Enable
	Enable/disable the LF	TIMEOUTERR	interrupt	
13	HFRCODIS	0	RW	HFRCODIS Interrupt Enable
	Enable/disable the HF	RCODIS interru	upt	
12	HFXOSHUNTOPTR- DY	0	RW	HFXOSHUNTOPTRDY Interrupt Enable
	Enable/disable the HF	XOSHUNTOPT	RDY inter	rupt
11	HFXOPEAKDETRDY	0	RW	HFXOPEAKDETRDY Interrupt Enable
	Enable/disable the HF	XOPEAKDETR	DY interru	pt
10	HFXOPEAKDETERR	0	RW	HFXOPEAKDETERR Interrupt Enable
	Enable/disable the HF	XOPEAKDETE	RR interru	pt
9	HFXOAUTOSW	0	RW	HFXOAUTOSW Interrupt Enable
	Enable/disable the HF	XOAUTOSW ir	nterrupt	
8	HFXODISERR	0	RW	HFXODISERR Interrupt Enable
	Enable/disable the HF	XODISERR into	errupt	

Bit	Name	Reset	Access	Description
7	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
6	CALOF	0	RW	CALOF Interrupt Enable
	Enable/disable the C	CALOF interrupt		
5	CALRDY	0	RW	CALRDY Interrupt Enable
	Enable/disable the C	CALRDY interrupt		
4	AUXHFRCORDY	0	RW	AUXHFRCORDY Interrupt Enable
	Enable/disable the A	UXHFRCORDY i	interrupt	
3	LFXORDY	0	RW	LFXORDY Interrupt Enable
	Enable/disable the L	FXORDY interrup	ot	
2	LFRCORDY	0	RW	LFRCORDY Interrupt Enable
	Enable/disable the L	FRCORDY interr	upt	
1	HFXORDY	0	RW	HFXORDY Interrupt Enable
	Enable/disable the H	IFXORDY interru	ot	
0	HFRCORDY	0	RW	HFRCORDY Interrupt Enable
	Enable/disable the H	IFRCORDY interr	rupt	

11.5.26 CMU_HFBUSCLKEN0 - High Frequency Bus Clock Enable Register 0

Offset															Bi	t Po	siti	on														
0x0B0	31	30	29	28	27	26	25	24	23	22	21	20	9	9	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset													ı														0	0	0	0	0	0
Access																											% ≷	% ≷	% ≷	₩ M	₩	RW
Name																											GPCRC	LDMA	PRS	GPIO	CRYPT00	Ш

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure c	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
5	GPCRC	0	RW	General Purpose CRC Clock Enable
	Set to enable the o	lock for GPCRC.		
4	LDMA	0	RW	Linked Direct Memory Access Controller Clock Enable
	Set to enable the o	lock for LDMA.		
3	PRS	0	RW	Peripheral Reflex System Clock Enable
	Set to enable the o	lock for PRS.		
2	GPIO	0	RW	General purpose Input/Output Clock Enable
	Set to enable the o	clock for GPIO.		
1	CRYPTO0	0	RW	Advanced Encryption Standard Accelerator 0 Clock Enable
	Set to enable the o	clock for CRYPTO	00.	
0	LE	0	RW	Low Energy Peripheral Interface Clock Enable
	Set to enable the o	clock for LE. Inter	face used fo	r bus access to Low Energy peripherals.

11.5.27 CMU_HFPERCLKEN0 - High Frequency Peripheral Clock Enable Register 0

Offset															Bi	t Po	siti	on														
0x0C0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset			•		•	•	•										•			•	0	0	0	0	0	0	0	0	0	0	0	0
Access																					R M	R.	RW	₽	M	₽	Σ	₩ M	Σ	R M M	₽	RW
Name																					IDAC0	VDAC0	ADC0	12C0	CRYOTIMER	ACMP1	ACMP0	USART1	USARTO	WTIMERO	TIMER1	TIMERO

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure comp tions	oatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	IDAC0	0	RW	Current Digital to Analog Converter 0 Clock Enable
	Set to enable the clo	ock for IDAC0.		
10	VDAC0	0	RW	Digital to Analog Converter 0 Clock Enable
	Set to enable the clo	ock for VDAC0.		
9	ADC0	0 1	RW	Analog to Digital Converter 0 Clock Enable
	Set to enable the clo	ock for ADC0.		
8	I2C0	0 1	RW	I2C 0 Clock Enable
	Set to enable the clo	ock for I2C0.		
7	CRYOTIMER	0	RW	CRYOTIMER Clock Enable
	Set to enable the clo	ock for CRYOTIMER	₹.	
6	ACMP1	0 I	RW	Analog Comparator 1 Clock Enable
	Set to enable the clo	ock for ACMP1.		
5	ACMP0	0 1	RW	Analog Comparator 0 Clock Enable
	Set to enable the clo	ock for ACMP0.		
4	USART1	0 1	RW	Universal Synchronous/Asynchronous Receiver/Transmitter 1 Clock Enable
	Set to enable the clo	ock for USART1.		
3	USART0	0 1	RW	Universal Synchronous/Asynchronous Receiver/Transmitter 0 Clock Enable
	Set to enable the clo	ock for USART0.		
2	WTIMER0	0 1	RW	Wide Timer 0 Clock Enable
	Set to enable the clo	ock for WTIMER0.		
1	TIMER1	0 1	RW	Timer 1 Clock Enable
	Set to enable the clo	ock for TIMER1.		
0	TIMER0	0	RW	Timer 0 Clock Enable
	Set to enable the clo	ock for TIMER0.		

11.5.28 CMU_HFRADIOALTCLKEN0 - High Frequency Alternate Radio Peripheral Clock Enable Register 0

Offset	Bit Position
0x0CC	33 34 36 37 38 39 30 30 31 32 33 34 35 36 37 47 48 40
Reset	
Access	
Name	

Bit	Name	Reset	Access	Description
31:0	Reserved	To ensure contions	npatibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-

11.5.29 CMU_LFACLKEN0 - Low Frequency a Clock Enable Register 0 (Async Reg)

Offset	Bit Position	
0x0E0	33 34 6 6 6 6 6 6 6 6 6 7 7 8 9 9 9 9	- 0
Reset		0
Access		RW RW
Name		LESENSE

Bit	Name	Reset	Access	Description									
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-									
1	LESENSE	0	RW	Low Energy Sensor Interface Clock Enable									
	Set to enable the cloc	k for LESENSE.											
0	LETIMER0	0	RW	Low Energy Timer 0 Clock Enable									
	Set to enable the cloc	Set to enable the clock for LETIMER0.											

11.5.30 CMU_LFBCLKEN0 - Low Frequency B Clock Enable Register 0 (Async Reg)

Offset															Bi	t Pc	siti	on														
0x0E8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	7	_	0
Reset		•	'		'							•		'													'	•	'		0	0
Access																															₽	Z N
Name																															LEUART0	SYSTICK

Bit	Name	Reset	Access	Description							
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-							
1	LEUART0	0	RW	Low Energy UART 0 Clock Enable							
	Set to enable the cloc	k for LEUART0.									
0	SYSTICK	0	RW	Clock Enable							
	Set to enable the cloc	e clock for SYSTICK.									

11.5.31 CMU_LFECLKEN0 - Low Frequency E Clock Enable Register 0 (Async Reg)

Offset	Bit Position	
0x0F0	3 3 4 4 2 9 9 0 1 1 1 1 2 1 3 1 4 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	7 - 0
Reset		0
Access		RW
Name		RTCC

Bit	Name	Reset	Access	Description							
31:1	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-							
0	RTCC	0	RW	Real-Time Counter and Calendar Clock Enable							
	Set to enable the clo	ock for RTCC.									

11.5.32 CMU_HFPRESC - High Frequency Clock Prescaler Register

Offset															Ві	t Po	siti	on														
0x100	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset					•			0x0														00X0					•	•				
Access								₹ Š														₩ M										
Name								HFCLKLEPRESC														PRESC										

Bit	Name	Reset	Access	Description
31:25	Reserved			with future devices, always write bits to 0. More information in 1.2 Conven-
24:24	HFCLKLEPRESC	0x0	RW	HFCLKLE Prescaler
	Specifies the clock d	ivider for HFCLK	ILE.	
	Value	Mode		Description
	0	DIV2		HFCLKLE is HFBUSCLK _{LE} divided by 2.
	1	DIV4		HFCLKLE is HFBUSCLK _{LE} divided by 4.
23:13	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	PRESC	0x00	RW	HFCLK Prescaler
	Specifies the clock d	ivider for HFCLK	(relative to	HFSRCCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.33 CMU_HFCOREPRESC - High Frequency Core Clock Prescaler Register

Offset															Bi	t Po	siti	on														
0x108	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	3	2	-	0
Reset							•				•			1						000x0		•					1					
Access																				Z N												
Name																				PRESC												

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
16:8	PRESC	0x000	RW	HFCORECLK Prescaler
	Specifies the clock div	vider for HFCOF	RECLK (rel	ative to HFCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.34 CMU_HFPERPRESC - High Frequency Peripheral Clock Prescaler Register

Offset															Ві	t Po	sitio	on														
0x10C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	တ	8	7	9	5	4	က	2	_	0
Reset		•		•	•					•	•		•		•					000x0		•				•	•					
Access																				₽												
Name																				PRESC												

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
16:8	PRESC	0x000	RW	HFPERCLK Prescaler
	Specifies the clo	ck divider for the H	IFPERCLK (r	relative to HFCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.35 CMU_HFRADIOPRESC - High Frequency Radio Peripheral Clock Prescaler Register

Offset															Bi	t Po	siti	on														
0x110	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	3	2	_	0
Reset			•																	000x0							•	1				
Access																				Z N												
Name																				PRESC												

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
16:8	PRESC	0x000	RW	HFRADIOCLK Prescaler
	Specifies the clock d	ivider for the HFI	RADIOCLK	(relative to HFCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.36 CMU_HFEXPPRESC - High Frequency Export Clock Prescaler Register

Offset															Bi	t Po	sitio	on														
0x114	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																						00x0										
Access																						₩ N										
Name																						PRESC										

Bit	Name	Reset	Access	Description
31:13	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	PRESC	0x00	RW	HFEXPCLK Prescaler
	Specifies the clock	divider for HFEXF	CLK (relati	ive to HFCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.37 CMU_LFAPRESC0 - Low Frequency a Prescaler Register 0 (Async Reg)

Offset			Bit Position
0x120	30 33 37 28 29 30 37 26 27 28 29 30 31	22 23 24 25 25 25 25 25 25 25 25 25 25 25 25 25	8
Reset			000 000
Access			RW W
			SE SE
Name			LESENSE
D:4	Name	David Assess	
31:6	Name Reserved	Reset Access To ensure compatibility	Description with future devices, always write bits to 0. More information in 1.2 Conven-
31.0	Reserved	tions	with rature devices, always write bits to 6. Word information in 1.2 conven-
5:4	LESENSE	0x0 RW	Low Energy Sensor Interface Prescaler
	Configure Low Energy	y Sensor Interface prescal	er
	Value	Mode	Description
	0	DIV1	LFACLK _{LESENSE} = LFACLK
	1	DIV2	LFACLK _{LESENSE} = LFACLK/2
	2	DIV4	LFACLK _{LESENSE} = LFACLK/4
	3	DIV8	LFACLK _{LESENSE} = LFACLK/8
3:0	LETIMER0	0x0 RW	Low Energy Timer 0 Prescaler
	Configure Low Energy	y Timer 0 prescaler	
	Value	Mode	Description
	0	DIV1	LFACLK _{LETIMER0} = LFACLK
	1	DIV2	LFACLK _{LETIMER0} = LFACLK/2
	2	DIV4	LFACLK _{LETIMER0} = LFACLK/4
	3	DIV8	LFACLK _{LETIMER0} = LFACLK/8
	4	DIV16	LFACLK _{LETIMER0} = LFACLK/16
	5	DIV32	LFACLK _{LETIMER0} = LFACLK/32
	6	DIV64	LFACLK _{LETIMER0} = LFACLK/64
	7	DIV128	LFACLK _{LETIMER0} = LFACLK/128
	8	DIV256	LFACLK _{LETIMER0} = LFACLK/256
	9	DIV512	LFACLK _{LETIMER0} = LFACLK/512
	10	DIV1024	LFACLK _{LETIMER0} = LFACLK/1024
	11	DIV2048	LFACLK _{LETIMER0} = LFACLK/2048
	12	DIV4096	LFACLK _{LETIMER0} = LFACLK/4096
	13	DIV8192	LFACLK _{LETIMER0} = LFACLK/8192

Bit	Name	Reset	Access	Description
	14	DIV16384		LFACLK _{LETIMER0} = LFACLK/16384
	15	DIV32768		LFACLK _{LETIMER0} = LFACLK/32768

11.5.38 CMU_LFBPRESC0 - Low Frequency B Prescaler Register 0 (Async Reg)

Offset															Bi	t Po	siti	on														
0x128	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	œ	7	9	2	4	က	2	_	0
Reset		•	•	•		•	•	•	•			•	•	•	•	•		•	•		•						2	OXO		OxO	2	
Access																											2	2				
Name																											OFOVI II			SYSTICK) - - -)	

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	LEUART0	0x0	RW	Low Energy UART 0 Prescaler
	Configure Low Energy	y UART 0 presca	aler	
	Value	Mode		Description
	0	DIV1		LFBCLK _{LEUART0} = LFBCLK
	1	DIV2		LFBCLK _{LEUART0} = LFBCLK/2
	2	DIV4		LFBCLK _{LEUART0} = LFBCLK/4
	3	DIV8		LFBCLK _{LEUART0} = LFBCLK/8
3:0	SYSTICK	0x0		Prescaler
	Configure prescaler			
	Value	Mode		Description
	0	DIV1		LFBCLK _{SYSTICK} = LFBCLK

11.5.39 CMU_LFEPRESC0 - Low Frequency E Prescaler Register 0 (Async Reg)

When waking up from EM4 make sure EM4UNLATCH in EMU_CMD is set for this to take effect

													Bi	t Po	siti	on														
33	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	- (_ >
·	•																	•									•		0×0	
																													ΑW	
																													RTCC	
3	30	30 33	29 30 31	31 30 29 28 27	29 29 27 27 26 26	31 30 29 28 27 27 26 26 25	29 33 34 55 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5	31 30 28 27 27 26 26 27 27 27 28 27 27 28 28 28 28 27 28 28 29 20 20 20 20 20 20 20 20 20 20 20 20 20	29 30 31 54 55 55 55 55 55 55 55 55 55 55 55 55	30 30 28 28 26 27 28 28 28 27 28 28 27 28 28 28 28 28 28 28 29 20 20 20 20 20 20 20 20 20 20 20 20 20	29 30 31 52 54 52 53 54 55 54 55 55 55 55 55 55 55 55 55 55	30 30 28 28 26 27 28 28 27 28 29 20 20 20 20 20 21 20 20 20 20 20 20 20 20 20 20 20 20 20	30 30 31 52 53 53 53 54 55 64 55 65 65 65 65 65 65 65 65 65 65 65 65																	CC RW 0x0 - 2 3 4 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 18 19 10 10 10 10 10 10 10 10 10 10 10 10 10

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	RTCC	0x0	RW	Real-Time Counter and Calendar Prescaler
	Configure Real-	Time Counter and	Calendar pre	scaler
	Value	Mode		Description
	0	DIV1		LFECLK _{RTCC} = LFECLK
	1	DIV2		LFECLK _{RTCC} = LFECLK/2
	2	DIV4		LFECLK _{RTCC} = LFECLK/4

11.5.40 CMU_HFRADIOALTPRESC - High Frequency Alternate Radio Peripheral Clock Prescaler Register

Offset															Bi	t Po	siti	on														
0x138	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	3	7	_	0
Reset													•	•						000×0												
Access																				X ≪												
Name																				PRESC												

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
16:8	PRESC	0x000	RW	HFRADIOALTCLK Prescaler
	Specifies the cloc	k divider for the H	FRADIOALT	CLK (relative to HFCLK).
	Value			Description
	PRESC			Clock division factor of PRESC+1.
7:0	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

11.5.41 CMU_SYNCBUSY - Synchronization Busy Register

Offset													Bit	Pos	sition													
0x140	33	29	28	27	26	25	24	23	22	20	19	18	17	16	5 4	13	12	7	10	6	ω	7	9	5	4	3	7	0
Reset		0	0	0	0	0	0	į	•			0		0						·	·		0		0		0	0
Access		ď	ď	Я	2	Я	œ					<u>~</u>		œ									2		œ		<u>~</u>	<u>~</u>
Name		LFXOBSY	HFXOBSY	LFRCOVREFBSY	LFRCOBSY	AUXHFRCOBSY	HFRCOBSY					LFEPRESC0		LFECLKENO									LFBPRESC0		LFBCLKEN0		LFAPRESC0	LFACLKEN0
Bit	Name					Res	set		Α	cces	s l	Desc	cript	tion														
31:30	Reser	ved				To tion		ire c	ompa	tibilit	y wit	th fut	ture	devi	ces, a	lway	's wr	ite b	its t	0 0. 1	Mor	e ini	form	natic	n in	1.2	Con	ven-
29	LFXO	BSY				0			R		ı	LFX	ЭΒι	usy														
	Used t	to ch	eck	the	synd	chro	nizat	ion	status	of C	MU_	_LFX	OC	TRL														
	Value										l	Desc	ripti	on														
	0											CMU	LF	XOC	CTRL i	s rea	ady 1	for u	pda	te								
	1										(CMU	LF	XOC	CTRL i	s bu	sy s	yncł	nron	izing	ne	w va	lue					
28	HFXO	BSY				0			R		I	HFX	ΟВ	usy														
	Used t														, CML	J_HF	XOS	STA	RTL	JPC1	ΓRL	, CN	1U_	HF>	(OS	TEA	DYS	TA-
	Value			_								Desc																
	0														CTRL,	CN	/IU I	HFX	OS1	ARI	TUP	CTF	RL,	СМ	U F	HFX	OSTI	 EA-
											I		TAT	ECT	RL, C													
	1										(СМС	l HF	-v_	ЭΤΟΙ	O.	<i>1</i> 11 1			۰, БТ		· ~ T-	21	СМ		OCT		are
											l I	ousy	TAT syn	ECT chro	RL, Conizing	MU_ nev	_HF> v val	(OT lue.	IME HF>	OUT (O is	CTI als	RL, so B	CMI US`	Y wh		thes		
27	LFRC	OVR	EFB	SY		0			R		 	ers a	TAT syn	ECT ichro	RL, C	MU_ nev ing u	_HF> v val	(OT lue.	IME HF>	OUT (O is	CTI als	RL, so B	CMI US`	Y wh		thes		
27	LFRC0				sync		nizat	ion			1	ters a	TAT syn are a	ECT active	RL, Conizing	MU_ nev ing u	_HF> v val	(OT lue.	IME HF>	OUT (O is	CTI als	RL, so B	CMI US`	Y wh		thes		
27					synd		nizat	ion			I I I GMC	ters a	TAT syn are a	ECT active VRE	RL, Conizing	MU_ nev ing u	_HF> v val	(OT lue.	IME HF>	OUT (O is	CTI als	RL, so B	CMI US`	Y wh		thes		
27	Used t				sync		nizat	ion			I I I I I	LFRO CUR	TAT syn are a CO '	VRE	RL, Conizing	MU_ new ing u	_HF) v val used	(OT lue. (e.g	IME HF> J. wh	OUT (O is nen H	CTI s als	RL, GOOR	CMI	1).	nen			
27	Used to				synd		nizat	ion			I I I I I	LFRO CUR	TAT syn are a CO ' TUN cripti	VRE on	RL, Conizing	MU_ new ing u y	HF) v valused	VOT lue. (e.g	IME HF> j. wh	OUT (O is ien F	GCT Gals HFX	RL, 6 SO B OEN	CMI US` NS=	y fo	r up	date		ew
27	Value 0	to ch	eck		syno		nizat	ion		of G	in the second se	LFRO CUR Desc	TAT synnare a	WRE. on	F Bus	MU_ new ing u y	HF) v valused	VOT lue. (e.g	IME HF> j. wh	OUT (O is ien F	GCT Gals HFX	RL, 6 SO B OEN	CMI US` NS=	y fo	r up	date		ew
	Value 0	OBS	eck Y	the		ohro 0			status	of G	I I I I I I I I I I I I I I I I I I I	cousy ders a LFRC CUR Desc CMU Value	TAT syn syn co TUN cripti LLF	rective when the control of the cont	F Bus	MU_ new ing u y	HF) v valused	VOT lue. (e.g	IME HF> j. wh	OUT (O is ien F	GCT Gals HFX	RL, 6 SO B OEN	CMI US` NS=	y fo	r up	date		ew
	Value 0 1	OBS	eck Y	the		ohro 0			status	of G	IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII	cousy ders a LFRC CUR Desc CMU Value	TATT Synnare a s	VRE on FRCC Busy CTR	F Bus	MU_ new ing u y	HF) v valused	VOT lue. (e.g	IME HF> j. wh	OUT (O is ien F	GCT Gals HFX	RL, 6 SO B OEN	CMI US` NS=	y fo	r up	date		ew

Bit	Name	Reset	Access	Description
	1			CMU_LFRCOCTRL is busy synchronizing new value
25	AUXHFRCOBSY	0	R	AUXHFRCO Busy
	Used to check the sy	nchronization st	atus of CM	U_AUXHFRCOCTRL.
	Value			Description
	0			CMU_AUXHFRCOCTRL is ready for update
	1			CMU_AUXHFRCOCTRL is busy synchronizing new value
24	HFRCOBSY	0	R	HFRCO Busy
	Used to check the sy	nchronization st	atus of CM	U_HFRCOCTRL.
	Value			Description
	0			CMU_HFRCOCTRL is ready for update
	1			CMU_HFRCOCTRL is busy synchronizing new value
23:19	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
18	LFEPRESC0	0	R	Low Frequency E Prescaler 0 Busy
	Used to check the sy	nchronization st	atus of CM	U_LFEPRESC0.
	Value			Description
	0			CMU_LFEPRESC0 is ready for update
	1			CMU_LFEPRESC0 is busy synchronizing new value
17	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
16	LFECLKEN0	0	R	Low Frequency E Clock Enable 0 Busy
	Used to check the sy	nchronization st	atus of CM	U_LFECLKEN0.
	Value			Description
	0			CMU_LFECLKEN0 is ready for update
	1			CMU_LFECLKEN0 is busy synchronizing new value
15:7	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
6	LFBPRESC0	0	R	Low Frequency B Prescaler 0 Busy
	Used to check the sy	nchronization st	atus of CM	U_LFBPRESC0.
	Value			Description
	0			CMU_LFBPRESC0 is ready for update
	1			CMU_LFBPRESC0 is busy synchronizing new value
5	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
4	LFBCLKEN0	0	R	Low Frequency B Clock Enable 0 Busy
	Used to check the	synchronization	status of CM	U_LFBCLKEN0.
	Value		-	Description
	0			CMU_LFBCLKEN0 is ready for update
	1			CMU_LFBCLKEN0 is busy synchronizing new value
3	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2	LFAPRESC0	0	R	Low Frequency a Prescaler 0 Busy
	Used to check the	synchronization	status of CM	U_LFAPRESC0.
	Value			Description
	•			
	0			CMU_LFAPRESC0 is ready for update
	1			CMU_LFAPRESC0 is ready for update CMU_LFAPRESC0 is busy synchronizing new value
1		To ensure tions	compatibility v	<u> </u>
1 0	1		compatibility v	CMU_LFAPRESC0 is busy synchronizing new value
,	1 Reserved	tions 0	R	CMU_LFAPRESC0 is busy synchronizing new value with future devices, always write bits to 0. More information in 1.2 Conven- Low Frequency a Clock Enable 0 Busy
,	1 Reserved LFACLKEN0	tions 0	R	CMU_LFAPRESC0 is busy synchronizing new value with future devices, always write bits to 0. More information in 1.2 Conven- Low Frequency a Clock Enable 0 Busy
,	1 Reserved LFACLKEN0 Used to check the	tions 0	R	CMU_LFAPRESC0 is busy synchronizing new value with future devices, always write bits to 0. More information in 1.2 Conven- Low Frequency a Clock Enable 0 Busy U_LFACLKEN0.

11.5.42 CMU_FREEZE - Freeze Register

Offset				Bit Position	
0x144	30 29 29 27 27 26	25 24 23 22 22	20 20 140	8 1 <th>0</th>	0
Reset					0
Access					₩
Name					REGFREEZE
Bit	Name	Reset	Access	Description	
31:1	Reserved	To ensure com	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven	7-
0	REGFREEZE	0	RW	Register Update Freeze	

When set, the update of the Low Frequency clock control registers is postponed until this bit is cleared. Use this bit to update several registers simultaneously.

Value	Mode	Description
0	UPDATE	Each write access to a Low Frequency clock control register is updated into the Low Frequency domain as soon as possible.
1	FREEZE	The LE Clock Control registers are not updated with the new written value.

11.5.43 CMU_PCNTCTRL - PCNT Control Register

Offset															Bi	t Po	siti	on														
0x150	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset				•		•				•		•		•					•					•			•	•		•	0	0
Access																															RWH	RWH
Name																															PCNT0CLKSEL	PCNT0CLKEN
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
31:2	Re	serv	red				To tio		ure	com	pati	bility	y wi	th fu	ture	dev	rices	s, alı	way	s wr	rite k	its :	to 0.	Мо	re ir	nforr	natio	on ir	1.2	? Co	nvei	า-
1	PC	NTC	CLŁ	KSE	EL		0				RW	/H		PCN	ITO	Clo	k S	elec	ct													
	Th	is bi	t cor	ntro	ls wl	hich	clo	ck th	at is	use	ed fo	or th	e P	CNT																		
	Va	lue					Мс	de						Des	cript	ion																_

11.5.44 CMU_ADCCTRL - ADC Control Register

11.0.77	O.I.I.OA.					٠.	0		<i>,</i> 9.0																						
Offset														Bi	t Po	siti	on														
0x15C	31	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset																							0			2	OX O				
Access																							RWH				[}				
Name																							ADCOCLKINV			2000	ADCUCLASEL				
Bit	Name Reset Access Description																														
31:9	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convetions															nve	n-														
8	ADC00	CLKI	NV			0				RV	VH		Inve	ert C	loci	k Se	elect	ted	Ву	ADC	COCL	ĸs	EL								
	This bi	it ena	ables	inv	/erti	ng t	he s	sele	cted	clo	ck to	AE	C0.																		
7:6	Reser	ved				To tion		ure	con	npat	ibilit _.	y wi	ith fu	ıture	dev	/ices	s, al	way	s w	rite l	bits t	o 0.	Мо	re ir	nforn	natio	on in	1.2	2 Co	nve	n-
5:4	ADC00	CLKS	SEL			0x0)			RV	VH		ADO	C0 C	loci	k Se	elect	t													
	This bi change when o	ed w	hen /	AD(CCL	.KM	ODI	E in	AD	Cn_	CTR	RL is	set	to S																	
	Value					Мо	de						Des	cript	ion																_
	0					DIS	SAB	LEC)				ADO	CO is	not	clo	cked	t													_
	1					AU	XHI	FRC	Ю				ΑU>	(HFI	RCC) is	cloc	king	j AE	C0											
	_					–							– 、	, .																	

Value	Mode	Description
0	DISABLED	ADC0 is not clocked
1	AUXHFRCO	AUXHFRCO is clocking ADC0
2	HFXO	HFXO is clocking ADC0
3	HFSRCCLK	HFSRCCLK is clocking ADC0

3:0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-
		tions

11.5.45 CMU_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Ві	t Po	siti	on														
0x170	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	7	_	0
Reset				0		'										'			•	•						'					0	0
Access				₩ N																											RW	RW W
Name				CLKINOPEN																											CLKOUT1PEN	CLKOUT0PEN

Bit	Name	Reset	Access	Description				
31:29	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-				
28	CLKIN0PEN	0	RW	CLKIN0 Pin Enable				
	When set, the CLKIN0 pin is enabled.							
27:2	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions						
1	CLKOUT1PEN	0	RW	CLKOUT1 Pin Enable				
	When set, the CLKOUT1 pin is enabled.							
0	CLKOUT0PEN	0	RW	CLKOUT0 Pin Enable				
	When set, the CLKOUT0 pin is enabled.							

11.5.46 CMU_ROUTELOC0 - I/O Routing Location Register

Offset				Bit Position						
0x174	33 33 34 25 28 29 30 34 26 27 28 29 29	22 24 25 25 25 25 25 25 25 25 25 25 25 25 25	20 27	8 1 4 1 4 4	8 6 10 17 17 13	7 9	ω 4 m α - 0			
Reset					00×0		00×0			
Access					WA O		W W			
Name					CLKOUT1LOC		CLKOUT0LOC			
					CLKC		CLKO			
Bit	Name	Reset	Access	Description						
31:14	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions								
13:8	CLKOUT1LOC	0x00	RW	I/O Location						
	Decides the location of									
	Value	Mode		Description						
	0	LOC0		Location 0						
	1	LOC1		Location 1						
	2	LOC2		Location 2						
	3	LOC3		Location 3						
	4	LOC4		Location 4						
	5	LOC5		Location 5						
	6	LOC6		Location 6						
	7	LOC7		Location 7						
7:6	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions									
5:0	CLKOUT0LOC	0x00	RW	I/O Location						
	Decides the location of the CMU CLKOUT0.									
	Value	Mode		Description						
	0	LOC0		Location 0						
	1	LOC1		Location 1						
	2	LOC2		Location 2						
	3	LOC3		Location 3						
	4	LOC4		Location 4						
	5	LOC5		Location 5						
	6	LOC6		Location 6						
	7	LOC7		Location 7						

11.5.47 CMU_ROUTELOC1 - I/O Routing Location Register

Offset															Bi	t Po	sitio	on														
0x178	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	∞	7	9	2	4	က	2	_	0
Reset																														0x00		
Access																														S N		
Name																														CLKINOLOC		
Bit	Na	me					Res	set			Ac	ces	,	Des	crip [.]	tion																
															OI IP																	
31:6	Re	serv	⁄ed					ens	ure	com								s, alı	way:	s wr	ite b	its t	o 0.	Моі	re in	forn	natio	on in	1	2 Co	nve	n-
			red 0LO	C			То	ens Is	ure	com		bility	/ Wit	th fu		dev	ices	s, alı	way:	s wr	ite b	its t	0 0.	Моі	re in	form	natio	on in	1	2 Co	nve	n-
31:6	CL	.KIN			atio	n of	To tion	ens ns			pati	bility	/ Wit	th fu	ture	dev	ices	s, alv	way	s wr	ite b	oits to	0 0.	Moi	re in	form	natio	on in	1	2 Ca	nve	n-
31:6	CL De	.KIN	0LO		atio	n of	To tion	ens ns 00 CL			pati	bility	/ Wii	th fu	ture	dev	ices	s, alv	way.	s wr	ite b	its to	0 0.	Моі	re in	form	natio	on in	1	2 Co	nve	n-
31:6	CL De	KIN cide	0LO		atio	n of	To tion 0x0	ens ns 00 CL			pati	bility	/ wii	th fu	ture _oca	dev	ices	s, alv	way	s wr	ite b	oits to	o 0.	Moi	re in	form	natio	on in	1	2 Ca	nve	n-
31:6	CL De	KIN cide	0LO		atio	n of	To tion 0x0 f the	ens ns 00 CL de			pati	bility	/ win	th fu	oca	dev	ices	s, alv	way.	s wr	ite b	oits to	0 0.	Moi	re in	form	natio	on in	1	2 Ca	nve	n-
31:6	CL De Va	KIN cide	0LO		eatio	n of	To tion 0x0 the Mo	ens ns 00 CL de C0			pati	bility	/ win	th fu	cripti	devion	ices	s, alv	way	s wr	ite b	its to	0.	Moi	re in	form	natio	on ir	1	2 Co	nve	n-
31:6	CL De Va 0	KIN cide	0LO		catio	n of	To tion 0x0 the Mo LO	ens ns no CL de C0 C1			pati	bility	/ wit	Des Loca	criptication	devo	ices	s, alı	way	s wr	ite L	its to	0 0.	Moi	re in	form	natic	on in	1	2 Co	nve	n-

11.5.48 CMU_LOCK - Configuration Lock Register

Offset															Bi	t Po	siti	on														
0x180	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			1	1			1		•			1		1	ı	1		1	ı		•		'		nnnxn			ı	•			
Access																									I A Y							
Name																								\ \ \ \ \	LOCKA							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock Key

Write any other value than the unlock code to lock CMU_CTRL, CMU_ROUTEPEN, CMU_ROUTELOC0, CMU_ROUTE-LOC1, CMU HFRCOCTRL, CMU AUXHFRCOCTRL, CMU LFRCOCTRL, CMU ULFRCOCTRL, CMU HFXOCTRL, CMU_HFXOCTRL1, CMU_HFXOSTARTUPCTRL, CMU_HFXOSTEADYSTATECTRL, CMU_HFXOTIMEOUTCTRL, CMU_LFXOCTRL, CMU_OSCENCMD, CMU_CMD, CMU_DBGCLKSEL, CMU_HFCLKSEL, CMU_LFACLKSEL, CMU LFECLKSEL, CMU_LFRCLKSEL, CMU HFBUSCLKENO, CMU HFUNDIVCLKENO, CMU LFBCLKSEL, CMU_HFPERCLKEN0, CMU_HFRADIOCLKEN0, CMU_HFRADIOALTCLKEN0, CMU_HFPRESC, CMU_HFCORE-CMU_HFRADIOPRESC, CMU_HFEXPPRESC, PRESC, CMU_HFPERPRESC, CMU_HFRADIOALTPRESC, CMU_LFACLKEN0, CMU_LFBCLKEN0, CMU_LFECLKEN0, CMU_LFRCLKEN0, CMU_LFAPRESC0, CMU_LFBPRESC0, CMU_LFEPRESC0, CMU_LFRPRESC0, CMU_ADCCTRL CMU_LVDSCTRL, and CMU_PCNTCTRL from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	CMU registers are unlocked
LOCKED	1	CMU registers are locked
Write Operation		
LOCK	0	Lock CMU registers
UNLOCK	0x580E	Unlock CMU registers

12. SMU - Security Management Unit



Quick Facts

What?

The Security Management Unit (SMU) forms the control and status/reporting component of bus-level security in the EFR32.

Why?

Enables a robust and low-energy security solution at the system level

How?

Hardware context switching and access control provided via BLS components.

12.1 Introduction

The Security Management Unit (SMU) peripheral adds hardware access control over all of the MCU peripherals that are managed by low level firmware integrated into a Real Timer Operating System (RTOS). The SMU is used in conjuntion with the Cortex-M operating modes (privileged and non-privileged) and the Memory Protection Unit (MPU). The EFR32 MCUs include the ARM v7-M MPU that defines configurable access parameters to regions within the entire CPU memory map. The MPU is not covered in detail in this reference manual. For a complete description of the MPU registers etc, consult the ARM v7-M Architecture Reference Manual. The MPU can define up to 8 regions of varying sizes within the memory map, with each region also being able to be split into 8 equal sub-regions. Using these regions, firmware can define rules that enforce privileged and non-privileged accesses to different memory locations. For example, sections of flash can be marked as priviliged access, whereas other areas within the flash can be marked as having non-privileged mode acess. Only privileged mode regions can access other privileged mode regions. Accesses attempted by a non-privileged region to a privileged region will cause a fault. The access permissions can be extended across the entire memory map including the peripheral region.

The Cortex-M starts up in privileged mode and the MPU is disabled after reset which means all regions in the memory map are accessble to the running application code. For many applications this is sufficient and the MPU remains disabled. However, when using a RTOS the kernel requires protection from user code and will switch to privileged mode and create tasks in non-privileged or thread mode. In addition, security is also a concern, so MCU peripherals should be protected to avoid security holes. Adding peripheral security to systems requires an increased number of MPU regions to protect areas such as the peripheral registers, including bit set/clear and bit banding regions. The defined regions are also dynamic based on the task requirements and in many cases the number of regions required exceeds the number of regions that can be enabled by the MPU.

The SMU is used to extend the access controls of each peripheral beyond the number of regions available using the MPU. The SMU peripheral registers provide the configuration and status bits for the Peripheral Protection Unit (PPU) to the CPU. The PPU is the underlying hardware component that operates on the low level bus interfaces within the SoC to derive the status for each peripheral.

12.2 Features

The main features of the SMU are as follows:

- · Contains control and status registers for hardware bus level component instances (e.g., the PPU)
- Simplifies RTOS context switching
 - · Hardware to complement any software context switching enabled by an MPU
 - Hardware-enforced access control extends capability of the v7-M MPU regions
 - · One bit control per peripheral reduces software overhead while dynamically modifying access permissions
- A configurable interrupt line that can be triggered from peripheral access fault events

12.3 Functional Description

An overview of the SMU module within the system is shown in Figure 12.1 Bus-Level Security System View on page 364.




Figure 12.1. Bus-Level Security System View

12.3.1 PPU - Peripheral Protection Unit

The number of peripheral memory regions on the device exceeds the number of configurable regions available using the MPU. While it is possible to manage finer granularity of memory security through software, the PPU provides a hardware solution for fine-grained peripheral-level protection to eliminate the performance degradation associated with a partially software-managed solution.

The PPU provides a hardware access barrier to any peripheral that is configured to be protected. When an attempt is made to access a peripheral without the required privilege level, the PPU detects the fault and intercepts the access. No write or read of the peripheral register space occurs, and an all-zero value is returned if the access is a read. See 12.3.2.2 PPU Control for more details on how access faults are reported to the CPU.

Note: The CPU is the only system bus master in the EFR32 that can trigger access faults. All other masters are given full access privileges and have no configurable context switching enabled.

12.3.2 Programming Model

The SMU does not provide any access control out of reset and needs to be configured by software. SMU access controls should be configured along with the MPU configuration. This is typically performed in a bootloader or other low level RTOS kernel/supervisor code prior to user code or other non-privileged code execution. At least one MPU region will be allocated to the entire peripheral region as a full access region (0x4000_0000 - 0x4006_FFFF). An RTOS kernel/supervisor can dynamically allocate peripheral accessibility by maintaining the hardware and software contexts available to each task. In the chart below there are mutiple tasks and the system switches between Task A and Task B via the RTOS handler. There are 16 peripherals shown in the example split between two regions. Task A has rights to access peripherals 0, 1, 4, 5 and 7, whereas task B has rights to access the complement of A (2, 3, and 6). After a Task B IRQ, the privileged OS handler is entered which signals the supervisor to reprogram the regions using the SMU based on an access control list. Control is then handed to Task B in non-privileged mode.




Figure 12.2. Peripheral Access Control Example

All hardware protections happen immediately in response to SMU configuration register writes without any latency cycles. However, since software instructions may be optimized or pipelined, it is important to make sure that software memory barrier instructions are used as needed after any SMU re-configuration before moving on or changing contexts. This ensures that the hardware context switch has taken full effect.

For the remainder of this section, the programming model is split into general SMU controls and component-specific controls (e.g., PPU).

12.3.2.1 Interrupt Control/Status

The SMU follows the standard EFR32 interrupt programming model with SMU IF/IFS/IFC/IEN registers.

There is one interrupt bit PPUPRIV that will trigger on privilege faults detected by the PPU. Such fault mechanisms are configured as specified in 12.3.2.2 PPU Control.

12.3.2.2 PPU Control

The PPU_CTRL register provides an ENABLE bit that allows bypassing all PPU checking when set to 0. In this case, the rest of the PPU registers have no effect, and no access faults will occur. This is the reset state of the SMU.

When the ENABLE bit of PPU_CTRL register is asserted, access protection is configured on a peripheral-by-peripheral basis using the SMU_PPUPATDx register(s). Setting a bit in the SMU_PPUPATDx register to one configures the corresponding peripheral controlled by that bit to privileged access only. The single bit mode control for each peripheral provides fast hardware context switching for peripheral sharing, while still supporting fast software context switches for task-based CPU context switching.

Note: The SMU itself is a peripheral which has protection afforded by the PPU. A proper security/privilege context configuration requires setting of the SMU's access control bits properly at startup so that only a top-level task (e.g., a uVisor from ARM) can perform security/privilege context switches.

When a peripheral has access protection configured and the peripheral is accessed with invalid privilege credentials, then an access fault occurs. The corresponding interrupt flag in SMU_IF is asserted and the ID of the peripheral for which an unpriviliged access was attempted is captured in the PERIPHID bit-field of the PPU Fault Status register (SMU_PPUFS). This peripheral ID is held stable until all PPU interrupt flags are cleared to ensure that the first unprivileged access that caused the fault is not overwritten due to subsequent faults before being acknowledged by software.

Note: In the case of simultaneously occurring faults (which may be possible in some systems), only one of the faults' peripheral IDs will be captured. There is no inherent peripheral priority defined that would result in one peripheral being recognized before another.

12.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x00C	SMU_IF	R	Interrupt Flag Register
0x010	SMU_IFS	W1	Interrupt Flag Set Register
0x014	SMU_IFC	(R)W1	Interrupt Flag Clear Register
0x018	SMU_IEN	RW	Interrupt Enable Register
0x040	SMU_PPUCTRL	RW	PPU Control Register
0x050	SMU_PPUPATD0	RW	PPU Privilege Access Type Descriptor 0
0x054	SMU_PPUPATD1	RW	PPU Privilege Access Type Descriptor 1
0x090	SMU_PPUFS	R	PPU Fault Status

12.5 Register Description

12.5.1 SMU_IF - Interrupt Flag Register

Offset															Ві	it Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•			•			•	•							•	•										•				0
Access																																ď
Name																																PPUPRIV

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PPUPRIV	0	R	PPU Privilege Interrupt Flag
	Triggered when a priv	rilege fault occur	s in the Pe	eripheral Protection Unit

12.5.2 SMU_IFS - Interrupt Flag Set Register

Offset	Bit Position	
0x010	33 3 3 4 5 5 6 7 8 8 8 7 9 9 9 9 9 9 9 9 9 9 9 9 9 9 9	0
Reset		0
Access		W1
Name		PPUPRIV

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PPUPRIV	0	W1	Set PPUPRIV Interrupt Flag
	Write 1 to set the	PPUPRIV interr	upt flag	

12.5.3 SMU_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	ဝ	∞	7	9	2	4	က	2	_	0
Reset																																0
Access																																(R)W1
Name																																PPUPRIV

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	PPUPRIV	0	(R)W1	Clear PPUPRIV Interrupt Flag
	Write 1 to clear th	e PPUPRIV inter	runt flag. Rea	iding returns the value of the IE and clears the corresponding interrupt flags

Write 1 to clear the PPUPRIV interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).

12.5.4 SMU_IEN - Interrupt Enable Register

Offset															Bi	t Pc	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Reset			•	•				•						•		•			•						•	•						0
Access																																RW
Name																																PPUPRIV

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PPUPRIV	0	RW	PPUPRIV Interrupt Enable
	Enable/disable the P	PUPRIV interru	pt	

12.5.5 SMU_PPUCTRL - PPU Control Register

Offset	Bit Position	
0x040	33 34 35 36 37 38 39 4 5 6 6 6 6 7 8 <th>0</th>	0
Reset		0
Access		₹
Name		ENABLE
Bit	Name Reset Access Description	
31:1	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convertions	n-
0	ENABLE 0 RW	
	Set to enable checking of peripheral access	
	Value Description	
	0 Privilege/Security-level checking completely bypassed in the PPU	
	1 Behavior controlled by PPU_PATD	
	1 Benavior controlled by PPU_PATD	

12.5.6 SMU_PPUPATD0 - PPU Privilege Access Type Descriptor 0

Set peripheral bits to 1 to mark as privileged access only

Offset															Ві	t Po	siti	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset	0	0	0		•	•	•	0		0	0	0	0	0	0	0	0	0		0	0	0	0	0	0		0		•	0	0	0
Access	R W	₩ M	₩					S S		₽	₩ W	₽W	₩	₩	₽	₽	₽	₩		₩ N	₽	₽	₽	₽	₽		₩ W			₩	₩	RW
Name	SMU	RTCC	RMU					PCNT0		LEUARTO	LETIMERO	LESENSE	LDMA	MSC	IDAC0	12C0	GPIO	GPCRC		FPUEH	ЕМU	PRS	VDAC0	CRYPT00	CRYOTIMER		CMU			ADC0	ACMP1	ACMP0

	S R R	PG B		
Bit	Name	Reset	Access	Description
31	SMU	0	RW	Security Management Unit access control bit
	Access control only for	or SMU		
30	RTCC	0	RW	Real-Time Counter and Calendar access control bit
	Access control only for	or RTCC		
29	RMU	0	RW	Reset Management Unit access control bit
	Access control only for	or RMU		
28:25	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
24	PCNT0	0	RW	Pulse Counter 0 access control bit
	Access control only for	or PCNT0		
23	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
22	LEUART0	0	RW	Low Energy UART 0 access control bit
	Access control only for	or LEUART0		
21	LETIMER0	0	RW	Low Energy Timer 0 access control bit
	Access control only for	or LETIMER0		
20	LESENSE	0	RW	Low Energy Sensor Interface access control bit
	Access control only for	or LESENSE		
19	LDMA	0	RW	Linked Direct Memory Access Controller access control bit
	Access control only for	or LDMA		
18	MSC	0	RW	Memory System Controller access control bit
	Access control only for	or MSC		
17	IDAC0	0	RW	Current Digital to Analog Converter 0 access control bit
	Access control only for	or IDAC0		
16	I2C0	0	RW	I2C 0 access control bit
	Access control only for	or I2C0		
15	GPIO	0	RW	General purpose Input/Output access control bit
	Access control only for	or GPIO		

Bit	Name	Reset	Access	Description
14	GPCRC	0	RW	General Purpose CRC access control bit
	Access control only	for GPCRC		
13	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
12	FPUEH	0	RW	FPU Exception Handler access control bit
	Access control only	for FPUEH		
11	EMU	0	RW	Energy Management Unit access control bit
	Access control only	for EMU		
10	PRS	0	RW	Peripheral Reflex System access control bit
	Access control only	for PRS		
9	VDAC0	0	RW	Digital to Analog Converter 0 access control bit
	Access control only	for VDAC0		
8	CRYPTO0	0	RW	Advanced Encryption Standard Accelerator 0 access control bit
	Access control only	for CRYPTO0		
7	CRYOTIMER	0	RW	CRYOTIMER access control bit
	Access control only	for CRYOTIMER		
6	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	CMU	0	RW	Clock Management Unit access control bit
	Access control only	for CMU		
4:3	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	ADC0	0	RW	Analog to Digital Converter 0 access control bit
	Access control only	for ADC0		
1	ACMP1	0	RW	Analog Comparator 1 access control bit
	Access control only	for ACMP1		
0	ACMP0	0	RW	Analog Comparator 0 access control bit
	Access control only	for ACMP0		

12.5.7 SMU_PPUPATD1 - PPU Privilege Access Type Descriptor 1

Set peripheral bits to 1 to mark as privileged access only

Offset															Bi	t Pc	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset								•				•				•		•		•				0	0	0	0	0		0	0	
Access																								₽	₽	₽	₩ N	₽		W.	₩.	
Name																								WTIMERO	WDOG1	WDOG0	USART1	USART0		TIMER1	TIMERO	

Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8	WTIMER0	0	RW	Wide Timer 0 access control bit
	Access control only for	or WTIMER0		
7	WDOG1	0	RW	Watchdog 1 access control bit
	Access control only for	or WDOG1		
6	WDOG0	0	RW	Watchdog 0 access control bit
	Access control only for	or WDOG0		
5	USART1	0	RW	Universal Synchronous/Asynchronous Receiver/Transmitter 1 access control bit
	Access control only for	or USART1		
4	USART0	0	RW	Universal Synchronous/Asynchronous Receiver/Transmitter 0 access control bit
	Access control only for	or USART0		
3	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2	TIMER1	0	RW	Timer 1 access control bit
	Access control only for	or TIMER1		
1	TIMER0	0	RW	Timer 0 access control bit
	Access control only for	or TIMER0		
0	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-

12.5.8 SMU_PPUFS - PPU Fault Status

Offset															Bi	t Po	siti	on														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	2	4	3	2	1	0
Reset																													00x0			
Access																													<u>~</u>			
Name																													PERIPHID			

Bit	Name	Reset	Access	Description
31:7	Reserved	To ensure co	mpatibility w	vith future devices, always write bits to 0. More information in 1.2 Conven-
6:0	PERIPHID	0x00	R	

Holds the peripheral ID of the first peripheral that was accessed resulting in an access fault. This ID is not valid unless one of the PPU interrupt flags is set. Any other access faults that occur are not captured until all the PPU interrupt flags are cleared

Value	Mode	Description
0	ACMP0	Analog Comparator 0
1	ACMP1	Analog Comparator 1
2	ADC0	Analog to Digital Converter 0
5	CMU	Clock Management Unit
7	CRYOTIMER	CRYOTIMER
8	CRYPTO0	Advanced Encryption Standard Accelerator 0
9	VDAC0	Digital to Analog Converter 0
10	PRS	Peripheral Reflex System
11	EMU	Energy Management Unit
12	FPUEH	FPU Exception Handler
14	GPCRC	General Purpose CRC
15	GPIO	General purpose Input/Output
16	I2C0	I2C 0
17	IDAC0	Current Digital to Analog Converter 0
18	MSC	Memory System Controller
19	LDMA	Linked Direct Memory Access Controller
20	LESENSE	Low Energy Sensor Interface
21	LETIMER0	Low Energy Timer 0
22	LEUART0	Low Energy UART 0
24	PCNT0	Pulse Counter 0
29	RMU	Reset Management Unit
30	RTCC	Real-Time Counter and Calendar

Bit	Name	Reset A	ccess	Description
	31	SMU		Security Management Unit
	33	TIMER0		Timer 0
	34	TIMER1		Timer 1
	36	USART0		Universal Synchronous/Asynchronous Receiver/Transmitter 0
	37	USART1		Universal Synchronous/Asynchronous Receiver/Transmitter 1
	38	WDOG0		Watchdog 0
	39	WDOG1		Watchdog 1
	40	WTIMER0		Wide Timer 0

13. RTCC - Real Time Counter and Calendar



Quick Facts

What?

The Real Time Counter and Calendar (RTCC) is a 32-bit counter ensuring timekeeping in low energy modes. The RTCC also includes a calendar mode for easy time and date keeping. In addition, the RTCC includes 128 bytes of general purpose retention data, allowing persistent data storage in all energy modes except EM4 Shutoff.

Why?

Timekeeping over long time periods while using as little power as possible is required in many low power applications.

How?

A low frequency oscillator is used as clock signal and the RTCC has three different Capture/Compare channels which can trigger wake-up, generate PRS signalling, or capture system events. 32-bit resolution and selectable prescaling allow the system to stay in low energy modes for long periods of time and still maintain reliable timekeeping.

13.1 Introduction

The Real Time Counter and Calendar (RTCC) contains a 32-bit counter/calendar in combination with a 15-bit pre-counter to allow flexible prescaling of the main counter. The RTCC is available in all energy modes except EM4 Shutoff.

Three individually configurable Capture/Compare channels are available in the RTCC. These can be used to trigger interrupts, generate PRS signals, capture system events, and to wake the device up from a low energy mode. The RTCC also includes 128 bytes of general purpose storage and a Binary Coded Decimal (BCD) calendar mode, enabling easy time and date keeping.

13.2 Features

- · 32-bit Real Time Counter.
- 15-bit pre-counter, for flexible frequency scaling or for use as an independent counter.
- · EM4 Hibernate operation and wakeup.
- · 128 byte general purpose retention data.
- · Oscillator failure detection.
- Can continue through system reset; only reset by power loss, pin, or software reset.
- · Calendar mode.
 - · BCD encoding.
 - · Three programmable alarms.
 - · Leap year correction.
- · Three Capture/Compare registers.
 - Capture of PRS events from other parts of the system.
 - · Compare match or input capture can trigger interrupts.
 - Compare register 1, RTCC_CC1_CCV can be used as a top value for the main counter.
 - Compare register 0, RTCC_CC0_CCV can be used as a top value for the pre-counter.
 - · Compare match events are available to other peripherals through the Peripheral Reflex System (PRS).

13.3 Functional Description

The RTCC is a 32-bit up-counter with three Capture/Compare channels. In addition, the RTCC includes a 15-bit pre-counter which can be used as an independent counter or to prescale the main counter. An overview of the RTCC module is shown in Figure 13.1 RTCC Overview on page 376.




Figure 13.1. RTCC Overview

13.3.1 Counter

The RTCC consists of two counters; the 32-bit main counter, RTCC_CNT (RTCC_TIME and RTCC_DATE in calendar mode), and a 15-bit pre-counter, RTCC_PRECNT. The pre-counter can be used as an independent counter or to generate a specific frequency for the main counter. In both configurations, the pre-counter can be used to generate compare match events or be captured in the Capture/Compare channels as a result of an external PRS event. Refer to 13.3.2 Capture/Compare Channels for details on how to configure the Capture/Compare channels for use with the pre-counter.




Figure 13.2. RTCC counters

The RTCC is enabled by setting the ENABLE bit in RTCC_CTRL. When the RTCC is enabled, the pre-counter (RTCC_PRECNT) increments upon each positive clock edge of LFCLK_{RTCC}. If CNTTICK in RTCC_CTRL is set to PRESC, the pre-counter will continue to count up, wrapping around to zero when it overflows. If CNTTICK in RTCC_CTRL is set to CCV0MATCH, the pre-counter will wrap around when it hits the value configured in RTCC_CCV.

The main counter of the RTCC, RTCC_CNT, has two modes; normal mode and calendar mode. In normal mode, the main counter is available in RTCC_CNT and increments upon each tick given from the pre-counter. Refer to 13.3.1.1 Normal Mode for a description on how to configure the frequency of these ticks. In calendar mode, the counter value is available in RTCC_TIME and RTCC_DATE, keeping track of seconds, minutes, hours, day of month, day of week, months, and years, all encoded in BCD format. Refer to 13.3.1.2 Calendar Mode for details on this mode. The mode of the main counter is configured in CNTMODE in RTCC_CTRL. The differences between the two modes are summarized below.

Normal mode

- · Incremental counter, RTCC CNT.
- RTCC_CCx_CCV used for Capture/Compare value.

· Calendar mode

- BCD counters, RTCC_DATE, RTCC_TIME.
- RTCC CCx TIME and RTCC CCx DATE used for Capture/Compare value.

Note: The mode of the RTCC must be configured for CALENDAR mode in RTCC_CTRL_CNTMODE before writing to the mode dependent registers, RTCC_TIME, RTCC_DATE, RTCC_CCx_TIME, and RTCC_CCx_DATE. Writes to these registers when in NORMAL mode will be ignored.

13.3.1.1 Normal Mode

The main counter can receive a tick based on different tappings from the pre-counter, allowing the ticks to be power of 2 divisions of the LFCLK_{RTCC}. For more accurate configuration of the tick frequency, RTCC_CC0_CCV[14:0] can be used as a top value for RTCC_PRECNT. When reaching the top value, the main counter receives a tick and the pre-counter wraps around. Table 13.1 RTCC Resolution Vs Overflow, $F_{LFCLK} = 32768$ Hz on page 378 summarizes the resolutions available when using a 32768 Hz oscillator as source for LFCLK_{RTCC}.

Table 13.1. RTCC Resolution Vs Overflow, F_{LFCLK} = 32768 Hz

RTCC_CTRL_CNTTICK	RTCC_CTRL_CNTPRESC	Main counter period, T _{CNT}	Overflow			
CCV0MATCH	Don't care	(RTCC_CC0_CCV + 1)/F _{LFCLK} s	2 ³² *T _{CNT} seconds			
	DIV1	30.5 µs	36.4 hours			
	DIV2	61 µs	72.8 hours			
	DIV4	122 µs	145.6 hours			
	DIV8	244 μs	12 days			
	DIV16	488 μs	24 days			
	DIV32	977 μs	48 days			
	DIV64	1.95 ms	97 days			
PRESC	DIV128	3.91 ms	194 days			
PRESC	DIV256	7.81 ms	388 days			
	DIV512	15.6 ms	776 days			
	DIV1024	31.25 ms	4.2 years			
	DIV2048	62.5 ms	8.5 years			
	DIV4096	0.125 s	17 years			
	DIV8192	0.25 s	34 years			
	DIV16384	0.5 s	68 years			
	DIV32768	1 s	136 years			

By default, the counter will keep counting until it reaches the top value, 0xFFFFFFF, before it wraps around and continues counting from zero. By setting CCV1TOP in RTCC_CTRL, a Capture/Compare channel 1 compare match will result in the main counter wrapping to 0. The timer will then wrap around on a channel 1 compare match (RTCC_CNT = RTCC_CC1_CCV). Before using the CCV1TOP setting, make sure to set this bit prior to or at the same time the RTCC is enabled. Setting CCV1TOP after enabling the RTCC (RTCC_CTRL_MODE != DISABLED) may cause unintended operation (e.g. if RTCC_CNT > RTCC_CC1_CCV, RTCC_CNT will wrap when reaching 0xFFFFFFFF rather than RTCC_CC1_CCV).

Note: If the RTCC is being reconfigured, and capture compare channel 1 has previously been used, a CCV1TOP wrap event might be pending. This would lead to the first tick of the main counter being a wrap to 0. To clear any pending wrap events, use the following procedure before reconfiguring the RTCC:

- 1. RTCC->CC[1].CTRL = RTCC_CC_CTRL_MODE_OFF;
- 2. RTCC->CTRL = RTCC_CTRL_CNTTICK_PRESC | RTCC_CTRL_CNTMODE_NORMAL | RTCC_CTRL_ENABLE;
- 3. rtcc_cnt_pre = RTCC->CNT;
- 4. while(RTCC->CNT == rtcc cnt pre);
- 5. Reconfigure the RTCC

13.3.1.2 Calendar Mode

The RTCC includes a calendar mode which implements time and date decoding in hardware. Calendar mode is enabled by configuring CNTMODE in RTCC_CTRL to CALENDAR. When in calendar mode, the counter value is available in RTCC_TIME and RTCC_DATE. RTCC_TIME shows seconds, minutes, and hours while RTCC_DATE shows day of month, month, year, and day of week. RTCC_TIME and RTCC_DATE are encoded in BCD format. In calendar mode, the pre-counter should be configured to give ticks with a period of one second, i.e. RTCC_CTRL_CNTTICK should be set to PRESC, and the CNTPRESC bitfield of the RTCC_CTRL register should be set to DIV32768 if a 32768 Hz clock source is used.

In calendar mode, the time and date registers of the capture compare channels, RTCC_CCx_TIME and RTCC_CCx_DATE, are used to set compare values. Compare values can be set on seconds, minutes, hours, days, and months. Whether day of week or day of month is used for a Capture/Compare channel, it is configured in RTCC_CCx_CTRL_DAYCC of the respective Capture/Compare channel.

The RTCC will automatically compensate for 28-, 29- (leap year), 30-, and 31-day months. The day of week counter, RTCC_DATE_DAYOW, is a three bit counter incrementing when RTCC_TIME_HOURT overflows, wrapping around every seventh day. Automatic leap year correction, extending the month of February from 28 to 29 days every fourth year is by default enabled, but can be disabled by setting the LYEARCORRDIS bit in RTCC_CTRL. The pseudo-code for leap year correction is as follows:

```
if RTCC_DATE_YEARU modulo 2 = 0:
    if RTCC_DATE_YEARU modulo 4 = 0:
        leap_year = true
    else:
        leap_year = false
else:
    if (RTCC_DATE_YEARU + 2) modulo 4 = 0:
        leap_year = true
    else:
        leap_year = false
```

The seconds, minute, hour segments are represented in 24-hour BCD format. The month segments are enumerated as shown in Table 13.2 RTCC calendar enumeration on page 379.

Month RTCC_DATE_MONTHT RTCC_DATE_MONTHU 0b0001 January 0b0 0b0 0b0010 February March 0b0 0b0011 April 0b0 0b0100 May 0b0 0b0101 June 0b0 0b0110 0b0 0b0111 July August 0b0 0b1000 September 0b0 0b1001 0b1 0b0000 October November 0b1 0b0001

0b0010

0b1

Table 13.2. RTCC calendar enumeration

December

13.3.1.3 RTCC Initialization

The counters of the RTCC, RTCC_CNT (RTCC_TIME and RTCC_DATE in calendar mode) and RTCC_PRECNT, can at any time be written by software, as long as the registers are not locked using RTCC_LOCKKEY. All RTCC registers use the immediate synchronization scheme, described in 4.3.1 Writing.

Note: Writing to the RTCC_PRECNT register may alter the frequency of the ticks for the RTCC_CNT register.

13.3.2 Capture/Compare Channels

Three capture/compare channels are available in the RTCC. Each channel can be configured as input capture or output compare, by setting the corresponding MODE in the RTCC_CCx_CTRL register.





Figure 13.3. RTCC Compare match and PRS output illustration

In input capture mode the RTCC_CNT (RTCC_TIME and RTCC_DATE in calendar mode) register is captured into the RTCC_CCx_CCV (RTCC_CCx_TIME and RTCC_CCx_DATE in calendar mode) register when an edge is detected on the selected PRS input channel. The active capture edge is configured in the ICEDGE control bits.

In output compare mode the compare values are set by writing to the RTCC compare channel registers RTCC_CCx_CCV (RTCC_CCx_TIME and RTCC_CCx_DATE in calendar mode). These values will be compared to the main counter, RTCC_CNT (RTCC_TIME and RTCC_DATE in calendar mode), or a mixture of the main counter and the pre-counter, as illustrated in Figure 13.4 RTCC Compare base illustration on page 382. Compare base for the capture compare channels is set by configuring COMP-BASE in RTCC_CCx_CTRL.






Figure 13.4. RTCC Compare base illustration

Table 13.3 RTCC Capture/Compare Subjects on page 382 summarizes which registers being subject to comparison for different configurations of RTCC_CTRL_CNTMODE and RTCC_CCx_CTRL_COMPBASE.

Table 13.3. RTCC Capture/Compare Subjects

RTCC_CTRL_CNTMODE	NORMAL	CALENDAR
RTCC_CCx_CTRL_COMPBASE = CNT	RTCC_CNT vs. RTCC_CCx_CCV	RTCC_TIME vs. RTCC_CCx_TIME and RTCC_DATE vs. RTCC_CCx_DATE
RTCC_CCx_CTRL_COMPBASE = PRECNT	{RTCC_CNT[16:0],RTCC_PRECNT[14:0]} vs. RTCC_CCx_CCV	RTCC_PRECNT vs. RTCC_CCx_CCV[14:0]

Figure 13.5 RTCC Compare in calendar mode, COMPBASE = CNT on page 383 illustrates how the compare events are evaluated when in calendar mode with RTCC_CCx_CTRL_COMPBASE = CNT. The SECU, SECT, MINU, MINT, HOURU, HOURT, MONTHU, and MONTHT bitfields in RTCC_CCx_TIME and RTCC_CCx_DATE are compared to the corresponding bitfields in RTCC_DATE and RTCC_TIME. The DAYU and DAYT bitfields in RTCC_CCx_DATE will be compared to {RTCC_DATE_DAYOM}, if DAYCC in RTCC_CCx_CTRL is set to MONTH. If DAYCC in RTCC_CCx_CTRL is set to WEEK, the DAYU and DAYT bitfields in RTCC_CCx_DATE will be compared to {0b000, RTCC_DATE_DAYOW}.




Figure 13.5. RTCC Compare in calendar mode, COMPBASE = CNT

To generate periodically recurring events, it is possible to mask out parts of the compare match values. By configuring COMPMASK in RTCC_CCx_CTRL, parts of the compare values will be masked out, limiting which part of the compare register being subject to comparison with the counter. Figure 13.6 RTCC Compare mask illustration, COMPMASK=11 on page 383 illustrates the effect of COMPMASK when in normal mode and calendar mode.




Figure 13.6. RTCC Compare mask illustration, COMPMASK=11

Upon a compare match, the respective Capture/Compare interrupt flag CCx is set. Additionally, the event selected by the CMOA setting is generated on the corresponding PRS output. This is illustrated in Figure 13.3 RTCC Compare match and PRS output illustration on page 381.

13.3.3 Interrupts and PRS Output

The RTCC has one interrupt for each of its 3 Capture/Compare channels, CC0, CC1, and CC2. Each Capture/Compare channel has a PRS output with configurable actions upon compare match.

The interrupt flag CNTTICK is set each time the main counter receives a tick (each second in calendar mode). In calendar mode, there are also interrupt flags being set each minute, hour, day, week, and month.

Upon oscillator failure detection, the OSCFAIL flag will be set.

13.3.3.1 Main Counter Tick PRS Output

To output the ticks for the main counter on PRS, it is possible to use a Capture/Compare channel and mask all the bits, i.e. RTCC_CCx_CTRL_COMPBASE=CNT and RTCC_CCx_CTRL_COMPMASK=31. PRS output of main counter ticks does not work if the main counter is not prescaled.

Note: To be able to mask all bits in the main counter, RTCC_CTRL_CNTMODE has to be set to CALENDAR. In NORMAL mode, the least significant bit can not be masked out.

13.3.4 Energy Mode Availability

The RTCC is available in all energy modes except EM4 Shutoff. To enable RTCC operation in EM4 Hibernate, the EMU_EM4CTRL register in the EMU has to be configured. Any enabled RTCC interrupt will wake the system up from EM4 Hibernate; if EM4WU in RTCC_EM4WUEN is set. Refer to 10. EMU - Energy Management Unit for details on how to configure the EMU.

13.3.5 Register Lock

To prevent accidental writes to the RTCC registers, the RTCC_LOCKKEY register can be written to any value other than the unlock value. To unlock the register, write the unlock value to RTCC_LOCKKEY. Registers affected by this lock are:

- RTCC_CTRL
- RTCC PRECNT
- · RTCC CNT
- RTCC TIME
- RTCC_DATE
- RTCC IEN
- RTCC POWERDOWN
- RTCC CCx CTRL
- RTCC CCx CCV
- RTCC_CCx_TIME
- RTCC CCx DATE

13.3.6 Oscillator Failure Detection

To be able to detect OSC failure, the RTCC includes a security mechanism ensuring that at least three OSC cycles are detected within one period of the ULFRCO. If no OSC cycles are detected, the OSCFAIL interrupt flag is set. OSC failure detection is enabled by setting the OSCFDETEN bit in RTCC_CTRL.

13.3.7 Retention Registers

The RTCC includes 32 x 32 bit registers which can be retained in all energy modes except EM4 Shutoff. The registers are accessible through the RETx_REG registers. Retention is by default enabled in EM0 Active through EM4 Hibernate/Shutoff. The registers can be shut off to save power by setting the RAM bit in RTCC_POWERDOWN.

Note: The retention registers are mapped to a RAM instance and have undefined state out of reset.

13.3.8 Debug Session

By default, the RTCC is halted when code execution is halted from the debugger. By setting the DEBUGRUN bit in the RTCC_CTRL register, the RTCC will continue to run even when the debugger has halted the system.

13.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	RTCC_CTRL	RW	Control Register
0x004	RTCC_PRECNT	RWH	Pre-Counter Value Register
0x008	RTCC_CNT	RWH	Counter Value Register
0x00C	RTCC_COMBCNT	R	Combined Pre-Counter and Counter Value Register
0x010	RTCC_TIME	RWH	Time of Day Register
0x014	RTCC_DATE	RWH	Date Register
0x018	RTCC_IF	R	RTCC Interrupt Flags
0x01C	RTCC_IFS	W1	Interrupt Flag Set Register
0x020	RTCC_IFC	(R)W1	Interrupt Flag Clear Register
0x024	RTCC_IEN	RW	Interrupt Enable Register
0x028	RTCC_STATUS	R	Status Register
0x02C	RTCC_CMD	W1	Command Register
0x030	RTCC_SYNCBUSY	R	Synchronization Busy Register
0x034	RTCC_POWERDOWN	RW	Retention RAM Power-down Register
0x038	RTCC_LOCK	RWH	Configuration Lock Register
0x03C	RTCC_EM4WUEN	RW	Wake Up Enable
0x040	RTCC_CC0_CTRL	RW	CC Channel Control Register
0x044	RTCC_CC0_CCV	RWH	Capture/Compare Value Register
0x048	RTCC_CC0_TIME	RWH	Capture/Compare Time Register
0x04C	RTCC_CC0_DATE	RWH	Capture/Compare Date Register
0x050	RTCC_CC1_CTRL	RW	CC Channel Control Register
0x054	RTCC_CC1_CCV	RWH	Capture/Compare Value Register
0x058	RTCC_CC1_TIME	RWH	Capture/Compare Time Register
0x05C	RTCC_CC1_DATE	RWH	Capture/Compare Date Register
0x060	RTCC_CC2_CTRL	RW	CC Channel Control Register
0x064	RTCC_CC2_CCV	RWH	Capture/Compare Value Register
0x068	RTCC_CC2_TIME	RWH	Capture/Compare Time Register
0x06C	RTCC_CC2_DATE	RWH	Capture/Compare Date Register
0x104	RTCC_RET0_REG	RW	Retention Register
	RTCC_RETx_REG	RW	Retention Register
0x180	RTCC_RET31_REG	RW	Retention Register

13.5 Register Description

13.5.1 RTCC_CTRL - Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset					Bit	t Po	siti	on									
0x000	31 30 29 28 27 27	24 24 23 23	20 2	9 3	17	16	15	4 5	12	11 0 8	7	5	4	က	2	1	0
Reset					0	0	0		0	0×0		0	0		0		0
Access					¥ M	¥ N	₹		\ N	RW.		₹	W.		N N		Z.
										ш.					_		
Name					LYEARCORRDIS	CNTMODE	OSCFDETEN		CNTTICK	CNTPRESC		CCV1TOP	PRECCV0TOP		DEBUGRUN		ENABLE
					- K	S	OSO		S	CN		ပ္ပ	PRE		DEE		E
Bit	Name	Reset	Access	Desc	ript	tion											
31:18	Reserved	To ensure co	mpatibility (with fut	ure	dev	vices	s, alwa	ys wi	rite bits to 0. Mo	re infori	natio	on in	1.2	Coi	nver	7-
17	LYEARCORRDIS	0	RW	Leap	Ye	ar (Corr	ection	Disa	abled							
	When cleared, Febru	uary has 29 days	s in leap yea	ars. Wł	nen	set,	, Fel	bruary	alwa	ys has 28 days.							
16	CNTMODE	0	RW	Main	Со	unt	er N	/lode									
	Configure count mod	le for the main c	ounter.														
	Value	Mode		Desc	ripti	on											_
	0	NORMAL		The r	mair	n co	unte	er is ind	crem	ented with 1 for	each tio	k.					
	1	CALENDAR		The r	mair	n co	unte	er is in	cale	ndar mode.							_
15	OSCFDETEN	0	RW	Osci	llate	or F	ailu	re Det	ectic	on Enable							
	When set, the OSCF	AIL interrupt flag	g will be set	t if no ti	icks	are	det	tected (on LF	CLK _{RTCC} within	n one U	LFR	СО	cycl	e.		
14:13	Reserved	To ensure co	mpatibility (with fut	ure	dev	vices	s, alwa	ys wi	rite bits to 0. Mo	re infori	natio	on in	1.2	Coi	nver)-
12	CNTTICK	0	RW	Cour	nter	Pre	esca	aler Mo	de								
	Select whether the n pre-counter tap select									pare match with	the pre-	-cou	nter	or ti	ck o	n a	
	Value	Mode		Desc	ripti	on											
	0	PRESC		CNT	reg	iste	r ticl	ks acco	ordin	g to configuratio	n in CN	TPR	RESC	Э.			
	1	CCV0MATCH	1	CNT	reg	iste	r ticl	ks whe	n PR	ECNT matches	RTCC_	CC	0_C	CV[14:0		_
11:8	CNTPRESC	0x0	RW	Cour	nter	Pre	esca	aler Va	lue								
	Configure counting f	requency of the	CNT registe	er.													
	Value	Mode		Desc	ripti	ion											_
	0	DIV1		CLK	CNT	= LI	FEC	LK _{RTC}	_C /1								_
	1	DIV2		CLK	CNT	= LI	FEC	LK _{RTC}	_C /2								

Bit	Name	Reset	Access	Description
	2	DIV4		CLK _{CNT} = LFECLK _{RTCC} /4
	3	DIV8		$CLK_{CNT} = LFECLK_{RTCC}/8$
	4	DIV16		CLK _{CNT} = LFECLK _{RTCC} /16
	5	DIV32		$CLK_{CNT} = LFECLK_{RTCC}/32$
	6	DIV64		CLK _{CNT} = LFECLK _{RTCC} /64
	7	DIV128		CLK _{CNT} = LFECLK _{RTCC} /128
	8	DIV256		CLK _{CNT} = LFECLK _{RTCC} /256
	9	DIV512		CLK _{CNT} = LFECLK _{RTCC} /512
	10	DIV1024		CLK _{CNT} = LFECLK _{RTCC} /1024
	11	DIV2048		CLK _{CNT} = LFECLK _{RTCC} /2048
	12	DIV4096		CLK _{CNT} = LFECLK _{RTCC} /4096
	13	DIV8192		CLK _{CNT} = LFECLK _{RTCC} /8192
	14	DIV16384		CLK _{CNT} = LFECLK _{RTCC} /16384
	15	DIV32768		CLK _{CNT} = LFECLK _{RTCC} /32768
7:6	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	CCV1TOP	0	RW	CCV1 Top Value Enable
	When set, the counter	er wraps around	on a CC1 e	event.
4	PRECCV0TOP	0	RW	Pre-counter CCV0 Top Value Enable
	When set, the pre-co	unter wraps arou	und when F	PRECNT equals RTCC_CC0_CCV[14:0].
3	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	DEBUGRUN	0	RW	Debug Mode Run Enable
	Set this bit to keep th	e RTCC running	during a d	ebug halt.
	Value			Description
	0			RTCC is frozen in debug mode
	1			RTCC is running in debug mode
1	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	ENABLE	0	RW	RTCC Enable
	Enable the RTCC.			

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset														,											0x0000							
Access																									RWH							
Name																									PRECNT							

Bit	Name	Reset	Access	Description
31:15	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
14:0	PRECNT	0x0000	RWH	Pre-Counter Value
	Gives access to the	Pre-counter val	lue of the RT	CC.

13.5.3 RTCC_CNT - Counter Value Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset		00000000000000000000000000000000000000																														
Access																																
Name																Ė	5															

Bit	Name	Reset	Access	Description
31:0	CNT	0x00000000	RWH	Counter Value
	Gives access to the n			TCC. Register can not be written and will be read as zero when

13.5.4 RTCC_COMBCNT - Combined Pre-Counter and Counter Value Register

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset			000000																					0000x0								
Access									<u>~</u>																<u>~</u>							
Name									CNTLSB																PRECNT							

Bit	Name	Reset	Access	Description
31:15	CNTLSB	0x00000	R	Counter Value
	Gives access to the 1 CALENDAR.	7 LSBs of the n	nain counte	r, CNT. Register will be read as zero when RTCC_CTRL_CNTMODE =
14:0	PRECNT	0x0000	R	Pre-Counter Value
	Gives access to the p	ore-counter, PRE	ECNT. Reg	ister will be read as zero when RTCC_CTRL_CNTMODE = CALENDAR.

13.5.5 RTCC_TIME - Time of Day Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	sitio	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	1	10	6	∞	7	9	5	4	က	2	_	0
Reset	et							5	S S		Š	e e				0x0			ÖXO	!				000			OXO	2				
Access											7/4/0								RWH			RWH					RWH			RWH		
Name		HOURT RV HOURU RV										MINT								SECT			I CHC	2								

Bit	Name	Reset	Access	Description
31:22	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
21:20	HOURT	0x0	RWH	Hours, Tens
		oart of the hour co		ter can not be written and will be read as zero when
19:16	HOURU	0x0	RWH	Hours, Units
		art of the hour cou NTMODE = NORM		er can not be written and will be read as zero when
15	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
14:12	MINT	0x0	RWH	Minutes, Tens
		oart of the minute on NTMODE = NORM		gister can not be written and will be read as zero when
11:8	MINU	0x0	RWH	Minutes, Units
		art of the minute o		ister can not be written and will be read as zero when
7	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
6:4	SECT	0x0	RWH	Seconds, Tens
		oart of the second NTMODE = NORM		gister can not be written and will be read as zero when
3:0	SECU	0x0	RWH	Seconds, Units
		art of the second on NTMODE = NORM		gister can not be written and will be read as zero when

13.5.6 RTCC_DATE - Date Register (Async Reg)

For more							_													-			`										
Offset																E	Bit Po	ositi	on														
0x014	31	30	29		28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	∞	7	. 9	2	4	က	7	_	c
Reset								OXO	2			0 0 0			(0X0					0		0×0						OX O		0	OX O	
Access								RWH				RWH			i	RWH					RWH		RWH						I M Y			[} Y	
Name								DAYOW				YEART				YEARU					MONTHT		MONTHU					!	DAYOMI			DATOINO	
Bit	Na	ame)					Reset Access Description To ensure compatibility with future devices always write hits to 0. More information in 1.2 Co.																									
31:27	Re	esei	ved	'				To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions														nve	7-										
26:24	DA	AYC	W					0:	к0			RV	٧H		Day	of	Wee	k															
		now: ORN			lay	of v	vee	k c	ounte	er. R	eg	ster	can	not	t be v	writ	ten a	nd v	/ill b	e re	ad a	as ze	ero w	he	n R	TC	C_C	TRL	_C	NTM	ODE	≣ =	
23:20	YE	EAR	T					0:	к0			RV	٧H		Yea	ır, 1	ens																
									e yea E = N				Regi	ster	can	no	t be	writte	en a	nd v	vill b	e re	ad a	s z	ero	wh	en						
19:16	YE	EAR	U					0:	к0			R۷	٧H		Yea	ır, l	Jnits																
									e yea E = N				egis	ter	can	not	be v	ritte	n ar	nd w	vill b	e rea	ad as	s ze	ero v	whe	en						
15:13	Re	esei	ved	'					o ens	sure	coi	npat	ibilit	y w	rith fu	utur	e de	/ices	s, alv	vay	s wr	ite b	its to	0.	Мо	re i	infori	nati	on	in 1.:	2 Co	nve	7-
12	М	ON	ГНТ					0				RV	٧H		Moi	nth	, Ter	s															
									e mo E = N				. Re	gist	ter ca	an r	not b	e wri	tten	and	l wil	l be	read	as	zer	о v	vhen						
11:8	N //		ГНІ	ı				<u>٠</u>	ν Ω			₽۱	٧H		Mo	nth	Hni	te															

		NTMODE = NOF	(IVI) (L.	
15:13	Reserved	To ensure tions	e compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
12	MONTHT	0	RWH	Month, Tens
	Shows the tens			ister can not be written and will be read as zero when
11:8	MONTHU	0x0	RWH	Month, Units
	Shows the unit p			ster can not be written and will be read as zero when
7:6	Reserved	To ensure tions	e compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	DAYOMT	0x0	RWH	Day of Month, Tens
	Shows the tens			er. Register can not be written and will be read as zero when
3:0	DAYOMU	0x0	RWH	Day of Month, Units
	Shows the unit p			r. Register can not be written and will be read as zero when

13.5.7 RTCC_IF - RTCC Interrupt Flags

Offset	Bit Position										
0x018	33 30 30 30 30 30 30 30 30 30 30 30 30 3	9	n	7	9	2	4	က	2	_	0
Reset		0	0	0	0	0	0	0	0	0	0
Access		۵ د	2 22	2	22	22	22	~	2	<u>~</u>	ď
Name		DNTH	DAYTICK	HOURTICK	MINTICK	CNTTICK	OSCFAIL	CC2	CC1	000	OF

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10	MONTHTICK	0	R	Month Tick
	Set each time the mo	nth counter incr	ements.	
9	DAYOWOF	0	R	Day of Week Overflow
	Set each time the day	of week counter	er overflows	S
8	DAYTICK	0	R	Day Tick
	Set each time the day	counter increm	ents.	
7	HOURTICK	0	R	Hour Tick
	Set each time the hou	ur counter increr	nents.	
6	MINTICK	0	R	Minute Tick
	Set each time the mir	nute counter inci	ements.	
5	CNTTICK	0	R	Main Counter Tick
	Set each time the ma	in counter is upo	dated.	
4	OSCFAIL	0	R	Oscillator Failure Interrupt Flag
	Set when an oscillato	r failure has bee	n detected	l
3	CC2	0	R	Channel 2 Interrupt Flag
	Set when a channel 2	event has occu	ırred.	
2	CC1	0	R	Channel 1 Interrupt Flag
	Set when a channel 1	event has occu	ırred.	
1	CC0	0	R	Channel 0 Interrupt Flag
	Set when a channel 0	event has occu	ırred.	
0	OF	0	R	Overflow Interrupt Flag
	Set when a RTCC ov	erflow has occu	rred.	

13.5.8 RTCC_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset			'		'	•					•				'							0	0	0	0	0	0	0	0	0	0	0
Access																						W W	W1	W	W1	W W	M	W W	W	W1	W1	W1
Name																						MONTHTICK	DAYOWOF	DAYTICK	HOURTICK	MINTICK	CNTTICK	OSCFAIL	CC2	CC1	CC0	OF

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10	MONTHTICK	0	W1	Set MONTHTICK Interrupt Flag
	Write 1 to set the MO	NTHTICK interr	upt flag	
9	DAYOWOF	0	W1	Set DAYOWOF Interrupt Flag
	Write 1 to set the DAY	OWOF interrup	t flag	
8	DAYTICK	0	W1	Set DAYTICK Interrupt Flag
	Write 1 to set the DAY	TICK interrupt	flag	
7	HOURTICK	0	W1	Set HOURTICK Interrupt Flag
	Write 1 to set the HO	JRTICK interrup	ot flag	
6	MINTICK	0	W1	Set MINTICK Interrupt Flag
	Write 1 to set the MIN	TICK interrupt f	lag	
5	CNTTICK	0	W1	Set CNTTICK Interrupt Flag
	Write 1 to set the CN	TTICK interrupt	flag	
4	OSCFAIL	0	W1	Set OSCFAIL Interrupt Flag
	Write 1 to set the OSC	CFAIL interrupt	flag	
3	CC2	0	W1	Set CC2 Interrupt Flag
	Write 1 to set the CC2	2 interrupt flag		
2	CC1	0	W1	Set CC1 Interrupt Flag
	Write 1 to set the CC	I interrupt flag		
1	CC0	0	W1	Set CC0 Interrupt Flag
	Write 1 to set the CCC) interrupt flag		
0	OF	0	W1	Set OF Interrupt Flag
	Write 1 to set the OF	interrupt flag		

13.5.9 RTCC_IFC - Interrupt Flag Clear Register

Offset				В	it Positio	n													
0x020	33 33 23 23 23 24 27 27	25 25 23 23	7 5 5	7 18	15 15	4 (5 5	1	10	ဝ	8	7	9	2	4	က	7	_	0
Reset									0	0	0	0	0	0	0	0	0	0	0
Access									(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name									MONTHTICK	DAYOWOF	DAYTICK	HOURTICK	MINTICK	CNTTICK	OSCFAIL	CC2	CC1	000	OF
Bit	Name	Reset	Access	Descrip	otion														
31:11	Reserved	To ensure c	ompatibility	with future	e devices,	alw	ays и	rite l	oits t	o 0.	Мог	re in	forn	natio	on in	1.2	? Co	nvei	n-
10	MONTHTICK	0	(R)W1	Clear M	IONTHTIC	ΚI	nterr	upt F	lag										
	Write 1 to clear the flags (This feature				eturns the	val	ue of	the I	F ar	nd cl	ears	the	COI	res	ono	ding	inte	rrup	ot
9	DAYOWOF	0	(R)W1	Clear D	AYOWOF	Int	errup	t Fla	ıg										
	Write 1 to clear the flags (This feature				turns the v	alue	e of th	e IF	and	clea	ars t	he c	orre	espc	ndir	ng in	nterr	upt	
8	DAYTICK	0	(R)W1	Clear D	AYTICK I	nte	rrupt	Flag											
	Write 1 to clear the (This feature must				rns the va	ue (of the	IF a	nd c	lears	s the	e co	rres	pon	ding	inte	errup	ot fla	ıgs
7	HOURTICK	0	(R)W1	Clear H	OURTICE	(Int	erru	t Fla	ag										
	Write 1 to clear the flags (This feature				turns the v	/alu	e of th	ne IF	and	clea	ars t	he d	corre	espo	ndiı	ng ir	nterr	upt	
6	MINTICK	0	(R)W1	Clear M	IINTICK II	nter	rupt	Flag											
	Write 1 to clear the (This feature must				ns the val	ue c	of the	IF ar	nd cl	ears	the	cor	resp	onc	ling	inte	rrup	t fla	gs
5	CNTTICK	0	(R)W1	Clear C	NTTICK I	ntei	rupt	Flag											
	Write 1 to clear the (This feature must				rns the val	ue (of the	IF a	nd c	lears	s the	e co	rres	pon	ding	inte	errup	ot fla	ıgs
4	OSCFAIL	0	(R)W1	Clear O	SCFAIL I	ntei	rupt	Flag											
	Write 1 to clear the (This feature must				ns the val	ue (of the	IF a	nd c	lears	s the	COI	res	pon	ding	inte	errup	t fla	ıgs
3	CC2	0	(R)W1	Clear C	C2 Interr	upt	Flag												
	Write 1 to clear the feature must be en			returns th	e value of	the	IF ar	id cle	ears	the	corr	espo	ondi	ng i	nter	rupt	flag	s (T	his

Write 1 to clear the CC1 interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This

Clear CC0 Interrupt Flag

Write 1 to clear the CC0 interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This

CC0

1

feature must be enabled globally in MSC.).

feature must be enabled globally in MSC.).

0

(R)W1

Bit	Name	Reset	Access	Description
0	OF	0	(R)W1	Clear OF Interrupt Flag
	Write 1 to clear the Office feature must be enabled	. •	•	turns the value of the IF and clears the corresponding interrupt flags (This

13.5.10 RTCC_IEN - Interrupt Enable Register

Offset		Bit Position	
0x024	20 29 29 30 30 30 50 50 50 50 50 50 50 50 50 50 50 50 50	6 8 7 1 <th>0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0</th>	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0
Reset			0 0 0 0 0 0 0 0 0 0
Access			M M M M M M M M M M M M M M M M M M M
Name			MONTHTICK DAYOWOF DAYTICK HOURTICK MINTICK CNTTICK CSC CC2 CC1 CC1 CC0

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure comp tions	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
10	MONTHTICK	0	RW	MONTHTICK Interrupt Enable
	Enable/disable the	MONTHTICK interru	upt	
9	DAYOWOF	0	RW	DAYOWOF Interrupt Enable
	Enable/disable the	DAYOWOF interrup	t	
8	DAYTICK	0	RW	DAYTICK Interrupt Enable
	Enable/disable the	DAYTICK interrupt		
7	HOURTICK	0	RW	HOURTICK Interrupt Enable
	Enable/disable the	HOURTICK interrup	ot	
6	MINTICK	0	RW	MINTICK Interrupt Enable
	Enable/disable the	MINTICK interrupt		
5	CNTTICK	0	RW	CNTTICK Interrupt Enable
	Enable/disable the	CNTTICK interrupt		
4	OSCFAIL	0	RW	OSCFAIL Interrupt Enable
	Enable/disable the	OSCFAIL interrupt		
3	CC2	0	RW	CC2 Interrupt Enable
	Enable/disable the	CC2 interrupt		
2	CC1	0	RW	CC1 Interrupt Enable
	Enable/disable the	CC1 interrupt		
1	CC0	0	RW	CC0 Interrupt Enable
	Enable/disable the	CC0 interrupt		
0	OF	0	RW	OF Interrupt Enable
	Enable/disable the	OF interrupt		

13.5.11 RTCC_STATUS - Status Register

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset										•		•		•				•								•		•				
Access																																
Name																																
														_																		

Bit	Name	Reset Acc	cess	Description
31:0	Reserved	To ensure compatible tions	ibility wi	ith future devices, always write bits to 0. More information in 1.2 Conven-

13.5.12 RTCC_CMD - Command Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset	Bit Position																															
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	_	0
Reset				'	'	•		•				•			•	•	'		•				•		•		'	'	•	•		0
Access																																W
Name																																TATUS
Name																																CLRS

Bit	Name	Reset	Access	Description						
31:1	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-						
0	CLRSTATUS	0 W1 Clear RTCC_STATUS Register								
	Write a 1 to clear the RTCC_STATUS register.									

13.5.13 RTCC_SYNCBUSY - Synchronization Busy Register

Bit Position	
2 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	υ 4 m 0 t 0
	0
	Y
	CMC
·~	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0

Bit	Name	Reset	Access	Description					
31:6	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-					
5	CMD	0	R CMD Register Busy						
	Set when the value w	ritten to CMD is	being synd	chronized.					
4:0	Reserved	To ensure contions	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions						

13.5.14 RTCC_POWERDOWN - Retention RAM Power-down Register (Async Reg)

Offset	Bit Position	
0x034	1 1 <th>0</th>	0
Reset		0
Access		RW
Name		RAM

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	RAM	0	RW	Retention RAM Power-down
	Shut off power to the	Retention RAM	. Once it is	powered down, it cannot be powered up again

13.5.15 RTCC_LOCK - Configuration Lock Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset							1	'			1			1							1				000000	•	1	ı	1			
Access																									[}							
Name) 	LOCAN							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock Key

Write any other value than the unlock code to lock RTCC_CTRL, RTCC_PRECNT, RTCC_CNT, RTCC_TIME, RTCC_DATE, RTCC_IEN, RTCC_POWERDOWN, and RTCC_CCx_XXX registers from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	All registers are unlocked
LOCKED	1	Registers are locked
Write Operation		
LOCK	0	Lock registers
UNLOCK	0xAEE8	Unlock all RTCC registers

13.5.16 RTCC_EM4WUEN - Wake Up Enable

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																																0
Access																																R W
Name																																EM4WU

Bit	Name	Reset	Access	Description						
31:1	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-						
0	EM4WU	0	RW	EM4 Wake-up Enable						
	Write 1 to enable wake-up request, write 0 to disable wake-up request.									

13.5.17 RTCC_CCx_CTRL - CC Channel Control Register (Async Reg)

Offset					Bi	t Position								
0x040	30 29 28 29	25 25 23 23 23	22 22 20 20	19	17	6 5 4	13	12	11	9	0 8 6	τυ 4	ю q	- 0
Reset					0	00X0			0		0x0	0x0	0x0	0×0
Access					RW W	Ž.			RW		RW	A W	§ §	Z S
Name					DAYCC	COMPMASK			COMPBASE		PRSSEL	ICEDGE	СМОА	MODE
Bit	Name	Reset	Access	Des	crip	tion								
31:18	Reserved	To ensure co	ompatibility	with fu	ture	devices, a	lway	s wr	ite b	oits t	o 0. More infor	mation ii	n 1.2 Co	nven-
17	DAYCC	0	RW	Day	Cap	oture/Com	pare	Sel	ecti	on				
	Select whether d	ay of week, or day	of month is	subjec	t for	Capture/C	omp	are.						
	Value	Mode		Desc	cript	ion								
	0	MONTH		Day	of n	nonth is se	ecte	d for	Ca	ptur	e/Compare.			
	1	WEEK		Day	of w	veek is sele	ctec	for (Сар	ture	/Compare.			
16:12	COMPMASK	0x00	RW	Cap	ture	Compare	Cha	anne	l Cc	mp	arison Mask			
	The COMPMASH	K most significant b	its of the co	mpare	valı	ue will not l	oe si	ubjed	t to	con	nparison.			
11	COMPBASE	0	RW	Cap	ture	Compare	Cha	anne	l Cc	mp	arison Base			
	Configure compa	rison base for com	pare chann	el										
	Value	Mode		Desc	cript	ion								
	0	CNT			C_{C}	CCx_CCV CCx_TIME	is DAT			are	d with RT with RTCC_TIM	CC_CN ME/DATI		ister. endar
	1	PRECNT		Leas	st siç	gnificant bi	s of	RTC	C_0	CCx	_CCV are com	pared w	ith PRE	CNT.
10	Reserved	To ensure co	ompatibility	with fu	ture	devices, a	lway	s wr	ite b	oits t	to 0. More infor	mation ii	n 1.2 Co	nven-
9:6	PRSSEL	0x0	RW	Com	ıpaı	e/Capture	Cha	anne	I PF	RS Ir	nput Channel	Selectio	n	
	Select PRS input	channel for Comp	are/Capture	e chann	el.									
	Value	Mode		Desc	cript	ion								
	0	PRSCH0		PRS	Ch	annel 0 sel	ecte	d as	inpı	ut				

Value	Mode	Description
0	PRSCH0	PRS Channel 0 selected as input
1	PRSCH1	PRS Channel 1 selected as input
2	PRSCH2	PRS Channel 2 selected as input
3	PRSCH3	PRS Channel 3 selected as input
4	PRSCH4	PRS Channel 4 selected as input
5	PRSCH5	PRS Channel 5 selected as input

			TOO - Iteal Time obtained and balenda
Bit	Name	Reset Acces	ss Description
	6	PRSCH6	PRS Channel 6 selected as input
	7	PRSCH7	PRS Channel 7 selected as input
	8	PRSCH8	PRS Channel 8 selected as input
	9	PRSCH9	PRS Channel 9 selected as input
	10	PRSCH10	PRS Channel 10 selected as input
	11	PRSCH11	PRS Channel 11 selected as input
5:4	ICEDGE	0x0 RW	Input Capture Edge Select
	These bits conti	rol which edges the PRS edg	e detector triggers on.
	Value	Mode	Description
	0	RISING	Rising edges detected
	1	FALLING	Falling edges detected
	2	ВОТН	Both edges detected
	3	NONE	No edge detection, signal is left as it is
3:2	СМОА	0x0 RW	Compare Match Output Action
	Select output ac	ction on compare match.	
	Value	Mode	Description
	0	PULSE	A single clock cycle pulse is generated on output
	1	TOGGLE	Toggle output on compare match
	2	CLEAR	Clear output on compare match
	3	SET	Set output on compare match
1:0	MODE	0x0 RW	CC Channel Mode
	These bits selec	ct the mode for Compare/Cap	ture channel.
	Value	Mode	Description
	0	OFF	Compare/Capture channel turned off
	1	INPUTCAPTURE	Input capture

13.5.18 RTCC_CCx_CCV - Capture/Compare Value Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	0000000000															
Access																																
Name																2	<u>}</u>															

Bit	Name	Reset	Access	Description
31:0	CCV	0x00000000	RWH	Capture/Compare Value
	Shows the Capture/Co	•		nel. Register can not be written and will be read as zero when

13.5.19 RTCC_CCx_TIME - Capture/Compare Time Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x048	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset												OX O		Š	e X				0x0			5	OXO				000	•		0×0		
Access											1/4/0				[} Y				RWH			ם, אלם	[}				RWH			RWH		
Name											FOI	5		<u>-</u>	חאחטש				MINT				0				SECT			SECU		

						2		_O	, o
Bit	Name	Reset	Access	Description					
31:22	Reserved	To ensure o	compatibility	with future devic	es, always w	rite bits to 0. Mo	ore in	formation i	n 1.2 Conven-
21:20	HOURT	0x0	RWH	Hours, Tens					
		oart of the Capture NTMODE = NORM		alue for hours. Re	egister can n	ot be written and	d will	be read as	zero when
19:16	HOURU	0x0	RWH	Hours, Units					
		art of the Capture/ NTMODE = NORM		alue for hours. Re	gister can no	ot be written and	d will	be read as	zero when
15	Reserved	To ensure o	compatibility	with future devic	es, always w	rite bits to 0. Mo	ore in	formation i	n 1.2 Conven-
14:12	MINT	0x0	RWH	Minutes, Tens	3				
		oart of the Capture NTMODE = NORM		alue for minutes.	Register can	not be written a	and v	vill be read	as zero when
11:8	MINU	0x0	RWH	Minutes, Unit	5				
		art of the Capture/ NTMODE = NORM		alue for minutes. I	Register can	not be written a	nd w	ill be read a	as zero when
7	Reserved	To ensure o	compatibility	with future devic	es, always w	rite bits to 0. Mo	ore in	formation i	n 1.2 Conven-
6:4	SECT	0x0	RWH	Seconds, Ten	s				
		part of the Capture NTMODE = NORM		alue for seconds.	Register car	n not be written	and v	will be read	as zero when
3:0	SECU	0x0	RWH	Seconds, Uni	ts				
		art of the Capture/ NTMODE = NORM		alue for seconds.	Register can	not be written a	and w	vill be read	as zero when

13.5.20 RTCC_CCx_DATE - Capture/Compare Date Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	it Po	siti	on														
0x04C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	2	4	က	2	_	0
Reset			'	•	'	•	•		•					•	'	'		'		0		2	OX O			•	2	2		OXO	2	
Access																				RWH							ם, אלו			RWE	-	
Name																				MONTHT		FINCE					F	-		DAYII	2	

Bit	Name	Reset	Access	Description
31:13	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
12	MONTHT	0	RWH	Month, Tens
	Shows the tens pa			alue for months. Register can not be written and will be read as zero when
11:8	MONTHU	0x0	RWH	Month, Units
	Shows the unit par RTCC_CTRL_CN			lue for months. Register can not be written and will be read as zero when
7:6	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	DAYT	0x0	RWH	Day of Month/week, Tens
	Shows the tens pa	•	•	lue for days. Register can not be written and will be read as zero when
3:0	DAYU	0x0	RWH	Day of Month/week, Units
	Shows the unit par RTCC_CTRL_CN	•	•	lue for days. Register can not be written and will be read as zero when


13.5.21 RTCC_RETx_REG - Retention Register

Offset															Bi	t Po	siti	on														
0x104	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Reset			XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX																													
Access																\ 0	2															
Name																	D L L															

Bit	Name	Reset	Access	Description
31:0	REG	0xXXXXXXX X	RW	General Purpose Retention Register

14. WDOG - Watchdog Timer





Quick Facts

What?

The Watchdog Timer (WDOG) resets the system in case of a fault condition, and can be enabled in all energy modes as long as the low frequency clock source is available.

Why?

If a software failure or external event renders the MCU unresponsive, a Watchdog timeout will reset the system to a known, safe state.

How?

An enabled Watchdog Timer implements a configurable timeout period. If the CPU fails to re-start the Watchdog Timer before it times out, a full system reset will be triggered. The Watchdog consumes insignificant power, and allows the device to remain safely in low energy modes for up to 256 seconds at a time.

14.1 Introduction

The purpose of the watchdog timer is to generate a reset in case of a system failure to increase application reliability. The failure can be caused by a variety of events, such as an ESD pulse or a software failure.

14.2 Features

- · Clock input from selectable oscillators
 - Internal 32 kHz LFRCO oscillator
 - · Internal 1 kHz ULFRCO oscillator
 - External 32.768 kHz LFXO XTAL oscillator
 - HFCORECLK
- Configurable timeout period from 9 to 256k watchdog clock cycles
- Individual selection to keep running or freeze when entering EM2 Deep Sleep or EM3 Stop
- · Selection to keep running or freeze when entering debug mode
- Selection to block the CPU from entering Energy Mode 4
- · Selection to block the CMU from disabling the selected watchdog clock
- · Configurable warning interrupt at 25%,50%, or 75% of the timeout period
- Configurable window interrupt at 12.5%,25%,37.5%,50%,62.5%,75%,87.5% of the timeout period
- · Timeout interrupt
- · PRS as a watchdog clear
- Interrupt for the event where a PRS rising edge is absent before a software reset

14.3 Functional Description

The watchdog is enabled by setting the EN bit in WDOGn_CTRL. When enabled, the watchdog counts up to the period value configured through the PERSEL field in WDOGn_CTRL. If the watchdog timer is not cleared to 0 (by writing a 1 to the CLEAR bit in WDOGn_CMD) before the period is reached, the chip is reset. If a timely clear command is issued, the timer starts counting up from 0 again. The watchdog can optionally be locked by writing the LOCK bit in WDOGn_CTRL. Once locked, it cannot be disabled or reconfigured by software.

When the EN bit in WDOGn_CTRL is cleared to 0, the watchdog counter is reset.

14.3.1 Clock Source

Three clock sources are available for use with the watchdog, through the CLKSEL field in WDOGn_CTRL. The corresponding clocks must be enabled in the CMU. The SWOSCBLOCK bit in WDOGn_CTRL can be written to prevent accidental disabling of the selected clocks. Also, setting this bit will automatically start the selected oscillator source when the watchdog is enabled. The PERSEL field in WDOGn_CTRL is used to divide the selected watchdog clock, and the timeout for the watchdog timer can be calculated with the formula:

$$T_{TIMEOUT} = (2^{3+PERSEL} + 1) / f$$

where f is the frequency of the selected clock.

When the watchdog is enabled, it is recommended to clear the watchdog before changing PERSEL.

To use this module, the LE interface clock must be enabled in CMU HFBUSCLKEN0.

14.3.2 Debug Functionality

The watchdog timer can either keep running or be frozen when the device is halted by a debugger. This configuration is done through the DEBUGRUN bit in WDOGn CTRL. When code execution is resumed, the watchdog will continue counting where it left off.

14.3.3 Energy Mode Handling

The watchdog timer can be configured to either keep on running or freeze when entering EM2 Deep Sleep or EM3 Stop. The configuration is done individually for each energy mode in the EM2RUN and EM3RUN bits in WDOGn_CTRL. When the watchdog has been frozen and is re-entering an energy mode where it is running, the watchdog timer will continue counting where it left off. For the watchdog there is no difference between EM0 Active and EM1 Sleep. The watchdog does not run in EM4 Hibernate/Shutoff. If EM4BLOCK in WDOGn_CTRL is set, the CPU will be prevented from entering EM4 Hibernate/Shutoff by software request.

Note:

If the WDOG is clocked by the LFXO or LFRCO, writing the SWOSCBLOCK bit will prevent the CPU from entering EM3 Stop. When running from the ULFRCO, writing the SWOSCBLOCK bit will prevent the CPU from entering EM4 Hibernate/Shutoff.

14.3.4 Register Access

Since this module is a Low Energy Peripheral, and runs off a clock which is asynchronous to the HFCORECLK, special considerations must be taken when accessing registers. Refer to 4.3 Access to Low Energy Peripherals (Asynchronous Registers) for a description on how to perform register accesses to Low Energy Peripherals. Note that clearing the EN bit in WDOGn_CTRL will reset the WDOG module, which will halt any ongoing register synchronization.

Note:

Never write to the WDOG registers when it is disabled, except to enable the watchdog by setting the EN bitfield in WDOGn_CTRL.

14.3.5 Warning Interrupt

The watchdog implements a warning interrupt which can be configured to occur at approximately 25%, 50%, or 75% of the timeout period through the WARNSEL field of the WDOGn_CTRL register. This interrupt can be used to wake up the cpu for clearing the watchdog. The warning point for the watchdog timer can be calculated with the formula:

$$T_{WARNING} = ((2^{3+PERSEL}) * (WARNSEL / 4) + 1) / f,$$

where f is the frequency of the selected clock.

When the watchdog is enabled, it is recommended to clear the watchdog before changing WARNSEL.

14.3.6 Window Interrupt

This interrupt occurs when the watchdog is cleared below a certain threshold. This threshold is given by the formula:

$$T_{WARNING} = ((2^{3+PERSEL}) * (WINSEL/8) + 1)/f,$$

where f is the frequency of the selected clock.

This value will be approximately 12.5%, 25%, 37.5%, 50%, 62.5%, 75%, or 87.5% of the timeout value based on the WINSEL field of the WDOGn_CTRL. Figure 14.2 WDOG Warning, Window, and Timeout on page 406 illustrates the warning, the window, and the timeout interrupts. Also, it shows where the prs rising edge needs to happen. The prs edge detection feature is discussed later.




Figure 14.2. WDOG Warning, Window, and Timeout

When the watchdog is enabled, it is recommended to clear the watchdog before changing WINSEL.

14.3.7 PRS as Watchdog Clear

The first PRS channel (selected by register WDOGn_PCH0_PRSCTRL) can be used to clear the watchdog counter. To enable this feature, CLRSRC must be set to 1. Figure 14.2 PRS Clearing WDOG on page 407 shows how the PRS channel takes over the WDOG clear function. Clearing the WDOG with the PRS is mutually exclusive of clearing the WDT by software.




Figure 14.2. PRS Clearing WDOG

14.3.8 PRS Rising Edge Monitoring

PRS channels can be used to monitor multiple processes. If enabled, every time the watch dog timer is cleared the PRS channels are checked and any channel which has not seen an event can trigger an interrupt.




Figure 14.3. PRS Edge Monitoring in WDOG

14.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	WDOG_CTRL	RW	Control Register
0x004	WDOG_CMD	W1	Command Register
0x008	WDOG_SYNCBUSY	R	Synchronization Busy Register
0x00C	WDOGn_PCH0_PRSCTRL	RW	PRS Control Register
0x010	WDOGn_PCH1_PRSCTRL	RW	PRS Control Register
0x01C	WDOG_IF	R	Watchdog Interrupt Flags
0x020	WDOG_IFS	W1	Interrupt Flag Set Register
0x024	WDOG_IFC	(R)W1	Interrupt Flag Clear Register
0x028	WDOG_IEN	RW	Interrupt Enable Register

14.5 Register Description

14.5.1 WDOG_CTRL - Control Register (Async Reg)

Offset															Ві	it Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset	0	0					0×0						1		2) X		•	Š) X		L	Š			0	0	0	0	0	0	0
Access	R W	R ≪					R M								2	≥ Y			2	≥ Y		i	≥ Y			Z.	Z.	R W	₩ M	W M	X ≪	X W
Name	WDOGRSTDIS	CLRSRC					WINSEL									WAKINSEL			Į.	CLRSEL		I C C L	PERSEL			SWOSCBLOCK	EM4BLOCK	LOCK	EM3RUN	EM2RUN	DEBUGRUN	EN

-				
Bit	Name	Reset	Access	Description
31	WDOGRSTDIS	0	RW	Watchdog Reset Disable
	Disable watchdog res	set output.		
	Value	Mode		Description
	0	EN		A timeout will cause a watchdog reset
	1	DIS		A timeout will not cause a watchdog reset
30	CLRSRC	0	RW	Watchdog Clear Source
	Select watchdog clea	ır source.		
	Value	Mode		Description
	0	SW		A write to the clear bit will clear the watchdog counter
	1	PCH0		A rising edge on the PRS Channel0 will clear the watchdog counter
29:27	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
26:24	WINSEL	0x0	RW	Watchdog Illegal Window Select
	Select watchdog illeg	al limit.		
	Value			Description
	0			Disabled.
	1			Window limit is 12.5% of the Timeout.
	2			Window limit is 25.0% of the Timeout.
	3			Window limit is 37.5% of the Timeout.
	4			Window limit is 50.0% of the Timeout.
	5			Window limit is 62.5% of the Timeout.
	6			Window limit is 75.0% of the Timeout.
	7			Window limit is 87.5% of the Timeout.

Bit	Name	Reset	Access	Description
23:18	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	WARNSEL	0x0	RW	Watchdog Timeout Period Select
	Select watchdog	warning timeout p	eriod.	
	Value			Description
	0			Disabled.
	1			Warning timeout is 25% of the Timeout.
	2			Warning timeout is 50% of the Timeout.
	3			Warning timeout is 75% of the Timeout.
15:14	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13:12	CLKSEL	0x0	RW	Watchdog Clock Select
	Selects the WDC	OG oscillator, i.e. th	ie clock on w	hich the watchdog will run.
	Value	Mode		Description
	0	ULFRCO		ULFRCO
	1	LFRCO		LFRCO
	2	LFXO		LFXO
	3	HFCORECI	_K	HFCORECLK
11:8	PERSEL	0xF	RW	Watchdog Timeout Period Select
	Select watchdog	timeout period.		
	Value			Description
	0			Timeout period of 9 watchdog clock cycles.
	1			Timeout period of 17 watchdog clock cycles.
	2			Timeout period of 33 watchdog clock cycles.
	3			Timeout period of 65 watchdog clock cycles.
	4			Timeout period of 129 watchdog clock cycles.
	5			Timeout period of 257 watchdog clock cycles.
	6			Timeout period of 513 watchdog clock cycles.
	7			Timeout period of 1k watchdog clock cycles.
	8			Timeout period of 2k watchdog clock cycles.
	9			Timeout period of 4k watchdog clock cycles.
	10			Timeout period of 8k watchdog clock cycles.
	11			Timeout period of 16k watchdog clock cycles.
	12			Timeout period of 32k watchdog clock cycles.
	13			Timeout period of 64k watchdog clock cycles.
	14			Timeout period of 128k watchdog clock cycles.
	11 12 13			Timeout period of 16k watchdog clock cycles. Timeout period of 32k watchdog clock cycles. Timeout period of 64k watchdog clock cycles.

7	15			
7				Timeout period of 256k watchdog clock cycles.
/	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6	SWOSCBLOCK	0	RW	Software Oscillator Disable Block
	Set to disallow disability is not already running		ed WDOG	oscillator. Writing this bit to 1 will turn on the selected WDOG oscillator if it
	Value			Description
	0			Software is allowed to disable the selected WDOG oscillator. See CMU for detailed description. Note that also CMU registers are lockable.
	1			Software is not allowed to disable the selected WDOG oscillator.
5	EM4BLOCK	0	RW	Energy Mode 4 Block
	Set to disallow EM4	entry by software	Э.	
	Value			Description
	0			EM4 can be entered by software. See EMU for detailed description.
	1			EM4 cannot be entered by software.
4	LOCK	0	RW	Configuration Lock
	Set to lock the watch	ndog configuratio	n. This bit	can only be cleared by reset.
	Value			Description
	0			Watchdog configuration can be changed.
	1			Watchdog configuration cannot be changed.
3	EM3RUN	0	RW	Energy Mode 3 Run Enable
	Set to keep watchdo	g running in EM3	3.	
	Value			Description
	0			Watchdog timer is frozen in EM3.
	1			Watchdog timer is running in EM3.
2	EM2RUN	0	RW	Energy Mode 2 Run Enable
	Set to keep watchdo	g running in EM2	2.	
	Value			Description
	0			Watchdog timer is frozen in EM2.
	1			Watchdog timer is running in EM2.
1	DEBUGRUN	0	RW	Debug Mode Run Enable
	Set to keep watchdo	g running in deb	ug mode.	
	Value			Description
	0			Watchdog timer is frozen in debug mode.
	1			Watchdog timer is running in debug mode.

Bit	Name	Reset	Access	Description
0	EN	0	RW	Watchdog Timer Enable
	Set to enabled watch	dog timer.		

14.5.2 WDOG_CMD - Command Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	1	10	တ	∞	7	9	5	4	က	2	_	0
Reset			•																									•				0
Access																																W1
Name																																CLEAR

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cor tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	CLEAR	0	W1	Watchdog Timer Clear
	Clear watchdog time	The bit must be	e written 4	watchdog cycles before the timeout.
	Value	Mode		Description
	0	UNCHANGED)	Watchdog timer is unchanged.
	1	CLEARED		Watchdog timer is cleared to 0.

14.5.3 WDOG_SYNCBUSY - Synchronization Busy Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	7	_	0
Reset					'											'				'								•	0	0	0	0
Access																													22	~	2	~
Name																													PCH1_PRSCTRL	PCH0_PRSCTRL	CMD	CTRL

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	PCH1_PRSCTRL	0	R	PCH1_PRSCTRL Register Busy
	Set when the value w	ritten to PCH1_	PRSCTRL	is being synchronized.
2	PCH0_PRSCTRL	0	R	PCH0_PRSCTRL Register Busy
	Set when the value w	ritten to PCH0_	PRSCTRL	is being synchronized.
1	CMD	0	R	CMD Register Busy
	Set when the value w	ritten to CMD is	being synd	chronized.
0	CTRL	0	R	CTRL Register Busy
	Set when the value w	ritten to CTRL is	s being syn	chronized.

14.5.4 WDOGn_PCHx_PRSCTRL - PRS Control Register (Async Reg)

Offset			В	Bit Position												
0x00C	30 30 28 28 27 27 27	25 23 23 24 27 27 27 27 27 27 27 27 27 27 27 27 27	20 19 18 17	6 2 4	13	1 =	10	တ ထ	_	9	2	4	8 2	- O		
Reset								c					0			
Access								\ <u>8</u>					·	 ≩		
								S T								
Name								PRSMISSRSTEN					;			
								NS:					Č	PKSSEL		
								A B					Ĺ	<u>,</u>		
Bit	Name	Reset Acc	cess Descri	ption												
31:9	Reserved	To ensure compatilitions	bility with futur	e devices, al	ways u	vrite b	its to	o 0. M	ore ir	nform	atio	n in	1.2 Co	nven-		
8	PRSMISSRSTEN	0 RW	PRS M	issing Even	t Will 7	Trigg	er a	Watch	idog	Res	et					
	When set, a PRS mis	n set, a PRS missing event will trigger a watchdog reset.														
7:4	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Cotions														
3:0	PRSSEL	0x0 RW	PRS C	hannel PRS	Select	t										
	These bits select the	PRS input for the PR	S channel.													
	Value	Mode	Descrip	otion												
	0	PRSCH0	PRS C	hannel 0 sele	ected a	ıs inpı	ut									
	1	PRSCH1	PRS C	hannel 1 sele	ected a	ıs inpı	ut									
	2	PRSCH2	PRS C	hannel 2 sele	ected a	ıs inpı	ut									
	3	PRSCH3	PRS C	hannel 3 sele	ected a	ıs inpı	ut									
	4	PRSCH4	PRS C	hannel 4 sele	ected a	ıs inpı	ut									
	5	PRSCH5	PRS C	hannel 5 sele	ected a	ıs inpı	ut									
	6	PRSCH6	PRS C	hannel 6 sele	ected a	ıs inpı	ut									
	7	PRSCH7	PRS C	hannel 7 sele	ected a	ıs inpı	ut									
	8	PRSCH8	PRS C	hannel 8 sele	ected a	ıs inpı	ut									
	9	PRSCH9	PRS C	hannel 9 sele	ected a	ıs inpı	ut									
	10	PRSCH10	PRS C	hannel 10 se	lected	as in	out									
	11	PRSCH11	PRS C	hannel 11 se	lected	as in	out									

14.5.5 WDOG_IF - Watchdog Interrupt Flags

Offset	Bit Position					
0x01C	30 30 30 30 30 30 30 30 30 30 30 30 30 3	4	က	2	_	0
Reset		0	0	0	0	0
Access		2	22	2	~	~
Name		PEM1	PEMO	NIW	WARN	TOUT

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	PEM1	0	R	PRS Channel One Event Missing Interrupt Flag
	Set when a WDOG c	lear happens be	fore a prs	event has been detected on PRS channel one.
3	PEM0	0	R	PRS Channel Zero Event Missing Interrupt Flag
	Set when a WDOG c	lear happens be	fore a prs	event has been detected on PRS channel zero.
2	WIN	0	R	WDOG Window Interrupt Flag
	Set when a WDOG c	lear happens be	low the wir	ndow limit value.
1	WARN	0	R	WDOG Warning Timeout Interrupt Flag
	Set when a WDOG w	varning timeout I	nas occurre	ed.
0	TOUT	0	R	WDOG Timeout Interrupt Flag
	Set when a WDOG ti	meout has occu	rred.	

14.5.6 WDOG_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Reset			'		'									•		'	•							•		•	'	0	0	0	0	0
Access																												W1	W	W1	W	W1
Name																												PEM1	PEM0	MIN	WARN	TOUT

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	PEM1	0	W1	Set PEM1 Interrupt Flag
	Write 1 to set the PEN	M1 interrupt flag		
3	PEM0	0	W1	Set PEM0 Interrupt Flag
	Write 1 to set the PEN	M0 interrupt flag		
2	WIN	0	W1	Set WIN Interrupt Flag
	Write 1 to set the WIN	N interrupt flag		
1	WARN	0	W1	Set WARN Interrupt Flag
	Write 1 to set the WA	RN interrupt flag	J	
0	TOUT	0	W1	Set TOUT Interrupt Flag
	Write 1 to set the TO	JT interrupt flag		

14.5.7 WDOG_IFC - Interrupt Flag Clear Register

14.5.7 V	VDO	۱۱_ز	·C -	ınte	rru	pt Fi	ag (Clea	ar Re	egis	ter																					
Offset															Bit	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset																												0	0	0	0	0
Access																												(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name																												PEM1	PEM0	N N	WARN	TOUT
Bit	Na	me					Re	set			Ac	cess	s [Des	cript	tion																
31:5	Re	serv	⁄ed				To tion		ure (com	pati	ibility	v wit	th fu	ture	dev	ices	s, alv	vay	s wi	ite k	oits t	o 0.	Мо	re in	forn	natio	on in	1.2	Co	nvei	7-
4	PE	M1					0				(R)	W1	(Clea	ar PE	EM1	Int	erru	pt F	Flag												
												eadii MSC		etur	ns th	ne va	alue	of t	the	IF a	nd c	lear	s th	e co	rres	pon	ding	inte	errup	ot fla	igs	
3	PE	M0					0				(R)	W1	(Clea	ar PE	EM0	Int	erru	pt F	Flag												
												eadii MSC		etur	ns th	ne va	alue	of t	the	IF a	nd c	lear	s th	e co	rres	pon	ding	inte	errup	ot fla	igs	
2	WI	N					0				(R)	W1	(Clea	ar W	IN Ir	nter	rupt	t Fla	ag												

Write 1 to clear the WARN interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).

Write 1 to clear the WIN interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This

0 TOUT 0 (R)W1 Clear TOUT Interrupt Flag

Write 1 to clear the TOUT interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).


14.5.8 WDOG_IEN - Interrupt Enable Register

Offset															Ві	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Reset							•				•		•	•	•		•			•			•					0	0	0	0	0
Access																												₩ M	₩ M	₩ M	₩ M	RW
Name																												PEM1	PEMO	NN	WARN	TOUT

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	PEM1	0	RW	PEM1 Interrupt Enable
	Enable/disable the	PEM1 interrupt		
3	PEM0	0	RW	PEM0 Interrupt Enable
	Enable/disable the	PEM0 interrupt		
2	WIN	0	RW	WIN Interrupt Enable
	Enable/disable the	WIN interrupt		
1	WARN	0	RW	WARN Interrupt Enable
	Enable/disable the	e WARN interrupt		
0	TOUT	0	RW	TOUT Interrupt Enable
	Enable/disable the	TOUT interrupt		

15. PRS - Peripheral Reflex System





Quick Facts

What?

The Peripheral Reflex System (PRS) allows configurable, fast, and autonomous communication between peripherals.

Why?

Events and signals from one peripheral can be used as input signals or triggered by other peripherals. Besides, PRS reduces latency and ensures predictable timing by reducing software overhead and thus current consumption.

How?

Without CPU intervention the peripherals can send Reflex signals (both pulses and level) to each other in single or chained steps. The peripherals can be set up to perform actions based on the incoming Reflex signals. This results in improved system performance and reduced energy consumption.

15.1 Introduction

The Peripheral Reflex System (PRS) is a network allowing direct communication between different peripheral modules without involving the CPU. Peripheral modules which send out Reflex signals are called producers. The PRS routes these Reflex signals through Reflex channels to consumer peripherals which perform actions depending on the Reflex signals received. The format for the Reflex signals is not given, but edge triggers and other functionality can be applied by the PRS.

15.2 Features

- · 12 Configurable Reflex Channels
 - Each channel can be connected to any producing peripheral, including the PRS channels
 - · Consumers can choose which channel to listen to
 - Selectable edge detector (Rising, falling and both edges)
 - · Configurable AND and OR between channels
 - · Optional channel invert
 - · PRS can generate event to CPU
 - · Two independent DMA requests based on PRS channels
- · Software controlled channel output
 - · Configurable level
 - · Triggered pulses

15.3 Functional Description

An overview of the PRS module is shown in Figure 15.1 PRS Overview on page 420. The PRS contains 12 Reflex channels. All channels can select any Reflex signal offered by the producers. The consumers can choose which PRS channel to listen to and perform actions based on the Reflex signals routed through that channel. The Reflex signals can be both edge signals and level signals.




Figure 15.1. PRS Overview

15.3.1 Channel Functions

Different functions can be applied to a Reflex signal within the PRS. Each channel includes an edge detector to enable generation of pulse signals from level signals. The PRS channels can also be manually triggered by writing to PRS_SWPULSE or PRS_SWLEVEL. SWLEVEL[n] is a programmable level for each channel and holds the value it is programmed to. Setting SWPULSE[n] will cause the PRS channel to output a high pulse that is one HFCLK cycle wide. The SWLEVEL[n] and SWPULSE[n] signals are then XOR'ed with the selected input from the producers to form the output signal sent to the consumers listening to the channel. For example, when SWLEVEL[n] is set, if a producer produces a signal of 1, this will cause a channel output of 0.

15.3.1.1 Operational Mode

Reflex channels can operate in two modes, synchronous or asynchronous. In synchronous mode Reflex signals are clocked on the HFCLK, and can be used by any Reflex consumer. However, this will not work in EM2/EM3, since the HFCLK will be turned off.

Asynchronous Reflex channels are not clocked on HFCLK, and can be used even in EM2/EM3. However, the asynchronous mode can only be used by a subset of the Reflex consumers.

The asynchronous Reflex signals generated by the producers are indicated in the SIGSEL field of PRS_CHx_CTRL register. The consumers capable of utilizing asynchronous Reflex signals include the LEUART and the PCNT. The USART can also utilize some particular asynchronous signals. Refer to the respective modules for details on how to configure them to use the PRS.

Note: If a Reflex channel with ASYNC field of PRS_CHx_CTRL register set to '1' is used in a consumer not supporting asynchronous reflexes, the behaviour is undefined

15.3.1.2 Edge Detection and Clock Domains

Using EDSEL in PRS_CHx_CTRL, edge detection can be applied to a PRS signal. When edge detection is enabled, changes in the PRS input will result in a pulse on the PRS channel. This requires that the ASYNC bit in PRS_CHx_CTRL is cleared. Signals on the PRS input must be at least one HFCLK period wide in order to be detected properly. This applies to all cases when ASYNC is not used in the PRS.

For communication between peripherals on different prescaled clocks (e.g. between peripherals on HFCLK and HFPERCLK), there are two options. One option is to use level signals. No additional action is needed for level signals, but software must make sure that the level signals are held long enough for the destination domain to detect them. The other option is to use pulse signals. For pulse signals, edge detection should be enabled (by configuring EDSEL in PRS_CHx_CTRL to positive edge, negative edge, or both) and STRETCH in PRS_CHx_CTRL should be set. When edge detection and stretch are enabled on a PRS source, the output on the PRS channel is held long enough for the destination domain to detect the pulse. This also works if there are multiple destination domains running at different frequencies.

15.3.1.3 Configurable PRS Logic

Each PRS channel has three logic functions that can be used by themselves or in combination. The selected PRS source can be AND'ed with the next PRS channel output, OR'ed with the previous PRS channel output and inverted. This is shown in Figure 15.1 PRS Overview on page 420. The order of the functions is important. If OR and AND are enabled at the same time, AND is applied first, and then OR. Note that the previous and next channel options wrap around. Using the ORPREV option on the first PRS channel OR's with the output of the last PRS channel. Likewise, using the ANDNEXT option on the last PRS channel AND's with the output of the first PRS channel.




Figure 15.2. Configurable PRS Logic

In addition to the logic functions that can combine a PRS channel with one of its neighbors, a PRS channel can also select any other PRS channel as input. This can allow relatively complex logic functions to be created.

15.3.2 Producers

Through SOURCESEL in PRS_CHx_CTRL, each PRS channel selects signal producers. Each producer outputs one or more signals which can be selected by setting the SIGSEL field in PRS_CHx_CTRL. Setting the SOURCESEL bits to 0 (Off) leads to a constant 0 output from the input mux. An overview of the available producers can be found in the SOURCESEL and SIGSEL fields in PRS_CHx_CTRL. Note that GPIO producers are selected in the GPIO module using the edge interrupt configuration settings described in 31.3.5.1 Edge Interrupt Generation. GPIOPIN0 uses the selection for the EXTI0 interrupt, GPIOPIN1 uses the selection for the EXTI1 interrupt, and so on.

15.3.3 Consumers

Consumer peripherals (Listed in Table 15.1 Reflex Consumers on page 422) can be set to listen to a PRS channel and perform an action based on the signal received on that channel. While most consumers can handle either only pulse input or only level input, some can handle both pulse and level inputs.

Table 15.1. Reflex Consumers

Module	Reflex Input	Input Format
TIMER	Compare/Capture Channel	Pulse / Level
	Alternate Input for DTI (Available only in specific TIMERs See data sheet for details)	Level
	Alternate Input for DTI Fault 0 (Available only in specific TIMERs See data sheet for details)	Level
	Alternate Input for DTI Fault 1 (Available only in specific TIMERs See data sheet for details)	Level
WTIMER	Compare/Capture Channel	Pulse / Level
	Alternate Input for DTI (Available only in specific WTIMERs See data sheet for details)	Level
	Alternate Input for DTI Fault 0 (Available only in specific WTIMERs See data sheet for details)	Level
	Alternate Input for DTI Fault 1 (Available only in specific WTIMERs See data sheet for details)	Level
USART	RX/TX Trigger	Pulse
	Alternate Input for IrDA	Level
	Alternate Input for RX	Level
	Alternate Input for CLK	Level
VDAC	Channel 0 Trigger	Pulse
	Channel 1 Trigger	Pulse
ADC	Single Sample Trigger	Pulse
	Scan Sequence Trigger	Pulse
IDAC	Alternate Input for OUTMODE	Level
СМИ	Alternate Input for Calibration Up-Counter	Level
	Alternate Input for Calibration Down-Counter	Level
LEUART	Alternate Input for RX	Level
PCNT	Compare/Clear Trigger	Pulse/Level
	Alternate Input for S0IN	Level
	Alternate Input for S1IN	Level

Module	Reflex Input	Input Format
LESENSE	Scan Start	Pulse
	LESENSE Decoder Bit 0	Level
	LESENSE Decoder Bit 1	Level
	LESENSE Decoder Bit 2	Level
	LESENSE Decoder Bit 3	Level
WDOG	Peripheral Watchdog	Pulse
LETIMER	Start LETIMER	Pulse
	Stop LETIMER	Pulse
	Clear LETIMER	Pulse
RTCC	Compare/Capture Channel	Pulse/Level
PRS	Set Event	Pulse
	DMA Request 0	Pulse
	DMA Request 1	Pulse

15.3.4 Event on PRS

The PRS can be used to send events to the MCU. This is very useful in combination with the Wait For Event (WFE) instruction. A single PRS channel can be selected for this using SEVONPRSSEL in PRS_CTRL, and the feature is enabled by setting SEVONPRS in the same register.

Using SEVONPRS, one can e.g. set up a timer to trigger an event to the MCU periodically, every time letting the MCU pass through a WFE instruction in its program. This can help in performance-critical sections where timing is known, and the goal is to wait for an event, then execute some code, then wait for an event, then execute some code and so on.

15.3.5 DMA Request on PRS

Up to two independent DMA requests can be generated by the PRS. The PRS signals triggering the DMA requests are selected using the LDMA_CHx_REQSEL register, by setting SOURCESEL to PRS and SIGSEL to either PRSREQ0 or PRSREQ1. The DMA requests are cleared when the DMA services the requests. The requests are set whenever the selected PRS signals are high.

The selected PRS signals must have ASYNC cleared when they are used as inputs to the DMA. Edge detection in the PRS can be enabled to only trigger transfers on edges.

15.3.6 Example

The example below (illustrated in Figure 15.3 TIMER0 Overflow Starting ADC0 Single Conversions Through PRS Channel 5. on page 424) shows how to set up ADC0 to start single conversions every time TIMER0 overflows (one HFPERCLK cycle high pulse), using PRS channel 5:

- · Set SOURCESEL in PRS CH5 CTRL to TIMER0 as input to PRS channel 5.
- Set SIGSEL in PRS CH5 CTRL to select the overflow signal (TIMER00F from TIMER0).
- · Configure ADC0 with the desired conversion set-up.
- Set SINGLEPRSEN in ADC0_SINGLECTRL to 1 to enable single conversions to be started by a high PRS input signal.
- Set SINGLEPRSSEL in ADC0_SINGLECTRL to 0x5 to select PRS channel 5 as input to start the single conversion.
- Start TIMER0 with the desired TOP value, an overflow PRS signal is output automatically on overflow. Note that the ADC results needs to be fetched either by the CPU or DMA.




Figure 15.3. TIMER0 Overflow Starting ADC0 Single Conversions Through PRS Channel 5.

15.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	PRS_SWPULSE	W1	Software Pulse Register
0x004	PRS_SWLEVEL	RW	Software Level Register
0x008	PRS_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x010	PRS_ROUTELOC0	RW	I/O Routing Location Register
0x014	PRS_ROUTELOC1	RW	I/O Routing Location Register
0x018	PRS_ROUTELOC2	RW	I/O Routing Location Register
0x030	PRS_CTRL	RW	Control Register
0x034	PRS_DMAREQ0	RW	DMA Request 0 Register
0x038	PRS_DMAREQ1	RW	DMA Request 1 Register
0x040	PRS_PEEK	R	PRS Channel Values
0x050	PRS_CH0_CTRL	RW	Channel Control Register
	PRS_CHx_CTRL	RW	Channel Control Register
0x07C	PRS_CH11_CTRL	RW	Channel Control Register

15.5 Register Description

15.5.1 PRS_SWPULSE - Software Pulse Register

Offset															Bi	t Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset		•	'		'			•			•		•	'		'			•		0	0	0	0	0	0	0	0	0	0	0	0
Access																					W	×	W M	N M	×	×	N M	W	×	W K	×	W
Name																					CH11PULSE	CH10PULSE	CH9PULSE	CH8PULSE	CH7PULSE	CH6PULSE	CH5PULSE	CH4PULSE	CH3PULSE	CH2PULSE	CH1PULSE	CH0PULSE

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	CH11PULSE	0	W1	Channel 11 Pulse Generation
	See bit 0.			
10	CH10PULSE	0	W1	Channel 10 Pulse Generation
	See bit 0.			
9	CH9PULSE	0	W1	Channel 9 Pulse Generation
	See bit 0.			
8	CH8PULSE	0	W1	Channel 8 Pulse Generation
	See bit 0.			
7	CH7PULSE	0	W1	Channel 7 Pulse Generation
	See bit 0.			
6	CH6PULSE	0	W1	Channel 6 Pulse Generation
	See bit 0.			
5	CH5PULSE	0	W1	Channel 5 Pulse Generation
	See bit 0.			
4	CH4PULSE	0	W1	Channel 4 Pulse Generation
	See bit 0.			
3	CH3PULSE	0	W1	Channel 3 Pulse Generation
	See bit 0.			
2	CH2PULSE	0	W1	Channel 2 Pulse Generation
	See bit 0.			
1	CH1PULSE	0	W1	Channel 1 Pulse Generation
	See bit 0.			
0	CH0PULSE	0	W1	Channel 0 Pulse Generation
				lse. This pulse is XOR'ed with the corresponding bit in the SWLEVEL regise the channel output.

15.5.2 PRS_SWLEVEL - Software Level Register

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	æ	7	9	2	4	က	2	_	0
Reset			'		'													'			0	0	0	0	0	0	0	0	0	0	0	0
Access																					₽	₩ M	RW	₩	Z.	W.	R M	₩ M	₩ M	RW	RW	₩ W
Name																					CH11LEVEL	CH10LEVEL	CH9LEVEL	CH8LEVEL	CH7LEVEL	CH6LEVEL	CH5LEVEL	CH4LEVEL	CH3LEVEL	CH2LEVEL	CH1LEVEL	CHOLEVEL

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	CH11LEVEL	0	RW	Channel 11 Software Level
	See bit 0.			
10	CH10LEVEL	0	RW	Channel 10 Software Level
	See bit 0.			
9	CH9LEVEL	0	RW	Channel 9 Software Level
	See bit 0.			
8	CH8LEVEL	0	RW	Channel 8 Software Level
	See bit 0.			
7	CH7LEVEL	0	RW	Channel 7 Software Level
	See bit 0.			
6	CH6LEVEL	0	RW	Channel 6 Software Level
	See bit 0.			
5	CH5LEVEL	0	RW	Channel 5 Software Level
	See bit 0.			
4	CH4LEVEL	0	RW	Channel 4 Software Level
	See bit 0.			
3	CH3LEVEL	0	RW	Channel 3 Software Level
	See bit 0.			
2	CH2LEVEL	0	RW	Channel 2 Software Level
	See bit 0.			
1	CH1LEVEL	0	RW	Channel 1 Software Level
	See bit 0.			
0	CH0LEVEL	0	RW	Channel 0 Software Level
Ü		egister is XOR'e		responding bit in the SWPULSE register and the selected PRS inpu

15.5.3 PRS_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	1	10	စ	∞	7	9	5	4	က	2	_	0
Reset			•				•		•											•	0	0	0	0	0	0	0	0	0	0	0	0
Access																					RW	₽	RW	₽	₽	RW	₽	₽	₽	RW	₽	R W
Name																					CH11PEN	CH10PEN	CH9PEN	CH8PEN	CH7PEN	CH6PEN	CH5PEN	CH4PEN	CH3PEN	CH2PEN	CH1PEN	CHOPEN

Name	Reset	Access	Description
Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
CH11PEN	0	RW	CH11 Pin Enable
When set, GPIO outp	out from PRS cha	annel 11 is	enabled
CH10PEN	0	RW	CH10 Pin Enable
When set, GPIO outp	out from PRS cha	annel 10 is	enabled
CH9PEN	0	RW	CH9 Pin Enable
When set, GPIO outp	out from PRS cha	annel 9 is e	enabled
CH8PEN	0	RW	CH8 Pin Enable
When set, GPIO outp	out from PRS cha	annel 8 is e	enabled
CH7PEN	0	RW	CH7 Pin Enable
When set, GPIO outp	out from PRS cha	annel 7 is e	enabled
CH6PEN	0	RW	CH6 Pin Enable
When set, GPIO outp	out from PRS cha	annel 6 is e	enabled
CH5PEN	0	RW	CH5 Pin Enable
When set, GPIO outp	out from PRS cha	annel 5 is e	enabled
CH4PEN	0	RW	CH4 Pin Enable
When set, GPIO outp	out from PRS cha	annel 4 is e	enabled
CH3PEN	0	RW	CH3 Pin Enable
When set, GPIO outp	out from PRS cha	annel 3 is e	enabled
CH2PEN	0	RW	CH2 Pin Enable
When set, GPIO outp	out from PRS cha	annel 2 is e	enabled
CH1PEN	0	RW	CH1 Pin Enable
When set, GPIO out	out from PRS cha	annel 1 is e	enabled
CH0PEN	0	RW	CH0 Pin Enable
When set, GPIO outp	out from PRS cha	annel 0 is e	enabled
	CH11PEN When set, GPIO outp CH10PEN When set, GPIO outp CH9PEN When set, GPIO outp CH8PEN When set, GPIO outp CH7PEN When set, GPIO outp CH6PEN When set, GPIO outp CH5PEN When set, GPIO outp CH4PEN When set, GPIO outp CH3PEN When set, GPIO outp CH3PEN When set, GPIO outp CH2PEN When set, GPIO outp CH1PEN When set, GPIO outp CH1PEN When set, GPIO outp	Reserved To ensure contions CH11PEN When set, GPIO output from PRS characters of the contions CH10PEN When set, GPIO output from PRS characters of the	Reserved To ensure compatibility tions CH11PEN 0 RW When set, GPIO output from PRS channel 11 is CH10PEN 0 RW When set, GPIO output from PRS channel 10 is CH9PEN 0 RW When set, GPIO output from PRS channel 9 is CH8PEN 0 RW When set, GPIO output from PRS channel 8 is CH7PEN 0 RW When set, GPIO output from PRS channel 7 is CH6PEN 0 RW When set, GPIO output from PRS channel 6 is CH5PEN 0 RW When set, GPIO output from PRS channel 5 is CH4PEN 0 RW When set, GPIO output from PRS channel 5 is CH4PEN 0 RW When set, GPIO output from PRS channel 3 is CH4PEN 0 RW When set, GPIO output from PRS channel 3 is CH4PEN 0 RW When set, GPIO output from PRS channel 3 is CH4PEN 0 RW When set, GPIO output from PRS channel 2 is CH4PEN 0 RW When set, GPIO output from PRS channel 2 is CH4PEN 0 RW When set, GPIO output from PRS channel 1 is CH4PEN

15.5.4 PRS_ROUTELOC0 - I/O Routing Location Register

15.5.4 P	NO_RU	J 1 E		- 1/		.ou	ung	, _0	cati	OII I	veg	ıəl	CI.																		_
Offset															it Po		on														
0x010	33	29	7 58		76	22	24	23	22	2	20	6.		17	16	15	4	13	12		2 ₀	ω ω		_	9	2	4	က	7	- c)
Reset				0x00									00x0							0x00								0	OOXO		
Access				\mathbb{R}									Α							₽								Š	<u>}</u>		
				20									၁င							20								(3		_
Name				СНЗГОС									CH2LOC							CH1LOC								2	200		
Bit	Name					Res	set			Ac	ces	s	De	scrip	otior	1															
31:30	Reserv	/ed				To tion		ure	con	npat	ibilit	yи	∕ith f	uture	e de	/ices	s, al	ways	write	bit	s to	0. Mc	ore	inf	orm	atio	n in	1.2	? Co	nven-	
29:24	CH3L0	C				0x0	00			RV	٧		I/O	Loc	atio	n															_
	Decide	s th	e loca	tion	of	the	cha	anne	el I/C) pir	1																				
	Value					Мо	de						Des	scrip	tion																
	0					LO	C0						Loc	atio	n 0																
	1					LO	C1						Loc	atio	n 1																
	2					LO	C2						Loc	atio	n 2																
	3					LO							Loc	atio	n 3																
	4					LO								atio																	
	5					LO								atio																	
	6					LO								atio																	
	7					LO								atio																	
	8					LO								atio																	
	9					LO								atio																	
	10						C10 C11								n 10 n 11																
	12						C12								n 12																
	13						C13								n 13																
	14						C14								n 14																
23:22	Reserv	/ed				To tion		ure	con	npat	ibilit	уи	∕ith f	uture	e de	/ices	s, al	ways	write	bit	s to	0. Mc	ore	e inf	orm	natio	n in	1.2	? Co	nven-	
21:16	CH2L0	C				0x0	00			RV	٧		I/O	Loc	atio	n															
	Decide	es the	e loca	tion	of	the	cha	anne	el I/C) pir	1																				
	Value		_			Мо	de						Des	scrip	tion																
	0					LO	C0						Loc	atio	n 0																
	1					LO	C1						Loc	atio	n 1																
	2					LO	C2						Loc	atio	n 2																

Bit	Name	Reset Access	Description							
	3	LOC3	Location 3							
	4	LOC4	Location 4							
	5	LOC5	Location 5							
	6	LOC6	Location 6							
	7	LOC7	Location 7							
15:14	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-							
13:8	CH1LOC	0x00 RW	I/O Location							
	Decides the location	of the channel I/O pin								
	Value	Mode	Description							
	0	LOC0	Location 0							
	1	LOC1	Location 1							
	2	LOC2	Location 2							
	3	LOC3	Location 3							
	4	LOC4	Location 4							
	5	LOC5	Location 5							
	6	LOC6	Location 6							
	7	LOC7	Location 7							
7:6	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-							
5:0	CH0LOC	0x00 RW	I/O Location							
	Decides the location	of the channel I/O pin								
	Value	Mode	Description							
	0	LOC0	Location 0							
	1	LOC1	Location 1							
	2	LOC2	Location 2							
	3	LOC3	Location 3							
	3 4	LOC3 LOC4	Location 3 Location 4							
	4	LOC4	Location 4							
	5	LOC4 LOC5	Location 4 Location 5							
	456	LOC4 LOC5 LOC6	Location 4 Location 5 Location 6							
	4 5 6 7	LOC4 LOC5 LOC6 LOC7	Location 4 Location 5 Location 6 Location 7							
	4 5 6 7 8	LOC4 LOC5 LOC6 LOC7 LOC8	Location 4 Location 5 Location 6 Location 7 Location 8							
	4 5 6 7 8 9	LOC4 LOC5 LOC6 LOC7 LOC8 LOC9	Location 4 Location 5 Location 6 Location 7 Location 8 Location 9							
	4 5 6 7 8 9 10	LOC4 LOC5 LOC6 LOC7 LOC8 LOC9	Location 4 Location 5 Location 6 Location 7 Location 8 Location 9 Location 10							
	4 5 6 7 8 9 10	LOC4 LOC5 LOC6 LOC7 LOC8 LOC9 LOC10	Location 4 Location 5 Location 6 Location 7 Location 8 Location 9 Location 10 Location 11							

Bit Name Reset Access Description

15.5.5 PRS_ROUTELOC1 - I/O Routing Location Register

	_	Bit Position																													
Orfset		<u> </u>	~		()	10		~	٥,				\ _~	1	T			m -													
0x014	30	59	78	27	26	25	2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2				19						0000 10 10 10 10 10 10 10 10 10 10 10 10					1 0	<u> </u>	9	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0					0	
Reset				OXO								0x00																			
Access				8	À Y								Σ																		
Name							СН6СОС									CH4LOC															
				CH.	5								CH6					CH5							CH4						
Bit	Name Reset Access									Des	Description																				
31:30	Reserved To ensure compatibility we tions						ith f	th future devices, always write bits to 0. More information in 1.2 Conven-													7-										
29:24	CH7LC	C				0x0	00			RV	V		I/O	I/O Location																	
	Decide	es th	e loc	atio	n of	the	cha	nne	l I/C) pir	1																				_
	Value					Mode								Description																	
	0					LOC0								Location 0																	
	1					LOC1								Location 1																	
	2					LOC2								Location 2																	
	3					LOC3								Location 3 Location 4																	
	5						LOC5							Location 5																	
	6					LOC6								Location 6																	
	7					LOC7								Location 7																	
	8 LOC8									Location 8																					
	9 LOC9						Loc	Location 9																							
	10					LO	C10						Loc	atio	n 10																
23:22	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions					7-																									
21:16	6 CH6LOC 0x00							RV	٧		I/O	I/O Location																			
	Decide	Decides the location of the channel I/O pin																													
	Value				Mode							Description																			
	0				LOC0						Location 0																				
	1 LOC1						Location 1																								
	2					LO	C2						Location 2																		
	3					LO	СЗ						Location 3																		
	4					LO	C4						Loc	atio	n 4																
	5					LO	C5						Location 5																		
	6						LOC6							atio	n 6																

Bit	Name	Reset Access	Description								
	7	LOC7	Location 7								
	8	LOC8	Location 8								
	9	LOC9	Location 9								
	10	LOC10	Location 10								
	11	LOC11	Location 11								
	12	LOC12	Location 12								
	13	LOC13	Location 13								
	14	LOC14	Location 14								
	15	LOC15	Location 15								
	16	LOC16	Location 16								
	17	LOC17	Location 17								
15:14	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-								
13:8	CH5LOC	0x00 RW	I/O Location								
	Decides the location of the channel I/O pin										
	Value	Mode	Description								
	0	LOC0	Location 0								
	1	LOC1	Location 1								
	2	LOC2	Location 2								
	3	LOC3	Location 3								
	4	LOC4	Location 4								
	5	LOC5	Location 5								
	6	LOC6	Location 6								
7:6	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-								
5:0	CH4LOC	0x00 RW	I/O Location								
	Decides the location of the channel I/O pin										
	Value	Mode	Description								
	0	LOC0	Location 0								
	1	LOC1	Location 1								
	2	LOC2	Location 2								
	3	LOC3	Location 3								
	4	LOC4	Location 4								
	5	LOC5	Location 5								
	6	LOC6	Location 6								

15.5.6 PRS_ROUTELOC2 - I/O Routing Location Register

Offset									В	it Po	sition														
0x018	30	29	27 26	25	23	22	21	19	18 7	16	15	13	12	7	10	6	∞	~	ַנ	ç	4	က	2	~ c	>
Reset			0×00					00X0						ć	00X0							Š	nxn		
Access			RW					Z K							 ≩								 ≩ Ƴ		_
																									_
Name			CH11LOC					CH10LOC						3	CHaroc							2	CH&LOC		
			<u> </u>					<u>ن</u>	i						ن							(5		_
Bit	Name			Reset		,	Acces	s D	escri _l	ption															
31:30	Reserv	⁄ed		To ens	ure c	omp	patibilit	y with	h futur	e dev	rices, a	lwa	ys w	rite l	bits to	o 0. I	Mor	e info	rma	atio	n in	1.2	? Co	nven-	
29:24	CH11L	.OC		0x00			RW	I/	O Loc	ation	1														_
	Decide	s the lo	cation o	of the cha	annel	I/O	pin																		
	Value			Mode				D	escrip	tion															
	0			LOC0				L	ocatio	n 0															
	1			LOC1				L	ocatio	n 1															
	2			LOC2				L	ocatio	n 2															
	3			LOC3				L	ocatio	n 3															
	4			LOC4				L	ocatio	n 4															
	5			LOC5				L	ocatio	n 5															
23:22	Reserv	/ed		To ens	ure c	отр	patibilit	y with	h futur	e dev	rices, a	lwa	ys w	rite l	bits to	o 0. I	Mor	e info	rma	atio	n in	1.2	? Co	nven-	
21:16	CH10L	.OC		0x00			RW	I/	O Loc	ation	1														
	Decide	s the lo	cation o	of the cha	annel	I/O	pin																		
	Value			Mode				D	escrip	tion															
	0			LOC0				L	ocatio	n 0															
	1			LOC1				L	ocatio	n 1															
	2			LOC2				L	ocatio	n 2															
	3			LOC3				L	ocatio	n 3															
	4			LOC4				L	ocatio	n 4															
	5			LOC5				L	ocatio	n 5															
15:14	Reserv	/ed		To ens	sure c	отр	patibilit	y with	h futur	e dev	rices, a	lwa	ys w	rite l	bits to	o 0. I	Mor	e info	rma	atio	n in	1.2	? Co	nven-	

0x00

Mode

LOC0

Decides the location of the channel I/O pin

RW

I/O Location

Description

Location 0

CH9LOC

Value

0

13:8

Bit	Name	Reset Access	Description
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
7:6	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
7:6 5:0	Reserved CH8LOC		with future devices, always write bits to 0. More information in 1.2 Conven- I/O Location
	CH8LOC	tions	
	CH8LOC	0x00 RW	
	CH8LOC Decides the location	0x00 RW of the channel I/O pin	I/O Location
	CH8LOC Decides the location	0x00 RW of the channel I/O pin Mode	I/O Location Description
	CH8LOC Decides the location of Value 0	0x00 RW of the channel I/O pin Mode LOC0	I/O Location Description Location 0
	CH8LOC Decides the location of Value 0 1	of the channel I/O pin Mode LOC0 LOC1	I/O Location Description Location 0 Location 1
	CH8LOC Decides the location of Value 0 1	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2	I/O Location Description Location 0 Location 1 Location 2
	CH8LOC Decides the location of Value 0 1 2 3	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3	I/O Location Description Location 0 Location 1 Location 2 Location 3
	CH8LOC Decides the location of Value 0 1 2 3 4	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3 LOC4	I/O Location Description Location 0 Location 1 Location 2 Location 3 Location 4
	CH8LOC Decides the location of Value 0 1 2 3 4 5	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3 LOC4 LOC5	I/O Location Description Location 0 Location 1 Location 2 Location 3 Location 4 Location 5
	CH8LOC Decides the location of Value 0 1 2 3 4 5	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3 LOC4 LOC5 LOC6	I/O Location Description Location 0 Location 1 Location 2 Location 3 Location 4 Location 5 Location 6
	CH8LOC Decides the location of Value 0 1 2 3 4 5 6 7	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3 LOC4 LOC5 LOC6 LOC7	I/O Location Description Location 0 Location 1 Location 2 Location 3 Location 4 Location 5 Location 6 Location 7
	CH8LOC Decides the location of Value 0 1 2 3 4 5 6 7	tions 0x00 RW of the channel I/O pin Mode LOC0 LOC1 LOC2 LOC3 LOC4 LOC5 LOC6 LOC7 LOC8	I/O Location Description Location 0 Location 1 Location 2 Location 3 Location 4 Location 5 Location 6 Location 7 Location 8

15.5.7 PRS_CTRL - Control Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset															•	•	•	•	•			•	•			•			ć	2	•	0
Access																													Š	≥ Y		R W
Name																														SEVONTROSEL		SEVONPRS
Bit	Na	me					Re	set			Ac	cess	s I	Des	crip	tion																

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4:1	SEVONPRSSEL	0x0	RW	SEVONPRS PRS Channel Select
	Selects PRS channe	I for SEVONPRS	3	
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected
	1	PRSCH1		PRS Channel 1 selected
	2	PRSCH2		PRS Channel 2 selected
	3	PRSCH3		PRS Channel 3 selected
	4	PRSCH4		PRS Channel 4 selected
	5	PRSCH5		PRS Channel 5 selected
	6	PRSCH6		PRS Channel 6 selected
	7	PRSCH7		PRS Channel 7 selected
	8	PRSCH8		PRS Channel 8 selected
	9	PRSCH9		PRS Channel 9 selected
	10	PRSCH10		PRS Channel 10 selected
	11	PRSCH11		PRS Channel 11 selected
0	SEVONPRS	0	RW	Set Event on PRS
	When set, an event i	s generated to th	ne CPU wh	en the PRS channel selected by SEVONPRSSEL is high

15.5.8 PRS_DMAREQ0 - DMA Request 0 Register

13.3.0 F	NO_DIVIANEQU - DIVIA	Request o Register	
Offset			Bit Position
0x034	30 30 29 28 27 27	22 23 23 20 20 20	0 1 2 3 4 5 9 6 8 7 9 9 7 7 7 7 7 8 8 8 7 9 9 7 7 9 9 8 8 7 9 9 9 7 9 9 9 9
Reset			000
Access			. Sa
Name			PRSSEL
Bit	Name	Reset Access	Description
31:10	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
9:6	PRSSEL	0x0 RW	DMA Request 0 PRS Channel Select
	Selects PRS channel	for DMA request 0 from t	he PRS (PRSREQ0).
	Value	Mode	Description
	0	PRSCH0	PRS Channel 0 selected
	1	PRSCH1	PRS Channel 1 selected
	2	PRSCH2	PRS Channel 2 selected
	3	PRSCH3	PRS Channel 3 selected
	4	PRSCH4	PRS Channel 4 selected
	5	PRSCH5	PRS Channel 5 selected
	6	PRSCH6	PRS Channel 6 selected
	7	PRSCH7	PRS Channel 7 selected
	8	PRSCH8	PRS Channel 8 selected
	9	PRSCH9	PRS Channel 9 selected
	10	PRSCH10	PRS Channel 10 selected
	11	PRSCH11	PRS Channel 11 selected
		_	

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

5:0

Reserved

tions

15.5.9 PRS_DMAREQ1 - DMA Request 1 Register

13.3.9 F	NO_DIMANEQT - DIM	A Request 1 Register	
Offset			Bit Position
0x038	31 30 29 28 27	22 23 24 20 20 20 20 20 20 20 20 20 20 20 20 20	2 6 8 7 9 5 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7
Reset			000
Access			MA MARKET
Name			PRSSEL
			ä.
Bit	Name	Reset Acces	ss Description
31:10	Reserved	To ensure compatibilitions	ity with future devices, always write bits to 0. More information in 1.2 Conven-
9:6	PRSSEL	0x0 RW	DMA Request 1 PRS Channel Select
	Selects PRS chann	el for DMA request 1 from	the PRS (PRSREQ1).
	Value	Mode	Description
	0	PRSCH0	PRS Channel 0 selected
	1	PRSCH1	PRS Channel 1 selected
	2	PRSCH2	PRS Channel 2 selected
	3	PRSCH3	PRS Channel 3 selected
	4	PRSCH4	PRS Channel 4 selected
	5	PRSCH5	PRS Channel 5 selected
	6	PRSCH6	PRS Channel 6 selected
	7	PRSCH7	PRS Channel 7 selected
	8	PRSCH8	PRS Channel 8 selected
	9	PRSCH9	PRS Channel 9 selected
	10	PRSCH10	PRS Channel 10 selected
	11	PRSCH11	PRS Channel 11 selected
5:0	Reserved	To ensure compatibility	ity with future devices, always write bits to 0. More information in 1.2 Conven-

tions

15.5.10 PRS_PEEK - PRS Channel Values

Offset															Ві	it Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•		•				•						•	•				•	0	0	0	0	0	0	0	0	0	0	0	0
Access																					<u>~</u>	œ	Ж	22	œ	22	œ	22	œ	2	œ	<u>~</u>
Name																					CH11VAL	CH10VAL	CH9VAL	CH8VAL	CH7VAL	CH6VAL	CH5VAL	CH4VAL	CH3VAL	CH2VAL	CH1VAL	CH0VAL

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	CH11VAL	0	R	Channel 11 Current Value
	See bit 0.			
10	CH10VAL	0	R	Channel 10 Current Value
	See bit 0.			
9	CH9VAL	0	R	Channel 9 Current Value
	See bit 0.			
8	CH8VAL	0	R	Channel 8 Current Value
	See bit 0.			
7	CH7VAL	0	R	Channel 7 Current Value
	See bit 0.			
6	CH6VAL	0	R	Channel 6 Current Value
	See bit 0.			
5	CH5VAL	0	R	Channel 5 Current Value
	See bit 0.			
4	CH4VAL	0	R	Channel 4 Current Value
	See bit 0.			
3	CH3VAL	0	R	Channel 3 Current Value
	See bit 0.			
2	CH2VAL	0	R	Channel 2 Current Value
	See bit 0.			
1	CH1VAL	0	R	Channel 1 Current Value
	See bit 0.			
0	CH0VAL	0	R	Channel 0 Current Value
				lue of channel 0. Any enabled edge detection will not be visible. This value C = 1, no value is returned

15.5.11 PRS_CHx_CTRL - Channel Control Register

Offset															Bi	t Po	sitio	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	1	0
Reset		0		0	0	0	0				2	SX.		•		•					00×0					•			•		0×0	
Access		RW		RW	₩ M	RW	Z.				2	2									% M										Z.	
Name		ASYNC		ANDNEXT	ORPREV	INV	STRETCH				1000	EDSEL									SOURCESEL										SIGSEL	
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																

	AS AN OF	≦ S		SS SIG
Bit	Name	Reset	Access	Description
31	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
30	ASYNC	0	RW	Asynchronous Reflex
	Set to enable async	chronous mode of	of this reflex	c signal
29	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
28	ANDNEXT	0	RW	And Next
	If set, channel outp	ut is AND'ed with	n the next ch	hannel output
27	ORPREV	0	RW	Or Previous
	If set, channel outp	ut is OR'ed with	the previous	s channel output
26	INV	0	RW	Invert Channel
	If set, channel outp	ut is inverted		
25	STRETCH	0	RW	Stretch Channel Output
	If set, stretches cha	innel output to e	nsure that th	he target clock domain sees it.
24:22	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
21:20	EDSEL	0x0	RW	Edge Detect Select
	Select edge detecti	on.		
	Value	Mode		Description
	0	OFF		Signal is left as it is
	1	POSEDGE		A one HFCLK cycle pulse is generated for every positive edge of the incoming signal
	2	NEGEDGE		A one HFCLK clock cycle pulse is generated for every negative edge of the incoming signal
	3	BOTHEDGE	ES	A one HFCLK clock cycle pulse is generated for every edge of the incoming signal
19:15	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
14:8	SOURCESEL	0x00	RW	Source Select
	Select input source to	PRS channel.		
	Value	Mode		Description
	0b0000000	NONE		No source selected
	0b0000001	PRSL		Peripheral Reflex System
	0b0000010	PRSH		Peripheral Reflex System
	0b0000011	ACMP0		Analog Comparator 0
	0b0000100	ACMP1		Analog Comparator 1
	0b0000101	ADC0		Analog to Digital Converter 0
	0b0000111	LESENSEL		Low Energy Sensor Interface
	0b0001000	LESENSEH		Low Energy Sensor Interface
	0b0001001	LESENSED		Low Energy Sensor Interface
	0b0001010	LESENSE		Low Energy Sensor Interface
	0b0001011	RTCC		Real-Time Counter and Calendar
	0b0001100	GPIOL		General purpose Input/Output
	0b0001101	GPIOH		General purpose Input/Output
	0b0001110	LETIMER0		Low Energy Timer 0
	0b0001111	PCNT0		Pulse Counter 0
	0b0010010	CMU		Clock Management Unit
	0b0011000	VDAC0		Digital to Analog Converter 0
	0b0011010	CRYOTIMER		CRYOTIMER
	0b0110000	USART0		Universal Synchronous/Asynchronous Receiver/Transmitter 0
	0b0110001	USART1		Universal Synchronous/Asynchronous Receiver/Transmitter 1
	0b0111100	TIMER0		Timer 0
	0b0111101	TIMER1		Timer 1
	0b0111110	WTIMER0		Wide Timer 0
	0b1000011	CM4		
7:3	Reserved	To ensure contions	npatibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
2:0	SIGSEL	0x0	RW	Signal Select
	Select signal input to I	PRS channel. Se	elected sig	nal depends on SOURCESEL as indicated.
	Value	Mode		Description
	SOURCESEL =	0b000000		(NONE)
	0bxxx	OFF		Channel input selection is turned off
	SOURCESEL =	0b0000001		(PRSL)
	0b000	PRSCH0		PRS channel 0 PRSCH0 (Asynchronous)

Name	Reset Access	Description
0b001	PRSCH1	PRS channel 1 PRSCH1 (Asynchronous)
0b010	PRSCH2	PRS channel 2 PRSCH2 (Asynchronous)
0b011	PRSCH3	PRS channel 3 PRSCH3 (Asynchronous)
0b100	PRSCH4	PRS channel 4 PRSCH4 (Asynchronous)
0b101	PRSCH5	PRS channel 5 PRSCH5 (Asynchronous)
0b110	PRSCH6	PRS channel 6 PRSCH6 (Asynchronous)
0b111	PRSCH7	PRS channel 7 PRSCH7 (Asynchronous)
SOURCESEL =	0b0000010	(PRSH)
0b000	PRSCH8	PRS channel 8 PRSCH8 (Asynchronous)
0b001	PRSCH9	PRS channel 9 PRSCH9 (Asynchronous)
0b010	PRSCH10	PRS channel 10 PRSCH10 (Asynchronous)
0b011	PRSCH11	PRS channel 11 PRSCH11 (Asynchronous)
SOURCESEL =	0b0000011	(ACMP0)
0b000	ACMP0OUT	Analog comparator output ACMP0OUT (Asynchronous)
SOURCESEL =	0b0000100	(ACMP1)
0b000	ACMP1OUT	Analog comparator output ACMP1OUT (Asynchronous)
SOURCESEL =	0b0000101	(ADC0)
0b000	ADC0SINGLE	ADC single conversion done ADC0SINGLE (Asynchronous)
0b001	ADC0SCAN	ADC scan conversion done ADC0SCAN (Asynchronous)
SOURCESEL =	0b0000111	(LESENSEL)
0b000	LESENSESCANRES0	LESENSE SCANRES register, bit 0 LESENSESCANRES0 (Async nous)
0b001	LESENSESCANRES1	LESENSE SCANRES register, bit 1 LESENSESCANRES1 (Asynctous)
0b010	LESENSESCANRES2	LESENSE SCANRES register, bit 2 LESENSESCANRES2 (Asynctous)
0b011	LESENSESCANRES3	LESENSE SCANRES register, bit 3 LESENSESCANRES3 (Async nous)
0b100	LESENSESCANRES4	LESENSE SCANRES register, bit 4 LESENSESCANRES4 (Async nous)
0b101	LESENSESCANRES5	LESENSE SCANRES register, bit 5 LESENSESCANRES5 (Async nous)
0b110	LESENSESCANRES6	LESENSE SCANRES register, bit 6 LESENSESCANRES6 (Async nous)
0b111	LESENSESCANRES7	LESENSE SCANRES register, bit 7 LESENSESCANRES7 (Asynctonus)
SOURCESEL =	0b0001000	(LESENSEH)
0b000	LESENSESCANRES8	LESENSE SCANRES register, bit 8 LESENSESCANRES8 (Asynctonus)
0b001	LESENSESCANRES9	LESENSE SCANRES register, bit 9 LESENSESCANRES9 (Async nous)


Name	Reset Access	Description
0b010	LESENSESCANRES10	LESENSE SCANRES register, bit 10 LESENSESCANRES10 (Asynchronous)
0b011	LESENSESCANRES11	LESENSE SCANRES register, bit 11 LESENSESCANRES11 (Asynchronous)
0b100	LESENSESCANRES12	LESENSE SCANRES register, bit 12 LESENSESCANRES12 (Asynchronous)
0b101	LESENSESCANRES13	LESENSE SCANRES register, bit 13 LESENSESCANRES13 (Asynchronous)
0b110	LESENSESCANRES14	LESENSE SCANRES register, bit 14 LESENSESCANRES14 (Asynchronous)
0b111	LESENSESCANRES15	LESENSE SCANRES register, bit 15 LESENSESCANRES15 (Asynchronous)
SOURCESEL =	0b0001001	(LESENSED)
0b000	LESENSEDEC0	LESENSE Decoder PRS out 0 LESENSEDEC0 (Asynchronous)
0b001	LESENSEDEC1	LESENSE Decoder PRS out 1 LESENSEDEC1 (Asynchronous)
0b010	LESENSEDEC2	LESENSE Decoder PRS out 2 LESENSEDEC2 (Asynchronous)
0b011	LESENSEDECCMP	LESENSE Decoder PRS compare value match channel LESENSE-DECCMP (Asynchronous)
SOURCESEL =	0b0001010	(LESENSE)
0b000	LESENSEMEASACT	LESENSE Measurement active LESENSEMEASACT (Asynchronous
SOURCESEL =	0b0001011	(RTCC)
0b001	RTCCCCV0	RTCC Compare 0 RTCCCCV0 (Asynchronous)
0b010	RTCCCCV1	RTCC Compare 1 RTCCCCV1 (Asynchronous)
0b011	RTCCCCV2	RTCC Compare 2 RTCCCCV2 (Asynchronous)
SOURCESEL =	0b0001100	(GPIOL)
0b000	GPIOPIN0	GPIO pin 0 GPIOPIN0 (Asynchronous)
0b001	GPIOPIN1	GPIO pin 1 GPIOPIN1 (Asynchronous)
0b010	GPIOPIN2	GPIO pin 2 GPIOPIN2 (Asynchronous)
0b011	GPIOPIN3	GPIO pin 3 GPIOPIN3 (Asynchronous)
0b100	GPIOPIN4	GPIO pin 4 GPIOPIN4 (Asynchronous)
0b101	GPIOPIN5	GPIO pin 5 GPIOPIN5 (Asynchronous)
0b110	GPIOPIN6	GPIO pin 6 GPIOPIN6 (Asynchronous)
0b111	GPIOPIN7	GPIO pin 7 GPIOPIN7 (Asynchronous)
SOURCESEL =	0b0001101	(GPIOH)
0b000	GPIOPIN8	GPIO pin 8 GPIOPIN8 (Asynchronous)
0b001	GPIOPIN9	GPIO pin 9 GPIOPIN9 (Asynchronous)
0b010	GPIOPIN10	GPIO pin 10 GPIOPIN10 (Asynchronous)
0b011	GPIOPIN11	GPIO pin 11 GPIOPIN11 (Asynchronous)
0b100	GPIOPIN12	GPIO pin 12 GPIOPIN12 (Asynchronous)
0b101	GPIOPIN13	GPIO pin 13 GPIOPIN13 (Asynchronous)

Bit	Name	Reset Access	Description
	0b110	GPIOPIN14	GPIO pin 14 GPIOPIN14 (Asynchronous)
	0b111	GPIOPIN15	GPIO pin 15 GPIOPIN15 (Asynchronous)
	SOURCESEL =	0b0001110	(LETIMERO)
	0b000	LETIMER0CH0	LETIMER CH0 Out LETIMER0CH0 (Asynchronous)
	0b001	LETIMER0CH1	LETIMER CH1 Out LETIMER0CH1 (Asynchronous)
	SOURCESEL =	0b0001111	(PCNT0)
	0b000	PCNT0TCC	PCNT0 Triggered compare match PCNT0TCC (Asynchronous)
	0b001	PCNT0UFOF	PCNT0 Counter overflow or underflow PCNT0UFOF (Asynchronous)
	0b010	PCNT0DIR	PCNT0 Counter direction PCNT0DIR (Asynchronous)
	SOURCESEL =	0b0010010	(CMU)
	0b000	CMUCLKOUT0	Clock Output 0 CMUCLKOUT0 (Asynchronous)
	0b001	CMUCLKOUT1	Clock Output 1 CMUCLKOUT1 (Asynchronous)
	SOURCESEL =	0b0011000	(VDAC0)
	0b000	VDAC0CH0	DAC ch0 conversion done VDAC0CH0
	0b001	VDAC0CH1	DAC ch1 conversion done VDAC0CH1
	0b010	VDAC0OPA0	OPA0 warmedup or outputvalid based on OPA0PRSOUTMODE mode in OPACTRL. VDAC0OPA0 (Asynchronous)
	0b011	VDAC0OPA1	OPA1 warmedup or outputvalid based on OPA1PRSOUTMODE mode in OPACTRL. VDAC0OPA1 (Asynchronous)
	SOURCESEL =	0b0011010	(CRYOTIMER)
	0b000	CRYOTIMERPERIOD	CRYOTIMER Output CRYOTIMERPERIOD (Asynchronous)
	SOURCESEL =	0b0110000	(USARTO)
	0b000	USART0IRTX	USART 0 IRDA out USART0IRTX
	0b001	USART0TXC	USART 0 TX complete USART0TXC
	0b010	USART0RXDATAV	USART 0 RX Data Valid USART0RXDATAV
	0b011	USART0RTS	USART 0 RTS USART0RTS
	0b101	USART0TX	USART 0 TX USART0TX
	0b110	USART0CS	USART 0 CS USART0CS
	SOURCESEL =	0b0110001	(USART1)
	0b001	USART1TXC	USART 1 TX complete USART1TXC
	0b010	USART1RXDATAV	USART 1 RX Data Valid USART1RXDATAV
	0b011	USART1RTS	USART 1 RTS USART1RTS
	0b101	USART1TX	USART 1 TX USART1TX
	0b110	USART1CS	USART 1 CS USART1CS
	SOURCESEL =	0b0111100	(TIMER0)
	0b000	TIMER0UF	Timer 0 Underflow TIMER0UF
	0b001	TIMER0OF	Timer 0 Overflow TIMER0OF
	0b010	TIMER0CC0	Timer 0 Compare/Capture 0 TIMER0CC0

			· · · · · · · · · · · · · · · · · · ·
Bit	Name	Reset Acce	s Description
	0b011	TIMER0CC1	Timer 0 Compare/Capture 1 TIMER0CC1
	0b100	TIMER0CC2	Timer 0 Compare/Capture 2 TIMER0CC2
	SOURCESEL =	0b0111101	(TIMER1)
	0b000	TIMER1UF	Timer 1 Underflow TIMER1UF
	0b001	TIMER10F	Timer 1 Overflow TIMER1OF
	0b010	TIMER1CC0	Timer 1 Compare/Capture 0 TIMER1CC0
	0b011	TIMER1CC1	Timer 1 Compare/Capture 1 TIMER1CC1
	0b100	TIMER1CC2	Timer 1 Compare/Capture 2 TIMER1CC2
	0b101	TIMER1CC3	Timer 1 Compare/Capture 3 TIMER1CC3
	SOURCESEL =	0b0111110	(WTIMER0)
	0b000	WTIMER0UF	Timer 2 Underflow WTIMER0UF
	0b001	WTIMER0OF	Timer 2 Overflow WTIMER0OF
	0b010	WTIMER0CC0	Timer 2 Compare/Capture 0 WTIMER0CC0
	0b011	WTIMER0CC1	Timer 2 Compare/Capture 1 WTIMER0CC1
	0b100	WTIMER0CC2	Timer 2 Compare/Capture 2 WTIMER0CC2
	SOURCESEL =	0b1000011	(CM4)
	0b000	CM4TXEV	CM4TXEV
	0b001	CM4ICACHEPCHIT- SOF	CM4ICACHEPCHITSOF
	0b010	CM4ICACHEPCMISS SOF	E- CM4ICACHEPCMISSESOF

16. PCNT - Pulse Counter





Quick Facts

What?

The Pulse Counter (PCNT) decodes incoming pulses. The module has a quadrature mode which may be used to decode the speed and direction of a mechanical shaft. PCNT can operate in EM0 Active down to EM3 Stop.

Why?

The PCNT generates an interrupt after a specific number of pulses (or rotations), eliminating the need for timing or I/O interrupts and CPU processing to measure pulse widths, etc.

How?

PCNT uses the LFACLK or may be externally clocked from a pin. The module incorporates a 16-bit up/down-counter to keep track of incoming pulses or rotations.

16.1 Introduction

The Pulse Counter (PCNT) can be used for counting incoming pulses on a single input or to decode quadrature encoded inputs in EM0 Active down to EM3 Stop. It can run from the internal LFACLK while counting pulses on the PCNTn_S0IN pin. Or, alternately, the PCNTn S0IN pin may be used as an external clock source that runs both the PCNT counter and register access.

16.2 Features

- · 16-bit counter with reload register
- · Auxiliary counter for counting a single direction
- · Single input oversampling up/down counter mode
- Externally clocked single input pulse up/down counter mode
- · Quadrature decoder modes
 - Externally clocked quadrature decoder 1X mode
 - · Oversampling quadrature decoder 1X, 2X and 4X modes
- · Interrupt on counter underflow and overflow
- · Interrupt when a direction change is detected (quadrature decoder mode only)
- · Optional pulse width filter
- · Optional input inversion/edge detect select
- · Optional inputs from PRS
- · Asynchronously triggered compare and clear

16.3 Functional Description

An overview of the PCNT module is shown in Figure 16.1 PCNT Overview on page 446.




Figure 16.1. PCNT Overview

16.3.1 Pulse Counter Modes

The pulse counter can operate in single input oversampling mode (OVSSINGLE), externally clocked single input counter mode (EXTCLKSINGLE), externally clocked quadrature decoder mode (EXTCLKQUAD) and oversampling quadrature decoder modes(OVSQUAD1X, OVSQUAD2X and OVSQUAD4X). The following sections describe operation of each of these modes and how they are enabled. Input timing constraints are described in 16.3.6 Clock Sources and 16.3.7 Input Filter.

16.3.1.1 Single Input Oversampling Mode

This mode is enabled by writing OVSSINGLE to the MODE field in the PCNTn_CTRL register and disabled by writing DISABLE to the same field. The LFACLK clock source to the pulse counter is configured by clearing PCNT0CLKSEL in the CMU_PCNTCTRL in the Clock Management Unit (CMU).

The optional pulse width filter is enabled by setting the FILT bit in the PCNTn_CTRL register. Additionally, the PCNTn_S0IN input may be inverted, so that falling edges are counted, by setting the EDGE bit in the PCNTn_CTRL register.

If S1CDIR in the PCNTn_CTRL register is cleared, PCNTn_S0IN is the only observed input in this mode. The PCNTn_S0IN input is sampled by the LFACLK and the number of detected positive or negative edges on PCNTn_S0IN appears in PCNTn_CNT. The counter may be configured to count down by setting the CNTDIR bit in PCNTn_CTRL. Default is to count up.

The counting direction can also be controlled externally in this mode by setting S1CDIR. This will make the input value on PCNTn_S1IN decide the direction counted on a PCNTn_S0IN edge. If PCNTn_S1IN is high, the count is done according to CNTDIR in PCNTn_CTRL. If low, the count direction is opposite.

16.3.1.2 Externally Clocked Single Input Counter Mode

This mode is enabled by writing EXTCLKSINGLE to the MODE field in the PCNTn_CTRL register and disabled by writing DISABLE to the same field. The external pin clock source is configured by setting PCNT0CLKSEL in the CMU_PCNTCTRL register (11. CMU - Clock Management Unit).

Positive edges on PCNTn_S0IN are used to clock the counter. Similar to the oversampled mode, PCNTn_S1IN is used to determine the count direction if S1CDIR is set. If not, CNTDIR in PCNTn CTRL solely defines count direction.

The digital pulse width filter is not available in this mode. The analog de-glitch filter in the GPIO pads is capable of removing some unwanted noise. However, this mode may be susceptible to spikes and unintended pulses from devices such as mechanical switches, and is therefore most suited to take input from electronic sensors etc. that generate single wire pulses.

16.3.1.3 Quadrature Decoder Modes

Two different types of quadrature decoding is supported in the pulse counter: the externally clocked (Asynchronous) quadrature decoding and the oversampling (Synchronous) quadrature decoding. The externally clocked mode supports 1X quadrature decoding whereas the oversampling mode supports 1X, 2X and 4X quadrature decoding. These modes are described in detail in 16.3.1.4 Externally Clocked Quadrature Decoder Mode and 16.3.1.5 Oversampling Quadrature Decoder Mode.

16.3.1.4 Externally Clocked Quadrature Decoder Mode

This mode is enabled by writing EXTCLKQUAD to the MODE field in PCNTn_CTRL and disabled by writing DISABLE to the same field. The external pin clock source is configured by setting PCNT0CLKSEL in the CMU_PCNTCTRL register (11. CMU - Clock Management Unit).

In this mode, both edges on PCNTn_S0IN pin are used to sample PCNTn_S1IN pin, in order to decode the quadrature code. A quadrature coded signal contains information about the relative speed and direction of a rotating shaft as illustrated by Figure 16.2 PCNT Quadrature Coding on page 448, hence the direction of the counter register PCNTn_CNT is controlled automatically.




Figure 16.2. PCNT Quadrature Coding

If PCNTn_S0IN leads PCNTn_S1IN in phase, the direction is clockwise, and if it lags in phase the direction is counter-clockwise. Default behavior is illustrated by Figure 16.2 PCNT Quadrature Coding on page 448.

The counter direction may be read from the DIR bit in the PCNTn_STATUS register. Additionally, the DIRCNG interrupt in the PCNTn_IF register is generated when a direction change is detected. When a change is detected, the DIR bit in the PCNTn_STATUS register must be read to determine the current new direction.

Note: The sector disc illustrated in the figure may be finer grained in some systems. Typically, they may generate 2-4 PCNTn_S0IN wave periods per 360° rotation.

The direction of the quadrature code and control of the counter is generated by the simple binary function outlined by Table 16.1 PCNT QUAD Mode Counter Control Function on page 448. Note that this function also filters some invalid inputs that may occur when the shaft changes direction or temporarily toggles direction.

Table 16.1. PCNT QUAD Mode Counter Control Function

Inputs		Control/Status	
S1IN posedge	S1IN negedge	Count Enable	CNTDIR status bit
0	0	0	0

Inputs		Control/Status	
S1IN posedge	S1IN negedge	Count Enable	CNTDIR status bit
0	1	1	0
1	0	1	1
1	1	0	0

Note: PCNTn_S1IN is sampled on both edges of PCNTn_S0IN.

16.3.1.5 Oversampling Quadrature Decoder Mode

There are three Oversampling Quadrature Decoder Modes supported: 1X , 2X and 4X. These modes are enabled by writing OVS-QUAD1X, OVSQUAD2X and OVSQUAD4X, respectively, to the MODE field in PCNTn_CTRL and disabled by writing DISABLE to the same field. The LFACLK clock source to the pulse counter must be configured by clearing PCNT0CLKSEL in the CMU_PCNTCTRL in the Clock Management Unit (CMU), 11. CMU - Clock Management Unit .

The optional pulse width filter is enabled by setting the FILT bit in the PCNTn_CTRL register. The filter applies to both inputs PCNTn_S0IN and PCNTn_S1IN. The filter length is configured by FILTLEN in PCNTn_OVSCFG register.

Based on the modes selected, the decoder updates the counter on different events. In the OVSQUAD1X mode, the counter is updated on the rising edge of the PCNTn_S0IN input when counting up, and on the negedge of the PCNTn_S0IN input when counting down. In the OVSQUAD2X mode, the counter is updated on both edges of PCNTn_S0IN input. In the OVSQUAD4X mode the counter is updated on both edges of both inputs PCNTn_S0IN and PCNTn_S1IN. Table 16.2 PCNT OVSQUAD 1X, 2X and 4X Mode Counter Control Function on page 450 outlines the increment or decrement of the counter based on the Quadrature Mode selected.

Note: The decoding behavior of OVSQUAD1X mode is slightly different compared to EXTCLKQUAD mode(also 1X mode). In the EXTCLKQUAD mode, the counter is updated only on the posedge of S0IN input. However, in the OVSQUAD1X mode, the counter is updated on the posedge of S0IN when counting up and on the negedge of S0IN when counting down.

Table 16.2. PCNT OVSQUAD 1X, 2X and 4X Mode Counter Control Function

Direction	Previou	ıs State	Next :	State	0\	/SQUAD MO	DE
	S1IN	SOIN	S1IN	SOIN	1X	2X	4X
	0	0	0	1	+1	+1	+1
Clockwise	0	1	1	1			+1
Ciockwise	1	1	1	0		+1	+1
	1	0	0	0			+1
	1	0	1	1		-1	-1
Counter Clock-	1	1	0	1			-1
wise	0	1	0	0	-1	-1	-1
	0	0	1	0			-1

Figure 16.3 PCNT State Transitions for Different Oversampling Quadrature Decoder Modes on page 451 illustrates the different states of the quadrature input and the state transitions that updates the counter for the different modes. Each cycle of the input states results in 1 update, 2 updates and 4 updates of the counter for OVSQUAD1X, OVSQUAD2X and OVSQUAD4X modes respectively.




Figure 16.3. PCNT State Transitions for Different Oversampling Quadrature Decoder Modes

The counter direction can be read from the DIR bit in PCNTn_STATUS register. Additionally, the DIRCNG interrupt in the PCNTn_IF is generated when the direction change is detected. When a change is detected, the DIR bit in the PCNTn_STATUS register must be read to determine the new direction.

In the oversampling quadrature decoder modes, the maximum input toggle frequency supported is 8KHz. For frequencies of 8KHz and higher, incorrect decoding occurs. The different decoding modes and the counter updates are further illustrated by Figure 16.4 PCNT Oversampling Quadrature Decoder 1X Mode on page 451, Figure 16.5 PCNT Oversampling Quadrature Decoder 2X Mode on page 452 and Figure 16.6 PCNT Oversampling Quadrature Decoder 4X Mode on page 452.




Figure 16.4. PCNT Oversampling Quadrature Decoder 1X Mode




Figure 16.5. PCNT Oversampling Quadrature Decoder 2X Mode




Figure 16.6. PCNT Oversampling Quadrature Decoder 4X Mode

The above modes, by default are prone to flutter effects in the inputs PCNTn_S0IN and PCNTn_S1IN. When this occurs, the counter changes directions rapidly causing DIRCNG interrupts and unnecessarily waking the core. To prevent this, set FLUTTERRM in PCNTn_OVSCFG register. When enabled, flutter is removed, thus preventing unnecessary wakeup of the core. The flutter removal logic works by preventing update of the counter value if the wheel keeps changing direction as a result of flutter. The counter is only updated if the current and previous state transition of the rotation are in the same direction. These state transitions are quadrature decoder mode specific. The highlighted state transitions in Figure 16.3 PCNT State Transitions for Different Oversampling Quadrature Decoder Modes on page 451 are the ones considered for the different quadrature decoder modes. Figure 16.7 PCNT Oversampling Quadrature Decoder with Flutter Removal on page 452 shows how the counter is updated for the different quadrature decoder modes with flutter removal FLUTTERRM enabled in PCNTn OVSCFG.




Figure 16.7. PCNT Oversampling Quadrature Decoder with Flutter Removal

16.3.2 Hysteresis

By default the pulse counter wraps to 0 when passing the configured top value, and wraps to the top value when counting down from 0. On these events, a system will likely want to wake up to store and track the overflow count. This is fine if the pulse counter is tracking a monotonic value or a value that does not change directions frequently. In the latter scenario, if the counter changes directions around the overflow/underflow point, the system will have to wake up frequently to keep track of the rotations, resulting in higher current consumption.

To solve this, the pulse counter has a way of introducing hysteresis to the counter. When HYST in PCNTn_CTRL is set, the pulse counter will always wrap to TOP/2 on underflows and overflows. This takes the counter away from the area where it might overflow or underflow, removing the problem. Figure 16.8 PCNT Hysteresis behavior of Counter on page 453 illustrates the hysteresis behavior.




Figure 16.8. PCNT Hysteresis behavior of Counter

Given a starting value of 0 for the counter, the absolute count value when hysteresis is enabled can be calculated with the equations Figure 16.9 Absolute Position With Hysteresis and Even TOP Value on page 453 or Figure 16.10 Absolute Position With Hysteresis and Odd TOP Value on page 453, depending on whether the TOP value is even or odd.

$$CNT_{abs} = CNT - UF_{CNT} x (TOP/2+1) + OF_{CNT} x (TOP/2+1)$$

Figure 16.9. Absolute Position With Hysteresis and Even TOP Value

$$CNT_{abs} = CNT - UF_{CNT} x (TOP/2+1) + OF_{CNT} x (TOP/2+2)$$

Figure 16.10. Absolute Position With Hysteresis and Odd TOP Value

16.3.3 Auxiliary Counter

To be able to keep explicit track of counting in one direction in addition to the regular counter which counts both up and down, the auxiliary counter can be used. The pulse counter can, for instance, be configured to keep track of the absolute rotation of the wheel, while at the same time the auxiliary counter can keep track of how much the wheel has reversed.

The auxiliary counter is enabled by configuring AUXCNTEV in PCNTn_CTRL. It will always count up, but it can be configured whether it should count up on up-events, down-events or both, keeping track of rotation either way or general movement. The value of the auxiliary counter can be read from the PCNTn_AUXCNT register.

Overflows on the auxiliary counter happen when the auxiliary counter passes the top value of the pulse counter, configured in PCNTn_TOP. In that event, the AUXOF interrupt flag is set, and the auxiliary counter wraps to 0.

As the auxiliary counter, the main counter can be configured to count only on certain events. This is done through CNTEV in PCNTn_CTRL, and it is possible like for the auxiliary counter, to make the main counter count on only up and down events. The difference between the counters is that where the auxiliary counter will only count up, the main counter will count up or down depending on the direction of the count event.

16.3.4 Triggered Compare and Clear

The pulse counter features triggered compare and clear. When enabled, a configurable trigger will induce a comparison between the main counter, PCNTn_CNT, and the top value, PCNTn_TOP. After the comparison, the counter is cleared. The trigger for a compare and clear event is configured in the TCCMODE bit-field in PCNTn_CTRL. There are two options, LFA and PRS. If LFA is selected, the pulse counter will be compared with the top value, and cleared every 2^N LFA clock cycle (where N is the value of TCCPRESC in PCNTn_CTRL). If a PRS trigger is selected, the active PRS channel is configured in TCCPRSSEL in PCNTn_CTRL. The PRS input can be inverted by setting TCCPRSPOL, triggering the compare and clear on the negative edge of the PRS input. The PRS input can also be used as a gate for the pulse counter clock. This is enabled by setting PRSGATEEN in PCNTn_CTRL.

Note: When PRSGATEEN is set, the clock to the entire pulse counter will be gated by the PRS input, meaning that register writes will not take effect while the gated clock is inactive.

Comparison with PCNTn_TOP can be performed in three ways: range, greater than or equal, and less than or equal. TCCCOMP in PCNTn_CTRL configures comparison mode. Upon a compare match, the TCC interrupt is set, and the PRS output from the pulse counter is set. The PRS output will remain set until the next compare and clear event. Triggered compare and clear is intended for use when the pulse counter is configured to count up. In this mode, PCNTn_CNT will not wrap to 0 when hitting PCNTn_TOP, it will keep counting. In addition, the counter will not overflow, it will rather stop counting, just setting the overflow interrupt flag.

Figure 16.11 PCNT Triggered Compare and Clear on page 455 shows an overview of the control circuitry for triggered compare and clear. The control circuitry includes two positive edge detectors (PED) and glitch filters, used to generate clocks for the pulse counter. The two clock outputs are mutually exclusive: If both edge detectors receive a pulse at the same time, the output pulse from one of them will be postponed until the other edge detectors output pulse has completed.




Figure 16.11. PCNT Triggered Compare and Clear

Note: TCCMODE, TCCPRESC, PRSGATEEN, TCCPRSPOL, and TCCPRSSEL in PCNTn_CTRL should only be altered when RSTEN in PCNTn_CTRL is set.

16.3.5 Register Access

The counter-clock domain may be clocked externally. To update the counter-clock domain registers from software in this mode, 2-3 clock pulses on the external clock are needed to synchronize accesses to the externally clocked domain. Clock source switching is controlled from the registers in the CMU (11. CMU - Clock Management Unit).

When the RSTEN bit in the PCNTn_CTRL register is set, the PCNT clock domain is asynchronously held in reset. The reset is synchronously released two PCNT clock edges after the RSTEN bit in the PCNTn_CTRL register is cleared by software. This asynchronous reset restores the reset values in PCNTn_TOP, PCNTn_CNT and other control registers in the PCNT clock domain.

CNTRSTEN works in a similar manner as RSTEN, but only resetting the counter, CNT. Note that the counter is also reset by RSTEN.

AUXCNTRSTEN works in a similar manner as RSTEN, but only resetting the auxiliary counter, PCNTn_AUXCNT. Note that the auxiliary counter is also reset by RSTEN.

Since this module is a Low Energy Peripheral, and runs off a clock which is asynchronous to the HFCORECLK, special considerations must be taken when accessing registers. Refer to 4.3 Access to Low Energy Peripherals (Asynchronous Registers) for a description on how to perform register accesses to Low Energy Peripherals.

Note: PCNTn_TOP and PCNTn_CNT are read-only registers. When writing to PCNTn_TOPB, make sure that the counter value, PCNTn CNT, can not exceed the value written to PCNTn TOPB within two clock cycles.

16.3.6 Clock Sources

The pulse counter may be clocked from two possible clock sources: LFACLK or an external clock. The clock selection is configured by the PCNT0CLKSEL bit in the CMU_PCNTCTRL in the Clock Management Unit (CMU), 11. CMU - Clock Management Unit . The default clock source is the LFACLK.

This PCNT module may also use PCNTn_S0IN as an external clock to clock the counter (EXTCLKSINGLE mode) and to sample PCNTn_S1IN (EXTCLKQUAD mode). Setup, hold and max frequency constraints for PCNTn_S0IN and PCNTn_S1IN for these modes are specified in the device data sheet.

To use this module, the LE interface clock must be enabled in CMU_HFBUSCLKEN0, in addition to the module clock in CMU_PCNTCTRL.

Note: PCNT Clock Domain Reset, RSTEN, should be set when changing clock source for PCNT. If changing to an external clock source, the clock pin has to be enabled as input prior to de-asserting RSTEN. Changing clock source without asserting RSTEN results in undefined behaviour.

16.3.7 Input Filter

An optional pulse width filter is available in OVSSINGLE and OVSQUAD modes, when LFACLK is selected as a clock source for the Pulse Counter in CMU 11. CMU - Clock Management Unit . The filter is enabled by writing 1 to the FILT bit in the PCNTn_CTRL register. When enabled, the high and low periods of PCNTn_S0IN and PCNTn_S1IN must be stable for a programmable number of consecutive clock cycles before the edge is passed to the edge detector. The filter length should be programmed in FILTLEN field of the PCNTn OVSCFG register.

The filter length is given by Figure 16.12 PCNT Input Filter Length Equation on page 456:

Filter length = (FILTLEN + 5) LFACLK cycles

Figure 16.12. PCNT Input Filter Length Equation

The maximum filter length configured is 260 LFACLK cycles.

In EXTCLKSINGLE and EXTCLKQUAD mode, there is no digital pulse width filter available.

16.3.8 Edge Polarity

The edge polarity can be set by configuring the EDGE bit in the PCNTn_CTRL register. When this bit is cleared, the pulse counter counts positive edges of PCNTn_S0IN input. When this bit is set, the pulse counter counts negative edges in OVSSINGLE mode. Also, when the EDGE bit is set in the OVSSINGLE and EXTCLKSINGLE modes, the PCNTn_S1IN input is inverted. In OVSQUAD 1X-4X modes the EDGE bit inverts both inputs.

Note: The EDGE bit in PCNTn_CTRL has no effect in EXTCLKQUAD mode.

16.3.9 PRS and PCNTn_S0IN,PCNTn_S1IN Inputs

It is possible to receive input from PRS on both PCNTn_S0IN (or PCNTn_S1IN) by setting S0PRSEN (or S1PRSEN) in PCNTn_IN-PUT. The PRS channel used can be selected using S0PRSSEL (or S1PRSSEL) in PCNTn_INPUT.

In the Oversampling quadrature decoder modes, the input frequency should be less than 8KHz to ensure correct functionality.

PCNT module generates three PRS outputs the TCC PRS output, the CNT OF/UF PRS output and the CNT DIR PRS output. The TCC PRS is generated on compare match of TCC event. The CNT OF/UF combined PRS is generated when the counter overflow or underflows. The CNT DIR PRS is a level PRS and indicates the current direction of count of counter CNT

Note: S0PRSEN,S1PRSEN,S0PRSSEL,S1PRSSEL should only be altered when RSTEN in PCNTn CTRL is set.

16.3.10 Interrupts

The interrupt generated by PCNT uses the PCNTn_INT interrupt vector. Software must read the PCNTn_IF register to determine which module interrupt that generated the vector invocation.

16.3.10.1 Underflow and Overflow Interrupts

The underflow interrupt flag (UF) is set when the counter counts down from 0. I.e. when the value of the counter is 0 and a new pulse is received. The PCNTn_CNT register is loaded with the PCNTn_TOP value after this event.

The overflow interrupt flag (OF) is set when the counter counts up from the PCNTn_TOP (reload) value. I.e. if PCNTn_CNT = PCNTn_TOP and a new pulse is received. The PCNTn_CNT register is loaded with the value 0 after this event.

16.3.10.2 Direction Change Interrupt

The PCNTn_PCNT module sets the DIRCNG interrupt flag (PCNTn_IF register) for EXTCLKQUAD and OVSQUAD1X-4X modes when the direction of the quadrature code changes. The behavior of this interrupt in the EXTCLKQUAD mode is illustrated by Figure 16.13 PCNT Direction Change Interrupt (DIRCNG) Generation on page 458.




Figure 16.13. PCNT Direction Change Interrupt (DIRCNG) Generation

16.3.11 Cascading Pulse Counters

When two or more Pulse Counters are available, it is possible to cascade them. For example two 16-bit Pulse Counters can be cascaded to form a 32-bit pulse counter. This can be done with the help of the CNT UF/OF PRS and CNT DIR PRS ouputs. The figure Figure 16.14 PCNT Cascading to two 16-bit PCNT to form a 32-bit PCNT on page 459 illustrates this structure.




Figure 16.14. PCNT Cascading to two 16-bit PCNT to form a 32-bit PCNT

For cascading of Pulse Counters to work, the PCNT1 according to the figure Figure 16.14 PCNT Cascading to two 16-bit PCNT to form a 32-bit PCNT on page 459 should be programmed in EXTCLKSINGLE mode and its S0IN and S1IN inputs should be configured to prs_ufof and prs_dir of PCNT0 respectively. In addition to this, a strict programming sequence needs to be followed to ensure both PCNTs are in sync with each other.

- Configure PCNT0 registers. eg. PCNT0_INPUT,PCNT0_CTRL,PCNT0_OVSCFG etc.
- · Wait for PCNT0 SYCNBUSY to be cleared to ensure the registers are synchronized to the asynchronous clock domain.
- Hold PCNT0 in sw reset by setting PCNT0_CTRL_RSTEN.
- Configure PCNT1_CTRL to EXTCLKSINLE mode with S1CDIR and CNTDIR bit set. Configure INPUT to accept "prs_ufof" and
 "prs_dir" of PCNT0 on S0IN and S1IN respectively.
- Wait for PCNTn_SYCNBUSY to be cleared to ensure the registers are synchronized to the asynchronous clock domain. Use three PRS_SWPULSE on the S0IN prs channel to ensure this synchronization.
- Hold PCNT1 in sw reset by setting PCNT1 CTRL RSTEN.
- Clear PCNT1 CTRL RSTEN and synchronize it by asserting two PRS SWPULSE on the S0IN input.
- Finally clear PCNT0_CTRL_RSTEN and start counting.

Note: When RSTEN in PCNTn_CTRL is set, the TOP value in the Pulse Counter gets cleared. Therefore, in order to update the TOP value while RSTEN is set, assert TOPBHFEN bit in PCNTn_CTRL. This will update the TOP value with the TOPB value even without having to synchronize the TOPB value. This only works if TOPBHFEN and TOPB are configured while RSTEN in PCNTn_CTRL is set.

16.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	PCNTn_CTRL	RW	Control Register
0x004	PCNTn_CMD	W1	Command Register
0x008	PCNTn_STATUS	R	Status Register
0x00C	PCNTn_CNT	R	Counter Value Register
0x010	PCNTn_TOP	R	Top Value Register
0x014	PCNTn_TOPB	RW	Top Value Buffer Register
0x018	PCNTn_IF	R	Interrupt Flag Register
0x01C	PCNTn_IFS	W1	Interrupt Flag Set Register
0x020	PCNTn_IFC	(R)W1	Interrupt Flag Clear Register
0x024	PCNTn_IEN	RW	Interrupt Enable Register
0x02C	PCNTn_ROUTELOC0	RW	I/O Routing Location Register
0x040	PCNTn_FREEZE	RW	Freeze Register
0x044	PCNTn_SYNCBUSY	R	Synchronization Busy Register
0x064	PCNTn_AUXCNT	R	Auxiliary Counter Value Register
0x068	PCNTn_INPUT	RW	PCNT Input Register
0x06C	PCNTn_OVSCFG	RW	Oversampling Config Register

16.5 Register Description

16.5.1 PCNTn_CTRL - Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	it Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	9	6	8	7	9	2	4	က	2	-	0
Reset	0				OX O		0	0	3	OXO		2	e N		2	2	0	0	0.0	0.00	2	0.00	0	0	0	0	0	0	0		0×0	
Access	₩ W			2	≥ Y		₩ M	₹	2	<u>}</u>		2	≥ Y		2	≥ Y	₽	RW	7	<u>}</u>	20	<u>}</u>	ΑW	₩	Z.	W.	₹	₽	₩ M		¥	
Name	TOPBHFSEL				CCPRSSEL		TCCPRSPOL	PRSGATEEN				COLL	Ц Ľ				EDGE	CNTDIR	A LINUXIIV	AOVONIEV) H) 	S1CDIR	HYST	DEBUGHALT	AUXCNTRSTEN	CNTRSTEN	RSTEN	FILT		MODE	

Bit	Name	Reset	Access	s Description							
31	TOPBHFSEL	0	RW	TOPB High Frequency Value Select							
	Apply High frequer	ncy value of TOPE	3 to TOP re	egister. Should be used only when RSTEN in PCNTn_CTRL is set							
30	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-							
29:26	TCCPRSSEL	0x0	RW	TCC PRS Channel Select							
	Select PRS channe	el used as compa	re and clea	ar trigger.							
	Value	Mode		Description							
	0	PRSCH0		PRS Channel 0 selected.							
	1	PRSCH1		PRS Channel 1 selected.							
	2	PRSCH2		PRS Channel 2 selected.							
	3	PRSCH3		PRS Channel 3 selected.							
	4	PRSCH4		PRS Channel 4 selected.							
	5	PRSCH5		PRS Channel 5 selected.							
	6	PRSCH6		PRS Channel 6 selected.							
	7	PRSCH7		PRS Channel 7 selected.							
	8	PRSCH8		PRS Channel 8 selected.							
	9	PRSCH9		PRS Channel 9 selected.							
	10	PRSCH10		PRS Channel 10 selected.							
	11	PRSCH11		PRS Channel 11 selected.							
25	TCCPRSPOL	0	RW	TCC PRS Polarity Select							
	Configure which ed	dge on the PRS ir	put is used	d to trigger a compare and clear event							
	Value	Mode		Description							
	0	RISING		Rising edge on PRS trigger compare and clear event.							
	1	FALLING		Falling edge on PRS trigger compare and clear event.							

Bit	Name	Reset	Access	Description
24	PRSGATEEN	0	RW	PRS Gate Enable
	When set, the clock	input to the pulse	e counter w	rill be gated when the selected PRS input is the inverse of TCCPRSPOL.
23:22	TCCCOMP	0x0	RW	Triggered Compare and Clear Compare Mode
	Selects the mode for	comparison upo	on a compa	re and clear event.
	Value	Mode		Description
	0	LTOE		Compare match if PCNT_CNT is less than, or equal to PCNT_TOP.
	1	GTOE		Compare match if PCNT_CNT is greater than or equal to PCNT_TOP.
	2	RANGE		Compare match if PCNT_CNT is less than, or equal to PCNT_TOP[15:8]], and greater than, or equal to PCNT_TOP[7:0].
21	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
20:19	TCCPRESC	0x0	RW	Set the LFA Prescaler for Triggered Compare and Clear
	Selects the prescale	r value for LFA c	ompare an	d clear events
	Value	Mode		Description
	0	DIV1		Compare and clear event each LFA cycle.
	1	DIV2		Compare and clear performed on every other LFA cycle.
	2	DIV4		Compare and clear performed on every 4th LFA cycle.
	3	DIV8		Compare and clear performed on every 8th LFA cycle.
18	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	TCCMODE	0x0	RW	Sets the Mode for Triggered Compare and Clear
	Selects whether com	pare and clear s	should be tr	iggered on each LFA clock, or from PRS
	Value	Mode		Description
	0	DISABLED		Triggered compare and clear not enabled.
	1	LFA		Compare and clear performed on each (optionally prescaled) LFA clock cycle.
	2	PRS		Compare and clear performed on positive PRS edges.
15	EDGE	0	RW	Edge Select
				This bit should be written when PCNT is in DISABLE mode, otherwise the DVSSINGLE, EXTCLKSINGLE and OVSQUAD1X-4X modes.
	Value	Mode		Description
	0	POS		Positive edges on the PCNTn_S0IN inputs are counted in OVSSINGLE mode. Does not invert PCNTn_S1IN input in OVSSINGLE and EXTCLKSINGLE modes
	1	NEG		Negative edges on the PCNTn_S0IN inputs are counted in OVSSIN-GLE mode. Inverts the PCNTn_S1IN input in OVSSINGLE and EXTCLKSINGLE modes

Bit	Name	Reset	Access	Description					
14	CNTDIR	0	RW	Non-Quadrature Mode Counter Direction Control					
	The direction of the TCLKQUAD mode a			OVSSINGLE and EXTCLKSINGLE modes. This bit is ignored in EXally detected.					
	Value	Mode		Description					
	0	UP		Up counter mode.					
	1	DOWN		Down counter mode.					
13:12	AUXCNTEV	0x0	RW	Controls When the Auxiliary Counter Counts					
	Selects whether the	auxiliary counter	responds t	to up-count events, down-count events or both					
	Value	Mode		Description					
	0	NONE		Never counts.					
	1	UP		Counts up on up-count events.					
	2	DOWN		Counts up on down-count events.					
	3	вотн		Counts up on both up-count and down-count events.					
11:10	CNTEV	0x0	RW	Controls When the Counter Counts					
	Selects whether the regular counter responds to up-count events, down-count events or both								
	Value	Mode		Description					
	0	вотн		Counts up on up-count and down on down-count events.					
	1	UP		Only counts up on up-count events.					
	2	DOWN		Only counts down on down-count events.					
	3	NONE		Never counts.					
9	S1CDIR	0	RW	Count Direction Determined By S1					
				VSSINGLE or EXTCLKSINGLE modes. When S1 is high, the count directed to count direction is the opposite					
8	HYST	0	RW	Enable Hysteresis					
	When hysteresis is	enabled, the PCN	IT will alwa	ys overflow and underflow to TOP/2.					
7	DEBUGHALT	0	RW	Debug Mode Halt Enable					
	Set to halt the PCN ^T TCLKQUAD modes			SSINGLE and OVSQUAD modes. When in EXTCLKSINGLE or EXtitle Pulse Counter.					
	Value			Description					
	0			PCNT is running in debug mode.					
	1			PCNT is frozen in debug mode.					
6	AUXCNTRSTEN	0	RW	Enable AUXCNT Reset					
		ges after this bit is	cleared. I	sly held in reset when this bit is set. The reset is synchronously released f an external clock is used, the reset should be performed by setting and bit.					

Bit	Name	Reset	Access	Description
5	CNTRSTEN	0	RW	Enable CNT Reset
	edges after this b	oit is cleared. If a	n external clo	set when this bit is set. The reset is synchronously released two PCNT clock ock is used, the reset should be performed by setting and clearing the bit clears the counter to its reset value
4	RSTEN	0	RW	Enable PCNT Clock Domain Reset
		this bit is cleared	d. If an extern	in reset when this bit is set. The reset is synchronously released two PCNT all clock is used, the reset should be performed by setting and clearing the
3	FILT	0	RW	Enable Digital Pulse Width Filter
	The filter passes OVSSINGLE,OVS			e at least (FILTLEN+5) clock cycles wide. This filter is only available in
2:0	MODE	0x0	RW	Mode Select
	Selects the mode	of operation. The	corresponding	ng clock source must be selected from the CMU.
	Value	Mode		Description
	0	DISABLE		The module is disabled.
	1	DISABLE		
		OVSSINGL	E	Single input LFACLK oversampling mode (available in EM0-EM3).
	2			Single input LFACLK oversampling mode (available in EM0-EM3). Externally clocked single input counter mode (available in EM0-EM3).
	3	OVSSINGL	NGLE	
		OVSSINGL	NGLE JAD	Externally clocked single input counter mode (available in EM0-EM3).
	3	OVSSINGL EXTCLKSII EXTCLKQU	NGLE JAD 1X	Externally clocked single input counter mode (available in EM0-EM3). Externally clocked quadrature decoder mode (available in EM0-EM3). LFACLK oversampling quadrature decoder 1X mode (available in EM0-

16.5.2 PCNTn_CMD - Command Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	2	_	0
Reset		•				•		1		•		•			'	'	•		•		•			•					'		0	0
Access																															×	W1
Name																															LTOPBIM	LCNTIM

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	LTOPBIM	0	W1	Load TOPB Immediately
	This bit has no effect	since TOPB is r	ot buffered	and it is loaded directly into TOP.
0	LCNTIM	0	W1	Load CNT Immediately
	Load PCNTn_TOP in	to PCNTn_CNT	on the nex	ct counter clock cycle.

16.5.3 PCNTn_STATUS - Status Register

Offset															Bi	it Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	1	0
Reset		•	'			1				•	•	•	•			'	•				"	•				•	'		'			0
Access																																Ж
Name																																DIR

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	DIR	0	R	Current Counter Direction
	Current direction	n status of the coun	nter. This bit is	s valid in EXTCLKQUAD mode only.
	Value	Mode		Description
	0	UP		Up counter mode (clockwise in EXTCLKQUAD mode with the EDGE bit in PCNTn_CTRL set to 0).
	_	DOWN		Down counter mode.

16.5.4 PCNTn_CNT - Counter Value Register

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset				,																				0000	00000		•		•			
Access																								۵	۷							
Name																								Ę	5							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	CNT	0x0000	R	Counter Value
	Gives read access to	the counter.		

16.5.5 PCNTn_TOP - Top Value Register

Offset															Bi	t Po	sitio	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Reset			•	•	•		•	•	•				•	•		•		•	•	•	•			טאט	- 5000		•					
Access																								۵	_							
Name																								10 E	5							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	TOP	0x00FF	R	Counter Top Value
	When counting down PCNTn_CNT register			PCNTn_CNT when counting past 0. When counting up, 0 is written to the alue.

16.5.6 PCNTn_TOPB - Top Value Buffer Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset			1				•		1	·		1		1					ı					1100×0	10000		1			'		
Access																								2	<u> </u>							
Name																								AGOT	1 2 2							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co tions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	TOPB	0x00FF	RW	Counter Top Buffer
	Loaded automatically	to TOP when v	vritten.	

16.5.7 PCNTn_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	2	4	က	7	_	0
Reset																											0	0	0	0	0	0
Access																											~	22	22	~	~	2
																											ERR			ഗ		
Name																											⊢	22	AUXOF	JIRCN	노	H.
Nume																											OOS	TCC	AUXC	DIRC		PP

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
5	OQSTERR	0	R	Oversampling Quadrature State Error Interrupt
	Set in the Oversal	mpling Quadratur	e Mode wher	n incorrect state transition occurs
4	TCC	0	R	Triggered Compare Interrupt Read Flag
	Set upon triggered	d compare match		
3	AUXOF	0	R	Auxiliary Overflow Interrupt Read Flag
	Set when an Auxi	liary CNT overflow	w occurs	
2	DIRCNG	0	R	Direction Change Detect Interrupt Flag
	Set when the coul	nt direction chang	jes. Set in Ελ	CTCLKQUAD mode only.
1	OF	0	R	Overflow Interrupt Read Flag
	Set when a CNT of	overflow occurs		
0	UF	0	R	Underflow Interrupt Read Flag
	Set when a CNT u	underflow occurs		

16.5.8 PCNTn_IFS - Interrupt Flag Set Register

Offset	Bit Position																															
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																											0	0	0	0	0	0
Access																											W	W1	W	M1	W	W1
																											ERR			9		
Name																											OQSTE	22	AUXOF	IRCN	OF.	ш
																											0	Ţ	⋖		0	\supset

Bit	Name	Reset	Access	Description					
31:6	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-					
5	OQSTERR	0	W1	Set OQSTERR Interrupt Flag					
	Write 1 to set the OQ	STERR interrup	t flag						
4	TCC	0	W1	Set TCC Interrupt Flag					
	Write 1 to set the TCC	C interrupt flag							
3	AUXOF	0	W1	Set AUXOF Interrupt Flag					
	Write 1 to set the AUXOF interrupt flag								
2	DIRCNG	0	W1	Set DIRCNG Interrupt Flag					
	Write 1 to set the DIRCNG interrupt flag								
1	OF	0	W1	Set OF Interrupt Flag					
	Write 1 to set the OF interrupt flag								
0	UF	0	W1	Set UF Interrupt Flag					
	Write 1 to set the UF	interrupt flag							

16.5.9 PCNTn_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		•	•												•	•	•										0	0	0	0	0	0
Access																											(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name																											OQSTERR	TCC	AUXOF	DIRCNG	OF	UF

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
5	OQSTERR	0	(R)W1	Clear OQSTERR Interrupt Flag
		ne OQSTERR inte e must be enabled		eading returns the value of the IF and clears the corresponding interrupt MSC.).
4	TCC	0	(R)W1	Clear TCC Interrupt Flag
		ne TCC interrupt fl enabled globally in		returns the value of the IF and clears the corresponding interrupt flags (This
3	AUXOF	0	(R)W1	Clear AUXOF Interrupt Flag
		ne AUXOF interru _l st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
2	DIRCNG	0	(R)W1	Clear DIRCNG Interrupt Flag
		ne DIRCNG interro st be enabled glob		ding returns the value of the IF and clears the corresponding interrupt flags.
1	OF	0	(R)W1	Clear OF Interrupt Flag
		ne OF interrupt fla enabled globally in		eturns the value of the IF and clears the corresponding interrupt flags (This
0	UF	0	(R)W1	Clear UF Interrupt Flag
		ne UF interrupt flag enabled globally in	•	eturns the value of the IF and clears the corresponding interrupt flags (This

16.5.10 PCNTn_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																					1						0	0	0	0	0	0
Access																											S. ≷	RW	₽	RW	W.	RW
Name																											rerr		F.	NG		
Name																											OQST	TCC	AUXO	DIRC	PF	占

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	OQSTERR	0	RW	OQSTERR Interrupt Enable
	Enable/disable the O	QSTERR interru	pt	
4	TCC	0	RW	TCC Interrupt Enable
	Enable/disable the TO	CC interrupt		
3	AUXOF	0	RW	AUXOF Interrupt Enable
	Enable/disable the AU	JXOF interrupt		
2	DIRCNG	0	RW	DIRCNG Interrupt Enable
	Enable/disable the DI	RCNG interrupt		
1	OF	0	RW	OF Interrupt Enable
	Enable/disable the Of	= interrupt		
0	UF	0	RW	UF Interrupt Enable
	Enable/disable the UF	interrupt		

16.5.11 PCNTn_ROUTELOC0 - I/O Routing Location Register

10.5.11					_																									
Offset														Ві	it P	osi	tion											-		
0x02C	30	29	78	27	26	22	24	23	22	21	20	19	18	17	16	7.	4	13	12	7 =	9	0	ω ω	7	9	2	4	ო ი	_	0
Reset																					0x00							00×0		
Access																					 ≩							¥ M		
Name																					S1INLOC							SOINLOC		
Bit	Name					Re	set			Ac	ces	s	Des	crip	tio	n														
31:14	Reserv	red				To tior		ure	con	npat	ibilit	y w	ith fu	ıture	de	vice	es, al	way	s v	vrite	bits i	to C). Мо	re ir	nforn	natic	n in	1.2 Co	onve	en-
13:8	S1INLC	C				0x0	00			RV	٧		I/O	Loca	atio	n														
	Defines	s the	loca	atio	n of	the	PCI	NT S	S1IN	N inp	out p	in.																		
	Value					Мо	de						Des	cript	ion															
	0					LO	C0						Loca	atior	า 0															
	1					LO	C1						Loca	atior	1 1															
	2					LO	C2						Loca	atior	12															
	3					LO	СЗ						Loca	atior	1 3															
	4					LO	C4						Loca	atior	1 4															
	5					LO	C5						Loca	atior	า 5															
	6					LO	C6						Loca	atior	16															
	7					LO							Loca																	
	8					LO	C8						Loca	atior	า 8															
	9					LO	C9						Loca	atior	า 9															
	10					LO	C10)					Loca	atior	10)														
	11					LO	C11						Loca	atior	า 11															
	12					LO	C12	2					Loca	atior	12	2														
	13					LO	C13	3					Loca	atior	13	3														
	14					LO	C14						Loca																	
	15					LO	C15	5					Loca	atior	า 15	5														
	16					LO	C16	6					Loca	atior	16	6														
	17					LO	C17	'					Loca	atior	า 17	7														
	18					LO	C18	3					Loca	atior	18	3														
	19 LOC19												Loca	atior	19)														
	20					LO	C20)					Loca	atior	20)														
	21					LO	C21						Loca	atior	1 21															
	22					LO	C22	2					Loca	atior	1 22	2														

Bit	Name	Reset Acces	s Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
7:6	Reserved	To ensure compatibilit	y with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	SOINLOC	0x00 RW	I/O Location
	Defines the loca	tion of the PCNT S0IN input p	in.
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

Bit	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

16.5.12 PCNTn_FREEZE - Freeze Register

Offset															Ві	it Po	siti	on														
0x040	31	39	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset		•								•	•			•		•				•	•		•	•			•					0
Access																																₩ N
Name																																REGFREEZE

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	REGFREEZE	0	RW	Register Update Freeze
	When set, the updaters simultaneously		Clock domair	n is postponed until this bit is cleared. Use this bit to update several regis-
	Value	Modo		Description

Value	Mode	Description
0	UPDATE	Each write access to a PCNT register is updated into the Low Frequency domain as soon as possible.
1	FREEZE	The PCNT clock domain is not updated with the new written value.

16.5.13 PCNTn_SYNCBUSY - Synchronization Busy Register

Offset															Ві	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset						•	•		•				•							•					•	•	•	•	0	0	0	0
Access																													œ	2	22	ď
Name																													OVSCFG	TOPB	CMD	CTRL

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	OVSCFG	0	R	OVSCFG Register Busy
	Set when the value w	ritten to OVSCF	G is being	synchronized.
2	ТОРВ	0	R	TOPB Register Busy
	Set when the value w	ritten to TOPB i	s being syr	nchronized.
1	CMD	0	R	CMD Register Busy
	Set when the value w	ritten to CMD is	being synd	chronized.
0	CTRL	0	R	CTRL Register Busy
	Set when the value w	ritten to CTRL is	s being syn	chronized.

16.5.14 PCNTn_AUXCNT - Auxiliary Counter Value Register

Offset															Bi	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	ဗ	2	_	0
Reset		'					•	·	•			1	1					1	1		•		·	0	nnnxn	,						<u> </u>
Access																								מ	צ							
Name																								(AUXCIN							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	AUXCNT	0x0000	R	Auxiliary Counter Value
	Gives read access to	the auxiliary co	unter.	

16.5.15 PCNTn_INPUT - PCNT Input Register

	PCNTn_INPUT - PC		-		D:4 B	:4:												
Offset					Bit Pos		T	1		I			T	ı			1	
0x068	29 29 27 27	25 24 29 29	2 2 8	1 6 8 1	7 9	5 4	13	12	11	9	တ ထ		9	2	4	w 0		
Reset									0			000		0			Š	
Access									RW			Ϋ́		₽			≷ Ƴ	
									Z			Ä		z			žEL	
Name									S1PRSEN			S1PRSSEL		SOPRSEN			SOPRSSEL	
									S			S		S			ກ 	_
Bit	Name	Reset	Acce	ss Desc	ription													
31:12	Reserved	To ensure co	ompatibil	ity with futu	ıre devi	ces, a	lway	's wr	ite b	its t	o 0. M	ore ir	nforn	natio	on in	1.2 Cd	nve	n-
11	S1PRSEN	0	RW	S1IN	PRS Er	able												
	When set, the PR	S channel is selec	ted as in	put to S1IN	l													
10	Reserved	To ensure co	ompatibil	ity with futu	ıre devi	ces, a	lway	s wr	ite b	its t	o 0. M	ore ir	nforn	natio	on in	1.2 Co	nve	n-
9:6	S1PRSSEL	0x0	RW	S1IN	PRS CI	nanne	l Se	lect										
	Select PRS chann	nel as input to S1IN	٧.															
	Value	Mode		Descr	iption													
	0	PRSCH0		PRS (Channe	l 0 sel	lecte	d.										
	1	PRSCH1		PRS (Channe	l 1 sel	lecte	d.										
	2	PRSCH2		PRS (Channe	l 2 sel	lecte	d.										
	3	PRSCH3		PRS (Channe	l 3 sel	lecte	d.										
	4	PRSCH4		PRS (Channe	l 4 sel	lecte	d.										
	5	PRSCH5		PRS (Channe	l 5 sel	ecte	d.										
	6	PRSCH6		PRS (Channe	l 6 sel	ecte	d.										
	7	PRSCH7		PRS (Channe	l 7 sel	ecte	d.										
	8	PRSCH8		PRS (Channe	l 8 sel	ecte	d.										
	9	PRSCH9		PRS (Channe	l 9 sel	lecte	d.										
	10	PRSCH10		PRS (Channe	l 10 s	elect	ed.										
	11	PRSCH11		PRS (Channe	l 11 s	elect	ed.										
5	SOPRSEN	0	RW	SOIN	PRS Er	able												
	When set, the PR	S channel is selec	ted as in	put to SOIN	l.													
4	Reserved	To ensure co	ompatibil	ity with futu	ıre devi	ces, a	lway	's wr	ite b	its t	o 0. M	ore ir	nforn	natio	on in	1.2 Co	nve	n-
3:0	S0PRSSEL	0x0	RW	SOIN	PRS CI	nanne	l Se	lect										
	Select PRS chann	nel as input to SOIN	٧.															
	Value	Mode		Descr	iption													_

Bit	Name	Reset	Access	Description
	0	PRSCH0		PRS Channel 0 selected.
	1	PRSCH1		PRS Channel 1 selected.
	2	PRSCH2		PRS Channel 2 selected.
	3	PRSCH3		PRS Channel 3 selected.
	4	PRSCH4		PRS Channel 4 selected.
	5	PRSCH5		PRS Channel 5 selected.
	6	PRSCH6		PRS Channel 6 selected.
	7	PRSCH7		PRS Channel 7 selected.
	8	PRSCH8		PRS Channel 8 selected.
	9	PRSCH9		PRS Channel 9 selected.
	10	PRSCH10		PRS Channel 10 selected.
	11	PRSCH11		PRS Channel 11 selected.

16.5.16 PCNTn_OVSCFG - Oversampling Config Register (Async Reg)


For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	t Po	siti	on													
0x06C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	5	4	က	2	- 0
Reset			•													•	•	•		0								0	0000		
Access																				Σ								i	≷		
Name																				FLUTTERRM								į	Z L L L		

Bit	Name	Reset	Access	Description
31:13	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
12	FLUTTERRM	0	RW	Flutter Remove
	When set, remove	s flutter from Qu	uaddecoder in	puts S0IN and S1IN. Available only in OVSQUAD1X-4X modes
11:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	FILTLEN	0x00	RW	Configure Filter Length for Inputs S0IN and S1IN
	Used only in OVSI (FILTLEN + 5) LFA		AD1X-4X mod	des. To use this first enable FILT in PCNTn_CTRL register. Filter length =

17. I2C - Inter-Integrated Circuit Interface





Quick Facts

What?

The I²C interface allows communication on I²C-buses with the lowest energy consumption possible.

Why?

I²C is a popular serial bus that enables communication with a number of external devices using only two I/O pins.

How?

With the help of DMA, the I 2 C interface allows I 2 C communication with minimal CPU intervention. Address recognition is available in all energy modes (except EM4), allowing the MCU to wait for data on the I 2 C-bus with sub- μ A current consumption.

17.1 Introduction

The I^2C module provides an interface between the MCU and a serial I^2C -bus. It is capable of acting as both a master and a slave and supports multi-master buses. Standard-mode, fast-mode and fast-mode plus speeds are supported, allowing transmission rates all the way from 10 kbit/s up to 1 Mbit/s. Slave arbitration and timeouts are also provided to allow implementation of an SMBus compliant system. The interface provided to software by the I^2C module allows precise control of the transmission process and highly automated transfers. Automatic recognition of slave addresses is provided in all energy modes (except EM4).

17.2 Features

- · True multi-master capability
- · Support for different bus speeds
 - · Standard-mode (Sm) bit rate up to 100 kbit/s
 - · Fast-mode (Fm) bit rate up to 400 kbit/s
 - · Fast-mode Plus (Fm+) bit rate up to 1 Mbit/s
- · Arbitration for both master and slave (allows SMBus ARP)
- · Clock synchronization and clock stretching
- · Hardware address recognition
 - · 7-bit masked address
 - · General call address
 - Active in all energy modes (except EM4)
- · 10-bit address support
- · Error handling
 - · Clock low timeout
 - · Clock high timeout
 - · Arbitration lost
 - · Bus error detection
- · Separate receive/ transmit 2-level buffers, with additional separate shift registers
- Full DMA support

17.3 Functional Description

An overview of the I2C module is shown in Figure 17.1 I2C Overview on page 478.




Figure 17.1. I2C Overview

17.3.1 I2C-Bus Overview

The I²C-bus uses two wires for communication; a serial data line (SDA) and a serial clock line (SCL) as shown in Figure 17.2 I2C-Bus Example on page 479. As a true multi-master bus it includes collision detection and arbitration to resolve situations where multiple masters transmit data at the same time without data loss.




Figure 17.2. I2C-Bus Example

Each device on the bus is addressable by a unique address, and an I²C master can address all the devices on the bus, including other masters.

Both the bus lines are open-drain. The maximum value of the pull-up resistor can be calculated as a function of the maximal rise-time **tr** for the given bus speed, and the estimated bus capacitance **Cb** as shown in Figure 17.3 I2C Pull-up Resistor Equation on page 479.

$$Rp(max) = t_r / (0.8473 \times Cb)$$

Figure 17.3. I2C Pull-up Resistor Equation

The maximal rise times for 100 kHz, 400 kHz and 1 MHz I²C are 1 µs, 300 ns and 120 ns respectively.

Note:

- · The GPIO drive strength can be used to control slew rate.
- If V_{dd} drops below the voltage on SCL and SDA lines, the MCU could become back powered and pull the SCL and SDA lines low.

17.3.1.1 START and STOP Conditions

START and STOP conditions are used to initiate and stop transactions on the I²C-bus. All transactions on the bus begin with a START condition (S) and end with a STOP condition (P). As shown in Figure 17.4 I2C START and STOP Conditions on page 480, a START condition is generated by pulling the SDA line low while SCL is high, and a STOP condition is generated by pulling the SDA line high while SCL is high.




Figure 17.4. I2C START and STOP Conditions

The START and STOP conditions are easily identifiable bus events as they are the only conditions on the bus where a transition is allowed on SDA while SCL is high. During the actual data transmission, SDA is only allowed to change while SCL is low, and must be stable while SCL is high. One bit is transferred per clock pulse on the I²C-bus as shown in Figure 17.5 I2C Bit Transfer on I²C-Bus on page 480.




Figure 17.5. I2C Bit Transfer on I²C-Bus

17.3.1.2 Bus Transfer

When a master wants to initiate a transfer on the bus, it waits until the bus is idle and transmits a START condition on the bus. The master then transmits the address of the slave it wishes to interact with and a single R/W bit telling whether it wishes to read from the slave (R/W bit set to 1) or write to the slave (R/W bit set to 0).

After the 7-bit address and the R/W bit, the master releases the bus, allowing the slave to acknowledge the request. During the next bit-period, the slave pulls SDA low (ACK) if it acknowledges the request, or keeps it high if it does not acknowledge it (NACK).

Following the address acknowledge, either the slave or master transmits data, depending on the value of the R/W bit. After every 8 bits (one byte) transmitted on the SDA line, the transmitter releases the line to allow the receiver to transmit an ACK or a NACK. Both the data and the address are transmitted with the most significant bit first.

The number of bytes in a bus transfer is unrestricted. The master ends the transmission after a (N)ACK by sending a STOP condition on the bus. After a STOP condition, any master wishing to initiate a transfer on the bus can try to gain control of it. If the current master wishes to make another transfer immediately after the current, it can start a new transfer directly by transmitting a repeated START condition (Sr) instead of a STOP followed by a START.

Examples of I²C transfers are shown in Figure 17.6 I2C Single Byte Write to Slave on page 481, Figure 17.7 I2C Double Byte Read from Slave on page 481, and Figure 17.8 I2C Single Byte Write, then Repeated Start and Single Byte Read on page 481. The identifiers used are:

- · ADDR Address
- · DATA Data
- · S Start bit
- · Sr Repeated start bit
- · P Stop bit
- W/R Read(1)/Write(0)
- A ACK
- N NACK



Figure 17.6. I2C Single Byte Write to Slave



Figure 17.7. I2C Double Byte Read from Slave



Figure 17.8. I2C Single Byte Write, then Repeated Start and Single Byte Read

17.3.1.3 Addresses

 I^2C supports both 7-bit and 10-bit addresses. When using 7-bit addresses, the first byte transmitted after the START-condition contains the address of the slave that the master wants to contact. In the 7-bit address space, several addresses are reserved. These addresses are summarized in Table 17.1 I2C Reserved I^2C Addresses on page 482, and include a General Call address which can be used to broadcast a message to all slaves on the I^2C -bus.

Table 17.1. I2C Reserved I²C Addresses

I ² C Address	R/W	Description
0000-000	0	General Call address
0000-000	1	START byte
0000-001	x	Reserved for the C-Bus format
0000-010	x	Reserved for a different bus format
0000-011	x	Reserved for future purposes
0000-1XX	x	Reserved for future purposes
1111-1XX	x	Reserved for future purposes
1111-0XX	X	10 Bit slave addressing mode

17.3.1.4 10-bit Addressing

To address a slave using a 10-bit address, two bytes are required to specify the address instead of one. The seven first bits of the first byte must then be 1111 0XX, where XX are the two most significant bits of the 10-bit address. As with 7-bit addresses, the eighth bit of the first byte determines whether the master wishes to read from or write to the slave. The second byte contains the eight least significant bits of the slave address.

When a slave receives a 10-bit address, it must acknowledge both the address bytes if they match the address of the slave.

When performing a master transmitter operation, the master transmits the two address bytes and then the remaining data, as shown in Figure 17.9 I2C Master Transmitter/Slave Receiver with 10-bit Address on page 482.




Figure 17.9. I2C Master Transmitter/Slave Receiver with 10-bit Address

When performing a master receiver operation however, the master first transmits the two address bytes in a master transmitter operation, then sends a repeated START followed by the first address byte and then receives data from the addressed slave. The slave addressed by the 10-bit address in the first two address bytes must remember that it was addressed, and respond with data if the address transmitted after the repeated start matches its own address. An example of this (with one byte transmitted) is shown in Figure 17.10 I2C Master Receiver/Slave Transmitter with 10-bit Address on page 482.




Figure 17.10. I2C Master Receiver/Slave Transmitter with 10-bit Address

17.3.1.5 Arbitration, Clock Synchronization, Clock Stretching

Arbitration and clock synchronization are features aimed at allowing multi-master buses. Arbitration occurs when two devices try to drive the bus at the same time. If one device drives it low, while the other drives it high, the one attempting to drive it high will not be able to do so due to the open-drain bus configuration. Both devices sample the bus, and the one that was unable to drive the bus in the desired direction detects the collision and backs off, letting the other device continue communication on the bus undisturbed.

Clock synchronization is a means of synchronizing the clock outputs from several masters driving the bus at once, and is a requirement for effective arbitration.

Slaves on the bus are allowed to force the clock output on the bus low in order to pause the communication on the bus and give themselves time to process data or perform any real-time tasks they might have. This is called clock stretching.

Arbitration is supported by the I²C module for both masters and slaves. Clock synchronization and clock stretching is also supported.

17.3.2 Enable and Reset

The I^2C is enabled by setting the EN bit in the I^2C is reset, terminating any ongoing transfers.

Note: When enabling the I²C, the ABORT command or the Bus Idle Timeout feature must be applied prior to use even if the BUSY flag is not set.

17.3.3 Safely Disabling and Changing Slave Configuration

The I²C slave is partially asynchronous, and some precautions are necessary to always ensure a safe slave disable or slave configuration change. These measures should be taken, if (while the slave is enabled) the user cannot guarantee that an address match will not occur at the exact time of slave disable or slave configuration change.

Worst case consequences for an address match while disabling slave or changing configuration is that the slave may end up in an undefined state. To reset the slave back to a known state, the EN bit in I2Cn_CTRL must be reset. This should be done regardless of whether the slave is going to be re-enabled or not.

17.3.4 Clock Generation

The SCL signal generated by the I²C master determines the maximum transmission rate on the bus. The clock is generated as a division of the peripheral clock, and is given by the following equation:

$$f_{SCL} = f_{HFPERCLK}/(((N_{low} + N_{high}) \times (DIV + 1)) + 8),$$

Figure 17.11. I2C Maximum Transmission Rate

 N_{low} and N_{high} in combination with the synchronization cycles (discussed below) specify the number of prescaled clock cycles in the low and high periods of the clock signal respectively. The worst case low and high periods of the signal are:

$$T_{high} >= ((N_{high}) \times (DIV + 1) + 4)/f_{HFPERCLK},$$

$$T_{low} >= (N_{low} \times (DIV + 1) + 4)/f_{HFPERCLK}.$$

Figure 17.12. I2C High and Low Cycles Equations

In worst case, T_{high} and T_{low} can be 1 $f_{HFPERCLK}$ cycle longer than the number found by above equations due to synchronization uncertainity (i.e., if the synchronization takes 3 $f_{HFPERCLK}$ cycles instead of 2). Similarly, in the worst case the number 8 in the denominator in f_{SCL} equation can be 9 (if the synchronization cycles were 3 instead of 2 in T_{high} or T_{low}) or 10 (if synchronization cycles were 3 in both T_{high} and T_{low}). The values of N_{low} and N_{high} and thus the ratio between the high and low parts of the clock signal is controlled by CLHR in the I2Cn_CTRL register.

Note: DIV must be set to 1 during slave mode operation.

17.3.5 Arbitration

Arbitration is enabled by default, but can be disabled by setting the ARBDIS bit in I2Cn_CTRL. When arbitration is enabled, the value on SDA is sensed every time the I^2C module attempts to change its value. If the sensed value is different than the value the I^2C module tried to output, it is interpreted as a simultaneous transmission by another device, and that the I^2C module has lost arbitration.

Whenever arbitration is lost, the ARBLOST interrupt flag in $I2Cn_IF$ is set, any lines held are released, and the I^2C device goes idle. If an I^2C master loses arbitration during the transmission of an address, another master may be trying to address it. The master therefore receives the rest of the address, and if the address matches the slave address of the master, the master goes into either slave transmitter or slave receiver mode.

Note: Arbitration can be lost both when operating as a master and when operating as a slave.

17.3.6 Buffers

The I2C peripheral includes separate receive and transmit buffers and shift registers.

17.3.6.1 Transmit Buffer and Shift Register

The I²C transmitter has a 2-level FIFO transmit buffer and a transmit shift register as shown in Figure 17.1 I2C Overview on page 478. A byte is loaded into the transmit buffer by writing to I2Cn_TXDATA or 2 bytes can be loaded simultaneously in the transmit buffer by writing to I2Cn_TXDOUBLE. Figure 17.13 I2C Transmit Buffer Operation on page 484 shows the basics of the transmit buffer. When the transmit shift register is empty and ready for new data, the byte from the transmit buffer is then loaded into the shift register. The byte is then kept in the shift register until it is transmitted. When a byte has been transmitted, a new byte is loaded into the shift register (if available in the transmit buffer). If the transmit buffer is empty, then the shift register also remains empty. The TXC flag in I2Cn_STA-TUS and the TXC interrupt flags in I2Cn_IF are then set, signaling that the transmit shift register is out of data. TXC is cleared when new data becomes available, but the TXC interrupt flag must be cleared by software.




Figure 17.13. I2C Transmit Buffer Operation

The TXBL flags in the I2Cn_STATUS and I2Cn_IF are used to indicate the level of the transmit buffer. TXBIL in I2Cn_CTRL controls the level at which these flag bits are set. If TXBIL is cleared, the flags are set whenever the transmit buffer becomes empty (used when transmitting using I2Cn_TXDOUBLE). If TXBIL is set, the flags are set whenever the transmit buffer goes from full to half-empty or empty (used when transmitting with I2Cn_TXDATA). Both the TXBL status flag and the TXBL interrupt flag are cleared automatically when the condition becomes false.

If an attempt is made to write more bytes to the transmit buffer than the space available, the TXOF interrupt flag in I2Cn_IF is set, indicating the overflow. The data already in the buffer remains preserved, and no new data is written.

The transmit buffer and the transmit shift register can be cleared by setting command bit CLEARTX in I2Cn_CMD. This will prevent the I²C module from transmitting the data in the buffer and the shift register, and will make them available for new data. Any byte currently being transmitted will not be aborted. Transmission of this byte will be completed.

17.3.6.2 Receive Buffer and Shift Register

The I²C receiver uses a 2-level FIFO receive buffer and a receive shift register as shown in Figure 17.14 I2C Receive Buffer Operation on page 485. When a byte has been fully received by the receive shift register, it is loaded into the receive buffer if there is room for it, making the shift register empty to receive another byte. Otherwise, the byte waits in the shift register until space becomes available in the buffer.




Figure 17.14. I2C Receive Buffer Operation

When a byte becomes available in the receive buffer, the RXDATAV in I2Cn_STATUS and RXDATAV interrupt flag in I2Cn_IF are set. When the buffer becomes full, RXFULL in the I2Cn_STATUS and I2Cn_IF are set. The status flags RXDATAV and RXFULL are automatically cleared by hardware when their condition is no longer true. This also goes for the RXDATAV interrupt flag, but the RXFULL interrupt flag must be cleared by software. When the RXFULL flag is set, notifying that the buffer is full, space is still available in the receive shift register for one more byte.

The data can be fetched from the buffer in two ways. I2Cn_RXDATA gives access to the received byte (if two bytes are received then the one received first is fetched first). I2Cn_RXDOUBLE makes it possible to read the two received bytes simultaneously. If an attempt is made to read more bytes from the buffer than available, the RXUF interrupt flag in I2Cn_IF is set to signal the underflow, and the data read from the buffer is undefined.

When using I2Cn_RXDOUBLE to pick data, AUTOACK in I2Cn_CTRL should be set to 1. This ensures that an ACK is automatically sent out after the first byte is received so that the reception of the next byte can begin. In order to stop receiving data bytes, a NACK must be sent out through the I2Cn_CMD register.

I2Cn_RXDATAP and I2Cn_RXDOUBLEP can be used to read data from the receive buffer without removing it from the buffer. The RXUF interrupt flag in I2Cn_IF will never be set as a result of reading from I2Cn_RXDATAP and I2Cn_RXDOUBLEP, but the data read through I2Cn_RXDATAP when the receive buffer is empty is still undefined.

Once a transaction is complete (STOP sent or received), the receive buffer needs to be flushed (all received data must be read) before starting a new transaction.

17.3.7 Master Operation

A bus transaction is initiated by transmitting a START condition (S) on the bus. This is done by setting the START bit in I2Cn_CMD. The command schedules a START condition, and makes the I²C module generate a start condition whenever the bus becomes free.

The I²C-bus is considered busy whenever another device on the bus transmits a START condition. Until a STOP condition is detected, the bus is owned by the master issuing the START condition. The bus is considered free when a STOP condition is transmitted on the bus. After a STOP is detected, all masters that have data to transmit send a START condition and begin transmitting data. Arbitration ensures that collisions are avoided.

When the START condition has been transmitted, the master must transmit a slave address (ADDR) with an R/W bit on the bus. If this address is available in the transmit buffer, the master transmits it immediately, but if the buffer is empty, the master holds the I²C-bus while waiting for software to write the address to the transmit buffer.

After the address has been transmitted, a sequence of bytes can be read from or written to the slave, depending on the value of the R/W bit (bit 0 in the address byte). If the bit was cleared, the master has entered a master transmitter role, where it now transmits data to the slave. If the bit was set, it has entered a master receiver role, where it now should receive data from the slave. In either case, an unlimited number of bytes can be transferred in one direction during the transmission.

At the end of the transmission, the master either transmits a repeated START condition (Sr) if it wishes to continue with another transfer, or transmits a STOP condition (P) if it wishes to release the bus. When operating in the master mode, HFPERCLK frequency must be higher than 2 MHz for Standard-mode, 9 MHz for Fast-mode, and 20 MHz for Fast-mode Plus.

17.3.7.1 Master State Machine

The master state machine is shown in Figure 17.15 I2C Master State Machine on page 487. A master operation starts in the far left of the state machine, and follows the solid lines through the state machine, ending the operation or continuing with a new operation when arriving at the right side of the state machine.

Branches in the path through the state machine are the results of bus events and choices made by software, either directly or indirectly. The dotted lines show where I²C-specific interrupt flags are set along the path and the full-drawn circles show places where interaction may be required by software to let the transmission proceed.




Figure 17.15. I2C Master State Machine

17.3.7.2 Interactions

Whenever the I^2C module is waiting for interaction from software, it holds the bus clock SCL low, freezing all bus activities, and the BUSHOLD interrupt flag in I^2Cn_IF is set. The action(s) required by software depends on the current state the of the I^2C module. This state can be read from the I^2Cn_IF state can be read from the I^2Cn_IF register.

As an example, Table 17.3 I2C Master Transmitter on page 490 shows the different states the I²C goes through when operating as a Master Transmitter, i.e., a master that transmits data to a slave. As seen in the table, when a start condition has been transmitted, a requirement is that there is an address and an R/W bit in the transmit buffer. If the transmit buffer is empty, then the BUSHOLD interrupt flag is set, and the bus is held until data becomes available in the buffer. While waiting for the address, I2Cn_STATE has a value 0x57, which can be used to identify exactly what the I²C module is waiting for.

Note: The bus would never stop at state 0x57 if the address was available in the transmit buffer.

The different interactions used by the I^2C module are listed in Table 17.2 I2C Interactions in Prioritized Order on page 488 in a prioritized order. If the I^2C module is in such a state that multiple courses of action are possible, then the action chosen is the one that has the highest priority. For example, after sending out a START, if an address is present in the buffer and a STOP is also pending, then the I^2C will send out the STOP since it has the higher priority.

Table 17.2. I2C Interactions in Prioritized Order

Interaction	Priority	Software action	Automatically continues if
STOP*	1	Set the STOP command bit in I2Cn_CMD	PSTOP is set (STOP pending) in I2Cn_STATUS
ABORT	2	Set the ABORT command bit in I2Cn_CMD	Never, the transmission is aborted
CONT*	3	Set the CONT command bit in I2Cn_CMD	PCONT is set in I2Cn_STATUS (CONT pending)
NACK*	4	Set the NACK command bit in I2Cn_CMD	PNACK is set in I2Cn_STATUS (NACK pending)
ACK*	5	Set the ACK command bit in I2Cn_CMD	AUTOACK is set in I2Cn_CTRL or PACK is set in I2Cn_STA-TUS (ACK pending)
ADDR+W -> TXDATA	6	Write an address to the transmit buffer with the R/W bit set	Address is available in transmit buffer with R/W bit set
ADDR+R -> TXDATA	7	Write an address to the transmit buffer with the R/W bit cleared	Address is available in transmit buffer with R/W bit cleared
START*	8	Set the START command bit in I2Cn_CMD	PSTART is set in I2Cn_STA- TUS (START pending)
TXDATA/ TXDOUBLE	9	Write data to the transmit buffer	Data is available in transmit buf- fer
RXDATA/ RXDOUBLE	10	Read data from receive buffer	Space is available in receive buffer
None	11	No interaction is required	

The commands marked with a * in Table 17.2 I2C Interactions in Prioritized Order on page 488 can be issued before an interaction is required. When such a command is issued before it can be used/consumed by the I²C module, the command is set in a pending state, which can be read from the STATUS register. A pending START command can for instance be identified by PSTART having a high value.

Whenever the I²C module requires an interaction, it checks the pending commands. If one or a combination of these can fulfill an interaction, they are consumed by the module and the transmission continues without setting the BUSHOLD interrupt flag in I2Cn_IF to get an interaction from software. The pending status of a command goes low when it is consumed.

When several interactions are possible from a set of pending commands, the interaction with the highest priority, i.e., the interaction closest to the top of Table 17.2 I2C Interactions in Prioritized Order on page 488 is applied to the bus.

Pending commands can be cleared by setting the CLEARPC command bit in I2Cn_CMD.

17.3.7.3 Automatic ACK Interaction

When receiving addresses and data, an ACK command in I2Cn_CMD is normally required after each received byte. When AUTOACK is set in I2Cn_CTRL, an ACK is always pending, and the ACK-pending bit PACK in I2Cn_STATUS is thus always set, even after an ACK has been consumed. This is used when data is picked using I2Cn_RXDOUBLE and can also be used with I2Cn_RXDATA in order to reduce the amount of software interaction required during a transfer.

17.3.7.4 Reset State

After a reset, the state of the I^2C -bus is unknown. To avoid interrupting transfers on the I^2C -bus after a reset of the I^2C module or the entire MCU, the I^2C -bus is assumed to be busy when coming out of a reset, and the BUSY flag in I^2C -bus is thus set. To be able to carry through master operations on the I^2C -bus, the bus must be idle.

The bus goes idle when a STOP condition is detected on the bus, but on buses with little activity, the time before the I^2C module detects that the bus is idle can be significant. There are two ways of assuring that the I^2C module gets out of the busy state.

- Use the ABORT command in I2Cn_CMD. When the ABORT command is issued, the I²C module is instructed that the bus is idle. The I²C module can then initiate master operations.
- Use the Bus Idle Timeout. When SCL has been high for a long period of time, it is very likely that the bus is idle. Set BITO in I2Cn_CTRL to an appropriate timeout period and set GIBITO in I2Cn_CTRL. If activity has not been detected on the bus within the timeout period, the bus is then automatically assumed idle, and master operations can be initiated.

Note: If operating in slave mode, the above approach is not necessary.

17.3.7.5 Master Transmitter

To transmit data to a slave, the master must operate as a master transmitter. Table 17.3 I2C Master Transmitter on page 490 shows the states the I²C module goes through while acting as a master transmitter. Every state where an interaction is required has the possible interactions listed, along with the result of the interactions. The table also shows which interrupt flags are set in the different states. The interrupt flags enclosed in parenthesis may be set. If the BUSHOLD interrupt in I2Cn_IF is set, the module is waiting for an interaction, and the bus is frozen. The value of I2Cn_STATE will be equal to the values given in the table when the BUSHOLD interrupt flag is set, and can be used to determine which interaction is required to make the transmission continue.

The interrupt flag START in I2Cn_IF is set when the I²C module transmits the START.

A master operation is started by issuing a START command by setting START in I2Cn_CMD. ADDR+W, i.e., the address of the slave + the R/W bit is then required by the I^2C module. If this is not available in the transmit buffer, then the bus is held and the BUSHOLD interrupt flag is set. The value of I2Cn_STATE will then be 0x57. As seen in the table, the I^2C module also stops in this state if the address is not available after a repeated start condition.

To continue, write a byte to I2Cn_TXDATA with the address of the slave in the 7 most significant bits and the least significant bit cleared (ADDR+W). This address will then be transmitted, and the slave will reply with an ACK or a NACK. If no slave replies to the address, the response will also be NACK. If the address was acknowledged, the master now has four choices. It can send data by placing it in I2Cn_TXDATA/ I2Cn_TXDOUBLE (the master should check the TXBL interrupt flag before writing to the transmit buffer), this data is then transmitted. The master can also stop the transmission by sending a STOP, it can send a repeated start by sending START, or it can send a STOP and then a START as soon as possible. If the master wishes to make another transfer immediately after the current, the preferred way is to start a new transfer directly by transmitting a repeated START instead of a STOP followed by a START. This is so because if a STOP is sent out, then any master wishing to initiate a transfer on the bus can try to gain control of it.

If a NACK was received, the master has to issue a CONT command in addition to providing data in order to continue transmission. This is not standard I²C, but is provided for flexibility. The rest of the options are similar to when an ACK was received.

If a new byte was transmitted, an ACK or NACK is received after the transmission of the byte, and the master has the same options as for when the address was sent.

The master may lose arbitration at any time during transmission. In this case, the ARBLOST interrupt flag in I2Cn_IF is set. If the arbitration was lost during the transfer of an address, and SLAVE in I2Cn_CTRL is set, the master then checks which address was transmitted. If it was the address of the master, then the master goes to slave mode.

After a master has transmitted a START and won any arbitration, it owns the bus until it transmits a STOP. After a STOP, the bus is released, and arbitration decides which bus master gains the bus next. The MSTOP interrupt flag in I2Cn_IF is set when a STOP condition is transmitted by the master.

Table 17.3. I2C Master Transmitter

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
0x57	Start transmitted	START interrupt flag (BUSHOLD interrupt	ADDR+W -> TXDATA	ADDR+W will be sent
		flag)	STOP	STOP will be sent and bus released.
			STOP + START	STOP will be sent and bus released. Then a START will be sent when bus becomes idle.
0x57	Repeated start trans- mitted	START interrupt flag (BUSHOLD interrupt	ADDR+W -> TXDATA	ADDR+W will be sent
		flag)	STOP	STOP will be sent and bus released.
			STOP + START	STOP will be sent and bus released. Then a START will be sent when bus becomes idle.
-	ADDR+W transmitted	TXBL interrupt flag (TXC interrupt flag)	None	

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
0x97	ADDR+W transmitted,	ACK interrupt flag	TXDATA	DATA will be sent
	ACK received	(BUSHOLD interrupt flag)	STOP	STOP will be sent. Bus will be released
			START	Repeated start condition will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle
0x9F	ADDR+W transmit- ted,NACK received	NACK (BUSHOLD interrupt flag)	CONT + TXDATA	DATA will be sent
			STOP	STOP will be sent. Bus will be released
			START	Repeated start condition will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle
-	Data transmitted	TXBL interrupt flag (TXC interrupt flag)	None	
0xD7	Data transmitted,ACK	ACK interrupt flag	TXDATA	DATA will be sent
	received	(BUSHOLD interrupt flag)	STOP	STOP will be sent. Bus will be released
			START	Repeated start condition will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle
0xDF	Data transmitted,NACK received	NACK(BUSHOLD interrupt flag)	CONT + TXDATA	DATA will be sent
			STOP	STOP will be sent. Bus will be released
			START	Repeated start condition will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle
-	Stop transmitted	MSTOP interrupt flag	None	
			START	START will be sent when bus becomes idle
-	Arbitration lost	ARBLOST interrupt flag	None	
			START	START will be sent when bus becomes idle

17.3.7.6 Master Receiver

To receive data from a slave, the master must operate as a master receiver, see Table 17.4 I2C Master Receiver on page 492. This is done by transmitting ADDR+R as the address byte instead of ADDR+W, which is transmitted to become a master transmitter. The address byte loaded into the data register thus has to contain the 7-bit slave address in the 7 most significant bits of the byte, and have the least significant bit set.

When the address has been transmitted, the master receives an ACK or a NACK. If an ACK is received, the ACK interrupt flag in I2Cn_IF is set, and if space is available in the receive shift register, reception of a byte from the slave begins. If the receive buffer and shift register is full however, the bus is held until data is read from the receive buffer or another interaction is made. Note that the STOP and START interactions have a higher priority than the data-available interaction, so if a STOP or START command is pending, the highest priority interaction will be performed, and data will not be received from the slave.

If a NACK was received, the CONT command in I2Cn_CMD has to be issued in order to continue receiving data, even if there is space available in the receive buffer and/or shift register.

After a data byte has been received the master must ACK or NACK the received byte. If an ACK is pending or AUTOACK in I2Cn_CTRL is set, an ACK is sent automatically and reception continues if space is available in the receive buffer.

If a NACK is sent, the CONT command must be used in order to continue transmission. If an ACK or NACK is issued along with a START or STOP or both, then the ACK/NACK is transmitted and the reception is ended. If START in I2Cn_CMD is set alone, a repeated start condition is transmitted after the ACK/NACK. If STOP in I2Cn_CMD is set, a stop condition is sent regardless of whether START is set. If START is set in this case, it is set as pending.

As when operating as a master transmitter, arbitration can be lost as a master receiver. When this happens the ARBLOST interrupt flag in I2Cn_IF is set, and the master has a possibility of being selected as a slave given the correct conditions.

Table 17.4. I2C Master Receiver

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
0x57	START transmitted	START interrupt flag (BUSHOLD interrupt	ADDR+R -> TXDATA	ADDR+R will be sent
		flag)	STOP	STOP will be sent and bus released.
			STOP + START	STOP will be sent and bus released. Then a START will be sent when bus becomes idle.
0x57	Repeated START transmitted	START interrupt flag(BUSHOLD inter-	ADDR+R -> TXDATA	ADDR+R will be sent
		rupt flag)	STOP	STOP will be sent and bus released.
			STOP + START	STOP will be sent and bus released. Then a START will be sent when bus becomes idle.
-	ADDR+R transmitted	TXBL interrupt flag (TXC interrupt flag)	None	
0x93	ADDR+R transmitted,	ACK interrupt flag(BUS-	RXDATA	Start receiving
	ACK received	HOLD)	STOP	STOP will be sent and the bus released
			START	Repeated START will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle
0x9B	ADDR+R transmit- ted,NACK received	NACK(BUSHOLD)	CONT + RXDATA	Continue, start receiving
			STOP	STOP will be sent and the bus released
			START	Repeated START will be sent
			STOP + START	STOP will be sent and the bus released. Then a START will be sent when the bus becomes idle

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
0xB3	Data received	RXDATA interrupt flag(BUSHOLD inter-	ACK + RXDA- TA	ACK will be transmitted, reception continues
		rupt flag)	NACK + CONT + RXDATA	NACK will be transmitted, reception continues
			ACK/NACK + STOP	ACK/NACK will be sent and the bus will be released.
			ACK/NACK + START	ACK/NACK will be sent, and then a repeated start condition.
			ACK/NACK + STOP + START	ACK/NACK will be sent and the bus will be released. Then a START will be sent when the bus becomes idle
-	Stop received	MSTOP interrupt flag	None	
			START	START will be sent when bus becomes idle
-	Arbitration lost	ARBLOST interrupt flag	None	
			START	START will be sent when bus becomes idle

17.3.8 Bus States

The I2Cn_STATE register can be used to determine which state the I^2C module and the I^2C bus are in at a given time. The register consists of the STATE bit-field, which shows which state the I^2C module is at in any ongoing transmission, and a set of single-bits, which reveal the transmission mode, whether the bus is busy or idle, and whether the bus is held by this I^2C module waiting for a software response.

The possible values of the STATE field are summarized in Table 17.5 I2C STATE Values on page 494. When this field is cleared, the I²C module is not a part of any ongoing transmission. The remaining status bits in the I2Cn_STATE register are listed in Table 17.6 I2C Transmission Status on page 494.

Table 17.5. I2C STATE Values

Mode	Value	Description
IDLE	0	No transmission is being performed by this module.
WAIT	1	Waiting for idle. Will send a start condition as soon as the bus is idle.
START	2	Start being transmitted
ADDR	3	Address being transmitted or has been received
ADDRACK	4	Address ACK/NACK being transmitted or received
DATA	5	Data being transmitted or received
DATAACK	6	Data ACK/NACK being transmitted or received

Table 17.6. I2C Transmission Status

Bit	Description
BUSY	Set whenever there is activity on the bus. Whether or not this module is responsible for the activity cannot be determined by this byte.
MASTER	Set when operating as a master. Cleared at all other times.
TRANSMITTER	Set when operating as a transmitter; either a master transmitter or a slave transmitter. Cleared at all other times
BUSHOLD	Set when the bus is held by this I ² C module because an action is required by software.
NACK	Only valid when bus is held and STATE is ADDRACK or DATAACK. In that case it is set if a NACK was received. In all other cases, the bit is cleared.

Note: I2Cn_STATE reflects the internal state of the I^2 C module, and therefore only held constant as long as the bus is held, i.e., as long as BUSHOLD in I2Cn_STATUS is set.

17.3.9 Slave Operation

The I²C module operates in master mode by default. To enable slave operation, i.e., to allow the device to be addressed as an I²C slave, the SLAVE bit in I2Cn_CTRL must be set. In this case the I²C module operates in a mixed mode, both capable of starting transmissions as a master, and being addressed as a slave. When operating in the slave mode, HFPERCLK frequency must be higher than 2 MHz for Standard-mode, 5 MHz for Fast-mode, and 14 MHz for Fast-mode Plus.

17.3.9.1 Slave State Machine

The slave state machine is shown in Figure 17.16 I2C Slave State Machine on page 495. The dotted lines show where I²C-specific interrupt flags are set. The full-drawn circles show places where interaction may be required by software to let the transmission proceed.




Figure 17.16. I2C Slave State Machine

17.3.9.2 Address Recognition

The I²C module provides automatic address recognition for 7-bit addresses. 10-bit address recognition is not fully automatic, but can be assisted by the 7-bit address comparator as shown in 17.3.11 Using 10-bit Addresses. Address recognition is supported in all energy modes (except EM4).

The slave address, i.e., the address which the I²C module should be addressed with, is defined in the I2Cn_SADDR register. In addition to the address, a mask must be specified, telling the address comparator which bits of an incoming address to compare with the address defined in I2Cn_SADDR. The mask is defined in I2Cn_SADDRMASK, and for every zero in the mask, the corresponding bit in the slave address is treated as a don't-care, i.e., the 0-masked bits are ignored.

An incoming address that fails address recognition is automatically replied to with a NACK. Since only the bits defined by the mask are checked, a mask with a value 0x00 will result in all addresses being accepted. A mask with a value 0x7F will only match the exact address defined in I2Cn_SADDR, while a mask 0x70 will match all addresses where the three most significant bits in I2Cn_SADDR and the incoming address are equal.

If GCAMEN in I2Cn_CTRL is not set, the start-byte, i.e., the general call address with the R/W bit set is ignored unless it is included in the defined slave address and and the address mask.

When an address is accepted by the address comparator, the decision of whether to ACK or NACK the address is passed to software.

17.3.9.3 Slave Transmitter

When SLAVE in I2Cn_CTRL is set, the RSTART interrupt flag in I2Cn_IF will be set when repeated START conditions are detected. After a START or repeated START condition, the bus master will transmit an address along with an R/W bit. If there is no room in the receive shift register for the address, the bus will be held by the slave until room is available in the shift register. Transmission then continues and the address is loaded into the shift register. If this address does not pass address recognition, it is automatically NACK'ed by the slave, and the slave goes to an idle state. The address byte is in this case discarded, making the shift register ready for a new address. It is not loaded into the receive buffer.

If the address was accepted and the R/W bit was set (R), indicating that the master wishes to read from the slave, the slave now goes into the slave transmitter mode. Software interaction is now required to decide whether the slave wants to acknowledge the request or not. The accepted address byte is loaded into the receive buffer like a regular data byte. If no valid interaction is pending, the bus is held until the slave responds with a command. The slave can reject the request with a single NACK command.

The slave will in that case go to an idle state, and wait for the next start condition. To continue the transmission, the slave must make sure data is loaded into the transmit buffer and send an ACK. The loaded data will then be transmitted to the master, and an ACK or NACK will be received from the master.

Data transmission can also continue after a NACK if a CONT command is issued along with the NACK. This is not standard I²C however.

If the master responds with an ACK, it may expect another byte of data, and data should be made available in the transmit buffer. If data is not available, the bus is held until data is available.

If the response is a NACK however, this is an indication of that the master has received enough bytes and wishes to end the transmission. The slave now automatically goes idle, unless CONT in I2Cn_CMD is set and data is available for transmission. The latter is not standard I²C.

The master ends the transmission by sending a STOP or a repeated START. The SSTOP interrupt flag in I2Cn_IF is set when the master transmits a STOP condition. If the transmission is ended with a repeated START, then the SSTOP interrupt flag is not set.

Note: The SSTOP interrupt flag in I2Cn_IF will be set regardless of whether the slave is participating in the transmission or not, as long as SLAVE in I2Cn_CTRL is set and a STOP condition is detected.

If arbitration is lost at any time during transmission, the ARBLOST interrupt flag in I2Cn_IF is set, the bus is released and the slave goes idle.

See Table 17.7 I2C Slave Transmitter on page 496 for more information.

Table 17.7. I2C Slave Transmitter

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
0x41	Repeated START received	RSTART interrupt flag (BUSHOLD interrupt flag)	RXDATA	Receive and compare address
0x75	ADDR + R received	ADDR interrupt flag	ACK + TXDA- TA	ACK will be sent, then DATA
		RXDATA interrupt flag	NACK	NACK will be sent, slave goes idle
		(BUSHOLD interrupt flag)	NACK + CONT + TXDATA	NACK will be sent, then DATA.
-	Data transmitted	TXBL interrupt flag (TXC interrupt flag)	None	
0xD5	Data transmitted, ACK received	ACK interrupt flag (BUSHOLD interrupt flag)	TXDATA	DATA will be transmitted
0xDD	Data transmitted, NACK	NACK interrupt flag	None	The slave goes idle
	received	(BUSHOLD interrupt flag)	CONT + TXDATA	DATA will be transmitted

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response
-	Stop received	SSTOP interrupt flag	None	The slave goes idle
			START	START will be sent when bus becomes idle
-	Arbitration lost	ARBLOST interrupt flag	None	The slave goes idle
			START	START will be sent when the bus becomes idle

17.3.9.4 Slave Receiver

A slave receiver operation is started in the same way as a slave transmitter operation, with the exception that the address transmitted by the master has the R/W bit cleared (W), indicating that the master wishes to write to the slave. The slave then goes into slave receiver mode.

To receive data from the master, the slave should respond to the address with an ACK and make sure space is available in the receive buffer. Transmission will then continue, and the slave will receive a byte from the master.

If a NACK is sent without a CONT, the transmission is ended for the slave, and it goes idle. If the slave issues both the NACK and CONT commands and has space available in the receive buffer, it will be open for continuing reception from the master.

When a byte has been received from the master, the slave must ACK or NACK the byte. The responses here are the same as for the reception of the address byte.

The master ends the transmission by sending a STOP or a repeated START. The SSTOP interrupt flag is set when the master transmits a STOP condition. If the transmission is ended with a repeated START, then the SSTOP interrupt flag in I2Cn IF is not set.

Note: The SSTOP interrupt flag in I2Cn_IF will be set regardless of whether the slave is participating in the transmission or not, as long as SLAVE in I2Cn_CTRL is set and a STOP condition is detected

If arbitration is lost at any time during transmission, the ARBLOST interrupt flag in I2Cn_IF is set, the bus is released and the slave goes idle.

See Table 17.8 I2C - Slave Receiver on page 498 for more information.

Table 17.8. I2C - Slave Receiver

I2Cn_STATE	Description	I2Cn_IF	Required in- teraction	Response			
-	Repeated START received	RSTART interrupt flag (BUSHOLD interrupt flag)	RXDATA	Receive and compare address			
0x71	ADDR + W received	ADDR interrupt flag RXDATA interrupt flag	ACK + RXDATA	ACK will be sent and data will be received			
		(BUSHOLD interrupt flag)	NACK	NACK will be sent, slave goes idle			
			NACK + CONT + RXDATA	NACK will be sent and DATA will be received.			
0xB1	Data received	RXDATA interrupt flag (BUSHOLD interrupt	ACK + RXDATA	ACK will be sent and data will be received			
		flag)	NACK	NACK will be sent and slave will go idle			
			NACK + CONT + RXDATA	NACK will be sent and data will be received			
-	Stop received	SSTOP interrupt flag	None	The slave goes idle			
			START	START will be sent when bus becomes idle			
-	Arbitration lost	ARBLOST interrupt flag	None	The slave goes idle			
			START	START will be sent when the bus becomes idle			

17.3.10 Transfer Automation

The I²C can be set up to complete transfers with a minimal amount of interaction.

17.3.10.1 DMA

DMA can be used to automatically load data into the transmit buffer and load data out from the receive buffer. When using DMA, software is thus relieved of moving data to and from memory after each transferred byte.

17.3.10.2 Automatic ACK

When AUTOACK in I2Cn_CTRL is set, an ACK is sent automatically whenever an ACK interaction is possible and no higher priority interactions are pending.

17.3.10.3 Automatic STOP

A STOP can be generated automatically on two conditions. These apply only to the master transmitter.

If AUTOSN in I2Cn_CTRL is set, the I²C module ends a transmission by transmitting a STOP condition when operating as a master transmitter and a NACK is received.

If AUTOSE in I2Cn_CTRL is set, the I²C module always ends a transmission when there is no more data in the transmit buffer. If data has been transmitted on the bus, the transmission is ended after the (N)ACK has been received by the slave. If a START is sent when no data is available in the transmit buffer and AUTOSE is set, then the STOP condition is sent immediately following the START. Software must thus make sure data is available in the transmit buffer before the START condition has been fully transmitted if data is to be transferred.

17.3.11 Using 10-bit Addresses

When using 10-bit addresses in slave mode, set the I2Cn_SADDR register to 1111 0XX where XX are the two most significant bits of the 10-bit address, and set I2Cn_SADDRMASK to 0xFF. Address matches will now be given on all 10-bit addresses where the two most significant bits are correct.

When receiving an address match, the slave must acknowledge the address and receive the first data byte. This byte contains the second part of the 10-bit address. If it matches the address of the slave, the slave should ACK the byte to continue the transmission, and if it does not match, the slave should NACK it.

When the master is operating as a master transmitter, the data bytes will follow after the second address byte. When the master is operating as a master receiver however, a repeated START condition is sent after the second address byte. The address sent after this repeated START is equal to the first of the address bytes transmitted previously, but now with the R/W byte set, and only the slave that found a match on the entire 10-bit address in the previous message should ACK this address. The repeated start should take the master into a master receiver mode, and after the single address byte sent this time around, the slave begins transmission to the master.

17.3.12 Error Handling

Note: The setting of GCAMEN and SLAVE fields in the I2Cn_CTRL register and the registers I2Cn_SADDR and I2Cn_ROUTELOC0 are considered static. This means that these need to be set before an I²C transaction starts and need to stay stable during the entire transaction.

17.3.12.1 ABORT Command

Some bus errors may require software intervention to be resolved. The I²C module provides an ABORT command, which can be set in I2Cn CMD, to help resolve bus errors.

When the bus for some reason is locked up and the I^2C module is in the middle of a transmission it cannot get out of, or for some other reason the I^2C wants to abort a transmission, the ABORT command can be used.

Setting the ABORT command will make the I²C module discard any data currently being transmitted or received, release the SDA and SCL lines and go to an idle mode. ABORT effectively makes the I²C module forget about any ongoing transfers.

17.3.12.2 Bus Reset

A bus reset can be performed by setting the START and STOP commands in I2Cn_CMD while the transmit buffer is empty. A START condition will then be transmitted, immediately followed by a STOP condition. A bus reset can also be performed by transmitting a START command with the transmit buffer empty and AUTOSE set.

17.3.12.3 I2C-Bus Errors

An I²C-bus error occurs when a START or STOP condition is misplaced, which happens when the value on SDA changes while SCL is high during bit-transmission on the I²C-bus. If the I²C module is part of the current transmission when a bus error occurs, any data currently being transmitted or received is discarded, SDA and SCL are released, the BUSERR interrupt flag in I2Cn_IF is set to indicate the error, and the module automatically takes a course of action as defined in Table 17.9 I2C Bus Error Response on page 500.

Table 17.9. I2C Bus Error Response

	Misplaced START	Misplaced STOP
In a master/slave operation	Treated as START. Receive address.	Go idle. Perform any pending actions.

17.3.12.4 Bus Lockup

A lockup occurs when a master or slave on the I²C-bus has locked the SDA or SCL at a low value, preventing other devices from putting high values on the bus, and thus making communication on the bus impossible.

Many slave-only devices operating on an I²C-bus are not capable of driving SCL low, but in the rare case that SCL is stuck LOW, the advice is to apply a hardware reset signal to the slaves on the bus. If this does not work, cycle the power to the devices in order to make them release SCL.

When SDA is stuck low and SCL is free, a master should send 9 clock pulses on SCL while tristating the SDA. This procedure is performed in the GPIO module after clearing the I2C_ROUTE register and disabling the I2C module. The device that held the bus low should release it sometime within those 9 clocks. If not, use the same approach as for when SCL is stuck, resetting and possibly cycling power to the slaves.

Lockup of SDA can be detected by keeping count of the number of continuous arbitration losses during address transmission. If arbitration is also lost during the transmission of a general call address, i.e., during the transmission of the STOP condition, which should never happen during normal operation, this is a good indication of SDA lockup.

Detection of SCL lockups can be done using the timeout functionality defined in 17.3.12.6 Clock Low Timeout

17.3.12.5 Bus Idle Timeout

When SCL has been high for a significant amount of time, this is a good indication of that the bus is idle. On an SMBus system, the bus is only allowed to be in this state for a maximum of 50 µs before the bus is considered idle.

The bus idle timeout BITO in I2Cn_CTRL can be used to detect situations where the bus goes idle in the middle of a transmission. The timeout can be configured in BITO, and when the bus has been idle for the given amount of time, the BITO interrupt flag in I2Cn_IF is set. The bus can also be set idle automatically on a bus idle timeout. This is enabled by setting GIBITO in I2Cn_CTRL.

When the bus idle timer times out, it wraps around and continues counting as long as its condition is true. If the bus is not set idle using GIBITO or the ABORT command in I2Cn CMD, this will result in periodic timeouts.

Note: This timeout will be generated even if SDA is held low.

The bus idle timeout is active as long as the bus is busy, i.e., BUSY in I2Cn_STATUS is set. The timeout can be used to get the I²C module out of the busy-state it enters when reset, see 17.3.7.4 Reset State.

17.3.12.6 Clock Low Timeout

The clock timeout, which can be configured in CLTO in I2Cn_CTRL, starts counting whenever SCL goes low, and times out if SCL does not go high within the configured timeout. A clock low timeout results in CLTOIF in I2Cn_IF being set, allowing software to take action.

When the timer times out, it wraps around and continues counting as long as SCL is low. An SCL lockup will thus result in periodic clock low timeouts as long as SCL is low.

17.3.12.7 Clock Low Error

The I^2C module can continue transmission in parallel with another device for the entire transaction, as long as the two communications are identical. A case may arise when (before an arbitration has been decided upon) the I^2C module decides to send out a repeated START or a STOP condition while the other device is still sending data. In the I^2C protocol specifications, such a combination results in an undefined condition. The I^2C deals with this by generating a clock low error. This means that if the I^2C is transmitting a repeated START or a STOP condition and another device (another master or a misbehaving slave) pulls SCL low before the I^2C sends out the START/STOP condition on SDA, a clock low error is generated. The CLERR interrupt flag is then set in the I^2C device goes to idle.

17.3.13 DMA Support

The I²C module has full DMA support. A request for the DMA controller to write to the I²C transmit buffer can come from TXBL (transmit buffer has room for more data). The DMA controller can write to the transmit buffer using the I2Cn_TXDATA or the I2Cn_TXDOUBLE register. In order to write to the I2Cn_TXDOUBLE register (i.e., transferring 2 bytes simultaneously to the transmit buffer using the DMA), DMA_USEBURSTS needs to be set to 1 for the selected DMA channel. This ensures that the transfer is made to the transmit buffer only when both buffer elements are empty. For performing a DMA write to the I2Cn_TXDATA register, DMA_USEBURSTC needs to be set to 1 for the selected DMA channel. This ensures that a DMA transfer is made even when the transmit buffer is half-empty.

A request for the DMA controller to read from the I²C receive buffer can come from RXDATAV (data available in the receive buffer). To receive from I2Cn_RXDOUBLE (i.e., receive only when both buffer elements are full), DMA_USEBURSTS needs to be set to 1 for the selected DMA channel. In order to receive from I2Cn_RXDATA through the DMA, DMA_USEBURSTC needs to be set to 1. This ensures that the data gets picked up even when the receive buffer is half-full.

17.3.14 Interrupts

The interrupts generated by the I^2C module are combined into one interrupt vector, $I2C_INT$. If I^2C interrupts are enabled, an interrupt will be made if one or more of the interrupt flags in $I2Cn_IEN$ are set.

17.3.15 Wake-up

The I²C receive section can be active all the way down to energy mode EM3 Stop, and can wake up the CPU on address interrupt. All address match modes are supported.

17.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	I2Cn_CTRL	RW	Control Register
0x004	I2Cn_CMD	W1	Command Register
0x008	I2Cn_STATE	R	State Register
0x00C	I2Cn_STATUS	R	Status Register
0x010	I2Cn_CLKDIV	RW	Clock Division Register
0x014	I2Cn_SADDR	RW	Slave Address Register
0x018	I2Cn_SADDRMASK	RW	Slave Address Mask Register
0x01C	I2Cn_RXDATA	R(a)	Receive Buffer Data Register
0x020	I2Cn_RXDOUBLE	R(a)	Receive Buffer Double Data Register
0x024	I2Cn_RXDATAP	R	Receive Buffer Data Peek Register
0x028	I2Cn_RXDOUBLEP	R	Receive Buffer Double Data Peek Register
0x02C	I2Cn_TXDATA	W	Transmit Buffer Data Register
0x030	I2Cn_TXDOUBLE	W	Transmit Buffer Double Data Register
0x034	I2Cn_IF	R	Interrupt Flag Register
0x038	I2Cn_IFS	W1	Interrupt Flag Set Register
0x03C	I2Cn_IFC	(R)W1	Interrupt Flag Clear Register
0x040	I2Cn_IEN	RW	Interrupt Enable Register
0x044	I2Cn_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x048	I2Cn_ROUTELOC0	RW	I/O Routing Location Register

17.5 Register Description

17.5.1 I2Cn_CTRL - Control Register

Offset									Bi	t Po	siti	on																				
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•	'	•	'	'		•	•			•			0×0		0		2	OXO			9	OXO	0	0	0	0	0	0	0	0
Access															₩		₩		2	<u>}</u>			i	<u>}</u>	S N	S.	₩	₩ M	₩ M	₩	₹	RW W
Name															CLTO		GIBITO		CHIC	2			-	Z E Z	TXBIL	GCAMEN	ARBDIS	AUTOSN	AUTOSE	AUTOACK	SLAVE	N E N

Bit	Name	Reset	Access	Description
31:19	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
18:16	CLTO	0x0	RW	Clock Low Timeout

Use to generate a timeout when CLK has been low for the given amount of time. Wraps around and continues counting when the timeout is reached. The timeout value can be calculated by

timeout =
$$PCC/(f_{SCL} x (N_{low} + N_{high}))$$

	Value	Mode	Description
	0	OFF	Timeout disabled
	1	40PCC	Timeout after 40 prescaled clock cycles. In standard mode at 100 kHz, this results in a 50us timeout.
	2	80PCC	Timeout after 80 prescaled clock cycles. In standard mode at 100 kHz, this results in a 100us timeout.
	3	160PCC	Timeout after 160 prescaled clock cycles. In standard mode at 100 kHz, this results in a 200us timeout.
	4	320PCC	Timeout after 320 prescaled clock cycles. In standard mode at 100 kHz, this results in a 400us timeout.
	5	1024PCC	Timeout after 1024 prescaled clock cycles. In standard mode at 100 kHz, this results in a 1280us timeout.
15	GIBITO	0 RW	Go Idle on Bus Idle Timeout
	When set, the bus	automatically goes idle on	a bus idle timeout, allowing new transfers to be initiated.
	Value		Description
	0		A bus idle timeout has no effect on the bus state.
	1		A bus idle timeout tells the I^2C module that the bus is idle, allowing new transfers to be initiated.
14	Reserved	To ensure compatibili tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
13:12	BITO	0x0	RW	Bus Idle Timeout

Use to generate a timeout when SCL has been high for a given amount time between a START and STOP condition. When in a bus transaction, i.e. the BUSY flag is set, a timer is started whenever SCL goes high. When the timer reaches the value defined by BITO, it sets the BITO interrupt flag. The BITO interrupt flag will then be set periodically as long as SCL remains high. The bus idle timeout is active as long as BUSY is set. It is thus stopped automatically on a timeout if GIBITO is set. It is also stopped a STOP condition is detected and when the ABORT command is issued. The timeout is activated whenever the bus goes BUSY, i.e. a START condition is detected. The timeout value can be calculated by

timeout =
$$PCC/(f_{SCL} x (N_{low} + N_{high}))$$

	Value	Mode		Description							
	0	OFF		Timeout disabled							
	1	40PCC		Timeout after 40 prescaled clock cycles. In standard mode at 100 kHz, this results in a 50us timeout.							
	2 80PCC 3 160PCC			Timeout after 80 prescaled clock cycles. In standard mode at 100 kHz, this results in a 100us timeout.							
				Timeout after 160 prescaled clock cycles. In standard mode at 100 kHz, this results in a 200us timeout.							
11:10	Reserved	To ensure con	npatibility	with future devices, always write bits to 0. More information in 1.2 Conven-							
9:8	CLHR	0x0	RW	Clock Low High Ratio							
	Determines the i	ratio between the low	and high p	parts of the clock signal generated on SCL as master.							
	Value	Mode		Description							
	0	STANDARD		The ratio between low period and high period counters (N _{low} :N _{high}) is 4:4							
	1	ASYMMETRIC	С	The ratio between low period and high period counters (N_{low} : N_{high}) is 6:3							
	2	FAST		The ratio between low period and high period counters (N_{low} : N_{high}) is 11:6							
7	TXBIL	0	RW	TX Buffer Interrupt Level							
	Determines the i	nterrupt and status le	vel of the	transmit buffer.							
	Value	Mode		Description							
	0	EMPTY		TXBL status and the TXBL interrupt flag are set when the transmit buffer becomes empty. TXBL is cleared when the buffer becomes non-empty.							
	1	HALFFULL		TXBL status and the TXBL interrupt flag are set when the transmit buffer goes from full to half-full or empty. TXBL is cleared when the buffer becomes full.							
6	GCAMEN	0	RW	General Call Address Match Enable							
	Set to enable ad	dress match on gene	ral call in a	addition to the programmed slave address.							
	Value			Description							
	0			General call address will be NACK'ed if it is not included by the slave address and address mask.							

Bit	Namo	Posot	Accese	Description
БП	Name 1	Reset	Access	When a general call address is received, a software response is re-
				quired.
5	ARBDIS	0	RW	Arbitration Disable
	A master or slav	e will not release t	he bus upon l	losing arbitration.
	Value			Description
	0			When a device loses arbitration, the ARB interrupt flag is set and the bus is released.
	1			When a device loses arbitration, the ARB interrupt flag is set, but communication proceeds.
4	AUTOSN	0	RW	Automatic STOP on NACK
	Write to 1 to make	ke a master transn	nitter send a S	STOP when a NACK is received from a slave.
	Value			Description
	0			Stop is not automatically sent if a NACK is received from a slave.
	1			The master automatically sends a STOP if a NACK is received from a slave.
3	AUTOSE	0	RW	Automatic STOP When Empty
	Write to 1 to make	ke a master transn	nitter send a S	STOP when no more data is available for transmission.
	Value			Description
	0			A stop must be sent manually when no more data is to be transmitted.
	1			The master automatically sends a STOP when no more data is available for transmission.
2	AUTOACK	0	RW	Automatic Acknowledge
	Set to enable au	tomatic acknowled	dges.	
	Value			Description
	0			Software must give one ACK command for each ACK transmitted on the I ² C bus.
	1			Addresses that are not automatically NACK'ed, and all data is automatically acknowledged.
1	SLAVE	0	RW	Addressable as Slave
	Set this bit to allo	ow the device to b	e selected as	an I ² C slave.
	Value			Description
	0			All addresses will be responded to with a NACK
	1			Addresses matching the programmed slave address or the general call address (if enabled) require a response from software. Other addresses are automatically responded to with a NACK.
0	EN	0	RW	I ² C Enable
	Use this bit to en	nable or disable the	e I ² C module.	

Bit	Name	Reset	Access	Description
	Value			Description
	0			The I ² C module is disabled. And its internal state is cleared
	1			The I ² C module is enabled.

17.5.2 I2Cn_CMD - Command Register

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																									0	0	0	0	0	0	0	0
Access																									×	×	×	W1	×	W1	W	X
Name																									CLEARPC	CLEARTX	ABORT	CONT	NACK	ACK	STOP	START

				0 0 4 0 2 4 0 0
Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7	CLEARPC	0	W1	Clear Pending Commands
	Set to clear pendi	ing commands.		
6	CLEARTX	0	W1	Clear TX
	Set to clear trans	mit buffer and shi	ft register. Wi	Il not abort ongoing transfer.
5	ABORT	0	W1	Abort Transmission
				o idle. When used in combination with STOP, a STOP condition is sent as on. The stop condition is subject to clock synchronization.
4	CONT	0	W1	Continue Transmission
	Set to continue tra	ansmission after	a NACK has I	peen received.
3	NACK	0	W1	Send NACK
	Set to transmit a	NACK the next tir	ne an acknov	vledge is required.
2	ACK	0	W1	Send ACK
	Set to transmit an	ACK the next tin	ne an acknow	rledge is required.
1	STOP	0	W1	Send Stop Condition
	Set to send stop	condition as soon	as possible.	
0	START	0	W1	Send Start Condition
	as soon as the bu	is is idle. If the cu	ırrent transmi	If a transmission is ongoing and not owned, the start condition will be sent ssion is owned by this module, a repeated start condition will be sent. Use atically send a STOP, then a START when the bus becomes idle.

17.5.3 I2Cn_STATE - State Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	80	7	9	2	4	က	7	_	0
Reset		'	•		'			•			•			•		•		'	•	'		'		'		000	'	0	0	0	0	_
Access																										<u>~</u>		22	œ	<u>~</u>	œ	<u>~</u>
Name																										STATE		BUSHOLD	NACKED	TRANSMITTER	MASTER	BUSY

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:5	STATE	0x0	R	Transmission State
	The state of any cur	rent transmissio	n. Cleared i	f the I ² C module is idle.
	Value	Mode		Description
	0	IDLE		No transmission is being performed.
	1	WAIT		Waiting for idle. Will send a start condition as soon as the bus is idle.
	2	START		Start transmitted or received
	3	ADDR		Address transmitted or received
	4	ADDRACK		Address ack/nack transmitted or received
	5	DATA		Data transmitted or received
	6	DATAACK		Data ack/nack transmitted or received
4	BUSHOLD	0	R	Bus Held
	Set if the bus is curr	ently being held	by this I ² C	module.
3	NACKED	0	R	Nack Received
	Set if a NACK was r	eceived and STA	ATE is ADD	RACK or DATAACK.
2	TRANSMITTER	0	R	Transmitter
	Set when operating receiver, a slave rec			slave transmitter. When cleared, the system may be operating as a master ont known.
1	MASTER	0	R	Master
	Set when operating	as an I ² C maste	r. When cle	eared, the system may be operating as an I ² C slave.
0	BUSY	1	R	Bus Busy
		of reset, the sta	ite of the bu	ule is in control of the bus or not has no effect on the value of this bit. When us is not known, and thus BUSY is set. Use the ABORT command or a bus

idle timeout to force the I²C module out of the BUSY state.

17.5.4 I2Cn_STATUS - Status Register

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																							0	0	_	0	0	0	0	0	0	0
Access																							R	22	<u>~</u>	22	22	22	22	22	22	<u>~</u>
Name																							RXFULL	RXDATAV	TXBL	TXC	PABORT	PCONT	PNACK	PACK	PSTOP	PSTART

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9	RXFULL	0	R	RX FIFO Full
	Set when the receive for one more frame in			n the receive buffer is no longer full. When this bit is set, there is still room
8	RXDATAV	0	R	RX Data Valid
	Set when data is avai	lable in the rece	eive buffer.	Cleared when the receive buffer is empty.
7	TXBL	1	R	TX Buffer Level
	Indicates the level of	the transmit buf	fer. Set wh	en the transmit buffer is empty, and cleared when it is full.
6	TXC	0	R	TX Complete
	Set when a transmiss sion starts.	sion has comple	ted and no	more data is available in the transmit buffer. Cleared when a new transmis-
5	PABORT	0	R	Pending Abort
	An abort is pending a	nd will be transr	mitted as so	oon as possible.
4	PCONT	0	R	Pending Continue
	A continue is pending	and will be tran	nsmitted as	soon as possible.
3	PNACK	0	R	Pending NACK
	A not-acknowledge is	pending and w	ill be transr	nitted as soon as possible.
2	PACK	0	R	Pending ACK
	An acknowledge is pe	ending and will b	e transmitt	ted as soon as possible.
1	PSTOP	0	R	Pending STOP
	A stop condition is pe	nding and will b	e transmitt	ed as soon as possible.
0	PSTART	0	R	Pending START
	A start condition is pe	ending and will b	e transmitt	ed as soon as possible.

17.5.5 I2Cn_CLKDIV - Clock Division Register

Offset															Bi	t Po	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	5	4	က	2	_	0
Reset		•	•	•		•	•	•		•		•	•	•	•	•		•	•		•						•	000x0	•	•		
Access																												RW				
Name																												DIV				

Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	DIV	0x000	RW	Clock Divider
	Specifies the clock di	vider for the I ² C	. Note that	DIV must be 1 or higher when slave is enabled.

17.5.6 I2Cn_SADDR - Slave Address Register

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	1	10	တ	8	7	9	5	4	က	2	_	0
Reset			•		•	•	•							•		•		•										00×0				
Access																												₽				
Name																												ADDR				

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:1	ADDR	0x00	RW	Slave Address
	Specifies the slave ad	dress of the dev	ice.	
0	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

17.5.7 I2Cn_SADDRMASK - Slave Address Mask Register

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	11	10	တ	∞	7	9	5	4	3	2	_	0
Reset			•	•	•					•					•	•								•			•	00×0	•			
Access																												8				
Name																												MASK				

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:1	MASK	0x00	RW	Slave Address Mask
	Specifies the significa will only match the ex			s. Setting the mask to 0x00 will match all addresses, while setting it to 0x7F DDR.
0	Reserved	To ensure con tions	npatibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-

17.5.8 I2Cn_RXDATA - Receive Buffer Data Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x01C	33	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset						•						•		•	•	•		•				•		•				2	000			•
Access																												۵	۲			
Name																												V T V U A	¥ 1 () () ()			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	RXDATA	0x00	R	RX Data
	Use this register to re	ead from the rec	eive buffer.	Buffer is emptied on read access.

17.5.9 I2Cn_RXDOUBLE - Receive Buffer Double Data Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	æ	7	9	2	4	က	2	_	0
Reset		'	•	1	'		•				•		•	•						, c	noxn							0				
Access																					צ							Ω	<u>-</u>			
Name																				,	KADATAT							PXDATAD	<u>.</u>			

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	RXDATA1	0x00	R	RX Data 1
	Second byte read from	n buffer. Buffer i	is emptied	on read access.
7:0	RXDATA0	0x00	R	RX Data 0
	First byte read from b	uffer. Buffer is e	mptied on	read access.

17.5.10 I2Cn_RXDATAP - Receive Buffer Data Peek Register

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•		•		'	'	'	•			'	•	•			'	1		•	•	1	,				0	000			-
Access																												Δ	۷			
Name																												DXTATAD	֡֝֞֝֟֝֓֓֓֓֓֓֓֓֓֓֓֓֓֡֓֓֓֓֓֡֡֓֓֡֓֡֡֡֓֓֓֡֓֡֡֡֡֓֡֡֡֡			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	RXDATAP	0x00	R	RX Data Peek
	Use this register to re	ead from the re	ceive buffer	Buffer is not emptied on read access.

17.5.11 I2Cn_RXDOUBLEP - Receive Buffer Double Data Peek Register

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	8	7	9	5	4	. ო	2	_	0
Reset			•	•	•	•	•		•	•	•	•		•							nxn	•	•	•			•	•	00×0		•	
Access																				מ	צ								<u>~</u>			
Name																				,	KADALAPI								RXDATAP0			

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	RXDATAP1	0x00	R	RX Data 1 Peek
	Second byte read from	m buffer. Buffer	is not emp	tied on read access.
7:0	RXDATAP0	0x00	R	RX Data 0 Peek
	First byte read from b	uffer. Buffer is n	ot emptied	on read access.

17.5.12 I2Cn_TXDATA - Transmit Buffer Data Register

Offset															Bi	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	1	0
Reset																												OVO				
Access																												>	:			
Name																												ATACIXT				

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TXDATA	0x00	W	TX Data
	Use this register to	write a byte to t	the transmit l	puffer.

17.5.13 I2Cn_TXDOUBLE - Transmit Buffer Double Data Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•		•	r				•	•	•	•	•				•	r		200	•		•			•	0	OXO			•
Access																				}	>							}	>			
Name																				TV TV TV								O V T V U V	N N N N N N N N N N N N N N N N N N N			

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	TXDATA1	0x00	W	TX Data
	Second byte to write	to buffer.		
7:0	TXDATA0	0x00	W	TX Data
	First byte to write to b	uffer.		

17.5.14 I2Cn_IF - Interrupt Flag Register

Offset			Bi	t Po	siti	on														
0x034	2	18	17	16	15	14	13	12	1	10	6	∞	7	9	2	4	က	2	_	0
Reset		0	0	0	0	0	0	0	0	0	0	0	0	0	0	_	0	0	0	0
Access		~	Я	В	22	2	2	22	2	2	~	22	22	2	22	22	22	22	22	22
Name		CLERR	RXFULL	SSTOP	CLTO	ВІТО	RXUF	TXOF	BUSHOLD	BUSERR	ARBLOST	MSTOP	NACK	ACK	RXDATAV	TXBL	TXC	ADDR	RSTART	START

				RXF BUS BUS BUS BUS BUS BUS BUS BUS ACK ACK ACK ADD ADD ADD ADD ADD STA
Bit	Name	Reset	Access	Description
31:19	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
18	CLERR	0	R	Clock Low Error Interrupt Flag
	Set when the clock	is pulled low before	ore a STAR	T or a STOP condition could be transmitted.
17	RXFULL	0	R	Receive Buffer Full Interrupt Flag
	Set when the receiv	e buffer become	s full.	
16	SSTOP	0	R	Slave STOP Condition Interrupt Flag
	Set when a STOP of	ondition has bee	en received.	Will be set regardless of the slave being involved in the transaction or not.
15	CLTO	0	R	Clock Low Timeout Interrupt Flag
	Set on each clock lo	w timeout. The	timeout valu	e can be set in CLTO bit field in the I2Cn_CTRL register.
14	BITO	0	R	Bus Idle Timeout Interrupt Flag
	Set on each bus idle	e timeout. The tir	meout value	can be set in the BITO bit field in the I2Cn_CTRL register.
13	RXUF	0	R	Receive Buffer Underflow Interrupt Flag
				rough the I2Cn_RXDATA register while the receive buffer is empty. It is CDOUBLE while the buffer is not full.
12	TXOF	0	R	Transmit Buffer Overflow Interrupt Flag
	Set when data is wr	itten to the trans	mit buffer w	hile the transmit buffer is full.
11	BUSHOLD	0	R	Bus Held Interrupt Flag
	Set when the bus be	ecomes held by	the I ² C mod	ule.
10	BUSERR	0	R	Bus Error Interrupt Flag
	Set when a bus erro	or is detected. Th	ne bus error	is resolved automatically, but the current transfer is aborted.
9	ARBLOST	0	R	Arbitration Lost Interrupt Flag
	Set when arbitration	is lost.		
8	MSTOP	0	R	Master STOP Condition Interrupt Flag
	Set when a STOP condition, then the N			ully transmitted. If arbitration is lost during the transmission of the STOP set.
7	NACK	0	R	Not Acknowledge Received Interrupt Flag
	Set when a NACK h	as been receive	d.	
6	ACK	0	R	Acknowledge Received Interrupt Flag
	Set when an ACK h	as been received	d	

Bit	Name	Reset	Access	Description
5	RXDATAV	0	R	Receive Data Valid Interrupt Flag
	Set when data is	available in the re	eceive buffer.	Cleared automatically when the receive buffer is read.
4	TXBL	1	R	Transmit Buffer Level Interrupt Flag
	Set when the train	nsmit buffer becor	mes empty. C	leared automatically when new data is written to the transmit buffer.
3	TXC	0	R	Transfer Completed Interrupt Flag
	Set when the train	nsmit shift registe	r becomes em	npty and there is no more data in the transmit buffer.
2	ADDR	0	R	Address Interrupt Flag
	Set when incomi	ng address is acc	epted, i.e. ow	n address or general call address is received.
1	RSTART	0	R	Repeated START Condition Interrupt Flag
	Set when a repea	ated start conditio	n is detected.	
0	START	0	R	START Condition Interrupt Flag
	Set when a start	condition is succe	essfully transn	nitted.

17.5.15 I2Cn_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset														0	0	0	0	0	0	0	0	0	0	0	0	0			0	0	0	0
Access														W	W 1	W	W1	W	W	W	W1	W 1	W1	W1	W1	W1			W M	W1	W	W1
Name														CLERR	RXFULL	SSTOP	СГТО	BITO	RXUF	TXOF	BUSHOLD	BUSERR	ARBLOST	MSTOP	NACK	ACK			TXC	ADDR	RSTART	START

Bit	Name	Reset	Access	Description
31:19	Reserved	To ensure col	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
18	CLERR	0	W1	Set CLERR Interrupt Flag
	Write 1 to set the CL	ERR interrupt fla	g	
17	RXFULL	0	W1	Set RXFULL Interrupt Flag
	Write 1 to set the RX	(FULL interrupt fl	ag	
16	SSTOP	0	W1	Set SSTOP Interrupt Flag
	Write 1 to set the SS	TOP interrupt fla	ıg	
15	CLTO	0	W1	Set CLTO Interrupt Flag
	Write 1 to set the CL	TO interrupt flag		
14	BITO	0	W1	Set BITO Interrupt Flag
	Write 1 to set the BI	ΓO interrupt flag		
13	RXUF	0	W1	Set RXUF Interrupt Flag
	Write 1 to set the RX	(UF interrupt flag		
12	TXOF	0	W1	Set TXOF Interrupt Flag
	Write 1 to set the TX	OF interrupt flag		
11	BUSHOLD	0	W1	Set BUSHOLD Interrupt Flag
	Write 1 to set the BU	SHOLD interrup	t flag	
10	BUSERR	0	W1	Set BUSERR Interrupt Flag
	Write 1 to set the BU	SERR interrupt	flag	
9	ARBLOST	0	W1	Set ARBLOST Interrupt Flag
	Write 1 to set the AR	BLOST interrupt	flag	
8	MSTOP	0	W1	Set MSTOP Interrupt Flag
	Write 1 to set the MS	STOP interrupt fla	ag	
7	NACK	0	W1	Set NACK Interrupt Flag
	Write 1 to set the NA	CK interrupt flag		
6	ACK	0	W1	Set ACK Interrupt Flag
	Write 1 to set the AC	K interrupt flag		
5:4	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
3	TXC	0	W1	Set TXC Interrupt Flag
	Write 1 to set th	e TXC interrupt fla	g	
2	ADDR	0	W1	Set ADDR Interrupt Flag
	Write 1 to set th	e ADDR interrupt f	lag	
1	RSTART	0	W1	Set RSTART Interrupt Flag
	Write 1 to set th	e RSTART interrup	ot flag	
0	START	0	W1	Set START Interrupt Flag
	Write 1 to set th	e START interrupt	flag	

17.5.16 I2Cn_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	7	_	0
Reset		'			'							•		0	0	0	0	0	0	0	0	0	0	0	0	0			0	0	0	0
Access														(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1			(R)W1	(R)W1	(R)W1	(R)W1
Name														CLERR	RXFULL	SSTOP	CLTO	BITO	RXUF	TXOF	BUSHOLD	BUSERR	ARBLOST	MSTOP	NACK	ACK			TXC	ADDR	RSTART	START
Rit	Na	me					Po	set			۸۵	000	s I	Jose	crin	tion																

				SST
Bit	Name	Reset	Access	Description
31:19	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
18	CLERR	0	(R)W1	Clear CLERR Interrupt Flag
		ne CLERR interrup et be enabled globe		ng returns the value of the IF and clears the corresponding interrupt flags .
17	RXFULL	0	(R)W1	Clear RXFULL Interrupt Flag
		ne RXFULL interru et be enabled globe		ling returns the value of the IF and clears the corresponding interrupt flags .
16	SSTOP	0	(R)W1	Clear SSTOP Interrupt Flag
		ne SSTOP interrup st be enabled globa		ng returns the value of the IF and clears the corresponding interrupt flags .
15	CLTO	0	(R)W1	Clear CLTO Interrupt Flag
		ne CLTO interrupt of be enabled glob		g returns the value of the IF and clears the corresponding interrupt flags
14	ВІТО	0	(R)W1	Clear BITO Interrupt Flag
		ne BITO interrupt f et be enabled globe		returns the value of the IF and clears the corresponding interrupt flags .
13	RXUF	0	(R)W1	Clear RXUF Interrupt Flag
		ne RXUF interrupt at be enabled globa		g returns the value of the IF and clears the corresponding interrupt flags .
12	TXOF	0	(R)W1	Clear TXOF Interrupt Flag
		ne TXOF interrupt of be enabled glob		g returns the value of the IF and clears the corresponding interrupt flags
11	BUSHOLD	0	(R)W1	Clear BUSHOLD Interrupt Flag
		ne BUSHOLD inter e must be enabled		ading returns the value of the IF and clears the corresponding interrupt dSC.).
10	BUSERR	0	(R)W1	Clear BUSERR Interrupt Flag
		ne BUSERR interro et be enabled globe		ding returns the value of the IF and clears the corresponding interrupt flags .
9	ARBLOST	0	(R)W1	Clear ARBLOST Interrupt Flag
		ne ARBLOST inter et be enabled globe		ading returns the value of the IF and clears the corresponding interrupt flags .

Bit	Name	Reset	Access	Description
8	MSTOP	0	(R)W1	Clear MSTOP Interrupt Flag
		the MSTOP interru ist be enabled glob		ing returns the value of the IF and clears the corresponding interrupt flags in
7	NACK	0	(R)W1	Clear NACK Interrupt Flag
		the NACK interrupt ist be enabled glob	•	g returns the value of the IF and clears the corresponding interrupt flags
6	ACK	0	(R)W1	Clear ACK Interrupt Flag
		the ACK interrupt fl enabled globally in		returns the value of the IF and clears the corresponding interrupt flags (This
5:4	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
3	TXC	0	(R)W1	Clear TXC Interrupt Flag
		the TXC interrupt fl enabled globally in		returns the value of the IF and clears the corresponding interrupt flags (This
2	ADDR	0	(R)W1	Clear ADDR Interrupt Flag
		the ADDR interrupt ist be enabled glob		g returns the value of the IF and clears the corresponding interrupt flags
1	RSTART	0	(R)W1	Clear RSTART Interrupt Flag
		the RSTART interroust be enabled glob		ding returns the value of the IF and clears the corresponding interrupt flags
0	START	0	(R)W1	Clear START Interrupt Flag
		the START interrup ist be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .

17.5.17 I2Cn_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset														0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access														W.	₩ W	Z.	RW	Z.	₩ M	₩.	RW	₩ W	RW	W.	Z M	Z.	₩ M	RW W	₩ W	₽	₩ M	RW
Name														CLERR	RXFULL	SSTOP	CLTO	BITO	RXUF	TXOF	BUSHOLD	BUSERR	ARBLOST	MSTOP	NACK	ACK	RXDATAV	TXBL	TXC	ADDR	RSTART	START

Bit	Name	Reset	Access	Description
31:19	Reserved	To ensure c tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
18	CLERR	0	RW	CLERR Interrupt Enable
	Enable/disable the	ne CLERR interrup	t	
17	RXFULL	0	RW	RXFULL Interrupt Enable
	Enable/disable tl	ne RXFULL interrup	pt	
16	SSTOP	0	RW	SSTOP Interrupt Enable
	Enable/disable the	ne SSTOP interrup	t	
15	CLTO	0	RW	CLTO Interrupt Enable
	Enable/disable the	ne CLTO interrupt		
14	BITO	0	RW	BITO Interrupt Enable
	Enable/disable the	ne BITO interrupt		
13	RXUF	0	RW	RXUF Interrupt Enable
	Enable/disable the	ne RXUF interrupt		
12	TXOF	0	RW	TXOF Interrupt Enable
	Enable/disable the	ne TXOF interrupt		
11	BUSHOLD	0	RW	BUSHOLD Interrupt Enable
	Enable/disable the	ne BUSHOLD inter	rupt	
10	BUSERR	0	RW	BUSERR Interrupt Enable
	Enable/disable th	ne BUSERR interru	ıpt	
9	ARBLOST	0	RW	ARBLOST Interrupt Enable
	Enable/disable th	ne ARBLOST interr	rupt	
8	MSTOP	0	RW	MSTOP Interrupt Enable
	Enable/disable tl	ne MSTOP interrup	ot	
7	NACK	0	RW	NACK Interrupt Enable
	Enable/disable tl	ne NACK interrupt		
6	ACK	0	RW	ACK Interrupt Enable
	Enable/disable the	ne ACK interrupt		
	Enable/disable the	ne ACK interrupt		

Bit	Name	Reset	Access	Description
5	RXDATAV	0	RW	RXDATAV Interrupt Enable
	Enable/disable the RX	KDATAV interru	ot	
4	TXBL	0	RW	TXBL Interrupt Enable
	Enable/disable the TX	(BL interrupt		
3	TXC	0	RW	TXC Interrupt Enable
	Enable/disable the TX	C interrupt		
2	ADDR	0	RW	ADDR Interrupt Enable
	Enable/disable the AD	DDR interrupt		
1	RSTART	0	RW	RSTART Interrupt Enable
	Enable/disable the RS	START interrupt		
0	START	0	RW	START Interrupt Enable
	Enable/disable the ST	TART interrupt		

17.5.18 I2Cn_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Bi	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Reset																															0	0
Access																															RW	RW
Name																															SCLPEN	SDAPEN

Bit	Name	Reset	Access	Description				
31:2	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-				
1	SCLPEN	0	RW	SCL Pin Enable				
	When set, the SCL pi	n of the I ² C is e	nabled.					
0	SDAPEN	0	RW	SDA Pin Enable				
	When set, the SDA pi	et, the SDA pin of the I ² C is enabled.						

17.5.19 I2Cn_ROUTELOC0 - I/O Routing Location Register


17.0.10	2011_1(001		., <	rtouti	9 –	Jour		vog.	3101																
Offset										В	it F	Posi	tion												
0x048	30 29	28	56	25	23	22	2 2	2 5	<u> </u>	17	4	5 4	5 4	13	12	7	9	တ ထ	_	9	2	4	_ω α	_	0
Reset																Č	0000						00×0		
Access																:	 }						A M		
-																									
Name																-	SCLLUC						SDALOC		
D:4	Nama			Doort			A		Door	- vite	7112	o ::					<i>D</i>						o o		
31:14	Name Reserved			Reset			Acce		Des				es al	wav	'C 14	ırita l	hite t	0 0 M	ore ii	nforr	natio	on in	1.2 Co	nnve	an_
31.14	Neserveu			tions	sui C	COM	Jalibii	iity (WILII IL	ituic	, u	CVIC	es, ai	way.	3 VI	me k	JIIS I	0 0. IVI	Ji C II	11011	iialic	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	1 1.2 00	JIIV	<i>-</i> 111-
13:8	SCLLOC			0x00			RW		I/O	Loc	ati	ion													
	Decides th	e location	on o	f the I ² 0	SC	L pin	•																		
	Value			Mode					Des	crip	tio	n													
	0			LOC0					Loc	atior	า 0)													
	1			LOC1					Loc	atior	า 1														
	2			LOC2					Loc	atior	า 2	2													
	3			LOC3					Loc	atior	า 3	3													
	4			LOC4					Loc	atior	า 4	1													
	5			LOC5					Loc	atior	า 5	5													
	6			LOC6					Loc	atior	า 6	3													
	7			LOC7					Loc																
	8			LOC8					Loc																
	9			LOC9					Loc																
	10			LOC10					Loc																
	11			LOC1					Loc																
	12			LOC12					Loc																
	13			LOC1					Loc																
	14			LOC1					Loc																
	15			LOC1					Loc																
	16			LOC1					Loc																
	17			LOC1					Loc																
	18			LOC18					Loc																
	19			LOC19					Loc																
	20			LOC2					Loc																
	21			LOC2					Loc																
	22			LOC2	2				Loc	atior	า 2	22													

Bit	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31
7:6	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	SDALOC	0x00	RW	I/O Location
	Decides the loc	ation of the I ² C SDA	pin.	
	Value	Mode		Description
	0	LOC0		Location 0
	1	LOC1		Location 1
	2	LOC2		Location 2
	3	LOC3		Location 3
	4	LOC4		Location 4
	5	LOC5		Location 5
	6	LOC6		Location 6
	7	LOC7		Location 7
	8	LOC8		Location 8
	9	LOC9		Location 9
	10	LOC10		Location 10
	11	LOC11		Location 11
	12	LOC12		Location 12
	13	LOC13		Location 13
	14	LOC14		Location 14
	15	LOC15		Location 15
	16	LOC16		Location 16
	17	LOC17		Location 17
	18	LOC18		Location 18
	19	LOC19		Location 19
	20	LOC20		Location 20
	21	LOC21		Location 21
	22	LOC22		Location 22

Bit	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31
	-			

18. USART - Universal Synchronous Asynchronous Receiver/Transmitter





Quick Facts

What?

The USART handles high-speed UART, SPI-bus, SmartCards, and IrDA communication.

Why?

Serial communication is frequently used in embedded systems and the USART allows efficient communication with a wide range of external devices.

How?

The USART has a wide selection of operating modes, frame formats and baud rates. The multi-processor mode allows the USART to remain idle when not addressed. Triple buffering and DMA support makes high data rates possible with minimal CPU intervention and it is possible to transmit and receive large frames while the MCU remains in EM1 Sleep.

18.1 Introduction

The Universal Synchronous Asynchronous serial Receiver and Transmitter (USART) is a very flexible serial I/O module. It supports full duplex asynchronous UART communication as well as RS-485, SPI, MicroWire and 3-wire. It can also interface with ISO7816 Smart-Cards, and IrDA devices.

18.2 Features

- · Asynchronous and synchronous (SPI) communication
- · Full duplex and half duplex
- Separate TX/RX enable
- · Separate receive / transmit multiple entry buffers, with additional separate shift registers
- Programmable baud rate, generated as an fractional division from the peripheral clock (HFPERCLK_{USARTn})
- · Max bit-rate
 - SPI master mode, peripheral clock rate/2
 - SPI slave mode, peripheral clock rate/8
 - UART mode, peripheral clock rate/16, 8, 6, or 4
- · Asynchronous mode supports
 - · Majority vote baud-reception
 - · False start-bit detection
 - · Break generation/detection
 - · Multi-processor mode
- · Synchronous mode supports
 - · All 4 SPI clock polarity/phase configurations
 - · Master and slave mode
- · Data can be transmitted LSB first or MSB first
- Configurable number of data bits, 4-16 (plus the parity bit, if enabled)
 - · HW parity bit generation and check
- Configurable number of stop bits in asynchronous mode: 0.5, 1, 1.5, 2
- · HW collision detection
- · Multi-processor mode
- IrDA modulator
- · SmartCard (ISO7816) mode
- · I2S mode
- · Separate interrupt vectors for receive and transmit interrupts
- · Loopback mode
 - · Half duplex communication
 - · Communication debugging
- · PRS RX input
- · 8 bit Timer
- · Hardware Flow Control
- · Automatic Baud Rate Detection

18.3 Functional Description

An overview of the USART module is shown in Figure 18.1 USART Overview on page 527.

This section describes all possible USART features. Refer to the device data sheet to see what features a specific USART instance supports.




Figure 18.1. USART Overview

18.3.1 Modes of Operation

The USART operates in either asynchronous or synchronous mode.

In synchronous mode, a separate clock signal is transmitted with the data. This clock signal is generated by the bus master, and both the master and slave sample and transmit data according to this clock. Both master and slave modes are supported by the USART. The synchronous communication mode is compatible with the Serial Peripheral Interface Bus (SPI) standard.

In asynchronous mode, no separate clock signal is transmitted with the data on the bus. The USART receiver thus has to determine where to sample the data on the bus from the actual data. To make this possible, additional synchronization bits are added to the data when operating in asynchronous mode, resulting in a slight overhead.

Asynchronous or synchronous mode can be selected by configuring SYNC in USARTn_CTRL. The options are listed with supported protocols in Table 18.1 USART Asynchronous Vs. Synchronous Mode on page 528. Full duplex and half duplex communication is supported in both asynchronous and synchronous mode.

Table 18.1. USART Asynchronous Vs. Synchronous Mode

SYNC	Communication Mode	Supported Protocols
0	Asynchronous	RS-232, RS-485 (w/external driver), IrDA, ISO 7816
1	Synchronous	SPI, MicroWire, 3-wire

Table 18.2 USART Pin Usage on page 528 explains the functionality of the different USART pins when the USART operates in different modes. Pin functionality enclosed in square brackets is optional, and depends on additional configuration parameters. LOOPBK and MASTER are discussed in 18.3.2.14 Local Loopback and 18.3.3.3 Master Mode respectively.

Table 18.2. USART Pin Usage

SYNC	LOOPBK	MASTER		Pin fund	ctionality	
SINC	LOOPBR	WASTER	U(S)n_TX (MOSI)	U(S)n_RX (MISO)	USn_CLK	USn_CS
0	0	x	Data out	Data in	-	[Driver enable]
0	1	х	Data out/in	-	-	[Driver enable]
1	0	0	Data in	Data out	Clock in	Slave select
1	0	1	Data out	Data in	Clock out	[Auto slave select]
1	1	0	Data out/in	-	Clock in	Slave select
1	1	1	Data out/in	-	Clock out	[Auto slave select]

18.3.2 Asynchronous Operation

The USART operates in asynchronous mode when SYNC in USARTn_CTRL is cleared to 0.

18.3.2.1 Frame Format

The frame format used in asynchronous mode consists of a set of data bits in addition to bits for synchronization and optionally a parity bit for error checking. A frame starts with one start-bit (S), where the line is driven low for one bit-period. This signals the start of a frame, and is used for synchronization. Following the start bit are 4 to 16 data bits and an optional parity bit. Finally, a number of stop-bits, where the line is driven high, end the frame. An example frame is shown in Figure 18.2 USART Asynchronous Frame Format on page 529.




Figure 18.2. USART Asynchronous Frame Format

The number of data bits in a frame is set by DATABITS in USARTn_FRAME, see Table 18.3 USART Data Bits on page 529, and the number of stop-bits is set by STOPBITS in USARTn_FRAME, see Table 18.4 USART Stop Bits on page 529. Whether or not a parity bit should be included, and whether it should be even or odd is defined by PARITY, also in USARTn_FRAME. For communication to be possible, all parties of an asynchronous transfer must agree on the frame format being used.

Table 18.3. USART Data Bits

DATA BITS [3:0]	Number of Data Bits
0001	4
0010	5
0011	6
0100	7
0101	8 (Default)
0110	9
0111	10
1000	11
1001	12
1010	13
1011	14
1100	15
1101	16

Table 18.4. USART Stop Bits

STOP BITS [1:0]	Number of Stop Bits
00	0.5
01	1 (Default)
10	1.5
11	2

The order in which the data bits are transmitted and received is defined by MSBF in USARTn_CTRL. When MSBF is cleared, data in a frame is sent and received with the least significant bit first. When it is set, the most significant bit comes first.

The frame format used by the transmitter can be inverted by setting TXINV in USARTn_CTRL, and the format expected by the receiver can be inverted by setting RXINV in USARTn_CTRL. These bits affect the entire frame, not only the data bits. An inverted frame has a low idle state, a high start-bit, inverted data and parity bits, and low stop-bits.

18.3.2.2 Parity Bit Calculation and Handling

When parity bits are enabled, hardware automatically calculates and inserts any parity bits into outgoing frames, and verifies the received parity bits in incoming frames. This is true for both asynchronous and synchronous modes, even though it is mostly used in asynchronous communication. The possible parity modes are defined in Table 18.5 USART Parity Bits on page 530. When even parity is chosen, a parity bit is inserted to make the number of high bits (data + parity) even. If odd parity is chosen, the parity bit makes the total number of high bits odd.

Table 18.5. USART Parity Bits

PARITY BITS [1:0]	Description
00	No parity bit (Default)
01	Reserved
10	Even parity
11	Odd parity

18.3.2.3 Clock Generation

The USART clock defines the transmission and reception data rate. When operating in asynchronous mode, the baud rate (bit-rate) is given by Figure 18.3 USART Baud Rate on page 531.

br = $f_{HFPERCLK}/(oversample x (1 + USARTn_CLKDIV/256))$

Figure 18.3. USART Baud Rate

where f_{HFPERCLK} is the peripheral clock (HFPERCLK_{USARTn}) frequency and oversample is the oversampling rate as defined by OVS in USARTn_CTRL, see Table 18.6 USART Oversampling on page 531.

Table 18.6. USART Oversampling

OVS [1:0]	Oversample
00	16
01	8
10	6
11	4

The USART has a fractional clock divider to allow the USART clock to be controlled more accurately than what is possible with a standard integral divider.

The clock divider used in the USART is a 20-bit value, with a 15-bit integral part and an 5-bit fractional part. The fractional part is configured in the lower 5 bits of DIV in USART CLKDIV.

Fractional clock division is implemented by distributing the selected fraction over thirty two baud periods. The fractional part of the divider tells how many of these periods should be extended by one peripheral clock cycle.

Given a desired baud rate brdesired, the clock divider USARTn_CLKDIV can be calculated by using Figure 18.4 USART Desired Baud Rate on page 531:

USARTn_CLKDIV = 256 x (f_{HFPERCLK}/(oversample x brdesired) - 1)

Figure 18.4. USART Desired Baud Rate

Table 18.7 USART Baud Rates @ 4MHz Peripheral Clock With 20 Bit CLKDIV on page 531 shows a set of desired baud rates and how accurately the USART is able to generate these baud rates when running at a 4 MHz peripheral clock, using 16x or 8x oversampling.

Table 18.7. USART Baud Rates @ 4MHz Peripheral Clock With 20 Bit CLKDIV

Desired baud rate [baud/s]	USARTn_OVS =00			USARTn_OVS =01		
	USARTn_CLKDIV/256 (to 32nd position)	Actual baud rate [baud/s]	Error %	USARTn_CLKDIV/256 (to 32nd position)	Actual baud rate [baud/s]	Error %
600	415.6563	600.015	0.003	832.3438	599.9925	-0.001
1200	207.3438	1199.94	-0.005	415.6563	1200.03	0.003
2400	103.1563	2400.24	0.010	207.3438	2399.88	-0.005
4800	51.09375	4799.04	-0.020	103.1563	4800.48	0.010
9600	25.03125	9603.842	0.040	51.09375	9598.08	-0.020
14400	16.375	14388.49	-0.080	33.71875	14401.44	0.010
19200	12.03125	19184.65	-0.080	25.03125	19207.68	0.040
28800	7.6875	28776.98	-0.080	16.375	28776.98	-0.080

Desired baud rate [baud/s]	USARTn_OVS =00			USARTn_OVS =01		
	USARTn_CLKDIV/256 (to 32nd position)	Actual baud rate [baud/s]	Error %	USARTn_CLKDIV/256 (to 32nd position)	Actual baud rate [baud/s]	Error %
38400	5.5	38461.54	0.160	12.03125	38369.3	-0.080
57600	3.34375	57553.96	-0.080	7.6875	57553.96	-0.080
76800	2.25	76923.08	0.160	5.5	76923.08	0.160
115200	1.15625	115942	0.644	3.34375	115107.9	-0.080
230400	0.09375	228571.4	-0.794	1.15625	231884.1	0.644

18.3.2.4 Auto Baud Detection

Setting AUTOBAUDEN in USARTn_CLKDIV uses the first frame received to automatically set the baud rate provided that it contains 0x55 (IrDA uses 0x00). AUTOBAUDEN can be used in a simple LIN configuration to auto detect the SYNC byte. The receiver will measure the number of local clock cycles between the beginning of the START bit and the beginning of the 8th data bit. The DIV field in USARTn_CLKDIV will be overwritten with the new value. The OVS in USARTn_CTRL and the +1 count of the Baud Rate equation are already factored into the result that gets written into the DIV field. To restart autobaud detection, clear AUTOBAUDEN and set it high again. Since the auto baud detection is done over 8 baud times, only the upper 3 bits of the fractional part of the clock divider are populated.

18.3.2.5 Data Transmission

Asynchronous data transmission is initiated by writing data to the transmit buffer using one of the methods described in 18.3.2.6 Transmit Buffer Operation. When the transmission shift register is empty and ready for new data, a frame from the transmit buffer is loaded into the shift register, and if the transmitter is enabled, transmission begins. When the frame has been transmitted, a new frame is loaded into the shift register if available, and transmission continues. If the transmit buffer is empty, the transmitter goes to an idle state, waiting for a new frame to become available.

Transmission is enabled through the command register USARTn_CMD by setting TXEN, and disabled by setting TXDIS in the same command register. When the transmitter is disabled using TXDIS, any ongoing transmission is aborted, and any frame currently being transmitted is discarded. When disabled, the TX output goes to an idle state, which by default is a high value. Whether or not the transmitter is enabled at a given time can be read from TXENS in USARTn_STATUS.

When the USART transmitter is enabled and there is no data in the transmit shift register or transmit buffer, the TXC flag in USARTn_STATUS and the TXC interrupt flag in USARTn_IF are set, signaling that the transmission is complete. The TXC status flag is cleared when a new frame becomes available for transmission, but the TXC interrupt flag must be cleared by software.

18.3.2.6 Transmit Buffer Operation

The transmit-buffer is a multiple entry FIFO buffer. A frame can be loaded into the buffer by writing to USARTn_TXDATA, USARTn_TXDATAX, USARTn_TXDOUBLE or USARTn_TXDOUBLEX. Using USARTn_TXDATA allows 8 bits to be written to the buffer, while using USARTn_TXDOUBLE will write 2 frames of 8 bits to the buffer. If 9-bit frames are used, the 9th bit of the frames will in these cases be set to the value of BIT8DV in USARTn_CTRL.

To set the 9th bit directly and/or use transmission control, USARTn_TXDATAX and USARTn_TXDOUBLEX must be used. USARTn_TXDATAX allows 9 data bits to be written, as well as a set of control bits regarding the transmission of the written frame. Every frame in the buffer is stored with 9 data bits and additional transmission control bits. USARTn_TXDOUBLEX allows two frames, complete with control bits to be written at once. When data is written to the transmit buffer using USARTn_TXDATAX and USARTn_TXDOUBLEX, the 9th bit(s) written to these registers override the value in BIT8DV in USARTn_CTRL, and alone define the 9th bits that are transmitted if 9-bit frames are used. Figure 18.5 USART Transmit Buffer Operation on page 533 shows the basics of the transmit buffer when DATABITS in USARTn_FRAME is configured to less than 10 bits.




Figure 18.5. USART Transmit Buffer Operation

When writing more frames to the transmit buffer than there is free space for, the TXOF interrupt flag in USARTn_IF will be set, indicating the overflow. The data already in the transmit buffer is preserved in this case, and no data is written.

In addition to the interrupt flag TXC in USARTn_IF and status flag TXC in USARTn_STATUS which are set when the transmission is complete, TXBL in USARTn_STATUS and the TXBL interrupt flag in USARTn_IF are used to indicate the level of the transmit buffer. TXBIL in USARTn_CTRL controls the level at which these bits are set. If TXBIL is cleared, they are set whenever the transmit buffer becomes empty, and if TXBIL is set, they are set whenever the transmit buffer goes from full to half-full or empty. Both the TXBL status flag and the TXBL interrupt flag are cleared automatically when their condition becomes false.

There is a TXIDLE status bit in USARTn_STATUS to provide an indication of when the transmitter is idle. The combined count of TX buffer element 0, TX buffer element 1, and TX shift register is called TXBUFCNT in USARTn_STATUS. For large frames, the count is only of TX buffer entry 0 and the TX shifter register.

The transmit buffer, including the transmit shift register can be cleared by setting CLEARTX in USARTn_CMD. This will prevent the USART from transmitting the data in the buffer and shift register, and will make them available for new data. Any frame currently being transmitted will not be aborted. Transmission of this frame will be completed.

18.3.2.7 Frame Transmission Control

The transmission control bits, which can be written using USARTn_TXDATAX and USARTn_TXDOUBLEX, affect the transmission of the written frame. The following options are available:

- Generate break: By setting TXBREAK, the output will be held low during the stop-bit period to generate a framing error. A receiver that supports break detection detects this state, allowing it to be used e.g. for framing of larger data packets. The line is driven high before the next frame is transmitted so the next start condition can be identified correctly by the recipient. Continuous breaks lasting longer than a USART frame are thus not supported by the USART. GPIO can be used for this.
- Disable transmitter after transmission: If TXDISAT is set, the transmitter is disabled after the frame has been fully transmitted.
- Enable receiver after transmission: If RXENAT is set, the receiver is enabled after the frame has been fully transmitted. It is enabled in time to detect a start-bit directly after the last stop-bit has been transmitted.
- Unblock receiver after transmission: If UBRXAT is set, the receiver is unblocked and RXBLOCK is cleared after the frame has been fully transmitted.
- Tristate transmitter after transmission: If TXTRIAT is set, TXTRI is set after the frame has been fully transmitted, tristating the transmitter output. Tristating of the output can also be performed automatically by setting AUTOTRI. If AUTOTRI is set TXTRI is always read as 0.

Note: When in SmartCard mode with repeat enabled, none of the actions, except generate break, will be performed until the frame is transmitted without failure. Generation of a break in SmartCard mode with repeat enabled will cause the USART to detect a NACK on every frame.

18.3.2.8 Data Reception

Data reception is enabled by setting RXEN in USARTn_CMD. When the receiver is enabled, it actively samples the input looking for a transition from high to low indicating the start baud of a new frame. When a start baud is found, reception of the new frame begins if the receive shift register is empty and ready for new data. When the frame has been received, it is pushed into the receive buffer, making the shift register ready for another frame of data, and the receiver starts looking for another start baud. If the receive buffer is full, the received frame remains in the shift register until more space in the receive buffer is available. If an incoming frame is detected while both the receive buffer and the receive shift register are full, the data in the shift register is overwritten, and the RXOF interrupt flag in USARTn_IF is set to indicate the buffer overflow.

The receiver can be disabled by setting the command bit RXDIS in USARTn_CMD. Any frame currently being received when the receiver is disabled is discarded. Whether or not the receiver is enabled at a given time can be read out from RXENS in USARTn_STATUS.

18.3.2.9 Receive Buffer Operation

When data becomes available in the receive buffer, the RXDATAV flag in USARTn_STATUS, and the RXDATAV interrupt flag in USARTn_IF are set, and when the buffer becomes full, RXFULL in USARTn_STATUS and the RXFULL interrupt flag in USARTn_IF are set. The status flags RXDATAV and RXFULL are automatically cleared by hardware when their condition is no longer true. This also goes for the RXDATAV interrupt flag, but the RXFULL interrupt flag must be cleared by software. When the RXFULL flag is set, notifying that the buffer is full, space is still available in the receive shift register for one more frame.

Data can be read from the receive buffer in a number of ways. USARTn_RXDATA gives access to the 8 least significant bits of the received frame, and USARTn_RXDOUBLE makes it possible to read the 8 least significant bits of two frames at once, pulling two frames from the buffer. To get access to the 9th, most significant bit, USARTn_RXDATAX must be used. This register also contains status information regarding the frame. USARTn_RXDOUBLEX can be used to get two frames complete with the 9th bits and status bits.

When a frame is read from the receive buffer using USARTn_RXDATA or USARTn_RXDATAX, the frame is pulled out of the buffer, making room for a new frame. USARTn_RXDOUBLE and USARTn_RXDOUBLEX pull two frames out of the buffer. If an attempt is done to read more frames from the buffer than what is available, the RXUF interrupt flag in USARTn_IF is set to signal the underflow, and the data read from the buffer is undefined.

Frames can be read from the receive buffer without removing the data by using USARTn_RXDATAXP and USARTn_RXDOUBLEXP. USARTn_RXDATAXP gives access the first frame in the buffer with status bits, while USARTn_RXDOUBLEXP gives access to both frames with status bits. The data read from these registers when the receive buffer is empty is undefined. If the receive buffer contains one valid frame, the first frame in USARTn_RXDOUBLEXP will be valid. No underflow interrupt is generated by a read using these registers, i.e. RXUF in USARTn_IF is never set as a result of reading from USARTn_RXDATAXP or USARTn_RXDOUBLEXP.

The basic operation of the receive buffer when DATABITS in USARTn_FRAME is configured to less than 10 bits is shown in Figure 18.6 USART Receive Buffer Operation on page 535.




Figure 18.6. USART Receive Buffer Operation

The receive buffer, including the receive shift register can be cleared by setting CLEARRX in USARTn_CMD. Any frame currently being received will not be discarded.

18.3.2.10 Blocking Incoming Data

When using hardware frame recognition, as detailed in 18.3.2.20 Multi-Processor Mode and 18.3.2.21 Collision Detection, it is necessary to be able to let the receiver sample incoming frames without passing the frames to software by loading them into the receive buffer. This is accomplished by blocking incoming data.

Incoming data is blocked as long as RXBLOCK in USARTn_STATUS is set. When blocked, frames received by the receiver will not be loaded into the receive buffer, and software is not notified by the RXDATAV flag in USARTn_STATUS or the RXDATAV interrupt flag in USARTn_IF at their arrival. For data to be loaded into the receive buffer, RXBLOCK must be cleared in the instant a frame is fully received by the receiver. RXBLOCK is set by setting RXBLOCKEN in USARTn_CMD and disabled by setting RXBLOCKDIS also in USARTn_CMD. There is one exception where data is loaded into the receive buffer even when RXBLOCK is set. This is when an address frame is received when operating in multi-processor mode. See 18.3.2.20 Multi-Processor Mode for more information.

Frames received containing framing or parity errors will not result in the FERR and PERR interrupt flags in USARTn_IF being set while RXBLOCK in USARTn_STATUS is set. Hardware recognition is not applied to these erroneous frames, and they are silently discarded.

Note:

- If a frame is received while RXBLOCK in USARTn_STATUS is cleared, but stays in the receive shift register because the receive buffer is full, the received frame will be loaded into the receive buffer when space becomes available even if RXBLOCK is set at that time.
- The overflow interrupt flag RXOF in USARTn_IF will be set if a frame in the receive shift register, waiting to be loaded into the receive buffer is overwritten by an incoming frame even though RXBLOCK in USARTn_STATUS is set.

18.3.2.11 Clock Recovery and Filtering

The receiver samples the incoming signal at a rate 16, 8, 6 or 4 times higher than the given baud rate, depending on the oversampling mode given by OVS in USARTn CTRL. Lower oversampling rates make higher baud rates possible, but give less room for errors.

When a high-to-low transition is registered on the input while the receiver is idle, this is recognized as a start-bit, and the baud rate generator is synchronized with the incoming frame.

For oversampling modes 16, 8 and 6, every bit in the incoming frame is sampled three times to gain a level of noise immunity. These samples are aimed at the middle of the bit-periods, as visualized in Figure 18.7 USART Sampling of Start and Data Bits on page 537. With OVS=0 in USARTn_CTRL, the start and data bits are thus sampled at locations 8, 9 and 10 in the figure, locations 4, 5 and 6 for OVS=1 and locations 3, 4, and 5 for OVS=2. The value of a sampled bit is determined by majority vote. If two or more of the three bit-samples are high, the resulting bit value is high. If the majority is low, the resulting bit value is low.

Majority vote is used for all oversampling modes except 4x oversampling. In this mode, a single sample is taken at position 3 as shown in Figure 18.7 USART Sampling of Start and Data Bits on page 537.

Majority vote can be disabled by setting MVDIS in USARTn CTRL.

If the value of the start bit is found to be high, the reception of the frame is aborted, filtering out false start bits possibly generated by noise on the input.




Figure 18.7. USART Sampling of Start and Data Bits

If the baud rate of the transmitter and receiver differ, the location each bit is sampled will be shifted towards the previous or next bit in the frame. This is acceptable for small errors in the baud rate, but for larger errors, it will result in transmission errors.

When the number of stop bits is 1 or more, stop bits are sampled like the start and data bits as seen in Figure 18.8 USART Sampling of Stop Bits when Number of Stop Bits are 1 or More on page 538. When a stop bit has been detected by sampling at positions 8, 9 and 10 for normal mode, or 4, 5 and 6 for smart mode, the USART is ready for a new start bit. As seen in Figure 18.8 USART Sampling of Stop Bits when Number of Stop Bits are 1 or More on page 538, a stop-bit of length 1 normally ends at c, but the next frame will be received correctly as long as the start-bit comes after position a for OVS=0 and OVS=3, and b for OVS=1 and OVS=2.




Figure 18.8. USART Sampling of Stop Bits when Number of Stop Bits are 1 or More

When working with stop bit lengths of half a baud period, the above sampling scheme no longer suffices. In this case, the stop-bit is not sampled, and no framing error is generated in the receiver if the stop-bit is not generated. The line must still be driven high before the next start bit however for the USART to successfully identify the start bit.

18.3.2.12 Parity Error

When parity bits are enabled, a parity check is automatically performed on incoming frames. When a parity error is detected in an incoming frame, the data parity error bit PERR in the frame is set, as well as the interrupt flag PERR in USARTn_IF. Frames with parity errors are loaded into the receive buffer like regular frames.

PERR can be accessed by reading the frame from the receive buffer using the USARTn_RXDATAX, USARTn_RXDATAXP, USARTn_RXDOUBLEX or USARTn_RXDOUBLEXP registers.

If ERRSTX in USARTn_CTRL is set, the transmitter is disabled on received parity and framing errors. If ERRSRX in USARTn_CTRL is set, the receiver is disabled on parity and framing errors.

18.3.2.13 Framing Error and Break Detection

A framing error is the result of an asynchronous frame where the stop bit was sampled to a value of 0. This can be the result of noise and baud rate errors, but can also be the result of a break generated by the transmitter on purpose.

When a framing error is detected in an incoming frame, the framing error bit FERR in the frame is set. The interrupt flag FERR in USARTn IF is also set. Frames with framing errors are loaded into the receive buffer like regular frames.

FERR can be accessed by reading the frame from the receive buffer using the USARTn_RXDATAX, USARTn_RXDATAXP, USARTn_RXDOUBLEX or USARTn_RXDOUBLEXP registers.

If ERRSTX in USARTn_CTRL is set, the transmitter is disabled on parity and framing errors. If ERRSRX in USARTn_CTRL is set, the receiver is disabled on parity and framing errors.

18.3.2.14 Local Loopback

The USART receiver samples U(S)n_RX by default, and the transmitter drives U(S)n_TX by default. This is not the only option however. When LOOPBK in USARTn_CTRL is set, the receiver is connected to the U(S)n_TX pin as shown in Figure 18.9 USART Local Loopback on page 539. This is useful for debugging, as the USART can receive the data it transmits, but it is also used to allow the USART to read and write to the same pin, which is required for some half duplex communication modes. In this mode, the U(S)n_TX pin must be enabled as an output in the GPIO.




Figure 18.9. USART Local Loopback

18.3.2.15 Asynchronous Half Duplex Communication

When doing full duplex communication, two data links are provided, making it possible for data to be sent and received at the same time. In half duplex mode, data is only sent in one direction at a time. There are several possible half duplex setups, as described in the following sections.

18.3.2.16 Single Data-link

In this setup, the USART both receives and transmits data on the same pin. This is enabled by setting LOOPBK in USARTn_CTRL, which connects the receiver to the transmitter output. Because they are both connected to the same line, it is important that the USART transmitter does not drive the line when receiving data, as this would corrupt the data on the line.

When communicating over a single data-link, the transmitter must thus be tristated whenever not transmitting data. This is done by setting the command bit TXTRIEN in USARTn_CMD, which tristates the transmitter. Before transmitting data, the command bit TXTRI-DIS, also in USARTn_CMD, must be set to enable transmitter output again. Whether or not the output is tristated at a given time can be read from TXTRI in USARTn_STATUS. If TXTRI is set when transmitting data, the data is shifted out of the shift register, but is not put out on U(S)n_TX.

When operating a half duplex data bus, it is common to have a bus master, which first transmits a request to one of the bus slaves, then receives a reply. In this case, the frame transmission control bits, which can be set by writing to USARTn_TXDATAX, can be used to make the USART automatically disable transmission, tristate the transmitter and enable reception when the request has been transmitted, making it ready to receive a response from the slave.

The timer, 18.3.10 Timer, can also be used to add delay between the RX and TX frames so that the interrupt service routine has time to process data that was just received before transmitting more data. Also hardware flow control is another method to insert time for processing the frame. RTS and CTS can be used to halt either the link partner's transmitter or the local transmitter. See the section on hardware flow control, 18.3.4 Hardware Flow Control, for more details.

Tristating the transmitter can also be performed automatically by the USART by using AUTOTRI in USARTn_CTRL. When AUTOTRI is set, the USART automatically tristates U(S)n_TX whenever the transmitter is idle, and enables transmitter output when the transmitter goes active. If AUTOTRI is set TXTRI is always read as 0.

Note: Another way to tristate the transmitter is to enable wired-and or wired-or mode in GPIO. For wired-and mode, outputting a 1 will be the same as tristating the output, and for wired-or mode, outputting a 0 will be the same as tristating the output. This can only be done on buses with a pull-up or pull-down resistor respectively.

18.3.2.17 Single Data-link With External Driver

Some communication schemes, such as RS-485 rely on an external driver. Here, the driver has an extra input which enables it, and instead of tristating the transmitter when receiving data, the external driver must be disabled.

This can be done manually by assigning a GPIO to turn the driver on or off, or it can be handled automatically by the USART. If AUTOCS in USARTn_CTRL is set, the USn_CS output is automatically activated a configurable number of baud periods before the transmitter starts transmitting data, and deactivated a configurable number of baud periods after the last bit has been transmitted and there is no more data in the transmit buffer to transmit. The number of baud periods are controlled by CSSETUP and CSHOLD in USARTn_TIMING. This feature can be used to turn the external driver on when transmitting data, and turn it off when the data has been transmitted.

The timer, 18.3.10 Timer, can also be used to configure CSSETUP and CSHOLD values between 1 to 256 baud-times by using TCMPVAL0, TCMPVAL1, or TCMPVAL2 for the TX sequencer.

USn CS is immediately deasserted when the transmitter becomes disabled.

Figure 18.10 USART Half Duplex Communication with External Driver on page 540 shows an example configuration where USn_CS is used to automatically enable and disable an external driver.




Figure 18.10. USART Half Duplex Communication with External Driver

The USn_CS output is active low by default, but its polarity can be changed with CSINV in USARTn_CTRL. AUTOCS works regardless of which mode the USART is in, so this functionality can also be used for automatic chip/slave select when in synchronous mode (e.g. SPI).

18.3.2.18 Two Data-links

Some limited devices only support half duplex communication even though two data links are available. In this case software is responsible for making sure data is not transmitted when incoming data is expected.

TXARXnEN in USARTn_TRIGCTRL may be used to automatically start transmission after the end of the RX frame plus any TXSTDE-LAY and CSSETUP delay in USARTn_TIMING. For enabling the receiver either use RXENAT in USARTn_TXDATAX or RXATXnEN in USARTn_TRIGCTRL.

18.3.2.19 Large Frames

As each frame in the transmit and receive buffers holds a maximum of 9 bits, both the elements in the buffers are combined when working with USART-frames of 10 or more data bits.

To transmit such a frame, at least two elements must be available in the transmit buffer. If only one element is available, the USART will wait for the second element before transmitting the combined frame. Both the elements making up the frame are consumed when transmitting such a frame.

When using large frames, the 9th bits in the buffers are unused. For an 11 bit frame, the 8 least significant bits are thus taken from the first element in the buffer, and the 3 remaining bits are taken from the second element as shown in Figure 18.11 USART Transmission of Large Frames on page 541. The first element in the transmit buffer, i.e. element 0 in Figure 18.11 USART Transmission of Large Frames on page 541 is the first element written to the FIFO, or the least significant byte when writing two bytes at a time using USARTn_TXDOUBLE.




Figure 18.11. USART Transmission of Large Frames

As shown in Figure 18.11 USART Transmission of Large Frames on page 541, frame transmission control bits are taken from the second element in FIFO.

The two buffer elements can be written at the same time using the USARTn_TXDOUBLE or USARTn_TXDOUBLEX register. The TXDATAX0 bitfield then refers to buffer element 0, and TXDATAX1 refers to buffer element 1.




Figure 18.12. USART Transmission of Large Frames, MSBF

Figure 18.12 USART Transmission of Large Frames, MSBF on page 541 illustrates the order of the transmitted bits when an 11 bit frame is transmitted with MSBF set. If MSBF is set and the frame is smaller than 10 bits, only the contents of transmit buffer 0 will be transmitted.

When receiving a large frame, BYTESWAP in USARTn_CTRL determines the order the way the large frame is split into the two buffer elements. If BYTESWAP is cleared, the least significant 8 bits of the received frame are loaded into the first element of the receive buffer, and the remaining bits are loaded into the second element, as shown in Figure 18.13 USART Reception of Large Frames on page 542. The first byte read from the buffer thus contains the 8 least significant bits. Set BYTESWAP to reverse the order.

The status bits are loaded into both elements of the receive buffer. The frame is not moved from the receive shift register before there are two free spaces in the receive buffer.




Figure 18.13. USART Reception of Large Frames

The two buffer elements can be read at the same time using the USARTn_RXDOUBLE or USARTn_RXDOUBLEX register. RXDATA0 then refers to buffer element 0 and RXDATA1 refers to buffer element 1.

Large frames can be used in both asynchronous and synchronous modes.

18.3.2.20 Multi-Processor Mode

To simplify communication between multiple processors, the USART supports a special multi-processor mode. In this mode the 9th data bit in each frame is used to indicate whether the content of the remaining 8 bits is data or an address.

When multi-processor mode is enabled, an incoming 9-bit frame with the 9th bit equal to the value of MPAB in USARTn_CTRL is identified as an address frame. When an address frame is detected, the MPAF interrupt flag in USARTn_IF is set, and the address frame is loaded into the receive register. This happens regardless of the value of RXBLOCK in USARTn_STATUS.

Multi-processor mode is enabled by setting MPM in USARTn_CTRL, and the value of the 9th bit in address frames can be set in MPAB. Note that the receiver must be enabled for address frames to be detected. The receiver can be blocked however, preventing data from being loaded into the receive buffer while looking for address frames.

Basic usage of the multi-processor mode is as follows:

- 1. All slaves enable multi-processor mode and, enable and block the receiver. They will now not receive data unless it is an address frame. MPAB in USARTn_CTRL is set to identify frames with the 9th bit high as address frames.
- 2. The master sends a frame containing the address of a slave and with the 9th bit set
- 3. All slaves receive the address frame and get an interrupt. They can read the address from the receive buffer. The selected slave unblocks the receiver to start receiving data from the master.
- 4. The master sends data with the 9th bit cleared
- 5. Only the slave with RX enabled receives the data. When transmission is complete, the slave blocks the receiver and waits for a new address frame.

When a slave has received an address frame and wants to receive the following data, it must make sure the receiver is unblocked before the next frame has been completely received in order to prevent data loss.

BIT8DV in USARTn_CTRL can be used to specify the value of the 9th bit without writing to the transmit buffer with USARTn_TXDATAX or USARTn_TXDOUBLEX, giving higher efficiency in multi-processor mode, as the 9th bit is only set when writing address frames, and 8-bit writes to the USART can be used when writing the data frames.

18.3.2.21 Collision Detection

The USART supports a basic form of collision detection. When the receiver is connected to the output of the transmitter, either by using the LOOPBK bit in USARTn_CTRL or through an external connection, this feature can be used to detect whether data transmitted on the bus by the USART did get corrupted by a simultaneous transmission by another device on the bus.

For collision detection to be enabled, CCEN in USARTn_CTRL must be set, and the receiver enabled. The data sampled by the receiver is then continuously compared with the data output by the transmitter. If they differ, the CCF interrupt flag in USARTn_IF is set. The collision check includes all bits of the transmitted frames. The CCF interrupt flag is set once for each bit sampled by the receiver that differs from the bit output by the transmitter. When the transmitter output is disabled, i.e. the transmitter is tristated, collisions are not registered.

18.3.2.22 SmartCard Mode

In SmartCard mode, the USART supports the ISO 7816 I/O line T0 mode. With exception of the stop-bits (guard time), the 7816 data frame is equal to the regular asynchronous frame. In this mode, the receiver pulls the line low for one baud, half a baud into the guard time to indicate a parity error. This NAK can for instance be used by the transmitter to re-transmit the frame. SmartCard mode is a half duplex asynchronous mode, so the transmitter must be tristated whenever not transmitting data.

To enable SmartCard mode, set SCMODE in USARTn_CTRL, set the number of databits in a frame to 8, and configure the number of stopbits to 1.5 by writing to STOPBITS in USARTn_FRAME.

The SmartCard mode relies on half duplex communication on a single line, so for it to work, both the receiver and transmitter must work on the same line. This can be achieved by setting LOOPBK in USARTn_CTRL or through an external connection. The TX output should be configured as open-drain in the GPIO module.

When no parity error is identified by the receiver, the data frame is as shown in Figure 18.14 USART ISO 7816 Data Frame Without Error on page 544. The frame consists of 8 data bits, a parity bit, and 2 stop bits. The transmitter does not drive the output line during the guard time.




Figure 18.14. USART ISO 7816 Data Frame Without Error

If a parity error is detected by the receiver, it pulls the line I/O line low after half a stop bit, see Figure 18.15 USART ISO 7816 Data Frame With Error on page 544. It holds the line low for one bit-period before it releases the line. In this case, the guard time is extended by one bit period before a new transmission can start, resulting in a total of 3 stop bits.




Figure 18.15. USART ISO 7816 Data Frame With Error

On a parity error, the NAK is generated by hardware. The NAK generated by the receiver is sampled as the stop-bit of the frame. Because of this, parity errors when in SmartCard mode are reported with both a parity error and a framing error.

When transmitting a T0 frame, the USART receiver on the transmitting side samples position 16, 17 and 18 in the stop-bit to detect the error signal when in 16x oversampling mode as shown in Figure 18.16 USART SmartCard Stop Bit Sampling on page 545. Sampling at this location places the stop-bit sample in the middle of the bit-period used for the error signal (NAK).

If a NAK is transmitted by the receiver, it will thus appear as a framing error at the transmitter, and the FERR interrupt flag in USARTn_IF will be set. If SCRETRANS USARTn_CTRL is set, the transmitter will automatically retransmit a NACK'ed frame. The transmitter will retransmit the frame until it is ACK'ed by the receiver. This only works when the number of databits in a frame is configured to 8.

Set SKIPPERRF in USARTn_CTRL to make the receiver discard frames with parity errors. The PERR interrupt flag in USARTn_IF is set when a frame is discarded because of a parity error.




Figure 18.16. USART SmartCard Stop Bit Sampling

For communication with a SmartCard, a clock signal needs to be generated for the card. This clock output can be generated using one of the timers. See the ISO 7816 specification for more info on this clock signal.

SmartCard T1 mode is also supported. The T1 frame format used is the same as the asynchronous frame format with parity bit enabled and one stop bit. The USART must then be configured to operate in asynchronous half duplex mode.

18.3.3 Synchronous Operation

Most of the features in asynchronous mode are available in synchronous mode. Multi-processor mode can be enabled for 9-bit frames, loopback is available and collision detection can be performed.

18.3.3.1 Frame Format

The frames used in synchronous mode need no start and stop bits since a single clock is available to all parts participating in the communication. Parity bits cannot be used in synchronous mode.

The USART supports frame lengths of 4 to 16 bits per frame. Larger frames can be simulated by transmitting multiple smaller frames, i.e. a 22 bit frame can be sent using two 11-bit frames, and a 21 bit frame can be generated by transmitting three 7-bit frames. The number of bits in a frame is set using DATABITS in USARTn_FRAME.

The frames in synchronous mode are by default transmitted with the least significant bit first like in asynchronous mode. The bit-order can be reversed by setting MSBF in USARTn CTRL.

The frame format used by the transmitter can be inverted by setting TXINV in USARTn_CTRL, and the format expected by the receiver can be inverted by setting RXINV, also in USARTn_CTRL.

18.3.3.2 Clock Generation

The bit-rate in synchronous mode is given by Figure 18.17 USART Synchronous Mode Bit Rate on page 546. As in the case of asynchronous operation, the clock division factor have a 15-bit integral part and a 5-bit fractional part.

Figure 18.17. USART Synchronous Mode Bit Rate

Given a desired baud rate brdesired, the clock divider USARTn_CLKDIV can be calculated using Figure 18.18 USART Synchronous Mode Clock Division Factor on page 546

$$USARTn_CLKDIV = 256 \times (f_{HFPERCLK}/(2 \times brdesired) - 1)$$

Figure 18.18. USART Synchronous Mode Clock Division Factor

When the USART operates in master mode, the highest possible bit rate is half the peripheral clock rate. When operating in slave mode however, the highest bit rate is an eighth of the peripheral clock:

- Master mode: br_{max} = f_{HFPERCLK}/2
- Slave mode: br_{max} = f_{HFPERCLK}/8

On every clock edge data on the data lines, MOSI and MISO, is either set up or sampled. When CLKPHA in USARTn_CTRL is cleared, data is sampled on the leading clock edge and set-up is done on the trailing edge. If CLKPHA is set however, data is set-up on the leading clock edge, and sampled on the trailing edge. In addition to this, the polarity of the clock signal can be changed by setting CLKPOL in USARTn_CTRL, which also defines the idle state of the clock. This results in four different modes which are summarized in Table 18.8 USART SPI Modes on page 546. Figure 18.19 USART SPI Timing on page 546 shows the resulting timing of data set-up and sampling relative to the bus clock.

SPI mode **CLKPOL CLKPHA** Leading Edge **Trailing Edge** 0 0 0 Rising, sample Falling, set-up 0 1 1 Rising, set-up Falling, sample 1 0 2 Falling, sample Rising, set-up 3 1 1 Falling, set-up Rising, sample

Table 18.8. USART SPI Modes




Figure 18.19. USART SPI Timing

If CPHA=1, the TX underflow flag, TXUF, will be set on the first setup clock edge of a frame in slave mode if TX data is not available. If CPHA=0, TXUF is set if data is not available in the transmit buffer three HFPERCLK cycles prior to the first sample clock edge. The

RXDATAV flag is updated on the last sample clock edge of a transfer, while the RX overflow interrupt flag, RXOF, is set on the first sample clock edge if the receive buffer overflows. When a transfer has been performed, interrupt flags TXBL and TXC are updated on the first setup clock edge of the succeeding frame, or when CS is deasserted.

18.3.3.3 Master Mode

When in master mode, the USART is in full control of the data flow on the synchronous bus. When operating in full duplex mode, the slave cannot transmit data to the master without the master transmitting to the slave. The master outputs the bus clock on USn_CLK.

Communication starts whenever there is data in the transmit buffer and the transmitter is enabled. The USART clock then starts, and the master shifts bits out from the transmit shift register using the internal clock.

When there are no more frames in the transmit buffer and the transmit shift register is empty, the clock stops, and communication ends. When the receiver is enabled, it samples data using the internal clock when the transmitter transmits data. Operation of the RX and TX buffers is as in asynchronous mode.

18.3.3.4 Operation of USn_CS Pin

When operating in master mode, the USn CS pin can have one of two functions, or it can be disabled.

If USn_CS is configured as an output, it can be used to automatically generate a chip select for a slave by setting AUTOCS in USARTn_CTRL. If AUTOCS is set, USn_CS is activated before a transmission begins, and deactivated after the last bit has been transmitted and there is no more data in the transmit buffer.

The time between when CS is asserted and the first bit is transmitted can be controlled using the USART Timer and with CSSETUP in USARTn_TIMING. Any of the three comparators can be used to set this delay. If new data is ready for transmission before CS is deasserted, the data is sent without deasserting CS in between. CSHOLD in USARTn_TIMING keeps CS asserted after the end of frame for the number of baud-times specified.

By default, USn CS is active low, but its polarity can be inverted by setting CSINV in USARTn CTRL.

When USn_CS is configured as an input, it can be used by another master that wants control of the bus to make the USART release it. When USn_CS is driven low, or high if CSINV is set, the interrupt flag SSM in USARTn_IF is set, and if CSMA in USARTn_CTRL is set, the USART goes to slave mode.

18.3.3.5 AUTOTX

A synchronous master is required to transmit data to a slave in order to receive data from the slave. In some cases, only a few words are transmitted and a lot of data is then received from the slave. In that case, one solution is to keep feeding the TX with data to transmit, but that consumes system bandwidth. Instead AUTOTX can be used.

When AUTOTX in USARTn_CTRL is set, the USART transmits data as long as there is available space in the RX shift register for the chosen frame size. This happens even though there is no data in the TX buffer. The TX underflow interrupt flag TXUF in USARTn_IF is set on the first word that is transmitted which does not contain valid data.

During AUTOTX the USART will always send the previous sent bit, thus reducing the number of transitions on the TX output. So if the last bit sent was a 0, 0's will be sent during AUTOTX and if the last bit sent was a 1, 1's will be sent during AUTOTX.

18.3.3.6 Slave Mode

When the USART is in slave mode, data transmission is not controlled by the USART, but by an external master. The USART is therefore not able to initiate a transmission, and has no control over the number of bytes written to the master.

The output and input to the USART are also swapped when in slave mode, making the receiver take its input from USn_TX (MOSI) and the transmitter drive USn_RX (MISO).

To transmit data when in slave mode, the slave must load data into the transmit buffer and enable the transmitter. The data will remain in the USART until the master starts a transmission by pulling the USn_CS input of the slave low and transmitting data. For every frame the master transmits to the slave, a frame is transferred from the slave to the master. After a transmission, MISO remains in the same state as the last bit transmitted. This also applies if the master transmits to the slave and the slave TX buffer is empty.

If the transmitter is enabled in synchronous slave mode and the master starts transmission of a frame, the underflow interrupt flag TXUF in USARTn IF will be set if no data is available for transmission to the master.

If the slave needs to control its own chip select signal, this can be achieved by clearing CSPEN in the ROUTE register. The internal chip select signal can then be controlled through CSINV in the CTRL register. The chip select signal will be CSINV inverted, i.e. if CSINV is cleared, the chip select is active and vice versa.

18.3.3.7 Synchronous Half Duplex Communication

Half duplex communication in synchronous mode is very similar to half duplex communication in asynchronous mode as detailed in 18.3.2.15 Asynchronous Half Duplex Communication. The main difference is that in this mode, the master must generate the bus clock even when it is not transmitting data, i.e. it must provide the slave with a clock to receive data. To generate the bus clock, the master should transmit data with the transmitter tristated, i.e. TXTRI in USARTn_STATUS set, when receiving data. If 2 bytes are expected from the slave, then transmit 2 bytes with the transmitter tristated, and the slave uses the generated bus clock to transmit data to the master. TXTRI can be set by setting the TXTRIEN command bit in USARTn_CMD.

Note: When operating as SPI slave in half duplex mode, TX has to be tristated (not disabled) during data reception if the slave is to transmit data in the current transfer.

18.3.3.8 I2S

I2S is a synchronous format for transmission of audio data. The frame format is 32-bit, but since data is always transmitted with MSB first, an I2S device operating with 16-bit audio may choose to only process the 16 msb of the frame, and only transmit data in the 16 msb of the frame.

In addition to the bit clock used for regular synchronous transfers, I2S mode uses a separate word clock. When operating in mono mode, with only one channel of data, the word clock pulses once at the start of each new word. In stereo mode, the word clock toggles at the start of new words, and also gives away whether the transmitted word is for the left or right audio channel; A word transmitted while the word clock is low is for the left channel, and a word transmitted while the word clock is high is for the right.

When operating in I2S mode, the CS pin is used as a the word clock. In master mode, this is automatically driven by the USART, and in slave mode, the word clock is expected from an external master.

18.3.3.9 Word Format

The general I2S word format is 32 bits wide, but the USART also supports 16-bit and 8-bit words. In addition to this, it can be specified how many bits of the word should actually be used by the USART. These parameters are given by FORMAT in USARTn_I2SCTRL.

As an example, configuring FORMAT to using a 32-bit word with 16-bit data will make each word on the I2S bus 32-bits wide, but when receiving data through the USART, only the 16 most significant bits of each word can be read out of the USART. Similarly, only the 16 most significant bits have to be written to the USART when transmitting. The rest of the bits will be transmitted as zeroes.

18.3.3.10 Major Modes

The USART supports a set of different I2S formats as shown in Table 18.9 USART I2S Modes on page 549, but it is not limited to these modes. MONO, JUSTIFY and DELAY in USARTn_I2SCTRL can be mixed and matched to create an appropriate format. MONO enables mono mode, i.e. one data stream instead of two which is the default. JUSTIFY aligns data within a word on the I2S bus, either left or right which can bee seen in figures Figure 18.22 USART Left-Justified I2S Waveform on page 550 and Figure 18.23 USART Right-Justified I2S Waveform on page 550. Finally, DELAY specifies whether a new I2S word should be started directly on the edge of the word-select signal, or one bit-period after the edge.

Table 18.9. USART I2S Modes

Mode	MONO	JUSTIFY	DELAY	CLKPOL
Regular I2S	0	0	1	0
Left-Justified	0	0	0	1
Right-Justified	0	1	0	1
Mono	1	0	0	0

The regular I2S waveform is shown in Figure 18.20 USART Standard I2S Waveform on page 549 and Figure 18.21 USART Standard I2S Waveform (Reduced Accuracy) on page 549. The first figure shows a waveform transmitted with full accuracy. The wordlength can be configured to 32-bit, 16-bit or 8-bit using FORMAT in USARTn_I2SCTRL. In the second figure, I2S data is transmitted with reduced accuracy, i.e. the data transmitted has less bits than what is possible in the bus format.

Note that the msb of a word transmitted in regular I2S mode is delayed by one cycle with respect to word select




Figure 18.20. USART Standard I2S Waveform




Figure 18.21. USART Standard I2S Waveform (Reduced Accuracy)

A left-justified stream is shown in Figure 18.22 USART Left-Justified I2S Waveform on page 550. Note that the MSB comes directly after the edge on the word-select signal in contradiction to the regular I2S waveform where it comes one bit-period after.




Figure 18.22. USART Left-Justified I2S Waveform

A right-justified stream is shown in Figure 18.23 USART Right-Justified I2S Waveform on page 550. The left and right justified streams are equal when the data-size is equal to the word-width.




Figure 18.23. USART Right-Justified I2S Waveform

In mono-mode, the word-select signal pulses at the beginning of each word instead of toggling for each word. Mono I2S waveform is shown in Figure 18.24 USART Mono I2S Waveform on page 550.




Figure 18.24. USART Mono I2S Waveform

18.3.3.11 Using I2S Mode

When using the USART in I2S mode, DATABITS in USARTn_FRAME must be set to 8 or 16 data-bits. 8 databits can be used in all modes, and 16 can be used in the modes where the number of bytes in the I2S word is even. In addition to this, MSBF in USARTn CTRL should be set, and CLKPOL and CLKPHA in USARTn CTRL should be cleared.

The USART does not have separate TX and RX buffers for left and right data, so when using I2S in stereo mode, the application must keep track of whether the buffers contain left or right data. This can be done by observing TXBLRIGHT, RXDATAVRIGHT and RXFULLRIGHT in USARTn_STATUS. TXBLRIGHT tells whether TX is expecting data for the left or right channel. It will be set with TXBL if right data is expected. The receiver will set RXDATAVRIGHT if there is at least one right element in the buffer, and RXFULL-RIGHT if the buffer is full of right elements.

When using I2S with DMA, separate DMA requests can be used for left and right data by setting DMASPLIT in USARTn I2SCTRL.

In both master and slave mode the USART always starts transmitting on the LEFT channel after being enabled. In master mode, the transmission will stop if TX becomes empty. In that case, TXC is set. Continuing the transmission in this case will make the data-stream continue where it left off. To make the USART start on the LEFT channel after going empty, disable and re-enable TX.

18.3.4 Hardware Flow Control

Hardware flow control can be used to hold off the link partner's transmission until RX buffer space is available. Use RTSPEN and CTSPEN in USARTn_ROUTEPEN to allocate the hardware flow control to GPlOs. RTS is an out going signal which indicates that RX buffer space is available to receive a frame. The link partner is being requested to send its data when RTS is asserted. CTS is an incoming signal to stop the next TX data from going out. When CTS is negated, the frame currently being transmitted is completed before stopping. CTS indicates that the link partner has RX buffer space available, and the local transmitter is clear to send. Also use CTSEN in USARTn_CTLX to enable the CTS input into the TX sequencer. For debug use set DBGHALT in USARTn_CTRLX which will force the RTS to request one frame from the link partner when the CPU core single steps.

18.3.5 Debug Halt

When DBGHALT in USART_CTRLX is clear, RTS is only dependent on the RX buffer having space available to receive data. Incoming data is always received until both the RX buffer is full and the RX shift register is full regardless of the state of DBGHALT or chip halt. Additional incoming data is discarded. When DBGHALT is set, RTS deasserts on RX buffer full or when chip halt is high. However, a low pulse detected on chip halt will keep RTS asserted when no frame is being received. At the start of frame reception, RTS will deassert if chip halt is high and DBGHALT is set. This behavior allows single stepping to pulse the chip halt low for a cycle, and receive the next frame. The link partner must stop transmitting when RTS is deasserted, or the RX buffer could overflow. All data in the transmit buffer is sent out even when chip halt is asserted; therefore, the DMA will need to be set to stop sending the USART TX data during chip halt.

18.3.6 PRS-triggered Transmissions

If a transmission must be started on an event with very little delay, the PRS system can be used to trigger the transmission. The PRS channel to use as a trigger can be selected using TSEL in USARTn_TRIGCTRL. When a positive edge is detected on this signal, the receiver is enabled if RXTEN in USARTn_TRIGCTRL is set, and the transmitter is enabled if TXTEN in USARTn_TRIGCTRL is set. Only one signal input is supported by the USART.

The AUTOTX feature can also be enabled via PRS. If an external SPI device sets a pin high when there is data to be read from the device, this signal can be routed to the USART through the PRS system and be used to make the USART clock data out of the external device. If AUTOTXTEN in USARTn_TRIGCTRL is set, the USART will transmit data whenever the PRS signal selected by TSEL is high given that there is enough room in the RX buffer for the chosen frame size. Note that if there is no data in the TX buffer when using AUTOTX, the TX underflow interrupt will be set.

AUTOTXTEN can also be combined with TXTEN to make the USART transmit a command to the external device prior to clocking out data. To do this, disable TX using the TXDIS command, load the TX buffer with the command and enable AUTOTXTEN and TXTEN. When the selected PRS input goes high, the USART will now transmit the loaded command, and then continue clocking out while both the PRS input is high and there is room in the RX buffer

18.3.7 PRS RX Input

The USART can be configured to receive data directly from a PRS channel by setting RXPRS in USARTn_INPUT. The PRS channel used is selected using RXPRSSEL in USARTn_INPUT. This way, for example, a differential RX signal can be input to the ACMP and the output routed via PRS to the USART.

18.3.8 PRS CLK Input

The USART can be configured to receive clock directly from a PRS channel by setting CLKPRS in USARTn_INPUT. The PRS channel used is selected using CLKPRSSEL in USARTn_INPUT. This is useful in synchronous slave mode and can together with RX PRS input be used to input data from PRS.

18.3.9 DMA Support

The USART has full DMA support. The DMA controller can write to the transmit buffer using the registers USARTn_TXDATA, USARTn_TXDOUBLE and USARTn_TXDOUBLEX, and it can read from the receive buffer using the registers USARTn_RXDATA, USARTn_RXDATAX, USARTn_RXDOUBLE and USARTn_RXDOUBLEX. This enables single byte transfers, 9 bit data + control/status bits, double byte and double byte + control/status transfers both to and from the USART.

A request for the DMA controller to read from the USART receive buffer can come from the following source:

- · Data available in the receive buffer
- Data available in the receive buffer and data is for the RIGHT I2S channel. Only used in I2S mode.

A write request can come from one of the following sources:

- Transmit buffer and shift register empty. No data to send.
- Transmit buffer has room for more data. This does not check the TXBIL for half full. For DMA use, it is either full or empty.
- · Transmit buffer has room for RIGHT I2S data. Only used in I2S mode

Even though there are two sources for write requests to the DMA, only one should be used at a time, since the requests from both sources are cleared even though only one of the requests are used.

In some cases, it may be sensible to temporarily stop DMA access to the USART when an error such as a framing error has occurred. This is enabled by setting ERRSDMA in USARTn CTRL.

For Synchronous mode full duplex operation, if both receive buffer and transmit buffer are served by DMA, to make sure receive buffer is not overflowed the settings below should be followed.

- The DMA channel that serves receive buffer should have higher priority than the DMA channel that serves transmit buffer.
- TXBL should be used as write request for transmit buffer DMA channel.
- · IGNORESREQ should be set for both DMA channel.

18.3.10 Timer

In addition to the TX sequence timer, there is a versatile 8 bit timer that can generate up to three event pulses. These pulses can be used to create timing for a variety of uses such as RX timeout, break detection, response timeout, and RX enable delay. Transmission delay, CS setup, inter-character spacing, and CS hold use the TX sequence counter. The TX sequencer counter can use the three 8 bit compare values or preset values for delays. There is one general counter with three comparators. Each comparator has a start source, a stop source, a restart enable, and a timer compare value. The start source enables the comparator, resets the counter, and starts the counter. If the counter is already running, the start source will reset the counter and restart it.

Any comparator could start the counter using the same start source but have different timing events programmed into TCMPVALn in USARTn_TIMECMPn. The TCMP0, TCMP1, or TCMP2 events can be preempted by using the comparator stop source to disable the comparator before the counter reaches TCMPVAL0, TCMPVAL1, or TCMPVAL2. If one comparator gets disabled while the other comparator is still enabled, the counter continues counting. By default the counter will count up to 256 and stop unless a RESTARTEN is set in one of the USARTn_TIMECMPn registers. By using RESTARTEN and an interval programmed into TCMPVAL, an interval timer can be set up. The TSTART field needs to be changed to DISABLE to stop the interval timer. The timer stops running once all of the comparators are disabled. If a comparator's start and stop sources both trigger the same cycle, the TCMPn event triggers, the comparator stays enabled, and the counter begins counting from zero.

The TXDELAY, CSSETUP, ICS, and CSHOLD in USARTn_TIMING are used to program start of transmission delay, chip select setup delay, inter-character space, and chip select hold delay. Either a preset value of 0, 1, 2, 3, or 7 can be used for any of these delays; or the value in TCMPVALn may be used to set the delay. Using the preset values leaves the TCMPVALn free for other uses. The same TCMPVALn may be used for multiple events that require the same timing. The transmit sequencer's counter can run in parallel with the timer's counter. The counters and controls are shown in Figure 18.25 USART Timer Block Diagram on page 554.




Figure 18.25. USART Timer Block Diagram

The following sections will go into more details on programming the various usage cases.

Table 18.10. USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn

Application	TSTARTn	TSTOPn	TCMPVALn	Other
Response Timeout	TSTART0 = TXEOF	TSTOP0 = RXACT	TCMPVAL0 = 0x08	TCMP0 in USARTn_IEN
Receiver Timeout	TSTART1 = RXEOF	TSTOP1 = RXACT	TCMPVAL1 = 0x08	TCMP1 in USARTn_IEN
Large Receiver Timeout	TSTART1 = RXEOF, TCMP1	TSTOP1 = RXACT	TCMPVAL1 = 0xFF	TCMP1 in USARTn_IEN; TIME- RRESTARTED in USARTn_STA- TUS; RESTART1EN in USARTn_TIMECMP1

Application	TSTARTn	TSTOPn	TCMPVALn	Other
Break Detect	TSTART1 = RXACT	TSTOP1 = RXACTN	TCMPVAL1 = 0x0C	TCMP1 in USARTn_IEN
TX delayed start of transmission and CS setup	TSTART0 = DISA- BLE, TSTART1 = DISABLE	TSTOP0 = TCMP0, TSTOP1 = TCMP1	TCMPVAL0 = 0x04, TCMPVAL1 = 0x02	TXDELAY = TCMP0, CSSETUP = TCMP1 in USARTn_TIMING; AUTOCS in USARTn_CTRL
TX inter-character spacing	TSTART2 = DISA- BLE	TSTOP2 = TCMP2	TCMPVAL2 = 0x03	ICS = TCMP2 in USARTn_TIMING; AUTOCS in USARTn_CTRL
TX Chip Select End Delay	TSTART1 = DISA- BLE	TSTOP1 = TCMP1	TCMPVAL1 = 0x04	CSHOLD = TCMP1 in USARTn_TIMING; AUTOCS in USARTn_CTRL
Response Delay	TSTART1 = RXEOF	TSTOP1 = TCMP1	TCMPVAL1 = 0x08	TXARX1EN in USARTn_TRIGCTRL
Combined TX and RX Example	TSTART1 = RXEOF, TSTART0 = TXEOF	TSTOP1 = TCMP1, TSTOP0 = TCMP0	TCMPVAL1 = 0x1C, TCMPVAL0 = 0x10	TXARX1EN, RXATX0EN in USARTn_TRIGCTRL; CSSETUP = 0x7, CSHOLD = 0x3 in USARTn_TIMING
Combined Delayed TX and Receiver Timeout Example	TSTART0 = TCMPVAL0, TSTART1 = RXEOF	TSTOP0 = RXACTN, TSTOP1 = RXACT	TCMPVAL0 = 0x20, TCMPVAL1 = 0x0C	TXARX0EN in USARTn_TRIGCTRL; TCMP0 in USARTn_IEN

Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 shows some examples of how the USART timer can be programmed for various applications. The following sections will describe more details for each applications shown in the table.

18.3.10.1 Response Timeout

Response Timeout is when a UART master sends a frame and expects the slave to respond within a certain number of baud-times. Refer to Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for specific register settings. Comparator 0 will be looking for TX end of frame to use as the timer start source. For this example, a receiver start of frame RXACT has not been detected for 8 baud-times, and the TCMP0 interrupt in USARTn_IF is set. If an RX start bit is detected before the 8 baud-times, comparator 0 is disabled before the TCMP0 event can trigger.




Figure 18.26. USART Response Timeout

18.3.10.2 RX Timeout

A receiver timeout function can be implemented by using the RX end of frame to start comparator 1 and look for the RX start bit RXACT to disable the comparator. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example. As long as the next RX start bit occurs before the counter reaches the comparator 1 value TCMPVAL1, the interrupt will not get set. In this example the RX Timeout was set to 8 baud-times. To get an RX timeout larger than 256 baud-times, RESTART1EN in USARTn_TIMER can used to restart the counter when it reaches TCMPVAL1. By setting TCMPVAL1 in USARTn_TIMING to 0xFF, an interrupt will be generated after 256 baud-times. An interrupt service routine can then increment a memory location until the desired timeout is reached. Once the RX start bit is detected, comparator 1 will be disabled. If TIMERRESTARTED in USARTn_STATUS is clear, the TCMP1 interrupt is the first interrupt after RXEOF.




Figure 18.27. USART RX Timeout

18.3.10.3 Break Detect

LIN bus and half-duplex UARTs can take advantage of the timer configured for break detection where RX is held low for a number of baud-times to indicate a break condition. Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 shows the settings for this mode. Each time RX is active (default of low) such as for a start bit, the timer begins counting. If the counter reaches 12 baud-times before RX goes to inactive RXACTN (default of high), an interrupt is asserted.




Figure 18.28. USART Break Detection

18.3.10.4 TX Start Delay

Some applications may require a delay before the start of transmission. This example in Figure 18.29 USART TXSEQ Timing on page 557 shows the TXSEQ timer used to delay the start of transmission by 4 baud times before the start of CS, and by 2 baud times with CS asserted. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on how to configure this mode. The TX sequencer could be enabled on PRS and start the TXSEQ counter running for 4 baud times as programmed in TCMPVAL0. Then CS is asserted for 2 baud times before the transmitter begins sending TX data. TXDELAY in USARTn_TIMING is the initial delay before any CS assertion, and CSSETUP is the delay during CS assertion. There are several small preset timing values such as 1, 2, 3, or 7 that can be used for some of the TX sequencer timing which leaves TCMPVAL0, TCMPVAL1, and TCMPVAL2 free for other uses.




Figure 18.29. USART TXSEQ Timing

18.3.10.5 Inter-Character Space

In addition to delaying the start of frame transmission, it is sometimes necessary to also delay the time between each transmit character (inter-character space). After the first transmission, the inter-character space will delay the start of all subsequent transmissions until the transmit buffer is empty. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example. For this example in Figure 18.29 USART TXSEQ Timing on page 557 ICS is set to TCMP2 in USARTn_TIMING. To keep CS asserted during the inter-character space, set AUTOCS in USARTn_CTRL. There are a few small preset timing values provided for TX sequence timing. Using these preset timing values can free up the TCMPVALn for other uses. For this example, the inter-character space is set to 0x03 and a preset value could be used.

18.3.10.6 TX Chip Select End Delay

The assertion of CS can be extended after the final character of the frame by using CSHOLD in USARTn_TIMING. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example. AUTOCS in USARTn_CTRL needs to be set to extend the CS assertion after the last TX character is transmitted as shown in Figure 18.29 USART TXSEQ Timing on page 557.

18.3.10.7 Response Delay

A response delay can be used to hold off the transmitter until a certain number of baud-times after the RX frame. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example. TXARX1EN in USARTn_TRIGCTRL tells the TX sequencer to trigger after RX EOF plus tcmp1val baud times.




Figure 18.30. USART Response Delay

18.3.10.8 Combined TX and RX Example

This example describes how to alternate between TX and RX frames. This has a 28 baud-time space after RX and a 16 baud-time space after TX. The TSTART1 in USARTn_TIMECMP1 is set to RXEOF which uses the the receiver end of frame to start the timer. The TSTOP1 is set to TCMP1 to generate an event after 28 baud times. Set TXARX1EN in USARTn_TRIGCTRL, and the transmitter is held off until 28 baud times. TCMPVAL in USARTn_TIMECMP1 is set to 0x1C for 28 baud times. By setting TSTART0 in USARTn_TIMECMP0 to TXEOF, the timer will be started after the transmission has completed. RXATX0EN in USARTn_TRIGCTRL is used to delay enabling of the receiver until 16 baud times after the transmitter has completed. Write 0x10 into TCMPVAL of USARTn_TIMECMP0 for a 16 baud time delay. CS is also asserted 7 baud-times before start of transmission by setting CSSETUP to 0x7 in USARTn_TIMING. To keep CS asserted for 3 baud-times after transmission completes, CSHOLD is set to 0x3 in USARTn_TIMING. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example.

18.3.10.9 Combined TX Delay and RX Break Detect

This example describes how to delay TX transmission after an RX frame and how to have a break condition signal an interrupt. See Table 18.10 USART Application Settings for USARTn_TIMING and USARTn_TIMECMPn on page 554 for details on setting up this example. The TX delay is set up by using transmit after RX, TXARX0EN in USARTn_TRIGCTRL to start the timer. TSTART0 in USARTn_TIMECMP0 is set to RXEOF which enables the transitter of the timer delay. For this example TCMPVAL in USARTn_TIMECMP0 is set to 0x20 to create a 32 baud-time delay between the end of the RX frame and the start of the TX frame. The break detect is configured by setting TSTART1 to RXACT to detect the start bit, and setting TSTOP1 to RXACTN to detect RX going high. In this case the interrupt asserts after RX stays low for 12 baud-times, so TCMPVAL1 is set to 0x0C.

18.3.10.10 Other Stop Conditions

There is also a timer stop on TX start using the TXST setting in TSTOP of USARTn_TIMECMPn. This can be used to see that the DMA has not written to the TXBUFFER for a given time.

18.3.11 Interrupts

The interrupts generated by the USART are combined into two interrupt vectors. Interrupts related to reception are assigned to one interrupt vector, and interrupts related to transmission are assigned to the other. Separating the interrupts in this way allows different priorities to be set for transmission and reception interrupts.

The transmission interrupt vector groups the transmission-related interrupts generated by the following interrupt flags:

- TXC
- TXBL
- TXOF
- CCF
- TXIDLE

The reception interrupt on the other hand groups the reception-related interrupts, triggered by the following interrupt flags:

- RXDATAV
- RXFULL
- RXOF
- RXUF
- PERR
- FERR
- MPAF
- SSM
- TCMPn

If USART interrupts are enabled, an interrupt will be made if one or more of the interrupt flags in USART_IF and their corresponding bits in USART_IEN are set.

18.3.12 IrDA Modulator/ Demodulator

The IrDA modulator implements the physical layer of the IrDA specification, which is necessary for communication over IrDA. The modulator takes the signal output from the USART module, and modulates it before it leaves the USART. In the same way, the input signal is demodulated before it enters the actual USART module. The modulator implements the original Rev. 1.0 physical layer and one high speed extension which supports speeds from 2.4 kbps to 1.152 Mbps.

The data from and to the USART is represented in a NRZ (Non Return to Zero) format, where the signal value is at the same level through the entire bit period. For IrDA, the required format is RZI (Return to Zero Inverted), a format where a "1" is signalled by holding the line low, and a "0" is signalled by a short high pulse. An example is given in Figure 18.31 USART Example RZI Signal for a given Asynchronous USART Frame on page 559.




Figure 18.31. USART Example RZI Signal for a given Asynchronous USART Frame

The IrDA module is enabled by setting IREN. The USART transmitter output and receiver input is then routed through the IrDA modulator.

The width of the pulses generated by the IrDA modulator is set by configuring IRPW in USARTn_IRCTRL. Four pulse widths are available, each defined relative to the configured bit period as listed in Table 18.11 USART IrDA Pulse Widths on page 559.

IRPW	Pulse width OVS=0	Pulse width OVS=1	Pulse width OVS=2	Pulse width OVS=3
00	1/16	1/8	1/6	1/4
01	2/16	2/8	2/6	N/A
10	3/16	3/8	N/A	N/A
11	4/16	N/A	N/A	N/A

Table 18.11. USART IrDA Pulse Widths

By default, no filter is enabled in the IrDA demodulator. A filter can be enabled by setting IRFILT in USARTn_IRCTRL. When the filter is enabled, an incoming pulse has to last for 4 consecutive clock cycles to be detected by the IrDA demodulator.

Note that by default, the idle value of the USART data signal is high. This means that the IrDA modulator generates negative pulses, and the IrDA demodulator expects negative pulses. To make the IrDA module use RZI signalling, both TXINV and RXINV in USARTn_CTRL must be set.

The IrDA module can also modulate a signal from the PRS system, and transmit a modulated signal to the PRS system. To use a PRS channel as transmitter source instead of the USART, set IRPRSEN in USARTn_IRCTRL high. The channel is selected by configuring IRPRSSEL in USARTn_IRCTRL.

18.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	USARTn_CTRL	RW	Control Register
0x004	USARTn_FRAME	RW	USART Frame Format Register
0x008	USARTn_TRIGCTRL	RW	USART Trigger Control Register
0x00C	USARTn_CMD	W1	Command Register
0x010	USARTn_STATUS	R	USART Status Register
0x014	USARTn_CLKDIV	RWH	Clock Control Register
0x018	USARTn_RXDATAX	R(a)	RX Buffer Data Extended Register
0x01C	USARTn_RXDATA	R(a)	RX Buffer Data Register
0x020	USARTn_RXDOUBLEX	R(a)	RX Buffer Double Data Extended Register
0x024	USARTn_RXDOUBLE	R(a)	RX FIFO Double Data Register
0x028	USARTn_RXDATAXP	R	RX Buffer Data Extended Peek Register
0x02C	USARTn_RXDOUBLEXP	R	RX Buffer Double Data Extended Peek Register
0x030	USARTn_TXDATAX	W	TX Buffer Data Extended Register
0x034	USARTn_TXDATA	W	TX Buffer Data Register
0x038	USARTn_TXDOUBLEX	W	TX Buffer Double Data Extended Register
0x03C	USARTn_TXDOUBLE	W	TX Buffer Double Data Register
0x040	USARTn_IF	R	Interrupt Flag Register
0x044	USARTn_IFS	W1	Interrupt Flag Set Register
0x048	USARTn_IFC	(R)W1	Interrupt Flag Clear Register
0x04C	USARTn_IEN	RW	Interrupt Enable Register
0x050	USARTn_IRCTRL	RW	IrDA Control Register
0x058	USARTn_INPUT	RW	USART Input Register
0x05C	USARTn_I2SCTRL	RW	I2S Control Register
0x060	USARTn_TIMING	RW	Timing Register
0x064	USARTn_CTRLX	RW	Control Register Extended
0x068	USARTn_TIMECMP0	RW	Used to Generate Interrupts and Various Delays
0x06C	USARTn_TIMECMP1	RW	Used to Generate Interrupts and Various Delays
0x070	USARTn_TIMECMP2	RW	Used to Generate Interrupts and Various Delays
0x074	USARTn_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x078	USARTn_ROUTELOC0	RW	I/O Routing Location Register
0x07C	USARTn_ROUTELOC1	RW	I/O Routing Location Register

18.5 Register Description

18.5.1 USARTn_CTRL - Control Register

Offset															Bi	t Po	siti	on													
0x000	31	30	29	28	27	56	25	24	23	22	21	20	9	8	17	16	15	4	13	12	7	9	6	_∞	7	9 2	4	က	7	_	0
Reset	0	0	0	0			0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0		0x0	0	0	0	0	0
Access	S. S.	Z.	§ N	Z.			\ N	Z N	X W	W.	¥ §	RW	₩ M	¥ ≷	W.	XX W	W.	Z.	ZW.	¥ §	Z.	W W	RW	W.		RW W	Z.	\ N	W W	RW	W.
Name	SMSDELAY	MVDIS	AUTOTX	BYTESWAP			SSSEARLY	ERRSTX	ERRSRX	ERRSDMA	BIT8DV	SKIPPERRF	SCRETRANS	SCMODE	AUTOTRI	AUTOCS	CSINV	VNIXL	RXINV	TXBIL	CSMA	MSBF	CLKPHA	CLKPOL		SNO	MPAB	MPM	CCEN	LOOPBK	SYNC
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion															
31	SM	1SDI	ELA	Υ			0				RW	/	;	Syn	chr	ono	us N	/last	ter S	Sam	ple	Dela	ay								
		lay s	-	chro	nous	s Ma	aste	r saı	mple	e po	int to	o the	e ne	ext s	etup	edo	ge to	im c	prov	e tir	ning	and	d allo	ow c	comi	municat	ion a	at hi	ghe	ſ	
30	M۱	/DIS					0				RW	/		Majo	ority	, Vo	te D)isa	ble												
	Dis	able	e ma	ajorit	ty vo	te f	or 10	6x, 8	3x a	nd 6	o x	ersa	amp	oling	mo	des.															
29	AU	ТОТ	ГХ				0				RW	/		Alwa	ays	Tra	nsm	nit V	Vhe	n R)	(No	t Fu	ıll								
	Tra	ansn	nits a	as lo	ong a	as F	RX is	not	full	. If 7	TX is	em	pty,	unc	lerfl	ows	are	ger	nera	ted.											
28	BY	TES	SWA	P			0				RW	/		Byte	eswa	ap i	n Do	oub	le A	cce	sse	S									
	Se	t to :	swite	ch th	ne or	der	of t	he b	ytes	s in (douk	ole a	acce	sse	S.																
	Va	lue												Des	cript	ion															
	0													Norr	nal l	byte	ord	ler													
	1													Byte	ord	ler s	wap	ped	I												_
27:26	Re	serv	/ed				To tion		ure	con	pati	bility	/ wi	th fu	ture	dev	/ices	s, al	way	s wr	ite k	its t	o 0.	Мо	re in	formatio	on ir	1.2	Col	nvei	7-
25	SS	SEA	\RL`	Y			0				RV	/		Syn	chr	ono	us S	Slav	e Se	etup	Ea	rly									
	Se	tup	data	on	sam	ple	edg	e in	syn	chrc	nou	s sla	ave	mod	de to	imi c	orov	e M	osi	set	up ti	me									
24	ER	RS	ГΧ				0				RW	/		Disa	ble	ΤX	on l	Erro	r												
	Wh	nen :	set,	the	trans	smit	ter i	s dis	sabl	ed c	n fra	amir	ng a	nd p	arity	y err	ors	(asy	ynch	ron	ous	mod	le or	nly)	in th	e receiv	er.				_
	Va	lue												Des	cript	ion															_
	0																									ect on tra		nitte	r		
	1													Rec	eive	d fra	amin	ng ai	nd p	arity	err/	ors (disa	ble t	the t	ransmit	ter				_
23	ER	RSF	₹X				0				RW	/		Disa	ble	RX	on	Erro	or												
	Wh	nen :	set,	the	rece	iver	is d	lisab	oled	on f	ram	ing a	and	pari	ty e	rrors	s (as	sync	hro	nous	s mo	de d	only).							
	Va	lue												Des	cript	ion															_
	0													Fran	ning	and	d pa	rity (erro	rs ha	ave	no e	ffec	t on	rec	eiver					_

Bit	Name	Reset	Access	Description
	1			Framing and parity errors disable the receiver
22	ERRSDMA	0	RW	Halt DMA on Error
	When set, DMA requ	ests will be clea	red on fran	ning and parity errors (asynchronous mode only).
	Value			Description
	0			Framing and parity errors have no effect on DMA requests from the USART
	1			DMA requests from the USART are blocked while the PERR or FERR interrupt flags are set
21	BIT8DV	0	RW	Bit 8 Default Value
	The default value of the 9th bit is set to the			re used, and an 8-bit write operation is done, leaving the 9th bit unspecified,
20	SKIPPERRF	0	RW	Skip Parity Error Frames
	When set, the receiv	er discards fram	es with par	ity errors (asynchronous mode only). The PERR interrupt flag is still set.
19	SCRETRANS	0	RW	SmartCard Retransmit
	When in SmartCard bled.	mode, a NACK'e	ed frame wi	Il be kept in the shift register and retransmitted if the transmitter is still ena-
18	SCMODE	0	RW	SmartCard Mode
	Use this bit to enable	e or disable Sma	artCard mod	de.
17	AUTOTRI	0	RW	Automatic TX Tristate
	When enabled, TXTF mission starts.	RI is set by hard	ware when	ever the transmitter is idle, and TXTRI is cleared by hardware when trans-
	Value			Description
	0			The output on U(S)n_TX when the transmitter is idle is defined by TXINV
	1			U(S)n_TX is tristated whenever the transmitter is idle
16	AUTOCS	0	RW	Automatic Chip Select
	When enabled, the o transmission ends.	utput on USn_C	S will be a	ctivated one baud-period before transmission starts, and deactivated when
15	CSINV	0	RW	Chip Select Invert
	Default value is activ as a slave.	e low. This affec	cts both the	selection of external slaves, as well as the selection of the microcontroller
	Value			Description
	0			Chip select is active low
	1			Chip select is active high
14	TXINV	0	RW	Transmitter Output Invert
	The output from the	USART transmit	tter can opt	ionally be inverted by setting this bit.
	Value			Description
	0			Output from the transmitter is passed unchanged to U(S)n_TX

Bit	Name	Reset	Access	Description			
	1			Output from the transmitter is inverted before it is passed to U(S)n_TX			
13	RXINV	0	RW	Receiver Input Invert			
	Setting this bit will inv	ert the input to t	he USART	receiver.			
	Value			Description			
	0			Input is passed directly to the receiver			
	1			Input is inverted before it is passed to the receiver			
12	TXBIL	0	RW	TX Buffer Interrupt Level			
	Determines the interre	upt and status le	evel of the	transmit buffer.			
	Value	Mode		Description			
	0	EMPTY		TXBL and the TXBL interrupt flag are set when the transmit buffer becomes empty. TXBL is cleared when the buffer becomes nonempty.			
	1	HALFFULL		TXBL and TXBLIF are set when the transmit buffer goes from full to half-full or empty. TXBL is cleared when the buffer becomes full.			
11	CSMA	0	RW	Action on Slave-Select in Master Mode			
	This register determin master mode.	nes the action to	be perform	ned when slave-select is configured as an input and driven low while in			
	Value	Mode		Description			
	0	NOACTION		No action taken			
	1	GOTOSLAVE	MODE	Go to slave mode			
10	MSBF	0	RW	Most Significant Bit First			
	Decides whether data	is sent with the	least sign	ificant bit first, or the most significant bit first.			
	Value			Description			
	0			Data is sent with the least significant bit first			
	1			Data is sent with the most significant bit first			
9	CLKPHA	0	RW	Clock Edge for Setup/Sample			
	Determines where da	ta is set-up and	sampled a	according to the bus clock when in synchronous mode.			
	Value	Mode		Description			
	0	SAMPLELEA	DING	Data is sampled on the leading edge and set-up on the trailing edge of the bus clock in synchronous mode			
	1	SAMPLETRA	ILING	Data is set-up on the leading edge and sampled on the trailing edge of the bus clock in synchronous mode			
8	CLKPOL	0	RW	Clock Polarity			
	Determines the clock	polarity of the b	us clock us	sed in synchronous mode.			
	Value	Mode		Description			
	0	IDLELOW		The bus clock used in synchronous mode has a low base value			

Bit	Name	Reset	Access	Description
	1	IDLEHIGH		The bus clock used in synchronous mode has a high base value
7	Reserved	To ensure cortions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6:5	OVS	0x0	RW	Oversampling
	Sets the number of cl gives better performa		UART bit-	period. More clock cycles gives better robustness, while less clock cycles
	Value	Mode		Description
	0	X16		Regular UART mode with 16X oversampling in asynchronous mode
	1	X8		Double speed with 8X oversampling in asynchronous mode
	2	X6		6X oversampling in asynchronous mode
	3	X4		Quadruple speed with 4X oversampling in asynchronous mode
4	MPAB	0	RW	Multi-Processor Address-Bit
	Defines the value of the frame as a multi-p			s bit. An incoming frame with its 9th bit equal to the value of this bit marks
3	MPM	0	RW	Multi-Processor Mode
	Multi-processor mode	uses the 9th bi	t of the US	ART frames to tell whether the frame is an address frame or a data frame.
	Value			Description
	0			The 9th bit of incoming frames has no special function
	1			An incoming frame with the 9th bit equal to MPAB will be loaded into the receive buffer regardless of RXBLOCK and will result in the MPAB interrupt flag being set
2	CCEN	0	RW	Collision Check Enable
	Enables collision che	cking on data wl	nen operat	ing in half duplex modus.
	Value			Description
	0			Collision check is disabled
	1			Collision check is enabled. The receiver must be enabled for the check to be performed
1	LOOPBK	0	RW	Loopback Enable
	Allows the receiver to	be connected d	lirectly to th	ne USART transmitter for loopback and half duplex communication.
	Value			Description
	0			The receiver is connected to and receives data from U(S)n_RX
	1			The receiver is connected to and receives data from U(S)n_TX
0	SYNC	0	RW	USART Synchronous Mode
		he USART is op		asynchronous or synchronous mode.
	Value			Description
	0			The USART operates in asynchronous mode

Bit	Name	Reset	Access	Description
	1			The USART operates in synchronous mode

18.5.2 USARTn_FRAME - USART Frame Format Register

Offset			Bit Position							
0x004	31 39 29 29 29 27 28 29 29	22 23 24 25 25 27 27 28 28 29 29 29 29 29 29 29 29 29 29 29 29 29	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	- 0						
Reset			000	2						
Access			\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	<u> </u>						
Name			STOPBITS	2 1 4 1 4 1						
Bit	Name	Reset Acc	s Description							
31:14	Reserved	To ensure compatib	ty with future devices, always write bits to 0. More information in 1.2 Cor	nven-						
13:12	STOPBITS	0x1 RW	Stop-Bit Mode							
	Determines the numb	er of stop-bits used.								
	Value	Mode	Description							
	0	HALF	The transmitter generates a half stop bit. Stop-bits are not verified by receiver							
	1	ONE	One stop bit is generated and verified							
	2	ONEANDAHALF	The transmitter generates one and a half stop bit. The receiver verifithe first stop bit	fies						
	3	TWO	The transmitter generates two stop bits. The receiver checks the first stop-bit only	st						
11:10	Reserved	To ensure compatib	ty with future devices, always write bits to 0. More information in 1.2 Cor	nven-						
9:8	PARITY	0x0 RW	Parity-Bit Mode							
	Determines whether prous mode.	parity bits are enabled	nd whether even or odd parity should be used. Only available in asynch	nro-						
	Value	Mode	Description							
	0	NONE	Parity bits are not used							
	2	EVEN	Even parity are used. Parity bits are automatically generated and checked by hardware.							
	3	ODD	Odd parity is used. Parity bits are automatically generated and chec by hardware.	cked						
7:4	Reserved	To ensure compatib	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions							
3:0	DATABITS	0x5 RW	Data-Bit Mode							
	This register sets the	number of data bits in	USART frame.							
	Value	Mode	Description							
	1	FOUR	Each frame contains 4 data bits							
	2	FIVE	Each frame contains 5 data bits							

it	Name	Reset	Access	Description
	3	SIX		Each frame contains 6 data bits
	4	SEVEN		Each frame contains 7 data bits
	5	EIGHT		Each frame contains 8 data bits
	6	NINE		Each frame contains 9 data bits
	7	TEN		Each frame contains 10 data bits
	8	ELEVEN		Each frame contains 11 data bits
	9	TWELVE		Each frame contains 12 data bits
	10	THIRTEEN		Each frame contains 13 data bits
	11	FOURTEEN		Each frame contains 14 data bits
	12	FIFTEEN		Each frame contains 15 data bits
	13	SIXTEEN		Each frame contains 16 data bits

18.5.3 USARTn_TRIGCTRL - USART Trigger Control Register

10.0.0	JAKIII_IIKK				98	,0. 0																					
Offset										В	it Po	siti	on														
0x008	30 29	28 27	26	25 24	23	22	21	20	6 6	12	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset										000					0	0	0	0	0	0	0	0	0				
Access										Z.					RW	₩	N N	S.	₩ M	S S S	S.	₹	S.				
																					_	_	_				
Name															X2EN	X E	XOE	X2EN	X1E	XOE	X	_	z				
										TSEL					RXATX2EN	RXATX1EN	RXATX0EN	TXARX2EN	TXARX1EN	TXARX0EN	AUTOTXTEN	TXTEN	RXTEN				
															<u>~</u>	œ	<u>~</u>	_	_	_	_ <	<u> </u>	<u>~</u>				
Bit	Name			Reset			Acc	es	s De	scrip	tion																
31:20	Reserved			To en	sure	com	patik	bility	y with	future	e dev	/ices	s, alı	ways	wr	ite b	its t	o 0.	Мо	re ir	forr	natio	on in	1.2	Cor	nven	1-
19:16	TSEL			0x0			RW	'	Tr	gger	PRS	s Cr	nanr	nel S	ele	ct											
	Select USA TXTEN.	Value Mode Description 0 PRSCH0 PRS Channel 0 selected														EN a	and										
	Value	Value Mode Description Description PRSCH0 PRS Channel 0 selected																									_
	Value Mode Description 0 PRSCH0 PRS Channel 0 selected																										
	1	PRSCH0 PRS Chann PRSCH1 PRS Chann																									
	2			PRSC	H2				PF	RS Ch	ann	el 2	sele	cted													
	3			PRSC	H3				PF	RS Ch	ann	el 3	sele	cted													
	4			PRSC	H4				PF	RS Ch	ann	el 4	sele	cted													
	5			PRSC	H5				PF	RS Ch	ann	el 5	sele	cted													
	6			PRSC	H6				PF	RS Ch	ann	el 6	sele	cted													
	7			PRSC	H7				PF	RS Ch	ann	el 7	sele	cted													
	8			PRSC	:H8				PF	RS Ch	ann	el 8	sele	cted	l												
	9			PRSC	H9				PF	RS Ch	ann	el 9	sele	cted													
	10			PRSC					PF	RS Ch	ann	el 10) se	lecte	d												
	11			PRSC	H11				PF	RS Ch	ann	el 1	1 se	lecte	d												_
15:13	Reserved			To en	sure	com	patik	bility	y with	future	e dev	vices	s, alı	ways	wr	ite b	its t	o 0.	Мо	re ir	forr	natio	on in	1.2	Cor	nven	1-
12	RXATX2EN	I		0			RW	,		able ud-ti			Tri	gge	r Af	ter ⁻	TX	End	of F	-rar	ne F	Plus	TC	MPV	AL2	2	
	When set, a	a TX er	nd of	frame	will t	rigge	er the	e re	ceiver	after	a To	CMF	PVAI	L2 ba	aud	-time	e de	elay									
11	RXATX1EN	I		0			RW	•		able ud-ti			Tri	gge	r Af	ter ⁻	TX	End	of F	-rar	ne F	Plus	TC	MPV	AL1	I	
	When set, a	a TX er	nd of	frame	will t	rigge	r the	e re	ceiver	after	a To	CMF	PVAI	L1 ba	aud	-time	e de	elay									
10	RXATX0EN	I		0			RW	'		able ud-ti			: Tri	gge	r Af	ter ⁻	TX	End	of F	-rar	ne F	Plus	TC	MPV	'ALC)	
	When set, a	a TX er	nd of	frame	will t	rigge	er the	e re	ceiver	after	a To	CMF	PVAI	L0 ba	aud	-time	e de	elay									

Bit	Name	Reset	Access	Description
9	TXARX2EN	0	RW	Enable Transmit Trigger After RX End of Frame Plus TCMP2VAL
	When set, an RX e	end of frame will	trigger the tra	ansmitter after TCMP2VAL bit times to force a minimum response delay
8	TXARX1EN	0	RW	Enable Transmit Trigger After RX End of Frame Plus TCMP1VAL
	When set, an RX e	end of frame will	trigger the tra	ansmitter after TCMP1VAL bit times to force a minimum response delay
7	TXARX0EN	0	RW	Enable Transmit Trigger After RX End of Frame Plus TCMP0VAL
	When set, an RX e	end of frame will	trigger the tra	ansmitter after TCMP0VAL bit times to force a minimum response delay
6	AUTOTXTEN	0	RW	AUTOTX Trigger Enable
	When set, AUTOT	X is enabled as	long as the P	RS channel selected by TSEL has a high value
5	TXTEN	0	RW	Transmit Trigger Enable
	When set, the PRS	S channel selecte	ed by TSEL s	ets TXEN, enabling the transmitter on positive trigger edges.
4	RXTEN	0	RW	Receive Trigger Enable
	When set, the PRS	S channel select	ed by TSEL s	ets RXEN, enabling the receiver on positive trigger edges.
3:0	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

																	-		<i>y</i> , ,	0111)									
SAR	Tn_	СМІ	D - 0	Con	nma	and	Reg	jist	ter																							
															Bit	Pos	sitio	on														
31	30	29	28	27	26	25	24	23	2 2	2	i	70	19	9	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
												,									0	0	0	0	0	0	0	0	0	0	0	0
																					W1	W	W1	W	W1	W	W	W	W	W1	W	W1
																					CLEARRX	CLEARTX	TXTRIDIS	TXTRIEN	RXBLOCKDIS	RXBLOCKEN	MASTERDIS	MASTEREN	TXDIS	TXEN	RXDIS	RXEN
											_																					
Na	me					R	eset			Α	CC	ess	; I	Des	cript	ion																
	me serv	red				To			е со						cript ture		ices	s, alı	vay	s wi	ite k	oits t	o 0.	Мо	re in	nforn	natio	on ir	1.2	? Co	nvei	n-
Re						To	o ens		e co		atib		wit	th fu		devi	ices	s, alı	vay	s wi	ite b	oits t	o 0.	Мо	re in	nforn	natio	on ir	1.2	? Co	nvei	n-
Re	serv	RRX	rec	ceive	e bu	To tio	o ens	sur		mpa V	atib /1	oility	wit	th fu	ture	devi	ices	;, alı	vay	s wr	ite b	oits t	to 0.	Мо	re in	nforn	matio	on ir	1.2	? Co	nvei	ท-
Re CL Se	serv	RRX	r rec	ceive	e bu	To tio	o ens	sur		mpa V	atib /1 ift	oility	wit	th fu	ture	devi	ices	;, alı	vay	s wi	ite b	oits t	o 0.	Mo	re in	nform	natio	on ir	1.2	? Co	nvei	n-
Re CL Se	EAF	RRX clear				To tio 0 uffer	o ens	sure	ie R	mpa W (sh	ntib /1 ift	regi	wit	th fu	ture	devi	ices	s, alv	way	s wi	ite k	oits t	o 0.	Mo	re in	nforn	natio	on ir	1.2	? Co	nvei	n-
Re CL Se CL Se	EAF	RRX clear RTX clear				To tio 0 uffer	o ens	sure	ie R	mpa W (sh	/1 ift /1	regi	wit	Clear.	ture	devi						its t	o 0.	Mo	re in	nforn	matio	on ir	1.2	? Co	nvei	n-
CL Se CL Se	EAR t to d EAR t to d	RRX clear RTX clear	r tra	nsm	nit b	To tion 0 uffer 0 outfer 0	o ens	I th	he T	W (sh	/1 ift //1	regi	wit	Clear.	ture ar RX	devi						nits t	do 0.	Mo	re in	nforn	matic	on ir	1.2	? Co.	nvei	n-
Re CL Se CL Se TX Dis	EAR t to d EAR t to d	RRX clear RTX clear DIS	r tra	nsm	nit b	To tion 0 uffer 0 outfer 0	o ensons r and	I th	he T	W (sh	/1 ift //1 ut.	regi	witi (iste	Clear. Trar	ture ar RX	devi	Tris	stat	e D	isab	ole	its t	do 0.	Mo	re in	nforn	matio	on ir	1.2	? Co.	nver	n-
			_		_				_	SARTn_CMD - Command Register				SARTn_CMD - Command Register Bit Pos	SARTn_CMD - Command Register Bit Position	SARTn_CMD - Command Register	SARTn_CMD - Command Register Bit Position	Bit Position S	SARTn_CMD - Command Register Bit Position	SARTn_CMD - Command Register Bit Position	SARTn_CMD - Command Register Bit Position											

18.5.5 USARTn_STATUS - USART Status Register

Offset													Bi	t Po	siti	on														
0x010	31	29	28	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	1	0
Reset			·									•	2	OXO		0	_	0	0	0	0	0	0	_	0	0	0	0	0	0
Access													٥	צ		22	22	22	22	~	<u>~</u>	2	~	22	22	22	22	22	2	2
Name													TVDIIGYT	ND LOBOLI		TIMERRESTARTED	TXIDLE	RXFULLRIGHT	RXDATAVRIGHT	TXBSRIGHT	TXBDRIGHT	RXFULL	RXDATAV	TXBL	TXC	TXTRI	RXBLOCK	MASTER	TXENS	RXENS
Bit	Name				Re	set			Ac	ces	s l	Des	crip	tion																
31:18	Reserv	red			To tio		ure	con	npati	bility	/ wi	th fu	ture	dev	vices	s, al	way.	s wr	ite b	its t	o 0.	Мог	re in	forn	natio	on in	1.2	? Coi	nver	1-
17:16	TXBUF	CNT			0x	0			R			TX E	Buff	er C	our	nt														
		Count of TX buffer entry 0, entry 1, and TX shift register. For large frames, the count is only of TX buffer entry 0 and the shifter register. Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions															the ⁻	ГΧ												
15	Reserv	Count of TX buffer entry 0, entry 1, and TX shift register. For large frames, the count is only of TX buffer entry 0 and shifter register. Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions														? Coi	nver	7-												
14	TIMER	reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Co																												
	When to the second TCMP memore	eque interi	nce o	f mu ind T	Itiple FIME	e TC ERR	MP EST	eve AR	nts. TED	Any	no 0x0,	n TC an	MP inte	time errup	er st	tart o	ever	nts v	vill c	lear	TIM	1ERI	RES	STAI	RTE	D. V	Vhe	n th	ere i	s a
13	TXIDLE	E			1				R		•	TX I	dle																	
	Set wh	en T	K idle																											
12	RXFUL	LRIG	SHT		0				R		I	RX F	ull	of F	Righ	t Da	ata													
	When	set, th	ne ent	ire R	X b	uffer	con	tain	ıs riç	ght d	lata	On	ly us	sed	in I2	S m	node	;												
11	RXDAT	ΓAVR	IGHT		0				R		I	RX [Data	Riç	ght															
	When	set, re	eading	g RX	DAT	ГА о	r RX	DA ⁻	TAX	give	es ri	ght	data	ı. Els	se le	eft d	ata i	s re	ad.	Only	use	ed ir	128	S mo	ode					
10	TXBSR	RIGH	Γ		0				R			TX E	Buff	er E	xpe	cts	Sin	gle	Rigl	nt D	ata									
	When	set, th	ne TX	buffe	er e	xpec	ts at	lea		sing	gle r	ight	data	a. El	lse i	t ex	pect	s le	ft da	ta. (Only	use	d in	128	mo	de				
9	TXBDF				0				R					er E	-															
	When	set, th	ne TX	buffe	er e	xpec	ts d	oub		ght c	data	. Els	e it	may	ex	pect	a si	ngle	rig	ht da	ata d	or le	ft da	ata.	Only	/ US	ed ir	12S	mc	de
8	RXFUL				0				R) Fu																
	Set who									n the	e re	ceive	e bu	ıffer	is n	o loi	nger	full	. Wr	nen t	his	bit is	s se	t, th	ere	is st	ill ro	om '	for c	ne —
7	RXDAT	ΓΑV			0				R		ı	RX [Data	Va	lid															
	Set wh	en da	ata is	availa	able	in t	he re	cei	ve b	uffe	r. C	leare	ed w	hen	the	rec	eive	but	fer i	s en	npty	-								
6	TXBL				1				R					er L																
	Indicate Otherw															set v	whei	neve	er th	e tra	nsn	nit b	uffe	r is	com	plet	ely e	emp	ty.	

Bit	Name	Reset	Access	Description
5	TXC	0	R	TX Complete
		mission has comp ten to the transmi		more data is available in the transmit buffer and shift register. Cleared
4	TXTRI	0	R	Transmitter Tristated
	Set when the tra this bit is always		d, and cleared	d when transmitter output is enabled. If AUTOTRI in USARTn_CTRL is set
3	RXBLOCK	0	R	Block Incoming Data
		ceiver discards inc the frame has be		s. An incoming frame will not be loaded into the receive buffer if this bit is received.
2	MASTER	0	R	SPI Master Mode
	Set when the US mand.	SART operates as	a master. Set	using the MASTEREN command and clear using the MASTERDIS com-
1	TXENS	0	R	Transmitter Enable Status
	Set when the tra	nsmitter is enable	d.	
0	RXENS	0	R	Receiver Enable Status
	Set when the rec	ceiver is enabled.		

18.5.6 USARTn_CLKDIV - Clock Control Register

Offset															Bit	Pos	itic	on													
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	5	, [4 ო	2	,	- 0
Reset	0		•			,		00000x0														•		•							
Access	RW																														
Name	AUTOBAUDEN																		2	2											

Bit	Name	Reset	Access	Description
31	AUTOBAUDEN	0	RW	AUTOBAUD Detection Enable
	Detects the baud rate	based on recei	ving a 0x55	frame (0x00 for IrDA). This is used in Asynchronous mode.
30:23	Reserved	To ensure cor	npatibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
22:3	DIV	0x00000	RWH	Fractional Clock Divider
	Specifies the fractional field.	al clock divider f	or the USA	RT. Setting AUTOBAUDEN in USARTn_CLKDIV will overwrite the DIV
2:0	Reserved	To ensure cor tions	npatibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-

18.5.7 USARTn_RXDATAX - RX Buffer Data Extended Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0																														
Access																	œ	22										<u>~</u>				
Name																	FERR	PERR										RXDATA				

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15	FERR	0	R	Data Framing Error
	Set if data in buffer	has a framing e	error. Can be	the result of a break condition.
14	PERR	0	R	Data Parity Error
	Set if data in buffer	has a parity err	or (asynchroi	nous mode only).
13:9	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	RXDATA	0x000	R	RX Data
	Use this register to	access data rea	ad from the U	SART. Buffer is cleared on read access.

18.5.8 USARTn_RXDATA - RX Buffer Data Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	œ	7	9	2	4	က	2	_	0
Reset		•		•		•	'	•		•		•				•		'			•		•	'			•	2	0000			
Access																												۵	۲			
Name																												V - V - V - V - V - V - V - V - V - V -	¥ 14044			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	RXDATA	0x00	R	RX Data
	Use this register to a register.	ccess data read	d from USA	RT. Buffer is cleared on read access. Only the 8 LSB can be read using this

18.5.9 USARTn_RXDOUBLEX - RX Buffer Double Data Extended Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	0	0		0000 0000 0000 0000 0000 0000 0000 0000 0000														•														
Access	2	2										2					2	22										2				
Name	FERR1	PERR1										RXDATA1					FERR0	PERR0										RXDATA0				

	шшш		<u> </u>	
Bit	Name	Reset	Access	Description
31	FERR1	0	R	Data Framing Error 1
	Set if data in buffer I	has a framing e	rror. Can be	the result of a break condition.
30	PERR1	0	R	Data Parity Error 1
	Set if data in buffer I	has a parity erro	or (asynchror	nous mode only).
29:25	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
24:16	RXDATA1	0x000	R	RX Data 1
	Second frame read	from buffer.		
15	FERR0	0	R	Data Framing Error 0
	Set if data in buffer I	has a framing e	rror. Can be	the result of a break condition.
14	PERR0	0	R	Data Parity Error 0
	Set if data in buffer I	has a parity erro	or (asynchror	nous mode only).
13:9	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	RXDATA0	0x000	R	RX Data 0
	First frame read from	m buffer.		

18.5.10 USARTn_RXDOUBLE - RX FIFO Double Data Register (Actionable Reads)

Offset		Bit Position																														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	5	4	က	2	_	0
Reset														0000								0000										
Access														α.								α_										
Name																				Z Z Z Z Z Z Z Z Z Z Z Z Z Z Z Z Z Z Z	7							PXDATAD	<u>-</u>			

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	RXDATA1	0x00	R	RX Data 1
	Second frame read fr	om buffer.		
7:0	RXDATA0	0x00	R	RX Data 0
	First frame read from	buffer.		

18.5.11 USARTn_RXDATAXP - RX Buffer Data Extended Peek Register

Offset	Bit Po	osition
0x028	33 30 30 30 30 30 30 30 30 30 30 30 30 3	27 4 17 17 17 17 19 19 19 19 19 19 19 19 19 19 19 19 19
Reset		000×0
Access		α α α
Name		PERRP

Bit	Name	Reset	Access	Description									
31:16	Reserved	To ensure cor tions	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions										
15	FERRP	0	R Data Framing Error Peek										
	Set if data in buffer ha	as a framing erro	or. Can be	the result of a break condition.									
14	PERRP	0 R Data Parity Error Peek											
	Set if data in buffer ha	as a parity error	(asynchror	nous mode only).									
13:9	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-									
8:0	RXDATAP	0x000	R	RX Data Peek									
	Use this register to a	ccess data read	from the U	SART.									

18.5.12 USARTn_RXDOUBLEXP - RX Buffer Double Data Extended Peek Register

Offset		Bit Position																														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset	0	0							000x0									0	00000													
Access	2	2										2					22	2				<u>~</u>										
Name	FERRP1	PERRP1							RXDATAP1								FERRP0	PERRP0										RXDATAP0				

Nama	Donot -	A	Description								
Name	Reset	Access	Description								
FERRP1	0	R	Data Framing Error 1 Peek								
Set if data in buffer ha	as a framing erro	or. Can be	the result of a break condition.								
PERRP1	0	Data Parity Error 1 Peek									
Set if data in buffer has a parity error (asynchronous mode only).											
Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
RXDATAP1	0x000	R	RX Data 1 Peek								
Second frame read from FIFO.											
FERRP0	0	R	Data Framing Error 0 Peek								
Set if data in buffer ha	as a framing erro	or. Can be	the result of a break condition.								
PERRP0	0	R	Data Parity Error 0 Peek								
Set if data in buffer ha	as a parity error	(asynchror	nous mode only).								
Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
RXDATAP0	0x000	R	RX Data 0 Peek								
First frame read from FIFO.											
	Set if data in buffer have PERRP1 Set if data in buffer have Reserved RXDATAP1 Second frame read from FERRP0 Set if data in buffer have PERRP0 Set if data in buffer have Reserved RXDATAP0	FERRP1 0 Set if data in buffer has a framing error PERRP1 0 Set if data in buffer has a parity error Reserved To ensure contions RXDATAP1 0x000 Second frame read from FIFO. FERRP0 0 Set if data in buffer has a framing error PERRP0 0 Set if data in buffer has a parity error Reserved To ensure contions RXDATAP0 0x000	FERRP1 0 R Set if data in buffer has a framing error. Can be PERRP1 0 R Set if data in buffer has a parity error (asynchror Reserved To ensure compatibility tions RXDATAP1 0x000 R Second frame read from FIFO. FERRP0 0 R Set if data in buffer has a framing error. Can be PERRP0 0 R Set if data in buffer has a parity error (asynchror Reserved To ensure compatibility tions RXDATAP0 0x000 R								

18.5.13 USARTn_TXDATAX - TX Buffer Data Extended Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	3	2	_	0
Reset																	0	0	0	0	0							000x0				
Access																	>	>	>	>	>							≥				
Name																	RXENAT	TXDISAT	TXBREAK	TXTRIAT	UBRXAT							TXDATAX				

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15	RXENAT	0	W	Enable RX After Transmission
	Set to enable red	eption after trans	mission.	
14	TXDISAT	0	W	Clear TXEN After Transmission
	Set to disable tra	nsmitter and relea	ase data bus o	directly after transmission.
13	TXBREAK	0	W	Transmit Data as Break
	Set to send data value of TXDATA		oient will see a	a framing error or a break condition depending on its configuration and the
12	TXTRIAT	0	W	Set TXTRI After Transmission
	Set to tristate tra	nsmitter by setting	g TXTRI after	transmission.
11	UBRXAT	0	W	Unblock RX After Transmission
	Set to clear RXB	LOCK after transi	mission, unblo	ocking the receiver.
10:9	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	TXDATAX	0x000	W	TX Data
	Use this register	to write data to th	e USART. If T	FXEN is set, a transfer will be initiated at the first opportunity.

18.5.14 USARTn_TXDATA - TX Buffer Data Register

Offset															Bi	t Po	siti	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	ω	7	9	2	4	က	2	_	0
Reset		•												1				•			1	•	1					0	noxo Oxo			
Access																												}	>			
Name																												\	Y DA I A			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TXDATA	0x00	W	TX Data
	This frame will be a	dded to TX buff	er. Only 8 LS	SB can be written using this register. 9th bit and control bits will be cleared.

18.5.15 USARTn_TXDOUBLEX - TX Buffer Double Data Extended Register

Offset															Bi	t Po	siti	on														
0x038	33	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	5	4	က	2	_	0
Reset	0	0	0	0	0							000x0					0	0	0	0	0							000x0	•			
Access	≥	≥	≥	≥	≥							≥					>	≥	≥	≥	>							≥				
Name	RXENAT1	TXDISAT1	TXBREAK1	TXTRIAT1	UBRXAT1							TXDATA1					RXENAT0	TXDISAT0	TXBREAK0	TXTRIAT0	UBRXAT0							TXDATA0				

			<u> </u>	
Bit	Name	Reset	Access	Description
31	RXENAT1	0	W	Enable RX After Transmission
	Set to enable recep	tion after transmi	ission.	
30	TXDISAT1	0	W	Clear TXEN After Transmission
	Set to disable trans	mitter and releas	e data bus	directly after transmission.
29	TXBREAK1	0	W	Transmit Data as Break
	Set to send data as value of USARTn_T		ent will see a	a framing error or a break condition depending on its configuration and the
28	TXTRIAT1	0	W	Set TXTRI After Transmission
	Set to tristate transr	mitter by setting	TXTRI after	transmission.
27	UBRXAT1	0	W	Unblock RX After Transmission
	Set clear RXBLOC	Cafter transmissi	ion, unblock	ring the receiver.
26:25	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
24:16	TXDATA1	0x000	W	TX Data
	Second frame to wr	ite to FIFO.		
15	RXENAT0	0	W	Enable RX After Transmission
	Set to enable recep	tion after transmi	ission.	
14	TXDISAT0	0	W	Clear TXEN After Transmission
	Set to disable trans	mitter and releas	e data bus	directly after transmission.
13	TXBREAK0	0	W	Transmit Data as Break
	Set to send data as value of TXDATA.	a break. Recipie	ent will see a	a framing error or a break condition depending on its configuration and the
12	TXTRIAT0	0	W	Set TXTRI After Transmission
	Set to tristate transr	mitter by setting	TXTRI after	transmission.
11	UBRXAT0	0	W	Unblock RX After Transmission
	Set clear RXBLOC	K after transmissi	ion, unblock	sing the receiver.
10:9	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	TXDATA0	0x000	W	TX Data
	First frame to write	to buffer.		

18.5.16 USARTn_TXDOUBLE - TX Buffer Double Data Register

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	1	10	6	ω	7	9	5	4	က	2	_	0
Reset			1		1	ı	1		1					ı					1	2	nxn		1	1		1		5	2000			1
Access																				3	>							}	>			
Name																				F	IADAIAI								סל ולטל ו			

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:8	TXDATA1	0x00	W	TX Data
	Second frame to write	e to buffer.		
7:0	TXDATA0	0x00	W	TX Data
	First frame to write to	buffer.		

18.5.17 USARTn_IF - Interrupt Flag Register

Offset	В	t Position	
0x040	33 30 30 30 30 30 30 30 30 30 30 30 30 3	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	0
Reset		0 0 0 0 0 0 0 0 0 0 0 0 0	0
Access		x x	<u>~</u>
Name		TCMP2 TCMP0 TXIDLE CCF SSM MPAF FERR FERR TXUF TXUF TXOF RXUF RXUF RXUF RXUF RXUF RXUF RXUF RXU	TXC

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
16	TCMP2	0	R	Timer Comparator 2 Interrupt Flag
	Set when the time	er reaches the co	mparator 2 va	alue, TCMP2.
15	TCMP1	0	R	Timer Comparator 1 Interrupt Flag
	Set when the time	er reaches the co	mparator 1 va	alue, TCMP1.
14	TCMP0	0	R	Timer Comparator 0 Interrupt Flag
	Set when the Tim	ner reaches the co	mparator 0 v	value, TCMP0.
13	TXIDLE	0	R	TX Idle Interrupt Flag
	Set when TX goe	es idle. At this poin	nt, transmissio	on has ended
12	CCF	0	R	Collision Check Fail Interrupt Flag
	Set when a collis	ion check notices	an error in th	e transmitted data.
11	SSM	0	R	Slave-Select in Master Mode Interrupt Flag
	Set when the dev	vice is selected as	a slave wher	n in master mode.
10	MPAF	0	R	Multi-Processor Address Frame Interrupt Flag
	Set when a multi-	-processor addres	s frame is de	etected.
9	FERR	0	R	Framing Error Interrupt Flag
	Set when a frame	e with a framing e	rror is receive	ed while RXBLOCK is cleared.
8	PERR	0	R	Parity Error Interrupt Flag
	Set when a frame	e with a parity erro	or (asynchron	ous mode only) is received while RXBLOCK is cleared.
7	TXUF	0	R	TX Underflow Interrupt Flag
	Set when operati of a new frame.	ng as a synchrono	ous slave, no	data is available in the transmit buffer when the master starts transmission
6	TXOF	0	R	TX Overflow Interrupt Flag
	Set when a write	is done to the tran	nsmit buffer v	while it is full. The data already in the transmit buffer is preserved.
5	RXUF	0	R	RX Underflow Interrupt Flag
	Set when trying t	o read from the re	ceive buffer v	when it is empty.
4	RXOF	0	R	RX Overflow Interrupt Flag
	Set when data is	incoming while th	e receive shi	ft register is full. The data previously in the shift register is lost.

Bit	Name	Reset	Access	Description
3	RXFULL	0	R	RX Buffer Full Interrupt Flag
	Set when the rec	eive buffer becom	es full.	
2	RXDATAV	0	R	RX Data Valid Interrupt Flag
	Set when data be	ecomes available i	in the receive	buffer.
1	TXBL	1	R	TX Buffer Level Interrupt Flag
	Set when buffer the fied buffer level.	becomes empty if	buffer level is	s set to 0x0, or when the number of empty TX buffer elements equals speci-
0	TXC	0	R	TX Complete Interrupt Flag
	This interrupt is s	set after a transmis	ssion when bo	oth the TX buffer and shift register are empty.

18.5.18 USARTn_IFS - Interrupt Flag Set Register

Offset															Ві	it Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset																0	0	0	0	0	0	0	0	0	0	0	0	0	0			0
Access																×	N 1	×	W 1	×	W	W 1	W1	W 1	N 1	×	N 1	×	N N			X
Name																TCMP2	TCMP1	TCMP0	TXIDLE	CCF	SSM	MPAF	FERR	PERR	TXUF	TXOF	RXUF	RXOF	RXFULL			TXC

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
16	TCMP2	0	W1	Set TCMP2 Interrupt Flag
	Write 1 to set the TC	MP2 interrupt fla	ıg	
15	TCMP1	0	W1	Set TCMP1 Interrupt Flag
	Write 1 to set the TC	MP1 interrupt fla	g	
14	TCMP0	0	W1	Set TCMP0 Interrupt Flag
	Write 1 to set the TC	MP0 interrupt fla	g	
13	TXIDLE	0	W1	Set TXIDLE Interrupt Flag
	Write 1 to set the TX	IDLE interrupt fla	ag	
12	CCF	0	W1	Set CCF Interrupt Flag
	Write 1 to set the CC	F interrupt flag		
11	SSM	0	W1	Set SSM Interrupt Flag
	Write 1 to set the SS	M interrupt flag		
10	MPAF	0	W1	Set MPAF Interrupt Flag
	Write 1 to set the MP	AF interrupt flag		
9	FERR	0	W1	Set FERR Interrupt Flag
	Write 1 to set the FE	RR interrupt flag		
8	PERR	0	W1	Set PERR Interrupt Flag
	Write 1 to set the PE	RR interrupt flag		
7	TXUF	0	W1	Set TXUF Interrupt Flag
	Write 1 to set the TX	UF interrupt flag		
6	TXOF	0	W1	Set TXOF Interrupt Flag
	Write 1 to set the TX	OF interrupt flag		
5	RXUF	0	W1	Set RXUF Interrupt Flag
	Write 1 to set the RX	UF interrupt flag		
4	RXOF	0	W1	Set RXOF Interrupt Flag
	Write 1 to set the RX	OF interrupt flag		
3	RXFULL	0	W1	Set RXFULL Interrupt Flag
	Write 1 to set the RX	FULL interrupt fl	ag	

Bit	Name	Reset	Access	Description
2:1	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	TXC	0	W1	Set TXC Interrupt Flag
	Write 1 to set the	TXC interrupt fla	ıg	

18.5.19 USARTn_IFC - Interrupt Flag Clear Register

Offset				В	it Po	siti	on														
0x048	30 30 28 29	24 25 24 23 23 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3	22 23	19 19 14 15	16	15	4	13	12	11	10	6	∞	7	9	2	4	က	7	_	0
Reset					0	0	0	0	0	0	0	0	0	0	0	0	0	0			0
Access					(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1			1W(R)
Name					TCMP2	TCMP1	TCMP0	TXIDLE	CCF	SSM	MPAF	FERR	PERR	TXUF	TXOF	RXUF	RXOF	RXFULL			TXC
Bit	Name	Reset	Access	Descri	otion																
31:17	Reserved	To ensure o	compatibility	with future	e de	/ices	s, alı	ways	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on ir	1.2	? Coi	nver	1-
16	TCMP2	0	(R)W1	Clear T	СМЕ	2 Ir	iterr	rupt	Fla	g											
		the TCMP2 interrup est be enabled glob			s the	valı	ue o	f the	e IF	and	clea	ars t	he c	orre	espo	ndir	ng ir	iterr	upt f	lags	i
15	TCMP1	0	(R)W1	Clear T	СМЕ	1 In	iterr	rupt	Fla	g											
		the TCMP1 interrup est be enabled glob			s the	valı	ne o	f the	e IF	and	clea	ars t	he c	orre	espo	ndir	ng ir	iterr	upt f	lags	i
14	TCMP0	0	(R)W1	Clear T	СМЕ	0 In	iterr	rupt	Fla	g											
		the TCMP0 interrup est be enabled glob			s the	valı	ue o	f the	e IF	and	clea	ars t	he c	orre	espo	ndir	ng ir	iterr	upt f	lags	i
13	TXIDLE	0	(R)W1	Clear T	XIDI	E Ir	nter	rupt	t Fla	ıg											
		the TXIDLE interru est be enabled glob			s the	val	ue o	of the	e IF	and	clea	ars t	he o	corre	espo	ndii	ng ir	nterr	upt f	flags	;
12	CCF	0	(R)W1	Clear C	CF I	nter	rup	t Fla	ag												
		the CCF interrupt fl enabled globally ir		g returns th	ie va	lue (of th	e IF	and	d cle	ars	the	corr	esp	ondi	ing i	nter	rupt	flag	s (T	his
11	SSM	0	(R)W1	Clear S	SM	Inte	rrup	t Fla	ag												
		the SSM interrupt f enabled globally ir		g returns th	ne va	lue	of th	ne IF	an	d cle	ears	the	corr	esp	ond	ing i	inter	rupt	flag	ıs (T	his
10	MPAF	0	(R)W1	Clear N	1PAF	Int	erru	ıpt F	Flag												
		the MPAF interrupt est be enabled glob			the \	/alue	e of	the I	IF a	nd c	lear	s th	e co	rres	pon	ding	j inte	erru	pt fla	ags	
9	FERR	0	(R)W1	Clear F	ERR	Inte	erru	pt F	lag												
		the FERR interrupt est be enabled glob	-	-	the v	alue	e of t	the I	IF a	nd c	lear	s the	e co	rres	pon	ding	inte	erru	ot fla	ıgs	
8	PERR	0	(R)W1	Clear P	EDE	14		4 =	-1												

Write 1 to clear the PERR interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags

Write 1 to clear the TXUF interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags

Clear TXUF Interrupt Flag

(This feature must be enabled globally in MSC.).

0

(This feature must be enabled globally in MSC.).

(R)W1

TXUF

7

Bit	Name	Reset	Access	Description
6	TXOF	0	(R)W1	Clear TXOF Interrupt Flag
		the TXOF interrupt ist be enabled glob	•	returns the value of the IF and clears the corresponding interrupt flags
5	RXUF	0	(R)W1	Clear RXUF Interrupt Flag
		the RXUF interrupt est be enabled glob	•	g returns the value of the IF and clears the corresponding interrupt flags
4	RXOF	0	(R)W1	Clear RXOF Interrupt Flag
		the RXOF interrup ist be enabled glob		g returns the value of the IF and clears the corresponding interrupt flags
3	RXFULL	0	(R)W1	Clear RXFULL Interrupt Flag
		the RXFULL interroust be enabled glob		ing returns the value of the IF and clears the corresponding interrupt flags
2:1	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	TXC	0	(R)W1	Clear TXC Interrupt Flag
		the TXC interrupt f enabled globally ir		returns the value of the IF and clears the corresponding interrupt flags (This

18.5.20 USARTn_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x04C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access																₩ M	R W	₹	₩ M	₩ M	₽	₩ W	RW	₩ W	₩	₩ M	₩ M	R W	₩ M	RW	₽	RW
Name																TCMP2	TCMP1	TCMP0	TXIDLE	CCF	SSM	MPAF	FERR	PERR	TXUF	TXOF	RXUF	RXOF	RXFULL	RXDATAV	TXBL	TXC

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
16	TCMP2	0	RW	TCMP2 Interrupt Enable
	Enable/disable the	TCMP2 interrupt		
15	TCMP1	0	RW	TCMP1 Interrupt Enable
	Enable/disable the	TCMP1 interrupt		
14	TCMP0	0	RW	TCMP0 Interrupt Enable
	Enable/disable the	TCMP0 interrupt		
13	TXIDLE	0	RW	TXIDLE Interrupt Enable
	Enable/disable the	TXIDLE interrupt		
12	CCF	0	RW	CCF Interrupt Enable
	Enable/disable the	CCF interrupt		
11	SSM	0	RW	SSM Interrupt Enable
	Enable/disable the	SSM interrupt		
10	MPAF	0	RW	MPAF Interrupt Enable
	Enable/disable the I	MPAF interrupt		
9	FERR	0	RW	FERR Interrupt Enable
	Enable/disable the I	FERR interrupt		
8	PERR	0	RW	PERR Interrupt Enable
	Enable/disable the I	PERR interrupt		
7	TXUF	0	RW	TXUF Interrupt Enable
	Enable/disable the	TXUF interrupt		
6	TXOF	0	RW	TXOF Interrupt Enable
	Enable/disable the	TXOF interrupt		
5	RXUF	0	RW	RXUF Interrupt Enable
	Enable/disable the I	RXUF interrupt		
4	RXOF	0	RW	RXOF Interrupt Enable
	Enable/disable the I	RXOF interrupt		

Bit	Name	Reset	Access	Description
3	RXFULL	0	RW	RXFULL Interrupt Enable
	Enable/disable the RX	KFULL interrupt		
2	RXDATAV	0	RW	RXDATAV Interrupt Enable
	Enable/disable the RX	KDATAV interru	ot	
1	TXBL	0	RW	TXBL Interrupt Enable
	Enable/disable the TX	(BL interrupt		
0	TXC	0	RW	TXC Interrupt Enable
	Enable/disable the TX	(C interrupt		

18.5.21 USARTn_IRCTRL - IrDA Control Register

								- 3																						
Offset													Ві	it Pos	itio	n														
0x050	31	29	28	-i 26	25	24	23	22	21	20	19	18	17	16	2	14	5 4	7	11	10	6	8	7	. ر	2	4	۰ ،	o (7	0
Reset																				2	2		c	,			6	5	0×0	0
Access																				20	>		S.				20	3	X W	Z M
Name																							RPRSFN				1	-	≷	z
																					=		RP P				0	<u> </u>	IRPW	IREN
Bit	Name				R	Reset			Ac	ces	s	Des	crip	tion																
31:12	Reserv	ed				o ens	sure	com	pati	ibilit	y w	ith fu	ıture	devi	es,	alv	vays	writ	e b	its t	o 0.	. Мо	re	info	rmat	ion	in 1	.2 (Conve	n-
11:8	IRPRS	SEL			0	x0			RW	V		IrD/	A PR	RS Ch	anr	nel	Selec	:t												
	A PRS	can h	oe us	ed a	ıs ir	nput t	o the	pul	se n	nod	ulat	tor in	stea	ad of T	Χ.	Thi	s valu	ie s	ele	cts	the	cha	nne	el to	use					
	Value				N	lode						Des	cript	tion																_
	0				Р	RSC	H0					PRS	S Ch	annel	0 s	sele	cted													
	1				Р	PRSC	H1					PRS	S Ch	annel	1 s	sele	cted													
	2				Р	RSC	H2					PRS	S Ch	annel	2 s	sele	cted													
	3				Р	PRSC	НЗ					PRS	S Ch	annel	3 s	sele	cted													
	4				Р	RSC	H4					PRS	S Ch	annel	4 s	sele	cted													
	5					PRSC								annel																
	6				Р	RSC	H6							annel																
	7					RSC								annel																
	8					PRSC								annel																
	9					PRSC								annel																
	10					RSC								annel																
	11				P	PRSC	H11					PRS	S Ch	annel	11	sel	ected													
7	IRPRS	EN			0				RW	V		IrD/	A PR	RS Ch	anr	nel	Enab	le												
	Enable	the F	PRS	chan	nel	sele	cted	by I	RPF	RSS	EL	as ir	put	to IrD	A n	nod	ule in	stea	ad (of T	Χ.									
6:4	Reserv	ed				o ens	sure	com	pati	ibilit	y w	ith fu	ıture	devi	es,	alv	vays	writ	e b	its t	0 0.	. Mo	re	info	rmat	ion .	in 1	.2 (Conve	n-
3	IRFILT				0				RW	V		IrD/	X RX	(Filte	r															
	Set to e	enabl	e filte	r on	lrD)A de	mod	ulato	or.																					
	Value											Des	cript	tion																_
	0											No f	filter	enab	ed															
	1													abled be d				mu	ıst l	oe h	iigh	for	at I	eas	t 4 c	ons	ecu	tive	e clock	

t	Name	Reset	Access	Description
:1	IRPW	0x0	RW	IrDA TX Pulse Width
	Configure the	pulse width generate	d by the IrDA	a modulator as a fraction of the configured USART bit period.
	Value	Mode		Description
	0	ONE		IrDA pulse width is 1/16 for OVS=0 and 1/8 for OVS=1
	1	TWO		IrDA pulse width is 2/16 for OVS=0 and 2/8 for OVS=1
	2	THREE		IrDA pulse width is 3/16 for OVS=0 and 3/8 for OVS=1
	3	FOUR		IrDA pulse width is 4/16 for OVS=0 and 4/8 for OVS=1
)	IREN	0	RW	Enable IrDA Module
	Enable IrDA m	odule and rout USAI	RT signals th	rough it.

18.5.22 USARTn_INPUT - USART Input Register

Offset				Bit Po	siti	on						
0x058	30 30 29 28 27 27	25 24 23 23 22 22	20 20	18 17 19	15	4 6	12	11 01	² တ ထ	7	0 7 4	8 7 - 0
Reset					0				0×0	0		0x0
Access					X N				Z.	\ N		AW.
Name					CLKPRS				CLKPRSSEL	RXPRS		RXPRSSEL
					김				딩	쭚		X
Bit	Name	Reset	Access	Description								
31:16	Reserved	To ensure contions	npatibility v	with future dev	/ices	s, alwa	ys wr	ite bits	to 0. Mo	re in	formation in	1.2 Conven-
15	CLKPRS	0	RW	PRS CLK E	nab	le						
	When set, the PRS c	hannel selected	as input to	CLK.								
14:12	Reserved	To ensure contions	npatibility v	vith future de	/ices	s, alwa	ys wr	ite bits	to 0. Mo	re in	formation in	1.2 Conven-
11:8	CLKPRSSEL	0x0	RW	CLK PRS C	han	nel Se	lect					
	Select PRS channel a	as input to CLK.										
	Value	Mode		Description								
	0	PRSCH0		PRS Chann	el 0	selecte	ed					
	1	PRSCH1		PRS Chann	el 1	selecte	ed					
	2	PRSCH2		PRS Chann	el 2	selecte	ed					
	3	PRSCH3		PRS Chann	el 3	selecte	ed					
	4	PRSCH4		PRS Chann	el 4	selecte	ed					
	5	PRSCH5		PRS Chann	el 5	selecte	ed					
	6	PRSCH6		PRS Chann	el 6	selecte	ed					
	7	PRSCH7		PRS Chann	el 7	selecte	ed					
	8	PRSCH8		PRS Chann	el 8	selecte	ed					
	9	PRSCH9		PRS Chann	el 9	selecte	ed					
	10	PRSCH10		PRS Chann	el 10) selec	ted					
	11	PRSCH11		PRS Chann	el 1	1 selec	ted					
7	RXPRS	0	RW	PRS RX En	able)						
	When set, the PRS c	hannel selected	as input to	RX.								
6:4	Reserved	To ensure contions	mpatibility v	vith future dev	/ices	s, alwa	ys wr	ite bits	to 0. Mo	re in	formation in	1.2 Conven-
3:0	RXPRSSEL	0x0	RW	RX PRS Ch	ann	el Sele	ect					
	Select PRS channel as input to RX.											
	Value	Mode		Description								
				-								

3it	Name	Reset	Access	Description
	0	PRSCH0		PRS Channel 0 selected
	1	PRSCH1		PRS Channel 1 selected
	2	PRSCH2		PRS Channel 2 selected
	3	PRSCH3		PRS Channel 3 selected
	4	PRSCH4		PRS Channel 4 selected
	5	PRSCH5		PRS Channel 5 selected
	6	PRSCH6		PRS Channel 6 selected
	7	PRSCH7		PRS Channel 7 selected
	8	PRSCH8		PRS Channel 8 selected
	9	PRSCH9		PRS Channel 9 selected
	10	PRSCH10		PRS Channel 10 selected
	11	PRSCH11		PRS Channel 11 selected

18.5.23 USARTn_I2SCTRL - I2S Control Register

Offset				Bit Position		
0x05C	30 29 29 27 28 26 26	23 23 25 25 25 25 25 25 25 25 25 25 25 25 25	2 2 5	6 8 7 9 5 4 6 7 7 0	6 8 7 9 5	4 ω α - ο
Reset					0×0	0 0 0 0
Access					RW	RW RW RW RW
Name					FORMAT	DELAY DMASPLIT JUSTIFY MONO EN
Bit	Name	Reset /	Access	Description		
31:11	Reserved	To ensure comp tions	atibility v	ith future devices, always write bits	to 0. More informatio	on in 1.2 Conven-
10:8	FORMAT	0x0 F	₹W	I2S Word Format		
	Configure the data-wid	dth used internally	for I2S	lata		
	Value	Mode		Description		
	0	W32D32		32-bit word, 32-bit data		
	1	W32D24M		32-bit word, 32-bit data with 8 lsb m	nasked	
	2	W32D24		32-bit word, 24-bit data		
	3	W32D16		32-bit word, 16-bit data		
	4	W32D8		32-bit word, 8-bit data		
	5	W16D16		16-bit word, 16-bit data		
	6	W16D8		16-bit word, 8-bit data		
	7	W8D8		8-bit word, 8-bit data		
7:5	Reserved	To ensure comp	atibility v	vith future devices, always write bits	to 0. More informatio	on in 1.2 Conven-
4	DELAY	0 F	₹W	Delay on I2S Data		
	Set to add a one-cycle ard I2S format	e delay between a	transitio	n on the word-clock and the start of t	the I2S word. Should	be set for stand-
3	DMASPLIT	0 F	RW	Separate DMA Request for Left/R	Right Data	
	When set DMA reques	sts for right-chann	el data a	re put on the TXBLRIGHT and RXD/	ATAVRIGHT DMA re	equests.
2	JUSTIFY	0 F	₹W	Justification of I2S Data		
	Determines whether the	he I2S data is left	or right ju	ıstified		
	Value	Mode		Description		
	0	LEFT		Data is left-justified		
	1	RIGHT		Data is right-justified		
1	MONO	0 F	RW	Stero or Mono		
	Switch between stered	o and mono mode	. Set for	mono		

Bit	Name	Reset	Access	Description
0	EN	0	RW	Enable I2S Mode
	Set the U(S)ART in I2	S mode.		

18.5.24 USARTn_TIMING - Timing Register

Offset															Bi	t Po	siti	on														
0x060	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset			000	•			0×0				0x0				0x0			•			•	•	•			•	•		•			
Access			RW				W.				ZW W				S.																	
Name			CSHOLD				SOI				CSSETUP				TXDELAY																	

Bit	Name	Reset	Access	Description
31	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
30:28	CSHOLD	0x0	RW	Chip Select Hold

Chip Select will be asserted after the end of frame transmission. When using TCMPn, normally set TIMECMPn_TSTART to DISABLE to stop general timer and to prevent unwanted interrupts.

Value	Mode	Description
0	ZERO	Disable CS being asserted after the end of transmission
1	ONE	CS is asserted for 1 baud-times after the end of transmission
2	TWO	CS is asserted for 2 baud-times after the end of transmission
3	THREE	CS is asserted for 3 baud-times after the end of transmission
4	SEVEN	CS is asserted for 7 baud-times after the end of transmission
5	TCMP0	CS is asserted after the end of transmission for TCMPVAL0 baud-times
6	TCMP1	CS is asserted after the end of transmission for TCMPVAL1 baud-times
7	TCMP2	CS is asserted after the end of transmission for TCMPVAL2 baud-times

27	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
26:24	ICS	0x0	RW	Inter-character Spacing

Inter-character spacing after each TX frame while the TX buffer is not empty. When using USART_TIMECMPn, normally set TSTART to DISABLE to stop general timer and to prevent unwanted interrupts.

Value	Mode	Description
0	ZERO	There is no space between charcters
1	ONE	Create a space of 1 baud-times before start of transmission
2	TWO	Create a space of 2 baud-times before start of transmission
3	THREE	Create a space of 3 baud-times before start of transmission
4	SEVEN	Create a space of 7 baud-times before start of transmission
5	TCMP0	Create a space of before the start of transmission for TCMPVAL0 baud-times

				OSAKT - Offiversal Synchronous Asynchronous Receiver/Transmitte
Bit	Name	Reset	Access	Description
	6	TCMP1		Create a space of before the start of transmission for TCMPVAL1 baud-times
	7	TCMP2		Create a space of before the start of transmission for TCMPVAL2 baud-times
23	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
22:20	CSSETUP	0x0	RW	Chip Select Setup
				rame transmission. When using USART_TIMECMPn, normally set TSTART tunwanted interrupts.
	Value	Mode		Description
	0	ZERO		CS is not asserted before start of transmission
	1	ONE		CS is asserted for 1 baud-times before start of transmission
	2	TWO		CS is asserted for 2 baud-times before start of transmission
	3	THREE		CS is asserted for 3 baud-times before start of transmission
	4	SEVEN		CS is asserted for 7 baud-times before start of transmission
	5	TCMP0		CS is asserted before the start of transmission for TCMPVAL0 baud-times
	6	TCMP1		CS is asserted before the start of transmission for TCMPVAL1 baud-times
	7	TCMP2		CS is asserted before the start of transmission for TCMPVAL2 baud-times
19	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
18:16	TXDELAY	0x0	RW	TX Frame Start Delay
				e transmission. When using USART_TIMECMPn, normally set TSTART to inwanted interrupts.
	Value	Mode		Description
	0	DISABLE		Disable - TXDELAY in USARTn_CTRL can be used for legacy
	1	ONE		Start of transmission is delayed for 1 baud-times
	2	TWO		Start of transmission is delayed for 2 baud-times
	3	THREE		Start of transmission is delayed for 3 baud-times
	4	SEVEN		Start of transmission is delayed for 7 baud-times
	5	TCMP0		Start of transmission is delayed for TCMPVAL0 baud-times
	6	TCMP1		Start of transmission is delayed for TCMPVAL1 baud-times
	7	TCMP2		Start of transmission is delayed for TCMPVAL2 baud-times
15:0	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

18.5.25 USARTn_CTRLX - Control Register Extended

Offset							Bit	Posi	tion_													
)x064	- C	- (O 10	+ 6	0 7	- 0	0 0					0											
	31 39 39 29 39 31	26 25	23 24	22	2 8	19	17	75	4	13	12	7	9	0	∞	7	9	2	4	က	2	_
Reset																				0	0	o >
Access																				₩	R W	8
Name																				RTSINV	CTSEN	CTSINV
Bit	Name	Res	et	Å	Acces	s Des	cripti	on														
31:4	Reserved	To e		сотр	atibilit _.	y with fu	iture d	device	es, a	way.	s w	rite i	bits t	to 0	. Мо	re in	form	atio	on in	1.2	? Co	nve
3	RTSINV	0		F	RW	RTS	Pin I	Inver	sion													
	When set, the R	TS pin pola	rity is i	nverte	ed.																	
	Value					Des	criptio	n														
	0					The	USn_	RTS	pin i	s lov	v tr	ле										
	1					The	USn_	_RTS	pin i	s hig	gh t	rue										
<u> </u>	CTSEN	0		F	RW	СТ	Fund	ction	Ena	bled	ı											
	When set, frame ue transmitting, t											S. A	ny c	data	in t	ne T	X sh	ift r	egis	ter v	will c	con
	ue transmitting, t	ne next 1A		uala v	• • • • • • • • • • • • • • • • • • • •	l load III	to the	1/2	11111111													
	Value	THE HEXT TA		uata v			criptio															
		ne next 1X		uata v		Des		n														
	Value	ne next 1x		uata v		Des	criptio	on S				S is	nega	atec	ı							
l	Value 0	0			RW	Des Ingo Stor	criptio	on S smitti	ng w			S is	nega	atec	I							
	Value 0 1	0	rity is i	F	RW	Des Ingo Stor	cription ore CT	on S smitti	ng w			S is	nega	atec	İ							
l	Value 0 1 CTSINV	0	rity is i	F	RW	Des Ingo Stop CTS	cription ore CT	on S smittii	ng w			S is	nega	atec	I							
I	Value 0 1 CTSINV When set, the C	0	rity is i	F	RW	Des Ingo Stop CTS	cription or CT or trans	on S smittin	ng w sion	hen	CT		nega	ated	i							
	Value 0 1 CTSINV When set, the CT	0	rity is i	F	RW	Des Ingo Stop CTS Des	cription or CT or trans	on S Smitti	ng w sion pin i	hen s	CT:	ıe	nega	atec	l							
	Value 0 1 CTSINV When set, the CTValue 0	0	rity is i	F	RW	Des Ingo Stop CTS Des The The	cription or cription or cription USn_	on S smitti Inver On _CTS _CTS	ng w sion pin i	hen s	CT:	ıe	nega	atec	ı							
	Value 0 1 CTSINV When set, the CT Value 0 1	0 TS pin pola	rity is i	F	RW ed.	Des Ingo Stop CTS Des The The	cription or cription USn_	on S smitti Inver On _CTS _CTS	ng w sion pin i	hen s	CT:	ıe	nega	atec	ı							
	Value 0 1 CTSINV When set, the CT Value 0 1	0 TS pin pola	rity is i	F	RW ed.	Des Ingo Stop CTS Des The The Deb	cription or cription USn_	Inver	ng w sion pin i	hen s	CT:	ıe	nega	atec	1							
0	Value 0 1 CTSINV When set, the CT Value 0 1 DBGHALT .	0 TS pin pola	rity is i	F	RW ed.	Des Ingo Stop CTS Des The The Deb	cription or cription USn_USn_	on TS Ssemittii Inver CTS CTS CTS	ng w sion pin i	s lov	CT:	ue										

frames instead of just transmitting one frame.

18.5.26 USARTn_TIMECMP0 - Used to Generate Interrupts and Various Delays

Offset												Bit	: Po	sitic	on														
0x068	30 29 29	28	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7		ם ער	,	4	က	7	- 0
Reset			'		0		'	0x0				0x0		'	'				•		'		'			00×0	1		
Access					§ S			Ŋ N				₩ M														Z N			
Name					RESTARTEN			TSTOP				TSTART														TCMPVAL			
Bit	Name			Res	et			Acc	ess	s l	Desc	cript	tion																
31:25	Reserved			To e		ire d	com	patik	oility	/ wit	th fut	ture	dev	ices	, alv	vay.	s wr	ite k	its t	to C	. Mc	re i	info	rmat	tior	in '	1.2 (Conv	/en-
24	RESTART	EN		0				RW		ı	Rest	art	Tim	er o	n T	СМ	P0												
	Each TCM	P0 eve	nt wi	II rese	et ar	nd r	esta	art th	e tii	mer																			
	Value									ı	Desc	cripti	on																
	0									ı	Disal	ble t	he t	imer	res	start	ing	on 7	CM	1P0									
	1						Enable the timer restarting on TCMP0																						
23	Reserved			To e		ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conve												/en-											
22:20	TSTOP			0x0				RW			Sour	rce l	Use	d to	Dis	sabl	e C	omp	ara	itor	0								
	Select the	source	whic	h dis	able	es c	omp	arat	or C)																			
	Value			Mod	de					ı	Desc	cripti	on																
	0			TCN	ЛP0						Com gers						d wl	nen	the	col	ınteı	eq	ual	s TC	CMI	PVA	L ar	nd tri	ig-
	1			TXS	ST					(Com	para	ator	0 is	disa	able	d at	the	sta	rt o	f trar	nsm	iss	ion					
	2			RXA	ACT					(Com	para	ator	0 is	disa	able	d or	RX	go	ing	goir	ıg A	ctiv	/e (d	lefa	ault:	low)	
	3			RXA	ACT	N				(Com	para	ator	0 is	disa	able	d or	RX	go	ing	Inac	tive	;						
19	Reserved			To e		ire d	com	patik	oility	/ wit	th fut	ture	dev	ices	, alv	vay.	s wr	ite k	its t	to C). Мс	re i	info	rmat	tior	in in	1.2 (Conv	/en-
18:16	TSTART			0x0				RW		•	Time	er St	tart	Sou	rce														
	Source use	ed to st	art co	ompa	rato	or O	and	time	er																				
	Value			Mod	de					ı	Desc	cripti	on																
	0			DIS	ABL	E.				(Com	para	ator	0 is	disa	able	d												
	1			TXE	OF					(Com	para	ator	0 an	ıd tiı	mer	are	sta	ted	at	TΧ є	end	of t	ram	е				
	2			TXC						(Com	para	ator	0 an	ıd tiı	mer	are	sta	rted	at	TX (Com	nple	ete					
	3			RXA	ACT					(Com	para	ator	0 an	ıd tiı	mer	are	sta	ted	at	RX (goin	ıg A	ctive	e (defa	ult:	low)	
	4			DVE	EOF			Comparator 0 and timer are started at RX end of frame																					

Bit	Name	Reset	Access	Description
15:8	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TCMPVAL	0x00	RW	Timer Comparator 0
				TCMP0 event and sets the TCMP0 flag. This event can also be used to 0x00 represents 256 baud times.

18.5.27 USARTn_TIMECMP1 - Used to Generate Interrupts and Various Delays

Offset											Ві	it Po	sitio	on														
0x06C	30 29 29	28	26	25	24	23	22	20	19	8	17	16	15	4	13	12	1	10	6	œ	7	9	2	4	က	2	_	0
Reset		'			0		d	OXO			0x0	•		'						•			•	0	00X0			
Access					\$		i	<u>}</u>			ΑŠ													2	≷			
Name					RESTARTEN		(<u> </u>			TSTART														ICMPVAL			
Bit	Name			Res	et		ļ	cce	ss	Des	crip	tion																
31:25	Reserved			To e		ire d	отр	atibili	ty w	ith fu	uture	dev	vices	s, alv	vays	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on ir	າ 1.	2 C	onve	en-
24	RESTARTE	ΞN		0			F	RW		Res	tart	Tim	er o	n T	СМЕ	P1												
	Each TCM	P1 eve	nt wi	II rese	et aı	nd r	estar	t the	time	r																		
	Value									Des	cript	ion																_
	0									Disa	able	the t	time	r res	start	ing (on T	СМ	P1									
	1									Ena	ble t	the t	imer	res	tarti	ng c	n T	СМЕ	P1									
23	Reserved			To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Convetions											onve	en-												
22:20	TSTOP			0x0			F	RW		Sou	ırce	Use	d to	Dis	sabl	e Co	omp	ara	tor	1								
	Select the s	source	whic	h dis	able	es co	ompa	rator	1																			
	Value			Mod	le					Des	cript	ion																
	0			TCM	/IP1						npar s a T					d wh	nen	the	coui	nter	equ	als	TCN	ИPV	/AL	and	l trig	-
	1			TXS	ST					Cor	npar	ator	1 is	disa	able	d at	TX	star	t TX	En	gine	!						
	2			RXA	ACT					Cor	npar	ator	1 is	disa	able	d on	RX	goi	ng g	goin	g Ac	tive	(de	faul	lt: Ic	ow)		
	3			RXA	ACT	N				Cor	npar	ator	1 is	disa	able	d on	RX	goi	ng I	nact	ive							_
19	Reserved			To e		ire c	сотр	atibili	ty w	ith fu	uture	dev	vices	s, alv	vays	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on ir	າ 1.	2 C	onve	en-
18:16	TSTART			0x0			F	RW		Tim	er S	tart	Sou	ırce														
	Source use	d to st	art co	ompa	rato	or 1	and t	imer																				
	Value			Mod	le					Des	cript	ion																
	0			DIS	ABL	E.				Cor	npar	ator	1 is	disa	able	d												
	1			TXE	OF					Cor	npar	ator	1 ar	nd tii	mer	are	sta	rted	at T	Хe	nd c	of fra	ame					
	2			TXC)					Cor	npar	ator	1 ar	nd tii	mer	are	sta	ted	at T	X C	omp	olete	9					
	3			RXA	ACT					Cor	npar)	ator	1 ar	nd tii	mer	are	sta	ted	at F	≀X g	oing	g goi	ing <i>i</i>	Activ	ve (defa	ault:	
	4			RXE	OF					Cor	npar	ator	1 ar	nd tii	mer	are	sta	rted	at F	RX e	nd o	of fra	ame	!				

Bit	Name	Reset	Access	Description
15:8	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TCMPVAL	0x00	RW	Timer Comparator 1
		,	0	a TCMP1 event and sets the TCMP1 flag. This event can also be used to 0x00 represents 256 baud times.

18.5.28 USARTn_TIMECMP2 - Used to Generate Interrupts and Various Delays

Offset								Е	it Po	sitic	on													
0x070	30 30 29 29	27	25	24	22 23	27 5	1 6	18 17	16	15	4	5 5	7 -	: 6	6	ω	7	9	2	4	က	2	_	0
Reset				0		000		000	1											6	0000			
Access				₩ ₩		Z M		Z S												Ž	≩ Ƴ			
Name				RESTARTEN		TSTOP		TSTART												()	ICMPVAL			
Bit	Name		Res	et		Acce	ss	Descri	otion															
31:25	Reserved		To e		e com	patibil	ity w	ith futur	e dev	vices	, alv	vays	write	bits	to 0	. Мо	re ii	nfor	mati	on ir	1 1.	2 Co	nvei	n-
24	RESTARTEN	١	0			RW		Restar	t Tim	er o	n T	CMP2	2											
	Each TCMP2	2 event v	will rese	et and	d resta	art the	time	r																
	Value							Descrip	tion															_
	0							Disable	the	timer	res	tartin	g on	TCI	MP2									
	1							Enable	the t	imer	rest	tarting	g on	TCN	/IP2									_
23	Reserved		To e		e com	patibil	ity w	ith futur	e dev	vices	, alv	vays	write	bits	to 0	. Мо	re ii	nfor	mati	on ir	1.	2 Co	nvei	n-
22:20	TSTOP		0x0			RW		Source	Use	d to	Dis	able	Con	npar	ator	2								
	Select the so	urce wh	nich disa	ables	comp	arato	2																	
	Value		Mod	le				Descrip	tion															_
	0		TCM	/IP2				Compa gers a					wher	n the	e cou	ınter	equ	uals	TCI	MPV	'AL	and	trig-	_
	1		TXS	Т				Compa	rator	2 is	disa	bled	at T	K sta	art T	X En	gine	е						
	2		RXA	CT				Compa	rator	2 is	disa	bled	on R	X go	oing	goin	g A	ctive	e (de	efaul	t: lo	w)		
	3		RXA	CTN				Compa	rator	2 is	disa	bled	on R	X go	oing	Inac	tive	:						_
19	Reserved		To e		e com	patibil	ity w	ith futur	e dev	vices	, alv	vays	write	bits	to 0	. Мо	re ii	nfor	mati	on ir	1.	2 Co	nvei	n-
18:16	TSTART		0x0			RW		Timer	Start	Sou	rce													
	Source used	to start	compa	rator	2 and	timer																		
	Value		Mod	le				Descrip	tion															_
	0		DISA	ABLE	•			Compa	rator	2 is	disa	bled												
	1		TXE	OF				Compa	rator	2 an	d tir	ner a	re st	arte	d at	TX e	nd o	of fr	ame	l				
	2		TXC					Compa																
	3		RXA	CT				Compa low)	rator	2 an	nd tir	mer a	re st	arte	d at	RX g	join	g go	oing .	Activ	ve (defa	ult:	
	4		RXE	OF				Compa	rator	2 an	d tir	mer a	re st	arte	d at	RX e	end	of fr	ame	;				_

Bit	Name	Reset	Access	Description
15:8	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TCMPVAL	0x00	RW	Timer Comparator 2
	•	•	-	TCMP2 event and sets the TCMP2 flag. This event can also be used to 0x00 represents 256 baud times.

18.5.29 USARTn_ROUTEPEN - I/O Routing Pin Enable Register

Offset				Bit Position
0x074	33 29 28	27 26 25 24 23	22 21 20 20	0 1 2 3 4 5 2 6 7 8 8 7 9 9 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Reset				0 0 0 0 0
Access				RW RW WW WW
Name				RTSPEN CTSPEN CSPEN CSPE
Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
5	RTSPEN	0	RW	RTS Pin Enable
	When set, the	RTS pin of the USA	RT is enable	d.
	Value			Description
	0			The USn_RTS pin is disabled
	1			The USn_RTS pin is enabled
4	CTSPEN	0	RW	CTS Pin Enable
	When set, the	CTS pin of the USA	RT is enable	d.
	Value			Description
	0			The USn_CTS pin is disabled
	1			The USn_CTS pin is enabled
3	CLKPEN	0	RW	CLK Pin Enable
	When set, the	CLK pin of the USA	RT is enable	d.
	Value			Description
	0			The USn_CLK pin is disabled
	1			The USn_CLK pin is enabled
2	CSPEN	0	RW	CS Pin Enable
	When set, the	CS pin of the USAR	T is enabled	
	Value			Description
	0			The USn_CS pin is disabled
	1			The USn_CS pin is enabled
1	TXPEN	0	RW	TX Pin Enable
	When set, the	TX/MOSI pin of the	USART is er	nabled
	Value			Description
	0			The U(S)n_TX (MOSI) pin is disabled
	1			The U(S)n_TX (MOSI) pin is enabled

Bit	Name	Reset	Access	Description
0	RXPEN	0	RW	RX Pin Enable
	When set, the RX	X/MISO pin of the	USART is ena	abled.
	Value			Description
	0			The U(S)n_RX (MISO) pin is disabled
	1			The U(S)n_RX (MISO) pin is enabled

18.5.30 USARTn_ROUTELOC0 - I/O Routing Location Register

Offset		Bit Position																														
0x078	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset					2	0000				•			6	noxo Oxo							2	000								0000		
Access					<u>}</u>	<u>}</u>							2	<u>}</u>							2	<u>}</u>							Š	<u>}</u>		
Name					2	CLALOC							0	CSLOC							\ \ \ \) VEQC							2	ZALOC		

Name		CLKLO			CSLOC		TXLOC		RXLOC
Bit	Name		Reset	Access	Description				
31:30	Reserv	red	To ensure cor tions	mpatibility	with future dev	vices, al	ways write bits to 0. Mo	re inforn	nation in 1.2 Conven-
29:24	CLKLC	OC .	0x00	RW	I/O Location	า			
	Decide	s the location of	of the USART C	LK pin.					
	Value		Mode		Description				
	0		LOC0		Location 0				
	1		LOC1		Location 1				
	2		LOC2		Location 2				
	3		LOC3		Location 3				
	4		LOC4		Location 4				
	5		LOC5		Location 5				
	6		LOC6		Location 6				
	7		LOC7		Location 7				
	8		LOC8		Location 8				
	9		LOC9		Location 9				
	10		LOC10		Location 10				
	11		LOC11		Location 11				
	12		LOC12		Location 12				
	13		LOC13		Location 13				
	14		LOC14		Location 14				
	15		LOC15		Location 15				
	16		LOC16		Location 16				
	17		LOC17		Location 17				
	18		LOC18		Location 18				
	19		LOC19		Location 19				
	20		LOC20		Location 20				
	21		LOC21		Location 21				
	22		LOC22		Location 22				
	23		LOC23		Location 23				

Bit	Name	Reset Access	Description
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
23:22	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	CSLOC	0x00 RW	I/O Location
	Decides the location	of the USART CS pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22
	23	LOC23	Location 23

Bit	Name	Reset Access	Description
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
15:14	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
13:8	TXLOC	0x00 RW	I/O Location
	Decides the location	of the USART TX pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22
	23	LOC23	Location 23

Bit	Name	Reset Access	Description
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
7:6	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	RXLOC	0x00 RW	I/O Location
	Decides the location	of the USART RX pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22
	23	LOC23	Location 23

Bit	Name	Reset	Access	Description
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

18.5.31 USARTn ROUTELOC1 - I/O Routing Location Register

18.5.31	USARTn_ROUTE	LOC1 - I/O Routin	g Location	Register			
Offset				Bit Position			
0x07C	330 239 239 239	25 25 24 23 23	22 21 20	6 8 7 9 4	8 8 8	7	2 4 8 7 -
Reset					00×0		00×0
Access					NA N		ZW W
Name					RTSLOC		CTSLOC F
Bit	Name	Reset	Access	Description			
31:14	Reserved	To ensure o	compatibility	with future devices, a	lways write bits to 0. Mo	re inforn	nation in 1.2 Conver
13:8	RTSLOC	0x00	RW	I/O Location			
	Decides the loca	tion of the USART	RTS pin.				
	Value	Mode		Description			
	0	LOC0		Location 0			
	1	LOC1		Location 1			
	2	LOC2		Location 2			
	3	LOC3		Location 3			
	4	LOC4		Location 4			
	5	LOC5		Location 5			
	6	LOC6		Location 6			
	7	LOC7		Location 7			
	8	LOC8		Location 8			
	9	LOC9		Location 9			
	10	LOC10		Location 10			
	11	LOC11		Location 11			
	12	LOC12		Location 12			
	13	LOC13		Location 13			
	14	LOC14		Location 14			
	15	LOC15		Location 15			
	16	LOC16		Location 16			
	17	LOC17		Location 17			

Location 18

Location 19

Location 20

Location 21

Location 22

LOC18

LOC19

LOC20

LOC21

LOC22

18

19

20

21


22

Name Reset Access Description	ts to 0. More information in 1.2 Conven-
24 LOC24 Location 24 25 LOC25 Location 25 26 LOC26 Location 26 27 LOC27 Location 27 28 LOC28 Location 28 29 LOC29 Location 29 30 LOC30 Location 30 31 LOC31 Location 31 7:6 Reserved To ensure compatibility with future devices, always write bit tions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	ts to 0. More information in 1.2 Conven-
25	ts to 0. More information in 1.2 Conven-
26 LOC26 Location 26 27 LOC27 Location 27 28 LOC28 Location 28 29 LOC29 Location 29 30 LOC30 Location 30 31 LOC31 Location 31 7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
27	its to 0. More information in 1.2 Conven-
28 LOC28 Location 28 29 LOC30 Location 30 31 LOC31 Location 31 7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
29 LOC29 Location 29 30 LOC30 Location 30 31 LOC31 Location 31 7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
30 LOC30 Location 30 31 LOC31 Location 31 7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
7:6 Reserved To ensure compatibility with future devices, always write bittions 5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
5:0 CTSLOC 0x00 RW I/O Location Decides the location of the USART CTS pin. Value Mode Description	its to 0. More information in 1.2 Conven-
Decides the location of the USART CTS pin. Value Mode Description	
Value Mode Description	
0 LOC0 Location 0	
1 LOC1 Location 1	
2 LOC2 Location 2	
3 LOC3 Location 3	
4 LOC4 Location 4	
5 LOC5 Location 5	
6 LOC6 Location 6	
7 LOC7 Location 7	
8 LOC8 Location 8	
9 LOC9 Location 9	
10 LOC10 Location 10	
11 LOC11 Location 11	
12 LOC12 Location 12	
13 LOC13 Location 13	
14 LOC14 Location 14	
15 LOC15 Location 15	
16 LOC16 Location 16	
17 LOC17 Location 17	
18 LOC18 Location 18	
19 LOC19 Location 19	
20 LOC20 Location 20	
21 LOC21 Location 21	
22 LOC22 Location 22	

Bit	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

19. LEUART - Low Energy Universal Asynchronous Receiver/Transmitter





Quick Facts

What?

The LEUART provides full UART communication using a low frequency 32.768 kHz clock, and has special features for communication without CPU intervention.

Why?

It allows UART communication to be performed in low energy modes, using only a few μA during active communication and only 150 nA when waiting for incoming data.

How?

A low frequency clock signal allows communication with less energy. Using DMA, the LEUART can transmit and receive data with minimal CPU intervention. Special UART-frames can be configured to help control the data flow, further automating data transmission.

19.1 Introduction

The unique Low Energy UART (LEUART) is a UART that allows two-way UART communication on a strict power budget. Only a 32.768 kHz clock is needed to allow UART communication up to 9600 baud.

Even when the system is in low energy mode EM2 Deep Sleep (with most core functionality turned off), the LEUART can wait for an incoming UART frame while having an extremely low energy consumption. When a UART frame is completely received, the CPU can quickly be woken up. Alternatively, multiple frames can be transferred via the Direct Memory Access (DMA) module into RAM memory before waking up the CPU.

Received data can optionally be blocked until a configurable start frame is detected. A signal frame can be configured to generate an interrupt indicating the end of a data transmission. The start frame and signal frame can be used in combination to handle higher level communication protocols.

Similarly, data can be transmitted in EM2 Deep Sleep either on a frame-by-frame basis with data from the CPU or through use of the DMA.

The LEUART includes all necessary hardware support to make asynchronous serial communication possible with minimal software overhead and low energy consumption.

19.2 Features

- · Low energy asynchronous serial communications
- · Full/half duplex communication
- · Separate TX / RX enable
- · Separate double buffered transmit buffer and receive buffer
- · Programmable baud rate, generated as a fractional division of the LFBCLK
 - · Supports baud rates from 300 baud to 9600 baud
- · Can use a high frequency clock source for even higher baud rates
- Configurable number of data bits: 8 or 9 (plus parity bit, if enabled)
- · Configurable parity: off, even or odd
 - · HW parity bit generation and check
- · Configurable number of stop bits, 1 or 2
- · Capable of sleep-mode wake-up on received frame
 - · Either wake-up on any received byte or
 - · Wake up only on specified start and signal frames
- · Supports transmission and reception in EM0 Active, EM1 Sleep and EM2 Deep Sleep with
 - Full DMA support
 - · Specified start-frame can start reception automatically
- IrDA modulator (pulse generator, pulse extender)
- · Multi-processor mode
- · Loopback mode
 - · Half duplex communication
 - · Communication debugging
- · PRS RX input

19.3 Functional Description

An overview of the LEUART module is shown in Figure 19.1 LEUART Overview on page 616.




Figure 19.1. LEUART Overview

19.3.1 Frame Format

The frame format used by the LEUART consists of a set of data bits in addition to bits for synchronization and optionally a parity bit for error checking. A frame starts with one start-bit (S), where the line is driven low for one bit-period. This signals the start of a frame, and is used for synchronization. Following the start bit are 8 or 9 data bits and an optional parity bit. The data is transmitted with the least significant bit first. Finally, a number of stop-bits, where the line is driven high, end the frame. The frame format is shown in Figure 19.2 LEUART Asynchronous Frame Format on page 617.




Figure 19.2. LEUART Asynchronous Frame Format

The number of data bits in a frame is set by DATABITS in LEUARTn_CTRL, and the number of stop-bits is set by STOPBITS in LEUARTn_CTRL. Whether or not a parity bit should be included, and whether it should be even or odd is defined by PARITY in LEUARTn_CTRL. For communication to be possible, all parties of an asynchronous transfer must agree on the frame format being used.

The frame format used by the LEUART can be inverted by setting INV in LEUARTn_CTRL. This affects the entire frame, resulting in a low idle state, a high start-bit, inverted data and parity bits, and low stop-bits. INV should only be changed while the receiver is disabled.

19.3.1.1 Parity Bit Calculation and Handling

Hardware automatically inserts parity bits into outgoing frames and checks the parity bits of incoming frames. The possible parity modes are defined in Table 19.1 LEUART Parity Bit on page 617. When even parity is chosen, a parity bit is inserted to make the number of high bits (data + parity) even. If odd parity is chosen, the parity bit makes the total number of high bits odd. When parity bits are disabled, which is the default configuration, the parity bit is omitted.

PARITY [1:0]

Description

No parity (default)

Reserved

Even parity

Odd parity

Table 19.1. LEUART Parity Bit

See 19.3.5.4 Parity Error for more information on parity bit handling.

19.3.2 Clock Source

The LEUART clock source is selected by the LFB bit field the CMU_LFBCLKSEL register. The clock is prescaled by the LEUARTn bitfield in the CMU_LFBPRESC0 register and enabled by the LEUARTn bit in the CMU_LFBCLKEN0. See Figure 11.2 CMU Overview - Low Frequency Portion on page 280 for a diagram of the clocking structure.

To use this module, the LE interface clock must be enabled in CMU_HFBUSCLKEN0, in addition to the module clock.

19.3.3 Clock Generation

The LEUART clock defines the transmission and reception data rate. The clock generator employs a fractional clock divider to allow baud rates that are not attainable by integral division of the 32.768 kHz clock that drives the LEUART.

The clock divider used in the LEUART is a 14-bit value, with a 9-bit integral part and a 5-bit fractional part. The baud rate of the LEUART is given by:

br = fLEUARTn / (1 + LEUARTn_CLKDIV / 256)

Figure 19.3. LEUART Baud Rate Equation

where fLEUARTn is the clock frequency supplied to the LEUART. The value of LEUARTn_CLKDIV thus defines the baud rate of the LEUART. The integral part of the divider is right-aligned in the upper 24 bits of LEUARTn_CLKDIV and the fractional part is left-aligned in the lower 8 bits. The divider is thus a 256th of LEUARTn_CLKDIV as seen in the equation.

As an example let us assume fLEUART = 22.5 kHz and the value of DIV in LEUARTn_CLKDIV is $0x0028 \text{ (LEUARTn_CLKDIV = } 0x00000140)$. The baud rate = 22.5 kHz / (1 + 0x140 / 256) = 22.5 kHz / 2.25 = 10 kHz.

For a desired baud rate br_{DESIRED}, LEUARTn_CLKDIV can be calculated by using:

LEUARTn_CLKDIV = 256 x (fLEUARTn/br_{DESIRED} - 1)

Figure 19.4. LEUART CLKDIV Equation

It's important to note that this equation results in a 32bit value for the LEUARTn_CLKDIV register but only bits [16:3] are valid and all others must be 0. For example if we have a 32 kHz clock and whish to achieve a baud rate of 10 kHz the equation above results in a LEUARTn_CLKDIV value of 0x233. However, the actual value of the register will be 0x230 since bits [2:0] cannot be set. This limits the best achievable acuracy. In this example the actual baud rate will be 32 kHz / (1+ 0x230 / 255) = 10.039 kHz instead of 32 kHz / (1+ 0x233 / 255) = 10.002 kHz.

Table 19.2 LEUART Baud Rates on page 618 lists a set of desired baud rates and the closest baud rates reachable by the LEUART with a 32.768 kHz clock source. It also shows the average baud rate error.

Desired baud rate	LEUARTn_CLKDIV	LEUARTn_CLKDIV/256	Actual Baud Rate	Error [%]
300	27704	108.21875	300.0217	0.01
600	13728	53.625	599.8719	-0.02
1200	6736	26.3125	1199.744	-0.02
2400	3240	12.65625	2399.487	-0.02
4800	1488	5.8125	4809.982	0.21
9600	616	2.40625	9619.963	0.21

Table 19.2. LEUART Baud Rates

19.3.4 Data Transmission

Data transmission is initiated by writing data to the transmit buffer using one of the methods described in 19.3.4.1 Transmit Buffer Operation. When the transmit shift register is empty and ready for new data, a frame from the transmit buffer is loaded into the shift register, and if the transmitter is enabled, transmission begins. When the frame has been transmitted, a new frame is loaded into the shift register if available, and transmission continues. If the transmit buffer is empty, the transmitter goes to an idle state, waiting for a new frame to become available. Transmission is enabled through the command register LEUARTn_CMD by setting TXEN, and disabled by setting TXDIS. When the transmitter is disabled using TXDIS, any ongoing transmission is aborted, and any frame currently being transmitted is discarded. When disabled, the TX output goes to an idle state, which by default is a high value. Whether or not the transmitter is enabled at a given time can be read from TXENS in LEUARTn_STATUS. After a transmission, when there is no more data in the shift register or transmit buffer, the TXC flag in LEUARTn_STATUS and the TXC interrupt flag in LEUARTn_IF are set, signaling that the transmitter is idle. The TXC status flag is cleared when a new byte becomes available for transmission, but the TXC interrupt flag must be cleared by software.

19.3.4.1 Transmit Buffer Operation

A frame can be loaded into the transmit buffer by writing to LEUARTn_TXDATA or LEUARTn_TXDATAX. Using LEUARTn_TXDATA allows 8 bits to be written to the buffer. If 9 bit frames are used, the 9th bit will in that case be set to the value of BIT8DV in LEUARTn_CTRL. To set the 9th bit directly and/or use transmission control, LEUARTn_TXDATAX must be used. When writing data to the transmit buffer using LEUARTn_TXDATAX, the 9th bit written to LEUARTn_TXDATAX overrides the value in BIT8DV, and alone defines the 9th bit that is transmitted if 9-bit frames are used.

If a write is attempted to the transmit buffer when it is not empty, the TXOF interrupt flag in LEUARTn_IF is set, indicating the overflow. The data already in the buffer is in that case preserved, and no data is written.

In addition to the interrupt flag TXC in LEUARTn_IF and the status flag TXC in LEUARTn_STATUS which are set when the transmitter becomes idle, TXBL in LEUARTn_STATUS and the TXBL interrupt flag in LEUARTn_IF are used to indicate the level of the transmit buffer. Whenever the transmit buffer becomes empty, these flags are set high. Both the TXBL status flag and the TXBL interrupt flag are cleared automatically when data is written to the transmit buffer.

There is also TXIDLE status in LEUART_STATUS which can be used to detect when the transmit state machine is in the idle state.

The transmit buffer, including the TX shift register can be cleared by setting command bit CLEARTX in LEUARTn_CMD. This will prevent the LEUART from transmitting the data in the buffer and shift register, and will make them available for new data. Any frame currently being transmitted will not be aborted. Transmission of this frame will be completed. An overview of the operation of the transmitter is shown in Figure 19.5 LEUART Transmitter Overview on page 619.




Figure 19.5. LEUART Transmitter Overview

19.3.4.2 Frame Transmission Control

The transmission control bits, which can be written using LEUARTn_TXDATAX, affect the transmission of the written frame. The following options are available:

- Generate break: By setting TXBREAK, the output will be held low during the first stop-bit period to generate a framing error. A receiver that supports break detection detects this state, allowing it to be used e.g. for framing of larger data packets. The line is driven high for one bit period before the next frame is transmitted so the next start condition can be identified correctly by the recipient. Continuous breaks lasting longer than an UART frame are thus not supported by the LEUART. GPIO can be used for this. Note that when AUTOTRI in LEUARTn_CTRL is used, the transmitter is not tristated before the high-bit after the break has been transmitted.
- · Disable transmitter after transmission: If TXDISAT is set, the transmitter is disabled after the frame has been fully transmitted.
- Enable receiver after transmission: If RXENAT is set, the receiver is enabled after the frame has been fully transmitted. It is enabled in time to detect a start-bit directly after the last stop-bit has been transmitted.

The transmission control bits in the LEUART cannot tristate the transmitter. This is performed automatically by hardware if AUTOTRI in LEUARTn_CTRL is set. See 19.3.7 Half Duplex Communication for more information on half duplex operation.

19.3.5 Data Reception

Data reception is enabled by setting RXEN in LEUARTn_CMD. When the receiver is enabled, it actively samples the input looking for a transition from high to low indicating the start bit of a new frame. When a start bit is found, reception of the new frame begins if the receive shift register is empty and ready for new data. When the frame has been received, it is pushed into the receive buffer, making the shift register ready for another frame of data, and the receiver starts looking for another start bit. If the receive buffer is full, the received frame remains in the shift register until more space in the receive buffer is available.

If an incoming frame is detected while both the receive buffer and the receive shift register are full, the data in the receive shift register is overwritten, and the RXOF interrupt flag in LEUARTn_IF is set to indicate the buffer overflow.

The receiver can be disabled by setting the command bit RXDIS in LEUARTn_CMD. Any frame currently being received when the receiver is disabled is discarded. Whether or not the receiver is enabled at a given time can be read out from RXENS in LEUARTn_STATUS.

The receive buffer,can be cleared by setting command bit CLEARRX in LEUARTn_CMD. This will make it avaliable for new data. Any frame currently being received will not be aborted and will become the first received frame when complete.

19.3.5.1 Receive Buffer Operation

When data becomes available in the receive buffer, the RXDATAV flag in LEUARTn_STATUS and the RXDATAV interrupt flag in LEUARTn_IF are set. Both the RXDATAV status flag and the RXDATAV interrupt flag are cleared by hardware when data is no longer available, i.e. when data has been read out of the buffer.

Data can be read from receive buffer using either LEUARTn_RXDATA or LEUARTn_RXDATAX. LEUARTn_RXDATA gives access to the 8 least significant bits of the received frame, while LEUARTn_RXDATAX must be used to get access to the 9th, most significant bit. The LEUARTn_RXDATAX register also contains status information regarding the frame.

When a frame is read from the receive buffer using LEUARTn_RXDATA or LEUARTn_RXDATAX, the frame is removed from the buffer, making room for a new one. If an attempt is done to read more frames from the buffer than what is available, the RXUF interrupt flag in LEUARTn IF is set to signal the underflow, and the data read from the buffer is undefined.

Frames can also be read from the receive buffer without removing the data by using LEUARTn_RXDATAXP, which gives access to the frame in the buffer including control bits. Data read from this register when the receive buffer is empty is undefined. No underflow interrupt is generated by a read using LEUARTn_RXDATAXP, i.e. the RXUF interrupt flag is never set as a result of reading from LEUARTn_RXDATAXP.

An overview of the operation of the receiver is shown in Figure 19.6 LEUART Receiver Overview on page 620.




Figure 19.6. LEUART Receiver Overview

19.3.5.2 Blocking Incoming Data

When using hardware frame recognition, as detailed in 19.3.5.6 Programmable Start Frame, 19.3.5.7 Programmable Signal Frame, and 19.3.5.8 Multi-Processor Mode, it is necessary to be able to let the receiver sample incoming frames without passing the frames to software by loading them into the receive buffer. This is accomplished by blocking incoming data.

Incoming data is blocked as long as RXBLOCK in LEUARTn_STATUS is set. When blocked, frames received by the receiver will not be loaded into the receive buffer, and software is not notified by the RXDATAV bit in LEUARTn_STATUS or the RXDATAV interrupt flag in LEUARTn_IF at their arrival. For data to be loaded into the receive buffer, RXBLOCK must be cleared in the instant a frame is fully received by the receiver. RXBLOCK is set by setting RXBLOCKEN in LEUARTn_CMD and disabled by setting RXBLOCKDIS also in LEUARTn_CMD. There are two exceptions where data is loaded into the receive buffer even when RXBLOCK is set. The first is when an address frame is received when in operating in multi-processor mode as shown in 19.3.5.8 Multi-Processor Mode. The other case is when receiving a start-frame when SFUBRX in LEUARTn_CTRL is set; see 19.3.5.6 Programmable Start Frame

Frames received containing framing or parity errors will not result in the FERR and PERR interrupt flags in LEUARTn_IF being set while RXBLOCK is set. Hardware recognition is not applied to these erroneous frames, and they are silently discarded.

Note:

- If a frame is received while RXBLOCK in LEUARTn_STATUS is cleared, but stays in the receive shift register because the receive buffer is full, the received frame will be loaded into the receive buffer when space becomes available even if RXBLOCK is set at that time.
- The overflow interrupt flag RXOF in LEUARTn_IF will be set if a frame in the receive shift register, waiting to be loaded into the receive buffer is overwritten by an incoming frame even though RXBLOCK is set.

19.3.5.3 Data Sampling

The receiver samples each incoming bit as close as possible to the middle of the bit-period. Except for the start-bit, only a single sample is taken of each of the incoming bits.

The length of a bit-period is given by 1 + LEUARTn_CLKDIV/256, as a number of 32.768 kHz clock periods. Let the clock cycle where a start-bit is first detected be given the index 0. The optimal sampling point for each bit in the UART frame is then given by the following equation:

 $S_{opt}(n) = n (1 + LEUARTn_CLKDIV/256) + LEUARTn_CLKDIV/512$

Figure 19.7. LEUART Optimal Sampling Point

where n is the bit-index.

Since samples are only done on the positive edges of the 32.768 kHz clock, the actual samples are performed on the closest positive edge, i.e. the edge given by the following equation:

 $S(n) = floor(n \times (1 + LEUARTn CLKDIV/256) + LEUARTn CLKDIV/512)$

Figure 19.8. LEUART Actual Sampling Point

The sampling location will thus have jitter according to difference between S_{opt} and S. The start-bit is found at n=0, then follows the data bits, any parity bit, and the stop bits.

If the value of the start-bit is found to be high, then the start-bit is discarded, and the receiver waits for a new start-bit.

19.3.5.4 Parity Error

When the parity bit is enabled, a parity check is automatically performed on incoming frames. When a parity error is detected in a frame, the data parity error bit PERR in the frame is set, as well as the interrupt flag PERR. Frames with parity errors are loaded into the receive buffer like regular frames.

PERR can be accessed by reading the frame from the receive buffer using the LEUARTn_RXDATAX register.

19.3.5.5 Framing Error and Break Detection

A framing error is the result of a received frame where the stop bit was sampled to a value of 0. This can be the result of noise and baud rate errors, but can also be the result of a break generated by the transmitter on purpose.

When a framing error is detected, the framing error bit FERR in the received frame is set. The interrupt flag FERR in LEUARTn_IF is also set. Frames with framing errors are loaded into the receive buffer like regular frames.

FERR can be accessed by reading the frame from the receive buffer using the LEUARTn_RXDATAX or LEUARTn_RXDATAXP registers.

19.3.5.6 Programmable Start Frame

The LEUART can be configured to start receiving data when a special start frame is detected on the input. This can be useful when operating in low energy modes, allowing other devices to gain the attention of the LEUART by transmitting a given frame.

When SFUBRX in LEUARTn_CTRL is set, an incoming frame matching the frame defined in LEUARTn_STARTFRAME will result in RXBLOCK in LEUARTn_STATUS being cleared. This can be used to enable reception when a specified start frame is detected. If the receiver is enabled and blocked, i.e. RXENS and RXBLOCK in LEUARTn_STATUS are set, the receiver will receive all incoming frames, but unless an incoming frame is a start frame it will be discarded and not loaded into the receive buffer. When a start frame is detected, the block is cleared, and frames received from that point, including the start frame, are loaded into the receive buffer.

An incoming start frame results in the STARTF interrupt flag in LEUARTn_IF being set, regardless of the value of SFUBRX in LEUARTn CTRL. This allows an interrupt to be made when the start frame is detected.

When 8 data-bit frame formats are used, only the 8 least significant bits of LEUARTn_STARTFRAME are compared to incoming frames. The full length of LEUARTn_STARTFRAME is used when operating with frames consisting of 9 data bits.

Note: The receiver must be enabled for start frames to be detected. In addition, a start frame with a parity error or framing error is not detected as a start frame.

19.3.5.7 Programmable Signal Frame

As well as the configurable start frame, a special signal frame can be specified. When a frame matching the frame defined in LEUARTn_SIGFRAME is detected by the receiver, the SIGF interrupt flag in LEUARTn_IF is set. As for start frame detection, the receiver must be enabled for signal frames to be detected.

One use of the programmable signal frame is to signal the end of a multi-frame message transmitted to the LEUART. An interrupt will then be triggered when the packet has been completely received, allowing software to process it. Used in conjunction with the programmable start frame and DMA, this makes it possible for the LEUART to automatically begin the reception of a packet on a specified start frame, load the entire packet into memory, and give an interrupt when reception of a packet has completed. The device can thus wait for data packets in EM2 Deep Sleep, and only be woken up when a packet has been completely received.

A signal frame with a parity error or framing error is not detected as a signal frame.

19.3.5.8 Multi-Processor Mode

To simplify communication between multiple processors and maintain compatibility with the USART, the LEUART supports a multi-processor mode. In this mode the 9th data bit in each frame is used to indicate whether the content of the remaining 8 bits is data or an address.

When multi-processor mode is enabled, an incoming 9-bit frame with the 9th bit equal to the value of MPAB in LEUARTn_CTRL is identified as an address frame. When an address frame is detected, the MPAF interrupt flag in LEUARTn_IF is set, and the address frame is loaded into the receive register. This happens regardless of the value of RXBLOCK in LEUARTn_STATUS.

Multi-processor mode is enabled by setting MPM in LEUARTn_CTRL. The mode can be used in buses with multiple slaves, allowing the slaves to be addressed using the special address frames. An addressed slave, which was previously blocking reception using RXBLOCK, would then unblock reception, receive a message from the bus master, and then block reception again, waiting for the next message. See the USART for a more detailed example.

Note: The programmable start frame functionality can be used for automatic address matching, enabling reception on a correctly configured incoming frame.

An address frame with a parity error or a framing error is not detected as an address frame. The Start, Signal, and address frames should not be set to match the same frame since each of these uses separate synchronization to the peripherial clock domain.

19.3.6 Loopback

The LEUART receiver samples LEUn_RX by default, and the transmitter drives LEUn_TX by default. This is not the only configuration however. When LOOPBK in LEUARTn_CTRL is set, the receiver is connected to the LEUn_TX pin as shown in Figure 19.9 LEUART Local Loopback on page 623. This is useful for debugging, as the LEUART can receive the data it transmits, but it is also used to allow the LEUART to read and write to the same pin, which is required for some half duplex communication modes. In this mode, the LEUn_TX pin must be enabled as an output in the GPIO.




Figure 19.9. LEUART Local Loopback

19.3.7 Half Duplex Communication

When doing full duplex communication, two data links are provided, making it possible for data to be sent and received at the same time. In half duplex mode, data is only sent in one direction at a time. There are several possible half duplex setups, as described in the following sections.

19.3.7.1 Single Data-link

In this setup, the LEUART both receives and transmits data on the same pin. This is enabled by setting LOOPBK in LEUARTn_CTRL, which connects the receiver to the transmitter output. Because they are both connected to the same line, it is important that the LEUART transmitter does not drive the line when receiving data, as this would corrupt the data on the line.

When communicating over a single data-link, the transmitter must thus be tristated whenever not transmitting data. If AUTOTRI in LEUARTn_CTRL is set, the LEUART automatically tristates LEUn_TX whenever the transmitter is inactive. It is then the responsibility of the software protocol to make sure the transmitter is not transmitting data whenever incoming data is expected.

The transmitter can also be tristated from software by configuring the GPIO pin as an input and disabling the LEUART output on LEUn_TX.

Note: Another way to tristate the transmitter is to enable wired-and or wired-or mode in GPIO. For wired-and mode, outputting a 1 will be the same as tristating the output, and for wired-or mode, outputting a 0 will be the same as tristating the output. This can only be done on buses with a pull-up or pull-down resistor respectively.

19.3.7.2 Single Data-link With External Driver

Some communication schemes, such as RS-485 rely on an external driver. Here, the driver has an extra input which enables it, and instead of Tristating the transmitter when receiving data, the external driver must be disabled. The USART has hardware support for automatically turning the driver on and off. When using the LEUART in such a setup, the driver must be controlled by a GPIO. Figure 19.10 LEUART Half Duplex Communication with External Driver on page 624 shows an example configuration using an external driver.




Figure 19.10. LEUART Half Duplex Communication with External Driver

19.3.7.3 Two Data-links

Some limited devices only support half duplex communication even though two data links are available. In this case software is responsible for making sure data is not transmitted when incoming data is expected.

19.3.8 Transmission Delay

By configuring TXDELAY in LEUARTn_CTRL, the transmitter can be forced to wait a number of bit-periods from when it is ready to transmit data, to when it actually transmits the data. This delay is only applied to the first frame transmitted after the transmitter has been idle. When transmitting frames back-to-back the delay is not introduced between the transmitted frames.

This is useful on half duplex buses, because the receiver always returns received frames to software during the first stop-bit. The bus may still be driven for up to 3 bit periods, depending on the current frame format. Using the transmission delay, a transmission can be started when a frame is received, and it is possible to make sure that the transmitter does not begin driving the output before the frame on the bus is completely transmitted.

To route the UART TX and RX signals to a pin first select the desired pins using the RXLOC and TXLOC fields in the LEUARTn_ROUTELOC0 register. Then enable the connection using TXPEN and RXPEN in the LEUARTn_ROUTPEN register. See the device data sheet for mappings between UART locations (LOC0, LOC1, etc.) and device pins (PA0, PA1, etc.).

19.3.9 PRS RX Input

In addition to receiving data on an external pin the LEUART can be configured to receive data directly from a PRS channel by setting RX_PRS in LEUARTn_INPUT. The PRS channel used can be selected using RX_PRS_SEL in LEUARTn_INPUT. See the PRS chapter for more details on the PRS block.

For example the output of a comparator could be routed to the LEUART through the PRS to allow for receiving a signal with low peak-to-peak voltage or a significant DC offset.

19.3.10 DMA Support

The LEUART has full DMA support in energy modes EM0 Active – EM2 Deep Sleep. The DMA controller can write to the transmit buffer using the registers LEUARTn_TXDATA and LEUARTn_TXDATAX, and it can read from receive buffer using the registers LEUARTn_RXDATA and LEUARTn_RXDATAX. This enables single byte transfers and 9 bit data + control/status bits transfers both to and from the LEUART. The DMA will start up the HFRCO and run from this when it is waken by the LEUART in EM2. The HFRCO is disabled once the transaction is done.

A request for the DMA controller to read from the receive buffer can come from one of the following sources:

· Receive buffer full

A write request can come from one of the following sources:

- · Transmit buffer and shift register empty. No data to send.
- · Transmit buffer empty

In some cases, it may be sensible to temporarily stop DMA access to the LEUART when a parity or framing error has occurred. This is enabled by setting ERRSDMA in LEUARTn_CTRL. When this bit is set, the DMA controller will not get requests from the receive buffer if a framing error or parity error is detected in the received byte. The ERRSDMA bit applies only to the RX DMA.

When operating in EM2 Deep Sleep, the DMA controller must be powered up in order to perform the transfer. This is automatically performed for read operations if RXDMAWU in LEUARTn_CTRL is set and for write operations if TXDMAWU in LEUARTn_CTRL is set. To make sure the DMA controller still transfers bits to and from the LEUART in low energy modes, these bits must thus be configured accordingly.

Note: When RXDMAWU or TXDMAWU is set, the system will not be able to go to EM2 Deep Sleep/EM3 Stop before all related LEUART DMA requests have been processed. This means that if RXDMAWU is set and the LEUART receives a frame, the system will not be able to go to EM2 Deep Sleep/EM3 Stop before the frame has been read from the LEUART. In order for the system to go to EM2 during the last byte transmission, LEUART_CTRL_TXDMAWU must be cleared in the DMA interrupt service routine. This is because TXBL will be high during that last byte transfer.

19.3.11 Pulse Generator/ Pulse Extender

The LEUART has an optional pulse generator for the transmitter output, and a pulse extender on the receiver input. These are enabled by setting PULSEEN in LEUARTn_PULSECTRL, and with INV in LEUARTn_CTRL set, they will change the output/input format of the LEUART from NRZ to RZI as shown in Figure 19.11 LEUART - NRZ vs. RZI on page 625.




Figure 19.11. LEUART - NRZ vs. RZI

If PULSEEN in LEUARTn_PULSECTRL is set while INV in LEUARTn_CTRL is cleared, the output waveform will look like RZI shown in Figure 19.11 LEUART - NRZ vs. RZI on page 625, only inverted.

The width of the pulses from the pulse generator can be configured using PULSEW in LEUARTn_PULSECTRL. The generated pulse width is PULSEW + 1 cycles of the 32.768 kHz clock, which makes pulse width from 31.25µs to 500µs possible.

Since the incoming signal is only sampled on positive clock edges, the width of the incoming pulses must be at least two 32.768 kHz clock periods wide for reliable detection by the LEUART receiver. They must also be shorter than half a UART bit period.

At 2400 baud or lower, the pulse generator is able to generate RZI pulses compatible with the IrDA physical layer specification. The external IrDA device must generate pulses of sufficient length for successful two-way communication.

PULSEFILT in the LEUARTn_PULSECTRL register can be used to extend the minimum receive pulse width from 2 clock periods to 3 clock periods.

19.3.11.1 Interrupts

The interrupts generated by the LEUART are combined into one interrupt vector. If LEUART interrupts are enabled, an interrupt will be made if one or more of the interrupt flags in LEUARTn_IF and their corresponding bits in LEUART_IEN are set.

19.3.12 Register Access

Since this module is a Low Energy Peripheral, and runs off a clock which is asynchronous to the HFCORECLK, special considerations must be taken when accessing registers. Refer to 4.3 Access to Low Energy Peripherals (Asynchronous Registers) for a description on how to perform register accesses to Low Energy Peripherals.

The registers LEUARTn_FREEZE and LEUARTn_SYNCBUSY are used for synchronization of this peripheral.

19.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	LEUARTn_CTRL	RW	Control Register
0x004	LEUARTn_CMD	W1	Command Register
0x008	LEUARTn_STATUS	R	Status Register
0x00C	LEUARTn_CLKDIV	RW	Clock Control Register
0x010	LEUARTn_STARTFRAME	RW	Start Frame Register
0x014	LEUARTn_SIGFRAME	RW	Signal Frame Register
0x018	LEUARTn_RXDATAX	R(a)	Receive Buffer Data Extended Register
0x01C	LEUARTn_RXDATA	R(a)	Receive Buffer Data Register
0x020	LEUARTn_RXDATAXP	R	Receive Buffer Data Extended Peek Register
0x024	LEUARTn_TXDATAX	W	Transmit Buffer Data Extended Register
0x028	LEUARTn_TXDATA	W	Transmit Buffer Data Register
0x02C	LEUARTn_IF	R	Interrupt Flag Register
0x030	LEUARTn_IFS	W1	Interrupt Flag Set Register
0x034	LEUARTn_IFC	(R)W1	Interrupt Flag Clear Register
0x038	LEUARTn_IEN	RW	Interrupt Enable Register
0x03C	LEUARTn_PULSECTRL	RW	Pulse Control Register
0x040	LEUARTn_FREEZE	RW	Freeze Register
0x044	LEUARTn_SYNCBUSY	R	Synchronization Busy Register
0x054	LEUARTn_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x058	LEUARTn_ROUTELOC0	RW	I/O Routing Location Register
0x064	LEUARTn_INPUT	RW	LEUART Input Register

19.5 Register Description

Offset

19.5.1 LEUARTn_CTRL - Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Bit Position

0.000	-						I		۵.	Π	_	_		Ι.					۵.				T		Τ			Τ			
0x000	30	53	78	27	26	52	24	23	22	2	20	19	9	17	16	15	4	13	12	7	9	ဝ	∞	/	9	2	4	ო	7	_	0
Reset																3	2	0	0	0	0	0	0	0	0	0	0	3	<u> </u>	0	0
Access																2	<u>}</u>	₩ W	₽	R₩	R ₩	RW	₩	₩	₽	₩	R ≪	2	≩ Y	S.	S S S
Name																\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	IADELAT	TXDMAWU	RXDMAWU	BIT8DV	MPAB	MPM	SFUBRX	LOOPBK	ERRSDMA	<u>N</u>	STOPBITS	5	TAK T	DATABITS	AUTOTRI
Bit	Name					Re	set			Ac	ces	s	Des	scrip	otior	1															
31:16	Reser	ved				To tion		ure	con	pat	ibilit _.	y w	ith f	uture	e de	vices	s, alı	way	s wr	ite b	its t	o 0.	Мо	re ir	nforr	natio	on ir	1.2	2 Co	nvei	n-
15:14	TXDEI	LAY				0x0)			RV	V		TX	Dela	ay T	rans	mis	sio	n												
	Config	urab	ole d	elay	bef	ore	new	/ tra	nsfe	rs. I	Fran	nes	sen	t ba	ck-to	o-ba	ck a	re n	ot d	elay	ed.										
	Value					Мо	de						Des	scrip	tion																_
	0					NC	NE						Fra	mes	are	tran	smit	tted	imn	nedia	ately	/									
	1					SIN	NGL	Е					Tra	nsm	issic	n of	nev	v fra	mes	s are	de	laye	d by	/as	singl	e bit	per	riod			
	2					DC	UBI	LE					Tra	nsm	issic	n of	nev	v fra	mes	s are	de	laye	d by	/ two	o bit	per	iods	;			
	3					TR	IPLI	E					Tra	nsm	issic	n of	nev	v fra	mes	are	de	laye	d by	/ thr	ee b	oit pe	erioc	ds			
13	TXDM	AWI	J			0				RV	V		TX	DMA	A Wa	akeı	ıp														
	Set to	wak	e the	e DN	/IA c	conti	rolle	r up	wh	en iı	n EN	/12	and	spac	ce is	ava	ilabl	le in	the	trar	ismi	t bu	ffer.								
	Value												Des	scrip	tion																_
	0															l2, the in t						ill no	ot ge	et re	que	sts a	abou	ut sp	ace	be-	
	1													A is		ilable fer	e in	EM2	2 for	the	req	uest	t ab	out s	spac	e a	vaila	able	in th	ie	_
12	RXDM	IAWI	U			0				RV	V		RX	DM	A W	akeı	ир														
	Set to	wak	e the	e DN	/IA c	conti	rolle	r up	wh	en iı	n EN	/12	and	data	is a	ıvaila	able	in tl	he r	ecei	ve b	uffe	r.								
	Value												Des	scrip	tion																_
	0															l2, th					er w	ill no	ot ge	et re	que	sts	abou	ut da	ata b	ein	3
	1												DM fer	A is	avai	ilable	e in	EM2	2 for	the	req	uest	t abo	out (data	in t	he r	ecei	ve b	uf-	
11	BIT8D	V				0				RV	V		Bit	8 De	efau	It Va	alue														

When 9-bit frames are transmitted, the default value of the 9th bit is given by BIT8DV. If TXDATA is used to write a frame, then the value of BIT8DV is assigned to the 9th bit of the outgoing frame. If a frame is written with TXDATAX however, the default value is overridden by the written value.

Bit	Name	Reset	Access	Description
10	MPAB	0	RW	Multi-Processor Address-Bit
		ue of the multi-proc multi-processor add		s bit. An incoming frame with its 9th bit equal to the value of this bit marks
)	MPM	0	RW	Multi-Processor Mode
	Set to enable m	ulti-processor mod	e.	
	Value			Description
	0			The 9th bit of incoming frames have no special function
	1			An incoming frame with the 9th bit equal to MPAB will be loaded into the receive buffer regardless of RXBLOCK and will result in the MPAB interrupt flag being set
3	SFUBRX	0	RW	Start-Frame UnBlock RX
	Clears RXBLOC	CK when the start-f	rame is found	in the incoming data. The start-frame is loaded into the receive buffer.
	Value			Description
	0			Detected start-frames have no effect on RXBLOCK
	1			When a start-frame is detected, RXBLOCK is cleared and the start-frame is loaded into the receive buffer
,	LOOPBK	0	RW	Loopback Enable
	200.2.			
		receiver to LEUn_T	X instead of L	.EUn_RX.
		receiver to LEUn_T	X instead of L	.EUn_RX. Description
	Set to connect r	receiver to LEUn_T	X instead of L	
	Set to connect r	receiver to LEUn_T	X instead of L	Description
	Set to connect r Value	receiver to LEUn_T	X instead of L	Description The receiver is connected to and receives data from LEUn_RX
	Value 0 1 ERRSDMA	0	RW	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX
	Value 0 1 ERRSDMA	0	RW	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error
6	Set to connect r Value 0 1 ERRSDMA When set, RX D	0	RW	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors.
	Value 0 1 ERRSDMA When set, RX E	0	RW	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the
5	Set to connect r Value 0 1 ERRSDMA When set, RX D Value 0	0	RW	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or
5	Set to connect r Value 0 1 ERRSDMA When set, RX E Value 0 1	0 DMA requests will b	RW se cleared on f	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output
5	Set to connect r Value 0 1 ERRSDMA When set, RX E Value 0 1	0 DMA requests will b	RW se cleared on f	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output
	Set to connect r Value 0 1 ERRSDMA When set, RX D Value 0 1 INV Set to invert the	0 DMA requests will b	RW se cleared on f	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output In LEUn_RX.
5	Set to connect r Value 0 1 ERRSDMA When set, RX E Value 0 1 INV Set to invert the Value	0 DMA requests will b	RW se cleared on f	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output In LEUn_RX. Description
6	Set to connect r Value 0 1 ERRSDMA When set, RX E Value 0 1 INV Set to invert the Value 0	0 DMA requests will b	RW se cleared on f	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output In LEUn_RX. Description A high value on the input/output is 1, and a low value is 0.
5	Set to connect rowal value 0 1 ERRSDMA When set, RX E Value 0 1 INV Set to invert the Value 0 1 STOPBITS	0 DMA requests will be 0 coutput on LEUn_1	RW RW X and input o	Description The receiver is connected to and receives data from LEUn_RX The receiver is connected to and receives data from LEUn_TX Clear RX DMA on Error framing and parity errors. Description Framing and parity errors have no effect on DMA requests from the LEUART RX DMA requests from the LEUART are disabled if a framing error or parity error occurs. Invert Input and Output In LEUn_RX. Description A high value on the input/output is 1, and a low value is 0. A low value on the input/output is 1, and a high value is 0.

Bit	Name	Reset	Access	Description
	0	ONE		One stop-bit is transmitted with every frame
	1	TWO		Two stop-bits are transmitted with every frame
3:2	PARITY	0x0	RW	Parity-Bit Mode
	Determines whet	ther parity bits are	enabled, and	I whether even or odd parity should be used.
	Value	Mode		Description
	0	NONE		Parity bits are not used
	2	EVEN		Even parity are used. Parity bits are automatically generated and checked by hardware.
	3	ODD		Odd parity is used. Parity bits are automatically generated and checked by hardware.
1	DATABITS	0	RW	Data-Bit Mode
	This register sets	s the number of da	ita bits.	
	Value	Mode		Description
	0	EIGHT		Each frame contains 8 data bits
	1	NINE		Each frame contains 9 data bits
0	AUTOTRI	0	RW	Automatic Transmitter Tristate
	When set, LEUn	_TX is tristated wh	nenever the tr	ansmitter is inactive.
	Value			Description
	0			LEUn_TX is held high when the transmitter is inactive. INV inverts the inactive state.
	1			LEUn_TX is tristated when the transmitter is inactive

19.5.2 LEUARTn_CMD - Command Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset			•					•			•			•	•		•			•					0	0	0	0	0	0	0	0
Access																									×	×	N N	W W	N N	M1	W	W M
Name																									CLEARRX	CLEARTX	RXBLOCKDIS	RXBLOCKEN	TXDIS	TXEN	RXDIS	RXEN

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7	CLEARRX	0	W1	Clear RX
	Set to clear receive	buffer and the R	X shift regis	ster.
6	CLEARTX	0	W1	Clear TX
	Set to clear transmit	buffer and the T	X shift regis	ster.
5	RXBLOCKDIS	0	W1	Receiver Block Disable
	Set to clear RXBLO	CK, resulting in a	III incoming	frames being loaded into the receive buffer.
4	RXBLOCKEN	0	W1	Receiver Block Enable
	Set to set RXBLOCI	K, resulting in all	incoming fr	ames being discarded.
3	TXDIS	0	W1	Transmitter Disable
	Set to disable transr	nission.		
2	TXEN	0	W1	Transmitter Enable
	Set to enable data to	ransmission.		
1	RXDIS	0	W1	Receiver Disable
	Set to disable data r	eception. If a fra	me is unde	reception when the receiver is disabled, the incoming frame is discarded.
0	RXEN	0	W1	Receiver Enable
	Set to activate data	reception on LEU	Jn_RX.	

19.5.3 LEUARTn_STATUS - Status Register

Offset															Bi	t Pc	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	9	8	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	_	0
Reset													ı													_	0	_	0	0	0	0
Access																										œ	<u>~</u>	<u>~</u>	22	<u>~</u>	22	<u>~</u>
Name																										TXIDLE	RXDATAV	TXBL	TXC	RXBLOCK	TXENS	RXENS

Bit	Name	Reset	Access	Description
31:7	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6	TXIDLE	1	R	TX Idle
	Set when TX is id	dle		
5	RXDATAV	0	R	RX Data Valid
	Set when data is	available in the re	eceive buffer.	Cleared when the receive buffer is empty.
4	TXBL	1	R	TX Buffer Level
	Indicates the leve	el of the transmit b	ouffer. Set wh	en the transmit buffer is empty, and cleared when it is full.
3	TXC	0	R	TX Complete
	Set when a trans sion starts.	mission has comp	oleted and no	more data is available in the transmit buffer. Cleared when a new transmis-
2	RXBLOCK	0	R	Block Incoming Data
		ceiver discards inc the frame has be		s. An incoming frame will not be loaded into the receive buffer if this bit is received.
1	TXENS	0	R	Transmitter Enable Status
	Set when the trai	nsmitter is enable	d.	
0	RXENS	0	R	Receiver Enable Status
	Set when the rec dress bit detection		The receiver r	must be enabled for start frames, signal frames, and multi-processor ad-

19.5.4 LEUARTn_CLKDIV - Clock Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	sitio	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•	•	•			•				•		•	•			•	·		•	OVOOVO	2000	•	•	•					•	•
Access																						χ Σ										
Name																						2	2									

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
16:3	DIV	0x0000	RW	Fractional Clock Divider
		16:8] + [7:3]/32)	. To make t	IART. Bits [7:3] are the fractional part and bits [16:8] are the integer part. he math easier the total divider can also be calculated as '([16:8] + [7:0]/
2:0	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-

19.5.5 LEUARTn_STARTFRAME - Start Frame Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Pc	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	8	2	_	0
Reset																												000x0				
Access																												Z ≪				
Name																												STARTFRAME				

Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	STARTFRAME	0x000	RW	Start Frame
		•		cted by the receiver, STARTF interrupt flag is set, and if SFUBRX is set, led into the RX buffer.

19.5.6 LEUARTn_SIGFRAME - Signal Frame Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Pc	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	1	0
Reset					•			,				,				•												000x0				
Access																												ΑW				
Name																												SIGFRAME				

Bit	Name	Reset	Access	Description
31:9	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	SIGFRAME	0x000	RW	Signal Frame
	When a frame match	ing SIGFRAME	is detected	by the receiver, SIGF interrupt flag is set.

19.5.7 LEUARTn_RXDATAX - Receive Buffer Data Extended Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset																	0	0										000×0				
Access																	2	22										2				
Name																	FERR	PERR										RXDATA				

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cortions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15	FERR	0	R	Receive Data Framing Error
	Set if data in buffer ha	as a framing erro	or. Can be	the result of a break condition.
14	PERR	0	R	Receive Data Parity Error
	Set if data in buffer ha	as a parity error.		
13:9	Reserved	To ensure cortions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	RXDATA	0x000	R	RX Data
	Use this register to ac	ccess data read	from the LI	EUART. Buffer is cleared on read access.

19.5.8 LEUARTn_RXDATA - Receive Buffer Data Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	ω	7	9	2	4	က	2	_	0
Reset		'	1		•				•	ı		1		1				•	'	•	1	•	1					2	noxn			
Access																													צ			
Name																												\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	KXDAIA			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	RXDATA	0x00	R	RX Data
	Use this register to	access data rea	ad from LEU	ART. Buffer is cleared on read access. Only the 8 LSB can be read using

Use this register to access data read from LEUART. Buffer is cleared on read access. Only the 8 LSB can be read using this register.

19.5.9 LEUARTn_RXDATAXP - Receive Buffer Data Extended Peek Register

Offset															Ві	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset		•	•		•									•	•	•	0	0		•								000x0				<u> </u>
Access																																
Name																	FERRP	PERRP										RXDATAP				

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15	FERRP	0	R	Receive Data Framing Error Peek
	Set if data in buffer h	as a framing erro	or. Can be	the result of a break condition.
14	PERRP	0	R	Receive Data Parity Error Peek
	Set if data in buffer h	as a parity error.		
13:9	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
8:0	RXDATAP	0x000	R	RX Data Peek
	Use this register to a	ccess data read	from the L	EUART.

19.5.10 LEUARTn_TXDATAX - Transmit Buffer Data Extended Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset				Bit Pos	ition									
0x024	30 33 24 28 29 29 29 29 24	23 24 25 25 25 25 25 25 25 25 25 25 25 25 25	2 8 5	8 7 9 7	5 4	13	2 2	6 6	8					
Reset				c	0	0			00000					
Access				3	3 3	>			3					
				ŀ	- 5	¥			4					
Name					XDISA	XBRE			XDAT,					
					<u> </u>				<u> </u>					
Bit	Name	Reset A	Access	Description										
31:16	Reserved	To ensure compa tions	atibility w	vith future devid	es, al	lway	s write b	its to 0.	More information in 1.2 Conven-					
15	RXENAT 0 W Enable RX After Transmission Set to enable reception after transmission. Value Description													
	Set to enable reception after transmission. Value Description O The receiver is not enabled after the frame has been transmitted													
	RXENAT 0 W Enable RX After Transmission Set to enable reception after transmission. Value Description The receiver is not enabled after the frame has been transmitted The receiver is enabled (setting RXENS) after the frame has been													
	RXENAT 0 W Enable RX After Transmission Set to enable reception after transmission. Value Description The receiver is not enabled after the frame has been transmitted													
	RXENAT 0 W Enable RX After Transmission Set to enable reception after transmission. Description The receiver is enabled (setting RXENS) after the frame has been transmission.													
14	TXDISAT	0 V	V	Disable TX A	fter T	rans	smission	1						
	Set to disable transm	nitter directly after tr	ansmiss	ion has compe	ed.									
	Value			Description										
	RXENAT 0 W Enable RX After Transmission Set to enable reception after transmission. Value Description The receiver is not enabled after the frame has been transmitted The receiver is enabled (setting RXENS) after the frame has been transmitted TXDISAT 0 W Disable TX After Transmission Set to disable transmitter directly after transmission has competed.													
	1				er is d	isab	led (clea	ring TX	ENS) after the frame has been					
13	TXBREAK	0 V	V	Transmit Dat	a as I	3rea	ık							
	Set to send data as a value of TXDATA.	a break. Recipient w	vill see a	framing error o	r a br	eak	condition	n depen	iding on its configuration and the					
	Value			Description										
	0			The specified	numb	er o	f stop-bit	s are tr	ansmitted					
	1				is ge	enera	ated afte		nsmitted to generate a break. A eak to allow the receiver to de-					
12:9	Reserved	To ensure compa	atibility v	vith future devic	es, ai	lway	s write b	its to 0.	More information in 1.2 Conven-					
8:0	TXDATA	0x000 V	V	TX Data										
	Use this register to w	rite data to the LEU	JART. If	the transmitter	is ena	bled	d, a trans	fer will	be initiated at the first opportunity.					

19.5.11 LEUARTn_TXDATA - Transmit Buffer Data Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•	•	•	•										•	•										•	•	0	noxo			
Access																												}	>			
Name																												\	IADAIA			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	TXDATA	0x00	W	TX Data
	This frame will be add cleared.	led to the transn	nit buffer. (Only 8 LSB can be written using this register. 9th bit and control bits will be

19.5.12 LEUARTn_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	2	_	0
Reset																						0	0	0	0	0	0	0	0	0	_	0
Access																						22	2	œ	22	œ	22	22	22	2	2	~
Name																						SIGF	STARTF	MPAF	FERR	PERR	TXOF	RXUF	RXOF	RXDATAV	TXBL	TXC

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10	SIGF	0	R	Signal Frame Interrupt Flag
	Set when a signa different synchro		d. MPA, STA	RT, and SIGNAL should not be set to match the same frame since they use
9	STARTF	0	R	Start Frame Interrupt Flag
	Set when a start different synchro		. MPA, STAR	T, and SIGNAL should not be set to match the same frame since they use
8	MPAF	0	R	Multi-Processor Address Frame Interrupt Flag
		-processor addres use different sync		tected. MPA, START, and SIGNAL should not be set to match the same
7	FERR	0	R	Framing Error Interrupt Flag
	Set when a frame	e with a framing e	rror is receive	d while RXBLOCK is cleared.
6	PERR	0	R	Parity Error Interrupt Flag
	Set when a frame	e with a parity erro	or is received	while RXBLOCK is cleared.
5	TXOF	0	R	TX Overflow Interrupt Flag
	Set when a write	is done to the tran	nsmit buffer w	hile it is full. The data already in the transmit buffer is preserved.
4	RXUF	0	R	RX Underflow Interrupt Flag
	Set when trying t	to read from the re	ceive buffer v	vhen it is empty.
3	RXOF	0	R	RX Overflow Interrupt Flag
	Set when data is new data.	incoming while th	e receive shif	t register is full. The data previously in shift register is overwritten by the
2	RXDATAV	0	R	RX Data Valid Interrupt Flag
	Set when data be	ecomes available i	in the receive	buffer.
1	TXBL	1	R	TX Buffer Level Interrupt Flag
	Set when space	becomes available	e in the transr	nit buffer for a new frame.
0	TXC	0	R	TX Complete Interrupt Flag
	Set after a transr	mission when both	the TX buffe	r and shift register are empty.

19.5.13 LEUARTn_IFS - Interrupt Flag Set Register

Offset															Ві	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset							•				•									•		0	0	0	0	0	0	0	0			0
Access																						W1	W1	W1	W1	W1	W1	W1	W1			W1
Name																						SIGF	STARTF	MPAF	FERR	PERR	TXOF	RXUF	RXOF			TXC

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10	SIGF	0	W1	Set SIGF Interrupt Flag
	Write 1 to set the	e SIGF interrupt flag	l	
9	STARTF	0	W1	Set STARTF Interrupt Flag
	Write 1 to set the	e STARTF interrupt	flag	
8	MPAF	0	W1	Set MPAF Interrupt Flag
	Write 1 to set the	e MPAF interrupt fla	g	
7	FERR	0	W1	Set FERR Interrupt Flag
	Write 1 to set the	e FERR interrupt fla	g	
6	PERR	0	W1	Set PERR Interrupt Flag
	Write 1 to set the	e PERR interrupt fla	g	
5	TXOF	0	W1	Set TXOF Interrupt Flag
	Write 1 to set the	e TXOF interrupt flag	g	
4	RXUF	0	W1	Set RXUF Interrupt Flag
	Write 1 to set the	e RXUF interrupt fla	g	
3	RXOF	0	W1	Set RXOF Interrupt Flag
	Write 1 to set the	e RXOF interrupt fla	g	
2:1	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	TXC	0	W1	Set TXC Interrupt Flag
	Write 1 to set the	e TXC interrupt flag		

19.5.14	LEUAR	Tn_l	FC ·	- Int	erru	ıpt F	Flag	Cle	ar I	Regi	ster	r																				
Offset														В	it F	Posit	ion															
0x034	30	29	28	27	26	25	24	23	22	21	20	10	5 6	17	6	15	4	<u> </u>	13	12	7	10	တ	ω	7	9	2	4	က	2	_	0
Reset													'									0	0	0	0	0	0	0	0			0
Access																						(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1			(R)W1
Name																						SIGF	STARTF	MPAF	FERR	PERR	TXOF	RXUF	RXOF			TXC
Bit	Name)				Re	set			Ac	ces	s	Des	cri	otic	on																
31:11	Reser	ved				To tio		sure	con	npat	ibilit	y v	vith fu	ıture	e d	evice	S, é	a/w	ays	wr	ite k	its t	o 0.	Мо	re ir	nforn	natio	on ir	1.2	? Co	onve	n-
10	SIGF					0				(R)W1		Cle	ar S	iG	F Int	errı	upt	Fla	ag												
	Write (This t													ns tl	he	value	e of	the	e IF	an	d cl	ears	the	cor	resp	onc	ding	inte	rrup	t fla	ags	
9	STAR	TF				0				(R)W1		Cle	ar S	TA	RTF	Int	erı	rupt	t FI	ag											
	Write (This t													eturi	ns t	the v	alue	e o	f the	e IF	an	d cle	ears	the	cor	resp	ond	ing	inter	rup	ot fla	gs
8	MPAF	-				0				(R)W1		Cle	ar N	/IP	AF In	ter	rup	ot F	lag												
	Write (This													rns	the	valu	e o	f th	ne II	Fa	nd c	lear	s th	e co	rres	pon	ding	j int	erru	pt f	lags	
7	FERR					0				(R)W1		Cle	ar F	ER	R In	teri	rup	t F	lag												
	Write (This t													rns	the	valu	e o	f th	ne II	= aı	nd c	lear	s th	e co	rres	pon	ding	j inte	erru	pt fl	ags	
6	PERR	2				0				(R)W1		Cle	ar P	PER	RR In	teri	rup	t F	lag												
	Write (This t													rns	the	valu	e o	f th	ne II	Fa	nd c	lear	s th	e co	rres	pon	ding	g int	erru	pt f	lags	
5	TXOF					0				(R)W1		Cle	ar T	XC)F In	terr	up	t FI	ag												
	Write (This t													rns	the	valu	e o	f th	ie IF	= aı	nd c	lear	s the	e co	rres	pon	ding	inte	erru	ot fl	ags	
4	RXUF					0				(R)W1		Cle	ar R	RXL	JF In	teri	rup	t F	lag												
	Write (This													rns	the	valu	e o	f th	ne II	= aı	nd c	lear	s th	e co	rres	pon	ding	j inte	erru	pt fl	ags	

RXOF 0 (R)W1 **Clear RXOF Interrupt Flag**

Write 1 to clear the RXOF interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).

2:1 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-0 0 **TXC**

(R)W1 **Clear TXC Interrupt Flag**

Write 1 to clear the TXC interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).

3

19.5.15 LEUARTn_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	3	2	_	0
Reset																						0	0	0	0	0	0	0	0	0	0	0
Access																						₩ W	₩.	₩ W	₩ N	W.	Z.	RW W	₩ W	₩ M	₽	RW
Name																						SIGF	STARTF	MPAF	FERR	PERR	TXOF	RXUF	RXOF	RXDATAV	TXBL	TXC

Bit	Name	Reset	Access	Description
31:11	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
10	SIGF	0	RW	SIGF Interrupt Enable
	Enable/disable the S	SIGF interrupt		
9	STARTF	0	RW	STARTF Interrupt Enable
	Enable/disable the S	STARTF interrupt		
8	MPAF	0	RW	MPAF Interrupt Enable
	Enable/disable the N	/IPAF interrupt		
7	FERR	0	RW	FERR Interrupt Enable
	Enable/disable the F	ERR interrupt		
6	PERR	0	RW	PERR Interrupt Enable
	Enable/disable the F	PERR interrupt		
5	TXOF	0	RW	TXOF Interrupt Enable
	Enable/disable the T	XOF interrupt		
4	RXUF	0	RW	RXUF Interrupt Enable
	Enable/disable the F	RXUF interrupt		
3	RXOF	0	RW	RXOF Interrupt Enable
	Enable/disable the F	RXOF interrupt		
2	RXDATAV	0	RW	RXDATAV Interrupt Enable
	Enable/disable the F	RXDATAV interru	pt	
1	TXBL	0	RW	TXBL Interrupt Enable
	Enable/disable the T	XBL interrupt		
0	TXC	0	RW	TXC Interrupt Enable
	Enable/disable the T	XC interrupt		

19.5.16 LEUARTn_PULSECTRL - Pulse Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset				Bit Position
0x03C	30 29 28 27	26 25 24 23	22 21 20	0 8 C 9 C 9 C 9 C 9 C 9 C 9 C 9 C 9 C 9 C
Reset				0 0 00
Access				A A A A A
Name				PULSEFILT PULSEEN PULSEW
Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
5	PULSEFILT	0	RW	Pulse Filter
	Enable a one-cycle	e pulse filter for	pulse extend	ler
	Value			Description
	0			Filter is disabled. Pulses must be at least 2 cycles long for reliable detection.
	1			Filter is enabled. Pulses must be at least 3 cycles long for reliable detection.
4	PULSEEN	0	RW	Pulse Generator/Extender Enable
	Filter LEUART out	put through puls	se generator	and the LEUART input through the pulse extender.
3:0	PULSEW	0x0	RW	Pulse Width

Configure the pulse width of the pulse generator as a number of 32.768 kHz clock cycles.

19.5.17 LEUARTn_FREEZE - Freeze Register

1

FREEZE

Offset															Bi	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	5	4	က	2	_	0
Reset				•		•		•				•								•	•					•						0
Access																																R W
Name																																REGFREEZE
																																ш.
Bit	Na	ıme					Re	set			Ac	ces	s I	Des	crip	tion																
Bit 31:1		ime eserv	/ed					ens	ure	com								s, al	way	s wr	ite b	oits t	o 0.	Мо	re in	forn	natio	on in	1.2	? Co	nver	
	Re	eserv	/ed	ZE			То	ens	ure	com		bility	/ Wit	th fu	ture		rices				ite b	oits t	o 0.	Мо	re in	forn	natio	on in	1.2	? Co	nver	
31:1	Re RE	eserv EGFI		the			To tion 0 of th	ens ns			npati RW	bility I	/ wit	th fu	ture iste	<i>dev</i>	dat	e Fı	eez	е												7-
31:1	RE Wi	eserv EGFI	REE	the			To tion 0 of th	ens ns e LE			npati RW	bility I	/ wit	th fu	ture iste	r Up	dat	e Fı	eez	е												7-

quency domain as soon as possible.

The LEUART is not updated with the new written value.

19.5.18 LEUARTn_SYNCBUSY - Synchronization Busy Register

Offset															Bi	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	8	7	9	2	4	က	7	_	0
Reset		'			'	•						•	•	•	'								•		0	0	0	0	0	0	0	0
Access																									22	22	22	22	22	~	~	<u>~</u>
Name																									PULSECTRL	TXDATA	TXDATAX	SIGFRAME	STARTFRAME	CLKDIV	CMD	CTRL

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7	PULSECTRL	0	R	PULSECTRL Register Busy
	Set when the value	written to PULSE	CTRL is be	eing synchronized.
6	TXDATA	0	R	TXDATA Register Busy
	Set when the value	written to TXDAT	A is being	synchronized.
5	TXDATAX	0	R	TXDATAX Register Busy
	Set when the value	written to TXDAT	AX is being	g synchronized.
4	SIGFRAME	0	R	SIGFRAME Register Busy
	Set when the value	written to SIGFR	AME is bei	ng synchronized.
3	STARTFRAME	0	R	STARTFRAME Register Busy
	Set when the value	written to START	FRAME is	being synchronized.
2	CLKDIV	0	R	CLKDIV Register Busy
	Set when the value	written to CLKDI	√ is being s	synchronized.
1	CMD	0	R	CMD Register Busy
	Set when the value	written to CMD is	being synd	chronized.
0	CTRL	0	R	CTRL Register Busy
	Set when the value	written to CTRL is	s being syn	nchronized.

19.5.19 LEUARTn_ROUTEPEN - I/O Routing Pin Enable Register

														_																		
Offset															Bi	t Po	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset			•		•	•	•					·			•			•				•		•	•		•				0	0
Access																															₽	RW
Name																															TXPEN	RXPEN
Bit	Na	me					Re	set			Ac	cess	s	Des	crip	tion																
31:2	Re	Reserved To ensure cortions										patibility with future devices, always write bits to 0. More information in 1.2 Conver														n-						
1	TX	PEN	1				0				RW	/	•	TX F	Pin E	Enal	ble															
	WI	nen	set,	the	TX	pin d	of th	e LE	UAI	RT i	s en	able	ed.																			
	Va	lue											ı	Des	cript	ion																_
	0												The LEUn_TX pin is disabled																_			
	1												_	The	LEU	Jn_T	ГΧр	in is	s en	able	d											
0	RX	(PEI	٧				0				RW	/	ı	RX I	Pin I	Ena	ble															
	WI	nen	set,	the	RX	pin (of th	e LE	EUA	RT i	s en	able	ed.																			
	Va	lue											ı	Des	cript	ion																_
	0										Description The LEUn RX pin is disabled																					

The LEUn_RX pin is enabled

1

19.5.20 LEUARTn_ROUTELOC0 - I/O Routing Location Register

Offset	Bit Position																															
0x058	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset							•		•	1		1	•		•	1		'		•	2	0000							0	000		·
Access																					2	Ž							<u> </u>	Ž		
Name																					\ \ \ \								2	NA P		

Bit	Name	Reset	Access	Description
31:14	Reserved	To ensure c	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
13:8	TXLOC	0x00	RW	I/O Location

Decides the location of the LEUART TX pin. See the device data sheet for the mapping between location and physical pins.

Value	Mode	Description
0	LOC0	Location 0
1	LOC1	Location 1
2	LOC2	Location 2
3	LOC3	Location 3
4	LOC4	Location 4
5	LOC5	Location 5
6	LOC6	Location 6
7	LOC7	Location 7
8	LOC8	Location 8
9	LOC9	Location 9
10	LOC10	Location 10
11	LOC11	Location 11
12	LOC12	Location 12
13	LOC13	Location 13
14	LOC14	Location 14
15	LOC15	Location 15
16	LOC16	Location 16
17	LOC17	Location 17
18	LOC18	Location 18
19	LOC19	Location 19
20	LOC20	Location 20
21	LOC21	Location 21
22	LOC22	Location 22
23	LOC23	Location 23

Bit	Name	Reset	Access	Description
Біс			Access	
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31
7:6	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	RXLOC	0x00	RW	I/O Location

Decides the location of the LEUART RX pin. See the device data sheet for the mapping between location and physical pins.

Value	Mode	Description
0	LOC0	Location 0
1	LOC1	Location 1
2	LOC2	Location 2
3	LOC3	Location 3
4	LOC4	Location 4
5	LOC5	Location 5
6	LOC6	Location 6
7	LOC7	Location 7
8	LOC8	Location 8
9	LOC9	Location 9
10	LOC10	Location 10
11	LOC11	Location 11
12	LOC12	Location 12
13	LOC13	Location 13
14	LOC14	Location 14
15	LOC15	Location 15
16	LOC16	Location 16
17	LOC17	Location 17
18	LOC18	Location 18
19	LOC19	Location 19
20	LOC20	Location 20
21	LOC21	Location 21
22	LOC22	Location 22
23	LOC23	Location 23


Bit	Name	Reset	Access	Description
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

19.5.21 LEUARTn_INPUT - LEUART Input Register

Offset														R	it Po	neiti	on.															
		_	~		(6)	10	-	~	C1			_	~	Т	T			~	٥,									T		T		
0x064	30	29	78	27	2	25	24	23	22	2	20	19	2	17	16	15	4	13	12	7	9	တ	∞	7	9	2	4	ď			- c	<u> </u>
Reset																										0				0XO		
Access																									MS				X			
Name																										RXPRS				RXPRSSEL		
Bit	Name					Res	Reset Access Description																									
31:6	Reser	ved				To e		ure	con	npat	bilit _.	y w	ith fu	uture	e de	/ices	s, al	way	'S W	rite l	bits	to 0.	Мо	re ii	nforr	natio	on ii	n 1	.2 C	onv	en-	
5	RXPR	S		PRS RX Enable																												
	When set, the PRS channel selected as input to RX.																															
4	Reserved To ensure compatibility with future devices, always write bits to 0. More information in tions															n 1	.2 C	onv	en-													
3:0	RXPR	SSE	L			0x0	0x0 RW RX PRS Channel Select																									
	Select	PRS	S ch	anne	el as	s inpi	ut to	RΣ	ζ.																							
	Value					Mod	de					Description																				
	0					PRS	SCH	10				PRS Channel 0 selected																				
	1					PRS	SCH	1 1					PRS	S Ch	ann	el 1	sele	ecte	d													
	2					PRS	SCF	12					PR	S Ch	ann	el 2	sele	ecte	d													
	3					PRS	SCH	1 3				PRS Channel 3 selected																				
	4					PRS	SCH	14				PRS Channel 4 selected																				
	5					PRS	SCF	15					PR	S Ch	ann	el 5	sele	ecte	d													
	6					PRS	SCF	H6					PRS	S Ch	ann	el 6	sele	ecte	d													
	7					PRS	SCF	17					PRS	S Ch	ann	el 7	sele	ecte	d													
	8					PRS	SCF	18					PRS	S Ch	ann	el 8	sele	ecte	d													
	9					PRS	SCF	1 9					PR	S Ch	ann	el 9	sele	ecte	d													
	10					PRS	SCF	H10					PRS	S Ch	ann	el 10) se	lect	ed													
	11					PRS	PRSCH11								ann	el 1	1 se	lect	ed													

20. TIMER/WTIMER - Timer/Counter





Quick Facts

What?

The TIMER (Timer/Counter) keeps track of timing and counts events, generates output waveforms, and triggers timed actions in other peripherals.

Why?

Most applications have activities that need to be timed accurately with as little CPU intervention and energy consumption as possible.

How?

The flexible 16/32-bit timer can be configured to provide PWM waveforms with optional dead-time insertion (e.g. motor control) or work as a frequency generator. The timer can also count events and control other peripherals through the PRS, which offloads the CPU and reduces energy consumption.

20.1 Introduction

The general purpose timer has 3 or 4 compare/capture channels for input capture and compare/Pulse-Width Modulation (PWM) output.

The TIMER and WTIMER peripherals are identical except for the timer width. A TIMER is 16-bits wide and a WTIMER is 32-bits wide. Some timers also include a Dead-Time Insertion module suitable for motor control applications.

Refer to the device data sheet to determine the capabilities (capture/compare channel count and DTI) of each timer instance.

20.2 Features

- · 16/32-bit auto reload up/down counter
 - Dedicated 16/32-bit reload register which serves as counter maximum
- 3 or 4 Compare/Capture channels
 - · Individually configurable as either input capture or output compare/PWM
- · Multiple Counter modes
 - · Count up
 - · Count down
 - · Count up/down
 - · Quadrature Decoder
 - · Direction and count from external pins
- · 2x Count Mode
- · Counter control from PRS or external pin
 - Start
 - Stop
 - · Reload and start
- · Inter-Timer connection
 - · Allows 32-bit counter mode
 - · Start/stop synchronization between several timers
- · Input Capture
 - · Period measurement
 - · Pulse width measurement
 - · Two capture registers for each capture channel
 - · Capture on either positive or negative edge
 - · Capture on both edges
 - · Optional digital noise filtering on capture inputs
- · Output Compare
 - · Compare output toggle/pulse on compare match
 - · Immediate update of compare registers
- PWM
 - · Up-count PWM
 - Up/down-count PWM
 - Predictable initial PWM output state (configured by SW)
 - Buffered compare register to ensure glitch-free update of compare values
- Clock sources
 - HFPERCLK_{TIMERn}
 - · 10-bit Prescaler
 - · External pin
 - · Peripheral Reflex System
- · Debug mode
 - · Configurable to either run or stop when processor is stopped (halt/breakpoint)
- Interrupts, PRS output and/or DMA request on:
 - · Underflow
 - · Overflow
 - · Compare/Capture event

- · Dead-Time Insertion Unit
 - · Complementary PWM outputs with programmable dead-time
 - · Dead-time is specified independently for rising and falling edge
 - · 10-bit prescaler
 - · 6-bit time value
 - · Outputs have configurable polarity
 - · Outputs can be set inactive individually by software.
 - · Configurable action on fault
 - · Set outputs inactive
 - · Clear output
 - · Tristate output
 - · Individual fault sources
 - · One or two PRS signals
 - Debugger
 - · Support for automatic restart
 - · Core lockup
 - · Configuration lock

20.3 Functional Description

An overview of the TIMER/WTIMER module is shown in Figure 20.1 TIMER/WTIMER Block Overview on page 651 and it consists of a 16/32 bit up/down counter with 3 Compare/Capture channels connected to pins TIMn_CC0, TIMn_CC1, and TIMn_CC2.




Figure 20.1. TIMER/WTIMER Block Overview

WTIMERs (Wide TIMERs) are 32-bit variants of the TIMER/WTIMER module.

20.3.1 Counter Modes

The timer consists of a counter that can be configured to the following modes:

- 1. Up-count: Counter counts up until it reaches the value in TIMERn TOP, where it is reset to 0 before counting up again.
- 2. Down-count: The counter starts at the value in TIMERn_TOP and counts down. When it reaches 0, it is reloaded with the value in TIMERn_TOP.
- 3. Up/Down-count: The counter starts at 0 and counts up. When it reaches the value in TIMERn_TOP, it counts down until it reaches 0 and starts counting up again.
- 4. Quadrature Decoder: Two input channels where one determines the count direction, while the other pin triggers a clock event.

In addition, to the TIMER/WTIMER modes listed above, the TIMER/WTIMER also supports a 2x Count Mode. In this mode the counter increments/decrements by 2. The 2x Count Mode intended use is to generate 2x PWM frequency when the Compare/Capture channel is put in PWM mode. The 2x Count Mode can be enabled by setting the X2CNT bitfield in the TIMERn_CTRL register.

The counter value can be read or written by software at any time by accessing the CNT field in TIMERn_CNT.

20.3.1.1 Events

Overflow is set when the counter value shifts from TIMERn_TOP to the next value when counting up. In up-count mode and Quadrature Decoder mode the next value is 0. In up/down-count mode, the next value is TIMERn_TOP-1.

Underflow is set when the counter value shifts from 0 to the next value when counting down. In down-count mode and Quadrature Decoder mode, the next value is TIMERn_TOP. In up/down-count mode the next value is 1.

An update event occurs on overflow in up-count mode and on underflow in down-count or up/down count mode. Additionally, an update event also occurs on overflow and underflow in Quadrature Decoder Mode. This event is used to time updates of buffered values.

20.3.1.2 Operation

Figure 20.2 TIMER/WTIMER Hardware Timer/Counter Control on page 653 shows the hardware Timer/Counter control. Software can start or stop the counter by setting the START or STOP bits in TIMERn_CMD. The counter value (CNT in TIMERn_CNT) can always be written by software to any 16/32-bit value.

It is also possible to control the counter through either an external pin or PRS input. This is done through the input logic for the Compare/Capture Channel 0. The Timer/Counter allows individual actions (start, stop, reload) to be taken for rising and falling input edges. This is configured in the RISEA and FALLA fields in TIMERn_CTRL. The reload value is 0 in up-count and up/down-count mode and TOP in down-count mode.

The RUNNING bit in TIMERn_STATUS indicates if the timer is running or not. If the SYNC bit in TIMERn_CTRL is set, the timer is started/stopped/reloaded (external pin or PRS) when any of the other timers are started/stopped/reloaded.

The DIR bit in TIMERn_STATUS indicates the counting direction of the timer at any given time. The counter value can be read or written by software through the CNT field in TIMERn_CNT. In Up/Down-Count mode the count direction will be set to up if the CNT value is written by software.




Figure 20.2. TIMER/WTIMER Hardware Timer/Counter Control

20.3.1.3 Clock Source

The counter can be clocked from several sources, which are all synchronized with the peripheral clock (HFPERCLK). See Figure 20.3 TIMER/WTIMER Clock Selection on page 653.




Figure 20.3. TIMER/WTIMER Clock Selection

20.3.1.4 Peripheral Clock (HFPERCLK)

The peripheral clock (HFPERCLK) can be used as a source with a configurable prescale factor of 2^PRESC, where PRESC is an integer between 0 and 10, which is set in PRESC in TIMERn_CTRL. However, if 2x Count Mode is enabled and the Compare/Capture channels are put in PWM mode, the CC output is updated on both clock edges so prescaling the peripheral clock will produce an incorrect result. The prescaler is stopped and reset when the timer is stopped.

20.3.1.5 Compare/ Capture Channel 1 Input

The timer can also be clocked by positive and/or negative edges on the Compare/Capture channel 1 input. This input can either come from the TIMn_CC1 pin or one of the PRS channels. The input signal must not have a higher frequency than f_{HFPERCLK}/3 when running from a pin input or a PRS input with FILT enabled in TIMERn_CCx_CTRL. When running from PRS without FILT, the frequency can be as high as f_{HFPERCLK}. Note that when clocking the timer from the same pulse that triggers a start (through RISEA/FALLA in TIMERn_CTRL), the starting pulse will not update the Counter Value.

20.3.1.6 Underflow/Overflow From Neighboring Timer

All timers are linked together (see Figure 20.4 TIMER/WTIMER Connections on page 654), allowing timers to count on overflow/ underflow from the lower numbered neighbouring timers to form a 32-bit or 48-bit timer. Note that all timers must be set to same count direction and less significant timer(s) can only be set to count up or down.




Figure 20.4. TIMER/WTIMER Connections

20.3.1.7 One-Shot Mode

By default, the counter counts continuously until it is stopped. If the OSMEN bit is set in the TIMERn_CTRL register, however, the counter is disabled by hardware on the first *update event* (see 20.3.1.1 Events). Note that when the counter is running with CC1 as clock source (0b01 in CLKSEL in TIMERn_CTRL) and OSMEN is set, a CC1 capture event will not take place on the *update event* (CC1 rising edge) that stops the timer.

20.3.1.8 Top Value Buffer

The TIMERn_TOP register can be altered either by writing it directly or by writing to the TIMER_TOPB (buffer) register. When writing to the buffer register the TIMERn_TOPB register will be written to TIMERn_TOP on the next *update event*. Buffering ensures that the TOP value is not set below the actual count value. The TOPBV flag in TIMERn_STATUS indicates whether the TIMERn_TOPB register contains data that has not yet been written to the TIMERn_TOP register (see Figure 20.5 TIMER/WTIMER TOP Value Update Functionality on page 655).

Note: When writing to TIMERn_TOP register directly, the TIMERn_TOPB register value will be invalidated and the TOPBV flag will be cleared. This prevents TIMERn_TOP register from being immediately updated by an existing valid TIMERn_TOPB value during the next *update event*.




Figure 20.5. TIMER/WTIMER TOP Value Update Functionality

20.3.1.9 Quadrature Decoder

Quadrature Decoding mode is used to track motion and determine both rotation direction and position. The Quadrature Decoder uses two input channels that are 90 degrees out of phase (see Figure 20.6 TIMER/WTIMER Quadrature Encoded Inputs on page 656).




Figure 20.6. TIMER/WTIMER Quadrature Encoded Inputs

In the timer these inputs are tapped from the Compare/Capture channel 0 (Channel A) and 1 (Channel B) inputs before edge detection. The Timer/Counter then increments or decrements the counter, based on the phase relation between the two inputs. The Quadrature Decoder Mode supports two channels, but if a third channel (Z-terminal) is available, this can be connected to an external interrupt and trigger a counter reset from the interrupt service routine. By connecting a periodic signal from another timer as input capture on Compare/Capture Channel 2, it is also possible to calculate speed and acceleration.

Note: In Quadrature Decoder mode, overflow and underflow triggers an update event.




Figure 20.7. TIMER/WTIMER Quadrature Decoder Configuration

The Quadrature Decoder can be set in either X2 or X4 mode, which is configured in the QDM bit in TIMERn_CTRL. See Figure 20.7 TIMER/WTIMER Quadrature Decoder Configuration on page 656

20.3.1.10 X2 Decoding Mode

In X2 Decoding mode, the counter increments or decrements on every edge of Channel A, see Table 20.1 TIMER/WTIMER Counter Response in X2 Decoding Mode on page 657 and Figure 20.8 TIMER/WTIMER X2 Decoding Mode on page 657.

Table 20.1. TIMER/WTIMER Counter Response in X2 Decoding Mode

Channel B	Chan	nel A
Cildillei B	Rising	Falling
0	Increment	Decrement
1	Decrement	Increment




Figure 20.8. TIMER/WTIMER X2 Decoding Mode

20.3.1.11 X4 Decoding Mode

In X4 Decoding mode, the counter increments or decrements on every edge of Channel A and Channel B, see Figure 20.9 TIMER/WTIMER X4 Decoding Mode on page 657 and Table 20.2 TIMER/WTIMER Counter Response in X4 Decoding Mode on page 657.

Table 20.2. TIMER/WTIMER Counter Response in X4 Decoding Mode

Opposite Channel	Chan	nnel A	Chan	nnel B
	Rising	Falling	Rising	Falling
Channel A = 0			Decrement	Increment
Channel A = 1			Increment	Decrement
Channel B = 0	Increment	Decrement		
Channel B = 1	Decrement	Increment		




Figure 20.9. TIMER/WTIMER X4 Decoding Mode

20.3.1.12 TIMER/WTIMER Rotational Position

To calculate a position Figure 20.10 TIMER/WTIMER Rotational Position Equation on page 658 can be used.

$$pos^{\circ} = (CNT/X \times N) \times 360^{\circ}$$

Figure 20.10. TIMER/WTIMER Rotational Position Equation

where X =Encoding type and N =Number of pulses per revolution.

20.3.2 Compare/Capture Channels

The timer contains 3 Compare/Capture channels, which can be configured in the following modes:

- 1. Input Capture
- 2. Output Compare
- 3. PWM

20.3.2.1 Input Pin Logic

Each Compare/Capture channel can be configured as an input source for the Capture Unit or as external clock source for the timer (see Figure 20.11 TIMER/WTIMER Input Pin Logic on page 658). Compare/Capture channels 0 and 1 are the inputs for the Quadrature Decoder Mode. The input channel can be filtered before it is used, which requires the input to remain stable for 5 cycles in a row before the input is propagated to the output.




Figure 20.11. TIMER/WTIMER Input Pin Logic

20.3.2.2 Compare/Capture Registers

The Compare/Capture channel registers are prefixed with TIMERn_CCx_, where the x stands for the channel number. Since the Compare/Capture channels serve three functions (input capture, compare, PWM), the behavior of the Compare/Capture registers (TIMERn_CCx_CCV) and buffer registers (TIMERn_CCx_CCVB) change depending on the mode the channel is set in.

20.3.2.3 Input Capture

In Input Capture Mode, the counter value (TIMERn_CNT) can be captured in the Compare/Capture Register (TIMERn_CCx_CCV) (see Figure 20.12 TIMER/WTIMER Input Capture on page 659). The CCPOL bits in TIMERn_STATUS indicate the polarity of the edge that triggered the capture in TIMERn CCx CCV.




Figure 20.12. TIMER/WTIMER Input Capture

The Compare/Capture Buffer Register (TIMERn_CCx_CCVB) and the TIMERn_CCx_CCV register form double-buffered capture registers allowing two subsequent capture events to take place before a read-out is required. The first capture can always be read from TIMERn_CCx_CCV, and reading this address will load the next capture value into TIMERn_CCx_CCV from TIMERn_CCx_CCVB if it contains valid data. The CC value can be read without altering the FIFO contents by reading TIMERn_CCx_CCVP. TIMERn_CCx_CCVB can also be read without altering the FIFO contents. The ICV flag in TIMERn_STATUS indicates if there is a valid unread capture in TIMERn_CCx_CCV. In this mode, TIMERn_CCx_CCV is read-only.

In the case where a capture is triggered while both TIMERn_CCx_CCV and TIMERn_CCx_CCVB contain unread capture values, the buffer overflow interrupt flag (ICBOF in TIMERn_IF) will be set. On overflow new capture values will overwrite the value in TIMERn_CCx_CCVB and the value of TIMERn_CCx_CCV will remain unchanged. TIMERn_CCx_CCV will always contain the oldest unread value and TIMERn_CCx_CCVB will always contain the newest value.

Note: In input capture mode, the timer will only trigger interrupts when it is running.

20.3.2.4 Period/Pulse-Width Capture

Period and/or pulse-width capture can only be possible with Channel 0 (CC0), because this is the only channel that can start and stop the timer. This can be done by setting the RISEA field in TIMERn_CTRL to Clear&Start, and select the wanted input from either external pin or PRS, see Figure 20.13 TIMER/WTIMER Period and/or Pulse width Capture on page 660. For period capture, the Compare/Capture Channel should then be set to input capture on a rising edge of the same input signal. To capture the width of a high pulse, the Compare/Capture Channel should be set to capture on a falling edge of the input signal. To measure the low pulse-width of a signal, opposite polarities should be chosen.




Figure 20.13. TIMER/WTIMER Period and/or Pulse width Capture

20.3.2.5 Compare

Each Compare/Capture channel contains a comparator which outputs a compare match if the contents of TIMERn_CCx_CCV matches the counter value, see Figure 20.14 TIMER/WTIMER Block Diagram Showing Comparison Functionality on page 661. In compare mode, each compare channel can be configured to either set, clear or toggle the output on an event (compare match, overflow or underflow). The output from each channel is represented as an alternative function on the port it is connected to, which needs to be enabled for the CC outputs to propagate to the pins.




Figure 20.14. TIMER/WTIMER Block Diagram Showing Comparison Functionality

The compare output is delayed by one cycle to allow for full 0% to 100% PWM generation. If occurring in the same cycle, match action will have priority over overflow or underflow action.

The input selected (through PRSSEL, INSEL and FILTSEL in TIMERn_CCx_CTRL) for the CC channel will also be sampled on compare match and the result is found in the CCPOL bits in TIMERn_STATUS. It is also possible to configure the CCPOL to always track the inputs by setting ATI in TIMERn_CTRL.

The COIST bit in TIMERn_CCx_CTRL is the initial state of the compare/PWM output. The COIST bit can also be used as an initial value to the compare outputs on a reload-start when RSSCOIST is set in TIMERn_CTRL. Also the resulting output can be inverted by setting OUTINV in TIMERn_CCx_CTRL. It is recommended to turn off the CC channel before configuring the output state to avoid any pulses on the output. The CC channel can be turned off by setting MODE to OFF in TIMER_CCx_CTRL. The following figure shows the output logic for the TIMER/WTIMER module.




Figure 20.15. TIMER/WTIMER Output Logic

20.3.2.6 Compare Mode Registers

When running in Output Compare or PWM mode, the value in TIMERn_CCx_CCV will be compared against the count value. In Compare mode the output can be configured to toggle, clear or set on compare match, overflow, and underflow through the CMOA, COFOA and CUFOA fields in TIMERn_CCx_CTRL. TIMERn_CCx_CCV can be accessed directly or through the buffer register TIMERn_CCx_CCVB, see Figure 20.16 TIMER/WTIMER Output Compare/PWM Buffer Functionality Detail on page 662. When writing to the buffer register, the value in TIMERn_CCx_CCVB will be written to TIMERn_CCx_CCV on the next *update event*. This functionality ensures glitch free PWM outputs. The CCVBV flag in TIMERn_STATUS indicates whether the TIMERn_CCx_CCVB register contains data that has not yet been written to the TIMERn_CCx_CCV register. Note that when writing 0 to TIMERn_CCx_CCVB in updown count mode the CCV value is updated when the timer counts from 0 to 1. Thus, the compare match for the next period will not happen until the timer reaches 0 again on the way down.




Figure 20.16. TIMER/WTIMER Output Compare/PWM Buffer Functionality Detail

20.3.2.7 Frequency Generation (FRG)

Frequency generation (see Figure 20.17 TIMER/WTIMER Up-count Frequency Generation on page 663) can be achieved in compare mode by:

- · Setting the counter in up-count mode
- · Enabling buffering of the TOP value.
- · Setting the CC channels overflow action to toggle




Figure 20.17. TIMER/WTIMER Up-count Frequency Generation

The output frequency is given by Figure 20.18 TIMER/WTIMER Up-count Frequency Generation Equation on page 663

$$f_{FRG} = f_{HFPERCLK}/(2^{(PRESC + 1)} \times (TOP + 1) \times 2)$$

Figure 20.18. TIMER/WTIMER Up-count Frequency Generation Equation

The figure below provides cycle accurate timing and event generation information for frequency generation.




Figure 20.19. TIMER/WTIMER Up-count Frequency Generation Detail

20.3.2.8 Pulse-Width Modulation (PWM)

In PWM mode, TIMERn_CCx_CCV is buffered to avoid glitches in the output. The settings in the Compare Output Action configuration bits are ignored in PWM mode and PWM generation is only supported for up-count and up/down-count mode.

20.3.2.9 Up-count (Single-slope) PWM

If the counter is set to up-count and the Compare/Capture channel is put in PWM mode, single slope PWM output will be generated (see Figure 20.20 TIMER/WTIMER Up-count PWM Generation on page 664). In up-count mode the PWM period is TOP+1 cycles and the PWM output will be high for a number of cycles equal to TIMERn_CCx_CCV. This means that a constant high output is achieved by setting TIMERn_CCx_CCV to TOP+1 or higher. The PWM resolution (in bits) is then given by Figure 20.21 TIMER/WTIMER Up-count PWM Resolution Equation on page 664.




Figure 20.20. TIMER/WTIMER Up-count PWM Generation

$$R_{PWM_{UD}} = log(TOP+1)/log(2)$$

Figure 20.21. TIMER/WTIMER Up-count PWM Resolution Equation

The PWM frequency is given by Figure 20.22 TIMER/WTIMER Up-count PWM Frequency Equation on page 664:

$$f_{PWM_{UD/down}} = f_{HFPERCLK}/(2^{PRESC} \times (TOP + 1))$$

Figure 20.22. TIMER/WTIMER Up-count PWM Frequency Equation

The high duty cycle is given by Figure 20.23 TIMER/WTIMER Up-count Duty Cycle Equation on page 664

$$DS_{up} = CCVx/(TOP+1)$$

Figure 20.23. TIMER/WTIMER Up-count Duty Cycle Equation

The figure below provides cycle accurate timing and event generation information for up-count mode.




Figure 20.24. TIMER/WTIMER Up-count PWM Generation Detail

20.3.2.10 2x Count Mode (Up-count)

When the timer is set in 2x mode, the TIMER/WTIMER will count up by two. This will in effect make any odd Top value be rounded down to the closest even number. Similarly, any odd CC value will generate a match on the closest lower even value as shown in Figure 20.25 TIMER/WTIMER CC out in 2x mode on page 665




Figure 20.25. TIMER/WTIMER CC out in 2x mode

The PWM resolution is given by Figure 20.26 TIMER/WTIMER 2x PWM Resolution Equation on page 665.

 $R_{PWM_{2xmode}} = log(TOP/2+1)/log(2)$

Figure 20.26. TIMER/WTIMER 2x PWM Resolution Equation

The PWM frequency is given by Figure 20.27 TIMER/WTIMER 2x Mode PWM Frequency Equation (Up-count) on page 665:

 $f_{PWM_{2xmode}} = f_{HFPERCLK} / floor(TOP/2) + 1$

Figure 20.27. TIMER/WTIMER 2x Mode PWM Frequency Equation(Up-count)

The high duty cycle is given by Figure 20.28 TIMER/WTIMER 2x Mode Duty Cycle Equation on page 665

 $DS_{2xmode} = CCVx/((floor(TOP/2)+1)*2)$

Figure 20.28. TIMER/WTIMER 2x Mode Duty Cycle Equation

20.3.2.11 Up/Down-count (Dual-slope) PWM

If the counter is set to up-down count and the Compare/Capture channel is put in PWM mode, dual slope PWM output will be generated by Figure 20.29 TIMER/WTIMER Up/Down-count PWM Generation on page 666. The resolution (in bits) is given by Figure 20.30 TIMER/WTIMER Up/Down-count PWM Resolution Equation on page 666.




Figure 20.29. TIMER/WTIMER Up/Down-count PWM Generation

$$R_{PWM_{up/down}} = log(TOP+1)/log(2)$$

Figure 20.30. TIMER/WTIMER Up/Down-count PWM Resolution Equation

The PWM frequency is given by Figure 20.31 TIMER/WTIMER Up/Down-count PWM Frequency Equation on page 666:

$$f_{PWM_{UD/down}} = f_{HFPERCLK} / (2^{(PRESC+1)} \times TOP))$$

Figure 20.31. TIMER/WTIMER Up/Down-count PWM Frequency Equation

The high duty cycle is given by Figure 20.32 TIMER/WTIMER Up/Down-count Duty Cycle Equation on page 666

$$DS_{up/down} = CCVx/TOP$$

Figure 20.32. TIMER/WTIMER Up/Down-count Duty Cycle Equation

The figure below provides cycle accurate timing and event generation information for up-count mode.




Figure 20.33. TIMER/WTIMER Up/Down-count PWM Generation

20.3.2.12 2x Count Mode (Up/Down-count)

When the timer is set in 2x mode, the TIMER/WTIMER will count up/down by two. This will in effect make any odd Top value be rounded down to the closest even number. Similarly, any odd CC value will generate a match on the closest lower even value as shown in Figure 20.34 TIMER/WTIMER CC out in 2x mode on page 667




Figure 20.34. TIMER/WTIMER CC out in 2x mode

Figure 20.35 TIMER/WTIMER 2x PWM Resolution Equation on page 667.

 $R_{PWM_{2xmode}} = log(TOP/2+1)/log(2)$

Figure 20.35. TIMER/WTIMER 2x PWM Resolution Equation

The PWM frequency is given by Figure 20.36 TIMER/WTIMER 2x Mode PWM Frequency Equation(Up/Down-count) on page 667:

 $f_{PWM_{2ymode}} = f_{HFPERCLK} / (floor(TOP/2)*2)$

Figure 20.36. TIMER/WTIMER 2x Mode PWM Frequency Equation(Up/Down-count)

The high duty cycle is given by two equations based on the CCVx values. Figure 20.37 TIMER/WTIMER 2x Mode Duty Cycle Equation for CCVx = 1 or CCVx = 000 on page 667 and Figure 20.38 TIMER/WTIMER 2x Mode Duty Cycle Equation for all other CCVx = 000 values on page 667

 $DS_{2xmode} = (CCVx*2)/(floor(TOP/2)*4)$

Figure 20.37. TIMER/WTIMER 2x Mode Duty Cycle Equation for CCVx = 1 or CCVx = even

 $DS_{2xmode} = (CCVx*2 - CCVx)/(floor(TOP/2)*4)$

Figure 20.38. TIMER/WTIMER 2x Mode Duty Cycle Equation for all other CCVx = odd values

20.3.2.13 Timer Configuration Lock

To prevent software errors from making changes to the timer configuration, a configuration lock is available similar to DTI configuration Lock. Writing any value but 0xCE80 to LOCKKEY in TIMERn_LOCK results in TIMERn_CTRL, TIMERn_CMD, TIMERn_TOP, TIMERn_CNT, TIMERn_CCx_CTRL and TIMERn_CCx_CCV being locked from writing. To unlock the registers, write 0xCE80 to LOCKKEY in TIMERn_LOCK. The value of TIMERn_LOCK is 1 when the lock is active, and 0 when the registers are unlocked.

20.3.3 Dead-Time Insertion Unit

Some of the timers include a Dead-Time Insertion module suitable for motor control applications. Refer to the device data sheet to check if a timer has this feature. The example settings in this section are for TIMER0, but identical settings can be used for other timers with DTI as well. The Dead-Time Insertion Unit aims to make control of brushless DC (BLDC) motors safer and more efficient by introducing complementary PWM outputs with dead-time insertion and fault handling, see Figure 20.39 TIMER/WTIMER Dead-Time Insertion Unit Overview on page 668.




Figure 20.39. TIMER/WTIMER Dead-Time Insertion Unit Overview

When used for motor control, the PWM outputs TIM0_CC0, TIM0_CC1 and TIM0_CC2 are often connected to the high-side transistors of a triple half-bridge setup (UH, VH and WH), and the complementary outputs connected to the respective low-side transistors (UL, VL, WL shown in Figure 20.40 TIMER/WTIMER Triple Half-Bridge on page 668). Transistors used in such a bridge often do not open/close instantaneously, and using the exact complementary inputs for the high and low side of a half-bridge may result in situations where both gates are open. This can give unnecessary current-draw and short circuit the power supply. The DTI unit provides dead-time insertion to deal with this problem.




Figure 20.40. TIMER/WTIMER Triple Half-Bridge

For each of the 3 compare-match outputs of TIMER0, an additional complementary output is provided by the DTI unit. These outputs, named TIM0_CDTI0, TIM0_CDTI1 and TIM0_CDTI2 are provided to make control of e.g. 3-channel BLDC or permanent magnet AC (PMAC) motors possible using only a single timer, see Figure 20.41 TIMER/WTIMER Overview of Dead-Time Insertion Block for a Single PWM channel on page 669.




Figure 20.41. TIMER/WTIMER Overview of Dead-Time Insertion Block for a Single PWM channel

The DTI unit is enabled by setting DTEN in TIMER0_DTCTRL. In addition to providing the complementary outputs, the DTI unit then also overrides the compare match outputs from the timer.

The DTI unit gives the rising edges of the PWM outputs and the rising edges of the complementary PWM outputs a configurable time delay. By doing this, the DTI unit introduces a dead-time where both the primary and complementary outputs in a pair are inactive as seen in Figure 20.42 TIMER/WTIMER Polarity of Both Signals are Set as Active-High on page 669.




Figure 20.42. TIMER/WTIMER Polarity of Both Signals are Set as Active-High

Dead-time is specified individually for the rising and falling edge of the original PWM. These values are shared across all the three PWM channels of the DTI unit. A single prescaler value is provided for the DTI unit, meaning that both the rising and falling edge dead-times share prescaler value. The prescaler divides the HFPERCLK_{TIMERn} by a configurable factor between 1 and 1024, which is set in the DTPRESC field in TIMERO_DTTIME. The rising and falling edge dead-times are configured in DTRISET and DTFALLT in TIMERO_DTTIME to any number between 1-64 HFPERCLK_{TIMERO} cycles.

The DTAR and DTFATS bits in TIMER0_DTCTRL control the DTI output behavior when the timer stops. By default the DTI block stops when the timer is stopped. Setting the DTAR bit will cause the DTI to output on channel 0 to continue when the timer is stopped. DTAR effects only channel 0. See 20.3.3.2 PRS Channel as a Source for an example of when this can be used. While in this mode the undivided HFPERCLK_TIMER0 (DTPRESC=0) is always used regardless of programmed DTPRESC value in TIMER0_DTTIME. This means that rise and fall dead times are calculated assuming DTPRESC = 0.

When the timer stops DTI outputs are frozen by default, preserving their last state. To allow the outputs to go to a safe state as programmed in the DTFA field of TIMERO_DTFC register and set the DTFATS bitfield in the TIMERO_DTCTRL reg. Note that when DTAR is also set, DTAR has priority over DTFATS for DTI channel 0 output.

The following table shows the DTI output when the timer is halted.

Table 20.3. DTI Output When Timer Halted

DTAR	DTFATS	State
0	0	frozen
0	1	safe
1	0	running
1	1	running

20.3.3.1 Output Polarity

The value of the primary and complementary outputs in a pair will never be set active at the same time by the DTI unit. The polarity of the outputs can be changed if this is required by the application. The active values of the primary and complementary outputs are set by the DTIPOL and DTCINV bits in the TIMERO_DTCTRL register. The DTIPOL bit of this register specifies the base polarity. If DTIPOL =0, then the outputs are active-high, and if DTIPOL = 1 they are active-low. The relative phase of the primary and complementary outputs is not changed by DTIPOL, as the polarity of both outputs is changed, see Figure 20.43 TIMER/WTIMER Output Polarities on page 670.

In some applications, it may be required that the primary outputs are active-high, while the complementary outputs are active-low. This can be accomplished by manipulating the DTCINV bit of the TIMERO_DTCTRL register, which inverts the polarity of the complementary outputs relative to the primary outputs. As an example, DTIPOL = 0 and DTCINV = 0 results in outputs with opposite phase and active-high states. Similarly, DTIPOL = 1 and DTCINV = 1 results in outputs with equal phase and the primary output will be active-high while the complementary will be active-low.




Figure 20.43. TIMER/WTIMER Output Polarities

Output generation on the individual DTI outputs can be disabled by configuring TIMER0_DTOGEN. When output generation on an output is disabled that output will go to and stay in its inactive state.

20.3.3.2 PRS Channel as a Source

A PRS channel can be used as input to the DTI module instead of the PWM output from the timer for DTI channel 0. Setting DTPRSEN in TIMERO_DTCTRL will override the source of the first DTI channel, driving TIMO_CC0 and TIMO_CDTI0, with the value on the PRS channel. The rest of the DTI channels will continue to be driven by the PWM output from the timer. The input PRS channel is chosen by configuring DTPRSSEL in TIMERO_DTCTRL. Note that the timer must be running even when PRS is used as DTI source. However, if it is required to keep the DTI channel 0 running even when the timer is stopped, set DTAR in TIMERO_DTCTRL. When this bit is set, it uses DTPRESC=0 regardless of the value programmed in DTPRESC in TIMERO_DTTIME.

The DTI prescaler, set by DTPRESC in TIMER0_DTTIME determines the accuracy with which the DTI can insert dead-time into a PRS signal. The maximum dead-time error equals 2^{DTPRESC} clock cycles. With zero prescaling, the inserted dead-times are therefore accurate, but they may be inaccurate for larger prescaler settings.

20.3.3.3 Fault Handling

The fault handling system of the DTI unit allows the outputs of the DTI unit to be put in a well-defined state in case of a fault. This hardware fault handling system enables a fast reaction to faults, reducing the possibility of damage to the system.

The fault sources which trigger a fault in the DTI module are determined by the bitfields of TIMER0_DTFC register. Any combination of the available error sources can be selected:

- PRS source 0, determined by DTPRS0FSEL in TIMER0_DTFC
- · PRS source 1, determined by DTPRS1FSEL in TIMER0 DTFC
- Debugger
- · Core Lockup

One or two PRS channels can be used as an error source. When PRS source 0 is selected as an error source, DTPRS0FSEL determines which PRS channel is used for this source. DTPRS1FSEL determines which PRS channel is selected as PRS source 1. Note that for Core Lockup, the LOCKUPRDIS in RMU_CTRL must be set. Otherwise this will generate a full reset of the chip.

20.3.3.4 Action on Fault

When a fault occurs, the bit representing the fault source is set in TIMER0_DTFAULT register, and the outputs from the DTI unit are set to a well-defined state. The following options are available, and can be enabled by configuring DTFACT in TIMER0_DTFC:

- · Set outputs to inactive level
- · Clear outputs
- · Tristate outputs

With the first option enabled, the output state in case of a fault depends on the polarity settings for the individual outputs. An output set to be active high will be set low if a fault is detected, while an output set to be active low will be driven high.

When a fault occurs, the fault source(s) can be read out from TIMERO DTFAULT register.

Additionally a fault action can also be triggered when the timer stops if DTFATS in TIMER0_DTCTRL is set. This allows the DTI output to go to safe state programmed in DTFACT in TIMER0_DTFC when timer stops. When DTAR and DTFATS in TIMER0_DTCTRL are both set, DTI channel 0 keeps running even when the timer stops. This is useful when DTI channel 0 has an input coming from PRS.

20.3.3.5 Exiting Fault State

When a fault is triggered by the PRS system, software intervention is required to re-enable the outputs of the DTI unit. This is done by manually clearing bits in TIMER0_DTFAULT register. If the fault source as determined by checking TIMER0_DEFAULT is the debugger alone, the outputs can be automatically restarted when the debugger exits. To enable automatic restart set DTDAS in TIMER0_DCTRL. When an automatic restart occurs the DTDBGF bit in TIMER0_DTFAULT will be automatically cleared by hardware. If any other bits in the TIMER0_DTFAULT register are set when the hardware clears DTDBGF the DTI module will not exit the fault state.

20.3.3.6 DTI Configuration Lock

To prevent software errors from making changes to the DTI configuration, a configuration lock is available. Writing any value but 0xCE80 to LOCKKEY in TIMER0_DTLOCK results in TIMER0_DTFC, TIMER0_DTCTRL, TIMER0_DTTIME and TIMER0_ROUTE being locked from writing. To unlock the registers, write 0xCE80 to LOCKKEY in TIMER0_DTLOCK. The value of TIMER0_DTLOCK is 1 when the lock is active, and 0 when the registers are unlocked.

20.3.4 Debug Mode

When the CPU is halted in debug mode, the timer can be configured to either continue to run or to be frozen. This is configured in DEBUGRUN in TIMERn CTRL.

20.3.5 Interrupts, DMA and PRS Output

The timer has 3 different types of output events:

- · Counter Underflow
- · Counter Overflow
- Compare match or input capture (one per Compare/Capture channel)

Each of the events has its own interrupt flag. Also, there is one interrupt flag for each Compare/Capture channel which is set on buffer overflow in capture mode. Buffer overflow happens when a new capture pushes an old unread capture out of the TIMERn_CCx_CCV/TIMERn_CCx_CCVB register pair.

If the interrupt flags are set and the corresponding interrupt enable bits in TIMERn_IEN are set high, the timer will send out an interrupt request. Each of the events will also lead to a one HFPERCLK_{TIMERn} cycle high pulse on individual PRS outputs. Setting PRSOCNF to LEVEL in TIMERn_CCx_CTRL will make the compare match PRS output follow the compare match output, instead of outputting one HFPERCLK_{TIMERn} cycle high pulse. Interrupts are cleared by setting the corresponding bit in the TIMERn_IFC register.

Each of the events will also set a DMA request when they occur. The different DMA requests are cleared when certain acknowledge conditions are met, see Table 20.4 TIMER/WTIMER DMA Events on page 672. Events which clear the DMA requests do not clear interrupt flags. Software must still manually clear the interrupt flag if interrupts are in use.

If DMACLRACT is set in TIMERn_CTRL, the DMA request is cleared when the triggered DMA channel is active, without having to access any timer registers. This is useful in cases where a timer event is used to trigger a DMA transfer that does not target the CCV or CCVB register.

Table 20.4. TIMER/WTIMER DMA Events

Event	Acknowledge/Clear
Underflow/Overflow	Read or write to TIMERn_CNT or TIMERn_TOPB
CC 0	Read or write to TIMERn_CC0_CCV or TIMERn_CC0_CCVB
CC 1	Read or write to TIMERn_CC1_CCV or TIMERn_CC1_CCVB
CC 2	Read or write to TIMERn_CC2_CCV or TIMERn_CC2_CCVB

20.3.6 GPIO Input/Output

The TIMn_CCx inputs/outputs and TIM0_CDTIx outputs are accessible as alternate functions through GPIO. Each pin connection can be enabled/disabled separately by setting the corresponding CCxPEN or CDTIxPEN bits in TIMERn_ROUTE. The LOCATION bits in the same register can be used to move all enabled pins to alternate pins. See the device data sheet for the mapping between block locations (LOC0, LOC1, etc.) and actual device pins (PA0, PA1, etc.).

20.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	TIMERn_CTRL	RW	Control Register
0x004	TIMERn_CMD	W1	Command Register
0x008	TIMERn_STATUS	R	Status Register
0x00C	TIMERn_IF	R	Interrupt Flag Register
0x010	TIMERn_IFS	W1	Interrupt Flag Set Register
0x014	TIMERn_IFC	(R)W1	Interrupt Flag Clear Register
0x018	TIMERn_IEN	RW	Interrupt Enable Register
0x01C	TIMERn_TOP	RWH	Counter Top Value Register
0x020	TIMERn_TOPB	RW	Counter Top Value Buffer Register
0x024	TIMERn_CNT	RWH	Counter Value Register
0x02C	TIMERn_LOCK	RWH	TIMER Configuration Lock Register
0x030	TIMERn_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x034	TIMERn_ROUTELOC0	RW	I/O Routing Location Register
0x03C	TIMERn_ROUTELOC2	RW	I/O Routing Location Register
0x060	TIMERn_CC0_CTRL	RW	CC Channel Control Register
0x064	TIMERn_CC0_CCV	RWH(a)	CC Channel Value Register
0x068	TIMERn_CC0_CCVP	R	CC Channel Value Peek Register
0x06C	TIMERn_CC0_CCVB	RWH	CC Channel Buffer Register
	TIMERn_CCx_CTRL	RW	CC Channel Control Register
	TIMERn_CCx_CCV	RWH(a)	CC Channel Value Register
	TIMERn_CCx_CCVP	R	CC Channel Value Peek Register
	TIMERn_CCx_CCVB	RWH	CC Channel Buffer Register
0x090	TIMERn_CC3_CTRL	RW	CC Channel Control Register
0x094	TIMERn_CC3_CCV	RWH(a)	CC Channel Value Register
0x098	TIMERn_CC3_CCVP	R	CC Channel Value Peek Register
0x09C	TIMERn_CC3_CCVB	RWH	CC Channel Buffer Register
0x0A0	TIMERn_DTCTRL	RW	DTI Control Register
0x0A4	TIMERn_DTTIME	RW	DTI Time Control Register
0x0A8	TIMERn_DTFC	RW	DTI Fault Configuration Register
0x0AC	TIMERn_DTOGEN	RW	DTI Output Generation Enable Register
0x0B0	TIMERn_DTFAULT	R	DTI Fault Register
0x0B4	TIMERn_DTFAULTC	W1	DTI Fault Clear Register
0x0B8	TIMERn_DTLOCK	RWH	DTI Configuration Lock Register

20.5 Register Description

20.5.1 T	IMERn_CTRL - Control Register Bit Position																														
Offset															Bi	t Po	siti	on													
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	2	17	16	15	4	13	12	11	10	6	ω	7	9	2	4	က	2	- 0
Reset			0	0		>	2								2	2		0	0		2	8	Š	OXO	0	0	0	0	0		0×0
Access			S N	₩ M		2	2								§	2		₩ M	R		2	2	2	<u>}</u>	S S	₩ M	S S	R ≪	₩ M		RW
Name		RSSCOIST RV ATI RV													CI KOEI	OLNSEL OLNSEL		DISSYNCOUT	X2CNT		Δ I I Δ	\ \ -	r old	Y SICK	DMACLRACT	DEBUGRUN	QDM	OSMEN	SYNC		MODE
Bit	Na	Name Reset Acc										ces	ss Description																		
31:30	Re	serv	/ed				To tion		ure	com	pati	bility	y wi	th fu	iture	dev	vices	s, al	way	s wr	ite b	its t	o 0.	Мо	re in	forn	natio	on in	1.2	? Co	nven-
20	DC	200)IC	-			Λ				DIV	,		Dala	204	Cto.	40	-4- 4	^~~			4	4 1	.:4:.	1 04	-4-					

Bit	Name	Reset	Access	Description
31:30	Reserved	To ensure c	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
29	RSSCOIST	0	RW	Reload-Start Sets Compare Output Initial State
	When set, compa	re output is set to	COIST value	e at Reload-Start event
28	ATI	0	RW	Always Track Inputs
	when set, makes	CCPOL always tra	ack the polar	ity of the inputs
27:24	PRESC	0x0	RW	Prescaler Setting
	These bits select	the prescaling fac	tor.	
	Value	Mode		Description
	0	DIV1		The HFPERCLK is undivided
	1	DIV2		The HFPERCLK is divided by 2
	2	DIV4		The HFPERCLK is divided by 4
	3	DIV8		The HFPERCLK is divided by 8
	4	DIV16		The HFPERCLK is divided by 16
	5	DIV32		The HFPERCLK is divided by 32
	6	DIV64		The HFPERCLK is divided by 64
	7	DIV128		The HFPERCLK is divided by 128
	8	DIV256		The HFPERCLK is divided by 256
	9	DIV512		The HFPERCLK is divided by 512
	10	DIV1024		The HFPERCLK is divided by 1024
23:18	Reserved	To ensure c	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	CLKSEL	0x0	RW	Clock Source Select
	These bits select	the clock source for	or the timer.	
	Value	Mode		Description

Prescaled HFPERCLK

PRESCHFPERCLK

0

Bit	Name	Reset	Access	Description
	1	CC1		Compare/Capture Channel 1 Input
	2	TIMEROUF		Timer is clocked by underflow(down-count) or overflow(up-count) in the lower numbered neighbor Timer
15	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
14	DISSYNCOUT	0	RW	Disable Timer From Start/Stop/Reload Other Synchronized Timers
	When this bit is set	, the Timer does n	ot start/sto	p/reload other timer with SYNC bit set
	Value			Description
	0			Timer can start/stop/reload other timers with SYNC bit set
	1			Timer cannot start/stop/reload other timers with SYNC bit set
13	X2CNT	0	RW	2x Count Mode
	Enable 2x count mo	ode		
12	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11:10	FALLA	0x0	RW	Timer Falling Input Edge Action
	These bits select th	ne action taken in t	he counter	when a falling edge occurs on the input.
	Value	Mode		Description
	0	NONE		No action
	1	START		Start counter without reload
	2	STOP		Stop counter without reload
	3	RELOADSTA	RT	Reload and start counter
9:8	RISEA	0x0	RW	Timer Rising Input Edge Action
	These bits select th	ne action taken in t	he counter	when a rising edge occurs on the input.
	Value	Mode		Description
	0	NONE		No action
	1	START		Start counter without reload
	2	STOP		Stop counter without reload
	3	RELOADSTA	RT	Reload and start counter
7	DMACLRACT	0	RW	DMA Request Clear on Active
	When this bit is set DMA requests to be			ed when the corresponding DMA channel is active. This enables the timer he timer.
6	DEBUGRUN	0	RW	Debug Mode Run Enable
	Set this bit to enabl	le timer to run in d	ebug mode	
	Value			Description
	0			Timer is frozen in debug mode

Bit	Name	Reset	Access	Description
5	QDM	0	RW	Quadrature Decoder Mode Selection
	This bit sets the	mode for the quad	rature decode	er.
	Value	Mode		Description
	0	X2		X2 mode selected
	1	X4		X4 mode selected
4	OSMEN	0	RW	One-shot Mode Enable
	Enable/disable	one shot mode.		
3	SYNC	0	RW	Timer Start/Stop/Reload Synchronization
	When this bit is	set, the Timer is sta	arted/stopped	I/reloaded by start/stop/reload commands in the other timers
	Value			Description
	0			Timer is not started/stopped/reloaded by other timers
	1			Timer is started/stopped/reloaded by other timers
			omnatihility ı	with future devices, always write bits to 0. More information in 1.2 Conven-
2	Reserved	tions	ompationity v	with fature devices, always write bits to 0. More information in 1.2 convert
	Reserved MODE		RW	Timer Mode
	MODE These bits set the	0x0 ne counting mode for	RW or the Timer.	
	MODE These bits set the	0x0 ne counting mode for	RW or the Timer.	Timer Mode Note, when Quadrature Decoder Mode is selected (MODE = 'b11), the
1:0	MODE These bits set the CLKSEL is don't	0x0 ne counting mode for t care. The Timer is	RW or the Timer.	Timer Mode Note, when Quadrature Decoder Mode is selected (MODE = 'b11), the he Decoder Mode clock output.
	MODE These bits set the CLKSEL is don'to Value	0x0 ne counting mode for t care. The Timer is	RW or the Timer.	Timer Mode Note, when Quadrature Decoder Mode is selected (MODE = 'b11), the he Decoder Mode clock output. Description
	MODE These bits set the CLKSEL is don't Value	tions 0x0 ne counting mode for t care. The Timer is Mode UP	RW or the Timer.	Timer Mode Note, when Quadrature Decoder Mode is selected (MODE = 'b11), the he Decoder Mode clock output. Description Up-count mode

20.5.2 TIMERn_CMD - Command Register

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset													•							'						•			'		0	0
Access																															W1	W1
Name																															STOP	START

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
1	STOP	0	W1	Stop Timer
	Set this bit to stop tim	er		
0	START	0	W1	Start Timer
	Set this bit to start tim	er		

20.5.3 TIMERn_STATUS - Status Register

26

25

24

Offset															Ві	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		•	•		0	0	0	0			•		0	0	0	0				•	0	0	0	0				•		0	0	0
Access					2	2	2	2					2	2	2	22					2	2	2	2						2	22	<u>~</u>
Name					CCPOL3	CCPOL2	CCPOL1	CCPOLO					ICV3	ICV2	ICV1	ICV0					CCVBV3	CCVBV2	CCVBV1	CCVBV0						TOPBV	DIR	RUNNING

Bit	Name	Reset	Access	Description
31:28	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
27	CCPOL3	0	R	CC3 Polarity

In Input Capture mode, this bit indicates the polarity of the edge that triggered capture in TIMERn_CC3_CCV. In Compare/PWM mode, this bit indicates the polarity of the selected input to CC channel 3. These bits are cleared when CCMODE is written to 0b00 (Off).

Value	Mode		Description
0	LOWRISE		CC3 polarity low level/rising edge
1	HIGHFALL		CC3 polarity high level/falling edge
CCPOL2	0	R	CC2 Polarity

In Input Capture mode, this bit indicates the polarity of the edge that triggered capture in TIMERn_CC2_CCV. In Compare/PWM mode, this bit indicates the polarity of the selected input to CC channel 2. These bits are cleared when CCMODE is written to 0b00 (Off).

Value	Mode		Description
0	LOWRISI	E	CC2 polarity low level/rising edge
1	HIGHFAL	L	CC2 polarity high level/falling edge
CCPOL1	0	R	CC1 Polarity

In Input Capture mode, this bit indicates the polarity of the edge that triggered capture in TIMERn_CC1_CCV. In Compare/PWM mode, this bit indicates the polarity of the selected input to CC channel 1. These bits are cleared when CCMODE is written to 0b00 (Off).

Value	Mode		Description							
0	LOWRISE		CC1 polarity low level/rising edge							
1	HIGHFALI	L	CC1 polarity high level/falling edge							
CCPOL0	0	R	CC0 Polarity							

In Input Capture mode, this bit indicates the polarity of the edge that triggered capture in TIMERn_CC0_CCV. In Compare/PWM mode, this bit indicates the polarity of the selected input to CC channel 0. These bits are cleared when CCMODE is written to 0b00 (Off).

Value	Mode	Description
0	LOWRISE	CC0 polarity low level/rising edge
1	HIGHFALL	CC0 polarity high level/falling edge

Bit	Name	Reset	Access	Description							
23:20	Reserved	To ensure c	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-							
19	ICV3	0	R	CC3 Input Capture Valid							
	This bit indicates th and are cleared wh			ins a valid capture value. These bits are only used in input capture mode 00 (Off).							
	Value			Description							
	0			TIMERn_CC3_CCV does not contain a valid capture value(FIFO empty)							
	1			TIMERn_CC3_CCV contains a valid capture value(FIFO not empty)							
18	ICV2	0	R	CC2 Input Capture Valid							
	This bit indicates th and are cleared wh			nins a valid capture value. These bits are only used in input capture mode 00 (Off).							
	Value			Description							
	0			TIMERn_CC2_CCV does not contain a valid capture value(FIFO empty)							
	1			TIMERn_CC2_CCV contains a valid capture value(FIFO not empty)							
17	ICV1	0	R	CC1 Input Capture Valid							
	This bit indicates th and are cleared wh			nins a valid capture value. These bits are only used in input capture mode 00 (Off).							
	Value			Description							
	0			TIMERn_CC1_CCV does not contain a valid capture value(FIFO empty)							
	1			TIMERn_CC1_CCV contains a valid capture value(FIFO not empty)							
16	ICV0	0	R	CC0 Input Capture Valid							
	This bit indicates th and are cleared wh			nins a valid capture value. These bits are only used in input capture mode 00 (Off).							
	Value			Description							
	0			TIMERn_CC0_CCV does not contain a valid capture value(FIFO empty)							
	1			TIMERn_CC0_CCV contains a valid capture value(FIFO not empty)							
15:12	Reserved	To ensure c	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-							
11	CCVBV3	0	R	CC3 CCVB Valid							
				3_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to							
	Value			Description							
	0			TIMERn_CC3_CCVB does not contain valid data							
	1			TIMERn_CC3_CCVB contains valid data which will be written to TIMERn_CC3_CCV on the next update event							

Bit	Name	Reset	Access	Description
10	CCVBV2	0	R	CC2 CCVB Valid
				2_CCVB registers contain data which have not been written to noutput compare/PWM mode and are cleared when CCMODE is written to
	Value			Description
	0			TIMERn_CC2_CCVB does not contain valid data
	1			TIMERn_CC2_CCVB contains valid data which will be written to TIMERn_CC2_CCV on the next update event
9	CCVBV1	0	R	CC1 CCVB Valid
				I_CCVB registers contain data which have not been written to noutput compare/PWM mode and are cleared when CCMODE is written to
	Value			Description
	0			TIMERn_CC1_CCVB does not contain valid data
	1			TIMERn_CC1_CCVB contains valid data which will be written to TIMERn_CC1_CCV on the next update event
	CCVBV0	0	R	CC0 CCVB Valid
8	CCVBVU	U		CCO CCVB Vallu
8	This field indic	cates that the	TIMERn_CC0	D_CCVB registers contain data which have not been written to
8	This field indic	cates that the	TIMERn_CC0	D_CCVB registers contain data which have not been written to
8	This field indic TIMERn_CC0_C 0b00 (Off).	cates that the	TIMERn_CC0	O_CCVB registers contain data which have not been written to n output compare/PWM mode and are cleared when CCMODE is written to
8	This field indic TIMERn_CC0_C 0b00 (Off).	cates that the	TIMERn_CC0	O_CCVB registers contain data which have not been written to noutput compare/PWM mode and are cleared when CCMODE is written to Description
7:3	This field indic TIMERn_CC0_C 0b00 (Off).	cates that the CV. These bits a	TIMERn_CC0 re only used in	D_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event
	This field indic TIMERn_CC0_C 0b00 (Off).	cates that the CV. These bits a	TIMERn_CC0 re only used in	D_CCVB registers contain data which have not been written to noutput compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved	To ensure tions 0 at TIMERn_TOPE	TIMERn_CCC re only used in compatibility v	D_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conven-
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates that	To ensure tions 0 at TIMERn_TOPE	TIMERn_CCC re only used in compatibility v	D_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional Contention of the Convention of the C
7:3	This field indic TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates that when TIMERn_T	To ensure tions 0 at TIMERn_TOPE	TIMERn_CCC re only used in compatibility v	Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates the when TIMERn_T Value	To ensure tions 0 at TIMERn_TOPE	TIMERn_CCC re only used in compatibility v	Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB does not which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared Description
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates that when TIMERn_T Value 0	To ensure tions 0 at TIMERn_TOPE	TIMERn_CCC re only used in compatibility v	Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared Description TIMERn_TOPB does not contain valid data TIMERn_TOPB contains valid data which will be written to TIMERn_TOPB contains valid data
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates the when TIMERn_T Value 0 1	To ensure tions 0 at TIMERn_TOPE OP is written.	re only used in compatibility v	D_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to a noutput compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared Description TIMERn_TOPB does not contain valid data TIMERn_TOPB contains valid data which will be written to TIMERn_TOP on the next update event
7:3	This field indict TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates the when TIMERn_T Value 0 1 DIR	To ensure tions 0 at TIMERn_TOPE OP is written.	re only used in compatibility v	D_CCVB registers contain data which have not been written to a output compare/PWM mode and are cleared when CCMODE is written to a noutput compare/PWM mode and are cleared when CCMODE is written to Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared Description TIMERn_TOPB does not contain valid data TIMERn_TOPB contains valid data which will be written to TIMERn_TOP on the next update event
7:3	This field indic TIMERn_CC0_C 0b00 (Off). Value 0 1 Reserved TOPBV This indicates that when TIMERn_T Value 0 1 DIR Indicates count descriptions	To ensure tions O eat TIMERn_TOPE OP is written.	re only used in compatibility v	Description TIMERn_CC0_CCVB does not contain valid data TIMERn_CC0_CCVB contains valid data which will be written to TIMERn_CC0_CCV on the next update event with future devices, always write bits to 0. More information in 1.2 Conventional data that has not been written to TIMERn_TOP. This bit is also cleared Description TIMERn_TOPB does not contain valid data TIMERn_TOPB contains valid data TIMERn_TOPB contains valid data which will be written to TIMERn_TOP on the next update event

Bit	Name	Reset	Access	Description
0	RUNNING	0	R	Running
	Indicates if timer is ru	nning or not.		

20.5.4 TIMERn_IF - Interrupt Flag Register

Offset		Bit Position																														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset				•		•								•	•			•			0	0	0	0	0	0	0	0		0	0	0
Access																					2	22	<u>~</u>	22	22	22	22	22		<u>~</u>	~	<u>~</u>
Name																					ICBOF3	ICBOF2	ICBOF1	ICBOF0	CC3	CC2	CC1	CCO		DIRCHG	UF	OF

Name	Reset	Access	Description
Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
ICBOF3	0	R	CC Channel 3 Input Capture Buffer Overflow Interrupt Flag
This bit indicates that	t a new capture	value has p	oushed an unread value out of TIMERn_CC3_CCVB.
ICBOF2	0	R	CC Channel 2 Input Capture Buffer Overflow Interrupt Flag
This bit indicates that	t a new capture	value has p	oushed an unread value out of TIMERn_CC2_CCVB.
ICBOF1	0	R	CC Channel 1 Input Capture Buffer Overflow Interrupt Flag
This bit indicates that	t a new capture	value has p	oushed an unread value out of TIMERn_CC1_CCVB.
ICBOF0	0	R	CC Channel 0 Input Capture Buffer Overflow Interrupt Flag
This bit indicates tha	t a new capture	value has p	oushed an unread value out of TIMERn_CC0_CCVB.
CC3	0	R	CC Channel 3 Interrupt Flag
This bit indicates that	t there has been	an interrup	ot event on Compare/Capture channel 3.
CC2	0	R	CC Channel 2 Interrupt Flag
This bit indicates that	t there has been	an interrup	ot event on Compare/Capture channel 2.
CC1	0	R	CC Channel 1 Interrupt Flag
This bit indicates that	t there has been	an interrup	ot event on Compare/Capture channel 1.
CC0	0	R	CC Channel 0 Interrupt Flag
This bit indicates that	t there has been	an interrup	ot event on Compare/Capture channel 0.
Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
DIRCHG	0	R	Direction Change Detect Interrupt Flag
This bit is set when o	ount direction ch	nanges. Se	t only in Quadrature Decoder mode
UF	0	R	Underflow Interrupt Flag
This bit indicates that	t there has been	an underfl	ow.
OF	0	R	Overflow Interrupt Flag
This bit indicates that	t there has been	an overflo	w.
	Reserved ICBOF3 This bit indicates that ICBOF2 This bit indicates that ICBOF1 This bit indicates that ICBOF0 This bit indic	Reserved To ensure contions ICBOF3 This bit indicates that a new capture of the continuous contions ICBOF2 This bit indicates that a new capture of the	Reserved To ensure compatibility tions ICBOF3 0 R This bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that a new capture value has placed bit indicates that there has been an interrupt bit indicates that there has been a

20.5.5 TIMERn_IFS - Interrupt Flag Set Register

Offset	Bit Position											
0x010		7	9	8	7	9	2	4	က	7	_	0
Reset		0	0 0	0	0	0	0	0		0	0	0
Access		×	W W	W	W1	W1	W1	W1		W1	W1	W1
Name		ᆼ	ICBOF2	ICBOF0	CC3	CC2	CC1	000		DIRCHG	J.	OF

Bit	Name	Reset	Access	Description							
31:12	Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-							
11	ICBOF3	0	W1	Set ICBOF3 Interrupt Flag							
	Write 1 to set the ICBOF3 interrupt flag										
10	ICBOF2	0	W1	Set ICBOF2 Interrupt Flag							
	Write 1 to set the ICBOF2 interrupt flag										
9	ICBOF1	0	W1	Set ICBOF1 Interrupt Flag							
	Write 1 to set the IC	BOF1 interrupt fla	ag								
8	ICBOF0	0	W1	Set ICBOF0 Interrupt Flag							
	Write 1 to set the IC	BOF0 interrupt fla	ag								
7	CC3	0	W1	Set CC3 Interrupt Flag							
	Write 1 to set the CC3 interrupt flag										
6	CC2	0	W1	Set CC2 Interrupt Flag							
	Write 1 to set the CO	22 interrupt flag									
5	CC1	0	W1	Set CC1 Interrupt Flag							
	Write 1 to set the CO	C1 interrupt flag									
4	CC0	0	W1	Set CC0 Interrupt Flag							
	Write 1 to set the CO	0 interrupt flag									
3	Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-							
2	DIRCHG	0	W1	Set DIRCHG Interrupt Flag							
	Write 1 to set the DI	RCHG interrupt fl	ag								
1	UF	0	W1	Set UF Interrupt Flag							
	Write 1 to set the UF	interrupt flag									
0	OF	0	W1	Set OF Interrupt Flag							
	Write 1 to set the OF	interrupt flag									

20.5.6 T	IMERn	_IF	C - I	nterr	up	t Fla	ag CI	ea	ır R	egi	iste	r																				
Offset															В	it P	ositi	ion														
0x014	31	3 8	23 25	27	90	07	2 2		23	22	21	20	19	18	17	16	15	14	<u> </u>	12	7	10	6	ω	7	9	5	4	က	7	_	_
Reset	'																				0	0	0	0	0	0	0	0		0	0	_
Access																					(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1		(R)W1	(R)W1	(P)W/1
Name																					ICB0F3	ICB0F2	ICB0F1	ICBOF0	CC3	CC2	CC1	000		DIRCHG	UF	OF.
Bit	Nam	е				F	Reset				Ac	ces	s	Des	crip	tio	n															
31:12	Rese	n/o	d			7	o en	su	re c	om	nati	hilit	17.147	ith fo	.4	-1-		_	- 1		rita l	ito i	·	۸.4-		£						
	, 1000	100	-				ons			,011	ipati	DIIIC.	y vv.	ונוו ונ	iture	e ae	vice	S, ĉ	aiwa	ys w	rite	JILS I	00.	IVIO	re in	тоrn	natio	on ir	1.2	? Co	nvei	n-
11	ICBC						ons			.011		W1					OF3						.0 0.	IVIO	re in	ntorn	natio	on ir	1.2	? Co	nvei	n-
11)F3	o cle			0 CBC	ons OF3 ir	nte	erru	pt f	(R)	W1 Rea	adin	Cle	ar IC	ВС)F3	Inte	erru	pt F	ag											
11	ICBC Write	F3 1 t	o cle			0 CBC	OF3 ir	nte	erru	pt f	(R) lag.	W1 Rea	adin	Cle	ar IC	BC s th)F3	Inte	erru of t	pt F l	ag											
	ICBC Write (This)F3 1 t fea)F2	o cle ture	mus ear th	t be	CBC	OF3 ir abled	nte d g	erru _l lob	pt fl ally	(R) lag. in M (R)	W1 Rea MSC W1 Rea	adin C.).	Cle	ar IC turn ar IC	s th	DF3 le va	lue	erru of t	pt Fi	ag and ag	l cle	ars	the	corr	espo	ondi	ng i	nteri	rupt	flag	s
	ICBC Write (This	F3 fea F2 1 t fea	o cle ture	mus ear th	t be	CBC	OF3 ir abled	nte d g	erru _l lob	pt fl ally	(R) lag. r in M (R) lag.	W1 Rea MSC W1 Rea	adin C.). adin C.).	Cle g re Cle	ar IC turn ar IC	s th	DF3 le va	Inte	erru of t erru of t	pt FI	ag and ag	l cle	ars	the	corr	espo	ondi	ng i	nteri	rupt	flag	s
10	ICBC Write (This	DF3 1 t fea DF2 1 t fea DF1	o cle	ear th mus	e lo	00 CBC CBC CBC CCBC CCBC	OF3 ir abled OF2 ir abled	nte d g	erru lob erru	pt fl ally pt fl ally	(R) lag. (R) (R) lag. (In M) (R) (R)	W1 Rea W1 Rea MSC W1 Rea	adin C.). adin C.).	Cleang re	ar IC turn ar IC turn	BC BC BC	DF3 e va DF2 e va	Inte	erru of t erru of t	pt Fi	ag ag ag ag	l cle	ars	the o	corre	espo	ondi	ng i	nteri	rupt	flag	s s

		he ICBOF3 interro st be enabled glo		ing returns the value of the IF and clears the corresponding interrupt flags
10	ICBOF2	0	(R)W1	Clear ICBOF2 Interrupt Flag
		he ICBOF2 interro st be enabled glo		ing returns the value of the IF and clears the corresponding interrupt flags .
9	ICBOF1	0	(R)W1	Clear ICBOF1 Interrupt Flag
		he ICBOF1 interro st be enabled glo		ing returns the value of the IF and clears the corresponding interrupt flags .
8	ICBOF0	0	(R)W1	Clear ICBOF0 Interrupt Flag
		he ICBOF0 interro st be enabled glo		ing returns the value of the IF and clears the corresponding interrupt flags .
7	CC3	0	(R)W1	Clear CC3 Interrupt Flag
		he CC3 interrupt i enabled globally i		returns the value of the IF and clears the corresponding interrupt flags (This
6	CC2	0	(R)W1	Clear CC2 Interrupt Flag
		he CC2 interrupt i enabled globally i		returns the value of the IF and clears the corresponding interrupt flags (This
5	CC1	0	(R)W1	Clear CC1 Interrupt Flag
		he CC1 interrupt tenabled globally i		returns the value of the IF and clears the corresponding interrupt flags (This
4	CC0	0	(R)W1	Clear CC0 Interrupt Flag
		he CC0 interrupt tenabled globally i		returns the value of the IF and clears the corresponding interrupt flags (This
3	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2	DIRCHG	0	(R)W1	Clear DIRCHG Interrupt Flag
		he DIRCHG interi st be enabled glo		ding returns the value of the IF and clears the corresponding interrupt flags).

Bit	Name	Reset	Access	Description								
1	UF	0	(R)W1	Clear UF Interrupt Flag								
		r the UF interrupt flag e enabled globally in	•	turns the value of the IF and clears the corresponding interrupt flags (This								
0	OF	0	(R)W1	Clear OF Interrupt Flag								
	Write 1 to clear the OF interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.).											

20.5.7 TIMERn_IEN - Interrupt Enable Register

Offset															Ві	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset							•				•		•	•							0	0	0	0	0	0	0	0		0	0	0
Access																					R≷	₽	R	₽	RW	₽	₽	₽		R	₽	RW
Name																					ICBOF3	ICBOF2	ICBOF1	ICBOF0	CC3	CC2	CC1	000		DIRCHG	UF	OF

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	ICBOF3	0	RW	ICBOF3 Interrupt Enable
	Enable/disable the IC	BOF3 interrupt		
10	ICBOF2	0	RW	ICBOF2 Interrupt Enable
	Enable/disable the IC	BOF2 interrupt		
9	ICBOF1	0	RW	ICBOF1 Interrupt Enable
	Enable/disable the IC	BOF1 interrupt		
8	ICBOF0	0	RW	ICBOF0 Interrupt Enable
	Enable/disable the IC	BOF0 interrupt		
7	CC3	0	RW	CC3 Interrupt Enable
	Enable/disable the C	C3 interrupt		
6	CC2	0	RW	CC2 Interrupt Enable
	Enable/disable the C	C2 interrupt		
5	CC1	0	RW	CC1 Interrupt Enable
	Enable/disable the C	C1 interrupt		
4	CC0	0	RW	CC0 Interrupt Enable
	Enable/disable the C	C0 interrupt		
3	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	DIRCHG	0	RW	DIRCHG Interrupt Enable
	Enable/disable the D	IRCHG interrupt		
1	UF	0	RW	UF Interrupt Enable
	Enable/disable the U	F interrupt		
0	OF	0	RW	OF Interrupt Enable
	Enable/disable the O	F interrupt		

20.5.8 TIMERn_TOP - Counter Top Value Register

Offset	Bit Position												
0x01C	33 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3												
Reset	00000FFF												
Access	RW H												
Name	TOP												

Bit	Name	Reset	Access	Description							
31:0	TOP	0x0000FFFF	RWH	Counter Top Value							
These bits hold the TOP value for the counter.											

20.5.9 TIMERn_TOPB - Counter Top Value Buffer Register

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		0000000XO																														
Access																2	<u>}</u>															
Name																	<u> </u>															

Bit	Name	Reset	Access	Description
31:0	ТОРВ	0x00000000	RW	Counter Top Value Buffer
	These bits hold the TO	OP buffer value.		

20.5.10 TIMERn_CNT - Counter Value Register

Offset											Bit	Pos	tion														
0x024	33	29	27	26	25	23	22	20	19	18	17	6 4	5 4	<u> </u>	5 5	1 =	10	စ	∞	7	9	2	4	က	2	_	0
Reset							·					00000000x0		·													
Access		χ Ή																									
Name												CNT															
Bit	Name				Reset		A	cces	ss	Des	cript	ion															
31:0	CNT				0x000	0000	0 F	RWH		Cou	nter	Valu	е														
	These bits hold the counter value.																										

20.5.11 TIMERn_LOCK - TIMER Configuration Lock Register

Offset															Bit	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	_	0
Reset																									nnnnxn							
Access																								2	I X Y							
Name																									IIMER CONFEY							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	TIMERLOCKKEY	0x0000	RWH	Timer Lock Kev

Write any other value than the unlock code to lock TIMERn_CTRL, TIMERn_CMD, TIMERn_TOP, TIMERn_CNT, TIMERn_CCx_CTRL and TIMERn_CCx_CCV from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Read Operation UNLOCKED 0 LOCKED 1	TIMER registers are unlocked
	•
LOCKED 1	TIMED registers are leaked
	TIMER registers are locked
Write Operation	
LOCK 0	Lock TIMER registers
UNLOCK 0xCE80	Unlock TIMER registers

20.5.12 TIMERn_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Bi	t Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	2	_	0
Reset																						0	0	0					0	0	0	0
Access																						W.	ΑM	₽					₽	RW	S.	Z.
Name																						CDTI2PEN	CDT11PEN	CDTIOPEN					CC3PEN	CC2PEN	CC1PEN	CCOPEN

Bit	Name	Reset	Access	Description										
31:11	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-										
10	CDTI2PEN	0	RW	CC Channel 2 Complementary Dead-Time Insertion Pin Enable										
	Enable/disable CC ch	nannel 2 comple	mentary de	ead-time insertion output connection to pin.										
9	CDTI1PEN	0	RW	CC Channel 1 Complementary Dead-Time Insertion Pin Enable										
	Enable/disable CC ch	nannel 1 comple	mentary de	ead-time insertion output connection to pin.										
8	CDTI0PEN	0	RW	CC Channel 0 Complementary Dead-Time Insertion Pin Enable										
	Enable/disable CC channel 0 complementary dead-time insertion output connection to pin.													
7:4	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions												
3	CC3PEN	0	RW	CC Channel 3 Pin Enable										
	Enable/disable CC ch	nannel 3 output/i	nput conne	ection to pin.										
2	CC2PEN	0	RW	CC Channel 2 Pin Enable										
	Enable/disable CC ch	nannel 2 output/i	nput conne	ection to pin.										
1	CC1PEN	0	RW	CC Channel 1 Pin Enable										
	Enable/disable CC ch	nannel 1 output/i	nput conne	ection to pin.										
0	CC0PEN	0	RW	CC Channel 0 Pin Enable										
	Enable/disable CC Cl	hannel 0 output/	input conn	ection to pin.										

20.5.13 TIMERn_ROUTELOC0 - I/O Routing Location Register

Offset															Ві	t Po	sitio	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	7	_	0
Reset					0	nxn								nxn		•					2	noxn	•			•			OxO			
Access					<u> </u>	<u>}</u>							2	<u>}</u>							Š	≥ Y							S N			
Name					701877	CCSEOC							(CCZEOC							7	CCIFOC							201023)		

Name		ссзго				CC2LO		CC1LO		CCOLO
Bit	Name		Reset		Access	Description				
31:30	Reserv	red	To ensu	re con	npatibility v	vith future dev	rices, al	ways write bits to 0. Mo	re inforn	nation in 1.2 Conven-
29:24	CC3LC	C	0x00		RW	I/O Location	n			
	Decide	s the location o	of the CC3	pin.						
	Value		Mode			Description				
	0		LOC0			Location 0				
	1		LOC1			Location 1				
	2		LOC2			Location 2				
	3		LOC3			Location 3				
	4		LOC4			Location 4				
	5		LOC5			Location 5				
	6		LOC6			Location 6				
	7		LOC7			Location 7				
	8		LOC8			Location 8				
	9		LOC9			Location 9				
	10		LOC10			Location 10				
	11		LOC11			Location 11				
	12		LOC12			Location 12				
	13		LOC13			Location 13				
	14		LOC14			Location 14				
	15		LOC15			Location 15				
	16		LOC16			Location 16				
	17		LOC17			Location 17				
	18		LOC18			Location 18				
	19		LOC19			Location 19				
	20		LOC20			Location 20				
	21		LOC21			Location 21				
	22		LOC22			Location 22				

Bit	Name	Reset Acces	s Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
23:22	Reserved	To ensure compatibility	y with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	CC2LOC	0x00 RW	I/O Location
	Decides the location	on of the CC2 pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

Bit	Name	Reset Acces	ss Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
15:14	Reserved	To ensure compatibili	ity with future devices, always write bits to 0. More information in 1.2 Conven-
13:8	CC1LOC	0x00 RW	I/O Location
	Decides the locatio	n of the CC1 pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

Bit	Name	Reset Acce	ess Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
7:6	Reserved	To ensure compatibi	lity with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	CC0LOC	0x00 RW	I/O Location
	Decides the location	on of the CC0 pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

t	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

20.5.14 TIMERn_ROUTELOC2 - I/O Routing Location Register

Offset												Bit Position																				
0x03C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset		•	•			•	•		•	•			0	0000				•		•	Ç	OOXO	•			•		•	000	000		
Access													2	<u>}</u>							Š	<u>}</u>							<u> </u>	Ž		
Name													COLCITION	CDIELOC							H	CDIIICOC								CD INC		

Bit	Name	Reset	Access	Description
31:22	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	CDTI2LOC	0x00	RW	I/O Location

Decides the location of the CDTI2 pin.

Value	Mode	Description
0	LOC0	Location 0
1	LOC1	Location 1
2	LOC2	Location 2
3	LOC3	Location 3
4	LOC4	Location 4
5	LOC5	Location 5
6	LOC6	Location 6
7	LOC7	Location 7
8	LOC8	Location 8
9	LOC9	Location 9
10	LOC10	Location 10
11	LOC11	Location 11
12	LOC12	Location 12
13	LOC13	Location 13
14	LOC14	Location 14
15	LOC15	Location 15
16	LOC16	Location 16
17	LOC17	Location 17
18	LOC18	Location 18
19	LOC19	Location 19
20	LOC20	Location 20
21	LOC21	Location 21
22	LOC22	Location 22

Bit	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31
15:14	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13:8	CDTI1LOC	0x00	RW	I/O Location
	Decides the loca	ation of the CDTI1 pi	n.	
	Value	Mode		Description
	0	LOC0		Location 0
	1	LOC1		Location 1
	2	LOC2		Location 2
	3	LOC3		Location 3
	4	LOC4		Location 4
	5	LOC5		Location 5
	6	LOC6		Location 6
	7	LOC7		Location 7
	8	LOC8		Location 8
	9	LOC9		Location 9
	10	LOC10		Location 10
	11	LOC11		Location 11
	12	LOC12		Location 12
	13	LOC13		Location 13
	14	LOC14		Location 14
	15	LOC15		Location 15
	16	LOC16		Location 16
	17	LOC17		Location 17
	18	LOC18		Location 18
	19	LOC19		Location 19
	20	LOC20		Location 20
	21	LOC21		Location 21
	22	LOC22		Location 22

Bit	Name	Reset Acces	s Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
7:6	Reserved	To ensure compatibilit	ty with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	CDTI0LOC	0x00 RW	I/O Location
	Decides the locati	on of the CDTI0 pin.	
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

t	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

20.5.15 TIMERn_CCx_CTRL - CC Channel Control Register

Offset															Bi	t Po	sitio	on														
0x060	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset		0	0	0	2	2	Ş	Š						>	2				2	3	0^0	3	2	3			•	0		0	ÖXO	?
Access		W.	₩ M	W.	2	Ž	Š	<u>}</u>						<u> </u>	Ž				2	Ž	/\/\	2	<u> </u>	2				RW		₩.	N N	:
Name		FILT	INSEL	PRSCONF	ICEVICTE	- >		ICEUGE						DDCCE	TROOF				V C II		COECOA		VON O					COIST		OUTINV	MODE	I))
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																

	<u> </u>		PR		2	8	Ö		8	8	W				
Name	Reset	Access	Description												
Reserved	To ensure contions	npatibility v	vith future dev	vices, alw	ays wri	te bits to	0. Mo	re informa	tion in 1.	2 Con	ven-				
FILT	0	RW	Digital Filte	r											
Enable digital filter.															
Value	Mode		Description												
0	DISABLE		Digital filter	disabled											
1	ENABLE		Digital filter	enabled											
INSEL	0	RW	Input Selection												
Select Compare/Capto	ure channel inpu	ıt.	/ Input Selection												
Value	Mode		Description												
0	PIN		TIMERnCC	c pin is se	elected										
1	PRS		PRS input (s	selected b	y PRS	SEL) is	selecte	ed							
PRSCONF	0	RW	PRS Config	uration											
Select PRS pulse or le	evel.														
Value	Mode		Description												
0	PULSE		Each CC ev	ent will ge	enerate	a one l	IFPER	CLK cycle	high pul	se					
1	LEVEL		The PRS ch	annel will	follow	CC out									
ICEVCTRL	0x0	RW	Input Captu	ıre Event	Contr	ol									
These bits control who every capture.	en a Compare/C	apture PR	S output pulse	e and inte	errupt fl	ag is se	t. DMA	request ho	owever is	s set o	n				
Value	Mode		Description												
0	EVERYEDGE		PRS output	pulse and	d interru	upt flag	set on e	every captu	ure						
1	EVERYSECO	NDEDGE	PRS output	pulse and	d interru	upt flag s	set on e	every seco	nd captu	ıre					
2	RISING		PRS output = BOTH)	pulse and	d interru	upt flag s	set on r	rising edge	only (if	ICEDO	3E				
3	FALLING		PRS output = BOTH)	pulse and	d interru	upt flag s	set on f	falling edge	e only (if	ICED	GE ——				
	Reserved FILT Enable digital filter. Value 0 1 INSEL Select Compare/Capte Value 0 1 PRSCONF Select PRS pulse or le Value 0 1 ICEVCTRL These bits control wheevery capture. Value 0 1 2	Name Reset Reserved To ensure contions FILT 0 Enable digital filter. Value Mode 0 DISABLE 1 ENABLE INSEL 0 Select Compare/Capture channel input Value Mode 0 PIN 1 PRS PRSCONF 0 Select PRS pulse or level. Value Mode 0 PULSE 1 LEVEL ICEVCTRL 0x0 These bits control when a Compare/Cevery capture. Value Mode 0 EVERYEDGE 1 EVERYSECOI 2 RISING	Name Reset Access Reserved To ensure compatibility vitions FILT 0 RW Enable digital filter. Value Mode 0 DISABLE 1 ENABLE INSEL 0 RW Select Compare/Capture channel input. Value Mode 0 PIN 1 PRS PRSCONF 0 RW Select PRS pulse or level. Value Mode 0 PULSE 1 LEVEL ICEVCTRL 0x0 RW These bits control when a Compare/Capture PRevery capture. Value Mode 0 EVERYEDGE 1 EVERYSECONDEDGE 1 EVERYSECONDEDGE 2 RISING	Name Reset Access Description Reserved To ensure compatibility with future devitions FILT 0 RW Digital Filter Enable digital filter. Value Mode Description 0 DISABLE Digital filter of Di	Name Reset Access Description Reserved To ensure compatibility with future devices, alwations FILT 0 RW Digital Filter Enable digital filter. Description Value Mode Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Description Description 0 PIN TIMERNCCx pin is set 1 PRS PRS input (selected to the property of the	Name Reset Access Description Reserved To ensure compatibility with future devices, always writions FILT 0 RW Digital Filter Enable digital filter. Digital Filter Value Mode Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Value Mode Description 0 PIN TIMERnCCx pin is selected 1 PRS PRS input (selected by PRS PRSCONF 0 RW PRS Configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate the properties of the	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to tions FILT 0 RW Digital Filter Enable digital filter. Digital Filter Value Mode Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Value Mode Description 0 PIN TIMERNCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is PRSCONF 0 RW PRS Configuration Select PRS pulse or level. Description Value Mode Description 0 PULSE Each CC event will generate a one in the PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set every capture. Value Mode Description 0<	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. Moditions FILT 0 RW Digital Filter Enable digital filter. Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Value Mode Description 0 PIN TIMERNCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is selected PRSCONF 0 RW PRS Configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate a one HFPER 1 LEVEL The PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set. DMA every capture. Value Mode Description 0 EVERYEDGE <t< td=""><td>Name Roset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More informations FILT 0 RW Digital Filter Enable digital filter. Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Value Mode Description 0 PIN TIMERnCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is selected PRSCONF 0 RW PRS configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate a one HFPERCLK cycle 1 LEVEL The PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set. DMA request he every capture. Value Mode Description <</td><td>Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1. tions FILT 0 RW Digital Filter Enable digital filter. Digital Filter Value Mode Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Description Description 0 PIN TIMERNCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is selected PRSCONF 0 RW PRS Configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate a one HFPERCLK cycle high put 1 LEVEL The PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set. DMA request however in every capture.</td><td>Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions FILT 0 RW Digital Filter Enable digital filter. Displace of the properties of the properti</td></t<>	Name Roset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More informations FILT 0 RW Digital Filter Enable digital filter. Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Value Mode Description 0 PIN TIMERnCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is selected PRSCONF 0 RW PRS configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate a one HFPERCLK cycle 1 LEVEL The PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set. DMA request he every capture. Value Mode Description <	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1. tions FILT 0 RW Digital Filter Enable digital filter. Digital Filter Value Mode Description 0 DISABLE Digital filter disabled 1 ENABLE Digital filter enabled INSEL 0 RW Input Selection Select Compare/Capture channel input. Description Description 0 PIN TIMERNCCx pin is selected 1 PRS PRS input (selected by PRSSEL) is selected PRSCONF 0 RW PRS Configuration Select PRS pulse or level. Value Mode Description 0 PULSE Each CC event will generate a one HFPERCLK cycle high put 1 LEVEL The PRS channel will follow CC out ICEVCTRL 0x0 RW Input Capture Event Control These bits control when a Compare/Capture PRS output pulse and interrupt flag is set. DMA request however in every capture.	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions FILT 0 RW Digital Filter Enable digital filter. Displace of the properties of the properti				

Bit	Name	Reset	Access	Description
25:24	ICEDGE	0x0	RW	Input Capture Edge Select
	These bits contro	ol which edges the e	dge detecto	or triggers on. The output is used for input capture and external clock input.
	Value	Mode		Description
	0	RISING		Rising edges detected
	1	FALLING		Falling edges detected
	2	вотн		Both edges detected
	3	NONE		No edge detection, signal is left as it is
23:20	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
19:16	PRSSEL	0x0	RW	Compare/Capture Channel PRS Input Channel Selection
	Select PRS inpu	t channel for Compa	re/Capture	channel.
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
15:14	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
13:12	CUFOA	0x0	RW	Counter Underflow Output Action
	Select output ac	tion on counter unde	erflow.	
	Value	Mode		Description
	0	NONE		No action on counter underflow
	1	TOGGLE		Toggle output on counter underflow
	2	CLEAR		Clear output on counter underflow
	3	SET		Set output on counter underflow
11:10	COFOA	0x0	RW	Counter Overflow Output Action
	Select output ac	tion on counter over	flow.	
	Value	Mode		Description

Bit	Name	Reset	Access	Description
	0	NONE		No action on counter overflow
	1	TOGGLE		Toggle output on counter overflow
	2	CLEAR		Clear output on counter overflow
	3	SET		Set output on counter overflow
9:8	CMOA	0x0	RW	Compare Match Output Action
	Select output act	tion on compare match	h.	
	Value	Mode		Description
	0	NONE		No action on compare match
	1	TOGGLE		Toggle output on compare match
	2	CLEAR		Clear output on compare match
	3	SET		Set output on compare match
7:5	Reserved	To ensure com tions	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
7:5	Reserved		RW	vith future devices, always write bits to 0. More information in 1.2 Conven- Compare Output Initial State
	COIST This bit is only us high when the co	0 sed in Output Compar	RW re and PW en countir	Compare Output Initial State //M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit
	COIST This bit is only us high when the co	tions 0 sed in Output Comparbunter is disabled. Who	RW re and PW en countir hen the co	Compare Output Initial State /M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit
4	COIST This bit is only us high when the cois cleared, the ou	tions 0 sed in Output Comparbunter is disabled. Who atput will be cleared will to ensure com	RW re and PW en countir hen the co	Compare Output Initial State //M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled.
3	COIST This bit is only us high when the cois cleared, the out reserved OUTINV	tions 0 sed in Output Compare ounter is disabled. Who atput will be cleared with the compare compare of the co	RW re and PW en countir hen the co	Compare Output Initial State //M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. // with future devices, always write bits to 0. More information in 1.2 Conven-
3	COIST This bit is only us high when the cois cleared, the out reserved OUTINV	tions 0 sed in Output Compare ounter is disabled. Who atput will be cleared with the compare compare of the co	RW re and PW en countir hen the co	Compare Output Initial State VM mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. Vith future devices, always write bits to 0. More information in 1.2 Conventional Control Control Output Invert
3 2	COIST This bit is only us high when the cois cleared, the out Reserved OUTINV Setting this bit in MODE	tions 0 sed in Output Compare ounter is disabled. Wheatput will be cleared with the compare compare of the compare compare of the compare of	RW re and PW en countir hen the co patibility v RW the CC ch	Compare Output Initial State /M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. with future devices, always write bits to 0. More information in 1.2 Conventional Invertance (Output Compare, PWM). CC Channel Mode
3 2	COIST This bit is only us high when the cois cleared, the out Reserved OUTINV Setting this bit in MODE	tions 0 sed in Output Comparounter is disabled. Who utput will be cleared with the cleared with the comparounter is disabled. Who utput will be cleared with the cleared with th	RW re and PW en countir hen the co patibility v RW the CC ch	Compare Output Initial State /M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. with future devices, always write bits to 0. More information in 1.2 Conventional Invertance (Output Compare, PWM). CC Channel Mode
3 2	COIST This bit is only us high when the cois cleared, the out reserved OUTINV Setting this bit in MODE These bits select	tions 0 sed in Output Compare punter is disabled. When the cleared with the cleared with the cleared with the cleared with the compare compared to the compar	RW re and PW en countir hen the co patibility v RW the CC ch	Compare Output Initial State I/M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. Ivith future devices, always write bits to 0. More information in 1.2 Conventional Invertance (Output Invertance) CC Channel Mode e channel.
3 2	COIST This bit is only us high when the cois cleared, the out Reserved OUTINV Setting this bit in MODE These bits selectivalue	tions 0 sed in Output Compare ounter is disabled. Who utput will be cleared with the cleared with the compare compare to the compare to the mode for Compare to the Mode	RW re and PW en countir hen the co patibility v RW the CC ch RW re/Capture	Compare Output Initial State /M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. // with future devices, always write bits to 0. More information in 1.2 Conventional Invertable (Output compare, PWM). CC Channel Mode c channel. Description
3 2	COIST This bit is only us high when the cois cleared, the out Reserved OUTINV Setting this bit in MODE These bits select Value 0	tions 0 sed in Output Comparounter is disabled. Whoutput will be cleared with the cleared with the comparounter is disabled. Who will be cleared with the mode for Comparounter is disabled. Who werts the output from the comparounter is disabled. Who were the output from the comparounter is disabled. Who were the comparounter is disabled. The comparounter is dis	RW re and PW en countir hen the co patibility w RW the CC ch RW re/Capture	Compare Output Initial State /M mode. When this bit is set in Compare or PWM mode, the output is set in gresumes, this value will represent the initial value for the output. If the bit ounter is disabled. with future devices, always write bits to 0. More information in 1.2 Conventional Invertance (Output compare, PWM). CC Channel Mode c channel. Description Compare/Capture channel turned off

20.5.16 TIMERn_CCx_CCV - CC Channel Value Register (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	0000000000															
Access																	[} Y															
Name																2	<u>}</u>															

Bit	Name	Reset	Access	Description
31:0	CCV	0x00000000	RWH	CC Channel Value

In input capture mode, this field holds the first unread capture value. When reading this register in input capture mode, the contents of the TIMERn_CCx_CCVB register will be written to TIMERn_CCx_CCV in the next cycle. In compare mode, this fields holds the compare value.

20.5.17 TIMERn_CCx_CCVP - CC Channel Value Peek Register

Offset															Bi	t Po	siti	on														
0x068	31	99	29	78	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	7	_	0
Reset																000000000000000000000000000000000000000	000000000000000000000000000000000000000															
Access																۵	۷															
Name																0/20	۱ ک															

Bit	Name	Reset	Access	Description
31:0	CCVP	0x00000000	R	CC Channel Value Peek
	This field is used to re	ad the CC value	e without p	ulling data through the FIFO in capture mode.

20.5.18 TIMERn_CCx_CCVB - CC Channel Buffer Register

Offset	Bit Position
0x06C	33 34 5 6 7 8 8 8 7 7 1 7 1 7 1 7 1 7 1 7 1 8 8 8 7 7 8 8 8 7 7 8 8 8 7 9 9 9 9 9 9
Reset	00000000000000000000000000000000000000
Access	NA H
Name	CCVB

Bit	Name	Reset	Access	Description
31:0	CCVB	0x00000000	RWH	CC Channel Value Buffer

In Input Capture mode, this field holds the last capture value if the TIMERn_CCx_CCV register already contains an earlier unread capture value. In Output Compare or PWM mode, this field holds the CC buffer value which will be written to TIMERn_CCx_CCV on an update event if TIMERn_CCx_CCVB contains valid data.

20.5.19 TIMERn DTCTRL - DTI Control Register

20.5.19	TIMERn_DTCTRL	ם ווע -	ontrol	ı Ke	yıste	r ———																				
Offset									В	it Po	ositi	on														
0x0A0	33 33 33 33 33 33 33 33 33 33 33 33 33	27 26 25 25	24	23	3 5	2 0	2 6	2 6	17	16	15	4	13	12	7	9	6	ω	/	9	2	4	က	7	-	
Reset																0	0			Š	Š		0	0	0	
Access			N N													\ N	X ≪			Ž	≥ Y		¥ N	ZX N	₩ M	
Name			DTPRSEN													DTFATS	DTAR				DIPROSEL		DTCINV	DTIPOL	DTDAS	i
Bit	Name	R	eset		A	cce	ss	Des	scrip	otior	n															
31:25	Reserved		o ensi ons	ure d	comp	atibil	ity v	vith f	uture	e de	vices	s, al	way	's w	rite i	bits t	to 0.	Мо	re in	forn	natio	on ir	1.2	? Co	nve	n-
24	DTPRSEN	0			F	RW		DT	PR	S Sc	ourc	e Eı	nabl	le												
	Enable/disable F	PRS as D	TI inp	ut.																						
23:11	Reserved		o ensi	ure d	comp	atibil	ity v	vith f	uture	e de	vices	s, al	way	's w	rite i	bits t	to 0.	Мо	re in	forn	natio	on ir	1.2	? Co	nve	n-
10	DTFATS	0			F	RW		DT	Fau	ılt A	ctio	n oı	n Tii	me	Sto	р										
	When Timer stop when DTAR is a channels go to s	also set, I	DTAR																							
9	DTAR	0			F	RW		DT	Alw	ays	Ru	n														
	This is used onl when its input so ue in DTPRESC	ource is P																								
8	Reserved		o ensi	ure d	comp	atibil	ity v	vith f	uture	e de	vices	s, al	way	's w	rite i	bits t	to 0.	Мо	re in	forn	natio	on ir	1.2	? Co	nve	n-
7:4	DTPRSSEL	0>	κ0		F	RW		DT	PR	S Sc	ourc	e Cl	han	nel	Sel	ect										
	Selects which P	RS chanr	nel co	mpa	ire ch	anne	el O v	will li	sten	to.																
	Value	М	ode					Des	scrip	tion																_
	0	PI	RSCH	10				PR	S Ch	ann	nel 0	sele	ecte	d as	s inp	ut										
	1	Pl	RSCH	11				PR	S Ch	ann	nel 1	sele	ecte	d as	s inp	ut										
	2	Pl	RSCH	12				PR	S Ch	ann	nel 2	sele	ecte	d as	s inp	ut										
	3	Pl	RSCH	13				PR	S Ch	ann	nel 3	sele	ecte	d as	s inp	ut										
	4	Pl	RSCH	14				PR	S Ch	ann	nel 4	sele	ecte	d as	s inp	ut										
	5		RSCH						S Ch																	
	6		RSCH						S Ch						-											
	7		RSCH						S Ch						-											
	8	Pl	RSCH	18				PR	S Ch	ann	nel 8	sele	ecte	d as	s inp	ut										

PRS Channel 9 selected as input
PRS Channel 10 selected as input

PRS Channel 11 selected as input

PRSCH9

PRSCH10

PRSCH11

9

10

11

Bit	Name	Reset	Access	Description
3	DTCINV	0	RW	DTI Complementary Output Invert
	Set to invert complem	entary outputs.		
2	DTIPOL	0	RW	DTI Inactive Polarity
	Set inactive polarity for	or outputs.		
1	DTDAS	0	RW	DTI Automatic Start-up Functionality
	Configure DTI restart	on debugger ex	it.	
	Value	Mode		Description
	0	NORESTART		No DTI restart on debugger exit
	1	RESTART		DTI restart on debugger exit
0	DTEN	0	RW	DTI Enable
	Enable/disable DTI.			

20.5.20 TIMERn_DTTIME - DTI Time Control Register

Offset			Bit Po	sition			
0x0A4	30 29 29 28	2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2	19 19 16 16	5 4	8 0 10 17 17	r 0 0 4	ю 7 г 0
Reset			00x0	'	00×0		0×0
Access			AW.		RW		A N
Name			DTFALLT		DTRISET		DTPRESC
Bit	Name	Reset Acc	ess Description				
31:22	Reserved	To ensure compatib	ility with future dev	ices, al	ways write bits to 0. Mo	re information ir	1.2 Conven-
21:16	DTFALLT	0x00 RW	DTI Fall-tim	9			
	Set time span fo	r the falling edge.					
	Value		Description				
	DTFALLT		Fall time of [TFALL	T+1 prescaled HFPER	CLK cycles	
15:14	Reserved	To ensure compatib	ility with future dev	ices, al	ways write bits to 0. Mo	re information ir	1.2 Conven-
13:8	DTRISET	0x00 RW	DTI Rise-tin	ie			
	Set time span fo	r the rising edge.					
	Value		Description				
	DTRISET		Rise time of	DTRISI	ET+1 prescaled HFPER	RCLK cycles	
7:4	Reserved	To ensure compatib	ility with future dev	ices, al	ways write bits to 0. Mo	re information ir	1.2 Conven-
3:0	DTPRESC	0x0 RW	DTI Prescal	er Setti	ng		
	Select prescaler	for DTI.					
	Value	Mode	Description				
	0	DIV1	The HFPER	CLK is	undivided		
	1	DIV2	The HFPER	CLK is	divided by 2		
	2	DIV4	The HFPER		<u> </u>		
	3	DIV8	The HFPER		<u> </u>		
	4	DIV16			divided by 16		
	5	DIV32			divided by 32		
	6	DIV64			divided by 64		
	7 8	DIV128 DIV256			divided by 128 divided by 256		
	9	DIV512			divided by 512		
	10	DIV1024			divided by 1024		

Bit Name Reset Access Description

20.5.21 TIMERn_DTFC - DTI Fault Configuration Register

Offset														Bi	t Po	sitio	on													
0x0A8	33 33	29	28	27	26	25	24	23	22	21	20	9	8	17	16	15	4	5	12	7	10	တ ထ) /	٠ (۵	ם ע	2 4	F (e 2	- 0	
Reset		'	'	0	0	0	0		'					2	OXO		'				0×0			•		<u>'</u>		(S S	_
Access				₩ N	N N	X N	X N							2	<u>۸</u>						RW							i	Ž	_
Name				DTLOCKUPFEN	DTDBGFEN	DTPRS1FEN	DTPRS0FEN							DTEA	Ā.						DTPRS1FSEL								DI PROOFSEL	_
Bit	Name)				Re	set			Ac	ces	s I	Des	crip	tion															
31:28	Rese	rved				To tion		ure	com	pati	bilit	y wit	th fu	ture	dev	rices	, alv	vay	s wr	ite k	its to	0. M	ore	info	rma	tion	in	1.2 Co	nven-	
27	DTLC	CKU	JPFE	N		0				RW	/	ı	DTI	Loc	kup	Fau	ılt E	nak	ole											-
	Set th	is bit	to 1	to e	enal	ole c	ore	lock	up a	is a	fau	lt so	urce	•																
26	DTDE	3GFE	N			0				RW	/	ı	DTI	Deb	ugg	jer F	aul	t En	nabl	е										_
	Set th	is bit	to 1	to e	enal	ole d	debu	gge	r as	a fa	ult	sour	се																	_
25	DTPRS1FEN 0 RW DTI PRS 1 Fault Enable																													
	-		bit to 1 to enable PRS source 1(PRS channel determined by DTPRS1FSEL) as a fault source															_												
24	DTPF					0				RW					6 0 F															
	Set th		to 1	to e	enal																-									
23:18	Rese	rved				To tion		ure	com	pati	bilit	y wit	th fu	ture	dev	rices	, alv	vay	s wr	ite k	its to	0. M	ore	info	rma	tion	in	1.2 Co	nven-	
17:16	DTFA	1				0x0)			RW	/	ı	DTI	Fau	lt A	ctio	า													
	Selec	t faul	lt act	ion.																										
	Value	}				Мо	de					ſ	Des	cript	ion															
	0					NC	NE					1	No a	actio	n on	ı fau	lt													
	1					INA	4CT	IVE				;	Set (outp	uts i	inac	tive													
	2					CL	EAF	₹				(Clea	ır ou	ıtput	s														
	3					TR	IST	ATE					Trist	ate	outp	uts														
15:12	Rese	rved				To tion		ure	com	pati	bilit	y wit	th fu	ture	dev	rices	, alv	vay	s wr	ite L	its to	0. M	ore	info	rma	tion	in	1.2 Co	nven-	
11:8	DTPF	RS1F	SEL			0x0)			RW	/	I	DTI	PRS	S Fa	ult S	Sour	rce	1 S	elec	t									
	Selec	t PR	S ch	ann	el fo	r faı	ult s	ourc	e 1.																					
	Value					Мо	de						Des	cript	ion															
	0					PR	SCI	10				F	PRS	Ch	anne	el 0	sele	cted	d as	fau	t sou	rce 1								
	1					PR	SCF	1 1				F	PRS	Ch	anne	el 1	sele	cted	d as	fau	t sou	rce 1								
	2 PRSCH2 PRS Channel 2 selected as fault source 1																													

Bit	Name	Reset	Access	Description
	3	PRSCH3		PRS Channel 3 selected as fault source 1
	4	PRSCH4		PRS Channel 4 selected as fault source 1
	5	PRSCH5		PRS Channel 5 selected as fault source 1
	6	PRSCH6		PRS Channel 6 selected as fault source 1
	7	PRSCH7		PRS Channel 7 selected as fault source 1
	8	PRSCH8		PRS Channel 8 selected as fault source 1
	9	PRSCH9		PRS Channel 9 selected as fault source 1
	10	PRSCH10		PRS Channel 10 selected as fault source 1
	11	PRSCH11		PRS Channel 11 selected as fault source 1
7:4	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	DTPRS0FSEL	0x0	RW	DTI PRS Fault Source 0 Select
	Select PRS channe	el for fault source 0.		
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as fault source 0
	1	PRSCH1		PRS Channel 1 selected as fault source 1
	2	PRSCH2		PRS Channel 2 selected as fault source 2
	3	PRSCH3		PRS Channel 3 selected as fault source 3
	4	PRSCH4		PRS Channel 4 selected as fault source 4
	5	PRSCH5		PRS Channel 5 selected as fault source 5
	6	PRSCH6		PRS Channel 6 selected as fault source 6
	7	PRSCH7		PRS Channel 7 selected as fault source 7
	•			
	8	PRSCH8		PRS Channel 8 selected as fault source 8
		PRSCH8 PRSCH9		PRS Channel 8 selected as fault source 8 PRS Channel 9 selected as fault source 9
	8			

20.5.22 TIMERn_DTOGEN - DTI Output Generation Enable Register

Offset															Ві	it Po	siti	on														
0x0AC	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	2	4	က	2	_	0
Reset					•						•		•			•								•			0	0	0	0	0	0
Access																											M	₽	₽	R M M	Z.	S.
Name																											DTOGCDTI2EN	DTOGCDT11EN	DTOGCDTI0EN	DTOGCC2EN	DTOGCC1EN	DTOGCC0EN

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	DTOGCDTI2EN	0	RW	DTI CDTI2 Output Generation Enable
	This bit enables/disab	les output gene	ration for tl	ne CDTI2 output from the DTI.
4	DTOGCDTI1EN	0	RW	DTI CDTI1 Output Generation Enable
	This bit enables/disab	les output gene	ration for tl	ne CDTI1 output from the DTI.
3	DTOGCDTI0EN	0	RW	DTI CDTI0 Output Generation Enable
	This bit enables/disab	oles output gene	ration for tl	ne CDTI0 output from the DTI.
2	DTOGCC2EN	0	RW	DTI CC2 Output Generation Enable
	This bit enables/disab	oles output gene	ration for tl	ne CC2 output from the DTI.
1	DTOGCC1EN	0	RW	DTI CC1 Output Generation Enable
	This bit enables/disab	les output gene	ration for tl	ne CC1 output from the DTI.
0	DTOGCC0EN	0	RW	DTI CC0 Output Generation Enable
	This bit enables/disab	les output gene	ration for tl	ne CC0 output from the DTI.

20.5.23 TIMERn_DTFAULT - DTI Fault Register

Offset															Bi	t Po	siti	on														
0x0B0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	2	4	3	2	_	0
Reset		•	•			•										•								•	•	•			0	0	0	0
Access																													2	œ	ď	<u>~</u>
Name																													DTLOCKUPF	DTDBGF	DTPRS1F	DTPRS0F

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
3	DTLOCKUPF	0	R	DTI Lockup Fault
	This bit is set to 1 if can be used to clea	•	ult has occu	rred and DTLOCKUPFEN is set to 1. The TIMER0_DTFAULTC register
2	DTDBGF	0	R	DTI Debugger Fault
	This bit is set to 1 if used to clear fault b		has occurr	ed and DTDBGFEN is set to 1. The TIMER0_DTFAULTC register can be
1	DTPRS1F	0	R	DTI PRS 1 Fault
	This bit is set to 1 if used to clear fault b		s occurred	and DTPRS1FEN is set to 1. The TIMER0_DTFAULTC register can be
0	DTPRS0F	0	R	DTI PRS 0 Fault
	This bit is set to 1 if used to clear fault b		s occurred	and DTPRS0FEN is set to 1. The TIMER0_DTFAULTC register can be

20.5.24 TIMERn_DTFAULTC - DTI Fault Clear Register

Offset															Bi	t Po	siti	on														
0x0B4	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	7	_	0
Reset		'	'		'										'					'							'	•	0	0	0	0
Access																													W1	W1	W1	W
Name																													TLOCKUPFC	DTDBGFC	DTPRS1FC	DTPRS0FC

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3	TLOCKUPFC	0	W1	DTI Lockup Fault Clear
	Write 1 to this bit to	clear core lock	up fault.	
2	DTDBGFC	0	W1	DTI Debugger Fault Clear
	Write 1 to this bit to	o clear debugger	fault.	
1	DTPRS1FC	0	W1	DTI PRS1 Fault Clear
	Write 1 to this bit to	clear PRS 1 fa	ult.	
0	DTPRS0FC	0	W1	DTI PRS0 Fault Clear
	Write 1 to this bit to	clear PRS 0 fa	ult.	

20.5.25 TIMERn_DTLOCK - DTI Configuration Lock Register

Offset															Bi	t Po	siti	on														
0x0B8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset							•											•							nannan							
Access																									[} Y							
Name																								\U\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LOCANE							


Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	DTI Lock Kev

Write any other value than the unlock code to lock TIMERn_ROUTE, TIMERn_DTCTRL, TIMERn_DTTIME and TIMERn_DTFC from editing. Write the unlock code to unlock. When reading the register, bit 0 is set when the lock is enabled.

Mode	Value	Description
Read Operation		
UNLOCKED	0	TIMER DTI registers are unlocked
LOCKED	1	TIMER DTI registers are locked
Write Operation		
LOCK	0	Lock TIMER DTI registers
UNLOCK	0xCE80	Unlock TIMER DTI registers

21. LETIMER - Low Energy Timer





Quick Facts

What?

The LETIMER is a down-counter that can keep track of time and output configurable waveforms. Running on a 32768 Hz clock, the LETIMER is available in EM0 Active, EM1 Sleep, EM2 Deep Sleep, and EM3 Stop.

Why?

The LETIMER can be used to provide repeatable waveforms to external components while remaining in EM2 Deep Sleep. It is well suited for applications such as metering systems or to provide more compare values than available in the RTC.

How?

With buffered repeat and top value registers, the LE-TIMER can provide glitch-free waveforms at frequencies up to 16 kHz. It can be coupled with RTC using PRS, allowing advanced time-keeping and wake-up functions in EM2 Deep Sleep and EM3 Stop

21.1 Introduction

The unique LETIMERTM, the Low Energy Timer, is a 16-bit timer that is available in energy mode EM0 Active, EM1 Sleep, EM2 Deep Sleep, and EM3 Stop. Because of this, it can be used for timing and output generation when most of the device is powered down, allowing simple tasks to be performed while the power consumption of the system is kept at an absolute minimum.

The LETIMER can be used to output a variety of waveforms with minimal software intervention. It can also be connected to the Real Time Counter (RTC) using PRS, and can be configured to start counting on compare matches from the RTC.

21.2 Features

- · 16-bit down count timer
- · 2 Compare match registers
- · Compare register 0 can be top timer top value
- · Compare registers can be double buffered
- · Double buffered 8-bit Repeat Register
- · Same clock source as the Real Time Counter
- · LETIMER can be triggered (started) by an RTC event via PRS or by software
- · LETIMER can be started, stopped, and/or cleared by PRS
- · 2 output pins can optionally be configured to provide different waveforms on timer underflow:
 - · Toggle output pin
 - Apply a positive pulse (pulse width of one LFACLK_{LETIMER} period)
 - PWM
- Interrupt on:
 - · Compare matches
 - · Timer underflow
 - · Repeat done
- · Optionally runs during debug
- · PRS Output

21.3 Functional Description

An overview of the LETIMER module is shown in Figure 21.1 LETIMER Overview on page 714. The LETIMER is a 16-bit down-counter with two compare registers, LETIMERn_COMP0 and LETIMERn_COMP1. The LETIMERn_COMP0 register can optionally act as a top value for the counter. The repeat counter LETIMERn_REP0 allows the timer to count a specified number of times before it stops. Both the LETIMERn_COMP0 and LETIMERn_REP0 registers can be double buffered by the LETIMERn_COMP1 and LETIMERn REP1 registers to allow continuous operation. The timer can generate a single pin output, or two linked outputs.




Figure 21.1. LETIMER Overview

21.3.1 Timer

The timer is started by setting command bit START in LETIMERn_CMD, and stopped by setting the STOP command bit in the same register. RUNNING in LETIMERn_STATUS is set as long as the timer is running. The timer can also be started on external signals, such as a compare match from the Real Time Counter. If START and STOP are set at the same time, STOP has priority, and the timer will be stopped.

The timer value can be read using the LETIMERn_CNT register. The value can be written, and it can also be cleared by setting the CLEAR command bit in LETIMERn_CMD. If the CLEAR and START commands are issued at the same time, the timer will be cleared, then start counting at the top value.

21.3.2 Compare Registers

The LETIMER has two compare match registers, LETIMERn_COMP0 and LETIMERn_COMP1. Each of these compare registers are capable of generating an interrupt when the counter value LETIMERn_CNT becomes equal to their value. When LETIMERn_CNT becomes equal to the value of LETIMERn_COMP0, the interrupt flag COMP0 in LETIMERn_IF is set, and when LETIMERn_CNT becomes equal to the value of LETIMERn_COMP1, the interrupt flag COMP1 in LETIMERn_IF is set.

21.3.3 Top Value

If COMP0TOP in LETIMERn_CTRL is set, the value of LETIMERn_COMP0 acts as the top value of the timer, and LETIMERn_COMP0 is loaded into LETIMERn_CNT on timer underflow. If COMP0TOP is cleared to 0, the timer wraps around to 0xFFFF. The underflow interrupt flag UF in LETIMERn IF is set when the timer reaches zero.

21.3.3.1 Buffered Top Value

If BUFTOP in LETIMERn_CTRL is set, the value of LETIMERn_COMP0 is buffered by LETIMERn_COMP1. In this mode, the value of LETIMERn_COMP1 is loaded into LETIMERn_COMP0 every time LETIMERn_REP0 is about to decrement to 0. This can for instance be used in conjunction with the buffered repeat mode to generate continually changing output waveforms.

Write operations to LETIMERn COMP0 have priority over buffer loads.

21.3.3.2 Repeat Modes

By default, the timer wraps around to the top value or 0xFFFF on each underflow, and continues counting. The repeat counters can be used to get more control of the operation of the timer, including defining the number of times the counter should wrap around. Four different repeat modes are available, see Table 21.1 LETIMER Repeat Modes on page 715.

Table 21.1. LETIMER Repeat Modes

REPMODE	Mode	Description
0600	Free-running	The timer runs until it is stopped.
0b01	One-shot	The timer runs as long as LETI-MERn_REP0 != 0. LETIMERn_REP0 is decremented at each timer underflow.
0b10	Buffered	The timer runs as long as LETI-MERn_REP0 != 0. LETIMERn_REP0 is decremented on each timer underflow. If LETIMERn_REP1 has been written, it is loaded into LETIMERn_REP0 when LETI-MERn_REP0 is about to be decremented to 0.
0b11	Double	The timer runs as long as LETI-MERn_REP0 != 0 or LETIMERn_REP1 != 0. Both LETIMERn_REP0 and LETI-MERn_REP1 are decremented at each timer underflow.

The interrupt flags REP0 and REP1 in LETIMERn_IF are set whenever LETIMERn_REP0 or LETIMERn_REP1 are decremented to 0 respectively. REP0 is also set when the value of LETIMERn_REP1 is loaded into LETIMERn_REP0 in buffered mode.

21.3.3.3 Free-Running Mode

In free-running mode, the LETIMER acts as a regular timer and the repeat counter is disabled. When started, the timer runs until it is stopped using the STOP command bit in LETIMERn_CMD. A state machine for this mode is shown in Figure 21.2 LETIMER State Machine for Free-running Mode on page 716.




Figure 21.2. LETIMER State Machine for Free-running Mode

Note that the CLEAR command bit in LETIMERn_CMD always has priority over other changes to LETIMERn_CNT. When the clear command is used, LETIMERn_CNT is set to 0 and an underflow event will not be generated when LETIMERn_CNT wraps around to the top value or 0xFFFF. Since no underflow event is generated, no output action is performed. LETIMERn_REP0, LETIMERn_REP1, LETIMERn_COMP0 and LETIMERn_COMP1 are also left untouched.

21.3.3.4 One-shot Mode

The one-shot repeat mode is the most basic repeat mode. In this mode, the repeat register LETIMERn_REP0 is decremented every time the timer underflows, and the timer stops when LETIMERn_REP0 goes from 1 to 0. In this mode, the timer counts down LETIMERn_REP0 times, i.e. the timer underflows LETIMERn_REP0 times.

Note: Write operations to LETIMERn_REP0 have priority over the timer decrement event. If LETIMERn_REP0 is assigned a new value in the same cycle as a timer decrement event occurs, the timer decrement will not occur and the new value is assigned.

LETIMERn_REP0 can be written while the timer is running to allow the timer to run for longer periods at a time without stopping. Figure 21.3 LETIMER One-shot Repeat State Machine on page 717.




Figure 21.3. LETIMER One-shot Repeat State Machine

21.3.3.5 Buffered Mode

The Buffered repeat mode allows buffered timer operation. When started, the timer runs LETIMERn_REP0 number of times. If LETIMERn_REP1 has been written since the last time it was used and it is nonzero, LETIMERn_REP1 is then loaded into LETIMERn_REP0, and counting continues the new number of times. The timer keeps going as long as LETIMERn_REP1 is updated with a nonzero value before LETIMERn_REP0 is finished counting down. The timer top value (LETIMERn_COMP0) may also optionally be buffered by setting BUFTOP in LETIMERn_CTRL.

If the timer is started when both LETIMERn_CNT and LETIMERn_REP0 are zero but LETIMERn_REP1 is non-zero, LETIMERn_REP1 is loaded into LETIMERn_REP0, and the counter counts the loaded number of times.

Used in conjunction with a buffered top value, both the top and repeat values of the timer may be buffered, and the timer can for instance be set to run 4 times with period 7 (top value 6), 6 times with period 200, then 3 times with period 50.

A state machine for the buffered repeat mode is shown in Figure 21.4 LETIMER Buffered Repeat State Machine on page 718. REP1_{USED} shown in the state machine is an internal variable that keeps track of whether the value in LETIMERn_REP1 has been loaded into LETIMERn_REP0 or not. The purpose of this is that a value written to LETIMERn_REP1 should only be counted once. REP1_{USED} is cleared whenever LETIMERn_REP1 is written.




Figure 21.4. LETIMER Buffered Repeat State Machine

21.3.3.6 Double Mode

The Double repeat mode works much like the one-shot repeat mode. The difference is that, where the one-shot mode counts as long as LETIMERn_REP0 is larger than 0, the double mode counts as long as either LETIMERn_REP0 or LETIMERn_REP1 is larger than 0. As an example, say LETIMERn_REP0 is 3 and LETIMERn_REP1 is 10 when the timer is started. If no further interaction is done with the timer, LETIMERn_REP0 will now be decremented 3 times, and LETIMERn_REP1 will be decremented 10 times. The timer counts a total of 10 times, and LETIMERn_REP0 is 0 after the first three timer underflows and stays at 0. LETIMERn_REP0 and LETIMERn_REP1 can be written at any time. After a write to either of these, the timer is guaranteed to underflow at least the written number of times if the timer is running. Use the Double repeat mode to generate output on both the LETIMER outputs at the same time. The state machine for this repeat mode can be seen in Figure 21.5 LETIMER Double Repeat State Machine on page 719.




Figure 21.5. LETIMER Double Repeat State Machine

21.3.3.7 Clock Source

The LETIMER clock source and its prescaler value are defined in the Clock Management Unit (CMU). The LFACLK_{LETIMERn} has a frequency given by Figure 21.6 LETIMER Clock Frequency on page 719.

 $f_{LFACKL_LETIMERn} = 32768/2^{LETIMERn}$

Figure 21.6. LETIMER Clock Frequency

where the exponent LETIMERn is a 4 bit value in the CMU LFAPRESC0 register.

To use this module, the LE interface clock must be enabled in CMU_HFBUSCLKEN0, in addition to the module clock.

21.3.3.8 PRS Input Triggers

The LETIMER can be configured to start, stop, and/or clear based on PRS inputs. The diagram showing the functions of the PRS input triggers is shown in Figure 21.7 LETIMER PRS Input Triggers on page 720.

There are 12 PRS inputs to the LETIMER. PRSSTARTSEL, PRSSTOPSEL, and PRSCLEARSEL select which PRS inputs are used to start, stop, and/or clear the LETIMER. PRSSTARTMODE, PRSSTOPMODE, and PRSCLEARMODE select which edge or edge(s) can trigger the start, stop, and/or clear action. The PRSSTARTEN, PRSSTOPEN, and PRSCLEAREN signals shown in the diagram are derived from the PRSSTARTMODE, PRSSTOPMODE, and PRSCLEARMODE fields; if the corresponding bit field is set to NONE, the feature is disabled.




Figure 21.7. LETIMER PRS Input Triggers

21.3.3.9 Debug

If DEBUGRUN in LETIMERn_CTRL is cleared, the LETIMER automatically stops counting when the CPU is halted during a debug session, and resumes operation when the CPU continues. Because of synchronization, the LETIMER is halted two clock cycles after the CPU is halted, and continues running two clock cycles after the CPU continues. RUNNING in LETIMERn_STATUS is not cleared when the LETIMER stops because of a debug-session.

Set DEBUGRUN in LETIMERn_CTRL to allow the LETIMER to continue counting even when the CPU is halted in debug mode.

21.3.4 Underflow Output Action

For each of the repeat registers, an underflow output action can be set. The configured output action is performed every time the counter underflows while the respective repeat register is nonzero. In PWM mode, the output is similarly only changed on COMP1 match if the repeat register is nonzero. As an example, the timer will perform 7 output actions if LETIMERn_REP0 is set to 7 when starting the timer in one-shot mode and leaving it untouched.

The output actions can be set by configuring UFOA0 and UFOA1 in LETIMERn_CTRL. UFOA0 defines the action on output 0, and is connected to LETIMERn_REP0, while UFOA1 defines the action on output 1 and is connected to LETIMERn_REP1. The possible actions are defined in Table 21.2 LETIMER Underflow Output Actions on page 721.

Table 21.2. LETIMER Underflow Output Actions

UF0A0/UF0A1	Mode	Description
0b00	Idle	The output is held at its idle value
0b01	Toggle	The output is toggled on LETIMERn_CNT underflow if LEIMERn_REPx is nonzero
0b10	Pulse	The output is held active for one clock cycle on LETIMERn_CNT underflow if LETI-MERn_REPx is nonzero. It then returns to its idle value
0b11	PWM	The output is set idle on LETIMERn_CNT underflow and active on compare match with LETIMERn_COMP1 if LETI-MERn_REPx is nonzero.

Note:

- For the Pulse and PWM modes, the outputs will return to their idle states regardless of the state of the corresponding LETI-MERn_REPx registers. They will only be set active if the LETIMERn_REPx registers are nonzero however.
- For free-running mode, LETIMERn_REP0 != 0 for output generation to be enabled.

The polarity of the outputs can be set individually by configuring OPOL0 and OPOL1 in LETIMERn_CTRL. When these are cleared, their respective outputs have a low idle value and a high active value. When they are set, the idle value is high, and the active value is low.

When using the toggle action, the outputs can be driven to their idle values by setting their respective CTO0/CTO1 command bits in LETIMERn_CTRL. This can be used to put the output in a well-defined state before beginning to generate toggle output, which may be important in some applications. The command bit can also be used while the timer is running.

Some simple waveforms generated with the different output modes are shown in Figure 21.8 LETIMER Simple Waveforms Output on page 722. For the example, REPMODE in LETIMERn_CTRL has been cleared, COMP0TOP also in LETIMERn_CTRL has been set and LETIMERn_COMP0 has been written to 3. As seen in the figure, LETIMERn_COMP0 now decides the length of the signal periods. For the toggle mode, the period of the output signal is 2(LETIMERn_COMP0 + 1), and for the pulse modes, the periods of the output signals are LETIMERn_COMP0+1. Note that the pulse outputs are delayed by one period relative to the toggle output. The pulses come at the end of their periods.




Figure 21.8. LETIMER Simple Waveforms Output

For the example in Figure 21.9 LETIMER Repeated Counting on page 722, the One-shot repeat mode has been selected, and LETI-MERn_REP0 has been written to 3. The resulting behavior is pretty similar to that shown in Figure 6, but in this case, the timer stops after counting to zero LETIMERn_REP0 times. By using LETIMERn_REP0 the user has full control of the number of pulses/toggles generated on the output.




Figure 21.9. LETIMER Repeated Counting

Using the Double repeat mode, output can be generated on both the LETIMER outputs. Figure 21.10 LETIMER Dual Output on page 723 shows an example of this. UFOA0 and UFOA1 in LETIMERn_CTRL are configured for pulse output and the outputs are configured for low idle polarity. As seen in the figure, the number written to the repeat registers determine the number of pulses generated on each of the outputs.




Figure 21.10. LETIMER Dual Output

21.3.5 PRS Output

The LETIMER outputs can be routed out onto the PRS system. Enabling the PRS connection can be done by setting SOURCESEL to LETIMERx and SIGSEL to LETIMERxCHn in PRS_CHx_CTRL. The PRS register description can be found in 15.5 Register Description

21.3.6 Examples

This section presents a couple of usage examples for the LETIMER.

21.3.6.1 Triggered Output Generation

If both LETIMERn_CNT and LETIMERn_REP0 are 0 in buffered mode, and COMP0TOP and BUFTOP in LETIMERn_CTRL are set, the values of LETIMERn_COMP1 and LETIMERn_REP1 are loaded into LETIMERn_CNT and LETIMERn_REP0 respectively when the timer is started. If no additional writes to LETIMERn_REP1 are done before the timer stops, LETIMERn_REP1 determines the number of pulses/toggles generated on the output, and LETIMERn_COMP1 determines the period lengths.

As the RTC can be used via PRS to start the LETIMER, the RTC and LETIMER can thus be combined to generate specific pulse-trains at given intervals. Software can update LETIMERn_COMP1 and LETIMERn_REP1 to change the number of pulses and pulse-period in each train, but if changes are not required, software does not have to update the registers between each pulse train.

For the example in Figure 21.11 LETIMER Triggered Operation on page 724, the initial values cause the LETIMER to generate two pulses with 3 cycle periods, or a single pulse 3 cycles wide every time the LETIMER is started. After the output has been generated, the LETIMER stops, and is ready to be triggered again.




Figure 21.11. LETIMER Triggered Operation

21.3.6.2 Continuous Output Generation

In some scenarios, it might be desired to make LETIMER generate a continuous waveform. Very simple constant waveforms can be generated without the repeat counter as shown in Figure 21.8 LETIMER Simple Waveforms Output on page 722, but to generate changing waveforms, using the repeat counter and buffer registers can prove advantageous.

For the example in Figure 21.12 LETIMER Continuous Operation on page 725, the goal is to produce a pulse train consisting of 3 sequences with the following properties:

- · 3 pulses with periods of 3 cycles
- · 4 pulses with periods of 2 cycles
- · 2 pulses with periods of 3 cycles




Figure 21.12. LETIMER Continuous Operation

The first two sequences are loaded into the LETIMER before the timer is started.

LETIMERn_COMP0 is set to 2 (cycles – 1), and LETIMERn_REP0 is set to 3 for the first sequence, and the second sequence is loaded into the buffer registers, i.e. COMP1 is set to 1 and LETIMERn_REP1 is set to 4.

The LETIMER is set to trigger an interrupt when LETIMERn_REP0 is done by setting REP0 in LETIMERn_IEN. This interrupt is a good place to update the values of the buffers. Last but not least REPMODE in LETIMERn_CTRL is set to buffered mode, and the timer is started.

In the interrupt routine the buffers are updated with the values for the third sequence. If this had not been done, the timer would have stopped after the second sequence.

The final result is shown in Figure 21.12 LETIMER Continuous Operation on page 725. The pulse output is grouped to show which sequence generated which output. Toggle output is also shown in the figure. Note that the toggle output is not aligned with the pulse outputs.

Note: Multiple LETIMER cycles are required to write a value to the LETIMER registers. The example in Figure 21.12 LETIMER Continuous Operation on page 725 assumes that writes are done in advance so they arrive in the LETIMER as described in the figure.

Figure 21.13 LETIMER LETIMERn_CNT Not Initialized to 0 on page 726 shows an example where the LETIMER is started while LETIMERn CNT is nonzero. In this case the length of the first repetition is given by the value in LETIMERn CNT.




Figure 21.13. LETIMER LETIMERn CNT Not Initialized to 0

21.3.6.3 PWM Output

There are several ways of generating PWM output with the LETIMER, but the most straight-forward way is using the PWM output mode. This mode is enabled by setting UFOA0 or UFOA1 in LETIMERn_CTRL to 3. In PWM mode, the output is set idle on timer underflow, and active on LETIMERn_COMP1 match, so if for instance COMP0TOP = 1 and OPOL0 = 0 in LETIMERn_CTRL, LETIMERn COMP0 determines the PWM period, and LETIMERn_COMP1 determines the active period.

The PWM period in PWM mode is LETIMERn_COMP0 + 1. There is no special handling of the case where LETIMERn_COMP1 > LETIMERn_COMP0, so if LETIMERn_COMP1 > LETIMERn_COMP0, the PWM output is given by the idle output value. This means that for OPOLx = 0 in LETIMERn_CTRL, the PWM output will always be 0 for at least one clock cycle, and for OPOLx = 1 LETIMERN CTRL, the PWM output will always be 1 for at least one clock cycle.

To generate a PWM signal using the full PWM range, invert OPOLx when LETIMERn_COMP1 is set to a value larger than LETI-MERn_COMP0.

21.3.6.4 Interrupts

The interrupts generated by the LETIMER are combined into one interrupt vector. If the interrupt for the LETIMER is enabled, an interrupt will be made if one or more of the interrupt flags in LETIMERn_IF and their corresponding bits in LETIMER_IEN are set.

21.3.7 Register Access

This module is a Low Energy Peripheral, and supports immediate synchronization. For description regarding immediate synchronization, the reader is referred to 4.3.1 Writing.

21.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	LETIMERn_CTRL	RW	Control Register
0x004	LETIMERn_CMD	W1	Command Register
0x008	LETIMERn_STATUS	R	Status Register
0x00C	LETIMERn_CNT	RWH	Counter Value Register
0x010	LETIMERn_COMP0	RWH	Compare Value Register 0
0x014	LETIMERn_COMP1	RW	Compare Value Register 1
0x018	LETIMERn_REP0	RWH	Repeat Counter Register 0
0x01C	LETIMERn_REP1	RWH	Repeat Counter Register 1
0x020	LETIMERn_IF	R	Interrupt Flag Register
0x024	LETIMERn_IFS	W1	Interrupt Flag Set Register
0x028	LETIMERn_IFC	(R)W1	Interrupt Flag Clear Register
0x02C	LETIMERn_IEN	RW	Interrupt Enable Register
0x034	LETIMERn_SYNCBUSY	R	Synchronization Busy Register
0x040	LETIMERn_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x044	LETIMERn_ROUTELOC0	RW	I/O Routing Location Register
0x050	LETIMERn_PRSSEL	RW	PRS Input Select Register

21.5 Register Description

21.5.1 LETIMERn_CTRL - Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on													
0x000	2	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ი	∞	7	9	5	4	3	7	- (
Reset		•	•	•		•	•	•	•			•		•	•	•		•	•	0			0	0	0	0	OXO	2	OxO	2	0x0
Access																				\ N			₩	₩ M	R.	\ N	8		NA NA		RW
Name																				DEBUGRUN			COMPOTOP	BUFTOP	OPOL1	OPOL0	LIEOA1		LIFOAO		REPMODE
Bit	N	lame					R	eset			Ac	ces	S	Des	crip	tior															
31:13	R	Reserv	/ed					o ens	ure	con	pati	bilit	y wi	th fu	ture	de	/ices	s, alı	way	's wr	rite b	its to	o 0.	Мо	re in	nforn	natio	n in	1.2	Coi	nven-
12	D	EBU	GRL	JN			0				RV	/		Deb	ug I	Mod	e R	un E	Ena	ble											
	S	et to	keep	o th	ne LE	TIM	IEF	R runi	ning	in d	ebu	g m	ode	•																	
	V	'alue												Des	cript	ion															
	0													LET	IME	R is	froz	zen i	in de	ebug	g mc	de									
	1													LET	IME	R is	run	ning	j in d	debu	ıg m	ode									
11:10	R	Reserv	/ed					o ens	ure	con	pati	bilit	y wi	th fu	ture	de	/ices	s, alı	way	s wr	rite k	its to	0 0.	Мо	re in	nforn	natio	n in	1.2	Coi	nven-
							_																								

11:10	Reservea	tions	е сотрацынц	with future devices, always write bits to 0. More information in 1.2 Conven-
9	COMP0TOP	0	RW	Compare Value 0 is Top Value
	When set, the cou	inter is cleared	in the clock c	ycle after a compare match with compare channel 0.
	Value			Description
	0			The top value of the LETIMER is 65535 (0xFFFF)
	1			The top value of the LETIMER is given by COMP0
8	BUFTOP	0	RW	Buffered Top

Set to load COMP1 into COMP0 when REP0 reaches 0,	allowing a buffered top value.

	Malue			Description
	Value			Description
	0			COMP0 is only written by software
	1			COMP0 is set to COMP1 when REP0 reaches 0
7	OPOL1	0	RW	Output 1 Polarity
	Defines the idle	e value of output 1		
6	OPOL0	0	RW	Output 0 Polarity
	Defines the idle	e value of output 0		

Bit	Name	Reset	Access	Description
5:4	UFOA1	0x0	RW	Underflow Output Action 1
	Defines the action	n on LETn_O1 on a	LETIMER	underflow.
	Value	Mode		Description
	0	NONE		LETn_O1 is held at its idle value as defined by OPOL1
	1	TOGGLE		LETn_O1 is toggled on CNT underflow
	2	PULSE		LETn_O1 is held active for one LFACLK _{LETIMER0} clock cycle on CNT underflow. The output then returns to its idle value as defined by OPOL1
	3	PWM		LETn_O1 is set idle on CNT underflow, and active on compare match with COMP1
3:2	UFOA0	0x0	RW	Underflow Output Action 0
	Defines the action	n on LETn_O0 on a	LETIMER (underflow.
	Value	Mode		Description
	0	NONE		LETn_O0 is held at its idle value as defined by OPOL0
	1	TOGGLE		LETn_O0 is toggled on CNT underflow
	2	PULSE		LETn_O0 is held active for one LFACLK _{LETIMER0} clock cycle on CNT underflow. The output then returns to its idle value as defined by OPOL0
	3	PWM		LETn_O0 is set idle on CNT underflow, and active on compare match with COMP1
1:0	REPMODE	0x0	RW	Repeat Mode
	Allows the repeat	counter to be enable	led and dis	abled.
	Value	Mode		Description
	0	FREE		When started, the LETIMER counts down until it is stopped by software
	1	ONESHOT		The counter counts REP0 times. When REP0 reaches zero, the counter stops
	2	BUFFERED		The counter counts REP0 times. If REP1 has been written, it is loaded into REP0 when REP0 reaches zero, otherwise the counter stops
	3	DOUBLE		Both REP0 and REP1 are decremented when the LETIMER wraps around. The LETIMER counts until both REP0 and REP1 are zero

21.5.2 LETIMERn_CMD - Command Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Pc	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	ဝ	œ	7	9	5	4	က	2	_	0
Reset					'			•	•			•				'	•		•					•				0	0	0	0	0
Access																												W W	W M	W	W	W ₁
Name																												СТО1	СТОО	CLEAR	STOP	START

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	CTO1	0	W1	Clear Toggle Output 1
	Set to drive toggle ou	tput 1 to its idle	value	
3	CTO0	0	W1	Clear Toggle Output 0
	Set to drive toggle ou	tput 0 to its idle	value	
2	CLEAR	0	W1	Clear LETIMER
	Set to clear LETIMER	₹		
1	STOP	0	W1	Stop LETIMER
	Set to stop LETIMER			
0	START	0	W1	Start LETIMER
	Set to start LETIMER	1		

21.5.3 LETIMERn_STATUS - Status Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	2	_	0
Reset																																0
Access																																2
																																Ŋ
Name																																NNN
																																2

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	RUNNING	0	R	LETIMER Running
	Set when LETIMER i	s running.		

21.5.4 LETIMERn_CNT - Counter Value Register

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset									•															00000	00000							
Access																								D/V/D								
Name																								TIVO	5							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	CNT	0x0000	RWH	Counter Value
	Use to read the curre	ent value of the l	LETIMER.	

21.5.5 LETIMERn_COMP0 - Compare Value Register 0 (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset	Bit Position	osition										
0x010	33 34 36 37 38 38 38 39 39 39 39 39 39 39 39 39 39 39 39 39	4 m 0 t 0										
Reset	0000×0											
Access	RWH											
Name	СОМРО											

Bit	Name	Reset	Access	Description								
31:16	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
15:0	COMP0	0x0000	RWH	Compare Value 0								
	Compare and optionally top value for LETIMER.											

21.5.6 LETIMERn_COMP1 - Compare Value Register 1 (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset	Bit Position														
0x014	31 32 33 34 35 36 37 38 39 30 31 31 32 33 34 36 37 37 31 32 33 34 35 36 37 37 48 49 40 <th>11 11 11 11 11 11 11 11 11 11 11 11 11</th>	11 11 11 11 11 11 11 11 11 11 11 11 11													
Reset		0000x0													
Access		R ≫													
Name		COMP1													

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	COMP1	0x0000	RW	Compare Value 1
	Compare and optiona	ally buffered top	value for L	ETIMER.

21.5.7 LETIMERn_REP0 - Repeat Counter Register 0 (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset	Bit Position	
0x018	8 8 6 8 7 2 8 7 8 7 8 8 8 8 8 8 8 8 8 8 8 8 8	L 0 0 4 0 1 0
Reset		00×0
Access		RWH
Name		REP0

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	REP0	0x00	RWH	Repeat Counter 0
	Optional repeat coun	ter.		

21.5.8 LETIMERn_REP1 - Repeat Counter Register 1 (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset	Bit Position	
0x01C	8 8 8 6 7 8 8 7 8 8 8 7 8 8 8 8 8 8 8 8	0 2 4 8 7 0
Reset		00×0
Access		RWH
Name		REP1

Bit	Name	Reset	Access	Description								
31:8	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-								
7:0	REP1	0x00	RWH	Repeat Counter 1								
	Optional repeat counter or buffer for REP0.											

21.5.9 LETIMERn_IF - Interrupt Flag Register

Offset	Bit Position																															
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	_∞	7	9	2	4	က	2	_	0
Reset					'	•													•					•		•		0	0	0	0	0
Access																												22	<u>~</u>	œ	œ	<u>~</u>
Name																												REP1	REP0	UF	COMP1	COMPO

Bit	Name	Reset	Access	Description									
31:5	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-									
4	REP1	0	R	Repeat Counter 1 Interrupt Flag									
	Set when repeat coul	nter 1 reaches z	ero.										
3	REP0	0	R	Repeat Counter 0 Interrupt Flag									
	Set when repeat counter 0 reaches zero or when the REP1 interrupt flag is loaded into the REP0 interrupt flag.												
2	UF	0	R	Underflow Interrupt Flag									
	Set on LETIMER und	lerflow.											
1	COMP1	0	R	Compare Match 1 Interrupt Flag									
	Set when LETIMER r	eaches the valu	e of COMP	1.									
0	COMP0	0	R	Compare Match 0 Interrupt Flag									
	Set when LETIMER r	eaches the valu	e of COMP	0.									

21.5.10 LETIMERn_IFS - Interrupt Flag Set Register

Offset	Bit Position																															
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	11	10	ဝ	æ	7	9	5	4	က	2	_	0
Reset			'									•				'								•				0	0	0	0	0
Access																												W	W	W1	W M	W
Name																												REP1	REP0	-H	COMP1	COMPO

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	REP1	0	W1	Set REP1 Interrupt Flag
	Write 1 to set the REI	P1 interrupt flag		
3	REP0	0	W1	Set REP0 Interrupt Flag
	Write 1 to set the REI	⊃0 interrupt flag		
2	UF	0	W1	Set UF Interrupt Flag
	Write 1 to set the UF	interrupt flag		
1	COMP1	0	W1	Set COMP1 Interrupt Flag
	Write 1 to set the CO	MP1 interrupt fla	ng	
0	COMP0	0	W1	Set COMP0 Interrupt Flag
	Write 1 to set the CO	MP0 interrupt fla	ng	

21.5.11 LETIMERn_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																												0	0	0	0	0
Access																												(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name																												REP1	REP0	UF	COMP1	COMPO

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	REP1	0	(R)W1	Clear REP1 Interrupt Flag
	Write 1 to clear the F (This feature must b			returns the value of the IF and clears the corresponding interrupt flags
3	REP0	0	(R)W1	Clear REP0 Interrupt Flag
	Write 1 to clear the F (This feature must be			returns the value of the IF and clears the corresponding interrupt flags
2	UF	0	(R)W1	Clear UF Interrupt Flag
	Write 1 to clear the l feature must be ena			turns the value of the IF and clears the corresponding interrupt flags (This
1	COMP1	0	(R)W1	Clear COMP1 Interrupt Flag
	Write 1 to clear the (This feature must be			ng returns the value of the IF and clears the corresponding interrupt flags
0	COMP0	0	(R)W1	Clear COMP0 Interrupt Flag
	Write 1 to clear the (This feature must be			ng returns the value of the IF and clears the corresponding interrupt flags

21.5.12 LETIMERn_IEN - Interrupt Enable Register

Offset															Ві	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	တ	8	7	9	5	4	က	2	_	0
Reset					•							•								•	•							0	0	0	0	0
Access																												₩ M	₩ M	RW W	₩ M	₩ M
Name																												REP1	REP0	UF	COMP1	COMPO

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4	REP1	0	RW	REP1 Interrupt Enable
	Enable/disable the RE	EP1 interrupt		
3	REP0	0	RW	REP0 Interrupt Enable
	Enable/disable the RE	EP0 interrupt		
2	UF	0	RW	UF Interrupt Enable
	Enable/disable the UF	= interrupt		
1	COMP1	0	RW	COMP1 Interrupt Enable
	Enable/disable the Co	OMP1 interrupt		
0	COMP0	0	RW	COMP0 Interrupt Enable
	Enable/disable the Co	OMP0 interrupt		

21.5.13 LETIMERn_SYNCBUSY - Synchronization Busy Register

Offset	Bit Position	
0x034	7 2 3 4 6 9 6 7 7 7 7 7 8 8 7 7 8 8 7 8 7 8 7 8 7 8	- 0
Reset		0
Access		<u>~</u>
Name		CMD

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	CMD	0	R	CMD Register Busy
	Set when the value w	ritten to CMD is	being synd	chronized.
0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

21.5.14 LETIMERn_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Bi	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset		'	'		'									'		'	•					•				•	'	•			0	0
Access																															Z.	RW
Name																															OUT1PEN	OUTOPEN

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	OUT1PEN	0	RW	Output 1 Pin Enable
	When set, output 1	of the LETIMER	R is enabled.	
	Value			Description
	0			The LETn_O1 pin is disabled
	1			The LETn_O1 pin is enabled
0	OUT0PEN	0	RW	Output 0 Pin Enable
	When set, output 0	of the LETIMER	R is enabled.	
	Value			Description
	0			The LETn_O0 pin is disabled
	1			The LETn_O0 pin is enabled

21.5.15 LETIMERn_ROUTELOC0 - I/O Routing Location Register

Offset															Bi	t Po	siti	on														
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Reset					•	•		•				•		•							Ç	0000		•		•			00	000		
Access																					2	<u>}</u>							<u> </u>	2		
Name																					<u> </u>	00 100							JO IOTI IO			

Bit	Name	Reset	Access	Description
31:14	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
13.8	OUT1LOC	0x00	RW	I/O Location

Decides the location of the LETIMER OUT1 pin.

Value	Mode	Description
0	LOC0	Location 0
1	LOC1	Location 1
2	LOC2	Location 2
3	LOC3	Location 3
4	LOC4	Location 4
5	LOC5	Location 5
6	LOC6	Location 6
7	LOC7	Location 7
8	LOC8	Location 8
9	LOC9	Location 9
10	LOC10	Location 10
11	LOC11	Location 11
12	LOC12	Location 12
13	LOC13	Location 13
14	LOC14	Location 14
15	LOC15	Location 15
16	LOC16	Location 16
17	LOC17	Location 17
18	LOC18	Location 18
19	LOC19	Location 19
20	LOC20	Location 20
21	LOC21	Location 21
22	LOC22	Location 22

Bit	Name	Reset Access	s Description
	23	LOC23	Location 23
	24	LOC24	Location 24
	25	LOC25	Location 25
	26	LOC26	Location 26
	27	LOC27	Location 27
	28	LOC28	Location 28
	29	LOC29	Location 29
	30	LOC30	Location 30
	31	LOC31	Location 31
7:6	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	OUT0LOC	0x00 RW	I/O Location
	Decides the location	of the LETIMER OUT0 pi	n.
	Value	Mode	Description
	0	LOC0	Location 0
	1	LOC1	Location 1
	2	LOC2	Location 2
	3	LOC3	Location 3
	4	LOC4	Location 4
	5	LOC5	Location 5
	6	LOC6	Location 6
	7	LOC7	Location 7
	8	LOC8	Location 8
	9	LOC9	Location 9
	10	LOC10	Location 10
	11	LOC11	Location 11
	12	LOC12	Location 12
	13	LOC13	Location 13
	14	LOC14	Location 14
	15	LOC15	Location 15
	16	LOC16	Location 16
	17	LOC17	Location 17
	18	LOC18	Location 18
	19	LOC19	Location 19
	20	LOC20	Location 20
	21	LOC21	Location 21
	22	LOC22	Location 22

t	Name	Reset	Access	Description
	23	LOC23		Location 23
	24	LOC24		Location 24
	25	LOC25		Location 25
	26	LOC26		Location 26
	27	LOC27		Location 27
	28	LOC28		Location 28
	29	LOC29		Location 29
	30	LOC30		Location 30
	31	LOC31		Location 31

21.5.16 LETIMERn_PRSSEL - PRS Input Select Register


	Bit Position											
0x020 E 8 8 8 2 8 8 2 8 8 2 8 8	r 4 w 7 - 0											
Reset 0 <th>0×0</th>	0×0											
Access & & & & & & & & & & & & & & & & & &	RW											
PRSCLEARMODE PRSSTARTMODE PRSSTOPMODE PRSSTOPSEL	PRSSTARTSEL											
Bit Name Reset Access Description												
31:28 Reserved To ensure compatibility with future devices, always write bits to 0. More informations	with future devices, always write bits to 0. More information in 1.2 Conven-											
27:26 PRSCLEARMODE 0x0 RW PRS Clear Mode												
Determines mode for PRS input clear.												
Value Mode Description	Description											
0 NONE PRS cannot clear the LETIMER												
1 RISING Rising edge of selected PRS input can clear the LE	TIMER											
2 FALLING Falling edge of selected PRS input can clear the LI	ETIMER											
3 BOTH Both the rising or falling edge of the selected PRS LETIMER	nput can clear the											
25:24 Reserved To ensure compatibility with future devices, always write bits to 0. More informations	nation in 1.2 Conven-											
23:22 PRSSTOPMODE 0x0 RW PRS Stop Mode	PRS Stop Mode											
Determines mode for PRS input stop.												
Value Mode Description												
0 NONE PRS cannot stop the LETIMER	PRS cannot stop the LETIMER											
1 RISING Rising edge of selected PRS input can stop the LE	TIMER											
2 FALLING Falling edge of selected PRS input can stop the LE	TIMER											
3 BOTH Both the rising or falling edge of the selected PRS LETIMER	Both the rising or falling edge of the selected PRS input can stop the LETIMER											
21:20 Reserved To ensure compatibility with future devices, always write bits to 0. More informations	nation in 1.2 Conven-											
19:18 PRSSTARTMODE 0x0 RW PRS Start Mode	PRS Start Mode											
Determines mode for PRS input start.												
Value Mode Description	Description											
0 NONE PRS cannot start the LETIMER												
	Rising edge of selected PRS input can start the LETIMER											

Bit	Name	Reset	Access	Description
	2	FALLING		Falling edge of selected PRS input can start the LETIMER
	3	вотн		Both the rising or falling edge of the selected PRS input can start the LETIMER
17:16	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:12	PRSCLEARSEL	0x0	RW	PRS Clear Select
	Determines which PR	RS input can clear	the LETII	MER.
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
11:10	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9:6	PRSSTOPSEL	0x0	RW	PRS Stop Select
	Determines which PR	RS input can stop t	the LETIN	MER.
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
-				

Bit	Name	Reset	Access	Description								
5:4	Reserved	To ensure comp tions	atibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
3:0	PRSSTARTSEL	0x0	RW	PRS Start Select								
	Determines which F	Determines which PRS input can start the LETIMER.										
	Value	Mode		Description								
	0	PRSCH0		PRS Channel 0 selected as input								
	1	PRSCH1		PRS Channel 1 selected as input								
	2	PRSCH2		PRS Channel 2 selected as input								
	3	PRSCH3		PRS Channel 3 selected as input								
	4	PRSCH4		PRS Channel 4 selected as input								
	5	PRSCH5		PRS Channel 5 selected as input								
	6	PRSCH6		PRS Channel 6 selected as input								
	7	PRSCH7		PRS Channel 7 selected as input								
	8	PRSCH8		PRS Channel 8 selected as input								
	9	PRSCH9		PRS Channel 9 selected as input								
	10	PRSCH10		PRS Channel 10 selected as input								
	11	PRSCH11		PRS Channel 11 selected as input								

22. CRYOTIMER - Ultra Low Energy Timer/Counter





Quick Facts

What?

The CRYOTIMER is a timer capable of providing wakeup events/interrupts after deterministic intervals in all energy modes, including EM4.

Why?

The CRYOTIMER enables the chip to remain in the lowest energy modes for long durations, while keeping track of time and being able to wake up at regular intervals, all with an absolute minimum current consumption.

How?

Using a counter running on a prescaled Low Frequency Oscillator, the CRYOTIMER can provide periodic wakeup events with a very wide period range.

22.1 Introduction

The CRYOTIMER is a 32 bit counter which operates on a low frequency oscillator, and is capable of running in all energy modes. It can provide periodic wakeup events and PRS signals which can be used to wake up peripherals from any energy mode. The CRYOTIMER provides a very wide range of periods for the interrupts facilitating flexible ultra-low energy operation.

Because of its simplicity, the CRYOTIMER is a lower energy solution for periodically waking up the MCU compared to the RTCC.

22.2 Features

- · 32 bit Counter
- · Works in all the energy modes
- · Only External and Power-On resets reset the CRYOTIMER
- · Interrupt/wake up event after deterministic intervals
- PRS Output
- · Debug mode
 - · Configurable to either run or stop when processor is stopped (break)

22.3 Functional Description

22.3.1 Block Diagram

An overview of the CRYOTIMER is shown in Figure 22.1 CRYOTIMER Block Overview on page 745.




Figure 22.1. CRYOTIMER Block Overview

22.3.2 Operation

The desired low frequency oscillator for the CRYOTIMER operation can be selected by using OSCSEL in CRYOTIMER_CTRL. The selection must be made before enabling the CRYOTIMER, and it must be ensured that the selected oscillator is ready. This can be checked by observing LFXORDY or LFRCORDY (depending upon the oscillator selection) in CMU_STATUS. Note that the ULFRCO is always ready.

By default the CRYOTIMER is held in reset. It can be started by setting EN in CRYOTIMER_CTRL. The CRYOTIMER, when running, is reset by clearing EN.

The timer counts at a frequency determined by PRESC in CRYOTIMER_CTRL. This value should be set before the CRYOTIMER is enabled. Setting PRESC to 0 gives the maximum resolution, while higher values allow longer periods, see Table 22.1 CRYOTIMER Resolution vs Maximum Wakeup Event/Interrupt Period, F_{CRYOCLK} = 32768 Hz on page 746.

The 32-bit Counter provides 32 different options for selecting the duration between the Wakeup events. The selected duration is specified by CRYOTIMER PERIODSEL. It should be configured before the CRYOTIMER is enabled.

$$T_{WU} = (2^{PRESC} \times 2^{PERIODSEL})/f_{CRYOCLK}$$

Figure 22.2. Duration Between the CRYOTIMER Wakeup Events in Seconds

Table 22.1. CRYOTIMER Resolution vs Maximum Wakeup Event/Interrupt Period, FCRYOCLK = 32768 Hz

CRYOTIMER_CTRL_PRESC	Resolution, 2PRESC/fcRYOCLK	Maximum Wakeup event/Interrupt Period
DIV1	30.5 µs	36.4 hours
DIV2	61 µs	72.8 hours
DIV4	122 µs	145.6 hours
DIV8	244 µs	12 days
DIV16	488 µs	24 days
DIV32	977 μs	48 days
DIV64	1.95 ms	97 days
DIV128	3.91 ms	194 days

The 32-bit counter value of the CRYOTIMER can be read using the CRYOTIMER_CNT register.

The PRS output pulses of the CRYOTIMER are 1 CRYOCLK clock cycle wide. However, if the PRESC and PERIODSEL are both set to 0, the width of these pulses will be half CRYOCLK time period.

The CRYOTIMER wakeup events set the flag in the CRYOTIMER_IF. Interrupt on this event can be enabled by using the CRYOTIM-ER_IEN register.

The CRYOTIMER is always reset by the External Pin and Power-On resets. Additionally, by using EMU_CTRL, it can also be configured to reset by Watchdog, lockup, and system request resets.

Note: The CRYOTIMER configuration bits/registers should only be changed when EN in CRYOTIMER_CTRL is cleared.

22.3.3 Debug Mode

When the CPU is halted in debug mode, the CRYOTIMER can be configured to either continue to run or to be frozen. This is configured using DEBUGRUN in CRYOTIMER CTRL.

22.3.4 Energy Mode Availability

The CRYOTIMER is available in all energy modes. Wakeup from EM2 Deep Sleep and EM3 Stop to EM0 Active can be performed using the regular interrupt as discussed in 22.3.2 Operation. To generate wakeup events during EM4 Hibernate/Shutoff, EM4WU in CRYOTIMER_EM4WUEN must be set to 1. Since the interrupt flag serves as the wakeup source, it must be cleared by software after exiting a low energy mode. Refer to 10. EMU - Energy Management Unit for details on how to configure the EMU.

22.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	CRYOTIMER_CTRL	RW	Control Register
0x004	CRYOTIMER_PERIODSEL	RW	Interrupt Duration
0x008	CRYOTIMER_CNT	R	Counter Value
0x00C	CRYOTIMER_EM4WUEN	RW	Wake Up Enable
0x010	CRYOTIMER_IF	R	Interrupt Flag Register
0x014	CRYOTIMER_IFS	W1	Interrupt Flag Set Register
0x018	CRYOTIMER_IFC	(R)W1	Interrupt Flag Clear Register
0x01C	CRYOTIMER_IEN	RW	Interrupt Enable Register

22.5 Register Description

22.5.1 CRYOTIMER CTRL - Control Register

Offset															Ri	t Po	eiti	on														
Oliset															וט	ιFU	SILI	UII														
0x000	33	30	59	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	∞	7	9	2	4	က	7	_	0
Reset						•												•								0x0			0x0	•	0	0
Access																										₩			Z		W.	M
Name																										PRESC			OSCSEL		DEBUGRUN	EN
Bit	Na	me					Re	set			Ac	cess	s [Des	crip	tion																
31:8	Re	serv	/ed				To tio		ure	com	pati	bility	wit	h fu	ture	dev	rices	s, al	way	'S WI	rite l	bits	to 0.	Мо	re in	forn	natio	on ii	1.2	Co.	nvei	7-
7:5	PF	RESC	0				0x0)			RW	1	F	res	scal	er S	ettii	ng														
	Th	ese	hits	sele	ect ti	he r	res	calin	a fa	ctor																						

These bits select the prescaling factor.

OSCSEL	0x0	RW	Select Low Frequency Oscillator
7	DIV128		LF Oscillator frequency divided by 128
6	DIV64		LF Oscillator frequency divided by 64
5	DIV32		LF Oscillator frequency divided by 32
4	DIV16		LF Oscillator frequency divided by 16
3	DIV8		LF Oscillator frequency divided by 8
2	DIV4		LF Oscillator frequency divided by 4
1	DIV2		LF Oscillator frequency divided by 2
0	DIV1		LF Oscillator frequency undivided
Value	Mode		Description

These bits select the low frequency oscillator for the CRYOTIMER operation. This field should be set after the oscillator to be selected is ready.

	Value	Mode		Description
	0	DISABLED		Output is driven low
	1	LFRCO		Select Low Frequency RC Oscillator
	2	LFXO		Select Low Frequency Crystal Oscillator
	3	ULFRCO		Select Ultra Low Frequency RC Oscillator
1	DEBUGRUN	0	RW	Debug Mode Run Enable
	Set this bit to enable	CRYOTIMER to	run in deb	ug mode.
0	EN	0	RW	Enable CRYOTIMER

Set this bit to start the CRYOTIMER. Clear this bit to reset the CRYOTIMER. This bit should be set after the oscillator to be selected is ready.

4:2

22.5.2 CRYOTIMER_PERIODSEL - Interrupt Duration

	_	•													
Offset				В	it Position					T					
0x004	31 28 29 31 26 27 28 29 26 29	23 24 25 25 25 25 25 25 25 25 25 25 25 25 25	2 8 5	7 3	15 4	13	12	9	တ ထ	~ «	ο ₁ ο	4 (2 3	- c	>
Reset													0x20		
Access													S.		
Name													PERIODSEL		
Bit	Name	Reset	Access	Descrip	otion										
31:6	Reserved	To ensure contions	npatibility v	vith future	e devices, a	always	s write i	bits to	0. Mc	ore info	rmatio	on in 1	1.2 Co	nven-	
5:0	PERIODSEL	0x20	RW	Interru	pts/Wakeu	p Eve	nts Pe	riod	Settin	g					
	Defines the duration b	etween the Inte	rrupts/Wak	eup ever	nts based o	n the	pre-sca	aled c	lock.						
	Value			Descrip	tion										
	0			Wakeup	event afte	er evei	y Pre-s	scaled	d clock	cycle.					
	1			Wakeup	event afte	er 2 Pr	e-scale	ed clo	ck cyc	les.					
	2			Wakeup	event afte	er 4 Pr	e-scale	ed clo	ck cyc	les.					
	3			Wakeup	event afte	er 8 Pr	e-scale	ed clo	ck cyc	les.					
	4			Wakeup	event afte	er 16 F	re-sca	led cl	ock cy	cles.					
	5			Wakeup	event afte	er 32 F	re-sca	led cl	ock cy	cles.					
	6			Wakeup	event afte	er 64 F	re-sca	led cl	ock cy	cles.					
	7			Wakeup	event afte	er 128	Pre-sc	aled o	clock c	ycles.					
	8			Wakeup	event afte	er 256	Pre-sc	aled o	clock c	ycles.					
	9			Wakeup	event afte	er 512	Pre-sc	aled o	clock c	ycles.					
	10			Wakeup	event afte	er 1k F	re-sca	led cl	ock cy	cles.					
	11			Wakeup	event afte	er 2k F	re-sca	led cl	ock cy	cles.					
	12			Wakeup	event afte	er 4k F	re-sca	led cl	ock cy	cles.					
	13			Wakeup	event afte	er 8k F	re-sca	led cl	ock cy	cles.					
	14			Wakeup	event afte	er 16k	Pre-sc	aled o	clock c	ycles.					
	15			Wakeup	event afte	er 32k	Pre-sc	aled o	clock c	ycles.					
	16			Wakeup	event afte	er 64k	Pre-sc	aled o	clock c	ycles.					
	17			Wakeup	o event afte	er 128	k Pre-s	caled	clock	cycles.	•				
	18			Wakeup	event afte	er 256	k Pre-s	caled	clock	cycles					
	19			Wakeup	o event afte	er 512	k Pre-s	caled	clock	cycles.					
	20			Wakeup	o event afte	er 1M	Pre-sca	aled c	lock c	ycles.					
	21			Wakeup	event afte	er 2M	Pre-sca	aled c	lock c	ycles.					
	22			Wakeup	o event afte	er 4M	Pre-sca	aled c	lock c	ycles.					

Bit	Name	Reset	Access	Description
	23			Wakeup event after 8M Pre-scaled clock cycles.
	24			Wakeup event after 16M Pre-scaled clock cycles.
	25			Wakeup event after 32M Pre-scaled clock cycles.
	26			Wakeup event after 64M Pre-scaled clock cycles.
	27			Wakeup event after 128M Pre-scaled clock cycles.
	28			Wakeup event after 256M Pre-scaled clock cycles.
	29			Wakeup event after 512M Pre-scaled clock cycles.
	30			Wakeup event after 1024M Pre-scaled clock cycles.
	31			Wakeup event after 2048M Pre-scaled clock cycles.
	32			Wakeup event after 4096M Pre-scaled clock cycles.
		,		

22.5.3 CRYOTIMER_CNT - Counter Value

Offset															Bi	t Pc	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	nnnnnnnn															
Access																٥	צ															
Name																Ė	5															

Bit	Name	Reset	Access	Description
31:0	CNT	0x00000000	R	Counter Value
	These bits hold the Co	ounter value.		

22.5.4 CRYOTIMER_EM4WUEN - Wake Up Enable

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																																0
Access																																₩ W
Name																																EM4WU

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
0	EM4WU	0	RW	EM4 Wake-up Enable
	Write 1 to enable wa	ke-up request, v	vrite 0 to dis	sable wake-up request.

22.5.5 CRYOTIMER_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	11	10	တ	8	7	9	5	4	က	2	_	0
Reset							•										•			•					•		•	•				0
Access																																2
Name																																PERIOD

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PERIOD	0	R	Wakeup Event/Interrupt
	Set when the Wakeu	ıp event/Interru	ot occurs.	

22.5.6 CRYOTIMER_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset																																0
Access																																×
Name																																PERIOD

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PERIOD	0	W1	Set PERIOD Interrupt Flag
	Write 1 to set the PE	RIOD interrupt t	flag	

22.5.7 CRYOTIMER_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																																0
Access																																(R)W1
Name																																PERIOD

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PERIOD	0	(R)W1	Clear PERIOD Interrupt Flag
	Write 1 to clear the		. •	ding returns the value of the IF and clears the corresponding interrupt flags


22.5.8 CRYOTIMER_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	11	10	6	∞	7	9	5	4	က	2	_	0
Reset					•																											0
Access																																ΑW
Name																																PERIOD

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co tions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	PERIOD	0	RW	PERIOD Interrupt Enable
	Enable/disable the P	ERIOD interrupt		

23. VDAC - Digital to Analog Converter





Quick Facts

What?

The VDAC is designed for low energy consumption, but can also provide very good performance. It can convert digital values to analog signals at up to 500 kilo samples/second with 12-bit accuracy.

Why?

The VDAC can be used to generate accurate analog signals for sound, sensors and other applications, using only a limited amount of energy.

How?

The VDAC can generate high-resolution analog signals while the MCU is operating at low frequencies and with low total power consumption. Using DMA and a timer, the VDAC can be used to generate waveforms without any CPU intervention. The VDAC is available down to Energy Mode 3.

23.1 Introduction

The Voltage Digital to Analog Converter (VDAC) can convert a digital value to an analog output voltage. The VDAC is fully differential rail-to-rail, with 12-bit resolution. It has two single ended output buffers which can be combined into one differential output. The VDAC may be used for a number of different applications such as sensor interfaces or sound output.

23.2 Features

- · 500 ksamples/s operation
- · Two single ended output channels
 - · Can be combined into one differential output
- Integrated prescaler with division factor selectable between 1-128
- · Selectable voltage reference
 - · Internal low noise 2.5 V
 - Internal low noise 1.25 V
 - · Internal low power 2.5 V
 - Internal low power 1.25 V
 - AVDD
 - · External Pin Reference
- · Conversion triggers
 - · Data write
 - · PRS input
 - · Refresh timer
 - LESENSE
- · Automatic refresh timer
 - · Selection from 16-64 DAC_CLK cycles
 - · Individual refresh enable for each channel
- · Interrupt generation on buffer empty or finished conversion
 - · Separate interrupt flags for each channel
- · PRS output pulse on finished conversion
 - · Separate line for each channel
- · DMA request on buffer empty
 - · Separate request for each channel
- · Support for offset and gain calibration
- · Output to dedicated pins or APORT bus
- · Internal connections to ADC and ACMP
- · Sine generation mode
- · Asynchronous clocking mode

23.3 Functional Description

An overview of the VDAC module is shown in the figure below.




Figure 23.1. VDAC Overview

23.3.1 Power Supply

The VDAC module power (V_{OPA}) is derived from the AVDD supply pin.

23.3.2 I/O Pin Considerations

The maximum usable analog signal that can be seen on external VDAC outputs depends on several factors: whether the signal is routed through the APORT, whether overvoltage is enabled, and on the IOVDD/AVDD supply voltages, as shown in the Table 23.1 Maximum Usable IO Voltage on page 755 table.

VDAC Pin Maximum IO Voltage (APORT Maximum IO Voltage (APORT Maximum IO Voltage (APORT UN-**USED** and **OVT** Enabled/ **UNUSED, OVT Enabled) USED**, OVT Disabled) Disabled) VDAC External VREF In-MIN(AVDD, IOVDD) MIN(AVDD, IOVDD) N/A puts **VDAC Outputs** MIN(AVDD, IOVDD) MIN(AVDD, IOVDD + 2 V) MIN(AVDD, IOVDD)

Table 23.1. Maximum Usable IO Voltage

23.3.3 Enabling and Disabling a Channel

A VDAC channel is enabled by writing 1 to the CHxEN and disabled by writing 1 to CHxDIS in VDACn_CMD. The channel enabled status can be read by polling the CHxENS bit in VDACn_STATUS. This bit will go high immediately following a write to CHxEN. After disabling a channel the CHxENS bit will stay high until the VDAC channel is completely disabled.

Software should configure the VDAC before enabling a channel. Software *must not* write to any of the following registers while *either* CH0ENS or CH1ENS are set:

- VDACn CTRL
- VDACn_CHxCTRL
- VDACn OPAxTIMER

A VDAC channel will not begin driving its output before it is enabled *and* has received a conversion trigger, see 23.3.4.3 Conversion Trigger. After a channel is enabled it will listen for trigger sources specified in TRIGMODE in VDACn_CHxCTRL. If TRIGMODE is set to SW, SWPRS or SWREFRESH and a value was written to CHxDATA or COMBDATA before enabling the channel a conversion will start immediately when the channel is enabled. When disabling a channel any pending triggers are flushed.

23.3.4 Conversions

The VDAC consists of two channels (channel 0 and 1) with separate 12-bit data registers (VDACn_CH0DATA and VDACn_CH1DATA). These can be used to produce two independent single ended outputs or the channel 0 register can be used to drive both outputs in differential mode. The VDAC supports two conversion modes: continuous and sample/off.

23.3.4.1 Continuous Mode

In continuous mode the VDAC channels will drive their outputs continuously with the data in the VDACn_CHxDATA registers. A channel is configured in continuous mode by programming the CONVMODE bitfield in VDACn_CHxCTRL to CONTINUOUS. This mode will maintain the output voltage and no manual refresh is needed.

In continuous mode the SETTLETIME field in VDACn OPAxTIMER should be programmed to zero to achive the maximum update rate.

23.3.4.2 Sample/Off Mode

In sample/off mode the VDAC will only drive the output for a limited time per conversion. A channel is configured in sample/off mode by programming the CONVMODE bitfield in VDACn_CHxCTRL to SAMPLEOFF. How long the channel should drive the output can be controlled by programming the SETTLETIME field in the VDACn_OPAxTIMER register. The VDAC will drive the output for SETTLE-TIME f_{DAC_CLK} cycles before tristating the output again (and therefore if SETTLETIME is set to zero, the output will never be driven when using sample/off mode).

23.3.4.3 Conversion Trigger

Conversions can only be done while a channel is enabled, see 23.3.3 Enabling and Disabling a Channel.

If TRIGMODE is programmed to SW, SWPRS or SWREFRESH a conversion can be started by writing to the VDACn_CHxDATA register. The data registers are also mapped to a combined data register, VDACn_COMBDATA, where the data values for both channels can be written simultaneously. Writing to this register will trigger all enabled channels.

If TRIGMODE is programmed to PRS or SWPRS, a conversion can be started by an incoming pulse on the PRS channel selected in PRSSEL in VDACn_CHxCTRL. The PRSASYNC bit in VDACn_CHxCTRL determines if the VDAC expects a PRS pulse coming from a synchronous or asynchronous PRS producer.

If TRIGMODE is programmed to REFRESH or SWREFRESH a conversion will start on an overflow of the internal refresh timer. See 23.3.10 Refresh Timer.

If TRIGMODE is programmed to LESENSE a conversion will start when the LESENSE block sends a request. This setting needs to be selected whenever the channel is under LESENE control.

23.3.4.4 PRS Triggers

PRS triggers can be used to set a constant sample frequency, for instance by using a TIMER. In order to get a jitter-free sample rate, set DACCLKMODE to SYNC, set the CH0PRESCRST bit and clear the PRSASYNC bit. Note that this is only possible for channel 0.

The PRSASYNC bit tells whether the VDAC expects a synchronous PRS producer or not. When this bit is cleared, the PRS pulse must come from a synchronous producer and HFPERCLK must be running (this clock is turned off in EM2 and below). When PRSASYNC is set, the corresponding PRS channels should also bet configued as asynchronous (see the PRS chapter).

When either DACCLKMODE is set to ASYNC or the PRSASYNC bit is set, the sample frequency cannot be guaranteed to be jitter-free with respect to the PRS pulses.

The PRS frequency should never be higher than 0.5 MHz (the fastest possible sample rate). In addition the PRS frequency should not be higher than f_{HFPERCLK}/12 (in synchronous mode). If the PRS frequency is set too high, some PRS pulses will be dropped and the output can jitter.

23.3.5 Reference Selection

These voltage references are available and are selected by programming the REFSEL field in VDACn CTRL.

- Internal 1.25 V Low Noise Bandgap Reference
- Internal 2.5 V Low Noise Bandgap Reference
- Internal 1.25 V Low Power Bandgap Reference
- · Internal 2.5 V Low Power Bandgap Reference
- AVDD

· External Pin

23.3.6 Warmup Time and Initial Conversion

When a channel is first enabled it needs to warm up. This is performed automatically during the first conversion. The time required to warm up depends on the programmed DRIVESTRENGTH field in VDACn_OPAx_CTRL. In Table 23.2 VDAC Warmup Time on page 757 the minimum WARMUPTIME field for each drive strength is specified. Software is responsible for programming the correct value to WARMUPTIME before enabling a channel. If the time is programmed too short, an undefined voltage may be output until the VDAC settles.

The CHxWARM bits in VDACn STATUS are set when the warmup period has completed.

A consequence of the warmup period is that in continuous mode, the first conversion might take longer than the following conversions. In order to make sure all samples have the same timing, perform a dummy conversion to make the VDAC settle to a known voltage first.

Table 23.2. VDAC Warmup Time

DRIVESTRENGTH	WARMUPTIME
0	100 μs
1	85 µs
2	8 µs
3	8 µs

23.3.7 Analog Output

The output selection for each VDAC channel is configured in the VDACn_OPAx_OUT registers. Each VDAC channel has its own main output pin, VDACn_OUTx, that can be enabled with MAINOUTEN. In addition, several alternate outputs can be selected. These are enabled by first setting ALTOUTEN and then setting the corresponding bit(s) in ALTOUTPADEN. The VDAC output can also be routed to APORT by setting APORTOUTEN and configuring the APORTOUTSEL field to select the desired APORT.

The VDAC outputs also have direct internal connections to ADCs and ACMPs. These outputs are always enabled and can be selected by configuring the input selection for the ADC/ACMP.

In sample/off mode the VDAC will only drive the output for the duration programmed in SETTLETIME (in VDACn_OPAx_TIMER register) for each incoming conversion trigger. In continuous mode the VDAC will continue to drive the output until the channel is disabled. However, note that also in this mode a conversion trigger is needed before the output is enabled. See 23.3.3 Enabling and Disabling a Channel and 23.3.4.3 Conversion Trigger.

23.3.8 Output Mode

The two VDAC channels can act as two separate single ended channels or be combined into one differential channel. This is selected through the DIFF bit in VDACn_CTRL.

23.3.8.1 Single Ended Output

When operating in single ended mode, the channel 0 output is on VDACn_OUT0 and the channel 1 output is on VDACn_OUT1. The output voltage can be calculated using Figure 23.2 VDAC Single Ended Output Voltage on page 757

V_{OUT} = V_{VDACn OUTx} - V_{SS}= V_{ref} x CHxDATA/4095

Figure 23.2. VDAC Single Ended Output Voltage

where CHxDATA is a 12-bit unsigned integer.

23.3.8.2 Differential Output

When operating in differential mode, both VDAC outputs are used. The differential conversion uses VDACn_CH0DATA as source. The positive output is on VDACn_OUT1 and the negative output is on VDACn_OUT0. Since the output can be negative, it is expected that

the data is written in 2's complement form with the MSB of the 12-bit value being the signed bit. The output voltage can be calculated using Figure 23.3 VDAC Differential Output Voltage on page 758:

V_{OUT} = V_{VDACn OUT1} - V_{VDACn OUT0} = V_{ref} x CH0DATA/2047

Figure 23.3. VDAC Differential Output Voltage

where CH0DATA is a 12-bit signed integer. The common mode voltage is $V_{ref}/2$.

When using differential mode, the user must make sure that both channels are set up identically. I.e. VDACn_CH0CTRL and VDACn_CH1CTRL must be programmed to identical values (with the exception that the PRSSEL bitfield is allowed to be programmed differently for usage together with the OUTENPRS feature). Similarly the user must program VDACn_OPA0TIMER and VDACn_OPA1TIMER to identical values.

23.3.9 Async Mode

The VDAC is default clocked from HFPERCLK, which is automatically turned off in EM2/3. In order to allow VDAC operation in EM2/3 an internal oscillator can be selected for the VDAC by setting the DACCLKMODE bitfield in VDACn_CTRL to ASYNC. Before entering EM2/3 software must make sure the channel is enabled first by polling CHxENS in VDACn_STATUS. Entering EM2/3 with an enabled VDAC channel while DACCLKMODE is set to SYNC is a programming error and will lead to EM23ERRIF getting set to 1.

In asynchronous mode both VDAC channels are not necessarily triggered synchronous to each other and therefore the user should not assume that e.g. PRS, refresh or VDACn_COMBDATA based conversion triggers are observed by both channels at the same time. In differential mode both channels will operate in lock step, even while using the asynchronous clocking mode.

23.3.10 Refresh Timer

The VDAC includes an internal refresh timer. The refresh timer is automatically started if a channel selects either REFRESH or SWRE-FRESH for TRIGMODE and the channel is enabled. The refresh timer will count the number of f_{DAC_CLK} cycles programmed in RE-FRESHPERIOD before wrapping and generating a conversion trigger.

23.3.11 Clock Prescaling

The VDAC has an internal clock prescaler, which can divide the input clock by any factor between 1 and 128, by setting the PRESC field in VDACn_CTRL. The resulting DAC_CLK is used by the converter core and the frequency is given by Figure 23.4 VDAC Clock Prescaling on page 758:

$$f_{DAC CLK} = f_{IN CLK} / (PRESC + 1)$$

Figure 23.4. VDAC Clock Prescaling

where f_{IN_CLK} is the input clock frequency. The f_{DAC_CLK} must be programmed to be at most 1 MHz. When the DACCLKMODE is set to SYNC, the input clock frequency is $f_{HFPERCLK}$. When DACCLKMODE is set to ASYNC, an internal 12Mhz oscillator is used. In this mode it is required that the PRESC field be program to 11 or higher.

The prescaler runs continuously when either of the channels are enabled. When running with a prescaler setting higher than 0, there will be an unpredictable delay from the time the conversion was triggered to the time the actual conversion takes place. This is because the conversions are controlled by the prescaled clock and the conversion can arrive at any time during a prescaled clock (DAC_CLK) period. A second reason for unpredictable delay between a trigger and the associated conversion is that the activity on one channel can impact whether the VDAC reference is warm or not and therefore it can impact whether warmup is required when using the other channel. The uncertainty related to the clock prescaler can be addressed by using CH0PRESCRST. If the CH0PRESCRST bit in VDACn_CTRL is set, the prescaler will be reset every time a conversion is triggered on channel 0. This leads to a predictable latency between channel 0 trigger and conversion (assuming the warmup sequence is deterministic as well). If channel 0 is used in continuous mode, the warmup sequence will only apply to its first conversion and software can use the CH0WARM status bit to determine if the VDAC has warmed up.

23.3.12 High Speed

The VDAC is able to do conversions up to 400 ksamples/s. In order to reach the maximum conversion rate it is recommended to configure the VDAC in the following way:

- 1. Make f_{DAC CLK} 1 Mhz
- 2. Set TRIGMODE to SW
- 3. Program SETTLETIME in OPAx_TIMER to 0

- Set up a DMA transfer from a buffer in RAM to CHxDATA
- 5. Set CONVMODE to CONTINUOUS

23.3.13 Sine Generation Mode

The VDAC contains an automatic sine-generation mode, which is enabled by setting the SINEMODE bit in VDACn_CTRL. In this mode, the VDAC data is overridden with a conversion data taken from a sine lookup table. The sine signal is controlled by the PRS line selected by CH0PRSSEL in VDACn_CH0CTRL. When the line is high, a sine wave will be produced. Each period, starting at 0 degrees, is made up of 16 samples and the frequency is given by Figure 23.5 VDAC Sine Generation on page 759. In case OUTENPRS equals 1, lowering the PRS line selected by CH0PRSSEL will reset the sine output to 0 degrees resulting in a voltage of Vref/2 on the output channel. In case OUTENPRS equals 0, lowering the PRS line selected by CH0PRSSEL will stop progress of the sine wave at the sample currently being output (and the sine will therefore not be reset to 0 degrees when raising the PRS line again).

$$f_{sine} = f_{HFPERCLK} / 32 x (PRESC + 1)$$

Figure 23.5. VDAC Sine Generation

Sine mode is supported only for the fastest configuration of the VDAC in continuous mode. Therefore the CONVMODE bitfield needs to be set to CONTINUOUS and the SETTLETIME bitfield in VDACn_OPAxTIMER need to be programmed to zero for the used channel(s) in order to use sine generation mode. The TRIGMODE bitfield needs to be programmed to PRS for any channel used for sine generation mode. The other trigger modes are not supported.

The SINE wave will be output on channel 0 and therefore requires that this channel is enabled by writing 1 to CH0EN in the VDACn_CMD register. If DIFF is set in VDACn_CTRL, the sine wave will be output on both channels, but inverted. Note that when OUTENPRS in VDACn_CTRL is set, the sine output will be reset to 0 degrees when the PRS line selected by CH1PRSSEL is low.




Figure 23.6. VDAC Sine Mode

23.3.14 Interrupt Flags

The VDAC has several interrupt flags, indicating state transitions and error conditions.

In addition to the VDAC interrupt flags the VDAC registers contain interrupt flags for the OPAMP modules. See The OPAMP chapter for more information on these flags.

23.3.14.1 Conversion Done

The Conversion Done (CHxCD) interrupt flags are set when a conversion is complete. The flags are set after a channel has driven the output with the new code for the time programmed in SETTLETIME in VDACn_OPAxTIMER.

23.3.14.2 Buffer Level

The Buffer Level (CHxBL) interrupt flags are set when there is space available in CHxDATA. These flags are initially set, get cleared when CHxDATA is written and set again when the value is used for a conversion.

23.3.14.3 Overflow/Underflow

If CHxDATA is written to while CHxBL is cleared, the channel overflow flag (CHxOF) will be set. If a new conversion is triggered (e.g. via PRS) before data is written to CHxDATA (CHxDATA is empty) the channel underflow flag (CHxUF) will be set.

23.3.14.4 EM2/3 Sleep Error

The VDAC can only operate in EM2/3 when DACCLKMODE is set to ASYNC. If EM2 or EM3 is entered while a channel is enabled and DACCLKMODE is set to SYNC the EM23ERRIF flag will be set.

23.3.15 PRS Outputs

The VDAC has two PRS outputs which will carry a one cycle (HFPERCLK) high pulse when the corresponding channel has finished a conversion. Only available when DACCLKMODE is set to SYNC.

23.3.16 DMA Request

Each channel sends a DMA request when there is space in the channel's data register (VDACn_CHxDATA). These registers are initially empty and also become empty every time a conversion is triggered. The request is cleared when VDACn_CHxDATA is written.

23.3.17 LESENSE Trigger Mode

The VDAC can be controlled by LESENSE by programming the TRIGMODE field in VDACn_CHxCTRL to LESENSE. In LESENSE mode the conversion data can come from either VDACn_CHxDATA registers or LESENSE registers, depending on the LESENSE configuration. The trigger events are also controlled by the LESENSE state machine. See the LESENSE chapter for more information.

23.3.18 Opamps

The VDAC includes a set of highly configurable opamps that can be accessed with the VDAC registers. OPA0 and OPA1 is used for the output stages of the two VDAC channels, but can be used as standalone opamps if the VDAC channels are not in use. Opamps with higher numbers are completely standalone. For a detailed description see the OPAMP chapter.

23.3.19 Calibration

The VDAC contains a calibration register, VDACn_CAL, where calibration values for both offset and gain correction can be written. The required (gain) calibration values depend on the chosen reference and on whether the main or alternative VDAC output is used. The Device Information page provides the required trim values depending on reference choice and output selection in the DEVINFO_VDACnMAINCAL, DEVINFO_VDACnALTCAL, and DEVINFO_VDACnCH1CAL locations.

The OPAMPs contain a calibration register, VDACn_OPAx_CAL, where calibration values for both offset and gain correction can be written. The required calibration settings depend on the chosen DRIVESTRENGTH. The required calibration values can be found in the Device Information pages. For a given OPAMP x, the calibration settings for DRIVESTRENGTH n can be found in DEVINFO_OPAx-CALn.

23.3.19.1 Channel 1 Calibration

For channel 1, the factory calibration values are only accurate for the main output. When using the alternative outputs or APORT, the error on the output may be larger than the data sheet values (even when loading values from DEVINFO_VDACn_ALTCAL). To get accurate output from channel 1, either use the main output or perform manual calibration.

23.3.19.2 Manual Calibration

To manually calibrate the VDAC:

- 1. Enable CH0 and CH1 in their desired modes
- 2. Set both channel outputs to 80% of full-scale by setting VDACn CHxDATA = 0xCCC
- 3. Measure CH0 output and sweep VDACn_CAL.GAINERRTRIM until the smallest calibration error is found
- 4. Measure CH1 output and sweep VDACn CAL.GAINERRTRIMCH1 until the smallest calibration error is found

The calibration error is given by

$$e = abs(V_{out}/(V_{REF} * 0.8) - 1)$$

Figure 23.7. Calibration Error

where V_{out} is the measured voltage at the pin and V_{REF} is the reference voltage.

Note that even if only CH1 is going to be used, the full calibration procedure should be followed. It is permissible to skip CH1 calibration if only CH0 is used. The following parameters influence the calibration. A change in any of these might require a re-calibration:

- VDACn CTRL.REFSEL
- VDACn OPAx OUT.MAINOUTEN
- VDACn_OPAx_OUT.ALTOUTEN
- VDACn_OPAx_CTRL.DRIVESTRENGTH

23.3.20 Warmup Mode

If the WARMUPMODE field in VDACn_CTRL is set to KEEPINSTANDBY, the VDAC keeps internal bias currents running between conversions. It does not reduce the startup time, but it can help reduce noise from the VDAC to other analog peripherals, like the ADC or ACMP.

23.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	VDACn_CTRL	RW	Control Register
0x004	VDACn_STATUS	R	Status Register
0x008	VDACn_CH0CTRL	RW	Channel 0 Control Register
0x00C	VDACn_CH1CTRL	RW	Channel 1 Control Register
0x010	VDACn_CMD	W1	Command Register
0x014	VDACn_IF	R	Interrupt Flag Register
0x018	VDACn_IFS	W1	Interrupt Flag Set Register
0x01C	VDACn_IFC	(R)W1	Interrupt Flag Clear Register
0x020	VDACn_IEN	RW	Interrupt Enable Register
0x024	VDACn_CH0DATA	RWH	Channel 0 Data Register
0x028	VDACn_CH1DATA	RWH	Channel 1 Data Register
0x02C	VDACn_COMBDATA	W	Combined Data Register
0x030	VDACn_CAL	RW	Calibration Register
0x0A0	VDACn_OPA0_APORTREQ	R	Operational Amplifier APORT Request Status Register
0x0A4	VDACn_OPA0_APORTCON- FLICT	R	Operational Amplifier APORT Conflict Status Register
0x0A8	VDACn_OPA0_CTRL	RW	Operational Amplifier Control Register
0x0AC	VDACn_OPA0_TIMER	RW	Operational Amplifier Timer Control Register
0x0B0	VDACn_OPA0_MUX	RW	Operational Amplifier Mux Configuration Register
0x0B4	VDACn_OPA0_OUT	RW	Operational Amplifier Output Configuration Register
0x0B8	VDACn_OPA0_CAL	RW	Operational Amplifier Calibration Register
0x0C0	VDACn_OPA1_APORTREQ	R	Operational Amplifier APORT Request Status Register
0x0C4	VDACn_OPA1_APORTCON- FLICT	R	Operational Amplifier APORT Conflict Status Register
0x0C8	VDACn_OPA1_CTRL	RW	Operational Amplifier Control Register
0x0CC	VDACn_OPA1_TIMER	RW	Operational Amplifier Timer Control Register
0x0D0	VDACn_OPA1_MUX	RW	Operational Amplifier Mux Configuration Register
0x0D4	VDACn_OPA1_OUT	RW	Operational Amplifier Output Configuration Register
0x0D8	VDACn_OPA1_CAL	RW	Operational Amplifier Calibration Register

23.5 Register Description

23.5.1 VDACn_CTRL - Control Register

Offset															Е	Bit P	ositi	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset	0			0			0) X					00X0										0x0			0	0	0				0
Access	R W			₽			i	≩ Y					M										X M			₩	₹	₩ M				RW
Name	DACCLKMODE			WARMUPMODE			1 1 1 1 1 1	XETXEVEN TEXTOO					PRESC										REFSEL			CHOPRESCRST	OUTENPRS	SINEMODE				DIFF

Bit	Name	Reset	Access	Description
31	DACCLKMODE	0	RW	Clock Mode
	Selects DAC clock so	ource from sync	hronous or	asynchronous - with respect to Peripheral Clock - clock source
	Value	Mode		Description
	0	SYNC		Uses HFPERCLK to generate DAC_CLK, DAC will run with static settings in EM2 in this mode
	1	ASYNC		Uses internal VDAC oscillator to generate DAC_CLK. DAC will be available in EM2
30:29	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
28	WARMUPMODE	0	RW	Warm-up Mode
	Select Warm-up Mod	e for DAC		
	Value	Mode		Description
	0	NORMAL		DAC is shut off after each sample off conversion
	1	KEEPINSTAI	NDBY	DAC is kept in standby mode between sample off conversions
27:26	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
25:24	REFRESHPERIOD	0x0	RW	Refresh Period

Select refresh counter period. A channel x will be refreshed with the period set in REFRESHPERIOD if the channel in VDACn_CHxCTRL has its TRIGMODE set to REFRESH or SWREFRESH.

Value	Mode	Description
0	8CYCLES	All channels with enabled refresh are refreshed every 8 DAC_CLK cycles
1	16CYCLES	All channels with enabled refresh are refreshed every 16 DAC_CLK cycles
2	32CYCLES	All channels with enabled refresh are refreshed every 32 DAC_CLK cycles

Bit	Name	Reset	Access	Description
	3	64CYCLES		All channels with enabled refresh are refreshed every 64 DAC_CLK cycles
23	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
22:16	PRESC	0x00	RW	Prescaler Setting for DAC Clock
	Selected DAC clock (DAC_CLK)	source (as selec	ted by DA0	CCLKMODE) is prescaled by PRESC+1 to generated DAC clock
	Value	Description		
	PRESC	Clock divisior PRESC+1.	n factor of	
15:11	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10:8	REFSEL	0x0	RW	Reference Selection
	Select reference			
	Value	Mode		Description
	0	1V25LN		Internal low noise 1.25 V bandgap reference
	1	2V5LN		Internal low noise 2.5 V bandgap reference
	2	1V25		Internal 1.25 V bandgap reference
	3	2V5		Internal 2.5 V bandgap reference
	4	VDD		AVDD reference
	6	EXT		External pin reference
7	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
6	CH0PRESCRST	0	RW	Channel 0 Start Reset Prescaler
	Select if prescaler (determining DAC	_CLK rate)	is reset on channel 0 start.
	Value			Description
	0			Prescaler not reset on channel 0 start
	1			Prescaler reset on channel 0 start
5	OUTENPRS	0	RW	PRS Controlled Output Enable
	Enable PRS Contro	ol of DAC output e	nable.	
	Value			Description
	0			DAC output enable always on
	1			DAC output enable controlled by PRS signal selected for CH1
4	SINEMODE	0	RW	Sine Mode
	Enable/disable sine	mode.		
	Value			Description

Bit	Name	Reset	Access	Description
	0			Sine mode disabled. Sine reset to 0 degrees
	1			Sine mode enabled
3:1	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	DIFF	0	RW	Differential Mode
	Select single en	ded or differential	mode.	
	Value			Description
	0			Single ended output
	1			Differential output

23.5.2 VDACn_STATUS - Status Register

Offset															Bi	t Po	ositi	on																
0x004	31	30	29	78	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	= :	9	6	ω	7	9	5	4		3	7	_	0
Reset			0	0			0	0			0	0			0	0												0	0	,	_	_	0	0
Access			œ	œ			22	œ			22	2			ď	<u>~</u>												2	2		צ	<u>~</u>	ന	<u>~</u>
Name			OPA10UTVALID	OPA0OUTVALID			OPA1WARM	OPA0WARM			OPA1ENS	OPA0ENS			OPA1APORTCONFLICT	OPA0APORTCONFLICT												CH1WARM	CHOWARM	0	CH1BL	CHOBL	CH1ENS	CHOENS
Bit	Na	me					Re	set			Ac	ces	s I	Desc	crip	tion	1																	
31:30	Re	serv	/ed				To tion		ure	com	oati	bility	v wit	th fu	ture	dev	vice	s, al	way	уѕ и	rite	bit	ts t	o 0.	Мо	re i	nfor	mati	on i	in 1	1.2	Cor	iver	7-
29	OF	PA10	DUT	VAL	_ID		0				R		(OPA	1 0	utp	ut V	/alic	l St	atu	S													
	OF	PA1	outp	ut is	s se	ttled	ext	erna	lly a	t the	loa	ad. lı	n PF	RS tr	rigge	erec	d mo	ode 1	this	sta	tus	fla	g is	no	t us	ed	anc	l ren	nain	s C)).			
28	OF	OPA0OUTVALID 0 R OPA0 Output Valid Status OPA0 output is settled externally at the load. In PRS triggered mode this status flag is not used (and remains 0).																																
	OPA0 output is settled externally at the load. In PRS triggered mode this status flag is not used (and remains 0).																																	
27:26	OPA0 output is settled externally at the load. In PRS triggered mode this status flag is not used (and remains 0). Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions															7-																		
25	OF	PA1V	VAR	RM			0				R		(OPA	1 W	arn	n St	atu	S															
	OF	PA1	is wa	arm	and	d out	put	is er	nabl	ed. I	n Pl	RS t	rigg	erec	d mo	de	this	stat	us	flag	is r	not	us	ed (anc	l rei	mair	ns 0)						
24		PA0V					0				R			OPA	-				_															
				arm	and	dout	-			ed. I															-			-						
23:22	Re	serv	/ed				To tion		ure	com	pati	bility	/ wit	th fu	ture	dev	vice	s, al	way	уѕ и	/rite	bit	ts t	o 0.	Мо	re i	nfor	mati	on i	in 1	1.2	Cor	iver	1-
21	OF	PA1E	ENS				0				R		(OPA	1 E	nab	led	Sta	tus	•														
		is bi			vhe	n OF	PA1	is e	nabl																									
20		PA0E					0				R		(OPA	0 E	nab	oled	Sta	tus	•														
40:40	_	is bi		set v	vhe	n OF					4:	L :1:4.		U- £	4	-1						<i>L</i> :		- 0				4:			1.0	0		_
19:18	Re	serv	/ea				tion		ure	com	oau	DIIITY	/ WII	n tu	ture	aeı	vice	s, aı	way	уѕи	rne	DI	is i	0 0.	IVIC	re i	nior	mau	on	n	1.2	Cor	iver	1-
17		PA1A ICT	APO	RTC	CON	1-	0				R		(OPA	1 B	us (Con	flic	t Oı	utpı	ut													
	1 it	fany	of t	the A	APC	DRT	s be	ing ı	equ	este	d by	y the	OF	PA1	are	alsc	be	ing	req	ues	ted	by	an	othe	er p	erip	hera	al.	_					
16		PA0A ICT	APO	RTC	CON	1-	0				R		(ОРА	0 B	us	Con	flic	t Oi	utpı	ut													_
	1 if	f any	of t	the A	APC	DRT	s be	ing ı	equ	este	d by	y the	OF	PA0	are	also	be	ing	req	ues	ted	by	an	othe	er p	erip	hera	al.						
15:6	Re	serv	red				To tion		ure	com	pati	bility	v wit	th fu	ture	dev	vice	s, al	way	уѕ и	rite	bit	ts t	o 0.	Мо	re i	nfor	mati	on	in 1	1.2	Cor	iver	7-

Bit	Name	Penet	A	Description
DIL	Name	Reset	Access	Description
5	CH1WARM	0	R	Channel 1 Warm
	This bit is set whe	n channel 1 is wa	arm.	
4	CH0WARM	0	R	Channel 0 Warm
	This bit is set whe	n channel 0 is wa	arm.	
3	CH1BL	1	R	Channel 1 Buffer Level
	This bit is set whe	n there is space	for new data i	in CH1DATA.
2	CH0BL	1	R	Channel 0 Buffer Level
	This bit is set whe	n there is space	for new data i	in CH0DATA.
1	CH1ENS	0	R	Channel 1 Enabled Status
	This bit is set whe	n channel 1 is er	nabled.	
0	CH0ENS	0	R	Channel 0 Enabled Status
	This bit is set whe	n channel 0 is er	nabled.	

23.5.3 VDACn_CH0CTRL - Channel 0 Control Register

Offset										Bi	t Po	sition												
0x008	30 31	3 8 1	27	25	73 74	22	20 23	19	18	17	16	5 4	13	12	7	9	o	ω ω	7	9 1	υ 4	3	7 7	- 0
Reset													0x0					0			 X			0
Access													Z.					Z ≷		i	≩ Y			Z S S
																	!	ပ္		l,	<u>ц</u>			
Name													PRSSEL					PRSASYNC		0	ו אופואוסטד			CONVMODE
Bit	Name			Rese	et		Acces	s	Des	crip	tion													
31:16	Reserved	1		To e		con	npatibilit	'y w	ith fu	ıture	dev	ices, a	always	s wri	te b	its to	o 0. N	Mor	e in	forma	ation i	n 1.2	Conv	en-
15:12	PRSSEL			0x0			RW		Cha	nne	I 0 P	RS T	iggei	r Sel	ect									
	Select Ch	nannel	0 PRS	S input	chanr	nel.																		
	Value	0 PRSCH0 PRS ch 0 triggers a conversion.																						
	0																							
	1		PRSCH1 PRS ch 1 triggers a conversion.																					
	2		PRSCH1 PRS ch 1 triggers a conversion. PRSCH2 PRS ch 2 triggers a conversion.																					
	3			PRS	СНЗ				PRS	S ch	3 triç	gers	a con	vers	ion.									
	4			PRS	CH4				PRS	S ch	4 trig	gers	a con	vers	ion.									
	5			PRS	CH5				PRS	S ch	5 trig	gers	a con	vers	ion.									
	6			PRS	CH6				PRS	S ch	6 triç	gers	a con	vers	ion.									
	7			PRS	CH7				PRS	S ch	7 triç	gers	a con	vers	ion.									
	8			PRS	CH8				PRS	S ch	8 trig	gers	a con	vers	ion.									
	9			PRS	CH9				PRS	S ch	9 triç	gers	a con	vers	ion.									
	10			PRS	CH10				PRS	S ch	10 tr	iggers	a co	nver	sion	١.								
	11			PRS	CH11				PRS	S ch	11 tr	iggers	a co	nver	sion	١.								
11:9	Reserved	1		To e		con	npatibilit	y w	ith fu	ıture	dev	ices, a	always	s wri	te b	its to	o 0. N	Mor	e in	forma	ation i	n 1.2	Conv	en-
8	PRSASY	NC		0			RW		Cha	nne	I 0 P	RS A	syncl	nron	ous	En	able							
	Set this b	it to 1 t	o trea	at PRS	chanr	nel a	is async	chro	nous	6														
7	Reserved	İ		To e		con	npatibilit	'y w	ith fu	ıture	dev	ices, a	always	s wri	te b	its to	o 0. N	Mor	e in	forma	ation i	n 1.2	Conv	ren-
6:4	TRIGMOI	DE		0x0			RW		Cha	nne	I 0 T	rigge	r Mod	le										
	Select Ch	nannel	0 con	versior	trigge	er.																		
	Value			Mod	e				Des	cript	ion													
	0			SW					Cha	nnel	l 0 is	trigge	red b	y Cŀ	HOD.	ATA	or C	CON	ИВС	ATA	write			
	1			PRS					Cha	nnel	l 0 is	trigge	red b	y PF	RS ir	nput								

Bit	Name	Reset	Access	Description
	2	REFRESH		Channel 0 is triggered by Refresh timer
	3	SWPRS		Channel 0 is triggered by CH0DATA/COMBDATA write or PRS input
	4	SWREFRESH		Channel 0 is triggered by CH0DATA/COMBDATA write or Refresh timer
	5	LESENSE		Channel 0 is triggered by LESENSE
3:1	Reserved	To ensure comp tions	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	CONVMODE	0	RW	Conversion Mode
	Configure convers	ion mode.		
	Value	Mode		Description
	0	CONTINUOUS		DAC channel 0 is set in continuous mode
	1	SAMPLEOFF		DAC channel 0 is set in sample/off mode
	· ·	<u> </u>		

23.5.4 VDACn_CH1CTRL - Channel 1 Control Register

Offset										Bit	t Po	sition												
0x00C	20 33	7 28 2	26 26	25	23	72	20 21	19	8	17	16	5 4	13	12	7	9	6	ω	7	0 r	o 4	က	7 7	- 0
Reset													0x0					0		9	e i			0
Access													Z Š					<u>%</u>		3	 } Y			Z N
																		ပ္		Ļ	<u> </u>			
Name													PRSSEL					PRSASYNC			ו אופואס מיסואים			CONVMODE
Bit	Name			Reset			Acces	s	Desc	crip	tion													
31:16	Reserved	1		To en	sure c	omp	oatibility	y WI	ith fui	ture	dev	ices, a	always	s wri	te b	its to	o 0. I	Mor	e in	forma	ition ii	n 1.2	Conv	en-
15:12	PRSSEL			0x0			RW		Cha	nne	I 1 P	RS T	iggei	r Se	lect									
	Select Ch	nannel 1	PRS	input c	hanne	el.																		
	Value	0 PRSCH0 PRS ch 0 triggers a conversion.																						
	0	·																						
	1		PRSCH1 PRS ch 1 triggers a conversion.																					
	2		PRSCH1 PRS ch 1 triggers a conversion. PRSCH2 PRS ch 2 triggers a conversion.																					
	3			PRSC	H3				PRS	ch :	3 triç	gers	a con	vers	ion.									
	4			PRSC	H4				PRS	ch 4	4 triç	gers	a con	vers	ion.									
	5			PRSC	H5				PRS	ch :	5 triç	gers	a con	vers	ion.									
	6			PRSC	H6				PRS	ch (6 triç	gers	a con	vers	ion.									
	7			PRSC	H7				PRS	ch	7 triç	gers	a con	vers	ion.									
	8			PRSC	H8				PRS	ch a	8 triç	gers	a con	vers	ion.									
	9			PRSC	H9				PRS	ch s	9 triç	gers	a con	vers	ion.									
	10			PRSC	H10				PRS	ch	10 tr	iggers	a co	nver	sion	١.								
	11			PRSC	H11				PRS	ch	11 tr	iggers	a co	nver	sion	١.								
11:9	Reserved	1		To en	sure c	omp	oatibility	y Wi	ith fu	ture	dev	ices, a	always	s wri	te b	its to	o 0. I	Mor	e in	forma	ition ii	n 1.2	Conv	en-
8	PRSASY	NC		0			RW		Cha	nne	I 1 P	RS A	syncl	hron	ous	En	able							
	Set this b	it to 1 to	trea	t PRS c	hanne	el as	async	hro	nous	i														
7	Reserved	1		To en	sure c	отр	oatibility	y Wi	ith fu	ture	dev	ices, a	always	s wri	te b	its to	o 0. I	Mor	e in	forma	ition ii	n 1.2	Conv	en-
6:4	TRIGMO	DE		0x0			RW		Chai	nne	I 1 T	rigge	r Mod	de										
	Select Ch	nannel 1	conv	ersion/	trigge	r.																		
	Value			Mode					Desc	cripti	ion													
	0			SW					Char	nnel	1 is	trigge	red b	у СН	H1D	ATA	or C	ON	ИВС	ATA	write			
	1			PRS					Char	nnel	1 is	trigge	red b	y PF	RS ir	nput								

Bit	Name	Reset	Access	Description
	2	REFRESH		Channel 1 is triggered by Refresh timer
	3	SWPRS		Channel 1 is triggered by CH1DATA/COMBDATA write or PRS input
	4	SWREFRESH		Channel 1 is triggered by CH1DATA/COMBDATA write or Refresh timer
	5	LESENSE		Channel 1 is triggered by LESENSE
3:1	Reserved	To ensure comp tions	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	CONVMODE	0	RW	Conversion Mode
	Configure convers	ion mode.		
	Value	Mode		Description
	0	CONTINUOUS		DAC channel 1 is set in continuous mode
	1	SAMPLEOFF		DAC channel 1 is set in sample/off mode

23.5.5 VDACn_CMD - Command Register

Offset	Bit Position			
0x010	33 4 4 5 6 6 7 8 8 8 9 9 9 10	ى د	4 <u>-</u>	0
Reset	0 0 0 0	0	0	0
Access		× ×		W
Name	PA0F PA1E	CH1DIS		CH0EN

Name	Reset	Access	Description
Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
OPA1DIS	0	W1	OPA1 Disable
Disables OPA1.			
OPA1EN	0	W1	OPA1 Enable
Enables OPA1			
OPA0DIS	0	W1	OPA0 Disable
Disables OPA0.			
OPA0EN	0	W1	OPA0 Enable
Enables OPA0			
Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
CH1DIS	0	W1	DAC Channel 1 Disable
Disables DAC Chann	nel 1		
CH1EN	0	W1	DAC Channel 1 Enable
Enables DAC Chann	el 1.		
CH0DIS	0	W1	DAC Channel 0 Disable
Disables DAC Chann	nel 0.		
CH0EN	0	W1	DAC Channel 0 Enable
Enables DAC Chann	el 0		
	Reserved OPA1DIS Disables OPA1. OPA1EN Enables OPA1 OPA0DIS Disables OPA0. OPA0EN Enables OPA0 Reserved CH1DIS Disables DAC Chann CH0DIS Disables DAC Chann CH0DIS Disables DAC Chann CH0DIS Disables DAC Chann	Reserved To ensure contions OPA1DIS OPA1DIS OPA1EN OPA1EN OPA0DIS OPA0DIS OPA0EN OPA0EN OPA0EN Enables OPA0 Enables OPA0 To ensure contions CH1DIS O Disables DAC Channel 1 CH1EN O Enables DAC Channel 1. CH0DIS O Disables DAC Channel 0.	Reserved To ensure compatibility of tions OPA1DIS OPA1DIS OPA1EN OPA1EN OPA0DIS OPA0DIS OPA0EN OPA0EN OPA0EN Enables OPA0 Reserved To ensure compatibility of tions CH1DIS OW1 Disables DAC Channel 1 CH0DIS OW1

23.5.6 VDACn_IF - Interrupt Flag Register

Offset														Bi	t Po	sitio	on														
0x014	30 31	29	78	27	26	25	24	23	22	7	20	19	18	17	16	15	4	13	12	7	10	2 0	0 00	7	9	2	4	က	2	_	0
Reset		0	0							0	0			0	0	0								-	-	0	0	0	0	0	0
Access		2	22							<u>~</u>	<u>~</u>			22	<u>~</u>	2								2	2	2	2	2	2	œ	Я
Name		OPA10UTVALID	OPA00UTVALID							OPA1PRSTIMEDERR	OPA0PRSTIMEDERR			OPA1APORTCONFLICT	OPA0APORTCONFLICT	EM23ERR								CH1BL	CH0BL	CH1UF	CH0UF	CH10F	CH00F	CH1CD	СНОСД
Bit	Name					Re	set			Ac	ces	S	Des	crip	tion																
31:30	Resen	/ed				To tior		ure	com	pati	bility	/ wi	th fu	ture	dev	vices	s, al	way	s w	rite	bits	to (0. M	ore ii	nfori	natio	on ir	1.2	? Co	nver	1-
29	OPA10	DUT	VAL	.ID		0				R			OPA	1 0	utp	ut V	alid	Int	terr	upt	Fla	g									
	OPA1	outp	ut is	set	tled	exte	erna	lly a	at the	e loa	ad																				
28	OPA0OUTVALID 0 R OPA0 Output Valid Interrupt Flag OPA0 output is settled externally at the load Page 1/20 Constitution of the control of th																														
	OPA0 output is settled externally at the load Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conv																														
27:22	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions														nver	7-															
21	OPA1F DERR	PRS	TIM	E-		0				R			OPA	1 P	RS	Trig	ger	Мо	de	Erre	or lı	nter	rupt	Fla	g						
	Indicat	es th	nat i	n TI	MED) PF	RS tı	rigge	ered	mo	de,	the	nega	ative	ed	ge o	f the	e PF	RS	puls	e ca	ame	bef	ore t	he C	PA	outp	out v	vas	valid	l
20	OPA0F DERR		TIM	E-		0				R			OPA	\0 P	RS	Trig	ger	Мо	de	Erre	or lı	nter	rupt	Fla	g						
	Indicat	es th	nat i	n TI	MED) PF	RS tı	rigge	ered	mo	de,	the	nega	ative	ed	ge o	f the	e PF	RS	puls	е са	ame	bef	ore t	he C	PA	outp	out v	vas	valid	l
19:18	Resen	/ed				To tior		ure	com	pati	bility	/ Wi	th fu	ture	dev	vices	s, al	way	s w	rite	bits	to (0. M	ore ii	nforr	natio	on ir	1.2	? Co	nver	7-
17	OPA1A FLICT	APO	RTC	CON	-	0				R			OPA	1 B	us (Con	flict	t Ou	ıtpı	ıt In	terr	upt	Fla	g							
	1 if any	of t	the A	APO	RTs	s bei	ing r	equ	este	d b	y the	e Ol	PA1	are	alsc	bei	ng r	requ	uest	ted b	оу а	notl	her p	erip	hera	I.					
16	OPA0/ FLICT	APO	RTC	CON	-	0				R			OPA	(0 B	us (Con	flict	t Ou	ıtpı	ıt In	terr	upt	Fla	g							
	1 if any	of t	the A	APO	RTs	s bei	ing r	equ	este	d b	y the	e Ol	PA0	are	alsc	bei	ng r	requ	uest	ted b	оу а	notl	her p	erip	hera	I.					
15	EM23E	ERR				0				R			EM2	/3 E	ntry	/ Er	ror	Flag	g												
	Set wh	en g	going	g to	EM2	2/3 v	while	DA	ACC	_KN	10D	Еe	qual	s S	/NC	and	dac	char	nne	l is e	enal	oled	l								
14:8	Reserv	/ed				To tior		ure	com	pati	bility	y wi	th fu	ture	dev	vices	s, al	way	s w	rite	bits	to	0. M	ore ii	nforr	natio	on ir	1.2	? Co	nver	7-
7	CH1BL	-				1				R			Cha	nne	I 1 E	Buff	er L	eve	el In	iterr	upt	Fla	ıg								_
	Indicat	es s	pace	e av	ailat	ole i	n Cl	H1D	ATA	١.																					

Bit	Name	Reset	Access	Description
6	CH0BL	1	R	Channel 0 Buffer Level Interrupt Flag
	Indicates space	available in CH0D	ATA.	
5	CH1UF	0	R	Channel 1 Data Underflow Interrupt Flag
	Indicates chann	el 1 data underflow	<i>I</i> .	
4	CH0UF	0	R	Channel 0 Data Underflow Interrupt Flag
	Indicates chann	el 0 data underflow	<i>I</i> .	
3	CH1OF	0	R	Channel 1 Data Overflow Interrupt Flag
	Indicates chann	el 1 data overflow.		
2	CH0OF	0	R	Channel 0 Data Overflow Interrupt Flag
	Indicates chann	el 0 data overflow.		
1	CH1CD	0	R	Channel 1 Conversion Done Interrupt Flag
	Indicates chann	el 1 conversion co	mplete.	
0	CH0CD	0	R	Channel 0 Conversion Done Interrupt Flag
	Indicates chann	el 0 conversion co	mplete.	

23.5.7 VDACn_IFS - Interrupt Flag Set Register

23.3.7 V	DAOII_II 0 -		iiup	,	ug O		gist	.																					
Offset	SSTIMEDERR W1 0 SSTIMEDERR W1 0 SORTCONFLICT W1 0 W1 0 W1 0 W1 0 W1 0 W1 0																												
0x018	Name Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions OPA10UTVALID O W1 Set OPA10UTVALID Interrupt Flag Write 1 to set the OPA10UTVALID interrupt flag OPA1PRSTIME- O W1 Set OPA1PRSTIMEDERR Interrupt Flag OPA0PRSTIMEDERR Interrupt Flag													1	0														
Reset	0	0	'		<u>'</u>		•	0	0			0	0	0			•							0	0	0	0	0	0
Access	W1	W						W	W1			X	M	W1										X	W W	W M	W M	W1	W
Name	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Control of the control														CH00F	CH1CD	СНОСД												
Bit	Name				Rese	et		Ac	ces	s C	Desc	ript	tion																
31:30	Name Reset Access Description Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Cortions OPA1OUTVALID 0 W1 Set OPA1OUTVALID Interrupt Flag Write 1 to set the OPA1OUTVALID interrupt flag Write 1 to set the OPA0OUTVALID interrupt flag Write 1 to set the OPA0OUTVALID interrupt flag Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Cortions OPA1PRSTIME-DERR 0 W1 Set OPA1PRSTIMEDERR Interrupt Flag														nvei	า-													
29	OPA1OUT\	OPA1OUTVALID 0 W1 Set OPA1OUTVALID Interrupt Flag Write 1 to set the OPA1OUTVALID interrupt flag																											
	OPA1OUTVALID 0 W1 Set OPA1OUTVALID Interrupt Flag Write 1 to set the OPA1OUTVALID interrupt flag OPA0OUTVALID 0 W1 Set OPA0OUTVALID Interrupt Flag																												
28	Write 1 to set the OPA1OUTVALID interrupt flag OPA0OUTVALID 0 W1 Set OPA0OUTVALID Interrupt Flag																												
	Write 1 to s	OPA1OUTVALID 0 W1 Set OPA1OUTVALID Interrupt Flag Write 1 to set the OPA1OUTVALID interrupt flag OPA0OUTVALID 0 W1 Set OPA0OUTVALID Interrupt Flag																											
27:22	Reserved						con	npati	bility	/ witl	h fut	ure	dev	rices	s, alv	vays	s wr	ite b	its t	0 0.	Моі	re in	forn	natio	on in	1.2	Co	nvei	7-
21		ΓIΜE	Ξ-		0			W1		S	Set C	PA	1PI	RST	IME	DEI	RR I	Inte	rrup	t Fla	ag								
	Write 1 to s	et th	ne O	PA1	PRS	TIME	DEF	RR ir	nterr	upt f	lag																		
20		TIME	Ξ-		0			W1		S	Set C	PA	(OPI	RST	IME	DEI	RR I	Inte	rrup	t Fla	ag								
	Write 1 to s	et th	ne O	PAC	PRS	TIME	DEF	RR ir	nterr	upt f	lag																		
19:18	Reserved				To ei tions		con	npati	bility	/ witl	h fut	ure	dev	rices	s, alv	vays	s wr	ite b	its t	0 0.	Моі	re in	forn	natio	on in	1.2	Col	nvei	7-
17	OPA1APOF FLICT	RTC	ON-		0			W1		S	Set C	PA	1A	POF	RTC	ONF	LIC	T Ir	iteri	upt	Fla	g							
	Write 1 to s	et th	ne O	PA1	APO	RTC	ONF	LIC	Γint	errup	ot fla	g																	
16	OPA0APOF FLICT	RTC	ON-	•	0			W1		S	Set C	PA	\0A	POF	RTC	ONF	FLIC	T Ir	iteri	upt	Fla	g							
	Write 1 to s	et th	ne O	PA0)APO	RTC	ONF	LIC	Γ int	errup	ot fla	g																	
15	EM23ERR				0			W1		S	Set E	M2	3EF	RR I	nter	rup	t Fla	ag											
	Write 1 to s	et th	ne E	M23	ERR	inter	rupt	flag																					

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

Set CH1UF Interrupt Flag

tions

W1

0

Write 1 to set the CH1UF interrupt flag

Reserved

CH1UF

14:6

5

Bit	Name	Reset	Access	Description
4	CH0UF	0	W1	Set CH0UF Interrupt Flag
	Write 1 to set t	he CH0UF interrupt	flag	
3	CH1OF	0	W1	Set CH1OF Interrupt Flag
	Write 1 to set t	he CH1OF interrupt	flag	
2	CH0OF	0	W1	Set CH0OF Interrupt Flag
	Write 1 to set t	he CH0OF interrupt	flag	
1	CH1CD	0	W1	Set CH1CD Interrupt Flag
	Write 1 to set t	he CH1CD interrupt	flag	
0	CH0CD	0	W1	Set CH0CD Interrupt Flag
	Write 1 to set t	he CH0CD interrupt	flag	

23.5.8 VDACn_IFC - Interrupt Flag Clear Register

Offset														Bi	t Po	siti	on														
0x01C	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	2	4	က	7	_	0
Reset		0	0							0	0			0	0	0										0	0	0	0	0	0
Access		(R)W1	(R)W1							(R)W1	(R)W1			(R)W1	(R)W1	(R)W1										(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
		R	(K)							<u>R</u>	<u>R</u>					ਨ										<u>R</u>	ਨ)	ਨ)	ਨ)	R)	<u>R</u>
Name		OPA10UTVALID	OPA00UTVALID							OPA1PRSTIMEDERR	OPA0PRSTIMEDERR			OPA1APORTCONFLICT	OPA0APORTCONFLICT	EM23ERR										CH10F	CH0UF	CH10F	CH00F	CH1CD	СНОСД
Bit	Name					Res	set			Acc	cess	s [Desc	rip	tion																
31:30	Reser	ved				To tion		ure	com	oatii	bility	/ wit	h fut	ure	dev	vices	s, al	way	's w	rite i	bits	to 0.	Мо	re in	form	natio	on in	1.2	Col	nver	7-
29	OPA1	OUT	VAL	_ID		0				(R)	W1	C	Clea	r O	PA1	OU.	TVA	ALID) In	terrı	ıpt l	Flag									
	Write rupt fla															eturr	ns th	ne v	alu	e of	the I	IF ar	nd cl	ears	the	cor	resp	onc	ding	inte	r-
28																															
	OPA0OUTVALID 0 (R)W1 Clear OPA0OUTVALID Interrupt Flag Write 1 to clear the OPA0OUTVALID interrupt flag. Reading returns the value of the IF and clears the corresponding in rupt flags (This feature must be enabled globally in MSC.). Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Con														inte	r- 															
27:22	Reser	ved				To tion		ure	com	oatii	bility	/ wit	h fut	ure	dev	vices	s, al	way	's w	rite i	bits	to 0.	Мо	re in	form	atic	on in	1.2	Col	nver	7-
21	OPA1I DERR		TIM	E-		0				(R)	W1	(Clea	r O	PA1	PR	STIN	MED	ER	RR In	terr	upt	Flaç	9							
	Write interru																retu	ırns	the	valu	ie o	f the	IF a	and o	clea	rs th	ie co	orres	spor	din	9
20	OPA0I DERR		TIM	E-		0				(R)	W1	C	Clea	r O	PA0	PR	STIN	MED	DER	RR In	terr	upt	Flaç	9							
	Write interru																retu	ırns	the	valu	ie o	f the	IF a	and o	clea	s th	ie co	orres	spor	din	9
19:18	Reser	ved				To tion		ure	com	oatii	bility	/ wit	h fut	ure	dev	vices	s, al	way	's w	rite i	bits	to 0.	Мо	re in	form	natio	on in	1.2	Col	nver	7-
17	OPA1/ FLICT		RTO	CON	1-	0				(R)	W1	C	Clea	r O	PA1	AP	ORT	ГСО	NF	LICT	「 Int	erru	ıpt F	lag							
	Write ing into																	etur	ns t	the v	alue	of t	he I	F an	ıd cl	ears	the	cor	resp	onc	-
16	OPA0, FLICT		RTC	CON	I -	0				(R)	W1	C	Clea	r O	PA0	AP	ORT	гсо	NF	LICT	「 Int	erru	ıpt F	lag							
	Write ing into																	etur	ns t	the v	alue	of t	he I	F an	ıd cl	ears	the	cor	resp	onc	-
15	EM23I	ERR				0				(R)	W1	C	Clea	r El	V123	ERF	R In	terr	upt	Fla	g										
	Write flags (etu	rns t	the v	valu	e of	f the	e IF a	and	clea	rs th	ie co	rres	por	nding	gint	erru	pt	

Bit	Name	Reset	Access	Description
14:6	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	CH1UF	0	(R)W1	Clear CH1UF Interrupt Flag
		he CH1UF interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
4	CH0UF	0	(R)W1	Clear CH0UF Interrupt Flag
		he CH0UF interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
3	CH1OF	0	(R)W1	Clear CH1OF Interrupt Flag
		he CH1OF interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
2	CH0OF	0	(R)W1	Clear CH0OF Interrupt Flag
		he CH0OF interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
1	CH1CD	0	(R)W1	Clear CH1CD Interrupt Flag
		he CH1CD interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .
0	CH0CD	0	(R)W1	Clear CH0CD Interrupt Flag
		he CH0CD interru st be enabled glob		ng returns the value of the IF and clears the corresponding interrupt flags .

23.5.9 VDACn_IEN - Interrupt Enable Register

Offset														Bi	t Po	sitio	on														
0x020	30	59	78	27	56	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	- w	_	9	5	4	က	2	_	0
Reset	17 17	0	0		, ,	1,,	,,,	' '	,,	0	0			0	0	0			1					0	0	0	0	0	0	0	0
Access		§ §	Z.							ZW W	X ≪			RW	X X	RW								\ N	Z.	Z.	X N	% §	W.	RW	RW
		I CE	I.E.							IY.	ir.					I.								I.C.	I.C.	I.E.	LE.	II.	ir.	ir.	<u> </u>
Name		OPA10UTVALID	OPA00UTVALID							OPA1PRSTIMEDERR	OPA0PRSTIMEDERR			OPA1APORTCONFLICT	OPA0APORTCONFLICT	EM23ERR								CH1BL	CH0BL	CH1UF	CH0UF	CH10F	CH00F	СН1СD	СНОСБ
Bit	Name					Re	eset			Ac	ces	s I	Des	crip	tion																
31:30	Reserv	/ed				To tio		sure	com	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/S WI	rite k	oits t	to C	. Мс	re ir	forn	natio	on in	1.2	Co	nver	7-
29	OPA10	DUT	VAL	.ID		0				RV	/	(OPA	10	UTV	'ALI	D In	iter	rupt	Ena	able)									
	Enable	/disa	able	the	OP	PA10	TUC	VAL	.ID ir	nteri	upt																				
28	OPA0OUTVALID 0 RW OPA0OUTVALID Interrupt Enable Enable/disable the OPA0OUTVALID interrupt																														
	Enable/disable the OPA0OUTVALID interrupt Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conv																														
27:22	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions														nver	1-															
21	OPA1F DERR	PRS	TIM	E-		0				RV	/	(OPA	1PF	RST	IME	DEI	RR	Inte	rrup	t Er	nab	le								
	Enable	disa/	able	the	e OP	A1F	PRS	TIM	EDE	RR	inte	rrup	ot																		
20	OPA0F DERR	PRS	TIM	E-		0				RV	/		OPA	0PF	RST	IME	DEI	RR	Inte	rrup	t Er	nab	le								
	Enable	disa/	able	the	OP	PA0F	PRS	TIM	EDE	RR	inte	rrup	ot																		
19:18	Reserv	⁄ed					ens ns	sure	com	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/S WI	rite k	oits t	to C	. Мс	re ir	nforn	natio	on in	1.2	Co	nver	7-
17	OPA1A FLICT	APO	RTO	CON	1 -	0				RV	/		OPA	1AI	POF	RTC	ONF	LIC	CT Ir	nteri	rupt	Er	abl	e							
	Enable	/disa	able	the	OP	PA1A	APO	RTC	CON	FLIC	CT ii	nter	rupt																		
16	OPA0A FLICT	APO	RTO	CON	1 -	0				RV	/	(OPA	(A)	POR	RTC	ONF	FLIC	CT Ir	nteri	rupt	Er	abl	9							
	Enable	/disa	able	the	OP	PA0A	APO	RTC	CON	FLIC	CT ii	nter	rupt																		
15	EM23E	RR				0				RV	/		EM2	3EF	RR I	nter	rup	t Er	nabl	е											
	Enable	/disa	able	the	e EM	123E	ERR	inte	rrup	t																					
14:8	Reserv	/ed				To tio		sure	com	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/s wi	rite k	oits t	to C	. Мс	re ir	nforn	natio	on in	1.2	Co	nver	1-
7	CH1BL	-				0				RV	/		CH1	BL	Inte	rrup	ot E	nab	le												
	Enable	/disa	able	the	e CH	I1BL	_ into	errup	ot																						

Di4	Nama	Poort	A	Description	
Bit	Name	Reset	Access	Description	
6	CH0BL	0	RW	CH0BL Interrupt Enable	
	Enable/disable	e the CH0BL interrupt			
5	CH1UF	0	RW	CH1UF Interrupt Enable	
	Enable/disable	the CH1UF interrupt			
4	CH0UF	0	RW	CH0UF Interrupt Enable	
	Enable/disable	the CH0UF interrupt			
3	CH1OF	0	RW	CH1OF Interrupt Enable	
	Enable/disable	the CH1OF interrupt			
2	CH0OF	0	RW	CH0OF Interrupt Enable	
	Enable/disable	the CH0OF interrupt			
1	CH1CD	0	RW	CH1CD Interrupt Enable	
	Enable/disable	the CH1CD interrupt			
0	CH0CD	0	RW	CH0CD Interrupt Enable	
	Enable/disable	e the CH0CD interrupt			

23.5.10 VDACn_CH0DATA - Channel 0 Data Register

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	1	0
Reset		00800																														
Access																										ם, ארם						
Name																										\ \ \ \	<u> </u>					

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11:0	DATA	0x800	RWH	Channel 0 Data
	This register contains	the value which	will be co	nverted by DAC channel 0.

23.5.11 VDACn_CH1DATA - Channel 1 Data Register

Offset															Bi	t Po	siti	on													
0x028	31	30	29	28	27	26	25	24	23	22	21	20	9	8	17	16	15	41	13	12	7	10	6	8	7	9	5	4	က	2	- c
Reset														•	•				•					•	•	000	008X0		·	·	·
Access																											I A Y				
Name																										F	DAIA				

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure co tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11:0	DATA	0x800	RWH	Channel 1 Data
	This register contains	the value which	h will be co	nverted by DAC channel 1.

23.5.12 VDACn_COMBDATA - Combined Data Register

Offset															Bi	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	8	7	9	2	4	က	2	_	0
Reset	et 08 00 00 00 00 00 00 00 00 00 00 00 00																															
Access										>	}															}	>					
Name										OH1DATA	K															VENDOLIN	K 140000					

Bit	Name	Reset	Access	Description
31:28	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
27:16	CH1DATA	0x800	W	Channel 1 Data
	Data written to this re	egister will be w	ritten to DA	TA in VDACn_CH1DATA.
15:12	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
11:0	CH0DATA	0x800	W	Channel 0 Data
	Data written to this re	egister will be w	ritten to DA	TA in VDACn_CH0DATA.

23.5.13 VDACn_CAL - Calibration Register

20.0.10						J. u.																										
Offset															Bi	it Po	siti	on														
0x030	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset														d	XX C						Ç	OXZO									0x4	
Access														i	≩ Ƴ						2	<u>}</u>									₽	
Name															GAINERKI KIMCHI							GAINERKI KIIVI									OFFSETTRIM	
Bit	Na	me					Re	set			Ac	ces	s	Des	crip	tior																
31:20	Re	serv	/ed				To tio		ure	COI	npat	ibilit	y wi	ith fu	ıture	de	/ices	s, al	way	's WI	rite k	oits	to 0.	Мо	re ir	nforr	nati	on i	in 1.2	2 Co	nver	7-
19:16	GΑ	INE	RR	TRII	MCH	11	0x	8			RV	٧		Gai	n Er	ror	Trin	ı Va	lue	for	CH	1										
											ror tr hose					grar	n wi	th D	evio	ce In	ıforn	nati	on v	alue	fou	ınd i	n D	EVI	N-			
15:14	Re	serv	/ed				To tio		ure	COI	npat	ibilit	y wi	ith fu	ıture	de	/ices	s, al	way	'S WI	rite k	oits	to 0.	Мо	re ir	nfori	nati	ion i	in 1.2	2 Co	nver	7-
13:8	GA	INF	RR	TRII	М		0x:	20			RV	V		Gai	n Fr	ror	Trin	ı Va	lue													

This register contains the fine gain error trim for CH0 and coarse gain error trim for CH1. Program with Device Information value found in DEVINFO_VDACnMAINCAL or DEVINFO_VDACnALTCAL depending on chosen reference and choice of main versus alternative output usage.

7:3	Reserved	To ensur	e compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	OFFSETTRIM	0x4	RW	Input Buffer Offset Calibration Value

This register contains the DAC input buffer offset calibration value. Program with Device Information value found in DDE-VINFO_VDACnCH1CAL.

23.5.14 VDACn_OPAx_APORTREQ - Operational Amplifier APORT Request Status Register

Offset															Ві	it Po	siti	on														
0x0A0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	← c	_ >
Reset					•									•				•					0	0	0	0	0	0	0	0		
Access																							R	2	~	22	2	22	22	2		
Name																							APORT4YREQ	APORT4XREQ	APORT3YREQ	APORT3XREQ	APORT2YREQ	APORT2XREQ	APORT1YREQ	APORT1XREQ		

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9	APORT4YREQ	0	R	1 If the Bus Connected to APORT4Y is Requested
	Reports if the bus co	nnected to APOI	RT4Y is be	ing requested from the APORT
8	APORT4XREQ	0	R	1 If the Bus Connected to APORT4X is Requested
	Reports if the bus co	nnected to APOI	RT4X is be	ing requested from the APORT
7	APORT3YREQ	0	R	1 If the Bus Connected to APORT3Y is Requested
	Reports if the bus co	nnected to APOI	RT3Y is be	ing requested from the APORT
6	APORT3XREQ	0	R	1 If the Bus Connected to APORT3X is Requested
	Reports if the bus co	nnected to APOI	RT3X is be	ing requested from the APORT
5	APORT2YREQ	0	R	1 If the Bus Connected to APORT2Y is Requested
	Reports if the bus co	nnected to APOI	RT2Y is be	ing requested from the APORT
4	APORT2XREQ	0	R	1 If the Bus Connected to APORT2X is Requested
	Reports if the bus co	nnected to APOI	RT2X is be	ing requested from the APORT
3	APORT1YREQ	0	R	1 If the Bus Connected to APORT1X is Requested
	Reports if the bus co	nnected to APOI	RT1X is be	ing requested from the APORT
2	APORT1XREQ	0	R	1 If the Bus Connected to APORT2X is Requested
	Reports if the bus co	nnected to APOI	RT2X is be	ing requested from the APORT
1:0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

23.5.15 VDACn_OPAx_APORTCONFLICT - Operational Amplifier APORT Conflict Status Register

Offset															Bi	it Po	siti	on														
0x0A4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset				•				•															0	0	0	0	0	0	0	0		
Access																							R	2	22	22	22	22	22	2		
Name																							APORT4YCONFLICT	APORT4XCONFLICT	APORT3YCONFLICT	APORT3XCONFLICT	APORT2YCONFLICT	APORT2XCONFLICT	APORT1YCONFLICT	APORT1XCONFLICT		

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9	APORT4YCONFLICT	0	R	1 If the Bus Connected to APORT4Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT4Y is is a	also being requested by another peripheral
8	APORT4XCONFLICT	0	R	1 If the Bus Connected to APORT4X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT4X is is a	also being requested by another peripheral
7	APORT3YCONFLICT	0	R	1 If the Bus Connected to APORT3Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT3Y is is a	also being requested by another peripheral
6	APORT3XCONFLICT	0	R	1 If the Bus Connected to APORT3X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT3X is is a	also being requested by another peripheral
5	APORT2YCONFLICT	0	R	1 If the Bus Connected to APORT2Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT2Y is is a	also being requested by another peripheral
4	APORT2XCONFLICT	0	R	1 If the Bus Connected to APORT2X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT2X is is a	also being requested by another peripheral
3	APORT1YCONFLICT	0	R	1 If the Bus Connected to APORT1X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1X is is a	also being requested by another peripheral
2	APORT1XCONFLICT	0	R	1 If the Bus Connected to APORT1X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1X is is a	also being requested by another peripheral
1:0	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

23.5.16 VDACn_OPAx_CTRL - Operational Amplifier Control Register

23.5.16	VDA	Cn_	UPA	4X_(CIR	(L -	Ope	erati	ona	II AI	npıı	Tier	Cor	itro	ı Ke	gist	er														
Offset															Bi	t Po	siti	on													
0x0A8	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	- 0
Reset		•				•	•				0	0		•		0		•		Š	OX O		0	0		•	•	0	_	-	0x2
Access											₩ M	R M				Σ				2	<u>}</u>		₩ M	R M M				₩	₩ M	W M	A W
Name											APORTYMASTERDIS	APORTXMASTERDIS				PRSOUTMODE					TROOF		PRSMODE	PRSEN				OUTSCALE	HCMDIS	INCBW	DRIVESTRENGTH
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion															
31:22	Re	sen	/ed				To		ure	con	npati	ibility	y wi	th fu	ture	de	vices	s, alı	way:	s wr	ite k	oits t	to 0.	Мо	re ir	forn	natio	on ir	1.2	2 Co	nven-

Bit	Name	Reset	Access	Description
31:22	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
21	APORTYMASTER- DIS	0	RW	APORT Bus Master Disable

Determines if the OPAx will request the APORT bus Y with POSSEL, NEGSEL or APORTOUTSEL. This bit allows multiple APORT connected devices to monitor the same APORT bus simultaneously by allowing the OPAx to not master the selected bus. When 1, the determination is expected to be from another peripheral, and the OPAx only passively looks at the bus. When 1, the selection of channel for a selected bus is ignored (the bus is not), and is whatever selection the external device mastering the bus has configured for the APORT bus.

1	Bus mastering disabled
0	Bus mastering enabled
Value	Description

20 APORTXMASTER- 0 RW **APORT Bus Master Disable** DIS

Determines if the OPAx will request the APORT bus X with POSSEL, NEGSEL or APORTOUTSEL. This bit allows multiple APORT connected devices to monitor the same APORT bus simultaneously by allowing the OPAx to not master the selected bus. When 1, the determination is expected to be from another peripheral, and the OPAx only passively looks at the bus. When 1, the selection of channel for a selected bus is ignored (the bus is not), and is whatever selection the external device mastering the bus has configured for the APORT bus.

	Value			Description								
	0			Bus mastering enabled								
	1 Bus mastering disabled											
19:17	7 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions											
16	PRSOUTMODE	TMODE 0		OPAx PRS Output Select								
	Selects OPAx Outp	ut to PRS.										
	Value	Mode		Description								
	0	WARM		Warm status available on PRS. Warm status indicates that opamp is warm and output is enabled.								

Value 0 1 2 3 4 5 6 7 8 9 10 11 9 PRSMODE PRS trigger m Value 0 1		
13:10 PRSSEL Select Channel Value 0 1 2 3 4 5 6 7 8 9 10 11 9 PRSMODE PRS trigger m Value 0 1 1 8 PRSEN Select OPAx of Value 0 1	OUTVALID	Outvalid status available on PRS. Outvalid status indicates that opamp output is settled externally at the load.
Select Channel Value	To ensure compa	ibility with future devices, always write bits to 0. More information in 1.2 Conven-
Value 0 1 2 3 4 5 6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	0x0 R\	OPAx PRS Trigger Select
0 1 2 3 4 5 6 7 8 9 10 11 9 PRSMODE PRS trigger m Value 0 1 1 8 PRSEN Select OPAx of Value 0 1	0 PRS input channel.	
1 2 3 4 5 6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 1 Select OPAx of Value 0 1 1	Mode	Description
2 3 4 5 6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 Value 0 Value 0 1	PRSCH0	PRS ch 0 triggers OPA.
3 4 5 6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH1	PRS ch 1 triggers OPA.
4	PRSCH2	PRS ch 2 triggers OPA.
5 6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH3	PRS ch 3 triggers OPA.
6 7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH4	PRS ch 4 triggers OPA.
7 8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH5	PRS ch 5 triggers OPA.
8 9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH6	PRS ch 6 triggers OPA.
9 10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH7	PRS ch 7 triggers OPA.
10 11 PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH8	PRS ch 8 triggers OPA.
PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH9	PRS ch 9 triggers OPA.
PRSMODE PRS trigger m Value 0 1 PRSEN Select OPAx of Value 0 1	PRSCH10	PRS ch 10 triggers OPA.
PRS trigger m Value 0 1 8 PRSEN Select OPAx of Value 0 1	PRSCH11	PRS ch 11 triggers OPA.
Value 0 1 PRSEN Select OPAx of Value 0 1	0 R\	OPAx PRS Trigger Mode
O 1 PRSEN Select OPAx of Value 0 1	ode of OPA.	
PRSEN Select OPAx of Value 0 1	Mode	Description
PRSEN Select OPAx of Value 0 1	PULSED	PULSED trigger is considered a regular asynchronous pulse that starts OPA warmup sequence. The end of warmup sequence is controlled by timeout settings in OPAxTIMER.
Value 0 1	TIMED	TIMED trigger is considered a pulse long enough to provide OPA warmup sequence. The end of warmup sequence is controlled by negative edge of the pulse.
Value 0 1	0 RI	√ OPAx PRS Trigger Enable
0	onversion trigger.	
1		Description
		OPAx is triggered by OPAxEN
7:5 Reserved		OPAx is triggered by PRS input
r.o Reserved	To ensure compa	ibility with future devices, always write bits to 0. More information in 1.2 Conven
4 OUTSCALE	0 RI	Scale OPAx Output Driving Strength

Bit	Name	Reset	Access	Description								
	Value	Mode		Description								
	0	FULL		Select this for full output driving strength.								
	1	HALF		Select this for half output driving strength.								
3	HCMDIS	1	RW	High Common Mode Disable								
				il-to-rail on input, while output still remains rail-to-rail. The input voltage to etween VSS and VDD-1.2V. Setting this bit improves output linearity when								
2	INCBW	1	RW	OPAx Unity Gain Bandwidth Scale								
	Unity gain bandwidth scale.											
	Value			Description								
	0			No scaling								
	1			When set the unity gain bandwidth will be scaled by factor of 2.5. useful to make OPA operate faster for closed-loop gain setting greater than 3x.								
1:0	DRIVESTRENGTH	0x2	RW	OPAx Operation Mode								
	Selects OPAx operat	ion mode.										
	Value			Description								
	0			Lower accuracy with Low drive strength.								
	1			Low accuracy with Low drive strength.								
	2			High accuracy with High drive strength.								
	3			Higher accuracy with High drive strength.								

23.5.17 VDACn_OPAx_TIMER - Operational Amplifier Timer Control Register

			_•.	<i>,</i>			٦,	J			P				•••			9.00															
Offset															Bi	it Po	siti	on															
0x0AC	.3	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	41	13	12	1 4	=	10	6	8	7	9	5	4	3	2	_	0
Reset								0x001								0x07								0000									
Access								RW													2	<u>></u>					RW						
Name			SETTLETIME															TANT TO THE							STARTUPDLY								
Bit	N	ame)				Re	eset			Ac	ces	s	Des	crip	tion																	
31:26	R	ese	rved				To tio	ens ns	ure	con	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/s v	vrite	e bi	its t	o 0.	Мс	re i	nfori	natio	on ir	1.2	2 Co	nve	n-
25:16	S	ETT	LET	IME			0x	0x001 RW OPAx Outp						ut S	ıt Settling Timeout Value																		
	Ν	umb	er of	f clo	ck c	ycle	s to	drive	e the	e ou	tput																						
15	R	ese.	rved				To tio	ens ns	ure	con	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/S V	vrite	e bi	its t	o 0.	Мс	re i	nforr	natio	on ir	1.2	2 Co	nve	n-
14:8	V	/ARI	MUP	TIM	E		0x	07			RV	/		OPA	X W	Varn	nup	Tim	ne (Cou	ınt '	Va	lue										
	0	PAx	war	mup	tim	eout	val	lue																									
7:6	R	ese	rved				To tio	ens ns	ure	con	pati	bilit	y wi	th fu	ture	dev	vices	s, al	way	/S V	vrite	bi	its t	o 0.	Мс	re i	nforr	natio	on ir	1.2	2 Co	nve	n-
5:0	S	TAR	RTUP	DLY	1		0x	00			RV	/		OPA	x S	tart	up [Dela	ıy C	ou	nt \	۷al	ue										

OPAx startup delay in us. Used only in PRS sample of mode of stand alone opamp.

23.5.18 VDACn_OPAx_MUX - Operational Amplifier Mux Configuration Register

Offset			Bit Position											
0x0B0	31 30 29 28 27	2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2	0 1 2 3 3 4 5 5 6 7 8 8 8 7 9 9 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1											
Reset		0×0	0x6 0xF1											
Access		X X												
Name		RESSEL	NEGSEL POSSEL											
Bit	Name	Reset Acces	Access Description											
31:27	Reserved	To ensure compatibili tions	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions											
26:24	RESSEL	0x0 RW	RW OPAx Resistor Ladder Select											
	Configures the resi	stor ladder tap for OPAx.												
	Value	Mode	Resistor Value											
	0	RES0	R2 = 1/3 x R1											
	1	RES1	R2 = R1											
	2	RES2	R2 = 1 2/3 x R1											
	3	RES3	R2 = 2 1/5 x R1											
	4	RES4	R2 = 3 x R1											
	5	RES5	R2 = 4 1/3 x R1											
	6	RES6	R2 = 7 x R1											
	7	RES7	R2 = 15 x R1											
23:21	Reserved	To ensure compatibili tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-											
20	GAIN3X	1 RW	OPAx Dedicated 3x Gain Resistor Ladder											
	Selects gain of 3x.													
	Value		Description											
	0		Disables 3x gain ladder.											
	1		Enables and sets the gain to 3x. If this is set to 1, RESSEL will only be used externally by other opamps. By default this is set to 1 for dac to work properly. For stand alone opamp and to configure gain based on RESSEL value, users need to configure this to 0.											
19	Reserved	To ensure compatibili tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-											
18:16	RESINMUX	0x6 RW	OPAx Resistor Ladder Input Mux											
	These bits selects	the source for the input mu	ux to the resistor ladder											
	Value	Mode	Description											
	0	DISABLE	Set for Unity Gain											

Bit	Name	Reset	Access	Description								
	1	OPANEXT		Set for NEXTOUT(x-1) input								
	2	NEGPAD		NEG pad connected								
	3	POSPAD		POS pad connected								
	4	COMPAD		Neg pad of OPA0 connected. Direct input to support common reference. OPA0 and OPA1 Resmux connected to form fully differential instrumentation amplifier.								
	5	CENTER										
	6	VSS		VSS connected								
5:8	NEGSEL	0xF2	RW	OPAx Inverting Input Mux								
	These bits selects the	he source for the	put on OPAx									
	Mode	Value		Description								
	APORT1YCH1	48		Select APORT1YCH1								
	APORT1YCH3	49		Select APORT1YCH3								
	APORT1YCH5	50		Select APORT1YCH5								
	APORT1YCH31	63		Select APORT1YCH31								
	APORT2YCH0	80		Select APORT2YCH0								
	APORT2YCH2	81		Select APORT2YCH2								
	APORT2YCH4	82		Select APORT2YCH3								
	APORT2YCH30	95		Select APORT2YCH30								
	APORT3YCH1	112		Select APORT3YCH1								
	APORT3YCH3	113		Select APORT3YCH3								
	APORT3YCH5	114		Select APORT3YCH5								
	APORT3YCH31	127		Select APORT3YCH31								
	APORT4YCH0	144		Select APORT4YCH0								
	APORT4YCH2	145		Select APORT4YCH2								
	APORT4YCH4	146		Select APORT4YCH4								
	APORT4YCH30	159		Select APORT4YCH30								
	DISABLE	240		Input disabled								
	UG	241		Unity Gain feedback path								
	OPATAP	242		OPAxTAP as input								
	NEGPAD	243		Input from NEG PAD								
7:0	POSSEL	0xF1	RW	OPAx Non-inverting Input Mux								

Bit	Name	Reset Access	Description
	Mode	Value	Description
	APORT1XCH0	32	Select APORT1XCH0
	APORT1XCH2	33	Select APORT1XCH2
	APORT1XCH4	34	Select APORT1XCH4
	APORT1XCH30	47	Select APORT1XCH30
	APORT2XCH1	64	Select APORT2XCH1
	APORT2XCH3	65	Select APORT2XCH3
	APORT2XCH5	66	Select APORT2XCH5
	APORT2XCH31	79	Select APORT2XCH30
	APORT3XCH0	96	Select APORT3XCH0
	APORT3XCH2	97	Select APORT3XCH2
	APORT3XCH4	98	Select APORT3XCH4
	APORT3XCH30	111	Select APORT3XCH30
	APORT4XCH1	128	Select APORT4XCH1
	APORT4XCH3	129	Select APORT4XCH3
	APORT4XCH5	130	Select APORT4XCH5
	APORT4XCH31	143	Select APORT4XCH31
	DISABLE	240	Input disabled
	DAC	241	DAC as input
	POSPAD	242	POS PAD as input
	OPANEXT	243	NEXTOUT(x-1) as input. For OPA0 not applicable.
	OPATAP	244	OPAxTAP as input. For OPA2 OPA0TAP.

23.5.19 VDACn_OPAx_OUT - Operational Amplifier Output Configuration Register

Offset				Bit Po	sition											
0x0B4	31 30 29 27 27 26	25 24	22 23 23	10 12 19 19	7 7 7	12 13	9 19	8 / 4	ο ro 4	က	2	1	0			
Reset			00x0							0	0	0	_			
Access			A W					\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \		\ \ \ \ \	W.	RW	₩ M			
										<u> </u>		ır.	<u>rr</u>			
Name			APORTOUTSEL					2 0 4 1		SHORT	APORTOUTEN	ALTOUTEN	MAINOUTEN			
Bit	Name	Reset	Access	Description												
31:24	Reserved	To ens	ure compatibility (with future dev	rices, al	ways write	bits to 0.	More info	rmation i	n 1.2	? Coi	nver	7-			
23:16	APORTOUTSEL	0x00	RW	OPAx APOI	RT Out	out										
	Select APORT output															
	Mode	Value	alue Description													
	APORT1YCH1	48		Select APORT1YCH1												
	APORT1YCH3	49		Select APO	RT1YCH	13										
	APORT1YCH5	50		Select APO												
	APORT1YCH31	63		Select APORT1YCH31												
	APORT2YCH0	80		Select APORT2YCH0												
	APORT2YCH2	81		Select APORT2YCH2												
	APORT2YCH4	82		Select APORT2YCH3												
	APORT2YCH30	95		Select APORT2YCH30												
	APORT3YCH1	112		Select APORT3YCH1												
	APORT3YCH3	113		Select APORT3YCH3												
	APORT3YCH5	114		Select APORT3YCH5												
	APORT3YCH31	127		Select APO	RT3YCH	131										
	APORT4YCH0	144		Select APO	RT4YCH	10										
	APORT4YCH2	145		Select APO	DRT4YCH2											
	APORT4YCH4	146		Select APORT4YCH4												
	APORT4YCH30	159 Select APORT4YCH30														
15:9	Reserved	To ens	ure compatibility (with future dev	rices, al	ways write	bits to 0.	More info	rmation i	n 1.2	? Coi	nver	7-			

Dia	Name	Doort	A	Description
Bit	Name	Reset	Access	Description
8:4	ALTOUTPADEN	0x00	RW	OPAx Output Enable Value
	Set to enable output	t, clear to disable	output	
	OUT ENABLE	VALUE		Description
	OUT0	xxxx1		Alternate Output 0
	OUT1	xxx1x		Alternate Output 1
	OUT2	xx1xx		Alternate Output 2
	OUT3	x1xxx		Alternate Output 3
	OUT4	1xxxx		Alternate Output 4
3	SHORT	0	RW	OPAx Main and Alternative Output Short
	Set this to short circ	uit main and alte	rnative outp	outs. This will keep the outputs shorted even when the VDAC is disabled.
2	APORTOUTEN	0	RW	OPAx Aport Output Enable
	Set this to enable ap	oort output of OP	Ax.	
1	ALTOUTEN	0	RW	OPAx Alternative Output Enable
	Set this to enable al	ternative output	of OPAx.	
0	MAINOUTEN	1	RW	OPAx Main Output Enable
	Set this to enable m	ain output of OP	Ax.	

23.5.20 VDACn_OPAx_CAL - Operational Amplifier Calibration Register

Offset															В	it P	osi	tion													
0x0B8	31	30	o c	27	26	25	24	33	2	22	27	3 5	19	18	17	16	15	4	13	12	11	10	6	8	7	9	5	4	cr.	2	- 0
Reset			0	000					(00x0					0X0			0x4			0	OXO				0x2				7	Š
Access	RW						i	₩ X					S N			¥ S			i	≥ Y				8		RW.					
Name			N L U U U U						(OFFSETP					GM3			W O				CM3				CM2				(<u> </u>
Bit	Na	me				Re	ese	t		1	Acce	ss	Į	De	scrip	otio	n														
31	Re	served	1			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	ite l	bits t	o 0.	Мо	re i	nfoi	mati	on ii	n 1.	2 Co	nven-
30:26	OF	FSETN	١			0x	00			ı	RW		(OP	Ax I	nve	rtir	ıg In	put	Offs	et C	Conf	igur	atio	on \	/alı	ıe				
		s regis ge (DE'																								d fro	m D	evic	e Ir	nform	ation
25	Re	served	'			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	ite l	bits t	o 0.	Мо	re i	nfoi	mati	on ii	n 1.	2 Co	nven-
24:20	OF	FSETF	>			0x	00			ı	RW		(OP	Ax N	Non-	-In	/erti	ng lı	nput	Off	set	Con	fig	ura	tion	Val	ue			
		s regis ormatio																											froi	m De	vice
19	Re	served	'			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	rite l	bits t	o 0.	Мо	re i	nfoi	mati	on ii	n 1.	2 Co	nven-
18:17	GM	13				0x	0			ı	RW		(Gn	ı3 Tı	rim '	Val	ue													
		n trim c ge (DE'																								ed '	from	Dev	/ice	Infor	mation
16	Re	served	'			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	rite l	bits t	o 0.	Мо	re i	nfoi	mati	on ii	n 1.	2 Co	nven-
15:13	GN	1				0x4	4			ı	RW		(Gn	Tri	m V	alu	е													
	obt	n trim v ained f ENGTI	fror																												
12	Re	served	'			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	ite l	bits t	o 0.	Мо	re i	nfoi	rmati	on ii	n 1.	2 Co	nven-
11:10	CN	13				0x	0			ı	RW		(Со	mpe	nsa	tio	n Ca	ір Сі	m3	rim	Val	ue								
		ogram v osen Di						fron	n C)evi	e Inf	orn	nat	tior	n pag	ge (I)E	/INF	:O_C)PA:	кСА	Ln) d	depe	endi	ing	on (APC	MP	nur	nber	and
9	Re	served	1			To tio		sure	e c	отр	atibil	ity	wit	th f	uture	e de	vic	es, a	lway	'S WI	ite l	bits t	o 0.	Мо	re i	nfoi	mati	on ii	n 1.	2 Co	nven-
											RW						tio														

Program with value obtained from Device Information page (DEVINFO_OPAxCALn) depending on OPAMP number and

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

Reserved

4


chosen DRIVESTRENGTH.

tions

Bit	Name	Reset	Access	Description			
3:0	CM1	0x7	RW	Compensation Cap Cm1 Trim Value			
	Program with value obtained from Device Information page (DEVINFO_OPAxCALn) depending on OPAMP number and chosen DRIVESTRENGTH.						

24. OPAMP - Operational Amplifier





Quick Facts

What?

The opamps are low power amplifiers with a high degree of flexibility targeting a wide variety of standard opamp application areas. With flexible gain and interconnection built-in, they can be configured to support multiple common opamp functions. All pins are available externally for filter configurations. Each opamp has a rail-to-rail input and a rail-to-rail output.

Why?

The opamps are included not only to save energy on a PCB compared to standalone opamps but also to reduce system cost by replacing external opamps.

How?

Two of the opamps are made available as part of the VDAC, while the other opamps are standalone. In addition to popular differential-to-single ended and differential-to-differential driver modes, an ADC unity gain buffer mode configuration makes it possible to isolate kickback noise. The opamps can also be configured as a multi-step cascaded PGA, and for all of the built-in modes no external components are necessary.

24.1 Introduction

The opamps are highly configurable general purpose opamps, suitable for simple filters and buffer applications. The 2 opamps can be configured to support various operational amplifier functions through a network of muxes with possibilities of selecting ranges of on-chip non-inverting and inverting gain configurations and selecting between outputs to various destinations. The opamps can also be configured with external feedback in addition to supporting cascade connections between two or three opamps. The opamps are rail-to-rail in and out. A user selectable mode has been added to optimize linearity, in which case the input voltage to the opamp is restricted to a range between VSS and AVDD-1.2V.

24.2 Features

- · 2 individually configurable opamps
- · Opamps support rail-to-rail inputs and outputs
- · Supports the following functions
 - · General opamp mode
 - · Voltage follower unity gain
 - · Inverting input PGA
 - · Non-inverting PGA
 - · Cascaded inverting PGA
 - · Cascaded non-inverting PGA
 - · Two opamp differential amplifier
 - · Three opamp differential amplifier
 - · Dual buffer ADC driver
- · Programmable gain
- · Programmable drive strength
- · Programmable start delay, warmup and settle time
- · Connection to APORT
- · Enable / Disable via PRS

· Output status to PRS

24.3 Functional Description

The 2 opamps can be configured to perform various opamp functions through a network of muxes. An overview of the opamps are shown in Figure 24.1 OPAMP System Overview on page 797. Two of the 2 opamps are part of the VDAC, while the others are standalone. The outputs of the opamps can be routed to the ADC and ACMP. All 2 opamps can also take input from pins. Since OPA0 and OPA1 are part of the VDAC, special considerations needs to be taken when both VDAC channel 0/channel 1 and OPA0/OPA1 are used. For detailed explanation, refer to 24.3.5 Opamp VDAC Combination.




Figure 24.1. OPAMP System Overview

There is a set of input muxes for each opamp, making it possible to select various input sources. A more detailed view of the 2 opamps, including the mux network is shown in Figure 24.2 OPAMP Overview on page 798. The POSSEL mux connected to the positive input makes it possible to select a pin, another opamp output, or tap from the resistor network. Similarly, the NEGSEL mux on the negative input makes it possible to select a pin or a feedback path as its source. The feedback path can be unity gain, 3x gain, or selected from the resistor network for programmable gain. Each opamp has several outputs, a main output, an alternative output network, APORT output and a next output. These outputs make it possible to route the output to a pin, another opamp input, the ADC, the ACMP, or into the feedback path. For details regarding configuring the outputs, see 24.3.1.8 Output Configuration. In addition, there is also a mux to configure the resistor ladder for connection to VSS, a pin, or another opamp output.




Figure 24.2. OPAMP Overview

24.3.1 Opamp Configuration

Since two of the 2 OPAMPs (OPA0, OPA1) are part of the VDAC, the opamp configuration registers are located in the VDAC.

Each OPAMP can be enabled by setting OPAxEN in VDACn_CMD and can be disabled by setting OPAxDIS in VDACn_CMD. The enabled status of each OPAMP can be read by polling the OPAxENS bit in VDACn_STATUS. OPAxENS goes high immediately after an OPAxEN is written and goes low when OPAxDIS is written and after OPAMP is completely disabled.

Software *must not* write to the following registers while OPAxENS set.

- VDACn OPAx CTRL
- VDACn_OPAx_TIMER
- VDACn OPAx MUX

24.3.1.1 Enable Sources

Opamp can be enabled either with software or PRS. The default source is software. Setting PRSEN to 1 in VDACn_OPAx_CTRL enables PRS mode. In PRS mode, opamp has two options, which are selectable with PRSMODE in VDACn_OPAx_CTRL. If PRSMODE is configured to TIMED, opamp is turned on the positive edge of PRS and stays on until PRS goes low. If PRSMODE is configured to PULSED, opamp is turned on the positive edge of PRS and stays on based on the timer configurations in VDACn_OPAxTIMER. The PRS channel is selected by PRSSEL in VDACn_OPAx_CTRL.

24.3.1.2 Warmup Time

When an opamp is enabled some initialization time is required. The warm up period is programmable with WARMUPTIME in VDACn_OPAx_TIME. The OPAxWARM bit in VDACn_STATUS are set when the warmup period has completed.

The warm up period depends on the selected DRIVESTRENGTH in VDACn_OPAx_CTRL.

Table 24.1. OPAMP Warmup Time

DRIVESTRENGTH	WARMUPTIME (μs)
0	100
1	85
2	8
3	6

24.3.1.3 Settle Time

After an opamp is enabled and the warmed-up time has elapsed the output settles externally. The settle period is programmable with SETTLETIME in VDACn_OPAx_TIME. The OPAxOUTVALID bit in VDACn_STATUS is set when the settle period has completed. When in use by the VDAC the default settling time is used.

The settling period depends on the load at opamp output and DRIVESTRENGTH of the opamp. Table 24.2 OPAMP Settling Time on page 799 specifies SETTLETIME settings for a load of 1KOhm and 75pF.

Table 24.2. OPAMP Settling Time

DRIVESTRENGTH	SETTLETIME (µs)
0	60
1	25
2	3
3	1

24.3.1.4 Startup Delay

Each opamp has an option to delay the warm up period. The startup delay is programmable with STARTDLY in VDACn_OPAx_TIME. If STARTDLY is programmed to a non-zero value, the opamp is warmed up after STARTDLY+WARMUPTIME, and the output settles after STARTDLY+WARMUPTIME+SETTLETIME.

24.3.1.5 Power Supply

The opamp module power (V_{OPA}) is derived from the AVDD supply pin.

24.3.1.6 I/O Pin Considerations

The maximum usable analog signal that can be applied to external opamp inputs (or seen on external opamp outputs) depends on several factors: whether the signal is routed through the APORT, whether High Linearity mode is used, whether overvoltage is enabled, and on the IOVDD/AVDD supply voltages, as shown in the Table 24.3 Maximum Usable IO Voltage on page 800 table.

Table 24.3. Maximum Usable IO Voltage

	Maximum IO Voltage (APORT USED and OVT Enabled/ Disabled)	` `	Maximum IO Voltage (APORT UN- USED, OVT Disabled)
Opamp Inputs - Normal Mode	MIN(AVDD, IOVDD)	MIN(AVDD, IOVDD)	MIN(AVDD, IOVDD)
Opamp Outputs	MIN(AVDD, IOVDD)	MIN(AVDD, IOVDD + 2 V)	MIN(AVDD, IOVDD)

24.3.1.7 Input Configuration

The inputs to the opamps are controlled through a set of input muxes. The mux connected to the positive input is configured by the POSSEL bit-field in the VDACn_OPAx_MUX register. Similarly, the mux connected to the negative input is configured by setting the NEGSEL bit-field in VDACn_OPAx_MUX. The input into the resistor ladder can be configured by setting the RESINMUX bit-field in VDACn_OPAx_MUX.

24.3.1.8 Output Configuration

Each opamp has three outputs: the main output, an alternative output network with lower drive strength, and an APORT output with low drive strength. These three outputs can be configured as shown in Figure 24.3 Opamp Output Stage Overview on page 801. The main output can be used to drive the main output by setting MAINOUTEN in VDACn_OPAx_OUT. The alternative output can drive the alternative output network by setting ALTOUTEN in VDACn_OPAx_OUT. The APORT output can drive the APORT selection mux by setting APORTOUTEN in VDACn_OPAx_OUT.




Figure 24.3. Opamp Output Stage Overview

The alternative output network consists of connections to pins and a connection to the next opamp. The connections to pins can be individually enabled by configuring ALTOUTPADEN in te VDACn_OPAx_OUT register. For cascaded opamp configurations, each opamp has a NEXTOUT connection.

The opamp outputs can also be routed to APORT1Y, APORT2Y, APORT3Y, and APORT4Y. The APORT channel can be selected by configuring APORTOUTSEL in VDACn_OPAx_OUT.

The opamps are also routed internally to the ADC. OPA0 and OPA1 are routed through the POSMUX of the ADC, and OPA2 is routed through the NEGMUX of the ADC. See 26.3.7 Input Selection in the ADC chapter for information on how to configure the ADC input mux.

In addition, OPA0 and OPA1 are internally routed to both the POSMUX and NEGMUX of ACMP. See 25.3.6 Input Selection in the ACMP chapter for information on how to configure the ACMP input mux.

The main and alternate outputs of each opamp can be shorted together by setting the SHORT bit-field in VDACn OPAx OUT.

24.3.1.9 Gain Programming

The feedback path of each mux includes a resistor ladder that can be used to select a set of gain values. Gain is configured by the RESSEL bit-field located in the VDACn_OPAx_MUX register. Gain values are determined by the resistor ladder based on ratio of R2/R1. It is also possible to bypass the resistor ladder in unity gain mode. In addition, there is also a preconfigured resistor ladder with 3X gain. The 3x gain resistor ladder is enabled by setting GAIN3X in VDACn_OPAx_MUX. By default all opamps are configured in 3x gain mode. When using RESSEL, GAIN3X should be set to zero.

24.3.1.10 Offset Calibration

Each opamp has a calibration register, VDACn_OPAx_CAL, where calibration values for both offset and gain correction can be written. The required calibration settings depend on the chosen DRIVESTRENGTH. The default calibration settings stored in VDACn_OPAx_CAL are for DRIVESTRENGTH=2. If an opamp is being reconfigured, the required calibration settings for DRIVESTRENGTH=n can be found in DEVINFO_OPAxCALn. Offsets can be programmed through the OFFSETP and OFFSETN bitfields of VDACn_OPAx_CAL.

24.3.1.11 Disabling of Rail-to-Rail Operation

Each opamp can have its input rail-to-rail stage disabled by setting the HCMDIS in VDACn_OPAx_CTRL. Disabling the rail-to-rail input stage improves linearity of the opamp, thus improving the total harmonic distortion (THD) at the cost of reduced input signal swing.

24.3.1.12 Unity Gain Bandwidth Scaling

Unity gain bandwidth of an opamp can be scaled setting the INCBW bit in VDACn_OPAx_CTRL. Note that this setting is used only when closed loop gain is greater than 3X. With this setting is enabled, the opamp is not unity gain stable.

24.3.1.13 Opamp Output Scaling

Opamp output drive strength is scaled by one half when the OUTSCALE bit in VDACn OPAx CTRL is set.

24.3.2 Interrupts and PRS Output

Each opamp has an interrupt flag OPAxOUTVALID in VDACn_IF that is set when the output is settled externally at the load. An interrupt will be requested if the OPAxOUTVALID interrupt flag in VDACn_IF is set and enabled by the OPAxOUTVALID bit in VDACn_IEN.

The OPAxERRPRSMODE interrupt flag in VDACn_IF indicates a protocol error when the opamp is triggered in PRS TIMED mode. This flag is set if the negative edge of the PRS pulse came before the output to opamp is valid. The interrupt flag is enabled by the OPAxERPRSMODE bit in VDACn_IEN.

An interrupt can also be requested when an APORT bus conflict occurs if the OPAxAPORTCONFLICT interrupt flag in VDACn_IF is set and enabled through by the OPAxAPORTCONFLICT bit in VDACn_IEN.

One of two aynchronous PRS outputs can be enabled for each opamp by setting PRSOUTMODE in VDACn_OPAx_CTRL. If PRSOUTMODE is WARM, opamp warm-up status is available. If PRSOUTMODE is OUTVALID, opamp output valid status is available.

24.3.3 APORT Request and Conflict Status

The opamps are connected to pins through the APORT system. To help debug over-utilization of APORT resources, the opamps provide request and conflict status information. The request status of APORT buses is visible through the DACn_OPAx_APORTREQ register.

If an APORT bus conflict occurs, it is reported in the DACn_OPAx_APORTCONFLICT register. An APORT conflict occurs if an opamp requests the same bus at the same time as another analog peripheral. In addition an APORT conflict is reported if any two of NEGSEL, POSSEL or APORTOUTSEL are configured to request the same APORT bus.

It is possible for the opamps to passively monitor APORT buses without controlling the switches and creating bus conflicts. This can be done by setting APORTXMASTERDIS or APORTYMASTERDIS in the DACH OPAX CTRL register.

24.3.4 Opamp Modes

The opamps can perform several different functions by configuring the internal signal routing between the opamps. The modes available are described in the following sections.

24.3.4.1 General Opamp Mode

In this mode, the resistor ladder is isolated from the feedback path, and the input signal routing is defined by POSSEL and NEGSEL in VDACn OPAx MUX. The output signal routing is defined by the setting of VDACn OPAx OUT.

Table 24.4. General Opamp Mode Configuration

OPA Bitfields	OPA Configuration
OPAx POSSEL	POSPADx, APORT[1-4]X
OPAx NEGSEL	OPATAP, UG, NEGPADx, APORT[1-4]Y
OPAx RESINMUX	NEXTOUT, POSPADx, NEGPADx, VSS

24.3.4.2 Voltage Follower Unity Gain

In this mode, the unity gain feedback path is selected for the negative input by setting the NEGSEL bit-field to UG in the VDACn_OPAx_MUX register as shown in Figure 24.4 Voltage Follower Unity Gain Overview on page 803. The positive input is selected by the POSSEL bit-field in VDACn_OPAx_MUX, and the output is configured by VDACn_OPAx_OUT register.




Figure 24.4. Voltage Follower Unity Gain Overview

Table 24.5. Voltage Follower Unity Gain Configuration

OPA Bitfields	OPA Configuration
OPAx POSSEL	OPATAP, NEXTOUT, POSPADx, APORT[1-4]X
OPAx NEGSEL	UG
OPAx RESINMUX	DISABLE

24.3.4.3 Inverting Input PGA

Figure 24.5 Inverting Input PGA Overview on page 803 shows the inverting input PGA configuration. In this mode, the negative input is connected to the resistor ladder by setting the NEGSEL bit-field to OPATAP in the VDACn_OPAx_MUX register. This setting provides a programmable gain on the negative input, which is set by the RESSEL bit-field in VDACn_OPAx_MUX. Signal ground for the positive input can come from off-chip by setting the POSSEL bit-field to PAD or APORT in VDACn_OPAx_MUX. In addition, the output is configured by VDACn_OPAx_OUT register.




Figure 24.5. Inverting Input PGA Overview

Table 24.6. Inverting Input PGA Configuration

OPA Bitfields	OPA Configuration
OPAx POSSEL	POSPADx, APORT[1-4]X
OPAx NEGSEL	ОРАТАР
OPAx RESINMUX	NEXTOUT, NEGPADx, POSPADx

24.3.4.4 Non-inverting PGA

Figure 24.6 Non-inverting PGA Overview on page 804 shows the non-inverting input configuration. In this mode, the negative input is connected to the resistor ladder by setting the NEGSEL bit-field to OPATAP in VDACn_OPAx_MUX. This setting provides a programmable gain on the negative input, which is set by the RESSEL bit-field in VDACn_OPAx_MUX. In addition, the RESINMUX bit-field must be set to VSS or NEGPAD in VDACn_OPAx_MUX. The positive input is selected by the POSSEL bit-field, and the output is configured by VDACn_OPAx_OUT register.




Figure 24.6. Non-inverting PGA Overview

Table 24.7. Non-inverting PGA Configuration

OPA Bitfields	OPA Configuration
OPAx POSSEL	NEXTOUT, POSPADx, APORT[1-4]X
OPAx NEGSEL	ОРАТАР
OPAx RESINMUX	VSS, NEGPAD

24.3.4.5 Cascaded Inverting PGA

This mode enables the opamp signals to be internally configured to cascade two or more opamps in inverting mode as shown in Figure 24.7 Cascaded Inverting PGA Overview on page 805. In both cases, the positive input is connected to signal ground by setting the POSSEL bit-field to PAD or APORT in VDACn_OPAx_MUX. When cascaded, the negative input is connected to the resistor ladder by setting the NEGSEL bit-field to OPATAP in VDACn_OPAx_MUX. The input to the resistor ladder is configured by the RESINMUX bit-field in VDACn_OPAx_MUX.




Figure 24.7. Cascaded Inverting PGA Overview

Table 24.8 Cascaded Inverting PGA Configuration on page 805 shows cascaded non-inverting PGA with OPA0,OPA1 and OPA2. The output from OPA0 is connected to OPA1 to create the second stage by setting the RESINMUX field to OPANEXT in VDACn OPA1 MUX. The last stage is created by setting the RESINMUX bit-field to OPANEXT in VDACn OPA2MUX.

Table 24.8. Cascaded Inverting PGA Configuration

OPA	OPA Bitfields	OPA Configuration
OPA0	POSSEL	POSPAD0, APORT[1-4]X
OPA0	NEGSEL	ОРАТАР
OPA0	RESINMUX	NEGPAD0
OPA1	POSSEL	POSPAD1, APORT[1-4]X
OPA1	NEGSEL	ОРАТАР
OPA1	RESINMUX	OPANEXT
OPA2	POSSEL	POSPAD2,APORT[1-4]X
OPA2	NEGSEL	ОРАТАР
OPA2	RESINMUX	OPANEXT

24.3.4.6 Cascaded Non-inverting PGA

This mode enables the opamp signals to be internally configured to cascade two or more opamps in non-inverting mode as shown in Figure 24.8 Cascaded Non-inverting PGA Overview on page 806. The negative input for all opamps will be connected to the resistor ladder by setting the NEGSEL bit-field to OPATAP. In addition the resistor ladder input must be set to VSS or NEGPADx by configuring the RESINMUX bit-field in VDACn_OPAx_MUX.




Figure 24.8. Cascaded Non-inverting PGA Overview

Table 24.9 Cascaded Non-inverting PGA Configuration on page 806 shows cascaded non-inverting PGA with OPA0,OPA1 and OPA2. When cascaded, the positive input on OPA0 is configured by the OPA0 POSSEL bit-field in VDACn_OPA0_MUX. The output from OPA0 is connected to OPA1 to create the second stage by setting the POSSEL field to OPANEXT in VDACn_OPA1_MUX. The last stage is created by setting the POSSEL bit-field to OPANEXT in VDACn_OPA2_MUX.

OPA OPA Bitfields OPA Configuration OPA0 **POSSEL** POSPAD0, APORT[1-4]X OPA0 **NEGSEL OPATAP RESINMUX** OPA0 VSS, NEGPAD0 OPA1 **POSSEL OPANEXT** OPA1 NEGSEL **OPATAP** VSS, NEGPAD1 OPA1 **RESINMUX** OPA2 POSSEL **OPANEXT** OPA2 **NEGSEL OPATAP** OPA2 **RESINMUX** VSS, NEGPAD2

Table 24.9. Cascaded Non-inverting PGA Configuration

24.3.4.7 Two Opamp Differential Amplifier

This mode allows OPA0 and OPA1 or OPA1 and OPA2 to be internally connected to form a two opamp differential amplifier as shown in Figure 24.9 Two Op-amp Differential Amplifier Overview on page 807. When using OPA0 and OPA1, the positive input of OPA0 can be connected to any input by setting the POSSEL bit-field in VDACn_OPA0_MUX. The OPA0 feedback path must be configured for unity gain by setting the NEGSEL bit-field to UG in VDACn_OPA0_MUX. In addition, the OPA0 RESINMUX bit-field must be set to DISABLED. The OPA0 NEXTOUT output must be connected to OPA1 by setting the RESINMUX bit-field to OPANEXT in VDAC_n_OPA1_MUX. The positive input onof OPA1 is selected by the POSSELbit-field in VDACn_OPA1_MUX. The OPA1 output is configured by DACn_OPA1_OUT.

When using OPA1 and OPA2, the positive input of OPA1 can be connected to any input by setting the POSSEL bit-field in VDACn_OPA1_MUX. The OPA1 feedback path must be configured for unity gain by setting the NEGSEL bit-field to UG in VDACn_OPA1_MUX. In addition, the OPA1 RESINMUX bit-field must be set to DISABLED. The OPA1 NEXTOUT output must be connected to OPA2 by setting the RESINMUX bit-field to OPANEXT in VDACn_OPA2_MUX. The positive input of OPA2 is selected by the POSSEL bit-field in VDACn_OPA2_MUX. The OPA2 output is configured by DACn_OPA2_OUT.




Figure 24.9. Two Op-amp Differential Amplifier Overview

Table 24.10. OPA0/OPA1 Differential Amplifier Configuration

OPA	OPA Bitfields	OPA Configuration
OPA0	POSSEL	POSPAD0, APORT[1-4]X
OPA0	NEGSEL	UG
OPA0	RESINMUX	DISABLE
OPA1	POSSEL	POSPAD1, APORT[1-4]X
OPA1	NEGSEL	ОРАТАР
OPA1	RESINMUX	OPANEXT

Table 24.11. OPA1/OPA2 Differential Amplifier Configuration

OPA	OPA Bitfields	OPA Configuration
OPA1	POSSEL	POSPAD1, APORT[1-4]X
OPA1	NEGSEL	UG
OPA1	RESINMUX	DISABLE
OPA2	POSSEL	POSPAD2, APORT[1-4]X
OPA2	NEGSEL	ОРАТАР
OPA2	RESINMUX	OPANEXT

24.3.4.8 Three Opamp Differential Amplifier

This mode allows the three opamps to be internally configured to form a three opamp differential amplifier as shown in Figure 24.10 Three Op-amp Differential Amplifier Overview on page 808. For both OPA0 and OPA1, the positive input can be connected to any input by configuring the OPA0 POSSEL and OPA1 POSSEL bitfields in VDACn_OPA0_MUX and VDACn_OPA1_MUX, respectivley. The OPA0 and OPA1 feedback paths must be configured for unity gain by setting the OPA0 NEGSEL and OPA1 NEGSEL bitfields to UG in VDACn_OPA0_MUX and VDACn_OPA1_MUX respectivley. In addition the OPA0 RESINMUX and OPA1 RESINMUX bitfields must be set to DISABLED. The OPA1 output must be connected to OPA2 by setting RESINMUX to OPANEXT in VDACn_OPA2_MUX and the OPA2 POSSEL must be set to OPATAP. The OPA2 output is configured by the DACn_OPA2_OUT register.




Figure 24.10. Three Op-amp Differential Amplifier Overview

The gain for the Three Opamp Differential Amplifier is determined by the combination of the gain settings of OPA0 and OPA2. Gain values of 1/3, 1 and 3, are available and programmed as shown in the table below.

Table 24.12. Three Opamp Differential Amplifier Gain Programming

Gain	OPA0 RESSEL	OPA2 RESSEL
1/3	4	0
1	1	1
3	0	4

Table 24.13. Three Opamp Differential Amplifier Configuration

OPA	OPA Bitfields	OPA Configuration
OPA0	POSSEL	POSPAD0, APORT[1-4]X
OPA0	NEGSEL	UG
OPA0	RESINMUX	DISABLE
OPA1	POSSEL	POSPAD1, APORT[1-4]X
OPA1	NEGSEL	UG
OPA1	RESINMUX	DISABLE
OPA2	POSSEL	ОРАТАР
OPA2	NEGSEL	ОРАТАР
OPA2	RESINMUX	OPANEXT

24.3.4.9 Instrumentation Amplifier

OPA0 and OPA1 can form a fully differential instrumentation amplifier by setting RESINMUX to CENTER for both opamps in VDACn_OPA0_MUX and VDACn_OPA1_MUX. Configuring RESINMUX to CENTER makes a connection between resistor ladder of the opamps as shown in Figure 24.11 Instrumentation Amplifier Overview on page 809.




Figure 24.11. Instrumentation Amplifier Overview

24.3.4.10 Common Reference

It is possible to configure all opamps to have a common reference by setting the RESINMUX to COMPAD in VDACn_OPAx_MUX. When RESINMUX of all opamps is set to COMPAD mode, the NEGPAD input of OPA0 is used.

24.3.4.11 Dual Buffer ADC Driver

It is possible to use any two of the opamps to form a Dual Buffer ADC driver as shown in Figure 24.12 Dual Buffer ADC Driver Overview on page 809. Both opamps used must be configured in the same way. The positive input is configured by setting the 0PAx POSSEL to PAD, and the negative input is connected to the resistor ladder by setting NEGSEL to OPATAP in VDACn_OPAx_MUX. The output from the opamps can be configure to drive pins through the alternative output network or the APORT. The ADC can sample pins that the opamps are driving through the APORT.




Figure 24.12. Dual Buffer ADC Driver Overview

Table 24.14. Dual Buffer ADC Driver Configuration

OPA	OPA Bitfields	OPA Configuration
OPAx	POSSEL	POSPADx, APORT[1-4]X
OPAx	NEGSEL	ОРАТАР
OPAx	RESINMUX	VSS

24.3.5 Opamp VDAC Combination

Since two of the OPAMPs are part of the VDAC, it is not possible to use both VDAC channels and all 2 OPAMPs at the same time. If both VDAC channels are used, OPA0 and OPA1 can not be used as stand-alone opamp. However, it is possible to use one of the VDAC channels in combination with OPA0 or OPA1. OPA1 is available when VDAC channel 0 is in use, and OPA0 is available when VDAC channel 1 is used.

24.4 Register Map


The register map of the opamp can be found in 23.4 Register Map in the VDAC chapter.

24.5 Register Description

The register description of the opamp can be found in 23.5 Register Description in the VDAC chapter.

25. ACMP - Analog Comparator





Quick Facts

What?

The Analog Comparator (ACMP) compares two analog signals and returns a digital value telling which is greater.

Why?

Applications often do not need to know the exact value of an analog signal, only if it has passed a certain threshold. Often the voltage must be monitored continuously, which requires extremely low power consumption.

How?

Available down to Energy Mode 3 and using as little as 100 nA, the ACMP can wake up the system when input signals pass the threshold. The analog comparator can compare two analog signals or one analog signal and a highly configurable internal reference.

25.1 Introduction

The Analog Comparator compares the voltage of two analog inputs and outputs a digital signal indicating which input voltage is higher. Inputs can either be from internal references or from external pins. Response time, and thereby the current consumption, can be configured by altering the current supply to the comparator.

25.2 Features

- Up to 160 selectable external I/O inputs for both positive and negative inputs
 - Up to 48 I/O can be used as a dividable reference
- · 5 selectable internal inputs
 - · VDAC channel 0 voltage as a reference
 - VDAC channel 1 voltage as a reference
 - Dividable Internal 1.25 V bandgap reference voltage
 - · Dividable Internal 2.5 V bandgap reference voltage
 - Dividable V_{ACMPVDD} reference voltage
- · Voltage supply monitoring
- Low power mode for internal V DD and bandgap references
- · Selectable hysteresis
 - · 8 values
 - · Values can be positive or negative
 - · Dividable references have scale for both both output values, allowing for even larger hysteresis
- · Selectable response time
- · Asynchronous interrupt generation on selectable edges
 - · Rising edge
 - · Falling edge
 - · Both edges
- · Operational in EM0 Active down to EM3 Stop
- · Dedicated capacitive sense mode with up to 8 inputs
 - · Adjustable internal resistor
- · Configurable output when inactive
- · Comparator output direct on PRS
- · Comparator output on GPIO through alternate functionality
 - · Output inversion available

25.3 Functional Description

An overview of the ACMP is shown in Figure 25.1 ACMP Overview on page 813.




Figure 25.1. ACMP Overview

The comparator has two analog inputs: one positive and one negative. When the comparator is active, the output indicates which of the two input voltages is higher. When the voltage on the positive input is higher than the voltage on the negative input, the digital output is high and vice versa.

The output of the comparator can be read in the ACMPOUT bit in ACMPn_STATUS. It is possible to switch inputs while the comparator is enabled, but all other configuration should only be changed while the comparator is disabled.

25.3.1 Power Supply

The comparator power supply $(V_{ACMPVDD})$ can be configured to be AVDD, DVDD, or IOVDD using the PWRSEL bitfield in ACMPn_CTRL. By default, $V_{ACMPVDD}$ is set to AVDD.

25.3.2 Warm-up Time

The analog comparator is enabled by setting the EN bit in ACMPn_CTRL. The comparator requires some time to stabilize after it is enabled. This time period is called the warm-up time. The warm-up period is self-timed and will complete within 5µs after EN is set.

During warm-up and when the comparator is disabled, the output level of the comparator is set to the value of the INACTVAL bit in ACMPn_CTRL. When the warm-up time is over, the ACMPACT bit in ACMPn_STATUS is set to 1 to indicate that the comparator is active.

An edge interrupt will be generated if the edge interrupt is enabled and the value set in INACTVAL differs from ACMPOUT when the comparator transitions from warm-up to active.

Software should wait until the warm-up period is over before entering EM2 or EM3, otherwise no comparator interrupts will be detected. EM1 can still be entered during warm-up. After the warm-up period is completed, interrupts will be detected in EM2 and EM3.

25.3.3 Response Time

There is a delay from when the input voltage changes polarity to when the output toggles. This delay is called the response time and can be altered by increasing or decreasing the bias current to the comparator through the BIASPROG and FULLBIAS fields in the ACMPn_CTRL register. The current and speed of the circuit increase as the values of FULLBIAS and BIASPROG are increased from their minimum setting of FULLBIAS=0 BIASPROG=0b000000 to the maximum setting FULLBIAS=1 BIASPROG=0b11111 (maximum). The setting of FULLBIAS has a greater affect on current and speed than the setting of BIASPROG. See the part data sheet for specific current and response times related to the setting of these fields.

If FULLBIAS is set, to avoid glitches the highest hysteresis level should be used.

25.3.4 Hysteresis

When the hysteresis level is set to a non-zero value, the digital output will not toggle until the positive input voltage is at a voltage equal to the hysteresis level above or below the negative input voltage (see Figure 25.3 Hysteresis on page 815). This feature can be used to avoid continual comparator output changes due to noise when the positive and negative inputs are nearly equal by requiring the input difference to exceed the hysteresis threshold.

In the analog comparator, hysteresis can be configured to 8 different levels. Level 0 is no hysteresis. Hysteresis is configured through the HYST field in ACMPn_HYSTERESIS0 and ACMPn_HYSTERESIS1 registers. The hysteresis value can be positive or negative. The comparator will output a 1 if:

POSSEL - NEGSEL > HYST

There are two hysteresis registers, ACMPn_HYSTERESISO and ACMPn_HYSTERESIS1, as the ACMP supports asymmetric hysteresis. ACMPn_HYSTERESISO are the hysteresis values used when the comparator output is 0; ACMPn_HYSTERESIS1 are the values used when the comparator output is 1. The user must set both registers to the same values if symmetric hysteresis is desired.

Along with the HYST field, the ACMPn_HYSTERESIS0/1 registers include the DIVVA and DIVVB fields. This allows the user to implement even larger hysteresis when comparing against VADIV or VBDIV, as the reference voltage can vary with the comparator output, also.




Figure 25.3. Hysteresis

25.3.5 Input Pin Considerations

For external ACMP inputs routed through the APORT, the maximum supported analog input voltage will be limited to the $MIN(V_{ACMPVDD}, IOVDD)$ (where $V_{ACMPVDD}$ is selected by the PWRSEL bitfield in ACMPn_CTRL). Note that pins configured as ACMP inputs should disable OVT (by setting the corresponding GPIO_Px_OVTDIS bit) to reduce any potential distortion introduced by the OVT circuitry.

25.3.6 Input Selection

The POSSEL and NEGSEL fields in ACMPn_INPUTSEL control the input connections to the positive and negative inputs of the comparator. The user can select external GPIO pins on the chip, or select a number of internal chip voltages. Pins are selected by configuring channels on APORT buses. Not all selectable channels are available on a given device, as different devices within a family may not implement or bring out all of the I/O defined for that family. Refer to the data sheet for channel availability and pin mapping.

There are limitations on the POSSEL and NEGSEL connections that can be made. The user cannot select an X-bus for both POSSEL and NEGSEL simultaneously, nor a Y-bus for both POSSEL and NEGSEL simultaneously. The second limitation is that when using the feedback resistor only X-bus selections can be made for POSSEL. (The resistor only physically exists on the positive input of the comparator).

The user may also select from a number of internal voltages. VADIV and VBDIV are two dividable voltages. VADIV can be $V_{ACMPVDD}$ divided, or the user can choose to select inputs from a number of APORT buses. VBDIV consists of two dividable band-gap references of either 1.25V or 2.5V. Each of these voltages have dividers in the ACMPn_HYSTERESIS0/1 registers. The formula for the division of these voltages is:

 $VADIV = VA \cdot ((DIVVA+1)/64)$

Figure 25.3. VA Voltage Division

 $VBDIV = VB \cdot ((DIVVB+1)/64)$

Figure 25.4. VB Voltage Division

Either VADIV and VBDIV can also be used as an input to a lower power reference: VLP. Which of the two is used is configured via the VLPSEL field in ACMPn_INPUTSEL. If the user selects VLP as an input source, then VADIV or VBDIV cannot be used as the source for the other input.

Note: The VLP should not be selected as an input source when the external override interface is enabled.


The POSSEL and NEGSEL fields also allow input from the on-chip VDAC channel 0 or VDAC channel 1.

ACMP can be configured to operate with a selected level of accuracy depending on the setting of ACCURACY in ACMPn_CTRL. The default is low-accuracy mode where ACMP operates with lower accuracy but consumes less current. When higher accuracy is needed the user can set ACCURACY=1 at the cost of higher current consumption.

25.3.7 Capacitive Sense Mode

The analog comparator includes specialized hardware for capacitive sensing of passive push buttons. Such buttons are traces on the PCB laid out in a way that creates a parasitic capacitor between the button and the ground node. Because a human finger will have a small intrinsic capacitance to ground, the capacitance of the button will increase when the button is touched. The capacitance is measured by including the capacitor in a free-running RC oscillator (see Figure 25.5 Capacitive Sensing Setup on page 818). The frequency produced will decrease when the button is touched compared to when it is not touched. By measuring the output frequency with a timer (via the PRS), the change in capacitance can be detected.

The analog comparator contains a feedback loop including an optional internal resistor. This resistor is enabled by setting the CSRE-SEN bit in ACMPn_INPUTSEL. The resistance can be set to any of 8 values by configuring the CSRESSEL bits in ACMPn_INPUTSEL. The source for VADIV is set to V_{ACMPVDD} by setting field VASEL=0 in ACMPn_INPUTSEL. The oscillation rails are defined by the VADIV fields in registers ACMPn_HYSTERESISO/1. The user should select VADIV as the source for NEGSEL, and APORTXCHc for POSSEL in ACMPn_INPUTSEL. When enabled, the comparator output will oscillate between the rails defined by VADIV in ACMPn_HYSTERESISO/1.






Figure 25.5. Capacitive Sensing Setup

25.3.8 Interrupts and PRS Output

The analog comparator includes an edge triggered interrupt flag (EDGE in ACMPn_IF). If either IRISE and/or IFALL in ACMPn_CTRL is set, the EDGE interrupt flag will be set on rising and/or falling edge of the comparator output respectively. An interrupt request will be sent if the EDGE interrupt flag in ACMPn_IF is set and enabled through the EDGE bit in ACMPn_IEN. The edge interrupt can also be used to wake up the device from EM3 Stop-EM1 Sleep.

The analog comparator includes the interrupt flag WARMUP in ACMPn_IF which is set when a warm-up sequence has finished. An interrupt request will be sent if the WARMUP interrupt flag in ACMPn_IF is set and enabled through the WARMUP bit in ACMPn_IEN.

The analog comparator can also generate an interrupt if a bus conflict occurs. An interrupt request will be sent if the APORTCONFLICT interrupt flag in ACMPn IF is set and enabled through the APORTCONFLICT bit in ACMPn IEN.

The synchronized comparator output is also available as a PRS output signal.

25.3.9 Output to GPIO

The output from the comparator and the capacitive sense output are available as alternate functions to the GPIO pins. Set the ACMP-PEN bit in ACMPn_ROUTE to enable the output to a pin and the LOCATION bits to select the output location. The GPIO-pin must also be set as output. The output to the GPIO can be inverted by setting the GPIOINV bit in ACMPn_CTRL.

25.3.10 APORT Conflicts

The analog comparator connects to chip pins through APORT buses. It is possible that another APORT client is using a given APORT bus. To help debugging over-utilization of APORT resources the ACMP provides a number of status registers. The ACMPn_APORTREQ gives the user visibility into what APORT buses the ACMP is requesting given the setting of registers ACMPn_INPUTSEL and ACMPn_CTRL. ACMPn_APORTCONFLICT indicates if any of the selections are in conflict, internally or externally.

For example, if the user selects APORT1XCH0 for POSSEL and APORT3XCH1 for NEGSEL, then bits APORT1XCONFLICT and APORT3XCONFLICT would be 1 in register ACMPn_APORTCONFLICT, as it is illegal for POSSEL and NEGSEL to both select an X-bus simultaneously.

If the user wishes the ACMP to monitor the same pin as another APORT client within the system, the ACMP can be configured to not attempt to control the switches on an APORT bus via the fields APORTXMASTERDIS, APORTYMASTERDIS, and APORTVMASTERDIS and APORTYMASTERDIS control if the X or Y bus selected via POSSEL or NEGESEL is mastered or not. APORTVMASTERDIS controls if either the X or Y bus selection of VASEL is mastered or not. When bus mastering is disabled, it is the other APORT client that determines which pin is connected to the APORT bus.

25.3.11 Supply Voltage Monitoring

The ACMP can be used to monitor supply voltages. The ACMP can select which voltage it uses via PWRSEL in ACMPn_CTRL. This voltage can be selected for VADIV using VASEL=0 in ACMPn_INPUTSEL and divided to a voltage with the band-gap reference range using DIVVA in registers ACMPn_HYSTERESIS0/1. The band-gap reference voltage can also be scaled via DIVVB in registers ACMPn_HYSTERESIS0/1 to provide a voltage higher or lower than the scaled VA voltage for comparison.

25.3.12 External Override Interface

The ACMP can be controlled by an external module, for instance LESENSE. In this mode, the external module will take control of the positive input mux control signal, which is normally controlled by ACMP_INPUTSEL_POSSEL. Only the APORTs are selectable for the positive input mux in this mode. Which APORT(s) used is configured in ACMP_EXTIFCTRL_APORTSEL. Additionally, the VLP should not be selected for the negative input mux in this mode.

Note: When the ACMP is controlled by the external interace, the ACMP warmup time may take up to 30 µs.

ACMP_EXTIFCTRL_APORTSEL also controls the base value for the positive input mux control signal. The external module will be able to add an offset to this base. The resulting mux configuration can be calculated using Figure 25.6 POSSEL in External Override Mode on page 820. The external module controls EXT_OFFSET, while EXT_BASE is controlled by ACMP. See register description of ACMP_EXTIFCTRL_APORTSEL to see values of EXT_BASE.

POSSEL = EXT_BASE + EXT_OFFSET

Figure 25.6. POSSEL in External Override Mode

Note: If only one APORT in a pair is used, the external module needs to be programmed to only use the channels that the ACMP has control of.

The external module is also able to override DIVVA and DIVVB in ACMP_HYSTERESIS0/HYSTERESIS1. This needs to be enabled in the external module. If the external module does not override DIVVA/DIVVB, the configuration in ACMP_HYSTERESIS0/HYSTERESIS1 will be used.

To enable the external override interface these steps must be performed:

- Configure the parts of the ACMP that will not be overridden, i.e. everything except ACMP_INPUTSEL_POSSEL and possibly ACMP_HYSTERESIS0/HYSTERESIS1. Make sure ACMP_CTRL_EN is set.
- Configure and enable the external override interface in ACMP_EXTIFCTRL.
- · Check for APORT conflicts in ACMP APORTCONFLICT.
- Wait for ACMP STATUS EXTIFACT to go high, indicating that the interface is ready to use.

25.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	ACMPn_CTRL	RW	Control Register
0x004	ACMPn_INPUTSEL	RW	Input Selection Register
0x008	ACMPn_STATUS	R	Status Register
0x00C	ACMPn_IF	R	Interrupt Flag Register
0x010	ACMPn_IFS	W1	Interrupt Flag Set Register
0x014	ACMPn_IFC	(R)W1	Interrupt Flag Clear Register
0x018	ACMPn_IEN	RW	Interrupt Enable Register
0x020	ACMPn_APORTREQ	R	APORT Request Status Register
0x024	ACMPn_APORTCONFLICT	R	APORT Conflict Status Register
0x028	ACMPn_HYSTERESIS0	RW	Hysteresis 0 Register
0x02C	ACMPn_HYSTERESIS1	RW	Hysteresis 1 Register
0x040	ACMPn_ROUTEPEN	RW	I/O Routing Pine Enable Register
0x044	ACMPn_ROUTELOC0	RW	I/O Routing Location Register
0x048	ACMPn_EXTIFCTRL	RW	External Override Interface Control

25.5 Register Description

25.5.1 A	CMF	n_(CTRI	L - (Con	trol	Reg	giste	er																							
Offset															Bi	t Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset	0				7070) OXO	•				0	0	5	OXO			0		0x0			0	0	0			•		0	0		0
Access	RW				2	<u>}</u>					₹	₩	2	<u>}</u>			₩ W		¥ M			₩ M	₽	₩					8	S M M		₹
Name	FULLBIAS				COGGOVIG	50Krokia					IFALL	IRISE					ACCURACY		PWRSEL			APORTVMASTERDIS	APORTYMASTERDIS	APORTXMASTERDIS					GPIOINV	INACTVAL		Z
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion	1															
31	FU	LLB	BIAS				0				RV	V	ı	Full	Bia	s Cı	urre	nt														
	Se	t this	s bit	to 1	for	full	bias	cur	rent	. Se	e th	e da	ıta s	hee	t for	det	ails.															

Bit	Name	Reset	Access	Description
31	FULLBIAS	0	RW	Full Bias Current
	Set this bit to 1 for	full bias current. S	See the data	a sheet for details.
30	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
29:24	BIASPROG	0x07	RW	Bias Configuration
	These bits control t	he bias current le	evel. See the	e data sheet for details.
23:22	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
21	IFALL	0	RW	Falling Edge Interrupt Sense
	Set this bit to 1 to s	et the EDGE inte	rrupt flag or	n falling edges of comparator output.
	Value	Mode		Description
	0	DISABLED		Interrupt flag is not set on falling edges
	1	ENABLED		Interrupt flag is set on falling edges
20	IRISE	0	RW	Rising Edge Interrupt Sense
	Set this bit to 1 to s	et the EDGE inte	rrupt flag or	n rising edges of comparator output.
	Value	Mode		Description
	0	DISABLED		Interrupt flag is not set on rising edges
	1	ENABLED		Interrupt flag is set on rising edges
19:18	INPUTRANGE	0x0	RW	Input Range
	Adjust performance	e of the comparate	or for a give	en input voltage range.
	Value	Mode		Description
	0	FULL		Setting when the input can be from 0 to ACMPVDD.
	1	GTVDDDIV2	2	Setting when the input will always be greater than ACMPVDD/2.

	Name	Reset	Access	Description
	2	LTVDDDIV2		Setting when the input will always be less than ACMPVDD/2.
17:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15	ACCURACY	0	RW	ACMP Accuracy Mode
		For such uses,	such as qu	the comparator. Note, high frequency changes can cause the ACMP per- uickly scanning through multiple channels or setting the ACMP to oscillate
	Value	Mode		Description
	0	LOW		ACMP operates in low-accuracy mode but consumes less current.
	1	HIGH		ACMP operates in high-accuracy mode but consumes more current.
14:12	PWRSEL	0x0	RW	Power Select
	Selects the power so (EN=0).	urce for the ACN	MP(ACMP\	/DD). NOTE, this field should only be changed when the block is disabled
	Value	Mode		Description
	0	AVDD		AVDD supply
	1	DVDD		DVDD supply
	2	IOVDD0		IOVDD/IOVDD0 supply
	4	IOVDD1		IOVDD1 supply (if part has two I/O voltages)
11	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
11	Reserved APORTVMASTER-DIS		mpatibility v	
	APORTVMASTER- DIS Determines if the ACI devices to monitor the determination is expected.	0 MP will request e same APORT expected to be for a selected by	RW the X or Y in the Standard	with future devices, always write bits to 0. More information in 1.2 Conven-
	APORTVMASTER- DIS Determines if the ACI devices to monitor the determination is explication of channel for the determination of the determination of channel for the determination of the deter	0 MP will request e same APORT expected to be for a selected by	RW the X or Y in the Standard	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, er peripheral, and the ACMP only passively looks at the bus. When 1, the det (the bus is not), and is whatever selection the external device mastering
	APORTVMASTER- DIS Determines if the ACI devices to monitor th the determination is e selection of channel f the bus has configure	0 MP will request e same APORT expected to be for a selected by	RW the X or Y in the Standard	with future devices, always write bits to 0. More information in 1.2 Conven- APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, er peripheral, and the ACMP only passively looks at the bus. When 1, the
	APORTVMASTER-DIS Determines if the ACI devices to monitor the the determination is eselection of channel of the bus has configure Value	0 MP will request e same APORT expected to be for a selected by	RW the X or Y in the Standard	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, er peripheral, and the ACMP only passively looks at the bus. When 1, the det (the bus is not), and is whatever selection the external device mastering
	APORTVMASTER-DIS Determines if the ACI devices to monitor the determination is eselection of channel of the bus has configure Value	0 MP will request e same APORT expected to be for a selected by	RW the X or Y in the Standard	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, er peripheral, and the ACMP only passively looks at the bus. When 1, the d (the bus is not), and is whatever selection the external device mastering Description Bus mastering enabled
10	APORTVMASTER-DIS Determines if the ACI devices to monitor the the determination is eselection of channel of the bus has configure Value 0 1 APORTYMASTER-DIS Determines if the ACI connected devices to When 1, the determine	tions 0 MP will request e same APORT expected to be for a selected bid for the APORT 0 MP will request monitor the sai ation is expected annel for a selected annel for a sel	RW the X or Y A bus simul from anoth us is ignore T bus. RW the APORT and to be from the control of the control t	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, are peripheral, and the ACMP only passively looks at the bus. When 1, the detection the external device mastering Description Bus mastering enabled Bus mastering disabled APORT Bus Y Master Disable T Y bus selected by POSSEL or NEGSEL. This bit allows multiple APORT bus simultaneously by allowing the ACMP to not master the selected bus. In another peripheral, and the ACMP only passively looks at the bus. When ignored (the bus is not), and is whatever selection the external device mastering device mastering disabled.
10	APORTVMASTER-DIS Determines if the ACI devices to monitor the the determination is eselection of channel of the bus has configured. Value 0 1 APORTYMASTER-DIS Determines if the ACI connected devices to When 1, the determinant, the selection of channel of the connected devices to the selection of channel of the connected devices to the selection of channel of the connected devices to the selection of channel of the connected devices to the selection of channel of the connected devices to the connected devices to the selection of channel of the connected devices to the connected device	tions 0 MP will request e same APORT expected to be for a selected bid for the APORT 0 MP will request monitor the sai ation is expected annel for a selected annel for a sel	RW the X or Y A bus simul from anoth us is ignore T bus. RW the APORT and to be from the control of the control t	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, are peripheral, and the ACMP only passively looks at the bus. When 1, the detection the external device mastering Description Bus mastering enabled Bus mastering disabled APORT Bus Y Master Disable T Y bus selected by POSSEL or NEGSEL. This bit allows multiple APORT bus simultaneously by allowing the ACMP to not master the selected bus. In another peripheral, and the ACMP only passively looks at the bus. When ignored (the bus is not), and is whatever selection the external device mastering device mastering disabled.
10	APORTVMASTER-DIS Determines if the ACI devices to monitor the the determination is eselection of channel of the bus has configure Value 0 1 APORTYMASTER-DIS Determines if the ACI connected devices to When 1, the determinant, the selection of charactering the bus has continued the selection of charactering the selection of charac	tions 0 MP will request e same APORT expected to be for a selected bid for the APORT 0 MP will request monitor the sai ation is expected annel for a selected annel for a sel	RW the X or Y A bus simul from anoth us is ignore T bus. RW the APORT and to be from the control of the control t	APORT Bus Master Disable for Bus Selected By VASEL APORT bus selected by VASEL. This bit allows multiple APORT connected taneously by allowing the ACMP to not master the selected bus. When 1, the peripheral, and the ACMP only passively looks at the bus. When 1, the did (the bus is not), and is whatever selection the external device mastering Description Bus mastering enabled Bus mastering disabled APORT Bus Y Master Disable TY bus selected by POSSEL or NEGSEL. This bit allows multiple APORT bus simultaneously by allowing the ACMP to not master the selected bus. In another peripheral, and the ACMP only passively looks at the bus. When ignored (the bus is not), and is whatever selection the external device massis.

Bit	Name	Reset	Access	Description
8	APORTXMASTER- DIS	0	RW	APORT Bus X Master Disable
	connected devices to When 1, the determine	monitor the sa nation is expect annel for a sele	ame APORT ted to be froi ected bus is i	T X bus selected by POSSEL or NEGSEL. This bit allows multiple APORT bus simultaneously by allowing the ACMP to not master the selected bus. In another peripheral, and the ACMP only passively looks at the bus. When ignored (the bus is not), and is whatever selection the external device masses.
	Value			Description
	0			Bus mastering enabled
	1			Bus mastering disabled
7:4	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	GPIOINV	0	RW	Comparator GPIO Output Invert
	Set this bit to 1 to inv	ert the compar	ator alternat	e function output to GPIO.
	Value	Mode		Description
	0	NOTINV		The comparator output to GPIO is not inverted
	1	INV		The comparator output to GPIO is inverted
2	INACTVAL	0	RW	Inactive Value
	The value of this bit is	s used as the c	comparator o	output when the comparator is inactive.
	Value	Mode		Description
	0	LOW		The inactive value is 0
	1	HIGH		The inactive state is 1
1	Reserved	To ensure co	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EN	0	RW	Analog Comparator Enable
	Enable/disable analo	g comparator.		

25.5.2 ACMPn_INPUTSEL - Input Selection Register

25.5.2 A	CIVIF	'II_INP	JIS	CL-	mp	ul 3	eie	cuo	II K	gis	tei																			
Offset														Ві	it Po	sitic	on													
0x004	31	30	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	9	2	4	3	2	_
Reset		0x0			0		0		0			;	00×0							00×0				00×00						
Access		§ S			₩ N		RW		S N			:	 ≷				RW								RW					
Name		CSRESSEL			CSRESEN		VLPSEL		VBSEL			i	VASEL								POSSEL									
Bit	Na	me				Res	set			Acc	cess	S	Des	crip	tion															
31	Re	served				To tion		ure	con	patii	bility	/ W	ith fu	ıture	dev	vices	, alv	way.	s w	/rite	bits	to 0.	Мо	re in	form	atic	on in	1	2 Cc	nven-
30:28	CS	RESSE	EL.			0x0)			RW	,		Cap	acit	ive	Sens	se N	l od	le I	nter	nal	Resi	stor	Sel	ect					
		ese bits device					anc	e va	alue	for tl	he ir	nte	rnal	сара	acitiv	e se	ense	e res	sist	or. F	Resu	lting	act	ual r	esist	tor v	valu	es	are (given
	Va	lue				Мо	de						Description																	
	0					RE	S0						Internal capacitive sense resistor value 0																	
	1					RE	S1						Internal capacitive sense resistor value 1																	
	2					RE	S2						Internal capacitive sense resistor value 2																	
	3					RE	S3						Internal capacitive sense resistor value 3																	
	4					RE	S4						Inte	rnal	capa	acitiv	e se	ens	e re	esist	or v	alue 4	4							
	5					RE	S5						Inte	rnal	capa	acitiv	e se	ens	e re	esist	or v	alue	5							
	6					RE	S6						Inte	rnal	сара	acitiv	e se	ens	e re	esist	or v	alue	3							
	7					RE	S7						Inte	rnal	сара	acitiv	e se	ens	e re	esist	or v	alue	7							
27	Re	served				To tion		ure	com	patii	bility	/ W	ith fu	ıture	dev	vices	, alv	vay.	s w	/rite	bits	to 0.	Мо	re in	form	atic	on in	1	2 Cc	nven-
26	CS	RESEN	1			0				RW	'		Cap	acit	ive	Sens	se N	l lod	le l	nter	nal	Resis	stor	En	able					
	En	able/dis	able	the	inte	rnal	cap	acit	tive	sens	e re	esis	stor.																	
25	Re	served				To tion		ure	con	patii	bility	/ W	ith fu	iture	dev	vices	, alv	way.	s w	rite	bits	to 0.	Мо	re in	form	atio	on in	1.	2 Cc	nven-
24	VL	PSEL				0				RW	,		Lov	/-Po	wer	San	nple	ed V	/olt	tage	Sel	ectic	n							
	Se	lect the	inpu	ıt to	the	sam	pled	d vo	ltage	e VL	Р																			
	Va	lue				Мо	de					Description																		
	0					VAI	DIV					VADIV																		
	1					VBI	DIV						VBDIV																	

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

tions

Reserved

23

Bit	Name	Reset	Access	Description
22	VBSEL	0	RW	VB Selection
	Select the input for the	e VB Divider		
	Value	Mode		Description
	0	1V25		1.25V
	1	2V5		2.50V
21:16	VASEL	0x00	RW	VA Selection
	Select the input for the	e VA Divider		
	Mode	Value		Description
	VDD	0x0		ACMPVDD
	APORT2YCH0	0x1		APORT2Y Channel 0
	APORT2YCH2	0x3		APORT2Y Channel 2
	APORT2YCH4	0x5		APORT2Y Channel 4
	APORT2YCH30	0x1f		APORT2Y Channel 30
	APORT1XCH0	0x20		APORT1X Channel 0
	APORT1YCH1	0x21		APORT1Y Channel 1
	APORT1XCH2	0x22		APORT1X Channel 2
	APORT1YCH3	0x23		APORT1Y Channel 3
	APORT1XCH4	0x24		APORT1X Channel 4
	APORT1YCH5	0x25		APORT1Y Channel 5
	APORT1XCH30	0x3e		APORT1X Channel 30
	APORT1YCH31	0x3f		APORT1Y Channel 31
15:8	NEGSEL	0x00	RW	Negative Input Select
	Select negative input.			
	APORT0XCH0	0x00		Dedicated APORT0X Channel 0
	APORT0XCH1	0x01		Dedicated APORT0X Channel 1
	APORT0XCH2	0x02		Dedicated APORT0X Channel 2
	APORT0XCH15	0x0f		Dedicated APORT0X Channel 15
	APORT0YCH0	0x10		Dedicated APORT0Y Channel 0
	APORT0YCH1	0x11		Dedicated APORT0Y Channel 1
	APORT0YCH2	0x12		Dedicated APORT0Y Channel 2
	APORT0YCH15	0x1f		Dedicated APORT0Y Channel 15

Name	Reset	Access	Description
APORT1XCH0	0x20		APORT1X Channel 0
APORT1YCH1	0x21		APORT1Y Channel 1
APORT1XCH2	0x22		APORT1X Channel 2
APORT1YCH3	0x23		APORT1Y Channel 3
APORT1XCH4	0x24		APORT1X Channel 4
APORT1YCH5	0x25		APORT1Y Channel 5
APORT1XCH30	0x3e		APORT1X Channel 30
APORT1YCH31	0x3f		APORT1Y Channel 31
APORT2YCH0	0x40		APORT2Y Channel 0
APORT2XCH1	0x41		APORT2X Channel 1
APORT2YCH2	0x42		APORT2Y Channel 2
APORT2XCH3	0x43		APORT2X Channel 3
APORT2YCH4	0x44		APORT2Y Channel 4
APORT2XCH5	0x45		APORT2X Channel 5
APORT2YCH30	0x5e		APORT2Y Channel 30
APORT2XCH31	0x5f		APORT2X Channel 31
APORT3XCH0	0x60		APORT3X Channel 0
APORT3YCH1	0x61		APORT3Y Channel 1
APORT3XCH2	0x62		APORT3X Channel 2
APORT3YCH3	0x63		APORT3Y Channel 3
APORT3XCH4	0x64		APORT3X Channel 4
APORT3YCH5	0x65		APORT3Y Channel 5
			•••
APORT3XCH30	0x7e		APORT3X Channel 30
APORT3YCH31	0x7f		APORT3Y Channel 31
APORT4YCH0	0x80		APORT4Y Channel 0
APORT4XCH1	0x81		APORT4X Channel 1
APORT4YCH2	0x82		APORT4Y Channel 2
APORT4XCH3	0x83		APORT4X Channel 3
APORT4YCH4	0x84		APORT4Y Channel 4
APORT4XCH5	0x85		APORT4X Channel 5
APORT4YCH30	0x9e		APORT4Y Channel 30
APORT4XCH31	0x9f		APORT4X Channel 31
DACOUT0	0xf2		DAC Channel 0 Output

				a real and a service of the service
Bit	Name	Reset	Access	Description
	DACOUT1	0xf3		DAC Channel 1 Output
	VLP	0xfb		Low-Power Sampled Voltage
	VBDIV	0xfc		Divided VB Voltage
	VADIV	0xfd		Divided VA Voltage
	VDD	0xfe		ACMPVDD as selected via PWRSEL
	VSS	0xff		VSS
7:0	POSSEL	0x00	RW	Positive Input Select
	Select positive input.			
	APORT0XCH0	0x00		Dedicated APORT0X Channel 0
	APORT0XCH1	0x01		Dedicated APORT0X Channel 1
	APORT0XCH2	0x02		Dedicated APORT0X Channel 2
	APORT0XCH15	0x0f		Dedicated APORT0X Channel 15
	APORT0YCH0	0x10		Dedicated APORT0Y Channel 0
	APORT0YCH1	0x11		Dedicated APORT0Y Channel 1
	APORT0YCH2	0x12		Dedicated APORT0Y Channel 2
				•••
	APORT0YCH15	0x1f		Dedicated APORT0Y Channel 15
	APORT1XCH0	0x20		APORT1X Channel 0
	APORT1YCH1	0x21		APORT1Y Channel 1
	APORT1XCH2	0x22		APORT1X Channel 2
	APORT1YCH3	0x23		APORT1Y Channel 3
	APORT1XCH4	0x24		APORT1X Channel 4
	APORT1YCH5	0x25		APORT1Y Channel 5
	APORT1XCH30	0x3e		APORT1X Channel 30
	APORT1YCH31	0x3f		APORT1Y Channel 31
	APORT2YCH0	0x40		APORT2Y Channel 0
	APORT2XCH1	0x41		APORT2X Channel 1
	APORT2YCH2	0x42		APORT2Y Channel 2
	APORT2XCH3	0x43		APORT2X Channel 3
	APORT2YCH4	0x44		APORT2Y Channel 4
	APORT2XCH5	0x45		APORT2X Channel 5
	APORT2YCH30	0x5e		APORT2Y Channel 30
	APORT2XCH31	0x5f		APORT2X Channel 31

Bit	Name	Reset Acces	ss Description
	APORT3XCH0	0x60	APORT3X Channel 0
	APORT3YCH1	0x61	APORT3Y Channel 1
	APORT3XCH2	0x62	APORT3X Channel 2
	APORT3YCH3	0x63	APORT3Y Channel 3
	APORT3XCH4	0x64	APORT3X Channel 4
	APORT3YCH5	0x65	APORT3Y Channel 5
	APORT3XCH30	0x7e	APORT3X Channel 30
	APORT3YCH31	0x7f	APORT3Y Channel 31
	APORT4YCH0	0x80	APORT4Y Channel 0
	APORT4XCH1	0x81	APORTAX Channel 1
	APORT4YCH2	0x82	APORT4Y Channel 2
	APORT4XCH3	0x83	APORT4X Channel 3
	APORT4YCH4	0x84	APORT4Y Channel 4
	APORT4XCH5	0x85	APORT4X Channel 5
	• • •		•••
	APORT4YCH30	0x9e	APORT4Y Channel 30
	APORT4XCH31	0x9f	APORT4X Channel 31
	DACOUT0	0xf2	DAC Channel 0 Output
	DACOUT1	0xf3	DAC Channel 1 Output
	VLP	0xfb	Low-Power Sampled Voltage
	VBDIV	0xfc	Divided VB Voltage
	VADIV	0xfd	Divided VA Voltage
	VDD	0xfe	ACMPVDD as selected via PWRSEL
	VSS	0xff	VSS

25.5.3 ACMPn_STATUS - Status Register

Offset															Ві	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	19	6	8	7	9	5	4	က	2	_	0
Reset					'											'											'		0	0	0	0
Access																													22	~	R	<u>~</u>
Name																													EXTIFACT	APORTCONFLICT	ACMPOUT	ACMPACT

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	EXTIFACT	0	R	External Override Interface Active
	This bit is set when the	ne external overri	ide interfac	ce is ready to use.
2	APORTCONFLICT	0	R	APORT Conflict Output
	1 if any of the APORT	Γ BUSes being re	equested b	by the ACMPn are also being requested by another peripheral
1	ACMPOUT	0	R	Analog Comparator Output
	Analog comparator or	utput value.		
0	ACMPACT	0	R	Analog Comparator Active
	Analog comparator a	ctive status.		

25.5.4 ACMPn_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset			'	•	'	•					•					'					<u>'</u>			'			'			0	0	0
Access																														2	22	~
Name																														APORTCONFLICT	WARMUP	EDGE

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure contions	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2	APORTCONFLICT	0	R	APORT Conflict Interrupt Flag
	1 if any of the APOR	Γ BUSes being r	equested l	by the ACMPn are also being requested by another peripheral
1	WARMUP	0	R	Warm-up Interrupt Flag
	Indicates that the ana	alog comparator	warm-up p	period is finished.
0	EDGE	0	R	Edge Triggered Interrupt Flag
	Indicates that there h	as been a rising	or falling e	edge on the analog comparator output.

25.5.5 ACMPn_IFS - Interrupt Flag Set Register

Offset															Bi	it Po	ositi	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•		•	•												•		•									•	0	0	0
Access																														W	×	W
Name																														APORTCONFLICT	WARMUP	EDGE

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2	APORTCONFLICT	0	W1	Set APORTCONFLICT Interrupt Flag
	Write 1 to set the AP	ORTCONFLICT	interrupt fla	ag
1	WARMUP	0	W1	Set WARMUP Interrupt Flag
	Write 1 to set the WA	RMUP interrupt	flag	
0	EDGE	0	W1	Set EDGE Interrupt Flag
	Write 1 to set the ED	GE interrupt flag		

25.5.6 ACMPn_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	80	7	9	2	4	က	7	_	0
Reset			<u> </u>		1									'		'											'	•		0	0	0
Access																														(R)W1	(R)W1	(R)W1
Name																														APORTCONFLICT	WARMUP	EDGE

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2	APORTCONFLICT	0	(R)W1	Clear APORTCONFLICT Interrupt Flag
	Write 1 to clear the A rupt flags (This feature			flag. Reading returns the value of the IF and clears the corresponding interv in MSC.).
1	WARMUP	0	(R)W1	Clear WARMUP Interrupt Flag
	Write 1 to clear the W (This feature must be		•	ading returns the value of the IF and clears the corresponding interrupt flags .
0	EDGE	0	(R)W1	Clear EDGE Interrupt Flag
	Write 1 to clear the E (This feature must be	•	•	g returns the value of the IF and clears the corresponding interrupt flags .

25.5.7 ACMPn_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset				•										'		'					<u>'</u>			'			'			0	0	0
Access																														₽	Z.	₩ M
Name																														APORTCONFLICT	WARMUP	EDGE

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	APORTCONFLICT	0	RW	APORTCONFLICT Interrupt Enable
	Enable/disable the Al	PORTCONFLIC	T interrupt	
1	WARMUP	0	RW	WARMUP Interrupt Enable
	Enable/disable the W	ARMUP interrup	ot	
0	EDGE	0	RW	EDGE Interrupt Enable
	Enable/disable the El	DGE interrupt		

25.5.8 ACMPn_APORTREQ - APORT Request Status Register

Offset	Bit Position							
0x020	33 34 35 36 37 38 39 30 30 30 30 31 32 33 34 44 45 46 47 47 48 40 <th>တ ထ</th> <th>7</th> <th>9 4</th> <th>4</th> <th>3</th> <th>7 7</th> <th>- 0</th>	တ ထ	7	9 4	4	3	7 7	- 0
Reset		0 0	0	0	0	0	0	0
Access		<u>م</u> م	2	<u>م</u> م	2 2	R	<u>م</u> 0	۷ مر
Name		APORT4YREQ APORT4XREQ	APORT3YREQ	APORT3XREQ	2 2	APORT1YREQ	APORT1XREQ	ORTOXRE

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
9	APORT4YREQ	0	R	1 If the Bus Connected to APORT4Y is Requested
	Reports if the bus cor	nnected to APOI	RT4Y is be	ing requested from the APORT
8	APORT4XREQ	0	R	1 If the Bus Connected to APORT4X is Requested
	Reports if the bus cor	nected to APOI	RT4X is be	ing requested from the APORT
7	APORT3YREQ	0	R	1 If the Bus Connected to APORT3Y is Requested
	Reports if the bus cor	nnected to APOI	RT3Y is be	ing requested from the APORT
6	APORT3XREQ	0	R	1 If the Bus Connected to APORT3X is Requested
	Reports if the bus cor	nnected to APOI	RT3X is be	ing requested from the APORT
5	APORT2YREQ	0	R	1 If the Bus Connected to APORT2Y is Requested
	Reports if the bus cor	nnected to APOI	RT2Y is be	ing requested from the APORT
4	APORT2XREQ	0	R	1 If the Bus Connected to APORT2X is Requested
	Reports if the bus cor	nnected to APOI	RT2X is be	ing requested from the APORT
3	APORT1YREQ	0	R	1 If the Bus Connected to APORT1X is Requested
	Reports if the bus cor	nnected to APOI	RT1X is be	ing requested from the APORT
2	APORT1XREQ	0	R	1 If the Bus Connected to APORT2X is Requested
	Reports if the bus cor	nnected to APOI	RT2X is be	ing requested from the APORT
1	APORT0YREQ	0	R	1 If the Bus Connected to APORT0Y is Requested
	Reports if the bus cor	nnected to APOI	RT0Y is be	ing requested from the APORT
0	APORT0XREQ	0	R	1 If the Bus Connected to APORT0X is Requested
	Reports if the bus cor	nected to APOI	RT0X is be	ing requested from the APORT

25.5.9 ACMPn_APORTCONFLICT - APORT Conflict Status Register

Offset	Bit Position									
0x024	33 34 35 36 37 38 39 30 30 31 32 33 34 35 36 37 38 39 30 30 30 30 30 30 30 30 30 40 <th>6</th> <th>ω</th> <th>7</th> <th>9 2</th> <th>4</th> <th>က</th> <th>7</th> <th>-</th> <th>0</th>	6	ω	7	9 2	4	က	7	-	0
Reset		0	0	0	0 0	0	0	0	0	0
Access		R	2	<u>م</u>	<u>م</u> م	2	2	2	2	<u>~</u>
Name		APORT4YCONFLICT	APORT4XCONFLICT		APORT3XCONFLICT APORT2YCONFLICT	APORT2XCONFLICT	APORT1YCONFLICT	APORT1XCONFLICT	ORTOYCONFLI	APORT0XCONFLICT

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9	APORT4YCONFLICT	0	R	1 If the Bus Connected to APORT4Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT4Y is is a	also being requested by another peripheral
8	APORT4XCONFLICT	0	R	1 If the Bus Connected to APORT4X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT4X is is a	also being requested by another peripheral
7	APORT3YCONFLICT	0	R	1 If the Bus Connected to APORT3Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT3Y is is	also being requested by another peripheral
6	APORT3XCONFLICT	0	R	1 If the Bus Connected to APORT3X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT3X is is	also being requested by another peripheral
5	APORT2YCONFLICT	0	R	1 If the Bus Connected to APORT2Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT2Y is is	also being requested by another peripheral
4	APORT2XCONFLICT	0	R	1 If the Bus Connected to APORT2X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT2X is is	also being requested by another peripheral
3	APORT1YCONFLICT	0	R	1 If the Bus Connected to APORT1X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1X is is	also being requested by another peripheral
2	APORT1XCONFLICT	0	R	1 If the Bus Connected to APORT1X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1X is is	also being requested by another peripheral
1	APORT0YCONFLICT	0	R	1 If the Bus Connected to APORT0Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOR	RT0Y is is	also being requested by another peripheral

Bit	Name	Reset	Access	Description
0	APORT0XCONFLICT	0	R	1 If the Bus Connected to APORT0X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT0X is is a	also being requested by another peripheral

25.5.10 ACMPn_HYSTERESIS0 - Hysteresis 0 Register

Offset															Ві	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•			0	OXO							0	nxn		•		•									•			>	3	
Access					2	<u>}</u>							Ž	≥ Y																2	2	
Name					מאלאני	۵ > ک								A V																F0 >I	- 2 - -	

Bit	Name	Reset	Access	Description
31:30	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
29:24	DIVVB	0x00	RW	Divider for VB Voltage When ACMPOUT=0
	Divider to scale VB w	hen ACMPOUT	=0. VBDIV	= VB * (DIVVB+1)/64.
23:22	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	DIVVA	0x00	RW	Divider for VA Voltage When ACMPOUT=0
	Divider to scale VA w	hen ACMPOUT	=0. VADIV	= VA * (DIVVA+1)/64.
15:4	Reserved	To ensure cor tions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	HYST	0x0	RW	Hysteresis Select When ACMPOUT=0

Select hysteresis level when comparator output is 0. The hysteresis levels can vary, please see the electrical characteristics for the device for more information.

Value	Mode	Description
0	HYST0	No hysteresis
1	HYST1	14 mV hysteresis
2	HYST2	25 mV hysteresis
3	HYST3	30 mV hysteresis
4	HYST4	35 mV hysteresis
5	HYST5	39 mV hysteresis
6	HYST6	42 mV hysteresis
7	HYST7	45 mV hysteresis
8	HYST8	No hysteresis
9	HYST9	-14 mV hysteresis
10	HYST10	-25 mV hysteresis
11	HYST11	-30 mV hysteresis
12	HYST12	-35 mV hysteresis
13	HYST13	-39 mV hysteresis
14	HYST14	-42 mV hysteresis
15	HYST15	-45 mV hysteresis

25.5.11 ACMPn_HYSTERESIS1 - Hysteresis 1 Register

Offset															Ві	t Po	siti	on														
0x02C	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset					0	OXO							0	nxn				•							•		•			5	3	
Access					2	<u>}</u>							Ž	≥ Y																20	2	
Name					מאלאני	۵ > ک								A V																FUXI		

Bit	Name	Reset	Access	Description
31:30	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
29:24	DIVVB	0x00	RW	Divider for VB Voltage When ACMPOUT=1
	Divider to scale VB w	hen ACMPOUT	=1. VBDIV	= VB * (DIVVB+1)/64.
23:22	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
21:16	DIVVA	0x00	RW	Divider for VA Voltage When ACMPOUT=1
	Divider to scale VA w	hen ACMPOUT	=1. VADIV	= VA * (DIVVA+1)/64.
15:4	Reserved	To ensure cortions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	HYST	0x0	RW	Hysteresis Select When ACMPOUT=1

Select hysteresis level when comparator output is 1. The hysteresis levels can vary, please see the electrical characteristics for the device for more information.

Value	Mode	Description
0	HYST0	No hysteresis
1	HYST1	14 mV hysteresis
2	HYST2	25 mV hysteresis
3	HYST3	30 mV hysteresis
4	HYST4	35 mV hysteresis
5	HYST5	39 mV hysteresis
6	HYST6	42 mV hysteresis
7	HYST7	45 mV hysteresis
8	HYST8	No hysteresis
9	HYST9	-14 mV hysteresis
10	HYST10	-25 mV hysteresis
11	HYST11	-30 mV hysteresis
12	HYST12	-35 mV hysteresis
13	HYST13	-39 mV hysteresis
14	HYST14	-42 mV hysteresis
15	HYST15	-45 mV hysteresis

25.5.12 ACMPn_ROUTEPEN - I/O Routing Pine Enable Register

Offset															Bi	t Po	siti	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	3	2	_	0
Reset				•	•	•			•					•													•					0
Access																																RW
Name																																OUTPEN
Bit	Na	me					Re	set			Ac	cess	s 1	Des	crip	tion																
31:1	Re	serv	red				To tio		ure	com	pati	bility	/ wit	th fu	ture	dev	ices	s, alv	vay.	s wr	rite k	oits	to 0.	Мо	re ir	forr	natio	on ir	າ 1.2	? Coi	nver	n-
0	OL	JTPE	ΞN				0				RW	/	-	ACN	IP C	utp	ut F	Pin E	Ena	ble												
	En	able	/disa	able	ana	alog	con	npar	ator	out	put t	o pi	n.																			

25.5.13 ACMPn_ROUTELOC0 - I/O Routing Location Register

				_	_		- CIII	9 -				9.51																
Offset													Ві	it Pos	sitio	n												
0x044	30	53	7	7 8	56	25	23	22	2	70	19	9	17	16	15	14	13	2 5	: 6	σ	0 00	7	9	2	4	ი 2	_	0
Reset																										0x00		
Access																										RW		
Name																										OUTLOC		
																										ō		
Bit	Name					Reset			Ac	ces	s	Des	crip	tion														
31:6	Reserv	⁄ed				To ens	sure	con	npat	ibilit	y w	ith fu	ture	devi	ces,	alv	vays	write	bits	to (0. Mc	ore ir	nforn	natic	n in	1.2 Cc	nve	÷n-
5:0	OUTLO	С				0x00			RV	V		I/O I	_oca	ation														
	Decide	s the	e loca	tion	of	the Ol	JT p	in.																				
	Value					Mode						Des	cript	tion														
	0					LOC0						Loca	ation	1 0														_
	1					LOC1						Loca	ation	າ 1														
	2					LOC2						Loca	ation	າ 2														
	3					LOC3						Loca	ation	1 3														
	4					LOC4						Loca	ation	1 4														
	5					LOC5						Loca	ation	า 5														
	6					LOC6						Loca																
	7					LOC7						Loca																
	8					LOC8						Loca																
	9					LOC9						Loca																
	10					LOC1						Loca																
	11					LOC1						Loca																
	12					LOC1						Loca																
	13					LOC1						Loca																
	14					LOC1						Loca																
	15					LOC1						Loca																
	16					LOC1						Loca																
	17					LOC1						Loca																
	18					LOC1						Loca																
	19					LOC1						Loca																
	20					LOC2						Loca																
	21					LOC2						Loca																
	22					LOC2	2					Loca	ation	1 22														

Name	Reset	Access	Description
23	LOC23		Location 23
24	LOC24		Location 24
25	LOC25		Location 25
26	LOC26		Location 26
27	LOC27		Location 27
28	LOC28		Location 28
29	LOC29		Location 29
30	LOC30		Location 30
31	LOC31		Location 31

25.5.14 ACMPn_EXTIFCTRL - External Override Interface Control

Offset		Bit Position																														
0x048	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset		•	•	•							•	•	•	•		•				•						Š	e e				•	0
Access																										2	<u>}</u>					RW
Name																										TOFOCA	2					Z U

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:4	APORTSEL	0x0	RW	APORT Selection for External Interface


Decides which APORT(s) the ACMP will use when controlled by an external module.

Value	Mode	Description
0	APORT0X	APORT0X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT0XCH0.
1	APORT0Y	APORT0Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT0YCH0.
2	APORT1X	APORT1X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT1XCH0.
3	APORT1Y	APORT1Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT1XCH0.
4	APORT1XY	APORT1X/Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT1XCH0.
5	APORT2X	APORT2X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT2YCH0.
6	APORT2Y	APORT2Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT2YCH0.
7	APORT2YX	APORT2Y/X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT2YCH0.
8	APORT3X	APORT3X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT3XCH0.
9	APORT3Y	APORT3Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT3XCH0.
10	APORT3XY	APORT3X/Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT3XCH0.
11	APORT4X	APORT4X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT4YCH0.
12	APORT4Y	APORT4Y used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT4YCH0.
13	APORT4YX	APORT4Y/X used. EXT_BASE = ACMP_INPUTSEL_POS- SEL_APORT4YCH0.

Bit	Name	Reset	Access	Description
3:1	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EN	0	RW	Enable External Interface
	Set to enable an	external module,	, like LESENS	E, to control the ACMP

26. ADC - Analog to Digital Converter





Quick Facts

What?

The ADC is used to convert analog signals into a digital representation and features low-power, autonomous operation.

Why?

In many applications there is a need to measure analog signals and record them in a digital representation, without exhausting the energy source.

How?

A low power ADC samples up to 32 input channels in a programmable sequence. With the help of PRS and DMA, the ADC can operate without CPU intervention in EM2 Deep Sleep and EM3 Stop, minimizing the number of powered up resources. The ADC can further be duty-cycled to reduce the energy consumption.

26.1 Introduction

The ADC uses a Successive Approximation Register (SAR) architecture, with a resolution of up to 12 bits at up to one million samples per second (1 Msps). The integrated input multiplexer can select from external I/Os and several internal signals.

26.2 Features

- Programmable resolution (6/8/12-bit)
 - 13 conversion clock cycles for a 12-bit conversion
 - Maximum 1 Msps @ 12-bit
 - Maximum 1.6 Msps @ 6-bit
- · Configurable acquisition time
- · Externally controllable conversion start time using PRS in TIMED mode
- · Integrated prescaler for conversion clock generation
 - · Selectable clock division factor from 1 to 128
- · Wide conversion clock range: 32 kHz to 16 MHz
- · Can be run during EM2 Deep Sleep and EM3 Stop, waking up the system upon various enabled interrupts
- Can be run during EM2 Deep Sleep and EM3 Stop with DMA enabled to pull data from the FIFOs without waking up the system
- Supports up to 144 external input channels and several internal inputs
 - Includes temperature sensor and random number generator function
- · Left or right adjusted results
 - · Results in 2's complement representation
 - · Differential results sign extended to 32-bits results
- · Programmable scan sequence
 - · Up to 32 configurable samples in scan sequence
 - · Mask to select which pins are included in the sequence
 - · Triggered by software or PRS input
 - · One shot or repetitive mode
 - · Oversampling available
 - · Four deep FIFO to store conversion data along with channel ID and option to overwrite old data when full
 - · Programmable watermark (DVL) to generate SCAN interrupt
 - · Supports overflow and underflow interrupt generation
 - · Supports window compare function
 - · Conversion tailgating support for predictable periodic scans
- · Programmable single channel conversion
 - · Triggered by software or PRS input
 - · Can be interleaved between two scan sequences
 - · One shot or repetitive mode
 - · Oversampling available
 - · Four deep FIFO to store conversion data with option to overwrite old data when full
 - programmable watermark (DVL) to generate SINGLE interrupt
 - · Supports overflow and underflow interrupt generation
 - Supports window compare function
- · Hardware oversampling support
 - · 1st order accumulate and dump filter
 - From 2 to 4096 oversampling ratio (OSR)
 - · Results in 16-bit representation
 - · Enabled individually for scan sequence and single channel mode
 - · Common OSR select
- Programmable and preset input full scale (peak-to-peak) range (VFS) with selectable reference sources
 - VFS=1.25 V using internal VBGR reference
 - · VFS=2.5 V using internal VBGR reference
 - · VFS=AVDD with AVDD as reference source
 - VFS=5 V with internal VBGR reference
 - · Single ended external reference
 - · Differential external reference
 - VFS=2xAVDD with AVDD as reference source
 - · User-programmable dividers for flexible VFS options from internal, external or supply voltage reference sources

- · Support for offset and gain calibration
- · Interrupt generation and/or DMA request when
 - · Programmable number of converted data available in the single FIFO (also generates DMA request)
 - · Programmable number of converted data available in the scan FIFO (also generates DMA request)
 - · Single FIFO overflow or underflow
 - · Scan FIFO overflow or underflow
 - · Latest Single conversion tripped compare logic
 - · Latest Scan conversion tripped compare logic
 - · Analog over-voltage interrupt
 - Programming Error interrupt due to APORT Bus Request conflict or NEGSEL programming error

26.3 Functional Description

An overview of the ADC is shown in Figure 26.1 ADC Overview on page 845.




Figure 26.1. ADC Overview

26.3.1 Clock Selection

The ADC logic is partitioned into two clock domains: HFPERCLK and ADC_CLK. The HFPERCLK domain contains the register interface logic, APORT request logic and portions of FIFO read logic. The HFPERCLK is the default clock for the ADC peripheral. The rest of the ADC is clocked by the ADC CLK domain. The ADC CLK is chosen by ADCCLKMODE bit in the ADCn CTRL register.

The ADC_CLK is the main clock for the ADC engine. If the ADCCLKMODE is set to SYNC, the ADC_CLK is equal to the HFPERCLK and the ADC operates in synchronous mode. If the ADCCLKMODE is set to ASYNC, the ADC_CLK is ASYNCCLK and the ADC operates in asynchronous mode. This distinction is important to understand as there are additional system restrictions and benefits to running the ADC in asynchronous mode detailed in 26.3.15 ASYNC ADC_CLK Usage Restrictions and Benefits.

Note: Whenever ADC is being used in asynchronous mode, then HFPERCLK must be at least 1.5 times higher than the ADC_CLK.

The ADC has an internal clock prescaler, controlled by PRESC bits in ADCn_CTRL, which can divide the ADC_CLK by any factor between 1 and 128 to generate the conversion clock (adc_clk_sar) for the ADC. This adc_clk_sar is also used to generate acquisition timing. Note that the maximum clock frequency for adc_clk_sar is 16 MHz. The ADC warmup time is determined by ADC_CLK and not by adc_clk_sar.

ASYNCCLK is a clock source from the CMU which is considered asynchronous to HFPERCLK. The CMU_ADCCTRL register can be programmed to request and use ASYNCCLK. It has multiple choices for its source, including AUXHFRCO, HFXO and HFSRCCLK, and can optionally be inverted. If the chosen source for ASYNCCLK is not active at the time of request, the CMU enables the source oscillator upon receiving the request, and shuts down the oscillator when the ADC stops requesting the clock. Consult the CMU chapter for details of how to program the clock sources for the ASYNCCLK and oscillator start-up time details.

Software may choose a clock request generation scheme by programming the ASYNCCLKEN and WARMMODE of the ADCn_CTRL register. If the ASYNCCLKEN is set to ASNEEDED with WARMMODE set to NORMAL, the ADC requests ASYNCCLK only when a conversion trigger is activated. The ASYNCCLK request is withdrawn after the conversion is complete. All other options keep the ASYNCCLK request "ON" until software programs these fields otherwise or changes the ADCCLKMODE to SYNC.

For EM2 Deep Sleep or EM3 Stop operation of the ADC, the ADC_CLK must be configured for AUXHFRCO as this is the only available option during EM2 Deep Sleep or EM3 Stop. The ADC_CLK source should not be changed as the system enters or exits various energy modes, otherwise measurement inaccuracies will result.

26.3.2 Conversions

A conversion consists of two phases: acquisition and approximation. The input is sampled in the acquisition phase before it is converted to digital representation during the approximation phase. The acquisition time can be configured independently for scan sequence and single channel conversions (see 26.3.3 ADC Modes) by setting AT in ADCn_SINGLECTRL/ADCn_SCANCTRL. The acquisition times can be set to 1, 2, 3 or any integer power of 2 from 4 to 256 adc clk sar cycles.

Note: For high impedance sources the acquisition time should be adjusted to allow enough time for the internal sample capacitor to fully charge. The minimum acquisition time for sampling at 1 Msps and typical input loading is 187.5 ns.

The ADC uses one adc clk sar cycle per output bit in the approximation phase plus 1 extra adc clk sar cycle.

Where T_{acq} is the acquisition time set by the AT bit field, N is the resolution (in bits), and OVSRSEL is the oversampling ratio according to the OVSRSEL field in ADCn_CTRL when oversampling is enabled (see 26.3.10.6 Oversampling).

Figure 26.2. ADC Total Conversion Time Per Output




Figure 26.3. ADC Conversion Timing

26.3.3 ADC Modes

The ADC contains two programmable modes: single channel mode and scan mode. Both modes have separate configuration registers and a four-deep FIFO for conversion results. Both modes may be set up to run only once per trigger or to automatically repeat after each operation. The scan mode has priority over the single channel mode. However by default, if scan sequence is running, a triggered single channel conversion will be interleaved between two scan samples.

26.3.3.1 Single Channel Mode

Single channel mode can be used to convert a single channel either once per trigger or repetitively. The configuration of single channel mode is done using the ADCn_SINGLECTRL and ADCn_SINGLECTRLX registers and the result FIFO can be read through the ADCn_SINGLEDATA register. The DVL field of the ADCn_SINGLECTRLX controls the FIFO watermark crossing which sets the SINGLEDV bit in ADCn_STATUS high and is cleared when the data is read and the number of unread data samples falls below the DVL threshold. The user can choose to throw out new samples or overwrite the old samples when the FIFO becomes full by programming the FIFOOFACT field of the ADCn_SINGLECTRLX register. Single channel results can also be read through ADCn_SINGLEDATAP without popping the FIFO, returning its latest element. The DIFF field in ADCn_SINGLECTRL selects whether differential or single ended inputs are used and POSSEL and NEGSEL selects the input signal(s). The CMPEN bit in the ADCn_SINGLECTRL register enables the window compare function, and the latest converted data is compared against values programmed into the ADGT and ADLT fields of the ADCn_CMPTHR register and generates SINGLECMP interrupts if enabled. The window compare function allows for compare triggering both within (if ADGT less than ADLT) or out of (if ADGT greater than ADLT) window.

26.3.3.2 Scan Mode

Scan mode is used to perform conversions across multiple channels, sweeping a set of selected inputs in a sequence. The configuration of scan mode is done in the ADCn_SCANCTRL and ADCn_SCANCTRLX registers. It has similar controls and data read mechanisms to single channel mode. There are two key differences between single channel mode and scan mode: the input sequence is programmed differently, and it has additional information in the result to indicate the channel on which the conversion was acquired. 26.3.7 Input Selection explains how the input sequence is chosen. When the scan sequence is triggered, the ADC samples all inputs that are included in the mask (ADCn_SCANMASK), starting at the lowest pin number. DIFF in ADCn_SCANCTRL selects whether single ended or differential inputs are used. The FIFO data is tagged with SCANINPUTID and can be read along with the scan data using ADCn_SCANDATAX register. The ADCn_SCANDATAXP can be used to read the latest valid entry from the scan FIFO without popping it. There is also a ADCn_SCANDATA register that contains results without the SCANINPUTID appended.

Note: If using scan mode with ADCn_SCANCTRL_REP = 1 and ADCn_SCANCTRLX_REPDELAY = NODELAY, the last channel in the scan will report a SCANINPUTID of 0. Using ADCn_SCANCTRLX_REPDELAY with any value other than NODELAY will report the correct SCANINPUTID.

26.3.4 Warm-up Time

After power-on, the ADC requires some time for internal bias currents and references to settle prior to starting a conversion. This time period is called the warm-up time. Warm-up timing is performed by hardware. Software must program the number of ADC_CLK cycles required to count at least 1 μ s in the TIMEBASE field of the ADCn_CTRL register. TIMEBASE only affects the timing of the warm-up sequence and is not dependent on adc_clk_sar. When enabling the ADC or changing references between samples, the ADC is automatically warmed up for 5 μ s (5 times the period indicated by TIMEBASE).

Normally, the ADC will be warmed up only when samples are requested and is shut off when there are no more samples waiting. However, if lower latency is needed, configuring the WARMUPMODE field in ADCn_CTRL allows the ADC and/or reference to stay warm between samples, reducing the warm-up time or eliminating it altogether. Figure 26.4 ADC Analog Power Consumption With Different WARMUPMODE Settings on page 849 shows the effects on analog power consumption in scenarios using different WARMUPMODE settings.

The user can program which reference should be kept warm in the CHCONREFWARMIDLE bitfield in the ADCn_CTRL register. By default the scan mode reference is kept warm. The user can also choose to keep the single channel mode reference warm or to keep the last used reference warm. If the default setting is kept (scan mode reference is to be kept warm) and if the single-mode reference setting is different than scan-mode, then single mode conversions will first warmup its reference for 5 µs before a conversion can begin.

Various warmup modes are described here:

- NORMAL: This is the lowest power option for general-purpose use and low sampling rates (below 35 ksps). The ADC and references are shut off when there are no samples waiting. The ADC does not consume any power when it is shut down. A 5 µs warmup time will be initiated prior to every conversion. Figure a in Figure 26.4 ADC Analog Power Consumption With Different WARMUP-MODE Settings on page 849 shows this mode.
- KEEPINSTANDBY: This mode is suitable for infrequent sampling of lower impedance inputs, and is the lowest power option for sampling rates between about 35 and 125 ksps. It may also be useful for lower sampling rates where latency is important. The reference selected for scan mode is kept warm, but the ADC is powered down. The ADC will initiate a 1 µs warmup period before a conversion begins. Because the reference is kept warm, the ADC will consume a small amount of standby current when it is not converting. Figure b in Figure 26.4 ADC Analog Power Consumption With Different WARMUPMODE Settings on page 849 shows this mode.
- KEEPINSLOWACC: This mode is useful for high-impedance inputs which are sampled infrequently. It is similar to KEEPINSTAND-BY, but continuously tracks the input, keeping the input multiplexer connected to the APORT bus. This mode consumes little more power than KEEPINSTANDBY mode (about 2 µA extra) when a conversion is not in progress. This allows the user to avoid programming long acquisition time that would otherwise be necessary for high-impedance inputs when ADC wakes up to full power mode, thereby reducing the total current consumption per conversion.
- KEEPADCWARM: This mode provides the lowest latency and allows for maximum sampling rates. The ADC and reference circuitry
 remain powered on even when conversions are not in progress. Figure c in Figure 26.4 ADC Analog Power Consumption With Different WARMUPMODE Settings on page 849 shows this mode. This mode consumes the most power, but as soon as a trigger
 event occurs, the acquisition and conversion begin with no warm-up time. Note that if KEEPADCWARM mode is set and HFXO is
 selected as the ADC clock source, the HFXO will remain on in EM2.

When KEEPADCWARM is chosen, ADC is termed as being in continuous operation. When any other warmup mode is chosen, ADC is termed to be in duty-cycled operation.

When entering EM2 Deep Sleep or EM3 Stop, if the ADC is not going to be used, it should be returned to an idle state and WARMUP-MODE in ADCn_CTRL written to 0. Refer to 26.3.17 ADC Programming Model for more information on placing the ADC in an idle state. If the ADC is going to be used in these low energy modes, the user can use any of the WARMUPMODE settings, but should be mindful of the power consumption that comes along with the different mode settings. For EM2 Deep Sleep or EM3 Stop operation, the ADC clock source must be configured to use AUXHFRCO.




Figure 26.4. ADC Analog Power Consumption With Different WARMUPMODE Settings

Note: When using any warm-up mode other than NORMAL, always switch back to the NORMAL mode before switching to another warm-up mode.

26.3.5 Power Supply

The ADC block power (V_{ADC}) is derived from the VDDX_ANA supply rail. VDDX_ANA can be selected from the AVDD or DVDD supply pins using the EMU_PWRCTRL_ANASW bit field.

26.3.6 Input Pin Considerations

For external ADC inputs routed through the APORT, the maximum supported analog input voltage will be limited to the MIN(V_{ADC} , IOVDD) (where V_{ADC} is VDDX_ANA, as described in 26.3.5 Power Supply). Note that pins configured as ADC inputs should disable OVT (by setting the corresponding GPIO_Px_OVTDIS bit) to reduce any potential distortion introduced by the OVT circuitry.

ADC external reference inputs are not routed through the APORT, and the maximum supported analog input voltage for an external reference will also be limited to the $MIN(V_{ADC}, IOVDD)$.

26.3.7 Input Selection

The ADC samples and converts the analog voltage differential at its positive and negative voltage inputs. The input multiplexers of the ADC can connect these inputs to one of several internal nodes (e.g., temperature sensor) or to external signals via analog ports (APORT0, APORT1, APORT2, APORT3 or APORT4).

The analog ports APORT1, APORT2, APORT3, and APORT4 connect to external pins via analog buses (BUSAX, BUSAY, BUSAY, etc.) which are shared among other analog peripherals on the device. APORT1 through APORT4 are each 32 channels wide with connections to two sub-buses: a 16-channel X bus and a 16-channel Y bus. In the ADC module, all X buses connect to the INP_MUX and all Y buses connect to the INN_MUX as shown in Figure 26.5 APORT Connection to the ADC on page 850. Connections to the X and Y sub-buses alternate channels on the APORT. On APORT1 and APORT3, even-numbered channels connect to the X bus, and odd-numbered channels connect to the Y bus. On APORT2 and APORT4, even-numbered channels connect to the Y bus and odd-numbered channels connect to the X bus. The APORT to BUS mappings may vary from device to device, Refer to the APORT Client Map in the device data sheet for exact mappings.

Unlike APORT1 through APORT4, APORT0 is not a shared resource. It consists of a 16-channel X bus and a 16-channel Y bus, each with dedicated I/O pin connections. Note that APORT0 is not available on all device families.




Figure 26.5. APORT Connection to the ADC

For differential measurements, one input must be chosen from an X bus and the other from a Y bus. Choosing both inputs from an X bus or both from a Y bus will generate a PROGERR interrupt (if enabled) of NEGSELCONF type. The PROGERR type can be checked in the ADCn_STATUS register.

The mapping and availability for external I/O connections to ADC0 inputs is shown in device data sheet.

Multiple peripherals may request the same shared system bus (BUSAX, BUSAY, BUSBX, etc.). When this happens, a conflict status is generated and that bus is kept floating. If this happens with the ADC, the PROGERR field in ADCn_STATUS is set to BUSCONF, and an interrupt may be generated (if enabled). When connecting dedicated I/Os through APORTO, all inputs are available to APORTOX and APORTOY and no bus conflict is possible. Refer to 26.3.7.3 APORT Conflicts for more information on identifying and resolving bus conflicts.

Note: The internal inputs can only be sampled in single channel, single-ended mode. NEGSEL should be fixed to VSS for these conversions

26.3.7.1 Configuring ADC Inputs in Single Channel Mode

In single channel mode, the ADCn_SINGLECTRL register provides the POSSEL and NEGSEL selection for positive and negative channel selection of the ADC. The APORT Client Map provides external pin to internal bus channel mapping enumeration for a particular device. Software can also choose internal nodes for POSSEL.

For single-ended conversions on external (APORT-connected) signals, POSSEL and NEGSEL are fully configurable. However, when performing conversions on internal signals, NEGSEL must be set to VSS. This NEGSEL reconfigurability feature in single-ended mode may not be available in all devices. If compatibility with devices that do not support this feature is desired, NEGSEL should be set to VSS for all single channel single-ended conversions.

Note that in both the POSSEL and NEGSEL fields, it is possible to choose inputs from both X and Y buses, even though X channels are physically connected to the positive mux (INP_MUX) and Y channels are physically connected to the negative mux (INN_MUX). For single-ended operation (DIFF = 0), if the positive input is chosen from a Y channel the ADC performs a negative single ended conversion and automatically inverts the result at the end, producing a positive result. For differential conversions (DIFF = 1), if a Y channel is chosen for the positive input and an X channel is chosen for the negative input, the ADC result will be inverted to produce the correct polarity.

Refer to device-specific data sheet for specific pin connection options. Note that the same I/O pin may appear in multiple locations.

26.3.7.2 Configuring ADC Inputs in Scan Mode

In scan mode, the ADC can sample and convert up to 32 external channels on each conversion trigger. Internal channels are not available in scan mode. The ADC's scanner logic automatically changes the input mux settings between conversions, eliminating the need for firmware intervention.

The ADC scanner logic is controlled by a set of 32 logical channels called SCANINPUTIDs. The 32 SCANINPUTIDs are arranged in four groups of 8 channels each. Each channel group can point to a predefined series of 8 sequential channels on any of the available APORTs. The ADCn_SCANINPUTSEL register is used to configure which group of physical APORT channels each of the SCANINPUTID channel groups map to. For example, selecting APORT1CH16TOCH23 in the INPUT7TO0SEL field selects APORT1CH16 for SCANINPUTID0, APORT1CH17 for SCANINPUTID1, APORT1CH18 for SCANINPUTID2, and so on.

The four SCANINPUTID groups are fully independent and may be selected from any APORT in any combination. It is possible also to repeat the same selection in multiple groups. For example, the user may select APORT2CH0TOCH7 for all four of the SCANINPUTID groups.

In many cases, the user application will not require all 32 channels of the scanner to be converted. Each of the scanner channels may be individually enabled according to the needs of the system. The ADCn_SCANMASK register is used to enable and disable individual SCANINPUTIDs. The bits in the ADCnSCANMASK register correspond one-to-one with the SCANINPUTID channel numbers. During a scan operation, the ADC scanner logic will convert only the enabled SCANINPUTIDs, in order from lowest to highest.

In single-ended mode, all conversions performed by the ADC will be relative to VSS. For any enabled SCANINPUTID, the selected APORT channel will be connected to the ADC with the opposite ADC input terminal connected to VSS. Note that the channel groups selected in ADCn_SCANINPUTSEL point to a block of 8 channels on an APORT, which includes both X and Y channels. Depending on the channels enabled by ADCn_SCANMASK, the ADC may perform conversions on the X or the Y bus associated with that APORT.

Figure 26.6 ADC Single-ended Scan Mode Example on page 852 shows an example of a single-ended scan configuration. In this example, ADCn_SCANINPUTSEL has been configured to place APORT1CH16TO23 in the first, third, and fourth channel groups. APORT4CH8TO15 has been placed in the second channel group. ADCn_SCANMASK selects six of these channels for inclusion in the scan. When an ADC scan is initiated with this configuration, the ADC begins at SCANINPUTID0 and converts each enabled channel in turn. This scan configuration results in a set of six single-ended ADC conversions: PF0, PF3, PA5, PA5, PF7, and PF4.




Figure 26.6. ADC Single-ended Scan Mode Example

In differential mode, the default operation of the ADC scanner is to perform a differential measurement between the selected APORT channel and the next channel on that APORT. For example, if the enabled SCANINPUTID points to APORT1CH6, the ADC will perform a differential conversion between APORT1CH6 and APORT1CH7.

There are two exceptions to this rule, listed in order of precedence:

- 1. When converting SCANINPUTID15, the differential conversion will be performed between the channel selected by SCANINPUTID15 and the channel selected by SCANINPUTID8.
- 2. When APORTnCH31 is the selected input, the differential conversion will be performed between APORTnCH31 and APORTnCH0.

Figure 26.7 ADC Differential Scan Mode Example on page 853 shows an example of a differential scan configuration. In this example, ADCn_SCANINPUTSEL has been configured to place APORT1CH16TO23 in the first, third, and fourth channel groups. APORT4CH8TO15 has been placed in the second channel group. ADCn_SCANMASK selects three channels pairs for inclusion in the scan. When an ADC scan is initiated with this configuration, the ADC begins at SCANINPUTID0 and converts each enabled channel in turn. This scan configuration results in a set of three differential ADC conversions: PF0-PF1, PF2-PF3, and PA4-PA5.

SCANINPUTSEL	APORT1CH16TO23					3	APORT1CH16TO23							APORT4CH8TO15							APORT1CH16TO23						;					
APORT-Channel (Positive)	1-23	1-22	1-21	1-20	1-19	1-18	1-17	1-16	1-23	1-22	1-21	1-20	1-19	1-18	1-17	1-16	4-15	4-14	4-13	4-12	4-11	4-10	4-9	4-8	1-23	1-22	1-21	1-20	1-19	1-18	1-17	1-16
APORT-Channel (Negative)	1-24	1-23	1-22	1-21	1-20	1-19	1-18	1-12	1-24	1-23	1-22	1-21	1-20	1-19	1-18	1-17	4-8	4-15	4-14	4-13	4-12	4-11	4-10	4-9	1-24	1-23	1-22	1-21	1-20	1-19	1-18	1-17
I/O Differential	PF7-none	PF6-FP7	PF5-PF6	PF4-PF5	PF3-PF4	PF2-PF3	PF1-PF2	PF0-PF1	PF7-none	PF6-FP7	PF5-PF6	PF4-PF5	PF3-PF4	PF2-PF3	PF1-PF2	PF0-PF1	none	none	PA5-none	PA4-PA5	PA3-PA4	PA2-PA3	PA1-PA2	PA0-PA1	PF7-none	PF6-FP7	PF5-PF6	PF4-PF5	က်	PF2-PF3	1-PF	PF0-PF1
SCANMASK	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	1	0	1
SCANINPUTID	31							24	23							16	15							8	7							0

Figure 26.7. ADC Differential Scan Mode Example

In certain applications it may be desirable to perform differential conversions on several channels against a common voltage. The ADCn_SCANNEGSEL register allows eight of the SCANINPUTIDs to re-map the negative terminal of a differential conversion to a common channel. In the first ADCn_SCANINPUTSEL group, the negative input for SCANINPUT 0, 2, 4, and 6 may be re-mapped to any of the odd-numbered channels in that group (SCANINPUT 1, 3, 5, or 7). Likewise, in the second ADCn_SCANINPUTSEL group, the negative input for SCANINPUT 9, 11, 13, and 15 may be re-mapped to any of the even-numbered channels in that group (SCANINPUT 8, 10, 12, or 14).

Figure 26.8 ADC Differential Scan Mode Re-mapping Negative Input Selections on page 853 shows the effects of the ADCn_SCAN-NEGSEL register on the re-mappable inputs. The left side of the figure shows the default channel mapping, and the right side of the figure shows how ADCn_SCANNEGSEL can be programmed to map the same negative input on up to four channels.




Figure 26.8. ADC Differential Scan Mode Re-mapping Negative Input Selections

26.3.7.3 APORT Conflicts

The ADC shares common analog buses connected to its APORTs (1-4) with other analog peripherals (see device-specific data sheet). As the ADC performs single or scan conversions, it requests the shared buses and sends selections for the control switches to connect the desired I/O pins. If another analog peripheral requests the same shared bus at the same time, there will be a collision and none of the peripherals will be granted control of that bus.

To help debug over-utilization of APORT resources, the ADC hardware provides status information in local registers. The ADCn_APORTREQ register gives the user visibility into which APORT(s) the ADC is requesting given the setting of the input selection registers. ADCn_APORTCONFLICT reports any conflicts that occur. If PROGERR in ADCn_IEN is set, any conflict generates an interrupt. The PROGERR field in the ADCn_STATUS register indicates whether the programming error happened as a result of an APORT bus conflict (BUSCONF) or from a negative-input selection conflict (NEGSELCONF). If the PROGERR interrupt occurred due to a negative selection conflict, then the interrupt can be cleared by software only after correcting the conflict. If a software clear is attempted without correcting the configuration, the interrupt will be cleared for one clock cycle but then it will trigger again as the invalid configuration still persists.

Note: The ADC requests shared bus connections as soon as that bus is selected in the input select registers, even if the ADC is not performing any conversions. This means that by using the APORT request, the ADC will acquire the associated shared analog bus, preventing other peripherals from using it. The bus will be released only when the input select registers are changed.

It is possible for the ADC to passively monitor shared bus signals without controlling the switches and creating bus conflicts. This can be done by setting the ADCn_APORTMASTERDIS register. When ADCn_APORTMASTERDIS is used, channel selection defers to the peripheral acting as the bus master for that shared bus, and no bus conflict will occur. The ADC will connect its input to the shared bus, but the specific channel will be controlled by the peripheral designated as the bus master.

26.3.8 Reference Selection and Input Range Definition

The full scale voltage (VFS) of the ADC is defined as the full input range, from the lowest possible input voltage to the highest. For single-ended conversions, the input range on the selected positive input is from 0 to VFS. For differential conversions, the input to the converter is the difference between the positive and negative input selections. This can range from -VFS/2 to +VFS/2.

VFS for the converter is determined by a combination of the selected voltage reference (VREF) and programmable divider circuits on the ADC input and voltage reference paths. Users have full control over the VREF and divider selections, offering a very flexible and wide selection of VFS values. In most applications however, it is not necessary to adjust VFS beyond a set of common pre-defined choices. For the simplest VFS configuration, refer to 26.3.8.1 Basic Full-Scale Voltage Configuration. If the application requires a VFS configuration not available in the pre-defined choices, 26.3.8.2 Advanced Full-Scale Voltage Configuration covers additional configuration options.

26.3.8.1 Basic Full-Scale Voltage Configuration

Basic configuration of the VFS (full scale voltage) for the converter is done by programming the REF bitfield in ADCn_SINGLECTRL (for single channel mode) or ADCn_SCANCTRL (for scan mode) to any of the pre-defined options. The list of available pre-defined VFS options is:

- VFS = 1.25 V using internal VBGR as the reference source
- VFS = 2.5 V using internal VBGR as the reference source
- VFS = AVDD using AVDD as the reference source (AVDD ≤ 3.6 V)
- VFS = 5 V using internal VBGR as the reference source
- VFS = ADCn EXTP external pin as a single-ended reference source (1.2 V 3.6 V)
- VFS = ADCn EXTP ADCn EXTN external pins as a differential reference source. (1.2 V 3.6 V difference)
- VFS = 2 x AVDD using AVDD as the reference source (AVDD ≤ 3.6 V)

The maximum and minimum input voltage which the ADC can recognize at any external pin is limited to the minimum of the V_{ADC} and IOVDD supply voltages (where V_{ADC} is VDDX_ANA, as described in 26.3.5 Power Supply). If VFS is configured to be larger than the supply range, the full ADC range will not be available. For example, with a 3.3 V supply and VFS configured to 5 V, the input voltage for single-ended conversions will be limited to 0 to 3.3 V, though the effective VFS is still 5 V.

The ADC uses a chip-level bias circuit to provide bias current for its operation. For highest accuracy when using a VBGR-derived internal bandgap reference source, GPBIASACC in ADCn_BIASPROG should be cleared to 0 (HIGHACC). This will allow the ADC to enable high-accuracy mode from the bias circuitry during conversions. When AVDD or an external pin reference option is used, software may set GPBIASACC in ADCn_BIASPROG to 1 (LOWACC) to conserve energy. Note that VDAC and dc-dc usage may also switch the chip-level bias to high- accuracy mode (even if GPBIASACC is set to LOWACC), potentially impacting ADC results. For example, if ADC is doing a conversion with GPBIASACC set to LOWACC and VDAC also starts a conversion using the internal low noise reference, then the chip-level bias circuit will be automatically switched to high-accuracy mode (potentially corrupting results of the on-going ADC conversion). Similarly, dc-dc startup automatically switches the chip-level bias circuit to high-accuracy mode for a short time, i.e., if dc-dc startup happens when ADC is doing a conversion (with GPBIASACC set to LOWACC), ADC results may get corrupted. DC-DC startup automatically switches the bias circuit to high-accuracy mode for 25 µs. It is during this time that ADC conversions with the GPBIASACC set to LOWACC should be avoided.

If the pre-defined VFS options do not suit the particular application, refer to 26.3.8.2 Advanced Full-Scale Voltage Configuration for more advanced VFS options.

26.3.8.2 Advanced Full-Scale Voltage Configuration

For most applications, the pre-defined VFS options described in 26.3.8.1 Basic Full-Scale Voltage Configuration are suitable. Advanced VFS configurations are also possible by programming the REF bitfield in ADCn_SINGLECTRL or ADCn_SCANCTRL to the CONF option. Programming the REF bitfield to CONF allows the user to select the specific VREF source and adjust the programmable input and reference divider options directly.

The general procedure for programming an advanced VFS configuration is as follows:

- 1. Select the voltage reference source using VREFSEL.
- 2. Configure VREFATTFIX and VREFATT so that the reference voltage at the ADC is between 0.7 and 1.05 V.
- 3. Configure VINATT to achieve the desired full-scale voltage.

The VREFSEL field in ADCn_SINGLECTRLX or ADCn_SCANCTRLX selects the voltage reference source. The ADC can choose from the following voltage reference (VREF) sources:

- VBGR: An internal 0.83 V bandgap reference voltage. This is the most precise internal reference source available.
- VDDXWATT: An attenuated version of the AVDD supply voltage. The attenuation factor is determined by the VREFATTFIX and/or VREFATT bit fields.
- VREFPWATT: An external reference source applied to the ADCn_EXTP pin, and attenuated by the attenuation factor (determined by the VREFATTFIX and/or VREFATT bit fields). This is the appropriate choice for external reference inputs greater than 1.05 V.
- VREFP: An external reference source applied to the ADCn_EXTP pin, without any attenuation. This is the appropriate choice for external reference inputs between 0.7 V and 1.05 V.
- VENTROPY: A very low internal reference voltage (approx. 0.1 V). This option is intended to be used only with the ADC inputs tied internally to VSS, for generating random noise at the ADC output.
- VREFPNWATT: A differential version of VREFPWATT, with the reference source applied to the ADCn_EXTP and ADCn_EXTN pins and attenuated. This is the appropriate choice where a differential reference of greater than 1.05 V is required.
- VREFPN: A differential version of VREFP, with the reference source applied to the ADCn_EXTP and ADCn_EXTN pins and no attenuation. This is the appropriate choice where a differential reference of between 0.7 V and 1.05 V is required.
- VBGRLOW: An internal 0.78 V bandgap reference voltage.

The ADC reference voltage should be attenuated to a lower voltage when using AVDD or the external reference source. A simple method for a wide range of reference sources is to set VREFATTFIX to 1. The VREF attenuation factor (ATT_{VREF}) can then be selected between 1/3 (when VREFATT is greater than 0), and 1/4 (when VREFATT is equal to 0). For reference sources between 1.2 V and 3.6 V, ATT_{VREF} = 1/3 is the best choice. ATT_{VREF} = 1/4 can be used with references from 1.6 V to 3.8 V, with slight performance degradation.

Finer granularity on ATT_{VREF} is possible as well, by clearing VREFATTFIX to 0, and setting the VREFATT field. For optimal performance with VREFATTFIX = 0, the attenuated ADC reference input should be limited to between 0.7 V and 1.05 V. When VREFATTFIX is cleared to 0, ATT_{VREF} is set according to the equation:

ATT_{VREF} = (VREFATT + 6) / 24 for VREFATT < 13, and (VREFATT - 3) / 12 for VREFATT ≥ 13

Figure 26.9. ATT_{VREF}: VREF Attenuation Factor

The ADC input also includes a programmable attenuator. The VIN attenuator is used to widen the available input range of the ADC beyond the reference source. The VIN attenuation factor (ATT_{VIN}) is determined by the VINATT field according to the equation:

ATT_{VIN} = VINATT / 12 for VINATT ≥ 3 (settings 0, 1, and 2 are not allowable values for VINATT)

Figure 26.10. ATT_{VIN}: VIN Attenuation Factor

VFS can be calculated by the formula given below for any given VREF source, VREF attenuation, and VIN attenuation:

VFS = 2 · VREF · ATT_{VREF} / ATT_{VIN}

VREF is selected in the VREFSEL bitfield, and

ATT_{VREF} is the VREF attenuation factor, determined by VREFATT or VREFATTFIX

ATT_{VIN} is the VIN attenuation factor, determined by VINATT

Figure 26.11. VFS: Full-Scale Input Range

The maximum and minimum input voltage which the ADC can recognize at any external pin is limited to the minimum of the V_{ADC} and IOVDD supply voltages (where V_{ADC} is VDDX_ANA, as described in 26.3.5 Power Supply). If VFS is configured to be larger than the supply range, the full ADC range will not be available. For example, with a 3.3 V supply and VFS configured to 5 V, the input voltage for single-ended conversions will be limited to 0 to 3.3 V, though the effective VFS is still 5 V.

The ADC uses a chip-level bias circuit to provide bias current for its operation. For highest accuracy when using a VBGR-derived internal bandgap reference source, GPBIASACC in ADCn_BIASPROG should be cleared to 0 (HIGHACC). This will allow the ADC to enable high-accuracy mode from the bias circuitry during conversions. When AVDD or an external pin reference option is used, software may set GPBIASACC in ADCn_BIASPROG to 1 (LOWACC) to conserve energy. Note that VDAC and dc-dc usage may also switch the chip-level bias to high- accuracy mode (even if GPBIASACC is set to LOWACC), potentially impacting ADC results. For example, if ADC is doing a conversion with GPBIASACC set to LOWACC and VDAC also starts a conversion using the internal low noise reference, then the chip-level bias circuit will be automatically switched to high-accuracy mode (potentially corrupting results of the on-going ADC conversion). Similarly, dc-dc startup automatically switches the chip-level bias circuit to high-accuracy mode for a short time, i.e., if dc-dc startup happens when ADC is doing a conversion (with GPBIASACC set to LOWACC), ADC results may get corrupted. DC-DC startup automatically switches the bias circuit to high-accuracy mode for 25 µs. It is during this time that ADC conversions with the GPBIASACC set to LOWACC should be avoided.

The combination of VREF, ATT_{VREF} and ATT_{VIN} can produce a wide range of full-scale voltage options for the converter. Table 26.1 Advanced VFS Configuration: VREF = AVDD on page 857 shows some example VFS configurations using AVDD as a reference source.

Table 26.1. Advanced VFS Configuration: VREF = AVDD

AVDD Voltage	VREF Attenuation Set- tings	Reference Voltage at ADC	VIN Attenuation Set- tings	VFS
1.85 V	VREFATTFIX = 0	0.925 V	VINATT = 12	1.85 V
	VREFATT = 6		ATT _{VIN} = 1	(+/-0.925 V differential)
	ATT _{VREF} = 1/2			
3.0 V	VREFATTFIX = 0	1.0 V	VINATT = 8	3.0 V
	VREFATT = 2		ATT _{VIN} = 2/3	(+/-1.5 V differential)
	ATT _{VREF} = 1/3			
3.0 V	VREFATTFIX = 0	1.0 V	VINATT = 4	6.0 V
	VREFATT = 2		ATT _{VIN} = 1/3	(+/-3.0 V differential)
	ATT _{VREF} = 1/3			
3.6 V	VREFATTFIX = 1	0.9 V	VINATT = 6	3.6 V
	VREFATT = 0		ATT _{VIN} = 1/2	(+/-1.8 V differential)
	ATT _{VREF} = 1/4			

26.3.9 Programming of Bias Current

The ADC uses a chip-level bias generator to provide bias current for its operation. The ADC's internal bias can be scaled by ADCBIA-SPROG field of the ADCn_BIASPROG register. At lower conversion speeds, the ADCBIASPROG can be used to lower active power. Some commonly used settings are given in the ADCBIASPROG register description. For proper operation, the ADC conversion speed must be scaled accordingly. The scale factor is calculated as:

Bias scale factor = (1- ADCBIASPROG[2:0]/8) / (1+3·ADCBIASPROG[3])

Figure 26.12. Bias Scale Factor

The bias programming register also includes the VFAULTCLR bit field. If VREFOF interrupt is enabled and it is triggered, then the user needs to set this bit in the ISR before clearing the interrupt flag. This bit then needs to be reset after the interrupt flag is cleared in order to enable the VREFOV flag to trigger on the next VREFOV condition.

The bias current settings should only be changed while the ADC is disabled (i.e. in NORMAL warm-up mode and no conversion in progress).

26.3.10 Feature Set

The following sections explain different ADC features.

26.3.10.1 Conversion Tailgating

Scan conversions have priority over single channel conversions. This means that if scan and single triggers are received simultaneously, or even if the scan is received later when ADC is being warmed up for performing a single conversion, the scan conversion will have priority and will be done before the single conversion. However, a scan trigger will not interrupt in the middle of a single conversion, i.e., if the single conversion is in the acquisition or approximation phase, then the scan will have to wait for the single conversion to complete. If a scan sequence is triggered by a timer on a periodic basis, single channel conversion that started just before a scan trigger can delay the start of the scan sequence, thus causing jitter in sample rate. To solve this, conversion tailgating can be chosen by setting TAILGATE in ADCn_CTRL. When this bit is set, any triggered single channels will wait for the next scan sequence to finish before activating (see Figure 26.13 ADC Conversion Tailgating on page 858). The single channel will then follow immediately after the scan sequence. In this way, the scan sequence will always start immediately when triggered, provided that the period between the scan triggers is big enough to allow the single sample conversion that was triggered to finish before the next scan trigger arrives. Note that if tailgating is set and a single channel conversion is triggered, it will indefinitely wait for a scan conversion before starting the single channel conversion.




Figure 26.13. ADC Conversion Tailgating

26.3.10.2 Repetitive Mode

Both single channel and scan mode can be run as a one shot conversion or in repetitive mode. The REP bitfield in ADCn_SIN-GLECTRL/ADCn_SCANCTRL registers can be used to activate the repetitive mode for single and scan respectively. In order to achieve the maximum sampling rate of 1 Msps, repetitive mode should be used.

It is also possible to have a programmable delay between these repetitive conversions. The REPDELAY bitfield in the ADCn SIN-GLECTRLX and ADCn SCANCTRLX registers can be used to set the delay between two repeated conversions in single channel and scan mode respectively. For single channel mode when a single conversion in repetitive mode ends, the user programmed REPDELAY is inserted and then the next single conversion is re triggered after the delay period is over. For scan mode the REPDELAY is inserted after the entire scan sequence ends. Once the delay period is over, scan mode is internally re-triggered. Note that when the ADC is in SYNC mode and REPDELAY is set to generate a delay, it takes an additional 5 HFPERCLK cycles after the trigger before the next conversion begins. If REPDELAY is set to NODELAY, the next conversion begins immediately, without any delay or additional HFPERCLKs. The 26.3.10.1 Conversion Tailgating explains how the single channel and scan mode conversions can push each other out of phase. Conversion tailgating can be chosen in repetitive mode as well in order to ensure that the scan sequence will always start immediately when triggered, provided the scan REPDELAY chosen is big enough for the single conversion to finish. The status flags SINGLEACT and SCANACT stay high throughout the repeat mode, i.e., even during the delay period. The flags show that the conversions are either active or pending. Whether the ADC turns off or stays warmed up between these repeated conversions depends on the WARMUPMODE chosen in the ADCn CTRL register. When using single channel mode with repeat mode and REPDELAY enabled, then once the ADC has started operation (i.e., singleact status flag has gone high) then no new single conversion triggers (software START/ PRS triggers) should be sent to the ADC until the ADC has stopped converting (i.e., singleact status flag has gone low). The same applies to scan sequence conversions.

26.3.10.3 Conversion Trigger

The conversion modes can be activated by writing a 1 to the SINGLESTART or SCANSTART bit in the ADCn_CMD register. The conversions can be stopped by writing a 1 to the SINGLESTOP or SCANSTOP bit in the ADCn_CMD register. A START command will have priority over a STOP command. When the ADC is stopped in the middle of a conversion, the result buffer is cleared (the FIFO contents for any prior conversions are still intact). Every time a STOP command is issued, the user should wait for the corresponding status flag (SINGLEACT/SCANACT) to go low and then either read all the data in the FIFO or send the corresponding FIFOCLEAR command. The SINGLEACT and SCANACT bits in ADCn_STATUS are set high when the modes are actively converting or have pending conversions.

It is also possible to trigger conversions from PRS signals. The PRS is treated as an asynchronous trigger. Setting PRSEN in ADCn_SINGLECTRL/ADCn_SCANCTRL enables triggering from PRS input. Which PRS channel to listen to is defined by PRSSEL in ADCn_SINGLECTRLX/ADCn_SCANCTRLX. When PRS trigger is selected, it is still possible to trigger a conversion from software. Refer to the PRS chapter for more information on how to set up the PRS channels. When the conversions are triggered using the ADCn_CMD register, then the SINGLEACT and SCANACT bits in the ADCn_STATUS are set as soon as the START command is written to the register. When the conversion is triggered using PRS, it takes some cycles from the time PRS trigger is received until the SINGLEACT and SCANACT bits are set due to the synchronization requirement. If SINGLEACT is already high then sending a new START command or a new PRS trigger for a single conversion will not have any impact as ADC already has a single conversion ongoing or a single conversion pending (single conversion can be pending if ADC is busy running a scan sequence). The same rules apply for SCANACT and SCAN START and PRS triggers. When software issues a SINGLE/SCAN STOP command, it must wait until SINGLEACT/ SCANACT flag goes low before issuing a new START.

The PRS may trigger the ADC in two possible ways, configured by PRSMODE in ADCn_SINGLECTRLX/ADCn_SCANCTRLX. In PULSED mode, a PRS pulse triggers the ADC to start the ADC_CLK (if not already enabled), warm up (if not already warm), start the acquisition period, and perform the conversion. This is identical to issuing a START command from software. In this mode, the input sampling finishes at the end of the acquisition period (AT).

If the ADC_CLK and the source of the trigger (START command or PRS pulse) are not synchronous, the frequency of the input sampling (FS), will experience a $1_{1/2}$ to $2_{1/2}$ ADC_CLK cycle jitter due to synchronization requirements.

To precisely control the sample frequency, the PRSMODE can be set to TIMED mode. In this mode, a long PRS pulse is expected to trigger the ADC and its negative edge directly finishes input sampling and starts the approximation phase, giving precise sampling frequency management. The restriction is that the PRS pulse has to be long enough to start the ADC_CLK (if not already enabled), and finish the acquisition period based on the AT field in ADCn_SINGLECTRL/ADCn_SCANCTRL. The PRS pulse needs to be high when AT event finishes. If it is not high when AT finishes, then it is ignored and input sampling finishes after AT event has ended (a two cycle latency is added to the conversion in this scenario). In this case, the ADC sets the PRSTIMEDERR interrupt flag.

If the PRS pulse is too long (e.g., FS = 32kHz), the analog ADC start can be delayed to save power. The CONVSTARTDELAY along with its EN in the ADCn_SINGLECTRLX or ADCn_SCANCTRLx can be programmed to implement a 0 to 8 microseconds delay. The microsecond tick is counted by TIMEBASE with ADC_CLK similar to warmup case. This saves power as the ADC is not enabled until the last possible microsecond before the fall edge of the PRS arrives to open the sampling switch and to start the approximation phase. Figure 26.14 ADC PRS Timed Mode with ASNEEDED ADC_CLK Request on page 860) shows PRS Timed mode triggering with CONVSTARTDELAY and ASNEEDED ADC_CLK request. See that power is saved by both delaying the ADC EN and by requesting the ADC_CLK only during ADC operation. This is especially useful in saving power when running the ADC in EM2 Deep Sleep or EM3 Stop power mode with low sampling frequency.




Figure 26.14. ADC PRS Timed Mode with ASNEEDED ADC CLK Request

When a PRS pulse is received, if the ADC_CLK is not running (ASNEEDED mode), then the ADC requests the clock by setting clkreq_adc_async high. If the chosen clock source (HFXO/ HFSRCCLK/ AUXHFRCO) is already running, then it takes 5 ADC_CLK cycles after the clock request is asserted for the ADC_CLK to start. HFXO and HFSRCCLK (if chosen as ADC clock source) need to be already running before ADC sends out the clock request. If AUXHFRCO is chosen as the ADC clock source, and it is not already

running, then the CMU automatically turns it on when the ADC sends a clock request. In such a case, it takes (7 ADC_CLK cycles + the oscillator startup time) for the ADC_CLK to start. The oscillator startup time can be found in the device data sheet.

When triggering repeat mode using PRS and then stopping the triggered mode using STOP command, ensure that the PRS pulse used to generate the repeat mode has gone low by the time the STOP command is issued. If the PRS pulse continues to stay high after ADC has stopped the ongoing conversion, then it will be picked as a new trigger to start a new conversion.

Note:

- The conversion settings should not be changed while the ADC is running. Doing so may lead to unpredictable behavior.
- The adc_clk_sar phase is always reset by a conversion trigger as long as a conversion is not in progress. This gives predictable latency from the time of the trigger to the time the conversion starts, regardless of when in the trigger occurs.
- Software and LESENSE should not trigger conversions if PRS Timed mode is selected and PRSEN is set to 1 in the ADCn_SIN-GLECTRL/ADCn_SCANCTRL register.
- If the PRS Timed mode is being used, the acquisition time (AT) must be set greater than 0.

Scan conversions can be triggered using LESENSE as well. LESENSE only triggers one input conversion at a time (not the whole sequence of 32 possible inputs). The input to be converted using LESENSE must be configured by the user in the ADCn_SCANINPUT-SEL register before triggering the conversion, i.e., one of the 32 inputs chosen in the ADCn_SCANINPUTSEL register must be the one that is to be converted using LESENSE. The ADCn_SCANMASK is not used for LESENSE triggered conversions. Instead, the user can select which input should be converted through LESENSE inside the LESENSE settings (LESENSE_CHX). The results of LESENSE triggered conversions are not loaded in the FIFO/ DATA registers but are instead available in the LESENSE register. Similarly, the SCAN interrupt flag is not set on completion of a LESENSE triggered conversion (because that flag is set only when the data is written to the Scan FIFO). When there is a LESENSE triggered conversion going on or pending, the SCANACT status flag is set. The SCAN-PEND interrupt flag is set when a software/PRS triggered scan goes pending because a LESENSE triggered scan is running (software/PRS triggered scan will start after the currently running LESENSE scan conversion completes). Similarly, SCANEXTPEND interrupt flag is set when the LESENSE triggered scan conversion goes pending because a software/PRS triggered scan is running. LESENSE triggered conversions can be stopped at any time using the SCANSTOP command in the ADCn_CMD register. Note that the LESENSE triggered conversion cannot trigger the Scan repeat mode.

The DBGHALT bit-field in the ADCn_CTRL register can be used to choose the ADC behavior in debug mode. If this bit is set to 1, then in debug mode ADC completes the current conversions and then halts. This means that all conversion triggers that were received before the debug halt occurred will be serviced before the ADC halts. All conversion triggers received after the ADC was halted, will be serviced when the debug mode is not halted any more. If the repetitive mode is running (in repetitive mode ADC keeps doing conversions until the user sends a software STOP) and a debug mode halt occurs, then the ADC will gracefully complete the current on-going conversion and then halt. The repetitive mode conversions will restart as soon as the debug mode is not halted any more.

26.3.10.4 Output Results

ADC output results are presented in 2's complement form and the format for single ended and differential conversions are given in Table 26.2 ADC Single Ended Conversion on page 862 and Table 26.3 ADC Differential Conversion on page 862, respectively. If differential mode is selected, the results are sign extended up to 32-bits (shown in Table 26.5 ADC Results Representation on page 863).

Table 26.2. ADC Single Ended Conversion

Input Voltage	Output Results											
input voltage	Binary	Hex value										
4095/4096 · VFS	111111111111	FFF										
0.5 · VFS	10000000000	800										
1/4096 · VFS	00000000001	001										
0	00000000000	000										

Table 26.3. ADC Differential Conversion

Innut	Output Results											
Input	Binary	Hex value										
2047/4096 · VFS	01111111111	7FF										
0.25 · VFS	01000000000	400										
1/4096 · VFS	00000000001	001										
0	00000000000	000										
-1/4096 · VFS	11111111111	FFF										
-0.25 · VFS	11000000000	C00										
-0.5 · VFS	10000000000	800										

26.3.10.5 Resolution

The ADC performs 12-bit conversions by default. However, if full 12-bit resolution is not needed, it is possible to speed up the conversion by selecting a lower resolution (6 or 8 bits). For more information on the accuracy of the ADC, the reader is referred to the electrical characteristics section for the device.

26.3.10.6 Oversampling

To achieve higher accuracy, hardware oversampling can be enabled individually for each mode (Set RES in ADCn_SINGLECTRL/ADCn_SCANCTRL to 0x3). The oversampling rate (OVSRSEL in ADCn_CTRL) can be set to any integer power of 2 from 2 to 4096 and the configuration is shared between the scan and single channel mode (OVSRSEL field in ADCn_CTRL).

With oversampling, each input is sampled at 12-bits of resolution a number of times (given by OVSRSEL), and the results are filtered by a first order accumulate and dump filter to form the end result. The data presented in the ADCn_SINGLEDATA and ADCn_SCANDATA registers are the direct contents of the accumulation register (sum of samples). However, if the oversampling ratio is set higher than 16x, the accumulated results are shifted to fit the MSB in bit 15 as shown in Table 26.4 Oversampling Result Shifting and Resolution on page 863.

Table 26.4. Oversampling Result Shifting and Resolution

Oversampling setting	# right shifts	Result Resolution # bits
2x	0	13
4x	0	14
8x	0	15
16x	0	16
32x	1	16
64x	2	16
128x	3	16
256x	4	16
512x	5	16
1024x	6	16
2048x	7	16
4096x	8	16

26.3.10.7 Adjustment

By default, all results are right adjusted, with the LSB of the result in bit position 0 (zero). In differential mode the signed bit is extended up to bit 31, but in single ended mode the bits above the result are read as 0. By setting ADJ in ADCn_SINGLECTRL/ADCn_SCANCTRL, the results are left adjusted as shown in Table 26.5 ADC Results Representation on page 863. When left adjusted, the MSB is always placed on bit 15 and sign extended to bit 31. All bits below the conversion result are read as 0 (zero).

Table 26.5. ADC Results Representation

Adjustment	Resolution								Bits									
		31 16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	12	11 11	11	11	11	11	11	10	9	8	7	6	5	4	3	2	1	0
Right	8	7 7	7	7	7	7	7	7	7	7	7	6	5	4	3	2	1	0
Right	6	5 5	5	5	5	5	5	5	5	5	5	5	5	4	3	2	1	0
	OVS	15 15	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	12	11 11	11	10	9	8	7	6	5	4	3	2	1	0	1	-	-	-
Left	8	7 7	7	6	5	4	3	2	1	0	-	-	-	-	-	-	-	-
Leit	6	5 5	5	4	3	2	1	0	-	-	-	-	-	-	-	-	-	-
	ovs	15 15	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0

26.3.10.8 Channel Connection

The inputs are connected to the analog ADC at the beginning of the acquisition phase and are disconnected at the end of the acquisition phase. The time when the APORT switches are closed (for the next input to be converted) can be controlled by the CHCONMODE bitfield in the ADCn_CTRL register. By default, this field is set to the MAXSETTLE option. For MAXSETTLE, APORT switches are closed on the next input as soon as the acquisition phase for the current conversion is complete. This means that the APORT switches are closed approximately 12 adc_clk_sar cycles (assuming 12 bit resolution) before the acquisition phase of the current conversion starts, giving APORT switches maximum time to settle. The time for which APORT switches should be closed before the acquisition phase starts, should be the same for all inputs in order to get consistent results. This means that if the ADC is warmed up with CHCON-REFWARMIDLE set to 0 (scan reference warmed up and the APORT switches for the first scan channel closed) and a single trigger comes in, the single conversion will have to wait 12 adc_clk_sar cycles before it can start (even if single is using the same reference as scan). In this case, it might be more suitable to switch to the MAXRESP option in the CHCONMODE bitfield. In MAXRESP, the APORT switches for the upcoming conversion are closed just before the acquisition phase starts. This gives less settling time to the APORT switches but removes the extra waiting time before a conversion can start (which could be the case with MAXSETTLE as discussed above).

26.3.10.9 Temperature Measurement

The ADC includes an internal temperature sensor. This sensor is measured during production test and the temperature readout from the ADC at production temperature, ADC0CAL3_TEMPREAD1V25, is given in the Device Information (DI) page. The production temperature, CAL_TEMP, is also given in this page. The temperature sensor slope, V_TS_SLOPE (mV/degree Celsius), for the sensor is found in the data sheet for the device. Using the 1.25 V VFS option and 12-bit resolution, the temperature can be calculated according to the following formula (VFS in the formula is 1250 mV):

T_{CELSIUS} = CAL_TEMP - (ADC0CAL3_TEMPREAD1V25 - ADC_result) · VFS / (4096· V_TS_SLOPE)

Figure 26.15. ADC Temperature Measurement

Note:

- The minimum acquisition time for the temperature reference is found in the electrical characteristics for the device. If using the 1.25 V reference, extra acquisition time is required. In this case the AT field of ADCn_SINGLECTRL or ADCn_SCANCTRL should be set to a value of 9 or higher.
- For the most accurate temperature sensor results, GPBIASACC in ADCn_BIASPROG should be set to 0 to keep the bias in HIGH-ACC mode.
- If the device has more than one ADC, all ADCs may not be equipped with the temperature sensor. See the device data sheet.

26.3.10.10 ADC as a Random Number Generator

The ADC can be used as a random number generator. This is done by:

- 1. Choose the REF in the ADCn_SINGLECTRL as CONF, setting the VREFSEL in the ADCn_SINGLECTRLX as VENTROPY and VINATT in the same register to its maximum value of 15.
- 2. Set DIFF to 1 and RES to 0 in the ADCn SINGLECTRL register.
- 3. Trigger a single channel conversion and then read ADCn_SINGLEDATA register when the conversion finishes.

The LSB[2:0] of each sample will be a random number. In this mode, the POSSEL or NEGSEL in ADCn_SINGLECTRL can be connected to VSS or any other noisy input.

26.3.11 Interrupts, PRS Output

The single and scan modes have separate SINGLE and SCAN interrupt flags indicating whether corresponding FIFO contains DVL # of valid conversion data. Corresponding interrupt enable bit has to be set in ADCn_IEN in order to generate interrupts. For these interrupts, there is no software clear mechanism by writing to ADCn_IFC. The user needs to read enough data from the interrupted FIFO to ensure it contains less than DVL # of elements. The ADCn_SINGLEFIFOCOUNT/ADCn_SCANFIFOCOUNT can provide number of valid elements remaining in corresponding FIFO. The FIFO can also be cleared by ADCn_SINGLEFIFOCLEAR/ADCn_SCANFIFOCLEAR, but any existing data will be lost by this operation.

In addition to the SINGLE and SCAN interrupt flags, there is separate scan and single channel result overflow interrupt flag which signals that a result from a scan or single channel FIFO has been overwritten before being read. There is also separate scan and single channel result underflow interrupt flag which signals that a FIFO read was issued when the FIFO was empty.

There is separate scan and single compare interrupt flag which signals a compare match with latest sample if the CMPEN in ADCn_SINGLECTRL/ADCn_SCANCTRL is enabled.

ADC has two separate PRS outputs, one for single channel and one for scan sequence. A finished conversion results in a one ADC_CLK cycle pulse, which is output to the Peripheral Reflex System (PRS). Note that the PRS pulse for scan is generated once after every channel conversion in the scan sequence.

26.3.12 DMA Request

The ADC has two DMA request lines, SINGLEREQ and SCANREQ, which are set when a single or scan FIFO receives DVL# of samples. The requests are cleared when the corresponding single or scan result register is read and corresponding FIFO count reaches lower than DVL. It also has two additional DMA Single request lines, SINGLESREQ and SCANSREQ, that are set when the corresponding FIFO is not empty.

26.3.13 Calibration

The ADC supports offset and gain calibration to correct errors due to process and temperature variations. This must be done individually for each reference used. For each reference, it needs to be repeated for single-ended, negative single-ended (see 26.3.7 Input Selection for details) and differential measurement. The ADC calibration (ADCn_CAL) register contains register fields for calibrating offset and gain for both single and scan mode. The gain and offset calibration are done in single channel mode, but the resulting calibration values can be used for both single and scan mode.

Gain and offset for various references and modes are calibrated during production and the calibration values for these can be found in the Device Information page. During reset, the gain and offset calibration registers are loaded with the production calibration values for the 1V25 reference. Others can be loaded as needed or the user can perform calibration on the fly using the particular reference and mode to be used and write the result in the ADCn CAL before starting the ADC conversion with them.

26.3.13.1 Offset Calibration

Offset calibration must be performed prior to gain calibration. Follow these steps for the offset calibration in single mode:

- 1. Select the desired full scale configuration by setting the REF bit field of the ADCn SINGLECTRL register.
- 2. Set the AT bit field of the ADCn SINGLECTRL register to 16CYCLES.
- 3. Set the POSSEL and NEGSEL of the ADCn_SINGLECTRL register to VSS, and set the DIFF to 1 for enabling differential input if calibrating for DIFF measurement. During calibration, the ADC samples represent the code coming out of the analog. Thus, since the input voltage is 0, the expected ADC output is 0b100000000000 in differential mode, 0b000000000000 in single-ended mode and 0b11111111111 in negative single-ended mode.
- 4. A binary search is used to find the offset calibration value. Set the CALEN to 1, and OFFSETINVMODE to 1 (if calibrating for negative single-ended conversion) in the ADCn_CAL register. If user is performing negative single-ended calibration, the SINGLEOFFSETINV provides the offset else SINGLEOFFSET bit provides the offset (for both single-ended and differential offset calibration). Start with 0b0000 (or 0b1111 if doing calibration for differential mode) in SINGLEOFFSET or with 0b1000 in SINGLEOFFSETINV (if calibrating for negative single-ended conversion). Set the SINGLESTART bit in the ADCn_CMD register to perform a 12-bit conversion and read the ADCn_SINGLEDATA register. The offset is (ADCn_SINGLEDATA expected ADC output). Calculate this and write [3:0] of the result into SINGLEOFFSET or SCANOFFSETINV (if doing negative single-ended conversion). The user repeats till ADCn_SINGLEDATA matches expected ADC output. The ADC has a 8LSB built in negative offset to allow for negative offset correction. So, with default offset value, which corrects for the negative offset, the converted ADCn_SINGLEDATA would match expected ADC output if there were no offset. To get better noise immunity, the sampling phase can be repeated with Oversampling enabled. The result of the binary search is written to the SINGLEOFFSET (or SINGLEOFFSETINV) field of the ADCn_CAL register.

26.3.13.2 Gain Calibration

Offset calibration must be performed prior to gain calibration. The Gain Calibration is done in the following manner:

- 1. Select an external ADC channel for single channel conversion (a differential channel can also be used).
- Apply an external voltage on the selected ADC input channel. This voltage should correspond to the top of the ADC input range for the selected reference.
- 3. Set SINGLEGAIN[6:0] to 64 in the ADCn_CAL and measure gain, repeat gain calibration walking the 1 in SINGLEGAIN[6] to SIN-GLEGAIN[0] till sampled ADCn_SINGLEDATA matches expected value. This is done by setting CALEN in ADCn_CAL set to 1 and performing single channel, reading in the raw ADC code from the ADCn_SINGLEDATA and comparing it with expected code, i.e. 0b11111111111 for single-ended or differential conversion, and 0b00000000000 for negative single-ended conversion. The target value is ideally the top of the ADC input range, but it is recommended to use a value a couple of LSBs below in order to avoid overshooting. The result of the binary search is written to the SINGLEGAIN field of the ADCn_CAL register.

For the VDD reference and external reference, there is no hardware gain calibration. Calibration can be done by software after taking a sample.

26.3.14 EM2 Deep Sleep or EM3 Stop Operation

The ADC can operate in EM2 Deep Sleep or EM3 Stop mode. For EM2 Deep Sleep or EM3 Stop operation the ADC_CLK must be selected as AUXHFRCO. The section 26.3.1 Clock Selection describes how to choose AUXHFRCO as the ADC_CLK. The AUXHFRCO can be kept on for as long as sample conversion is needed or it can be requested by trigger event and after the conversion is done, the AUXHFRCO can be shut down. The second option saves power at the expense of the delay to start the AUXHFRCO oscillator. All the trigger modes are available in EM2 Deep Sleep or EM3 Stop as well.

While in EM2 Deep Sleep or EM3 Stop, the ADC can wake the system to EM0 Active on enabled interrupts. Following interrupts can wake up the system to EM0 Active:

- SINGLE or SCAN interrupt indicating that the corresponding FIFO has reached the DVL watermark.
- · Overflow interrupt (SINGLEOF or SCANOF)
- Underflow interrupt (SINGLEUF or SCANUF), triggered if DMA pops more data than present in the FIFO while the system is asleep
- · Compare interrupt (SINGLECMP or SCANCMP)
- Over voltage interrupt (VREFOV)

The ADC can also work with the DMA so that the system does not have to wake up to consume data. This can happen if the SCAN or SINGLE interrupt is disabled and the SINGLEDMAWU or SCANDMAWU in the ADCn_CTRL is set. The DMA will be triggered by the ADC when DVL samples become available in the corresponding FIFO. The DMA will then pop all the elements of the corresponding FIFO and put the system back into the low power state. A system-level wake up will occur upon the DMA done interrupt. Note that other enabled ADC interrupts can still wake up the system when operating with the DMA. For example, the user can configure the window compare function to trip when the result reaches a certain threshold while gathering ADC data in EM2 Deep Sleep or EM3 Stop.

The ADC works with the EMU to wake up the system or the DMA. It takes 2 µs from the time the ADC request a wakeup to start of the peripheral clocks. In this ASYNC mode of ADC_CLK, it takes 6 HFPERCLK cycles to read a single entry from the single or scan FIFO. So, with a 20MHz HFPERCLK, it takes about 4 µs per DMA wakeup to empty a full FIFO (4 entries). This restricts the sampling rate in EM2 Deep Sleep or EM3 Stop in order to avoid FIFO overflows.

The AUXHFRCO power can be reduced by reducing the clock speed, and the user may adjust the ADCBIASPROG field in the ADCn_BIASPROG register to reduce active power of the ADC during the conversions, thus reducing power even more in EM2 Deep Sleep/EM3 Stop. Refer to the data sheet for relevant power consumption numbers.

If the ADC is not to be used in EM2 Deep Sleep or EM3 Stop, then the user should ensure that the ADC is not busy before going to the low power mode. 26.3.17 ADC Programming Model explains how to ensure the ADC is not busy. If the chip enters EM2 Deep Sleep or EM3 Stop when ADC is busy without using AUXHFRCO, then the ADC clock will stop but the ADC will stay on, resulting in higher supply current. If this occurs, the EM23ERR interrupt flag will be set. Software will see this interrupt flag only when the chip wakes up.

26.3.15 ASYNC ADC_CLK Usage Restrictions and Benefits

When the ADC_CLK is chosen to come from ASYNCCLK, (ADCCLKMODE is set to ASYNC), the ADC_CLK and the ADC peripheral clock are considered asynchronous and this adds some restrictions:

- Due to a synchronization delay, accessing the following registers takes extra time (up to additional 7 HFPERCLK cycles):
 ADCn_SINGLEDATA, ADCn_SCANDATA, ADCn_SINGLEDATAP, ADCn_SCANDATAP, ADCn_SCANDATAX, ADCn_SCANDATAXP, ADCn_SINGLEFIFOCOUNT, ADCn_SCANFIFOCOUNT, ADCn_SINGLEFIFOCLEAR, ADCn_SCANFIFOCLEAR.
- The safe time to change the ADCn_SINGLECTRL, ADCn_SINGLECTRLX, ADCn_SCANCTRL, ADCn_SCANCTRLX, ADC
- When the ADC needs to run in EM2 Deep Sleep or EM3 Stop, only AUXHFRCO can provide the ADC_CLK to the ADC. Thus the
 user needs to set ASYNC mode of ADCCLKMODE and setup the CMU to provide the AUXHFRCO clock as ASYNCCLK.
- If the ADC needs to run on a particular adc_clk_sar frequency to achieve a sample rate and the HFPERCLK is not a proper multiple
 for such clock frequency, a higher frequency system clock, HFRCO, can be chosen to be ADC_CLK using ASYNC mode. This allows HFPERCLK to be set to an optimum value from a system view point.
- ASYNC mode can also help with digital noise mitigation as this clock is asynchronous (not balanced) with the system clock. Moreover, the user can use the invert option to invert the source of ASYNCCLK helping in noise mitigation further.
- · Whenever ADC is being used in asynchronous mode, then HFPERCLK must be at least 1.5 times higher than the ADC CLK.
- With ASNEEDED setting for ASYNCCLK request, the ADC_CLK power can be reduced.

26.3.16 Window Compare Function

The ADC supports a window compare function on both the latest single and scan outputs. The compare thresholds, ADGT and ADLT, are defined in the ADCn_CMPTHR register. These are 16-bit values and their format must match the type of conversion (single-ended or differential) the user is trying to compare with. For example, a 12-bit differential conversion is sign extended to 16 bits while a 12-bit single-ended conversion result would get zero padded to 16-bit result before comparing with ADGT and ADLT. If over-sampling is enabled, the conversion result could grow to 16-bits. There is a single set of ADLT and ADGT threshold for both single and scan compare. The user can however enable single or scan compare logic individually by enabling CMPEN in ADCn_SINGLECTRL or ADCn_SCANCTRL register.

The user can perform comparison both within or outside of the window defined by the ADGT and ADLT. If the ADLT is greater than ADGT, the ADC compares if the current sample is within the window. Otherwise, the ADC compares if the current sample is outside of the window.

26.3.17 ADC Programming Model

The ADC configuration registers are considered static and can only be updated when (1) ADC is in SYNC mode and (2) ADC is idle. ADC is considered busy when it is doing conversions (either the SINGLEACT or SCANACT status flag is high) or when it is warmed up (one of the following status flags is high: WARM, SINGLEREFWARM, SCANREFWARM). The following registers are considered ADC configuration registers: CMU_ADCCTRL, ADCn_CTRL, ADCn_SINGLECTRL, ADCn_SINGLECTRLX, ADCn_SCANCTRL, ADCn_SCANCTRL, ADCn_SCANCTRLX, ADCn_SCANINPUTSEL, ADCn_SCANNEGSEL, ADCn_IEN, ADCn_BIASPROG, ADCn_SCANMASK, ADCn_CAL and ADCn_CMPTHR.

From reset, the ADC is in SYNC mode by default. The user can program the configuration registers as needed. If PRS is to be used, PRSEN in ADCn_SINGLECTRL/ADCn_SCANCTRL should be set after all other configuration is complete, the ADC is ready to receive triggers. The user must ensure that no LESENSE triggers come in during the time the ADC configuration registers are being updated.

After the ADC has been used to perform conversions, the user must ensure that the ADC is idle before updating the configuration registers. The first step is to ensure that no new triggers (PRS, LESENSE) are being issued. It can take a few cycles from when a trigger is received to when SINGELACT/SCANACT flags go high due to synchronization requirement. If it is unclear when the triggers were issued and if those are under synchronization or not, the user should add a small delay before checking the status flags. If the SINGLE-ACT/SCANACT status flags are high, the corresponding STOP command should be issued and the user should wait until the SINGLE-ACT/SCANACT flags go low. If the ADC was warmed up, then the WARMUPMODE should be changed to NORMAL and then the user should wait on WARM, SINGLEREFWARM and SCANREFWARM flags until those go low. Now the ADC is idle.

If both LESENSE scan and PRS/software scan conversions are taking place, then since there are two scans occurring, the SCAN STOP command needs to be issued twice. The user can check the SCANPENDING status flag. If the flag is set then the user needs to send out 2 SCAN STOP commands. After sending out the first SCAN STOP, the user needs to wait until the SCANPENDING flag goes low. Then the second SCAN STOP command should be issued and the user should wait on the SCANACT status flag to go low.

Note:

When switching ADCCLKMODE in the ADCn_CTRL register, use the appropriate sequence below:

- · SYNC to ASYNC:
 - 1. Disable ADC interrupts
 - 2. Clear the FIFOs
 - 3. Switch the ADCCLKMODE

If the ADC is to be used in ASYNC clock mode with WARMUPMODE set to KEEPADCWARM, then both ADCCLKMODE and WARMUPMODE fields in the ADCn_CTRL register should be set to the desired values in the same register write. This will ensure that the ADC power-on sequence is valid.

- ASYNC TO SYNC:
 - 1. Disable ADC interrupts
 - 2. Switch the ADCCLKMODE
 - 3. Clear the FIFOs

The FIFOs are cleared by writing 1 to the ADCn_SCANFIFOCLEAR and ADCn_SINGLEFIFOCLEAR registers.

When switching from ASYNC to SYNC, ensure that the ASYNC clock is turned off before doing the switch.

26.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	ADCn_CTRL	RW	Control Register
0x008	ADCn_CMD	W1	Command Register
0x00C	ADCn_STATUS	R	Status Register
0x010	ADCn_SINGLECTRL	RW	Single Channel Control Register
0x014	ADCn_SINGLECTRLX	RW	Single Channel Control Register Continued
0x018	ADCn_SCANCTRL	RW	Scan Control Register
0x01C	ADCn_SCANCTRLX	RW	Scan Control Register Continued
0x020	ADCn_SCANMASK	RW	Scan Sequence Input Mask Register
0x024	ADCn_SCANINPUTSEL	RW	Input Selection Register for Scan Mode
0x028	ADCn_SCANNEGSEL	RW	Negative Input Select Register for Scan
0x02C	ADCn_CMPTHR	RW	Compare Threshold Register
0x030	ADCn_BIASPROG	RW	Bias Programming Register for Various Analog Blocks Used in ADC Operation
0x034	ADCn_CAL	RW	Calibration Register
0x038	ADCn_IF	R	Interrupt Flag Register
0x03C	ADCn_IFS	W1	Interrupt Flag Set Register
0x040	ADCn_IFC	(R)W1	Interrupt Flag Clear Register
0x044	ADCn_IEN	RW	Interrupt Enable Register
0x048	ADCn_SINGLEDATA	R(a)	Single Conversion Result Data
0x04C	ADCn_SCANDATA	R(a)	Scan Conversion Result Data
0x050	ADCn_SINGLEDATAP	R	Single Conversion Result Data Peek Register
0x054	ADCn_SCANDATAP	R	Scan Sequence Result Data Peek Register
0x068	ADCn_SCANDATAX	R(a)	Scan Sequence Result Data + Data Source Register
0x06C	ADCn_SCANDATAXP	R	Scan Sequence Result Data + Data Source Peek Register
0x07C	ADCn_APORTREQ	R	APORT Request Status Register
0x080	ADCn_APORTCONFLICT	R	APORT Conflict Status Register
0x084	ADCn_SINGLEFIFOCOUNT	R	Single FIFO Count Register
0x088	ADCn_SCANFIFOCOUNT	R	Scan FIFO Count Register
0x08C	ADCn_SINGLEFIFOCLEAR	W1	Single FIFO Clear Register
0x090	ADCn_SCANFIFOCLEAR	W1	Scan FIFO Clear Register
0x094	ADCn_APORTMASTERDIS	RW	APORT Bus Master Disable Register

26.5 Register Description

26.5.1 ADCn_CTRL - Control Register

Offset														Bit	t Po	siti	on													
0x000	33	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	- 0
Reset	0x0	0	0		>	OX O						0x1F								00×0				0	0		0	0	0	0x0
Access	RW	Z.	R		2	≥ Y						Α								RW				X ≪	R W		W.	R ⊗	RW	RW
Name	CHCONREFWARMIDLE	CHCONMODE	DBGHALT		OVSPSEI	OVSKSEL						TIMEBASE								PRESC				ADCCLKMODE	ASYNCCLKEN		TAILGATE	SCANDMAWU	SINGLEDMAWU	WARMUPMODE

Bit	Name	Reset	Access	Description
31:30	CHCONREFWARMI- DLE	0x0	RW	Channel Connect and Reference Warm Sel When ADC is IDLE
	Channel connect and	reference warm	preferenc	е
	Value	Mode		Description
	0	PREFSCAN		Keep scan reference warm and APORT switches for first scan channel closed if WARMUPMODE is not NORMAL
	1	PREFSINGLE		Keep single reference warm and keep APORT switches for single channel closed if WARMUPMODE is not NORMAL
	2	KEEPPREV		Keep last used reference warm and keep APORT switches for corresponding channel closed if WARMUPMODE is not NORMAL
29	CHCONMODE	0	RW	Channel Connect
	Selects Channel Con	nect Mode		
	Value	Mode		Description
	0	MAXSETTLE		Connect APORT switches for the next input as soon as possible. This optimizes settling time.
	1	MAXRESP		Connect APORT switches for the next input at the end of the conversion.
28	DBGHALT	0	RW	Debug Mode Halt Enable
	Selects ADC behavio	r during debug n	node.	
	Value			Description
	0			Continue operation as normal during debug mode.
	1			Complete the current conversion and then halt during debug mode.
27:24	OVSRSEL	0x0	RW	Oversample Rate Select
	Select oversampling r	ate. Oversampli	ng must be	e enabled for this setting to take effect.

	Name	Reset	Access	Description
	Value	Mode		Description
	0	X2		2 samples for each conversion result
	1	X4		4 samples for each conversion result
	2	X8		8 samples for each conversion result
	3	X16		16 samples for each conversion result
	4	X32		32 samples for each conversion result
	5	X64		64 samples for each conversion result
	6	X128		128 samples for each conversion result
	7	X256		256 samples for each conversion result
	8	X512		512 samples for each conversion result
	9	X1024		1024 samples for each conversion result
	10	X2048		2048 samples for each conversion result
	11	X4096		4096 samples for each conversion result
23	Reserved	To ensure c	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
22:16	TIMEBASE	0x1F	RW	1us Time Base
	produce timing of 1		S warm up s	equence based on ADC_CLK. The TIMEBASE field should be set equal to
	Value			Description
	Value			Description A DO STANDDY/OLOWAGO and a superior in state 4 or /TIMEDAGE is
	Value			Description ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles.
15		To ensure of tions	ompatibility v	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIME-
	TIMEBASE		ompatibility v	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIME-BASE + 1) ADC_CLK cycles.
	TIMEBASE Reserved PRESC	0x00	RW	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conven-
	TIMEBASE Reserved PRESC	0x00	RW	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock
	Reserved PRESC Sets the prescale fa	0x00	RW	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock (adc_sar_clk) from ADC_CLK.
15 14:8	Reserved PRESC Sets the prescale fa	0x00	RW	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock (adc_sar_clk) from ADC_CLK. Description Clock prescale factor. ADC_CLK is divided by (PRESC+1) to produce
14:8	Reserved PRESC Sets the prescale factorists Value PRESC ADCCLKMODE	0x00 actor to generate	RW the ADC co	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock (adc_sar_clk) from ADC_CLK. Description Clock prescale factor. ADC_CLK is divided by (PRESC+1) to produce adc_clk_sar.
14:8	Reserved PRESC Sets the prescale factorists Value PRESC ADCCLKMODE	0x00 actor to generate	RW the ADC co	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock (adc_sar_clk) from ADC_CLK. Description Clock prescale factor. ADC_CLK is divided by (PRESC+1) to produce adc_clk_sar. ADC Clock Mode
14:8	Reserved PRESC Sets the prescale favorable PRESC ADCCLKMODE Selects ADC_CLK	0 source as synch	RW the ADC co	ADC STANDBY/SLOWACC mode warm-up is set to 1 x (TIMEBASE + 1) ADC_CLK cycles and NORMAL mode warm-up is set to 5 x (TIMEBASE + 1) ADC_CLK cycles. with future devices, always write bits to 0. More information in 1.2 Conventional Conversion Clock (adc_sar_clk) from ADC_CLK. Description Clock prescale factor. ADC_CLK is divided by (PRESC+1) to produce adc_clk_sar. ADC Clock Mode Synchronous - with respect to the Peripheral Clock (HFPERCLK).

Second Part Second Part					
Write a 1 to keep ASYNC CLK always enabled. Yalue Mode Description	Bit	Name	Reset	Access	Description
Value	6	ASYNCCLKEN	0	RW	Selects ASYNC CLK Enable Mode When ADCCLKMODE=1
ASNEEDED ASYNC CLK is enabled only during ADC Conversion.		Write a 1 to keep ASY	YNC CLK alway	s enabled.	
1 ALWAYSON ASYNC CLK is always enabled. 7 Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions TAILGATE 0 RW Conversion Tailgating Enable/disable conversion tailgating. Single channel conversions wait for a scan sequence to finish before starting. Value Description 0 Scan sequence has priority, but can be delayed by ongoing single channels. 1 Scan sequence has priority and single channels will only start immediately after completion of a scan sequence. 3 SCANDMAWU 0 RW SCANFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DxL request whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 1 DMA is available in EM2 for processing SINGLEFIFO DVL request WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 1 KEEPINSTANDBY ADC is shut down after each conversion. 5us warmup time is used before each conversion. ADC is kept in slandby mode between conversions. 1us warm-up time is used before each conversion.		Value	Mode		Description
To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions		0	ASNEEDED		ASYNC CLK is enabled only during ADC Conversion.
TAILGATE 0 RW Conversion Tailgating Enable/disable conversion tailgating. Single channel conversions wait for a scan sequence to finish before starting. Value Description 0 Scan sequence has priority, but can be delayed by ongoing single channels. 1 Scan sequence has priority and single channels will only start immediately after completion of a scan sequence. 3 SCANDMAWU 0 RW SCANFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 1 DMA is available in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warm-up time is used before each conversion.		1	ALWAYSON		ASYNC CLK is always enabled.
Enable/disable conversion tailgating. Single channel conversions wait for a scan sequence to finish before starting. Value	5	Reserved		mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
Value Description	4	TAILGATE	0	RW	Conversion Tailgating
Scan sequence has priority, but can be delayed by ongoing single channels. 1 Scan sequence has priority and single channels will only start immediately after completion of a scan sequence. 3 SCANDMAWU 0 RW SCANFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in slandby mode between conversions. 1us warm-up time is used before each conversion.		Enable/disable conve	rsion tailgating.	Single cha	nnel conversions wait for a scan sequence to finish before starting.
channels. 1 Scan sequence has priority and single channels will only start immediately after completion of a scan sequence. 3 SCANDMAWU 0 RW SCANFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warm-up time is used before each conversion.		Value			Description
SCANDMAWU 0 RW SCANFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description 0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warm-up time is used before each conversion.		0			
Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SCANFIFO Value Description While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO DMA is available in EM2 for processing SCANFIFO DVL request Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request WARMUPMODE ON RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description ONORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion.		1			
Value Description While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO DMA is available in EM2 for processing SCANFIFO DVL request SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.	3	SCANDMAWU	0	RW	SCANFIFO DMA Wakeup
0 While in EM2, the DMA controller will not get requests about DVL reached in SCANFIFO 1 DMA is available in EM2 for processing SCANFIFO DVL request 2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion.		Selects whether to wa	akeup the DMA	controller v	when in EM2 and DVL is reached in SCANFIFO
reached in SCANFIFO DMA is available in EM2 for processing SCANFIFO DVL request SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		Value			Description
2 SINGLEDMAWU 0 RW SINGLEFIFO DMA Wakeup Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description 0 While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO 1 DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		0			
Selects whether to wakeup the DMA controller when in EM2 and DVL is reached in SINGLEFIFO Value Description While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warm-up time is used before each conversion. KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warm-up time is used before each conversion.		1			DMA is available in EM2 for processing SCANFIFO DVL request
Value Description While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. ADC is kept in slow acquisition mode between conversions. 1us warm-up time is used before each conversion.	2	SINGLEDMAWU	0	RW	SINGLEFIFO DMA Wakeup
While in EM2, the DMA controller will not get requests about Data Valid Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		Selects whether to wa	akeup the DMA	controller v	when in EM2 and DVL is reached in SINGLEFIFO
Level (DVL) reached in SINGLEFIFO DMA is available in EM2 for processing SINGLEFIFO DVL request 1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description O NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warm-up time is used before each conversion.		Value			Description
1:0 WARMUPMODE 0x0 RW Warm-up Mode Select Warm-up Mode for ADC Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warm-up time is used before each conversion.		0			• • • • • • • • • • • • • • • • • • • •
Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		1			DMA is available in EM2 for processing SINGLEFIFO DVL request
Value Mode Description 0 NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.	1:0	WARMUPMODE	0x0	RW	Warm-up Mode
NORMAL ADC is shut down after each conversion. 5us warmup time is used before each conversion. KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		Select Warm-up Mod	e for ADC		
fore each conversion. 1 KEEPINSTANDBY ADC is kept in standby mode between conversions. 1us warmup time is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warmup time is used before each conversion.		Value	Mode		Description
is used before each conversion. 2 KEEPINSLOWACC ADC is kept in slow acquisition mode between conversions. 1us warm-up time is used before each conversion.		0	NORMAL		
up time is used before each conversion.		1	KEEPINSTAN	IDBY	
3 KEEPADCWARM ADC is kept on after conversions, allowing for continuous conversion.		2	KEEPINSLOV	VACC	
		3	KEEPADCWA	ARM	ADC is kept on after conversions, allowing for continuous conversion.

26.5.2 ADCn_CMD - Command Register

Offset															Ві	it Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	0	8	7	9	5	4	က	7	_	0
Reset		'	'		'						•	•		•	'											'	'	•	0	0	0	0
Access																													W M	W	W1	W1
Name																													SCANSTOP	SCANSTART	SINGLESTOP	SINGLESTART

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure c	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3	SCANSTOP	0	W1	Scan Sequence Stop
	Write a 1 to stop sca	an sequence.		
2	SCANSTART	0	W1	Scan Sequence Start
	Write a 1 to start sc	an sequence.		
1	SINGLESTOP	0	W1	Single Channel Conversion Stop
	Write a 1 to stop sin	gle channel con	versions.	
0	SINGLESTART	0	W1	Single Channel Conversion Start
	Write to 1 to start co	onverting in sing	le channel m	node.

26.5.3 ADCn_STATUS - Status Register

	_																											
Offset			T								Bi	it Po	ositi	on														
0x00C	30 31	28	26	25	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	^	9	2	4	က	7	-	0
Reset											0	0				0	2	Š	0	0						0	0	0
Access											22	22				22	۵	۲	<u>~</u>	22						œ	œ	~
Name											SCANDV	SINGLEDV				WARM	aau	7 7 7 7 7 7 7 7	SCANREFWARM	SINGLEREFWARM						SCANPENDING	SCANACT	SINGLEACT
Bit	Name			Rese	t		Ac	ces	s	Des	crip	tior	1															
31:18	Reserved			To er	sure	con	npat	ibilit _.	y wi	th fu	ture	de	/ices	s, al	way	s wi	rite b	its t	o 0.	Мо	re in	forn	natic	n in	1.2	Coi	nvei	n-
17	SCANDV			0			R			Sca	n Da	ata '	Vali	d														
	SCANCTRL	X_DVI	L # c	of scar	con	vers	ion (data	res	ults	are	ava	ilabl	e in	Sca	n Fl	FO.											
16	SINGLEDV			0			R			Sing	gle (Cha	nne	l Da	ta V	alid	l											
	SINGLECT	RLX_D	VL #	# of sir	igle c	chan	nel d	conv	ers	ion r	esu	lts a	re a	vaila	able	in S	Singl	e FI	FO.									
15:13	Reserved			To er	sure	con	npat	ibilit <u>.</u>	y wi	th fu	ture	de	/ices	s, al	way	s wi	rite b	oits t	o 0.	Мо	re in	forn	natic	n in	1.2	Col	nvei	n-
12	WARM			0			R			ADO	: Wa	arm	ed l	Jp														
	ADC is warr	med up).																									
11:10	PROGERR			0x0			R			Prog	grar	nmi	ng l	Erro	r St	atus	S											
	Programmir	ng Erro	r Sta	atus																								
	Mode			Value	;					Des	cript	ion																_
	BUSCONF			x1						APC																		
	NEGSELCO	ONF		1x																	with Y c		•					_
9	SCANREFV	WARM		0			R			Sca	n Re	efer	enc	e W	arm	ed l	Up											
	Reference s	selecte	d for	scan	mode	e is	warn	ned	up.																			
8	SINGLERE	FWARI	M	0			R			Sing	gle (Cha	nne	l Re	fere	nce	Wa	rme	d U	lр								
	Reference s	selecte	d for	single	cha	nne	l mo	de is	s wa	arme	d up) .																
7:3	Reserved			To er tions	sure	con	npat	ibilit <u>.</u>	y wi	th fu	ture	de	/ices	s, al	way	s wi	rite b	oits t	o 0.	Мо	re in	forn	natic	n in	1.2	Coi	nvei	n-
2	SCANPEND	DING		0			R			Sca	n Co	onv	ersi	on I	Pend	ding	J											
	Indicates the															oftw	are	trigg	jere	d sc	an h	as (gone	e pe	ndin	g. S	CA	N-
1	SCANACT			0			R			Sca	n Co	onv	ersi	on A	Activ	ve												
	Scan seque	ence is	activ	e or h	as pe	endi	ng c	onve	ersio	ons.																		

Bit	Name	Reset	Access	Description
0	SINGLEACT	0	R	Single Channel Conversion Active
	Single channel conve	rsion is active o	r has pendi	ng conversions.

26.5.4 A	DCn	_SI	NGL	EC.	TRL	. - Si	ingl	e C	hanı	nel (Con	trol	Re	gist	er																	
Offset															Bi	t Pc	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset	0		0			2	OXO						L							1	L					0x0		2	OXO	0	0	0
Access	RW		₩ M			20	<u>}</u>					2	<u>}</u>							2	<u>}</u>					₩ M		2	<u>}</u>	RW	Z.	RW
Name	CMPEN		PRSEN			-	<u>-</u>					[]	NEGOEL								TOSSEL					REF		010	N L L	ADJ	DIFF	REP
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
31	CN	1PE	N				0				RV	V		Con	npar	e L	ogic	En	able	foi	Sir	ngle	Ch	ann	el							
	En	able	/disa	able	Coi	mpa	ire L	ogio	2																							

Name	CMPI	AT	NEG.		POS	REF	RES	ADJ DIFF REP
Bit	Name	Reset	Access	Description				
31	CMPEN	0	RW	Compare L	ogic Enable for Single Chann	el		
	Enable/disable C	Compare Logic						
	Value			Description				
	0			Disable Con	npare Logic.			
	1			Enable Com	pare Logic.			
30	Reserved	To ensure c	ompatibility v	with future dev	rices, always write bits to 0. Mor	re informatio	on in 1.:	2 Conven-
29	PRSEN	0	RW	Single Cha	nnel PRS Trigger Enable			
	Enabled/disable	PRS trigger of sing	le channel.					
	Value			Description				
	0			Single chan	nel is not triggered by PRS inpu	t.		
	1			Single chan	nel is triggered by PRS input se	lected by P	RSSEL	
28	Reserved	To ensure c	ompatibility v	with future dev	rices, always write bits to 0. Mor	re informatio	on in 1.:	2 Conven-
27:24	AT	0x0	RW	Single Cha	nnel Acquisition Time			
	Select the acquis							
		sition time for single	e channel.					
	Value	sition time for single Mode	e channel.	Description				
	Value 0		e channel.		n clock cycle acquisition time for	single cha	nnel	
	-	Mode	e channel.	1 conversion	n clock cycle acquisition time for	-		
	0	Mode 1CYCLE	e channel.	1 conversion	<u> </u>	or single ch	annel	
	0	Mode 1CYCLE 2CYCLES	e channel.	1 conversion 2 conversion 3 conversion	clock cycles acquisition time for	or single cha	annel	
	0 1 2	Mode 1CYCLE 2CYCLES 3CYCLES	e channel.	1 conversion 2 conversion 3 conversion 4 conversion	n clock cycles acquisition time for clock cycles acquisition time for	or single char or single char or single char	annel annel annel	
	0 1 2 3	Mode 1CYCLE 2CYCLES 3CYCLES 4CYCLES		1 conversion 2 conversion 3 conversion 4 conversion 8 conversion	n clock cycles acquisition time for n clock cycles acquisition time for n clock cycles acquisition time for	or single char or single char or single char or single char	annel annel annel annel	
	0 1 2 3 4	Mode 1CYCLE 2CYCLES 3CYCLES 4CYCLES 8CYCLES		1 conversion 2 conversion 3 conversion 4 conversion 8 conversion 16 conversion	a clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for	or single charsingle c	annel annel annel annel hannel	
	0 1 2 3 4 5	Mode 1CYCLE 2CYCLES 3CYCLES 4CYCLES 8CYCLES 16CYCLES		1 conversion 2 conversion 3 conversion 4 conversion 8 conversion 16 conversion 32 conversion	a clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time	or single charsingle c	annel annel annel annel hannel	
	0 1 2 3 4 5	Mode 1CYCLE 2CYCLES 3CYCLES 4CYCLES 8CYCLES 16CYCLES 32CYCLES		1 conversion 2 conversion 3 conversion 4 conversion 8 conversion 16 conversion 32 conversion 64 conversion	a clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time for clock cycles acquisition time on clock cycles acquisition time on clock cycles acquisition time	or single character sin	annel annel annel annel hannel hannel	

Bit	Name	Reset	Access	Description
23:16	NEGSEL	0xFF	RW	Single Channel Negative Input Selection

Selects the negative input to the ADC for Single Channel Differential mode (in case of singled ended mode, the negative input is grounded). The user can choose any of the 32 channels of any of the 5 BUSes but must ensure that POSSEL and NEGSEL are chosen from different resources (X or Y) BUS. In case of an invalid configuration, the ADC will perform a single-ended sampling and issue a BUSCONFLICT IRQ.

Mode	Value		Description
APORT0XCH0	0		Select APORT0XCH0
APORT0XCH1	1		Select APORT0XCH1
APORT0XCH15	15		Select APORT0XCH15
APORT0YCH0	16		Select APORT0YCH0
APORT0YCH1	17		Select APORT0YCH1
APORT0YCH15	31		Select APORT0YCH15
APORT1XCH0	32		Select APORT1XCH0
APORT1YCH1	33		Select APORT1YCH1
APORT1YCH31	63		Select APORT1YCH31
APORT2YCH0	64		Select APORT2YCH0
APORT2XCH1	65		Select APORT2XCH1
APORT2XCH31	95		Select APORT2XCH31
APORT3XCH0	96		Select APORT3XCH0
APORT3YCH1	97		Select APORT3YCH1
APORT3YCH31	127		Select APORT3YCH31
APORT4YCH0	128		Select APORT4YCH0
APORT4XCH1	129		Select APORT4XCH1
APORT4XCH31	159		Select APORT4XCH31
TESTN	245		Reserved for future expansion
VSS	255		VSS
POSSEL	0xFF	RW	Single Channel Positive Input Selection

Selects the positive input to the ADC for single channel operation. Software can choose any of the 32 channels of any BUS as positive input. In DIFF mode POSSEL and NEGSEL need to be chosen from different resources (X or Y). If an X BUS is connected to POSSEL, only a Y BUS can connect to NEGSEL, and vice-versa. The user can also select some internal nodes as positive input for single-ended sampling. These internal nodes cannot be sampled differentially.

Mode	Value	Description
APORT0XCH0	0	Select APORT0XCH0
APORT0XCH1	1	Select APORT0XCH1

15:8

Name	Reset	Access	Description
APORT0XCH15	15		Select APORT0XCH15
APORT0YCH0	16		Select APORT0YCH0
APORT0YCH1	17		Select APORT0YCH1
APORT0YCH15	31		Select APORT0YCH15
APORT1XCH0	32		Select APORT1XCH0
APORT1YCH1	33		Select APORT1YCH1
APORT1YCH31	63		Select APORT1YCH31
APORT2YCH0	64		Select APORT2YCH0
APORT2XCH1	65		Select APORT2XCH1
APORT2XCH31	95		Select APORT2XCH31
APORT3XCH0	96		Select APORT3XCH0
APORT3YCH1	97		Select APORT3YCH1
APORT3YCH31	127		Select APORT3YCH31
APORT4YCH0	128		Select APORT4YCH0
APORT4XCH1	129		Select APORT4XCH1
APORT4XCH31	159		Select APORT4XCH31
AVDD	224		Select AVDD
BUVDD	225		Select BUVDD
DVDD	226		Select DVDD
PAVDD	227		Reserved for future use
DECOUPLE	228		Select DECOUPLE
IOVDD	229		Select IOVDD
IOVDD1	230		Select IOVDD1. Not Applicable if no IOVDD1 is available.
VSP	231		Reserved for future expansion
OPA2	242		OPA2 output. Not Applicable if no OPA is available.
TEMP	243		Temperature sensor
DAC0OUT0	244		DAC0 output 0. Not Applicable if no DAC is available.
R5VOUT	245		5V sub-system ADC mux output. Not Applicable if no 5V sub-system available.
SP1	246		Reserved for future expansion
SP2	247		Reserved for future expansion
DAC0OUT1	248		DAC0 output 1. Not Applicable if no DAC is available.

Bit	Name	Reset	Access	Description
	SUBLSB	249		SUBLSB measurement enabled.
	OPA3	250		OPA3 output. Not Applicable if no OPA is available.
	VSS	255		VSS
7:5	REF	0x0	RW	Single Channel Reference Selection
	Select reference to	o ADC single chann	nel mode.	
	Value	Mode		Description
	0	1V25		VFS = 1.25V with internal VBGR reference
	1	2V5		VFS = 2.5V with internal VBGR reference
	2	VDD		VFS = AVDD with AVDD as reference source
	3	5V		VFS = 5V with internal VBGR reference
	4	EXTSINGLE		Single ended external reference
	5	2XEXTDIFF		Differential external reference, 2x
	6	2XVDD		VFS = 2xAVDD with AVDD as the reference source
	7	CONF		Use SINGLECTRLX to configure reference
4:3	RES	0x0	RW	Single Channel Resolution Select
	Select single char	nnel conversion reso	olution.	
	Value	Mode		Description
	0	12BIT		12-bit resolution.
	1	8BIT		8-bit resolution.
	2	6BIT		6-bit resolution.
	3	OVS		Oversampling enabled. Oversampling rate is set in OVSRSEL.
2	ADJ	0	RW	Single Channel Result Adjustment
	Select single char	nnel result adjustme	nt.	
	Value	Mode		Description
	0	RIGHT		Results are right adjusted.
	1	LEFT		Results are left adjusted.
1	DIFF	0	RW	Single Channel Differential Mode
	Select single ende	ed or differential inp	ut.	
	Value			Description
	0			Single ended input.
	1			Differential input.
0	REP	0	RW	Single Channel Repetitive Mode
	Enable/disable rep	petitive single chanr	nel convers	sions.
	Value			Description

Bit	Name	Reset	Access	Description
	0			ADC will perform one conversion per trigger in single channel mode.
	1			ADC will repeat conversions in single channel mode continuously until SINGLESTOP is written.

26.5.5 ADCn_SINGLECTRLX - Single Channel Control Register Continued

Offset															Ві	t Po	siti	on														
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		000			0			00x0					0×0			0		0	2	0x0		0×0				2	OXO	•	0		0X0	
Access		M			₹			¥ M					2	≩ Y		₽		₽	2	2		2	<u>}</u>			2	<u>}</u>		₹		₽	
Name		REPDELAY			CONVSTARTDELAYEN			CONVSTARTDELAY					10000	PRSSEL		PRSMODE		FIFOOFACT	70	D.		FFANIX				VDEEATT	VRETATI		VREFATTFIX		VREFSEL	

	REPD	CON		PRSS PRSS PRSS VINAT VINAT VREF VREF											
Bit	Name	Reset	Access	Description											
31:29	REPDELAY	0x0	RW	REPDELAY Select for SINGLE REP Mode											
	Delay value between t	two repeated con	versions.												
	Value	Mode		Description											
	0	NODELAY		No delay											
	1	4CYCLES		4 conversion clock cycles											
	2	8CYCLES		8 conversion clock cycles											
	3	16CYCLES		16 conversion clock cycles											
	4	32CYCLES		32 conversion clock cycles											
	5	64CYCLES		64 conversion clock cycles											
	6	128CYCLES		128 conversion clock cycles											
	7	256CYCLES		256 conversion clock cycles											
28	Reserved	To ensure comp tions	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conver											
	CONVSTARTDE-	0	RW	Enable Delaying Next Conversion Start											
27	LAYEN	Ū		Litable Delaying Next Conversion Start											
27				Chable belaying Next Conversion Start											
27	LAYEN			Description											
27	LAYEN Delay value for next of														
27	LAYEN Delay value for next of Value			Description											
26:22	LAYEN Delay value for next or Value 0	onversion start ev		Description CONVSTARTDELAY is disabled.											
	LAYEN Delay value for next of Value 0 1 CONVSTARTDELAY	onversion start ev	vent.	Description CONVSTARTDELAY is disabled. CONVSTARTDELAY is enabled. Delay Value for Next Conversion Start If CONVSTARTDELAYEN is											
	LAYEN Delay value for next of Value 0 1 CONVSTARTDELAY	onversion start ev	vent.	Description CONVSTARTDELAY is disabled. CONVSTARTDELAY is enabled. Delay Value for Next Conversion Start If CONVSTARTDELAYEN is Set											

Bit	Name	Reset Acces	ss Description
21	Reserved	To ensure compatibilitions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
20:17	PRSSEL	0x0 RW	Single Channel PRS Trigger Select
	Select PRS trigger	r for single channel.	
	Value	Mode	Description
	0	PRSCH0	PRS ch 0 triggers single channel
	1	PRSCH1	PRS ch 1 triggers single channel
	2	PRSCH2	PRS ch 2 triggers single channel
	3	PRSCH3	PRS ch 3 triggers single channel
	4	PRSCH4	PRS ch 4 triggers single channel
	5	PRSCH5	PRS ch 5 triggers single channel
	6	PRSCH6	PRS ch 6 triggers single channel
	7	PRSCH7	PRS ch 7 triggers single channel
	8	PRSCH8	PRS ch 8 triggers single channel
	9	PRSCH9	PRS ch 9 triggers single channel
	10	PRSCH10	PRS ch 10 triggers single channel
	11	PRSCH11	PRS ch 11 triggers single channel
16	PRSMODE	0 RW	Single Channel PRS Trigger Mode
	PRS trigger mode	of single channel.	
	Value	Mode	Description
	0	PULSED	Single channel trigger is considered a regular asynchronous pulse that starts ADC warm-up, then acquisition/conversion sequence. The ADC_CLK controls the warmup-time.
	1	TIMED	Single channel trigger should be a pulse long enough to provide the required warm-up time for the selected ADC warmup mode. The negative edge requests sample acquisition. DELAY can be used to delay the warm-up request if the pulse is too long.
15	Reserved	To ensure compatibili	ty with future devices, always write bits to 0. More information in 1.2 Conven-
14	FIFOOFACT	0 RW	Single Channel FIFO Overflow Action
	Select how FIFO b	pehaves when full	
	Value	Mode	Description
	0	DISCARD	FIFO stops accepting new data if full, triggers SINGLEOF IRQ.
	1	OVERWRITE	FIFO overwrites old data when full, triggers SINGLEOF IRQ.
13:12	DVL	0x0 RW	Single Channel DV Level Select
		nel Data Valid level. SINGl re available in the Single F	LE IRQ is set when (DVL+1) number of single channels have been converted FO.

Bit	Name	Reset	Access	Description									
11:8	VINATT	0x0	RW	Code for VIN Attenuation Factor									
	Used to set the VII	N attenuation factor.											
7:4	VREFATT	0x0	RW	Code for VREF Attenuation Factor When VREFSEL is 1, 2 or 5									
	Used to set VREF	attenuation factor.											
3	VREFATTFIX	0	RW	Enable Fixed Scaling on VREF									
	Enables fixed scali	ing on VREF											
	Value			Description									
	0			VREFATT setting is used to scale VREF when VREFSEL is 1, 2 or 5.									
	1			A fixed VREF attenuation is used to cover a large reference source range. When VREFATT = 0, the scaling factor is 1/4. For non-zero values of VREFATT, the scaling factor is 1/3.									
2:0	VREFSEL	0x0	RW	Single Channel Reference Selection									
	Select reference V	REF to ADC single of	channel m	node.									
	Value	Mode		Description									
	0	VBGR		Internal 0.83V Bandgap reference									
	1	VDDXWATT		Scaled AVDD: AVDD*(the VREF attenuation factor)									
	2	VREFPWATT		Scaled singled ended external Vref: ADCn_EXTP*(the VREF attenuation factor)									
	3	VREFP		Raw single ended external Vref: ADCn_EXTP									
	4	VENTROPY		Special mode used to generate ENTROPY.									
	5	VREFPNWATT	-	Scaled differential external Vref from : (ADCn_EXTP-ADCn_EXTN)*(the VREF attenuation factor)									
	_			Raw differential external Vref from : (ADCn_EXTP-ADCn_EXTN)									
	6	VREFPN		Naw differential external viernom: (ADOI_EXTI -ADOI_EXTIV)									

26.5.6 ADCn_SCANCTRL - Scan Control Register

Offset		Bit Position																														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset	0		0			2	e X							•	•	•	•	•	•							0x0	•	2	2	0	0	0
Access	₩		Z.			2	<u>}</u>																			₩		λ Δ		₽	W.	RW W
Name	CMPEN		PRSEN			L	_																			REF		O.) 	ADJ	DIFF	REP

	S R	TA			R.	A.	A P B									
Bit	Name	Reset	Access	Description												
31	CMPEN	0	RW	Compare Logic Enable for Scan												
	Enable/disable Com	npare Logic														
	Value			Description												
	0			Disable Compare Logic.												
	1			Enable Compare Logic.												
30	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-												
29	PRSEN	0	RW	Scan Sequence PRS Trigger Enable												
	Enabled/disable PR	S trigger of scan	sequence.													
	Value			Description												
	0			Scan sequence is not triggered by PRS input	ut											
	1			Scan sequence is triggered by PRS input se	elected by l	PRSSE	L									
28	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. Mo	re informati	on in 1.	2 Conven-									
27:24	AT	0x0	RW	Scan Acquisition Time												
	Select the acquisition	on time for scan.														
	Value	Mode		Description												
	0	1CYCLE		1 conversion clock cycle acquisition time for	r scan											
	1	2CYCLES		2 conversion clock cycles acquisition time for	or scan											
	2	3CYCLES		3 conversion clock cycles acquisition time for	or scan											
	3	4CYCLES		4 conversion clock cycles acquisition time for	or scan											
	4	8CYCLES		8 conversion clock cycles acquisition time for	or scan											
	5	16CYCLES		16 conversion clock cycles acquisition time	for scan											
	6	32CYCLES		32 conversion clock cycles acquisition time for scan												
	7	64CYCLES		64 conversion clock cycles acquisition time for scan												
	8	128CYCLES		128 conversion clock cycles acquisition time	e for scan											
	9	256CYCLES		256 conversion clock cycles acquisition time for scan												

Bit	Name	Reset	Access	Description
23:8	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:5	REF	0x0	RW	Scan Sequence Reference Selection
	Select reference	to ADC scan seque	ence.	
	Value	Mode	-	Description
	0	1V25		VFS = 1.25V with internal VBGR reference
	1	2V5		VFS = 2.5V with internal VBGR reference
	2	VDD		VFS = AVDD with AVDD as reference source
	3	5V		VFS = 5V with internal VBGR reference
	4	EXTSINGLE		Single ended external reference
	5	2XEXTDIFF		Differential external reference, 2x
	6	2XVDD		VFS=2xAVDD with AVDD as the reference source
	7	CONF		Use SCANCTRLX to configure reference
4:3	RES	0x0	RW	Scan Sequence Resolution Select
	Select scan sequ	uence conversion re	solution.	
	Value	Mode		Description
	0	12BIT		12-bit resolution
	1	8BIT		8-bit resolution
	2	6BIT		6-bit resolution
	3	ovs		Oversampling enabled. Oversampling rate is set in OVSRSEL
2	ADJ	0	RW	Scan Sequence Result Adjustment
	Select scan seq	uence result adjustn	nent.	
	Value	Mode		Description
	0	RIGHT		Results are right adjusted
	1	LEFT		Results are left adjusted
1	DIFF	0	RW	Scan Sequence Differential Mode
	Select single en	ded or differential in	put.	
	Value			Description
	0			Single ended input
	1			Differential input
0	REP	0	RW	Scan Sequence Repetitive Mode
		repetitive scan seque		•
	Value			Description
	0			Scan conversion mode is deactivated after one sequence.

Bit	Name	Reset	Access	Description
	1			Scan conversion mode repeats continuously until SCANSTOP is written.

26.5.7 ADCn_SCANCTRLX - Scan Control Register Continued

Offset															Bi	it Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	000000000000000000000000000000000000000										0 0 0		0		0	2	OXO			0 0 0			2	OXO	•	0		0×0				
Access	RW RW								i	≥ Y		ZW W		₩ M	2	≥ Y			Σ			2	<u>}</u>		Z M		Z. M					
Name		REPDELAY			CONVSTARTDELAYEN			CONVSTARTDELAY						PRSSEL		PRSMODE		FIFOOFACT	70	DVL			VINATT			VDEE A T T			VREFATTFIX		VREFSEL	

	CON	CON		PRS PRS											
Bit	Name	Reset	Access	Description											
31:29	REPDELAY	0x0	RW	REPDELAY Select for SCAN REP Mode											
	Delay value between	two repeated co	nversions.												
	Value	Mode		Description											
	0	NODELAY		No delay											
	1	4CYCLES		4 conversion clock cycles											
	2	8CYCLES		8 conversion clock cycles											
	3	16CYCLES		16 conversion clock cycles											
	4	32CYCLES		32 conversion clock cycles											
	5	64CYCLES		64 conversion clock cycles											
	6	128CYCLES		128 conversion clock cycles											
	7	256CYCLES		256 conversion clock cycles											
28	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-											
27	CONVSTARTDE- LAYEN	0	RW	Enable Delaying Next Conversion Start											
	Delay value for next of	onversion start e	event.												
	Value			Description											
	0			CONVSTARTDELAY is disabled											
	1			CONVSTARTDELAY is enabled.											
26:22	CONVSTARTDELAY	0x00	RW	Delay Next Conversion Start If CONVSTARTDELAYEN is Set											
	Delay value for next c	onversion start e	event in 1u	s ticks (based on TIMEBASE)											
	Value	Description	-												
	DELAY	Delay the nex sion start by (Dus		-											

Bit	Name	Reset Access	Description									
21	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-									
20:17	PRSSEL	0x0 RW	Scan Sequence PRS Trigger Select									
	Select PRS trigge	r for scan sequence.										
	Value	Mode	Description									
	0	PRSCH0	PRS ch 0 triggers scan sequence									
	1	PRSCH1	PRS ch 1 triggers scan sequence									
	2	PRSCH2	PRS ch 2 triggers scan sequence									
	3	PRSCH3	PRS ch 3 triggers scan sequence									
	4	PRSCH4	PRS ch 4 triggers scan sequence									
	5	PRSCH5	PRS ch 5 triggers scan sequence									
	6	PRSCH6	PRS ch 6 triggers scan sequence									
	7	PRSCH7	PRS ch 7 triggers scan sequence									
	8	PRSCH8	PRS ch 8 triggers scan sequence									
	9	PRSCH9	PRS ch 9 triggers scan sequence									
	10	PRSCH10	PRS ch 10 triggers scan sequence									
	11	PRSCH11	PRS ch 11 triggers scan sequence									
16	PRSMODE	0 RW	Scan PRS Trigger Mode									
	PRS trigger mode	e of scan.										
	Value	Mode	Description									
	0	PULSED	Scan trigger is considered a regular async pulse that starts ADC warm-up, then acquisition/conversion sequence. The ADC_CLK controls the warmup-time.									
	1	TIMED	Scan trigger should be a pulse long enough to provide the required warm-up time for the selected ADC warmup mode. The negative edge requests sample acquisition. DELAY can be used to delay the warm-up request if the pulse is too long.									
15	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-									
14	FIFOOFACT	0 RW	Scan FIFO Overflow Action									
	Select how FIFO	behaves when full										
	Value	Mode	Description									
	0	DISCARD	FIFO stops accepting new data if full, triggers SCANOF IRQ.									
	1	OVERWRITE	FIFO overwrites old data when full, triggers SCANOF IRQ.									
13:12	DVL	0x0 RW	Scan DV Level Select									
		Valid level. SCAN IRQ is set ble in the SCAN FIFO.	when (DVL+1) number of scan channels have been converted and their									

Bit	Name	Reset	Access	Description
11:8	VINATT	0x0	RW	Code for VIN Attenuation Factor
	Used to set the V	IN attenuation factor.		
7:4	VREFATT	0x0	RW	Code for VREF Attenuation Factor When VREFSEL is 1, 2 or 5
	Used to set VREF	attenuation factor.		
3	VREFATTFIX	0	RW	Enable Fixed Scaling on VREF
	Enables fixed sca	lling on VREF		
	Value			Description
	0			VREFATT setting is used to scale VREF when VREFSEL is 1, 2 or 5.
	1			A fixed VREF attenuation is used to cover a large reference source range. When VREFATT = 0, the scaling factor is 1/4. For non-zero values of VREFATT, the scaling factor is 1/3.
2:0	VREFSEL	0x0	RW	Scan Channel Reference Selection
	Select reference	VDEE to ADC occup of	nannel mo	ode.
		VREF 10 ADC SCAILC	iailiici iiic	
	Value	Mode		Description
	Value 0			Description Internal 0.83V Bandgap reference
		Mode		· · · · · · · · · · · · · · · · · · ·
	0	Mode VBGR		Internal 0.83V Bandgap reference
	0	Mode VBGR VDDXWATT		Internal 0.83V Bandgap reference Scaled AVDD: AVDD*(the VREF attenuation factor) Scaled singled ended external Vref: ADCn_EXTP*(the VREF attenua-
	0 1 2	Mode VBGR VDDXWATT VREFPWATT		Internal 0.83V Bandgap reference Scaled AVDD: AVDD*(the VREF attenuation factor) Scaled singled ended external Vref: ADCn_EXTP*(the VREF attenuation factor)
	0 1 2 3	Mode VBGR VDDXWATT VREFPWATT VREFP		Internal 0.83V Bandgap reference Scaled AVDD: AVDD*(the VREF attenuation factor) Scaled singled ended external Vref: ADCn_EXTP*(the VREF attenuation factor) Raw single ended external Vref: ADCn_EXTP Scaled differential external Vref from: (ADCn_EXTP-

26.5.8 ADCn_SCANMASK - Scan Sequence Input Mask Register

0x00000000

RW

Offset	Bit Position																													
0x020	31	30	29	28	27	26	25	24	23	22	21	20	9 8	17	16	2 ;	4	5 5	; =====================================	10	6	8	7	9	5	4	က	2	- 0	>
Reset		00000000000000000000000000000000000000																												
Access		₽₩																												
Name	SCANINPUTEN																													
Bit	Na	me					Re	set			Acc	cess	Des	crip	tion															

Set one or more bits in this mask to select which inputs are included in scan sequence in either single ended or differential mode. This works with SCANINPUTSEL register. The SCANINPUTSEL chooses 32 possible channels for single-ended or 32 pairs of possible channels for differential scanning from BUSes. These chosen channels are referred as ADCn_INPUTx in the description. Four even inputs from first group of 8 ADCn_INPUTx and four odd inputs from second group of 8 ADCn_INPUTx have programmable NEGSEL, defined in SCANNEGSEL register. If the SCANMASK is set to 0 and scan conversion is triggered, ADC will do a conversion with garbage results since no inputs were enabled for conversion.

Scan Sequence Input Mask

Mode	Value	Description
DIFF = 0		
INPUT0	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT0 included in mask
INPUT1	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT1 included in mask
INPUT2	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT2 included in mask
INPUT3	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT3 included in mask
INPUT4	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT4 included in mask
INPUT5	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT5 included in mask
INPUT6	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT6 included in mask
INPUT7	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT7 included in mask
INPUT31	1xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	ADCn_INPUT31 included in mask
DIFF = 1		
INPUT0INPUT0NEG- SEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT0 Negative input: chosen by IN-PUT0NEGSEL) included in mask

31:0

SCANINPUTEN

	Name	Reset Access	Description
-	INPUT1INPUT2	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT1 Negative input: ADCn_INPUT2) inc ded in mask
	INPUT2INPUT2NEG- SEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT2 Negative input: chosen by IN-PUT2NEGSEL) included in mask
I	INPUT3INPUT4	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT3 Negative input: ADCn_INPUT4) inc ded in mask
	INPUT4INPUT4NEG- SEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT4 Negative input: chosen by IN-PUT4NEGSEL) included in mask
I	INPUT5INPUT6	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT5 Negative input: ADCn_INPUT6) included in mask
	INPUT6INPUT6NEG- SEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT6 Negative input: chosen by IN-PUT6NEGSEL) included in mask
I	INPUT7INPUT0	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT7 Negative input: ADCn_INPUT8) included in mask
I	INPUT8INPUT9	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT8 Negative input: ADCn_INPUT9) included in mask
	INPUT9INPUT9NEG- SEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT9 Negative input: chosen by IN-PUT9NEGSEL) included in mask
I	INPUT10INPUT11	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT10 Negative input: ADCn_INPUT11) cluded in mask
	INPUT11IN- PUT11NEGSEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT11 Negative input: chosen by IN-PUT11NEGSEL) included in mask
I	INPUT12INPUT13	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT12 Negative input: ADCn_INPUT13) cluded in mask
	INPUT13IN- PUT13NEGSEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT13 Negative input: chosen by IN-PUT13NEGSEL) included in mask
I	INPUT14INPUT15	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT14 Negative input: ADCn_INPUT15) cluded in mask
	INPUT15IN- PUT15NEGSEL	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT15 Negative input: chosen by IN-PUT15NEGSEL) included in mask
I	INPUT16INPUT17	xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT16 Negative input: ADCn_INPUT17) cluded in mask
I	INPUT28INPUT29	xxx1xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT28 Negative input: ADCn_INPUT29) cluded in mask
I	INPUT29INPUT30	xx1xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT29 Negative input: ADCn_INPUT30) cluded in mask
I	INPUT30INPUT31	x1xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT30 Negative input: ADCn_INPUT31) cluded in mask
I	INPUT31INPUT24	1xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx	(Positive input: ADCn_INPUT31 Negative input: ADCn_INPUT24) cluded in mask

26.5.9 ADCn_SCANINPUTSEL - Input Selection Register for Scan Mode

Offset											Bi	t Po	si <u>ti</u>	on															
0x024	30 29 29	28	56	25	23	22	21	20	19	18	17	16	15	4	13	12	7	10	0	- ω	_	. 9	2	, .	4	က	7	_	0
Reset	0,0,0		00X0				.,	•••	`	00X0	`		`	`	,	<u> </u>	\	00X0	1	"			1		`		00×0	1	
Access			8							₩								₩ N									R		
Name			INPUT24T031SEL							INPUT16TO23SEL								INPUT8T015SEL									INPUT0T07SEL		
Bit	Name			Reset			Acc	ces	s I	Des	crip	tion																	
31:29	Reserved			To ens	ure	сотр	patil	bility	y wit	th fu	ture	dev	ices	, al	way	's wr	ite k	oits	to 0	Мо	re	infor	mat	ior	ı in	1.2	Co	nvei	7-
28:24	INPUT24T	O31SEL	,				Chos ASk		for	AD	Cn_	INP	UT2	24-A	DCı	n_l	NPL	JT31	l a	s R	efe	rre	d in						
	Mode			[Des	cript	ion																	_					
	APORT0C	H0TO7		0						Sele	ct A	POF	RT0'	s C	H0-	CH7	' as	AD	Cn_	INP	UT	24-A	DCı	n_	INP	UT	31		_
	APORT0C	H8TO15		1					5	Sele	ct A	POF	RT0'	s C	H8-	CH1	5 as	s A[OCn	_INF	PU	T24-	ADO	Cn	_IN	PU	T31		
	APORT1C	Н0ТО7		4					5	Sele	ct A	POF	RT1'	s C	H0-	CH7	as	AD	Cn_	INP	UT	24-A	DCı	n_	INP	UT	31		
	APORT1C	H8TO15		5					Select APORT1's CH8-CH15 as ADCn_INPUT24-ADCn_INPUT31																				
	APORT1C	H16TO2	3	6					5	Sele	ct A	POF	RT1'	s C	H16	6-CH	123 a	as A	DC	n_IN	ΝPl	UT24	1-AC	C	n_ll	NΡ	JT3	31	
	APORT1C	H24TO3	1	7					(Sele	ct A	POF	RT1'	s C	H24	I-CH	131 a	as A	NDC	n_IN	۱P۱	UT24	1-AC	C	n_II	NΡ	JT3	31	
	APORT2C	Н0ТО7		8					(Sele	ct A	POF	RT2'	s C	H0-	CH7	as	AD	Cn_	INP	UT	24-A	DCı	n_	INP	UT	31		
	APORT3C	Н0ТО7		12					(Sele	ct A	POF	RT3'	s C	H0-	CH7	as	AD	Cn_	INP	UT	24-A	DCı	n_	INP	UT	31		
	APORT4C	Н0ТО7		16				Select APORT4's CH0-CH7 as ADCn_INPUT24-ADCn_INPUT31																					
	<u></u>																									_			
23:21 Reserved To ensure compatibility with future devices, always write bits to 0. More in tions											infor	mat	ior	n in	1.2	Co	nvei	7-											
20:16 INPUT16TO23SEL 0x00 RW Inputs Chosen for ADCn_INPUT16-SCANMASK											16-A	DCı	n_l	NPU	JT23	3 a	s R	efe	rre	d in									
	Mode			Value					[Desc	cript	ion																	_
	APORT0C	Н0ТО7		0					5	Sele	ct A	POF	RT0'	s C	H0-	CH7	as	AD	Cn_	INP	UT	16-A	DCı	n_	INP	UT	23		_
	APORT0C	H8TO15		1					5	Sele	ct A	POF	RT0'	s C	H8-	CH1	5 as	s A[OCn	_INF	PU	T16-	ADO	Cn _.	_IN	PU	T23	3	
	APORT1C	Н0ТО7		4					5	Sele	ct A	POF	RT1'	s C	H0-	CH7	as	AD	DCn_INPUT16-ADCn_INPUT23										

Bit	Name	Reset	Access	Description
	APORT1CH8TO15	5		Select APORT1's CH8-CH15 as ADCn_INPUT16-ADCn_INPUT23
	APORT1CH16TO23	6		Select APORT1's CH16-CH23 as ADCn_INPUT16-ADCn_INPUT23
	APORT1CH24TO31	7		Select APORT1's CH24-CH31 as ADCn_INPUT16-ADCn_INPUT23
	APORT2CH0TO7	8		Select APORT2's CH0-CH7 as ADCn_INPUT16-ADCn_INPUT23
	APORT3CH0TO7	12		Select APORT3's CH0-CH7 as ADCn_INPUT16-ADCn_INPUT23
		•		
	APORT4CH0TO7	16		Select APORT4's CH0-CH7 as ADCn_INPUT16-ADCn_INPUT23
15:13	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	INPUT8TO15SEL	0x00	RW	Inputs Chosen for ADCn_INPUT8-ADCn_INPUT15 as Referred in SCANMASK
	Mode	Value		Description
	APORT0CH0T07	0		Select APORT0's CH0-CH7 as ADCn_INPUT8-ADCn_INPUT15
	APORT0CH8TO15	1		Select APORT0's CH8-CH15 as ADCn_INPUT8-ADCn_INPUT15
	APORT1CH0TO7	4		Select APORT1's CH0-CH7 as ADCn_INPUT8-ADCn_INPUT15
	APORT1CH8TO15	5		Select APORT1's CH8-CH15 as ADCn_INPUT8-ADCn_INPUT15
	APORT1CH16TO23	6		Select APORT1's CH16-CH23 as ADCn_INPUT8-ADCn_INPUT15
	APORT1CH24TO31	7		Select APORT1's CH24-CH31 as ADCn_INPUT8-ADCn_INPUT15
	APORT2CH0TO7	8		Select APORT2's CH0-CH7 as ADCn_INPUT8-ADCn_INPUT15
	APORT3CH0TO7	12		Select APORT3's CH0-CH7 as ADCn_INPUT8-ADCn_INPUT15
	APORT4CH0TO7	16		Select APORT4's CH0-CH7 as ADCn_INPUT8-ADCn_INPUT15
7:5	Reserved	To ensure comp	patibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4:0	INPUT0T07SEL	0x00	RW	Inputs Chosen for ADCn_INPUT7-ADCn_INPUT0 as Referred in SCANMASK
	Mode	Value		Description
	APORT0CH0TO7	0		Select APORT0's CH0-CH7 as ADCn_INPUT0-ADCn_INPUT7
	APORT0CH8TO15	1		Select APORT0's CH8-CH15 as ADCn_INPUT0-ADCn_INPUT7
	APORT1CH0TO7	4		Select APORT1's CH0-CH7 as ADCn_INPUT0-ADCn_INPUT7
	APORT1CH8TO15	5		Select APORT1's CH8-CH15 as ADCn_INPUT0-ADCn_INPUT7

Bit	Name	Reset	Access	Description
	APORT1CH24TO31	7		Select APORT1's CH24-CH31 as ADCn_INPUT0-ADCn_INPUT7
	APORT2CH0TO7	8		Select APORT2's CH0-CH7 as ADCn_INPUT0-ADCn_INPUT7
	APORT3CH0TO7	12		Select APORT3's CH0-CH7 as ADCn_INPUT0-ADCn_INPUT7
	APORT4CH0TO7	16		Select APORT4's CH0-CH7 as ADCn_INPUT0-ADCn_INPUT7

26.5.10 ADCn_SCANNEGSEL - Negative Input Select Register for Scan

Offset				Bit Po	sition							
0x028	33 30 28 28 27 26 26	22 24 22 23 23 23	1 2 2 5	1 18 19	τ 1	13	- 2	တ ထ	7 9	ro 4	e 0	- 0
Reset					0x0	0x3	0x2	0×1	0x3	0x2	1X0	0x0
Access					S S S	W.	₩ M	§ S	§ N	§ N	§ N	N N
											_	_
					NPUT15NEGSEL	NPUT13NEGSEL	NPUT11NEGSEL	NPUT9NEGSEL	NPUT6NEGSEL	INPUT4NEGSEL	NPUT2NEGSEL	INPUTONEGSEL
Name					T15N	T13N	T111	N6L	T6NF	N 4TI	IT2NI	NOL.
					INPL	INPL	INPL	INPL	INPL	INPL	INPL	INPL
Bit	Name	Reset	Access	Description	1							
31:16	Reserved	To ensure co	mpatibility v			ways wr	ite bits t	o 0. Mo	re inforn	nation in	1.2 Co	nven-
15:14	INPUT15NEGSEL	0x0	RW	Nogotivo Im	nut Cal	oot Boa	intor fo	r ADCn	INDIIT	15 in Di	fforonti	al .
15.14	INPUTISHEGSEL	UXU	RVV	Negative In Scan Mode		ect Reg	ister 10	r ADCII	_INPUT	וט ווו פּד	nierenu	aı
	Selects negative char	nnel										
	Value	Mode		Description								
	0	INPUT8		Selects AD0	Cn_INP	JT8 as r	negative	channe	el input			
	1	INPUT10		Selects AD0	Cn_INP	JT10 as	negativ	e chanr	nel input			
	2	INPUT12		Selects AD0	Cn_INP	JT12 as	negativ	e chanr	el input			
	3	INPUT14		Selects AD0	Cn_INP	JT14 as	negativ	e chanr	el input			
13:12	INPUT13NEGSEL	0x3	RW	Negative In Scan Mode		ect Reg	ister fo	r ADCn	_INPUT	13 in Di	ifferenti	al
	Selects negative char	nnel										
	Value	Mode		Description								
	0	INPUT8		Selects AD0	Cn_INP	JT8 as r	negative	channe	el input			
	1	INPUT10		Selects AD0	Cn_INP	JT10 as	negativ	e chanr	nel input			
	2	INPUT12		Selects AD0	Cn_INP	JT12 as	negativ	e chanr	nel input			
	3	INPUT14		Selects AD0	Cn_INP	JT14 as	negativ	e chanr	nel input			
11:10	INPUT11NEGSEL	0x2	RW	Negative In Scan Mode		ect Reg	ister fo	r ADCn	_INPUT	11 in Di	ifferenti	al
	Selects negative char	nnel										
	Value	Mode		Description								
	0	INPUT8		Selects AD0	Cn_INP	JT8 as r	negative	channe	el input			
	1	INPUT10		Selects AD0	Cn_INP	JT10 as	negativ	e chanr	nel input			
	2	INPUT12		Selects AD0	Cn_INP	JT12 as	negativ	e chanr	nel input			
	3	INPUT14		Selects AD0	Cn_INP	JT14 as	negativ	e chanr	el input			

Bit	Name	Reset	Access	Description
9:8	INPUT9NEGSEL	0x1	RW	Negative Input Select Register for ADCn_INPUT9 in Differential Scan Mode
	Selects negative cha	annel		
	Value	Mode		Description
	0	INPUT8		Selects ADCn_INPUT8 as negative channel input
	1	INPUT10		Selects ADCn_INPUT10 as negative channel input
	2	INPUT12		Selects ADCn_INPUT12 as negative channel input
	3	INPUT14		Selects ADCn_INPUT14 as negative channel input
7:6	INPUT6NEGSEL	0x3	RW	Negative Input Select Register for ADCn_INPUT1 in Differential Scan Mode
	Selects negative cha	annel		
	Value	Mode		Description
	0	INPUT1		Selects ADCn_INPUT1 as negative channel input
	1	INPUT3		Selects ADCn_INPUT3 as negative channel input
	2	INPUT5		Selects ADCn_INPUT5 as negative channel input
	3	INPUT7		Selects ADCn_INPUT7 as negative channel input
5:4	INPUT4NEGSEL	0x2	RW	Negative Input Select Register for ADCn_INPUT4 in Differential Scan Mode
	Selects negative cha	annel		
	Value	Mode		Description
	0	INPUT1		Selects ADCn_INPUT1 as negative channel input
	1	INPUT3		Selects ADCn_INPUT3 as negative channel input
	2	INPUT5		Selects ADCn_INPUT5 as negative channel input
	3	INPUT7		Selects ADCn_INPUT7 as negative channel input
3:2	INPUT2NEGSEL	0x1	RW	Negative Input Select Register for ADCn_INPUT2 in Differential Scan Mode
	Selects negative cha	annel		
	Value	Mode		Description
	0	INPUT1		Selects ADCn_INPUT1 as negative channel input
	1	INPUT3		Selects ADCn_INPUT3 as negative channel input
	2	INPUT5		Selects ADCn_INPUT5 as negative channel input
	3	INPUT7		Selects ADCn_INPUT7 as negative channel input
	INPUT0NEGSEL	0x0	RW	Negative Input Select Register for ADCn_INPUT0 in Differential
1:0	0101120022			Scan Mode
1:0	Selects negative cha	annel		Scan Mode

0 INPUT1 1 INPUT3	Selects ADCn_INPUT1 as negative channel input
1 INPUT3	
	Selects ADCn_INPUT3 as negative channel input
2 INPUT5	Selects ADCn_INPUT5 as negative channel input
3 INPUT7	Selects ADCn_INPUT7 as negative channel input

26.5.11 ADCn_CMPTHR - Compare Threshold Register

Offset		Bit Pos											osition														
0x02C	331 330 330 330 330 341 351 352 352 352 353 363 363 363 363 363 363 363 363 363											16	2 2 4 8 7 1 1 0 0 8 7 0 0 4 8 7 0 0										0				
Reset		0000x0										0000×0															
Access		≷										\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\															
Name		ADGT																	F	ADE							

Bit	Name	Reset	Access	Description
31:16	ADGT	0x0000	RW	Greater Than Compare Threshold
	Compare threshold	value for greate	r-than comp	arison. Must match the conversion data representation chosen.
15:0	ADLT	0x0000	RW	Less Than Compare Threshold
	Compare threshold	value for less-th	an comparis	son. Must match the conversion data representation chosen.

26.5.12 ADCn_BIASPROG - Bias Programming Register for Various Analog Blocks Used in ADC Operation

Offset			Bit Position													
0x030	30 30 29 28 27 27	20 21 22 23 24 20 20 20 20 20 20 20 20 20 20 20 20 20	0 8 1 9 9 9 10 10 10 10 10 10 10 10 10 10 10 10 10													
Reset			0 0													
Access			N N N N N N N N N N N N N N N N N N N													
Name			GPBIASACC VFAULTCLR ADCBIASPROG													
Bit	Name	Reset Access	s Description													
31:17	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-													
16	GPBIASACC	0 RW	Accuracy Setting for the System Bias During ADC Operation													
		y mode for ADC operation. Inces configure GPBIASAC	For devices with multiple ADCs, the bias will use the high accuracy setting CC to LOWACC.													
	Value	Mode	Description													
	0	HIGHACC	High accuracy setting. Use when configured for an internal VBGR reference source.													
	1	LOWACC	Low accuracy setting. Can be used for all references other than VBGR to conserve energy.													
15:13	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-													
12	VFAULTCLR	0 RW	Clear VREFOF Flag													
			flag. If VREFOF irq is enabled and is triggered, the user must set this bit in eset this bit to enable VREFOF to trigger further IRQs upon VREF overflow													
11:4	Reserved	To ensure compatibility tions	with future devices, always write bits to 0. More information in 1.2 Conven-													
3:0	ADCBIASPROG	0x0 RW	Bias Programming Value of Analog ADC Block													
	These bits are used	to adjust the bias current in	n ADC analog block.													
	Value	Mode	Description													
	0	NORMAL	Normal power (use for 1Msps operation)													
	4	SCALE2	Scaling bias to 1/2													
	8	SCALE4	Scaling bias to 1/4													
	12	SCALE8	Scaling bias to 1/8													
	14	SCALE16	Scaling bias to 1/16													
	15	SCALE32	Scaling bias to 1/32													

26.5.13 ADCn_CAL - Calibration Register

Offset		Bit Position																											
0x034	31	30 30 29 27 27 26 26 26 27 27				23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	-	0
Reset	0	0				7x0				0x8			0	0x40							2	3							
Access	Z N	RW RW				RW					2	Ž	RW	R W								2	2		RW				
Name	CALEN	NGAIN				VIAIT LIGHT ON A CO	SCANOFFUELINV			COANOEEGET	SCANOPIOE		OFFSETINVMODE				SINGLEGAIN					SINICI EDEESETINIV	2 2			SING! EDEESET			

	SC,		SC,	SC,	OF	SIS	N Z	S										
Bit	Name	Reset	Access	s Descriptio	n													
31	CALEN	0	RW	Calibration	Calibration Mode is Enabled													
	When enabled, the a data conversion	dc perform	ns conversion a	and sends raw	data	to the ADC fifos. This can	also be used to o	debug the adc										
30:24	SCANGAIN	0x40	RW	Scan Mode	e Gai	n Calibration Value												
		25 internal	reference durir	ng reset, hence		nversions. This field is set reset value might differ fro												
23:20	SCANOFFSETINV	0x7	RW	Scan Mode Mode	Off	set Calibration Value for	Negative Single	e-ended										
	set to the production	offset calib	oration value fo	r the 1V25 inte	rnal i	conversions for negative si reference during reset, her ement number. Higher valu	nce the reset valu	ue might differ										
19:16	SCANOFFSET	0x8	RW	Scan Mode gle-ended		set Calibration Value for e	Differential or F	Positive Sin-										
	This field is set to the	productio	n offset calibra	tion value for th	ne 1\	onversions for differential /25 internal reference duried 2's complement number	ng reset, hence t	he reset value										
15	OFFSETINVMODE	0	RW	Negative S	ingle	e-ended Offset Calibratio	n is Enabled											
						singled ended conversion sitive single-ended or differ												
14:8	SINGLEGAIN	0x40	RW	Single Mod	de G	ain Calibration Value												
		25 internal	reference durir	ng reset, hence		onversions. This field is se reset value might differ fro												
7:4	SINGLEOFFSETINV	0x7	RW	Single Mod Mode	de O	ffset Calibration Value fo	r Negative Sing	le-ended										
	set to the production	offset calil	oration value fo	or the 1V25 inte	ernal	conversions for negative s	nce the reset val	ue might differ										

from device to device. The field is encoded as a signed 2's complement number. Higher values lead to lower ADC results.

Bit	Name	Reset	Access	Description							
3:0	SINGLEOFFSET	EOFFSET 0x8 RW Single Mode Offset Calibration Value for Differential or Positive Single-ended Mode									
	This field is set to the	production offs	et calibration	e used with single conversions for differential or positive single-ended mode. on value for the 1V25 internal reference during reset, hence the reset value encoded as a signed 2's complement number. Higher values lead to lower							

26.5.14 ADCn_IF - Interrupt Flag Register

Offset															Ві	t Po	ositi	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	2	4	က	2	_	0
Reset		'	0	0	0	0	0	0			'				0	0				'	0	0	0	0		'	'	•		'	0	0
Access			2	2	22	2	2	~							22	2					~	22	2	2							22	<u>~</u>
Name			EM23ERR	PRSTIMEDERR	SCANPEND	SCANEXTPEND	PROGERR	VREFOV							SCANCMP	SINGLECMP					SCANUF	SINGLEUF	SCANOF	SINGLEOF							SCAN	SINGLE

	S P E	S F >		08 18		S III
Bit	Name	Reset	Access	Description		
31:30	Reserved	To ensure tions	compatibility (with future devices, al	ways write bits to 0. More informati	on in 1.2 Conven-
29	EM23ERR	0	R	EM23 Entry Error F	Flag	
	Indicates that an inc	orrect clock wa	as selected as	S ADC_CLK when goi	ng into EM23 resulting in an incorre	ect conversion.
28	PRSTIMEDERR	0	R	PRS Timed Mode B	Error Flag	
	Indicates that in PR	S timed mode,	a PRS negat	ive edge arrived befor	e the AT event and it was ignored.	
27	SCANPEND	0	R	Scan Trigger Pend	ing Flag	
	Indicates that an ex	ternal scan (e.ç	g., LESENSE	triggered) is running a	and PRS/software triggered scan h	as gone pending.
26	SCANEXTPEND	0	R	External Scan Trig	ger Pending Flag	
	Indicates that a PRS ing.	S/software trigg	gered scan is	running and the exter	nal scan (e.g., LESENSE triggered) has gone pend-
25	PROGERR	0	R	Programming Erro	r Interrupt Flag	
	Indicates that a prog	gramming error	has occurred	d. Read the STATUS	register for cause.	
24	VREFOV	0	R	VREF Over Voltage	e Interrupt Flag	
	Indicates that attenuence when this hap				The ADC stops converting and dis	connects the refer-
23:18	Reserved	To ensure tions	compatibility (with future devices, al	ways write bits to 0. More informati	on in 1.2 Conven-
17	SCANCMP	0	R	Scan Result Comp	are Match Interrupt Flag	
	Indicates scan resul	t compare mat	ched the wind	dow conditions when t	his bit is set.	
16	SINGLECMP	0	R	Single Result Com	pare Match Interrupt Flag	
	Indicates single resu	ult compare ma	atched the wir	ndow conditions when	this bit is set.	
15:12	Reserved	To ensure tions	compatibility (with future devices, al	ways write bits to 0. More informati	on in 1.2 Conven-
11	SCANUF	0	R	Scan FIFO Underfl	ow Interrupt Flag	
	Indicates scan resul able.	t FIFO underflo	ow when this	bit is set. An underflov	v occurs if the FIFO is read and the	ere is no data avail-
10	SINGLEUF	0	R	Single FIFO Under	flow Interrupt Flag	
	Indicates single resu available.	ult FIFO underf	flow when this	bit is set. An underflo	ow occurs if the FIFO is read and th	ere is no data

Bit	Name	Reset	Access	Description
9	SCANOF	0	R	Scan FIFO Overflow Interrupt Flag
	Indicates scan re result.	sult FIFO overflo	w when this bi	it is set. An overflow occurs if there is not room in the FIFO to store a new
8	SINGLEOF	0	R	Single FIFO Overflow Interrupt Flag
	Indicates single r result.	esult FIFO overflo	ow when this I	bit is set. An overflow occurs if there is not room in the FIFO to store a new
7:2	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
1	SCAN	0	R	Scan Conversion Complete Interrupt Flag
	Indicates (DVL+1) number of scan	channel resu	ilts are available in the Scan FIFO.
	SINGLE	0	R	Single Conversion Complete Interrupt Flag
0	SINGLE	ū		- J

26.5.15 ADCn_IFS - Interrupt Flag Set Register

26.5.15															·4 P															
Offset										T				В	T	_	tion	T	T		T		T T	T						
0x03C	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	9	ი	∞	7	ဖ	2	4	က	7	~ c
Reset		0	0	0	0	0	0							0	0					0	0	0	0							
Access		Ž	8	×	×	×	×							\ \ \	Ž					X	×	W	×							
Name		EM23ERR	PRSTIMEDERR	SCANPEND	SCANEXTPEND	PROGERR	VREFOV							SCANCMP	SINGLECMP					SCANUF	SINGLEUF	SCANOF	SINGLEOF							
Bit	Name					Re	set			Ac	ces	s	Des	crip	otio	n														
31:30	Resen	∕ed				To tio		ure	con	npat	ibilit	ty w	ith fu	ıture	e de	vice	es, a	lway	'S W	rite l	oits t	o 0.	Мо	re in	forn	natic	on in	1.2	Cor	nven-
29	EM23E	ERR				0				W	1		Set	EM	23E	RR	Inte	rrup	ot FI	ag										
	Write 1	1 to	set t	he E	EM2	3EF	RR ir	nterr	upt	flag																				
28	PRSTI	MEI	DER	R		0				W	1		Set	PRS	STI	MEI	DER	R In	terr	upt	Flag	I								
	Write 1 to set the PRSTIMEDERR interrupt flag SCANPEND 0 W1 Set SCANPEND Interrupt Flag																													
27																														
	Write 1 to set the SCANPEND interrupt flag																													
26	SCAN					0				W			Set	SC	ANE	EXT	PEN	D Ir	iteri	upt	Fla	g								
	Write 1			he S	SCA		KTPI	END) int			ag																		
25	PROG					0	DD :	4		W			Set	PR	OGI	ERF	R Int	erru	pt F	lag										
24	Write 1		set t	ne i	RC		KK I	nter	rup				Cat	VDI		N/ I			- Fi-											
24	VREFO		aat t	·ha \	/DE	0 	/ int	o rri i	∽t fl	W ²	ı		Set	VKI	EFC	ו עכ	nter	rupt	гіа	g										
23:18	Reserv		seri	ne v	/KE		ens		•		ibilit	ty w	ith fu	ıture	e de	vice	es, a	lway	'S W	rite l	oits t	ю О.	Мо	re in	forn	natic	on in	1.2	Cor	nven-
17	SCAN	CME				0	115			W	1		Sot	SC/	۸۸۱	·ME	P Inte	orrii	nt E	lan										
17	Write 1			he S	SCA		MP i	nter	rupt				361	30,	-1140	J V F	mi	511 U	ριι	iay										
16	SINGL	.ECI	MP			0				W	1		Set	SIN	GL	ECI	MP I	nter	rupt	Fla	g									
	Write 1	1 to :	set t	he S	SINC	GLE	СМЕ	o int	erru	ıpt fl	ag																			
15:12	Resen	ved				To tio		ure	con	npat	ibilit	ty w	ith fu	ıture	e de	vice	es, a	lway	s W	rite l	oits t	o 0.	Мо	re in	forn	natic	on in	1.2	Cor	nven-
11	SCAN	UF				0				W	1		Set	sc	ANU	JF I	nter	rupt	Fla	g										
	Write 1	1 to	set t	he S	SCA	NUF	= int	erru	pt fl	ag																				
10	SINGL	EUF	=			0				W	1		Set	SIN	GL	EUF	- Int	erru	pt F	lag										
	Write 1	1 to	set t	he S	SINC	GLE	UF i	nter	rupt	t flag)																			
9	SCAN	OF				0				W	1		Set	SC	ANC	OF I	nter	rupt	: Fla	g										

Write 1 to set the SCANOF interrupt flag

Bit	Name	Reset	Access	Description
8	SINGLEOF	0	W1	Set SINGLEOF Interrupt Flag
	Write 1 to set the	SINGLEOF interr	upt flag	
7:0	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

26.5.16 ADCn_IFC - Interrupt Flag Clear Register

Offset														Bi	t Po	siti	on													
0x040	33	59	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	7	- 0
Reset		0	0	0	0	0	0			•	•	•		0	0			•		0	0	0	0			,	·		•	·
Access		(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1							(R)W1	(R)W1					(R)W1	(R)W1	(R)W1	(R)W1							
Name		EM23ERR	PRSTIMEDERR	SCANPEND	SCANEXTPEND	PROGERR	VREFOV							SCANCMP	SINGLECMP					SCANUF	SINGLEUF	SCANOF	SINGLEOF							
Bit	Name					Re	set			Ac	ces	s I	Des	crip	tion															
31:30	Reserv	red				To tio		ure	con	npat	tibilit	ty wi	th fu	ture	dev	/ices	s, alv	vays	s wri	te b	its t	o 0.	Мо	re in	form	atio	n in	1.2	Con	/en-
29	EM23E	RR				0				(R)W1	(Clea	r El	VI23	ERI	R Int	erru	ıpt F	Flag										
	Write 1 to clear the EM23ERR interrupt flag. Reading returns the value of the IF and clears the corresponding interrupt flags (This feature must be enabled globally in MSC.). PRSTIMEDERR 0 (R)W1 Clear PRSTIMEDERR Interrupt Flag															errup	t													
28	PRSTIMEDERR 0 (R)W1 Clear PRSTIMEDERR Interrupt Flag																													
	PRSTIMEDERR 0 (R)W1 Clear PRSTIMEDERR Interrupt Flag Write 1 to clear the PRSTIMEDERR interrupt flag. Reading returns the value of the IF and clears the corresponding in rupt flags (This feature must be enabled globally in MSC.).															ter-														
27	SCANF	PEN	D			0				(R)W1	(Clea	ır S0	CAN	IPE	ND I	nter	rup	t Fla	ag									
	Write 1 flags (1													g re	turn	s th	e val	lue d	of th	e IF	and	d cle	ars	the	corre	espo	ondii	ng ir	iterru	ıpt
26	SCANE	ΞXΤ	PEN	1D		0				(R)W1	(Clea	ır S0	CAN	IEX.	TPE	ND I	Inte	rrup	ot Fl	ag								
	Write 1 rupt fla															eturr	ns th	e va	lue	of th	ne IF	an an	d cle	ears	the	corr	esp	ondi	ng in	ter-
25	PROG	ERF	₹			0				(R)W1		Clea	r Pi	300	3ER	R In	terr	upt	Fla	g									
	Write 1 flags (1													retu	ırns	the	valu	ie of	f the	IF a	and	clea	ırs tl	ne c	orres	spoi	ndin	g int	errup	ot
24	VREFO	V				0				(R)W1	(Clea	r VI	REF	OV	Inte	rrup	t FI	ag										
	Write 1 (This fe												ng re	eturr	s th	ne va	alue	of th	ne IF	an	d cle	ears	the	cor	resp	ond	ing i	nter	rupt 1	flags
23:18	Reserv	red				To tio		ure	con	npat	tibilit	ty wit	th fu	ture	dev	/ices	s, alv	vays	s wri	te b	its t	0 0.	Moi	re in	form	atio	n in	1.2	Con	/en-
17	SCAN	CMF	•			0				(R)W1		Clea	r S	CAN	ICM	IP In	terr	upt	Fla	g									
	Write 1 flags (1													retu	ırns	the	valu	ie of	the	IF a	and	clea	rs tl	ne c	orres	spor	ndin	g int	errup	ot
16	SINGL	ECN	ЛP			0				(R)W1	(Clea	r SI	NG	LEC	MP	Inte	rrup	ot F	lag									
	Write 1													ng re	eturr	ns th	ne va	alue	of th	ne II	= an	d cl	ears	the	corr	esp	ond	ing i	nterr	upt

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

Reserved

15:12

flags (This feature must be enabled globally in MSC.).

tions

Bit	Name	Reset	Access	Description
11	SCANUF	0	(R)W1	Clear SCANUF Interrupt Flag
	Write 1 to clear the (This feature mus		. •	ding returns the value of the IF and clears the corresponding interrupt flags .
10	SINGLEUF	0	(R)W1	Clear SINGLEUF Interrupt Flag
	Write 1 to clear the flags (This feature			eading returns the value of the IF and clears the corresponding interrupt MSC.).
9	SCANOF	0	(R)W1	Clear SCANOF Interrupt Flag
	Write 1 to clear th (This feature mus			ding returns the value of the IF and clears the corresponding interrupt flags .
8	SINGLEOF	0	(R)W1	Clear SINGLEOF Interrupt Flag
	Write 1 to clear the flags (This feature			eading returns the value of the IF and clears the corresponding interrupt MSC.).
7:0	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-

26.5.17 ADCn_IEN - Interrupt Enable Register

26.5.17	ADCII_II	_ IN -		511 U	pt L	.iiak	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	.og.	0.0.	•																					
Offset														Ві	it Po	osit	ion														
0x044	31	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	1	10	6	8	7	9	5	4	3	2	1	0
Reset		0	0	0	0	0	0						'	0	0		'			0	0	0	0			'	•	•		0	0
Access		Z.	Z.	ZX W	RW	Z.	ZX W							Z.	₩ N					RW	Z.	RW	Z.							RW	W W
Name		EM23ERR	PRSTIMEDERR	SCANPEND	SCANEXTPEND	PROGERR	VREFOV							SCANCMP	SINGLECMP					SCANUF	SINGLEUF	SCANOF	SINGLEOF							SCAN	SINGLE
Bit	Name					Re	set			Ac	ces	s	Des	crip	tio	า															
31:30	Reser	/ed				To tio		ure	con	npati	bilit	y wi	ith fu	ture	de	vice	s, al	way	's WI	ite k	oits t	o 0.	Мо	re in	fori	mati	on in	า 1.2	Col	nvei	7-
29	EM23E	ERR				0				RV	/		EM2	3EF	RR I	Inte	rrup	t Er	nabl	е											
	Enable	dis/	able	the	EM	23E	RR	inte	rrup	ot																					
28	PRSTIMEDERR 0 RW PRSTIMEDERR Interrupt Enable Enable/disable the PRSTIMEDERR interrupt																														
	·																														
27	SCAN	SCANPEND 0 RW SCANPEND Interrupt Enable																													
	·																														
26	SCAN	EXT	PEN	N D		0				RV	/		SCA	NE	XTF	PEN	D In	terr	upt	Ena	ble										
	Enable	/dis	able	the	SC	ANE	EXTI	PEN	ID ir	nterr	upt																				
25	PROG					0				RV	V		PRC	GE	RR	Inte	erru	pt E	nab	le											
	Enable	e/dis	able	the	PR	OGI	ERR	inte	erru	pt																					
24	VREF					0				RV	/		VRE	FO'	V In	ter	rupt	Ena	ble												
	Enable	/dis	able	the	VR																										
23:18	Reser	/ed				To tio		ure	con	npati	bilit	y wi	ith fu	ture	de	vice	es, al	way	'S WI	ite k	oits t	o 0.	Мо	re in	fori	mati	on in	1.2 ו	Col	nvei	1-
17	SCAN	CMF)			0				RV	V		SCA	NC	MP	Inte	erru	pt E	nab	le											
	Enable	dis.	able	the	SC	ANG	CMP	inte	erru	pt																					
16	SINGL					0				RV	V		SIN	GLE	CM	IP li	nteri	upt	Ena	ble											
	Enable		able	the	SIN																										
15:12	Resen	/ed				To tio		ure	con			y wi	ith fu	ture	de	vice	es, al	way	'S WI	ite k	oits t	o 0.	Мо	re in	fori	mati	on in	1.2	Col	nvei	7-
11	SCAN	UF				0				RV	/		SCA	NU	F In	iter	rupt	Ena	able												
	Enable	/dis	able	the	SC	ANU	JF ir	nterr	upt																						
10	SINGL	EUF	=			0				RV	V		SIN	GLE	UF	Inte	erru	pt E	nab	le											

SCANOF

9

Enable/disable the SINGLEUF interrupt

Enable/disable the SCANOF interrupt

0

RW

SCANOF Interrupt Enable

Bit	Name	Reset	Access	Description
8	SINGLEOF	0	RW	SINGLEOF Interrupt Enable
	Enable/disable the	e SINGLEOF inte	rrupt	
7:2	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
1	SCAN	0	RW	SCAN Interrupt Enable
	Enable/disable the	e SCAN interrupt		
0	SINGLE	0	RW	SINGLE Interrupt Enable
	Enable/disable the	e SINGLE interru	pt	

26.5.18 ADCn_SINGLEDATA - Single Conversion Result Data (Actionable Reads)

Offset	Bit Position														
0x048	3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3														
Reset	000000000000000000000000000000000000000														
Access	<u>~</u>														
Name	DATA														

Bit	Name	Reset	Access	Description
31:0	DATA	0x00000000	R	Single Conversion Result Data
	This register holds the	e results from th	e last singl	e channel mode conversion. Reading this field pops one entry from the

26.5.19 ADCn_SCANDATA - Scan Conversion Result Data (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x04C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	ဝ	∞	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	000000000000000000000000000000000000000															
Access																۵	_															
Name																\ \ \	<u>(</u>															

Bit	Name	Reset	Access	Description
31:0	DATA	0x00000000	R	Scan Conversion Result Data
	The register holds the	e results from the	e last scan	mode conversion. Reading this field pops one entry from the SCAN FIFO.

SINGLE FIFO.

26.5.20 ADCn_SINGLEDATAP - Single Conversion Result Data Peek Register

Offset															Bi	t Po	siti	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	00000000000000000000000000000000000000																															
Access																۵	۷															
Name																	-															

Bit	Name	Reset	Access	Description
31:0	DATAP	0x00000000	R	Single Conversion Result Data Peek

The register holds the results from the last single channel mode conversion. Reading this field will not pop an entry from the SINGLE FIFO.

26.5.21 ADCn_SCANDATAP - Scan Sequence Result Data Peek Register

Offset															Bi	t Po	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	7	_	0
Reset																000000000000000000000000000000000000000	nannnnnan															
Access																۵	۲															
Name																	L															

Bit	Name	Reset	Access	Description
31:0	DATAP	0x00000000	R	Scan Conversion Result Data Peek
	The register holds the FIFO.	e results from the	e last scan	mode conversion. Reading this field will not pop an entry from the SCAN

26.5.22 ADCn_SCANDATAX - Scan Sequence Result Data + Data Source Register (Actionable Reads)

Offset	Bit Position													
0x068	30 30 30 30 30 30 30 30 30 4 4 4 4 4 4 5 5 5 6 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7 7													
Reset	00000													
Access	α α													
Name	SCANINPUTID													

Bit	Name	Reset	Access	Description
31:21	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
20:16	SCANINPUTID	0x00	R	Scan Conversion Input ID
	Indicates from which	input the results	in SCAND	ATA originated. Reading this field pops one entry from the SCAN FIFO.
15:0	DATA	0x0000	R	Scan Conversion Result Data
	Holds the results from	n the last scan c	onversion.	Reading this field pops one entry from the SCAN FIFO.

26.5.23 ADCn_SCANDATAXP - Scan Sequence Result Data + Data Source Peek Register

Offset															Bi	t Po	sitio	on														
0x06C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	5	4	က	7	_	0
Reset	Δ α α ο ο ο ο ο ο ο ο ο ο ο ο ο ο ο ο ο																															
Access	α																					۵	צ									
Name														SCANINPUTIDPEEK											DATAP							

Bit	Name	Reset	Access	Description
31:21	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
20:16	SCANINPUTIDPEEK	0x00	R	Scan Conversion Data Source Peek
	Indicates from which in SCAN FIFO.	nput channel the	e results in	SCANDATA originated. Reading this field does not pop any entry from the
15:0	DATAP	0x0000	R	Scan Conversion Result Data Peek
	The register holds the FIFO.	results from the	last scan	conversion. Reading this field does not pop any entry from the SCAN

26.5.24 ADCn_APORTREQ - APORT Request Status Register

Offset															Bi	t Po	siti	on														
0x07C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	7	_	0
Reset		'			'										'								0	0	0	0	0	0	0	0	0	0
Access																							œ	œ	2	œ	œ	22	22	œ	ď	ď
Name																							APORT4YREQ	APORT4XREQ	APORT3YREQ	APORT3XREQ	APORT2YREQ	APORT2XREQ	APORT1YREQ	APORT1XREQ	APORTOYREQ	APORT0XREQ

Bit	Name	Reset	Access	Description
31:10	Reserved	To ensure col	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
9	APORT4YREQ	0	R	1 If the Bus Connected to APORT4Y is Requested
	Reports if the bus co	onnected to APO	RT4Y is be	ing requested from the APORT
8	APORT4XREQ	0	R	1 If the Bus Connected to APORT4X is Requested
	Reports if the bus co	onnected to APO	RT4X is be	ing requested from the APORT
7	APORT3YREQ	0	R	1 If the Bus Connected to APORT3Y is Requested
	Reports if the bus co	onnected to APO	RT3Y is be	ing requested from the APORT
6	APORT3XREQ	0	R	1 If the Bus Connected to APORT3X is Requested
	Reports if the bus co	onnected to APO	RT3X is be	ing requested from the APORT
5	APORT2YREQ	0	R	1 If the Bus Connected to APORT2Y is Requested
	Reports if the bus co	onnected to APO	RT2Y is be	ing requested from the APORT
4	APORT2XREQ	0	R	1 If the Bus Connected to APORT2X is Requested
	Reports if the bus co	onnected to APO	RT2X is be	ing requested from the APORT
3	APORT1YREQ	0	R	1 If the Bus Connected to APORT1Y is Requested
	Reports if the bus co	onnected to APO	RT1Y is be	ing requested from the APORT
2	APORT1XREQ	0	R	1 If the Bus Connected to APORT1X is Requested
	Reports if the bus co	onnected to APO	RT1X is be	ing requested from the APORT
1	APORT0YREQ	0	R	1 If the Bus Connected to APORT0Y is Requested
	Reports if the bus co	onnected to APO	RT0Y is be	ing requested from the APORT
0	APORT0XREQ	0	R	1 If the Bus Connected to APORT0X is Requested
	Reports if the bus co	onnected to APO	RT0X is be	ing requested from the APORT

26.5.25 ADCn_APORTCONFLICT - APORT Conflict Status Register

Offset	Bit Position									
0x080	1 1 <th>6</th> <th>ω </th> <th>7</th> <th>5</th> <th>4</th> <th>3</th> <th>2</th> <th>_</th> <th>0</th>	6	ω	7	5	4	3	2	_	0
Reset		0	0	0	0	0	0	0	0	0
Access		2	ا ک	<u>س</u> س	2	2	R	2	2	<u>~</u>
Name		ORT4YCONFLI	T4XCONFL	APORT3YCONFLICT APORT3XCONFLICT	APORT2YCONFLICT	APORT2XCONFLICT	APORT1YCONFLICT	APORT1XCONFLICT	APORT0YCONFLICT	APORT0XCONFLICT

Bit Name Reset Access Description 31:10 Reserved To ensure compatibility with future devices, always write bits to 0. Minutions 9 APORT4YCONFLICT 0 R 1 If the Bus Connected to APORT4Y is in Peripheral Reports if the bus connected to APORT4Y is is also being requested by another peripheral 8 APORT4XCONFLICT 0 R 1 If the Bus Connected to APORT4X is in Peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral 7 APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is in Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral 8 APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral		
Peripheral Reports if the bus connected to APORT4Y is is also being requested by another peripheral Reports if the bus connected to APORT4Y is is also being requested by another peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is is Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral		
Reports if the bus connected to APORT4Y is is also being requested by another peripheral 8 APORT4XCONFLICT 0 R 1 If the Bus Connected to APORT4X is is Peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral 7 APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is in Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral 6 APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral	in Conflict W	ith Another
8 APORT4XCONFLICT 0 R 1 If the Bus Connected to APORT4X is in Peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral 7 APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is in Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral 6 APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral		
Peripheral Reports if the bus connected to APORT4X is is also being requested by another peripheral APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is in Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral		
7 APORT3YCONFLICT 0 R 1 If the Bus Connected to APORT3Y is in Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral 6 APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral	in Conflict Wi	ith Another
Peripheral Reports if the bus connected to APORT3Y is is also being requested by another peripheral APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral		
6 APORT3XCONFLICT 0 R 1 If the Bus Connected to APORT3X is in Peripheral	in Conflict Wi	ith Another
Peripheral		
	in Conflict Wi	ith Another
Reports if the bus connected to APORT3X is is also being requested by another peripheral		
5 APORT2YCONFLICT 0 R 1 If the Bus Connected to APORT2Y is i Peripheral	in Conflict Wi	ith Another
Reports if the bus connected to APORT2Y is is also being requested by another peripheral		
4 APORT2XCONFLICT 0 R 1 If the Bus Connected to APORT2X is i Peripheral	in Conflict Wi	ith Another
Reports if the bus connected to APORT2X is is also being requested by another peripheral		
3 APORT1YCONFLICT 0 R 1 If the Bus Connected to APORT1Y is in Peripheral	in Conflict Wi	ith Another
Reports if the bus connected to APORT1Y is is also being requested by another peripheral		
2 APORT1XCONFLICT 0 R 1 If the Bus Connected to APORT1X is i Peripheral	in Conflict Wi	ith Another
Reports if the bus connected to APORT1X is is also being requested by another peripheral		
1 APORTOYCONFLICT 0 R 1 If the Bus Connected to APORTOY is in Peripheral		
Reports if the bus connected to APORT0Y is is also being requested by another peripheral	in Conflict Wi	ith Another

Bit	Name	Reset	Access	Description
0	APORT0XCONFLICT	0	R	1 If the Bus Connected to APORT0X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT0X is is a	also being requested by another peripheral

26.5.26 ADCn_SINGLEFIFOCOUNT - Single FIFO Count Register

0x084	Offset															Bi	t Po	siti	on														
Access	0x084	31	33	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	7	_	0
	Reset																															0x0	
Name SINGLEDC	Access																															<u>~</u>	
	Name																															SINGLEDC	

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	SINGLEDC	0x0	R	Single Data Count
	Number of unread da	ta available in S	ingle FIFO	

26.5.27 ADCn_SCANFIFOCOUNT - Scan FIFO Count Register

Offset															Bi	t Po	siti	on														
0x088	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	ဝ	8	7	9	5	4	က	2	1	0
Reset															•		•			•											0×0	
Access																															<u>~</u>	
Name																															SCANDC	

Bit	Name	Reset	Access	Description
31:3	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
2:0	SCANDC	0x0	R	Scan Data Count
	Number of unread	d data available i	in Scan FIFO.	

26.5.28 ADCn_SINGLEFIFOCLEAR - Single FIFO Clear Register

Offset															Ві	it Po	siti	on														
0x08C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	ω	7	9	5	4	t ო	2	_	0
Reset				•																	•		•						·			0
Access																																W
Name																																SINGLEFIFOCLEAR

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	SINGLEFIFOCLEAR	0	W1	Clear Single FIFO Content
	Write a 1 to clear Sing	le FIFO conten	t.	

26.5.29 ADCn_SCANFIFOCLEAR - Scan FIFO Clear Register

Offset															Bi	t Po	siti	on														
0x090	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset			•			•		•				•											•	•		•	•			•		0
Access																																W
Name																																SCANFIFOCLEAR

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure co	mpatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
0	SCANFIFOCLEAR	0	W1	Clear Scan FIFO Content
	Write a 1 to clear Sca	an FIFO conten	t.	

26.5.30 ADCn_APORTMASTERDIS - APORT Bus Master Disable Register

Offset				Bit Position	
0x094	31 30 29 27 27 26	25 24 23 23	22 23 5	2 3 4 5 6 6 7 8 8 9 10 11 12 13 14 15 15 15 15 15 15 15 15 15 15 15 15 15	
Reset				0000000	
Access				M M M M M M M M M M M M M M M M M M M	
Name				APORT4YMASTERDIS APORT3YMASTERDIS APORT3YMASTERDIS APORT3YMASTERDIS APORT2YMASTERDIS APORT2YMASTERDIS APORT2YMASTERDIS APORT2YMASTERDIS APORT1YMASTERDIS APORT1YMASTERDIS	
Bit	Name	Reset	Access	Description	
31:10	Reserved	To ensure	compatibility (with future devices, always write bits to 0. More information in 1.2 Con	ven-
•		tions			
	APORT4YMASTER- DIS		RW	APORT4Y Master Disable	
	APORT4YMASTER- DIS Determines if the ADO ADC only passively m	0 C will reques onitors the Ane device that	st this APORT APORT bus ar at masters the	APORT4Y Master Disable bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). Who defend the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored.	anne
	APORT4YMASTER- DIS Determines if the ADO ADC only passively m selection is done by the	0 C will reques onitors the Ane device that	st this APORT APORT bus ar at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). Who did the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored.	anne
9	APORT4YMASTER- DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus	0 C will reques onitors the Ane device that	st this APORT APORT bus ar at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored.	anne
	APORT4YMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus Value	0 C will reques onitors the Ane device that	st this APORT APORT bus ar at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored.	anne
9	APORT4YMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus Value 0	0 C will reques onitors the Ane device that simultaneous	st this APORT APORT bus ar at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored bus in the channel for the selected bus is ignored. The channel for the selected bus is ignored bus in the channel for the selected bus is ignored. The channel for the selected bus is ignored bus in the channel for the selected bus is ignored bus in the selected bus is ignored bus in the selected bus is ignored bus in the selected bus is ignored bus in the selected bus is ignored bus in the selected bus is ignored bus in the selected bus is ignored bus in the selected bus in the selected bus is ignored bus in the selected bus in the selected bus in the selected bus is ignored bus in the selected bus in the select	anne
9	APORT4YMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus Value 0 1 APORT4XMASTER-DIS Determines if the ADO ADC only passively m	0 C will request onitors the Anne device that simultaneous onitors the Anne device that onitors the Anne device that one device the device that one device the dev	st this APORT APORT bus are at masters the usly. RW St this APORT APORT bus are at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). Who do the selection of the channel for the selected bus is ignored. The channel for the channel for the selected bus is ignored. The channel for the channel for the selected bus is ignored. The channel for the	en 1
9	APORT4YMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus Value 0 1 APORT4XMASTER-DIS Determines if the ADO ADC only passively m selection is done by the selection is done	0 C will request onitors the Anne device that simultaneous onitors the Anne device that onitors the Anne device that one device the device that one device the dev	st this APORT APORT bus are at masters the usly. RW St this APORT APORT bus are at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). Who do the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected bus is ignored.	en 1
	APORT4YMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus Value 0 1 APORT4XMASTER-DIS Determines if the ADO ADC only passively m selection is done by the same APORT bus	0 C will request onitors the Anne device that simultaneous onitors the Anne device that onitors the Anne device that one device the device that one device the dev	st this APORT APORT bus are at masters the usly. RW St this APORT APORT bus are at masters the	bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). Who do the selection of the channel for the selected bus is ignored. The channel for the selected bus is ignored. The channel for the selected devices to more devices. This bit allows multiple APORT connected devices to more devices. The channel for the selected bus is ignored. The channel for the selected devices to more devices. This bit allows multiple APORT connected devices to more devices.	en 1,

Determines if the ADC will request this APORT bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, ADC only passively monitors the APORT bus and the selection of the channel for the selected bus is ignored. The channel selection is done by the device that masters the APORT bus. This bit allows multiple APORT connected devices to monitor the same APORT bus simultaneously.

APORT3Y Master Disable

RW

Value	Description
0	APORT mastering enabled
1	APORT mastering disabled

APORT3YMASTER- 0

DIS


7

Bit	Name	Reset	Access	Description
6	APORT3XMASTER- DIS	0	RW	APORT3X Master Disable
	ADC only passively n	nonitors the AP0 he device that n	ORT bus ar	Γ bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, and the selection of the channel for the selected bus is ignored. The channel APORT bus. This bit allows multiple APORT connected devices to monitor
	Value			Description
	0			APORT mastering enabled
	1			APORT mastering disabled
5	APORT2YMASTER- DIS	0	RW	APORT2Y Master Disable
	ADC only passively n	nonitors the AP0 he device that n	ORT bus ar	T bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, and the selection of the channel for the selected bus is ignored. The channel APORT bus. This bit allows multiple APORT connected devices to monitor
	Value			Description
	0			APORT mastering enabled
	1			APORT mastering disabled
4	APORT2XMASTER- DIS	0	RW	APORT2X Master Disable
	ADC only passively n	nonitors the AP0 he device that n	ORT bus ar nasters the	Γ bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, and the selection of the channel for the selected bus is ignored. The channel APORT bus. This bit allows multiple APORT connected devices to monitor
	Value			Description
	0			APORT mastering enabled
	1			APORT mastering disabled
3	APORT1YMASTER- DIS	0	RW	APORT1Y Master Disable
	ADC only passively n	nonitors the AP0 he device that n	ORT bus ar	T bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, and the selection of the channel for the selected bus is ignored. The channel APORT bus. This bit allows multiple APORT connected devices to monitor
	Value			Description
	0			APORT mastering enabled
	1			APORT mastering disabled
2	APORT1XMASTER- DIS	0	RW	APORT1X Master Disable
	ADC only passively n	nonitors the AP0 he device that n	ORT bus ar	T bus (if selected by POSSEL or NEGSEL or SCANINPUTSEL). When 1, and the selection of the channel for the selected bus is ignored. The channel APORT bus. This bit allows multiple APORT connected devices to monitor
	Value			Description

Bit	Name	Reset Access Description
	0	APORT mastering enabled
	1	APORT mastering disabled
1:0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions

27. IDAC - Current Digital to Analog Converter





Quick Facts

What?

The IDAC can sink or source a configurable constant current.

Why?

The IDAC can be used to bias external circuits or (in conjunction with the ADC) measure capacitance by injecting a controlled current into a component.

How?

In addition to providing a constant current, the IDAC can be switched on and off with a PRS signal all the way down to EM3.

27.1 Introduction

The current digital to analog converter (IDAC) can source or sink a configurable constant current from APORT and/or main pad (OUT-PAD). The current is configurable with several ranges of various step sizes.

27.2 Features

- · Can source and sink current
- · Programmable constant output current
 - Selectable current range between 0.05 μA and 64 μA
 - Each range is linearly programmable in 32 steps
 - · Support for current calibration
- Support for manual and PRS triggered output enable
- Available in EM0-EM3

27.3 Functional Description

An overview of the IDAC module is shown in Figure 27.1 IDAC Overview on page 919. The IDAC is designed to source or sink a programmable current which can be controlled by setting the range and the step in the RANGESEL and STEPSEL bitfields in IDAC_CURRPROG register. The IDAC output enable can be controlled by software or PRS. The IDAC is enabled by setting EN in IDAC_CTRL.




Figure 27.1. IDAC Overview

27.3.1 Current Programming

The four different current ranges can be selected by configuring the RANGESEL bitfield in IDAC_CURRPROG. The current output in each range is linearly programmable in 32 steps, and is controlled by the STEPSEL bitfield in IDAC_CURRPROG. These current ranges and their step sizes are shown in Table 27.1 Range Selection on page 919.

Range Select Range Value [µA] Step Size [nA] **Step Counts** 0 0.05 - 1.650 32 1 1.6 - 4.7100 32 2 0.5 - 16500 32 3 2 - 64 2000 32

Table 27.1. Range Selection

27.3.2 IDAC Enable and Warm-up

The IDAC is enabled by setting the EN bit in IDAC_CTRL. When this bit is set, the IDAC must stabilize before its output current is stable.

It is important to wait until the IDAC is warmed up, or until any current programming is complete and the output current is stabilized, before entering EM1, EM2, or EM3.

27.3.3 Output Control

The IDAC output enable is controlled separately for APORT and main pad. If APORTOUTENPRS/MAINOUTENPRS is set, output enable is controlled by PRS, else it is controlled by software via APORTOUTEN/MAINOUTEN.

27.3.4 APORT Configuration

The IDAC APORT outputs can be routed to pins through the APORT system. Note that the IDAC has only two local APORT interfaces APORT1X and APORT1Y, which are connected to the APORT BUSCX and BUSCY, respectively. The pins are selected by requesting an APORT channel in APORTOUTSEL in IDAC_CTRL. For mapping between APORT channel and physical pin, please refer to data sheet. The IDAC can be in either master or slave mode when connecting to the APORT. By default the IDAC is in master mode. To enable slave mode, set APORTMASTERDIS in IDAC_CTRL. As IDAC is only capable of driving an APORT channel, only master mode is meaningful for IDAC. If the IDAC is in master mode, and another module is currently driving the requested channel, the APORTCONFLICT bitfield in IDAC_STATUS will be set together with APORT1XCONFLICT or APORT1YCONFLICT in IDAC_APORTCONFLICT. The APORTCONFLICT can also be configured to trigger an interrupt, see 27.3.5 Interrupts for details.

27.3.5 Interrupts

The APORTCONFLICT interrupt flag in the IDAC_IF register indicates that a conflict has occurred when requesting a channel from the APORT. The APORTCONFLICT interrupt can be enabled by setting the APORTCONFLICT bit in IDAC_IEN, or cleared by setting the APORTCONFLICT bit in IDAC_IFC.

27.3.6 Minimizing Output Transition

If the internal output of the IDAC differs from the voltage at the output pin, enabling the output can cause an unwanted transition. To minimize this transition, it is possible to charge or discharge the internal output node before enabling the output to the pin. Setting MINOUTTRANS in IDAC_CTRL when the IDAC is sourcing current connects the internal node to GND. Alternatively, setting MINOUTTRANS when the IDAC is sinking current connects the internal output node to VDD. Setting APORTOUTEN/MAINOUTEN when MINOUTTRANS is set will halt the charge/discharge until either APORTOUTEN/MAINOUTEN is cleared or MINOUTTRANS is cleared.

27.3.7 Duty Cycle Configuration

The references for the IDAC can be duty-cycled, meaning that it can source current at very low overhead current consumption at the cost of response time and accuracy. By default duty-cycling is enabled in EM2 and EM3 and disabled in EM0 and EM1. Setting EM2DUTYCYCLEDIS in IDAC_DUTYCONFIG will disable duty cycling in EM2 and EM3. Note that sinking current can not be done with duty-cycled references so measures needs to be taken to always disable duty-cycling while sinking current.

27.3.8 Calibration

The IDAC can be calibrated to accurately compensate for process, supply voltage and temperature variations. During the production test, the middle step of each range is calibrated at room temperature. The TUNING bitfield in the IDAC_CAL register can be used to do further calibration of each step with an external resistor connected to IDAC_OUT. The calibrated tuning value for each band can be read from the Device Information (DI) page.

27.3.9 PRS Triggered Charge Injection

The amount of charge sourced or sunk by the IDAC can be controlled by the PRS (e.g., using a timer as producer) via the output switch. Figure 27.2 IDAC Charge Injection Example on page 921 shows a case where the IDAC is configured to periodically supply charge using the PRS. The amount of charge injected is proportional to the the period the IDAC is on. The total charge injected is the current multiplied by the time the output switch is enabled.

The PRS system is enabled by setting APORTOUTENPRS/MAINOUTENPRS in IDAC_CTRL, and the PRS channel is selected by PRSSEL in IDAC_CTRL. To generate the periodic control signal, the TIMER module can be used, by configuring for example a CC channel to compare match with a configurable level.




Figure 27.2. IDAC Charge Injection Example

27.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	IDAC_CTRL	RW	Control Register
0x004	IDAC_CURPROG	RW	Current Programming Register
0x00C	IDAC_DUTYCONFIG	RW	Duty Cycle Configuration Register
0x018	IDAC_STATUS	R	Status Register
0x020	IDAC_IF	R	Interrupt Flag Register
0x024	IDAC_IFS	W1	Interrupt Flag Set Register
0x028	IDAC_IFC	(R)W1	Interrupt Flag Clear Register
0x02C	IDAC_IEN	RW	Interrupt Enable Register
0x034	IDAC_APORTREQ	R	APORT Request Status Register
0x038	IDAC_APORTCONFLICT	R	APORT Request Status Register

27.5 Register Description

27.5.1 IDAC_CTRL - Control Register

Offset													В	it Po	siti	on														
0x000	30 30	7 78	72	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	11	10	6	8	7	9	2	4	က	2	_	-
Reset								() X	1	0	0		0		0	0	0				, c	noxo	-	1	1	0	0	0	_
Access								:	 } Ƴ		¥ M	¥ M		\$		¥ M	ZW W	¥ X					- } Y				\ N N	ZW W	8	×
									<u>-</u>							-														
Name								i () ()	PRSSEL		MAINOUTENPRS	MAINOUTEN		APORTOUTENPRS		APORTMASTERDIS	EM2DELAY	PWRSEL					APORIOUISEL				APORTOUTEN	MINOUTTRANS	CURSINK	NH
Bit	Name				Res	set			Ac	ces	s	Des	crip	tion																
31:24	Reserved				To tion		ure	con								s, al	way	s wi	ite b	its t	o 0.	Мо	re ir	nfori	mati	on ii	າ 1.2	? Co	nve	า-
23:20	PRSSEL				0x0)			RV	V		IDA	СО	utpı	ıt E	nab	le P	RS	Cha	nne	l Se	elec	t							
	Selects whi	ich Pl	RS	cha	anne	el to	use	to	enal	ole c	utp	ut.																		
	Value				Mo	de						Des	crip	tion																_
	0				PR	Mode Description PRSCH0 PRS Channel 0 selected. PRSCH1 PRS Channel 1 selected.																								
	1				PR:	SCH	11																							
	2				PR:	SCH	12					PRS Channel 2 selected. PRS Channel 3 selected.																		
	3				PR	SCH	13					PRS	S Ch	ann	el 3	sele	ecte	d.												
	4				PR	SCH	14					PRS	S Ch	ann	el 4	sele	ecte	d.												
	5				PR	SCH	15					PRS	S Ch	ann	el 5	sele	ecte	d.												
	6				PR:	SCH	16					PRS	S Ch	ann	el 6	sele	ecte	d.												
	7				PR:	SCH	17					PRS	S Ch	ann	el 7	sele	ecte	d.												
	8				PR	SCH	18					PRS	S Ch	ann	el 8	sele	ecte	d.												
	9				PR	SCH	19					PRS	S Ch	ann	el 9	sele	ecte	d.												
	10				PR:	SCH	110					PRS	S Ch	ann	el 10) se	lect	ed.												
	11				PR	SCH	111					PRS	S Ch	ann	el 1	1 se	lect	ed.												_
19	MAINOUTE			ol of	0 IDA	C N	1ain	Pa	RV d ou					ontro	olled	d Ma	ain F	Pad	Out	put	Ena	able	l							
	Value											Des	crip	tion																_
	0														ıtput	ena	able	cor	trolle	ed b	y IE	AC	_M/	AIN	TUC	EN.				_
	1											Maiı	n pa	d ou	ıtput	ena	able	con	trolle	ed b	уΡ	RS	inpu	ıt se	elect	ed b	y Pl	RSS	EL.	_
18	MAINOUTE	ΞN			0				RV	V		Out	put	Ena	ble															
	Set to enab	ole ID	AC	ma	ain o	utpu	ıt to	ра	d if N	IΑN	NOL	JTEI	NPR	RS is	not	set														

Bit	Name	Reset	Access	Description
17	Reserved			with future devices, always write bits to 0. More information in 1.2 Conven-
16	APORTOUTENPRS		RW	PRS Controlled APORT Output Enable
	Enable PRS Control	of the IDAC AF		·
	Value			Description
	0			APORT output enable controlled by IDAC_APORTOUTEN.
	1			APORT output enable controlled by PRS channel selected by PRSSEL.
15	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
14	APORTMASTERDIS	S 0	RW	APORT Bus Master Disable
	ted devices to monit the determination is	or the same AP expected to be for a selected l	ORT bus sire from anoth	bus selected by APORTOUTSEL. This bit allows multiple APORT connec- multaneously by allowing the IDAC to not master the selected bus. When 1, her peripheral, and the IDAC only passively looks at the bus. When 1, the ed (the bus is not), and will be whatever selection the external device mas- is.
	Value			Description
	0			Bus mastering enabled
	1			Bus mastering disabled
13	EM2DELAY	0	RW	EM2 Delay
	Delays EM2 entry ur	ntil the IDAC ou	tput is stable	e
12	PWRSEL	0	RW	Power Select
	Selects the power so	ource for the ID	AC	
	Mode	Value		Description
	ANA	0		VDDX_ANA
	Ю	1		IOVDD
11:4	APORTOUTSEL	0x00	RW	APORT Output Select
	Select output mode.			·
	APORT1XCH0	0x20		APORT1X Channel 0
	APORT1YCH1	0x21		APORT1Y Channel 1
	APORT1XCH2	0x22		APORT1X Channel 2
	APORT1YCH3	0x23		APORT1Y Channel 3
	APORT1XCH4	0x24		APORT1X Channel 4
	APORT1YCH5	0x25		APORT1Y Channel 5
				ADDDT/// 01
	APORT1XCH30	0x3e		APORT1X Channel 30

Bit	Name	Reset	Access	Description
3	APORTOUTEN	0	RW	APORT Output Enable
	Set to enable the IDA	AC output to APO	ORT if APC	RTOUTENPRS is not set.
2	MINOUTTRANS	0	RW	Minimum Output Transition Enable
	Set to enable minimu	ım output transit	ion mode fo	or the IDAC.
1	CURSINK	0	RW	Current Sink Enable
	Set to enable the IDA	AC as a current	sink. By def	ault, the IDAC sources current.
0	EN	0	RW	Current DAC Enable
	Set to enable the IDA	AC.		

27.5.2 IDAC_CURPROG - Current Programming Register

Offset															Bi	t Pc	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	-	0
Reset		•				•			0x9B									00×0									•		•		0×0	
Access									N N													Ŋ.									§ S	:
Name													9									STEPSEL									RANGESEL	7

Bit	Name	Reset	Access	Description
31:24	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
23:16	TUNING	0x9B	RW	Tune the Current to Given Accuracy
	In production test	. the middle step (16) of each r	ange is calibrated and can be read from the Device Information (DI) page.
15:13	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	STEPSEL	0x00	RW	Current Step Size Select
	•	•		ach step depends on the RANGESEL setting. RANGESEL settings of 0, 1, nA, 500 nA, and 2000 nA, respectively. See step details.
7:2	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	RANGESEL	0x0	RW	Current Range Select
	Selects current ra	nge of the output.		
	Value			Description .
	value	Mode		Description
	0	Mode RANGE0		Current range set to 0 - 1.6 uA.
				·
	0	RANGE0		Current range set to 0 - 1.6 uA.

27.5.3 IDAC_DUTYCONFIG - Duty Cycle Configuration Register

Offset	Bit Position	
0x00C	33 34 4 5 6 6 6 7 7 8 8 10	- 0
Reset		0
Access		RW
Name		EM2DUTYCYCLEDIS

Bit	Name	Reset	Access	Description						
31:2	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-						
1	EM2DUTYCYCLE- DIS	0	RW	Duty Cycle Enable						
	Set to disable duty cy	cycling in EM2.								
0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions								

27.5.4 IDAC_STATUS - Status Register

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset		•	•	•		•	•	•		•	•	•		•		•	•	•	•		•		•	•	•	•	•		•	•	0	
Access																															22	
Name																															APORTCONFLICT	

Bit	Name	Reset	Access	Description						
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-						
1	APORTCONFLICT	0	R APORT Conflict Output							
	1 if any of the APORT	BUSes being re	equested b	by the IDAC are also being requested by another peripheral						
0	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions								

27.5.5 IDAC_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	2	_	0
Reset			'	•							•					'											'			1	0	
Access																															22	
Name																															APORTCONFLICT	

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	APORTCONFLICT	0	R	APORT Conflict Interrupt Flag
	1 if any of the APORT	BUSes being r	equested b	by the IDAC are also being requested by another peripheral
0	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

27.5.6 IDAC_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset		•				•		•		•		•	•				•		•	•	•	•			•		•				0	
Access																															W1	
Name																															APORTCONFLICT	

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	APORTCONFLICT	0	W1	Set APORTCONFLICT Interrupt Flag
	Write 1 to set the APC	ORTCONFLICT	interrupt fla	ag
0	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

27.5.7 IDAC_IFC - Interrupt Flag Clear Register

Offset															Bi	it Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset			•				•				•			•		•		•										•	•		0	
Access																															(R)W1	
Name																															APORTCONFLICT	

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	APORTCONFLICT	0	(R)W1	Clear APORTCONFLICT Interrupt Flag
	Write 1 to clear the AF rupt flags (This feature		•	flag. Reading returns the value of the IF and clears the corresponding interin MSC.).
0	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

27.5.8 IDAC_IEN - Interrupt Enable Register

Offset	Bit Position	
0x02C	2 3 4 4 5 6 6 7 8 8 8 9 10 11 12 13 14 15 16 16 17 18 18 18 18 18 18 18 18 18 18 18 18 18	- 0
Reset		0
Access		Z.
Name		APORTCONFLICT

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	APORTCONFLICT	0	RW	APORTCONFLICT Interrupt Enable
	Enable/disable the AF	PORTCONFLICT	「interrupt	
0	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

27.5.9 IDAC_APORTREQ - APORT Request Status Register

Offset															Bi	t Po	siti	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset											•		•	•						•			•					•	0	0		
Access																													22	Я		
Name																													APORT1YREQ	APORT1XREQ		

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure cortions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3	APORT1YREQ	0	R	1 If the Bus Connected to APORT1Y is Requested
	Reports if the bus cor	nnected to APOF	RT1Y is be	ing requested by the APORT
2	APORT1XREQ	0	R	1 If the APORT Bus Connected to APORT1X is Requested
	Reports if the bus cor	nnected to APOF	RT1X is be	ing requested by the APORT
1:0	Reserved	To ensure cortions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-


27.5.10 IDAC_APORTCONFLICT - APORT Request Status Register

Offset	Bit Position	
0x038	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	- 0
Reset	0 0	
Access		
Name	APORT1YCONFLICT APORT1XCONFLICT	

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	APORT1YCONFLICT	0	R	1 If the Bus Connected to APORT1Y is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1Y is is	also being requested by another peripheral
2	APORT1XCONFLICT	0	R	1 If the Bus Connected to APORT1X is in Conflict With Another Peripheral
	Reports if the bus con	nected to APOF	RT1X is is	also being requested by another peripheral
1:0	Reserved	To ensure cortions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

28. LESENSE - Low Energy Sensor Interface





Quick Facts

What?

LESENSE is a low energy sensor interface capable of autonomously collecting and processing data from multiple sensors even when in EM2. Flexible configuration makes LESENSE a versatile sensor interface compatible with a wide range of sensors and measurement schemes.

Why?

Capability to autonomously monitor sensors allows the EFR32 to reside in a low energy mode for long periods of time while keeping track of sensor status and sensor events.

How?

LESENSE is highly configurable and is capable of collecting data from a wide range of sensor types. Once the data is collected, the programmable state machine, LESENSE decoder, is capable of processing sensor data without CPU intervention. A large result buffer allows the chip to remain in EM2 for long periods of time while autonomously collecting data.

28.1 Introduction

LESENSE is a low energy sensor interface utilizing on-chip peripherals to perform measurement of a configurable set of sensors. The sensor measurements results can be processed by the LESENSE decoder, a configurable state machine with up to 32 states. The results can also be stored in a result buffer to be collected by the CPU or DMA for further processing.

LESENSE operates from EM0 down to EM2, and can wake up the CPU on configurable events.

28.2 Features

- · Up to 16 sensors
- Autonomous sensor monitoring in EM0, EM1, and EM2
- · Highly configurable decoding of sensor results
- · Interrupt on sensor events
- · Configurable enable signals to external sensors
- · Circular buffer for storage of up to 16 sensor results
- · Multiple evaluation modes minimize the need for software interaction
- · Supports ADC0 sampling and evaluation
- · Support for multiple sensor types
 - · LC sensors
 - · Capacitive sensing
 - · General analog sensors

28.3 Functional Description

The LESENSE module is capable of controlling on-chip peripherals in order to perform monitoring of different sensors with little or no CPU intervention. LESENSE uses the analog comparators (ACMP) or ADC0 for measurement of sensor signals. LESENSE can also control the VDAC to generate accurate reference voltages. Figure 28.1 LESENSE Block Diagram on page 930 shows an overview of the LESENSE module.

The LESENSE module consists of a sequencer, an evaluation block, a decoder, and a RAM block:

- The sequencer handles interaction with other peripherals and controls timing of sensor measurements. It also includes a counter that can be used to count pulses on the ACMP output.
- The evaluation block is used to process the data collected by the sequencer.
- To autonomously analyze sensor results, the LESENSE decoder provides the ability to define a finite state machine with up to 32 states, as well as define programmable actions upon state transitions. This allows the decoder to implement a wide range of decoding schemes, such as quadrature decoding.
- A RAM block is used for storage of configuration and measurement results. This allows LESENSE to have a relatively large result buffer enabling the chip to remain in a low energy mode for long periods of time while collecting sensor data.




Figure 28.1. LESENSE Block Diagram

28.3.1 Channel Configuration

LESENSE has 16 individually configurable channels, each with its own set of configuration registers. Channel configuration is split into three registers; CHx_TIMING, CHx_INTERACT, and CHx_EVAL. Individual timing for each sensor is configured in CHx_INTERACT, and configurations regarding evaluation of the measurements are done in CHx_EVAL. For improved readability, CHx_CONF will be used to refer to the channel configuration registers (CHx_TIMING, CHx_INTERACT, and CHx_EVAL) throughout this chapter.

By default, the channel configuration registers are directly mapped to the channel number. Configuring SCANCONF in CTRL makes it possible to alter this mapping.

Configuring SCANCONF to INVMAP will make channels 0-7 use the channel configuration registers for channels 8-15, and vice versa. This feature allows an application to quickly and easily switch the configuration set for the channels.

Setting SCANCONF to TOGGLE will make channel x alternate between using CH_{X-S} CONF and CH_{X+8} CONF. The configuration used is decided by the state of the corresponding bit in SCANRES. For instance, if channel 3 is performing a scan and bit 3 in SCANRES is set, CH_{11} CONF will be used. Channels 8 through 15 will toggle between CH_{X-S} CONF and CH_{X-8} CONF. This mode provides an easy way to implement hysteresis on channel events, as threshold values can be changed depending on the sensor status.

Setting SCANCONF to DECDEF will make the state of the decoder define which scan configuration to be used. If the decoder state is at index 16 or higher, channel x will use CH_{X+8} _CONF, otherwise it will use CH_{X} _CONF. Similarly, channels 8 through 15 will use CH_{X} _CONF when the decoder state index is less than 8 and CH_{X-8} _CONF when the decoder state index is higher than 7. Allowing the decoder state to define which configuration to use enables easy implementation of hysteresis, for example, as different threshold values can be used for the same channel depending on the state of the application. Table 28.1 LESENSE Scan Configuration Selection on page 931 summarizes how channel configuration is selected for different settings of SCANCONF.

SCANCONF LESENSE TOGGLE DECDEF channel x DIRMAP INVMAP SCANRES[n] = 0SCANRES[n] = 1DECSTATE < 16 DECSTATE >= 16 $0 \le x \le 8$ CH_x_CONF CH_{x+8}_CONF CH_x_CONF CH_{x+8}_CONF CH_x_CONF CH_{x+8}_CONF $8 \le x \le 16$ CH_x CONF CH_{x-8}_CONF CH_x CONF CH_{x-8}_CONF CH_x CONF CH_{x-8}_CONF

Table 28.1. LESENSE Scan Configuration Selection

Channels are enabled in the CHEN register, where bit x enables channel x. During a scan, all enabled channels are measured, starting with the lowest indexed channel. Figure 28.3 Scan Sequence on page 932 illustrates a scan sequence with channels 3, 5, and 9 enabled.

28.3.2 Scan Sequence

LESENSE runs on LFACLK_{LESENSE}, which is a prescaled version of LFACLK. The prescaling factor for LFACLK_{LESENSE} is selected in the CMU, available prescaling factors are:

- DIV1: LFACLK_{LESENSE} = LFACLK/1
- DIV2: LFACLK_{LESENSE} = LFACLK/2
- DIV4: LFACLK_{LESENSE} = LFACLK/4
- DIV8: LFACLK_{I ESENSE} = LFACLK/8

All enabled channels are scanned each scan period. How a new scan is started is configured in the SCANMODE bit field in CTRL. If set to PERIODIC, the scan frequency is generated using a counter which is clocked by LFACLK_{LESENSE}. This counter has its own prescaler. This prescaling factor is configured in PCPRESC in TIMCTRL. A new scan sequence is started each time the counter reaches the top value, PCTOP. The scan frequency is calculated using Figure 28.2 Scan Frequency on page 932. If SCANMODE is set to ONE-SHOT, a single scan will be made when START in CMD is set. To start a new scan on a PRS event, set SCANMODE to PRS and configure PRS channel in PRSSEL. The PRS start signal needs to be active for at least one LFACLK_{LESENSE} cycle to make sure LE-SENSE is able to register it.

Figure 28.2. Scan Frequency

It is possible to interleave additional sensor measurements in between the periodic scans. Issuing a start command when LESENSE is idle will immediately start a new scan, without disrupting the frequency of the periodic scans. If the period counter overflows during the interleaved scan, the periodically scheduled scan will start immediately after the interleaved scan completes.




Figure 28.3. Scan Sequence

28.3.3 Sensor Timing

For each channel in the scan sequence, the LESENSE interface goes through three phases: idle, excite, and measure. The durations of the excite and measure phases are configured in the CHx_TIMING registers. The excite phase duration can be configured to be either a number of AUXHFRCO cycles or a number of LFACLK_{LESENSE} cycles, depending on which one is selected by the EXCLK bit in the CHx_INTERACT register. LESENSE includes two timers: A low frequency timer, running on LFACLK_{LESENSE}, and a high frequency timer, running on AUXHFRCO. The low frequency or high frequency timers can be prescaled by configuring LFPRESC or AUXPRESC, respectively, in the TIMCTRL register. The duration of the measure phase is programmed via MEASUREDLY and SAMPLEDLY in the CHx_TIMING registers. The output of the ACMP will be ignored for MEASUREDLY EXCLK cycles after start of the sensor measurement. Sampling of the sensor will happen after SAMPLEDLY LFACLK_{LESENSE}, or AUXHFRCO cycles, depending on the configuration of the SAMPLECLK in the CHx_INTERACT register. The configurable measure- and sample delays enables LESENSE to easily define exact time windows for sensor measurements. A start delay can be inserted before sensor measurement begin by configuring STARTDLY in TIMCTRL. This delay can be used to ensure that the VDAC conversion is done and voltages have stabilized before the sensor measurement begins. The AUXHFRCO startup can be delayed until the system enters the excite phase, by configuring AUX-STARTUP in TIMCTRL to ONDEMAND. This will reduce the time the AUXHFRCO is enabled and reduce power consumption, with the tradeoff that that the starting point for high frequency timing will also be delayed the same amount as the AUXHFRCO startup time.

Figure 28.4 Timing Diagram, AUXHFRCO Based Timing on page 933 depicts a sensor sequence with AUXHFRCO based timing (EXTIME=5, MEASUREDLY=7, SAMPLEDLY=13), while Figure 28.5 Timing Diagram, LFACLK Based Timing on page 934 depicts a sequence with LFACLK_{LESENSE} based timing (EXTIME=1, MEASUREDLY=1, SAMPLEDLY=2).




Figure 28.4. Timing Diagram, AUXHFRCO Based Timing




Figure 28.5. Timing Diagram, LFACLK Based Timing

28.3.4 Sensor Interaction

Many sensor types require some type of excitation in order to work. The LESENSE module can generate a variety of sensor stimuli, both on the same pin as the measurement is to be made on, as well as alternative pins.

By default, excitation is performed on the pin associated with the channel (i.e., excitation and sensor measurement is performed on the same pin). The mode of the pin during the excitation phase is configured by the EXMODE bitfield in CHx_INTERACT. The available modes during the excite phase are:

- · DISABLED: The pin is disabled.
- · HIGH: The pin is driven high.
- · LOW: The pin is driven low.
- DACOUT: The pin is connected to the output of a VDAC channel.

Note: Excitation with VDAC output is only available on some channels. Refer to 28.3.9 VDAC Interface for details. If the VDAC is in opamp-mode, setting EXMODE to DACOUT will result in excitation with output from the opamp.

LESENSE is able to perform sensor excitation on a pin other than the one being measured. When ALTEX in CHx_INTERACT is set, the excitation will occur on the alternative excite pin associated with the given channel. By default, the alternative excite pins are mapped to the LES_ALTEX pins, but they can also be mapped to LESENSE $CH_{X+8 \mod 16}$. Mapping of the alternative excite pins is configured in ALTEXMAP in the CTRL register. Table 28.2 LESENSE Excitation Pin Mapping on page 935 summarizes the mapping of excitation pins for different configurations.

Table 28.2. LESENSE Excitation Pin Mapping

LESENSE channel	ALTEX = 0	ALTEX = 1	
		ALTEXMAP = CH	ALTEXMAP = ALTEX
0	LES_CH0	LES_CH8	LES_ALTEX0
1	LES_CH1	LES_CH9	LES_ALTEX1
2	LES_CH2	LES_CH10	LES_ALTEX2
3	LES_CH3	LES_CH11	LES_ALTEX3
4	LES_CH4	LES_CH12	LES_ALTEX4
5	LES_CH5	LES_CH13	LES_ALTEX5
6	LES_CH6	LES_CH14	LES_ALTEX6
7	LES_CH7	LES_CH15	LES_ALTEX7
8	LES_CH8	LES_CH0	LES_ALTEX0
9	LES_CH9	LES_CH1	LES_ALTEX1
10	LES_CH10	LES_CH2	LES_ALTEX2
11	LES_CH11	LES_CH3	LES_ALTEX3
12	LES_CH12	LES_CH4	LES_ALTEX4
13	LES_CH13	LES_CH5	LES_ALTEX5
14	LES_CH14	LES_CH6	LES_ALTEX6
15	LES_CH15	LES_CH7	LES_ALTEX7

Figure 28.6 Pin Sequencing on page 936 illustrates the sequencing of the pin associated with the active channel and its alternative excite pin.




Figure 28.6. Pin Sequencing

The LES_ALTEXn pins have the ability to excite regardless of what channel is active. Setting AEXn in ALTEXCONF will make LES_ALTEXn excite for all channels using alternative excitation (i.e., ALTEX in CHx_INTERACT is set).

Note: When exciting on the pin associated with the active channel, the pin will go through a tri-stated phase before returning to the idle configuration. This will not happen on pins used as alternative excitation pins.

The pin configuration for the idle phase can be configured individually for each LESENSE channel and alternative excite pin in the IDLECONF and ALTEXCONF registers. The modes available are the same as the modes available in the excitation phase. In the measure phase, the pin mode on the active channel is always disabled (analog input).

To allow the LESENSE mode to control a GPIO pin, the pin must be enabled in the ROUTEPEN register and configured as push-pull. The IDLECONF configuration should not be altered while the pin enable for a given pin is set in ROUTEPEN.

28.3.5 Sensor Sampling

During the measurement phase, LESENSE can sample data from sensors using either ADC0 or an ACMP. This is configured in CHx_INTERACT_SAMPLE. If the ACMP is used, LESENSE can evaluate the ACMP output at a single point in time (CHx_INTERACT_SAMPLE = ACMPCOUNT) for a programmable period of time.

LESENSE includes the ability to sample both analog comparators simultaneously, effectively cutting the time spent on sensor interaction in some applications in half. Setting DUALSAMPLE in CTRL enables this mode. In dual sample mode, channels X and X+8 are paired, meaning they will be sampled at the same time. DUALSAMPLE mode only works when CHx_INTERACT_SAMPLE is set to ACMP.

If ADC0 is used, LESENSE will initiate ADC conversions and fetch the ADC data for further evaluation. If the ADC is configured in differential mode, CHx_INTERACT_SAMPLE must be set to ADCDIFF. In this mode, the output from the ADC and the threshold used for comparison are given in two's complement notation.

See sections28.3.12 ADC Interface and 28.3.10 ACMP Interface for more details on the LESENSE interface to the ADC and ACMPs. The sampled data from ADC or ACMP will be referred to as sensor data in the remainder of this manual.

28.3.6 Sensor Evaluation

When a measurement phase is completed, the sensor data is evaluated by the evaluation block. If the sensor data is taken from ACMP sample in a single point in time (CHx_INTERACT_SAMPLE = ACMP), the evaluation is limited to determining if the sensor data is 0 or 1. For the other sample modes, there are three ways to do sensor evaluation; threshold comparison, sliding window, or step detection. Evaluation mode is configured in CHx_EVAL_MODE.

If the evaluation of sensor data evaluates to true, the corresponding bit in the result register (SCANRES) is set. By configuring SETIF in CHx_INTERACT, interrupt flags can also be set on SCANRES events. Figure 28.7 Scan Result and Interrupt Generation on page 937 illustrates how the sensor data or ACMP sample is used for evaluation and interrupt generation.

Note: For initialization purposes, SCANRES can be written by software. SCANRES should not be written while LESENSE is running (i.e., the RUNNING bit in LESENSE_STATUS is high).




Figure 28.7. Scan Result and Interrupt Generation

The results from sensor data evaluation can be fed into the decoder through the SENSORSTATE register. In DUALSAMPLE mode, results from both the sampled ACMPs will be stored in both SCANRES and SENSORSTATE.

28.3.6.1 Threshold Comparison

In threshold comparison mode, the sensor data is compared to a threshold configured in CHx_EVAL_COMPTHRES. There are two modes of threshold comparison: 'less than' and 'greater than or equal'. Threshold comparison mode is configured in CHx_EVAL_COMP.

28.3.6.2 Sliding Window

In sliding window mode, the sensor data is compared against the upper and lower limits of a window range. The window is defined by a base, given by CHx_EVAL_COMPTHRES, and a size configured in EVALCTRL_WINSIZE. The window size is constant and the same for all LESENSE channels, while the base is specific to each channel and will be updated by LESENSE when the sensor data is outside the current window range. If the sensor data is within the window range, the sensor evaluation will remain the same as it was for the previous measurement. If the sensor data is below the window range, the measurement will be evaluated to false. If the sensor data is above the window range, the measurement will be evaluated to true. In both cases, the window base in CHx_EVAL_COMPTHRES will be updated to reflect the new window range. Figure 28.8 Sliding Window on page 938 shows how the sliding window evaluation mode can be used to implement a system with two self calibrating thresholds.




Figure 28.8. Sliding Window

28.3.6.3 Step Detection

Step detection is used to detect steps in the sensor data compared to sensor data from the previous measurement. The size of the step is configured in EVALCTRL_WINSIZE. In this mode, step up and step down are evaluated as described in Figure 28.9 Step Detection on page 938:

STEP_UP = SENSORDATA_i >= SENSORDATA_{i-1} + EVALCTRL_WINSIZE STEP_DOWN = SENSORDATA_i < SENSORDATA_{i-1} - EVALCTRL_WINSIZE

Figure 28.9. Step Detection

If either a step up or a step down is detected, the SCANRES bit for the active channel will be set. In addition, the STEPDIR bit for the channel will be updated to indicate if a step up or a step down was detected. STEPDIR = 1 indicates a step up. In this mode, previous sensor data is stored in CHx_EVAL_COMPTHRES.

28.3.7 Decoder

Many applications, such as quadrature decoding, require some sort of processing of the sensor readings. In quadrature decoding, the sensors repeatedly pass through a set of states which correspond to the position of the sensors. This sequence, and many other decoding schemes, can be described as a finite state machine. To support this type of decoding without CPU intervention, the LESENSE module includes a highly configurable decoder capable of decoding input from up to four sensors. The decoder is implemented as a programmable state machine with up to 32 states. When doing a sensor scan, the results from the sensors are placed in the decoder input register, SENSORSTATE, if DECODE in CHx_INTERACT is set. The resulting position after a scan is illustrated in Figure 28.10 Sensor Scan and Decode Sequence on page 939, where the bottom blocks show how the SENSORSTATE register is filled. If step detection is enabled, the step direction is placed in SENSORSTATE in the position after the sensor result. When the scan sequence is complete, the decoder evaluates the state of the sensors chosen for decoding, as depicted in Figure 28.10 Sensor Scan and Decode Sequence on page 939.




Figure 28.10. Sensor Scan and Decode Sequence

Upon a state transition, LESENSE can generate a pulse on one or more of the decoder PRS channels. Which PRS channel to generate a pulse on is configured in the PRSACT bit field. If PRSCNT in DECCTRL is set, count signals will be generated on decoder PRS channels 0 and 1 according to the PRSACT configuration. In this mode, channel 0 will pulse each time a count event occurs, while channel 1 indicates the count direction (1 being up and 0 being down). The count direction will be kept at its previous state in between count events. The EFR32 pulse counter may be used to keep track of events based on these PRS outputs.

If SETIF is set, the DECODER interrupt flag will be set when the transition occurs. If INTMAP in DECCTRL and SETIF is set, a transition from state x or x+16 will set the CHx interrupt flag in addition to the DECODER flag.

Setting CHAIN in STx_TCONFA enables the decoder to evaluate more than two possible transitions for each state. If none of the transitions defined in STx_TCONFA or STx_TCONFB match, the decoder will jump to the next descriptor pair and evaluate the transitions defined there. The decoder uses two LFACLK_{LESENSE} cycles for each descriptor pair to be evaluated. If ERRCHK in CTRL is set, the decoder will check that the sensor state has not changed if none of the defined transitions match. The DECERR interrupt flag will be set if none of the transitions match and the sensor state has changed. Figure 28.11 Decoder State Transition Evaluation on page 940 illustrates state transitions. The "Generate PRS signals and set interrupt flag" blocks will perform actions according to the configuration in STx TCONFA and STx TCONFB.

Note: If only one transition from a state is used, STx TCONFA and STx TCONFB should be configured equally.




Figure 28.11. Decoder State Transition Evaluation

The DECODER has a PRS output named DECCMP. This output can be used to indicate which state, or subset of states, the decoder is currently in. This PRS output is enabled by setting DECCMPEN in PRSCTRL, and configured through DECCMPMASK and DECCMPV-AL in PRSCTRL. The value of this PRS output is given by Figure 28.12 DECCMP PRS Output on page 941,

PRS_DECCMP = (DECSTATE & ~DECCMPMASK) == (DECCMPVAL & ~DECCMPMASK)

Figure 28.12. DECCMP PRS Output

To prevent unnecessary interrupt requests or PRS outputs when the decoder toggles back and forth between two states, a hysteresis option is available. The hysteresis function is triggered if a type A transition is preceded by a type B transition, and vice versa. A type A transition is defined in STx_TCONFA, and a type B transition is defined in STx_TCONFB. When descriptor chaining is used, a jump to another descriptor will cancel out the hysteresis effect. Figure 28.13 Decoder Hysteresis on page 941 illustrates how the hysteresis triggers upon state transitions.




Figure 28.13. Decoder Hysteresis

- When HYSTPRSx is set, PRS signal x is suppressed when the hysteresis triggers.
- When HYSTIRQ is set, interrupt requests are suppressed when the hysteresis triggers.

Note: The decoder error interrupt flag, DECERR, is not affected by the hysteresis.

28.3.8 Measurement Results

Part of the LESENSE RAM is treated as a circular buffer for storage of up to 16 sensor measurements results. Each time LESENSE writes data to the result buffer, the result write pointer (PTR_WR) is incremented. Each time a new result is read through the BUFDATA register, the result read pointer (PTR_RD) is incremented. The read pointer will not be incremented if there is no valid, unread data in the result buffer. By default LESENSE will not write additional data to a full result buffer until the data is read by software or DMA. Setting BUFOW in CTRL enables LESENSE to write to the result buffer even if it is full. In this mode, the result read pointer will follow the write pointer if the buffer is full. The result of this is that data read from the result read register (BUFDATA) will be the oldest unread result. The location pointers are available in PTR.

The result buffer has three flags in the STATUS register: BUFDATAV, BUFHALFFULL, and BUFFULL. The flags indicate when new data is available, when the buffer is half full, and when it is full, respectively.

The result buffer also has three interrupt flags in the IR register: BUFDATAV, BUFLEVEL, and BUFOF. BUFDATAV is set when data is available in the buffer. BUFLEVEL is set when the buffer is either full or half-full, depending on the configuration of BUFIDL in CTRL. BUFOF is set if the result buffer overflows.

During a scan, the state of each sensor is stored in SCANRES. If a sensor triggers, a 1 is stored in SCANRES, else a 0 is stored in SCANRES. Whether or not a sensor is said to be triggered depends of the configuration for the given channel. See 28.3.6 Sensor Evaluation for details. If STRSAMPLE in CHx_EVAL is set, the sensor data for each channel will be stored in the LESENSE result buffer. If STRSCANRES in CTRL is set, the result vector, SCANRES, will also be stored in the result buffer. This will be stored after each scan and will be interleaved with the counter values. The contents of the result buffer can be read from BUFDATA or from BUF[x]_DATA. When reading from BUF[x]_DATA, neither the result read pointer or the status flags BUFDATAV, BUFHALFFULL, or BUFFULL will be updated. When reading through the BUFDATA register, the oldest unread result will be read.




Figure 28.14. Circular Result Buffer

Figure 28.14 Circular Result Buffer on page 942 illustrates how the result buffer would be filled when channels 3,5, and 9 are enabled and have STRSAMPLE in CHx_EVAL set, in addition to STRSCANRES in CTRL. The measurement result from the three channels will be sequentially written during the scan, while SCANRES is written to the result buffer upon scan completion.

28.3.9 VDAC Interface

LESENSE is able to drive the VDAC for generation of accurate reference voltages. This is enabled by setting DACCHxEN in PERCTRL. The refresh rate of the VDAC channels can be configured in DACCONVTRIG in PERCTRL. If DACCONVTRIG is set to CHANNELSTART, the VDAC channels are refreshed prior to each sensor measurement, as depicted in Figure 28.4 Timing Diagram, AUXHFRCO Based Timing on page 933. If DACCONVTRIG is set to SCANSTART, the VDAC channels are refreshed prior to each scan. The conversion data is either taken from the data registers in the EFR32 VDAC interface (VDAC0_CH0DATA and VDAC0_CH1DATA) or from the THRES bitfield in the CHx_INTERACT register for the active LESENSE channel. VDAC data used is configured in DACCHxDATA in PERCTRL.

Bias configuration, calibration and reference selection is done in the EFR32 VDAC module and LESENSE will not override these configurations.

LESENSE has the possibility to control switches that connect the VDAC alternate outputs. This allows LESENSE to excite sensors with output from the VDAC channels, this is done by setting CHx_INTERACT_EXMODE to DACOUT. The LESENSE channels can also be connected to the VDAC output when the given channel is idle, this is done by setting IDLECONF_CHx to DAC.

Note: Only LESENSE channels 4, 5, 7, 10, 12, 13 have the possibility to excite using the VDAC alternate outputs, or connect to the VDAC alternate outputs during the idle phase.

The VDAC may be chosen as reference to the analog comparators for accurate reference generation. If the VDAC is configured in continuous mode this does not require any external components. If sample/off mode is used, an external capacitor is needed to maintain the voltage between samples. To configure the VDAC to use this external capacitor, connect the capacitor to the VDAC pin for the given channel and set SHORT in VDAC_OPAx_OUT.

Note: The VDAC mode should not be altered while DACACTIVE in STATUS is set

28.3.10 ACMP Interface

The analog comparators (ACMPs) are used to measure the sensors, and have to be configured according to the application in order for LESENSE to work properly. Depending on the configuration in the ACMP0MODE and ACMP1MODE bit-fields in PERCTRL, LESENSE will take control of the positive input mux and the voltage dividers (DIVVA, DIVVB) for ACMP0 and ACMP1. The remaining configuration of the analog comparators is done in the ACMP register interface.

If ACMPxMODE in PERCTRL is set to MUX, LESENSE will take control of the positive input mux of the ACMP, through the external override interface, described in the ACMP chapter (see 25.3.12 External Override Interface). The offset given by LESENSE, EXT_OFFSET, depends on whether one or two ACMPs are controlled by LESENSE. If only one ACMP is used, EXT_OFFSET will have the same value as the active channel. If both ACMP0 and ACMP1 are used, LESENSE channel 0-7 will use ACMP0 with EXT_OFFSET_0-7, and LESENSE channel 8-15 will use ACMP1 with EXT_OFFSET_0-7.

If ACMPxMODE in PERCTRL is set to MUXTHRES, LESENSE will also take control of the voltage dividers in the ACMP, DIVVA and DIVVB. The thresholds used are individual to each channel and is configured using the 6 LSBs of CHx_INTERACT_THRES. By default, ACMP_HYSTERESIS0_DIVVX and ACMP_HYSTERESIS1_DIVVX will be given the same value, the 6 LSBs of CHx_INTERACT_THRES. To allow different values for ACMP_HYSTERESIS0_DIVVX and ACMP_HYSTERESIS1_DIVVX, ACMPxHYSTEN in PERCTRL needs to be set. This allows the hysteresis feature in the ACMP to be utilized. ACMP_HYSTERESIS0_DIVVX will get the value programmed in CHx_INTERACT_THRES[5:0], while ACMP_HYSTERESIS1_DIVVX will get the value programmed in CHx_INTERACT_THRES[11:6].

28.3.11 ACMP and VDAC Duty Cycling

By default, the analog comparators and the VDAC are shut down between LESENSE scans to save energy. If this is not desired, WAR-MUPMODE in PERCTRL can be configured to prevent them from being shut down.

Both the VDAC and analog comparators rely on a bias module for correct operation. This bias module has a low power mode which consumes less energy at the cost of reduced accuracy. BIASMODE in BIASCTRL configures how the bias module is controlled by LESENSE. When set to DUTYCYCLE, LESENSE will set the bias module in high accuracy mode whenever LESENSE is active, and keep it in the low power mode otherwise. When BIASMODE is set to HIGHACC, the high accuracy mode is always selected. When set to DONTTOUCH, LESENSE will not control the bias module.

28.3.12 ADC Interface

The LESENSE module can be configured to trigger conversions on ADC0 and use data from ADC0 to evaluate sensor status. In order to do this, the scan mode of the ADC has to be configured. When the sample delay configured in CHx_TIMING_SAMPLEDLY has expired, LESENSE will initiate an ADC sample. The active LESENSE channel determines which ADC0 channel to be sampled, where LESENSE channel X corresponds to ADC0 scan channel X.

28.3.13 DMA Requests

LESENSE issues a DMA request when the result buffer is either full or half full, depending on the configuration of BUFIDL in CTRL. The request is cleared when the buffer level drops below the threshold defined in BUFIDL. A single DMA request is also set whenever there is unread data in the buffer. DMAWU in CTRL configures at which buffer level LESENSE should wake-up the DMA when in EM2.

Note: The DMA controller should always fetch data from the BUFDATA register.

28.3.14 PRS Output

LESENSE is an asynchronous PRS producer and has twenty PRS outputs. The decoder has four outputs and in addition, all bits in the SCANRES register are available as PRS outputs. For further information on the decoder PRS output, refer to 28.3.7 Decoder.

28.3.15 RAM

LESENSE includes a RAM block used for storage of configuration and results. Registers mapped to the RAM include: STx_TCONFA, STx_TCONFB, BUFx_DATA, BUFDATA, CHx_TIMING, CHx_INTERACT, and CHx_EVAL. These registers have unknown value out of reset and have to be initialized before use.

Note: Read-modify-write operations on uninitialized RAM register produces undefined values.

28.3.16 Application Examples

The following sections detail several example applications for the LESENSE block.

28.3.16.1 Capacitive Sense

Figure 28.15 Capacitive Sense Setup on page 945 illustrates how the EFR32 can be configured to monitor four capacitive buttons.




Figure 28.15. Capacitive Sense Setup


The following steps show how to configure LESENSE to scan through the four buttons 100 times per second, issuing an interrupt if one of them is pressed.

- 1. Assuming LFACLK_{LESENSE} is 32 kHz, set PCPRESC to 3 and PCTOP to 39 in CTRL. This will set the LESENSE scan frequency to 100 Hz.
- 2. Enable channels 0 through 3 in CHEN and set IDLECONF for these channels to DISABLED. In capacitive sense mode, the GPIO should always be disabled (i.e., analog input).
- 3. Configure the ACMP to operate in CAPSENSE mode (refer to the ACMP chapter for more details).
- 4. Configure the following bit fields in CHx_CONF, for channels 0 through 3:
 - a. Set EXTIME to 0. No excitation is needed in this mode.
 - b. Set SAMPLE to ACMPCOUNT and COMP to LESS. This makes LESENSE interpret a sensor as active if the frequency on a channel drops below the threshold (i.e., the button is pressed).
 - c. Set SAMPLEDLY to an appropriate value each sensor will be measured for SAMPLEDLY/F_{LFACLK_LESENSE} seconds. MEAS-UREDLY should be set to 0
- 5. Set CTRTHRESHOLD to an appropriate value. An interrupt will be issued if the counter value for a sensor is below this threshold after the measurement phase.
- 6. Enable interrupts on channels 0 through 3.
- 7. Start scan sequence by writing a 1 to START in CMD.

In a capacitive sense application, it might be required to calibrate the threshold values on a periodic basis, for example to compensate for humidity and other physical variations. LESENSE is able to store up to 16 counter values from a configurable number of channels, making it possible to collect sample data while in EM2. When calibration is to be performed, the CPU only has to be woken up for a short period of time as the data to be processed already lies in the result registers. To enable storing of the count value for a channel, set STRSAMPLE in the CHx_INTERACT register.

28.3.16.2 LC Sensor

Figure 28.16 LC Sensor Setup on page 946 below illustrates how the EFR32 can be set up to monitor four LC sensors.






Figure 28.16. LC Sensor Setup

LESENSE can be used to excite and measure the damping factor in LC sensor oscillations. To measure the damping factor, the ACMP can be used to generate a high output each time the sensor voltage exceeds a certain level. These pulses are counted using an asynchronous counter and compared with the threshold in COMPTHRES in the CHx_EVAL register. If the number of pulses exceeds the threshold level, the sensor is said to be active, otherwise it is inactive. Figure 28.17 LC Sensor Oscillations on page 946 illustrates how the output pulses from the ACMP correspond to damping of the oscillations. The results from sensor evaluation can automatically be fed into the decoder in order to keep track of rotations.




Figure 28.17. LC Sensor Oscillations

The following steps show how to configure LESENSE to scan through the four LC sensors 100 times per second.

- 1. Assuming LFACLK_{LESENSE} is 32kHz, set PCPRESC to 3 and PCTOP to 39 in CTRL. This will set the LESENSE scan frequency to 100Hz.
- 2. Enable the VDAC and configure it to produce a voltage of Vdd/2.

- 3. Enable channels 0 through 3 in CHEN. Set IDLECONF for the active channels to DACOUT. The channel pins should be connected to the VDAC output (effectively shorting the LC sensor) in the idle phase to damp the oscillations.
- 4. Configure the ACMP to use scaled Vdd as negative input, refer to ACMP chapter for details.
- 5. Enable and configure PCNT and asynchronous PRS.
- 6. Configure the GPIOs used as PUSHPULL.
- 7. Configure the following bit fields in CHx CONF, for channels 0 through 3:
 - a. Set EXCLK to AUXHFRCO. AUXHFRCO is needed to achieve short excitation time.
 - b. Set EXTIME to an appropriate value. Excitation will last for EXTIME/F_{AUXHFRCO} seconds.
 - c. Set EXMODE to HIGH. The LC sensors are excited by pulling the excitation pin high.
 - d. Set SAMPLE to ACMPCOUNT and COMP to LESS. Status of each sensor is evaluated based on the number of pulses generated by the ACMP. If they are less than the threshold value, the sensor is said to be active.
 - e. Set SAMPLEDLY to an appropriate value, each sensor will be measured for SAMPLEDLY/F_{LFACLK} LESENSE seconds.
- 8. Set CTRTHRESHOLD to an appropriate value. If the sensor is active, the counter value after the measurement phase should be less than the threshold. If it is inactive, the counter value should be greater than the threshold.
- 9. Start scan sequence by writing a 1 to START in CMD.

Note: Exciting the LC sensor by pulling the excitation pin high allows the ESD protection in the pads to clamp any voltage swings below the ground voltage, giving a consistent starting point for the oscillations.

28.3.16.3 LESENSE Decoder 1

The example below illustrates how the LESENSE module can be used for decoding using three sensors.




Figure 28.18. FSM Example 1

Figure 28.18 FSM Example 1 on page 948, configure the following LESENSE registers:

- 1. Configure the channels to be used, be sure to set DECODE in CHx EVAL.
- 2. Set PRSCNT to enable generation of count waveforms on PRS. Also configure a PCNT to listen to the PRS channels and count accordingly.
- 3. Configure the following in STx TCONFA and STx TCONFB:
 - a. Set MASK = 0b1000 in STx_TCONFA and STx_TCONFB for all used states. This enables three sensors to be evaluated by the decoder.
 - b. Configure the remaining bit fields in STx_TCONFA and STx_TCONFB as described in Table 28.3 LESENSE Decoder Configuration for FSM Example 1 on page 948.
- 4. To initialize the decoder, run one scan, and read the present sensor status from SENSORSTATE. Then write the index of this state to DECSTATE.
- 5. Write to START in CMD to start scanning of sensors and decoding.

Table 28.3. LESENSE Decoder Configuration for FSM Example 1

Register	TCONFA_ NEXTSTATE	TCONFA_COMP	TCONFA_ PRSACT	TCONFB_ NEXTSTATE	TCONFB_COMP	TCONFB_ PRSACT
ST0	1	0b001	UP	7	0b100	DOWN
ST1	2	0b011	UP	0	0b000	DOWN
ST2	3	0b010	UP	1	0b001	DOWN
ST3	4	0b110	UP	2	0b011	DOWN
ST4	5	0b111	UP	3	0b010	DOWN
ST5	6	0b101	UP	4	0b110	DOWN
ST6	7	0b100	UP	5	0b111	DOWN
ST7	0	0b000	UP	6	0b101	DOWN

28.3.16.4 LESENSE Decoder 2

The example below illustrates how the LESENSE decoder can be used to implement the state machine seen in Figure 28.19 FSM Example 2 on page 949.




Figure 28.19. FSM Example 2

- 1. Configure STx_TCONFA and STx_TCONFB as described in Table 28.4 LESENSE Decoder Configuration for FSM Example 2 on page 949.
- 2. To initialize the decoder, run one scan, and read the present sensor status from SENSORSTATE. Then write the index of this state to DECSTATE.
- 3. Write to START in CMD to start scanning of sensors and decoding.

Table 28.4. LESENSE Decoder Configuration for FSM Example 2

Register	NEXTSTATE	СОМР	MASK	CHAIN
ST0_TCONFA	8	0b1000	0b0111	1
ST0_TCONFB	2	0b0001	0b1000	-
ST1_TCONFA	6	0b0010	0b1000	0
ST1_TCONFB	6	0b0010	0b1000	-
ST2_TCONFA	8	0b1000	0b0111	1
ST2_TCONFB	4	0b0011	0b1000	-
ST3_TCONFA	0	0b0000	0b1000	0
ST3_TCONFB	0	0b0000	0b1000	-
ST4_TCONFA	8	0b1000	0b0111	1
ST4_TCONFB	6	0b0010	0b1000	-
ST5_TCONFA	2	0b0001	0b1000	0
ST5_TCONFB	2	0b0001	0b1000	-
ST6_TCONFA	8	0b1000	0b0111	1
ST6_TCONFB	0	0b0000	0b1000	-
ST7_TCONFA	4	0b0011	0b1000	0
ST7_TCONFB	4	0b0011	0b1000	-

28.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	LESENSE_CTRL	RW	Control Register
0x004	LESENSE_TIMCTRL	RW	Timing Control Register
0x008	LESENSE_PERCTRL	RW	Peripheral Control Register
0x00C	LESENSE_DECCTRL	RW	Decoder Control Register
0x010	LESENSE_BIASCTRL	RW	Bias Control Register
0x014	LESENSE_EVALCTRL	RW	LESENSE Evaluation Control
0x018	LESENSE_PRSCTRL	RW	PRS Control Register
0x01C	LESENSE_CMD	W1	Command Register
0x020	LESENSE_CHEN	RW	Channel Enable Register
0x024	LESENSE_SCANRES	RWH	Scan Result Register
0x028	LESENSE_STATUS	R	Status Register
0x02C	LESENSE_PTR	R	Result Buffer Pointers
0x030	LESENSE_BUFDATA	R(a)	Result Buffer Data Register
0x034	LESENSE_CURCH	R	Current Channel Index
0x038	LESENSE_DECSTATE	RWH	Current Decoder State
0x03C	LESENSE_SENSORSTATE	RWH	Decoder Input Register
0x040	LESENSE_IDLECONF	RW	GPIO Idle Phase Configuration
0x044	LESENSE_ALTEXCONF	RW	Alternative Excite Pin Configuration
0x050	LESENSE_IF	R	Interrupt Flag Register
0x054	LESENSE_IFS	W1	Interrupt Flag Set Register
0x058	LESENSE_IFC	(R)W1	Interrupt Flag Clear Register
0x05C	LESENSE_IEN	RW	Interrupt Enable Register
0x060	LESENSE_SYNCBUSY	R	Synchronization Busy Register
0x064	LESENSE_ROUTEPEN	RW	I/O Routing Register
0x100	LESENSE_ST0_TCONFA	RW	State Transition Configuration a
0x104	LESENSE_ST0_TCONFB	RW	State Transition Configuration B
	LESENSE_STx_TCONFA	RW	State Transition Configuration a
	LESENSE_STx_TCONFB	RW	State Transition Configuration B
0x1F8	LESENSE_ST31_TCONFA	RW	State Transition Configuration a
0x1FC	LESENSE_ST31_TCONFB	RW	State Transition Configuration B
0x200	LESENSE_BUF0_DATA	RWH	Scan Results
	LESENSE_BUFx_DATA	RWH	Scan Results
0x23C	LESENSE_BUF15_DATA	RWH	Scan Results
0x240	LESENSE_CH0_TIMING	RW	Scan Configuration
0x244	LESENSE_CH0_INTERACT	RW	Scan Configuration

Offset	Name	Туре	Description
0x248	LESENSE_CH0_EVAL	RWH	Scan Configuration
	LESENSE_CHx_TIMING	RW	Scan Configuration
	LESENSE_CHx_INTERACT	RW	Scan Configuration
	LESENSE_CHx_EVAL	RWH	Scan Configuration
0x330	LESENSE_CH15_TIMING	RW	Scan Configuration
0x334	LESENSE_CH15_INTERACT	RW	Scan Configuration
0x338	LESENSE_CH15_EVAL	RWH	Scan Configuration

28.5 Register Description

28.5.1 LESENSE_CTRL - Control Register (Async Reg)

Offset															Ві	t Po	siti	on													
0x000	33	30	29	28	27	26	25	24	23	22	2	20	19	8	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	2	- 0
Reset		•	•	•	•	•	•	•	•	0	5	OX O	0		0	0			0		0			5	2				0×0	•	0x0
Access										RW	غ م	Ž	₩ M		Z.	Z.			Z.		Z.			ک ا	}				N N		A W
Name										DEBUGRUN		סאגע מאנים	BUFIDL		STRSCANRES	BUFOW			DUALSAMPLE		ALTEXMAP			EINO CINA CO					PRSSEL		SCANMODE

D:4	Name	Booot	A 00000	Description
Bit	Name	Reset	Access	Description
31:23	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
22	DEBUGRUN	0	RW	Debug Mode Run Enable
	Set to keep LESEN	SE running in d	ebug mode.	
	Value			Description
	0			LESENSE can not start new scans in debug mode
	1			LESENSE can start new scans in debug mode
21:20	DMAWU	0x0	RW	DMA Wake-up From EM2
	Set buffer threshold	l for waking up t	he DMA con	troller when the system is in EM2
	Value	Mode		Description
	0	DISABLE		No DMA wake-up from EM2
	1	BUFDATAV	′	DMA wake-up from EM2 when data is valid in the result buffer
	2	BUFLEVEL		DMA wake-up from EM2 when the result buffer is full/half-full depending on BUFIDL configuration
19	BUFIDL	0	RW	Result Buffer Interrupt and DMA Trigger Level
	Set buffer threshold	I for DMA reque	sts and inter	rupt generation
	Value	Mode		Description
	0	HALFFULL		DMA and interrupt flags set when result buffer is half-full
	1	FULL		DMA and interrupt flags set when result buffer is full
18	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
17	STRSCANRES	0	RW	Enable Storing of SCANRES
	When set, SCANRE	S will be stored	l in the result	buffer after each scan

Bit	Name	Reset	Access	Description
16	BUFOW	0	RW	Result Buffer Overwrite
	If set, LESENSE wil	l always write to	the result b	uffer, even if it is full
15:14	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13	DUALSAMPLE	0	RW	Enable Dual Sample Mode
	When set, both ACN	VIPs will be samp	led simultar	neously.
12	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	ALTEXMAP	0	RW	Alternative Excitation Map
	This bit is used to co	onfigure which pi	ns alternate	e excitation is mapped to.
	Value	Mode		Description
	0	ALTEX		Alternative excitation is mapped to the LES_ALTEX pins.
	1	СН		Alternative excitation is mapped to the pin of LESENSE channel (X+8 mod 16), X being the active channel.
10:9	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
8:7	SCANCONF	0x0	RW	Select Scan Configuration
	These bits control w	hich CHx_CONF	registers to	o be used.
	Value	Mode		Description
	0	DIRMAP		The channel configuration register registers used are directly mapped to the channel number.
	1	INVMAP		The channel configuration register registers used are CH_{X+8} _CONF for channels 0-7 and CH_{X-8} _CONF for channels 8-15.
	2	TOGGLE		The channel configuration register registers used toggles between CH_{X} _CONF and CH_{X+8} _CONF when channel x triggers
	3	DECDEF		The decoder state defines the CONF registers to be used.
6	Reserved	To ensure co	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5:2	PRSSEL	0x0	RW	Scan Start PRS Select
	Select PRS source	for scan start if S	CANMODE	is set to PRS.
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input

Bit	Name	Reset	Access	Description
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
1:0	SCANMODE	0x0	RW	Configure Scan Mode
	These bits control	how the scan frequ	ency is de	cided
	These bits control Value	how the scan frequ	ency is de	Description
		·	ency is de	
	Value	Mode	ency is dec	Description
	Value 0	Mode PERIODIC	ency is dec	Description A new scan is started each time the period counter overflows

28.5.2 LESENSE_TIMCTRL - Timing Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset														Ві	it P	osit	ion																			
0x004	33	59	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10		, ω	_	\neg	9	2	4	က	7	~ c					
Reset		•	0		•	•		2	OXO					•	•	00×0	•					2	2) X			•	0x0					
Access			% M					<u> </u>	 }							<u>~</u> 8					T		<u> </u>				 ≩				§ §					
								_													H		_				_									
Name			AUXSTARTUP					VIOTO VI	SIARIDEI							PCTOP											LFPRESC				AUXPRESC					
Bit	Name					Re	set			Ac	ces	s	Des	crip	tio	n																				
31:29	Resen	ved				To tion		ure	com	pati	bilit	y wi	ith fu	ıture	e de	vice	s, al	way	/s и	rite	bits	to (0. M	ore	inf	orma	atio	n ir	1.2	2 Co	nven-					
28	AUXS ⁻	TAR	TUP)		0				RV	/		ΑUX	KHF	RC	O S	tartu	рС	on	iguı	atio	on														
	This bi	t car	n be	set	t to C	DND	EMA	AND) to (dela	y sta	artu	ıp of	the	AU	XHF	RC	O w	hen	higl	n fre	equ	ency	tim	ner	is u	sec	t								
	Value					Мо	de						Des	cript	tion	l																				
	0					PR	EDE	ΞMΑ	ND				ΑUX	KHFI	RC	O is	star	ted	half	a cl	ock	сус	cle b	efo	re i	t's n	ee	ded								
	1					ON	IDEI	MAN	N D				ΑUX	KHFI	RC	O is	star	ted	at tl	ne tir	ne	it is	nee	dec	t											
27:24	Resen	ved				To tion		ure	com	pati	bilit	y wi	ith fu	ıture	de	vice	s, al	way	/S W	rite	bits	to (0. M	ore	inf	orma	atio	n ir	1.2	1.2 Conven						
23:22	STAR	TDL	Y			0x0)			RV	/		Sta	rt De	elay	y Co	nfig	ura	tior	1																
	Delay		or ir	nter	actio	on S	TAF	RTD	ELA	Y LI	FAC	LK	LESE	NSE	сус	cles	for e	ach	ch	anne	el															
21:20	Resen	ved				To tion		ure	com	pati	bilit	y wi	ith fu	ıture	de	vice	s, al	way	/S W	rite	bits	to (0. M	ore	inf	orma	atio	n ir	1.2	? Co	nven-					
19:12	РСТО	Р				0x0	00			RV	/		Per	iod (Coı	unte	r To	рV	alu	е																
	These	bits	con	tain	the	top	valu	e fo	r the	е ре	riod	col	unte	r.																						
11	Resen	ved.				To tion		ure	com	pati	bilit	y wi	ith fu	ıture	de	vice	s, al	way	/S W	rite	bits	to (0. M	ore	inf	orma	atio	n ir	1.2	? Co	nven-					
10:8	PCPR	ESC				0x0)			RV	/		Per	iod (Coı	unte	r Pr	esc	alir	g																
	This bi	tfield	d is u	use	d to	divid	de th	ne cl	ock	to tl	ne p	eric	od co	ounte	er																					
	Value					Мо	de						Des	cript	tion	l																				
	0					DI۱	/1					-	The	per	iod	cou	nter	clo	ck fr	eque	enc	y is	LFA	CL	K _{LI}	ESEN	SE/	/1								
	1					DI۱	/2						The	per	iod	cou	nter	clo	ck fr	eque	enc	y is	LFA	CL	KLI	ESEN	SE/	/2								
	2					D۱۱	/4						The	per	iod	cou	nter	clo	ck fr	eque	enc	y is	LFA	CL	KLI	ESEN	SE/	/4								
	3					DI۱	/8						The	per	iod	cou	nter	clo	ck fr	eque	enc	y is	LFA	CL	KLI	ESEN	SE/	/8								
							/16						The	nor	امط				. I. E.					\sim 1	v			14.0								

The period counter clock frequency is LFACLK $_{LESENSE}/32$

DIV32

5

Bit	Name	Reset /	Access	Description
	6	DIV64		The period counter clock frequency is LFACLK _{LESENSE} /64
	7	DIV128		The period counter clock frequency is LFACLK _{LESENSE} /128
7	Reserved	To ensure comp	atibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
6:4	LFPRESC	0x0 F	RW.	Prescaling Factor for Low Frequency Timer
	This bitfield is use	ed to divide the clock to	the low	frequency timer
	Value	Mode		Description
	0	DIV1		Low frequency timer is clocked with LFACLK _{LESENSE} /1
	1	DIV2		Low frequency timer is clocked with LFACLK _{LESENSE} /2
	2	DIV4		Low frequency timer is clocked with LFACLK _{LESENSE} /4
	3	DIV8		Low frequency timer is clocked with LFACLK _{LESENSE} /8
	4	DIV16		Low frequency timer is clocked with LFACLK _{LESENSE} /16
	5	DIV32		Low frequency timer is clocked with LFACLK _{LESENSE} /32
	6	DIV64		Low frequency timer is clocked with LFACLK _{LESENSE} /64
	7	DIV128		Low frequency timer is clocked with LFACLK _{LESENSE} /128
3:2	Reserved	To ensure comp	atibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	AUXPRESC	0x0 F	RW	Prescaling Factor for High Frequency Timer
	This bitfield is use	ed to divide the clock to	the higl	n frequency timer
	Value	Mode		Description
	0	DIV1		High frequency timer is clocked with AUXHFRCO/1
	1	DIV2		High frequency timer is clocked with AUXHFRCO/2
	2	DIV4		High frequency timer is clocked with AUXHFRCO/4
	3	DIV8		High frequency timer is clocked with AUXHFRCO/8

28.5.3 LESENSE_PERCTRL - Peripheral Control Register (Async Reg)

Offset									Bit F	Position	1												
0x008	33	29	27	26	25	24	23	20	18 7 4	5 5	<u>4</u> (5	12	11	9	o &	7	9	5	4	3	7	_	0
Reset	·	0x0	0	0	0	0	0x0	0x0			·				0		0			0	0	0	0
Access		₩ W	₹	₩ M	\ N	Z.	N N	Z Š							¥ S		₹			RW	₩	RW	RW
			-	-																			
Name		WARMUPMODE	ACMP1HYSTEN	ACMPOHYSTEN	ACMP1INV	ACMPOINV	ACMP1MODE	ACMPOMODE							DACCONVTRIG		DACSTARTUP			DACCH1DATA	DACCH0DATA	DACCH1EN	DACCH0EN
		>	A	Δ.			∢																
Bit	Name					set		Access	Description		,		., ,	., ,			_						
31:30	Reserv	/ed			To tio		ure com	patibility	ith future d	evices,	alway	/S Wr	ite bi	its to	0. M	ore in	nforr	natio	on in	1.2	Cor	iver	7-
29:28	WARM	IUPMOI	DE		0x0)		RW	ACMP and	d VDAC	Duty	у Су	cle N	/lod	е								
	This bi	tfield is	use	d to	conf	figur	e how th	ne VDA0	nd ACMP a	are duty	cycle	ed wh	nen L	ES	ENSE	is co	ontro	lling	the	m			
	Value				Мо	de			Description	n													_
	0				NC	RM	AL		The analogidle	g compa	arator	s an	d VD	AC	are sh	ut do	own	whe	n LE	ESE	NSE	is	_
	1				KE	EP/	ACMPW	ARM	The analog	g compa	arator	s are	kep	t po	wered	up v	vhei	n LE	SEN	ISE	is id	le	
	2				KE	EPE	DACWA	RM	The VDAC	c is kept	powe	ered	up w	hen	LESE	NSE	is i	dle					
	3				KE	EPA	ACMPDA	ACWAR	The analog		arator	s an	d VD	AC	are ke	pt po	owe	red ι	w qı	hen	LE-		
27	ACMP	1HYSTE	ΞN		0			RW	ACMP1 H	ysteres	is En	able	!										
	Set to	control A	4CM	1P1_	_HY	STE	RESISC	_DIVVX	nd ACMP1	_HYSTE	ERES	SIS1_	DIV	VX s	epara	tely.							
26	ACMP	0HYSTE	ΞN		0			RW	ACMP0 H	ysteres	is En	able											
	Set to	control A	ACM	1P0_	HY.	STE	RESISC	_DIVVX	nd ACMP0	_HYSTE	ERES	SIS1_	DIV	VX s	epara	tely.							
25	ACMP	1INV			0			RW	Invert Ana	alog Co	mpa	rator	10	utpı	ut								
	This bi	t can be	set	to ir	nver	t the	output	coming	m ACMP1														
24	ACMP	0INV			0			RW	Invert Ana	alog Co	mpa	rator	0 0	utpı	ut								
				to ir			output		m ACMP0														
23:22		1MODE			0x0			RW	ACMP1 M	lode													
	Config	ure how	LES	SEN	ISE	cont	trols AC	MP1															_
	Value				Мо	de			Description	n													
	0				DIS	SAB	LE		LESENSE	does n	ot co	ntrol .	ACN	1P1									
	1				MU	JX			LESENSE	control	s the	inpu	t mu	x (P	OSSE	L) of	AC	MP1					
	2	2 MUXTHRES					LESENSE controls the input mux and the threshold value (VDDLEVEL) of ACMP1) —					

Bit	Name	Reset Acc	ess Description
21:20	ACMP0MODE	0x0 RW	ACMP0 Mode
		ENSE controls ACMP0	
	Value	Mode	Description
	0	DISABLE	LESENSE does not control ACMP0
	1	MUX	LESENSE controls the input mux (POSSEL) of ACMP0
	2	MUXTHRES	LESENSE controls the input mux (POSSEL) and the threshold value (VDDLEVEL) of ACMP0
19:9	Reserved	To ensure compatib	ility with future devices, always write bits to 0. More information in 1.2 Conven-
8	DACCONVTRIG	0 RW	VDAC Conversion Trigger Configuration
	This bit is used to co	onfigure how frequently	a VDAC conversion is triggered
	Value	Mode	Description
	0	CHANNELSTART	VDAC is enabled before every LESENSE channel measurement.
	1	SCANSTART	VDAC is only enabled once per scan.
7	Reserved	To ensure compatib	ility with future devices, always write bits to 0. More information in 1.2 Conven-
6	DACSTARTUP	0 RW	VDAC Startup Configuration
	This bit is used to co	onfigure the duration be	tween the VDAC conversion trigger and the sensor interaction
	Value	Mode	Description
	0	FULLCYCLE	VDAC is started a full LFACLK $_{\mbox{\scriptsize LESENSE}}$ cycle before sensor interaction starts.
	1	HALFCYCLE	VDAC is started half a LFACLK _{LESENSE} cycle before sensor interaction starts.
5:4	Reserved	To ensure compatib	ility with future devices, always write bits to 0. More information in 1.2 Conven-
3	DACCH1DATA	0 RW	VDAC CH1 Data Selection
	This bit decides if the	e data used for VDAC	conversion is taken from the VDAC interface or from LESENSE
	Value	Mode	Description
	0	DACDATA	VDAC data is defined by CH1DATA in the VDAC interface.
	1	THRES	VDAC data is defined by THRES in CHx_INTERACT.
2	DACCH0DATA	0 RW	VDAC CH0 Data Selection
	This bit decides if the	ne data used for VDAC o	conversion is taken from the VDAC interface or from LESENSE
	Value	Mode	Description
	0	DACDATA	VDAC data is defined by CH0DATA in the VDAC interface.
	1	THRES	VDAC data is defined by THRES in CHx_INTERACT.

Bit	Name	Reset	Access	Description									
1	DACCH1EN	0	RW	VDAC CH1 Enable									
	Enable LESENSE co	entrol of VDAC0	CH1										
0	DACCH0EN	0	RW	VDAC CH0 Enable									
	Enable LESENSE control of VDAC0 CH0												

28.5.4 LESENSE_DECCTRL - Decoder Control Register (Async Reg)

For more	information a	about asyno	chronou	s reg	isters	see 4	4.3	Ac	cess to	Low E	nerg	у Р	eriphe	als (Asyr	nchr	ono	us F	Regis	sters	s).			
Offset									Bi	t Positi	on													
0x00C	30 30 29	28 27 26	25	23	22	20	10	<u>n</u>	18 7	15	4	13	12 1	: 6	6	∞	/	9	2	4	က	7	-	0
Reset		0x0			0X0				2	2			0x0			0	0	0	0	0	0	0	0	0
Access		Z.			Z.				<u> </u>	}			RW			§ S	Z S	\ N N	S S	S N	\ N	S N	§ S	Z.
Name		PRSSEL3			PRSSEL2				0000				PRSSEL0			INPUT	PRSCNT	HYSTIRQ	HYSTPRS2	HYSTPRS1	HYSTPRS0	INTMAP	ERRCHK	DISABLE
Bit	Name		Reset		,	Acces	s	D	escrip	tion														
31:29	Reserved		To en	sure	сотр	atibilit	ty v	vith	future	device	s, al	way	s write	bits	to 0.	Мо	re in	forn	natio	on in	1.2	? Co	nve	n-
28:25	PRSSEL3		0x0			RW		LI	ESENS	SE Dec	ode	r PR	S Inpu	ıt 3 C	Conf	iguı	ratio	n						
	Select PRS	S input for b	it 3 of tl	ne LE	ESEN	SE de	co	der	ſ															
	Value		Mode					D	escript	ion														_
	0		PRSC	:H0				Р	RS Ch	annel 0	sele	ected	d as in	put										
	1		PRSC	H1				Ρ	RS Ch	annel 1	sele	ected	d as in	put										
	2		PRSC	H2				Ρ	RS Ch	annel 2	sele	ected	d as in	put										
	3		PRSC	H3				Ρ	RS Ch	annel 3	sele	ected	d as in	put										
	4		PRSC	H4				Ρ	RS Ch	annel 4	sele	ected	d as in	put										
	5		PRSC	H5				Р	RS Ch	annel 5	sele	ected	d as in	put										
	6		PRSC	H6				Р	RS Ch	annel 6	sele	ected	d as in	put										
	7		PRSC	H7				Р	RS Ch	annel 7	sele	ected	d as in	put										
	8		PRSC	:H8				Р	RS Ch	annel 8	sele	ected	d as in	put										
	9		PRSC					Р	RS Ch	annel 9	sele	ected	d as in	put										
	10		PRSC							annel 1				-										
	11		PRSC	H11				Р	RS Ch	annel 1	1 se	lecte	ed as i	nput										_
24	Reserved		To entions	sure	comp	atibilit	ty v	vith	future	device	s, al	way	s write	bits	to 0.	Мо	re in	forn	natio	on in	1.2	? Co	nve	n-
23:20	PRSSEL2		0x0			RW		L	ESENS	SE Dec	ode	r PR	S Inpu	ıt 2 (Conf	iguı	ratio	n						
	Select PRS	S input for b	it 2 of tl	ne LE	ESEN	SE de	co	der	ſ															
	Value		Mode					D	escript	ion														_
	0		PRSC	H0				Р	RS Ch	annel 0	sele	ected	as in	put										_
	1		PRSC	H1				Р	RS Ch	annel 1	sele	ected	d as in	put										
	2		PRSC	H2				Р	RS Ch	annel 2	sele	ected	d as in	put										
	3		PRSC	:H3				Ρ	RS Ch	annel 3	sele	ected	d as in	put										

PRS Channel 4 selected as input

PRSCH4

4

Bit	Name	Reset	Access	Description
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
19	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
18:15	PRSSEL1	0x0	RW	LESENSE Decoder PRS Input 1 Configuration
	Select PRS input for t	he bit 1 of the LI	ESENSE d	lecoder
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input
	8	PRSCH8		PRS Channel 8 selected as input
	9	PRSCH9		PRS Channel 9 selected as input
	10	PRSCH10		PRS Channel 10 selected as input
	11	PRSCH11		PRS Channel 11 selected as input
14	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13:10	PRSSEL0	0x0	RW	LESENSE Decoder PRS Input 0 Configuration
	Select PRS input for t	he bit 0 of the LI	ESENSE d	lecoder
	Value	Mode		Description
	0	PRSCH0		PRS Channel 0 selected as input
	1	PRSCH1		PRS Channel 1 selected as input
	2	PRSCH2		PRS Channel 2 selected as input
	3	PRSCH3		PRS Channel 3 selected as input
	4	PRSCH4		PRS Channel 4 selected as input
	5	PRSCH5		PRS Channel 5 selected as input
	6	PRSCH6		PRS Channel 6 selected as input
	7	PRSCH7		PRS Channel 7 selected as input

Bit	Name	Reset Acc	ess Description
	8	PRSCH8	PRS Channel 8 selected as input
	9	PRSCH9	PRS Channel 9 selected as input
	10	PRSCH10	PRS Channel 10 selected as input
	11	PRSCH11	PRS Channel 11 selected as input
9	Reserved	To ensure compatible tions	oility with future devices, always write bits to 0. More information in 1.2 Conven-
8	INPUT	0 RW	LESENSE Decoder Input Configuration
	Select input to the	LESENSE decoder	
	Value	Mode	Description
	0	SENSORSTATE	The SENSORSTATE register is used as input to the decoder.
	1	PRS	PRS channels are used as input to the decoder.
7	PRSCNT	0 RW	Enable Count Mode on Decoder PRS Channels 0 and 1
	When set, decode	er PRS0 and PRS1 will be	used to produce output which can be used by a PCNT to count up or down.
6	HYSTIRQ	0 RW	Enable Decoder Hysteresis on Interrupt Requests
	When set, hystere	esis is enabled in the deco	oder, suppressing interrupt requests.
5	HYSTPRS2	0 RW	Enable Decoder Hysteresis on PRS2 Output
	When set, hystere	esis is enabled in the deco	oder, suppressing changes on PRS channel 2
4	HYSTPRS1	0 RW	Enable Decoder Hysteresis on PRS1 Output
	When set, hystere	esis is enabled in the deco	oder, suppressing changes on PRS channel 1
3	HYSTPRS0	0 RW	Enable Decoder Hysteresis on PRS0 Output
	When set, hystere	esis is enabled in the deco	oder, suppressing changes on PRS channel 0
2	INTMAP	0 RW	Enable Decoder to Channel Interrupt Mapping
	When set, a transi	ition from state x in the de	ecoder will set interrupt flag CH[x mod 16]
1	ERRCHK	0 RW	Enable Check of Current State
	When set, the dec	coder checks the current	state in addition to the states defined in TCONF
0	DISABLE	0 RW	Disable the Decoder
	When set, the dec	coder is disabled. When d	isabled the decoder will keep its current state

28.5.5 LESENSE_BIASCTRL - Bias Control Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset				•																			•				•		•		2	2
Access																															2	2
Name																															HOMOVIA	

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	BIASMODE	0x0	RW	Select Bias Mode
	This bitfield is use	ed to configure ho	w LESENSE	interacts with the bias module
	Value	Mode	-	Description
	0	DONTTOU	СН	Bias module is controlled by the EMU and is not affected by LESENSE
	1	DUTYCYCI	LE	Bias module duty cycled between low power and high accuracy mode
	2	HIGHACC		Bias module always in high accuracy mode

28.5.6 LESENSE_EVALCTRL - LESENSE Evaluation Control (Async Reg)

Offset	Bit Po	sition
0x014	31 30 29 28 28 27 27 27 27 27 27 27 27 27 27 27 27 27	7 4 4 5 4 6 7 7 7 8 8 8 9 9 4 8 8 9 9 9 9 10 </th
Reset		0000×0
Access		RW M
Name		WINSIZE NINSIZE

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	WINSIZE	0x0000	RW	Sliding Window and Step Detection Size
	In sliding window mod threshold for step dete		onfigures t	he window size. In step detection mode, this bitfield is used to configure the

28.5.7 LESENSE_PRSCTRL - PRS Control Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	8	7	9	5	4	က	7	1	0
Reset				•	•											0		•				0x00								00×0		<u> </u>
Access																₽						Z N								R W		
Name																DECCMPEN						DECCMPMASK								DECCMPVAL		

Bit	Name	Reset	Access	Description
31:17	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
16	DECCMPEN	0	RW	Enable PRS Output DECCMP
	Enables decoder sta	te compare mato	h PRS out	put
15:13	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	DECCMPMASK	0x00	RW	Decoder State Compare Value Mask
	Masks DECCMPVA	and DECSTATI	E for comp	arison
7:5	Reserved	To ensure contions	npatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
4:0	DECCMPVAL	0x00	RW	Decoder State Compare Value
	Triggers PRS output	when equal to D	ECSTATE	

28.5.8 LESENSE_CMD - Command Register (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	9	6	8	7	9	2	4	ဗ	2	_	0
Reset		'	'		'				•		•				'	'	•									•			0	0	0	0
Access																													W1	W1	W1	W1
Name																													CLEARBUF	DECODE	STOP	START

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	CLEARBUF	0	W1	Clear Result Buffer
	Set this bit to reset the	e read and write	pointers o	f the result buffer.
2	DECODE	0	W1	Start Decoder
	Set this bit to start the	LESENSE dec	oder.	
1	STOP	0	W1	Stop Scanning of Sensors
	Set this bit to stop LE	SENSE. If issue	d during a	scan, the command will take effect after scan completion.
0	START	0	W1	Start Scanning of Sensors
	Set this bit to start LE	SENSE.		

28.5.9 LESENSE_CHEN - Channel Enable Register (Async Reg)

Offset															Bi	t Po	sitio	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	14	13	12	7	10	စ	8	7	9	5	4	က	2	_	0
Reset																•								00000	00000							<u> </u>
Access																								2	2							
Name																								Z I								

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	CHEN	0x0000	RW	Enable Scan Channel
	Set bit X to enable ch	annel X		

28.5.10 LESENSE_SCANRES - Scan Result Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset			00000X0															1	ı		•		1		00000	•		,	•	1		
Access			RWH 0x00																					- 1	[} }							
Name								GICOTE	П Г																ב ב ב							

Bit	Name	Reset	Access	Description
31:16	STEPDIR	0x0000	RWH	Direction of Previous Step Detection
	In step detection mod	e, bit X will be s	et if a step	up was detected on channel X
15:0	SCANRES	0x0000	RWH	Scan Results
	Bit X will be set deper	nding on channe	l X evaluat	tion

28.5.11 LESENSE_STATUS - Status Register (Async Reg)

Offset	Bit Position					
0x028	33 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3	5	4	3	2 -	0
Reset		0	0	0	0 0	0
Access		Я	2	В	<u>م</u> م	2
Name		DACACTIVE	SCANACTIVE	RUNNING	BUFFULL BUFHALFFULL	BUFDATAV

Bit	Name	Reset	Access	Description
Dit	Name	Neset	A00033	Description
31:6	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	DACACTIVE	0	R	LESENSE VDAC Interface is Active
	LESENSE is currently	using the VDA	C.	
4	SCANACTIVE	0	R	LESENSE Scan Active
	LESENSE is currently	/ interfacing to s	ensors.	
3	RUNNING	0	R	LESENSE Periodic Counter Running
	LESENSE is running	in periodic mode	€.	
2	BUFFULL	0	R	Result Buffer Full
	Set when the result b	uffer is full		
1	BUFHALFFULL	0	R	Result Buffer Half Full
	Set when the result b	uffer is half full		
0	BUFDATAV	0	R	Result Data Valid
	Set when data is avai	lable in the resu	It buffer. C	leared when the buffer is empty.

28.5.12 LESENSE_PTR - Result Buffer Pointers (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	sitic	on														
0x02C	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	- (0
Reset																										2	2			OXO	2	
Access																										۵	<u> </u>			Ω	<u> </u>	
Name																										0/	<u>{</u>			2	2	

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:4	WR	0x0	R	Result Buffer Write Pointer
	These bits show the r	next index in the	result buff	er to be written to. Incremented when LESENSE writes to result buffer
3:0	RD	0x0	R	Result Buffer Read Pointer
	These bits show the in	ndex of the olde	st unread o	data in the result buffer. Incremented on read from BUFDATA.

28.5.13 LESENSE_BUFDATA - Result Buffer Data Register (Async Reg) (Actionable Reads)

Offset	Bit Position
0x030	31 31 31 31 31 31 31 31 31 31 31 31 31 3
Reset	XXXXXX
Access	α α
Name	BUFDATASRC

Bit	Name	Reset	Access	Description
31:20	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
19:16	BUFDATASRC	0xX	R	Result Data Source
	This bitfield contains	the channel ind	ex for the s	ensor result in BUFDATA.
15:0	BUFDATA	0xXXXX	R	Result Data
	This register can be	used to read the	e oldest unre	ead data from the result buffer.

28.5.14 LESENSE_CURCH - Current Channel Index (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Ві	t Po	siti	on														
0x034	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																														2	2	
Access																														Ω	<u> </u>	
Name																														HUGI		

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	CURCH	0x0	R	Current Channel Index
	Shows the index of the	ne current chanr	nel	

28.5.15 LESENSE_DECSTATE - Current Decoder State (Async Reg)

Offset															Bi	t Po	siti	on														
0x038	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset		•		•	•				•			•	•			•		•					•	•	•	•	•		•	00X0		
Access																														RWH		
Name																														DECSTATE		

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
4:0	DECSTATE	0x00	RWH	Current Decoder State
	Shows the current de	coder state		

28.5.16 LESENSE_SENSORSTATE - Decoder Input Register (Async Reg)

Offset															Bi	t Po	siti	on														
0x03C	31	30	29	78	27	56	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	- 0	,
Reset																														0x0		
Access																														RWH		_
Name																														SENSORSTATE		_

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure co tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	SENSORSTATE	0x0	RWH	Decoder Input Register
	Shows the status of	sensors chosen	as input to	the decoder

28.5.17 LESENSE_IDLECONF - GPIO Idle Phase Configuration (Async Reg)

Offset															Bi	t Po	sitio	on														
0x040	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	11	10	6	8	7	9	5	4	က	2	-	0
Reset	OXO	000	OAO	OXO	2	OXO	2	S S	3	OX O	2	OX O	2	2	2	2	2	2	2	3	UAU	3	>	2	Ovo	8	2	2	2	040	000	
Access	NA NA		/\/Q	<u>}</u>	7/0	<u>}</u>	Š	≥ Y	2	<u>}</u>	2	<u>}</u>	<u> </u>	<u>}</u>	Š	2	Š	2	Š	2	Wa	2	Š	2	W	2	Š	2	7	<u> </u>	RW	
Name	CH15	-	717	_	7	_]	<u> </u>	2	_		_	OH C	=	ă	2	7H7	<u>-</u>	OH O	2	SHO	-	ZHZ	=	٤НЭ	-	CHO	_	Ç	-	CHO	

	CH7	- 당	공	공	공	공	CH3	SHS	CH7	СН6	CHE	Š	SH3	CHS	공	공
Bit	Name			Reset		Access	Des	cription								
31:30	CH15			0x0		RW	Cha	nnel 15	ldle Ph	ase Co	nfigurat	ion				
	This bit	field de	termine	s how th	e chan	nel is con	figured	during t	he idle	phase						
	Value			Mode			Des	cription								
	0			DISAB	LE		CH1	5 outpu	t is disal	oled in i	dle phas	е				
	1			HIGH			CH1	5 outpu	t is high	in idle p	hase					
	2			LOW			CH1	5 outpu	t is low i	n idle pl	nase					
	3			DAC				5 outpure is only							ote that	this
29:28	CH14			0x0		RW	Cha	nnel 14	ldle Ph	ase Co	nfigurat	ion				
	This bit	field de	termine	s how th	e chan	nel is con	figured	during t	he idle	phase						
	Value			Mode			Des	cription								
	0			DISAB	LE		CH1	4 outpu	t is disal	oled in i	dle phas	е				
	1			HIGH			CH1	4 outpu	t is high	in idle p	hase					
	2			LOW			CH1	4 outpu	t is low i	n idle pl	nase					
	3			DAC				4 outpure is only							ote that	this
				0x0		RW	Cha	nnel 13	ldle Ph	ase Co	nfigurat	ion				
27:26	CH13															
27:26		field de	termine	s how th	e chan	nel is con	figured	during t	he idle	phase						
27:26		field de	termine	s how th	e chan	nel is con		during t	he idle	ohase						
27:26	This bit	field de	termine			nel is con	Des				dle phas	e				
27:26	This bit	field de	termine	Mode		nel is cont	Des	cription	t is disal	oled in i	-	е				
27:26	This bit Value	field de	termine	Mode DISAB		nel is cont	Des CH1	cription 3 output	t is disal	oled in i	hase	е				
27:26	This bit Value 0	field de	termine	Mode DISAB HIGH		nel is cont	Desc CH1 CH1 CH1	cription 3 output 3 output	t is disal t is high t is low i	oled in io in idle p n idle pl	hase nase VDAC	output i			ote that	this
27:26	Value 0 1 2	field de	termine	Mode DISAB HIGH LOW		nel is cont	Desc CH1 CH1 CH1 CH1	cription 3 output 3 output 3 output 3 output	t is disal t is high t is low i t is conr r availat	oled in ion in idle plants of the plants of	ohase nase o VDAC nannels	output i 4, 5, 7,			ote that	this
	Value 0 1 2 3 CH12			Mode DISAB HIGH LOW DAC	LE		Desc CH1 CH1 CH1 CH1 mod	cription 3 output 3 output 3 output 3 output e is only	t is disal t is high t is low i t is conr v availab	oled in ion in idle properties to the interest of the interest	ohase nase o VDAC nannels	output i 4, 5, 7,			ote that	this

Bit	Name	Reset Access	Description
	0	DISABLE	CH12 output is disabled in idle phase
	1	HIGH	CH12 output is high in idle phase
	2	LOW	CH12 output is low in idle phase
	3	DAC	CH12 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
23:22	CH11	0x0 RW	Channel 11 Idle Phase Configuration
	This bitfield dete	ermines how the channel is con	figured during the idle phase
	Value	Mode	Description
	0	DISABLE	CH11 output is disabled in idle phase
	1	HIGH	CH11 output is high in idle phase
	2	LOW	CH11 output is low in idle phase
	3	DAC	CH11 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
21:20	CH10	0x0 RW	Channel 10 Idle Phase Configuration
	This bitfield dete	ermines how the channel is con	figured during the idle phase
	Value	Mode	Description
	0	DISABLE	CH10 output is disabled in idle phase
	1	HIGH	CH10 output is high in idle phase
	2	LOW	CH10 output is low in idle phase
	3	DAC	CH10 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
19:18	CH9	0x0 RW	Channel 9 Idle Phase Configuration
	This bitfield dete	ermines how the channel is con	figured during the idle phase
	Value	Mode	Description
	0	DISABLE	CH9 output is disabled in idle phase
	1	HIGH	CH9 output is high in idle phase
	2	LOW	CH9 output is low in idle phase
	3	DAC	CH9 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
17:16	CH8	0x0 RW	Channel 8 Idle Phase Configuration
		ermines how the channel is con	•
	Value	Mode	Description
	0	DISABLE	CH8 output is disabled in idle phase
	1	HIGH	CH8 output is high in idle phase
	2	LOW	CH8 output is low in idle phase
	3	DAC	CH8 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13

Bit	Name	Reset	Access	Description
15:14	CH7	0x0	RW	Channel 7 Idle Phase Configuration
	This bitfield determin	es how the chan	nel is confi	gured during the idle phase
	Value	Mode		Description
	0	DISABLE		CH7 output is disabled in idle phase
	1	HIGH		CH7 output is high in idle phase
	2	LOW		CH7 output is low in idle phase
	3	DAC		CH7 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
13:12	CH6	0x0	RW	Channel 6 Idle Phase Configuration
	This bitfield determin	es how the chan	nel is confi	gured during the idle phase
	Value	Mode		Description
	0	DISABLE		CH6 output is disabled in idle phase
	1	HIGH		CH6 output is high in idle phase
	2	LOW		CH6 output is low in idle phase
	3	DAC		CH6 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
11:10	CH5	0x0	RW	Channel 5 Idle Phase Configuration
	This bitfield determin	es how the chan	nel is confi	gured during the idle phase
	Value	Mode		Description
	0	DISABLE		CH5 output is disabled in idle phase
	1	HIGH		CH5 output is high in idle phase
	2	LOW		CH5 output is low in idle phase
	3	DAC		CH5 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
9:8	CH4	0x0	RW	Channel 4 Idle Phase Configuration
	This bitfield determin	es how the chan	nel is confi	gured during the idle phase
	Value	Mode		Description
	0	DISABLE		CH4 output is disabled in idle phase
	1	HIGH		CH4 output is high in idle phase
	2	LOW		CH4 output is low in idle phase
	3	DAC		CH4 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
7:6	CH3	0x0	RW	Channel 3 Idle Phase Configuration
	This bitfield determin	es how the chan	nel is confi	gured during the idle phase
	Value	Mode		Description
	0	DISABLE		CH3 output is disabled in idle phase

Bit	Name	Reset Ac	cess Description
	1	HIGH	CH3 output is high in idle phase
	2	LOW	CH3 output is low in idle phase
	3	DAC	CH3 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
5:4	CH2	0x0 RW	Channel 2 Idle Phase Configuration
	This bitfield det	ermines how the channel is	configured during the idle phase
	Value	Mode	Description
	0	DISABLE	CH2 output is disabled in idle phase
	1	HIGH	CH2 output is high in idle phase
	2	LOW	CH2 output is low in idle phase
	3	DAC	CH2 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
3:2	CH1	0x0 RW	Channel 1 Idle Phase Configuration
	This bitfield det	ermines how the channel is	configured during the idle phase
	Value	Mode	Description
	0	DISABLE	CH1 output is disabled in idle phase
	0	DISABLE HIGH	CH1 output is disabled in idle phase CH1 output is high in idle phase
			<u> </u>
	1	HIGH	CH1 output is high in idle phase CH1 output is low in idle phase
1:0	1 2	HIGH LOW	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
1:0	1 2 3 CH0	HIGH LOW DAC	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13
1:0	1 2 3 CH0	HIGH LOW DAC	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13 Channel 0 Idle Phase Configuration
1:0	1 2 3 CH0 This bitfield det	HIGH LOW DAC 0x0 RW ermines how the channel is	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13 Channel 0 Idle Phase Configuration configured during the idle phase
1:0	1 2 3 CH0 This bitfield det	HIGH LOW DAC 0x0 RW ermines how the channel is	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13 Channel 0 Idle Phase Configuration configured during the idle phase Description
1:0	1 2 3 CH0 This bitfield detection	HIGH LOW DAC 0x0 RW ermines how the channel is Mode DISABLE	CH1 output is high in idle phase CH1 output is low in idle phase CH1 output is connected to VDAC output in idle phase. Note that this mode is only available on channels 4, 5, 7, 10, 12, 13 Channel 0 Idle Phase Configuration configured during the idle phase Description CH0 output is disabled in idle phase

28.5.18 LESENSE_ALTEXCONF - Alternative Excite Pin Configuration (Async Reg)

Offset															Ві	t Po	siti	on													
0x044	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	- 0
Reset			•		•		•		0	0	0	0	0	0	0	0	ç	S S	0	0000	ç) X	0) X	2	OX O	Ş	2	2	OK)	0×0
Access									₹	RW	S.	S N N	S.	S N	₩ M	S N	2	<u>}</u>	i	≩	2	<u>}</u>	i	≩	2	<u>}</u>	2	2	2	2	R W
Name								AEX7	AEX6	AEX5	AEX4	AEX3	AEX2	AEX1	AEX0	14000	IDLECOINF.		IDLECONF6	U) L		IDLECONF4					IDI ECONE1		IDLECONF0	

		4	4 4 4	اعام	4 4 =	: =	=	=	=	=	=	=
Bit	Name	Reset	Acces	s Desc	ription							
31:24	Reserved	To ensure c tions	ompatibility	y with futu	ıre devices	s, always w	rite bits t	to 0. Mo	re infori	mation ir	1.2 Co	nven-
23	AEX7	0	RW	ALTE	X7 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX7 regard	lless of wh	at channe	el is active							
22	AEX6	0	RW	ALTE	X6 Always	S Excite E	nable					
	Set this bit to excit	e ALTEX6 regard	lless of wh	at channe	el is active							
21	AEX5	0	RW	ALTE	X5 Always	S Excite E	nable					
	Set this bit to excit	e ALTEX5 regard	lless of wh	at channe	el is active							
20	AEX4	0	RW	ALTE	X4 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX4 regard	lless of wh	at channe	l is active							
19	AEX3	0	RW	ALTE	X3 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX3 regard	lless of wh	at channe	el is active							
18	AEX2	0	RW	ALTE	X2 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX2 regard	lless of wh	at channe	el is active							
17	AEX1	0	RW	ALTE	X1 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX1 regard	lless of wh	at channe	l is active							
16	AEX0	0	RW	ALTE	X0 Always	s Excite E	nable					
	Set this bit to excit	e ALTEX0 regard	lless of wh	at channe	l is active							
15:14	IDLECONF7	0x0	RW	ALTE	X7 Idle Ph	ase Confi	guration	1				
	This bitfield determ	nines how the alte	ernate exci	te pin is c	onfigured o	during the	idle phas	se				
	Value	Mode		Descr	ription							
	0	DISABLE		ALTE	X7 output i	s disabled	in idle pl	hase				
	1	HIGH		ALTE	X7 output i	s high in ic	lle phase	;				
	2	LOW		ALTE	X7 output i	s low in idl	e phase					
13:12	IDLECONF6	0x0	RW	ALTE	X6 Idle Ph	ase Confi	guration	1				
	This bitfield determ	nines how the alte	ernate exci	te pin is c	onfigured o	during the	idle phas	se				

D.1	N		
Bit	Name	Reset Acc	
	Value	Mode	Description
	0	DISABLE	ALTEX6 output is disabled in idle phase
	1	HIGH	ALTEX6 output is high in idle phase
	2	LOW	ALTEX6 output is low in idle phase
11:10	IDLECONF5	0x0 RW	ALTEX5 Idle Phase Configuration
	This bitfield determine	es how the alternate e	cite pin is configured during the idle phase
	Value	Mode	Description
	0	DISABLE	ALTEX5 output is disabled in idle phase
	1	HIGH	ALTEX5 output is high in idle phase
	2	LOW	ALTEX5 output is low in idle phase
9:8	IDLECONF4	0x0 RW	ALTEX4 Idle Phase Configuration
	This bitfield determine	es how the alternate e	cite pin is configured during the idle phase
	Value	Mode	Description
	0	DISABLE	ALTEX4 output is disabled in idle phase
	1	HIGH	ALTEX4 output is high in idle phase
	2	LOW	ALTEX4 output is low in idle phase
7:6	IDLECONF3	0x0 RW	ALTEX3 Idle Phase Configuration
	This bitfield determine	es how the alternate e	cite pin is configured during the idle phase
	Value	Mode	Description
	0	DISABLE	ALTEX3 output is disabled in idle phase
	1	HIGH	ALTEX3 output is high in idle phase
	2	LOW	ALTEX3 output is low in idle phase
5:4	IDLECONF2	0x0 RW	ALTEX2 Idle Phase Configuration
	This bitfield determine	es how the alternate e	cite pin is configured during the idle phase
	Value	Mode	Description
	0	DISABLE	ALTEX2 output is disabled in idle phase
	1	HIGH	ALTEX2 output is high in idle phase
	2	LOW	ALTEX2 output is low in idle phase
3:2	IDLECONF1	0x0 RW	ALTEX1 Idle Phase Configuration
	This bitfield determine	es how the alternate e	cite pin is configured during the idle phase
	Value	Mode	Description
	0	DISABLE	ALTEX1 output is disabled in idle phase
	1	HIGH	ALTEX1 output is high in idle phase
	2	LOW	ALTEX1 output is low in idle phase

Bit	Name	Reset	Access	Description
1:0	IDLECONF0	0x0	RW	ALTEX0 Idle Phase Configuration
	This bitfield determin	es how the alter	nate excite	pin is configured during the idle phase
	Value	Mode		Description
	0	DISABLE		ALTEX0 output is disabled in idle phase
	1	HIGH		ALTEX0 output is high in idle phase
	2	LOW		ALTEX0 output is low in idle phase

28.5.19 LESENSE_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•							0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access										~	22	22	22	22	22	22	22	~	22	22	22	22	22	22	22	22	~	22	22	~	22	œ
Name										CNTOF	BUFOF	BUFLEVEL	BUFDATAV	DECERR	DEC	SCANCOMPLETE	CH15	CH14	CH13	CH12	CH11	CH10	СНЭ	СН8	CH7	СН6	CH5	CH4	СНЗ	CH2	CH1	СНО

Bit	Name	Reset	Access	Description
31:23	Reserved	To ensure tions	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
22	CNTOF	0	R	CNTOF Interrupt Flag
	Set when the LESE	NSE counter o	verflows.	
21	BUFOF	0	R	BUFOF Interrupt Flag
	Set when the result	buffer overflow	vs	
20	BUFLEVEL	0	R	BUFLEVEL Interrupt Flag
	Set when the data b	ouffer is full.		
19	BUFDATAV	0	R	BUFDATAV Interrupt Flag
	Set when data is av	ailable in the re	esult buffer.	
18	DECERR	0	R	DECERR Interrupt Flag
	Set when the decod	ler detects an e	error	
17	DEC	0	R	DEC Interrupt Flag
	Set when the decod	ler has issued	an interrupt re	quest
16	SCANCOMPLETE	0	R	SCANCOMPLETE Interrupt Flag
	Set when a scan se	quence is com	pleted	
15	CH15	0	R	CH15 Interrupt Flag
	Set when channel 1	5 triggers		
14	CH14	0	R	CH14 Interrupt Flag
	Set when channel 1	4 triggers		
13	CH13	0	R	CH13 Interrupt Flag
	Set when channel 1	3 triggers		
12	CH12	0	R	CH12 Interrupt Flag
	Set when channel 1	2 triggers		
11	CH11	0	R	CH11 Interrupt Flag
	Set when channel 1	1 triggers		
10	CH10	0	R	CH10 Interrupt Flag
	Set when channel 1	0 triggers		

Bit	Name	Reset	Access	Description
9	CH9	0	R	CH9 Interrupt Flag
	Set when cha	nnel 9 triggers		
8	CH8	0	R	CH8 Interrupt Flag
	Set when cha	annel 8 triggers		
7	CH7	0	R	CH7 Interrupt Flag
	Set when cha	annel 7 triggers		
6	CH6	0	R	CH6 Interrupt Flag
	Set when cha	annel 6 triggers		
5	CH5	0	R	CH5 Interrupt Flag
	Set when cha	annel 5 triggers		
4	CH4	0	R	CH4 Interrupt Flag
	Set when cha	annel 4 triggers		
3	CH3	0	R	CH3 Interrupt Flag
	Set when cha	annel 3 triggers		
2	CH2	0	R	CH2 Interrupt Flag
	Set when cha	annel 2 triggers		
1	CH1	0	R	CH1 Interrupt Flag
	Set when cha	annel 1 triggers		
0	CH0	0	R	CH0 Interrupt Flag
	Set when cha	annel 0 triggers		

28.5.20 LESENSE_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x054	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset				'	'					0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access										W	W W	W W	×	W W	W W	W W	W	×	W	X	W	W W	W W	N K	W W	W K	W W	W W	W	W1	N N	M
Name										CNTOF	BUFOF	BUFLEVEL	BUFDATAV	DECERR	DEC	SCANCOMPLETE	CH15	CH14	CH13	CH12	CH11	CH10	СНЭ	CH8	CH7	СН6	CH5	CH4	CH3	CH2	CH1	СНО

Bit	Name	Reset	Access	Description
31:23	Reserved	To ensure comp tions	patibility v	vith future devices, always write bits to 0. More information in 1.2 Conven-
22	CNTOF	0	W1	Set CNTOF Interrupt Flag
	Write 1 to set the CN	TOF interrupt flag		
21	BUFOF	0	W1	Set BUFOF Interrupt Flag
	Write 1 to set the BUI	FOF interrupt flag		
20	BUFLEVEL	0	W1	Set BUFLEVEL Interrupt Flag
	Write 1 to set the BUI	FLEVEL interrupt	flag	
19	BUFDATAV	0	W1	Set BUFDATAV Interrupt Flag
	Write 1 to set the BUI	FDATAV interrupt	flag	
18	DECERR	0	W1	Set DECERR Interrupt Flag
	Write 1 to set the DE	CERR interrupt fla	ıg	
17	DEC	0	W1	Set DEC Interrupt Flag
	Write 1 to set the DE	C interrupt flag		
16	SCANCOMPLETE	0	W1	Set SCANCOMPLETE Interrupt Flag
	Write 1 to set the SC	ANCOMPLETE in	terrupt fla	g
15	CH15	0	W1	Set CH15 Interrupt Flag
	Write 1 to set the CH	15 interrupt flag		
14	CH14	0	W1	Set CH14 Interrupt Flag
	Write 1 to set the CH	14 interrupt flag		
13	CH13	0	W1	Set CH13 Interrupt Flag
	Write 1 to set the CH	13 interrupt flag		
12	CH12	0	W1	Set CH12 Interrupt Flag
	Write 1 to set the CH	12 interrupt flag		
11	CH11	0	W1	Set CH11 Interrupt Flag
	Write 1 to set the CH	11 interrupt flag		

Bit	Name	Reset	Access	Description	
10	CH10	0	W1	Set CH10 Interrupt Flag	
	Write 1 to set	the CH10 interrupt flag			
9	CH9	0	W1	Set CH9 Interrupt Flag	
	Write 1 to set	the CH9 interrupt flag			
8	CH8	0	W1	Set CH8 Interrupt Flag	
	Write 1 to set	the CH8 interrupt flag			
7	CH7	0	W1	Set CH7 Interrupt Flag	
	Write 1 to set	the CH7 interrupt flag			
6	CH6	0	W1	Set CH6 Interrupt Flag	
	Write 1 to set	the CH6 interrupt flag			
5	CH5	0	W1	Set CH5 Interrupt Flag	
	Write 1 to set	the CH5 interrupt flag			
4	CH4	0	W1	Set CH4 Interrupt Flag	
	Write 1 to set	the CH4 interrupt flag			
3	CH3	0	W1	Set CH3 Interrupt Flag	
	Write 1 to set	the CH3 interrupt flag			
2	CH2	0	W1	Set CH2 Interrupt Flag	
	Write 1 to set	the CH2 interrupt flag			
1	CH1	0	W1	Set CH1 Interrupt Flag	
	Write 1 to set	the CH1 interrupt flag			
0	CH0	0	W1	Set CH0 Interrupt Flag	
	Write 1 to set	the CH0 interrupt flag			

28.5.21 LESENSE_IFC - Interrupt Flag Clear Register

Offset														Bi	t Po	sitio	on														
0x058	31	59	28	27	26	25	24	23	22	21	20	9	8	17	16	15	4	13	12	11	10	6	œ	7	9	5	4	က	2	_	0
Reset									0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access									(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name									CNTOF	BUFOF	BUFLEVEL	BUFDATAV	DECERR	DEC	SCANCOMPLETE	CH15	CH14	CH13	CH12	CH11	CH10	СНЭ	СН8	CH7	СН6	CH5	CH4	СНЗ	CH2	CH1	СНО
Bit	Name					Re	set			Ac	ces	s I	Des	crip	tion																
31:23	Reser	ved				To tion	ensi 1s	ıre	com	pati	bility	y wit	th fu	ture	dev	rices	s, alı	vay:	s wr	ite b	its t	o 0.	Мог	re in	forn	natio	on in	1.2	. Coi	nvei	า-
22	CNTO	F				0				(R)	W1	(Clea	ır Cl	NTC	F Ir	iteri	rupt	Fla	g											
	Write '(This f												ret	urns	the	valı	ue o	f the	e IF	and	clea	ars t	he c	corre	espc	ndir	ng ir	iterr	upt 1	lags	8
21	BUFO	F				0				(R)	W1	(Clea	ır Bl	UFC	F Ir	iteri	rupt	Fla	g											
	Write '(This f												ı reti	urns	the	valu	ue o	f the	e IF	and	clea	ars t	he c	orre	espo	ndir	ng in	iterr	upt f	lags	3
20	BUFLE	EVEL	-			0				(R)	W1	(Clea	ır Bl	UFL	EVE	EL II	nter	rup	Fla	g										
	Write flags (retu	urns	the	valı	ue o	f the	e IF	and	clea	ars t	he c	corre	espo	ndir	ng in	iterri	upt	
19	BUFD	ATA۱	V			0				(R)	W1	(Clea	ır Bl	UFD	ATA	AV I	nter	rup	t Fla	ag										
	Write flags (urns	the	val	ue c	of th	e IF	and	cle	ars t	the o	corr	espo	ondi	ng ii	nterr	upt	
18	DECE	RR				0				(R)	W1	(Clea	ır Di	ECE	RR	Inte	erru	pt F	lag											
	Write '(This f												ng re	eturr	ns th	ne va	alue	of t	he I	F an	d cl	ears	s the	e cor	rres	pond	ding	inte	rrup	t fla	gs
17	DEC					0				(R)	W1	(Clea	ır Di	EC I	ntei	rrup	t Fla	ag												
	Write feature											g re	turn	s the	e va	lue (of th	e IF	and	d cle	ars	the	corr	esp	ond	ing i	nter	rupt	flag	s (T	his
16	SCAN	COM	1PLE	ETE		0				(R)	W1	(Clea	ır S(CAN	ICO	MPI	_ET	E In	terr	upt	Flag	g								
	Write rupt fla															retu	rns	the	valu	e of	the	IF a	and (clea	rs th	ne c	orre	spoi	ndin	g int	er-
15	CH15					0				(R)	W1	(Clea	ır Cl	H15	Inte	erru	pt F	lag												
	Write '(This f												etur	ns th	ne v	alue	of t	he I	F ar	nd cl	ears	s the	e cor	rres	pon	ding	inte	errup	t fla	gs	
14	CH14			-		0			-	(R)	W1	(Clea	ır Cl	H14	Inte	erru	pt F	lag		-									-	_
	Write (This f												etur	ns th	ne v	alue	of t	he I	F ar	nd cl	ears	s the	e cor	rres	pone	ding	inte	errup	t fla	gs	

Bit	Name	Reset	Accoss	Description
13	CH13	0	Access (R)W1	Clear CH13 Interrupt Flag
15	Write 1 to clear the		ı. Reading	returns the value of the IF and clears the corresponding interrupt flags
12	CH12	0	(R)W1	Clear CH12 Interrupt Flag
		e CH12 interrupt flag be enabled globally		returns the value of the IF and clears the corresponding interrupt flags
11	CH11	0	(R)W1	Clear CH11 Interrupt Flag
		e CH11 interrupt flag be enabled globally		returns the value of the IF and clears the corresponding interrupt flags
10	CH10	0	(R)W1	Clear CH10 Interrupt Flag
		e CH10 interrupt flag be enabled globally		returns the value of the IF and clears the corresponding interrupt flags
9	CH9	0	(R)W1	Clear CH9 Interrupt Flag
		e CH9 interrupt flag. nabled globally in MS		eturns the value of the IF and clears the corresponding interrupt flags (This
8	CH8	0	(R)W1	Clear CH8 Interrupt Flag
		e CH8 interrupt flag. nabled globally in M\$		eturns the value of the IF and clears the corresponding interrupt flags (This
7	CH7	0	(R)W1	Clear CH7 Interrupt Flag
		e CH7 interrupt flag. nabled globally in MS		eturns the value of the IF and clears the corresponding interrupt flags (This
6	CH6	0	(R)W1	Clear CH6 Interrupt Flag
		e CH6 interrupt flag. nabled globally in M\$		eturns the value of the IF and clears the corresponding interrupt flags (This
5	CH5	0	(R)W1	Clear CH5 Interrupt Flag
		e CH5 interrupt flag. nabled globally in M\$		eturns the value of the IF and clears the corresponding interrupt flags (This
4	CH4	0	(R)W1	Clear CH4 Interrupt Flag
		e CH4 interrupt flag. nabled globally in MS		eturns the value of the IF and clears the corresponding interrupt flags (This
3	CH3	0	(R)W1	Clear CH3 Interrupt Flag
		e CH3 interrupt flag. nabled globally in MS		eturns the value of the IF and clears the corresponding interrupt flags (This
2	CH2	0	(R)W1	Clear CH2 Interrupt Flag
		e CH2 interrupt flag. nabled globally in M\$		eturns the value of the IF and clears the corresponding interrupt flags (This
1	CH1	0	(R)W1	Clear CH1 Interrupt Flag
		e CH1 interrupt flag. nabled globally in MS		eturns the value of the IF and clears the corresponding interrupt flags (This
0	CH0	0	(R)W1	Clear CH0 Interrupt Flag
		e CH0 interrupt flag. nabled globally in M\$		eturns the value of the IF and clears the corresponding interrupt flags (This

28.5.22 LESENSE_IEN - Interrupt Enable Register

Offset															Ві	it Po	siti	on														
0x05C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset			'	•						0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access										RW	₩ M	R M	₩	₽	₩ M	S.	RW	₽	RW	₩ M	RW	₩ M	R M	R M	Z N	R M	R M	RW	₩.	RW	₩ M	RW
Name										CNTOF	BUFOF	BUFLEVEL	BUFDATAV	DECERR	DEC	SCANCOMPLETE	CH15	CH14	CH13	CH12	CH11	CH10	СНЭ	CH8	CH7	СН6	CH5	CH4	СНЗ	CH2	CH1	СНО

		_		
Bit	Name	Reset	Access	Description
31:23	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
22	CNTOF	0	RW	CNTOF Interrupt Enable
	Enable/disable the C	NTOF interrupt		
21	BUFOF	0	RW	BUFOF Interrupt Enable
	Enable/disable the B	UFOF interrupt		
20	BUFLEVEL	0	RW	BUFLEVEL Interrupt Enable
	Enable/disable the B	UFLEVEL interru	ıpt	
19	BUFDATAV	0	RW	BUFDATAV Interrupt Enable
	Enable/disable the B	UFDATAV interr	upt	
18	DECERR	0	RW	DECERR Interrupt Enable
	Enable/disable the D	ECERR interrup	t	
17	DEC	0	RW	DEC Interrupt Enable
	Enable/disable the D	EC interrupt		
16	SCANCOMPLETE	0	RW	SCANCOMPLETE Interrupt Enable
	Enable/disable the S	CANCOMPLETE	E interrupt	
15	CH15	0	RW	CH15 Interrupt Enable
	Enable/disable the C	H15 interrupt		
14	CH14	0	RW	CH14 Interrupt Enable
	Enable/disable the C	H14 interrupt		
13	CH13	0	RW	CH13 Interrupt Enable
	Enable/disable the C	H13 interrupt		
12	CH12	0	RW	CH12 Interrupt Enable
	Enable/disable the C	H12 interrupt		
11	CH11	0	RW	CH11 Interrupt Enable
	Enable/disable the C	H11 interrupt		

Bit	Name	Reset	Access	Description
10	CH10	0	RW	CH10 Interrupt Enable
	Enable/disable the C	H10 interrupt		
9	CH9	0	RW	CH9 Interrupt Enable
	Enable/disable the C	H9 interrupt		
8	CH8	0	RW	CH8 Interrupt Enable
	Enable/disable the C	H8 interrupt		
7	CH7	0	RW	CH7 Interrupt Enable
	Enable/disable the C	H7 interrupt		
6	CH6	0	RW	CH6 Interrupt Enable
	Enable/disable the C	H6 interrupt		
5	CH5	0	RW	CH5 Interrupt Enable
	Enable/disable the C	H5 interrupt		
4	CH4	0	RW	CH4 Interrupt Enable
	Enable/disable the C	H4 interrupt		
3	CH3	0	RW	CH3 Interrupt Enable
	Enable/disable the C	H3 interrupt		
2	CH2	0	RW	CH2 Interrupt Enable
	Enable/disable the C	H2 interrupt		
1	CH1	0	RW	CH1 Interrupt Enable
	Enable/disable the C	H1 interrupt		
0	CH0	0	RW	CH0 Interrupt Enable
	Enable/disable the C	H0 interrupt		

28.5.23 LESENSE_SYNCBUSY - Synchronization Busy Register

Offset															Ві	it P	ositi	on														
0x060	33	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	5 5	4	13	12	7	10	6	8	7	9	2	4	က	2	1	0
Reset		•	•		•	•	•	•	•		•			·	•	•	•		•	•					0		•			•		
Access																									Я							
Name																									CMD							
																									O							

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7	CMD	0	R	CMD Register Busy
	Set when the value w	ritten to CMD is	being synd	chronized.
6:0	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-

28.5.24 LESENSE_ROUTEPEN - I/O Routing Register (Async Reg)

Offset															Ві	t Po	siti	on														
0x064	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset					•		•	•	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
Access									₽	₽	W.	₽	Z.	₽	Z.	₽	₽	₽	R M	₽	R M	₽	₽	₽	₽	₽	₽	₽	₽	RW	X ≪	RW W
Name									ALTEX7PEN	ALTEX6PEN	ALTEX5PEN	ALTEX4PEN	ALTEX3PEN	ALTEX2PEN	ALTEX1PEN	ALTEXOPEN	CH15PEN	CH14PEN	CH13PEN	CH12PEN	CH11PEN	CH10PEN	CH9PEN	CH8PEN	CH7PEN	CH6PEN	CH5PEN	CH4PEN	CH3PEN	CH2PEN	CH1PEN	CH0PEN

		ALT		
Bit	Name	Reset	Access	Description
31:24	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
23	ALTEX7PEN	0	RW	ALTEX7 Pin Enable
	Set this bit to enable	LESENSE ALT	EX7 pin	
22	ALTEX6PEN	0	RW	ALTEX6 Pin Enable
	Set this bit to enable	LESENSE ALT	EX6 pin	
21	ALTEX5PEN	0	RW	ALTEX5 Pin Enable
	Set this bit to enable	LESENSE ALT	EX5 pin	
20	ALTEX4PEN	0	RW	ALTEX4 Pin Enable
	Set this bit to enable	LESENSE ALT	EX4 pin	
19	ALTEX3PEN	0	RW	ALTEX3 Pin Enable
	Set this bit to enable	LESENSE ALT	EX3 pin	
18	ALTEX2PEN	0	RW	ALTEX2 Pin Enable
	Set this bit to enable	LESENSE ALT	EX2 pin	
17	ALTEX1PEN	0	RW	ALTEX1 Pin Enable
	Set this bit to enable	LESENSE ALT	EX1 pin	
16	ALTEX0PEN	0	RW	ALTEX0 Pin Enable
	Set this bit to enable	LESENSE ALT	EX0 pin	
15	CH15PEN	0	RW	CH15 Pin Enable
	Set this bit to enable	LESENSE CH1	5 pin	
14	CH14PEN	0	RW	CH14 Pin Enable
	Set this bit to enable	LESENSE CH1	4 pin	
13	CH13PEN	0	RW	CH13 Pin Enable
	Set this bit to enable	LESENSE CH1	3 pin	
12	CH12PEN	0	RW	CH12 Pin Enable
	Set this bit to enable	LESENSE CH1	2 pin	
11	CH11PEN	0	RW	CH11 Pin Enable
	Set this bit to enable	LESENSE CH1	1 pin	

Bit	Name	Reset	Access	Description
10	CH10PEN	0	RW	CH10 Pin Enable
	Set this bit to enable	LESENSE CH1	0 pin	
9	CH9PEN	0	RW	CH9 Pin Enable
	Set this bit to enable	LESENSE CH9	pin	
8	CH8PEN	0	RW	CH8 Pin Enable
	Set this bit to enable	LESENSE CH8	pin	
7	CH7PEN	0	RW	CH7 Pin Enable
	Set this bit to enable	LESENSE CH7	pin	
6	CH6PEN	0	RW	CH6 Pin Enable
	Set this bit to enable	LESENSE CH6	pin	
5	CH5PEN	0	RW	CH5 Pin Enable
	Set this bit to enable	LESENSE CH5	pin	
4	CH4PEN	0	RW	CH4 Pin Enable
	Set this bit to enable	LESENSE CH4	pin	
3	CH3PEN	0	RW	CH3 Pin Enable
	Set this bit to enable	LESENSE CH3	pin	
2	CH2PEN	0	RW	CH2 Pin Enable
	Set this bit to enable	LESENSE CH2	pin	
1	CH1PEN	0	RW	CH1 Pin Enable
	Set this bit to enable	LESENSE CH1	pin	
0	CH0PEN	0	RW	CH0 Pin Enable
	Set this bit to enable	LESENSE CH0	pin	

28.5.25 LESENSE_STx_TCONFA - State Transition Configuration a (Async Reg)

Offset															Bi	t Po	siti	on														
0x100	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			•		•					,		,			XXO		×	×				XXX	•	•		>	Š	•		× >	S	
Access															RW		RW	R M				Z N				2	<u>}</u>			<u> </u>	2	
Name															PRSACT		SETIF	CHAIN				NEXTSTATE				70	MASK			awo.	5	

				PRS	SEI	CH		<u> </u>	MA	Ō
Bit	Name	Reset	Access	Description	n					
31:19	Reserved	To ensure co	ompatibility v	with future de	vices	s, alwa	ays	write bits to 0. Moi	re information in	1.2 Conven-
18:16	PRSACT	0xX	RW	Configure	Tran	sition	ı A	ction		
	Configure which actio	n to perform w	hen sensor	state equals	COM	ΙP				
	DECCTRL_PRSCNT = 0									
	Mode	Value		Description						
	NONE	0		No PRS pu	lses	gener	ate	d		
	PRS0	1		Generate p	ulse	on LE	SP	RS0		
	PRS1	2		Generate p	ulse	on LE	SP	RS1		
	PRS01	3		Generate p	ulse	on LE	SP	RS0 and LESPRS	1	
	PRS2	4		Generate p	ulse	on LE	SP	RS2		
	PRS02	5		Generate p	ulse	on LE	SP	RS0 and LESPRS	2	
	PRS12	6		Generate p	ulse	on LE	SP	RS1 and LESPRS	2	
	PRS012	7		Generate p	ulse	on LE	SP	RS0, LESPRS1 ar	nd LESPRS2	
	DECCTRL_PRSCNT = 1									
	NONE	0		Do not cour	nt					
	UP	1		Count up						
	DOWN	2		Count dowr	ı					
	PRS2	4		Generate p	ulse	on LE	SP	RS2		
	UPANDPRS2	5		Count up a	nd ge	enerat	ер	ulse on LESPRS2		
	DOWNANDPRS2	6		Count dowr	n and	l gene	erat	e pulse on LESPR	S2.	
15	SETIF	Х	RW	Set Interru	pt FI	ag En	nab	le		
	Set interrupt flag when	n sensor state	equals COM	I P						
14	CHAIN	Х	RW	Enable Sta	te D	escrip	oto	r Chaining		
	When set, descriptor i	in the next loca	ation will also	be evaluate	d					

Bit	Name	Reset	Access	Description
13	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
12:8	NEXTSTATE	0xXX	RW	Next State Index
	Index of next state	to be entered if	the sensor st	ate equals COMP
7:4	MASK	0xX	RW	Sensor Mask
	Set bit X to exclude	e sensor X from	evaluation.	
3:0	COMP	0xX	RW	Sensor Compare Value
	State transition is to	riggered when se	ensor state e	quals COMP

28.5.26 LESENSE_STx_TCONFB - State Transition Configuration B (Async Reg)

For more information about asynchronous registers see 4.3 Access to Low Energy Peripherals (Asynchronous Registers).

Offset															Bi	t Po	siti	on														
0x104	31	30	29	28	27	26	25	24	23	22	2	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Reset					•										XXO		×					XXX0				>	ž			>	S	
Access															ΑX		W.					RW				2	≥ Y			M	2	
Name															PRSACT		SETIF					NEXTSTATE				70	MAUA					

				PRS	SET		X Z	MAS	CO
Bit	Name	Reset	Access	Description					
31:19	Reserved	To ensure tions	compatibility (with future dev	rice	s, alway	vs write bits to 0. Mo.	re information ir	1.2 Conven-
18:16	PRSACT	0xX	RW	Configure T	ran	sition	Action		
	Configure which action	n to perform	when sensor	state equals C	ON	1P			
	DECCTRL_PRSCNT = 0								
	Mode	Value		Description					
	NONE	0		No PRS puls	ses	genera	ted		
	PRS0	1		Generate pu	lse	on PRS	50		
	PRS1	2		Generate pu	lse	on PRS	S1		
	PRS01	3		Generate pu	lse	on PRS	S0 and PRS1		
	PRS2	4		Generate pu	lse	on PRS	52		
	PRS02	5		Generate pu	lse	on PRS	S0 and PRS2		
	PRS12	6		Generate pu	lse	on PRS	S1 and PRS2		
	PRS012	7		Generate pu	lse	on PRS	S0, PRS1 and PRS2		
	DECCTRL_PRSCNT = 1								
	NONE	0		Do not coun	t				
	UP	1		Count up					
	DOWN	2		Count down					
	PRS2	4		Generate pu	lse	on PRS	52		
	UPANDPRS2	5		Count up an	d g	enerate	pulse on PRS2.		
	DOWNANDPRS2	6		Count down	and	d gener	ate pulse on PRS2.		
15	SETIF	Х	RW	Set Interrup	t F	ag			
	Set interrupt flag whe	n sensor stat	e equals CON	ИP					
14:13	Reserved	To ensure	compatibility v	with future dev	ice:	s, alway	s write bits to 0. Mo	re information ir	1.2 Conven-

tions

Bit	Name	Reset	Access	Description								
12:8	NEXTSTATE	0xXX	RW	Next State Index								
	Index of next state	to be entered if	the sensor st	ate equals COMP								
7:4	MASK	0xX	RW	Sensor Mask								
	Set bit X to exclude	e sensor X from	evaluation.									
3:0	COMP	0xX	RW	Sensor Compare Value								
	State transition is t	tte transition is triggered when sensor state equals COMP										

28.5.27 LESENSE_BUFx_DATA - Scan Results (Async Reg)

Offset															Bi	t Po	sitio	on														
0x200	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset														>	X X X									>>>	XXXXX							
Access														כ	צ									2	I A Y							
Name														() () () () () () () () () ()	DAIASKC									<	DAIA							

Bit	Name	Reset	Access	Description
31:20	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
19:16	DATASRC	0xX	R	Result Data Source
	This bitfield contains t	the channel inde	x for the s	ensor result in DATA.
15:0	DATA	0xXXXX	RWH	Scan Result Buffer
	This bitfield contains t	the sensor resul	t.	

28.5.28 LESENSE_CHx_TIMING - Scan Configuration (Async Reg)

Offset															Bi	t Po	siti	on															
0x240	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	- ∞	1	_ (٥	2	4	က	2	_	0
Reset		•	•	•	•								>	XXXX	•								XXX		•	·					XXX		
Access													2	≥ Y								i	≶ Ƴ							i	≷		
Name														MEASUREDLY									SAMPLEDLY							l i	EXIME		

Bit	Name	Reset	Access	Description
31:24	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
23:14	MEASUREDLY	0xXXX	RW	Set Measure Delay
	Configure measure of	delay. Sensor me	easuring is	delayed for MEASUREDLY EXCLK cycles.
13:6	SAMPLEDLY	0xXX	RW	Set Sample Delay
	Configure sample de	elay. Sampling w	ill occur afte	er SAMPLEDLY SAMPLECLK cycles.
5:0	EXTIME	0xXX	RW	Set Excitation Time
	Configure excitation	time. Excitation	will last EX	TIME EXCLK cycles.

28.5.29 LESENSE_CHx_INTERACT - Scan Configuration (Async Reg)

Offset													В	it P	ositi	ion														
0x244	30	53	28	26	25	24	23	22	72	20	19	ά	1 2	16	15	4	13	12	7	10	တ	œ	7	9	2	4	٣	, ,	1 ←	. 0
Reset		·	·				•	•	×	×	×		XX		XXO	•	>	<u> </u>					•	3	XXXX				•	·
Access									R ⊗	RW	R ≪		ΑM		R		\ \ \	<u>}</u>						i	≷					
Name									ALTEX	SAMPLECLK	EXCLK		EXMODE		SETIF		E AND	SAINITE						() [[IHKES					
Bit	Name				Re	eset			Ac	ces	s	De	scrip	tio	n															
31:22	Reserve	ed			To tio		sure	com	pati	bilit	y wi	ith	future	de	vice	s, al	way.	s wr	ite b	its to	o O.	Мо	re in	forr	nati	on i	in 1	.2 C	onve	en-
21	ALTEX				Х				RV	/		Us	e Alt	ern	ativ	е Ех	cite	Pin												
	If set, al	terna	ative e	excit	e pii	n wil	ll be	use	d fo	exc	citat	tior	1																	
20	SAMPLI	ECL	K		Χ				RV	/		Se	lect (Cloc	ck U	sed	for	Tim	ing	of S	am	ple	Dela	ay						
	This bit	is us	ed to	con	figur	re w	hich	cloc	k is	use	ed fo	or t	iming	of S	SAM	1PLE	DLY	′												
	Value				Мс	ode						De	scrip	tion																
	0				LF	ACL	K					LF	ACL	(wi	ll be	use	d fo	r tim	ing											
	1				ΑL	JXH	FRC	0				ΑL	JXHF	RC	O wi	ll be	use	d fo	r tim	ing										
19	EXCLK				Х				RV	/		Se	lect (Cloc	ck U	sed	for	Exc	itati	on T	Γimi	ing								
	This bit	is us	ed to	con	figuı	re w	hich	cloc	ck is	use	ed fo	or t	iming	of I	EXT	IME	and	ME	ASL	JRE	DLY	,								
	Value				Мс	ode						De	scrip	tion																
	0				LF	ACL	K					LF	ACL	(wi	ll be	use	d fo	r tim	ing											
	1				ΑL	JXH	FRC	Ю				ΑL	JXHF	RC	o wi	ll be	use	d fo	r tim	ing										
18:17	EXMOD	E			0x	X			RV	/		Se	t GPI	O N	/lode	9														
	GPIO m 13	ode	for th	e ex	citat	tion	phas	se of	f the	sca	an s	eq	uence	e. N	ote 1	that	DAC	COU	T is	only	ava	ailak	ole d	on c	han	nels	s 4,	5, 7	, 10,	, 12,
	Value				Мо	ode						De	scrip	tion																
	0				DI	SAB	BLE					Dis	sable	b																
	1				HI	GH						Pu	sh Pı	ıll, C	GPIC) is	drive	n hi	gh											
	2				LC	W						Pu	sh Pı	ıll, C	GPIC) is	drive	en lo	W											
	3				DA	4CO	UT					VD	AC c	utp	ut															
16:14	SETIF				0x	X			RV	/		En	able	Inte	erru	pt G	ene	ratio	on											
	Select ir	nterr	upt ge	enera	atior	n mo	de f	or C	Нх і	nter	rup	t fla	ag.																	
	Value				Мо	ode						De	scrip	tion																

Bit	Name	Reset	Access	Description
	0	NONE		No interrupt is generated
	1	LEVEL		Set interrupt flag if the sensor triggers.
	2	POSEDGE		Set interrupt flag on positive edge of the sensor state
	3	NEGEDGE		Set interrupt flag on negative edge of the sensor state
	4	BOTHEDGE	ΞS	Set interrupt flag on both edges of the sensor state
13:12	SAMPLE	0xX	RW	Select Sample Mode
	Select measurer	ment to be used for	evaluation	
	Value	Mode		Description
	0	ACMPCOU	NT	Counter output will be used in evaluation
	1	ACMP		ACMP output will be used in evaluation
	2	ADC		ADC output will be used in evaluation
	3	ADCDIFF		Differential ADC output will be used in evaluation
11:0	THRES	0xXXX	RW	ACMP Threshold or VDAC Data

28.5.30 LESENSE_CHx_EVAL - Scan Configuration (Async Reg)

Offset									Bi	t P	osition														
0x248	30 31	28	56	25	23	22	20	19 19	17	16	5 4	13	12	=======================================	10) o	α	1 (_	ဖ ၊	Ω	4	ო (۷ .	- 0
Reset						XX0	×	XXO	×	×								0xxxxx							
Access						A.W.	₩ M	A.W.	RW	₹								RWH							
Name						MODE	SCANRESINV	STRSAMPLE	DECODE	COMP								COMPTHRES							
Bit	Name			Reset		Ac	ces	s Des	crip	tio	n														
31:23	Reserved			To ens	sure	compat	ibilit	y with fu	ıture	de	vices, a	lway	/S N	rite i	bits	to (D. M	ore	info	orma	atioi	n in	1.2 (Con	/en-
22:21	MODE			0xX		RV	V	Con	figu	re	Evalua	tion	Мо	de											
	Select whi	ich eval	uatio	n mode	to b	e used	on t	he meas	sure	mei	nt resul	:													
	Value			Mode				Des	cript	ion															
	0			THRE	S			Thre	sho	ld c	compari	son	is u	sed 1	to e	valu	ıate	se	nso	r res	ult				
	1			SLIDIN	νGW	/IN		Slidi	ing v	vinc	dow is ι	sed	to e	evalu	ate	ser	nsor	res	sult						
	2			STEPI	DET			Step	det	ect	ion is u	sed t	to e	valua	ate	sen	sor	res	ult						
20	SCANRES	SINV		Х		RV	٧	Ena	ble	Inv	ersion	of R	esı	ılt											
	If set, the	bit store	d in s	SCANR	RES v	will be ir	nver	ted.																	
19:18	STRSAME	PLE		0xX		RV	V	Ena	ble	Sto	ring of	Sen	ISO	Sar	npl	e in	Re	sul	t Bı	uffei	•				
	If set, the	sensor	samp	ole value	e wil	l be stor	ed a	and avai	lable	e in	the res	ult b	uffe	er											
	Value			Mode				Des	cript	ion															
	0			DISAB	BLE			Noth	ning	will	be sto	ed ir	n th	e res	sult	buff	er.								
	1			DATA				The	sen	sor	sample	dat	a w	ill be	sto	ored	in t	he	resı	ılt bı	uffe	r.			
	2			DATAS	SRC			The sam			ource (i. a.	e., th	he c	hanı	nel)	will	be	sto	red	alor	ıgsi	de t	he s	enso	or ——
17	DECODE			X		RV	V	Sen	d R	esu	It to De	cod	ler												
	If set, the	result fr	om th	nis char	nel	will be s	hifte	ed into th	ne d	eco	der reg	ister													
16	COMP			Χ		RV	V	Sele	ect N	/loc	le for T	hres	sho	ld C	om	pari	son	1							
	Set compa	are mod	le for	thresho	old c	omparis	ons	(CHx_I	NTE	RA	.CT_SA	MPL	E!	= AC	MF	an	d Cl	Hx_	EV	AL_	MO	DE	== T	HRI	ΞS).
	Value			Mode				Des	cript	ion															
	0			LESS				Con	npar	isor	n evalua	ates	to 1	if se	ens	or d	ata	is le	ess	than	CC	OMF	PTHF	RES	
	1			GE				Con CON			n evalua ES.	ates	to 1	if se	ens	or d	ata	is g	rea	ter t	nan	or e	equa	l to	

Bit	Name	Reset	Access	Description							
15:0	COMPTHRES	0xXXXX RWH Decision Threshold for Sensor Data									
	bitfield is written by L	son mode, this bitfield is used to configure threshold used for comparison. In step detection mode, this LESENSE, and contains the value from previous sensor measurement. In sliding window mode, this LESENSE, and contains the window base for the given channel.									

29. GPCRC - General Purpose Cyclic Redundancy Check



Quick Facts

What?

The GPCRC is an error-detecting module commonly used in digital networks and storage systems to detect accidental changes to data.

Why?

The GPCRC module can detect errors in data, giving a higher system reliability and robustness.

How?

Blocks of data entering GPCRC module can have a short checksum, based on the remainder of a polynomial division of their contents; on retrieval the calculation is repeated, and corrective action can be taken against presumed data corruption if the check values do not match.

29.1 Introduction

The GPCRC module is a slave peripheral that implements a Cyclic Redundancy Check (CRC) function. It supports both 32-bit and 16-bit polynomials. The supported 32-bit polynomial is 0x04C11DB7(IEEE 802.3), while the 16-bit polynomial can be programmed to any value, depending on the needs of the application. Common 16-bit polynomials are 0x1021 (CCITT-16), 0x3D65 (IEC16-MBus), and 0x8005 (zigbee, 802.15.4, and USB).

29.2 Features

- Programmable 16-bit polynomial, fixed 32-bit polynomial
- Byte-level bit reversal for the CRC input
- Byte-order reorientation for the CRC input
- · Word or half-word bit reversal of the CRC result
- · Ability to configure and seed an operation in a single register write
- Single-cycle CRC computation for 32-, 16-, or 8-bit blocks
- · DMA operation

29.3 Functional Description

An overview of the GPCRC module is shown in Figure 29.1 GPCRC Overview on page 998.





Figure 29.1. GPCRC Overview

29.3.1 Polynomial Specification

POLYSEL in GPCRC_CTRL selects between 32-bit and 16-bit polynomial functions. When a 32-bit polynomial is selected, the fixed IEEE 802.3 polynomial(0x04C11DB7) is used. When a 16-bit polynomial is selected, any valid polynomial can be defined by the user in GPCRC_POLY.

A valid 16-bit CRC polynomial must have an x^0 16 term and an x^0 0 term. Theoretically, a 16-bit polynomial has 17 terms total. The convention used is to omit the x^1 6 term. The polynomial should be written in **reversed** (little endian) bit order. The most significant bit corresponds to the lowest order term. Thus, the most significant bit in CRC_POLY represents the x^0 0 term, and the least significant bit in CRC_POLY represents the x^1 15 term. The highest significant bit of CRC_POLY should always set to 1. The polynomial representation for the CRC-16-CCIT polynomial x^1 6 + x^1 7 + x^1 7 + x^1 7 + x^2 7 + x^2 8 + 1, or 0x8408 in reversed order, is shown in Figure 29.2 Polynomial Representation on page 999.



CRC-16-CCITT Normal: 0x1021 Reversed: 0x8408

Figure 29.2. Polynomial Representation

29.3.2 Input and Output Specification

The CRC input data can be written to the GPCRC_INPUTDATA, GPCRC_INPUTDATAHWORD or GPCRC_INPUTDATABYTE register via the APB bus based on different data size. If BYTEMODE in GPCRC_CTRL is set, only the least significant byte of the data word will be used for the CRC calculation no matter which input register is written. There are also three output registers for different ordering. Reading from GPCRC_DATA will get the result based on the polynomial in reversed order, while reading from GPCRC_DATAREV will get the result based on the polynomial in normal order. The CRC calculation needs one clock cycle, reading from GPCRC_DATA, GPCRC_DATAREV or GPCRC_DATABYTEREV register or writting to GPCRC_CMD register is halted while the calculation is in progress.

29.3.3 Initialization

The CRC can be pre-loaded or re-initialized by first writing a 32-bit programmable init value to INIT in GPCRC_INIT and then setting INIT in GPCRC_CMD. It can also be re-initialized automatically when read from DATA, DATAREV or DATABYTEREV provided that AUTOINIT in GPCRC_CTRL is set, the CRC would be re-initialized with the stored init value.

29.3.4 DMA Usage

A DMA channel may be used to transfer data into the CRC engine. All bytes and half-word writes must be word-aligned. The recommended DMA usage model is to use the DMA to transfer all avaliable words of data and use software writes to capture any remaining bytes.

29.3.5 Byte-Level Bit Reversal and Byte Reordering

The byte-level bit reversal and byte reordering operations occur before the data is used in the CRC calculation. Byte reordering can occur on words or half words. The hardware ignores the BYTEREVERSE field with any byte writes or operations with byte mode enabled (BYTEMODE = 1), but the bit reversal settings (BITREVERSE) are still applied to the byte. 32-bit little endian MSB-first data can be treated like 32-bit little endian LSB-first data, as shown in Figure 29.3 Data Ordering Example - 32-bit MSB -first to LSB-first on page 1000. In this example, 32-bit data is written to GPCRC_INPUTDATA, BYTEREVERSE is set for byte ordering, and BITREVERSE is set for byte-level bit reversal.




Figure 29.3. Data Ordering Example - 32-bit MSB -first to LSB-first

When handling 16-bit data, the byte reordering function only swap the two lowest bytes and clear the two highest bytes, as shown in Figure 29.4 Data Ordering Example - 16-bit MSB -first to LSB-first on page 1001. In this example, 16-bit data is written to GPCRC_IN-PUTDATAHWORD, BYTEREVERSE is set for byte ordering, and BITREVERSE is set for byte-level bit reversal.




Figure 29.4. Data Ordering Example - 16-bit MSB -first to LSB-first

Assuming a word input byte order of B3 B2 B1 B0, the values used in the CRC calculation for the various settings of the byte-level bit reversal and byte reordering are shown in Table 29.1 Byte-Level Bit Reversal and Byte Reordering Results (B3 B2 B1 B0 Input Order) on page 1001.

Table 29.1. Byte-Level Bit Reversal and Byte Reordering Results (B3 B2 B1 B0 Input Order)

Input Width(bits)	BYTEREVERSE Setting	BITREVERSE Setting	Input to CRC Calculation
32	0	0	B3 B2 B1 B0
32	1	1	'B0 'B1 'B2 'B3
32	1	0	B0 B1 B2 B3
32	0	1	'B3 'B2 'B1 'B0
16	0	0	XX XX B1 B0
16	1	1	XX XX 'B0 'B1
16	1	0	XX XX B0 B1
16	0	1	XX XX 'B1 'B0
8	-	0	XX XX XX XX B0
8	-	1	XX XX XX XX 'B0

Input Width(bits)	BYTEREVERSE Setting	BITREVERSE Setting	Input to CRC Calculation
Note:			
1. X indicates a "don't	care".		
2. Bn is the byte field	within the word.		
3. 'Bn is the bit-revers	ed byte field within the word.		

29.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	GPCRC_CTRL	RW	Control Register
0x004	GPCRC_CMD	W1	Command Register
0x008	GPCRC_INIT	RWH	CRC Init Value
0x00C	GPCRC_POLY	RW	CRC Polynomial Value
0x010	GPCRC_INPUTDATA	W	Input 32-bit Data Register
0x014	GPCRC_INPUTDATAHWORD	W	Input 16-bit Data Register
0x018	GPCRC_INPUTDATABYTE	W	Input 8-bit Data Register
0x01C	GPCRC_DATA	R	CRC Data Register
0x020	GPCRC_DATAREV	R	CRC Data Reverse Register
0x024	GPCRC_DATABYTEREV	R	CRC Data Byte Reverse Register

29.5 Register Description

Offset												В	it Po	sitio	on_													
0x000	30	53	27	56	25	7.4	23	22	21	20	<u>5</u> 9	0 7	16	15	4	13	12	7	9	ဝ	ω	7	9	2	4	က	7	- -
Reset		1	, , , ,						,,				1			0			0	0	0				0			c
Access																ZW W			₩ M	₩	M				₩ M			Ž
Name																AUTOINIT			BYTEREVERSE	BITREVERSE	BYTEMODE				POLYSEL			Z
Bit	Nome																											
	Name				Res	et			Ac	cess	D	escri	otion															
31:14	Reser	ved				ทรเ	ıre d	com				escri _l future			, al	ways	s wr	ite b	oits t	o 0.	Мог	re in	nforn	natio	on in	1.2	Con	ven-
					То е	ทรเ	ıre d			bility	with		e dev	vices		ways	s wr	ite b	oits t	o 0.	Мог	re in	nforn	natio	on ir	1.2	? Con	ven-
31:14 13	Reser	INIT	o init b	y re-	To e tions	nsı			pati RW	bility I	with A ı	future	e dev	vices nable	9													
13	Reserr AUTO Enable	INIT es auto	o init b	y re-	To e tions 0	nsu	the	CR	RW C re	bility / esult	with A	future	it Er	nable value	e in	INIT	afte	er re	adir	ng of	f DA	ιΤΑ,	DA	TAR	REV	or D	АТА	BY-
13	AUTO Enable TERE	INIT es auto V. ved		y re-	To e tions 0 -seed	nsu	the	CR	RW C re	bility / esult	with Au base with	future uto In	it Er	vices nable value	e in	INIT way:	afte	er re	adir	ng of	f DA	ιΤΑ,	DA	TAR	REV	or D	АТА	BY-
	AUTO Enable TERE	INIT es auto v. ved	RSE		To e tions 0 -seed To e tions 0	nsi	the	CR com	RW C re	bility / esult bility	with base with	future uto In ed on future	it Er	vices value	e in	INIT ways	afte	er re	adir	ng of	f DA	ιΤΑ,	DA	TAR	REV	or D	АТА	BY-
13	AUTO Enable TERE Resen	INIT es auto v. ved	RSE		To e tions 0 -seed To e tions 0	nsu	the	CR com	RW C re	bility / esult bility	An An An An An An An An An An An An An A	future uto In ed on future	it Er the v	vices value	e in	INIT ways	afte	er re	adir	ng of	f DA	ιΤΑ,	DA	TAR	REV	or D	АТА	BY-

13	AUTOINIT	0	RW	Auto Init Enable
	Enables auto init by TEREV.	re-seeding the C	CRC result	based on the value in INIT after reading of DATA, DATAREV or DATABY-
12:11	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
10	BYTEREVERSE	0	RW	Byte Reverse Mode
	Allows byte level re	verse of bytes B3	3, B2, B1, B	30 within the 32-bit data word
	Value	Mode		Description
	0	NORMAL		No reverse: B3, B2, B1, B0
	1	REVERSED		Reverse byte order. For 32-bit: B0, B1, B2, B3; For 16-bit: 0, 0, B0, B1
9	BITREVERSE	0	RW	Byte-level Bit Reverse Enable
	Reverses bits within	n each byte of the	e 32-bit data	a word
	Value	Mode		Description
	0	NORMAL		No reverse
	1	REVERSED		Reverse bit order in each byte
8	BYTEMODE	0	RW	Byte Mode Enable
	Treats all writes as	bytes. Only the le	east signific	ant byte of the data-word will be used for CRC calculation for all writes
7:5	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
4	POLYSEL	0	RW	Polynomial Select
	Selects 16-bit CRC	programmable p	olynomial c	or 32-bit CRC fixed polynomial
	Value	Mode		Description
	0	CRC32		CRC-32 (0x04C11DB7) polynomial selected
	1	16		16-bit CRC programmable polynomial selected

Value	Mode	Description
0	CRC32	CRC-32 (0x04C11DB7) polynomial selected
1	16	16-bit CRC programmable polynomial selected

Bit	Name	Reset	Access	Description
3:1	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	EN	0	RW	CRC Functionality Enable
	Enables CRC fun	ctionality.		
	Value	Mode		Description
	0	DISABLE		Disable CRC function. Reordering function is available, only BITRE- VERSE and BYTEREVERSE bits are configurable in this mode
	1	ENABLE		Writes to inputdata registers result in CRC operations

29.5.2 GPCRC_CMD - Command Register

Offset															Bi	t Po	sitio	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	တ	8	7	9	5	4	က	2	_	0
Reset		•	•		•		•		•				•	•				•											•			0
Access																																W
Name																																<u>F</u>

Bit	Name	Reset	Access	Description
31:1	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
0	INIT	0	W1	Initialization Enable
	Writing 1 to this bit init	tialize the CRC	by writing t	he INIT value in CRC_INIT to CRC_DATA.

29.5.3 GPCRC_INIT - CRC Init Value

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	000000000000000000000000000000000000000																															
Access																	[} Y															
Name																Ė	Ž															

Bit	Name	Reset	Access	Description
31:0	INIT	0x00000000	RWH	CRC Initialization Value
	This value is loaded in	nto CRC_DATA	upon issui	ng the INIT command in CRC_CMD

29.5.4 GPCRC_POLY - CRC Polynomial Value

Offset															Bi	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset			•									•	•	•									'	00000	000000			•		'		•
Access																								7	<u>}</u>							
Name																								>								

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	POLY	0x0000	RW	CRC Polynomial Value

This value defines 16-bit POLY, which is used as the polynomial during the 16-bit CRC calculation. The polynomial is defined in reversed representation, meaning that the lowest degree term is in the highest bit position of POLY. Additionally, the highest degree term in the polynomial is implicit. Further examples of the CRC configuration can be found in the documentation.

29.5.5 GPCRC_INPUTDATA - Input 32-bit Data Register

Offset															Bit	t Po	siti	on														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																00000000																
Access																}	}															
Name																ATACTICATA																

Bit	Name	Reset	Access	Description
31:0	INPUTDATA	0x00000000	W	Input Data for 32-bit
	CRC Input 32-bit Data	can be written t	to this reai	ster. Each time this register is written, the CRC value is undated

29.5.6 GPCRC_INPUTDATAHWORD - Input 16-bit Data Register

0x014 Image: light control of the control	Offset															Bi	t Po	sitic	on														
Access	0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	3	2	_	0
	Reset																	•		•						nnnnxn				•	•		
Name Name	Access																								,	>							
	Name																								() () ()	INPULDATAHWORD							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	INPUTDATAHWORD	0x0000	W	Input Data for 16-bit
	CRC Input 16-bit Data	can be written	to this regi	ster. Each time this register is written, the CRC value is updated.

29.5.7 GPCRC_INPUTDATABYTE - Input 8-bit Data Register

Offset	Bit Position	
0x018	31 32 33 34 35 37 37 37 37 37 37 37 37 37 37 37 37 37	L 0 0 4 0 0 0
Reset		00×0
Access		
Name		INPUTDATABYTE

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	INPUTDATABYTE	0x00	W	Input Data for 8-bit
	CRC Input 8-bit Data	can be written to	this regis	ter. Each time this register is written, the CRC value is updated.

29.5.8 GPCRC_DATA - CRC Data Register

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	000000000000000000000000000000000000000															
Access																۵	۷															
Name																\ F	<u> </u>															

Bit	Name	Reset	Access	Description
31:0	DATA	0x00000000	R	CRC Data Register

CRC Data Register, read only. The CRC data register may still be indirectly written from software, by writing the INIT register and then issue an INITIALIZE command.

29.5.9 GPCRC_DATAREV - CRC Data Reverse Register

Offset															Bi	t Po	siti	on														
0x020	33	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																000000000000000000000000000000000000000	00000000000															
Access																۵	۷															
Name																	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \															

Bit	Name	Reset	Access	Description
31:0	DATAREV	0x00000000	R	Data Reverse Value

Bit reversed version of CRC Data register. When a 32-bit CRC polynomial is selected, the reversal occurs on the entire 32-bit word. When a 16-bit CRC polynomial is selected, the bits [15:0] are reversed.

29.5.10 GPCRC_DATABYTEREV - CRC Data Byte Reverse Register


Offset															Bi	t Po	sitio	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset																00000000																
Access																Ω	_															
Name																DATARVTEREV																
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
04-0		T ^ F			. ,		0	2000	2000		_			D-4-	. n	4- 0			\/_I													

Bit	Name	Reset	Access	Description
31:0	DATABYTEREV	0x00000000	R	Data Byte Reverse Value

Byte reversed version of CRC Data register. When a 32-bit CRC polynomial is selected, the bytes are swizzled to {B0, B1, B2, B3}. When a 16-bit CRC polynomial is selected, the bytes are swizzled to {0, 0, B0, B1}.

30. CRYPTO - Crypto Accelerator





Quick Facts

What?

A fast and energy efficient autonomous hardware accelerator for AES encryption and decryption with 128- or 256-bit keys, ECC over prime and binary Galois finite fields, SHA-1, SHA-224 and SHA-256.

Why?

Efficient cryptography with little or no CPU intervention helps to meet the speed and energy demands of the application. Hardware implementations are generally more secure against side-channel attacks than software implementations.

How?

Programmable sequences of instructions on big numbers allow fast processing with little CPU intervention. Furthermore, CRYPTO is linked to the Buffer Controller (BUFC), thus enabling fast and efficient autonomous cipher operations on data buffer content.

30.1 Introduction

The CRYPTO module allows efficient acceleration of common cryptographic operations and allows these to be used efficiently with a low CPU load. Operations performed by CRYPTO can be set up as a sequence of instructions on a set of 128-bit, 256-bit or 512-bit registers to implement or accelerate Elliptic Curve Cryptography (ECC), SHA-1, SHA-224, SHA-256, and various block cipher modes based on the Advanced Encryption Standard, also known as AES (FIPS-197).

CRYPTO is capable of autonomously fetching data, performing cipher operations and storing data across multiple blocks. When the source data is not a multiple of 16 bytes (128 bits), Zero-padding can be included in the last block. Block operations such as Counter Mode (CTR), Electronic Code Book (ECB), Cipher Block Chaining (CBC), Cipher Feedback (CFB) and Output Feedback (OFB) are easily implemented. Block Cipher modes of operation such as Electronic Code Book (ECB), Counter Mode (CTR), Cipher Block Chaining (CBC), CBC-MAC (CBC Message Authentication Code), CCM (Counter with CBC-MAC) and GCM (Galois Counter mode) are easily implemented.

CRYPTO is delivered with an extensive software library in Simplicity Studio that implements all major cryptographic algorithms, including but not limited to AES, SHA-1, SHA-2, ECC, and legacy algorithms DES, 3DES, MD4, MD5 and RC4. The implementation accelerates the algorithms using CRYPTO when possible.

30.2 Features

- · Efficient AES core
 - Encryption/decryption using 128-bit key (54 clock cycles) or 256-bit key (75 clock cycles)
 - · Key buffer
 - Supports autonomous cipher block modes (e.g. ECB, CTR, CBC, PCBC, CFB, CBC-MAC, GMAC, CCM, CCM* and GCM) across multiple blocks
- Accelerated SHA-1, SHA-224 and SHA-256
- Accelerated Elliptic Curve Cryptography (ECC)
 - · Binary and Prime fields
 - Supports NIST recommended curves: P-192, P-224, P-256, K-163, K-233, B-163, and B-233
- Galois/Counter Mode (GCM)
 - · ALU operations on GCM GF(2^128) field
- Flexible 256-bit ALU and sequencer
 - 5 general purpose 256-bit registers
 - Supports ADD, SUB, MUL, shift, XOR, etc.
 - Up to 20 instructions can be chained to implement various block cipher modes
- · Efficient operation
 - Automatic data loading and storing from registers (through BUFC, the buffer controller)
 - · DMA request signals for data read and write
 - · Optional XOR Data write
 - · Interrupt on finished operations
- · Extensive software support
 - · Extensive software library in Simplicity Studio
 - Implements all major cryptographic algorithms: AES, SHA-1, SHA-2, and ECC
 - · Implements legacy algorithms: DES, 3DES, MD4, MD5, and RC4
 - · Hardware accelerated when possible

30.3 Usage and Programming Interface

Many security systems fail due to mistakes in the implementation. Therefore implementations should be left to experts in cryptographic algorithms.

To solve this, the module is supported by an hardened cryptography software library and API delivered through Silicon Labs' Simplicity Studio. The software API is a frontend for performing all supported cryptographic operations both for radio-protocols and applications, and must be used to receive prompt support.

30.4 Functional Description

A block diagram of the CRYPTO module is shown in Figure 30.1 CRYPTO Overview on page 1011.




Figure 30.1. CRYPTO Overview

30.4.1 Data and Key Registers

The CRYPTO module contains five 256-bit registers. Accelerators are implemented through instructions operating on these registers, either by copying data between registers and external components like the BUFC or through DMA, or by executing instructions on the registers.

Depending on the instruction, the registers can be accessed as 128-bit, 256-bit or 512-bit registers. The registers can also be accessed through different interface registers to achieve different results.

When writing to and reading from the CRYPTO_DATAX, CRYPTO_KEY, CRYPTO_KEYBUF, CRYPTO_DDATAX and CRYPTO_QDATAX registers, the least significant part is accessed first and the most significant part last, see Figure 30.2 CRYPTO Data and Key Register Operation on page 1013. The same is the case for the XOR and byte-access registers for DATA0 and DATA1. It is important to note that some of the 256-bit registers are composed of the 128-bit registers, and both the 512-bit registers are composed of the 256-bit registers.

Note: From here on, the 128, 256 and 512-bit registers are named DATAx, DDATAx, QDATAx, etc, And the access-points to these registers are named CRYPTO_DATAx, CRYPTO_DDATAx, CRYPTO_QDATAx, etc.

DATA0 can be accessed through CRYPTO_DATA0 (32-bit), CRYPTO_DATA0XOR (32-bit), CRYPTO_DATA0BYTE (8-bit) and CRYPTO_DATA0XORBYTE (8-bit). Direct access to bytes 12 - 15 is available through CRYPTO_DATA0BYTE12-15 (8-bit). The DATA0XOR (in CRYPTO_DATA0XOR) is used for XOR'ing a value with the current value in DATA0. This is used in a large variety of block cipher modes. All of these registers operate on DATA0.

DATA1 can be accessed through CRYPTO_DATA1 (32-bit) and CRYPTO_DATA1BYTE (8-bit).

The remaining data registers have regular 32-bit access through their respective registers. Note that all data registers require a full read or write to be fully accessed. This means that the 128-bit registers need four 32-bit reads/writes, the 256-bit registers need 8 reads/writes and the 512-bit registers need 16 reads/writes. For a read, if all read accesses are not done, the register will end up as a shifted version of the original value.

Note: For byte-wise data accesses (DDATAxBYTE, DATAxBYTE, etc.), all reads and writes must be performed in groups of 4, due to internal buffering and shifting of 32 bits at a time. Accessing a number of bytes that is not a multiple of four can cause data incoherency in all of the data registers.

The KEY and KEYBUF registers are 256 bit wide when AES256 is set in CRYPTO_CTRL. Else they are 128 bit wide. When used as a part of DDATAx and QDATAx, they are always 256 bit wide.

The registers DDATA0BIG and QDATA1BIG produce byte-swapped versions of DDATA0 and QDATA1 respectively. These may be used when a computation requires byte-swapping. An example of this is SHA computation, where data needs to be changed to big endian before CRYPTO can work with it. Little endian data is then loaded in through QDATA1BIG and the resulting little endian hash can be read out from DDATA0BIG, see 30.4.5 SHA.

Except for KEYBUF, the contents of all data registers are lost when going to EM2.




Figure 30.2. CRYPTO Data and Key Register Operation

30.4.1.1 DATA0 Zero

DATA0ZERO in CRYPTO_DSTATUS contains status flags indicating if any 32-bit blocks within DATA0 is 0. For example, if DATA0[95:64] is equal to 0x00000000, ZERO64TO95 is set.

30.4.1.2 DDATA0 and DDATA1 Quick Observation

DDATA0LSBS in CRYPTO_DSTATUS shows the 4 least significant bits in DDATA0. DDATA0MSBS in CRYPTO_DSTATUS shows the 4 most significant bits of DDATA0, while DDATA1MSB in CRYPTO_DSTATUS shows the msb of DDATA1. These observation bitfields are useful for determining the sign of the value in the data registers without having to read out the full register data register values

The 4 bits observed by DDATA0MSBS will change depending on RESULTWIDTH in CRYPTO_WAC. When using 260-bit results, DDATA0MSBS shows bits 259-256, when using 256-bit results, it is bits 255-252, and for 128-bit results, bits 127-124 can be observed. When RESULTWIDTH is 260 bits, the 4 most significant bits, e.g. bits 259-256 are also available in CRYPTO_DDATA0BYTE32, where they can also be written. Using this register is the only way of inputting the upper 4 bits of a 260-bit number to CRYPTO.

30.4.1.3 Result Width

RESULTWIDTH in CRYPTO_WAC determines the width of the operation when performing arithmetic/shift instructions with CRYPTO. Using less wide results will reduce the current consumption of the CRYPTO module. The higher-order bits that are beyond the selected result width are ignored in the computation of arithmetic/shift operations, however, these higher-order bits will be undefined in the result of such instructions.

When RESULTWIDTH=260BIT, all DDATA registers effectively become 260 bits wide, so that the upper 4 bits are not lost when transferring data from DDATA0 to the other DDATA registers. Likewise, the arithmetic/shift instructions shall consider the full 260-bit values of DDATA0-DDATA4 when used as operation inputs. Note that DDATA0 is the only 260-bit register of which MSBs can be observed/written. The upper 4 bits are observed through DDATA0MSBS in CRYPTO_DSTATUS or through CRYPTO_DDATA0BYTE32. For all DDATAx registers, the extra MSBs are cleared when DDATAx is written. Furthermore, for a particular x, a write to DDATAx or any of its aliased registers will cause DDATAx MSBs to be cleared. Note, writing to KEY/KEYBUF will only clear MSBs of DDATA1/DDATA4 when AES256 mode is set. Likewise, writing to DATA0/DATA2 will not clear DDATA2/DDATA3 MSBs.

Since the DATA0-DATA3 registers are always 128-bit, all bit positions greater than 128 are interpreted as 0 when RESULTWIDTH is greater than 128 bits. However, the assignment instructions DATAxTODDATAy will not zero-out the upper 128 bits of the DDATAy target. Instead, those upper words become undefined after such operations.

30.4.2 Instructions and Execution

The CRYPTO module implements a set of instructions in order to load and manipulate data effectively. These instructions are grouped into four types:

- · ALU instructions arithmetic and logical bitwise operations
- Transfer instructions moving data between registers and external peripherals like DMA and the BUFC
- Conditional instructions conditionally execute instructions based on context
- Special instructions various crypto and support instructions

A single instruction can be executed by writing INSTR in CRYPTO_CMD. This will execute the instruction, and the interface of CRYP-TO will be locked until the execution has completed. Multiple commands can safely be issued after each other by the CPU as long as NOBUSYSTALL in CRYPTO_CTRL is not set. If CRYPTO gets a new command or a data access request while busy it will then stall the bus, and execute the new command as soon as it is done with the previous one. Note, there are some exceptions to this rule. For example, see 30.4.8 DMA.

Stalling of the bus can be disabled by setting NOBUSYSTALL in CRYPTO_CTRL, however manipulating (reading or writing) registers while running an instruction will result in undefined behaviour. Additionally, if NOBUSYSTALL=0 and a new command or data access request is made while the CRYPTO is simultaneously performing a data transfer instruction, it is possible for system lockup due to bus stalling loops. The safest approach is to always check if an instruction is running by looking at INSTRRUNNING in CRYPTO_STATUS.

Note that this automatic stalling feature does not apply to automated CRYPTO instruction sequences (described next), since there may be cycle delays between individual instructions for which bus accesses are not prevented. For sequences, always check the SEQRUNNING status bit or the SEQDONE interrupt flag to ensure the sequence is finished before attempting CRYPTO register accesses.

30.4.2.1 Sequences

For executing a set of instructions, it is more efficient to load them into the CRYPTO module and run them as a sequence. This is done by writing the instructions into CRYPTO_SEQ0-CRYPTO_SEQ4, and marking the end of the instruction sequence with either an END or an EXEC instruction. The END simply means end-of-instructions, while writing EXEC means end-of-instructions and execute immediately.

The five registers allow up to 20 instructions to be loaded. To start execution, either end the instructions with an EXEC instruction, or set SEQSTART in CRYPTO_CMD. CRYPTO will then execute the instructions, starting in CRYPTO_SEQ0, and ending at the first END instruction. SEQRUNNING in CRYPTO_STATUS is set while the sequence is running, and the interrupt flag SEQDONE in CRYPTO_IF will be set when the sequence has completed.

A sequence can be stopped by issuing the SEQSTOP command in the CRYPTO_CMD register. This command also clears the state of ongoing CRYPTO instructions including DMA and BUFC access. Check SEQRUNNING in CRYPTO_STATUS after issuing the SEQSTOP command flag to make sure any ongoing sequence/transfer has completed before accessing data registers again.

30.4.2.2 Available Instructions

The available ALU instructions are listed in Table 30.1 ALU Instructions on page 1016, data transfer instructions are listed in Table 30.3 Transfer Instructions on page 1017, conditional instructions are listed in Table 30.4 Conditional Instructions on page 1018 and special instructions are listed in Table 30.5 Special Instructions on page 1018. The tables explains the side-effects of the instructions and shows which registers are affected. For instructions involving BUFC, the BUFC Buffers are defined by READBUFSEL and WRITE-BUFSEL in CRYPTO_CTRL for BUFC reads and writes respectively. V0 and V1 in the instructions descriptions can be any of the DDA-TAX registers and a selection of the DATAX registers. They can be selected using the SELDDATAXDDATAY, SELDATAXDDATAY, SELDATAXDATAY instructions. The first register in the instruction will be selected for V0, and the second for V1. This configuration stays even when the sequence is complete, and can also be set up front. The currently selected V0 and V1 can be read V0 and V1 in CRYPTO_CSTATUS.

Table 30.1. ALU Instructions

Instruction	Description	Constraints/Notes
ADD	DDATA0 = V0 + V1	If V0 != DDATA0, then V1 != DDATA0
ADDO	DDATA0 = V0 + V1	Carry is only set, not cleared. If V0 != DDATA0, then V1 != DDATA0
ADDC	DDATA0 = V0 + V1 + carry	If V0 != DDATA0, then V1 != DDATA0
ADDIC	DDATA0 = V0 + V1 + carry << 128	If V0 != DDATA0, then V1 != DDATA0. If resultwidth is 128b, then carry is undefined
MADD	DDATA0 = (V0 + V1) mod P	If V0 != DDATA0, then V1 != DDATA0
MADD32	DDATA0[i] = V0[i] + V1[i]. Word-wise addition	carry is not modified. If V0 != DDATA0, then V1 != DDATA0
SUB	DDATA0 = V0 - V1	V1 != DDATA0. If V1 is 128b and resultwidth > 128b, then upper 128b are unknown
SUBC	DDATA0 = V0 - V1 - carry	V1 != DDATA0. If V1 is 128b and resultwidth > 128b, then upper 128b are unknown
MSUB	DDATA0 = (V0 - V1) mod P	V1 != DDATA0. If V1 is 128b and resultwidth > 128b, then upper 128b are unknown
MUL	DDATA0 = DDATA1 * V1. See 30.4.2.3 MULx Details	V1 != DDATA0,DDATA1
MULC	DDATA0 = DDATA1 * V1 + (DDATA0 << MULWIDTH) See 30.4.2.3 MULx Details	.V1 != DDATA0,DDATA1
MMUL	DDATA0 = (DDATA1 * V1) mod P	V1 != DDATA0,DDATA1
MULO	DDATA0 = DDATA1 * V1. See 30.4.2.3 MULx Details	V1 != DDATA0,DDATA1. Carry is only set, not cleared
SHL	DDATA0 = V0 << 1	If V0 is 128b and resultwidth is 260b, then upper 4b are unknown
SHLC	DDATA0 = V0 << 1 carry	If V0 is 128b and resultwidth is 260b, then upper 4b are unknown
SHLB	DDATA0 = V0 << 1 V0[resultwidth-1]	If V0 is 128b and resultwidth is 260b, then upper 4b are unknown
SHL1	DDATA0 = V0 << 1 1	If V0 is 128b and resultwidth is 260b, then upper 4b are unknown
SHR	DDATA0 = V0 >> 1	
SHRC	DDATA0 = V0 >> 1 carry << resultwidth-1	

Instruction	Description	Constraints/Notes
SHRB	DDATA0 = V0 >> 1 V0[0] << resultwidth-1	
SHR1	DDATA0 = V0 >> 1 1 << resultwidth-1	
SHRA	DDATA0 = V0 >> 1 V0[resultwidth-1] << result-width-1	
CLR	DDATA0 = 0	
XOR	DDATA0 = V0 ^ V1	If V0 != DDATA0, then V1 != DDATA0
INV	DDATA0 = ~V0	
CSET	CARRY = 1	
CCLR	CARRY = 0	
BBSWAP128	DDATA0[127:0] = bbswap(V0[127:0])	See 30.4.2.5 BBSWAP128 Instruction
INC	DDATA0 = DDATA0 + 1	
DEC	DDATA0 = DDATA0 - 1	

Table 30.2.

Table 30.3. Transfer Instructions

Instruction	Operation	Constraints/Notes
DATAxTOBUF	BUFC = DATAx	x = 0,1. BUFC buffer defined by WRITEBUFSEL
DATAxXORBUF	BUFC = BUFC ^ DATAx	x = 0,1. BUFC buffer defined by WRITEBUFSEL
BUFTODATAx	DATAx = BUFC	x = 0,1. BUFC buffer defined by READBUFSEL
BUFTODATA0XOR	DATA0 = DATA0 ^ BUFC	BUFC buffer defined by READBUFSEL
DATATODMA0	DMA = DATAX, DMA request DMA0RD	DATAX = DATA0, DDATA0, DDATA0BIG, QDATA0 as defined by DMA0RSEL
DMA0TODATA	DATAX = DMA, DMA request DATA0WR	DATAX = DATA0, DDATA0, DDATA0BIG, QDATA0
DMA0TODATAXOR	DATA0 = DATA0 ^ DMA, DMA request DA- TA0XORWR	
DATATODMA1	DMA = DATAX, DMA request DMA1RD	DATAX = DATA1, DDATA1, QDATA1BIG as defined by DMA1RSEL
DMA1TODATA	DATAX = DMA, DMA request DATA0WR	DATAX = DATA1, DDATA1, QDATA1, QDATA1BIG
DATAxTODATAy	DATAy = DATAx	
DATAxTODATA0XOR	DATA0 = DATA0 ^ DATAx	If resultwidth is 128b, then carry is undefined
DATAXTODATA0XOR- LEN	DATA0 = DATA0 ^ (DATAx & (2**LENGTH-1))	LENGTH is LENGTHA or LENGTHB depending on active part of sequence. If resultwidth is 128b, then carry is undefined
DDATAxTODDATAy	DDATAy = DDATAx	
DDATAxHTODATA1	DATA1 = DDATAx[255:128]	Bits DDATA2[259:256] become undefined
DDATAxLTODATAy	DATAy = DDATAx[127:0]	
SELDDATAxDDATAy	Use DDATAx as V0, DDATAy as V1	x = 0,1,2,3,4; y = 0,1,2,3,4

Instruction	Operation	Constraints/Notes
SELDATAxDDATAy	Use DATAx as V0, DDATAy as V1	x = 0,1,2; y = 0,1,2,3,4
SELDDATAxDATAy	Use DDATAx as V0, DATAy as V1	x = 0,1,2,3,4; y = 0,1
SELDATAxDATAy	Use DATAx as V0, DATAy as V1	x = 0,1,2; y = 0,1

Table 30.4. Conditional Instructions

Instruction	Operation Constrain	
EXECIFA	Execute following instructions if in part A of sequence	
EXECIFB	Execute following instructions if in part B of sequence	
EXECIFNLAST	Execute following instructions if not in last iteration of sequence	
XECIFLAST Execute following instructions if in last iteration of sequence		
EXECIFCARRY Execute following instructions if carry bit is set		
EXECIFNCARRY	ECIFNCARRY Execute following instructions if carry bit not is set	
EXECALWAYS	Always execute following instructions	

Table 30.5. Special Instructions

Instruction	Operation
END	Ends execution.
EXEC	When written to CRYPTO_SEQx register, automatically triggers execution of all instruction up to this point.
AESENC	DATA0 = AESENC(DATA0)
AESDEC	DATA0 = AESDEC(DATA0)
SHA	DDATA0 = SHA(Q1)
DATA1INC	DATA1 = inc(DATA1). See 30.4.2.4 DATA1INC and DATA1INCCLR Instructions
DATA1INCCLR	DATA1 = clearinc(DATA1). See 30.4.2.4 DATA1INC and DATA1INCCLR Instructions

30.4.2.3 MULx Details

For the MULx instructions (not MMUL), MULWIDTH in CRYPTO_WAC specifies the width of operands DDATA1 (and sometimes V1). This is useful in order to optimize performance because multiplications take the same number of cycles as the bits in the operands plus a couple of cycles for setup.

As with the other ALU instructions, RESULTWIDTH limits the width of the final result of the MULx and MMUL instructions.

30.4.2.4 DATA1INC and DATA1INCCLR Instructions

DATA1INC and DATA1INCCLR operate on the 1, 2, 3 or 4 most significant bytes in DATA1, depending on INCWIDTH in CRYP-TO_CTRL. DATA1INC increments these bytes in big endian, while DATA1INCCLR clears the bytes.

30.4.2.5 BBSWAP128 Instruction

The BBSWAP128 instruction copies the contents of the V0 operand to DDATA0 while swapping the bits of the lower 16 bytes. The operand is not changed. This operation is required for GCM. See 30.4.7 GCM and GMAC

30.4.2.6 Carry

The carry output from most instructions can be observed through the CARRY bit in CRYPTO_DSTATUS. Shift-instructions set CARRY to the value that is shifted out of the register, addition and multiplication set it on register overflow, and subtraction sets it on borrow, e.g. underflow.

In addition to generating carry information, some instructions also use the current value of CARRY. ADDC, SUBC, SHLC and SHRC all use carry to generate the result. For all of these instructions, carry allows a program to chain instructions together to operate on bigger numbers than allowed by CRYPTO. For example, by chaining first an ADD, and then an ADDC which uses the carry from the ADD operation, two 512-bit numbers can be added. By chaining more instructions, even larger numbers can be manipulated.

Other uses of CARRY include observation. To check if a register is 0, one can subtract 1 using the DEC instruction, and check if goes negative by checking the CARRY bit. CARRY can be set manually and in CRYPTO programs using the CSET and CCLR instructions, which set and clear the CARRY bit.

The MULC instruction does not use CARRY like the other carry instructions (i.e., instructions ending in 'C' such as 'ADDC'), but rather preserves the old contents of the multiplication register.

30.4.3 Repeated Sequence

To maximize efficiency, it is desirable to be able to run a set of instructions over multiple blocks of data autonomously. To repeat a sequence over a larger set of data, set LENGTHA in CRYPTO_SEQCTRL to the number of bytes in the set, and BLOCKSIZE to the size of the blocks in the set. The sequence will then be repeated N times, where N is LENGTHA / BLOCKSIZE if LENGTHA is a multiple of BLOCKSIZE, or ceiling(LENGTHA / BLOCKSIZE) if not. In the latter case, data written by DMA or received from BUFC will be zero-padded up to BLOCKSIZE if it is written to a register which has a size equal to BLOCKSIZE. One notable exception is when LENGTHA is 0. In this case the sequence will still execute once, but the block transfer instructions will not execute.

Note: If DMAxRSEL in CRYPTO_CTRL selects a register that is smaller than the specified blocksize, DATATODMAx/DMAxTODATA instructions will not use the full blocksize, but will only transfer enough data to empty/fill the register once. For example, if BLOCKSIZE is set to 64B and DMA0RSEL=DDATA0, the instruction DATATODMA0 will only read 32B instead of 64B. The processing of LENGTHA/B will continue as if all 64B had been transferred.

A repeated sequence can also be made do slightly different operations on different parts of the data set. A sequence can be divided into two parts; part A, and part B. By configuring LENGTHA in CRYPTO_SEQCTRL to the length of part A, and LENGTHB in CRYPTO_SEQCTRLB to the length of part B, CRYPTO will first run iterations over part A, knowing it is A, and then part B, knowing it is part B. By using the conditional instructions listed in Table 30.4 Conditional Instructions on page 1018, a program can execute different instructions depending on whether it is in part A or part B.

30.4.4 AES

The AES core operates on data in the 128-bit register DATA0 using the either a 128-bit or 256-bit key from the KEY register. The key width is specified by AES256 in CRYPTO_CTRL. AES operations are implemented as the AESENC and AESDEC instructions, for AES encryption and AES decryption respectively. An overview of the AES functionality is shown in Figure 30.3 CRYPTO AES Overview on page 1020.

AES encryption and decryption enables various block cipher modes like ECB, CTR, CBC, PCBC, CFB, OFB, CBC-MAC, GMAC, CCM, CCM*, and GCM.




Figure 30.3. CRYPTO AES Overview

The input data before encryption is called the PlainText and output from the encryption is called CipherText. For encryption, the key is called PlainKey. After encryption, the resulting key in the KEY registers is the CipherKey. This key must be loaded into the KEY registers prior to the decryption. After one decryption, the resulting key will be the PlainKey. The resulting PlainKey/CipherKey is only dependent on the value in the KEY registers before encryption/decryption. The resulting keys and data are shown in Figure 30.4 CRYPTO Key and Data Definitions on page 1020.




Figure 30.4. CRYPTO Key and Data Definitions

The KEY is by default loaded from KEYBUF prior to each AESENC or AESDEC instruction. If the KEY is not to be overwritten, key buffering should be disabled (KEYBUFDIS in CRYPTO_CTRL). Disabling key buffering also allows the use of key loading through DMA.

The data and key orientation in the CRYPTO registers are shown in Figure 30.5 CRYPTO Data and Key Orientation as Defined in the Advanced Encryption Standard on page 1021.




Figure 30.5. CRYPTO Data and Key Orientation as Defined in the Advanced Encryption Standard

30.4.5 SHA

The CRYPTO SHA instruction implements SHA-1 with a 160-bit digest or SHA-2 with a 224-bit digest (SHA-224) or 256-bit digest (SHA-256). Depending on SHAMODE in CRYPTO_CTRL, SHA-1, SHA-224 or SHA-256 will be run on the data in QDATA1, and the result will be put on DDATA0. The contents in QDATA1 will be destroyed in the process.

To run SHA on a dataset, it must first be pre-processed by appending a bit '1' to the message, then padding the data with '0' bits until the message length in bits modulo 512 is 448. Then append the length of the message before pre-processing as a 64-bit big-endian integer. This pre-processing is known as MD-strengthening, and must be done by software before processing with the CRYPTO module.

The pre-processed data can now be run through the CRYPTO module. Begin by writing the values listed in Table 30.6 SHA Init Values on page 1022 to CRYPTO_DDATA1 from top to bottom, then execute the instructions listed in Table 30.7 SHA Preparations on page 1022.

Table 30.6. SHA Init Values

SHA-1	SHA-224	SHA-256
0x67452301	0xC1059ED8	0x6A09E667
0xEFCDAB89	0x367CD507	0xBB67AE85
0x98BADCFE	0x3070DD17	0x3C6EF372
0x10325476	0xF70E5939	0xA54FF53A
0xC3D2E1F0	0xFFC00B31	0x510E527F
0x00000000	0x68581511	0x9B05688C
0x00000000	0x64F98FA7	0x1F83D9AB
0x0000000	0xBEFA4FA4	0x5BE0CD19

Table 30.7. SHA Preparations

STEP	ACTION	Description
STEP0	DDATA1TODDATA0	Copy init data to DDATA0
STEP1	SELDDATA0DDATA1	Select DDATA0 and DDATA1 as operands for SHA instruction

Then, for each 512-bit block, write the block to CRYPTO_QDATA1BIG, execute the instructions listed in Table 30.8 SHA for 512-bit Block on page 1022.

Table 30.8. SHA for 512-bit Block

STEP	ACTION	Description
STEP0	SHA	Perform SHA operation on data in QDATA1
STEP1	MADD32	Accumulate with previous data in DDATA1
STEP2	DDATA0TODDATA1	Copy hash to DDATA1

After the last iteration, the resulting hash can be read out from CRYPTO_DDATA0BIG.

30.4.6 ECC

The CRYPTO module implements support for Elliptic Curve Cryptography through the modular instructions MADD, MMUL and MSUB, which perform modular addition, multiplication and subtraction respectively. The instructions can operate on a set of both prime fields GF(p) and binary fields $GF(2^m)$.

The type of modular arithmetic used and the modulus for the modular operations are specified by MODOP and MODULUS in CRYP-TO WAC respectively. Changing these in the middle of an operation leads to undefined behaviour.

30.4.7 GCM and GMAC

CRYPTO implements support for Galois/Counter Mode (GCM), and also Galois Message Authentication Code (GMAC), by providing AES instructions and allowing multiplication on the field $GF(2^128)$ defined by the polynomial $x^128 + x^7 + x^2 + x + 1$.

Note: BBSWAP128 needs to be applied to both operands and the result of the MMUL instruction when using it for GCM and GMAC

Efficient sequencer programs can be set up to perform GCM authentication and encryption/decryption on data from either BUFC, DMA, or CPU. To achieve a single-pass solution, LENGTHA in CRYPTO_SEQCTRL is set to the length of the authentication part, and LENGTHB is set to the length of the rest of the message. Conditional instructions can then be used to make sure the two parts of the message are processed correctly. A similar approach is used to implement CCM.

30.4.8 DMA

The CRYPTO module has 5 DMA request signals (see Table 30.9 DMA Signals on page 1023) split over 2 internal DMA channels: DMA0 and DMA1. These DMA channels are not associated with channel 0 and 1 of the system DMA, and any system DMA channel can serve any of the 5 DMA requests. See the DMA chapter for information on how to configure the system DMA.

The DMA signals are set through the use of DMA oriented instructions, and cleared by reading or writing the respective CRYPTO data registers.

Name	Set on	Cleared on
DMA0WR	Instruction DMA0TODATA, and DMA0TODATAXOR if COMBDMA0WEREQ in CRYPTO_CTRL is set	Full CRYPTO_DATA0, CRYPTO_DDATA0, CRYPTO_DDATA0BIG or CRYPTO_QDATA0 write, or CRYPTO_DDATA0XOR if COMBDMA0WEDMAREQ in CRYPTO_CTRL is set
DMA0XORWR	Instruction DMA0TODATAXOR	Full CRYPTO_DATA0XOR write
DMA0RD	Instructions DATATODMA0	Full CRYPTO_DATA0, CRYPTO_DDATA0, CRYPTO_DDATA0BIG or CRYPTO_QDATA0 read, depending on DMA0MODE in CRYPTO_CTRL
DMA1WR	Instructions DMA1TODATA	Full CRYPTO_DATA1, CRYPTO_DDATA1, CRYPTO_QDATA1 or CRYPTO_QDATA1BIG write
DMA1RD	Instructions DATATODMA1	Full CRYPTO_DATA1, CRYPTO_DDATA1, CRYP- TO_QDATA1 or CRYPTO_QDATA1BIG read, depend- ing on DMA1MODE in CRYPTO_CTRL

Table 30.9. DMA Signals

Note: DMAxRSEL in CRYPTO_CTRL has to be set to the data registers that are to be read using the respective DMA channels on a DATATODMAx instruction. As an important note, DMAxRSEL in CRYPTO_CTRL selects what is read from **any** of the selectable read registers during an ongoing DATATODMAx transfer .

When a DMA oriented CRYPTO instruction is used (either through a STEP in a Sequence or through CRYPTO_CMD), the corresponding DMA signal is set. The instruction is complete when the entire source/destination is read/written (e.g. if DMA0TODATA is used, the operation is complete when a total of 128 valid bits have been written through the CRYPTO_DATA0 register). DMAACTIVE in CRYPTO_STATUS is set while CRYPTO is working on a DMA-related instruction, e.g. waiting for the DMA to read or write data to CRYPTO (see 30.4.8.1 DMA Initial Bytes Skip).

Normally, when a sequence or instruction is executed, access to most CRYPTO registers will stall the CPU or DMA that is trying to access CRYPTO until the operation is done, preventing accesses to CRYPTO that could potentially interfere with an operation. During DMA operations, all non-DMA registers are writeable and readable, but progress through the DMA operation will only be tracked with the registers targeted by the DMA operation (i.e., if the DMA operation is supposed to transfer 3 words to DATA0, the DMA can first choose to transfer data to e.g. DATA3, and then fulfill the transfer to DATA0).

Because the bus interface to CRYPTO is normally locked outside of DMA transfers, a wrongly set up DMA transfer (e.g., transferring one byte too many) may lock up the interface. One way to assist in debugging such issues can be setting NOBUSYSTALL in CRYPTO_CTRL. This will prevent any stall on CRYPTO register accesses during sequences and instructions. Use this option with care, as modifying a register that is being used by CRYPTO can lead to undefined behavior.

30.4.8.1 DMA Initial Bytes Skip

The DMA must be configured to use 32-bit transfer size. This normally would imply that the source data must be aligned to a 4 byte address boundary. However, it is possible to skip the initial bytes (1 to 3) when using DMA to write to DATA0 or DATA1 through a CRYPTO instruction operation. The number of bytes to skip are set in DMA0SKIP and DMA1SKIP in CRYPTO_SEQCTRL. This implies that if DMA0SKIP is set to another value than 0, the initial DMA access will require 5 DMA transfers, even though only 4x32-bit is required.

Note: Any valid unused bytes from a previous DMA write will be used before new DMA data is requested. This data is invalidated by using STOP in CRYPTO CMD.

30.4.8.2 DMA Unaligned Read/Write

Except for DATA0 and DATA1, which can be loaded bytewise using the CRYPTO_DATA0BYTE, CRYPTO_DATA0XORBYTE and CRYPTO_DATA1BYTE registers, the CRYPTO data registers are loaded 32-bits at a time. Special care must be taken when using the DMA and the data buffer is not aligned to a 32-bit address, because the DMA does not directly support 32-bit unaligned accesses.

As an example, let an in-memory 16-byte data buffer start at address 4*N + M and end at the byte before. 4*N + 16 + M, where M is between 0 and 3 inclusive. With an M=0, we have fully aligned accesses, and everything is fine. For M>0 however, the access is unaligned. If M=1, that means that the first 32-bit aligned word of the memory buffer contains 1 byte before the buffer, and 3 bytes of the buffer. Similarly, the last 32-bit aligned word of the memory buffer contains the last byte of the buffer, and three bytes after the buffer.

When doing an unaligned read, we want to only pass the 16 bytes of the buffer to the CRYPTO module. Not the N bytes before in the 32-bit aligned word, and not the 4-N words at the end. To achieve this, set DxDMAREADMODE in CRYPTO_CTRL to either UN-ALIGNEDFULL or UNALIGNEDLENLIMIT, and set DATAxDMASKIP in CRYPTO_SEQCTRL equal to N. When reading in data using a DMA-oriented instruction to DATAx, DDATAx or QDATAx, the read will now only contain the 16 bytes, and not the N bytes before or 4-N words after. Note that in this case, the DMA has to be set up to transfer 5 32-bit words instead of the effective 4.

Being able to read unaligned data does not solve all cases however. If data is to be written back to the buffer after passing through CRYPTO, e.g. when doing an in-place encryption or decryption, it is very undesirable to actually modify the N bytes before and 4-N bytes after the buffer. This is solved using the UAR-suffixed registers in CRYPTO when reading data out from the CRYPTO module, e.g. CRYPTO_DATA0UAR, CRYPTO_DATA1UAR, CRYPTO_DDATA0UAR, CRYPTO_DDATA1UAR, CRYPTO_DDATA1UAR, CRYPTO_DDATA0UAR, etc. When an unaligned buffer is written to a CRYPTO buffer, CRYPTO stores the N first bytes and the 4-N last bytes internally. When reading out from an UAR register, these bytes are placed back into the data if DATAXDMAPRES is set in CRYPTO SEQCTRL.

Note that the latter case only works if the first N and the last 4-N bytes are not changed while CRYPTO works on the data. Internally CRYPTO has 2 buffers for the bytes before and after. The first one is connected to read/write of the DATA0, DDATA0 and QDATA0 registers, and the second is connected to the DATA1, DDATA1 and QDATA1 registers.

If DMAxRMODE in CRYPTO_CTRL is set to FULL or UNALIGNEDFULL and the corresponding DMAxPRES in CRYPTO_SEQCTRL is set, then a whole number of data buffers have to be written by the DMA. In all other cases, it is enough to write the number of 32-bit words to pass all LENGTH bits to the target CRYPTO buffer.

30.4.9 BUFC Data Transfer

To allow automatic encryption/decryption or other operations on radio data, CRYPTO has instructions for moving data from and to BUFC, the Buffer Controller. Both DATA0 and DATA1 can be loaded with data from the buffer selected by READBUFSEL (CRYPTO_CTRL register) as shown in Figure 30.6 CRYPTO BUFC Data Transfer on page 1025. Similarly, the content of DATA0 and DATA1 can be written to the buffer selected by WRITEBUFSEL (also in the CRYPTO_CTRL register).




Figure 30.6. CRYPTO BUFC Data Transfer

When reading from CRYPTO to the BUFC, the number of bytes read are determined by the DMAxRMODE configuration in CRYPTO_CTRL. If it is set to either LENLIMIT or LENLIMITBYTE, only the number of bytes given by LENGTH in CRYPTO_SEQCTRL are transferred. Else the full width of the last buffer is also written, e.g. a full number of 16-byte buffers are written to the BUFC.

Note:

The buffer selected by READBUFSEL and WRITEBUFSEL in the CRYPTO_CTRL registers must be appropriately configured in the BUFC module prior to using instructions involving BUFC.

All BUFC reads start at the current BUFC read pointer, and move the pointer according to the number of bytes read. BUFC writes normally also work in the same way, starting at the current BUFC write pointer, and moving it the right number of positions. For BUFC XOR writes, software has the option to change this by setting either of DATAxTOBUFXOROW in CRYPTO_CTRL. With this bit set, the BUFC write pointer will be reset to the start of the previous write before writing to the BUFC. Using this feature, BUFC data can be written with using the DATAxTOBUFC instructions, and then XOR'ed with another set of data using the DATAxTOBUFCXOR instruction.

BUFACTIVE in CRYPTO STATUS is set while CRYPTO is reading or writing from/to the BUFC.

30.4.10 Debugging

There are multiple ways of debugging CRYPTO sequences. The most straight-forward way is to write individual instructions to INSTR in CRYPTO_CMD. An instruction can be written, and data can be read out and examined before running another instruction.

Running individual instructions to debug a program falls short when working with repeated sequences. In these cases, a sequence is run multiple times over a set of data. This cannot be directly replicated with individual instructions

To debug a sequence, set HALT in CRYPTO_SEQCTRL. When set, CRYPTO requires software or the debugger to step it through each instruction in the sequence. To step through the sequence, set SEQSTEP in CRYPTO_CMD. This will execute the current instruction, and make CRYPTO ready to execute the next one.

When stepping through a sequence, the current instruction index can be read from SEQIP in CRYPTO_CSTATUS. SEQSKIP, also in CRYPTO_CSTATUS tells whether the next instruction will be executed or not, based on previous conditionals in the program. SEQ-PART in CRYPTO_CSTATUS shows whether CRYPTO is currently in part A or B of a sequence. Even with NOBUSYSTALL in CRYPTO_CTRL cleared, read and write accesses to CRYPTO will be allowed when CRYPTO is waiting to be stepped. This is to allow data registers to be inspected during debugging.

Note: The data registers in CRYPTO (those marked read-actionable) require shifting of data in order to return the result. For this reason, reading these registers will have no effect and will return unknown values during normal debugger read accesses (see 6.3.6 Debugger Reads of Actionable Registers).

30.4.11 Example: Cipher Block Chaining (CBC)

In the following the setup and operation of CBC is explained and illustrated. The example can easily be adjusted to perform other cipher block modes.

30.4.11.1 CBC Encryption

In CBC encryption, the cipher input is the PlainText XOR'ed with the previous cipher output (an initialization vector IV is used during the first block). This mode is easily implemented using the CRYPTO instruction sequence BUFTODATA0XOR, AESENC then DATA0TOBUF. The BUFTODATA0XOR reads data from the buffer set by READBUFSEL and XOR's it with the content in DATA0. Then the cipher operation is performed and subsequently the DATA0TOBUF writes the content of DATA0 to the buffer set by WRITEBUFSEL (normally the same as READBUFSEL).

Prior to the operation, the initialization vector IV and key must be loaded to DATA0 and KEYBUF, respectively. Additionally, the total number of bytes to be included in the repeated sequence must be set in LENGTHA in CRYPTO_SEQCTRL. Finally, the buffers selected by READBUFSEL and WRITEBUFSEL must be configured correctly in the BUFC. The sequence is started by issuing the SEQ-START command in CRYPTO_CMD.

In Figure 30.7 CBC Encryption Operation on page 1027 the CBC encryption is illustrated and in Table 30.10 CBC Encryption Steps on page 1027 each step in the loop is explained.

2

Steps

 P_0

1

CBC Encryption

BUF

Figure 30.7. CBC Encryption Operation

P₁

1

 C_1

3

2

Steps

 C_0

3

Table 30.10. CBC Encryption Steps

STEP	ACTION	Description
STEP0	BUFTODATA0XOR	Move data (PlainText, P _i) from buffer to DATA0 using XOR write.
STEP1	CIPHER	The AES Cipher Core operates on DATA0
STEP2	DATA0TOBUF	The cipher output C _i is written to the buffer.

30.4.11.2 CBC Decryption

In CBC decryption, CipherText (C_i) is used as input to the Cipher Core. The output from the Cipher Core is XOR'ed with the CipherText from the previous block C_{i-1} to form the PlainText P_i (an initialization vector IV is used as C_{i-1} during the first block).

Because each block requires both C_{i-1} and C_i , decryption is somewhat more complex than encryption. Nevertheless, CBC decryption can be performed in as a repeated sequence by having C_{i-1} from the previous block stored in DATA1 and then writing it to buffer without updating the write pointer (using the DATA1TOBUF instruction). Then the cipher output is XOR'ed with C_{i-1} in the buffer by using the DATA0TOBUFXOR instruction.

In Figure 30.8 CBC Decryption Operation on page 1028 the CBC decryption is illustrated and in Table 30.11 CBC Decryption Steps on page 1028 each step in the loop is explained.

CBC Decryption




Figure 30.8. CBC Decryption Operation

Table 30.11. CBC Decryption Steps

STEP	ACTION	Description
STEP0	BUFTODATA0	Moves data (CipherText, C _i) from buffer to DATA0
STEP1	DATA1TOBUF	DATA1 (CipherText, C _{i-1}) is moved to buffer. BUFC Write pointer is not incremented!
STEP2	DATA0TODATA1	Value of DATA0 is copied to DATA1.
STEP3	CIPHER Operation	The AES Cipher Core operates on DATA0
STEP4	DATA0TOBUFXOR	The cipher output is XOR'ed with C_{i-1} (placed in the buffer at Step 2) to form the PlainText, P_i .

30.5 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	CRYPTO_CTRL	RW	Control Register
0x004	CRYPTO_WAC	RW	Wide Arithmetic Configuration
0x008	CRYPTO_CMD	W	Command Register
0x010	CRYPTO_STATUS	R	Status Register
0x014	CRYPTO_DSTATUS	R	Data Status Register
0x018	CRYPTO_CSTATUS	R	Control Status Register
0x020	CRYPTO_KEY	RWH(nB)(a)	KEY Register Access
0x024	CRYPTO_KEYBUF	RWH(nB)(a)	KEY Buffer Register Access
0x030	CRYPTO_SEQCTRL	RWH	Sequence Control
0x034	CRYPTO_SEQCTRLB	RWH	Sequence Control B
0x040	CRYPTO_IF	R	AES Interrupt Flags
0x044	CRYPTO_IFS	W1	Interrupt Flag Set Register
0x048	CRYPTO_IFC	(R)W1	Interrupt Flag Clear Register
0x04C	CRYPTO_IEN	RW	Interrupt Enable Register
0x050	CRYPTO_SEQ0	RW	Sequence Register 0
0x054	CRYPTO_SEQ1	RW	Sequence Register 1
0x058	CRYPTO_SEQ2	RW	Sequence Register 2
0x05C	CRYPTO_SEQ3	RW	Sequence Register 3
0x060	CRYPTO_SEQ4	RW	Sequence Register 4
0x080	CRYPTO_DATA0	RWH(nB)(a)	DATA0 Register Access
0x084	CRYPTO_DATA1	RWH(nB)(a)	DATA1 Register Access
0x088	CRYPTO_DATA2	RWH(nB)(a)	DATA2 Register Access
0x08C	CRYPTO_DATA3	RWH(nB)(a)	DATA3 Register Access
0x0A0	CRYPTO_DATA0XOR	RWH(nB)(a)	DATA0XOR Register Access
0x0B0	CRYPTO_DATA0BYTE	RWH(nB)(a)	DATA0 Register Byte Access
0x0B4	CRYPTO_DATA1BYTE	RWH(nB)(a)	DATA1 Register Byte Access
0x0BC	CRYPTO_DATA0XORBYTE	RWH(nB)(a)	DATA0 Register Byte XOR Access
0x0C0	CRYPTO_DATA0BYTE12	RWH(nB)	DATA0 Register Byte 12 Access
0x0C4	CRYPTO_DATA0BYTE13	RWH(nB)	DATA0 Register Byte 13 Access
0x0C8	CRYPTO_DATA0BYTE14	RWH(nB)	DATA0 Register Byte 14 Access
0x0CC	CRYPTO_DATA0BYTE15	RWH(nB)	DATA0 Register Byte 15 Access
0x100	CRYPTO_DDATA0	RWH(nB)(a)	DDATA0 Register Access
0x104	CRYPTO_DDATA1	RWH(nB)(a)	DDATA1 Register Access
0x108	CRYPTO_DDATA2	RWH(nB)(a)	DDATA2 Register Access
0x10C	CRYPTO_DDATA3	RWH(nB)(a)	DDATA3 Register Access

Offset	Name	Туре	Description
0x110	CRYPTO_DDATA4	RWH(nB)(a)	DDATA4 Register Access
0x130	CRYPTO_DDATA0BIG	RWH(nB)(a)	DDATA0 Register Big Endian Access
0x140	CRYPTO_DDATA0BYTE	RWH(nB)(a)	DDATA0 Register Byte Access
0x144	CRYPTO_DDATA1BYTE	RWH(nB)(a)	DDATA1 Register Byte Access
0x148	CRYPTO_DDATA0BYTE32	RWH(nB)	DDATA0 Register Byte 32 Access
0x180	CRYPTO_QDATA0	RWH(nB)(a)	QDATA0 Register Access
0x184	CRYPTO_QDATA1	RWH(nB)(a)	QDATA1 Register Access
0x1A4	CRYPTO_QDATA1BIG	RWH(nB)(a)	QDATA1 Register Big Endian Access
0x1C0	CRYPTO_QDATA0BYTE	RWH(nB)(a)	QDATA0 Register Byte Access
0x1C4	CRYPTO_QDATA1BYTE	RWH(nB)(a)	QDATA1 Register Byte Access

30.6 Register Description

30.6.1 CRYPTO_CTRL - Control Register

Offset															Bi	t Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset	0		0×0				0	OXO				0X0			0	UXU	0.00	OXO				0								0	0	0
Access	W.		X N				2	<u>}</u>			2	≩ Ƴ			Š	<u>^</u>	7\0	<u>}</u>				RW								₩ W	₩ M	RW
Name	COMBDMA0WEREQ		DMA1RSEL					DIVIALINOUE			L	DIMAURSEL			DMAOMODE	DIVIDADINODE	HEOWIDE					NOBUSYSTALL								SHA	KEYBUFDIS	AES

Bit	Name	Reset	Access	Description
31	COMBDMA0WEREQ	0	RW	Combined Data0 Write DMA Request
	When cleared, the DA given through DATA0		ATA0XORV	WR operate independently. When set, DATA0XORWR requests are also
30	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
29:28	DMA1RSEL	0x0	RW	DATA0 DMA Unaligned Read Register Select
	Specifies which read responses Sequence)	egister is used	for DMA1F	RD DMA requests (see related notes in 30.4.8 DMA and 30.4.3 Repeated
	Value	Mode		Description
	0	DATA1		
	1	DDATA1		
	2	QDATA1		
	3	QDATA1BIG		
27:26	Reserved	To ensure contions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
25:24	DMA1MODE	0x0	RW	DMA1 Read Mode
	This field determines			DMA

This field determines how data is read when using DMA

Value	Mode	Description
0	FULL	Target register is fully read/written during every DMA transaction
1	LENLIMIT	Length Limited. When the current length, i.e. LENGTHA or LENGTHB indicates that there are less bytes available than the register size, only length + 1 bytes + necessary zero padding is read. Zero padding is automatically added when writing.
2	FULLBYTE	Target register is fully read/written during every DMA transaction. Bytewise DMA.

Bit	Name	Reset	Access	Description
	3	LENLIMITBYT	E	Length Limited. When the current length, i.e. LENGTHA or LENGTHB indicates that there are less bytes available than the register size, only length + 1 bytes + necessary zero padding is read. Bytewise DMA. Zero padding is automatically added when writing.
23:22	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
21:20	DMA0RSEL	0x0	RW	DMA0 Read Register Select
	Specifies which read Sequence)	d register is used f	for DMA0F	RD DMA requests (see related notes in 30.4.8 DMA and 30.4.3 Repeated
	Value	Mode		Description
	0	DATA0		
	1	DDATA0		
	2	DDATA0BIG		
	3	QDATA0		
19:18	Reserved	To ensure con	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	DMA0MODE	0x0	RW	DMA0 Read Mode
	This field determines	s how data is read	d when usi	ng DMA.
	Value	Mode		Description
	0	FULL		Target register is fully read/written during every DMA transaction
	1	LENLIMIT		Length Limited. When the current length, i.e. LENGTHA or LENGTHB indicates that there are less bytes available than the register size, only length + necessary zero padding is read. Zero padding is automatically added when writing.
	2	FULLBYTE		Target register is fully read/written during every DMA transaction. Bytewise DMA.
	3	LENLIMITBYT	E	Length Limited. When the current length, i.e. LENGTHA or LENGTHB indicates that there are less bytes available than the register size, only length + necessary zero padding is read. Bytewise DMA. Zero padding is automatically added when writing.
15:14	INCWIDTH	0x0	RW	Increment Width
	This field determines	s the number of by	ytes used	for the increment function in data1.
	Value	Mode		Description
	0	INCWIDTH1		Byte 15 in DATA1 is used for the increment function.
	1	INCWIDTH2		Bytes 14 and 15 in DATA1 are used for the increment function.
	2	INCWIDTH3		Bytes 13 to 15 in DATA1 are used for the increment function.
	3	INCWIDTH4		Bytes 12 to 15 in DATA1 are used for the increment function.
13:11	Reserved	To ensure con tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
10	NOBUSYSTALL	0	RW	No Stalling of Bus When Busy
	When set, bus acces	sses will not be st	alled on a	ccess during an operation

Bit	Name	Reset	Access	Description
9:3	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
2	SHA	0	RW	SHA Mode
	Select SHA-1 or S	SHA-2 mode.		
	Value	Mode		Description
	0	SHA1		SHA-1 mode
	1	SHA2		SHA-2 mode (SHA-224 or SHA-256)
1	KEYBUFDIS	0	RW	Key Buffer Disable
	Set to Disable key	buffering.		
0	AES	0	RW	AES Mode
	Select AES mode			
	Value	Mode		Description
	0	AES128		AES-128 mode
	1	AES256		AES-256 mode

30.6.2 CRYPTO_WAC - Wide Arithmetic Configuration

Offset				Bit Position	<u> </u>				
0x004	30 30 29 28 28 27 27	24 25 23 22 22	20 20 2	8 7 9 5 2	5 5	တ ထ	6 7	4	0 7 2 3
Reset					0×0	0×0		0	0×0
Access					A W	RW		R M M	RW
					HTC				
Name					RESULTWIDTH	DTH		0	sn-
					SUL	MULWIDTH		MODOP	MODULUS
					<u> </u>	Ĭ		ž	ĕ
Bit	Name	Reset	Access	Description					
31:12	Reserved	To ensure con tions	npatibility v	vith future devices, always w	rite bits t	o 0. Mo	re informatio	on in	1.2 Conven-
11:10	RESULTWIDTH	0x0	RW	Result Width					
	Result-size for non-n	nodulus instructio	ns						
	Value	Mode		Description					
	0	256BIT		Results have 256 bits					
	1	128BIT		Results have 128 bits					
	2	260BIT		Results have 260 bits. Upp TA0MSBS in CRYPTO_ST		result o	can be read	thro	ugh DDA-
9:8	MULWIDTH	0x0	RW	Multiply Width					
	Number of bits to mu	ultiply on non-mod	lulus multi _l	oly instruction					
	Value	Mode		Description					
	Value								
	0	MUL256		Multiply 256 bits					
				Multiply 256 bits Multiply 128 bits					
	0	MUL256		· •	ecified b	y MODL	JLUS		
7:5	0	MUL256 MUL128 MULMOD	npatibility v	Multiply 128 bits				on in	1.2 Conven-
7:5	0 1 2	MUL256 MUL128 MULMOD To ensure con	npatibility v	Multiply 128 bits Same number of bits as sp	rite bits t			on in	1.2 Conven-
	0 1 2 Reserved	MUL256 MUL128 MULMOD To ensure contions 0	RW	Multiply 128 bits Same number of bits as sp with future devices, always w	rite bits t			on in	1.2 Conven-
	0 1 2 Reserved MODOP	MUL256 MUL128 MULMOD To ensure contions 0	RW	Multiply 128 bits Same number of bits as sp with future devices, always w	rite bits t			on in	1.2 Conven-
	0 1 2 Reserved MODOP Field type used for m	MUL256 MUL128 MULMOD To ensure contions 0 nodular operations	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field	rite bits t	o 0. Mo	re informatio		
	0 1 2 Reserved MODOP Field type used for m	MUL256 MUL128 MULMOD To ensure contions 0 nodular operations Mode	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field Description	Type OR as rec	o 0. Mo	re information	orith	nms
	0 1 2 Reserved MODOP Field type used for m Value 0	MUL256 MUL128 MULMOD To ensure contions 0 nodular operations Mode BINARY	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field Description Modular operations use XC	Type OR as recormal modern	o 0. Mo	re information	orith	nms
4	0 1 2 Reserved MODOP Field type used for m Value 0 1	MUL256 MUL128 MULMOD To ensure contions 0 modular operations Mode BINARY REGULAR 0x0	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field Description Modular operations use XC Modular operations use no	Type OR as recormal modern	o 0. Mo	re information	orith	nms
4	0 1 2 Reserved MODOP Field type used for m Value 0 1 MODULUS	MUL256 MUL128 MULMOD To ensure contions 0 modular operations Mode BINARY REGULAR 0x0	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field Description Modular operations use XC Modular operations use no	Type OR as recormal modern	o 0. Mo	re information	orith	nms
4	0 1 2 Reserved MODOP Field type used for modulus used for modulus used for modulus	MUL256 MUL128 MULMOD To ensure contions 0 nodular operations Mode BINARY REGULAR 0x0 odular operations	RW	Multiply 128 bits Same number of bits as sp with future devices, always w Modular Operation Field Description Modular operations use XC Modular operations use no	Type OR as recommal modellus	o 0. Mo	re information	orith	nms

Bit	Name	Reset A	ccess	Description
	1	BIN128		Generic modulus. p = 2^128
	2	ECCBIN233P		Modulus for B-233 and K-233 ECC curves. p(t) = t^233 + t^74 + 1
	3	ECCBIN163P		Modulus for B-163 and K-163 ECC curves. $p(t) = t^163 + t^7 + t^6 + t^3 + 1$
	4	GCMBIN128		Modulus for GCM. $P(t) = t^128 + t^7 + t^2 + t + 1$
	5	ECCPRIME256P		Modulus for P-256 ECC curve. p = 2^256 - 2^224 + 2^192 + 2^96 - 1
	6	ECCPRIME224P		Modulus for P-224 ECC curve. p = 2^224 - 2^96 - 1
	7	ECCPRIME192P		Modulus for P-192 ECC curve. p = 2^192 - 2^64 - 1
	8	ECCBIN233N		P modulus for B-233 ECC curve
	9	ECCBIN233KN		P modulus for K-233 ECC curve
	10	ECCBIN163N		P modulus for B-163 ECC curve
	11	ECCBIN163KN		P modulus for K-163 ECC curve
	12	ECCPRIME256N		P modulus for P-256 ECC curve
	13	ECCPRIME224N		P modulus for P-224 ECC curve
	14	ECCPRIME192N		P modulus for P-192 ECC curve

30.6.3 CRYPTO_CMD - Command Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	2	4	က	2	_	0
Reset			•		•	•						•		•	•			•		•	0	0	0						0000			
Access																					W	×	×					}	>			
Name																					SEQSTEP	SEQSTOP	SEQSTART					O F OI N				

Bit	Name	Reset	Access	Description
31:12	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
11	SEQSTEP	0	W1	Sequence Step
	When in a halted seq	uence, executes	s the currer	nt instruction and moves to the next
10	SEQSTOP	0	W1	Sequence Stop
	Set to stop encryption	n/decryption rega	ardless of i	t being a single or a SEQUENCE.
9	SEQSTART	0	W1	Encryption/Decryption SEQUENCE Start
	Set to start encryption	n/decryption SE	QUENCE.	
8	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	INSTR	0x00	W	Execute Instruction

Write to this field to perform any of the instructions described below. Illegal values are ignored. See 30.4.2.2 Available Instructions for details and requirements of each instruction

Value	Mode	Description
0	END	End of program
1	EXEC	Start executing instructions up to this point, which also marks end of program
3	DATA1INC	See detailed instruction listing
4	DATA1INCCLR	See detailed instruction listing
5	AESENC	AES Encryption
6	AESDEC	AES Decryption
7	SHA	SHA
8	ADD	Add
9	ADDC	Add with carry
12	MADD	Modular addition
13	MADD32	Word-wise addition
16	SUB	Subtract
17	SUBC	Subtract with carry
20	MSUB	Modular subtraction

Bit	Name	Reset Access	Description
	24	MUL	Multiply
	25	MULC	See detailed instruction listing
	28	MMUL	Modular multiplication
	29	MULO	See detailed instruction listing
	32	SHL	Shift left
	33	SHLC	Shift left with carry (Rotate left)
	34	SHLB	See detailed instruction listing
	35	SHL1	See detailed instruction listing
	36	SHR	Shift right
	37	SHRC	Shift right with carry (Rotate right)
	38	SHRB	See detailed instruction listing
	39	SHR1	See detailed instruction listing
	40	ADDO	See detailed instruction listing
	41	ADDIC	See detailed instruction listing
	48	CLR	Clear DDATA0
	49	XOR	XOR
	50	INV	Invert operand
	52	CSET	Carry set
	53	CCLR	Carry clear
	54	BBSWAP128	See detailed instruction listing
	56	INC	Increment DDATA0
	57	DEC	Decrement DDATA0
	62	SHRA	Arithmetic shift right
	64	DATA0TODATA0	DATA0 = DATA0
	65	DATA0TODATA0XOR	DATA0 = DATA0 ^ DATA0
	66	DATA0TODATA0XOR- LEN	DATA0[len-1:0] = DATA0[len-1:0] ^ DATA0[len-1:0]
	68	DATA0TODATA1	DATA1 = DATA0
	69	DATA0TODATA2	DATA2 = DATA0
	70	DATA0TODATA3	DATA3 = DATA0
	72	DATA1TODATA0	DATA0 = DATA1
	73	DATA1TODATA0XOR	DATA0 = DATA0 ^ DATA1
	74	DATA1TODATA0XOR- LEN	DATA0[len-1:0] = DATA0[len-1:0] ^ DATA1[len-1:0]
	77	DATA1TODATA2	DATA2 = DATA1
	78	DATA1TODATA3	DATA3 = DATA1
	80	DATA2TODATA0	DATA0 = DATA2
	81	DATA2TODATA0XOR	DATA0 = DATA0 ^ DATA2

-			
Bit	Name	Reset Access	Description
	82	DATA2TODATA0XOR- LEN	DATA0[len-1:0] = DATA0[len-1:0] ^ DATA2[len-1:0]
	84	DATA2TODATA1	DATA1 = DATA2
	86	DATA2TODATA3	DATA3 = DATA2
	88	DATA3TODATA0	DATA0 = DATA3
	89	DATA3TODATA0XOR	DATA0 = DATA0 ^ DATA3
	90	DATA3TODATA0XOR- LEN	DATA0[len-1:0] = DATA0[len-1:0] ^ DATA3[len-1:0]
	92	DATA3TODATA1	DATA1 = DATA3
	93	DATA3TODATA2	DATA2 = DATA3
	99	DATATODMA0	See detailed instruction listing
	100	DATA0TOBUF	See detailed instruction listing
	101	DATA0TOBUFXOR	See detailed instruction listing
	107	DATATODMA1	See detailed instruction listing
	108	DATA1TOBUF	See detailed instruction listing
	109	DATA1TOBUFXOR	See detailed instruction listing
	112	DMA0TODATA	See detailed instruction listing
	113	DMA0TODATAXOR	See detailed instruction listing
	114	DMA1TODATA	See detailed instruction listing
	120	BUFTODATA0	See detailed instruction listing
	121	BUFTODATA0XOR	See detailed instruction listing
	122	BUFTODATA1	See detailed instruction listing
	129	DDATA0TODDATA1	DDATA1 = DDATA0
	130	DDATA0TODDATA2	DDATA2 = DDATA0
	131	DDATA0TODDATA3	DDATA3 = DDATA0
	132	DDATA0TODDATA4	DDATA4 = DDATA0
	133	DDATA0LTODATA0	DATA0 = DDATA0[127:0]
	134	DDATA0HTODATA1	DATA1 = DDATA0[255:128]
	135	DDATA0LTODATA2	DATA2 = DDATA0[127:0]
	136	DDATA1TODDATA0	DDATA0 = DDATA1
	138	DDATA1TODDATA2	DDATA2 = DDATA1
	139	DDATA1TODDATA3	DDATA3 = DDATA1
	140	DDATA1TODDATA4	DDATA4 = DDATA1
	141	DDATA1LTODATA0	DATA0 = DDATA1[127:0]
	142	DDATA1HTODATA1	DATA1 = DDATA1[255:128]
	143	DDATA1LTODATA2	DATA2 = DDATA1[127:0]
	144	DDATA2TODDATA0	DDATA0 = DDATA2
	145	DDATA2TODDATA1	DDATA1 = DDATA2

147 DDATA2TODDATA3 DDATA3 = DDATA2 148 DDATA2TODDATA4 DDATA4 = DDATA2 151 DDATA2TODDATA4 DATA2 = DDATA2 152 DDATA3TODDATA1 DDATA1 = DDATA3 153 DDATA3TODDATA1 DDATA1 = DDATA3 154 DDATA3TODDATA2 DDATA2 = DDATA3 156 DDATA3TODDATA2 DDATA2 = DDATA3 157 DDATA3TODDATA0 DATA6 = DDATA3 158 DDATA3TODDATA0 DATA6 = DDATA3 159 DDATA3TODDATA1 DATA1 = DDATA3 150 DDATA3TODDATA0 DATA6 = DDATA3 157 DDATA3TODDATA0 DATA6 = DDATA3 [127:0] 158 DDATA3TODDATA1 DATA1 = DDATA4 160 DDATA4TODDATA1 DATA1 = DDATA4 161 DDATA4TODDATA1 DATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA2 DATA2 = DDATA4 164 DDATA4TODATA1 DATA1 = DDATA4[127:0] 166 DDATA4TODATA2 DATA6 = DDATA4[127:0] 166 DDATA4TODATA2 DATA6 = DDATA4[127:0] 168 DATA6TODDATA0 DATA6 = DATA6 169 DATA6TODDATA1 DATA1 = DATA6 169 DATA6TODDATA1 DATA1 = DATA6 169 DATA6TODDATA1 DATA1 = DATA6 169 DATA6TODDATA1 DATA1 = DATA6 169 DATA6TODDATA1 DATA1 = DATA6 177 DATA1TODDATA1 DATA1 = DATA6 184 DATA6TODDATA1 DATA1 = DATA6 185 DATA6TODDATA1 DATA1 = DATA6 186 DATA6TODDATA1 DATA1 = DATA6 187 DATA1 DDATA1 = DATA6 188 DATA6TODDATA1 DATA1 = DATA6 189 DATA6TODDATA1 DATA1 = DATA6 180 DATA6TODDATA1 DATA1 = DATA6 181 DATA6TODDATA1 DATA1 = DATA6 182 DATA6TODDATA1 DATA1 = DATA6 185 DATA6TODDATA1 DATA1 = DATA6 186 DATA6TODDATA1 DATA1 = DATA6 187 DATA6TODDATA1 DATA1 = DATA6 188 DATA6TODDATA1 DATA1 = DATA6 189 SELDATA6DDATA0 Use DATA6 as V0, DATA6 as V1 190 SELDATA6DDATA0 Use DATA6 as V0, DATA6 as V1 191 SELDATA6DDATA0 Use DATA6 as V0, DATA6 as V1 192 SELDATA6DDATA0 Use DATA6 as V0, DATA6 as V1 193 SELDATA6DDATA0 Use DATA6 as V0, DATA6 as V1 199 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 199 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 199 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 199 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 199 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 190 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 190 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1 190 SELDATA6DDATA1 Use DATA6 as V0, DATA6 as V1	Bit	Name	Reset Access	Description
151 DDATA2LTODATA2 DATA2 = DDATA3 152 DDATA3TODDATA0 DDATA0 = DDATA3 153 DDATA3TODDATA1 DDATA1 = DDATA3 154 DDATA3TODDATA2 DDATA2 = DDATA3 156 DDATA3TODDATA4 DDATA3 DDATA3 157 DDATA3LTODATA0 DATA4 = DDATA3 157 DDATA3LTODATA0 DATA1 = DDATA3 158 DDATA3HTODATA1 DATA1 = DDATA3 159 DDATA3HTODATA1 DATA1 = DDATA4 160 DDATA4TODDATA1 DDATA1 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA2 DATA2 = DDATA4 165 DDATA4LTODATA0 DATA2 = DDATA4 165 DDATA4LTODATA1 DATA1 = DDATA4 166 DDATA4HTODATA1 DATA1 = DDATA4 167 DDATA4LTODATA2 DATA2 = DDATA4 168 DATA0TODDATA1 DATA1 = DDATA4 169 DATA0TODDATA0 DATA0 = DATA0 169 DATA0TODDATA1 DATA1 = DATA0 170 DATA1TODDATA1 DATA1 = DATA0 171 DATA1TODDATA1 DDATA1 = DATA0 172 DATA1TODDATA1 DATA1 = DATA0 173 DATA1TODDATA1 DDATA1 = DATA1 174 DATA1TODDATA1 DDATA1 = DATA1 175 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA1 DDATA1 = DATA2 187 DATA1 = DATA0 198 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 199 SELDDATA0DDATA0 Use DDATA4 as V0, DDATA0 as V1 190 SELDDATA0DDATA0 Use DDATA4 as V0, DDATA0 as V1 191 SELDDATA0DDATA0 Use DDATA4 as V0, DDATA0 as V1 196 SELDDATA0DDATA0 Use DATA3 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA3 as V0, DDATA0 as V1 198 SELDATA0DDATA0 Use DATA3 as V0, DDATA0 as V1 199 SELDATA0DDATA1 Use DATA3 as V0, DDATA0 as V1 190 SELDATA0DDATA1 Use DATA2 as V0, DDATA0 as V1 190 SELDATA0DDATA1 Use DATA3 as V0, DDATA1 as V1 200 SELDATA0DDATA1 Use DATA3 as V0, DDATA1 as V1 201 SELDATA0DATA1 Use DATA3 as V0, DDATA1 as V1 202 SELDATA0DATA1 Use DATA3 as V0, DDATA1 as V1 203 SELDATA0DATA1 Use DATA3 as V0, DDATA1 as V1 204 SELDATA0DA		147	DDATA2TODDATA3	DDATA3 = DDATA2
152 DDATA3TODDATA0 DDATA0 = DDATA3 153 DDATA3TODDATA1 DDATA1 = DDATA3 154 DDATA3TODDATA2 DDATA2 = DDATA3 156 DDATA3TODDATA2 DDATA2 = DDATA3 157 DDATA3LTODATA0 DATA0 = DDATA3[127:0] 158 DDATA3HTODATA1 DATA1 = DDATA3[127:0] 158 DDATA3HTODATA1 DATA1 = DDATA3[127:0] 160 DDATA4TODDATA1 DATA1 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA3 DDATA3 = DDATA4 164 DDATA4TODDATA3 DDATA3 = DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 168 DATA0TODDATA1 DATA1 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 176 DATA1TODDATA1 DDATA1 = DATA0 177 DATA1TODDATA0 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA1 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA0 DDATA0 = DATA2 187 DATA1 = DATA2 188 DATA2TODDATA0 DDATA1 = DATA2 189 DATA0TODDATA1 DDATA1 = DATA2 180 DATA2 = DDATA4 = DATA2 191 DATA1 = DATA2 192 SELDDATA0DATA0 DDATA1 = DATA2 193 SELDDATA0DATA0 DDATA2 = DATA2 194 SELDDATA0DATA0 DDATA2 = DATA2 195 SELDDATA0DDATA0 Use DATA3 as V0, DDATA0 as V1 196 SELDDATA3DDATA0 Use DATA3 as V0, DDATA0 as V1 197 SELDATA3DDATA0 Use DATA4 as V0, DDATA0 as V1 198 SELDATA2DDATA0 Use DATA4 as V0, DDATA0 as V1 199 SELDATA2DDATA0 Use DATA1 as V0, DDATA0 as V1 199 SELDATA2DDATA1 Use DATA1 as V0, DDATA1 as V1 200 SELDATA2DDATA1 Use DATA2 as V0, DDATA1 as V1 201 SELDATA3DDATA1 Use DATA2 as V0, DDATA1 as V1 202 SELDATA3DDATA1 Use DATA2 as V0, DDATA1 as V1		148	DDATA2TODDATA4	DDATA4 = DDATA2
153 DATASTODDATA1 DDATA1 = DDATA3 154 DDATASTODDATA2 DDATA2 = DDATA3 156 DDATASTODDATA4 DDATA4 = DDATA3 157 DDATASLTODATA0 DATA6 = DDATA3[127:0] 158 DDATASHTODATA1 DATA1 = DDATA3[25:128] 160 DDATA4TODDATA1 DDATA4 = DDATA4 161 DDATA4TODDATA1 DDATA4 = DDATA4 162 DDATA4TODDATA2 DDATA4 = DDATA4 163 DDATA4TODDATA3 DDATA4 = DDATA4 165 DDATA4LTODATA3 DDATA5 = DDATA4 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[127:0] 167 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DDATA6[127:0] 169 DATA0TODDATA1 DDATA6 = DATA0 170 DATA11ODDATA1 DDATA1 = DATA0 171 DATA11ODDATA1 DDATA1 = DATA0 172 DATA11ODDATA1 DDATA1 = DATA0 173 DATA17ODDATA1 DDATA1 = DATA1 174 DATA17ODDATA1 DDATA1 = DATA2 185 DATA2TODDATA0 DDATA0 = DATA2 186 DATA2TODDATA0 DDATA0 = DATA2 186 DATA2TODDATA0 DDATA1 = DATA2 186 DATA2TODDATA0 DDATA1 = DATA2 186 DATA2TODDATA0 DDATA1 = DATA2 186 DATA2TODDATA0 DDATA1 = DATA2 187 SELDDATA0DDATA0 DDATA1 = DATA2 188 DATA2TODDATA0 DDATA1 = DATA2 199 SELDDATA0DDATA0 Use DDATA0 as V0 DDATA0 as V1 191 SELDDATA1DDATA0 Use DDATA0 as V0 DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA0 as V0 DDATA0 as V1 194 SELDDATA2DDATA0 Use DATA0 as V0 DDATA0 as V1 195 SELDDATA2DDATA0 Use DATA1 as V0 DDATA0 as V1 198 SELDATA2DDATA0 Use DATA1 as V0 DDATA0 as V1 199 SELDATA2DDATA0 Use DATA1 as V0 DDATA1 as V1 199 SELDATA2DDATA1 Use DATA1 as V0 DDATA1 as V1 200 SELDATA2DDATA1 Use DATA2 as V0 DDATA1 as V1 201 SELDATA3DDATA1 Use DATA3 as V0 DDATA1 as V1 202 SELDATA3DDATA1 Use DATA3 as V0 DDATA1 as V1 203 SELDATA3DDATA1 Use DATA3 as V0 DDATA1 as V1 204 SELDATA3DDATA1 Use DATA3 as V0 DDATA1 as V1		151	DDATA2LTODATA2	DATA2 = DDATA2[127:0]
154 DDATA3TODDATA2 DDATA3 = DDATA3 156 DDATA3TODDATA4 DDATA4 = DDATA3 157 DDATA3LTODATA0 DATA0 = DDATA3[127:0] 158 DDATA3HTODATA1 DATA1 = DDATA3[255:128] 160 DDATA4TODDATA0 DDATA0 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4HODDATA1 DDATA2 = DDATA4 163 DDATA4TODDATA2 DDATA3 = DDATA4 165 DDATA4HODDATA3 DDATA3 = DDATA4[127:0] 166 DDATA4HTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[27:0] 167 DDATA4HTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA1 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA1 = DATA1 177 DATA1TODDATA0 DDATA1 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDATA0DDATA0 Use DDATA3 as V0, DDATA0 as V1		152	DDATA3TODDATA0	DDATA0 = DDATA3
156 DDATA3TODDATA4 DDATA4 = DDATA3 157 DDATA3LTODATA0 DATA0 = DDATA3[127:0] 158 DDATA3HTODATA1 DATA1 = DDATA3[255:128] 160 DDATA4TODDATA0 DDATA0 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA3 DDATA3 = DDATA4 166 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 167 DDATA4LTODATA2 DDATA0 = DATA0 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA0 DDATA0 = DATA0 176 DATA1TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA1 DDATA1 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 177 DATA1TODDATA1 DDATA2 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA3DODATA0 DDATA0 = DATA2 193 SELDDATA3DODATA0 Use DDATA0 as V0, DDATA0 as V1 <td< td=""><th></th><td>153</td><td>DDATA3TODDATA1</td><td>DDATA1 = DDATA3</td></td<>		153	DDATA3TODDATA1	DDATA1 = DDATA3
157 DDATA3LTODATA0 DATA0 = DDATA3[127:0] 158 DDATA3HTODATA1 DATA1 = DDATA3[255:128] 160 DDATA4TODDATA0 DDATA0 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA3 DDATA3 = DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 166 DDATA4LTODATA1 DATA1 = DDATA4[127:0] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA1 DATA1 = DATA0 169 DATA0TODDATA1 DDATA0 = DATA0 170 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA1 DDATA1 = DATA2 185 DATA2TODDATA0 DDATA0 = DATA2 186 DATA2TODDATA1 DDATA1 = DATA2 192 SELDDATA0DATA2 DDATA2 = DATA2 193 SELDDATA1DDATA0 Use DDATA0 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA1 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA4 as V0, DDATA0 as V1 199 SELDATA1DDATA0 Use DATA2 as V0, DDATA0 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA0 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA0 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA0 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 199 SELDATA2DDATA1 Use DATA2 as V0, DDATA2 as V1 200 SELDATA2DDATA1 Use DATA2 as V0, DDATA1 as V1 201 SELDATA2DDATA1 Use DATA2 as V0, DDATA1 as V1 202 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 203 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 204 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 205 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 206 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 207 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 208 SELDATA3DDATA1 Use DATA3 as V0, DDATA1 as V1 209 SELD		154	DDATA3TODDATA2	DDATA2 = DDATA3
DDATA3HTODATA1 DATA1 = DDATA3[255:128]		156	DDATA3TODDATA4	DDATA4 = DDATA3
160 DDATA4TODDATA0 DDATA0 = DDATA4 161 DDATA4TODDATA1 DDATA1 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA3 DDATA3 = DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA1 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA1 DDATA1 = DATA2 185 DATA2TODDATA1 DDATA2 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA1 as V0, DDATA0 as V1 193 SELDDATA3DDATA0 Use DDATA2 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA3 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDATA0DDATA0 Use DATA0		157	DDATA3LTODATA0	DATA0 = DDATA3[127:0]
161 DDATA4TODDATA1 DDATA4 = DDATA4 162 DDATA4TODDATA2 DDATA2 = DDATA4 163 DDATA4TODDATA3 DDATA3 = DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA0 DDATA1 = DATA1 184 DATA2TODDATA1 DDATA1 = DATA2 185 DATA2TODDATA0 DDATA2 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA3DDATA0 Use DDATA2 as V0, DDATA0 as V1 194 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA4 as V0, DDATA0 as V1 196 SELDATA3DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA2DDATA0		158	DDATA3HTODATA1	DATA1 = DDATA3[255:128]
162 DDATA4TODDATA2 DDATA4 163 DDATA4TODDATA3 DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4LTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA1 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA2 = DATA2 185 DATA2TODDATA0 DDATA2 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA0DDATA0 Use DDATA2 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA3 as V0, DDATA0 as V1 195 SELDATA3DDATA0 Use DATA4 as V0, DDATA0 as V1 196 SELDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 198 SELDATA4DDATA0 Use DATA2 as V0, DDATA0 as V1 199 SELDATA2DDATA1 Us		160	DDATA4TODDATA0	DDATA0 = DDATA4
163 DDATA4TODDATA3 DDATA4 165 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA0 DDATA2 = DATA2 186 DATA2TODDATA1 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA4 as V0, DDATA0 as V1 196 SELDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA4DDATA0 Use DATA1 as V0, DDATA0 as V1 198 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDATA2D		161	DDATA4TODDATA1	DDATA1 = DDATA4
165 DDATA4LTODATA0 DATA0 = DDATA4[127:0] 166 DDATA4HTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA0DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA3DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA4 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA1DDATA0 Use DATA1 as V0, DDATA0 as V1 198 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 201<		162	DDATA4TODDATA2	DDATA2 = DDATA4
166 DDATA4HTODATA1 DATA1 = DDATA4[255:128] 167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA1 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 200 SELDDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 201 SELDDATA0DDATA1 Use DDATA2 as V0, DDATA1 as V1		163	DDATA4TODDATA3	DDATA3 = DDATA4
167 DDATA4LTODATA2 DATA2 = DDATA4[127:0] 168 DATA0TODDATA0 DDATA0 = DATA0 169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA1 as V0, DDATA1 as V1 198 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDATA2DDATA0 Use DATA1 as V0, DDATA1 as V1 201 SELDDATA4DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA3DDATA1 Use DDATA2 as V0, DDATA1 as V1		165	DDATA4LTODATA0	DATA0 = DDATA4[127:0]
168 DATAOTODDATAO DDATAO = DATAO 169 DATAOTODDATA1 DDATA1 = DATAO 176 DATA1TODDATAO DDATAO = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATAO Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA1DDATA0 Use DATA1 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA2 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1 <th></th> <td>166</td> <td>DDATA4HTODATA1</td> <td>DATA1 = DDATA4[255:128]</td>		166	DDATA4HTODATA1	DATA1 = DDATA4[255:128]
169 DATA0TODDATA1 DDATA1 = DATA0 176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA2 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA2 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA1 as V0, DDATA1 as V1 198 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDDATA0DDATA1 Use DATA2 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA2 as V0, DDATA1 as V1 202 SELDDATA3DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		167	DDATA4LTODATA2	DATA2 = DDATA4[127:0]
176 DATA1TODDATA0 DDATA0 = DATA1 177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDATA2DDATA1 Use DATA0 as V0, DDATA1 as V1 201 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA3 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		168	DATA0TODDATA0	DDATA0 = DATA0
177 DATA1TODDATA1 DDATA1 = DATA1 184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA1 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 200 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		169	DATA0TODDATA1	DDATA1 = DATA0
184 DATA2TODDATA0 DDATA0 = DATA2 185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA2 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		176	DATA1TODDATA0	DDATA0 = DATA1
185 DATA2TODDATA1 DDATA1 = DATA2 186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA1 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA2 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		177	DATA1TODDATA1	DDATA1 = DATA1
186 DATA2TODDATA2 DDATA2 = DATA2 192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		184	DATA2TODDATA0	DDATA0 = DATA2
192 SELDDATA0DDATA0 Use DDATA0 as V0, DDATA0 as V1 193 SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA2 as V0, DDATA1 as V1		185	DATA2TODDATA1	DDATA1 = DATA2
SELDDATA1DDATA0 Use DDATA1 as V0, DDATA0 as V1 194 SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA2 as V0, DDATA1 as V1 204 SELDDATA3DDATA1 Use DDATA2 as V0, DDATA1 as V1		186	DATA2TODDATA2	DDATA2 = DATA2
SELDDATA2DDATA0 Use DDATA2 as V0, DDATA0 as V1 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 SELDATA2DDATA1 Use DDATA0 as V0, DDATA1 as V1 SELDDATA1DDATA1 Use DDATA1 as V1 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		192	SELDDATA0DDATA0	Use DDATA0 as V0, DDATA0 as V1
195 SELDDATA3DDATA0 Use DDATA3 as V0, DDATA0 as V1 196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		193	SELDDATA1DDATA0	Use DDATA1 as V0, DDATA0 as V1
196 SELDDATA4DDATA0 Use DDATA4 as V0, DDATA0 as V1 197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		194	SELDDATA2DDATA0	Use DDATA2 as V0, DDATA0 as V1
197 SELDATA0DDATA0 Use DATA0 as V0, DDATA0 as V1 198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		195	SELDDATA3DDATA0	Use DDATA3 as V0, DDATA0 as V1
198 SELDATA1DDATA0 Use DATA1 as V0, DDATA1 as V1 199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		196	SELDDATA4DDATA0	Use DDATA4 as V0, DDATA0 as V1
199 SELDATA2DDATA0 Use DATA2 as V0, DDATA2 as V1 200 SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		197	SELDATA0DDATA0	Use DATA0 as V0, DDATA0 as V1
SELDDATA0DDATA1 Use DDATA0 as V0, DDATA1 as V1 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		198	SELDATA1DDATA0	Use DATA1 as V0, DDATA1 as V1
201 SELDDATA1DDATA1 Use DDATA1 as V0, DDATA1 as V1 202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		199	SELDATA2DDATA0	Use DATA2 as V0, DDATA2 as V1
202 SELDDATA2DDATA1 Use DDATA2 as V0, DDATA1 as V1 203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		200	SELDDATA0DDATA1	Use DDATA0 as V0, DDATA1 as V1
203 SELDDATA3DDATA1 Use DDATA3 as V0, DDATA1 as V1		201	SELDDATA1DDATA1	Use DDATA1 as V0, DDATA1 as V1
		202	SELDDATA2DDATA1	Use DDATA2 as V0, DDATA1 as V1
204 SELDDATA4DDATA1 Use DDATA4 as V0, DDATA1 as V1		203	SELDDATA3DDATA1	Use DDATA3 as V0, DDATA1 as V1
		204	SELDDATA4DDATA1	Use DDATA4 as V0, DDATA1 as V1
205 SELDATA0DDATA1 Use DATA0 as V0, DDATA0 as V1		205	SELDATA0DDATA1	Use DATA0 as V0, DDATA0 as V1

Bit	Name	Reset Access	Description
	206	SELDATA1DDATA1	Use DATA1 as V0, DDATA1 as V1
	207	SELDATA2DDATA1	Use DATA2 as V0, DDATA2 as V1
	208	SELDDATA0DDATA2	Use DDATA0 as V0, DDATA2 as V1
	209	SELDDATA1DDATA2	Use DDATA1 as V0, DDATA2 as V1
	210	SELDDATA2DDATA2	Use DDATA2 as V0, DDATA2 as V1
	211	SELDDATA3DDATA2	Use DDATA3 as V0, DDATA2 as V1
	212	SELDDATA4DDATA2	Use DDATA4 as V0, DDATA2 as V1
	213	SELDATA0DDATA2	Use DATA0 as V0, DDATA0 as V1
	214	SELDATA1DDATA2	Use DATA1 as V0, DDATA1 as V1
	215	SELDATA2DDATA2	Use DATA2 as V0, DDATA2 as V1
	216	SELDDATA0DDATA3	Use DDATA0 as V0, DDATA3 as V1
	217	SELDDATA1DDATA3	Use DDATA1 as V0, DDATA3 as V1
	218	SELDDATA2DDATA3	Use DDATA2 as V0, DDATA3 as V1
	219	SELDDATA3DDATA3	Use DDATA3 as V0, DDATA3 as V1
	220	SELDDATA4DDATA3	Use DDATA4 as V0, DDATA3 as V1
	221	SELDATA0DDATA3	Use DATA0 as V0, DDATA0 as V1
	222	SELDATA1DDATA3	Use DATA1 as V0, DDATA1 as V1
	223	SELDATA2DDATA3	Use DATA2 as V0, DDATA2 as V1
	224	SELDDATA0DDATA4	Use DDATA0 as V0, DDATA4 as V1
	225	SELDDATA1DDATA4	Use DDATA1 as V0, DDATA4 as V1
	226	SELDDATA2DDATA4	Use DDATA2 as V0, DDATA4 as V1
	227	SELDDATA3DDATA4	Use DDATA3 as V0, DDATA4 as V1
	228	SELDDATA4DDATA4	Use DDATA4 as V0, DDATA4 as V1
	229	SELDATA0DDATA4	Use DATA0 as V0, DDATA4 as V1
	230	SELDATA1DDATA4	Use DATA1 as V0, DDATA4 as V1
	231	SELDATA2DDATA4	Use DATA2 as V0, DDATA4 as V1
	232	SELDDATA0DATA0	Use DDATA0 as V0, DATA0 as V1
	233	SELDDATA1DATA0	Use DDATA1 as V0, DATA0 as V1
	234	SELDDATA2DATA0	Use DDATA2 as V0, DATA0 as V1
	235	SELDDATA3DATA0	Use DDATA3 as V0, DATA0 as V1
	236	SELDDATA4DATA0	Use DDATA4 as V0, DATA0 as V1
	237	SELDATA0DATA0	Use DATA0 as V0, DATA0 as V1
	238	SELDATA1DATA0	Use DATA1 as V0, DATA0 as V1
	239	SELDATA2DATA0	Use DATA2 as V0, DATA0 as V1
	240	SELDDATA0DATA1	Use DDATA0 as V0, DATA1 as V1
	241	SELDDATA1DATA1	Use DDATA1 as V0, DATA1 as V1
	242	SELDDATA2DATA1	Use DDATA2 as V0, DATA1 as V1

Bit	Name	Reset	Access	Description
	243	SELDDATA3E	DATA1	Use DDATA3 as V0, DATA1 as V1
	244	SELDDATA40	DATA1	Use DDATA4 as V0, DATA1 as V1
	245	SELDATA0DA	TA1	Use DATA0 as V0, DATA1 as V1
	246	SELDATA1DA	TA1	Use DATA1 as V0, DATA1 as V1
	247	SELDATA2DA	TA1	Use DATA2 as V0, DATA1 as V1
	248	EXECIFA		Run following if in A sequence
	249	EXECIFB		Run following if in B sequence
	250	EXECIFNLAS	Т	Run following if in last iteration of combined A and B sequence
	251	EXECIFLAST		Run following if in last iteration of combined A and B sequence
	252	EXECIFCARE	Υ	Run following if CARRY bit is set
	253	EXECIFNCAR	EXECIFNCARRY Ru	Run following if CARRY bit is not set
	254	EXECALWAY	S	Resume execution

30.6.4 CRYPTO_STATUS - Status Register

Offset		Bit Position																														
0x010	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset			•																				•							0	0	0
Access																														2	œ	ď
Name																														DMAACTIVE	INSTRRUNNING	SEQRUNNING

Bit	Name	Reset	Access	Description								
31:3	Reserved	To ensure co	o ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conve ons									
2	DMAACTIVE	0	R DMA Action is Active									
	This bit indicates tha	t the AES modul	AES module is waiting for a DMA transfer to complete.									
1	INSTRRUNNING	0	R	Action is Active								
	This bit indicates that TO_CMD or due to a		•	ecuting an instruction. The origin of the instruction is either through CRYP-								
0	SEQRUNNING	0	R	AES SEQUENCE Running								
	This bit indicates that the AES module is running an encryption/decryption SEQUENCE.											

30.6.5 C	RYP	TO_	_DS	TAT	rus	- Da	ata S	Stati	us R	egi	ster	•																					
Offset															Bi	t Po	sitio	on															
0x014	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	0.	α	o 1	_	9	2	4	က	2	_	0
Reset						•		0		×				XX							X X								<u> </u>				
Access								<u>~</u>				<u>~</u>		α α														ב	۷				
Name								CARRY				DDATA1MSB DDATA0MSBS)DATA0LSBS													DAIAUZENO	
Bit	Na	me					Re	set			Ac	ces	S	Des	crip	tion																	
31:25	Re	serv	/ed				To tion		ure (com	pati	bility	y wi	ith fu	ıture	dev	ices	s, alv	way	's WI	rite b	oits	to (). M	lore	e info	orn	natio	on in	1.2	Co.	nver	า-
24	CA	RR'	Y				0				R	Carry From Arithmetic Operation																					
	Se	t on	carr	y fro	om a	arith	meti	c op	erat	ions	3																						
23:21	Re	serv	/ed				To tion		ure (com	pati	bility	y wi	ith fu	ıture	dev	ices	s, alv	way	's WI	rite k	oits	to (). M	lore	e info	orm	natio	on in	1.2	? Co	nver	า-
20	DE	ATA	41M	SB X R								MSE	3 in	DD/	ATA	1																	
	All	ows	read	d of	255	in [DDA	TA1	. Do	es r	not d	depe	end	on F	RESI	ULT	WID	тн	in C	CRY	PTC)_V	VAC	;									
19:16	DE	ATA	40M	SBS	3		0x)	<			R			MSB in DDATA0																			

	Allows read of 4	MSBs in DDATA0. The bits depend on RESULTWIDTH in CRYPTO_WAC
15:12	Reserved	To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

		แบบร			
11:8	DDATA0LSBS	0xX	R	LSBs in DDATA0	

Allows read	of 4 LSBs	in DDATA0
-------------	-----------	-----------

7:4	Reserved	To ensure tions	compatibilit	y with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	DATA0ZERO	0xX	R	Data 0 Zero

This field contains flags indicating if any 32 bit part of DATA0 is 0.

1 ZERO0TO31 In DATA0 bits 0 to 31 are all zero. 2 ZERO32TO63 In DATA0 bits 32 to 63 are all zero. 4 ZERO64TO95 In DATA0 bits 64 to 95 are all zero.	Mode	Value
4 ZERO64TO95 In DATA0 bits 64 to 95 are all zero.	ZERO0TO31	1
	ZERO32TO63	2
	ZERO64TO95	4
8 ZERO96TO127 In DATA0 bits 96 to 127 are all zero.	ZERO96TO127	8

30.6.6 CRYPTO_CSTATUS - Control Status Register

Offset														Ві	it F	Posi	ion														
0x018	31	29	28	27	26	25	24	23	22	21	20	10	2 8	17	16	5 2	14	13	12	1	4	2 σ	8)	7	9	5	4	3	2	_
Reset						•			00×0		•		·	0	c	>	•		•	•		2	1		•	•					0×1
Access						α								2	۵	2						Ω									
Name									SEQIP					SEQSKIP	TOPODA							5	-								0/
Bit	Name					Re	set			A	ces	s	Des	crip	tic	on															
31:25	Reser	ved				To tion		ure	con	npa	tibilit	ty v	vith fo	ıture	d	evice	es, a	lwa	ys v	rite	bit	s to (). M	ore	info	orm	atio	n in	1.2	Co	nven
24:20	SEQIF	QIP 0x00 R									Sec	luen	се	Nex	t Ins	strı	uctio	n P	oir	iter											
	Next sequence instruction when in halted sequence																														
19:18	Reser	ved		To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Contions											nven																
17	SEQS	KIP				0 R Sequence Skip Next Instruction																									
	When	in ha	lted	sec	quer	nce,	tells	s wh	eth	er n	ext i	nsi	truction	on w	ill	be s	kippe	ed													
16	SEQP Shows			r cui	ren	0 tly ir	ı pa	rt A	or I	R 3 of	a se	equ		_	ce	Par	t														
	Value					Мо	de						Des	cript	tio	n															
	0					SE	QA																								
	1					SE	QB																								
15:11	Reser	ved				To tion		ure	con	npa	tibilit	ty v	vith f	ıture	e d	evice	es, a	lwa	ys v	rite	bit	s to (D. M	ore	info	orm	atio	n in	1.2	Co	nven
10:8	V1					0x2	2			R			Sel	ecte	d A	ALU	Ope	rai	nd 1												
	Select	able	ope	rand	d for	arit	hme	etic	ope	ratio	ons																				
	Value					Мо	de						Des	cript	tio	n															
	0					DD	ATA	۹0																							
	1					DD	ATA	41																							
	2					DD	ATA	42																							

7:3

4

5

6

7

Reserved

DDATA4

DATA0

DATA1

DATA2

tions

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

R	Selected ALU Operand 0 Description
operations	Description
	Description
	2000.1910.1

30.6.7 CRYPTO_KEY - KEY Register Access (No Bit Access) (Actionable Reads)

Offset		Bit Position																														
0x020	31	31 31 32 33 33 34 35 36 36 36 36 36 36 36 36 36 36 36 36 36									0																					
Reset		XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX																														
Access		RWH																														
Name																\ 	- U 2															

Bit	Name	Reset	Access	Description
31:0	KEY	0xXXXXXXX X	RWH	Key Access

Access the KEY. 4x32bits (8x32bits if AES256 in CRYPTO_CTRL is set) read/write accesses are required to fully read/write KEY.

30.6.8 CRYPTO_KEYBUF - KEY Buffer Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	ositi	on														
0x024	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																	XXXXXXXX															
Access																i	KWH															
Name																Ĺ	KEYBUF															
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tior	n															
31:0	KE	YBU	JF				0x) X	XXX	XXX	ίΧ	RW	/H	ı	Key	Buf	fer	Acc	ess														
		cess te Kl				F. 4x	x32b	oits (8x3	2bits	s if A	AES:	256	in C	RYI	PTC	D_C	ΓRL	is s	set) r	ead	/wri	te a	cces	ses	are	req	uire	d to	fully	rea	ıd/

30.6.9 CRYPTO_SEQCTRL - Sequence Control

Offset											Bit P	ositi	on												
0x030	31	30	29	28	27	25	23	22	21	6 8 8	16	15	4	13	12	-	9 ,	ο α	1 0	_ (ני	> <	1 ი	2	1 0
Reset	0		0	0	0×0	0×0			0×0											0000x0					
Access	RW		RW	A W	RWH	RWH			RW											RWH					
Name	HALT		DMA1PRESA	DMA0PRESA	DMA1SKIP	DMA0SKIP			BLOCKSIZE											LENGTHA					
Bit	Na	me				Reset			Acces	s Desc	riptio	n													
31	НА	LT				0			RW	Halt	Seque	ence													
	Allo	Allows stepping through CRYPTO instructions in the sequence for debugging. Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-																							
30	Re	Reserved To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conventions												nven-											
29	DN	1A1F	PRE	SA		0			RW	DMA	1 Pres	serve	a												
					pped by		k on	nex	t DMA1	WR trigg	ered \	write.	Use	e this	toge	ethe	r wit	h DN	/A1	SKIF	o to	ena	ıble i	n-pla	ce con-
28	DN	1A0F	PRE	SA		0			RW	DMA	0 Pres	serve	a												
					pped by		k on	nex	t DMAC	WR trigg	ered v	write.	Use	e this	toge	ethe	r wit	h DN	/AO	SKIF	o to	ena	ıble i	n-pla	ce con-
27:26	DN	1A19	SKIF)		0x0			RWH	DMA	1 Skip)													
	Se	t to ı	num	ber	of bytes	to excl	ude 1	from	data re	eceived b	y next	t DMA	A1R	D ins	sructi	ion									
25:24	DN	1A05	SKIF	•		0x0			RWH	DMA	0 Skip)													
	Se	t to	num	ber	of bytes	to excl	ude 1	from	data re	eceived b	y next	t DMA	40R	D ins	sructi	ion									
23:22	Re	serv	/ed			To ens	ure	com	patibilit	with fut	ure de	evices	s, alı	ways	write	e bii	ts to	0. M	lore	info	rma	tion	in 1.	2 Co	nven-
21:20	BL	OCŁ	(SIZ	Έ		0x0			RW	Size	of Dat	ta Blo	ock	s											
					dth of blood ed Sequ		ces	sed	in each	iteration	of a s	eque	nce	runn	ning o	on a	dat	aset	(se	e rel	ated	l no	te in		
	Va	lue				Mode				Desc	ription	1													
	0					16BYT	ES			A blo	ck is 1	16 byt	tes I	ong											
	1					32BYT	ES			A blo	ck is 3	32 byt	tes I	ong											
	2					64BYT	ES			A blo	ck is 6	64 byt	tes I	ong											
19:14	Re	serv	/ed			To ens	ure	com	patibilit	with fut	ure de	evices	s, alı	ways	write	e bii	ts to	0. M	lore	info	rma	tion	in 1.	2 Co	nven-
13:0	LE	NG	ГНА			0x0000)		RWH	Buffe	r Len	gth a	in	Byte	s										
										led durinç ast data b													of b	ytes.	If the

30.6.10 CRYPTO_SEQCTRLB - Sequence Control B

Offset														Ві	it Po	siti	on																
0x034	33	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	11	- 5	2	D	œ	7	9	5	-	t 0	ر د	7	-	0
Reset		0	0																						0000	nnnnn							
Access		RW	RW																							I A Y							
Name		DMA1PRESB	DMA0PRESB																							LENGINE							

Bit	Name	Reset	Access	Description
31:30	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
29	DMA1PRESB	0	RW	DMA1 Preserve B
	• • • • • • • • • • • • • • • • • • • •	•	_	DMA1PRESA for in-place conversions where all data is written out from a-set is written, enable only this to preserve the data read in during part A
28	DMA0PRESB	0	RW	DMA0 Preserve B
				DMA0PRESA for in-place conversions where all data is written out from a-set is written, enable only this to preserve the data read in during part A
27:14	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
13:0	LENGTHB	0x0000	RWH	Buffer Length B in Bytes
	Sets the number of	f bytes to be han	idled in a sec	ond iteration over a programmed sequence.

30.6.11 CRYPTO_IF - AES Interrupt Flags

Offset															Bi	t Po	siti	on														
0x040	31	30	53	28	27	26	25	24	23	22	72	20	19	9	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset					•											•		•			•	•						•	0	0	0	0
Access																													2	Я	22	2
Name																													BUFUF	BUFOF	SEQDONE	INSTRDONE

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	BUFUF	0	R	Buffer Underflow
	Set if the buffer RE	EADBUFFER exp	periences an	underflow when attempting a read.
2	BUFOF	0	R	Buffer Overflow
	Set if the buffer W	RITEBUFFER ex	periences an	overflow when attempting a write.
1	SEQDONE	0	R	Sequence Done
	Set when an instru	ıction sequence l	has complete	d
0	INSTRDONE	0	R	Instruction Done
	Set when an instru	ection has comple	eted	

30.6.12 CRYPTO_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x044	31	30	59	28	27	26	25	24	23	22	21	20	19	2	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	7	_	0
Reset			•						•		•			•	•			•	•								•	•	0	0	0	0
Access																													W M	W	W	W1
Name																													BUFUF	BUFOF	SEQDONE	INSTRDONE

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure cortions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	BUFUF	0	W1	Set BUFUF Interrupt Flag
	Write 1 to set the BU	FUF interrupt fla	g	
2	BUFOF	0	W1	Set BUFOF Interrupt Flag
	Write 1 to set the BU	FOF interrupt fla	g	
1	SEQDONE	0	W1	Set SEQDONE Interrupt Flag
	Write 1 to set the SE	QDONE interrup	t flag	
0	INSTRDONE	0	W1	Set INSTRDONE Interrupt Flag
	Write 1 to set the INS	TRDONE interro	upt flag	

30.6.13 CRYPTO_IFC - Interrupt Flag Clear Register

Offset															Bi	it Po	siti	on														
0x048	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset			'		'											•								'			•	•	0	0	0	0
Access																													(R)W1	(R)W1	(R)W1	(R)W1
Name																													BUFUF	BUFOF	SEQDONE	INSTRDONE

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure c	ompatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	BUFUF	0	(R)W1	Clear BUFUF Interrupt Flag
	Write 1 to clear the (This feature must	•	•	ng returns the value of the IF and clears the corresponding interrupt flags .
2	BUFOF	0	(R)W1	Clear BUFOF Interrupt Flag
	Write 1 to clear the (This feature must			ng returns the value of the IF and clears the corresponding interrupt flags .
1	SEQDONE	0	(R)W1	Clear SEQDONE Interrupt Flag
	Write 1 to clear the flags (This feature			eading returns the value of the IF and clears the corresponding interrupt MSC.).
0	INSTRDONE	0	(R)W1	Clear INSTRDONE Interrupt Flag
	Write 1 to clear the flags (This feature			Reading returns the value of the IF and clears the corresponding interrupt //SC.).

30.6.14 CRYPTO_IEN - Interrupt Enable Register

Offset															Bi	t Po	siti	on														
0x04C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	ω	7	9	2	4	3	2	_	0
Reset		'	•			•						•		•	'	'	•								'	'	'		0	0	0	0
Access																													RW	RW	₽	RW
Name																													BUFUF	BUFOF	SEQDONE	INSTRDONE

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
3	BUFUF	0	RW	BUFUF Interrupt Enable
	Enable/disable the Bl	JFUF interrupt		
2	BUFOF	0	RW	BUFOF Interrupt Enable
	Enable/disable the Bl	JFOF interrupt		
1	SEQDONE	0	RW	SEQDONE Interrupt Enable
	Enable/disable the SI	EQDONE interru	ıpt	
0	INSTRDONE	0	RW	INSTRDONE Interrupt Enable
	Enable/disable the IN	STRDONE inter	rrupt	

30.6.15 CRYPTO_SEQ0 - Sequence Register 0

Offset															Bi	t Po	siti	on														
0x050	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	∞	7	9	5	4	က	2	_	0
Reset			•	2	noxo		•	•		·		0	200							0	000							0	OOXO			
Access				2	≥ Y							<u> </u>	}							<u> </u>	<u> </u>							Š	≥ Y			
Name				COFOIN	2X 0X							INSTRO	2							NCTD1								Ę	OX I SNI			

Bit	Name	Reset	Access	Description
31:24	INSTR3	0x00	RW	Sequence Instruction 3
	Sequence instr	uction. See INSTR in	CRYPTO_0	CMD for a possible values.
23:16	INSTR2	0x00	RW	Sequence Instruction 2
	Sequence instr	ruction. See INSTR in	CRYPTO_0	CMD for a possible values.
15:8	INSTR1	0x00	RW	Sequence Instruction 1
	Sequence instr	ruction. See INSTR in	CRYPTO_0	CMD for a possible values.
7:0	INSTR0	0x00	RW	Sequence Instruction 0
	Sequence instr	ruction. See INSTR in	CRYPTO_0	CMD for a possible values.

30.6.16 CRYPTO_SEQ1 - Sequence Register 1

Offset		Bit Po	sition	
0x054	31 30 29 28 27 27 26 26 27 27	23 22 21 20 20 19 19 17 17	6 9 9 8	r 9 & 4 & 7 - 0
Reset	00×0	00×0	00×0	00×0
Access	RW	RW	RW	RW
Name	INSTR7	INSTR6	INSTR5	INSTR4

Bit	Name	Reset	Access	Description
31:24	INSTR7	0x00	RW	Sequence Instruction 7
	Sequence instruction	n. See INSTR in	CRYPTO_	CMD for a possible values.
23:16	INSTR6	0x00	RW	Sequence Instruction 6
	Sequence instruction	n. See INSTR in	CRYPTO_	CMD for a possible values.
15:8	INSTR5	0x00	RW	Sequence Instruction 5
	Sequence instruction	n. See INSTR in	CRYPTO_	CMD for a possible values.
7:0	INSTR4	0x00	RW	Sequence Instruction 4
	Sequence instruction	n. See INSTR in	CRYPTO_	CMD for a possible values.

30.6.17 CRYPTO_SEQ2 - Sequence Register 2

Offset		Bit Po	osition	
0x058	31 30 29 28 27 27 26 25 24	23 22 21 20 20 19 19 17 17	6 9 9 8	7 9 2 4 8 7 10
Reset	00×0	00×0	00×0	00×0
Access	W.W.	XW.	RW	RW
Name	INSTR11	INSTR10	INSTR9	INSTR8

Bit	Name	Reset	Access	Description
31:24	INSTR11	0x00	RW	Sequence Instruction 11
	Sequence instru	iction. See INSTR ir	CRYPTO_	CMD for a possible values.
23:16	INSTR10	0x00	RW	Sequence Instruction 10
	Sequence instru	iction. See INSTR ir	CRYPTO_	CMD for a possible values.
15:8	INSTR9	0x00	RW	Sequence Instruction 9
	Sequence instru	iction. See INSTR ir	CRYPTO_	CMD for a possible values.
7:0	INSTR8	0x00	RW	Sequence Instruction 8
	Sequence instru	iction. See INSTR ir	CRYPTO_	CMD for a possible values.

30.6.18 CRYPTO_SEQ3 - Sequence Register 3

Offset															Bi	t Po	siti	on														
0x05C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset		•	•	0	0000					•		2	noxn								OOXO							0	nxn			
Access				<u>}</u>	<u>}</u>							Š	≥ Y							Ž	≥ Y							2	<u>}</u>			
Name				ALOTONIA R	2							E C	1 N N N N N N N N N N N N N N N N N N N							Š	21212							CTOTOIN	7 CNI			

Bit	Name	Reset	Access	Description
31:24	INSTR15	0x00	RW	Sequence Instruction 15
	Sequence instru	iction. See INSTR in	CRYPTO_0	CMD for a possible values.
23:16	INSTR14	0x00	RW	Sequence Instruction 14
	Sequence instru	iction. See INSTR in	CRYPTO_0	CMD for a possible values.
15:8	INSTR13	0x00	RW	Sequence Instruction 13
	Sequence instru	iction. See INSTR in	CRYPTO_0	CMD for a possible values.
7:0	INSTR12	0x00	RW	Sequence Instruction 12
	Sequence instru	iction. See INSTR in	CRYPTO_0	CMD for a possible values.

30.6.19 CRYPTO_SEQ4 - Sequence Register 4

Offset															Bi	t Po	sitio	on														
0x060	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	2	4	က	2	_	0
Reset					OXO OXO					·		2	200							2	200								00X0			
Access				2	<u>}</u>							2	2							2	<u>}</u>								X N			
Name				Ę	2 2 0 2							NCTD18	2							NCTD17									INSTR16			

Bit	Name	Reset	Access	Description	
31:24	INSTR19	0x00	RW	Sequence Instruction 19	
	Sequence instruction	n. See INSTR ir	CRYPTO_	CMD for a possible values.	
23:16	INSTR18	0x00	RW	Sequence Instruction 18	
	Sequence instruction	n. See INSTR ir	CRYPTO_	CMD for a possible values.	
15:8	INSTR17	0x00	RW	Sequence Instruction 17	
	Sequence instruction	n. See INSTR ir	CRYPTO_	CMD for a possible values.	
7:0	INSTR16	0x00	RW	Sequence Instruction 16	
	Sequence instruction	n. See INSTR ir	CRYPTO_	CMD for a possible values.	

30.6.20 CRYPTO_DATA0 - DATA0 Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	ositi	on														
0x080	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	9	6	8	7	9	5	4	က	2	_	0
Reset																22222	UXXXXXXXX															
Access	RWH H																															
Name																C F	DATAO															
Bit	Na	me					Re	set			Ac	cess	s I	Des	crip	tior	1															
31:0	DA	TA0					0x> X	(XX	XXX	X	RW	/H		Data	a 0 A	Acc	ess															
	Acc	cess	to [DAT	A0.	4x3	2bit	s rea	ad/w	rite	acc	esse	es a	re re	equii	red	to fu	lly r	ead	l/writ	e D	ΑТА	0									

30.6.21 CRYPTO_DATA1 - DATA1 Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x084	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	2	4	က	2	_	0
Reset		XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX																														
Access																	2															
Name																	<u> </u>															
Rit	No	mo					D.	sot			Λο.	cass		200	ovin	4i o n																

Bit	Name	Reset	Access	Description
31:0	DATA1	0xXXXXXXX X	RWH	Data 1 Access
	Access to DATA1 4x	32hits read/write	accesses	are required to fully read/write DATA1

Access to DATA1. 4x32bits read/write accesses are required to fully read/write DATA

30.6.22 CRYPTO_DATA2 - DATA2 Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	ositi	on														
0x088	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	2	4	က	2	_	0
Reset																	0xxxxxxxx 0xxxxxxxxx															
Access	MW XX																															
Name																(DATA2															
Bit	Na	me					Re	set			Ac	ces	S	Des	crip	tior	า															
31:0	DA	TA2					0xX X	ΚXX	XXX	ίX	RW	/H		Data	a 2 A	Acc	ess															
	Aco	cess	to E	DAT	A2.	4x3	2bit	s rea	ad/w	/rite	acc	esse	es a	are re	equi	red	to fu	ılly r	ead	/writ	e D	AT/	12.									

30.6.23 CRYPTO_DATA3 - DATA3 Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x08C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset	XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX																															
Access																																
Name																C V L V C	2															

Bit	Name	Reset	Access	Description
31:0	DATA3	0xXXXXXXX X	RWH	Data 3 Access
	Access to DATA3 4v	32hite read/write	30000000	are required to fully read/write DATA3

Access to DATAS. 4x32bits read/write accesses are required to fully read/write DATAS

30.6.24 CRYPTO_DATA0XOR - DATA0XOR Register Access (No Bit Access) (Actionable Reads)

Offset												Bit F	ositi	on														
0x0A0	31	29	28	26	25	24	23	21	20	19	18	7 2	15	41	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset													0xxxxxxxxx															
Access		RWH OXX																										
Name													DATA0XOR															
Bit	Name				Res	set		Ac	cess	s D)esc	riptic	n															
31:0	DATA	0XOF			0x>	(XXX	(XXX	RV	٧H	Х	OR	Data	0 Ac	ces	s													

Any value written to this register will be XOR'ed with the value of DATA0. The result is stored in DATA0. Reads return DATA0 directly. 4x32bits read/write accesses are required to perform a full XOR write to DATA0

30.6.25 CRYPTO_DATA0BYTE - DATA0 Register Byte Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x0B0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	∞	7	9	5	4	က	2	_	0
Reset		•	•		•	•						•	•			•		•					•	•			•		XXX			
Access																												i	RWH			
Name																												į	DATA0BYTE			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA0BYTE	0xXX	RWH	Data 0 Byte Access
	Access to DATA0. 16 multiples of 4, or data			are required to fully read/write DATA0. Accesses must be performed in

30.6.26 CRYPTO_DATA1BYTE - DATA1 Register Byte Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x0B4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	9	6	∞	7	9	5	4	က	2	_	0
Reset								•			•	•							•				•					3	XXX	•		
Access																												i	I X Y			
Name																												<u> </u>	DAIA1BY IE			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA1BYTE	0xXX	RWH	Data 1 Byte Access
	Access to DATA1. 16 multiples of 4, or data			are required to fully read/write DATA1. Accesses must be performed in

30.6.27 CRYPTO_DATA0XORBYTE - DATA0 Register Byte XOR Access (No Bit Access) (Actionable Reads)

Offset															Bit	t Po	siti	on														
0x0BC	31	99	29	78	27	56	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	∞	7	9	2	4	က	2	_	0
Reset																												3	XXX			
Access																													I A Y			
Name																												ţ	DATAUXORBYTE			

Bit	Name	Reset	Access	Description								
31:8	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-								
7:0	DATA0XORBYTE	0xXX	RWH	Data 0 XOR Byte Access								
		OATA0. 16x8bits read/write accesses are required to fully read/write DATA0. Written data is XOR'ed with sent data in DATA0. Accesses must be performed in multiples of 4, or data incoherency may occur										

30.6.28 CRYPTO_DATA0BYTE12 - DATA0 Register Byte 12 Access (No Bit Access)

Offset															Bi	t Po	siti	on														
0x0C0	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	3	2	1	0
Reset																												>	XXX			
Access																													[} Y			
Name																												DATA0874612				

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA0BYTE12	0xXX	RWH	Data 0 Byte 12 Access
	Access to DATA0 by	/te 12.		

30.6.29 CRYPTO_DATA0BYTE13 - DATA0 Register Byte 13 Access (No Bit Access)

Offset															Bi	t Po	siti	on														
0x0C4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	← c	>
Reset																												>	XXX			
Access																													I X Y			
Name																												Ę	DATAUBYTETS			_

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA0BYTE13	0xXX	RWH	Data 0 Byte 13 Access
	Access to DATA0 by	te 13.		

30.6.30 CRYPTO_DATA0BYTE14 - DATA0 Register Byte 14 Access (No Bit Access)

Offset															Bi	t Po	siti	on													
0x0C8	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	6	ω	7	9	2	4 (٥ ر	1 -	. 0
Reset																												XXX0			
Access																												RWH			
Name																												DATA0BYTE14			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA0BYTE14	0xXX	RWH	Data 0 Byte 14 Access
	Access to DATA0 by	yte 14.		

30.6.31 CRYPTO_DATA0BYTE15 - DATA0 Register Byte 15 Access (No Bit Access)

Offset															Bi	t Po	siti	on														
0x0CC	31	30	29	28	27	26	25	24	23	22	21	20	9	8	17	16	15	4	13	12	7	9	6	ω	7	9	5	4	က	2	-	0
Reset																												XXX				
Access																												RWH				
Name																												DATA0BYTE15	I			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure o	compatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DATA0BYTE15	0xXX	RWH	Data 0 Byte 15 Access
	Access to DATA0 by	te 15.		

30.6.32 CRYPTO_DDATA0 - DDATA0 Register Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	ositi	on														
0x100	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																	UXXXXXXXX															
Access																	I M Y															
Name																() () () () () () () () () ()	DDATA0															
Bit	Na	me					Re	set			Ac	cess	s I	Des	crip	tior	1															
31:0	DD	ATA)				0xX X	ΧX	XXX	ίX	RW	/H		Dou	ble	Dat	a 0 .	Acc	ess	8												
	Acc	cess t	to D	DA	TAC). 8x	(32b	its r	ead	/writ	e ac	ces	ses	are	requ	uire	d to	fully	re	ad/w	rite	DD.	ATA	0.								

30.6.33 CRYPTO_DDATA1 - DDATA1 Register Access (No Bit Access) (Actionable Reads)

Offset															Bit	Pos	sitic	on														
0x104	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	9 1	15	4	13	12	7	10	6	80	7	9	2	4	က	7	_	0
Reset																XXXXXXXXX																
Access																RWH																
Name																DDATA1																

Bit	Name	Reset	Access	Description
31:0	DDATA1	0xXXXXXXX X	RWH	Double Data 0 Access

Access to DDATA1, which is equal to the full width of KEY regardless of AES256 in CRYPTO_CTRL. 8x32bits read/write accesses are required to fully read/write DDATA1.

30.6.34 CRYPTO_DDATA2 - DDATA2 Register Access (No Bit Access) (Actionable Reads)

Offset															Bit	Po	siti	on														
0x108	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset																XXXXXXXXX																
Access																RWH																
Name																DDATA2	! :															

Bit	Name	Reset	Access	Description
31:0	DDATA2	0xXXXXXXX	RWH	Double Data 0 Access

Access to DDATA2, which consists of {DATA1, DATA0}. 8x32bits read/write accesses are required to fully read/write DDATA2.

30.6.35 CRYPTO_DDATA3 - DDATA3 Register Access (No Bit Access) (Actionable Reads)

Offset															Bit	Pos	tio	n													
0x10C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	9 4	2 ;	4 (5 3	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																0xxxxxxxx															
Access																RWH															
Name																DDATA3															

Bit	Name	Reset	Access	Description
31:0	DDATA3	0xXXXXXXX X	RWH	Double Data 0 Access

Access to DDATA3, which consists of {DATA3, DATA2}. 8x32bits read/write accesses are required to fully read/write DDATA3.

30.6.36 CRYPTO_DDATA4 - DDATA4 Register Access (No Bit Access) (Actionable Reads)

Offset	Bit Position
0x110	33 34 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5
Reset	XXXXXXX0
Access	RWH H
Name	DDATA4

Bit	Name	Reset	Access	Description
31:0	DDATA4	0xXXXXXXX X	RWH	Double Data 0 Access

Access to DDATA4, which is equal to the full width of KEYBUF regardless of AES256 in CRYPTO_CTRL. 8x32bits read/write accesses are required to fully read/write DDATA4.

30.6.37 CRYPTO_DDATA0BIG - DDATA0 Register Big Endian Access (No Bit Access) (Actionable Reads)

Offset															Bit	t Po	siti	on														
0x130	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	တ	∞	7	9	2	4	က	2	_	0
Reset																XXXXXXXX	VAAAAAAA															
Access																EWH																
Name																DIATAORIG																

Bit	Name	Reset	Access	Description
31:0	DDATA0BIG	0xXXXXXXX X	RWH	Double Data 0 Big Endian Access
	Big endian access to	DDATA0. 8x32b	oits read/w	rite accesses are required to fully read/write DDATA0.

30.6.38 CRYPTO_DDATA0BYTE - DDATA0 Register Byte Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x140	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset			•		•	•	•	•				•		•	•	•	•						•				•	>	XX		·	
Access																													I A Y			
Name																												Į	DDAIAUBYIE			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure tions	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DDATA0BYTE	0xXX	RWH	Ddata 0 Byte Access
	Access to DDATA0 multiples of 4, or da			es are required to fully read/write DDATA0. Accesses must be performed in

30.6.39 CRYPTO_DDATA1BYTE - DDATA1 Register Byte Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x144	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	6	ω	7	9	2	4	က	2	_	0
Reset																												;	XXX			
Access																													RWH H			
Name																												Į	DDATA1BYTE			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	DDATA1BYTE	0xXX	RWH	Ddata 1 Byte Access
	Access to DDATA1.3 multiples of 4, or data			es are required to fully read/write DDATA1. Accesses must be performed in

30.6.40 CRYPTO_DDATA0BYTE32 - DDATA0 Register Byte 32 Access (No Bit Access)

Offset	Bit Position	
0x148	31 31 32 33 33 34 35 35 35 35 35 35 35 35 35 35 35 35 35	0 7 7 3
Reset		XX
Access		RWH H
Name		DDATA0BYTE32

Bit	Name	Reset	Access	Description
31:4	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
3:0	DDATA0BYTE32	0xX	RWH	Ddata 0 Byte 32 Access
	Access to DDATA0 b	yte 32. This is	used when I	RESULTWIDTH in CRYPTO_WAC is set to 260BIT.

30.6.41 CRYPTO_QDATA0 - QDATA0 Register Access (No Bit Access) (Actionable Reads)

Offset															Bit	Pos	sitio	on														
0x180	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	ω	7	9	5	4	က	2	_	0
Reset																0xxxxxxxxx																
Access																RWH																
Name																QDATA0																

Bit	Name	Reset	Access	Description
31:0	QDATA0	0xXXXXXXX X	RWH	Quad Data 0 Access
	Access to QDATA0, v QDATA0.	vhich is equal to	{DDATA1	DDATA0}. 16x32bits read/write accesses are required to fully read/write

30.6.42 CRYPTO_QDATA1 - QDATA1 Register Access (No Bit Access) (Actionable Reads)

Offset															Bit	t Po	siti	on														
0x184	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	14	13	12	7	10	6	8	7	9	2	4	က	7	_	0
Reset			•													*********	VVVVVVV															
Access																H/WA	- - - -															
Name																ODATA1	, ,															
Bit	Na	me					Re	set			Ac	cess	s [Des	cript	tion																

Bit	Name	Reset	Access	Description
31:0	QDATA1	0xXXXXXXX X	RWH	Quad Data 1 Access

Access to QDATA1, which is equal to {DATA3, DATA2, DATA1, DATA0} and {DDATA3, DDATA2}. 16x32bits read/write accesses are required to fully read/write QDATA1.

30.6.43 CRYPTO_QDATA1BIG - QDATA1 Register Big Endian Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x1A4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	ω	7	9	2	4	က	2	_	0
Reset																******	VVVVVVV															
Access																H/V/G	- -															
Name																COATATRIC																

Bit	Name	Reset	Access	Description
31:0	QDATA1BIG	0xXXXXXXX X	RWH	Quad Data 1 Big Endian Access
	Dia andian access to	ODATA1 which	io oqual ta	(DATA2 DATA2 DATA1 DATA0) and (DDATA2 DDATA2) 16v222hita

Big endian access to QDATA1, which is equal to {DATA3, DATA1, DATA0} and {DDATA3, DDATA2}. 16x32bits read/write accesses are required to fully read/write QDATA1.

30.6.44 CRYPTO_QDATA0BYTE - QDATA0 Register Byte Access (No Bit Access) (Actionable Reads)

Offset	Bit Position	
0x1C0	30 30 30 30 30 30 30 30 30 30 4 4 4 4 4	ν Θ
Reset		×××
Access		RWH
Name		QDATA0BYTE

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	QDATA0BYTE	0xXX	RWH	Qdata 0 Byte Access
	Access to QDATA0.	64x8bits read/w	rite accesse	es are required to fully read/write QDATA0. Accesses must be performed in

multiples of 4, or data incoherency may occur


30.6.45 CRYPTO_QDATA1BYTE - QDATA1 Register Byte Access (No Bit Access) (Actionable Reads)

Offset															Bi	t Po	siti	on														
0x1C4	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	41	13	12	7	10	6	ω	7	9	5	4	က	2	- (0
Reset																												>	XX			
Access																													I X Y			
Name																												H 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4 4	QDAIAIBYIE			

Bit	Name	Reset	Access	Description
31:8	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
7:0	QDATA1BYTE	0xXX	RWH	Qdata 1 Byte Access
	Access to QDATA1. 6 multiples of 4, or data			es are required to fully read/write QDATA1. Accesses must be performed in

31. GPIO - General Purpose Input/Output





Quick Facts

What?

The General Purpose Input/Output (GPIO) is used for pin configuration, direct pin manipulation and sensing, as well as routing for peripheral pin connections.

Why?

Easy to use and highly configurable input/output pins are important to fit many communication protocols as well as minimizing software control overhead. Flexible routing of peripheral functions helps to ease PCB layout.

How?

Each pin on the device can be individually configured as either an input or an output with several different drive modes. Also, individual bit manipulation registers minimizes control overhead. Peripheral connections to pins can be routed to several different locations, thus solving congestion issues that may arise with multiple functions on the same pin. Fully asynchronous interrupts can also be generated from any pin.

31.1 Introduction

In the EFR32 devices the General Purpose Input/Output (GPIO) pins are organized into ports with up to 16 pins each. These GPIO pins can individually be configured as either an output or input. More advanced configurations like open-drain, open-source, and glitch filtering can be configured for each individual GPIO pin. The GPIO pins can also be overridden by peripheral pin connections, like Timer PWM outputs or USART communication, which can be routed to several locations on the device. The GPIO supports up to 16 asynchronous external pin interrupts, which enable interrupts from any pin on the device. Also, the input value of a pin can be routed through the Peripheral Reflex System to other peripherals.

Note: To use the GPIO, the GPIO clock must first be enabled in CMU_HFBUSCLKEN0. Setting this bit enables the HFBUSCLK for the GPIO.

31.2 Features

- · Individual configuration for each pin
 - · Tristate (reset state)
 - Push-pull
 - · Open-drain
 - · Pull-up resistor
 - · Pull-down resistor
 - · Drive strength
 - 1 mA
 - 10 mA
 - Slewrate
 - · Over Voltage Tolerance
- · EM4 IO pin retention
 - · Output enable
 - · Output value
 - · Pull enable
 - · Pull direction
 - · Over Voltage Tolerance
- · EM4 wake-up on selected GPIO pins
- · Glitch suppression input filter
- · Alternate functions (e.g. peripheral outputs and inputs)
 - · Routed to several locations on the device
 - · Pin connections can be enabled individually
 - · Output data can be overridden by peripheral
 - · Output enable can be overridden by peripheral
- · Toggle register for output data
- · Dedicated data input register (read-only)
- Interrupts
 - · 2 Interrupt lines using either levels or edges
 - · EM4 wake-up pins are selectable for level interrupts
 - · All GPIO pins are selectable for edge interrupts
 - · Separate enable, status, set and clear registers
 - · Asynchronous sensing
 - · Rising, falling or both edges
 - · High or low level detection
 - · Wake up from EM0 Active-EM3 Stop
- · Peripheral Reflex System producer
 - · All GPIO pins are selectable
- · Configuration lock functionality to avoid accidental changes

31.3 Functional Description

An overview of the GPIO module is shown in Figure 31.1 Pin Configuration on page 1069. The GPIO pins are grouped into 16-pin ports. Each individual GPIO pin is called Pxn where x indicates the port (A, B, C ...) and n indicates the pin number (0,1,....,15). Fewer than 16 bits may be available on some ports, depending on the total number of I/O pins on the package. After a reset, both input and output are disabled for all pins on the device, except for the Serial Wire Debug pins.

To use a pin, the Mode Register (GPIO_Px_MODEL/GPIO_Px_MODEH) must be configured for the pin to make it an input or output. These registers can also do more advanced configuration, which is covered in 31.3.1 Pin Configuration. When the port is configured as an input or an output, the Data In Register (GPIO_Px_DIN) can be used to read the level of each pin in the port (bit n in the register is connected to pin n on the port). When configured as an output, the value of the Data Out Register (GPIO_Px_DOUT) will be driven to the pin.

The DOUT value can be changed in 4 different ways:

- · Writing to the GPIO_Px_DOUT register
- · Writing the BITSET address of the GPIO Px DOUT register sets the DOUT bits
- · Writing the BITCLEAR address of the GPIO_Px_DOUT register clears the DOUT bits
- Writing the GPIO_Px_DOUTTGL register toggles the corresponding DOUT bits

Reading the GPIO_Px_DOUT register will return its contents. Reading the GPIO_Px_DOUTTGL register will return 0.




Figure 31.1. Pin Configuration

31.3.1 Pin Configuration

In addition to setting the pins as either outputs or inputs, the GPIO_Px_MODEL and GPIO_Px_MODEH registers can be used for more advanced configurations. GPIO_Px_MODEL contains 8 bit fields named MODEn (n=0,1,..7) which control pins 0-7, while GPIO_Px_MODEH contains 8 bit fields named MODEn (n=8,9,..15) which control pins 8-15. In some modes GPIO_Px_DOUT is also used for extra configurations like pull-up/down and glitch suppression filter enable. Table 31.1 Pin Configuration on page 1070 shows the available configurations.

Table 31.1. Pin Configuration

MODEn	Input	Output	DOUT	Pull- down	Pull- up	Alt Port Ctrl	Input Filter	Description
DISABLED	Disabled	Disabled	0					Input disabled
			1		On			Input disabled with pull-up
INPUT	Enabled		0					Input enabled
	if not DINDIS		1				On	Input enabled with filter
INPUTPULL			0	On				Input enabled with pull-down
			1		On			Input enabled with pull-up
INPUTPULLFILTER			0	On			On	Input enabled with pull- down and filter
			1		On		On	Input enabled with pull-up and filter
PUSHPULL		Push-	х					Push-pull
PUSHPULLALT		pull	х			On		Push-pull with alternate port control values
WIREDOR		Open	х					Open-source
WIREDORPULLDOWN		Source (Wired- OR)	х	On				Open-source with pull-down
WIREDAND		Open	х					Open-drain
WIREDANDFILTER		Drain (Wired-	х				On	Open-drain with filter
WIREDANDPULLUP		AND)	х		On			Open-drain with pull-up
WIREDANDPULLUPFILTER			х		On		On	Open-drain with pull-up and filter
WIREDANDALT			х			On		Open-drain with alternate port control values
WIREDANDALTFILTER			х			On	On	Open-drain with alternate port control values and filter
WIREDANDALTPULLUP			х		On	On		Open-drain with alternate port control values and pull-up
WIREDANDALTPULLUPFILTER			х		On	On	On	Open-drain with alternate port control values, pull-up and filter

MODEn determines which mode the pin is in at a given time. Setting MODEn to DISABLED disables the pin, reducing power consumption to a minimum. When the output driver, input driver and Over Voltage Tolerance is disabled, the pin can be used as a connection for an analog module. An input is enabled by setting MODEn to any value other than DISABLED while DINDIS for the given port is cleared.

Set DINDIS to disable the input of a gpio port. The pull-down and glitch filter function can optionally be applied to the input, see Figure 31.2 Tristated Output With Optional Pull-up or Pull-down on page 1071.




Figure 31.2. Tristated Output With Optional Pull-up or Pull-down

When MODEn is PUSHPULL or PUSHPULLALT, the pin operates in push-pull mode. In this mode, the pin can have alternate port control values and can be driven either high or low, dependent on the value of GPIO_Px_DOUT. The push-pull configuration is shown in Figure 31.3 Push-Pull Configuration on page 1071.




Figure 31.3. Push-Pull Configuration

When MODEn is WIREDOR or WIREDORPULLDOWN, the pin operates in open-source mode (with a pull-down resistor for WIREDORPULLDOWN). When driving a high value in open-source mode, the pull-down is disconnected to save power.

When the mode is prefixed with WIREDAND, the pin operates in open-drain mode as shown in Figure 31.4 Open-drain on page 1071. In open-drain mode, the pin can have an input filter, a pull-up, alternate port control values or any combination of these. When driving a low value in open-drain mode, the pull-up is disconnected to save power.




Figure 31.4. Open-drain

31.3.1.1 Over Voltage Tolerance

Over voltage capability is available for most pins. If available, it allows the pin to be used at the minimum of IOVDD + 2V and 5.5V (for 5V tolerant pads). The data sheet specifies which pins can be used as 5V tolerant pins. Default over voltage is enabled for each pin supporting that feature. Over voltage tolerance (OVT) can be disabled on a per pin basis. The over voltage tolerance feature applied to the selected pins is configured in the GPIO_Px_OVTDIS register. Disabling the over voltage tolerance for a pin will provide less distortion on that pin, which is useful when the pin is used as analog input.

Note: The VDAC (and OPAMPs) can drive outputs above IOVDD and therefore the involved pads typically require OVT to be be enabled.

31.3.1.2 Alternate Port Control

The Alternate Port Control allows for additional flexibilty of port level settings. A user may setup two different port configurations (normal and alternate modes) and select which is applied on a pin by pin bases. For example you may configure half of port A to use the low drive strength setting (normal mode) while the other half uses high drive strength (alternate mode).

Alternate port control is enabled when MODEn is set to any of the ALT enumerated modes (ie. PUSHPULLALT). When MODEn is an alternate mode, the pin uses the alternate port control values specified in the DINDISALT, SLEWRATEALT, and DRIVESTRENGTHALT fields in GPIO_Px_CTRL. In all other modes, the port control values are used from the DINDIS, SLEWRATE, and DRIVESTRENGTH fields in GPIO_Px_CTRL.

31.3.1.3 Drive Strength

The drive strength can be applied to pins on a port-by-port basis. The drive strength applied to pins configured using normal MODEn settings can be controlled using the DRIVESTRENGTH field in GPIO_Px_CTRL. The drive strength applied to pins configured using alternate MODEn settings can be controlled using the DRIVESTRENGTHALT field.

31.3.1.4 Slewrate

The slewrate can be applied to pins on a port-by-port basis. The slewrate applied to pins configured using normal MODEn settings can be controlled using the SLEWRATE fields in GPIO_Px_CTRL. The slewrate applied to pins configured using the alternate MODEn settings can be controlled using the SLEWRATEALT field.

31.3.1.5 Input Disable

The pin inputs can be disabled on a port-by-port basis. The input of pins configured using the normal MODEn settings can be disabled by setting DINDIS in GPIO_Px_CTRL. The input of pins configured using the alternate MODEn settings can be disabled by setting DINDISALT.

31.3.1.6 Configuration Lock

GPIO_Px_MODEL, GPIO_Px_MODEH, GPIO_Px_CTRL, GPIO_Px_PINLOCKN, GPIO_Px_OVTDIS, GPIO_EXTIPSELL, GPIO_EXTIPSELH, GPIO_EXTIPINSELL, GPIO_EXTIPINSELH, GPIO_INSENSE, GPIO_ROUTEPEN, and GPIO_ROUTELOC0 can be locked by writing any value other than 0xA534 to GPIO_LOCK. Writing the value 0xA534 to the GPIOx_LOCK register unlocks the configuration registers.

In addition to configuration lock, GPIO_Px_MODEL, GPIO_Px_MODEH, GPIO_Px_DOUT, GPIO_Px_DOUTTGL, and GPIO_Px_OVT-DIS can be locked individually for each pin by clearing the corresponding bit in GPIO_Px_PINLOCKN. When a bit in the GPIO_Px_PINLOCKN register is cleared, it will stay cleared until reset.

31.3.2 EM4 Wake-up

It is possible to trigger a wake-up from EM4 using any of the selectable EM4WU GPIO pins. The wake-up request can be triggered through the pins by enabling the corresponding bit in the GPIO_EM4WUEN register. When EM4 wake-up is enabled for the pin, the input filter is enabled during EM4. This is done to avoid false wake-up caused by glitches. In addition, the polarity of the EM4 wake-up request can be selected using the GPIO_EXTILEVEL register.




Figure 31.5. EM4 Wake-up Logic

The pins used for EM4 wake-up must be configured as inputs with glitch filters using the GPIO_Px_MODEL/GPIO_Px_MODEH register. If the input is disabled and the wakeup polarity is low, a false wakeup will occur when entering EM4. If the input is enabled, the glitch filtered is disabled, and the polarity is set low, a glitch will occur when going into EM4 that will cause an immediate wake-up. Before going down to EM4, it is important to clear the wake-up logic by setting the GPIO_IFC bit, which clears the wake-up logic, including the GPIO_IF register. It is possible to determine which pin caused the EM4WU by reading the GPIO_IF register. The mapping between EM4WU pins and the bit indexes in the GPIO_EM4WUEN, GPIO_EXTILEVEL, GPIO_IFC, GPIO_IFS, GPIO_IEN, and GPIO_IF registers is as follows:

Table 31.2. EM4WU Register Bit Index to EM4WU Pin Mapping

EM4WU Register Bit Indexes	EM4WU Pin	
16	GPIO_EM4WU0	
17	GPIO_EM4WU1	
18	GPIO_EM4WU2	
19	GPIO_EM4WU3	
31	GPIO_EM4WU15	

31.3.3 EM4 Retention

By default, GPIO pins revert back to their reset state when EM4 is entered. The GPIO pins can be configured to retain the settings for output enable, output value, pull enable, pull direction and over voltage tolerance while in EM4.

EM4 GPIO retention is controlled with the EM4IORETMODE field in the EMU_EM4CTRL register. Setting EM4IORETMODE to EM4EXIT will cause retention to persist while in EM4 and reset the GPIOs during wakeup. Setting EM4IORETMODE to SWUNLATCH will cause the retention to persist until the EM4UNLATCH bit is written by software. Note that when using SWUNLATCH, the GPIO register values are still reset on wakeup from EM4. In order to ensure that the GPIO state does not change, sofware must re-write the GPIO registers before setting EM4UNLATCH and ending EM4 GPIO retention. See the EMU chapter for additional documentation on its registers and the EM4UNLATCH bit.

31.3.4 Alternate Functions

Alternate functions are connections to pins from peripherals, i.e. Timers, USARTs, etc.. These peripherals contain route registers, where the pin connections are enabled. In addition, the route registers contain a location bit field that configures which pin an output of that peripheral will be connected to if enabled. After connecting a peripheral, the pin configuration stays as set in GPIO_Px_MODEL, GPIO_Px_MODEH and GPIO_Px_DOUT registers. For example, the pin configuration must be set to output enable in GPIO_Px_MODEL or GPIO_Px_MODEH for a peripheral to be able to use the pin as an output.

It is not recommended to select two or more peripherals as output on the same pin. The reader is referred to the pin map section of the device data sheet for more information on the possible locations of each alternate function.

31.3.4.1 Analog Connections

When using the GPIO pin for analog functionality, it is recommended to disable the over voltage tolerance by setting the corresponding pin in the GPIO_Px_OVTDIS register and setting the MODEn in GPIO_Px_MODEL or GPIO_Px_MODEH equal to DISABLE to disable the input sense, output driver and pull resistors.

31.3.4.2 Debug Connections

31.3.4.2.1 Serial Wire Debug Connection

The SW Debug Port is routed as an alternate function and the SWDIO and SWCLK pin connections are enabled by default with internal pull up and pull down resistors, respectively. It is possible to disable these pin connections (and disable the pull resistors) by setting the SWDIOTMSPEN and SWCLKTCKPEN bits in GPIO ROUTEPEN to 0.

31.3.4.2.2 JTAG Debug Connection

The JTAG Debug Port is routed as an alternate function and the TMS, TCK, TDO, and TDI pin connections are enabled by default with internal pull up, pull down, no pull, and pull up resistors, respectively. It is possible to disable these pin connections (and disable the pull resistors) by setting the SWDIOTMSPEN, SWCLKTCKPEN, TDOPEN, and TDIPEN bits in GPIO ROUTEPEN to 0.

31.3.4.2.3 Disabling Debug Connections

When the debug pins are disabled, the device can no longer be accessed by a debugger. A reset will set the debug pins back to their enabled default state. The GPIO_ROUTEPEN register can only be updated when the debugger is disconnected from the system. Any attempts to modify GPIO_ROUTEPEN when the debugger is connected will not occur. If you do disable the debug pins, make sure you have at least a 3 second timeout at the start of your program code before you disable the debug pins. This way the debugger will have time to connect to the the device after a reset and before the pins are disabled.

31.3.5 Interrupt Generation

Interrupts may be triggered on edge events for any GPIO pin, or on pin input levels for GPIO capable of EM4 wake-up.

31.3.5.1 Edge Interrupt Generation

The GPIO can generate an interrupt from any edge of the input of any GPIO pin on the device. The edge interrupts have asynchronous sense capability, enabling wake-up from energy modes as low as EM3 Stop, see Figure 31.6 Pin N Interrupt Generation on page 1075.




Figure 31.6. Pin N Interrupt Generation

External pin interrupts can be represented in the form of EXTI[index], where index is the external interrupt number. For example, the EXTI7 interrupt has an index of 7. All pins within a group of four (0-3,4-7,8-11,12-15) from all ports are grouped together to trigger one interrupt. The group of pins available to trigger an interrupt is determined by the interrupt index and calculated as int(index/4). For example the first 4 interrupts (EXTI0 - EXTI3) are triggered by pins in the first group (Px[3:0]) and the second 4 interrupts (EXTI4-EXTI7) are triggered by pins in the second group (Px[7:4]).

The EXTIPSELn bits in GPIO_EXTIPSELL or GPIO_EXTIPSELH select which PORT in the group will trigger the interrupt. The EXTI-PINSELn bits in GPIO_EXTIPINSELL or GPIO_EXTIPINSELH will determine which pin inside the selected group will trigger the interrupt.

For example if EXTIPSEL11 = PORTB and EXTPINSEL11 = 0 then PB8 will be used for EXTI11. EXTI11 uses the third group (11/4 = 2) so the list of possible pins is Px[11:8]. The setting of EXTIPSEL11 further narrows the selection to PB[11:8]. Finally EXTPINSEL11 selects the first pin in that group which is PB8.

The GPIO_EXTIRISE[n] and GPIO_EXTIFALL[n] registers enable sensing of rising and falling edges. By setting the EXT[n] bit in GPIO_IEN, a high interrupt flag n, will trigger one of two interrupt lines. The even interrupt line is triggered by any enabled even numbered interrupt flag index, while the odd interrupt line is triggered by odd flag indexes. The interrupt flags can be set and cleared by software when writing the GPIO_IFS and GPIO_IFC registers. Since the external interrupts are asynchronous, they are sensitive to noise. To increase noise tolerance, the MODEL and MODEH fields in the GPIO_Px_MODEL and GPIO_Px_MODEH registers, respectively, should be set to include glitch filtering for pins that have external interrupts enabled.

31.3.5.2 Level Interrupt Generation

GPIO can generate a level interrupt using the input of any GPIO EM4 wake-up pins on the device. The interrupts have asynchronous sense capability, enabling wake-up from energy modes as low as EM4.

In order to enable the level interrupt, set the EM4WU field in the GPIO_IEN register and the EM4WUn field in the GPIO_EXTILEVEL register. Upon a level interrupt occuring, the corresponding EM4WU index in the GPIO_IF register will be set along with the odd or even interrupt line depending on the index inside of GPIO_IF. For example, by setting the EM4WU8 in GPIO_EXTILEVEL and EM4WU[8] in GPIO_IEN, the interrupt flag EM4WU[8] in GPIO_IF will be triggered by a high level on pin EM4WU8 and a interrupt request will be sent on IRQ_GPIO_EVEN.

The wake-up granulalrity of the level interrupts is based on the settings of the EM4WU field in the GPIO_IEN register and the EM4WUEN field in the GPIO_EM4WUEN register, see Table 31.3 Level Interrupt Energy Mode Wakeup on page 1076

Table 31.3. Level Interrupt Energy Mode Wakeup

GPIO_IEN	GPIO_EM4WUEN	Energy Mode Wakeup
0	0	No Interrupt
0	1	EM4H,EM4S
1	0	EM1,EM2,EM3,EM4H,EM4S
1	1	EM1,EM2,EM3,EM4H,EM4S

31.3.6 Output to PRS

All pins within a group of four(0-3,4-7,8-11,12-15) from all ports are grouped together to form one PRS producer which outputs to the PRS. The pin from which the output should be taken is selected in the same fashion as the edge interrupts.

PRS output is not affected by the interrupt edge detection logic or gated by the IEN bits. See Figure 31.6 Pin N Interrupt Generation on page 1075 for an illustration of where the PRS output signal is generated.

31.3.7 Synchronization

To avoid metastability in synchronous logic connected to the pins, all inputs are synchronized with double flip-flops. The flip-flops for the input data run on the HFBUSCLK. Consequently, when a pin changes state, the change will have propagated to GPIO_Px_DIN after two 2 HFBUSCLK cycles. Synchronization (also running on the HFBUSCLK) is also added for interrupt input. To save power when the external interrupts or level interrupts are not used, the synchronization flip-flops for these can be turned off by clearing INT or EM4WU,respectively, in GPIO_INSENSE register.

31.4 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	GPIO_PA_CTRL	RW	Port Control Register
0x004	GPIO_PA_MODEL	RW	Port Pin Mode Low Register
0x008	GPIO_PA_MODEH	RW	Port Pin Mode High Register
0x00C	GPIO_PA_DOUT	RW	Port Data Out Register
0x018	GPIO_PA_DOUTTGL	W1	Port Data Out Toggle Register
0x01C	GPIO_PA_DIN	R	Port Data in Register
0x020	GPIO_PA_PINLOCKN	RW	Port Unlocked Pins Register
0x028	GPIO_PA_OVTDIS	RW	Over Voltage Disable for All Modes
	GPIO_Px_CTRL	RW	Port Control Register
	GPIO_Px_MODEL	RW	Port Pin Mode Low Register
	GPIO_Px_MODEH	RW	Port Pin Mode High Register
	GPIO_Px_DOUT	RW	Port Data Out Register
	GPIO_Px_DOUTTGL	W1	Port Data Out Toggle Register
	GPIO_Px_DIN	R	Port Data in Register
	GPIO_Px_PINLOCKN	RW	Port Unlocked Pins Register
	GPIO_Px_OVTDIS	RW	Over Voltage Disable for All Modes
0x210	GPIO_PL_CTRL	RW	Port Control Register
0x214	GPIO_PL_MODEL	RW	Port Pin Mode Low Register
0x218	GPIO_PL_MODEH	RW	Port Pin Mode High Register
0x21C	GPIO_PL_DOUT	RW	Port Data Out Register
0x228	GPIO_PL_DOUTTGL	W1	Port Data Out Toggle Register
0x22C	GPIO_PL_DIN	R	Port Data in Register
0x230	GPIO_PL_PINLOCKN	RW	Port Unlocked Pins Register
0x238	GPIO_PL_OVTDIS	RW	Over Voltage Disable for All Modes
0x400	GPIO_EXTIPSELL	RW	External Interrupt Port Select Low Register
0x404	GPIO_EXTIPSELH	RW	External Interrupt Port Select High Register
0x408	GPIO_EXTIPINSELL	RW	External Interrupt Pin Select Low Register
0x40C	GPIO_EXTIPINSELH	RW	External Interrupt Pin Select High Register
0x410	GPIO_EXTIRISE	RW	External Interrupt Rising Edge Trigger Register
0x414	GPIO_EXTIFALL	RW	External Interrupt Falling Edge Trigger Register
0x418	GPIO_EXTILEVEL	RW	External Interrupt Level Register
0x41C	GPIO_IF	R	Interrupt Flag Register
0x420	GPIO_IFS	W1	Interrupt Flag Set Register
0x424	GPIO_IFC	(R)W1	Interrupt Flag Clear Register
0x428	GPIO_IEN	RW	Interrupt Enable Register

Offset	Name	Туре	Description
0x42C	GPIO_EM4WUEN	RW	EM4 Wake Up Enable Register
0x440	GPIO_ROUTEPEN	RW	I/O Routing Pin Enable Register
0x444	GPIO_ROUTELOC0	RW	I/O Routing Location Register
0x450	GPIO_INSENSE	RW	Input Sense Register
0x454	GPIO_LOCK	RWH	Configuration Lock Register

31.5 Register Description

31.5.1 GPIO_Px_CTRL - Port Control Register

Offset			Bit Position
0x000	30 30 27 28 29 29	20 21 23 24 25 20 25 25 26 26	0 1 2 3 4 6 2 6 7 8 8 7 9 9 6 7 7 1 13 1 13 1 1 1 1 1 1 1 1 1 1 1 1 1
Reset	0	0x5	0 0 0 0 0
Access	XX XX	RW	MA WA WA
Name	DINDISALT	SLEWRATEALT	DRIVESTRENGTHALT DINDIS SLEWRATE DRIVESTRENGTH
Bit	Name	Reset Acces	ss Description
31:29	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
28	DINDISALT	0 RW	Alternate Data in Disable
	Data input disable fo	or port pins using alternate	e modes.
27:23	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
22:20	SLEWRATEALT	0x5 RW	Alternate Slewrate Limit for Port
	Slewrate limit for por	t pins using alternate mod	des. Higher values represent faster slewrates.
19:17	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
16	DRIVESTRENGTH- ALT	0 RW	Alternate Drive Strength for Port
	Drive strength setting	g for port pins using alterr	nate drive strength.
	Value	Mode	Description
	0	STRONG	10 mA drive current
	1	WEAK	1 mA drive current
15:13	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
12	DINDIS	0 RW	Data in Disable
	Data input disable fo	or port pins not using alter	rnate modes.
11:7	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-
6:4	SLEWRATE	0x5 RW	Slewrate Limit for Port
	Slewrate limit for por	-	modes. Higher values represent faster slewrates.
3:1	Reserved	To ensure compatibilit tions	ty with future devices, always write bits to 0. More information in 1.2 Conven-

Bit	Name	Reset	Access	Description
0	DRIVESTRENGTH	0	RW	Drive Strength for Port
	Drive strength setting	for port pins no	ot using alte	rnate modes.
	Value	Mode		Description
	0	STRONG		10 mA drive current
	1	STRONG		10 mA drive current 1 mA drive current

31.5.2 GPIO_Px_MODEL - Port Pin Mode Low Register

Offset															Bi	t Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset		2	2			2	e X			Š	e e			2	e e	•		Š	e X			2	2	•		2	e e			2	2	
Access		2	<u>}</u>			20	<u>}</u>			2	<u>}</u>			2	<u>}</u>			2	<u>}</u>			Š.				2	<u>}</u>			2	<u>}</u>	
Name		71000	NOUN INCOME			A D D D	MODE MODE			L C	S C C C C C C C C C C C C C C C C C C C				20 N				MODES			MODE?	i))				П П				NO.	

Name	MODE	MODE	MODE	MODE	MODE	MODE	MODE	MODE
Bit	Name	Reset	Access	s Descriptior	1			
31:28	MODE7	0x0	RW	Pin 7 Mode				
	Configure mod	e for pin 7.						
	Value	Mode		Description				
	0	DISABI	_ED	Input disable	ed. Pullup if DO	JT is set.		
	1	INPUT		Input enable	ed. Filter if DOU	Γ is set		
	2	INPUT	PULL	Input enable	ed. DOUT deterr	mines pull direct	tion	
	3	INPUT	PULLFILTER	Input enable	ed with filter. DO	UT determines	pull direction	
	4	PUSHF	PULL	Push-pull or	utput			
	5	PUSHF	PULLALT	Push-pull us	sing alternate co	ntrol		
	6	WIRED	OR	Wired-or ou	tput			
	7	WIRED	ORPULLDOW	N Wired-or ou	tput with pull-do	wn		
	8	WIRED	AND	Open-drain	output			
	9	WIRED	ANDFILTER	Open-drain	output with filter			
	10	WIRED	ANDPULLUP	Open-drain	output with pullu	ıp		
	11	WIRED FILTER	ANDPULLUP-	Open-drain	output with filter	and pullup		
	12	WIRED	ANDALT	Open-drain	output using alte	ernate control		
	13	WIRED	ANDALTFILTE	R Open-drain	output using alte	ernate control w	rith filter	
	14	WIRED UP	ANDALTPULL-	Open-drain	output using alte	ernate control w	rith pullup	
	15	WIRED LUPFIL	ANDALTPUL- TER	Open-drain	output using alte	ernate control w	ith filter and pull	lup
27:24	MODE6	0x0	RW	Pin 6 Mode				<u> </u>
	Configure mod	e for pin 6.						
	Value	Mode		Description				
	0	DISABI	LED	Input disable	ed. Pullup if DO	JT is set.		
	1	INPUT		Input enable	ed. Filter if DOU	T is set		
	2	INPUTI	PULL	Input enable	ed. DOUT deterr	nines pull direct	tion	
	3	INPUT	PULLFILTER	Input enable	ed with filter. DO	UT determines	pull direction	

Bit	Name	Reset Access	Description
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
23:20	MODE5	0x0 RW	Pin 5 Mode
	Configure mode for	or pin 5.	
	Value	Mode	Description
	0	DISABLED	Input disabled. Pullup if DOUT is set.
	1	INPUT	Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup

Bit	Name	Reset	Access	Description
19:16	MODE4	0x0	RW	Pin 4 Mode
	Configure mode for pire	n 4.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFI	LTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL	_T	Push-pull using alternate control
	6	WIREDOR		Wired-or output
	7	WIREDORPU	LLDOWN	Wired-or output with pull-down
	8	WIREDAND		Open-drain output
	9	WIREDANDFI	LTER	Open-drain output with filter
	10	WIREDANDP	ULLUP	Open-drain output with pullup
	11	WIREDANDPI FILTER	ULLUP-	Open-drain output with filter and pullup
	12	WIREDANDAI	LT	Open-drain output using alternate control
	13	WIREDANDAI	LTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDAI UP	LTPULL-	Open-drain output using alternate control with pullup
	15	WIREDANDAI LUPFILTER	LTPUL-	Open-drain output using alternate control with filter and pullup
15:12	MODE3	0x0	RW	Pin 3 Mode
	Configure mode for pire	n 3.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFI	LTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL	т_т	Push-pull using alternate control
	6	WIREDOR		Wired-or output
	7	WIREDORPU	LLDOWN	Wired-or output with pull-down
	8	WIREDAND		Open-drain output
	9	WIREDANDFI	LTER	Open-drain output with filter
	10	WIREDANDP	ULLUP	Open-drain output with pullup
	11	WIREDANDPI FILTER	ULLUP-	Open-drain output with filter and pullup

Bit	Name	Reset	Access	Description
	12	WIREDANDAL	Т	Open-drain output using alternate control
	13	WIREDANDAL	TFILTER	Open-drain output using alternate control with filter
	14	WIREDANDAL UP	TPULL-	Open-drain output using alternate control with pullup
	15	WIREDANDAL LUPFILTER	TPUL-	Open-drain output using alternate control with filter and pullup
11:8	MODE2	0x0	RW	Pin 2 Mode
	Configure mode for pi	n 2.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFIL	_TER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL ⁻	Т	Push-pull using alternate control
	6	WIREDOR		Wired-or output
	7	WIREDORPUL	LDOWN	Wired-or output with pull-down
	8	WIREDAND		Open-drain output
	9	WIREDANDFIL	TER	Open-drain output with filter
	10	WIREDANDPU	JLLUP	Open-drain output with pullup
	11	WIREDANDPU FILTER	JLLUP-	Open-drain output with filter and pullup
	12	WIREDANDAL	T	Open-drain output using alternate control
	13	WIREDANDAL	TFILTER	Open-drain output using alternate control with filter
	14	WIREDANDAL UP	TPULL-	Open-drain output using alternate control with pullup
	15	WIREDANDAL LUPFILTER	TPUL-	Open-drain output using alternate control with filter and pullup
7:4	MODE1	0x0	RW	Pin 1 Mode
	Configure mode for pi	n 1.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFIL	_TER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL	Т	Push-pull using alternate control
	6	WIREDOR		Wired-or output

3it	Name	Reset Access	Description
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
:0	MODE0	0x0 RW	Pin 0 Mode
	Configure mode for pi	in 0.	
	Value	Mode	Description
			· · · · · · · · · · · · · · · · · · ·
	0	DISABLED	Input disabled. Pullup if DOUT is set.
			Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup

31.5.3 GPIO_Px_MODEH - Port Pin Mode High Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	6	5	4	က	2	1	0
Reset		2	2			2	2			2	2			2	2	•		2	e X			2	2			2	2			Š	3	
Access		2	<u>}</u>			<u> </u>	<u>}</u>			<u> </u>	<u>}</u>			2	<u>}</u>			<u> </u>	<u>}</u>			<u> </u>	2			<u>ک</u>	<u>}</u>			Z N		
Name		34 T C C M	NO N			Z T T C C M	<u>-</u> ⊔			MODE13) 			C1100M	_			144 144	MODM			MODETO	J			ON COM	3			MODES)	

	MOE	MOE	MOE	MO MOE										
Bit	Name	Reset	Access	Description	1									
31:28	MODE15	0x0	RW	Pin 15 Mod	е									
	Configure mod	e for pin 15.												
	Value	Mode		Description										
	0	DISAB	LED	Input disabl	ed. Pullup if DO	UT is set.								
	1	INPUT		Input enable	ed. Filter if DOU	T is set								
	2	INPUT	PULL	Input enable	ed. DOUT deter	mines pull direct	ion							
	3	INPUT	PULLFILTER	Input enable	ed with filter. DC	OUT determines	pull direction							
	4	PUSHF	PULL	Push-pull or	utput									
	5	PUSHF	PULLALT	Push-pull us	sing alternate co	ontrol								
	6	WIRED	OOR	Wired-or ou	tput									
	7	WIRED	ORPULLDOWN	Wired-or ou	tput with pull-do	wn								
	8	WIRED	AND	Open-drain	output									
	9	WIRED	ANDFILTER	Open-drain	output with filter	-								
	10	WIRED	ANDPULLUP	Open-drain	output with pull	ap								
	11	WIRED FILTER	OANDPULLUP- R	Open-drain	output with filter	and pullup								
	12	WIRED	DANDALT	Open-drain	output using alt	ernate control								
	13	WIRED	ANDALTFILTER	R Open-drain	output using alt	ernate control w	ith filter							
	14	WIRED UP	ANDALTPULL-	Open-drain	output using alt	ernate control w	ith pullup							
	15	WIRED LUPFIL	ANDALTPUL- TER	Open-drain	output using alt	ernate control w	ith filter and pull	up						
27:24	MODE14	0x0	RW	Pin 14 Mod	е									
	Configure mod	e for pin 14.												
	Value	Mode		Description										
	0	DISAB	LED	Input disabl	ed. Pullup if DO	UT is set.								
	1	INPUT		Input enable	ed. Filter if DOU	T is set								
	2	INPUT	PULL	Input enable	ed. DOUT deter	mines pull direct	ion							
	3	INPUT	PULLFILTER	Input enable	ed with filter. DC	OUT determines	pull direction							

Bit	Name	Reset Access	Description
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
23:20	MODE13	0x0 RW	Pin 13 Mode
	Configure mode for pir	n 13.	
	Value	Mode	Description
	0	DISABLED	Input disabled. Pullup if DOUT is set.
	1	INPUT	Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup

Bit	Name	Reset	Access	Description
19:16	MODE12	0x0	RW	Pin 12 Mode
	Configure mode for pi	n 12.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFI	LTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL	.T	Push-pull using alternate control
	6	WIREDOR		Wired-or output
	7	WIREDORPUI	LLDOWN	Wired-or output with pull-down
	8	WIREDAND		Open-drain output
	9	WIREDANDFI	LTER	Open-drain output with filter
	10	WIREDANDPL	JLLUP	Open-drain output with pullup
	11	WIREDANDPU FILTER	JLLUP-	Open-drain output with filter and pullup
	12	WIREDANDAL	_T	Open-drain output using alternate control
	13	WIREDANDAL	TFILTER	Open-drain output using alternate control with filter
	14	WIREDANDAL UP	_TPULL-	Open-drain output using alternate control with pullup
	15	WIREDANDAL LUPFILTER	_TPUL-	Open-drain output using alternate control with filter and pullup
15:12	MODE11	0x0	RW	Pin 11 Mode
	Configure mode for pi	n 11.		
	Value	Mode		Description
	0	DISABLED		Input disabled. Pullup if DOUT is set.
	1	INPUT		Input enabled. Filter if DOUT is set
	2	INPUTPULL		Input enabled. DOUT determines pull direction
	3	INPUTPULLFI	LTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL		Push-pull output
	5	PUSHPULLAL	.T	Push-pull using alternate control
	6	WIREDOR		Wired-or output
	7	WIREDORPUI	LLDOWN	Wired-or output with pull-down
	8	WIREDAND		Open-drain output
	9	WIREDANDFI	LTER	Open-drain output with filter
	10	WIREDANDPL	JLLUP	Open-drain output with pullup
	11	WIREDANDPU FILTER	JLLUP-	Open-drain output with filter and pullup

Bit	Name	Reset Access	Description
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
11:8	MODE10	0x0 RW	Pin 10 Mode
	Configure mode for pi	n 10.	
	Value	Mode	Description
	0	DISABLED	Input disabled. Pullup if DOUT is set.
	1	INPUT	Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
7:4	MODE9	0x0 RW	Pin 9 Mode
	Configure mode for pi	n 9.	
	Value	Mode	Description
	0	DISABLED	Input disabled. Pullup if DOUT is set.
	1	INPUT	Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output

3it	Name	Reset Access	Description
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup
:0	MODE8	0x0 RW	Pin 8 Mode
	Configure mode for p	n 8.	
	Value	Mode	Description
			· · · · · · · · · · · · · · · · · · ·
	0	DISABLED	Input disabled. Pullup if DOUT is set.
			Input enabled. Filter if DOUT is set
	2	INPUTPULL	Input enabled. DOUT determines pull direction
	3	INPUTPULLFILTER	Input enabled with filter. DOUT determines pull direction
	4	PUSHPULL	Push-pull output
	5	PUSHPULLALT	Push-pull using alternate control
	6	WIREDOR	Wired-or output
	7	WIREDORPULLDOWN	Wired-or output with pull-down
	8	WIREDAND	Open-drain output
	9	WIREDANDFILTER	Open-drain output with filter
	10	WIREDANDPULLUP	Open-drain output with pullup
	11	WIREDANDPULLUP- FILTER	Open-drain output with filter and pullup
	12	WIREDANDALT	Open-drain output using alternate control
	13	WIREDANDALTFILTER	Open-drain output using alternate control with filter
	14	WIREDANDALTPULL- UP	Open-drain output using alternate control with pullup
	15	WIREDANDALTPUL- LUPFILTER	Open-drain output using alternate control with filter and pullup

31.5.4 GPIO_Px_DOUT - Port Data Out Register

Offset															Bi	t Po	sitio	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset					•									•	,										00000							
Access																								2	<u>}</u>							
Name																								Ė	5							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	DOUT	0x0000	RW	Data Out
	Data output on pin.			

31.5.5 GPIO_Px_DOUTTGL - Port Data Out Toggle Register

Offset															Bi	t Pc	siti	on														
0x018	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset														•	,				•						00000							
Access																								5	<u>-</u>							
Name																																

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	DOUTTGL	0x0000	W1	Data Out Toggle
	Write bits to 1 to togg	le correspondin	g bits in GF	PIO_Px_DOUT. Bits written to 0 will have no effect.

31.5.6 GPIO_Px_DIN - Port Data in Register

Offset															Bi	t Po	siti	on														
0x01C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset		1				-		'		1				'	ı	1		1						00000	00000		1		1			
Access																								۵	۷							
Name																								2								

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure co	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	DIN	0x0000	R	Data in
	Port data input.			

31.5.7 GPIO_Px_PINLOCKN - Port Unlocked Pins Register

Offset															Ві	it Po	siti	on														
0x020	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	7	_	0
Reset			•		•		•																	L L	L						•	
Access																								Š	≩ Ƴ							
Name																									PINCON							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	PINLOCKN	0xFFFF	RW	Unlocked Pins
	Shows unlocked pins	in the port. To lo	ock pin n, c	clear bit n. The pin is then locked until reset.

31.5.8 GPIO_Px_OVTDIS - Over Voltage Disable for All Modes

Offset															Bi	t Po	siti	on														
0x028	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	2	_	0
Reset							•		•											•					nnnxn							
Access																								2	<u>}</u>							
Name																								Si C	SICINO							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure contions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	OVTDIS	0x0000	RW	Disable Over Voltage Capability
	Disabling the Over Vo	oltage capability	will provide	e less distortion on analog inputs.

31.5.9 GPIO_EXTIPSELL - External Interrupt Port Select Low Register

Offset		Bit Po	sition	
0x400	31 30 29 28 27 27 26 26 27 27	23 22 22 21 20 20 19 17 16	15 41 12 11 11 11 10 <th>r 9 r 4 r 7 r 0</th>	r 9 r 4 r 7 r 0
Reset	000	000	000	000
Access	RW RW	RW RW	RW RW	RW W
Name	EXTIPSEL7	EXTIPSEL5 EXTIPSEL4	EXTIPSEL3 EXTIPSEL2	EXTIPSEL1 EXTIPSEL0

	Ш	Ш —	Δ	<u> </u>	Ш	й	Ш	Δ̈́
Bit	Name	Reset	Access	Description				
31:28	EXTIPSEL7	0x0	RW	External Int	errupt 7 Port S	Select		
	Select input po	rt for external inter	rupt 7.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	7	
	1	PORTB		Port B group	selected for ex	ternal interrupt	7	
	2	PORTC		Port C group	selected for ex	cternal interrupt	7	
	3	PORTD		Port D group	selected for ex	kternal interrupt	7	
	5	PORTF		Port F group	selected for ex	ternal interrupt	7	
27:24	EXTIPSEL6	0x0	RW	External Int	errupt 6 Port S	Select		
	Select input po	rt for external inter	rupt 6.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	6	
	1	PORTB		Port B group	selected for ex	ternal interrupt	6	
	2	PORTC		Port C group	selected for ex	kternal interrupt	6	
	3	PORTD		Port D group	selected for ex	kternal interrupt	6	
	5	PORTF		Port F group	selected for ex	ternal interrupt	6	
23:20	EXTIPSEL5	0x0	RW	External Int	errupt 5 Port S	Select		-
	Select input po	rt for external inter	rupt 5.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	5	
	1	PORTB		Port B group	selected for ex	ternal interrupt	5	
	2	PORTC		Port C group	selected for ex	kternal interrupt	5	
	3	PORTD		Port D group	selected for ex	kternal interrupt	5	
	5	PORTF		Port F group	selected for ex	ternal interrupt	5	
19:16	EXTIPSEL4	0x0	RW	External Int	errupt 4 Port S	Select		
	Select input po	rt for external inter	rupt 4.					

Bit	Name	Reset	Access	Description
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 4
	1	PORTB		Port B group selected for external interrupt 4
	2	PORTC		Port C group selected for external interrupt 4
	3	PORTD		Port D group selected for external interrupt 4
	5	PORTF		Port F group selected for external interrupt 4
15:12	EXTIPSEL3	0x0	RW	External Interrupt 3 Port Select
	Select input port for e	external interrupt	3.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 3
	1	PORTB		Port B group selected for external interrupt 3
	2	PORTC		Port C group selected for external interrupt 3
	3	PORTD		Port D group selected for external interrupt 3
	5	PORTF		Port F group selected for external interrupt 3
11:8	EXTIPSEL2	0x0	RW	External Interrupt 2 Port Select
	Select input port for e	external interrupt	2.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 2
	1	PORTB		Port B group selected for external interrupt 2
	2	PORTC		Port C group selected for external interrupt 2
	3	PORTD		Port D group selected for external interrupt 2
	5	PORTF		Port F group selected for external interrupt 2
7:4	EXTIPSEL1	0x0	RW	External Interrupt 1 Port Select
	Select input port for e	external interrupt	1.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 1
	1	PORTB		Port B group selected for external interrupt 1
	2	PORTC		Port C group selected for external interrupt 1
	3	PORTD		Port D group selected for external interrupt 1
	5	PORTF		Port F group selected for external interrupt 1
3:0	EXTIPSEL0	0x0	RW	External Interrupt 0 Port Select
	Select input port for e	external interrupt	0.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 0
	1	PORTB		Port B group selected for external interrupt 0

Bit	Name	Reset	Access	Description
	2	PORTC		Port C group selected for external interrupt 0
	3	PORTD		Port D group selected for external interrupt 0
	5	PORTF		Port F group selected for external interrupt 0

31.5.10 GPIO_EXTIPSELH - External Interrupt Port Select High Register

Offset											Bit Position																				
0x404	31 30 30 28 28 27 27 27 27 27 27 27 27 27 27 27 27 27				20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0						
Reset	'	OXO	3			>	3			0x0				0x0			0×0			0×0					2) X		0×0			
Access	s % %			AS .			RW				RW				S. S.				RW				A W								
Name	EL15			EXTIDSE! 14	_			EVTIBEEL 13	A IIPSEL I			EVTIDOE 1	A IIP SEL I			EXTIPSEI 11	-		EXTIPSEL10					CYTIDOELO	_			FXTIDSELA			

	Ш	Ш	Ш	Ш	Ш	Ш	Ш	Ш
Bit	Name	Reset	Access	Description				
31:28	EXTIPSEL15	0x0	RW	External Int	errupt 15 Port	Select		
	Select input po	rt for external inte	errupt 15.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	15	
	1	PORTB		Port B group	selected for ex	ternal interrupt	15	
	2	PORTC		Port C group	selected for ex	ternal interrupt	15	
	3	PORTD		Port D group	selected for ex	ternal interrupt	15	
	5	PORTF		Port F group	selected for ex	ternal interrupt	15	
27:24	EXTIPSEL14	0x0	RW	External Int	errupt 14 Port	Select		
	Select input po	rt for external inte	errupt 14.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	14	
	1	PORTB		Port B group	selected for ex	ternal interrupt	14	
	2	PORTC		Port C group	selected for ex	ternal interrupt	14	
	3	PORTD		Port D group	selected for ex	ternal interrupt	14	
	5	PORTF		Port F group	selected for ex	ternal interrupt	14	
23:20	EXTIPSEL13	0x0	RW	External Int	errupt 13 Port	Select		
	Select input po	rt for external into	errupt 13.					
	Value	Mode		Description				
	0	PORTA		Port A group	selected for ex	ternal interrupt	13	_
	1	PORTB		Port B group	selected for ex	ternal interrupt	13	
	2	PORTC		Port C group	selected for ex	ternal interrupt	13	
	3	PORTD		Port D group	selected for ex	ternal interrupt	13	
	5	PORTF		Port F group	selected for ex	ternal interrupt	13	
19:16	EXTIPSEL12	0x0	RW	External Int	errupt 12 Port	Select		
	Select input po	rt for external inte	errupt 12.					
	-							

Bit	Name	Reset	Access	Description
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 12
	1	PORTB		Port B group selected for external interrupt 12
	2	PORTC		Port C group selected for external interrupt 12
	3	PORTD		Port D group selected for external interrupt 12
	5	PORTF		Port F group selected for external interrupt 12
15:12	EXTIPSEL11	0x0	RW	External Interrupt 11 Port Select
	Select input port for e	external interrupt	11.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 11
	1	PORTB		Port B group selected for external interrupt 11
	2	PORTC		Port C group selected for external interrupt 11
	3	PORTD		Port D group selected for external interrupt 11
	5	PORTF		Port F group selected for external interrupt 11
11:8	EXTIPSEL10	0x0	RW	External Interrupt 10 Port Select
	Select input port for e	external interrupt	10.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 10
	1	PORTB		Port B group selected for external interrupt 10
	2	PORTC		Port C group selected for external interrupt 10
	3	PORTD		Port D group selected for external interrupt 10
	5	PORTF		Port F group selected for external interrupt 10
7:4	EXTIPSEL9	0x0	RW	External Interrupt 9 Port Select
	Select input port for e	external interrupt	9.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 9
	1	PORTB		Port B group selected for external interrupt 9
	2	PORTC		Port C group selected for external interrupt 9
	3	PORTD		Port D group selected for external interrupt 9
	5	PORTF		Port F group selected for external interrupt 9
3:0	EXTIPSEL8	0x0	RW	External Interrupt 8 Port Select
	Select input port for e	external interrupt	8.	
	Value	Mode		Description
	0	PORTA		Port A group selected for external interrupt 8
	1	PORTB		Port B group selected for external interrupt 8

			Description
2	2	PORTC	Port C group selected for external interrupt 8
3	3	PORTD	Port D group selected for external interrupt 8
5	5	PORTF	Port F group selected for external interrupt 8

31.5.11 GPIO_EXTIPINSELL - External Interrupt Pin Select Low Register

Offset									Bit Po	sition										
0x408	33	29	27	25	23	21	20	19 19	17	15	13 13	11 01	o 8	7	ۍ 4	e 2	- 0			
Reset		0x3		0x2			Š Z		0x0		0x3		0x2		0×1		0x0			
Access		SX SX		SX SX			<u>×</u>		X N		A N		ZX.		SK SK		§ S			
Name		EXTIPINSEL7		EXTIPINSEL6			EXTIPINSEL5		EXTIPINSEL4		EXTIPINSEL3		EXTIPINSEL2		EXTIPINSEL1		EXTIPINSELO			
Bit	Name			Reset		Ac	cces	s Des	criptior											
31:30	Reserv	⁄ed		To ens	ure co	mpa	tibility	/ with fu	ture de	vices, a	ılways wı	rite bits t	o 0. Mo	re inforr	nation in	1.2 Co	onven-			
29:28	EXTIP	INSEL7		0x3		R۱	N	Exte	External Interrupt 7 Pin Select											
	Select	the pin t	for exter	nal inter	rupt 7															
	Value			Mode				Des	cription											
	0			PIN4				Pin 4	4											
	1			PIN5				Pin												
	2						Pin (
	3			PIN7					/											
27:26	Reserv	red		To ens	ure co	mpa	tibility	/ with fu	ture de	vices, a	ılways wı	rite bits t	o 0. Mo	re inforr	mation in	1.2 Co	onven-			
25:24		INSEL6		0x2		R۱	N	Exte	ernal Int	errupt	6 Pin Se	elect								
	Select	the pin t	for exter	nal inter	rrupt 6															
	Value			Mode				Des	cription											
	0			PIN4				Pin 4												
	1			PIN5				Pin												
	3			PIN6 PIN7				Pin (
23:22	Reserv	red .			ure co	mpa	tibility			vices, a	ılways wı	rite bits t	o 0. Mo	re inforr	mation in	1.2 Co	onven-			
21:20	EXTIP	INSEL5		0x1		R۱	N	Exte	ernal In	errupt	5 Pin S	elect								
	Select	the pin t	for exter	nal inter	rupt 5															
	Value			Mode				Des	cription											
	0 PIN4				Pin 4	4														
	1 PIN5				Pin 5															
	2			PIN6				Pin												
	3 PIN7						Pin 7													

Bit	Name	Reset	Access	Description
19:18	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	EXTIPINSEL4	0x0	RW	External Interrupt 4 Pin Select
	Select the pin for 6	external interrupt	4.	
	Value	Mode		Description
	0	PIN4		Pin 4
	1	PIN5		Pin 5
	2	PIN6		Pin 6
	3	PIN7		Pin 7
15:14	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
13:12	EXTIPINSEL3	0x3	RW	External Interrupt 3 Pin Select
	Select the pin for e	external interrupt	3.	
	Value	Mode		Description
	0	PIN0		Pin 0
	1	PIN1		Pin 1
	2	PIN2		Pin 2
	3	PIN3		Pin 3
11:10	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
9:8	EXTIPINSEL2	0x2	RW	External Interrupt 2 Pin Select
	Select the pin for 6	external interrupt	2.	
	Value	Mode		Description
	0	PIN0		Pin 0
	1	PIN1		Pin 1
	2	PIN2		Pin 2
	3	PIN3		Pin 3
7:6	Reserved	To ensure tions	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	EXTIPINSEL1	0x1	RW	External Interrupt 1 Pin Select
	Select the pin for e	external interrupt	1.	
	Value	Mode		Description
	0	PIN0		Pin 0
	1	PIN1		Pin 1
	2	PIN2		Pin 2
	3	PIN3		Pin 3

Bit	Name	Reset	Access	Description
3:2	Reserved	To ensure co	ompatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	EXTIPINSEL0	0x0	RW	External Interrupt 0 Pin Select
	Select the pin for e	xternal interrupt ().	
	Value	Mode		Description
	0	PIN0		Pin 0
	1	PIN1		Pin 1
	2	PIN2		Pin 2
	3	PIN3		Pin 3

31.5.12 GPIO_EXTIPINSELH - External Interrupt Pin Select High Register

Offset								Bit Po	sition							
0x40C	31	29	27	25	23	21	19	17	5 4	13	1 0	o 8	7	ۍ 4	8 2	- 0
Reset		0x3		0x2	·	0x1		0x0		0x3		0x2		0×1		0x0
Access		SK SK		SX SX		SX SX		A W		A N		Z.		SK SK		₩ Ş
Name		EXTIPINSEL15		EXTIPINSEL14		EXTIPINSEL13		EXTIPINSEL12		EXTIPINSEL11		EXTIPINSEL10		EXTIPINSEL9		EXTIPINSEL8
Bit	Name			Reset		Acces	s Des	cription								
31:30	Reserv	/ed		To ens	ure con	npatibilit	y with fu	ture de	/ices, a	lways wi	rite bits	to 0. Ma	re inforr	nation ir	1.2 Co	nven-
29:28	EXTIP	INSEL1	5	0x3		RW	Exte	ernal Int	terrupt	15 Pin S	Select					
	Select	the pin	for exter	nal inte	rupt 15											
	Value			Mode			Des	cription								
	0			PIN12			Pin	12								
	1			PIN13			Pin									
	3			PIN14			Pin [•]									
				PIN15												
27:26	Reserv	/ed		To ens	ure con	npatibilit	y with fu	ture de	/ices, a	lways wi	rite bits	to 0. Mo	re inforr	nation ir	1.2 Co	nven-
25:24		INSEL1		0x2		RW	Exte	ernal Int	terrupt	14 Pin S	Select					
	Select	the pin t	for exter	nal inte	rupt 14											
	Value			Mode				cription								
	0			PIN12			Pin									
	1			PIN13			Pin									
	3			PIN14 PIN15			Pin ¹									
							,									
23:22	Reserv	/ea		tions	ure con	npatibilit	y with tu	ture ae	/ices, a	lways wi	ite bits i	to U. Mo	re intorr	nation ir	1 1.2 Co	nven-
21:20	EXTIP	INSEL1:	3	0x1		RW	Exte	ernal Int	terrupt	13 Pin S	Select					
	Select	the pin	for exter	nal inte	rupt 13											
	Value			Mode			Des	cription								
	0			PIN12			Pin	12								
	1			PIN13			Pin									
				PIN14			Pin									
	3 PIN15						Pin	15								

Bit	Name	Reset Ac	ccess Description
19:18	Reserved	To ensure compat	tibility with future devices, always write bits to 0. More information in 1.2 Conven-
17:16	EXTIPINSEL12	0x0 RV	N External Interrupt 12 Pin Select
	Select the pin for ex	xternal interrupt 12.	
	Value	Mode	Description
	0	PIN12	Pin 12
	1	PIN13	Pin 13
	2	PIN14	Pin 14
	3	PIN15	Pin 15
15:14	Reserved	To ensure compat	tibility with future devices, always write bits to 0. More information in 1.2 Conven-
13:12	EXTIPINSEL11	0x3 RV	N External Interrupt 11 Pin Select
	Select the pin for ex	xternal interrupt 11.	
	Value	Mode	Description
	0	PIN8	Pin 8
	1	PIN9	Pin 9
	2	PIN10	Pin 10
	3	PIN11	Pin 11
11:10	Reserved	To ensure compat	tibility with future devices, always write bits to 0. More information in 1.2 Conven-
9:8	EXTIPINSEL10	0x2 RV	N External Interrupt 10 Pin Select
	Select the pin for ex	xternal interrupt 10.	
	Value	Mode	Description
	0	PIN8	Pin 8
	1	PIN9	Pin 9
	2	PIN10	Pin 10
	3	PIN11	Pin 11
7:6	Reserved	To ensure compat	tibility with future devices, always write bits to 0. More information in 1.2 Conven-
5:4	EXTIPINSEL9	0x1 RV	N External Interrupt 9 Pin Select
	Select the pin for ex	xternal interrupt 9.	
	Value	Mode	Description
	0	PIN8	Pin 8
	1	PIN9	Pin 9
	2	PIN10	Pin 10

Bit	Name	Reset	Access	Description
3:2	Reserved	To ensure o	compatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
1:0	EXTIPINSEL8	0x0	RW	External Interrupt 8 Pin Select
	Select the pin for e	xternal interrupt	8.	
	Value	Mode		Description
	0	PIN8		Pin 8
	1	PIN9		Pin 9
	2	PIN10		Pin 10
	3	PIN11		Pin 11

31.5.13 GPIO_EXTIRISE - External Interrupt Rising Edge Trigger Register

Offset															Bi	t Po	siti	on														
0x410	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	41	13	12	7	10	စ	8	7	9	5	4	က	2	_	0
Reset		•			•		•																		nonnxn	•			•			
Access																								2	<u>}</u>							
Name																																

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure col	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	EXTIRISE	0x0000	RW	External Interrupt N Rising Edge Trigger Enable
	Set bit n to enable tr	iggering of exterr	nal interrup	t n on rising edge.
	Value	Description		
	EXTIRISE[n] = 0	Rising edge to	rigger disa-	_
	EXTIRISE[n] = 1	Rising edge to	rigger ena-	_

31.5.14 GPIO_EXTIFALL - External Interrupt Falling Edge Trigger Register

Offset															Bi	t Po	siti	on														
0x414	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	7	9	5	4	3	2	_	0
Reset																									000000							
Access																								i	≩							
Name																								L L	EXIIFALL							
Bit	Na	me					Re	set			Ac	ces	s I	Des	crip	tion																
31:16	Re	serv	⁄ed				To tion		ure	con	pati	bility	/ Wii	th fu	ture	dev	ices	s, alı	way	s wr	ite k	its t	o 0.	Мо	re ir	nfori	nati	on i	n 1	2 Co	nve	en-
15:0	EX	TIF	٩LL				0x0	0000)		RW	/	I	Exte	rna	l Int	erru	ıpt l	N Fa	allin	g E	dge	Triç	gge	r En	abl	е					
	Se	t bit	n to	ena	able	trig	gerir	ng o	f ext	terna	al int	erru	ıpt r	on	falliı	ng e	dge															
	Va	lue					De	scrip	otior	1																						_
	EX	TIF	ALL[[n] =	0		Fal abl		edg	je tri	gge	r dis	;-																			
	EX	TIF	ALL[[n] =	: 1		Fal ble		edge trigger ena-																							

31.5.15 GPIO_EXTILEVEL - External Interrupt Level Register

31.5.15	01 10_L					CIII	ai ii	iteri	upt	LC	/ G1 1	\egi	13161																		
Offset														Bi	it Po	ositi	on														
0x418	33	29	28	27	26	25	24	23	22	7	20	19	8	17	16	15	4	73	12	7	9	6	ω	7	9	5	4	က	7	_	0
Reset	·	•	0			0	0				0			0	0									•	•	•					
Access			S.			S S S	RW				₽			R N N	RW W																
Name			EM4WU12			EM4WU9	EM4WU8				EM4WU4			EM4WU1	EM4WU0																
Bit	Name					Re	set			Ac	ces	s i	Des	crip	tior	1															
31:29	Reser	ved				To tio		ure	com	pati	bility	y wit	th fu	ture	de	/ices	s, al	way	s wi	rite l	oits	to 0	. Мо	re i	nfori	nati	on in	1.2	? Co	nve	n-
28	EM4W	/U12	2			0				RV	/	I	EM4	Wa	ake	Up I	Leve	el fo	r El	M4V	VU1	2 P	in								
27:26	Reser	ved				To tio		ure	com	pati	ibility	y wit	th fu	ture	de	/ices	s, al	way	's WI	rite l	oits	to 0	. Мо	re i	nfori	nati	on in	1.2	? Co	nve	n-
25	EM4W	/U9				0				RV	/	ı	EM4	l Wa	ake	Up I	Leve	el fo	r El	M4V	VU9	Pir	1								
24	EM4W	/U8				0				RV	/	ı	EM4	Wa	ake	Up I	Leve	el fo	r El	M4V	8UV	Pir	1								
23:21	Reser	ved				To tio		ure	com	pati	bility	y wit	th fu	ture	de	/ices	s, al	way	's WI	rite l	oits	to 0	. Мо	re i	nfori	nati	on in	1.2	? Co	nve	n-
20	EM4W	/U4				0				RV	/	ı	EM4	Wa	ake	Up I	Leve	el fo	r El	M4V	VU4	Pir	1								
19:18	Reser	ved				To tion		ure	com	pati	ibility	y wit	th fu	ture	de	/ices	s, al	way	's WI	rite l	oits	to 0	. Мо	re i	nfori	nati	on in	1.2	? Co	nve	n-

EM4 Wake Up Level for EM4WU1 Pin

EM4 Wake Up Level for EM4WU0 Pin

To ensure compatibility with future devices, always write bits to 0. More information in 1.2 Conven-

17

16

15:0

EM4WU1

EM4WU0

Reserved

0

0

tions

RW

RW

31.5.16 GPIO_IF - Interrupt Flag Register

Offset	Bit Posi	ition
0x41C	3. 3. 3. 4. 4. 4. 4. 4. 4. 4. 4. 4. 4. 4. 4. 4.	2 4 5 7 1 1 2 1 3 4 5 6 7 9 8 8 7 9 9 7 7 7 7 7 9 9 9 9 7 9 9 9 9
Reset	00000×0	00000x0
Access	α	<u>«</u>
Name	EM4WU	EXT

Bit	Name	Reset	Access	Description
31:16	EM4WU	0x0000	R	EM4 Wake Up Pin Interrupt Flag
	EM4 wake up Pir	n Interrupt flag.		•
	Value	Description		
	0	Interrupt flag	cleared	_
	1	Interrupt flag	set	_
15:0	EXT	0x0000	R	External Pin Interrupt Flag
	Pin n external int	errupt flag.		
	Value	Description		
	0	External inter	rupt flag	_
	1	External inter	rupt flag	

31.5.17 GPIO_IFS - Interrupt Flag Set Register

Offset															Bi	t Po	siti	on														
0x420	31	30	53	78	27	26	25	24	23	22	21	20	9	8	17	16	15	14	13	12	7	10	စ	∞	7	9	5	4	က	2	_	0
Reset			000000000000000000000000000000000000000																		0	nnnnxn										
Access			W1 0x0																	2	<u> </u>											
Name			~																		ŀ	ΕXΙ										

Bit	Name	Reset	Access	Description
31:16	EM4WU	0x0000	W1	Set EM4WU Interrupt Flag
	Write 1 to set the EM	4WU interrupt fla	ag	
15:0	EXT	0x0000	W1	Set EXT Interrupt Flag
	Write 1 to set the EX			

31.5.18 GPIO_IFC - Interrupt Flag Clear Register

Offset	Bit Po	osition
0x424	1 1 <th>5 4 5 1</th>	5 4 5 1
Reset	00000x0	0000x0
Access	(R)W1	(R)W1
Name	EM4WU	EXT

Bit	Name	Reset	Access	Description
31:16	EM4WU	0x0000	(R)W1	Clear EM4WU Interrupt Flag
	Write 1 to clear the E (This feature must be	•	•	ing returns the value of the IF and clears the corresponding interrupt flags .
15:0	EXT	0x0000	(R)W1	Clear EXT Interrupt Flag
	Write 1 to clear the E feature must be enab		•	returns the value of the IF and clears the corresponding interrupt flags (This

31.5.19 GPIO_IEN - Interrupt Enable Register

Offset	Bit Po	osition
0x428	33 3 3 3 3 3 3 3 3 3 3 3 4 3 4 4 4 4 4	5 4 5 7 1
Reset	00000X0	0000x0
Access	»X ≫	X X
Name	EM4WU	EXT

Bit	Name	Reset	Access	Description
31:16	EM4WU	0x0000	RW	EM4WU Interrupt Enable
	Enable/disable the EN	M4WU interrupt		
15:0	EXT	0x0000	RW	EXT Interrupt Enable
	Enable/disable the EX	KT interrupt		

31.5.20 GPIO_EM4WUEN - EM4 Wake Up Enable Register

Offset															Bi	t P	ositi	on													
0x42C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	6	8	2	6	2	4	3	2	1
Reset								00000	00000																						
Access								2	2																						
Name		EM4WUEN																													
-	Name Reset Access Description																														
Bit	Na	me					Re		J		Ac	ces	s	Des	crip	tior	1														
Bit 31:16			UEN	J							Ac		S	Des EM4				Enal	ble												
	EM	l4W			ole E	EM4	0x0	set)	que	RV	V			Wa	ike	Up I			equ	est.										
	EM	I4W ite 1			ole E	EM4	0x0	set)	que	RV	V		EM4	W able	ake EN	Up I			equ	est.										
	EN Wr	I4W ite 1			ole E	EM4	0x0	set)	que	RV	V		EM 4 o dis	l Waable	e EM	Up I 14 w	ake	up r												
	EM Wr	I4W ite 1			ole E	EM4	0x0	set)	que	RV	V		EM4 o dis Des	able cript	e EM	Up I 14 w 4 wa	ake ike u	up r	n piı	า										

31.5.21 GPIO_ROUTEPEN - I/O Routing Pin Enable Register

Offset															Bi	it Po	siti	on														
0x440	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	2	4	က	7	_	0
Reset			'		'						'			'	'	'					<u>'</u>				'			0	_	_	-	_
Access																												RW	₩ M	RW	Z.	A W
Name																												SWVPEN	TDIPEN	TDOPEN	SWDIOTMSPEN	SWCLKTCKPEN

Bit	Name	Reset	Access	Description
31:5	Reserved	To ensure contions	mpatibility (with future devices, always write bits to 0. More information in 1.2 Conven-
4	SWVPEN	0	RW	Serial Wire Viewer Output Pin Enable
	Enable Serial Wire V	iewer connection	n to pin.	
3	TDIPEN	1	RW	JTAG Test Debug Input Pin Enable
	Enable JTAG TDI co	nnection to pin.		
2	TDOPEN	1	RW	JTAG Test Debug Output Pin Enable
	Enable JTAG TDO c	onnection to pin.		
1	SWDIOTMSPEN	1	RW	Serial Wire Data and JTAG Test Mode Select Pin Enable
	can no longer be acc make sure you have	essed by a debuat least a 3 seco	igger. A res	Select connection to pin. WARNING: When this pin is disabled, the device set will set the pin back to a default state as enabled. If you disable this pin, t at the start of you program code before you disable the pin. This way, the a reset before the pin is disabled.
0	SWCLKTCKPEN	1	RW	Serial Wire Clock and JTAG Test Clock Pin Enable
	accessed by a debug	gger. A reset will ond timeout at th	set the pin ne start of y	to pin. WARNING: When this pin is disabled, the device can no longer be a back to a default state as enabled. If you disable this pin, make sure you you program code before you disable the pin. This way, the debugger will the pin is disabled.

31.5.22 GPIO_ROUTELOC0 - I/O Routing Location Register

Offset															Bi	t Po	siti	on													
0x444	31	30	29	28	27	26	25	24	23	22	21	20	19	8	17	16	15	4	13	12	7	9	တ	∞	7	9	2	4	დ <i>ი</i>	1 _	0
Reset																													00×0		
Access																													ΑW		
Name																													SWVLOC		

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5:0	SWVLOC	0x00	RW	I/O Location
	Decides the loca	ation of the SWV pi	ns.	
	Value	Mode		Description
	0	LOC0		Location 0
	1	LOC1		Location 1
	2	LOC2		Location 2
	3	LOC3		Location 3

31.5.23 GPIO_INSENSE - Input Sense Register

Offset															Bi	t Pc	siti	on														
0x450	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	7	10	6	∞	7	9	5	4	က	2	_	0
Reset																															_	_
Access																															R ≪	RW
Name																															EM4WU	Ā

Bit	Name	Reset	Access	Description
31:2	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
1	EM4WU	1	RW	EM4WU Interrupt Sense Enable
	Set this bit to enable i	nput sensing for	EM4WU i	nterrupts.
0	INT	1	RW	Interrupt Sense Enable
	Set this bit to enable i	nput sensing for	interrupts	

31.5.24 GPIO_LOCK - Configuration Lock Register


Offset															Bi	t Po	siti	on														
0x454	31	30	29	28	27	26	25	24	23	22	21	20	19	9	17	16	15	4	13	12	7	10	6	8	7	9	5	4	က	2	_	0
Reset							1		•					1	ı	1		1	ı		'		'		nnnnxn			ı				
Access																									I A Y							
Name																								\L\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	LOCKNEY							

Bit	Name	Reset	Access	Description
31:16	Reserved	To ensure c tions	ompatibility	with future devices, always write bits to 0. More information in 1.2 Conven-
15:0	LOCKKEY	0x0000	RWH	Configuration Lock Key

Write any other value than the unlock code to lock MODEL, MODEH, CTRL, PINLOCKN, OVTDIS, EXTIPSELL,
Mode	Value	Description
Read Operation		
UNLOCKED	0	GPIO registers are unlocked
LOCKED	1	GPIO registers are locked
Write Operation		
LOCK	0	Lock GPIO registers
UNLOCK	0xA534	Unlock GPIO registers

32. APORT - Analog Port





Quick Facts

What?

The Analog Port (APORT) is a set of analog buses which are used to connect I/O pins to analog peripheral signals.

Why?

The APORT gives on-chip analog resources access to a large number of I/O pins, and provides the system designer with a high degree of routing flexibility.

How?

An analog peripheral requests a pad by simply configuring its input/output to use a channel on APORT. That selection becomes an APORT request where the APORT control switches the pad and the analog signal onto a common bus.

32.1 Introduction

APORT consists of wires, switches, and control logic needed to route signals between analog peripherals and I/O pins. On-chip clients can be either producers or consumers. Analog producers are active devices that drive current/voltage into an APORT, such as current or voltage DACs. Consumers are passive devices that monitor or react to the current/voltage routed to them via the APORT, such as ADCs or analog comparators (ACMP).

32.2 Features

- Pins are typically mapped to two different APORT buses
- Arbitration and conflict status provided to each APORT client

32.3 Functional Description




Figure 32.1. Analog Bus (ABUS)

An analog bus (ABUS) consists of analog switches connected to a common wire as shown in Figure 32.1 Analog Bus (ABUS) on page 1115. An APORT consists of multiple ABUSes. Since many clients can operate differentially, buses are grouped by pairs as X and Y. If a given client uses a single ABUS (e.g. single-ended ADC), X and Y are just labels to differentiate the two buses.

When operating differentially, most APORT clients require that one input be chosen from an X bus and the other from a Y bus. For example, the ACMP block will not allow both positive and negative inputs to be chosen from X buses.

32.3.1 I/O Pin Considerations

For external analog signals routed through the APORT, the maximum supported analog I/O voltage will typically be limited to the MIN(V_{ANALOGSUPPLY}, IOVDD) (where V_{ANALOGSUPPLY} is the supply pin powering the analog module). Practically, this means that if IOVDD=1.8 V, the maximum supported analog IO voltage on APORT-routed signals will be limited to 1.8 V, regardless of the analog module supply voltage.

32.3.2 APORT ABUS Naming




Figure 32.2. Conceptual APORT Structure

APORT ABUSes are prefixed with "BUS" and are grouped in pairs. Each pair is uniquely identified using a letter prefix ("A", "B", "C", etc.) followed by either a "X" or "Y" to identify the ABUS in the pair. For example, "BUSDX" decodes as: "BUS"=ABUS, "D"=pair, "X"=bus. Figure 32.2 Conceptual APORT Structure on page 1116 illustrates this organization.

APORT clients are generally described once in this reference manual regardless of its number of instances. For example, the ACMP client is described once, but the device could contain multiple instances of the ACMP. Because of this, for APORT client descriptions in this reference manual, the ABUS connections are generalized with the prefix "APORT" followed by a number (instead of the "BUS"

followed by a letter). It is possible that different instances of an APORT client connect to different ABUSes. For example, ACMPO APORT1X might connect to the ABUS BUSAX while ACMP1 APORT1X might connect to ABUS BUSCX. Refer to the APORT Client Map in the device data sheet to map the generalized APORT client bus name to an actual device ABUS. A given ABUS has multiple switches which need to be identified. The switches on a bus are specified with the ABUS connection ID followed by a channel ID. For example, channel switch 7 on a given APORT client might be given as APORT1XCH7. Not all APORT channels map to actual GPIO. Refer to the APORT Client Maps in the device data sheet for APORT to GPIO mapping.




Figure 32.3. Detailed APORT Structure

Figure 32.3 Detailed APORT Structure on page 1117 shows all the possible routes between different peripherals and different pins via APORT BUS for the largest package of the EFR32 device family. Note that, in the figure, the BUSxX and BUSxY are annotated as xX and xY, where x=A,B,C,D and the APORTnX and APORTnY are annotated as nX and nY, where n=1,2,3,4.

For example, the IDAC APORT output 1X can be routed to pin PB14 through BUSCX. The configuration required for this routing is as follows:

- Set IDAC_CTRL_APORTOUTSEL = APORT1XCH30. This selects the IDAC APORT output 1X and pin PB14.
- Set IDAC_CTRL_APORTOUTEN = 1 and IDAC_CTRL_APORTOUTENPRS = 0. This enables the IDAC to ungate it's output to BUSCX.

Another example, when ADC is configured to operate in single channel mode for differential inputs (see 26.3.3.1 Single Channel Mode for how to configure ADC in single channel mode), the positive ADC APORT input 2X and the negative ADC APORT input 2Y can be routed to pin PC9 and PC10 via BUSBX and BUSBY respectively with the following configuration:

- Set ADCn_SINGLECTRL_POSSEL = APORT2XCH9. This selects the pin PC9 for the positive input to the ADC.
- Set ADCn_SINGLECTRL_NEGSEL = APORT2YCH10. This selects the pin PC10 for the negative input to the ADC.

For smaller packages, not all GPIO pins are available. See the pinout sections of the device data sheet for pin availability on a specific device.

32.3.3 Managing ABUSes

The ABUSes of an APORT are shared resources. The user needs to be mindful of this in assigning I/O for different clients throughout the chip, as it is possible to have conflicts for a given ABUS. Each ABUS has an arbiter responsible for limiting the control over the ABUS to one and only one client. If multiple clients attempt to control an ABUS, the arbiter allows no client control over the ABUS and asserts a conflict signal to the clients. The user has the ability to check for such a conflict in each client's status, as well as generate an interrupt.

Having only one client control an ABUS is not the same as having only one user of an ABUS. It is possible for multiple clients to access a single ABUS, but requires all but one client to relinquish control of the ABUS. To do this, some clients have bits to disable bus mastership which are 0 by default. One example is the APORTXMASTERDIS bit in the ACMPn_CTRL. When set to 1, the client will not assert control of the APORT X BUS switches, but may still connect to an APORT X BUS that is controlled by another client.

For example, the ADC and ACMP both want to use the same pin on a particular ABUS the user might set the bus master disable bit to 1 for the ACMP. The ADC is the sole master of the switch configuration on that ABUS, so switches are configured using the configuration set in the ADC. When the ACMP channel is chosen on that same bus, the actual pin connection is dictated by the ADC settings for that bus.




Figure 32.4. APORT Example 1

Figure 32.4 APORT Example 1 on page 1119 illustrates the sharing of APORT. For illustration purposes, each ABUS is identified by a numeric index (instead of BUSAX, BUSAY, BUSBX, etc.). Also, the requests from all the APORT clients are packed into a bit-vector named APORT_REQ to illustrate the request from the APORT Clients (instead of by name such as APORT1XREQ, APORT1YREQ, APORT2XREQ, etc.). In Figure 32.4 APORT Example 1 on page 1119, ABUS and client are the same color if the client has been granted the ABUS.

In Figure 32.4 APORT Example 1 on page 1119 ADC0 has requested ABUS[3:0], ACMP1 has requested ABUS[5:4], ACMP0 has requested ABUS[7], and ABUS[6] is unused. No APORT Client has requested the same ABUS as another, so there is no conflict.




Figure 32.5. APORT Example 2: Bus Conflict

In Figure 32.5 APORT Example 2: Bus Conflict on page 1120 is a similar example to Figure 32.4 APORT Example 1 on page 1119, but now both ACMP0 and ACMP1 are requesting ABUS[4]. This is a configuration error, so APORT grants neither client ABUS[4]. The user must resolve the conflict before ABUS[4] is useable.





Figure 32.6. APORT Example 3: Sharing an ABUS

Figure 32.6 APORT Example 3: Sharing an ABUS on page 1120 illustrates ABUS sharing. Both ACMPs are configured identically, except ACMP0 has its APORTXMASTERDIS bit-field set to 1. There is only one APORT master for ABUS[5:4] in this case, so there is no conflict.

33. FPUEH - Floating Point Unit Exception Handler



Quick Facts

What?

FPU exception handler allows user defined handling of FPU exceptions.

Why?

Proper handling of exceptions is crucial in many applications.

How?

The FPU exception handler monitors status flags from the FPU and issues an interrupt when exceptions occur.

33.1 Functional Description

The Floating Point Unit, FPU, included in the Cortex-M4 has a set of status flags indicating mathematical errors that cause floating-point exceptions. Available status flags are:

- · FPIOC FPU invalid operation.
- · FPDZC FPU divide-by-zero exception.
- · FPUFC FPU underflow exception.
- · FPOFC FPU overflow exception.
- · FPIDC FPU input denormal exception.
- · FPIXC FPU inexact exception.

Refer to the ARM Cortex-M4 Devices Generic User Guide for more information about the FPU status flags. The FPU exception handler, FPUEH, monitors these status flags and sets the corresponding interrupt flag in FPUEH_IF when they are asserted. An interrupt request will be set if the corresponding bit in FPUEH_IEN is set. The interrupt flags can also be set and cleared using the FPUEH_IFS and FPUEH_IFC registers, respectively.

Note: Before the FPUEH interrupt flags can be cleared, the corresponding status flag in the FPU has to be cleared. Refer to ARM Cortex-M4 Devices Generic User Guide for information on how to do this.

33.2 Register Map

The offset register address is relative to the registers base address.

Offset	Name	Туре	Description
0x000	FPUEH_IF	R	Interrupt Flag Register
0x004	FPUEH_IFS	W1	Interrupt Flag Set Register
0x008	FPUEH_IFC	(R)W1	Interrupt Flag Clear Register
0x00C	FPUEH_IEN	RW	Interrupt Enable Register

33.3 Register Description

33.3.1 FPUEH_IF - Interrupt Flag Register

Offset															Bi	t Po	siti	on														
0x000	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	80	7	9	5	4	က	2	_	0
Reset					•						•		•						•	•							0	0	0	0	0	0
Access																											22	~	22	22	22	<u>~</u>
Name																											FPIXC	FPIDC	FPOFC	FPUFC	FPDZC	FPIOC

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	FPIXC	0	R	FPU inexact exception
	Set upon FPU inexact	t exception		
4	FPIDC	0	R	FPU input denormal exception
	Set upon FPU input d	enormal except	ion	
3	FPOFC	0	R	FPU overflow exception
	Set upon FPU overflo	w exception		
2	FPUFC	0	R	FPU underflow exception
	Set upon FPU underfl	low exception		
1	FPDZC	0	R	FPU divide-by-zero exception
	Set upon FPU divide-	by-zero exception	on	
0	FPIOC	0	R	FPU invalid operation
	Set upon FPU invalid	operation		

33.3.2 FPUEH_IFS - Interrupt Flag Set Register

Offset															Bi	it Po	siti	on														
0x004	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	8	7	9	2	4	က	2	_	0
Reset			'													'											0	0	0	0	0	0
Access																											W	W1	W1	W1	W	M
Name																											FPIXC	FPIDC	FPOFC	FPUFC	FPDZC	FPIOC

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure cor tions	mpatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	FPIXC	0	W1	Set FPIXC Interrupt Flag
	Write 1 to set the FPI	XC interrupt flag	l	
4	FPIDC	0	W1	Set FPIDC Interrupt Flag
	Write 1 to set the FPI	DC interrupt flag	1	
3	FPOFC	0	W1	Set FPOFC Interrupt Flag
	Write 1 to set the FP0	OFC interrupt fla	g	
2	FPUFC	0	W1	Set FPUFC Interrupt Flag
	Write 1 to set the FPI	JFC interrupt fla	g	
1	FPDZC	0	W1	Set FPDZC Interrupt Flag
	Write 1 to set the FPI	DZC interrupt fla	g	
0	FPIOC	0	W1	Set FPIOC Interrupt Flag
	Write 1 to set the FPI	OC interrupt flag	9	

33.3.3 FPUEH_IFC - Interrupt Flag Clear Register

Offset															Bi	t Po	siti	on														
0x008	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	œ	7	9	5	4	က	2	_	0
Reset			1					1															1				0	0	0	0	0	0
Access																											(R)W1	(R)W1	(R)W1	(R)W1	(R)W1	(R)W1
Name																											FPIXC	FPIDC	FPOFC	FPUFC	FPDZC	FPIOC

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure cor tions	npatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	FPIXC	0	(R)W1	Clear FPIXC Interrupt Flag
	Write 1 to clear the FF	PIXC interrupt fla	ag	
4	FPIDC	0	(R)W1	Clear FPIDC Interrupt Flag
	Write 1 to clear the FF	PIDC interrupt fla	ag	
3	FPOFC	0	(R)W1	Clear FPOFC Interrupt Flag
	Write 1 to clear the FF	POFC interrupt f	lag	
2	FPUFC	0	(R)W1	Clear FPUFC Interrupt Flag
	Write 1 to clear the FF	PUFC interrupt f	lag	
1	FPDZC	0	(R)W1	Clear FPDZC Interrupt Flag
	Write 1 to clear the FF	PDZC interrupt f	lag	
0	FPIOC	0	(R)W1	Clear FPIOC Interrupt Flag
	Write 1 to clear the FF	PIOC interrupt fl	ag	

33.3.4 FPUEH_IEN - Interrupt Enable Register

Offset															Ві	t Po	siti	on														
0x00C	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	4	13	12	7	10	6	_∞	7	9	2	4	က	2	_	0
Reset		•	'		'	'								•		'	•							•			0	0	0	0	0	0
Access																											W.	W.	W.	W.	W.	R W
Name																											FPIXC	FPIDC	FPOFC	FPUFC	FPDZC	FPIOC

Bit	Name	Reset	Access	Description
31:6	Reserved	To ensure o	compatibility v	with future devices, always write bits to 0. More information in 1.2 Conven-
5	FPIXC	0	RW	FPIXC Interrupt Enable
	Enable/disable th	ne FPIXC interrupt		
4	FPIDC	0	RW	FPIDC Interrupt Enable
	Enable/disable th	ne FPIDC interrupt		
3	FPOFC	0	RW	FPOFC Interrupt Enable
	Enable/disable th	ne FPOFC interrup	t	
2	FPUFC	0	RW	FPUFC Interrupt Enable
	Enable/disable th	ne FPUFC interrup	t	
1	FPDZC	0	RW	FPDZC Interrupt Enable
	Enable/disable th	ne FPDZC interrup	t	
0	FPIOC	0	RW	FPIOC Interrupt Enable
	Enable/disable th	ne FPIOC interrupt		

34. Revision History

Revision 1.4

July, 2022

- Changed incorrect SysTick resolution from 32 to 24 bits in 2.16 Timers.
- Size of bootloader region in flash added to 7.3.4 Bootloader.
- User guide references in 7.3.4 Bootloader updated to reflect specific Gecko SDK versions.
- Corrected Figure 11.7 CMU HFXO Control State Machine on page 292 to reflect startup timeout configuration from the STARTUP-TIMEOUT field of the CMU_HFXOTIMEOUTCTRL register.
- References to selecting a third clock output removed from 11.3.5 Clock Output on a Pin and 11.3.7 Clock Output on PRS because the CMU CTRL register does not contain the CLKOUT2 bit field.
- · Added 33. FPUEH Floating Point Unit Exception Handler chapter.
- · Removed all references to RFSENSE.

Revision 1.3

March, 2021

- Added description of VLP and ACMP startup behavior in 25.3.12 External Override Interface.
- Added low frequency oscillators as Systick timer source in under 2.16 Timers.
- Removed a paragraph about Peripheral Access Wait Mode in 4.2.5.2 Peripheral Access Performance since this family of pats does
 not have configurable wait states.
- Corrected Information Block address in Table 7.1 MSC Flash Memory Mapping on page 126.
- Added some additional information about the Configuration Lock Word 0 (CLW0) to 7.3.2 Lock Bits (LB) Page Description.
- Added UG266 User's Guide reference in 7.3.4 Bootloader section.
- · Removed Device Revision section from 7. MSC Memory System Controller .
- · Added a Note to 26.3.3.2 Scan Mode.
- Updated 26.3.10.9 Temperature Measurement and added an additional Note.

Revision 1.2

September, 2018

- · Removed TRNG and associated details throughout document.
- · Corrections to Note formatting throughout document.
- Changed references from "EM01" to EM0/EM1 and from "EM23" to "EM2/EM3" throughout document.

Revision 1.1

March, 2018

- Removed PLFRCO and associated details throughout document.
- 9.3.3 Power-On Reset (POR): Clarification of Power-On Reset supply connection (AVDD) and threshold (1.2V).
- Added information about analog peripheral power connections and VDDX_ANA supply rail throughout document.
- Added information about IOVDD and AVDD restrictions on analog input signals throughout document.
- 10.3.9.1 EM0/EM1 Voltage Scaling: Clarification of reset effects on voltage scaling operations in progress.
- 10.3.12 Voltage Monitor (VMON): Added note about VMON hystereis and riding/falling thresholds.
- 11.3.2.4 HFXO Configuration: Clarified steady state timeout and state transition to ready.
- 11.3.2.5 LFXO Configuration: Added recommendations for GAIN setting.
- 15.3.1.3 Configurable PRS Logic: Clarified ANDNEXT and ORPREV behavior for first and last PRS channels.
- 15.3.2 Producers: Added more detail about GPIO producer source.
- 15.3.5 DMA Request on PRS: Fixed incorrect bit / register names and clarified signals for DMA are PRSRQE0 and PRSREQ1.
- 26.3.17 ADC Programming Model: Added note about changing to ASYNC clock mode with KEEPADCWARM.

Revision 1.0

October, 2017

• Remove "Confidential" watermark.

Revision 0.1

September 17th, 2017

Initial release.

Appendix 1. Abbreviations


This section lists abbreviations used in this document.

Table 1.1. Abbreviations

ADC Analog to Digital Converter AES Advanced Encryption Standard AFC Automatic Frequency Control AGC Automatic Gain Control AHB AMBA Advanced High-performance Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". AFB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". AFB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". AFC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy BLE-LR Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CCC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Ciear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator DEMOD Demodulator	Abbreviation	Description
AFC Automatic Frequency Control AGC Automatic Gain Control AHB AMBA Advanced High-performance Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CCC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	ADC	Analog to Digital Converter
AdGC Automatic Gain Control AHB AMBA Advanced High-performance Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	AES	Advanced Encryption Standard
AMBA Advanced High-performance Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Fitter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M3 CM6 Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Corrent DBG Debug DC Direct Current DEC Direct Current DEC Decimator	AFC	Automatic Frequency Control
ture". APB AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture". APC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Fitter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M3 CM4 ARM Cortex-M3 CM9 Command CM0 Command CM0 Command CM0 Command CM0 Command CM0 Command CM1 Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current	AGC	Automatic Gain Control
APC Automatic Power Control ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CCC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M3 CM5 Command CMC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) AHB		
ASK Amplitude Shift Keying BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CCC Compare / Capture CCA Cilear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Direct Current	APB	AMBA Advanced Peripheral Bus. AMBA is short for "Advanced Microcontroller Bus Architecture".
BLE Bluetooth Low Energy BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Direct Current	APC	Automatic Power Control
BLE-LR Bluetooth Low Energy Long Range BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	ASK	Amplitude Shift Keying
BR Baud Rate BT Bandwidth Time product BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BLE	Bluetooth Low Energy
BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BLE-LR	Bluetooth Low Energy Long Range
BUFC Buffer Controller BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BR	Baud Rate
BW Bandwidth CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BT	Bandwidth Time product
CBC Cipher Block Chaining (AES mode of operation) CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BUFC	Buffer Controller
CBC-MAC Cipher Block Chaining - Message Authentication Code (AES mode of operation) CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	BW	Bandwidth
CC Compare / Capture CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CBC	Cipher Block Chaining (AES mode of operation)
CCA Clear Channel Assessment CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CBC-MAC	Cipher Block Chaining - Message Authentication Code (AES mode of operation)
CFB Cipher Feedback (AES mode of operation) CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CC	Compare / Capture
CHF Channel Filter CLK Clock CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CCA	Clear Channel Assessment
CLK CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CFB	Cipher Feedback (AES mode of operation)
CM3 ARM Cortex-M3 CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CHF	Channel Filter
CM4 ARM Cortex-M4 CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CLK	Clock
CMD Command CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CM3	ARM Cortex-M3
CMU Clock Management Unit CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CM4	ARM Cortex-M4
CRC Cyclic Redundancy Check CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CMD	Command
CTR Counter mode (AES mode of operation) CTRL Control DBG Debug DC Direct Current DEC Decimator	CMU	Clock Management Unit
CTRLControlDBGDebugDCDirect CurrentDECDecimator	CRC	Cyclic Redundancy Check
DBG Debug DC Direct Current DEC Decimator	CTR	Counter mode (AES mode of operation)
DC Direct Current DEC Decimator	CTRL	Control
DEC Decimator	DBG	Debug
	DC	Direct Current
DEMOD Demodulator	DEC	Decimator
	DEMOD	Demodulator

DSA Detection of Signal Antival DSSS Direct Sequence Spread Spectrum ECB Electronic Code Book (AES mode of operation) EFR32 Wireless Gecko EM Energy Mode EMU Energy Mode EMU Energy Management Unit FEC Forward Error Correction FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Frequency Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HW Hardware Hz Hertz IF Interrupt Service Routine LERCO Low Frequency RC Oscillator LERCO Low Frequency RC Oscillator LINA Low Frequency RC Oscillator LINA Low Frequency Crystal Oscillator MOD Modulator MODEM Modulator MODEM Modulator MODEM	Abbreviation	Description
ECB Electronic Code Book (AES mode of operation) EFR32 Wireless Gecko EM Energy Mode EMU Energy Mode FEC Forward Error Correction FIR Finite impuise Response FRC Frame Controller FSK Frequency Shift Keying GPIO High Frequency Shift Keying HFRCO High Frequency Coscillator HV Hardware Hz Hertz IF Internut Service Routine LFRCO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Noise Amplifier	DSA	Detection of Signal Arrival
EFR32 Wireless Gecko EM Energy Mode EMU Energy Mode EMU Energy Management Unit FEC Forward Error Correction FIR Finite Impulse Response FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Frequency Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFKX High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFRA Low Noise Amplifer LO Local Oscillator MODE Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER	DSSS	Direct Sequence Spread Spectrum
EM Energy Mode EMU Energy Management Unit FEC Forward Error Correction FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency Crystal Oscillator HFXO High Frequency Crystal Oscillator HFX Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Requency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	ECB	Electronic Code Book (AES mode of operation)
EMU Energy Management Unit FEC Forward Error Correction FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Requency Crystal Oscillator LFXO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER	EFR32	Wireless Gecko
FEC Forward Error Correction FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency Coscillator HFKO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying ORPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Down PHY Physical Layer PROTIMER Protocol Timer	EM	Energy Mode
FIR Finite Impulse Response FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFRCO High Frequency RC Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LINA Low Noise Amplifier LO Load Oscillator MOD Modulator MODEM Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OGPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer PROTIMER	EMU	Energy Management Unit
FRC Frame Controller FSK Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator MOD Modulator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OGPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	FEC	Forward Error Correction
FSK Gaussian Frequency Shift Keying GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency Crystal Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	FIR	Finite Impulse Response
GFSK Gaussian Frequency Shift Keying GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency Crystal Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	FRC	Frame Controller
GMSK Gaussian Minimum Shift Keying GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	FSK	Frequency Shift Keying
GPIO General Purpose Input / Output HFRCO High Frequency RC Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency Crystal Oscillator LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	GFSK	Gaussian Frequency Shift Keying
HFRCO High Frequency RC Oscillator HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency Crystal Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Serguency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OGPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	GMSK	Gaussian Minimum Shift Keying
HFXO High Frequency Crystal Oscillator HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LFXO Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Down PHY Physical Layer PROTIMER Protocol Timer	GPIO	General Purpose Input / Output
HW Hardware Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Down PHY Physical Layer PROTIMER Protocol Timer	HFRCO	High Frequency RC Oscillator
Hz Hertz IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	HFXO	High Frequency Crystal Oscillator
IF Intermediate Frequency ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	HW	Hardware
ISR Interrupt Service Routine LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	Hz	Hertz
LFRCO Low Frequency RC Oscillator LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	IF	Intermediate Frequency
LFXO Low Frequency Crystal Oscillator LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	ISR	Interrupt Service Routine
LNA Low Noise Amplifier LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	LFRCO	Low Frequency RC Oscillator
LO Local Oscillator MOD Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	LFXO	Low Frequency Crystal Oscillator
MODEM Modulator MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	LNA	Low Noise Amplifier
MODEM Modulator and Demodulator MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	LO	Local Oscillator
MSK Minimum Shift Keying NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	MOD	Modulator
NRZ Non Return to Zero NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	MODEM	Modulator and Demodulator
NVIC Nested Vector Interrupt Controller OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	MSK	Minimum Shift Keying
OFB Output Feedback Mode (AES mode of operation) OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	NRZ	Non Return to Zero
OOK On Off Keying OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	NVIC	Nested Vector Interrupt Controller
OQPSK Offset Quadrature Phase Shift Keying OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	OFB	Output Feedback Mode (AES mode of operation)
OSR Over-Sampling Ratio PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	OOK	On Off Keying
PA Power Amplifier PD Power Down PHY Physical Layer PROTIMER Protocol Timer	OQPSK	Offset Quadrature Phase Shift Keying
PD Power Down PHY Physical Layer PROTIMER Protocol Timer	OSR	Over-Sampling Ratio
PHY Physical Layer PROTIMER Protocol Timer	PA	Power Amplifier
PROTIMER Protocol Timer	PD	Power Down
	PHY	Physical Layer
PRS Peripheral Reflex System	PROTIMER	Protocol Timer
	PRS	Peripheral Reflex System

Abbreviation	Description
PWM	Pulse Width Modulation
RAC	Radio Controller
RAM	Random Access Memory
RF	Radio Frequency
RMU	Reset Management Unit
RSM	Radio State Machine
RSSI	Received Signal Strength Indicator
RTC	Real Time Counter
RX	Receive
SEQ	Radio Sequencer
SPI	Serial Peripheral Interface
SRC	Sample Rate Converter
STIMER	Sequencer Timer
SW	Software
SYNTH	Synthesizer
TX	Transmit
WOR	Wake On Radio
XTAL	Crystal





IoT Portfolio www.silabs.com/IoT



SW/HW www.silabs.com/simplicity



Quality www.silabs.com/quality



Support & Community www.silabs.com/community

Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs may update product firmware during the manufacturing process for security or reliability reasons. Such changes will not alter the specifications or the performance of the product. Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons. Silicon Labs products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such unauthorized applications. Note: This content may contain offensive terminology that is now obsolete. Silicon Labs is replacing these term

Trademark Information

Silicon Laboratories Inc.®, Silicon Laboratories®, Silicon Labs®, SiLabs® and the Silicon Labs logo®, Bluegiga®, Bluegiga Logo®, EFM®, EFM32®, EFR, Ember®, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Redpine Signals®, WiSeConnect, n-Link, ThreadArch®, EZLink®, EZRadio®, EZRadio®, Cecko®, Gecko®, Gecko OS, Gecko OS Studio, Precision32®, Simplicity Studio®, Telegesis, the Telegesis Logo®, USBXpress®, Zentri, the Zentri logo and Zentri DMS, Z-Wave®, and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc. 400 West Cesar Chavez Austin, TX 78701 USA