


AN0016.2: Oscillator Design Considerations

This application note provides an introduction to the oscillators in EFM32 and EFR32 Wireless Gecko Series 2 devices and provides guidelines in selecting correct components for their oscillator circuits.

The EFM32 and EFR32 Wireless Gecko Series 2 devices contain two crystal oscillators: one low frequency (32.768 kHz) and one high frequency (38.4 / 39 MHz). Topics covered include oscillator theory and some recommended crystals for these devices.

KEY POINTS

- Learn which parameters are important when selecting an oscillator.
- Learn how to properly configure a crystal oscillator for use with EFM32 and EFR32 Wireless Gecko Series 2 devices.



1. Device Compatibility

This application note supports multiple device families, and some functionality is different depending on the device.

EFR32 Wireless Gecko Series 2 consists of:

- EFR32BG21
- EFR32MG21
- EFR32BG22
- EFR32BG22L
- EFR32FG22
- EFR32MG22
- EFR32FG23
- EFR32ZG23
- EFR32SG23
- EFR32BG24
- EFR32BG24L
- EFR32MG24
- EFR32FG25
- EFR32MG26
- EFR32BG26
- EFR32BG27
- EFR32MG27
- EFR32FG28
- EFR32ZG28
- EFR32SG28
- EFR32BG29

EFM32 Series 2 consists of:

- EFM32PG22
- EFM32PG23
- EFM32PG26
- EFM32PG28

2. Oscillator Theory

2.1 What is an Oscillator?

An oscillator is an electronic circuit which generates a repetitive, or periodic, time-varying signal. In the context of EFM32 and EFR32 Wireless Gecko Series 2 devices, this oscillator signal is used to clock execution of instructions and peripherals in the device. For radio communication the oscillator also provides an accurate and low noise frequency reference to the transceiver. There are multiple ways of generating such a signal, each with different properties that influence project cost, board size, and stability of the clock signal.

RC oscillators

RC oscillators are built from resistors, capacitors, and an inverting amplifier. They come at a low cost and have a shorter startup time than the crystal oscillator, but are generally less accurate and produce more noise. The EFM32 and EFR32 Wireless Gecko Series 2 devices provide multiple internal RC oscillators including one High Frequency RC Oscillator (HFRCO) and one Low Frequency RC Oscillator (LFRCO). While the internal RC oscillators will ensure proper operation of the EFM32 and EFR32 Wireless Gecko Series 2 device, they are inadequate for applications such as radio communication.

Crystal oscillators

Crystal oscillators use the mechanical vibration of a crystal to generate the clock signal. Due to the molecular composition of the crystal matter and the angle of which the crystal is cut, this type of oscillator is very precise and stable over a wide temperature range. The most commonly used crystal is the quartz crystal. Producing quartz crystals requires very stable temperature and pressure conditions over a few weeks. This makes crystal oscillators more expensive than RC oscillators.

2.1.1 Piezoelectricity

Quartz crystals hold the direct piezoelectric property. This means an applied electric field will cause the crystal to deform. Conversely, a deformation of the crystal will cause a voltage across the terminals. Once the oscillator has started, the changing voltage on the terminals of the vibrating crystal is used as the clock signal.

2.2 Basic Principle of Oscillators




Figure 2.1. Simplified Feedback Oscillator Loop

The principle behind the oscillator is a positive feedback loop satisfying the Barkhausen condition: If the closed-loop gain is larger than unity and the total phase lag is 360° , the resulting closed-loop system is unstable and will self-reinforce. This is a necessary, but not sufficient, condition for oscillations to be present. When the necessary conditions are met, any disturbance (noise) in the oscillator will cause oscillations to start. The frequency that fulfills the Barkhausen condition is amplified the most, because it is in phase with the original signal.

The initial oscillations are very weak, and it takes time to amplify the signal to the desired magnitude. When oscillations are established, only a small amount of energy is needed to compensate for losses in the circuit. Mathematically, a closed-loop gain of one is required to maintain steady state oscillations. The EFM32 and EFR32 Wireless Gecko Series 2 relies on an adjustable current source controlled by automatic gain controller to achieve and maintain the desired amplitude.

Figure 2.1 Simplified Feedback Oscillator Loop on page 4 shows that the oscillator circuitry consists of two parts: an amplification stage and a filter that decides which frequency experiences a 360° phase lag. In the case of a crystal oscillator, the filter consists of the crystal and external load capacitors.

2.2.1 Startup time

The magnitude of the closed-loop gain has great influence on the startup time. Low gain can cause excessively long startup time or failure, and too high gain can startup to fail altogether. The ideal gain is dependent on the negative resistance of the oscillator circuit, which is defined in [Negative Resistance](#).

For the same reason, the oscillation frequency influences the startup time. A crystal in the kHz range would have a considerably longer startup time than a crystal in the MHz range because the time it takes to circulate the loop is longer. Typical startup times for the EFM32 and EFR32 Wireless Gecko Series 2 are 63 ms for the low frequency oscillator and 159 μ s for the high frequency oscillator.

2.3 Modeling the Crystal

The crystal can be described by the electrical equivalent circuit in [Figure 2.2 The Electrical Equivalent Circuit of a Crystal on page 5](#).




Figure 2.2. The Electrical Equivalent Circuit of a Crystal

- C_S is the motional capacitance. It represents the piezoelectric charge gained from a displacement in the crystal.
- R_S is the motional resistance. It represents the mechanical losses in the crystal.
- L_S is the motional inductance. It represents the moving mass in the crystal.
- C_0 is the shunt capacitance between the electrodes and stray capacitance from the casing.

For low frequencies, the electrical equivalent circuit will exhibit capacitive behavior as depicted in [Figure 2.3 Reactance vs. Frequency on page 5](#). The presence of the inductor becomes more noticeable as the frequency, and thus the reactance, increases. Ignoring the shunt capacitance C_0 , the series resonant frequency is defined where the reactance of the inductor and capacitor cancels. At this frequency the crystal appears only resistive with no shift in phase. The series resonance frequency, f_S , therefore determines the relationship between C_S and L_S . This can be calculated with the equation below. The series resonance frequency is the natural resonance frequency where the energy transformation between mechanical and electrical energy is most effective.




Figure 2.3. Reactance vs. Frequency

$$f_S = \frac{1}{\left(2 \times \pi \times \left(L_S \times C_S\right)^{\frac{1}{2}}\right)}$$

At higher frequencies, the equivalent circuit will appear inductive, which implies higher impedance. When the inductive reactance from the crystal cancels the capacitive reactance from shunt capacitance C_0 , another resonance frequency with zero phase shift exists. This frequency is called the anti-resonant frequency, f_A . At this frequency, the impedance is 0.

$$f_A = \frac{1}{2 \times \pi \times \left(L_S \times \frac{C_S \times C_0}{C_S + C_0} \right)^{\frac{1}{2}}}$$

The range of frequencies between f_S and f_A is called the area of parallel resonance and is where the crystal will normally oscillate. At the resonant frequency, the phase lag in the feedback loop is provided by an amplifier with 180° phase lag and two capacitors with a combined 180° phase lag. In practice, the amplifier provides a little more than 180° phase shift, which means the crystal must appear slightly inductive to fulfill the Barkhausen criterion.

2.3.1 Series and Parallel Resonant Crystals

Physically there is no difference between series and parallel resonant crystals. Series resonant crystals are specified to oscillate at the series resonant frequency where the crystal appears with no reactance. Because of this, no external capacitance should be present as this would lower the oscillating frequency to below the natural resonance frequency. These crystals are intended for use in circuits with no external capacitors where the oscillator circuit provides 360° phase shift.

Parallel resonant crystals require a capacitive load to oscillate at the specified frequency and this is the resonance mode required for EFM32 and EFR32 Wireless Gecko Series 2 devices. On EFM32 and EFR32 Wireless Gecko Series 2 devices, the load capacitors are located on-chip, and their values can be controlled by firmware. Thus, EFM32 and EFR32 Wireless Gecko Series 2 devices do not require external load capacitors, reducing BOM cost and saving PCB space. The exact oscillation frequency for a parallel resonant crystal can be calculated with the equation below, where C_L is the load capacitance seen by the crystal. C_L is therefore an important design parameter and is given in the data sheet for parallel resonant crystals.

$$f_P = f_S \left(1 + \frac{C_S}{2 \times C_L} \right)$$

3. EFM32 and EFR32 Wireless Gecko Series 2 Crystal Oscillators

EFM32 and EFR32 Wireless Gecko Series 2 devices include two crystal oscillators, the Low Frequency Crystal Oscillator (LFXO) and the High Frequency Crystal Oscillator (HFXO). These oscillators require a crystal connected to the specific oscillator's pins on the device. However, no external crystal load capacitors are required because each oscillator has on-chip tunable load capacitors. The LFXO supports crystals with a nominal frequency of 32.768 kHz, while the HFXO supports crystals in the range of 38 to 40 MHz depending on the specific device and radio protocol requirements. External oscillators are also supported. Both the high and low frequency clock sources can be used simultaneously.

Both the LFXO and HFXO on EFM32 and EFR32 Wireless Gecko Series 2 devices implement a Pierce oscillator as shown in [Figure 3.1 The Pierce Oscillator in the EFM32 and EFR32 Wireless Gecko Series 2 on page 7](#).




Figure 3.1. The Pierce Oscillator in the EFM32 and EFR32 Wireless Gecko Series 2

The Pierce oscillator is known to be stable for a wide range of frequencies and for its low power consumption.

The EFM32 and EFR32 Wireless Gecko Series 2 crystal oscillators use a relatively low oscillation amplitude, which can lead to a lower oscillation frequency than stated as the nominal value in the crystal's data sheet. More information on this effect is given in [6.4 Frequency Pulling](#).

3.1 Timeout

To ensure that the XO clock signals are not used internally in the EFM32 and EFR32 Wireless Gecko Series 2 before they are stable, both the HFXO and the LFXO include a configurable timeout. When the XO starts up, the timeout counter will count to the configured number of cycles before the clock signal propagates to the internal clock trees and the digital logic.

3.2 Software Configuration

The LFXO/HFXO can be easily configured by leveraging the `em_lib` library. The library contains oscillator initialization structures and functions which abstract the software options available for each oscillator. The included [7. Software Examples](#) showcase using the library to initialize the oscillators.

At the register level, the HFXO and LFXO oscillation start-up are controlled by the `HFXO_XTALCTRL`, `HFXO_XTALCFG`, `LFXO_CFG` registers. See the reference manual for detailed register level descriptions of the configuration options available for the external oscillators.

Starting up the HFXO in crystal mode

When configuring the HFXO for proper crystal startup, most fields such as the bias currents and timeout durations should adhere to the `em_lib` defaults (`CMU_HFXOINIT_DEFAULT` in `em_cmu.h`). The tuning capacitor values should be customized by setting the `ctuneXoAna` and `ctuneXiAna` fields of the HFXO initialization struct. The tuning capacitor values can be determined via the following methods.

- For parts on a starter or development kit, the calibrated tuning values can be read from the `DEVINFO_MODXOCAL` register the Device information page (see [7. Software Examples](#) for details).
- For oscillators on our [Recommended Oscillators](#) list, use the `emlib` defaults.
- For other oscillators, the setting should be determined based on the oscillator load capacitance, and the tuning capacitor range and step size values from the EFM32 and EFR32 Wireless Gecko Series 2 device data sheet.

For any of these methods, the tuning values should be trimmed or calibrated for optimal accuracy. See the [Tuning Strategies](#) section for details.

Starting up the LFXO in crystal mode

When configuring the LFXO for proper crystal startup, the gain and tuning values may need to be modified from the `em_lib` defaults (`CMU_LFXOINIT_DEFAULT` in `em_cmu.h`). These correspond to the `ctune` and `gain` fields of the `em_lib` LFXO initialization struct. The tuning values can be determined via the following methods

- For parts on a starter or development kit, the calibrated tuning values can be read from the `DEVINFO_MODXOCAL` register the Device information page (see [7. Software Examples](#) for details).
- For other oscillators, the setting should be determined based on the oscillator load capacitance, and the tuning capacitor range and step size values from the EFM32 and EFR32 Wireless Gecko Series 2 device data sheet.

The gain value should be set according to the load capacitance of the crystal.

- For $12.5 \text{ pF} \leq CL \leq 18 \text{ pF}$, set `GAIN` = 3
- For $10 \text{ pF} \leq CL \leq 12.5 \text{ pF}$, set `GAIN` = 2
- For $6 \text{ pF} \leq CL \leq 10 \text{ pF}$, set `GAIN` = 1
- For $4 \text{ pF} \leq CL \leq 6 \text{ pF}$, set `GAIN` = 0

3.3 PCB Layout

To minimize noise sensitivity caused by parasitic antenna and spurious coupling phenomena, the distance between the crystal, and the EFM32 and EFR32 Wireless Gecko Series 2 oscillator pins should be as short as possible. If it is not possible to place the external oscillator components close to the oscillator pins, care should be taken when routing these signals. Avoid long traces underneath the EFM32 and EFR32 Wireless Gecko Series 2 package and other circuitry that could create spurious coupling with logic activity. Also avoid routing any other signals through the crystal area.

Ensure that the ground plane underneath the oscillator is of good quality. Do not use a separate ground plane under the oscillator with a narrow connection to the reference ground as this can act as an antenna. To avoid coupling from surrounding signal traces, it is a good practice to place a grounded guard ring around the oscillator and its components.

4. Considerations for Applications with the EFM32 and EFR32 Wireless Gecko Series 2 Portfolio

4.1 General Notes for Radio Applications

This section adds a few details about specific requirements related to wireless applications.

Crystal frequency selection is dependent on both the specific EFR32 Wireless Gecko Series 2 device and its radio protocol requirements. Most devices support only a single crystal frequency, such as 38.4 MHz for EFR32xG21 or 39 MHz for EFR32x23. While some devices may allow a second crystal frequency option if permitted by the specific radio protocol implementation, a given device's transceiver electrical specifications are based on its datasheet-specified crystal frequency.

The crystal frequency tolerance is determined by various aspects of the design:

Required frequency tolerance of the protocol

For example, 802.15.4 applications require ± 40 ppm accuracy under all conditions.

Temperature range

The S-shaped temperature characteristic of AT-cut crystals becomes steeply negative at low temperatures, steeply positive at high temperatures. A larger temperature range requires a specific cut angle of the crystal to bound the absolute accuracy. Most crystals are specified from -40 °C to $+85$ °C, but some applications may require operation up to 105 °C or 125 °C ambient temperature.

Manufacturing accuracy

Individual crystals have a frequency error at 25 °C. This is typically specified as ± 10 ppm "manufacturing tolerance" or "make tolerance". This error adds to the temperature error.

Aging tolerance

Crystals drift over time, typically 1-2 ppm per year. Excessive heat during assembly or from hand soldering may also prematurely age a crystal.

The allowable frequency error of the crystal is the sum of temperature, board-to-board, and crystal-to-crystal variations.

4.2 Crystal Loading and Production Tuning

The load capacitance, C_L , is implemented on-chip by two tunable capacitors. External capacitors are neither required nor recommended.

The load capacitor tuning range in pF is given in the data sheet by C_{HFXO_T} with a resolution of SS_{HFXO} per step. The resulting frequency per step depends on the crystal's pulling sensitivity and the shunt capacitance of the oscillator circuit.

4.2.1 Tuning Strategies

The on-chip variable load capacitor may be used in one of two ways.

- A fixed value may be used for all units. During design, a number of units should be characterized and an average center CTUNE value determined. Some crystal vendors may provide characterized samples to help tune to the center of the crystal distribution. In corner cases the remaining error should be in the order of a few ppm only, depending on manufacturing spread (PCB parasitics, component variation, etc.).
- Each unit may also be calibrated in production. A unique value of CTUNE is determined per unit and stored in flash memory. This calibrates out the manufacturing error of the crystal, leaving only the temperature error and aging components. This may allow the system to operate across a broader temperature range or with a less accurate crystal at the expense of production calibration time.

The variable on-chip loading capacitor can theoretically be used to offset temperature-induced errors as well. While simple in concept, this is difficult in practice primarily due to temperature characteristic differences from crystal to crystal.

Crystal ppm error can be measured by outputting a clock signal to a GPIO pin. This process, along with example code demonstrating oscillator calibration, is described in [AN0004.2: EFR32 Series 2 Wireless MCU Clock Management Unit \(CMU\)](#).

4.3 External Tuning Capacitance

All required crystal loading capacitance is on-chip; therefore, external loading capacitors are not recommended.

4.4 External Oscillator Operation

For narrowband applications the system reference frequency may be provided by an external oscillator such as a Temperature Compensated Crystal Oscillator (TCXO). To use a TCXO, the output should be connected to the HFXTAL_I pin and the CMU_HFXOINIT_EXTERNAL_SINE struct definitions should be used for HFXO initialization in software using the `em_cmu` library.

Sine and clipped sine waveforms are supported by the HFXO in this mode. The external waveform should adhere to the following limitations for ideal performance.

Parameter	Min (V)	Max (V)
Input Voltage	0.0	1.2
Peak-to-Peak Amplitude	0.55	1.2

The input signal can be directly connected to the HFXTAL_I pin (DC coupled) or connected through a series capacitor (AC coupled). The series capacitor can be used to limit current into the device and keep the input voltage within the recommended range. Lower capacitance results in higher impedance. A typical value for the series capacitor is 100 pF, although testing should be done to make sure the input voltage is within the recommended range.

When using an AC coupled input, the bit HFXO_CFG.ENXIDCBIASANA must be set. This will enable an internal DC bias of 350 mV. This bit does not need to be set with a DC coupled input, but it will not cause any problems if it is. The advantage of AC coupling is that the DC bias is fixed, and the amplitude can be managed with the series capacitor. The input capacitance at the HFXTAL_I pin with CTUNEXIANA = 0 and CTUNEFIXANA = 0 is about 10 pF.

See [Recommended Oscillators](#) for a list of recommended TCXOs.

4.5 Reducing Power Consumption

The power consumption of the crystal oscillator is mostly determined by the drive level of the oscillator. This equals the power dissipated in the crystal as given in the equation below.

$$DL = \frac{1}{2} \times ESR \times (2 \times \pi \times f \times V_{pp} \times (C_0 + C_L))^2$$

V_{pp} is the peak to peak voltage across the crystal at the resonance frequency. In EFM32 and EFR32 Wireless Gecko Series 2 devices the target V_{pp} varies, but for a safe estimate to check the maximum drive level for a given crystal, calculate the above formula with a 500mV V_{pp} value.

During startup the current consumption is higher than after oscillations have stabilized. A short startup time reduces the period in which the current consumption of the oscillator is high and is therefore essential if the oscillator is frequently switched on and off. In general, one would like the circuit to be operational as fast as possible and a fast startup time is therefore favorable. Crystals with low ESR and load capacitance typically have the shortest startup time and consume the least amount of power.

On EFM32 and EFR32 Wireless Gecko Series 2 devices, the oscillators can be configured to be "on-demand". This means that the oscillator will be automatically enabled as requested by the clock management unit and then automatically disabled when not in use. This can help save power at the cost of incurring repeated startup delays whenever the oscillator is needed. Alternatively, the oscillator can be enabled in software and forced to stay on, consuming extra current in exchange for no recurring startup delays. This option is showcased in the included [Software Examples](#).

5. Recommended Crystals

5.1 General Notes for Crystal Selection

When deciding upon which crystal to employ, the following considerations could be helpful to ensure a proper functioning oscillator.

Operating environment

Temperature, humidity, and mechanical vibration affect the stability properties. For crystals, define what crystal cut is most appropriate for the application. For most applications, AT cut is an excellent choice due to good temperature stability over a wide temperature range. SC cut has good stability when exposed to mechanical vibrations, but suffers from humidity and temperature changes. Many more cuts with different properties exist.

Package

Surface mount or through-hole. If size is critical, define maximum package dimensions.

Match load capacitors

Ensure that C_L is within range specified by the EFM32 and EFR32 Wireless Gecko Series 2 data sheet. Generally lower load capacitance crystals have better startup and current consumption performance, see [4.5 Reducing Power Consumption](#) for details.

Match ESR

Ensure that ESR is within range specified by the EFM32 and EFR32 Wireless Gecko Series 2 data sheet. Generally lower ESR crystals have better startup and current consumption performance, see [4.5 Reducing Power Consumption](#) for details.

The recommended crystals are chosen from a selection of popular crystals with different ESR, cost, frequency stability, and tolerance. By examining the list of considerations above, one should be able to find a suitable crystal.

All the recommended crystals are fundamental mode, as is required for EFM32 and EFR32 Wireless Gecko Series 2.

5.2 Crystal Specifications for EFM32 and EFR32 Wireless Gecko Series 2 Devices

The following crystals have been tested for use with EFM32 and EFR32 Wireless Gecko Series 2 devices. Suitability for a particular application should be verified. Different frequency tolerance / temperature ranges may be available. Contact the crystal vendor for details.

Note: The following component recommendations do not apply to EFR32ZG23 and EFR32ZG28 devices. Instead, refer to [UG522: Mandatory Crystal Adjustment for EFR32ZG14/EFR32ZG23 Based Products](#) for component recommendations. [UG517: Z-Wave 800 Series Integration Guide](#) discusses this and other aspects of EFR32ZG23 and EFR32ZG28 product integration.

Table 5.1. 38 MHz Crystals

Mfg	Part	ESR (Ω)	Max C_0 (pF)	Temp ($^{\circ}\text{C}$)	Temp Tolerance (ppm)	Mfg Tolerance (ppm)	C_L (pF)	Footprint (mm)
TXC	8Y38072001	50	2	-40 to +125	± 40	± 8	10	1.6 x 2.0

Table 5.2. 38.4 MHz Crystals

Mfg	Part	ESR (Ω)	Max C_0 (pF)	Temp ($^{\circ}\text{C}$)	Temp Tolerance (ppm)	Mfg Tolerance (ppm)	C_L (pF)	Footprint (mm)
Tai-Saw	TZ2205E	40	3	-40 to +125	± 30	± 10	10	1.6 x 2.0
Tai-Saw	TZ3398B	40	3	-40 to +105	± 20	± 10	10	1.65 x 2.05
TXC	8Y38472016	50	2	-40 to +125	± 40	± 8	10	1.6 x 2.0

Table 5.3. 38.4 MHz TCXOs

Mfg	Part	Supply Voltage (V)	Output Voltage (V_{pk-pk})	Temp ($^{\circ}\text{C}$)	Current Consumption (mA)	Frequency Tolerance (ppm)	Footprint (mm)
NDK	NT2016SA-NSC5318C	1.8 to 3.6	0.8	-30 to +85	2	± 2	1.6 x 2.0

Table 5.4. 39 MHz Crystals

Mfg	Part	ESR (Ω)	Max C_0 (pF)	Temp ($^{\circ}\text{C}$)	Temp Tolerance (ppm)	Mfg Tolerance (ppm)	C_L (pF)	Footprint (mm)
NDK	NX2520SA-EXS00A-CS13074	40	1.28	-40 to +125	± 32	± 10	10	2.0 x 2.5
Siward	XTL501350-S315-027	40	3	-40 to +125	± 35	± 8	10	1.6 x 2.0
Siward	XTL501250-S315-038	40	3	-40 to +110	± 25	± 10	10	1.6 x 2.0
Tai-Saw	TZ3541C	35	2	-40 to +125	± 30	± 8	10	1.6 x 2.0
Tai-saw	TZ3541B	35	1	-40 to +110	± 16	± 7	10	1.6 x 2.0
TXC	8Y39072002	35	1	-40 to +95	± 13	± 8	10	1.6 x 2.0
TXC	8Y39072003	50	2	-40 to +125	± 40	± 8	10	1.6 x 2.0
TXC	8Y39072005	35	1	-40 to +125	-33/+35	-5/+7	10	1.6 x 2.0

Table 5.5. 40 MHz Crystals

Mfg	Part	ESR (Ω)	Max C_0 (pF)	Temp ($^{\circ}\text{C}$)	Temp Tolerance (ppm)	Mfg Tolerance (ppm)	C_L (pF)	Footprint (mm)
Kyocera	CX2016DB40000D0FLJCC	50	—	-30 to +85	± 15	± 10	8	1.6 x 2.0
TXC	8Y40072014	50	2	-40 to +125	± 40	± 8	10	1.6 x 2.0

Table 5.6. 32768 Hz Crystals

Mfg	Part	Ordering Specification	ESR (k Ω)	Typ C_0 (pF)	Temp ($^{\circ}\text{C}$)	Tolerance (ppm)	C_L (pF)	Footprint (mm)
KDS	DST1610A	1TJH070DN1A0153	70	1.3	-40 to +85	20	7.0	1.6 x 1.0
KDS	DST210AC	1TJG070DN1AC001	70	1.3	-40 to +85	20	7.0	1.2 x 2.0
Abracon	ABS07	32.768KHZ-7	70	1.5	-40 to +85	20	7.0	1.5 x 3.2
Micro Crystal	CM8V-T1A	32.768KHZ-12.5-20P PM-TB-QA	55	1.1	-40 to +125	20	12.5	1.2 x 2.0
Micro Crystal	MS3V-T1R	32.768KHZ-12.5-20P PM-TA-QC	65	0.9	-40 to +85	20	12.5	Tuning Fork

6. Crystal Parameters

6.1 Quality Factor

The quality factor Q is a measure of the efficiency or the relative storage of energy to dissipation of energy in the crystal. For the electrical-equivalent circuit, the equation below states the relation between R, C and Q. In practice, crystals with higher Q-values are more accurate, but have a smaller bandwidth for which they oscillate. Therefore, high Q-factor crystals will start slower than crystals with higher frequency tolerance.

$$Q = \frac{X_{LS}}{R_S} = \frac{1}{(X_{LS} \times R_S)} = \frac{1}{(2 \times \pi \times f \times C_S \times R_S)} = \frac{2 \times \pi \times f \times L_S}{R_S}$$

X_{LS} and X_{CS} are the reactance of L_S and C_S , respectively, at the operating frequency of the crystal.

6.2 Load Capacitance

As seen in the equation below, the two capacitors C_{L1} and C_{L2} provide capacitive load for the crystal. The effective load capacitance, C_L , as seen from the HFX TAL_I and HFX TAL_O pins on the EFM32 and EFR32 Wireless Gecko Series 2 is the series combination of C_{L1} and C_{L2} through ground.

$$C_L = \frac{(C_{L1} \times C_{L2})}{(C_{L1} + C_{L2})} + C_{\text{stray}}$$

Where C_{stray} is the pin capacitance of the microcontroller and any parasitic capacitance, and can often be assumed in the range 2-5 pF. Right choice of C_L is important for proper operating frequency. Crystals with small load capacitance would typically start faster than crystals requiring a large C_L . Large load capacitors also increase power consumption. It is recommended to use a crystal with C_L as specified in [5. Recommended Crystals](#). The EFM32 and EFR32 Wireless Gecko Series 2 device data sheets also contain more information on the allowed load capacitance range.

Note: The EFM32 and EFR32 Wireless Gecko Series 2 devices have internal loading capacitors and do not need external capacitors connected to the crystal. See the device data sheet or reference manual for more information.

6.3 Equivalent Series Resistance

The Equivalent Series Resistance is the resistance in the crystal during oscillation and varies with the resonance frequency. ESR, given by the equation below, will typically decrease with increasing oscillation frequency.

$$ESR = R_S \left(1 + \frac{C_0}{C_L} \right)^2$$

The HFXO/LFXO circuits of the EFM32 and EFR32 Wireless Gecko Series 2 cannot guarantee startup of crystals with ESR larger than a certain limit. Please refer to the device data sheet for further details. The smaller the ESR, compared to this maximum value, the better gain margin for startup of the crystal which in turn reduces the startup time. Additionally, a small ESR value gives lower power consumption during oscillation.

Note that HF crystals have ESR of a few tens of Ohms as compared to the LF crystals, which have ESR values normally measured in kΩ. Therefore, a few Ohms of series resistance has more influence on the startup margin in the MHz range as compared to the kHz range.

6.4 Frequency Pulling

The EFM32 and EFR32 Wireless Gecko Series 2 devices use a relatively low oscillation amplitude with crystal oscillators. Because of this, the oscillation frequency can be lower than the nominal frequency stated in the crystal data sheet when using the suggested load capacitance. This offset is best found by measuring the resulting frequency when using the suggested load capacitance. The offset will be stable and not affected by temperature, voltage or aging. If it is desirable to achieve the nominal frequency given for the crystal, there are two options:

- Option A — Order a crystal from the crystal vendor that has a nominal frequency equal to the frequency you want to achieve plus the measured offset frequency.
- Option B — It is possible to slightly alter the oscillation frequency of a crystal by adjusting the load capacitance (C_{L1} and C_{L2}). The pullability of the oscillation system refers to which extent it is possible to tune the resonance frequency of the crystal by changing these values. The crystal sees these capacitors in series through ground, parallel to the closed loop. They will therefore slightly alter the anti-resonance frequency of the crystal. The equation below shows the pullability in terms of frequency change in ppm per change in combined load capacitance in pF.

$$\text{Average pullability (ppm/pF)} = \frac{C_S \times 10^6}{2 \times (C_0 + C_L)^2}$$

6.5 Drive Level

Drive level is a measure of the power dissipated in the crystal. The crystal manufacturer should specify the maximum power dissipation value tolerated by the crystal in the crystal data sheet. Exceeding this value can damage the crystal.

$$DL = ESR \times I^2$$

Here, I is the RMS current flowing through the crystal.

6.6 Minimum Negative Resistance

A critical condition for oscillations to build up requires the energy supplied to exceed the energy dissipated in the circuit. In other words, the negative resistance of the amplifier has to exceed the equivalent series resistance in the crystal. An approximate formula for negative resistance is given in the equation below.

$$R_{\text{neg}} = \frac{-g_m}{((2 \times \pi \times f)^2 \times C_{L1} \times C_{L2})}$$

Where g_m is the transconductance of the oscillator circuitry. To ensure safe operation over all voltage and temperature variations, ensure that the ESR does not exceed the device data sheet maximum. This maximum value corresponds to the oscillator circuit's realizable negative resistance.

If the crystal ESR does not satisfy this criterion, another crystal with lower ESR should be chosen. The equation above shows an approximate formula for this calculation which excludes shunt capacitance and internal loss.

6.7 Frequency Stability

Frequency stability is the maximum frequency deviation from the specified oscillating frequency over the given operating temperature range.

6.8 Frequency Tolerance

Frequency tolerance is the maximum frequency deviation from the specified oscillating frequency at 25 °C. This parameter gives an indication of variations between individual crystals.

7. Software Examples

The software example project and source code is available through the Silicon Labs technical resource search: <https://www.silabs.com/support/resources.ct-example-code?query=an0016%202>. The software example is run on the EFR32xG21 Radio Board and Wireless Starter Kit, but is easily ported to other EFM32 and EFR32 Wireless Gecko Series 2 devices on custom boards.

8. Revision History

Revision 2.6

August, 2025

- Added EFR32BG22L and EFR32BG24L to [1. Device Compatibility](#).
- Minor formatting updates.

Revision 2.51

February, 2025

- Added EFR32BG29 to [1. Device Compatibility](#).

Revision 2.5

February, 2025

- Added EFR32BG26 and EFM32PG26 to [1. Device Compatibility](#).
- Removed NT2016SA-38.4MHz-END5109A from [Table 5.3 38.4 MHz TCXOs on page 12](#).
- Added NT2016SA-NSC5318C to [Table 5.3 38.4 MHz TCXOs on page 12](#).

Revision 2.4

February, 2024

- Added EFR32MG26 to [1. Device Compatibility](#).
- Removed XRCGB38M400F1S2AR0 from [Table 5.2 38.4 MHz Crystals on page 12](#).
- Removed NX2520SA-EXS00A-CS08361 from [Table 5.2 38.4 MHz Crystals on page 12](#).
- Added CX2016DB40000D0FLJCC to [Table 5.5 40 MHz Crystals on page 13](#).

Revision 2.3

October, 2023

- Added EFR32SG23 and EFR32SG28 to [1. Device Compatibility](#).
- Added information about input requirements for DC coupled and AC coupled TCXO connections to [4.4 External Oscillator Operation](#).
- Clarified description of [6.4 Frequency Pulling](#).

Revision 2.2

April, 2023

- Added EFM32PG28, EFR32FG28, and EFR32ZG28 device to [1. Device Compatibility](#).
- References to specific devices and crystal frequencies removed from [3. EFM32 and EFR32 Wireless Gecko Series 2 Crystal Oscillators](#).
- Simplified introductory text in [4.1 General Notes for Radio Applications](#).
- Added NX2520SA-EXS00A-CS13074 to [Table 5.4 39 MHz Crystals on page 12](#).

Revision 2.1

April, 2023

- Added EFR32BG27 and EFR32MG27 device to [1. Device Compatibility](#).

Revision 2.0

February, 2023

- Added EFR32FG25 device to [1. Device Compatibility](#).
- Added TXC 8Y39072003 and 8Y39072005 to [Table 5.4 39 MHz Crystals on page 12](#).
- Removed table notes from [5.2 Crystal Specifications for EFM32 and EFR32 Wireless Gecko Series 2 Devices](#).
- Removed 39 MHz TCXO table from [5.2 Crystal Specifications for EFM32 and EFR32 Wireless Gecko Series 2 Devices](#).

Revision 1.9

October, 2022

- [5.2 Crystal Specifications for EFM32 and EFR32 Wireless Gecko Series 2 Devices](#) updated to note that component recommendations do not apply to Z-Wave devices and that users are instead referred to [UG522: Mandatory Crystal Adjustment for EFR32ZG14/EFM32ZG23 Based Products](#) for this information.

Revision 1.8

July, 2022

- Updated LFXO startup load capacitance ranges for GAIN settings in [3.2 Software Configuration](#).
- Modified minimum peak-to-peak voltage for external oscillator driving HFXTAL_I in [4.4 External Oscillator Operation](#).

Revision 1.7

May, 2022

- Added EFM32PG23 device to [1. Device Compatibility](#).

Revision 1.6

April, 2022

- Added EFR32FG22 and EFM32PG22 devices to [1. Device Compatibility](#).
- Modified product family references throughout document to incorporate EFM32 Series 2 MCUs.
- Added TXC 8Y38072001 for 38 MHz, TXC 8Y38472016 for 38.4 MHz and TXC 8Y40072014 for 40 MHz in the [recommended crystals list](#).

Revision 1.5

March, 2022

- Added EFR32xG24 devices to [1. Device Compatibility](#).
- Added support for 39 MHz crystals in EFR32xG24 devices.
- Added the Tai-saw TZ3541B and Siward XTL501250-S315-038 to [Table 5.4 39 MHz Crystals on page 12](#).
- Added notes to [Table 5.4 39 MHz Crystals on page 12](#) and [Table 5.6 32768 Hz Crystals on page 13](#) to highlight device-crystal compatibility.

Revision 1.4

December, 2021

- Updated device compatibility list, removing nonexistent EFR32xG23 devices and adding EFR32ZG23.
- Corrected the minimum and maximum peak-to-peak amplitude values in [4.4 External Oscillator Operation](#). The previously specified values were peak amplitudes (center to minimum/maximum, not trough to peak).

Revision 1.3

August, 2020

- Added EFR32xG23 devices to [1. Device Compatibility](#).
- Added support for 39 MHz crystals in EFR32xG23 devices.
- Added initial 39 MHz crystals and TCXOs to the recommended crystals list.
- Added the Abracon ABS07 and Micro Crystal CM8V-T1A to the recommended crystals list.

Revision 1.2

July, 2020

- Added the Murata XRCGB-F-S HFXO to the recommended crystals list.
- Updated diagram for Figure 3.1, corrected pin names.

Revision 1.1

June, 2020

- Updated supported frequencies for radio operation in [4.1 General Notes for Radio Applications](#).
- Updated External Sine Operation section to provide recommendations for input waveforms.
- Added recommended TCXO list.

Revision 1.0

March, 2020

- Added device compatibility for EFR32BG22 and EFR32MG22.
- Added DST1610A and DST210AC specifications to the [Recommended Crystals](#) section.
- Added drive level calculation and additional information to the [Recommended Crystals](#) section.

Revision 0.3

July, 2019

- Added TZ3398B, fixed NX2520SA specifications, and removed the unpopulated Crystal Configuration table from the [Recommended Crystals](#) section.
- Removed references to crystal configuration table in the [Software Configuration](#) section.
- Corrected minor wording and grammar issues.

Revision 0.2

May, 2019

- Added oscillator recommendations.

Revision 0.1

April, 2019

- Initial revision.

Simplicity Studio

One-click access to MCU and wireless tools, documentation, software, source code libraries & more. Available for Windows, Mac and Linux!



IoT Portfolio
www.silabs.com/iot



SW/HW
www.silabs.com/simplicity



Quality
www.silabs.com/quality



Support & Community
www.silabs.com/community

Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs may update product firmware during the manufacturing process for security or reliability reasons. Such changes will not alter the specifications or the performance of the product. Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for military applications. Silicon Labs products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons. Silicon Labs disclaims all express and implied warranties and shall not be responsible or liable for any injuries or damages related to use of a Silicon Labs product in such unauthorized applications.

Trademark Information

Silicon Laboratories Inc., Silicon Laboratories®, Silicon Labs®, SiLabs® and the Silicon Labs logo®, Bluegiga®, Bluegiga Logo®, EFM®, EFM32®, EFR, Ember®, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Redpine Signals®, WiSeConnect, n-Link, EZLink®, EZRadio®, EZRadioPRO®, Gecko®, Gecko OS, Gecko OS Studio, Precision32®, Simplicity Studio®, Telegesis, the Telegesis Logo®, USBXpress®, Zentri, the Zentri logo and Zentri DMS, Z-Wave®, and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc.
400 West Cesar Chavez
Austin, TX 78701
USA

www.silabs.com