



# Platform 5.1.0 GA

## Simplicity SDK Suite 2024.12.0

### December 16, 2024

The Platform provides infrastructure support for applications developed with higher-level protocols, and it provides an interface with the underlying hardware. It is composed of the following modules:

- **CMSIS Device** is a vendor-independent hardware abstraction layer for the Cortex®-M processor series.
- **Peripherals** provides a complete peripheral API for all Silicon Labs EFM32, EZR32 and EFR32 MCUs and SoCs.
- **Drivers** is the Gecko Platform driver library for EFM32 and EFR32 on-chip peripherals. Drivers are typically DMA-based and use all available low-energy features.
- **Services** includes common services such as NVM3 and Power Manager.
- **CPC (Co-Processor Communication)** provides a library to communicate between two processors using a serial link. CPC is used by the NCP & RCP solutions.
- **Common** components are used throughout the SDKs.
- **Middleware** includes the Capacitive Sensing Firmware Library and the GLIB graphics library.
- **Security** includes mbed TLS and other security services.
- **Operating System** includes Micrium OS Kernel as well as other things related to Operating Systems such as a CMSIS-RTOS2 layer.
- The **Gecko Bootloader** is a code library configurable through Simplicity Studio's IDE to generate bootloaders that can be used with a variety of Silicon Labs protocol stacks. The Gecko Bootloader can be used with EFM32 and EFR32 Series 2 and later devices.
- **MVP Math Library** includes *Real* and *Complex* Matrix and Vector operations using the Matrix Vector Processor available on EFR32xG24. The library is an alternative to CMSIS-DSP for Matrix and Vector math operations.
- **Examples** are example applications illustrating platform functionality.
- **Boards and External Devices** cover supported hardware.
- **Other Gecko Platform Components** regroups changes to documentation, project building and configuration, as well as any other aspects related to Gecko Platform.
- **RAIL (Radio Abstraction Interface Layer)** provides a customizable radio interface layer that supports proprietary or standards-based wireless protocols. RAIL use by application protocols such as Silicon Labs Zigbee or Silicon Labs Connect is managed through the stack library. Direct RAIL use is exposed through the Flex SDK.

These release notes cover SDK version(s):

Platform 5.1.0 released December 16, 2024



#### KEY FEATURES

##### CMSIS Device

- Added support for new EFR32xG27 OPN, EFR32xG26 OPN's, Module OPN's(MGM260PB22VNA2,MGM260PB32VNA2,MGM260PB32VNN2)

##### CPC

- Experimental support of NETLINK-SDIO interface on the SiWx917m platform

##### Security

- Mbed TLS upgraded to latest version 3.6.2

##### Boards and External Devices

- Added support for board OPN's BRD2709A, BRD2711A, BRD4350A, BRD4351A, BRD4412A, BRD4413A.

##### RAIL 5.1.0

- Added support for Bluetooth Low Energy (BLE) Channel Sounding (CS) on the EFR32xG24.  
This feature enables accurate distance measurement between two devices when used with the Silicon Labs BLE stack and distance measurement libraries.
- Added support for Concurrent listening feature on the EFR32xG26 part.
- Added support for 1 Mbps and 2 Mbps custom 802.15.4 SUN PHYs on the EFR32xG26 part.

**Contents**

1 New Items ..... 3

2 CMSIS Device ..... 4

3 Peripherals ..... 6

4 Drivers ..... 8

5 Services ..... 9

6 CPC ..... 11

7 Common ..... 12

8 Middleware ..... 13

9 Security ..... 14

10 Operating System ..... 16

11 Gecko Bootloader ..... 17

12 MVP Math Library ..... 18

13 Examples ..... 19

14 Boards and External Devices ..... 20

15 Other Gecko Platform Software Components ..... 21

16 RAIL Library ..... 22

## 1 New Items

None.

## 2 CMSIS Device

### 2.1 New Items

#### Added in release 5.1.0

- Added the following: EFR32xG27 OPN: EFR32BG27C320F768IJ39
- Added support for the following module OPN's:  
MGM260PB22VNA2  
MGM260PB32VNA2  
MGM260PB32VNN2
- Added the following EFR32xG26 OPNs:

EFR32MG26B211F3200IM48, EFR32MG26B221F3200IM48, EFR32MG26B211F2048IM68, EFR32MG26B221F2048IM68, EFM32PG26B301F2048IM68, EFM32PG26B101F512IM68, EFM32PG26B301F1024IM68, EFR32MG26B311F3200IL136, EFM32PG26B301F2048IL136, EFM32PG26B101F512IL136, EFM32PG26B301F1024IL136, EFR32BG26B311F2048IM48, EFR32BG26B321F2048IM48, EFR32BG26B311F2048IM68, EFR32BG26B321F2048IM68, EFR32BG26B311F2048IL136, EFR32BG26B311F1024IM68, EFR32BG26B321F1024IM68, EFR32BG26B311F1024IL136, EFR32MG26B411F3200IM48, EFR32MG26B421F3200IM48, EFR32MG26B511F3200IM48, EFR32MG26B521F3200IM48, EFR32MG26B411F3200IM68, EFR32MG26B421F3200IM68, EFR32MG26B511F3200IM68, EFR32MG26B521F3200IM68, EFR32MG26B511F3200IL136, EFR32BG26B511F3200IM48, EFR32BG26B511F3200IM68, EFR32BG26B511F3200IL136, EFM32PG26B501F3200IM68, EFM32PG26B501F3200IL136, EFM32PG26B501F3200IM48, EFM32PG26B500F3200IM48, EFR32BG26B411F3200IM48, EFR32BG26B421F3200IM48, EFR32BG26B410F3200IM48, EFR32BG26B420F3200IM48

### 2.2 Improvements

#### Changed in release 5.1.0

None.

### 2.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1321003	Fixed missing HFRCO bus clock enable that could lead to bus faults in SystemHFRCODPLLCKGet() and SystemHFRCOEM23ClockGet().

### 2.4 Known Issues in the Current Release

None.

### 2.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

---

## 2.6 Removed Items

### Removed in release 5.1.0

GCC and IAR specific assembly startup files have been removed. The C startup file should be used instead.

## 3 Peripherals

### 3.1 New Items

#### Added in release 5.1.0

None.

### 3.2 Improvements

#### Changed in release 5.1.0

- em\_acmp: Added the ACMP\_OutputGet function to get ACMP output value.
- em\_ldma: Removed unnecessary assert in LDMA\_Init and LDMA\_StartTransfer.

### 3.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1307127	em_emu: Fixed a bug in EMU_RamPowerDown() function leading to not covering all RAM shutdown cases for series 2.
1333169	Fixed rare race-condition where DMADRV could return a transfer count of 0 instead of 1 when interrupts are masked and the channel IF is set.
1337998	em_ldma: On EFR32XG25 devices, the MATCHEN and MATCHVAL fields in the LDMA descriptors described in the em_ldma driver were inverted. This issue was fixed so that the structure properly represents the EFR32XG25 hardware.
1260083	em_prs: Added missing PRS asynchronous channels in header file for each channel in xG24 and xG26 family. Added missing channels definition in em_prs.h.
1344396	Added the following headers after they were accidentally removed from the SiSDK: peripheral_dcdc_coulomb_counter.h, peripheral_dcdc_coulomb_counter_compat.h, peripheral_etampdet.h, peripheral_etampdet_compat, peripheral_keyscan.h, peripheral_keyscan_compat.h, peripheral_sysrtc.h and peripheral_sysrtc_compat.h.
1357932	em_emu: Fixed default EM0/1 default peak current for EFR32xG27 Boost parts. The previous value was emuDcdcBoostEM01PeakCurrent_Load25mA. It has been corrected to emuDcdcBoostEM01PeakCurrent_Load23mA.
1286382	em_rmu: Fix compiler warnings for analyzer-null-dereference. em_bus: Fix compiler warnings for analyzer-shift-count-overflow.

### 3.4 Known Issues in the Current Release

None.

### 3.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

---

## 3.6 Removed Items

### Removed in release 5.1.0

- em\_dbg: Removed DBG\_DisableDebugAccess() as it was not available for Series 2 devices.

## 4 Drivers

### 4.1 New Items

#### Added in release 5.1.0

None.

### 4.2 Improvements

#### Changed in release 5.1.0

None.

### 4.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1361482	UARTDRV: Fixed a bug in UARTDRV_Abort() where the callback function was called passing a NULL pointer instead of a pointer to the data buffer.
1284781	UARTDRV: Fixed issues in UARTDRV_Abort() leading to incorrect number of EM1 requirements. Fixed handling of enableRxWhensleeping.
1332867	DMADRV: Fixed a rare issue where DMADRV_TransferRemainingCount could return 0 when the DMA had a single byte to transfer. This happened on systems with high IRQ latency, or that called the API in an atomic/critical section.
1290690	Spidrv: Fixed issue of wrong order of operations for Series 2 devices, which leads to incorrect pin configuration initialization, by enabling routing after configuring pins in SPIDRV_Init function.
1321680	Spidrv: Fixed issue of SPIDRV instantiation using USART on EFR32XG25 despite the absence of USART on these platforms.
1173169	NVM3 optimization for cache search is added, which can be enabled using configuration NVM3_OPTIMIZATION.

### 4.4 Known Issues in the Current Release

None.

### 4.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 4.6 Removed Items

#### Removed in release 5.1.0

None.



## 5 Services

### 5.1 New Items

#### Added in release 5.1.0

- Clock Manager: Added an AUTO option to enable the HFXO and to use it as the default high frequency clock when radio is used (i.e. when RAIL library is present in the project).
- Clock Manager: Added support for CLKIN0 to the Clock Manager. The CLKIN0 was added to the SYSCLK, DPLL, and EM01GRPCLK clock branch as a reference option in the `sl_clock_manager_tree_config.h` and `sl_clock_manager_oscillator_config.h` configuration file. A `SL_CLOCK_MANAGER_CLKIN0_FREQ` configuration and a pintool annotation were added to configure a GPIO to receive an external clock and use it for the above references.

### 5.2 Improvements

#### Changed in release 5.1.0

- Sleptimer: Changed type of `overflow_counter` variable to prevent the variable from overflowing when the peripheral used by sleptimer is clocked out of a high frequency clock.
- Clock Manager: The default value of `SL_CLOCK_MANAGER_PCLK_DIVIDER` is now 1 on Series 2 devices to align with the default value that was present in `device_init`.

### 5.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1308159	Memory manager: Fix bug in <code>realloc</code> algorithm making sure metadata of free blocks is updated correctly. This will avoid running out of memory when using <code>realloc()</code> when it is actually still available. It also fixes issues related to the usage of reservations, as heap can be corrupted when using reservations. The fix makes sure reservation offsets are considered in <code>alloc</code> and <code>free</code> , <code>realloc</code> , <code>reserve</code> and <code>release</code> blocks.
1181978	Memory Manager: Fixed an issue where <code>SLI_BLOCK_LEN_BYTE_TO_DWORD()</code> would sometimes return the wrong number of words. Allocations made with an alignment that is not multiples of 4 could, in a rare scenario, overlap each other.
1346413	Memory Manager: Fixed heap corruption in <code>sl_memory_realloc()</code> when reducing an allocated block.
1354963	Memory manager: Fixed issue related to statistic feature. The heap high watermark was overflowing. The fix makes sure the heap high watermark is always accurate.
1323169	Memory Manager: Added a missing closure of critical section within the function <code>sl_memory_free()</code> in an early exit path. An issue could arise if <code>sl_memory_free()</code> is called twice with the same block leading to an infinite atomic section.
1324463	<code>sl_mpu</code> : Fixed a bug where the first bytes of the <code>.data</code> section would still be marked as executable after calling <code>sl_mpu_disable_execute_from_ram()</code> . The fix consists in properly aligning the end of the <code>ramfunc</code> section (it must be 32 bytes aligned in case the MPU is used).
1251562	HFXO Manager: Fixed a corner case where the HFXO startup time measurement could be started with a wrong start measurement leading to a bad value. In a previous version of the SiSDK, the bad start-up values were discarded but the assertion in <code>sl_hfxo_manager.c</code> - Line 199 would fail. This correction fixes the root cause of this issue.
1305241	Fixed the FreeRTOS Power Manager/Sleptimer integration code where the number of elapsed OS ticks during sleep was not evaluated properly, leading to the unnecessary creation of sleptimers with very small timeout values.
1336345	Power manager: Fixed an issue where removing a requirement that was not added previously would lead to an assertion failure.
1336702	Power Manager: Fixed an issue where interrupts could be delayed until the next interrupt cycle due to a missing ISB instruction in the critical section of the power manager.

1290210	Power manager: Fixed issue of sl_power_manager_init not enabling GPIO bus clock. The GPIO bus clock may not be initialized if the project doesn't have a component that initializes it. Added sl_clock_manager_enable_bus_clock(SL_BUS_CLOCK_GPIO) function in sl_power_manager_init() to initialize the GPIO bus clock.
1289318	Sleep Timer: Defined module name for the Power Manager debug feature to correctly display the requirement set by the sleep timer.
1336478	Sleep Timer: Fixed an issue where the callback would be incorrectly called when the callback execution time exceeded the period of a periodic timer.
1356508	Clock Manager: Fixed issue where invalid LFXO and HFXO CTune MFG tokens caused clock_manager_init to attempt to initialize the LFXO and HFXO improperly on Series 2.
1351026	Clock Manager: Fixed an issue leading to an unused variable warning related to rfpll configuration.
1356859	Clock Manager: Added missing VDAC1 clock initialization for EFR32xG24 and EFR32xG26 devices.
1312889	Clock Manager: Fixed a reference to cmuClock_LCDCLK undeclared for the EFR32SG23B020F512IM40 device leading to a compilation error.
1272260	Updated documentation to make it easier for the customers to update the iostream handles for CLI.

## 5.4 Known Issues in the Current Release

None.

## 5.5 Deprecated Items

### Deprecated in release 5.1.0

- The sl\_ram\_interrupt\_vector\_init component is deprecated. Interrupt Manager should be used instead.

## 5.6 Removed Items

### Removed in release 5.1.0

None.

## 6 CPC

### 6.1 New Items

#### Added in release 4.6.0

- Introduced experimental support for NETLINK-SDIO on the SiWx917m platform.

### 6.2 Improvements

#### Changed in release 4.6.0

- Increased the maximum supported SPI USART bitrate, allowing the Host to configure higher data transfer speeds for improved performance.
- Addressed a few minor static code analysis issues.
- Enhanced CPCd error handling for improved management of invalid packets received.
- Refined the error messages printed by CPCd for improved clarity.

### 6.3 Fixed Issues

#### Fixed in release 4.6.0

ID #	Description
1378389	Resolved an issue in CPC Journal where the ID and timestamp were displayed incorrectly, ensuring accurate data representation.
1355407	Fixed an issue where some Linux SPI drivers would skip over a transfer of 0 bytes. This caused CPCd and secondary to lose synchronization and cause a "The IRQ it stuck abnormally long in the de-asserted state."
1319502	Resolved an issue with the CPCd binary included in the OpenWRT asset.
1307636	Fixed a rare race condition in the SPI driver on systems with high interrupt latency which could lead to CPC system losing communication with the host.

### 6.4 Known Issues in the Current Release

- The sample app `CPC Secondary on Micrium OS` generates warnings at link time when LTO (Link Time Optimization) is enabled.
- CPCd NETLINK-SDIO is stable on Linux kernel v4.x but may experience stability issues on Linux kernel v6.x.

### 6.5 Deprecated Items

#### Deprecated in release 4.6.0

None.

### 6.6 Removed Items

#### Removed in release 5.1.0

None.

## 7 Common

### 7.1 New Items

#### Added in release 5.1.0

- Event System: Added features to unregister and free a publisher context.
- Event System: Added a feature to unsubscribe from events from a given event class.
- Event System: New `sl_event` API '`sl_event_queue_delete()`', that accepts an event queue as a parameter, safely deletes the queue. In the process of deleting the event queue, all events that the queue was subscribed to will be unsubscribed from.
- Event System: Added a feature (`sl_event_publish_static`) which allows a publisher to publish events using a pre-allocated event structure.

### 7.2 Improvements

#### Changed in release 5.1.0

- Event System: Improved error handling when pushing events onto subscriber queues. Publishing an event to a subscriber queue should not be considered an error from the point of view of the publisher.

### 7.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1379854	Event System: Added a missing <code>memory_manager</code> dependency to the <code>slcc</code> component which could lead to compilation errors under certain circumstances.
1351448	The GNU linker template was modified to move the <code>.noinit</code> section after the <code>.bss</code> in order to fix the problem where the bootloader's <code>.bss</code> section overlaps with the <code>.noinit</code> section of the application, and initializes those variables to zero when they should not be initialized at all.

### 7.4 Known Issues in the Current Release

None.

### 7.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 7.6 Removed Items

#### Removed in release 5.1.0

None.

---

## 8 Middleware

### 8.1 New Items

#### Added in release 5.1.0

None.

### 8.2 Improvements

#### Changed in release 5.1.0

None.

### 8.3 Fixed Issues

#### Fixed in release 5.1.0

None.

### 8.4 Known Issues in the Current Release

None.

### 8.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 8.6 Removed Items

#### Removed in release 5.1.0

None.

## 9 Security

### 9.1 New Items

#### Added in release 5.1.0

- Upgrade to Mbed TLS version 3.6.2 (latest).
  - Mbed TLS 3.6 is a long-term support (LTS) branch. It will be supported with bug-fixes and security fixes until at least March 2027.
  - Release Notes can be found at: <https://github.com/Mbed-TLS/mbedtls/releases>.
- Add SLC component to support Deterministic ECDSA using the PSA Crypto API.
  - User documentation can be found at: <https://arm-software.github.io/psa-api/crypto/1.1/api/ops/sign.html>.

### 9.2 Improvements

#### Changed in release 5.1.0

- Upgraded the Legacy Deterministic ECDSA component using the legacy Mbed TLS API to production quality. Users are recommended to use the corresponding PSA Crypto component for Deterministic ECDSA, since the legacy crypto APIs of Mbed TLS will be obsoleted in Mbed TLS 4.0, which is planned to be released in 2025 by Trusted-Firmware.org.
- Added call to SE Manager initialisation function `sl_se_init` in `sl_system_init`. This means applications that calls `sl_system_init` during initialization will not need to call `sl_se_init` explicitly. The `sl_system_init` is recommended to be included in the application configuration.
- Added support for calling SE Manager APIs from critical sections. In general, it is recommended to avoid calling the SE Manager from critical sections.

### 9.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1363898	Fixed the Mbed TLS ALT plugin for the API function called <code>mbedtls_ecdsa_verify</code> , which allowed signature components ( <code>r</code> and <code>s</code> ) to be negative. All SDK versions are affected. All xG2x device families are affected.
1361396	Fixed a build error in function <code>sli_cryptoacc_driver_single_shot_pbkdf2</code> , which is called by the PSA Crypto API function, <code>sl_psa_key_derivation_single_shot</code> , on VSE devices when the user selects algorithm <code>PSA_ALG_PBKDF2_AES_CMAC_PRF_128</code> . Affected device is xG27. Affected SDK versions are 4.4.x (23Q4) and <code>sisdk-2024.6.x</code> .
1354904	Fixed bug in PSA AEAD drivers which did not check output buffer size before processing context saved data. This may cause buffer overflow. Both HSE and VSE PSA AEAD drivers are affected, meaning all EFR32xG2x devices are affected. Affected SDK versions are 4.0.0 (21Q4) and later.
1378069	Fixed bug in PSA AEAD driver for VSE devices, where the function <code>sli_cryptoacc_transparent_aead_update</code> (called by API function <code>psa_aead_update</code> ) did not release a mutex (used to apply mutual exclusion of CRYPTOACC hardware) before returning when the algorithm is not supported, and the algorithm is CCM and there is 16 bytes in the last AES block. This will cause all PSA VSE drivers to fail in the next calls to any PSA Crypto APIs that need to access the CRYPTOACC accelerator hardware). Affected devices are xG22 and xG27. Affected SDK versions are 4.0.0 (21Q4) and later.

---

## 9.4 Known Issues in the Current Release

None.

## 9.5 Deprecated Items

### Deprecated in release 5.1.0

All APIs in `em_se.h` have been deprecated and will be removed in a future release. The functionality has been ported as an internal API under the SE Manager component. All usage of `emlib SE` should be replaced by calls to the public SE Manager API.

## 9.6 Removed Items

### Removed in release 5.1.0

None.

## 10 Operating System

### 10.1 New Items

#### Added in release 5.1.0

None.

### 10.2 Improvements

#### Changed in release 5.1.0

None.

### 10.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1108940	Fixed a bug in the Micrium CMSIS RTOS 2 layer where a memory leak would happen when a task would call osThreadTerminate on self.

### 10.4 Known Issues in the Current Release

ID #	Description	Workaround
1166857	OSTaskQPost doesn't send a message to current task when called with a null pointer as argument.	N/A

### 10.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 10.6 Removed Items

#### Removed in release 5.1.0

None.



---

## 11 Gecko Bootloader

### 11.1 New Items

#### Added in release 5.1.0

None.

### 11.2 Improvements

#### Changed in release 5.1.0

None.

### 11.3 Fixed Issues

#### Fixed in release 5.1.0

None.

### 11.4 Known Issues in the Current Release

None.

### 11.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 11.6 Removed Items

#### Removed in release 5.1.0

None.

---

## 12 MVP Math Library

### 12.1 New Items

#### Added in release 5.1.0

None.

### 12.2 Improvements

#### Changed in release 5.1.0

None.

### 12.3 Fixed Issues

#### Fixed in release 5.1.0

None.

### 12.4 Known Issues in the Current Release

None.

### 12.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 12.6 Removed Items

#### Removed in release 5.1.0

None.

## 13 Examples

### 13.1 New Items

#### Added in release 5.1.0

None.

### 13.2 Improvements

#### Changed in release 5.1.0

None.

### 13.3 Fixed Issues

#### Fixed in release 5.1.0

None.

### 13.4 Known Issues in the Current Release

Issues in bold were added since the previous release. If you have missed a release, recent release notes are available on <https://www.silabs.com/products/software>.

ID #	Description	Workaround
664803	Se_manager and psa_crypto sample apps do not work correctly in Simplicity Studio 5's launch console.	In the launch console, change the line terminator selection to None.

### 13.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 13.6 Removed Items

#### Removed in release 5.1.0

None.

## 14 Boards and External Devices

### 14.1 New Items

#### Added in release 5.1.0

Added support for the following new drivers

- ICM40627- IMU sensor
- SHT4X sensor- Humidity and Temperature sensor

#### Added support for the following new OPNs:

- [BRD2709A](#)
- [BRD2711A](#)
- [BRD4350A](#)
- [BRD4351A](#)
- [BRD4412A](#)
- [BRD4413A](#)

### 14.2 Improvements

#### Changed in release 5.1.0

None.

### 14.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1320271	Microphone: Added EM1 requirement when initializing the microphones to prevent chip from entering Low Energy modes (EM2 through EM4).

### 14.4 Known Issues in the Current Release

None.

### 14.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 14.6 Removed Items

#### Removed in release 5.1.0

None.

## 15 Other Gecko Platform Software Components

### 15.1 New Items

#### Added in release 5.1.0

None.

### 15.2 Improvements

#### Changed in release 5.1.0

None.

### 15.3 Fixed Issues

#### Fixed in release 5.1.0

None.

### 15.4 Known Issues in the Current Release

Issues in bold were added since the previous release. If you have missed a release, recent release notes are available on <https://www.silabs.com/products/software>.

ID #	Description	Workaround
	An issue is detected when updating the GCC toolchain from version 10.3 to 12.2, which increases the RAM usage by about 400 bytes in some cases when using stdio.	--

### 15.5 Deprecated Items

#### Deprecated in release 5.1.0

None.

### 15.6 Removed Items

#### Removed in release 5.1.0

None.

## 16 RAIL Library

### 16.1 New Items

#### Added in release 5.1.0

- Added RAIL\_GetRxIncomingPacketRssi to get the RSSI associated with the incoming packet.
- Added support for "RAIL Utility, CS Antenna Offset" component for BLE Channel Sounding feature on the EFR32xG24 that allows customer to configure offsets for a wired or wireless antenna configuration.
- Added support for TrustZone APIs on the EFR32xG23 and EFR32xG28 parts to allow RAIL to access the CMU, EMU, GPIO, LDMA, HFXO, PRS and SYSRTC peripherals when they are running in the secure state despite the RAIL library being non-secure.

### 16.2 Improvements

#### Changed in release 5.1.0

- To prepare for RAIL 3.0 specifications, RAIL\_Status\_t is now sl\_status\_t and RAIL\_STATUS\_ values are mapped to similar SL\_STATUS\_ values.

### 16.3 Fixed Issues

#### Fixed in release 5.1.0

ID #	Description
1120643	Fixed an issue where the phy was not re-configured correctly when using the RAIL_ConfigSyncWords API with certain custom modem configurations.
1273595	To better reflect Z-Wave spec naming conventions, renamed RAIL_ZWAVE_REGION_US_LR_END_DEVICE to RAIL_ZWAVE_REGION_US_LR3, RAIL_ZWAVE_REGION_EU_LR_END_DEVICE to RAIL_ZWAVE_REGION_EU_LR3, RAIL_ZWAVE_REGIONID_US_LR_END_DEVICE to RAIL_ZWAVE_REGIONID_US_LR3, and RAIL_ZWAVE_REGIONID_EU_LR_END_DEVICE to RAIL_ZWAVE_REGIONID_EU_LR3.
1290731	Fixed a multiprotocol issue where RAIL_BLE_SetNextTxRepeat() or RAIL_SetNextTxRepeat() information mistakenly survived across RAIL_Idle() to the surprise of a subsequent non-repeated transmit.
1300509	Fixed an issue with IEEE 802.15.4 High Data Rate (HDR) packets such that PTI now properly indicates they have a 2-byte 802.15.4 PHY header on the EFR32xG26 part.
1306804	Fixed an issue where glitches could occur when using RAIL_RxDataSource_t values other than RX_PACKET_DATA on the EFR32xG23 and newer chips.
1309139	Fixed an issue on the EFR32xG22 and later where RAIL_StopTx() being called before the transmit has started could cause the radio to return to receive with the radio partially misconfigured for transmit.
1309208	Fixed a minor issue on the EFR32xG21 where the TX-to-RX turnaround timing could be a bit longer than specified.
1321076	Fixed an issue with setDebugSignal railtest command that broke DOUT and DCLK signals.
1352393	Fixed an issue on ZGM230S modules where PHY signatures were computed incorrectly, and the device would assert on startup.
1357948	Fixed a DMP issue where the device would incorrectly switch to a background receive task with insufficient time to switch back to an upcoming high priority scheduled task.
1369901	Fixed an issue where the device would become stuck when running image rejection calibration on an OFDM PHY from the event callback on the EFR32xG25 part.

## 16.4 Known Issues in the Current Release

Issues in bold were added since the previous release.

ID #	Description	Workaround
	Using direct mode (or IQ) functionality on EFR32xG23 requires a specifically set radio configuration that is not yet supported by the radio configurator. For these requirements, reach out to technical support who could provide that configuration based on your specification	
641705	Infinite receive operations where the frame's fixed length is set to 0 are not working correctly on the EFR32xG23 series chips.	
732659	On EFR32xG23: Wi-SUN FSK mode 1a exhibits a PER floor with frequency offsets around $\pm 8$ to 10 KHz Wi-SUN FSK mode 1b exhibits a PER floor with frequency offsets around $\pm 18$ to 20 KHz	

## 16.5 Deprecated Items

### Deprecated in release 5.1.0

- The RAIL 2.x API is planned for deprecation in the 25Q2-GA release (June 2025). At that time, the new RAIL 3.0 API will be released for all supported chips along with a RAIL 2.x compatibility layer and migration guide.
  - The goal of this new API is to get rid of some unused features, add better support for concurrent listening use cases, and to simplify channel and PA configurations.
  - The migration is intended to be straight forward and simple for the majority of customers. However, in some cases manual help might be required to ease this transition.

## 16.6 Removed Items

### Removed in release 5.1.0

None.

# Simplicity Studio

One-click access to MCU and wireless tools, documentation, software, source code libraries & more. Available for Windows, Mac and Linux!



**IoT Portfolio**  
[www.silabs.com/IoT](http://www.silabs.com/IoT)



**SW/HW**  
[www.silabs.com/simplicity](http://www.silabs.com/simplicity)



**Quality**  
[www.silabs.com/quality](http://www.silabs.com/quality)



**Support & Community**  
[www.silabs.com/community](http://www.silabs.com/community)

## Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs may update product firmware during the manufacturing process for security or reliability reasons. Such changes will not alter the specifications or the performance of the product. Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for military applications. Silicon Labs products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons. Silicon Labs disclaims all express and implied warranties and shall not be responsible or liable for any injuries or damages related to use of a Silicon Labs product in such unauthorized applications.

## Trademark Information

Silicon Laboratories Inc.<sup>®</sup>, Silicon Laboratories<sup>®</sup>, Silicon Labs<sup>®</sup>, SiLabs<sup>®</sup> and the Silicon Labs logo<sup>®</sup>, Bluegiga<sup>®</sup>, Bluegiga Logo<sup>®</sup>, EFM<sup>®</sup>, EFM32<sup>®</sup>, EFR, Ember<sup>®</sup>, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Redpine Signals<sup>®</sup>, WiSeConnect<sup>®</sup>, n-Link, EZLink<sup>®</sup>, EZRadio<sup>®</sup>, EZRadioPRO<sup>®</sup>, Gecko<sup>®</sup>, Gecko OS, Gecko OS Studio, Precision32<sup>®</sup>, Simplicity Studio<sup>®</sup>, Telegesis, the Telegesis Logo<sup>®</sup>, USBXpress<sup>®</sup>, Zentri, the Zentri logo and Zentri DMS, Z-Wave<sup>®</sup>, and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc.  
400 West Cesar Chavez  
Austin, TX 78701  
USA

[www.silabs.com](http://www.silabs.com)